

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999166

Luminaire Tested: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999166
REPORT IS A COMBINATION OF REPORTS P984915 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-D_4000K
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6269.0 lumens
Efficiency: N/A
Efficacy: 92.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999166

CATALOG NUMBER: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P999166

CATALOG NUMBER: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55
1	96	91	87	83	88	84	80	77	70	68	65	58	56	54	46	45	44
2	87	79	72	66	80	73	67	62	61	56	53	50	47	44	40	38	36
3	79	69	61	55	72	63	56	51	53	48	44	44	40	36	35	32	30
4	72	60	52	46	66	56	48	43	47	41	37	39	34	31	31	28	25
5	66	54	45	39	60	50	42	36	42	36	31	35	30	26	28	24	22
6	61	48	40	33	55	44	37	31	37	32	27	31	26	23	25	22	19
7	56	43	35	29	51	40	33	27	34	28	24	28	24	20	23	19	17
8	52	39	31	26	47	36	29	24	31	25	21	26	21	18	21	17	15
9	48	36	28	23	44	33	26	21	28	23	19	24	19	16	19	16	13
10	45	33	25	20	41	30	24	19	26	20	17	22	17	14	18	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14326	14326	14326
5°	14390	13714	13636
10°	14294	13239	13046
15°	14091	12747	12439
20°	13837	12231	11864
25°	13585	11737	11343
30°	13234	11236	10827
35°	12878	10751	10447
40°	12502	10333	10070
45°	12145	9953	9742
50°	11761	9603	9417
55°	11357	9232	9087
60°	10863	8845	8741
65°	10352	8400	8341
70°	9770	7922	7911
75°	9023	7444	7505
80°	7856	6946	7087
85°	6667	6480	6723

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12145 cd/sqm

TEST NUMBER: P999166

CATALOG NUMBER: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.8	1.4
10°-20°	246.0	3.9
20°-30°	372.8	5.9
30°-40°	454.0	7.2
40°-50°	488.4	7.8
50°-60°	474.4	7.6
60°-70°	414.3	6.6
70°-80°	318.8	5.1
80°-90°	215.2	3.4
90°-100°	179.0	2.9
100°-110°	225.6	3.6
110°-120°	384.0	6.1
120°-130°	558.6	8.9
130°-140°	568.0	9.1
140°-150°	515.2	8.2
150°-160°	412.0	6.6
160°-170°	265.5	4.2
170°-180°	91.4	1.5
0°-30°	704.6	11.2
0°-40°	1158.6	18.5
0°-60°	2121.4	33.8
0°-90°	3069.7	49.0
90°-120°	788.6	12.6
90°-150°	2430.4	38.8
90°-180°	3199.0	51.0
0°-180°	6269.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	905	905	905	905	905	
5°	908	904	896	904	902	86
15°	866	868	868	880	879	244
25°	787	796	808	824	828	362
35°	678	700	725	754	763	424
45°	556	592	637	678	691	429
55°	426	474	542	589	606	381
65°	291	355	433	487	504	289
75°	161	235	319	375	392	171
85°	47	128	212	268	286	50
90°	14	98	187	243	260	12
95°	56	94	178	231	246	62
105°	218	277	155	209	226	233
115°	405	431	507	225	190	398
125°	567	576	632	672	686	506
135°	700	711	731	765	774	541
145°	811	810	822	834	838	507
155°	893	886	895	899	893	411
165°	940	936	938	943	938	266
175°	962	957	959	963	956	92
180°	960	960	960	960	960	

TEST NUMBER: P999166

CATALOG NUMBER: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	905.0	905.0	905.0	905.0	905.0
2.5°	911.5	907.6	898.4	905.0	902.3
5°	907.6	903.6	895.8	903.6	902.3
7.5°	901.0	898.4	891.8	901.0	899.7
10°	893.2	890.5	886.6	897.1	895.8
12.5°	880.0	881.3	878.7	889.2	887.9
15°	865.6	868.2	868.2	880.0	878.7
17.5°	847.2	852.5	856.4	868.2	868.2
20°	828.9	835.4	840.7	855.1	855.1
22.5°	809.2	817.1	825.0	839.4	842.0
25°	786.9	796.1	807.9	823.6	827.6
27.5°	760.7	775.1	788.2	807.9	810.5
30°	734.5	751.5	768.6	789.5	793.5
32.5°	705.6	725.3	746.3	771.2	779.1
35°	678.1	700.4	725.3	754.1	763.3
37.5°	647.9	672.8	704.3	735.8	745.0
40°	617.7	646.6	682.0	716.1	727.9
42.5°	588.9	617.7	659.7	697.7	709.5
45°	556.1	591.5	637.4	678.1	691.2
47.5°	524.6	562.6	615.1	657.1	671.5
50°	491.8	532.5	591.5	636.1	650.5
52.5°	460.3	503.6	566.6	612.5	628.2
55°	426.2	473.5	541.7	588.9	605.9
57.5°	393.5	445.9	514.1	565.3	582.3
60°	358.0	414.4	489.2	539.0	557.4
62.5°	326.6	385.6	460.3	514.1	531.2
65°	291.2	355.4	432.8	486.6	503.6
67.5°	259.7	326.6	405.3	459.0	477.4
70°	225.6	293.8	375.1	431.5	447.2
72.5°	194.1	264.9	347.6	402.6	422.3
75°	161.3	234.8	318.7	375.1	392.1
77.5°	129.8	205.9	291.2	347.6	365.9
80°	98.4	178.4	263.6	318.7	337.1
82.5°	72.1	150.8	237.4	292.5	309.5
85°	47.2	128.5	212.5	267.6	285.9
87.5°	28.9	107.5	191.5	245.3	262.3
90°	13.8	97.5	187.0	243.0	260.1
92.5°	29.2	95.9	178.0	230.6	247.0
95°	55.7	94.3	177.9	231.3	246.3
97.5°	90.5	89.9	177.0	227.7	244.1
100°	132.1	85.5	170.8	224.9	240.6
102.5°	176.7	218.5	163.0	217.8	234.3
105°	217.8	276.6	155.2	208.7	225.9
107.5°	267.1	315.9	147.4	199.6	216.8
110°	312.9	353.8	217.3	189.8	207.0

TEST NUMBER: P999166

CATALOG NUMBER: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	357.4	390.9	439.5	182.0	198.6
115°	404.6	430.9	507.3	225.0	189.5
117.5°	444.3	468.7	535.6	475.7	306.8
120°	490.1	505.9	570.8	615.9	536.5
122.5°	529.0	541.5	603.9	643.5	656.0
125°	567.3	576.4	631.6	671.8	685.7
127.5°	603.5	611.9	657.7	697.4	709.9
130°	637.5	647.3	682.5	721.6	731.4
132.5°	672.2	680.0	707.3	743.6	753.4
135°	700.1	711.2	730.6	765.1	774.2
137.5°	730.7	739.0	752.5	784.4	791.5
140°	760.5	764.8	775.0	802.3	806.7
142.5°	785.5	789.1	798.1	819.4	822.5
145°	810.6	809.9	821.7	834.5	837.5
147.5°	833.6	831.5	843.3	848.1	849.2
150°	855.8	850.9	862.0	866.2	862.7
152.5°	874.5	869.0	879.4	883.6	878.7
155°	892.6	886.3	894.7	898.8	893.3
157.5°	907.2	901.6	907.9	912.7	907.2
160°	919.7	915.5	919.7	923.9	919.0
162.5°	930.8	926.6	930.1	935.0	928.7
165°	940.5	936.4	938.4	943.3	938.4
167.5°	948.2	944.0	946.1	950.9	944.7
170°	954.4	950.3	951.6	956.5	950.3
172.5°	958.6	954.4	955.8	960.7	954.4
175°	962.1	957.2	958.6	963.4	956.5
177.5°	963.4	958.6	959.3	964.1	957.9
180°	960.0	960.0	960.0	960.0	960.0

TEST NUMBER: P999166

CATALOG NUMBER: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-D_4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.36	15.26	15.32	16.24	17.52	17.44	18.34	18.39	19.32	20.60
	3H	15.83	16.64	16.79	17.63	18.93	20.03	20.84	20.99	21.83	23.13
	4H	16.30	17.08	17.28	18.07	19.38	21.28	22.06	22.26	23.05	24.36
	6H	16.59	17.31	17.58	18.30	19.63	22.58	23.30	23.57	24.30	25.62
	8H	16.65	17.33	17.64	18.35	19.67	23.24	23.93	24.24	24.94	26.26
	12H	16.67	17.32	17.67	18.33	19.67	23.97	24.62	24.97	25.63	26.98
4H	2H	15.42	16.19	16.40	17.18	18.49	17.77	18.55	18.76	19.54	20.85
	3H	17.13	17.78	18.12	18.80	20.13	20.57	21.22	21.56	22.24	23.57
	4H	17.75	18.36	18.75	19.37	20.72	21.98	22.59	22.99	23.60	24.95
	6H	18.17	18.70	19.18	19.73	21.07	23.45	23.98	24.47	25.02	26.36
	8H	18.28	18.77	19.29	19.80	21.16	24.21	24.71	25.23	25.74	27.10
	12H	18.32	18.77	19.36	19.82	21.18	25.04	25.49	26.08	26.54	27.90
8H	4H	18.54	19.04	19.56	20.07	21.43	22.13	22.63	23.14	23.65	25.01
	6H	19.18	19.60	20.22	20.66	22.02	23.76	24.18	24.80	25.25	26.60
	8H	19.40	19.77	20.45	20.83	22.20	24.65	25.02	25.70	26.08	27.45
	12H	19.54	19.86	20.59	20.92	22.33	25.65	25.98	26.70	27.03	28.44
12H	4H	18.74	19.20	19.78	20.24	21.60	22.11	22.56	23.14	23.60	24.97
	6H	19.51	19.88	20.56	20.94	22.31	23.79	24.16	24.83	25.21	26.59
	8H	19.82	20.15	20.87	21.20	22.61	24.72	25.05	25.77	26.10	27.51

END OF REPORT