

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931442

Luminaire Tested: DFN2DS-TR3F0-090DS950-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931442
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-090DS950-RLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7229.2 lumens
Efficiency: N/A
Efficacy: 72.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 99.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931442

CATALOG NUMBER: DFN2DS-TR3F0-090DS950-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931442

CATALOG NUMBER: DFN2DS-TR3F0-090DS950-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4380	4380	4380
5°	4397	4325	4349
10°	4363	4255	4218
15°	4313	4128	4010
20°	4244	3948	3750
25°	4173	3744	3499
30°	4074	3533	3176
35°	3978	3305	2894
40°	3881	3068	2567
45°	3767	2803	2270
50°	3651	2535	1980
55°	3531	2246	1700
60°	3393	1942	1411
65°	3236	1632	1285
70°	3048	1344	1182
75°	2817	1225	1104
80°	2487	1094	1005
85°	1953	864	864

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3767 cd/sqm

TEST NUMBER: P931442

CATALOG NUMBER: DFN2DS-TR3F0-090DS950-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	329.4	4.6
10°-20°	904.4	12.5
20°-30°	1269.7	17.6
30°-40°	1384.1	19.1
40°-50°	1272.1	17.6
50°-60°	999.0	13.8
60°-70°	650.3	9.0
70°-80°	334.7	4.6
80°-90°	85.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2503.5	34.6
0°-40°	3887.6	53.8
0°-60°	6158.8	85.2
0°-90°	7229.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7229.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3515	3515	3515	3515	3515	
5°	3515	3499	3458	3486	3477	333
15°	3343	3308	3200	3140	3108	942
25°	3035	2933	2723	2593	2545	1396
35°	2615	2453	2173	1972	1902	1637
45°	2138	1924	1591	1364	1288	1651
55°	1625	1377	1034	843	783	1452
65°	1098	840	554	446	436	1088
75°	585	362	254	232	229	619
85°	137	70	60	60	60	164
90°	0	0	0	0	0	

TEST NUMBER: P931442

CATALOG NUMBER: DFN2DS-TR3F0-090DS950-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3515.1	3515.1	3515.1	3515.1	3515.1
2.5°	3531.0	3515.1	3480.0	3512.1	3505.7
5°	3515.1	3499.2	3457.8	3486.4	3476.9
7.5°	3486.4	3467.5	3423.0	3435.5	3419.6
10°	3448.3	3426.0	3362.6	3352.8	3333.9
12.5°	3400.7	3372.0	3286.0	3267.1	3231.9
15°	3343.3	3308.3	3200.2	3139.8	3108.1
17.5°	3276.5	3225.6	3091.9	3022.0	2971.1
20°	3200.2	3136.5	2977.4	2898.1	2827.9
22.5°	3117.6	3044.3	2859.7	2751.7	2704.1
25°	3034.9	2932.9	2723.0	2592.7	2544.8
27.5°	2936.3	2827.9	2595.7	2446.2	2373.0
30°	2831.3	2710.2	2455.7	2293.7	2207.6
32.5°	2729.3	2582.9	2322.3	2131.4	2051.7
35°	2615.0	2452.7	2172.8	1972.4	1902.2
37.5°	2503.6	2328.5	2032.8	1813.1	1733.8
40°	2385.8	2195.1	1886.3	1660.6	1577.9
42.5°	2265.0	2061.5	1740.1	1504.6	1425.2
45°	2137.8	1924.5	1590.6	1364.5	1288.2
47.5°	2016.9	1791.2	1447.6	1221.4	1151.6
50°	1883.3	1657.4	1307.5	1087.8	1021.3
52.5°	1752.7	1514.1	1173.9	963.9	903.5
55°	1625.4	1377.3	1033.7	843.1	782.6
57.5°	1495.2	1240.7	909.9	731.7	680.8
60°	1361.5	1107.0	779.3	617.3	566.3
62.5°	1231.2	976.8	667.9	515.4	490.1
65°	1097.5	839.7	553.5	445.5	435.7
67.5°	970.3	712.4	445.5	391.1	381.7
70°	836.7	588.6	368.9	337.2	324.3
72.5°	709.4	473.8	308.4	283.1	276.8
75°	585.2	362.5	254.5	232.2	229.2
77.5°	461.3	257.5	200.4	187.7	181.3
80°	346.6	184.7	152.5	140.0	140.0
82.5°	241.6	124.2	105.0	98.6	98.6
85°	136.6	69.8	60.4	60.4	60.4
87.5°	50.9	25.3	25.3	22.3	22.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931442

CATALOG NUMBER: DFN2DS-TR3F0-090DS950-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.37	17.89	16.73	18.20	18.52	12.33	13.85	12.69	14.16	14.48
	3H	18.13	19.50	18.51	19.82	20.19	13.59	14.96	13.97	15.29	15.65
	4H	18.80	20.08	19.20	20.43	20.81	14.09	15.37	14.49	15.72	16.10
	6H	19.29	20.47	19.70	20.84	21.23	14.47	15.66	14.89	16.02	16.42
	8H	19.45	20.58	19.88	20.97	21.37	14.60	15.73	15.03	16.12	16.52
	12H	19.56	20.63	19.99	21.02	21.44	14.68	15.76	15.11	16.14	16.57
4H	2H	16.47	17.75	16.87	18.10	18.48	13.02	14.30	13.42	14.65	15.03
	3H	18.40	19.47	18.81	19.87	20.27	14.47	15.53	14.88	15.93	16.33
	4H	19.15	20.11	19.59	20.53	20.96	15.07	16.02	15.50	16.44	16.88
	6H	19.75	20.58	20.20	21.02	21.48	15.55	16.39	16.01	16.83	17.29
	8H	19.96	20.74	20.42	21.18	21.65	15.72	16.49	16.18	16.94	17.40
	12H	20.11	20.81	20.59	21.29	21.76	15.83	16.53	16.31	17.01	17.48
8H	4H	19.18	19.95	19.64	20.40	20.87	15.42	16.20	15.88	16.64	17.11
	6H	19.82	20.46	20.31	20.95	21.43	16.01	16.65	16.50	17.14	17.62
	8H	20.07	20.64	20.58	21.15	21.64	16.23	16.80	16.74	17.31	17.80
	12H	20.27	20.78	20.78	21.27	21.84	16.41	16.92	16.92	17.41	17.97
12H	4H	19.16	19.86	19.64	20.33	20.81	15.46	16.16	15.94	16.64	17.11
	6H	19.80	20.37	20.31	20.88	21.37	16.07	16.65	16.58	17.16	17.64
	8H	20.08	20.59	20.59	21.08	21.65	16.34	16.85	16.85	17.34	17.91

END OF REPORT