

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931465

Luminaire Tested: DFN2DS-TR4F0-050DS840-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931465
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-050DS840-FLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4955.0 lumens
Efficiency: N/A
Efficacy: 102.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 48.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931465

CATALOG NUMBER: DFN2DS-TR4F0-050DS840-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931465

CATALOG NUMBER: DFN2DS-TR4F0-050DS840-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1547	1547	1547
5°	1553	1531	1540
10°	1544	1515	1523
15°	1525	1495	1494
20°	1498	1466	1465
25°	1471	1430	1430
30°	1436	1397	1385
35°	1404	1357	1337
40°	1363	1317	1291
45°	1323	1277	1246
50°	1280	1236	1192
55°	1235	1188	1144
60°	1184	1131	1089
65°	1130	1074	1024
70°	1062	1005	957
75°	965	925	903
80°	857	831	788
85°	699	666	598

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1323 cd/sqm

TEST NUMBER: P931465

CATALOG NUMBER: DFN2DS-TR4F0-050DS840-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.3	3.7
10°-20°	515.7	10.4
20°-30°	757.9	15.3
30°-40°	880.3	17.8
40°-50°	879.2	17.7
50°-60°	766.6	15.5
60°-70°	566.7	11.4
70°-80°	320.6	6.5
80°-90°	84.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1456.9	29.4
0°-40°	2337.2	47.2
0°-60°	3983.0	80.4
0°-90°	4955.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4955.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1947	1947	1947	1947	1947	
5°	1947	1940	1919	1934	1931	185
15°	1854	1843	1818	1826	1816	522
25°	1678	1663	1631	1635	1631	772
35°	1448	1429	1399	1388	1378	904
45°	1178	1165	1137	1116	1109	909
55°	892	880	858	835	826	797
65°	601	590	571	554	545	594
75°	314	311	301	290	294	336
85°	77	75	73	67	66	90
90°	0	0	0	0	0	

TEST NUMBER: P931465

CATALOG NUMBER: DFN2DS-TR4F0-050DS840-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1947.4	1947.4	1947.4	1947.4	1947.4
2.5°	1958.8	1949.4	1928.8	1947.4	1943.9
5°	1947.4	1940.1	1919.4	1934.3	1930.8
7.5°	1934.3	1923.2	1902.6	1917.7	1913.9
10°	1913.9	1900.8	1878.4	1893.2	1887.7
12.5°	1885.7	1874.6	1852.2	1861.5	1857.7
15°	1853.9	1842.7	1818.3	1825.9	1816.5
17.5°	1814.5	1803.4	1779.0	1788.3	1779.0
20°	1771.5	1760.4	1734.1	1739.6	1732.3
22.5°	1728.5	1711.6	1687.2	1687.2	1683.4
25°	1677.9	1663.0	1631.1	1634.7	1631.1
27.5°	1621.6	1608.5	1584.3	1578.7	1569.4
30°	1565.6	1550.5	1522.5	1516.9	1509.4
32.5°	1505.6	1494.5	1464.5	1453.2	1445.6
35°	1447.5	1428.9	1398.9	1387.6	1378.3
37.5°	1382.0	1365.2	1335.1	1322.0	1312.7
40°	1314.7	1299.6	1269.6	1252.9	1245.3
42.5°	1249.1	1234.0	1204.2	1185.3	1174.2
45°	1178.0	1164.9	1136.6	1116.2	1108.6
47.5°	1108.6	1095.5	1065.6	1044.8	1033.7
50°	1035.5	1026.2	1000.0	973.8	964.4
52.5°	964.4	951.3	927.0	906.4	893.3
55°	891.5	880.2	857.7	835.2	825.9
57.5°	818.3	809.0	784.6	762.2	754.6
60°	745.2	737.9	711.7	691.0	685.5
62.5°	674.2	661.1	642.3	623.6	616.1
65°	601.2	589.9	571.2	554.4	544.9
67.5°	526.3	516.8	500.1	487.0	479.4
70°	457.0	449.4	432.5	419.4	412.1
72.5°	385.9	378.3	369.0	355.9	350.2
75°	314.5	310.9	301.4	290.3	294.1
77.5°	251.0	243.3	239.6	234.0	228.5
80°	187.4	185.4	181.6	176.1	172.3
82.5°	127.3	127.3	125.5	118.0	118.0
85°	76.7	74.9	73.1	67.4	65.6
87.5°	33.7	30.0	26.2	20.6	18.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931465

CATALOG NUMBER: DFN2DS-TR4F0-050DS840-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.80	14.41	13.16	14.72	15.04	12.35	13.97	12.72	14.28	14.59
	3H	14.55	16.00	14.93	16.33	16.69	14.06	15.51	14.44	15.84	16.20
	4H	15.20	16.56	15.59	16.91	17.29	14.70	16.07	15.10	16.42	16.79
	6H	15.66	16.93	16.08	17.30	17.69	15.16	16.43	15.57	16.80	17.19
	8H	15.81	17.02	16.23	17.41	17.81	15.30	16.52	15.73	16.90	17.30
	12H	15.90	17.06	16.33	17.44	17.87	15.39	16.55	15.82	16.93	17.36
4H	2H	13.36	14.73	13.76	15.08	15.45	13.01	14.38	13.41	14.72	15.10
	3H	15.33	16.48	15.74	16.88	17.28	14.93	16.07	15.34	16.47	16.87
	4H	16.11	17.15	16.54	17.56	18.00	15.69	16.72	16.12	17.14	17.57
	6H	16.71	17.61	17.16	18.05	18.51	16.28	17.18	16.73	17.62	18.08
	8H	16.90	17.74	17.36	18.19	18.65	16.46	17.31	16.92	17.75	18.21
	12H	17.03	17.79	17.51	18.26	18.73	16.58	17.34	17.06	17.81	18.28
8H	4H	16.38	17.23	16.84	17.67	18.14	16.01	16.86	16.47	17.30	17.76
	6H	17.10	17.80	17.59	18.29	18.77	16.72	17.42	17.21	17.91	18.38
	8H	17.36	17.99	17.87	18.49	18.98	16.97	17.60	17.48	18.10	18.59
	12H	17.56	18.12	18.06	18.61	19.17	17.14	17.70	17.65	18.19	18.75
12H	4H	16.41	17.17	16.89	17.65	18.12	16.05	16.81	16.53	17.28	17.75
	6H	17.14	17.78	17.65	18.28	18.77	16.78	17.41	17.29	17.91	18.40
	8H	17.46	18.02	17.96	18.51	19.07	17.08	17.64	17.59	18.13	18.69