

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999220

Luminaire Tested: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999220
REPORT IS A COMBINATION OF REPORTS P984969 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_3500K
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7483.0 lumens
Efficiency: N/A
Efficacy: 99.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999220

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P999220

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	98	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49
2	90	83	77	72	83	77	72	67	66	62	59	55	52	50	46	44	42
3	82	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32
5	70	58	50	45	64	54	47	42	47	41	37	40	36	33	33	30	28
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	23	20
9	52	40	32	27	48	37	31	26	33	27	23	28	24	21	24	21	18
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	27277	27277	27277	27277
5°	27344	29085	27448	23140
10°	27026	31750	27195	19078
15°	26370	33490	26736	16069
20°	25958	31444	25958	13968
25°	25132	27013	25246	12490
30°	23771	21235	24223	11314
35°	22564	14684	22942	10351
40°	21178	11087	21419	9583
45°	19468	9111	19787	8756
50°	17990	7996	18024	8016
55°	16305	6814	16411	7211
60°	14511	5691	14711	6293
65°	12901	4629	13139	5374
70°	11299	3632	11589	4334
75°	9482	2638	9857	3143
80°	7401	1671	7928	1865
85°	4859	842	5241	623

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 28197 cd/sqm

TEST NUMBER: P999220

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.1	2.2
10°-20°	477.7	6.4
20°-30°	693.3	9.3
30°-40°	730.9	9.8
40°-50°	646.8	8.6
50°-60°	516.4	6.9
60°-70°	350.8	4.7
70°-80°	179.5	2.4
80°-90°	44.6	0.6
90°-100°	41.4	0.6
100°-110°	154.2	2.1
110°-120°	409.1	5.5
120°-130°	678.5	9.1
130°-140°	720.7	9.6
140°-150°	669.9	9.0
150°-160°	538.5	7.2
160°-170°	347.0	4.6
170°-180°	119.4	1.6
0°-30°	1335.2	17.8
0°-40°	2066.1	27.6
0°-60°	3229.3	43.2
0°-90°	3804.2	50.8
90°-120°	604.7	8.1
90°-150°	2673.8	35.7
90°-180°	3679.0	49.2
0°-180°	7483.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1723	1723	1723	1723	1723	
5°	1725	1925	1731	1531	1725	163
15°	1620	2366	1642	1135	1620	458
25°	1456	1971	1462	911	1456	665
35°	1188	1073	1208	756	1188	743
45°	891	646	906	621	891	692
55°	612	454	616	481	612	546
65°	363	280	370	324	363	361
75°	170	138	176	164	170	182
85°	34	36	37	26	34	40
90°	1	24	1	24	1	5
95°	59	39	59	39	59	70
105°	276	69	276	69	276	295
115°	522	74	522	74	522	514
125°	738	776	738	776	738	658
135°	913	943	913	943	913	706
145°	1060	1076	1060	1076	1060	663
155°	1167	1168	1167	1168	1167	538
165°	1229	1227	1229	1227	1229	347
175°	1258	1250	1258	1250	1258	120
180°	1255	1255	1255	1255	1255	

TEST NUMBER: P999220

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1732.5	1736.5	1743.1	1744.4	1757.7	1768.3	1780.2	1780.2	1784.2	1782.8	1772.3
5°	1724.6	1736.5	1753.7	1768.3	1792.1	1802.7	1818.6	1830.5	1841.1	1849.1	1847.8
7.5°	1711.3	1732.5	1757.7	1785.5	1817.3	1835.8	1858.3	1879.5	1894.1	1907.4	1916.6
10°	1688.8	1724.6	1759.0	1796.1	1837.2	1862.3	1888.8	1916.6	1939.1	1964.3	1988.2
12.5°	1658.3	1710.0	1752.4	1801.4	1851.7	1879.5	1921.9	1943.1	1986.8	2050.4	2067.6
15°	1619.9	1690.1	1729.9	1792.1	1858.3	1880.9	1939.1	1973.6	2063.7	2103.4	2151.1
17.5°	1584.2	1662.3	1715.3	1786.8	1851.7	1895.4	1952.4	2022.6	2098.1	2155.0	2208.0
20°	1555.0	1630.5	1694.1	1773.6	1855.7	1911.3	1970.9	2055.7	2137.8	2196.1	2237.2
22.5°	1488.8	1585.5	1659.7	1748.4	1847.8	1924.6	1981.5	2074.3	2163.0	2198.8	2234.5
25°	1455.7	1539.1	1625.2	1725.9	1842.5	1933.8	1982.9	2086.2	2164.3	2177.6	2185.5
27.5°	1394.8	1488.8	1589.5	1704.7	1841.1	1918.0	1980.2	2074.3	2136.5	2127.2	2103.4
30°	1319.3	1434.5	1545.8	1670.3	1822.6	1906.0	1964.3	2050.4	2082.2	2034.5	1992.1
32.5°	1263.6	1372.2	1495.4	1639.8	1801.4	1880.9	1937.8	2005.4	2012.0	1925.9	1854.4
35°	1188.1	1308.7	1447.7	1600.1	1765.6	1837.2	1890.1	1931.2	1899.4	1778.9	1694.1
37.5°	1120.6	1239.8	1388.1	1543.1	1716.6	1786.8	1829.2	1835.8	1757.7	1651.7	1527.2
40°	1046.4	1169.6	1324.6	1487.5	1662.3	1723.2	1749.7	1729.9	1617.3	1494.1	1349.7
42.5°	972.2	1094.1	1261.0	1427.9	1593.4	1645.1	1655.7	1601.4	1463.6	1319.3	1152.4
45°	891.4	1018.6	1185.5	1353.7	1514.0	1543.1	1544.4	1466.3	1303.4	1152.4	997.4
47.5°	825.2	943.1	1108.7	1276.9	1412.0	1431.8	1423.9	1333.8	1156.3	986.8	851.7
50°	752.3	864.9	1029.2	1194.7	1310.0	1315.3	1295.4	1166.9	993.4	838.4	731.2
52.5°	674.2	788.1	939.1	1098.1	1201.4	1193.4	1155.0	1017.3	854.3	725.9	643.7
55°	611.9	712.6	854.3	1009.3	1082.2	1059.6	1017.3	876.9	748.4	639.8	568.2
57.5°	543.1	631.8	770.9	906.0	948.4	927.2	884.8	753.7	634.5	552.3	504.7
60°	478.2	559.0	680.8	793.4	826.5	804.0	755.0	637.1	551.0	482.1	446.4
62.5°	418.6	488.8	590.8	694.1	707.3	684.8	642.4	547.0	472.9	418.6	392.1
65°	362.9	429.2	511.3	589.4	601.3	577.5	533.8	464.9	402.7	368.2	343.1
67.5°	308.6	361.6	434.5	491.4	498.0	475.5	439.8	384.1	345.7	308.6	290.1
70°	260.9	300.7	357.6	404.0	406.6	385.4	366.9	316.6	287.4	260.9	246.4
72.5°	214.6	242.4	286.1	320.5	321.9	308.6	291.4	259.6	234.4	215.9	201.3
75°	169.5	193.4	219.9	250.3	249.0	238.4	225.2	205.3	184.1	172.2	165.6
77.5°	129.8	144.4	165.6	185.4	185.4	180.1	172.2	157.6	144.4	132.5	125.8
80°	92.7	102.0	119.2	125.8	128.5	127.2	120.5	109.9	104.6	95.4	92.7
82.5°	59.6	66.2	74.2	80.8	84.8	82.1	80.8	75.5	67.6	64.9	62.3
85°	34.4	37.1	41.1	45.0	46.4	45.0	47.7	43.7	39.7	39.7	38.4
87.5°	14.6	15.9	18.5	18.5	19.9	19.9	18.5	19.9	19.9	18.5	17.2
90°	0.9	3.1	5.3	7.6	9.8	10.9	11.7	13.3	15.0	16.6	18.2
92.5°	22.7	21.9	21.1	20.3	19.5	19.1	19.4	20.0	20.6	21.2	21.8
95°	59.0	52.4	45.7	39.1	32.4	29.1	29.8	31.2	32.6	34.0	35.4
97.5°	106.2	89.7	73.1	56.6	40.1	31.8	33.4	36.6	39.9	43.1	46.3
100°	160.7	133.1	105.4	77.8	50.1	36.3	38.0	41.5	44.9	48.4	51.8
102.5°	220.6	220.2	219.8	219.4	219.0	218.8	200.4	163.7	127.0	90.3	53.6
105°	276.0	282.1	288.1	294.2	300.3	303.3	275.8	220.7	165.6	110.5	55.4
107.5°	340.5	345.5	350.6	355.6	360.7	363.2	329.2	261.2	193.2	125.2	57.2
110°	402.2	406.4	410.7	414.9	419.2	421.3	392.1	333.8	275.5	217.2	158.9

TEST NUMBER: P999220

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	460.4	464.0	467.6	471.3	474.9	476.7	475.0	471.6	468.1	464.7	461.3
115°	522.1	525.5	528.9	532.4	535.8	537.5	540.0	545.1	550.1	555.2	560.2
117.5°	575.7	579.7	583.7	587.8	591.8	593.8	595.5	599.0	602.4	605.9	609.3
120°	635.6	638.6	641.6	644.7	647.7	649.2	651.0	654.7	658.3	662.0	665.6
122.5°	686.4	689.6	692.9	696.1	699.4	701.0	703.0	707.0	711.1	715.1	719.1
125°	738.2	740.8	743.4	746.1	748.7	750.0	751.9	755.8	759.6	763.5	767.3
127.5°	785.4	788.2	791.0	793.9	796.7	798.1	799.6	802.7	805.7	808.8	811.8
130°	829.9	833.1	836.3	839.6	842.8	844.4	845.5	847.7	850.0	852.2	854.4
132.5°	875.3	877.9	880.5	883.2	885.8	887.1	888.2	890.4	892.7	894.9	897.1
135°	913.4	916.6	919.9	923.1	926.4	928.0	928.9	930.7	932.5	934.3	936.1
137.5°	953.4	955.8	958.2	960.7	963.1	964.3	965.3	967.3	969.4	971.4	973.4
140°	992.4	994.0	995.6	997.3	998.9	999.7	1000.8	1003.0	1005.3	1007.5	1009.7
142.5°	1025.1	1026.5	1027.9	1029.4	1030.8	1031.5	1032.8	1035.4	1038.1	1040.7	1043.3
145°	1059.6	1059.4	1059.2	1059.0	1058.8	1058.7	1060.4	1063.9	1067.3	1070.8	1074.2
147.5°	1089.6	1089.0	1088.4	1087.8	1087.2	1086.9	1088.6	1092.0	1095.5	1098.9	1102.3
150°	1118.7	1117.3	1115.9	1114.4	1113.0	1112.3	1113.9	1117.1	1120.4	1123.6	1126.8
152.5°	1143.2	1141.6	1140.0	1138.3	1136.7	1135.9	1137.4	1140.4	1143.5	1146.5	1149.5
155°	1166.8	1165.0	1163.2	1161.3	1159.5	1158.6	1159.8	1162.2	1164.7	1167.1	1169.5
157.5°	1185.8	1184.2	1182.6	1181.0	1179.4	1178.6	1179.5	1181.3	1183.2	1185.0	1186.8
160°	1202.2	1201.0	1199.8	1198.5	1197.3	1196.7	1197.3	1198.5	1199.8	1201.0	1202.2
162.5°	1216.7	1215.5	1214.3	1213.1	1211.9	1211.3	1211.8	1212.8	1213.8	1214.8	1215.8
165°	1229.4	1228.2	1227.0	1225.8	1224.6	1224.0	1224.3	1224.9	1225.5	1226.1	1226.7
167.5°	1239.4	1238.2	1237.0	1235.8	1234.6	1234.0	1234.3	1234.9	1235.5	1236.1	1236.7
170°	1247.6	1246.4	1245.2	1243.9	1242.7	1242.1	1242.3	1242.7	1243.2	1243.6	1244.0
172.5°	1253.0	1251.8	1250.6	1249.4	1248.2	1247.6	1247.8	1248.2	1248.6	1249.0	1249.4
175°	1257.6	1256.2	1254.8	1253.3	1251.9	1251.2	1251.4	1251.8	1252.2	1252.6	1253.0
177.5°	1259.4	1258.0	1256.6	1255.1	1253.7	1253.0	1253.1	1253.3	1253.5	1253.7	1253.9
180°	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9

TEST NUMBER: P999220

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1790.8	1792.1	1794.8	1808.0	1814.6	1816.0	1810.7	1822.6	1826.6	1822.6	1819.9
5°	1875.6	1883.5	1899.4	1916.6	1915.3	1916.6	1924.6	1932.5	1935.2	1924.6	1928.5
7.5°	1949.7	1965.6	1982.9	2009.3	2009.3	2022.6	2027.9	2034.5	2050.4	2042.5	2039.8
10°	2034.5	2055.7	2087.5	2129.9	2131.2	2144.5	2157.7	2178.9	2185.5	2180.2	2182.9
12.5°	2140.5	2181.5	2184.2	2230.5	2251.7	2254.4	2275.6	2271.6	2284.9	2284.9	2307.4
15°	2186.8	2250.4	2286.2	2331.2	2344.5	2328.6	2345.8	2364.3	2365.7	2365.7	2364.3
17.5°	2270.3	2295.5	2331.2	2355.1	2360.4	2360.4	2361.7	2369.6	2364.3	2353.7	2361.7
20°	2287.5	2298.1	2311.3	2308.7	2311.3	2298.1	2284.9	2271.6	2272.9	2266.3	2286.2
22.5°	2255.7	2253.1	2222.6	2202.7	2202.7	2176.2	2151.1	2139.2	2127.2	2131.2	2137.8
25°	2176.2	2135.2	2098.1	2069.0	2062.3	2019.9	1985.5	1974.9	1955.0	1970.9	1973.6
27.5°	2049.1	2002.7	1943.1	1918.0	1883.5	1866.3	1842.5	1810.7	1769.6	1793.4	1789.5
30°	1912.7	1843.8	1794.8	1733.8	1679.5	1675.6	1630.5	1577.5	1556.3	1556.3	1568.3
32.5°	1760.3	1668.9	1597.4	1511.3	1458.3	1435.8	1381.5	1328.5	1340.4	1300.7	1315.3
35°	1582.8	1462.3	1372.2	1288.8	1249.1	1222.6	1152.4	1123.2	1091.4	1072.9	1107.3
37.5°	1413.3	1274.2	1159.0	1067.6	1053.0	1005.3	957.7	939.1	920.6	928.5	927.2
40°	1206.7	1083.5	980.2	908.6	883.5	861.0	829.2	806.7	794.7	801.4	802.7
42.5°	1019.9	916.6	839.8	789.4	768.2	752.3	736.5	717.9	713.9	713.9	719.2
45°	875.5	790.8	739.1	698.0	686.1	674.2	662.3	654.3	651.7	646.4	650.4
47.5°	760.3	692.7	661.0	630.5	617.2	614.6	604.0	600.0	594.7	593.4	594.7
50°	663.6	621.2	592.1	574.9	565.6	561.6	556.3	548.4	545.7	552.3	549.7
52.5°	596.0	556.3	540.4	523.2	517.9	512.6	504.7	506.0	504.7	502.0	502.0
55°	528.5	503.3	487.4	474.2	472.9	467.6	460.9	458.3	457.0	454.3	458.3
57.5°	474.2	454.3	439.8	427.8	422.5	422.5	415.9	410.6	410.6	409.3	410.6
60°	419.9	400.0	390.7	378.8	374.8	373.5	369.6	366.9	362.9	362.9	362.9
62.5°	369.6	353.7	343.1	332.5	333.8	327.2	321.9	319.2	319.2	320.5	320.5
65°	321.9	311.3	298.0	288.8	286.1	284.8	282.1	280.8	276.8	279.5	279.5
67.5°	278.2	263.6	255.6	251.7	247.7	246.4	243.7	241.1	239.7	238.4	241.1
70°	234.4	222.5	215.9	213.3	209.3	208.0	206.6	202.7	204.0	205.3	206.6
72.5°	194.7	184.1	182.8	174.8	174.8	174.8	169.5	172.2	170.9	168.2	170.9
75°	153.6	148.3	145.7	141.7	143.1	141.7	140.4	136.4	136.4	137.8	139.1
77.5°	121.9	116.6	115.2	111.3	108.6	111.3	108.6	107.3	107.3	108.6	108.6
80°	90.1	87.4	83.4	83.4	83.4	82.1	82.1	82.1	80.8	79.5	80.8
82.5°	59.6	59.6	58.3	57.0	58.3	55.6	57.0	57.0	57.0	57.0	57.0
85°	38.4	37.1	37.1	35.8	35.8	35.8	37.1	34.4	34.4	35.8	35.8
87.5°	17.2	17.2	17.2	18.5	17.2	17.2	17.2	18.5	17.2	17.2	17.2
90°	19.2	20.2	21.2	22.2	22.7	22.9	23.3	23.7	24.1	24.5	24.1
92.5°	22.2	22.6	23.0	23.4	23.6	23.7	23.9	24.1	24.3	24.5	24.3
95°	36.4	37.4	38.5	39.5	40.0	39.9	39.7	39.4	39.2	39.0	39.2
97.5°	46.9	47.5	48.1	48.7	49.0	49.1	49.3	49.5	49.7	49.9	49.7
100°	53.4	55.0	56.6	58.2	59.0	59.2	59.6	60.0	60.4	60.8	60.4
102.5°	55.8	58.0	60.3	62.5	63.6	63.9	64.5	65.1	65.7	66.3	65.7
105°	57.6	59.8	62.1	64.3	65.4	65.8	66.6	67.4	68.2	69.0	68.2
107.5°	59.4	61.6	63.9	66.1	67.2	67.6	68.4	69.2	70.0	70.8	70.0
110°	138.7	118.5	98.4	78.2	68.1	68.5	69.3	70.1	70.9	71.7	70.9

TEST NUMBER: P999220

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	374.3	287.3	200.4	113.4	69.9	70.2	70.8	71.4	72.0	72.6	72.0
115°	466.8	373.4	279.9	186.5	139.8	132.5	118.0	103.5	89.0	74.5	89.0
117.5°	580.4	551.6	522.7	493.8	479.4	453.0	400.1	347.2	294.4	241.5	294.4
120°	668.0	670.4	672.9	675.3	676.5	662.9	635.6	608.4	581.1	553.9	581.1
122.5°	720.3	721.5	722.8	724.0	724.6	724.7	724.9	725.1	725.3	725.5	725.3
125°	768.7	770.1	771.5	772.9	773.6	773.9	774.5	775.1	775.7	776.3	775.7
127.5°	813.8	815.8	817.8	819.8	820.8	820.9	821.1	821.3	821.5	821.7	821.5
130°	856.6	858.8	861.1	863.3	864.4	864.3	864.1	863.9	863.7	863.5	863.7
132.5°	898.9	900.7	902.6	904.4	905.3	905.2	905.0	904.8	904.6	904.4	904.6
135°	938.1	940.1	942.2	944.2	945.2	945.0	944.6	944.2	943.8	943.4	943.8
137.5°	975.4	977.4	979.5	981.5	982.5	982.2	981.6	980.9	980.3	979.7	980.3
140°	1011.5	1013.3	1015.2	1017.0	1017.9	1017.4	1016.4	1015.3	1014.3	1013.3	1014.3
142.5°	1044.9	1046.5	1048.2	1049.8	1050.6	1050.1	1049.1	1048.0	1047.0	1046.0	1047.0
145°	1075.6	1077.0	1078.4	1079.8	1080.5	1080.0	1079.0	1078.0	1077.0	1076.0	1077.0
147.5°	1103.3	1104.3	1105.4	1106.4	1106.9	1106.5	1105.7	1104.8	1104.0	1103.2	1104.0
150°	1128.0	1129.2	1130.5	1131.7	1132.3	1131.8	1130.8	1129.7	1128.7	1127.7	1128.7
152.5°	1150.7	1151.9	1153.2	1154.4	1155.0	1154.3	1152.9	1151.4	1150.0	1148.6	1150.0
155°	1170.7	1171.9	1173.2	1174.4	1175.0	1174.2	1172.6	1170.9	1169.3	1167.7	1169.3
157.5°	1188.2	1189.6	1191.0	1192.4	1193.1	1192.3	1190.7	1189.0	1187.4	1185.8	1187.4
160°	1203.4	1204.6	1205.8	1207.0	1207.6	1206.9	1205.5	1204.1	1202.7	1201.3	1202.7
162.5°	1217.2	1218.6	1220.1	1221.5	1222.2	1221.3	1219.5	1217.6	1215.8	1214.0	1215.8
165°	1228.1	1229.5	1231.0	1232.4	1233.1	1232.4	1231.0	1229.5	1228.1	1226.7	1228.1
167.5°	1238.1	1239.5	1241.0	1242.4	1243.1	1242.2	1240.4	1238.5	1236.7	1234.9	1236.7
170°	1245.4	1246.8	1248.2	1249.6	1250.3	1249.4	1247.6	1245.7	1243.9	1242.1	1243.9
172.5°	1250.8	1252.2	1253.7	1255.1	1255.8	1254.9	1253.1	1251.2	1249.4	1247.6	1249.4
175°	1254.4	1255.8	1257.3	1258.7	1259.4	1258.4	1256.4	1254.3	1252.3	1250.3	1252.3
177.5°	1255.3	1256.7	1258.2	1259.6	1260.3	1259.4	1257.6	1255.7	1253.9	1252.1	1253.9
180°	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9

TEST NUMBER: P999220

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1826.6	1817.3	1809.3	1810.7	1817.3	1812.0	1798.7	1781.5	1774.9	1767.0	1774.9
5°	1936.5	1928.5	1912.7	1914.0	1910.0	1904.7	1883.5	1857.0	1857.0	1835.8	1833.2
7.5°	2045.1	2033.2	2022.6	2019.9	2005.4	1994.8	1976.2	1939.1	1924.6	1899.4	1884.8
10°	2167.0	2157.7	2145.8	2131.2	2123.3	2104.7	2074.3	2019.9	1993.5	1959.0	1933.8
12.5°	2290.2	2288.8	2262.3	2233.2	2231.9	2202.7	2181.5	2108.7	2072.9	2026.6	1967.0
15°	2368.3	2361.7	2347.1	2332.5	2336.5	2304.7	2257.0	2170.9	2147.1	2091.5	2027.9
17.5°	2367.0	2367.0	2363.0	2360.4	2356.4	2347.1	2320.6	2263.7	2225.2	2155.0	2095.4
20°	2291.5	2308.7	2312.7	2311.3	2324.6	2331.2	2329.9	2294.1	2263.7	2201.4	2140.5
22.5°	2140.5	2180.2	2197.4	2208.0	2235.8	2250.4	2284.9	2271.6	2263.7	2217.3	2165.6
25°	2000.1	2013.3	2065.0	2067.6	2106.0	2141.8	2176.2	2198.8	2227.9	2210.7	2167.0
27.5°	1818.6	1849.1	1886.2	1914.0	1921.9	1994.8	2051.7	2094.1	2160.3	2165.6	2151.1
30°	1613.3	1627.9	1688.8	1725.9	1768.3	1821.3	1903.4	1976.2	2035.8	2090.1	2108.7
32.5°	1363.0	1422.6	1458.3	1503.4	1540.5	1634.5	1735.2	1829.2	1898.1	1989.5	2029.2
35°	1133.8	1180.2	1241.1	1259.6	1327.2	1406.7	1537.8	1658.3	1763.0	1855.7	1936.5
37.5°	944.4	981.5	1046.4	1075.5	1115.3	1217.3	1327.2	1476.9	1602.7	1716.6	1817.3
40°	814.6	842.4	891.4	900.7	933.8	1026.5	1115.3	1255.7	1422.6	1576.2	1686.2
42.5°	725.9	739.1	772.2	784.1	805.3	867.6	947.1	1079.5	1234.5	1393.4	1548.4
45°	662.3	671.5	691.4	702.0	728.5	756.3	821.2	927.2	1049.0	1209.3	1376.2
47.5°	605.3	617.2	625.2	631.8	646.4	676.8	719.2	797.4	913.9	1061.0	1222.6
50°	557.6	561.6	576.2	577.5	586.8	606.6	646.4	694.1	786.8	906.0	1062.3
52.5°	510.0	513.9	523.2	532.5	536.4	552.3	578.8	618.6	687.4	781.5	920.6
55°	462.3	467.6	476.8	483.5	487.4	500.7	516.6	555.0	609.3	675.5	789.4
57.5°	414.6	426.5	429.2	433.1	439.8	454.3	468.9	491.4	533.8	594.7	678.2
60°	369.6	373.5	382.8	386.8	393.4	401.3	419.9	437.1	467.6	515.3	590.8
62.5°	323.2	332.5	336.4	340.4	345.7	355.0	366.9	385.4	411.9	450.3	510.0
65°	283.5	284.8	292.7	298.0	303.3	309.9	321.9	339.1	355.0	390.7	434.5
67.5°	245.0	247.7	250.3	255.6	262.3	268.9	279.5	288.8	308.6	332.5	366.9
70°	208.0	208.0	214.6	218.6	217.2	225.2	233.1	243.7	258.3	280.8	308.6
72.5°	174.8	173.5	178.8	180.1	182.8	188.1	193.4	204.0	211.9	229.1	250.3
75°	139.1	141.7	144.4	144.4	148.3	152.3	157.6	162.9	172.2	182.8	198.7
77.5°	109.9	109.9	112.6	113.9	117.9	116.6	121.9	127.2	133.8	143.1	155.0
80°	80.8	83.4	83.4	83.4	84.8	86.1	91.4	95.4	99.3	106.0	111.3
82.5°	57.0	57.0	59.6	59.6	59.6	62.3	62.3	63.6	66.2	70.2	74.2
85°	35.8	35.8	35.8	37.1	35.8	37.1	39.7	38.4	39.7	42.4	42.4
87.5°	17.2	17.2	17.2	17.2	17.2	18.5	17.2	18.5	19.9	19.9	19.9
90°	23.7	23.3	22.9	22.7	22.2	21.2	20.2	19.2	18.2	16.6	15.0
92.5°	24.1	23.9	23.7	23.6	23.4	23.0	22.6	22.2	21.8	21.2	20.6
95°	39.4	39.7	39.9	40.0	39.5	38.5	37.4	36.4	35.4	34.0	32.6
97.5°	49.5	49.3	49.1	49.0	48.7	48.1	47.5	46.9	46.3	43.1	39.9
100°	60.0	59.6	59.2	59.0	58.2	56.6	55.0	53.4	51.8	48.4	44.9
102.5°	65.1	64.5	63.9	63.6	62.5	60.3	58.0	55.8	53.6	50.3	47.0
105°	67.4	66.6	65.8	65.4	64.3	62.1	59.8	57.6	55.4	52.1	48.8
107.5°	69.2	68.4	67.6	67.2	66.1	63.9	61.6	59.4	57.2	54.0	50.8
110°	70.1	69.3	68.5	68.1	67.2	65.0	62.8	60.6	58.4	55.2	52.0

TEST NUMBER: P999220

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	71.4	70.8	70.2	69.9	113.4	200.4	287.3	374.3	461.3	464.7	468.1
115°	103.5	118.0	132.5	139.8	186.5	279.9	373.4	466.8	560.2	555.2	550.1
117.5°	347.2	400.1	453.0	479.4	493.8	522.7	551.6	580.4	609.3	605.9	602.4
120°	608.4	635.6	662.9	676.5	675.3	672.9	670.4	668.0	665.6	662.0	658.3
122.5°	725.1	724.9	724.7	724.6	724.0	722.8	721.5	720.3	719.1	715.1	711.1
125°	775.1	774.5	773.9	773.6	772.9	771.5	770.1	768.7	767.3	763.5	759.6
127.5°	821.3	821.1	820.9	820.8	819.8	817.8	815.8	813.8	811.8	808.8	805.7
130°	863.9	864.1	864.3	864.4	863.3	861.1	858.8	856.6	854.4	852.2	850.0
132.5°	904.8	905.0	905.2	905.3	904.4	902.6	900.7	898.9	897.1	894.9	892.7
135°	944.2	944.6	945.0	945.2	944.2	942.2	940.1	938.1	936.1	934.3	932.5
137.5°	980.9	981.6	982.2	982.5	981.5	979.5	977.4	975.4	973.4	971.4	969.4
140°	1015.3	1016.4	1017.4	1017.9	1017.0	1015.2	1013.3	1011.5	1009.7	1007.5	1005.3
142.5°	1048.0	1049.1	1050.1	1050.6	1049.8	1048.2	1046.5	1044.9	1043.3	1040.7	1038.1
145°	1078.0	1079.0	1080.0	1080.5	1079.8	1078.4	1077.0	1075.6	1074.2	1070.8	1067.3
147.5°	1104.8	1105.7	1106.5	1106.9	1106.4	1105.4	1104.3	1103.3	1102.3	1098.9	1095.5
150°	1129.7	1130.8	1131.8	1132.3	1131.7	1130.5	1129.2	1128.0	1126.8	1123.6	1120.4
152.5°	1151.4	1152.9	1154.3	1155.0	1154.4	1153.2	1151.9	1150.7	1149.5	1146.5	1143.5
155°	1170.9	1172.6	1174.2	1175.0	1174.4	1173.2	1171.9	1170.7	1169.5	1167.1	1164.7
157.5°	1189.0	1190.7	1192.3	1193.1	1192.4	1191.0	1189.6	1188.2	1186.8	1185.0	1183.2
160°	1204.1	1205.5	1206.9	1207.6	1207.0	1205.8	1204.6	1203.4	1202.2	1201.0	1199.8
162.5°	1217.6	1219.5	1221.3	1222.2	1221.5	1220.1	1218.6	1217.2	1215.8	1214.8	1213.8
165°	1229.5	1231.0	1232.4	1233.1	1232.4	1231.0	1229.5	1228.1	1226.7	1226.1	1225.5
167.5°	1238.5	1240.4	1242.2	1243.1	1242.4	1241.0	1239.5	1238.1	1236.7	1236.1	1235.5
170°	1245.7	1247.6	1249.4	1250.3	1249.6	1248.2	1246.8	1245.4	1244.0	1243.6	1243.2
172.5°	1251.2	1253.1	1254.9	1255.8	1255.1	1253.7	1252.2	1250.8	1249.4	1249.0	1248.6
175°	1254.3	1256.4	1258.4	1259.4	1258.7	1257.3	1255.8	1254.4	1253.0	1252.6	1252.2
177.5°	1255.7	1257.6	1259.4	1260.3	1259.6	1258.2	1256.7	1255.3	1253.9	1253.7	1253.5
180°	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9

TEST NUMBER: P999220

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1768.3	1761.7	1757.7	1760.3	1752.4	1732.5	1732.5	1739.1	1731.2	1723.2	1711.3
5°	1817.3	1804.0	1796.1	1794.8	1776.2	1744.4	1737.8	1731.2	1714.0	1695.4	1675.6
7.5°	1865.0	1841.1	1827.9	1818.6	1792.1	1751.1	1733.8	1719.3	1691.5	1663.6	1638.5
10°	1904.7	1870.3	1854.4	1839.8	1805.4	1753.7	1725.9	1699.4	1663.6	1627.9	1596.1
12.5°	1936.5	1896.8	1876.9	1855.7	1813.3	1745.8	1711.3	1668.9	1633.2	1585.5	1553.7
15°	1989.5	1907.4	1888.8	1868.9	1825.2	1732.5	1690.1	1642.4	1593.4	1529.9	1495.4
17.5°	2031.9	1921.9	1920.6	1878.2	1821.3	1727.2	1662.3	1600.1	1547.1	1483.5	1429.2
20°	2057.0	1944.4	1923.3	1879.5	1808.0	1691.5	1623.9	1555.0	1498.1	1421.2	1366.9
22.5°	2078.2	1976.2	1920.6	1867.6	1780.2	1679.5	1580.2	1515.3	1437.1	1353.7	1302.0
25°	2086.2	1982.9	1924.6	1863.6	1760.3	1645.1	1532.5	1462.3	1374.9	1299.4	1229.2
27.5°	2087.5	1981.5	1910.0	1846.4	1732.5	1600.1	1484.8	1410.6	1314.0	1226.5	1156.3
30°	2074.3	1967.0	1902.1	1833.2	1706.0	1559.0	1426.5	1344.4	1241.1	1153.7	1080.8
32.5°	2034.5	1937.8	1884.8	1809.3	1671.6	1502.0	1370.9	1279.5	1170.9	1084.8	1014.6
35°	1968.3	1902.1	1843.8	1773.6	1626.6	1449.1	1315.3	1208.0	1098.1	1015.9	949.7
37.5°	1886.2	1850.4	1796.1	1727.2	1574.9	1401.4	1253.0	1133.8	1023.9	944.4	879.5
40°	1774.9	1784.2	1731.2	1668.9	1514.0	1336.5	1172.2	1058.3	955.0	880.8	817.2
42.5°	1654.4	1692.8	1662.3	1602.7	1446.4	1264.9	1112.6	986.8	886.1	809.3	756.3
45°	1524.6	1590.8	1572.2	1528.5	1376.2	1189.4	1027.9	906.0	817.2	743.1	696.7
47.5°	1382.8	1476.9	1476.9	1445.1	1298.1	1113.9	955.0	830.5	743.1	690.1	645.1
50°	1238.5	1344.4	1361.6	1340.4	1210.6	1027.9	866.3	753.7	678.2	626.5	593.4
52.5°	1087.5	1210.6	1242.4	1231.8	1117.9	945.7	793.4	683.5	614.6	569.6	540.4
55°	943.1	1086.1	1120.6	1124.5	1018.6	855.7	712.6	615.9	549.7	519.2	494.1
57.5°	806.7	944.4	982.8	989.4	917.9	773.5	637.1	552.3	492.7	467.6	447.7
60°	690.1	805.3	855.7	870.2	808.0	678.2	566.9	484.8	439.8	415.9	397.4
62.5°	594.7	687.4	740.4	744.4	716.6	594.7	494.1	425.2	386.8	365.6	356.3
65°	502.0	585.5	617.2	633.1	610.6	515.3	426.5	369.6	339.1	320.5	311.3
67.5°	427.8	480.8	507.3	528.5	506.0	434.5	362.9	316.6	294.1	275.5	270.2
70°	351.0	394.7	414.6	435.8	415.9	361.6	309.9	267.6	247.7	233.1	226.5
72.5°	280.8	315.2	333.8	347.0	335.1	290.1	247.7	218.6	204.0	193.4	189.4
75°	222.5	246.4	257.0	266.2	260.9	226.5	200.0	176.2	162.9	153.6	151.0
77.5°	169.5	186.8	198.7	201.3	194.7	172.2	149.7	135.1	124.5	119.2	116.6
80°	120.5	131.1	137.8	141.7	135.1	125.8	109.9	99.3	90.1	83.4	82.1
82.5°	80.8	86.1	91.4	90.1	87.4	79.5	70.2	64.9	60.9	55.6	55.6
85°	46.4	47.7	50.3	51.7	50.3	45.0	39.7	37.1	34.4	30.5	30.5
87.5°	19.9	21.2	21.2	22.5	19.9	19.9	17.2	14.6	14.6	13.2	11.9
90°	13.3	11.7	10.9	9.8	7.6	5.3	3.1	0.9	3.1	5.3	7.6
92.5°	20.0	19.4	19.1	19.5	20.3	21.1	21.9	22.7	21.9	21.1	20.3
95°	31.2	29.8	29.1	32.4	39.1	45.7	52.4	59.0	52.4	45.7	39.1
97.5°	36.6	33.4	31.8	40.1	56.6	73.1	89.7	106.2	89.7	73.1	56.6
100°	41.5	38.0	36.3	50.1	77.8	105.4	133.1	160.7	133.1	105.4	77.8
102.5°	163.7	200.4	218.8	219.0	219.4	219.8	220.2	220.6	220.2	219.8	219.4
105°	220.7	275.8	303.3	300.3	294.2	288.1	282.1	276.0	282.1	288.1	294.2
107.5°	261.2	329.2	363.2	360.7	355.6	350.6	345.5	340.5	345.5	350.6	355.6
110°	333.8	392.1	421.3	419.2	414.9	410.7	406.4	402.2	406.4	410.7	414.9

TEST NUMBER: P999220

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	471.6	475.0	476.7	474.9	471.3	467.6	464.0	460.4	464.0	467.6	471.3
115°	545.1	540.0	537.5	535.8	532.4	528.9	525.5	522.1	525.5	528.9	532.4
117.5°	599.0	595.5	593.8	591.8	587.8	583.7	579.7	575.7	579.7	583.7	587.8
120°	654.7	651.0	649.2	647.7	644.7	641.6	638.6	635.6	638.6	641.6	644.7
122.5°	707.0	703.0	701.0	699.4	696.1	692.9	689.6	686.4	689.6	692.9	696.1
125°	755.8	751.9	750.0	748.7	746.1	743.4	740.8	738.2	740.8	743.4	746.1
127.5°	802.7	799.6	798.1	796.7	793.9	791.0	788.2	785.4	788.2	791.0	793.9
130°	847.7	845.5	844.4	842.8	839.6	836.3	833.1	829.9	833.1	836.3	839.6
132.5°	890.4	888.2	887.1	885.8	883.2	880.5	877.9	875.3	877.9	880.5	883.2
135°	930.7	928.9	928.0	926.4	923.1	919.9	916.6	913.4	916.6	919.9	923.1
137.5°	967.3	965.3	964.3	963.1	960.7	958.2	955.8	953.4	955.8	958.2	960.7
140°	1003.0	1000.8	999.7	998.9	997.3	995.6	994.0	992.4	994.0	995.6	997.3
142.5°	1035.4	1032.8	1031.5	1030.8	1029.4	1027.9	1026.5	1025.1	1026.5	1027.9	1029.4
145°	1063.9	1060.4	1058.7	1058.8	1059.0	1059.2	1059.4	1059.6	1059.4	1059.2	1059.0
147.5°	1092.0	1088.6	1086.9	1087.2	1087.8	1088.4	1089.0	1089.6	1089.0	1088.4	1087.8
150°	1117.1	1113.9	1112.3	1113.0	1114.4	1115.9	1117.3	1118.7	1117.3	1115.9	1114.4
152.5°	1140.4	1137.4	1135.9	1136.7	1138.3	1140.0	1141.6	1143.2	1141.6	1140.0	1138.3
155°	1162.2	1159.8	1158.6	1159.5	1161.3	1163.2	1165.0	1166.8	1165.0	1163.2	1161.3
157.5°	1181.3	1179.5	1178.6	1179.4	1181.0	1182.6	1184.2	1185.8	1184.2	1182.6	1181.0
160°	1198.5	1197.3	1196.7	1197.3	1198.5	1199.8	1201.0	1202.2	1201.0	1199.8	1198.5
162.5°	1212.8	1211.8	1211.3	1211.9	1213.1	1214.3	1215.5	1216.7	1215.5	1214.3	1213.1
165°	1224.9	1224.3	1224.0	1224.6	1225.8	1227.0	1228.2	1229.4	1228.2	1227.0	1225.8
167.5°	1234.9	1234.3	1234.0	1234.6	1235.8	1237.0	1238.2	1239.4	1238.2	1237.0	1235.8
170°	1242.7	1242.3	1242.1	1242.7	1243.9	1245.2	1246.4	1247.6	1246.4	1245.2	1243.9
172.5°	1248.2	1247.8	1247.6	1248.2	1249.4	1250.6	1251.8	1253.0	1251.8	1250.6	1249.4
175°	1251.8	1251.4	1251.2	1251.9	1253.3	1254.8	1256.2	1257.6	1256.2	1254.8	1253.3
177.5°	1253.3	1253.1	1253.0	1253.7	1255.1	1256.6	1258.0	1259.4	1258.0	1256.6	1255.1
180°	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9

TEST NUMBER: P999220

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1704.7	1711.3	1710.0	1696.8	1682.2	1670.3	1647.7	1650.4	1642.4	1643.8	1651.7
5°	1662.3	1662.3	1657.0	1638.5	1614.6	1601.4	1576.2	1569.6	1553.7	1552.4	1551.1
7.5°	1617.3	1610.7	1604.0	1577.5	1548.4	1527.2	1492.8	1484.8	1468.9	1458.3	1453.0
10°	1564.3	1555.0	1541.8	1511.3	1475.6	1449.1	1413.3	1402.7	1372.2	1359.0	1351.0
12.5°	1506.0	1500.7	1479.5	1454.4	1396.1	1366.9	1315.3	1325.9	1295.4	1268.9	1264.9
15°	1447.7	1427.9	1415.9	1374.9	1304.7	1291.4	1250.4	1229.2	1201.4	1180.2	1180.2
17.5°	1390.8	1360.3	1333.8	1290.1	1238.5	1201.4	1170.9	1160.3	1125.9	1104.7	1100.7
20°	1315.3	1280.8	1274.2	1212.0	1176.2	1135.1	1106.0	1079.5	1054.3	1045.1	1038.4
22.5°	1243.8	1204.0	1193.4	1140.4	1104.7	1063.6	1034.5	1015.9	997.4	990.8	978.8
25°	1166.9	1143.1	1127.2	1070.2	1030.5	992.1	972.2	959.0	941.8	940.4	932.5
27.5°	1092.8	1070.2	1054.3	1000.0	970.9	935.1	919.2	904.7	895.4	891.4	887.5
30°	1029.2	1004.0	985.5	945.7	910.0	880.8	867.6	858.3	853.0	846.4	845.1
32.5°	959.0	944.4	919.2	888.8	861.0	833.1	825.2	818.6	810.6	808.0	806.7
35°	899.4	879.5	863.6	829.2	817.2	793.4	784.1	778.8	768.2	765.6	762.9
37.5°	841.1	822.5	805.3	784.1	761.6	748.4	743.1	735.1	729.8	731.2	728.5
40°	782.8	768.2	755.0	732.5	719.2	712.6	702.0	694.1	691.4	692.7	691.4
42.5°	725.9	712.6	704.7	687.4	674.2	667.6	661.0	653.0	657.0	657.0	661.0
45°	674.2	662.3	657.0	643.7	635.8	625.2	618.6	617.2	622.5	621.2	621.2
47.5°	621.2	617.2	610.6	598.7	588.1	581.5	580.2	580.2	585.5	588.1	586.8
50°	580.2	572.2	564.3	555.0	547.0	544.4	540.4	543.1	548.4	548.4	551.0
52.5°	528.5	523.2	520.5	512.6	507.3	507.3	507.3	508.6	512.6	516.6	515.3
55°	483.5	479.5	476.8	472.9	466.2	467.6	466.2	468.9	472.9	476.8	479.5
57.5°	435.8	434.5	431.8	425.2	425.2	423.9	427.8	429.2	435.8	438.4	442.4
60°	393.4	389.4	389.4	384.1	384.1	384.1	388.1	392.1	397.4	398.7	401.3
62.5°	348.4	348.4	347.0	343.1	343.1	347.0	348.4	353.7	356.3	356.3	360.3
65°	306.0	304.6	303.3	304.6	306.0	306.0	309.9	312.6	315.2	316.6	317.9
67.5°	263.6	262.3	264.9	263.6	266.2	271.5	270.2	274.2	278.2	278.2	279.5
70°	223.8	226.5	225.2	227.8	226.5	229.1	233.1	234.4	234.4	235.8	239.7
72.5°	186.8	186.8	186.8	185.4	186.8	189.4	192.1	193.4	196.0	197.4	201.3
75°	151.0	151.0	148.3	151.0	151.0	153.6	156.3	156.3	156.3	158.9	162.9
77.5°	113.9	115.2	113.9	116.6	116.6	117.9	120.5	119.2	121.9	123.2	124.5
80°	83.4	82.1	82.1	82.1	83.4	83.4	86.1	87.4	87.4	91.4	88.7
82.5°	53.0	54.3	53.0	54.3	54.3	55.6	54.3	55.6	57.0	59.6	58.3
85°	30.5	29.1	29.1	30.5	29.1	29.1	30.5	29.1	30.5	29.1	30.5
87.5°	11.9	10.6	10.6	10.6	10.6	9.3	9.3	7.9	7.9	7.9	6.6
90°	9.8	10.9	11.7	13.3	15.0	16.6	18.2	19.2	20.2	21.2	22.2
92.5°	19.5	19.1	19.4	20.0	20.6	21.2	21.8	22.2	22.6	23.0	23.4
95°	32.4	29.1	29.8	31.2	32.6	34.0	35.4	36.4	37.4	38.5	39.5
97.5°	40.1	31.8	33.4	36.6	39.9	43.1	46.3	46.9	47.5	48.1	48.7
100°	50.1	36.3	38.0	41.5	44.9	48.4	51.8	53.4	55.0	56.6	58.2
102.5°	219.0	218.8	200.4	163.7	127.0	90.3	53.6	55.8	58.0	60.3	62.5
105°	300.3	303.3	275.8	220.7	165.6	110.5	55.4	57.6	59.8	62.1	64.3
107.5°	360.7	363.2	329.2	261.2	193.2	125.2	57.2	59.4	61.6	63.9	66.1
110°	419.2	421.3	392.1	333.8	275.5	217.2	158.9	138.7	118.5	98.4	78.2

TEST NUMBER: P999220

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	474.9	476.7	475.0	471.6	468.1	464.7	461.3	374.3	287.3	200.4	113.4
115°	535.8	537.5	540.0	545.1	550.1	555.2	560.2	466.8	373.4	279.9	186.5
117.5°	591.8	593.8	595.5	599.0	602.4	605.9	609.3	580.4	551.6	522.7	493.8
120°	647.7	649.2	651.0	654.7	658.3	662.0	665.6	668.0	670.4	672.9	675.3
122.5°	699.4	701.0	703.0	707.0	711.1	715.1	719.1	720.3	721.5	722.8	724.0
125°	748.7	750.0	751.9	755.8	759.6	763.5	767.3	768.7	770.1	771.5	772.9
127.5°	796.7	798.1	799.6	802.7	805.7	808.8	811.8	813.8	815.8	817.8	819.8
130°	842.8	844.4	845.5	847.7	850.0	852.2	854.4	856.6	858.8	861.1	863.3
132.5°	885.8	887.1	888.2	890.4	892.7	894.9	897.1	898.9	900.7	902.6	904.4
135°	926.4	928.0	928.9	930.7	932.5	934.3	936.1	938.1	940.1	942.2	944.2
137.5°	963.1	964.3	965.3	967.3	969.4	971.4	973.4	975.4	977.4	979.5	981.5
140°	998.9	999.7	1000.8	1003.0	1005.3	1007.5	1009.7	1011.5	1013.3	1015.2	1017.0
142.5°	1030.8	1031.5	1032.8	1035.4	1038.1	1040.7	1043.3	1044.9	1046.5	1048.2	1049.8
145°	1058.8	1058.7	1060.4	1063.9	1067.3	1070.8	1074.2	1075.6	1077.0	1078.4	1079.8
147.5°	1087.2	1086.9	1088.6	1092.0	1095.5	1098.9	1102.3	1103.3	1104.3	1105.4	1106.4
150°	1113.0	1112.3	1113.9	1117.1	1120.4	1123.6	1126.8	1128.0	1129.2	1130.5	1131.7
152.5°	1136.7	1135.9	1137.4	1140.4	1143.5	1146.5	1149.5	1150.7	1151.9	1153.2	1154.4
155°	1159.5	1158.6	1159.8	1162.2	1164.7	1167.1	1169.5	1170.7	1171.9	1173.2	1174.4
157.5°	1179.4	1178.6	1179.5	1181.3	1183.2	1185.0	1186.8	1188.2	1189.6	1191.0	1192.4
160°	1197.3	1196.7	1197.3	1198.5	1199.8	1201.0	1202.2	1203.4	1204.6	1205.8	1207.0
162.5°	1211.9	1211.3	1211.8	1212.8	1213.8	1214.8	1215.8	1217.2	1218.6	1220.1	1221.5
165°	1224.6	1224.0	1224.3	1224.9	1225.5	1226.1	1226.7	1228.1	1229.5	1231.0	1232.4
167.5°	1234.6	1234.0	1234.3	1234.9	1235.5	1236.1	1236.7	1238.1	1239.5	1241.0	1242.4
170°	1242.7	1242.1	1242.3	1242.7	1243.2	1243.6	1244.0	1245.4	1246.8	1248.2	1249.6
172.5°	1248.2	1247.6	1247.8	1248.2	1248.6	1249.0	1249.4	1250.8	1252.2	1253.7	1255.1
175°	1251.9	1251.2	1251.4	1251.8	1252.2	1252.6	1253.0	1254.4	1255.8	1257.3	1258.7
177.5°	1253.7	1253.0	1253.1	1253.3	1253.5	1253.7	1253.9	1255.3	1256.7	1258.2	1259.6
180°	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9

TEST NUMBER: P999220

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1642.4	1646.4	1637.1	1634.5	1637.1	1627.9	1630.5	1633.2	1633.2	1637.1	1639.8
5°	1547.1	1541.8	1532.5	1529.9	1527.2	1531.2	1528.5	1532.5	1533.8	1543.1	1544.4
7.5°	1453.0	1445.1	1437.1	1429.2	1426.5	1419.9	1426.5	1426.5	1435.8	1433.2	1439.8
10°	1341.8	1340.4	1329.9	1325.9	1320.6	1310.0	1324.6	1320.6	1327.2	1339.1	1341.8
12.5°	1259.6	1245.1	1251.7	1233.2	1239.8	1229.2	1230.5	1230.5	1241.1	1242.4	1239.8
15°	1181.5	1169.6	1152.4	1144.4	1140.4	1135.1	1152.4	1153.7	1145.7	1164.3	1157.7
17.5°	1102.0	1102.0	1086.1	1082.2	1071.6	1076.9	1074.2	1075.5	1072.9	1086.1	1092.8
20°	1033.2	1026.5	1021.2	1022.6	1009.3	1006.7	1004.0	1006.7	1015.9	1025.2	1027.9
22.5°	977.5	973.5	960.3	963.0	952.4	956.3	953.7	960.3	961.6	961.6	970.9
25°	924.5	919.2	920.6	915.3	911.3	911.3	907.3	911.3	916.6	919.2	920.6
27.5°	884.8	880.8	874.2	870.2	872.9	866.3	871.6	875.5	875.5	872.9	875.5
30°	837.1	839.8	839.8	826.5	831.8	829.2	833.1	835.8	835.8	837.1	834.5
32.5°	805.3	797.4	796.1	794.7	794.7	789.4	789.4	793.4	794.7	796.1	800.0
35°	762.9	762.9	756.3	760.3	755.0	756.3	755.0	756.3	759.0	755.0	759.0
37.5°	724.5	725.9	723.2	725.9	727.2	724.5	721.9	727.2	724.5	724.5	721.9
40°	691.4	690.1	691.4	691.4	691.4	692.7	690.1	690.1	690.1	687.4	684.8
42.5°	663.6	655.7	658.3	659.6	655.7	655.7	657.0	655.7	659.6	651.7	651.7
45°	623.9	621.2	622.5	622.5	625.2	621.2	623.9	625.2	621.2	619.9	617.2
47.5°	588.1	590.8	588.1	590.8	590.8	593.4	588.1	589.4	590.8	585.5	581.5
50°	552.3	552.3	556.3	555.0	556.3	553.7	553.7	552.3	553.7	551.0	547.0
52.5°	519.2	515.3	521.9	520.5	519.2	517.9	516.6	517.9	515.3	512.6	512.6
55°	478.2	478.2	482.1	483.5	483.5	480.8	478.2	479.5	478.2	476.8	475.5
57.5°	445.0	439.8	442.4	443.7	443.7	439.8	442.4	439.8	439.8	441.1	437.1
60°	402.7	402.7	400.0	404.0	404.0	401.3	401.3	402.7	400.0	398.7	397.4
62.5°	357.6	359.0	362.9	364.3	365.6	362.9	360.3	361.6	361.6	357.6	359.0
65°	319.2	321.9	327.2	325.8	323.2	324.5	321.9	323.2	319.2	320.5	316.6
67.5°	282.1	280.8	282.1	282.1	284.8	283.5	280.8	280.8	279.5	283.5	279.5
70°	242.4	242.4	242.4	242.4	243.7	245.0	242.4	239.7	241.1	238.4	237.1
72.5°	201.3	202.7	201.3	204.0	200.0	202.7	202.7	201.3	200.0	200.0	200.0
75°	162.9	165.6	161.6	162.9	161.6	164.2	162.9	162.9	160.3	158.9	160.3
77.5°	124.5	125.8	123.2	124.5	123.2	124.5	124.5	123.2	123.2	123.2	123.2
80°	88.7	90.1	88.7	87.4	86.1	88.7	86.1	87.4	88.7	87.4	90.1
82.5°	57.0	57.0	55.6	57.0	54.3	54.3	55.6	55.6	54.3	57.0	54.3
85°	27.8	27.8	30.5	27.8	26.5	26.5	26.5	27.8	26.5	29.1	27.8
87.5°	6.6	5.3	6.6	6.6	5.3	5.3	6.6	5.3	6.6	7.9	5.3
90°	22.7	22.9	23.3	23.7	24.1	24.5	24.1	23.7	23.3	22.9	22.7
92.5°	23.6	23.7	23.9	24.1	24.3	24.5	24.3	24.1	23.9	23.7	23.6
95°	40.0	39.9	39.7	39.4	39.2	39.0	39.2	39.4	39.7	39.9	40.0
97.5°	49.0	49.1	49.3	49.5	49.7	49.9	49.7	49.5	49.3	49.1	49.0
100°	59.0	59.2	59.6	60.0	60.4	60.8	60.4	60.0	59.6	59.2	59.0
102.5°	63.6	63.9	64.5	65.1	65.7	66.3	65.7	65.1	64.5	63.9	63.6
105°	65.4	65.8	66.6	67.4	68.2	69.0	68.2	67.4	66.6	65.8	65.4
107.5°	67.2	67.6	68.4	69.2	70.0	70.8	70.0	69.2	68.4	67.6	67.2
110°	68.1	68.5	69.3	70.1	70.9	71.7	70.9	70.1	69.3	68.5	68.1

TEST NUMBER: P999220

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	69.9	70.2	70.8	71.4	72.0	72.6	72.0	71.4	70.8	70.2	69.9
115°	139.8	132.5	118.0	103.5	89.0	74.5	89.0	103.5	118.0	132.5	139.8
117.5°	479.4	453.0	400.1	347.2	294.4	241.5	294.4	347.2	400.1	453.0	479.4
120°	676.5	662.9	635.6	608.4	581.1	553.9	581.1	608.4	635.6	662.9	676.5
122.5°	724.6	724.7	724.9	725.1	725.3	725.5	725.3	725.1	724.9	724.7	724.6
125°	773.6	773.9	774.5	775.1	775.7	776.3	775.7	775.1	774.5	773.9	773.6
127.5°	820.8	820.9	821.1	821.3	821.5	821.7	821.5	821.3	821.1	820.9	820.8
130°	864.4	864.3	864.1	863.9	863.7	863.5	863.7	863.9	864.1	864.3	864.4
132.5°	905.3	905.2	905.0	904.8	904.6	904.4	904.6	904.8	905.0	905.2	905.3
135°	945.2	945.0	944.6	944.2	943.8	943.4	943.8	944.2	944.6	945.0	945.2
137.5°	982.5	982.2	981.6	980.9	980.3	979.7	980.3	980.9	981.6	982.2	982.5
140°	1017.9	1017.4	1016.4	1015.3	1014.3	1013.3	1014.3	1015.3	1016.4	1017.4	1017.9
142.5°	1050.6	1050.1	1049.1	1048.0	1047.0	1046.0	1047.0	1048.0	1049.1	1050.1	1050.6
145°	1080.5	1080.0	1079.0	1078.0	1077.0	1076.0	1077.0	1078.0	1079.0	1080.0	1080.5
147.5°	1106.9	1106.5	1105.7	1104.8	1104.0	1103.2	1104.0	1104.8	1105.7	1106.5	1106.9
150°	1132.3	1131.8	1130.8	1129.7	1128.7	1127.7	1128.7	1129.7	1130.8	1131.8	1132.3
152.5°	1155.0	1154.3	1152.9	1151.4	1150.0	1148.6	1150.0	1151.4	1152.9	1154.3	1155.0
155°	1175.0	1174.2	1172.6	1170.9	1169.3	1167.7	1169.3	1170.9	1172.6	1174.2	1175.0
157.5°	1193.1	1192.3	1190.7	1189.0	1187.4	1185.8	1187.4	1189.0	1190.7	1192.3	1193.1
160°	1207.6	1206.9	1205.5	1204.1	1202.7	1201.3	1202.7	1204.1	1205.5	1206.9	1207.6
162.5°	1222.2	1221.3	1219.5	1217.6	1215.8	1214.0	1215.8	1217.6	1219.5	1221.3	1222.2
165°	1233.1	1232.4	1231.0	1229.5	1228.1	1226.7	1228.1	1229.5	1231.0	1232.4	1233.1
167.5°	1243.1	1242.2	1240.4	1238.5	1236.7	1234.9	1236.7	1238.5	1240.4	1242.2	1243.1
170°	1250.3	1249.4	1247.6	1245.7	1243.9	1242.1	1243.9	1245.7	1247.6	1249.4	1250.3
172.5°	1255.8	1254.9	1253.1	1251.2	1249.4	1247.6	1249.4	1251.2	1253.1	1254.9	1255.8
175°	1259.4	1258.4	1256.4	1254.3	1252.3	1250.3	1252.3	1254.3	1256.4	1258.4	1259.4
177.5°	1260.3	1259.4	1257.6	1255.7	1253.9	1252.1	1253.9	1255.7	1257.6	1259.4	1260.3
180°	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9

TEST NUMBER: P999220

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2	1723.2
2.5°	1635.8	1646.4	1642.4	1627.9	1645.1	1645.1	1657.0	1657.0	1671.6	1676.9	1684.8
5°	1543.1	1551.1	1557.7	1551.1	1563.0	1581.5	1592.1	1601.4	1621.3	1629.2	1641.1
7.5°	1443.8	1458.3	1465.0	1465.0	1484.8	1506.0	1527.2	1540.5	1568.3	1578.9	1590.8
10°	1347.1	1364.3	1377.5	1376.2	1409.3	1422.6	1449.1	1479.5	1507.3	1523.2	1540.5
12.5°	1245.1	1254.4	1272.9	1299.4	1307.3	1331.2	1361.6	1400.1	1450.4	1465.0	1490.1
15°	1160.3	1185.5	1200.0	1212.0	1230.5	1253.0	1286.1	1323.2	1373.6	1405.4	1431.8
17.5°	1088.8	1121.9	1131.2	1128.5	1152.4	1186.8	1225.2	1253.0	1298.1	1336.5	1361.6
20°	1030.5	1043.7	1059.6	1066.3	1084.8	1121.9	1159.0	1190.8	1227.9	1258.3	1287.5
22.5°	972.2	982.8	996.1	1008.0	1022.6	1043.7	1079.5	1119.2	1155.0	1184.2	1217.3
25°	924.5	931.2	943.1	952.4	968.2	982.8	1008.0	1051.7	1094.1	1111.3	1140.4
27.5°	878.2	883.5	891.4	902.0	910.0	924.5	947.1	982.8	1026.5	1043.7	1083.5
30°	837.1	841.1	849.0	854.3	858.3	875.5	892.7	920.6	953.7	977.5	1006.7
32.5°	798.7	802.7	810.6	812.0	817.2	826.5	842.4	867.6	896.7	916.6	941.8
35°	756.3	759.0	766.9	769.6	773.5	781.5	793.4	812.0	838.4	853.0	875.5
37.5°	723.2	721.9	727.2	731.2	736.5	740.4	744.4	762.9	782.8	796.1	813.3
40°	687.4	684.8	686.1	691.4	694.1	699.4	699.4	717.9	731.2	741.7	755.0
42.5°	651.7	650.4	647.7	650.4	653.0	654.3	655.7	668.9	682.1	691.4	706.0
45°	615.9	614.6	611.9	613.3	613.3	615.9	619.9	625.2	634.5	642.4	650.4
47.5°	582.8	580.2	576.2	574.9	577.5	577.5	577.5	582.8	592.1	594.7	602.7
50°	548.4	544.4	539.1	536.4	536.4	535.1	537.8	539.1	547.0	549.7	556.3
52.5°	511.3	508.6	503.3	498.0	499.4	496.7	498.0	499.4	502.0	506.0	510.0
55°	474.2	468.9	464.9	463.6	459.6	459.6	455.6	460.9	459.6	460.9	466.2
57.5°	438.4	433.1	426.5	423.9	419.9	418.6	415.9	414.6	415.9	419.9	423.9
60°	396.0	393.4	389.4	385.4	382.8	378.8	376.2	376.2	374.8	374.8	376.2
62.5°	355.0	353.7	348.4	347.0	344.4	341.7	337.8	335.1	335.1	337.8	339.1
65°	315.2	313.9	309.9	308.6	302.0	299.3	298.0	296.7	294.1	294.1	294.1
67.5°	278.2	274.2	274.2	267.6	262.3	259.6	257.0	255.6	255.6	255.6	257.0
70°	237.1	237.1	233.1	229.1	223.8	225.2	221.2	217.2	217.2	214.6	215.9
72.5°	197.4	196.0	192.1	190.7	186.8	182.8	180.1	182.8	178.8	177.5	178.8
75°	158.9	157.6	155.0	152.3	153.6	149.7	145.7	144.4	144.4	141.7	141.7
77.5°	121.9	124.5	119.2	117.9	115.2	112.6	111.3	109.9	109.9	109.9	112.6
80°	84.8	86.1	86.1	83.4	84.8	80.8	80.8	80.8	76.8	78.1	79.5
82.5°	54.3	54.3	53.0	54.3	53.0	53.0	51.7	51.7	50.3	50.3	51.7
85°	30.5	29.1	27.8	30.5	29.1	29.1	27.8	27.8	27.8	27.8	27.8
87.5°	6.6	7.9	7.9	7.9	7.9	9.3	9.3	9.3	10.6	10.6	10.6
90°	22.2	21.2	20.2	19.2	18.2	16.6	15.0	13.3	11.7	10.9	9.8
92.5°	23.4	23.0	22.6	22.2	21.8	21.2	20.6	20.0	19.4	19.1	19.5
95°	39.5	38.5	37.4	36.4	35.4	34.0	32.6	31.2	29.8	29.1	32.4
97.5°	48.7	48.1	47.5	46.9	46.3	43.1	39.9	36.6	33.4	31.8	40.1
100°	58.2	56.6	55.0	53.4	51.8	48.4	44.9	41.5	38.0	36.3	50.1
102.5°	62.5	60.3	58.0	55.8	53.6	50.3	47.0	43.7	40.4	38.8	53.0
105°	64.3	62.1	59.8	57.6	55.4	52.2	49.0	45.8	42.6	40.4	55.8
107.5°	66.1	63.9	61.6	59.4	57.2	54.0	50.8	47.6	44.4	42.2	58.6
110°	78.2	98.4	118.5	138.7	158.9	217.2	275.5	333.8	392.1	421.3	419.2

TEST NUMBER: P999220

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	113.4	200.4	287.3	374.3	461.3	464.7	468.1	471.6	475.0	476.7	474.9
115°	186.5	279.9	373.4	466.8	560.2	555.2	550.1	545.1	540.0	537.5	535.8
117.5°	493.8	522.7	551.6	580.4	609.3	605.9	602.4	599.0	595.5	593.8	591.8
120°	675.3	672.9	670.4	668.0	665.6	662.0	658.3	654.7	651.0	649.2	647.7
122.5°	724.0	722.8	721.5	720.3	719.1	715.1	711.1	707.0	703.0	701.0	699.4
125°	772.9	771.5	770.1	768.7	767.3	763.5	759.6	755.8	751.9	750.0	748.7
127.5°	819.8	817.8	815.8	813.8	811.8	808.8	805.7	802.7	799.6	798.1	796.7
130°	863.3	861.1	858.8	856.6	854.4	852.2	850.0	847.7	845.5	844.4	842.8
132.5°	904.4	902.6	900.7	898.9	897.1	894.9	892.7	890.4	888.2	887.1	885.8
135°	944.2	942.2	940.1	938.1	936.1	934.3	932.5	930.7	928.9	928.0	926.4
137.5°	981.5	979.5	977.4	975.4	973.4	971.4	969.4	967.3	965.3	964.3	963.1
140°	1017.0	1015.2	1013.3	1011.5	1009.7	1007.5	1005.3	1003.0	1000.8	999.7	998.9
142.5°	1049.8	1048.2	1046.5	1044.9	1043.3	1040.7	1038.1	1035.4	1032.8	1031.5	1030.8
145°	1079.8	1078.4	1077.0	1075.6	1074.2	1070.8	1067.3	1063.9	1060.4	1058.7	1058.8
147.5°	1106.4	1105.4	1104.3	1103.3	1102.3	1098.9	1095.5	1092.0	1088.6	1086.9	1087.2
150°	1131.7	1130.5	1129.2	1128.0	1126.8	1123.6	1120.4	1117.1	1113.9	1112.3	1113.0
152.5°	1154.4	1153.2	1151.9	1150.7	1149.5	1146.5	1143.5	1140.4	1137.4	1135.9	1136.7
155°	1174.4	1173.2	1171.9	1170.7	1169.5	1167.1	1164.7	1162.2	1159.8	1158.6	1159.5
157.5°	1192.4	1191.0	1189.6	1188.2	1186.8	1185.0	1183.2	1181.3	1179.5	1178.6	1179.4
160°	1207.0	1205.8	1204.6	1203.4	1202.2	1201.0	1199.8	1198.5	1197.3	1196.7	1197.3
162.5°	1221.5	1220.1	1218.6	1217.2	1215.8	1214.8	1213.8	1212.8	1211.8	1211.3	1211.9
165°	1232.4	1231.0	1229.5	1228.1	1226.7	1226.1	1225.5	1224.9	1224.3	1224.0	1224.6
167.5°	1242.4	1241.0	1239.5	1238.1	1236.7	1236.1	1235.5	1234.9	1234.3	1234.0	1234.6
170°	1249.6	1248.2	1246.8	1245.4	1244.0	1243.6	1243.2	1242.7	1242.3	1242.1	1242.7
172.5°	1255.1	1253.7	1252.2	1250.8	1249.4	1249.0	1248.6	1248.2	1247.8	1247.6	1248.2
175°	1258.7	1257.3	1255.8	1254.4	1253.0	1252.6	1252.2	1251.8	1251.4	1251.2	1251.9
177.5°	1259.6	1258.2	1256.7	1255.3	1253.9	1253.7	1253.5	1253.3	1253.1	1253.0	1253.7
180°	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9	1254.9

TEST NUMBER: P999220

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1723.2	1723.2	1723.2	1723.2
2.5°	1691.5	1691.5	1711.3	1732.5
5°	1654.4	1663.6	1695.4	1724.6
7.5°	1618.6	1634.5	1674.2	1711.3
10°	1574.9	1596.1	1645.1	1688.8
12.5°	1532.5	1552.4	1609.3	1658.3
15°	1472.9	1498.1	1559.0	1619.9
17.5°	1413.3	1438.5	1512.6	1584.2
20°	1343.1	1376.2	1459.7	1555.0
22.5°	1278.2	1319.3	1412.0	1488.8
25°	1206.7	1270.2	1356.3	1455.7
27.5°	1143.1	1206.7	1294.1	1394.8
30°	1071.6	1136.5	1226.5	1319.3
32.5°	1002.7	1062.3	1149.7	1263.6
35°	931.2	988.1	1072.9	1188.1
37.5°	866.3	921.9	1014.6	1120.6
40°	802.7	861.0	940.4	1046.4
42.5°	743.1	794.7	866.3	972.2
45°	688.8	725.9	792.1	891.4
47.5°	631.8	664.9	725.9	825.2
50°	578.8	606.6	659.6	752.3
52.5°	527.2	551.0	600.0	674.2
55°	480.8	503.3	539.1	611.9
57.5°	433.1	450.3	484.8	543.1
60°	386.8	402.7	430.5	478.2
62.5°	340.4	353.7	380.1	418.6
65°	299.3	309.9	329.8	362.9
67.5°	259.6	266.2	282.1	308.6
70°	221.2	226.5	239.7	260.9
72.5°	180.1	185.4	200.0	214.6
75°	145.7	147.0	157.6	169.5
77.5°	113.9	112.6	120.5	129.8
80°	78.1	82.1	88.7	92.7
82.5°	53.0	54.3	57.0	59.6
85°	29.1	30.5	30.5	34.4
87.5°	11.9	13.2	13.2	14.6
90°	7.6	5.3	3.1	0.9
92.5°	20.3	21.1	21.9	22.7
95°	39.1	45.7	52.4	59.0
97.5°	56.6	73.1	89.7	106.2
100°	77.8	105.4	133.1	160.7
102.5°	219.4	219.8	220.2	220.6
105°	294.2	288.1	282.1	276.0
107.5°	355.6	350.6	345.5	340.5
110°	414.9	410.7	406.4	402.2

TEST NUMBER: P999220

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	471.3	467.6	464.0	460.4
115°	532.4	528.9	525.5	522.1
117.5°	587.8	583.7	579.7	575.7
120°	644.7	641.6	638.6	635.6
122.5°	696.1	692.9	689.6	686.4
125°	746.1	743.4	740.8	738.2
127.5°	793.9	791.0	788.2	785.4
130°	839.6	836.3	833.1	829.9
132.5°	883.2	880.5	877.9	875.3
135°	923.1	919.9	916.6	913.4
137.5°	960.7	958.2	955.8	953.4
140°	997.3	995.6	994.0	992.4
142.5°	1029.4	1027.9	1026.5	1025.1
145°	1059.0	1059.2	1059.4	1059.6
147.5°	1087.8	1088.4	1089.0	1089.6
150°	1114.4	1115.9	1117.3	1118.7
152.5°	1138.3	1140.0	1141.6	1143.2
155°	1161.3	1163.2	1165.0	1166.8
157.5°	1181.0	1182.6	1184.2	1185.8
160°	1198.5	1199.8	1201.0	1202.2
162.5°	1213.1	1214.3	1215.5	1216.7
165°	1225.8	1227.0	1228.2	1229.4
167.5°	1235.8	1237.0	1238.2	1239.4
170°	1243.9	1245.2	1246.4	1247.6
172.5°	1249.4	1250.6	1251.8	1253.0
175°	1253.3	1254.8	1256.2	1257.6
177.5°	1255.1	1256.6	1258.0	1259.4
180°	1254.9	1254.9	1254.9	1254.9

TEST NUMBER: P999220

CATALOG NUMBER: SA2XXDIP-B865D925UB2750-4F0-XX-W2A-A_3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.41	18.24	18.37	19.21	20.47	14.90	15.74	15.86	16.70	17.97
	3H	18.22	18.97	19.19	19.94	21.23	16.24	16.99	17.21	17.97	19.25
	4H	18.39	19.09	19.37	20.07	21.37	16.71	17.41	17.69	18.39	19.69
	6H	18.43	19.08	19.42	20.07	21.37	17.01	17.66	18.00	18.65	19.95
	8H	18.41	19.03	19.41	20.03	21.33	17.10	17.71	18.09	18.72	20.02
	12H	18.37	18.96	19.37	19.95	21.28	17.14	17.72	18.14	18.72	20.05
4H	2H	17.45	18.15	18.44	19.13	20.43	15.34	16.05	16.33	17.03	18.32
	3H	18.43	19.01	19.42	20.02	21.33	16.80	17.39	17.80	18.40	19.71
	4H	18.70	19.24	19.71	20.24	21.57	17.34	17.87	18.34	18.88	20.21
	6H	18.83	19.29	19.85	20.32	21.65	17.72	18.18	18.73	19.20	20.53
	8H	18.83	19.26	19.85	20.28	21.62	17.83	18.26	18.84	19.27	20.62
	12H	18.79	19.18	19.83	20.21	21.56	17.88	18.27	18.92	19.30	20.65
8H	4H	18.71	19.14	19.73	20.16	21.50	17.48	17.91	18.50	18.93	20.27
	6H	18.89	19.24	19.93	20.30	21.64	17.91	18.27	18.95	19.33	20.67
	8H	18.92	19.23	19.97	20.28	21.63	18.06	18.37	19.11	19.42	20.78
	12H	18.90	19.17	19.95	20.22	21.62	18.15	18.43	19.21	19.47	20.87
12H	4H	18.66	19.05	19.70	20.09	21.43	17.45	17.84	18.49	18.87	20.22
	6H	18.86	19.18	19.91	20.22	21.58	17.91	18.22	18.96	19.27	20.63
	8H	18.90	19.17	19.95	20.21	21.61	18.07	18.34	19.12	19.38	20.79