

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931109

Luminaire Tested: DFN2DS-SQ4F0-080DS927-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931109
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ4F0-080DS927-FLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6272.6 lumens
Efficiency: N/A
Efficacy: 79.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.92' x L: 3.92' x H: 0')
CIE Type: Direct

Input Watts (W): 79.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931109

CATALOG NUMBER: DFN2DS-SQ4F0-080DS927-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931109

CATALOG NUMBER: DFN2DS-SQ4F0-080DS927-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1730	1730	1730
5°	1736	1712	1722
10°	1726	1694	1703
15°	1705	1672	1671
20°	1674	1639	1638
25°	1645	1599	1599
30°	1606	1562	1548
35°	1570	1517	1495
40°	1524	1472	1444
45°	1480	1428	1393
50°	1431	1382	1333
55°	1381	1328	1279
60°	1324	1264	1218
65°	1264	1201	1145
70°	1187	1123	1070
75°	1079	1035	1009
80°	958	929	881
85°	782	746	668

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1480 cd/sqm

TEST NUMBER: P931109

CATALOG NUMBER: DFN2DS-SQ4F0-080DS927-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.0	3.7
10°-20°	652.9	10.4
20°-30°	959.5	15.3
30°-40°	1114.4	17.8
40°-50°	1113.0	17.7
50°-60°	970.5	15.5
60°-70°	717.4	11.4
70°-80°	405.9	6.5
80°-90°	107.1	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1844.4	29.4
0°-40°	2958.8	47.2
0°-60°	5042.2	80.4
0°-90°	6272.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6272.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2465	2465	2465	2465	2465	
5°	2465	2456	2430	2449	2444	234
15°	2347	2333	2302	2312	2300	661
25°	2124	2105	2065	2070	2065	977
35°	1832	1809	1771	1757	1745	1144
45°	1491	1475	1439	1413	1404	1151
55°	1128	1114	1086	1057	1046	1009
65°	761	747	723	702	690	752
75°	398	394	382	368	372	425
85°	97	95	93	85	83	114
90°	0	0	0	0	0	

TEST NUMBER: P931109

CATALOG NUMBER: DFN2DS-SQ4F0-080DS927-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2465.3	2465.3	2465.3	2465.3	2465.3
2.5°	2479.7	2467.9	2441.7	2465.3	2460.8
5°	2465.3	2456.1	2429.9	2448.8	2444.3
7.5°	2448.8	2434.7	2408.6	2427.6	2422.9
10°	2422.9	2406.3	2377.8	2396.7	2389.7
12.5°	2387.2	2373.1	2344.6	2356.4	2351.7
15°	2346.9	2332.8	2301.9	2311.5	2299.7
17.5°	2297.1	2283.0	2252.1	2263.9	2252.1
20°	2242.5	2228.5	2195.3	2202.3	2193.0
22.5°	2188.2	2166.8	2135.9	2135.9	2131.1
25°	2124.1	2105.2	2065.0	2069.5	2065.0
27.5°	2052.9	2036.3	2005.6	1998.5	1986.7
30°	1982.0	1962.8	1927.4	1920.4	1910.8
32.5°	1906.0	1891.9	1853.9	1839.6	1830.1
35°	1832.5	1808.9	1770.9	1756.6	1744.8
37.5°	1749.5	1728.1	1690.2	1673.6	1661.8
40°	1664.3	1645.1	1607.2	1586.1	1576.5
42.5°	1581.3	1562.1	1524.4	1500.5	1486.5
45°	1491.3	1474.6	1438.9	1413.0	1403.5
47.5°	1403.5	1386.9	1348.9	1322.7	1308.6
50°	1310.9	1299.1	1265.9	1232.7	1220.9
52.5°	1220.9	1204.2	1173.6	1147.4	1130.8
55°	1128.5	1114.2	1085.8	1057.4	1045.5
57.5°	1036.0	1024.2	993.2	964.8	955.2
60°	943.4	934.2	900.9	874.8	867.7
62.5°	853.4	836.8	813.1	789.5	780.0
65°	761.1	746.8	723.1	701.7	689.9
67.5°	666.2	654.2	633.0	616.5	606.9
70°	578.5	568.9	547.6	531.0	521.6
72.5°	488.4	478.9	467.0	450.5	443.4
75°	398.1	393.6	381.6	367.5	372.2
77.5°	317.7	308.1	303.3	296.3	289.2
80°	237.2	234.7	229.9	222.9	218.0
82.5°	161.3	161.3	159.0	149.4	149.4
85°	97.1	94.8	92.6	85.3	83.0
87.5°	42.8	38.0	33.2	26.1	23.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931109

CATALOG NUMBER: DFN2DS-SQ4F0-080DS927-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.19	14.80	13.55	15.11	15.43	12.74	14.35	13.11	14.67	14.98
	3H	14.94	16.39	15.31	16.72	17.08	14.45	15.90	14.82	16.23	16.59
	4H	15.58	16.95	15.98	17.30	17.68	15.09	16.46	15.49	16.81	17.18
	6H	16.05	17.32	16.46	17.69	18.08	15.55	16.82	15.96	17.18	17.57
	8H	16.20	17.41	16.62	17.80	18.19	15.69	16.90	16.12	17.29	17.69
	12H	16.29	17.45	16.72	17.83	18.26	15.77	16.93	16.20	17.31	17.74
4H	2H	13.75	15.12	14.15	15.46	15.84	13.39	14.76	13.79	15.11	15.49
	3H	15.72	16.87	16.13	17.27	17.67	15.32	16.46	15.73	16.86	17.26
	4H	16.50	17.53	16.93	17.95	18.38	16.07	17.11	16.51	17.52	17.96
	6H	17.10	18.00	17.55	18.44	18.90	16.66	17.57	17.12	18.01	18.46
	8H	17.28	18.13	17.75	18.57	19.04	16.85	17.69	17.31	18.14	18.60
	12H	17.42	18.18	17.90	18.65	19.12	16.96	17.72	17.44	18.20	18.67
8H	4H	16.77	17.62	17.23	18.06	18.53	16.40	17.24	16.86	17.69	18.15
	6H	17.49	18.19	17.98	18.68	19.15	17.10	17.81	17.60	18.30	18.77
	8H	17.75	18.38	18.26	18.88	19.37	17.35	17.98	17.86	18.49	18.98
	12H	17.95	18.50	18.45	18.99	19.56	17.53	18.09	18.04	18.58	19.14
12H	4H	16.80	17.56	17.28	18.03	18.50	16.43	17.19	16.91	17.67	18.14
	6H	17.53	18.16	18.04	18.67	19.16	17.16	17.80	17.67	18.30	18.79
	8H	17.85	18.40	18.35	18.89	19.46	17.47	18.03	17.97	18.52	19.08