

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332320-927

Luminaire Tested: **S123RDIP-S775D1025U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332320-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D1025U927-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5354.2 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332320-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot



TEST NUMBER: P332320-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	93	89	86	89	86	82	80	71	69	67	58	57	56	46	45	45
2	89	82	76	71	81	75	70	66	63	60	56	52	49	47	41	40	38
3	81	72	65	60	74	67	61	56	56	52	48	46	43	41	37	35	33
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	30	28	26
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	20
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	18
9	51	39	32	27	47	36	30	25	31	26	22	26	22	20	22	19	17
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10428	10428	10428	10428
5°	12431	10472	9223	10472
10°	15522	10413	8332	10413
15°	18219	10307	7598	10307
20°	20333	10148	6975	10148
25°	20009	9980	6590	9980
30°	14382	9825	6196	9825
35°	9603	9625	5941	9625
40°	7075	9382	5675	9382
45°	5934	8958	5416	8958
50°	5238	8403	5056	8403
55°	4592	7767	4560	7767
60°	4090	7160	4179	7160
65°	3591	6507	3889	6507
70°	2820	5926	3550	5926
75°	2483	5178	3244	5178
80°	2163	4395	3186	4395
85°	1741	3532	3384	3532

TEST NUMBER: P332320-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.3	1.8
10°-20°	297.7	5.6
20°-30°	467.6	8.7
30°-40°	487.9	9.1
40°-50°	417.5	7.8
50°-60°	318.2	5.9
60°-70°	204.0	3.8
70°-80°	98.1	1.8
80°-90°	29.0	0.5
90°-100°	217.4	4.1
100°-110°	615.6	11.5
110°-120°	605.5	11.3
120°-130°	483.0	9.0
130°-140°	380.8	7.1
140°-150°	284.2	5.3
150°-160°	198.1	3.7
160°-170°	116.4	2.2
170°-180°	37.9	0.7
0°-30°	860.6	16.1
0°-40°	1348.4	25.2
0°-60°	2084.2	38.9
0°-90°	2415.3	45.1
90°-120°	1438.5	26.9
90°-150°	2586.5	48.3
90°-180°	2939.0	54.9
0°-180°	5354.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	969	969	969	969	969	
5°	1150	969	854	969	1150	119
15°	1635	925	682	925	1635	464
25°	1685	840	555	840	1685	724
35°	731	732	452	732	731	479
45°	390	588	356	588	390	307
55°	245	414	243	414	245	221
65°	141	256	153	256	141	139
75°	60	124	78	124	60	64
85°	14	29	27	29	14	17
90°	23	2	23	2	23	13
95°	92	27	92	27	92	165
105°	1006	92	1006	92	1006	992
115°	1223	162	1223	162	1223	1189
125°	965	225	965	225	965	874
135°	782	264	782	264	782	607
145°	611	301	611	301	611	389
155°	507	342	507	342	507	236
165°	442	374	442	374	442	126
175°	398	390	398	390	398	39
180°	391	391	391	391	391	

TEST NUMBER: P332320-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1031.9	1033.2	1028.9	1028.3	1023.3	1021.9	1021.9	1014.9	1010.7	1005.0	1001.7
5°	1150.5	1157.1	1153.8	1146.4	1133.9	1131.0	1123.2	1110.7	1096.6	1079.2	1070.9
7.5°	1298.6	1307.7	1304.2	1292.7	1279.7	1269.2	1246.9	1226.2	1197.3	1171.9	1150.2
10°	1420.1	1410.6	1403.1	1391.9	1379.9	1360.3	1337.1	1305.2	1268.3	1239.3	1206.9
12.5°	1511.0	1509.4	1500.0	1488.4	1471.5	1452.9	1424.4	1385.5	1342.6	1300.7	1263.7
15°	1634.9	1637.4	1631.2	1619.1	1595.1	1562.3	1519.2	1503.0	1441.7	1396.1	1350.4
17.5°	1720.7	1720.2	1719.4	1702.7	1678.2	1654.9	1614.9	1572.3	1516.7	1452.5	1391.0
20°	1775.1	1771.0	1771.8	1753.1	1734.9	1707.9	1669.0	1607.2	1561.5	1487.3	1423.8
22.5°	1773.8	1773.0	1776.2	1769.7	1756.4	1735.8	1705.1	1653.0	1594.7	1519.8	1448.3
25°	1684.7	1681.4	1700.9	1706.3	1727.4	1731.2	1722.0	1693.4	1638.2	1561.1	1472.7
27.5°	1410.0	1408.2	1444.3	1489.6	1547.0	1591.7	1634.7	1655.6	1638.2	1583.0	1494.5
30°	1157.1	1196.1	1214.4	1279.9	1352.9	1440.0	1516.3	1588.9	1606.7	1582.7	1510.1
32.5°	960.8	994.7	1010.0	1066.2	1134.2	1236.3	1350.8	1453.5	1526.1	1544.5	1500.8
35°	730.8	731.2	766.0	790.9	854.0	958.9	1070.1	1207.8	1344.6	1448.3	1459.0
37.5°	583.1	585.2	606.3	631.1	678.3	733.9	831.7	946.2	1104.3	1263.5	1356.8
40°	503.5	507.2	523.0	547.5	581.5	623.4	699.7	807.6	939.4	1116.5	1261.2
42.5°	452.4	458.4	466.6	485.4	506.5	545.7	607.4	690.7	810.6	978.1	1145.1
45°	389.8	393.2	399.4	408.1	427.2	454.6	496.1	552.0	651.6	786.4	953.5
47.5°	343.9	342.1	348.7	355.8	368.4	387.1	414.9	460.7	531.6	639.8	781.6
50°	312.8	312.3	316.9	322.3	334.3	348.0	370.8	405.2	461.6	551.2	681.0
52.5°	283.5	285.1	288.4	295.1	303.7	314.8	335.3	360.0	408.5	485.8	594.1
55°	244.7	246.0	250.5	254.2	260.5	271.6	284.6	305.2	338.4	392.4	481.5
57.5°	211.8	211.3	215.6	216.6	223.6	232.7	242.7	258.8	282.9	322.9	382.9
60°	190.0	188.7	192.4	195.4	199.1	206.5	214.8	230.6	249.7	279.1	330.6
62.5°	170.1	169.4	172.2	175.1	178.2	185.0	191.9	204.1	219.1	244.0	284.8
65°	141.0	142.3	143.5	144.7	146.4	150.5	157.2	165.5	175.9	193.3	222.7
67.5°	110.8	112.1	112.5	115.0	118.6	121.2	125.2	132.6	139.8	154.6	171.3
70°	89.6	89.2	89.6	90.9	95.4	100.0	105.4	110.7	115.3	125.6	139.7
72.5°	77.0	76.2	77.3	77.6	79.8	81.0	84.4	89.5	95.4	102.4	112.6
75°	59.7	59.7	59.7	59.7	61.4	62.2	63.5	64.7	66.8	70.1	77.6
77.5°	44.1	44.2	44.8	45.2	45.6	46.0	46.8	48.0	48.8	50.5	53.8
80°	34.9	35.3	34.9	35.3	35.3	36.0	36.5	37.7	38.2	40.2	41.5
82.5°	26.2	26.0	26.2	26.6	26.6	27.5	27.6	28.4	28.5	29.6	30.9
85°	14.1	13.3	14.1	13.7	14.5	13.7	14.1	14.9	14.9	15.4	17.0
87.5°	7.9	8.7	7.9	8.1	8.2	8.2	8.1	7.9	8.5	8.2	8.2
90°	22.9	23.7	22.9	22.1	22.9	21.4	20.6	19.8	19.0	19.8	17.4
92.5°	38.1	39.5	38.7	41.1	42.5	46.7	52.8	66.5	91.7	121.6	133.8
95°	91.7	94.9	100.4	107.6	122.6	151.1	193.0	284.6	380.3	468.9	417.5
97.5°	249.7	256.5	277.9	313.5	371.8	466.4	568.4	709.6	777.4	726.7	532.0
100°	495.8	495.0	525.9	583.6	663.5	775.7	868.2	932.3	904.6	748.8	506.0
102.5°	727.3	745.5	771.3	817.0	879.2	950.3	1004.2	1006.3	910.9	707.7	468.1
105°	1005.8	1009.8	1035.1	1065.1	1101.5	1122.0	1107.1	1027.9	862.7	635.7	421.4
107.5°	1166.2	1173.5	1182.0	1192.2	1191.5	1163.3	1094.1	965.7	778.2	572.2	391.7
110°	1232.0	1233.6	1235.2	1228.8	1206.7	1151.3	1051.7	906.2	725.1	536.1	380.3

TEST NUMBER: P332320-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1245.2	1244.9	1238.9	1219.3	1178.8	1107.6	996.0	847.3	678.9	512.1	374.0
115°	1223.3	1219.3	1203.5	1168.7	1109.4	1023.2	907.0	769.4	623.1	486.3	371.6
117.5°	1153.3	1148.0	1125.2	1085.4	1023.5	936.0	831.7	713.0	589.4	471.1	373.0
120°	1095.2	1090.4	1071.4	1027.1	964.7	884.9	790.0	683.2	571.7	464.1	375.6
122.5°	1040.8	1034.7	1013.9	974.1	918.5	844.4	756.5	659.8	557.1	459.7	380.0
125°	964.7	959.2	939.4	904.6	854.0	790.8	714.9	628.7	538.5	453.9	386.7
127.5°	902.1	897.0	879.2	849.4	804.3	746.8	678.3	601.4	522.0	451.1	394.3
130°	866.6	860.3	843.8	815.2	773.3	719.5	655.5	584.4	513.2	449.2	399.3
132.5°	831.9	827.4	812.7	784.3	744.9	693.6	634.0	568.5	504.9	448.5	403.1
135°	782.0	776.5	762.2	738.6	699.8	654.7	603.3	547.2	494.2	447.6	408.8
137.5°	729.4	725.7	713.8	689.7	657.1	618.1	573.8	527.8	484.9	445.8	412.6
140°	692.7	693.5	680.8	658.7	628.7	594.6	556.7	516.3	479.2	445.2	415.1
142.5°	658.5	659.3	647.9	628.4	602.7	573.1	540.3	505.6	474.1	443.9	417.0
145°	611.2	609.7	603.3	586.7	567.0	544.0	518.7	492.7	467.3	442.0	418.3
147.5°	572.4	571.7	565.7	554.4	539.5	523.2	502.7	482.0	460.7	439.0	418.3
150°	549.5	549.5	544.8	536.1	524.3	509.2	492.7	474.4	456.2	436.5	418.3
152.5°	530.6	530.6	527.8	519.7	510.3	497.9	483.2	467.5	451.2	433.3	416.4
155°	506.8	506.0	504.5	498.2	491.1	481.6	469.7	457.0	443.6	427.8	414.3
157.5°	485.2	485.4	484.1	479.3	473.2	465.7	456.5	446.0	435.1	422.9	411.7
160°	471.3	472.1	472.1	467.3	461.8	456.2	448.4	439.7	429.4	419.1	410.4
162.5°	458.6	459.4	459.4	455.3	451.7	446.8	439.5	432.1	423.7	415.3	407.9
165°	442.0	442.0	442.8	439.7	436.5	432.5	427.0	422.2	415.9	409.6	404.1
167.5°	426.2	426.2	427.0	424.8	423.3	420.5	417.3	413.7	408.5	403.9	400.3
170°	416.7	416.7	417.5	415.9	415.1	413.5	410.4	408.1	404.1	400.1	397.8
172.5°	407.9	408.5	410.0	408.4	408.2	407.3	404.7	403.0	399.7	397.0	395.9
175°	397.8	398.5	399.3	398.5	398.5	398.5	397.0	396.2	394.6	393.0	393.0
177.5°	391.9	391.9	393.2	392.5	393.2	393.2	392.5	391.9	391.3	390.6	391.3
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6

TEST NUMBER: P332320-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1000.4	999.3	994.7	989.4	982.5	977.8	974.1	972.2	966.2	958.9	953.9
5°	1062.2	1049.7	1036.5	1020.3	1005.4	990.0	980.5	969.2	955.6	940.2	929.5
7.5°	1128.4	1104.0	1077.7	1050.6	1023.7	999.7	978.5	960.3	938.5	916.5	901.1
10°	1179.2	1143.4	1106.5	1068.8	1034.4	1002.0	977.2	952.7	926.5	901.3	882.2
12.5°	1225.3	1178.3	1135.8	1089.4	1045.4	1006.7	970.8	942.1	910.6	883.7	861.9
15°	1283.7	1235.6	1184.1	1113.6	1055.1	1006.2	962.7	924.9	886.8	853.6	832.4
17.5°	1338.2	1265.8	1196.7	1137.9	1061.9	1000.8	947.6	902.5	860.6	825.5	799.4
20°	1360.8	1290.7	1215.6	1140.6	1065.9	997.4	935.6	885.9	842.3	802.6	778.5
22.5°	1374.4	1295.0	1215.9	1135.3	1056.0	984.8	923.8	868.9	821.8	783.9	754.2
25°	1390.2	1295.7	1208.6	1128.9	1048.1	970.9	898.3	840.3	789.3	749.0	717.5
27.5°	1400.7	1289.4	1186.5	1098.0	1016.0	939.1	872.6	811.1	759.3	716.8	682.9
30°	1402.6	1284.4	1169.6	1073.8	990.4	919.9	849.4	790.5	735.8	690.5	659.0
32.5°	1405.3	1272.2	1146.7	1044.9	959.6	889.7	825.9	769.6	713.5	669.0	636.8
35°	1394.4	1265.4	1111.9	995.0	909.5	841.9	784.3	732.5	677.3	634.1	601.3
37.5°	1347.3	1238.4	1075.9	938.7	849.4	786.8	739.8	694.6	644.0	597.5	566.6
40°	1299.8	1211.9	1048.1	904.6	811.3	746.9	704.6	667.7	618.8	575.3	542.1
42.5°	1229.2	1175.8	1021.5	868.7	768.1	706.2	670.5	635.9	592.9	548.7	517.5
45°	1099.5	1106.5	967.2	811.7	708.4	646.2	612.6	588.5	550.4	513.9	482.0
47.5°	936.9	1002.8	903.4	750.8	645.4	587.0	557.7	536.7	511.0	475.2	446.0
50°	830.8	924.9	852.3	710.0	605.9	547.9	518.9	501.8	479.4	451.2	423.4
52.5°	732.8	834.0	790.6	664.6	563.2	510.1	481.7	467.7	449.9	423.3	398.2
55°	597.6	700.1	690.1	596.0	498.9	451.2	429.7	413.9	401.9	382.0	362.1
57.5°	483.5	580.6	585.7	519.7	442.4	395.2	376.7	364.8	357.0	341.9	323.5
60°	411.5	500.6	518.0	468.3	401.9	360.4	342.1	332.6	326.4	314.4	300.3
62.5°	351.7	427.6	447.3	411.5	363.1	324.2	310.0	300.8	296.5	286.1	273.7
65°	269.2	332.2	351.3	331.4	306.1	275.0	263.4	255.5	251.8	246.0	236.8
67.5°	202.4	248.3	269.3	255.2	246.1	226.5	219.0	214.8	211.5	207.6	199.9
70°	162.6	196.6	218.2	214.4	207.0	196.6	191.2	188.3	185.0	181.6	175.0
72.5°	130.7	154.2	174.4	176.3	170.2	168.0	163.3	162.1	160.1	156.1	152.5
75°	86.7	102.8	116.9	122.3	124.8	126.9	124.8	124.5	124.0	120.7	118.6
77.5°	56.8	65.5	74.4	83.6	87.5	90.3	91.0	92.5	91.4	89.7	88.6
80°	43.6	45.6	51.8	59.7	65.9	68.4	70.1	70.9	70.5	70.1	68.4
82.5°	31.6	33.4	36.3	41.8	47.1	51.2	52.2	52.0	52.9	53.2	51.8
85°	17.0	17.4	18.2	19.1	21.9	26.5	27.8	28.6	29.5	29.5	26.9
87.5°	8.3	7.5	7.7	7.4	8.1	7.9	9.6	10.9	11.6	10.5	11.0
90°	15.1	12.7	10.3	8.7	7.1	4.8	3.2	1.6	3.2	4.8	7.1
92.5°	100.4	66.4	45.7	34.0	27.3	21.2	14.6	9.8	14.6	21.2	27.3
95°	287.8	170.0	102.8	71.9	51.4	37.9	29.2	26.9	29.2	37.9	51.4
97.5°	315.8	183.0	118.7	85.4	65.1	53.5	46.7	45.9	46.7	53.5	65.1
100°	298.1	181.1	125.7	94.9	75.9	64.9	59.3	58.5	59.3	64.9	75.9
102.5°	282.9	183.6	134.0	105.7	88.6	78.1	73.2	71.8	73.2	78.1	88.6
105°	272.0	190.6	147.9	123.3	108.4	98.9	94.1	91.7	94.1	98.9	108.4
107.5°	271.2	203.5	166.0	143.3	129.2	119.9	115.3	112.9	115.3	119.9	129.2
110°	274.4	214.3	178.7	156.5	143.1	134.4	130.5	128.1	130.5	134.4	143.1

TEST NUMBER: P332320-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	280.7	225.1	192.0	170.5	157.0	148.4	144.4	142.0	144.4	148.4	157.0
115°	291.0	242.7	212.7	191.4	177.9	170.0	165.2	162.1	165.2	170.0	177.9
117.5°	304.6	261.6	231.9	212.1	197.0	189.8	185.8	182.2	185.8	189.8	197.0
120°	314.7	273.6	245.1	225.4	210.3	202.4	198.4	196.1	198.4	202.4	210.3
122.5°	324.2	286.2	258.4	237.4	223.0	214.4	210.5	208.1	210.5	214.4	223.0
125°	339.2	304.4	276.8	255.4	240.3	231.7	227.0	225.4	227.0	231.7	240.3
127.5°	351.6	320.3	293.5	272.2	255.6	246.7	240.8	238.5	240.8	246.7	255.6
130°	359.8	329.7	303.6	282.3	265.7	256.2	249.1	246.7	249.1	256.2	265.7
132.5°	367.4	337.9	312.5	291.8	275.2	263.8	256.0	253.0	256.0	263.8	275.2
135°	377.2	350.3	325.7	304.4	287.8	276.0	267.3	264.1	267.3	276.0	287.8
137.5°	384.4	358.9	335.3	315.5	299.0	286.4	277.9	274.6	277.9	286.4	299.0
140°	388.2	364.6	341.6	321.9	306.0	293.3	285.4	281.5	285.4	293.3	306.0
142.5°	392.1	369.0	346.7	328.1	312.4	301.0	292.4	289.1	292.4	301.0	312.4
145°	396.2	374.8	354.3	336.0	322.7	310.8	303.6	301.3	303.6	310.8	322.7
147.5°	398.7	379.5	360.8	345.2	332.2	322.0	315.1	313.6	315.1	322.0	332.2
150°	399.3	382.7	364.6	350.3	339.2	328.9	322.7	321.9	322.7	328.9	339.2
152.5°	400.6	384.6	369.0	355.4	345.5	336.5	330.2	330.0	330.2	336.5	345.5
155°	400.9	388.2	374.8	363.8	355.1	347.1	342.4	342.4	342.4	347.1	355.1
157.5°	401.7	390.3	379.5	371.0	363.6	356.6	352.8	352.2	352.8	356.6	363.6
160°	401.7	392.2	382.7	374.8	369.2	363.0	359.8	359.8	359.8	363.0	369.2
162.5°	401.1	392.8	384.6	378.0	373.0	368.0	365.5	365.5	365.5	368.0	373.0
165°	399.3	393.8	387.5	381.9	378.7	374.8	373.2	374.0	373.2	374.8	378.7
167.5°	398.1	393.6	389.0	385.6	383.3	380.3	379.5	380.5	379.5	380.3	383.3
170°	396.2	393.0	389.0	387.5	385.9	383.5	382.7	384.3	382.7	383.5	385.9
172.5°	395.5	393.0	389.7	388.7	387.8	386.0	385.9	386.8	385.9	386.0	387.8
175°	393.8	392.2	390.6	389.8	389.8	388.2	389.0	389.8	389.0	388.2	389.8
177.5°	392.5	391.3	390.6	390.6	390.6	390.0	390.6	391.3	390.6	390.0	390.6
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6

TEST NUMBER: P332320-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	952.3	947.9	945.0	938.3	934.0	929.4	924.7	927.7	927.4	927.0	927.0
5°	920.4	910.8	902.1	890.9	883.8	875.1	868.5	867.7	869.3	863.5	860.2
7.5°	888.7	875.6	863.2	850.9	837.8	827.4	820.8	817.7	813.5	809.9	806.2
10°	866.4	851.0	839.0	823.7	809.6	797.2	789.3	783.9	780.9	778.1	772.7
12.5°	843.5	828.5	813.2	795.8	782.4	767.9	762.1	756.0	750.4	747.2	739.8
15°	810.0	790.5	774.4	756.1	741.2	727.1	718.7	706.7	705.0	700.9	693.5
17.5°	776.4	755.3	732.9	719.5	702.6	687.9	675.3	671.2	659.3	654.9	648.4
20°	749.9	730.4	713.4	695.5	671.1	657.4	647.5	642.1	632.5	626.7	622.5
22.5°	727.0	707.2	687.5	666.7	646.5	631.1	623.8	615.4	610.3	602.1	597.6
25°	694.3	672.7	649.1	626.7	612.2	600.6	588.9	581.5	574.0	570.3	562.0
27.5°	656.3	633.7	611.6	594.7	576.9	565.4	554.8	548.2	539.2	533.0	528.4
30°	635.4	608.9	589.8	574.4	551.6	540.8	533.0	524.7	518.0	511.4	506.8
32.5°	611.2	586.9	568.9	549.9	532.3	520.6	510.4	503.1	497.4	491.2	486.6
35°	573.1	552.9	534.2	515.1	502.2	490.2	478.2	472.0	466.6	460.8	456.6
37.5°	538.8	519.8	502.1	484.0	468.1	458.3	448.6	443.9	436.6	432.7	428.4
40°	517.6	498.9	479.8	462.5	445.8	438.4	429.7	422.6	416.0	413.1	408.5
42.5°	494.4	475.7	459.6	440.8	427.3	417.2	409.1	401.4	396.4	392.2	389.6
45°	459.9	443.4	427.6	408.9	396.1	387.4	378.3	371.2	366.6	363.8	359.2
47.5°	426.5	410.0	394.0	377.6	365.2	355.3	346.2	341.3	335.2	331.6	328.6
50°	402.3	387.4	370.3	355.5	343.0	333.0	325.6	319.3	313.9	309.4	307.4
52.5°	380.1	364.2	349.4	335.6	322.4	311.2	304.4	297.8	293.7	288.5	286.1
55°	343.4	328.0	315.6	301.9	289.1	279.6	271.2	265.5	261.3	255.5	252.2
57.5°	309.0	295.2	280.4	268.5	255.2	247.2	240.3	232.4	227.4	222.8	219.6
60°	285.7	270.0	257.1	246.0	234.3	223.9	217.8	211.5	206.1	201.5	198.7
62.5°	261.6	247.8	235.6	223.4	212.8	203.7	196.5	191.3	186.6	183.6	180.8
65°	224.3	213.6	201.1	191.2	181.3	174.6	168.8	164.2	160.9	158.8	156.4
67.5°	190.2	179.7	168.9	159.1	152.5	147.4	143.6	139.7	138.0	135.4	133.7
70°	167.9	157.2	147.7	140.2	133.6	129.8	127.3	124.5	122.8	119.5	117.8
72.5°	143.8	135.9	129.0	122.9	117.6	114.2	111.1	107.5	104.9	101.2	99.6
75°	113.2	106.2	100.8	96.6	93.3	88.7	84.2	80.5	79.2	78.0	77.6
77.5°	83.9	79.4	75.5	72.0	67.9	64.6	63.5	62.7	62.4	61.8	61.8
80°	65.9	61.8	58.9	54.7	52.3	52.3	52.3	51.4	51.8	51.8	51.8
82.5°	49.0	45.2	43.6	42.1	41.7	42.0	42.0	42.1	41.9	42.5	42.2
85°	25.3	25.7	26.5	26.1	26.5	26.5	27.4	26.9	27.4	26.5	27.4
87.5°	11.0	12.4	13.2	13.9	14.7	14.9	15.1	15.2	15.7	15.8	16.2
90°	8.7	10.3	12.7	15.1	17.4	19.8	19.0	19.8	20.6	21.4	22.9
92.5°	34.0	45.7	66.4	100.4	133.8	121.6	91.7	66.5	52.8	46.7	42.5
95°	71.9	102.8	170.0	287.8	417.5	468.9	380.3	284.6	193.0	151.1	122.6
97.5°	85.4	118.7	183.0	315.8	532.0	726.7	777.4	709.6	568.4	466.4	371.8
100°	94.9	125.7	181.1	298.1	506.0	748.8	904.6	932.3	868.2	775.7	663.5
102.5°	105.7	134.0	183.6	282.9	468.1	707.7	910.9	1006.3	1004.2	950.3	879.2
105°	123.3	147.9	190.6	272.0	421.4	635.7	862.7	1027.9	1107.1	1122.0	1101.5
107.5°	143.3	166.0	203.5	271.2	391.7	572.2	778.2	965.7	1094.1	1163.3	1191.5
110°	156.5	178.7	214.3	274.4	380.3	536.1	725.1	906.2	1051.7	1151.3	1206.7

TEST NUMBER: P332320-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	170.5	192.0	225.1	280.7	374.0	512.1	678.9	847.3	996.0	1107.6	1178.8
115°	191.4	212.7	242.7	291.0	371.6	486.3	623.1	769.4	907.0	1023.2	1109.4
117.5°	212.1	231.9	261.6	304.6	373.0	471.1	589.4	713.0	831.7	936.0	1023.5
120°	225.4	245.1	273.6	314.7	375.6	464.1	571.7	683.2	790.0	884.9	964.7
122.5°	237.4	258.4	286.2	324.2	380.0	459.7	557.1	659.8	756.5	844.4	918.5
125°	255.4	276.8	304.4	339.2	386.7	453.9	538.5	628.7	714.9	790.8	854.0
127.5°	272.2	293.5	320.3	351.6	394.3	451.1	522.0	601.4	678.3	746.8	804.3
130°	282.3	303.6	329.7	359.8	399.3	449.2	513.2	584.4	655.5	719.5	773.3
132.5°	291.8	312.5	337.9	367.4	403.1	448.5	504.9	568.5	634.0	693.6	744.9
135°	304.4	325.7	350.3	377.2	408.8	447.6	494.2	547.2	603.3	654.7	699.8
137.5°	315.5	335.3	358.9	384.4	412.6	445.8	484.9	527.8	573.8	618.1	657.1
140°	321.9	341.6	364.6	388.2	415.1	445.2	479.2	516.3	556.7	594.6	628.7
142.5°	328.1	346.7	369.0	392.1	417.0	443.9	474.1	505.6	540.3	573.1	602.7
145°	336.0	354.3	374.8	396.2	418.3	442.0	467.3	492.7	518.7	544.0	567.0
147.5°	345.2	360.8	379.5	398.7	418.3	439.0	460.7	482.0	502.7	523.2	539.5
150°	350.3	364.6	382.7	399.3	418.3	436.5	456.2	474.4	492.7	509.2	524.3
152.5°	355.4	369.0	384.6	400.6	416.4	433.3	451.2	467.5	483.2	497.9	510.3
155°	363.8	374.8	388.2	400.9	414.3	427.8	443.6	457.0	469.7	481.6	491.1
157.5°	371.0	379.5	390.3	401.7	411.7	422.9	435.1	446.0	456.5	465.7	473.2
160°	374.8	382.7	392.2	401.7	410.4	419.1	429.4	439.7	448.4	456.2	461.8
162.5°	378.0	384.6	392.8	401.1	407.9	415.3	423.7	432.1	439.5	446.8	451.7
165°	381.9	387.5	393.8	399.3	404.1	409.6	415.9	422.2	427.0	432.5	436.5
167.5°	385.6	389.0	393.6	398.1	400.3	403.9	408.5	413.7	417.3	420.5	423.3
170°	387.5	389.0	393.0	396.2	397.8	400.1	404.1	408.1	410.4	413.5	415.1
172.5°	388.7	389.7	393.0	395.5	395.9	397.0	399.7	403.0	404.7	407.3	408.2
175°	389.8	390.6	392.2	393.8	393.0	393.0	394.6	396.2	397.0	398.5	398.5
177.5°	390.6	390.6	391.3	392.5	391.3	390.6	391.3	391.9	392.5	393.2	393.2
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6

TEST NUMBER: P332320-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	923.1	922.7	923.1	921.7	923.1	922.7	923.1	927.0	927.0	927.4	927.7
5°	859.0	858.5	857.3	853.6	857.3	858.5	859.0	860.2	863.5	869.3	867.7
7.5°	803.0	802.4	798.8	798.8	798.8	802.4	803.0	806.2	809.9	813.5	817.7
10°	769.8	770.2	765.2	762.3	765.2	770.2	769.8	772.7	778.1	780.9	783.9
12.5°	737.6	735.7	731.7	728.5	731.7	735.7	737.6	739.8	747.2	750.4	756.0
15°	695.1	690.9	681.0	681.8	681.0	690.9	695.1	693.5	700.9	705.0	706.7
17.5°	645.1	642.1	641.8	636.0	641.8	642.1	645.1	648.4	654.9	659.3	671.2
20°	615.9	613.9	614.7	608.9	614.7	613.9	615.9	622.5	626.7	632.5	642.1
22.5°	593.0	591.0	587.5	585.7	587.5	591.0	593.0	597.6	602.1	610.3	615.4
25°	559.5	556.2	552.9	554.9	552.9	556.2	559.5	562.0	570.3	574.0	581.5
27.5°	526.0	523.5	520.1	519.8	520.1	523.5	526.0	528.4	533.0	539.2	548.2
30°	504.8	502.2	500.6	498.5	500.6	502.2	504.8	506.8	511.4	518.0	524.7
32.5°	483.2	482.7	479.7	479.3	479.7	482.7	483.2	486.6	491.2	497.4	503.1
35°	455.0	452.5	451.6	452.1	451.6	452.5	455.0	456.6	460.8	466.6	472.0
37.5°	428.2	424.8	423.3	421.9	423.3	424.8	428.2	428.4	432.7	436.6	443.9
40°	408.9	405.6	404.8	403.9	404.8	405.6	408.9	408.5	413.1	416.0	422.6
42.5°	387.4	386.0	385.6	384.0	385.6	386.0	387.4	389.6	392.2	396.4	401.4
45°	357.9	357.5	355.1	355.8	355.1	357.5	357.9	359.2	363.8	366.6	371.2
47.5°	326.9	325.1	323.4	324.5	323.4	325.1	326.9	328.6	331.6	335.2	341.3
50°	305.7	304.8	301.1	301.9	301.1	304.8	305.7	307.4	309.4	313.9	319.3
52.5°	284.5	281.3	279.9	279.4	279.9	281.3	284.5	286.1	288.5	293.7	297.8
55°	249.3	245.5	243.8	243.0	243.8	245.5	249.3	252.2	255.5	261.3	265.5
57.5°	214.8	213.7	212.5	213.3	212.5	213.7	214.8	219.6	222.8	227.4	232.4
60°	194.5	194.5	194.5	194.1	194.5	194.5	194.5	198.7	201.5	206.1	211.5
62.5°	179.0	177.9	177.6	178.2	177.6	177.9	179.0	180.8	183.6	186.6	191.3
65°	155.1	154.7	153.0	152.7	153.0	154.7	155.1	156.4	158.8	160.9	164.2
67.5°	132.6	131.1	130.6	130.1	130.6	131.1	132.6	133.7	135.4	138.0	139.7
70°	115.7	114.9	112.4	112.8	112.4	114.9	115.7	117.8	119.5	122.8	124.5
72.5°	97.4	96.6	96.2	95.5	96.2	96.6	97.4	99.6	101.2	104.9	107.5
75°	77.2	76.8	76.3	78.0	76.3	76.8	77.2	77.6	78.0	79.2	80.5
77.5°	61.8	61.8	62.0	61.4	62.0	61.8	61.8	61.8	61.8	62.4	62.7
80°	51.8	51.8	51.4	51.4	51.4	51.8	51.8	51.8	51.8	51.8	51.4
82.5°	41.6	41.9	42.1	41.5	42.1	41.9	41.6	42.2	42.5	41.9	42.1
85°	27.4	26.9	27.8	27.4	27.8	26.9	27.4	27.4	26.5	27.4	26.9
87.5°	16.7	16.2	16.3	16.6	16.3	16.2	16.7	16.2	15.8	15.7	15.2
90°	22.1	22.9	23.7	22.9	23.7	22.9	22.1	22.9	21.4	20.6	19.8
92.5°	41.1	38.7	39.5	38.1	39.5	38.7	41.1	42.5	46.7	52.8	66.5
95°	107.6	100.4	94.9	91.7	94.9	100.4	107.6	122.6	151.1	193.0	284.6
97.5°	313.5	277.9	256.5	249.7	256.5	277.9	313.5	371.8	466.4	568.4	709.6
100°	583.6	525.9	495.0	495.8	495.0	525.9	583.6	663.5	775.7	868.2	932.3
102.5°	817.0	771.3	745.5	727.3	745.5	771.3	817.0	879.2	950.3	1004.2	1006.3
105°	1065.1	1035.1	1009.8	1005.8	1009.8	1035.1	1065.1	1101.5	1122.0	1107.1	1027.9
107.5°	1192.2	1182.0	1173.5	1166.2	1173.5	1182.0	1192.2	1191.5	1163.3	1094.1	965.7
110°	1228.8	1235.2	1233.6	1232.0	1233.6	1235.2	1228.8	1206.7	1151.3	1051.7	906.2

TEST NUMBER: P332320-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1219.3	1238.9	1244.9	1245.2	1244.9	1238.9	1219.3	1178.8	1107.6	996.0	847.3
115°	1168.7	1203.5	1219.3	1223.3	1219.3	1203.5	1168.7	1109.4	1023.2	907.0	769.4
117.5°	1085.4	1125.2	1148.0	1153.3	1148.0	1125.2	1085.4	1023.5	936.0	831.7	713.0
120°	1027.1	1071.4	1090.4	1095.2	1090.4	1071.4	1027.1	964.7	884.9	790.0	683.2
122.5°	974.1	1013.9	1034.7	1040.8	1034.7	1013.9	974.1	918.5	844.4	756.5	659.8
125°	904.6	939.4	959.2	964.7	959.2	939.4	904.6	854.0	790.8	714.9	628.7
127.5°	849.4	879.2	897.0	902.1	897.0	879.2	849.4	804.3	746.8	678.3	601.4
130°	815.2	843.8	860.3	866.6	860.3	843.8	815.2	773.3	719.5	655.5	584.4
132.5°	784.3	812.7	827.4	831.9	827.4	812.7	784.3	744.9	693.6	634.0	568.5
135°	738.6	762.2	776.5	782.0	776.5	762.2	738.6	699.8	654.7	603.3	547.2
137.5°	689.7	713.8	725.7	729.4	725.7	713.8	689.7	657.1	618.1	573.8	527.8
140°	658.7	680.8	693.5	692.7	693.5	680.8	658.7	628.7	594.6	556.7	516.3
142.5°	628.4	647.9	659.3	658.5	659.3	647.9	628.4	602.7	573.1	540.3	505.6
145°	586.7	603.3	609.7	611.2	609.7	603.3	586.7	567.0	544.0	518.7	492.7
147.5°	554.4	565.7	571.7	572.4	571.7	565.7	554.4	539.5	523.2	502.7	482.0
150°	536.1	544.8	549.5	549.5	549.5	544.8	536.1	524.3	509.2	492.7	474.4
152.5°	519.7	527.8	530.6	530.6	530.6	527.8	519.7	510.3	497.9	483.2	467.5
155°	498.2	504.5	506.0	506.8	506.0	504.5	498.2	491.1	481.6	469.7	457.0
157.5°	479.3	484.1	485.4	485.2	485.4	484.1	479.3	473.2	465.7	456.5	446.0
160°	467.3	472.1	472.1	471.3	472.1	472.1	467.3	461.8	456.2	448.4	439.7
162.5°	455.3	459.4	459.4	458.6	459.4	459.4	455.3	451.7	446.8	439.5	432.1
165°	439.7	442.8	442.0	442.0	442.0	442.8	439.7	436.5	432.5	427.0	422.2
167.5°	424.8	427.0	426.2	426.2	426.2	427.0	424.8	423.3	420.5	417.3	413.7
170°	415.9	417.5	416.7	416.7	416.7	417.5	415.9	415.1	413.5	410.4	408.1
172.5°	408.4	410.0	408.5	407.9	408.5	410.0	408.4	408.2	407.3	404.7	403.0
175°	398.5	399.3	398.5	397.8	398.5	399.3	398.5	398.5	398.5	397.0	396.2
177.5°	392.5	393.2	391.9	391.9	391.9	393.2	392.5	393.2	393.2	392.5	391.9
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6

TEST NUMBER: P332320-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	924.7	929.4	934.0	938.3	945.0	947.9	952.3	953.9	958.9	966.2	972.2
5°	868.5	875.1	883.8	890.9	902.1	910.8	920.4	929.5	940.2	955.6	969.2
7.5°	820.8	827.4	837.8	850.9	863.2	875.6	888.7	901.1	916.5	938.5	960.3
10°	789.3	797.2	809.6	823.7	839.0	851.0	866.4	882.2	901.3	926.5	952.7
12.5°	762.1	767.9	782.4	795.8	813.2	828.5	843.5	861.9	883.7	910.6	942.1
15°	718.7	727.1	741.2	756.1	774.4	790.5	810.0	832.4	853.6	886.8	924.9
17.5°	675.3	687.9	702.6	719.5	732.9	755.3	776.4	799.4	825.5	860.6	902.5
20°	647.5	657.4	671.1	695.5	713.4	730.4	749.9	778.5	802.6	842.3	885.9
22.5°	623.8	631.1	646.5	666.7	687.5	707.2	727.0	754.2	783.9	821.8	868.9
25°	588.9	600.6	612.2	626.7	649.1	672.7	694.3	717.5	749.0	789.3	840.3
27.5°	554.8	565.4	576.9	594.7	611.6	633.7	656.3	682.9	716.8	759.3	811.1
30°	533.0	540.8	551.6	574.4	589.8	608.9	635.4	659.0	690.5	735.8	790.5
32.5°	510.4	520.6	532.3	549.9	568.9	586.9	611.2	636.8	669.0	713.5	769.6
35°	478.2	490.2	502.2	515.1	534.2	552.9	573.1	601.3	634.1	677.3	732.5
37.5°	448.6	458.3	468.1	484.0	502.1	519.8	538.8	566.6	597.5	644.0	694.6
40°	429.7	438.4	445.8	462.5	479.8	498.9	517.6	542.1	575.3	618.8	667.7
42.5°	409.1	417.2	427.3	440.8	459.6	475.7	494.4	517.5	548.7	592.9	635.9
45°	378.3	387.4	396.1	408.9	427.6	443.4	459.9	482.0	513.9	550.4	588.5
47.5°	346.2	355.3	365.2	377.6	394.0	410.0	426.5	446.0	475.2	511.0	536.7
50°	325.6	333.0	343.0	355.5	370.3	387.4	402.3	423.4	451.2	479.4	501.8
52.5°	304.4	311.2	322.4	335.6	349.4	364.2	380.1	398.2	423.3	449.9	467.7
55°	271.2	279.6	289.1	301.9	315.6	328.0	343.4	362.1	382.0	401.9	413.9
57.5°	240.3	247.2	255.2	268.5	280.4	295.2	309.0	323.5	341.9	357.0	364.8
60°	217.8	223.9	234.3	246.0	257.1	270.0	285.7	300.3	314.4	326.4	332.6
62.5°	196.5	203.7	212.8	223.4	235.6	247.8	261.6	273.7	286.1	296.5	300.8
65°	168.8	174.6	181.3	191.2	201.1	213.6	224.3	236.8	246.0	251.8	255.5
67.5°	143.6	147.4	152.5	159.1	168.9	179.7	190.2	199.9	207.6	211.5	214.8
70°	127.3	129.8	133.6	140.2	147.7	157.2	167.9	175.0	181.6	185.0	188.3
72.5°	111.1	114.2	117.6	122.9	129.0	135.9	143.8	152.5	156.1	160.1	162.1
75°	84.2	88.7	93.3	96.6	100.8	106.2	113.2	118.6	120.7	124.0	124.5
77.5°	63.5	64.6	67.9	72.0	75.5	79.4	83.9	88.6	89.7	91.4	92.5
80°	52.3	52.3	52.3	54.7	58.9	61.8	65.9	68.4	70.1	70.5	70.9
82.5°	42.0	42.0	41.7	42.1	43.6	45.2	49.0	51.8	53.2	52.9	52.0
85°	27.4	26.5	26.5	26.1	26.5	25.7	25.3	26.9	29.5	29.5	28.6
87.5°	15.1	14.9	14.7	13.9	13.2	12.4	11.0	11.0	10.5	11.6	10.9
90°	19.0	19.8	17.4	15.1	12.7	10.3	8.7	7.1	4.8	3.2	1.6
92.5°	91.7	121.6	133.8	100.4	66.4	45.7	34.0	27.3	21.2	14.6	9.8
95°	380.3	468.9	417.5	287.8	170.0	102.8	71.9	51.4	37.9	29.2	26.9
97.5°	777.4	726.7	532.0	315.8	183.0	118.7	85.4	65.1	53.5	46.7	45.9
100°	904.6	748.8	506.0	298.1	181.1	125.7	94.9	75.9	64.9	59.3	58.5
102.5°	910.9	707.7	468.1	282.9	183.6	134.0	105.7	88.6	78.1	73.2	71.8
105°	862.7	635.7	421.4	272.0	190.6	147.9	123.3	108.4	98.9	94.1	91.7
107.5°	778.2	572.2	391.7	271.2	203.5	166.0	143.3	129.2	119.9	115.3	112.9
110°	725.1	536.1	380.3	274.4	214.3	178.7	156.5	143.1	134.4	130.5	128.1

TEST NUMBER: P332320-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	678.9	512.1	374.0	280.7	225.1	192.0	170.5	157.0	148.4	144.4	142.0
115°	623.1	486.3	371.6	291.0	242.7	212.7	191.4	177.9	170.0	165.2	162.1
117.5°	589.4	471.1	373.0	304.6	261.6	231.9	212.1	197.0	189.8	185.8	182.2
120°	571.7	464.1	375.6	314.7	273.6	245.1	225.4	210.3	202.4	198.4	196.1
122.5°	557.1	459.7	380.0	324.2	286.2	258.4	237.4	223.0	214.4	210.5	208.1
125°	538.5	453.9	386.7	339.2	304.4	276.8	255.4	240.3	231.7	227.0	225.4
127.5°	522.0	451.1	394.3	351.6	320.3	293.5	272.2	255.6	246.7	240.8	238.5
130°	513.2	449.2	399.3	359.8	329.7	303.6	282.3	265.7	256.2	249.1	246.7
132.5°	504.9	448.5	403.1	367.4	337.9	312.5	291.8	275.2	263.8	256.0	253.0
135°	494.2	447.6	408.8	377.2	350.3	325.7	304.4	287.8	276.0	267.3	264.1
137.5°	484.9	445.8	412.6	384.4	358.9	335.3	315.5	299.0	286.4	277.9	274.6
140°	479.2	445.2	415.1	388.2	364.6	341.6	321.9	306.0	293.3	285.4	281.5
142.5°	474.1	443.9	417.0	392.1	369.0	346.7	328.1	312.4	301.0	292.4	289.1
145°	467.3	442.0	418.3	396.2	374.8	354.3	336.0	322.7	310.8	303.6	301.3
147.5°	460.7	439.0	418.3	398.7	379.5	360.8	345.2	332.2	322.0	315.1	313.6
150°	456.2	436.5	418.3	399.3	382.7	364.6	350.3	339.2	328.9	322.7	321.9
152.5°	451.2	433.3	416.4	400.6	384.6	369.0	355.4	345.5	336.5	330.2	330.0
155°	443.6	427.8	414.3	400.9	388.2	374.8	363.8	355.1	347.1	342.4	342.4
157.5°	435.1	422.9	411.7	401.7	390.3	379.5	371.0	363.6	356.6	352.8	352.2
160°	429.4	419.1	410.4	401.7	392.2	382.7	374.8	369.2	363.0	359.8	359.8
162.5°	423.7	415.3	407.9	401.1	392.8	384.6	378.0	373.0	368.0	365.5	365.5
165°	415.9	409.6	404.1	399.3	393.8	387.5	381.9	378.7	374.8	373.2	374.0
167.5°	408.5	403.9	400.3	398.1	393.6	389.0	385.6	383.3	380.3	379.5	380.5
170°	404.1	400.1	397.8	396.2	393.0	389.0	387.5	385.9	383.5	382.7	384.3
172.5°	399.7	397.0	395.9	395.5	393.0	389.7	388.7	387.8	386.0	385.9	386.8
175°	394.6	393.0	393.0	393.8	392.2	390.6	389.8	389.8	388.2	389.0	389.8
177.5°	391.3	390.6	391.3	392.5	391.3	390.6	390.6	390.6	390.0	390.6	391.3
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6

TEST NUMBER: P332320-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	974.1	977.8	982.5	989.4	994.7	999.3	1000.4	1001.7	1005.0	1010.7	1014.9
5°	980.5	990.0	1005.4	1020.3	1036.5	1049.7	1062.2	1070.9	1079.2	1096.6	1110.7
7.5°	978.5	999.7	1023.7	1050.6	1077.7	1104.0	1128.4	1150.2	1171.9	1197.3	1226.2
10°	977.2	1002.0	1034.4	1068.8	1106.5	1143.4	1179.2	1206.9	1239.3	1268.3	1305.2
12.5°	970.8	1006.7	1045.4	1089.4	1135.8	1178.3	1225.3	1263.7	1300.7	1342.6	1385.5
15°	962.7	1006.2	1055.1	1113.6	1184.1	1235.6	1283.7	1350.4	1396.1	1441.7	1503.0
17.5°	947.6	1000.8	1061.9	1137.9	1196.7	1265.8	1338.2	1391.0	1452.5	1516.7	1572.3
20°	935.6	997.4	1065.9	1140.6	1215.6	1290.7	1360.8	1423.8	1487.3	1561.5	1607.2
22.5°	923.8	984.8	1056.0	1135.3	1215.9	1295.0	1374.4	1448.3	1519.8	1594.7	1653.0
25°	898.3	970.9	1048.1	1128.9	1208.6	1295.7	1390.2	1472.7	1561.1	1638.2	1693.4
27.5°	872.6	939.1	1016.0	1098.0	1186.5	1289.4	1400.7	1494.5	1583.0	1638.2	1655.6
30°	849.4	919.9	990.4	1073.8	1169.6	1284.4	1402.6	1510.1	1582.7	1606.7	1588.9
32.5°	825.9	889.7	959.6	1044.9	1146.7	1272.2	1405.3	1500.8	1544.5	1526.1	1453.5
35°	784.3	841.9	909.5	995.0	1111.9	1265.4	1394.4	1459.0	1448.3	1344.6	1207.8
37.5°	739.8	786.8	849.4	938.7	1075.9	1238.4	1347.3	1356.8	1263.5	1104.3	946.2
40°	704.6	746.9	811.3	904.6	1048.1	1211.9	1299.8	1261.2	1116.5	939.4	807.6
42.5°	670.5	706.2	768.1	868.7	1021.5	1175.8	1229.2	1145.1	978.1	810.6	690.7
45°	612.6	646.2	708.4	811.7	967.2	1106.5	1099.5	953.5	786.4	651.6	552.0
47.5°	557.7	587.0	645.4	750.8	903.4	1002.8	936.9	781.6	639.8	531.6	460.7
50°	518.9	547.9	605.9	710.0	852.3	924.9	830.8	681.0	551.2	461.6	405.2
52.5°	481.7	510.1	563.2	664.6	790.6	834.0	732.8	594.1	485.8	408.5	360.0
55°	429.7	451.2	498.9	596.0	690.1	700.1	597.6	481.5	392.4	338.4	305.2
57.5°	376.7	395.2	442.4	519.7	585.7	580.6	483.5	382.9	322.9	282.9	258.8
60°	342.1	360.4	401.9	468.3	518.0	500.6	411.5	330.6	279.1	249.7	230.6
62.5°	310.0	324.2	363.1	411.5	447.3	427.6	351.7	284.8	244.0	219.1	204.1
65°	263.4	275.0	306.1	331.4	351.3	332.2	269.2	222.7	193.3	175.9	165.5
67.5°	219.0	226.5	246.1	255.2	269.3	248.3	202.4	171.3	154.6	139.8	132.6
70°	191.2	196.6	207.0	214.4	218.2	196.6	162.6	139.7	125.6	115.3	110.7
72.5°	163.3	168.0	170.2	176.3	174.4	154.2	130.7	112.6	102.4	95.4	89.5
75°	124.8	126.9	124.8	122.3	116.9	102.8	86.7	77.6	70.1	66.8	64.7
77.5°	91.0	90.3	87.5	83.6	74.4	65.5	56.8	53.8	50.5	48.8	48.0
80°	70.1	68.4	65.9	59.7	51.8	45.6	43.6	41.5	40.2	38.2	37.7
82.5°	52.2	51.2	47.1	41.8	36.3	33.4	31.6	30.9	29.6	28.5	28.4
85°	27.8	26.5	21.9	19.1	18.2	17.4	17.0	17.0	15.4	14.9	14.9
87.5°	9.6	7.9	8.1	7.4	7.7	7.5	8.3	8.2	8.2	8.5	7.9
90°	3.2	4.8	7.1	8.7	10.3	12.7	15.1	17.4	19.8	19.0	19.8
92.5°	14.6	21.2	27.3	34.0	45.7	66.4	100.4	133.8	121.6	91.7	66.5
95°	29.2	37.9	51.4	71.9	102.8	170.0	287.8	417.5	468.9	380.3	284.6
97.5°	46.7	53.5	65.1	85.4	118.7	183.0	315.8	532.0	726.7	777.4	709.6
100°	59.3	64.9	75.9	94.9	125.7	181.1	298.1	506.0	748.8	904.6	932.3
102.5°	73.2	78.1	88.6	105.7	134.0	183.6	282.9	468.1	707.7	910.9	1006.3
105°	94.1	98.9	108.4	123.3	147.9	190.6	272.0	421.4	635.7	862.7	1027.9
107.5°	115.3	119.9	129.2	143.3	166.0	203.5	271.2	391.7	572.2	778.2	965.7
110°	130.5	134.4	143.1	156.5	178.7	214.3	274.4	380.3	536.1	725.1	906.2

TEST NUMBER: P332320-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	144.4	148.4	157.0	170.5	192.0	225.1	280.7	374.0	512.1	678.9	847.3
115°	165.2	170.0	177.9	191.4	212.7	242.7	291.0	371.6	486.3	623.1	769.4
117.5°	185.8	189.8	197.0	212.1	231.9	261.6	304.6	373.0	471.1	589.4	713.0
120°	198.4	202.4	210.3	225.4	245.1	273.6	314.7	375.6	464.1	571.7	683.2
122.5°	210.5	214.4	223.0	237.4	258.4	286.2	324.2	380.0	459.7	557.1	659.8
125°	227.0	231.7	240.3	255.4	276.8	304.4	339.2	386.7	453.9	538.5	628.7
127.5°	240.8	246.7	255.6	272.2	293.5	320.3	351.6	394.3	451.1	522.0	601.4
130°	249.1	256.2	265.7	282.3	303.6	329.7	359.8	399.3	449.2	513.2	584.4
132.5°	256.0	263.8	275.2	291.8	312.5	337.9	367.4	403.1	448.5	504.9	568.5
135°	267.3	276.0	287.8	304.4	325.7	350.3	377.2	408.8	447.6	494.2	547.2
137.5°	277.9	286.4	299.0	315.5	335.3	358.9	384.4	412.6	445.8	484.9	527.8
140°	285.4	293.3	306.0	321.9	341.6	364.6	388.2	415.1	445.2	479.2	516.3
142.5°	292.4	301.0	312.4	328.1	346.7	369.0	392.1	417.0	443.9	474.1	505.6
145°	303.6	310.8	322.7	336.0	354.3	374.8	396.2	418.3	442.0	467.3	492.7
147.5°	315.1	322.0	332.2	345.2	360.8	379.5	398.7	418.3	439.0	460.7	482.0
150°	322.7	328.9	339.2	350.3	364.6	382.7	399.3	418.3	436.5	456.2	474.4
152.5°	330.2	336.5	345.5	355.4	369.0	384.6	400.6	416.4	433.3	451.2	467.5
155°	342.4	347.1	355.1	363.8	374.8	388.2	400.9	414.3	427.8	443.6	457.0
157.5°	352.8	356.6	363.6	371.0	379.5	390.3	401.7	411.7	422.9	435.1	446.0
160°	359.8	363.0	369.2	374.8	382.7	392.2	401.7	410.4	419.1	429.4	439.7
162.5°	365.5	368.0	373.0	378.0	384.6	392.8	401.1	407.9	415.3	423.7	432.1
165°	373.2	374.8	378.7	381.9	387.5	393.8	399.3	404.1	409.6	415.9	422.2
167.5°	379.5	380.3	383.3	385.6	389.0	393.6	398.1	400.3	403.9	408.5	413.7
170°	382.7	383.5	385.9	387.5	389.0	393.0	396.2	397.8	400.1	404.1	408.1
172.5°	385.9	386.0	387.8	388.7	389.7	393.0	395.5	395.9	397.0	399.7	403.0
175°	389.0	388.2	389.8	389.8	390.6	392.2	393.8	393.0	393.0	394.6	396.2
177.5°	390.6	390.0	390.6	390.6	390.6	391.3	392.5	391.3	390.6	391.3	391.9
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6

TEST NUMBER: P332320-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1021.9	1021.9	1023.3	1028.3	1028.9	1033.2	1031.9
5°	1123.2	1131.0	1133.9	1146.4	1153.8	1157.1	1150.5
7.5°	1246.9	1269.2	1279.7	1292.7	1304.2	1307.7	1298.6
10°	1337.1	1360.3	1379.9	1391.9	1403.1	1410.6	1420.1
12.5°	1424.4	1452.9	1471.5	1488.4	1500.0	1509.4	1511.0
15°	1519.2	1562.3	1595.1	1619.1	1631.2	1637.4	1634.9
17.5°	1614.9	1654.9	1678.2	1702.7	1719.4	1720.2	1720.7
20°	1669.0	1707.9	1734.9	1753.1	1771.8	1771.0	1775.1
22.5°	1705.1	1735.8	1756.4	1769.7	1776.2	1773.0	1773.8
25°	1722.0	1731.2	1727.4	1706.3	1700.9	1681.4	1684.7
27.5°	1634.7	1591.7	1547.0	1489.6	1444.3	1408.2	1410.0
30°	1516.3	1440.0	1352.9	1279.9	1214.4	1196.1	1157.1
32.5°	1350.8	1236.3	1134.2	1066.2	1010.0	994.7	960.8
35°	1070.1	958.9	854.0	790.9	766.0	731.2	730.8
37.5°	831.7	733.9	678.3	631.1	606.3	585.2	583.1
40°	699.7	623.4	581.5	547.5	523.0	507.2	503.5
42.5°	607.4	545.7	506.5	485.4	466.6	458.4	452.4
45°	496.1	454.6	427.2	408.1	399.4	393.2	389.8
47.5°	414.9	387.1	368.4	355.8	348.7	342.1	343.9
50°	370.8	348.0	334.3	322.3	316.9	312.3	312.8
52.5°	335.3	314.8	303.7	295.1	288.4	285.1	283.5
55°	284.6	271.6	260.5	254.2	250.5	246.0	244.7
57.5°	242.7	232.7	223.6	216.6	215.6	211.3	211.8
60°	214.8	206.5	199.1	195.4	192.4	188.7	190.0
62.5°	191.9	185.0	178.2	175.1	172.2	169.4	170.1
65°	157.2	150.5	146.4	144.7	143.5	142.3	141.0
67.5°	125.2	121.2	118.6	115.0	112.5	112.1	110.8
70°	105.4	100.0	95.4	90.9	89.6	89.2	89.6
72.5°	84.4	81.0	79.8	77.6	77.3	76.2	77.0
75°	63.5	62.2	61.4	59.7	59.7	59.7	59.7
77.5°	46.8	46.0	45.6	45.2	44.8	44.2	44.1
80°	36.5	36.0	35.3	35.3	34.9	35.3	34.9
82.5°	27.6	27.5	26.6	26.6	26.2	26.0	26.2
85°	14.1	13.7	14.5	13.7	14.1	13.3	14.1
87.5°	8.1	8.2	8.2	8.1	7.9	8.7	7.9
90°	20.6	21.4	22.9	22.1	22.9	23.7	22.9
92.5°	52.8	46.7	42.5	41.1	38.7	39.5	38.1
95°	193.0	151.1	122.6	107.6	100.4	94.9	91.7
97.5°	568.4	466.4	371.8	313.5	277.9	256.5	249.7
100°	868.2	775.7	663.5	583.6	525.9	495.0	495.8
102.5°	1004.2	950.3	879.2	817.0	771.3	745.5	727.3
105°	1107.1	1122.0	1101.5	1065.1	1035.1	1009.8	1005.8
107.5°	1094.1	1163.3	1191.5	1192.2	1182.0	1173.5	1166.2
110°	1051.7	1151.3	1206.7	1228.8	1235.2	1233.6	1232.0

TEST NUMBER: P332320-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	996.0	1107.6	1178.8	1219.3	1238.9	1244.9	1245.2
115°	907.0	1023.2	1109.4	1168.7	1203.5	1219.3	1223.3
117.5°	831.7	936.0	1023.5	1085.4	1125.2	1148.0	1153.3
120°	790.0	884.9	964.7	1027.1	1071.4	1090.4	1095.2
122.5°	756.5	844.4	918.5	974.1	1013.9	1034.7	1040.8
125°	714.9	790.8	854.0	904.6	939.4	959.2	964.7
127.5°	678.3	746.8	804.3	849.4	879.2	897.0	902.1
130°	655.5	719.5	773.3	815.2	843.8	860.3	866.6
132.5°	634.0	693.6	744.9	784.3	812.7	827.4	831.9
135°	603.3	654.7	699.8	738.6	762.2	776.5	782.0
137.5°	573.8	618.1	657.1	689.7	713.8	725.7	729.4
140°	556.7	594.6	628.7	658.7	680.8	693.5	692.7
142.5°	540.3	573.1	602.7	628.4	647.9	659.3	658.5
145°	518.7	544.0	567.0	586.7	603.3	609.7	611.2
147.5°	502.7	523.2	539.5	554.4	565.7	571.7	572.4
150°	492.7	509.2	524.3	536.1	544.8	549.5	549.5
152.5°	483.2	497.9	510.3	519.7	527.8	530.6	530.6
155°	469.7	481.6	491.1	498.2	504.5	506.0	506.8
157.5°	456.5	465.7	473.2	479.3	484.1	485.4	485.2
160°	448.4	456.2	461.8	467.3	472.1	472.1	471.3
162.5°	439.5	446.8	451.7	455.3	459.4	459.4	458.6
165°	427.0	432.5	436.5	439.7	442.8	442.0	442.0
167.5°	417.3	420.5	423.3	424.8	427.0	426.2	426.2
170°	410.4	413.5	415.1	415.9	417.5	416.7	416.7
172.5°	404.7	407.3	408.2	408.4	410.0	408.5	407.9
175°	397.0	398.5	398.5	398.5	399.3	398.5	397.8
177.5°	392.5	393.2	393.2	392.5	393.2	391.9	391.9
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6

(END OF REPORT)