

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999401

Luminaire Tested: SA2XXRDIP-B1005D725UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999401
REPORT IS A COMBINATION OF REPORTS P987952 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D725UB2750-4F0-XX-W2A-F_4000K
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6287.0 lumens
Efficiency: N/A
Efficacy: 76.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999401

CATALOG NUMBER: SA2XXRDIP-B1005D725UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P999401

CATALOG NUMBER: SA2XXRDIP-B1005D725UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61			55
1	99	95	92	88	92	89	86	83	76	74	72	65	63	62	55	54	53			48
2	91	84	78	73	84	78	73	69	68	64	60	58	55	53	49	47	45			41
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	41	39			35
4	77	66	58	52	71	62	55	50	54	49	44	46	42	39	39	36	34			31
5	71	59	51	45	65	55	48	43	48	43	39	42	38	34	36	33	30			27
6	65	53	45	40	60	50	43	38	44	38	34	38	34	30	33	29	27			24
7	60	48	41	35	56	45	38	33	40	34	30	35	30	27	30	27	24			21
8	56	44	36	31	52	41	35	30	37	31	27	32	28	24	28	24	22			19
9	52	40	33	28	49	38	31	27	34	28	24	30	25	22	26	22	20			18
10	49	37	30	25	46	35	29	24	31	26	22	27	23	20	24	20	18			16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26715	26715	26715
5°	26759	25416	25228
10°	26494	24106	23311
15°	26130	22559	21124
20°	25649	20799	18839
25°	25156	18994	16748
30°	24492	17236	14463
35°	23844	15464	12501
40°	23184	13722	10481
45°	22417	11925	8719
50°	21623	10191	7098
55°	20797	8460	5635
60°	19836	6765	4264
65°	18731	5159	3465
70°	17396	3742	2756
75°	15719	2854	2105
80°	13293	1932	1413
85°	9281	884	682

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22417 cd/sqm

TEST NUMBER: P999401

CATALOG NUMBER: SA2XXRDIP-B1005D725UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.2	2.5
10°-20°	434.2	6.9
20°-30°	609.6	9.7
30°-40°	664.5	10.6
40°-50°	610.8	9.7
50°-60°	479.7	7.6
60°-70°	312.2	5.0
70°-80°	160.7	2.6
80°-90°	42.7	0.7
90°-100°	31.7	0.5
100°-110°	118.0	1.9
110°-120°	313.0	5.0
120°-130°	519.1	8.3
130°-140°	551.4	8.8
140°-150°	512.4	8.2
150°-160°	412.0	6.6
160°-170°	265.5	4.2
170°-180°	91.4	1.5
0°-30°	1202.0	19.1
0°-40°	1866.6	29.7
0°-60°	2957.0	47.0
0°-90°	3472.7	55.2
90°-120°	462.7	7.4
90°-150°	2045.5	32.5
90°-180°	2814.0	44.8
0°-180°	6287.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1688	1688	1688	1688	1688	
5°	1688	1680	1660	1674	1669	160
15°	1605	1588	1536	1508	1492	452
25°	1457	1408	1307	1245	1222	670
35°	1256	1178	1043	947	913	786
45°	1026	924	764	655	619	793
55°	780	661	496	405	376	697
65°	527	403	266	214	209	522
75°	281	174	122	112	110	297
85°	66	34	29	29	29	75
90°	1	8	14	17	19	6
95°	45	22	27	31	30	53
105°	211	232	42	50	53	226
115°	399	411	429	107	57	393
125°	565	574	587	592	594	504
135°	699	710	716	723	722	540
145°	811	810	822	827	823	507
155°	893	886	895	899	893	411
165°	940	936	938	943	938	266
175°	962	957	959	963	956	92
180°	960	960	960	960	960	

TEST NUMBER: P999401

CATALOG NUMBER: SA2XXRDIP-B1005D725UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1687.7	1687.7	1687.7	1687.7	1687.7
2.5°	1695.4	1687.7	1670.9	1686.2	1683.1
5°	1687.7	1680.1	1660.2	1674.0	1669.4
7.5°	1674.0	1664.8	1643.4	1649.5	1641.9
10°	1655.6	1644.9	1614.4	1609.8	1600.7
12.5°	1632.7	1619.0	1577.7	1568.6	1551.8
15°	1605.2	1588.4	1536.5	1507.5	1492.2
17.5°	1573.2	1548.7	1484.6	1451.0	1426.5
20°	1536.5	1506.0	1429.6	1391.4	1357.8
22.5°	1496.8	1461.7	1373.1	1321.2	1298.2
25°	1457.1	1408.2	1307.4	1244.8	1221.9
27.5°	1409.7	1357.8	1246.3	1174.5	1139.4
30°	1359.3	1301.3	1179.1	1101.2	1060.0
32.5°	1310.5	1240.2	1115.0	1023.3	985.1
35°	1255.5	1177.6	1043.2	947.0	913.4
37.5°	1202.0	1118.0	976.0	870.6	832.4
40°	1145.5	1053.9	905.7	797.3	757.6
42.5°	1087.5	989.7	835.5	722.4	684.2
45°	1026.4	924.0	763.7	655.2	618.6
47.5°	968.3	859.9	694.9	586.5	552.9
50°	904.2	795.7	627.7	522.4	490.3
52.5°	841.6	727.0	563.6	462.8	433.8
55°	780.5	661.3	496.4	404.7	375.7
57.5°	717.9	595.7	436.8	351.3	326.9
60°	653.7	531.5	374.2	296.3	271.9
62.5°	591.1	468.9	320.7	247.4	235.2
65°	526.9	403.2	265.8	213.8	209.2
67.5°	465.8	342.1	213.8	187.9	183.3
70°	401.7	282.6	177.2	161.9	155.8
72.5°	340.6	227.6	148.2	135.9	132.9
75°	281.0	174.1	122.2	111.5	110.0
77.5°	221.5	123.7	96.2	90.1	87.1
80°	166.5	88.6	73.3	67.2	67.2
82.5°	116.1	59.6	50.4	47.3	47.3
85°	65.7	33.6	29.0	29.0	29.0
87.5°	24.4	12.2	12.2	10.7	10.7
90°	0.7	8.3	13.9	17.4	18.8
92.5°	17.4	14.6	16.7	18.1	18.8
95°	45.2	22.2	27.1	30.6	29.9
97.5°	81.3	24.3	35.4	37.5	38.2
100°	122.9	27.8	39.6	45.2	46.5
102.5°	168.8	167.4	41.0	48.6	50.7
105°	211.2	232.0	42.4	50.0	52.8
107.5°	260.5	277.9	43.8	51.4	54.2
110°	307.7	322.3	121.6	52.1	54.9



TEST NUMBER: P999401

CATALOG NUMBER: SA2XXRDIP-B1005D725UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	352.2	364.7	352.9	53.5	55.6
115°	399.4	411.2	428.6	107.0	57.0
117.5°	440.4	454.3	466.1	366.8	184.8
120°	486.2	496.7	509.2	517.5	423.7
122.5°	525.1	536.3	550.1	554.3	555.0
125°	564.7	573.8	587.0	591.8	593.9
127.5°	600.9	610.6	621.0	627.9	628.6
130°	634.9	646.0	653.6	661.3	660.6
132.5°	669.6	678.7	686.3	692.5	691.8
135°	698.8	709.9	716.2	723.1	721.7
137.5°	729.4	737.7	744.6	751.6	749.5
140°	759.2	764.8	772.4	778.7	775.2
142.5°	784.2	789.1	798.1	803.7	800.2
145°	810.6	809.9	821.7	826.6	823.1
147.5°	833.6	831.5	843.3	846.8	844.0
150°	855.8	850.9	862.0	866.2	862.7
152.5°	874.5	869.0	879.4	883.6	878.7
155°	892.6	886.3	894.7	898.8	893.3
157.5°	907.2	901.6	907.9	912.7	907.2
160°	919.7	915.5	919.7	923.9	919.0
162.5°	930.8	926.6	930.1	935.0	928.7
165°	940.5	936.4	938.4	943.3	938.4
167.5°	948.2	944.0	946.1	950.9	944.7
170°	954.4	950.3	951.6	956.5	950.3
172.5°	958.6	954.4	955.8	960.7	954.4
175°	962.1	957.2	958.6	963.4	956.5
177.5°	963.4	958.6	959.3	964.1	957.9
180°	960.0	960.0	960.0	960.0	960.0

(END OF REPORT)