

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332343-940

Luminaire Tested: **S123RDIP-S1000D805U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332343-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1000D805U940-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5991.1 lumens  
Efficiency: N/A  
Efficacy: 110.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332343-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332343-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	93	89	94	90	87	84	79	76	74	68	66	65	58	57	56	51
2	92	85	79	74	86	80	74	70	70	66	62	60	58	55	52	50	48	44
3	84	75	68	63	79	71	64	59	62	57	53	54	50	47	47	44	42	38
4	78	67	59	54	72	63	56	51	56	50	46	49	44	41	42	39	36	33
5	72	60	52	46	67	57	50	44	50	44	40	44	40	36	38	35	32	29
6	66	54	46	41	62	51	44	39	45	40	35	40	35	32	35	31	29	26
7	61	49	41	36	57	47	39	34	41	36	31	37	32	29	32	28	26	23
8	57	45	37	32	53	42	36	31	38	32	28	34	29	26	30	26	23	21
9	53	41	34	29	50	39	32	28	35	29	25	31	26	23	27	24	21	19
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	25	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	15259	15259	15259	15259
5°	18189	15324	13493	15324
10°	22710	15235	12191	15235
15°	26658	15081	11117	15081
20°	29751	14848	10204	14848
25°	29276	14602	9644	14602
30°	21044	14375	9066	14375
35°	14051	14082	8692	14082
40°	10352	13728	8304	13728
45°	8683	13108	7926	13108
50°	7661	12295	7398	12295
55°	6718	11365	6673	11365
60°	5983	10478	6114	10478
65°	5254	9521	5687	9521
70°	4126	8670	5196	8670
75°	3635	7573	4741	7573
80°	3161	6434	4668	6434
85°	2544	5175	4940	5175



TEST NUMBER: P332343-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.4	2.3
10°-20°	435.5	7.3
20°-30°	684.2	11.4
30°-40°	713.8	11.9
40°-50°	610.9	10.2
50°-60°	465.6	7.8
60°-70°	298.4	5.0
70°-80°	143.6	2.4
80°-90°	40.6	0.7
90°-100°	57.8	1.0
100°-110°	173.1	2.9
110°-120°	294.3	4.9
120°-130°	387.1	6.5
130°-140°	435.1	7.3
140°-150°	427.7	7.1
150°-160°	360.1	6.0
160°-170°	239.7	4.0
170°-180°	83.9	1.4
0°-30°	1259.1	21.0
0°-40°	1973.0	32.9
0°-60°	3049.5	50.9
0°-90°	3532.1	59.0
90°-120°	525.2	8.8
90°-150°	1775.2	29.6
90°-180°	2459.0	41.0
0°-180°	5991.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1418	1418	1418	1418	1418	
5°	1683	1418	1249	1418	1683	174
15°	2392	1353	998	1353	2392	678
25°	2465	1230	812	1230	2465	1059
35°	1069	1072	662	1072	1069	701
45°	570	861	521	861	570	449
55°	358	606	356	606	358	324
65°	206	374	223	374	206	203
75°	87	182	114	182	87	94
85°	21	42	40	42	21	24
90°	21	1	21	1	21	11
95°	54	41	54	41	54	56
105°	166	157	166	157	166	176
115°	297	296	297	296	297	294
125°	429	434	429	434	429	383
135°	562	563	562	563	562	432
145°	682	682	682	682	682	426
155°	780	782	780	782	780	359
165°	848	851	848	851	848	239
175°	882	885	882	885	882	84
180°	888	888	888	888	888	



TEST NUMBER: P332343-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1509.8	1511.7	1505.5	1504.5	1497.2	1495.2	1495.2	1485.1	1478.7	1470.5	1465.6
5°	1683.4	1693.1	1688.2	1677.3	1659.1	1654.8	1643.3	1625.1	1604.5	1579.0	1566.8
7.5°	1900.1	1913.3	1908.3	1891.4	1872.3	1856.9	1824.4	1794.2	1751.9	1714.7	1682.9
10°	2077.8	2063.9	2052.9	2036.6	2018.9	1990.4	1956.4	1909.7	1855.7	1813.2	1765.9
12.5°	2210.8	2208.5	2194.7	2177.8	2152.9	2125.8	2084.1	2027.2	1964.4	1903.1	1848.9
15°	2392.2	2395.8	2386.7	2369.1	2333.9	2286.0	2222.9	2199.2	2109.3	2042.6	1975.9
17.5°	2517.7	2516.9	2515.7	2491.4	2455.4	2421.3	2362.8	2300.5	2219.2	2125.1	2035.2
20°	2597.3	2591.2	2592.4	2565.1	2538.4	2498.9	2442.0	2351.5	2284.7	2176.1	2083.3
22.5°	2595.3	2594.1	2598.7	2589.3	2570.0	2539.8	2494.8	2418.5	2333.3	2223.7	2119.2
25°	2465.0	2460.1	2488.7	2496.5	2527.5	2532.9	2519.6	2477.7	2397.0	2284.1	2154.9
27.5°	2063.0	2060.3	2113.3	2179.5	2263.5	2328.8	2391.9	2422.4	2397.0	2316.2	2186.7
30°	1693.1	1750.2	1776.8	1872.7	1979.5	2106.9	2218.6	2324.8	2350.9	2315.7	2209.5
32.5°	1405.7	1455.5	1477.7	1560.0	1659.6	1808.8	1976.4	2126.7	2232.9	2259.9	2195.9
35°	1069.3	1069.9	1120.8	1157.3	1249.5	1403.0	1565.7	1767.1	1967.4	2119.1	2134.8
37.5°	853.2	856.2	887.1	923.4	992.6	1073.7	1216.9	1384.5	1615.8	1848.7	1985.2
40°	736.7	742.2	765.3	801.0	850.8	912.0	1023.8	1181.5	1374.5	1633.6	1845.4
42.5°	661.9	670.8	682.7	710.2	741.1	798.4	888.8	1010.7	1186.2	1431.2	1675.5
45°	570.4	575.2	584.4	597.1	625.0	665.1	725.8	807.7	953.3	1150.6	1395.1
47.5°	503.2	500.6	510.2	520.6	539.1	566.4	607.1	674.0	777.8	936.1	1143.5
50°	457.5	456.9	463.6	471.5	489.1	509.2	542.5	592.9	675.4	806.5	996.4
52.5°	414.8	417.1	421.9	431.7	444.4	460.6	490.5	526.8	597.7	710.9	869.2
55°	358.0	359.9	366.5	372.0	381.1	397.4	416.3	446.7	495.2	574.1	704.5
57.5°	310.0	309.2	315.6	316.9	327.2	340.5	355.1	378.7	413.8	472.5	560.4
60°	277.9	276.1	281.6	285.8	291.3	302.2	314.3	337.4	365.3	408.4	483.7
62.5°	248.8	248.0	252.0	256.2	260.7	270.6	280.9	298.5	320.7	357.0	416.7
65°	206.3	208.1	210.0	211.8	214.2	220.3	230.0	242.1	257.3	282.8	325.8
67.5°	162.1	164.0	164.6	168.4	173.5	177.4	183.2	194.0	204.6	226.1	250.7
70°	131.1	130.5	131.1	132.9	139.6	146.2	154.2	162.0	168.7	183.9	204.5
72.5°	112.6	111.6	113.2	113.5	116.7	118.6	123.6	131.0	139.6	149.9	164.7
75°	87.4	87.4	87.4	87.4	89.8	91.0	92.8	94.7	97.7	102.5	113.5
77.5°	64.6	64.6	65.5	66.2	66.6	67.3	68.5	70.3	71.3	73.9	78.6
80°	51.0	51.5	51.0	51.5	51.5	52.8	53.4	55.2	55.8	58.9	60.7
82.5°	38.3	38.0	38.3	39.0	39.0	40.2	40.3	41.6	41.7	43.3	45.1
85°	20.6	19.4	20.6	20.1	21.2	20.1	20.6	21.8	21.8	22.5	24.9
87.5°	9.0	10.0	8.9	9.4	9.3	9.6	9.5	9.5	10.3	9.6	9.7
90°	21.0	20.6	20.3	20.0	19.7	19.2	18.5	18.0	17.4	16.8	14.7
92.5°	28.2	28.4	28.5	28.7	28.9	28.7	28.3	27.7	27.3	26.8	25.6
95°	54.4	54.4	54.4	54.4	54.4	54.0	53.4	52.8	52.3	51.6	50.4
97.5°	83.6	83.7	83.8	83.8	83.9	83.6	82.8	82.1	81.4	80.7	79.8
100°	105.9	105.7	105.3	105.0	104.8	104.3	103.9	103.4	103.0	102.5	101.7
102.5°	128.9	128.9	128.9	129.0	129.1	128.9	128.4	128.0	127.5	127.1	126.0
105°	165.9	165.6	165.3	165.0	164.7	164.5	164.5	164.5	164.5	164.5	163.2
107.5°	204.6	204.7	204.9	205.1	205.3	205.2	204.6	204.1	203.7	203.1	202.6
110°	230.8	231.0	231.4	231.7	232.0	231.8	231.2	230.6	230.0	229.3	229.1



TEST NUMBER: P332343-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	258.7	258.7	258.8	258.9	258.9	258.6	257.8	257.1	256.4	255.6	255.6
115°	297.0	297.1	297.3	297.5	297.7	297.7	297.5	297.3	297.1	297.0	297.3
117.5°	335.9	336.4	336.8	337.2	337.6	337.9	337.9	338.0	338.0	338.0	338.4
120°	363.2	363.6	363.8	364.2	364.4	364.7	364.9	365.0	365.2	365.3	366.1
122.5°	389.4	389.9	390.3	390.7	391.2	391.6	392.0	392.4	392.8	393.2	393.6
125°	428.7	429.4	430.0	430.6	431.2	431.9	432.5	433.1	433.7	434.4	434.6
127.5°	468.0	468.7	469.4	470.1	470.8	471.6	472.4	473.3	474.2	475.0	475.4
130°	493.6	494.7	495.8	496.9	497.9	498.8	499.4	500.1	500.6	501.2	501.8
132.5°	520.4	521.2	522.0	522.9	523.7	524.5	525.2	526.0	526.7	527.4	527.8
135°	562.0	562.2	562.6	562.8	563.2	563.7	564.3	564.9	565.5	566.1	566.2
137.5°	598.6	599.2	599.8	600.4	600.9	601.5	602.3	602.9	603.5	604.1	603.8
140°	622.6	623.7	624.7	625.8	627.0	627.5	627.7	627.9	628.0	628.1	628.0
142.5°	647.1	647.9	648.8	649.6	650.5	650.9	651.1	651.3	651.4	651.6	651.3
145°	682.5	683.1	683.8	684.4	685.0	685.4	685.5	685.7	685.9	686.0	685.5
147.5°	714.1	715.0	715.9	716.8	717.7	718.3	718.3	718.3	718.3	718.3	717.8
150°	734.1	735.0	736.0	736.9	737.9	738.3	738.3	738.3	738.3	738.3	738.0
152.5°	753.7	754.5	755.3	756.1	756.9	757.2	756.9	756.6	756.4	756.2	756.0
155°	780.2	781.2	782.3	783.4	784.4	784.7	784.1	783.5	782.8	782.2	782.1
157.5°	804.2	805.1	806.0	806.9	807.7	807.8	807.2	806.6	805.9	805.2	805.1
160°	819.8	820.5	821.1	821.7	822.3	822.2	821.5	820.7	819.9	819.2	819.2
162.5°	831.6	832.6	833.6	834.6	835.5	835.7	834.9	834.1	833.3	832.6	832.4
165°	848.5	849.5	850.6	851.8	852.8	852.9	851.9	851.0	850.1	849.2	849.2
167.5°	862.8	863.8	864.8	865.7	866.7	866.7	865.7	864.8	863.8	862.8	862.7
170°	870.0	871.2	872.3	873.3	874.4	874.4	873.3	872.3	871.2	870.0	870.0
172.5°	875.7	876.7	877.8	878.9	880.0	880.0	879.1	878.2	877.2	876.2	876.2
175°	881.9	883.0	884.1	885.2	886.3	886.4	885.4	884.5	883.6	882.6	882.6
177.5°	885.3	886.2	887.0	887.9	888.8	888.8	888.1	887.3	886.5	885.8	885.8
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P332343-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1463.7	1462.2	1455.5	1447.7	1437.4	1430.7	1425.3	1422.5	1413.7	1403.0	1395.7
5°	1554.1	1535.9	1516.5	1492.8	1471.0	1448.5	1434.6	1418.2	1398.1	1375.7	1359.9
7.5°	1651.0	1615.2	1576.8	1537.1	1497.9	1462.8	1431.6	1405.1	1373.1	1341.0	1318.4
10°	1725.3	1673.0	1619.1	1563.8	1513.4	1466.2	1429.7	1393.9	1355.7	1318.7	1290.8
12.5°	1792.7	1724.0	1661.8	1593.9	1529.5	1472.9	1420.5	1378.4	1332.4	1292.9	1261.1
15°	1878.1	1807.8	1732.5	1629.3	1543.8	1472.2	1408.5	1353.3	1297.4	1248.8	1217.9
17.5°	1958.0	1852.1	1751.0	1664.9	1553.7	1464.3	1386.5	1320.4	1259.2	1207.7	1169.7
20°	1991.0	1888.5	1778.6	1668.8	1559.6	1459.5	1369.0	1296.2	1232.5	1174.2	1139.1
22.5°	2010.9	1894.8	1779.1	1661.1	1545.0	1441.0	1351.6	1271.5	1202.4	1147.0	1103.6
25°	2034.1	1895.8	1768.4	1651.8	1533.5	1420.6	1314.4	1229.5	1154.9	1095.9	1049.8
27.5°	2049.4	1886.7	1736.1	1606.5	1486.5	1374.1	1276.8	1186.7	1111.0	1048.7	999.3
30°	2052.4	1879.4	1711.3	1571.1	1449.1	1345.9	1242.8	1156.6	1076.6	1010.4	964.3
32.5°	2056.2	1861.4	1677.8	1528.8	1404.0	1301.8	1208.4	1126.1	1044.0	978.8	931.7
35°	2040.2	1851.5	1626.9	1455.8	1330.8	1231.9	1147.5	1071.7	991.0	927.8	879.9
37.5°	1971.2	1812.0	1574.2	1373.5	1242.8	1151.2	1082.4	1016.4	942.3	874.2	829.0
40°	1901.8	1773.2	1533.5	1323.5	1187.0	1092.9	1031.0	977.0	905.4	841.7	793.2
42.5°	1798.4	1720.3	1494.7	1271.0	1123.8	1033.2	981.0	930.4	867.5	802.8	757.2
45°	1608.7	1619.1	1415.1	1187.6	1036.4	945.5	896.3	861.1	805.3	751.9	705.2
47.5°	1370.8	1467.3	1321.8	1098.6	944.3	858.9	815.9	785.2	747.6	695.2	652.6
50°	1215.5	1353.3	1247.1	1038.9	886.6	801.6	759.1	734.2	701.5	660.2	619.6
52.5°	1072.3	1220.2	1156.7	972.4	823.9	746.3	704.8	684.3	658.3	619.5	582.6
55°	874.4	1024.3	1009.8	872.0	730.0	660.2	628.7	605.6	588.0	558.9	529.8
57.5°	707.3	849.4	856.9	760.4	647.3	578.3	551.2	533.8	522.3	500.2	473.3
60°	602.0	732.5	758.0	685.1	588.0	527.4	500.6	486.7	477.6	459.9	439.3
62.5°	514.6	625.6	654.5	602.1	531.2	474.4	453.5	440.1	433.9	418.7	400.6
65°	393.9	486.1	514.0	484.8	447.8	402.3	385.3	373.8	368.4	359.9	346.5
67.5°	296.1	363.4	394.0	373.4	360.1	331.4	320.6	314.3	309.5	303.6	292.5
70°	237.9	287.7	319.2	313.7	302.8	287.7	279.7	275.5	270.6	265.8	256.1
72.5°	191.3	225.5	255.1	257.9	249.0	245.9	239.0	237.2	234.3	228.5	223.1
75°	126.8	150.5	171.1	179.1	182.6	185.7	182.6	182.1	181.5	176.6	173.5
77.5°	83.1	95.9	108.9	122.3	128.0	132.2	133.1	135.4	133.8	131.2	129.7
80°	63.8	66.8	75.9	87.4	96.5	100.1	102.5	103.8	103.2	102.5	100.1
82.5°	46.3	48.8	53.1	61.2	68.8	74.9	76.3	76.1	77.4	77.8	75.9
85°	24.9	25.5	26.7	27.9	32.2	38.9	40.7	41.9	43.1	43.1	39.4
87.5°	10.3	9.5	10.0	9.6	10.8	11.0	13.6	15.7	16.5	14.8	15.2
90°	12.7	10.7	8.6	6.9	5.4	3.8	2.2	0.7	2.2	3.8	5.4
92.5°	24.5	23.4	22.2	21.0	20.1	19.0	17.9	16.9	17.9	19.0	20.1
95°	49.1	47.9	46.6	45.5	44.4	43.3	42.2	41.1	42.2	43.3	44.4
97.5°	78.9	78.0	77.1	76.3	75.4	74.6	73.8	73.0	73.8	74.6	75.4
100°	100.9	100.1	99.4	98.5	97.6	96.7	95.8	94.8	95.8	96.7	97.6
102.5°	125.0	123.9	123.0	122.2	121.6	121.0	120.5	119.9	120.5	121.0	121.6
105°	161.8	160.3	159.0	158.1	157.8	157.5	157.2	156.9	157.2	157.5	157.8
107.5°	202.1	201.5	200.9	200.5	200.4	200.2	200.0	199.8	200.0	200.2	200.4
110°	228.7	228.5	228.1	227.8	227.5	227.2	226.9	226.6	226.9	227.2	227.5





TEST NUMBER: P332343-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	255.5	255.4	255.3	255.2	255.0	254.9	254.7	254.5	254.7	254.9	255.0
115°	297.7	297.9	298.3	298.2	297.7	297.2	296.8	296.3	296.8	297.2	297.7
117.5°	338.8	339.2	339.6	339.7	339.3	339.0	338.8	338.4	338.8	339.0	339.3
120°	366.8	367.7	368.5	368.4	367.4	366.5	365.5	364.6	365.5	366.5	367.4
122.5°	394.0	394.4	394.8	394.7	394.0	393.3	392.6	392.0	392.6	393.3	394.0
125°	435.0	435.2	435.6	435.5	435.1	434.5	434.1	433.6	434.1	434.5	435.1
127.5°	475.7	476.1	476.4	476.1	475.1	474.1	473.1	472.2	473.1	474.1	475.1
130°	502.2	502.7	503.1	502.7	501.5	500.2	499.0	497.8	499.0	500.2	501.5
132.5°	528.2	528.5	528.9	528.4	527.2	525.9	524.7	523.4	524.7	525.9	527.2
135°	566.4	566.6	566.8	566.3	565.4	564.5	563.6	562.6	563.6	564.5	565.4
137.5°	603.3	603.0	602.5	602.0	601.2	600.4	599.7	598.9	599.7	600.4	601.2
140°	627.9	627.7	627.5	627.1	626.3	625.5	624.7	623.9	624.7	625.5	626.3
142.5°	651.0	650.8	650.5	650.0	649.2	648.4	647.6	646.8	647.6	648.4	649.2
145°	685.1	684.7	684.1	683.8	683.5	683.1	682.9	682.5	682.9	683.1	683.5
147.5°	717.4	716.9	716.5	716.0	715.4	714.9	714.3	713.8	714.3	714.9	715.4
150°	737.7	737.4	737.1	736.7	736.5	736.1	735.8	735.5	735.8	736.1	736.5
152.5°	755.8	755.6	755.5	755.1	754.7	754.2	753.8	753.4	753.8	754.2	754.7
155°	781.9	781.8	781.6	781.5	781.5	781.5	781.5	781.5	781.5	781.5	781.5
157.5°	805.0	804.9	804.8	804.8	804.9	805.1	805.3	805.5	805.3	805.1	804.9
160°	819.2	819.2	819.2	819.3	819.7	819.9	820.3	820.6	820.3	819.9	819.7
162.5°	832.3	832.2	832.1	832.2	832.7	833.1	833.6	833.9	833.6	833.1	832.7
165°	849.2	849.2	849.2	849.4	849.9	850.3	850.8	851.2	850.8	850.3	849.9
167.5°	862.6	862.5	862.4	862.6	863.2	863.8	864.4	865.0	864.4	863.8	863.2
170°	870.0	870.0	870.0	870.4	871.0	871.6	872.3	872.9	872.3	871.6	871.0
172.5°	876.2	876.2	876.2	876.6	877.2	877.8	878.4	879.0	878.4	877.8	877.2
175°	882.6	882.6	882.6	883.0	883.6	884.2	884.8	885.4	884.8	884.2	883.6
177.5°	885.8	885.8	885.8	886.1	886.5	887.1	887.6	888.1	887.6	887.1	886.5
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P332343-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1393.3	1387.0	1382.6	1372.9	1366.6	1359.8	1353.0	1357.4	1356.9	1356.4	1356.4
5°	1346.6	1332.6	1319.9	1303.5	1293.2	1280.4	1270.7	1269.5	1271.9	1263.5	1258.6
7.5°	1300.2	1281.1	1263.1	1245.0	1225.8	1210.5	1201.0	1196.4	1190.3	1185.0	1179.6
10°	1267.7	1245.3	1227.6	1205.1	1184.5	1166.4	1154.9	1146.9	1142.6	1138.4	1130.5
12.5°	1234.2	1212.2	1189.8	1164.4	1144.8	1123.6	1115.0	1106.2	1098.1	1093.2	1082.4
15°	1185.2	1156.6	1133.0	1106.3	1084.4	1063.8	1051.7	1034.0	1031.6	1025.6	1014.7
17.5°	1136.0	1105.0	1072.4	1052.7	1028.0	1006.5	988.0	982.1	964.7	958.2	948.7
20°	1097.2	1068.6	1043.7	1017.7	981.9	961.8	947.3	939.4	925.4	916.9	910.9
22.5°	1063.6	1034.7	1005.9	975.4	945.9	923.5	912.8	900.5	892.9	881.0	874.4
25°	1015.8	984.3	949.7	916.9	895.7	878.7	861.7	850.8	839.9	834.4	822.2
27.5°	960.3	927.3	894.9	870.0	844.0	827.2	811.8	802.1	789.0	779.8	773.1
30°	929.7	890.8	862.9	840.4	807.1	791.3	779.8	767.7	758.0	748.2	741.5
32.5°	894.2	858.8	832.3	804.6	778.9	761.7	746.8	736.1	727.8	718.6	711.9
35°	838.7	809.0	781.6	753.7	734.9	717.3	699.7	690.5	682.7	674.2	668.2
37.5°	788.4	760.6	734.7	708.2	684.8	670.6	656.4	649.4	638.7	633.0	626.9
40°	757.3	730.0	702.1	676.6	652.4	641.4	628.7	618.4	608.7	604.4	597.7
42.5°	723.4	696.1	672.5	645.1	625.2	610.4	598.6	587.3	580.1	573.8	570.1
45°	673.0	648.7	625.6	598.3	579.5	566.8	553.4	543.1	536.5	532.2	525.5
47.5°	624.1	599.8	576.4	552.6	534.4	519.8	506.5	499.3	490.4	485.3	480.7
50°	588.6	566.8	541.9	520.0	501.9	487.3	476.4	467.3	459.4	452.7	449.7
52.5°	556.1	532.8	511.3	491.0	471.7	455.2	445.3	435.7	429.8	422.1	418.6
55°	502.5	480.0	461.8	441.8	422.9	409.0	396.9	388.3	382.3	373.8	369.0
57.5°	452.1	431.9	410.2	392.9	373.4	361.7	351.6	340.1	332.7	326.0	321.3
60°	418.1	395.0	376.2	359.9	342.9	327.7	318.6	309.5	301.6	294.9	290.7
62.5°	382.6	362.6	344.6	326.8	311.3	298.1	287.5	279.9	273.0	268.7	264.5
65°	328.3	312.5	294.4	279.7	265.2	255.5	247.0	240.3	235.4	232.4	228.8
67.5°	278.3	263.0	247.1	232.8	223.1	215.7	210.1	204.4	202.0	198.0	195.6
70°	245.8	230.0	216.1	205.1	195.4	189.9	186.3	182.1	179.6	174.8	172.4
72.5°	210.4	198.9	188.9	179.9	172.1	167.1	162.5	157.3	153.4	148.0	145.6
75°	165.7	155.3	147.5	141.4	136.5	129.8	123.1	117.7	115.9	114.0	113.5
77.5°	122.7	116.2	110.5	105.3	99.2	94.4	93.0	91.8	91.4	90.4	90.4
80°	96.5	90.4	86.1	80.1	76.4	76.4	76.4	75.3	75.9	75.9	75.9
82.5°	71.7	66.2	63.8	61.6	60.9	61.4	61.4	61.6	61.3	62.2	61.8
85°	37.0	37.6	38.9	38.3	38.9	38.9	40.0	39.4	40.0	38.9	40.0
87.5°	15.0	16.8	17.7	18.5	19.4	19.4	20.0	20.1	20.7	20.9	21.0
90°	6.9	8.6	10.7	12.7	14.7	16.8	17.4	18.0	18.5	19.2	19.7
92.5°	21.0	22.2	23.4	24.5	25.6	26.8	27.3	27.7	28.3	28.7	28.9
95°	45.5	46.6	47.9	49.1	50.4	51.6	52.3	52.8	53.4	54.0	54.4
97.5°	76.3	77.1	78.0	78.9	79.8	80.7	81.4	82.1	82.8	83.6	83.9
100°	98.5	99.4	100.1	100.9	101.7	102.5	103.0	103.4	103.9	104.3	104.8
102.5°	122.2	123.0	123.9	125.0	126.0	127.1	127.5	128.0	128.4	128.9	129.1
105°	158.1	159.0	160.3	161.8	163.2	164.5	164.5	164.5	164.5	164.5	164.7
107.5°	200.5	200.9	201.5	202.1	202.6	203.1	203.7	204.1	204.6	205.2	205.3
110°	227.8	228.1	228.5	228.7	229.1	229.3	230.0	230.6	231.2	231.8	232.0



TEST NUMBER: P332343-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	255.2	255.3	255.4	255.5	255.6	255.6	256.4	257.1	257.8	258.6	258.9
115°	298.2	298.3	297.9	297.7	297.3	297.0	297.1	297.3	297.5	297.7	297.7
117.5°	339.7	339.6	339.2	338.8	338.4	338.0	338.0	338.0	337.9	337.9	337.6
120°	368.4	368.5	367.7	366.8	366.1	365.3	365.2	365.0	364.9	364.7	364.4
122.5°	394.7	394.8	394.4	394.0	393.6	393.2	392.8	392.4	392.0	391.6	391.2
125°	435.5	435.6	435.2	435.0	434.6	434.4	433.7	433.1	432.5	431.9	431.2
127.5°	476.1	476.4	476.1	475.7	475.4	475.0	474.2	473.3	472.4	471.6	470.8
130°	502.7	503.1	502.7	502.2	501.8	501.2	500.6	500.1	499.4	498.8	497.9
132.5°	528.4	528.9	528.5	528.2	527.8	527.4	526.7	526.0	525.2	524.5	523.7
135°	566.3	566.8	566.6	566.4	566.2	566.1	565.5	564.9	564.3	563.7	563.2
137.5°	602.0	602.5	603.0	603.3	603.8	604.1	603.5	602.9	602.3	601.5	600.9
140°	627.1	627.5	627.7	627.9	628.0	628.1	628.0	627.9	627.7	627.5	627.0
142.5°	650.0	650.5	650.8	651.0	651.3	651.6	651.4	651.3	651.1	650.9	650.5
145°	683.8	684.1	684.7	685.1	685.5	686.0	685.9	685.7	685.5	685.4	685.0
147.5°	716.0	716.5	716.9	717.4	717.8	718.3	718.3	718.3	718.3	718.3	717.7
150°	736.7	737.1	737.4	737.7	738.0	738.3	738.3	738.3	738.3	738.3	737.9
152.5°	755.1	755.5	755.6	755.8	756.0	756.2	756.4	756.6	756.9	757.2	756.9
155°	781.5	781.6	781.8	781.9	782.1	782.2	782.8	783.5	784.1	784.7	784.4
157.5°	804.8	804.8	804.9	805.0	805.1	805.2	805.9	806.6	807.2	807.8	807.7
160°	819.3	819.2	819.2	819.2	819.2	819.2	819.9	820.7	821.5	822.2	822.3
162.5°	832.2	832.1	832.2	832.3	832.4	832.6	833.3	834.1	834.9	835.7	835.5
165°	849.4	849.2	849.2	849.2	849.2	849.2	850.1	851.0	851.9	852.9	852.8
167.5°	862.6	862.4	862.5	862.6	862.7	862.8	863.8	864.8	865.7	866.7	866.7
170°	870.4	870.0	870.0	870.0	870.0	870.0	871.2	872.3	873.3	874.4	874.4
172.5°	876.6	876.2	876.2	876.2	876.2	876.2	877.2	878.2	879.1	880.0	880.0
175°	883.0	882.6	882.6	882.6	882.6	882.6	883.6	884.5	885.4	886.4	886.3
177.5°	886.1	885.8	885.8	885.8	885.8	885.8	886.5	887.3	888.1	888.8	888.8
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P332343-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1350.6	1350.1	1350.6	1348.6	1350.6	1350.1	1350.6	1356.4	1356.4	1356.9	1357.4
5°	1256.8	1256.2	1254.4	1248.8	1254.4	1256.2	1256.8	1258.6	1263.5	1271.9	1269.5
7.5°	1174.8	1174.0	1168.7	1168.8	1168.7	1174.0	1174.8	1179.6	1185.0	1190.3	1196.4
10°	1126.3	1126.9	1119.6	1115.4	1119.6	1126.9	1126.3	1130.5	1138.4	1142.6	1146.9
12.5°	1079.2	1076.4	1070.6	1065.9	1070.6	1076.4	1079.2	1082.4	1093.2	1098.1	1106.2
15°	1017.1	1011.0	996.4	997.6	996.4	1011.0	1017.1	1014.7	1025.6	1031.6	1034.0
17.5°	943.9	939.4	939.1	930.7	939.1	939.4	943.9	948.7	958.2	964.7	982.1
20°	901.2	898.1	899.3	890.8	899.3	898.1	901.2	910.9	916.9	925.4	939.4
22.5°	867.6	864.6	859.5	856.8	859.5	864.6	867.6	874.4	881.0	892.9	900.5
25°	818.6	813.8	809.0	812.0	809.0	813.8	818.6	822.2	834.4	839.9	850.8
27.5°	769.6	766.0	761.1	760.5	761.1	766.0	769.6	773.1	779.8	789.0	802.1
30°	738.5	734.9	732.5	729.4	732.5	734.9	738.5	741.5	748.2	758.0	767.7
32.5°	706.9	706.2	701.9	701.2	701.9	706.2	706.9	711.9	718.6	727.8	736.1
35°	665.7	662.1	660.8	661.5	660.8	662.1	665.7	668.2	674.2	682.7	690.5
37.5°	626.5	621.6	619.5	617.2	619.5	621.6	626.5	626.9	633.0	638.7	649.4
40°	598.3	593.5	592.3	591.0	592.3	593.5	598.3	597.7	604.4	608.7	618.4
42.5°	566.8	564.8	564.1	562.0	564.1	564.8	566.8	570.1	573.8	580.1	587.3
45°	523.7	523.1	519.4	520.7	519.4	523.1	523.7	525.5	532.2	536.5	543.1
47.5°	478.3	475.6	473.1	474.7	473.1	475.6	478.3	480.7	485.3	490.4	499.3
50°	447.3	446.0	440.6	441.8	440.6	446.0	447.3	449.7	452.7	459.4	467.3
52.5°	416.2	411.5	409.5	408.8	409.5	411.5	416.2	418.6	422.1	429.8	435.7
55°	364.7	359.3	356.9	355.6	356.9	359.3	364.7	369.0	373.8	382.3	388.3
57.5°	314.2	312.7	310.9	312.2	310.9	312.7	314.2	321.3	326.0	332.7	340.1
60°	284.6	284.6	284.6	284.0	284.6	284.6	284.6	290.7	294.9	301.6	309.5
62.5°	261.8	260.3	259.8	260.7	259.8	260.3	261.8	264.5	268.7	273.0	279.9
65°	226.9	226.3	223.9	223.3	223.9	226.3	226.9	228.8	232.4	235.4	240.3
67.5°	194.0	191.9	191.2	190.3	191.2	191.9	194.0	195.6	198.0	202.0	204.4
70°	169.3	168.1	164.4	165.1	164.4	168.1	169.3	172.4	174.8	179.6	182.1
72.5°	142.6	141.4	140.6	139.8	140.6	141.4	142.6	145.6	148.0	153.4	157.3
75°	112.9	112.3	111.6	114.0	111.6	112.3	112.9	113.5	114.0	115.9	117.7
77.5°	90.4	90.4	90.8	89.8	90.8	90.4	90.4	90.4	90.4	91.4	91.8
80°	75.9	75.9	75.3	75.3	75.3	75.9	75.9	75.9	75.9	75.9	75.3
82.5°	60.8	61.3	61.6	60.7	61.6	61.3	60.8	61.8	62.2	61.3	61.6
85°	40.0	39.4	40.7	40.0	40.7	39.4	40.0	40.0	38.9	40.0	39.4
87.5°	21.9	21.0	21.1	21.7	21.1	21.0	21.9	21.0	20.9	20.7	20.1
90°	20.0	20.3	20.6	21.0	20.6	20.3	20.0	19.7	19.2	18.5	18.0
92.5°	28.7	28.5	28.4	28.2	28.4	28.5	28.7	28.9	28.7	28.3	27.7
95°	54.4	54.4	54.4	54.4	54.4	54.4	54.4	54.4	54.0	53.4	52.8
97.5°	83.8	83.8	83.7	83.6	83.7	83.8	83.8	83.9	83.6	82.8	82.1
100°	105.0	105.3	105.7	105.9	105.7	105.3	105.0	104.8	104.3	103.9	103.4
102.5°	129.0	128.9	128.9	128.9	128.9	128.9	129.0	129.1	128.9	128.4	128.0
105°	165.0	165.3	165.6	165.9	165.6	165.3	165.0	164.7	164.5	164.5	164.5
107.5°	205.1	204.9	204.7	204.6	204.7	204.9	205.1	205.3	205.2	204.6	204.1
110°	231.7	231.4	231.0	230.8	231.0	231.4	231.7	232.0	231.8	231.2	230.6



TEST NUMBER: P332343-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	258.9	258.8	258.7	258.7	258.7	258.8	258.9	258.9	258.6	257.8	257.1
115°	297.5	297.3	297.1	297.0	297.1	297.3	297.5	297.7	297.7	297.5	297.3
117.5°	337.2	336.8	336.4	335.9	336.4	336.8	337.2	337.6	337.9	337.9	338.0
120°	364.2	363.8	363.6	363.2	363.6	363.8	364.2	364.4	364.7	364.9	365.0
122.5°	390.7	390.3	389.9	389.4	389.9	390.3	390.7	391.2	391.6	392.0	392.4
125°	430.6	430.0	429.4	428.7	429.4	430.0	430.6	431.2	431.9	432.5	433.1
127.5°	470.1	469.4	468.7	468.0	468.7	469.4	470.1	470.8	471.6	472.4	473.3
130°	496.9	495.8	494.7	493.6	494.7	495.8	496.9	497.9	498.8	499.4	500.1
132.5°	522.9	522.0	521.2	520.4	521.2	522.0	522.9	523.7	524.5	525.2	526.0
135°	562.8	562.6	562.2	562.0	562.2	562.6	562.8	563.2	563.7	564.3	564.9
137.5°	600.4	599.8	599.2	598.6	599.2	599.8	600.4	600.9	601.5	602.3	602.9
140°	625.8	624.7	623.7	622.6	623.7	624.7	625.8	627.0	627.5	627.7	627.9
142.5°	649.6	648.8	647.9	647.1	647.9	648.8	649.6	650.5	650.9	651.1	651.3
145°	684.4	683.8	683.1	682.5	683.1	683.8	684.4	685.0	685.4	685.5	685.7
147.5°	716.8	715.9	715.0	714.1	715.0	715.9	716.8	717.7	718.3	718.3	718.3
150°	736.9	736.0	735.0	734.1	735.0	736.0	736.9	737.9	738.3	738.3	738.3
152.5°	756.1	755.3	754.5	753.7	754.5	755.3	756.1	756.9	757.2	756.9	756.6
155°	783.4	782.3	781.2	780.2	781.2	782.3	783.4	784.4	784.7	784.1	783.5
157.5°	806.9	806.0	805.1	804.2	805.1	806.0	806.9	807.7	807.8	807.2	806.6
160°	821.7	821.1	820.5	819.8	820.5	821.1	821.7	822.3	822.2	821.5	820.7
162.5°	834.6	833.6	832.6	831.6	832.6	833.6	834.6	835.5	835.7	834.9	834.1
165°	851.8	850.6	849.5	848.5	849.5	850.6	851.8	852.8	852.9	851.9	851.0
167.5°	865.7	864.8	863.8	862.8	863.8	864.8	865.7	866.7	866.7	865.7	864.8
170°	873.3	872.3	871.2	870.0	871.2	872.3	873.3	874.4	874.4	873.3	872.3
172.5°	878.9	877.8	876.7	875.7	876.7	877.8	878.9	880.0	880.0	879.1	878.2
175°	885.2	884.1	883.0	881.9	883.0	884.1	885.2	886.3	886.4	885.4	884.5
177.5°	887.9	887.0	886.2	885.3	886.2	887.0	887.9	888.8	888.8	888.1	887.3
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P332343-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1353.0	1359.8	1366.6	1372.9	1382.6	1387.0	1393.3	1395.7	1403.0	1413.7	1422.5
5°	1270.7	1280.4	1293.2	1303.5	1319.9	1332.6	1346.6	1359.9	1375.7	1398.1	1418.2
7.5°	1201.0	1210.5	1225.8	1245.0	1263.1	1281.1	1300.2	1318.4	1341.0	1373.1	1405.1
10°	1154.9	1166.4	1184.5	1205.1	1227.6	1245.3	1267.7	1290.8	1318.7	1355.7	1393.9
12.5°	1115.0	1123.6	1144.8	1164.4	1189.8	1212.2	1234.2	1261.1	1292.9	1332.4	1378.4
15°	1051.7	1063.8	1084.4	1106.3	1133.0	1156.6	1185.2	1217.9	1248.8	1297.4	1353.3
17.5°	988.0	1006.5	1028.0	1052.7	1072.4	1105.0	1136.0	1169.7	1207.7	1259.2	1320.4
20°	947.3	961.8	981.9	1017.7	1043.7	1068.6	1097.2	1139.1	1174.2	1232.5	1296.2
22.5°	912.8	923.5	945.9	975.4	1005.9	1034.7	1063.6	1103.6	1147.0	1202.4	1271.5
25°	861.7	878.7	895.7	916.9	949.7	984.3	1015.8	1049.8	1095.9	1154.9	1229.5
27.5°	811.8	827.2	844.0	870.0	894.9	927.3	960.3	999.3	1048.7	1111.0	1186.7
30°	779.8	791.3	807.1	840.4	862.9	890.8	929.7	964.3	1010.4	1076.6	1156.6
32.5°	746.8	761.7	778.9	804.6	832.3	858.8	894.2	931.7	978.8	1044.0	1126.1
35°	699.7	717.3	734.9	753.7	781.6	809.0	838.7	879.9	927.8	991.0	1071.7
37.5°	656.4	670.6	684.8	708.2	734.7	760.6	788.4	829.0	874.2	942.3	1016.4
40°	628.7	641.4	652.4	676.6	702.1	730.0	757.3	793.2	841.7	905.4	977.0
42.5°	598.6	610.4	625.2	645.1	672.5	696.1	723.4	757.2	802.8	867.5	930.4
45°	553.4	566.8	579.5	598.3	625.6	648.7	673.0	705.2	751.9	805.3	861.1
47.5°	506.5	519.8	534.4	552.6	576.4	599.8	624.1	652.6	695.2	747.6	785.2
50°	476.4	487.3	501.9	520.0	541.9	566.8	588.6	619.6	660.2	701.5	734.2
52.5°	445.3	455.2	471.7	491.0	511.3	532.8	556.1	582.6	619.5	658.3	684.3
55°	396.9	409.0	422.9	441.8	461.8	480.0	502.5	529.8	558.9	588.0	605.6
57.5°	351.6	361.7	373.4	392.9	410.2	431.9	452.1	473.3	500.2	522.3	533.8
60°	318.6	327.7	342.9	359.9	376.2	395.0	418.1	439.3	459.9	477.6	486.7
62.5°	287.5	298.1	311.3	326.8	344.6	362.6	382.6	400.6	418.7	433.9	440.1
65°	247.0	255.5	265.2	279.7	294.4	312.5	328.3	346.5	359.9	368.4	373.8
67.5°	210.1	215.7	223.1	232.8	247.1	263.0	278.3	292.5	303.6	309.5	314.3
70°	186.3	189.9	195.4	205.1	216.1	230.0	245.8	256.1	265.8	270.6	275.5
72.5°	162.5	167.1	172.1	179.9	188.9	198.9	210.4	223.1	228.5	234.3	237.2
75°	123.1	129.8	136.5	141.4	147.5	155.3	165.7	173.5	176.6	181.5	182.1
77.5°	93.0	94.4	99.2	105.3	110.5	116.2	122.7	129.7	131.2	133.8	135.4
80°	76.4	76.4	76.4	80.1	86.1	90.4	96.5	100.1	102.5	103.2	103.8
82.5°	61.4	61.4	60.9	61.6	63.8	66.2	71.7	75.9	77.8	77.4	76.1
85°	40.0	38.9	38.9	38.3	38.9	37.6	37.0	39.4	43.1	43.1	41.9
87.5°	20.0	19.4	19.4	18.5	17.7	16.8	15.0	15.2	14.8	16.5	15.7
90°	17.4	16.8	14.7	12.7	10.7	8.6	6.9	5.4	3.8	2.2	0.7
92.5°	27.3	26.8	25.6	24.5	23.4	22.2	21.0	20.1	19.0	17.9	16.9
95°	52.3	51.6	50.4	49.1	47.9	46.6	45.5	44.4	43.3	42.2	41.1
97.5°	81.4	80.7	79.8	78.9	78.0	77.1	76.3	75.4	74.6	73.8	73.0
100°	103.0	102.5	101.7	100.9	100.1	99.4	98.5	97.6	96.7	95.8	94.8
102.5°	127.5	127.1	126.0	125.0	123.9	123.0	122.2	121.6	121.0	120.5	119.9
105°	164.5	164.5	163.2	161.8	160.3	159.0	158.1	157.8	157.5	157.2	156.9
107.5°	203.7	203.1	202.6	202.1	201.5	200.9	200.5	200.4	200.2	200.0	199.8
110°	230.0	229.3	229.1	228.7	228.5	228.1	227.8	227.5	227.2	226.9	226.6



TEST NUMBER: P332343-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	256.4	255.6	255.6	255.5	255.4	255.3	255.2	255.0	254.9	254.7	254.5
115°	297.1	297.0	297.3	297.7	297.9	298.3	298.2	297.7	297.2	296.8	296.3
117.5°	338.0	338.0	338.4	338.8	339.2	339.6	339.7	339.3	339.0	338.8	338.4
120°	365.2	365.3	366.1	366.8	367.7	368.5	368.4	367.4	366.5	365.5	364.6
122.5°	392.8	393.2	393.6	394.0	394.4	394.8	394.7	394.0	393.3	392.6	392.0
125°	433.7	434.4	434.6	435.0	435.2	435.6	435.5	435.1	434.5	434.1	433.6
127.5°	474.2	475.0	475.4	475.7	476.1	476.4	476.1	475.1	474.1	473.1	472.2
130°	500.6	501.2	501.8	502.2	502.7	503.1	502.7	501.5	500.2	499.0	497.8
132.5°	526.7	527.4	527.8	528.2	528.5	528.9	528.4	527.2	525.9	524.7	523.4
135°	565.5	566.1	566.2	566.4	566.6	566.8	566.3	565.4	564.5	563.6	562.6
137.5°	603.5	604.1	603.8	603.3	603.0	602.5	602.0	601.2	600.4	599.7	598.9
140°	628.0	628.1	628.0	627.9	627.7	627.5	627.1	626.3	625.5	624.7	623.9
142.5°	651.4	651.6	651.3	651.0	650.8	650.5	650.0	649.2	648.4	647.6	646.8
145°	685.9	686.0	685.5	685.1	684.7	684.1	683.8	683.5	683.1	682.9	682.5
147.5°	718.3	718.3	717.8	717.4	716.9	716.5	716.0	715.4	714.9	714.3	713.8
150°	738.3	738.3	738.0	737.7	737.4	737.1	736.7	736.5	736.1	735.8	735.5
152.5°	756.4	756.2	756.0	755.8	755.6	755.5	755.1	754.7	754.2	753.8	753.4
155°	782.8	782.2	782.1	781.9	781.8	781.6	781.5	781.5	781.5	781.5	781.5
157.5°	805.9	805.2	805.1	805.0	804.9	804.8	804.8	804.9	805.1	805.3	805.5
160°	819.9	819.2	819.2	819.2	819.2	819.2	819.3	819.7	819.9	820.3	820.6
162.5°	833.3	832.6	832.4	832.3	832.2	832.1	832.2	832.7	833.1	833.6	833.9
165°	850.1	849.2	849.2	849.2	849.2	849.2	849.4	849.9	850.3	850.8	851.2
167.5°	863.8	862.8	862.7	862.6	862.5	862.4	862.6	863.2	863.8	864.4	865.0
170°	871.2	870.0	870.0	870.0	870.0	870.0	870.4	871.0	871.6	872.3	872.9
172.5°	877.2	876.2	876.2	876.2	876.2	876.2	876.6	877.2	877.8	878.4	879.0
175°	883.6	882.6	882.6	882.6	882.6	882.6	883.0	883.6	884.2	884.8	885.4
177.5°	886.5	885.8	885.8	885.8	885.8	885.8	886.1	886.5	887.1	887.6	888.1
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P332343-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1425.3	1430.7	1437.4	1447.7	1455.5	1462.2	1463.7	1465.6	1470.5	1478.7	1485.1
5°	1434.6	1448.5	1471.0	1492.8	1516.5	1535.9	1554.1	1566.8	1579.0	1604.5	1625.1
7.5°	1431.6	1462.8	1497.9	1537.1	1576.8	1615.2	1651.0	1682.9	1714.7	1751.9	1794.2
10°	1429.7	1466.2	1513.4	1563.8	1619.1	1673.0	1725.3	1765.9	1813.2	1855.7	1909.7
12.5°	1420.5	1472.9	1529.5	1593.9	1661.8	1724.0	1792.7	1848.9	1903.1	1964.4	2027.2
15°	1408.5	1472.2	1543.8	1629.3	1732.5	1807.8	1878.1	1975.9	2042.6	2109.3	2199.2
17.5°	1386.5	1464.3	1553.7	1664.9	1751.0	1852.1	1958.0	2035.2	2125.1	2219.2	2300.5
20°	1369.0	1459.5	1559.6	1668.8	1778.6	1888.5	1991.0	2083.3	2176.1	2284.7	2351.5
22.5°	1351.6	1441.0	1545.0	1661.1	1779.1	1894.8	2010.9	2119.2	2223.7	2333.3	2418.5
25°	1314.4	1420.6	1533.5	1651.8	1768.4	1895.8	2034.1	2154.9	2284.1	2397.0	2477.7
27.5°	1276.8	1374.1	1486.5	1606.5	1736.1	1886.7	2049.4	2186.7	2316.2	2397.0	2422.4
30°	1242.8	1345.9	1449.1	1571.1	1711.3	1879.4	2052.4	2209.5	2315.7	2350.9	2324.8
32.5°	1208.4	1301.8	1404.0	1528.8	1677.8	1861.4	2056.2	2195.9	2259.9	2232.9	2126.7
35°	1147.5	1231.9	1330.8	1455.8	1626.9	1851.5	2040.2	2134.8	2119.1	1967.4	1767.1
37.5°	1082.4	1151.2	1242.8	1373.5	1574.2	1812.0	1971.2	1985.2	1848.7	1615.8	1384.5
40°	1031.0	1092.9	1187.0	1323.5	1533.5	1773.2	1901.8	1845.4	1633.6	1374.5	1181.5
42.5°	981.0	1033.2	1123.8	1271.0	1494.7	1720.3	1798.4	1675.5	1431.2	1186.2	1010.7
45°	896.3	945.5	1036.4	1187.6	1415.1	1619.1	1608.7	1395.1	1150.6	953.3	807.7
47.5°	815.9	858.9	944.3	1098.6	1321.8	1467.3	1370.8	1143.5	936.1	777.8	674.0
50°	759.1	801.6	886.6	1038.9	1247.1	1353.3	1215.5	996.4	806.5	675.4	592.9
52.5°	704.8	746.3	823.9	972.4	1156.7	1220.2	1072.3	869.2	710.9	597.7	526.8
55°	628.7	660.2	730.0	872.0	1009.8	1024.3	874.4	704.5	574.1	495.2	446.7
57.5°	551.2	578.3	647.3	760.4	856.9	849.4	707.3	560.4	472.5	413.8	378.7
60°	500.6	527.4	588.0	685.1	758.0	732.5	602.0	483.7	408.4	365.3	337.4
62.5°	453.5	474.4	531.2	602.1	654.5	625.6	514.6	416.7	357.0	320.7	298.5
65°	385.3	402.3	447.8	484.8	514.0	486.1	393.9	325.8	282.8	257.3	242.1
67.5°	320.6	331.4	360.1	373.4	394.0	363.4	296.1	250.7	226.1	204.6	194.0
70°	279.7	287.7	302.8	313.7	319.2	287.7	237.9	204.5	183.9	168.7	162.0
72.5°	239.0	245.9	249.0	257.9	255.1	225.5	191.3	164.7	149.9	139.6	131.0
75°	182.6	185.7	182.6	179.1	171.1	150.5	126.8	113.5	102.5	97.7	94.7
77.5°	133.1	132.2	128.0	122.3	108.9	95.9	83.1	78.6	73.9	71.3	70.3
80°	102.5	100.1	96.5	87.4	75.9	66.8	63.8	60.7	58.9	55.8	55.2
82.5°	76.3	74.9	68.8	61.2	53.1	48.8	46.3	45.1	43.3	41.7	41.6
85°	40.7	38.9	32.2	27.9	26.7	25.5	24.9	24.9	22.5	21.8	21.8
87.5°	13.6	11.0	10.8	9.6	10.0	9.5	10.3	9.7	9.6	10.3	9.5
90°	2.2	3.8	5.4	6.9	8.6	10.7	12.7	14.7	16.8	17.4	18.0
92.5°	17.9	19.0	20.1	21.0	22.2	23.4	24.5	25.6	26.8	27.3	27.7
95°	42.2	43.3	44.4	45.5	46.6	47.9	49.1	50.4	51.6	52.3	52.8
97.5°	73.8	74.6	75.4	76.3	77.1	78.0	78.9	79.8	80.7	81.4	82.1
100°	95.8	96.7	97.6	98.5	99.4	100.1	100.9	101.7	102.5	103.0	103.4
102.5°	120.5	121.0	121.6	122.2	123.0	123.9	125.0	126.0	127.1	127.5	128.0
105°	157.2	157.5	157.8	158.1	159.0	160.3	161.8	163.2	164.5	164.5	164.5
107.5°	200.0	200.2	200.4	200.5	200.9	201.5	202.1	202.6	203.1	203.7	204.1
110°	226.9	227.2	227.5	227.8	228.1	228.5	228.7	229.1	229.3	230.0	230.6





TEST NUMBER: P332343-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	254.7	254.9	255.0	255.2	255.3	255.4	255.5	255.6	255.6	256.4	257.1
115°	296.8	297.2	297.7	298.2	298.3	297.9	297.7	297.3	297.0	297.1	297.3
117.5°	338.8	339.0	339.3	339.7	339.6	339.2	338.8	338.4	338.0	338.0	338.0
120°	365.5	366.5	367.4	368.4	368.5	367.7	366.8	366.1	365.3	365.2	365.0
122.5°	392.6	393.3	394.0	394.7	394.8	394.4	394.0	393.6	393.2	392.8	392.4
125°	434.1	434.5	435.1	435.5	435.6	435.2	435.0	434.6	434.4	433.7	433.1
127.5°	473.1	474.1	475.1	476.1	476.4	476.1	475.7	475.4	475.0	474.2	473.3
130°	499.0	500.2	501.5	502.7	503.1	502.7	502.2	501.8	501.2	500.6	500.1
132.5°	524.7	525.9	527.2	528.4	528.9	528.5	528.2	527.8	527.4	526.7	526.0
135°	563.6	564.5	565.4	566.3	566.8	566.6	566.4	566.2	566.1	565.5	564.9
137.5°	599.7	600.4	601.2	602.0	602.5	603.0	603.3	603.8	604.1	603.5	602.9
140°	624.7	625.5	626.3	627.1	627.5	627.7	627.9	628.0	628.1	628.0	627.9
142.5°	647.6	648.4	649.2	650.0	650.5	650.8	651.0	651.3	651.6	651.4	651.3
145°	682.9	683.1	683.5	683.8	684.1	684.7	685.1	685.5	686.0	685.9	685.7
147.5°	714.3	714.9	715.4	716.0	716.5	716.9	717.4	717.8	718.3	718.3	718.3
150°	735.8	736.1	736.5	736.7	737.1	737.4	737.7	738.0	738.3	738.3	738.3
152.5°	753.8	754.2	754.7	755.1	755.5	755.6	755.8	756.0	756.2	756.4	756.6
155°	781.5	781.5	781.5	781.5	781.6	781.8	781.9	782.1	782.2	782.8	783.5
157.5°	805.3	805.1	804.9	804.8	804.8	804.9	805.0	805.1	805.2	805.9	806.6
160°	820.3	819.9	819.7	819.3	819.2	819.2	819.2	819.2	819.2	819.9	820.7
162.5°	833.6	833.1	832.7	832.2	832.1	832.2	832.3	832.4	832.6	833.3	834.1
165°	850.8	850.3	849.9	849.4	849.2	849.2	849.2	849.2	849.2	850.1	851.0
167.5°	864.4	863.8	863.2	862.6	862.4	862.5	862.6	862.7	862.8	863.8	864.8
170°	872.3	871.6	871.0	870.4	870.0	870.0	870.0	870.0	870.0	871.2	872.3
172.5°	878.4	877.8	877.2	876.6	876.2	876.2	876.2	876.2	876.2	877.2	878.2
175°	884.8	884.2	883.6	883.0	882.6	882.6	882.6	882.6	882.6	883.6	884.5
177.5°	887.6	887.1	886.5	886.1	885.8	885.8	885.8	885.8	885.8	886.5	887.3
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P332343-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1495.2	1495.2	1497.2	1504.5	1505.5	1511.7	1509.8
5°	1643.3	1654.8	1659.1	1677.3	1688.2	1693.1	1683.4
7.5°	1824.4	1856.9	1872.3	1891.4	1908.3	1913.3	1900.1
10°	1956.4	1990.4	2018.9	2036.6	2052.9	2063.9	2077.8
12.5°	2084.1	2125.8	2152.9	2177.8	2194.7	2208.5	2210.8
15°	2222.9	2286.0	2333.9	2369.1	2386.7	2395.8	2392.2
17.5°	2362.8	2421.3	2455.4	2491.4	2515.7	2516.9	2517.7
20°	2442.0	2498.9	2538.4	2565.1	2592.4	2591.2	2597.3
22.5°	2494.8	2539.8	2570.0	2589.3	2598.7	2594.1	2595.3
25°	2519.6	2532.9	2527.5	2496.5	2488.7	2460.1	2465.0
27.5°	2391.9	2328.8	2263.5	2179.5	2113.3	2060.3	2063.0
30°	2218.6	2106.9	1979.5	1872.7	1776.8	1750.2	1693.1
32.5°	1976.4	1808.8	1659.6	1560.0	1477.7	1455.5	1405.7
35°	1565.7	1403.0	1249.5	1157.3	1120.8	1069.9	1069.3
37.5°	1216.9	1073.7	992.6	923.4	887.1	856.2	853.2
40°	1023.8	912.0	850.8	801.0	765.3	742.2	736.7
42.5°	888.8	798.4	741.1	710.2	682.7	670.8	661.9
45°	725.8	665.1	625.0	597.1	584.4	575.2	570.4
47.5°	607.1	566.4	539.1	520.6	510.2	500.6	503.2
50°	542.5	509.2	489.1	471.5	463.6	456.9	457.5
52.5°	490.5	460.6	444.4	431.7	421.9	417.1	414.8
55°	416.3	397.4	381.1	372.0	366.5	359.9	358.0
57.5°	355.1	340.5	327.2	316.9	315.6	309.2	310.0
60°	314.3	302.2	291.3	285.8	281.6	276.1	277.9
62.5°	280.9	270.6	260.7	256.2	252.0	248.0	248.8
65°	230.0	220.3	214.2	211.8	210.0	208.1	206.3
67.5°	183.2	177.4	173.5	168.4	164.6	164.0	162.1
70°	154.2	146.2	139.6	132.9	131.1	130.5	131.1
72.5°	123.6	118.6	116.7	113.5	113.2	111.6	112.6
75°	92.8	91.0	89.8	87.4	87.4	87.4	87.4
77.5°	68.5	67.3	66.6	66.2	65.5	64.6	64.6
80°	53.4	52.8	51.5	51.5	51.0	51.5	51.0
82.5°	40.3	40.2	39.0	39.0	38.3	38.0	38.3
85°	20.6	20.1	21.2	20.1	20.6	19.4	20.6
87.5°	9.5	9.6	9.3	9.4	8.9	10.0	9.0
90°	18.5	19.2	19.7	20.0	20.3	20.6	21.0
92.5°	28.3	28.7	28.9	28.7	28.5	28.4	28.2
95°	53.4	54.0	54.4	54.4	54.4	54.4	54.4
97.5°	82.8	83.6	83.9	83.8	83.8	83.7	83.6
100°	103.9	104.3	104.8	105.0	105.3	105.7	105.9
102.5°	128.4	128.9	129.1	129.0	128.9	128.9	128.9
105°	164.5	164.5	164.7	165.0	165.3	165.6	165.9
107.5°	204.6	205.2	205.3	205.1	204.9	204.7	204.6
110°	231.2	231.8	232.0	231.7	231.4	231.0	230.8



TEST NUMBER: P332343-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	257.8	258.6	258.9	258.9	258.8	258.7	258.7
115°	297.5	297.7	297.7	297.5	297.3	297.1	297.0
117.5°	337.9	337.9	337.6	337.2	336.8	336.4	335.9
120°	364.9	364.7	364.4	364.2	363.8	363.6	363.2
122.5°	392.0	391.6	391.2	390.7	390.3	389.9	389.4
125°	432.5	431.9	431.2	430.6	430.0	429.4	428.7
127.5°	472.4	471.6	470.8	470.1	469.4	468.7	468.0
130°	499.4	498.8	497.9	496.9	495.8	494.7	493.6
132.5°	525.2	524.5	523.7	522.9	522.0	521.2	520.4
135°	564.3	563.7	563.2	562.8	562.6	562.2	562.0
137.5°	602.3	601.5	600.9	600.4	599.8	599.2	598.6
140°	627.7	627.5	627.0	625.8	624.7	623.7	622.6
142.5°	651.1	650.9	650.5	649.6	648.8	647.9	647.1
145°	685.5	685.4	685.0	684.4	683.8	683.1	682.5
147.5°	718.3	718.3	717.7	716.8	715.9	715.0	714.1
150°	738.3	738.3	737.9	736.9	736.0	735.0	734.1
152.5°	756.9	757.2	756.9	756.1	755.3	754.5	753.7
155°	784.1	784.7	784.4	783.4	782.3	781.2	780.2
157.5°	807.2	807.8	807.7	806.9	806.0	805.1	804.2
160°	821.5	822.2	822.3	821.7	821.1	820.5	819.8
162.5°	834.9	835.7	835.5	834.6	833.6	832.6	831.6
165°	851.9	852.9	852.8	851.8	850.6	849.5	848.5
167.5°	865.7	866.7	866.7	865.7	864.8	863.8	862.8
170°	873.3	874.4	874.4	873.3	872.3	871.2	870.0
172.5°	879.1	880.0	880.0	878.9	877.8	876.7	875.7
175°	885.4	886.4	886.3	885.2	884.1	883.0	881.9
177.5°	888.1	888.8	888.8	887.9	887.0	886.2	885.3
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5

(END OF REPORT)