

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999436

Luminaire Tested: SA2XXRDIP-B1005D925UB2750-4F0-XX-W2A-A_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999436
REPORT IS A COMBINATION OF REPORTS P987987 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B1005D925UB2750-4F0-XX-W2A-A_4000K
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7443.0 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999436

CATALOG NUMBER: SA2XXRDIP-B1005D925UB2750-4F0-XX-W2A-A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P999436

CATALOG NUMBER: SA2XXRDIP-B1005D925UB2750-4F0-XX-W2A-A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	57	57	57
1	99	95	91	88	91	88	85	82	75	73	71	63	61	60	52	51	50	50	50	45
2	91	84	78	73	84	78	73	69	66	63	60	56	54	51	47	45	43	43	43	39
3	83	74	68	62	77	69	63	58	59	55	51	50	47	44	42	40	38	38	38	34
4	77	66	59	53	71	62	55	50	53	48	45	46	42	39	38	36	33	33	33	30
5	71	60	52	46	65	56	49	44	48	43	39	41	37	34	35	32	30	30	30	27
6	65	54	46	41	61	51	44	39	44	39	35	38	34	31	32	29	27	27	27	24
7	61	49	42	36	56	46	39	34	40	35	31	35	31	27	30	26	24	24	24	22
8	57	45	37	32	53	42	35	31	37	32	28	32	28	25	27	24	22	22	22	20
9	53	41	34	29	49	39	32	28	34	29	25	30	26	23	25	22	20	20	20	18
10	50	38	31	26	46	36	30	25	32	27	23	28	24	21	24	21	19	19	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	34790	34790	34790	34790
5°	34870	36952	34991	29520
10°	34486	39056	34731	24377
15°	33737	39069	34309	18313
20°	32837	32295	33552	15109
25°	31746	20180	32433	12854
30°	30353	12920	31178	11065
35°	28658	9930	29585	9470
40°	26768	8347	27912	8283
45°	24749	7104	25784	6953
50°	22680	6036	23739	6014
55°	20390	5245	21487	5177
60°	18352	4000	19326	3952
65°	16452	3009	17430	3415
70°	14352	2404	15478	2783
75°	12133	1841	13241	2105
80°	9636	1253	10363	1381
85°	6681	647	7331	682

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 31825 cd/sqm

TEST NUMBER: P999436

CATALOG NUMBER: SA2XXRDIP-B1005D925UB2750-4F0-XX-W2A-A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.5	2.8
10°-20°	581.9	7.8
20°-30°	748.9	10.1
30°-40°	710.4	9.5
40°-50°	608.9	8.2
50°-60°	463.7	6.2
60°-70°	292.4	3.9
70°-80°	145.9	2.0
80°-90°	39.7	0.5
90°-100°	41.0	0.6
100°-110°	152.7	2.1
110°-120°	405.1	5.4
120°-130°	671.9	9.0
130°-140°	713.7	9.6
140°-150°	663.3	8.9
150°-160°	533.3	7.2
160°-170°	343.6	4.6
170°-180°	118.3	1.6
0°-30°	1539.2	20.7
0°-40°	2249.6	30.2
0°-60°	3322.2	44.6
0°-90°	3800.2	51.1
90°-120°	598.8	8.0
90°-150°	2647.7	35.6
90°-180°	3643.0	48.9
0°-180°	7443.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2198	2198	2198	2198	2198	
5°	2199	2445	2207	1953	2199	209
15°	2072	2760	2108	1294	2072	583
25°	1839	1472	1879	938	1839	844
35°	1509	726	1558	692	1509	944
45°	1133	504	1181	493	1133	875
55°	765	350	806	345	765	690
65°	463	182	490	206	463	459
75°	217	96	237	110	217	235
85°	47	28	52	29	47	54
90°	1	24	1	24	1	6
95°	58	39	58	39	58	69
105°	273	68	273	68	273	292
115°	517	74	517	74	517	509
125°	731	769	731	769	731	652
135°	904	934	904	934	904	699
145°	1049	1066	1049	1066	1049	656
155°	1155	1156	1155	1156	1155	532
165°	1217	1215	1217	1215	1217	344
175°	1245	1238	1245	1238	1245	119
180°	1243	1243	1243	1243	1243	

TEST NUMBER: P999436

CATALOG NUMBER: SA2XXRDIP-B1005D925UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2211.5	2220.7	2225.2	2231.4	2245.1	2254.3	2268.0	2271.1	2269.5	2275.7	2258.9
5°	2199.3	2219.1	2237.5	2252.7	2277.2	2292.5	2309.3	2329.1	2333.7	2356.6	2342.9
7.5°	2182.5	2211.5	2237.5	2268.0	2304.7	2324.5	2350.5	2381.0	2394.8	2422.3	2429.9
10°	2155.0	2196.2	2240.5	2272.6	2323.0	2358.1	2382.6	2431.4	2463.5	2504.7	2498.6
12.5°	2110.7	2164.2	2223.7	2277.2	2342.9	2365.8	2411.6	2462.0	2503.2	2541.4	2575.0
15°	2072.5	2133.6	2199.3	2265.0	2339.8	2382.6	2428.4	2494.1	2538.3	2605.5	2634.6
17.5°	2020.6	2098.5	2176.4	2249.7	2338.3	2387.1	2443.7	2507.8	2573.5	2637.6	2660.5
20°	1967.1	2051.1	2135.1	2234.4	2335.2	2382.6	2440.6	2520.0	2584.2	2634.6	2634.6
22.5°	1903.0	2005.3	2101.5	2196.2	2306.2	2374.9	2434.5	2527.7	2573.5	2584.2	2542.9
25°	1838.8	1941.2	2046.6	2164.2	2289.4	2350.5	2417.7	2504.7	2520.0	2477.3	2370.3
27.5°	1762.5	1877.0	1996.2	2122.9	2254.3	2330.6	2391.7	2449.8	2420.7	2306.2	2139.7
30°	1684.6	1808.3	1942.7	2063.4	2222.2	2292.5	2344.4	2361.2	2269.5	2083.2	1867.9
32.5°	1603.6	1724.3	1866.3	2011.4	2171.8	2239.0	2272.6	2228.3	2060.3	1825.1	1562.4
35°	1509.0	1644.9	1793.0	1944.2	2103.1	2153.5	2173.3	2064.9	1849.5	1545.6	1284.4
37.5°	1423.4	1559.4	1718.2	1872.4	2026.7	2054.2	2034.3	1864.8	1591.4	1290.6	1035.5
40°	1322.6	1467.7	1623.5	1796.1	1922.8	1930.5	1881.6	1661.7	1322.6	1040.1	882.8
42.5°	1229.5	1376.1	1531.9	1707.5	1803.7	1777.8	1712.1	1423.4	1104.2	896.5	769.8
45°	1133.2	1272.2	1440.2	1596.0	1664.7	1603.6	1504.4	1197.4	927.1	771.3	673.5
47.5°	1040.1	1169.9	1336.4	1486.0	1498.3	1429.5	1311.9	1003.4	803.4	678.1	598.7
50°	948.4	1078.3	1234.0	1357.8	1345.5	1250.8	1118.0	872.1	698.0	598.7	533.0
52.5°	856.8	974.4	1125.6	1223.4	1171.4	1079.8	948.4	739.2	609.4	522.3	471.9
55°	765.2	875.1	1005.0	1085.9	1003.4	898.0	804.9	633.8	528.4	458.2	420.0
57.5°	688.8	775.9	895.0	943.9	844.6	762.1	681.2	545.2	458.2	407.8	363.5
60°	604.8	684.2	782.0	811.0	708.7	641.5	572.7	461.2	392.5	348.2	319.2
62.5°	533.0	598.7	673.5	673.5	583.4	533.0	481.1	386.4	329.9	294.8	281.0
65°	462.8	510.1	563.6	557.5	481.1	436.8	395.6	319.2	276.4	252.0	238.3
67.5°	394.0	430.7	465.8	444.4	389.5	351.3	313.1	258.1	229.1	212.3	194.0
70°	331.4	360.4	378.8	358.9	303.9	271.9	244.4	207.7	184.8	163.4	152.7
72.5°	278.0	290.2	296.3	271.9	226.0	207.7	187.9	161.9	142.0	131.3	128.3
75°	216.9	227.6	223.0	204.7	166.5	152.7	137.5	119.1	114.5	108.4	105.4
77.5°	169.5	169.5	161.9	145.1	119.1	108.4	102.3	93.2	88.6	87.1	84.0
80°	120.7	119.1	114.5	96.2	80.9	74.8	74.8	68.7	67.2	64.1	64.1
82.5°	79.4	79.4	73.3	58.0	53.5	51.9	50.4	47.3	47.3	45.8	45.8
85°	47.3	44.3	36.7	32.1	30.5	30.5	29.0	27.5	29.0	27.5	27.5
87.5°	21.4	16.8	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2
90°	0.9	3.1	5.3	7.5	9.7	10.8	11.6	13.2	14.8	16.4	18.0
92.5°	22.5	21.7	20.9	20.1	19.3	18.9	19.2	19.8	20.4	21.0	21.6
95°	58.4	51.8	45.2	38.7	32.1	28.8	29.5	30.9	32.3	33.7	35.1
97.5°	105.2	88.8	72.4	56.1	39.7	31.5	33.1	36.3	39.5	42.7	45.9
100°	159.1	131.7	104.4	77.0	49.7	36.0	37.7	41.1	44.4	47.8	51.2
102.5°	218.5	218.1	217.7	217.3	216.9	216.7	198.5	162.1	125.8	89.4	53.0
105°	273.3	279.3	285.3	291.3	297.3	300.3	273.0	218.5	163.9	109.4	54.8
107.5°	337.2	342.2	347.2	352.1	357.1	359.6	325.9	258.6	191.3	123.9	56.6
110°	398.3	402.5	406.7	410.9	415.1	417.2	388.3	330.6	272.8	215.1	157.3

TEST NUMBER: P999436

CATALOG NUMBER: SA2XXRDIP-B1005D925UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	455.9	459.5	463.1	466.6	470.2	472.0	470.3	466.9	463.6	460.2	456.8
115°	517.0	520.4	523.8	527.2	530.6	532.3	534.8	539.8	544.8	549.8	554.8
117.5°	570.0	574.0	578.0	582.0	586.0	588.0	589.7	593.1	596.5	599.9	603.3
120°	629.4	632.4	635.4	638.4	641.4	642.9	644.7	648.3	651.9	655.5	659.1
122.5°	679.7	682.9	686.1	689.3	692.5	694.1	696.1	700.1	704.1	708.1	712.1
125°	731.0	733.6	736.2	738.8	741.4	742.7	744.6	748.4	752.2	756.0	759.8
127.5°	777.7	780.5	783.3	786.1	788.9	790.3	791.8	794.8	797.8	800.8	803.8
130°	821.8	825.0	828.2	831.4	834.6	836.2	837.3	839.5	841.7	843.9	846.1
132.5°	866.8	869.4	872.0	874.5	877.1	878.4	879.5	881.7	883.9	886.1	888.3
135°	904.5	907.7	910.9	914.1	917.3	918.9	919.8	921.6	923.4	925.2	927.0
137.5°	944.1	946.5	948.9	951.3	953.7	954.9	955.9	957.9	959.9	961.9	963.9
140°	982.7	984.3	985.9	987.5	989.1	989.9	991.0	993.2	995.4	997.6	999.8
142.5°	1015.1	1016.5	1017.9	1019.3	1020.7	1021.4	1022.7	1025.3	1027.9	1030.5	1033.1
145°	1049.3	1049.1	1048.9	1048.7	1048.5	1048.4	1050.1	1053.5	1056.9	1060.3	1063.7
147.5°	1078.9	1078.3	1077.7	1077.1	1076.5	1076.2	1077.9	1081.3	1084.7	1088.1	1091.5
150°	1107.7	1106.3	1104.9	1103.5	1102.1	1101.4	1103.0	1106.2	1109.4	1112.6	1115.8
152.5°	1132.0	1130.4	1128.8	1127.2	1125.6	1124.8	1126.3	1129.3	1132.3	1135.3	1138.3
155°	1155.4	1153.6	1151.8	1150.0	1148.2	1147.3	1148.5	1150.9	1153.3	1155.7	1158.1
157.5°	1174.2	1172.6	1171.0	1169.5	1167.9	1167.1	1168.0	1169.8	1171.5	1173.3	1175.1
160°	1190.4	1189.2	1188.0	1186.8	1185.6	1185.0	1185.6	1186.8	1188.0	1189.2	1190.4
162.5°	1204.8	1203.6	1202.4	1201.2	1200.0	1199.4	1199.9	1200.9	1201.9	1202.9	1203.9
165°	1217.4	1216.2	1215.0	1213.8	1212.6	1212.0	1212.3	1212.9	1213.5	1214.1	1214.7
167.5°	1227.3	1226.1	1224.9	1223.7	1222.5	1221.9	1222.2	1222.8	1223.4	1224.0	1224.6
170°	1235.4	1234.2	1233.0	1231.8	1230.6	1230.0	1230.2	1230.6	1231.0	1231.4	1231.8
172.5°	1240.8	1239.6	1238.4	1237.2	1236.0	1235.4	1235.6	1236.0	1236.4	1236.8	1237.2
175°	1245.3	1243.9	1242.5	1241.1	1239.7	1239.0	1239.2	1239.6	1240.0	1240.4	1240.8
177.5°	1247.1	1245.7	1244.3	1242.9	1241.5	1240.8	1240.9	1241.1	1241.3	1241.5	1241.7
180°	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6

TEST NUMBER: P999436

CATALOG NUMBER: SA2XXRDIP-B1005D925UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2275.7	2278.7	2283.3	2304.7	2307.7	2313.8	2310.8	2310.8	2312.3	2309.3	2310.8
5°	2373.4	2378.0	2400.9	2426.9	2433.0	2426.9	2434.5	2445.2	2445.2	2445.2	2442.1
7.5°	2465.0	2481.8	2507.8	2546.0	2553.6	2561.3	2575.0	2565.8	2568.9	2582.6	2578.1
10°	2553.6	2578.1	2607.1	2639.1	2655.9	2666.6	2672.7	2686.5	2718.6	2681.9	2695.7
12.5°	2637.6	2672.7	2703.3	2738.4	2750.6	2764.4	2769.0	2781.2	2781.2	2779.7	2790.3
15°	2692.6	2724.7	2752.2	2775.1	2778.1	2775.1	2772.0	2773.5	2778.1	2759.8	2770.5
17.5°	2704.8	2707.9	2717.0	2707.9	2709.4	2677.3	2659.0	2654.4	2611.7	2613.2	2648.3
20°	2645.3	2593.3	2579.6	2529.2	2498.6	2416.2	2413.1	2390.2	2300.1	2327.6	2321.5
22.5°	2481.8	2393.3	2275.7	2217.6	2188.6	2101.5	2034.3	1987.0	1954.9	1922.8	1909.1
25°	2266.5	2122.9	1956.4	1841.9	1825.1	1744.2	1620.4	1562.4	1493.7	1472.3	1509.0
27.5°	1988.5	1802.2	1614.3	1438.7	1406.6	1333.3	1270.7	1229.5	1150.0	1145.5	1148.5
30°	1611.3	1423.4	1266.1	1151.6	1072.2	1038.6	997.3	966.8	934.7	946.9	950.0
32.5°	1324.2	1145.5	998.8	937.8	901.1	879.7	844.6	824.7	811.0	806.4	804.9
35°	1052.3	933.2	867.5	807.9	786.6	771.3	745.3	736.1	723.9	725.5	725.5
37.5°	901.1	801.8	753.0	722.4	702.5	694.9	678.1	668.9	661.3	658.3	662.8
40°	777.4	708.7	678.1	650.6	633.8	630.8	621.6	610.9	601.7	603.3	607.9
42.5°	687.3	647.6	610.9	589.5	577.3	572.7	565.1	557.5	557.5	552.9	551.3
45°	615.5	583.4	552.9	533.0	525.4	519.3	510.1	508.6	502.5	504.0	505.5
47.5°	551.3	525.4	502.5	482.6	475.0	473.5	464.3	458.2	458.2	456.7	455.1
50°	493.3	467.3	447.5	436.8	426.1	423.1	421.5	420.0	416.9	416.9	418.5
52.5°	446.0	420.0	404.7	395.6	389.5	386.4	386.4	384.9	384.9	384.9	383.3
55°	394.0	372.7	360.4	357.4	354.3	352.8	351.3	348.2	346.7	349.7	346.7
57.5°	345.2	337.5	326.8	323.8	316.1	316.1	311.6	308.5	305.5	308.5	308.5
60°	307.0	296.3	290.2	281.0	274.9	268.8	261.2	259.6	256.6	255.1	253.5
62.5°	267.3	258.1	242.8	229.1	219.9	213.8	210.8	209.2	209.2	207.7	207.7
65°	223.0	201.6	194.0	189.4	187.9	186.3	183.3	181.7	183.3	181.7	183.3
67.5°	174.1	171.1	166.5	163.4	161.9	160.4	160.4	158.8	158.8	158.8	158.8
70°	151.2	143.6	142.0	139.0	139.0	137.5	137.5	137.5	137.5	135.9	139.0
72.5°	125.2	120.7	119.1	117.6	117.6	117.6	116.1	116.1	116.1	114.5	116.1
75°	102.3	100.8	97.7	97.7	96.2	97.7	96.2	96.2	94.7	96.2	96.2
77.5°	82.5	80.9	79.4	79.4	77.9	77.9	77.9	77.9	77.9	77.9	79.4
80°	62.6	61.1	59.6	61.1	59.6	61.1	59.6	59.6	61.1	59.6	59.6
82.5°	45.8	44.3	44.3	42.8	42.8	42.8	42.8	42.8	42.8	42.8	42.8
85°	27.5	26.0	26.0	27.5	26.0	27.5	26.0	26.0	26.0	27.5	27.5
87.5°	12.2	13.7	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2	13.7
90°	19.0	20.0	21.0	22.0	22.5	22.7	23.1	23.5	23.9	24.3	23.9
92.5°	22.0	22.4	22.8	23.2	23.4	23.5	23.7	23.9	24.1	24.3	24.1
95°	36.1	37.1	38.1	39.1	39.6	39.5	39.3	39.1	38.9	38.7	38.9
97.5°	46.5	47.1	47.7	48.3	48.6	48.7	48.9	49.1	49.3	49.5	49.3
100°	52.8	54.4	56.0	57.6	58.4	58.6	59.0	59.4	59.8	60.2	59.8
102.5°	55.2	57.4	59.6	61.8	62.9	63.2	63.8	64.4	65.0	65.6	65.0
105°	57.0	59.2	61.4	63.6	64.7	65.1	65.9	66.7	67.5	68.3	67.5
107.5°	58.8	61.0	63.2	65.4	66.5	66.9	67.7	68.5	69.3	70.1	69.3
110°	137.3	117.3	97.4	77.4	67.4	67.8	68.6	69.4	70.2	71.0	70.2

TEST NUMBER: P999436

CATALOG NUMBER: SA2XXRDIP-B1005D925UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	370.7	284.5	198.4	112.3	69.2	69.5	70.1	70.7	71.3	71.9	71.3
115°	462.3	369.8	277.3	184.8	138.5	131.3	116.9	102.5	88.1	73.7	88.1
117.5°	574.7	546.1	517.6	489.0	474.7	448.5	396.2	343.9	291.5	239.2	291.5
120°	661.5	663.9	666.2	668.6	669.8	656.3	629.4	602.4	575.5	548.5	575.5
122.5°	713.3	714.5	715.7	716.9	717.5	717.6	717.8	718.0	718.2	718.4	718.2
125°	761.2	762.6	763.9	765.3	766.0	766.3	766.9	767.5	768.1	768.7	768.1
127.5°	805.8	807.8	809.8	811.8	812.8	812.9	813.1	813.3	813.5	813.7	813.5
130°	848.3	850.5	852.7	854.9	856.0	855.9	855.7	855.5	855.3	855.1	855.3
132.5°	890.1	891.9	893.7	895.5	896.4	896.3	896.1	895.9	895.7	895.5	895.7
135°	929.0	931.0	933.0	935.0	936.0	935.8	935.4	935.0	934.6	934.2	934.6
137.5°	965.9	967.9	969.8	971.8	972.8	972.5	971.9	971.3	970.7	970.1	970.7
140°	1001.6	1003.4	1005.2	1007.0	1007.9	1007.4	1006.4	1005.4	1004.4	1003.4	1004.4
142.5°	1034.7	1036.3	1037.9	1039.5	1040.3	1039.8	1038.8	1037.8	1036.8	1035.8	1036.8
145°	1065.1	1066.5	1067.9	1069.3	1070.0	1069.5	1068.5	1067.5	1066.5	1065.5	1066.5
147.5°	1092.5	1093.5	1094.5	1095.5	1096.0	1095.6	1094.8	1094.0	1093.2	1092.4	1093.2
150°	1117.0	1118.2	1119.4	1120.6	1121.2	1120.7	1119.7	1118.7	1117.7	1116.7	1117.7
152.5°	1139.5	1140.7	1141.9	1143.1	1143.7	1143.0	1141.6	1140.2	1138.8	1137.4	1138.8
155°	1159.3	1160.5	1161.7	1162.9	1163.5	1162.7	1161.1	1159.5	1157.9	1156.3	1157.9
157.5°	1176.5	1177.9	1179.3	1180.7	1181.4	1180.6	1179.0	1177.4	1175.8	1174.2	1175.8
160°	1191.6	1192.8	1194.0	1195.2	1195.8	1195.1	1193.7	1192.3	1190.9	1189.5	1190.9
162.5°	1205.3	1206.7	1208.1	1209.5	1210.2	1209.3	1207.5	1205.7	1203.9	1202.1	1203.9
165°	1216.1	1217.5	1218.9	1220.3	1221.0	1220.3	1218.9	1217.5	1216.1	1214.7	1216.1
167.5°	1226.0	1227.4	1228.8	1230.2	1230.9	1230.0	1228.2	1226.4	1224.6	1222.8	1224.6
170°	1233.2	1234.6	1236.0	1237.4	1238.1	1237.2	1235.4	1233.6	1231.8	1230.0	1231.8
172.5°	1238.6	1240.0	1241.4	1242.8	1243.5	1242.6	1240.8	1239.0	1237.2	1235.4	1237.2
175°	1242.2	1243.6	1245.0	1246.4	1247.1	1246.1	1244.1	1242.1	1240.1	1238.1	1240.1
177.5°	1243.1	1244.5	1245.9	1247.3	1248.0	1247.1	1245.3	1243.5	1241.7	1239.9	1241.7
180°	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6

TEST NUMBER: P999436

CATALOG NUMBER: SA2XXRDIP-B1005D925UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2316.9	2306.2	2303.1	2306.2	2303.1	2304.7	2294.0	2254.3	2265.0	2248.2	2257.3
5°	2448.2	2439.1	2419.2	2416.2	2413.1	2410.1	2394.8	2359.7	2345.9	2323.0	2321.5
7.5°	2573.5	2573.5	2558.2	2547.5	2533.8	2523.1	2503.2	2451.3	2429.9	2402.4	2387.1
10°	2697.2	2657.5	2674.3	2663.6	2630.0	2623.9	2587.2	2556.7	2515.4	2487.9	2463.5
12.5°	2785.8	2773.5	2758.3	2749.1	2739.9	2720.1	2695.7	2617.8	2596.4	2541.4	2513.9
15°	2782.7	2775.1	2779.7	2779.7	2776.6	2772.0	2752.2	2695.7	2659.0	2605.5	2558.2
17.5°	2633.0	2652.9	2672.7	2686.5	2717.0	2730.8	2749.1	2715.5	2692.6	2646.8	2596.4
20°	2371.9	2420.7	2478.8	2491.0	2518.5	2599.4	2636.1	2665.1	2674.3	2659.0	2617.8
22.5°	2008.4	2049.6	2190.1	2187.1	2226.8	2323.0	2429.9	2517.0	2585.7	2623.9	2608.6
25°	1573.1	1631.1	1706.0	1762.5	1892.3	2035.9	2168.7	2307.7	2426.9	2532.2	2558.2
27.5°	1189.8	1266.1	1325.7	1400.5	1466.2	1635.7	1806.8	2023.6	2162.6	2362.7	2466.6
30°	962.2	997.3	1056.9	1092.0	1124.1	1253.9	1447.9	1661.7	1906.0	2136.7	2315.4
32.5°	821.7	846.1	890.4	905.7	939.3	1026.3	1148.5	1344.0	1596.0	1875.5	2110.7
35°	737.7	763.6	772.8	786.6	814.0	869.0	953.0	1095.1	1322.6	1596.0	1877.0
37.5°	665.9	679.6	705.6	714.8	723.9	765.2	821.7	921.0	1072.2	1296.7	1608.2
40°	615.5	623.1	636.9	644.5	650.6	679.6	730.0	797.2	908.7	1079.8	1366.9
42.5°	562.0	571.2	580.4	589.5	597.2	620.1	650.6	714.8	789.6	919.4	1127.1
45°	510.1	516.2	526.9	533.0	543.7	562.0	589.5	633.8	701.0	783.5	951.5
47.5°	462.8	470.4	475.0	482.6	490.3	510.1	536.1	565.1	620.1	701.0	823.2
50°	420.0	429.2	435.3	436.8	442.9	461.2	482.6	514.7	549.8	612.4	719.3
52.5°	389.5	391.0	395.6	401.7	400.1	410.8	430.7	455.1	491.8	542.2	620.1
55°	354.3	358.9	362.0	363.5	363.5	372.7	383.3	406.3	435.3	476.5	542.2
57.5°	310.0	314.6	323.8	326.8	331.4	336.0	340.6	355.9	380.3	420.0	473.5
60°	264.2	267.3	276.4	282.5	285.6	297.8	303.9	316.1	329.9	358.9	409.3
62.5°	212.3	215.3	219.9	226.0	232.1	250.5	265.7	278.0	288.7	308.5	349.7
65°	184.8	186.3	189.4	190.9	192.4	200.1	213.8	230.6	250.5	265.7	290.2
67.5°	160.4	161.9	163.4	166.5	168.0	169.5	175.6	180.2	200.1	221.5	239.8
70°	137.5	140.5	142.0	142.0	143.6	146.6	149.7	155.8	161.9	172.6	195.5
72.5°	116.1	117.6	120.7	120.7	120.7	123.7	126.8	129.8	132.9	139.0	148.1
75°	96.2	99.3	99.3	99.3	100.8	100.8	103.9	106.9	110.0	114.5	117.6
77.5°	79.4	79.4	79.4	79.4	80.9	80.9	82.5	85.5	87.1	88.6	91.6
80°	59.6	61.1	61.1	61.1	62.6	62.6	62.6	65.7	67.2	67.2	70.3
82.5°	44.3	44.3	44.3	45.8	44.3	45.8	45.8	47.3	45.8	47.3	48.9
85°	27.5	27.5	27.5	29.0	29.0	29.0	29.0	29.0	29.0	29.0	30.5
87.5°	13.7	13.7	13.7	13.7	13.7	13.7	13.7	13.7	15.3	13.7	13.7
90°	23.5	23.1	22.7	22.5	22.0	21.0	20.0	19.0	18.0	16.4	14.8
92.5°	23.9	23.7	23.5	23.4	23.2	22.8	22.4	22.0	21.6	21.0	20.4
95°	39.1	39.3	39.5	39.6	39.1	38.1	37.1	36.1	35.1	33.7	32.3
97.5°	49.1	48.9	48.7	48.6	48.3	47.7	47.1	46.5	45.9	42.7	39.5
100°	59.4	59.0	58.6	58.4	57.6	56.0	54.4	52.8	51.2	47.8	44.4
102.5°	64.4	63.8	63.2	62.9	61.8	59.6	57.4	55.2	53.0	49.4	45.8
105°	66.7	65.9	65.1	64.7	63.6	61.4	59.2	57.0	54.8	50.4	46.9
107.5°	68.5	67.7	66.9	66.5	65.4	63.2	61.0	58.8	56.6	52.9	49.3
110°	69.4	68.6	67.8	67.4	77.4	97.4	117.3	137.3	157.3	215.1	272.8

TEST NUMBER: P999436

CATALOG NUMBER: SA2XXRDIP-B1005D925UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	70.7	70.1	69.5	69.2	112.3	198.4	284.5	370.7	456.8	460.2	463.6
115°	102.5	116.9	131.3	138.5	184.8	277.3	369.8	462.3	554.8	549.8	544.8
117.5°	343.9	396.2	448.5	474.7	489.0	517.6	546.1	574.7	603.3	599.9	596.5
120°	602.4	629.4	656.3	669.8	668.6	666.2	663.9	661.5	659.1	655.5	651.9
122.5°	718.0	717.8	717.6	717.5	716.9	715.7	714.5	713.3	712.1	708.1	704.1
125°	767.5	766.9	766.3	766.0	765.3	763.9	762.6	761.2	759.8	756.0	752.2
127.5°	813.3	813.1	812.9	812.8	811.8	809.8	807.8	805.8	803.8	800.8	797.8
130°	855.5	855.7	855.9	856.0	854.9	852.7	850.5	848.3	846.1	843.9	841.7
132.5°	895.9	896.1	896.3	896.4	895.5	893.7	891.9	890.1	888.3	886.1	883.9
135°	935.0	935.4	935.8	936.0	935.0	933.0	931.0	929.0	927.0	925.2	923.4
137.5°	971.3	971.9	972.5	972.8	971.8	969.8	967.9	965.9	963.9	961.9	959.9
140°	1005.4	1006.4	1007.4	1007.9	1007.0	1005.2	1003.4	1001.6	999.8	997.6	995.4
142.5°	1037.8	1038.8	1039.8	1040.3	1039.5	1037.9	1036.3	1034.7	1033.1	1030.5	1027.9
145°	1067.5	1068.5	1069.5	1070.0	1069.3	1067.9	1066.5	1065.1	1063.7	1060.3	1056.9
147.5°	1094.0	1094.8	1095.6	1096.0	1095.5	1094.5	1093.5	1092.5	1091.5	1088.1	1084.7
150°	1118.7	1119.7	1120.7	1121.2	1120.6	1119.4	1118.2	1117.0	1115.8	1112.6	1109.4
152.5°	1140.2	1141.6	1143.0	1143.7	1143.1	1141.9	1140.7	1139.5	1138.3	1135.3	1132.3
155°	1159.5	1161.1	1162.7	1163.5	1162.9	1161.7	1160.5	1159.3	1158.1	1155.7	1153.3
157.5°	1177.4	1179.0	1180.6	1181.4	1180.7	1179.3	1177.9	1176.5	1175.1	1173.3	1171.5
160°	1192.3	1193.7	1195.1	1195.8	1195.2	1194.0	1192.8	1191.6	1190.4	1189.2	1188.0
162.5°	1205.7	1207.5	1209.3	1210.2	1209.5	1208.1	1206.7	1205.3	1203.9	1202.9	1201.9
165°	1217.5	1218.9	1220.3	1221.0	1220.3	1218.9	1217.5	1216.1	1214.7	1214.1	1213.5
167.5°	1226.4	1228.2	1230.0	1230.9	1230.2	1228.8	1227.4	1226.0	1224.6	1224.0	1223.4
170°	1233.6	1235.4	1237.2	1238.1	1237.4	1236.0	1234.6	1233.2	1231.8	1231.4	1231.0
172.5°	1239.0	1240.8	1242.6	1243.5	1242.8	1241.4	1240.0	1238.6	1237.2	1236.8	1236.4
175°	1242.1	1244.1	1246.1	1247.1	1246.4	1245.0	1243.6	1242.2	1240.8	1240.4	1240.0
177.5°	1243.5	1245.3	1247.1	1248.0	1247.3	1245.9	1244.5	1243.1	1241.7	1241.5	1241.3
180°	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6

TEST NUMBER: P999436

CATALOG NUMBER: SA2XXRDIP-B1005D925UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2243.6	2235.9	2235.9	2231.4	2231.4	2206.9	2206.9	2214.6	2205.4	2194.7	2179.4
5°	2301.6	2284.8	2280.2	2274.1	2254.3	2223.7	2211.5	2206.9	2188.6	2165.7	2139.7
7.5°	2356.6	2329.1	2315.4	2301.6	2275.7	2232.9	2208.4	2191.6	2164.2	2129.0	2095.4
10°	2410.1	2374.9	2339.8	2323.0	2286.3	2232.9	2197.8	2170.3	2130.6	2083.2	2035.9
12.5°	2458.9	2385.6	2379.5	2345.9	2292.5	2231.4	2177.9	2138.2	2087.8	2032.8	1977.8
15°	2501.7	2426.9	2390.2	2359.7	2289.4	2213.0	2156.5	2107.6	2040.4	1977.8	1910.6
17.5°	2523.1	2442.1	2417.7	2367.3	2295.5	2196.2	2119.9	2060.3	1987.0	1912.2	1835.8
20°	2544.5	2449.8	2410.1	2374.9	2277.2	2164.2	2078.6	2009.9	1929.0	1840.4	1756.4
22.5°	2555.1	2449.8	2402.4	2353.5	2258.9	2129.0	2028.2	1947.3	1852.6	1762.5	1661.7
25°	2536.8	2440.6	2384.1	2333.7	2226.8	2086.3	1970.2	1878.6	1777.8	1675.4	1573.1
27.5°	2491.0	2419.2	2353.5	2301.6	2182.5	2031.3	1909.1	1805.2	1701.4	1586.8	1483.0
30°	2405.5	2373.4	2321.5	2263.4	2133.6	1982.4	1837.3	1730.4	1615.9	1501.3	1392.9
32.5°	2272.6	2300.1	2266.5	2216.1	2075.6	1915.2	1761.0	1652.5	1527.3	1403.6	1304.3
35°	2110.7	2208.4	2190.1	2155.0	2014.5	1843.4	1689.2	1557.8	1432.6	1307.4	1208.1
37.5°	1933.5	2081.7	2097.0	2075.6	1944.2	1770.1	1600.6	1472.3	1344.0	1217.2	1116.4
40°	1690.7	1918.3	1967.1	1976.3	1870.9	1681.5	1504.4	1379.1	1252.4	1128.7	1006.5
42.5°	1467.7	1754.8	1815.9	1854.1	1777.8	1594.5	1415.8	1276.8	1151.6	1040.1	917.9
45°	1258.5	1557.8	1657.1	1706.0	1672.4	1495.2	1310.4	1180.6	1066.0	963.7	846.1
47.5°	1043.1	1344.0	1483.0	1560.9	1560.9	1394.4	1209.6	1081.3	971.4	884.3	780.4
50°	899.6	1150.0	1293.6	1395.9	1423.4	1292.1	1118.0	992.7	888.9	794.2	714.8
52.5°	766.7	991.2	1110.3	1217.2	1296.7	1182.1	1015.6	902.6	800.3	711.7	649.1
55°	662.8	830.8	939.3	1056.9	1145.5	1070.6	916.4	806.4	717.8	644.5	591.1
57.5°	563.6	710.2	798.8	902.6	997.3	940.8	817.1	722.4	644.5	580.4	533.0
60°	479.6	598.7	667.4	748.4	866.0	826.3	723.9	636.9	574.3	516.2	476.5
62.5°	407.8	502.5	560.5	618.5	725.5	707.1	627.7	560.5	507.1	458.2	424.6
65°	334.5	412.4	458.2	508.6	594.1	601.7	537.6	490.3	441.4	398.6	368.1
67.5°	270.3	331.4	372.7	415.4	484.1	505.5	461.2	421.5	380.3	345.2	317.7
70°	218.4	261.2	291.7	325.3	381.8	407.8	384.9	357.4	323.8	294.8	270.3
72.5°	172.6	200.1	218.4	244.4	290.2	316.1	314.6	290.2	265.7	245.9	226.0
75°	126.8	148.1	163.4	180.2	216.9	241.3	247.4	236.7	212.3	197.0	181.7
77.5°	96.2	108.4	116.1	128.3	154.3	175.6	184.8	181.7	164.9	152.7	142.0
80°	73.3	76.4	79.4	84.0	105.4	125.2	131.3	129.8	120.7	116.1	103.9
82.5°	51.9	53.5	55.0	56.5	64.1	80.9	87.1	90.1	82.5	77.9	67.2
85°	30.5	32.1	32.1	35.1	36.7	41.2	51.9	51.9	50.4	44.3	42.8
87.5°	15.3	15.3	13.7	13.7	15.3	16.8	19.9	22.9	19.9	18.3	16.8
90°	13.2	11.6	10.8	9.7	7.5	5.3	3.1	0.9	3.1	5.3	7.5
92.5°	19.8	19.2	18.9	19.3	20.1	20.9	21.7	22.5	21.7	20.9	20.1
95°	30.9	29.5	28.8	32.1	38.7	45.2	51.8	58.4	51.8	45.2	38.7
97.5°	36.3	33.1	31.5	39.7	56.1	72.4	88.8	105.2	88.8	72.4	56.1
100°	41.1	37.7	36.0	49.7	77.0	104.4	131.7	159.1	131.7	104.4	77.0
102.5°	162.1	198.5	216.7	216.9	217.3	217.7	218.1	218.5	218.1	217.7	217.3
105°	218.5	273.0	300.3	297.3	291.3	285.3	279.3	273.3	279.3	285.3	291.3
107.5°	258.6	325.9	359.6	357.1	352.1	347.2	342.2	337.2	342.2	347.2	352.1
110°	330.6	388.3	417.2	415.1	410.9	406.7	402.5	398.3	402.5	406.7	410.9

TEST NUMBER: P999436

CATALOG NUMBER: SA2XXRDIP-B1005D925UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	466.9	470.3	472.0	470.2	466.6	463.1	459.5	455.9	459.5	463.1	466.6
115°	539.8	534.8	532.3	530.6	527.2	523.8	520.4	517.0	520.4	523.8	527.2
117.5°	593.1	589.7	588.0	586.0	582.0	578.0	574.0	570.0	574.0	578.0	582.0
120°	648.3	644.7	642.9	641.4	638.4	635.4	632.4	629.4	632.4	635.4	638.4
122.5°	700.1	696.1	694.1	692.5	689.3	686.1	682.9	679.7	682.9	686.1	689.3
125°	748.4	744.6	742.7	741.4	738.8	736.2	733.6	731.0	733.6	736.2	738.8
127.5°	794.8	791.8	790.3	788.9	786.1	783.3	780.5	777.7	780.5	783.3	786.1
130°	839.5	837.3	836.2	834.6	831.4	828.2	825.0	821.8	825.0	828.2	831.4
132.5°	881.7	879.5	878.4	877.1	874.5	872.0	869.4	866.8	869.4	872.0	874.5
135°	921.6	919.8	918.9	917.3	914.1	910.9	907.7	904.5	907.7	910.9	914.1
137.5°	957.9	955.9	954.9	953.7	951.3	948.9	946.5	944.1	946.5	948.9	951.3
140°	993.2	991.0	989.9	989.1	987.5	985.9	984.3	982.7	984.3	985.9	987.5
142.5°	1025.3	1022.7	1021.4	1020.7	1019.3	1017.9	1016.5	1015.1	1016.5	1017.9	1019.3
145°	1053.5	1050.1	1048.4	1048.5	1048.7	1048.9	1049.1	1049.3	1049.1	1048.9	1048.7
147.5°	1081.3	1077.9	1076.2	1076.5	1077.1	1077.7	1078.3	1078.9	1078.3	1077.7	1077.1
150°	1106.2	1103.0	1101.4	1102.1	1103.5	1104.9	1106.3	1107.7	1106.3	1104.9	1103.5
152.5°	1129.3	1126.3	1124.8	1125.6	1127.2	1128.8	1130.4	1132.0	1130.4	1128.8	1127.2
155°	1150.9	1148.5	1147.3	1148.2	1150.0	1151.8	1153.6	1155.4	1153.6	1151.8	1150.0
157.5°	1169.8	1168.0	1167.1	1167.9	1169.5	1171.0	1172.6	1174.2	1172.6	1171.0	1169.5
160°	1186.8	1185.6	1185.0	1185.6	1186.8	1188.0	1189.2	1190.4	1189.2	1188.0	1186.8
162.5°	1200.9	1199.9	1199.4	1200.0	1201.2	1202.4	1203.6	1204.8	1203.6	1202.4	1201.2
165°	1212.9	1212.3	1212.0	1212.6	1213.8	1215.0	1216.2	1217.4	1216.2	1215.0	1213.8
167.5°	1222.8	1222.2	1221.9	1222.5	1223.7	1224.9	1226.1	1227.3	1226.1	1224.9	1223.7
170°	1230.6	1230.2	1230.0	1230.6	1231.8	1233.0	1234.2	1235.4	1234.2	1233.0	1231.8
172.5°	1236.0	1235.6	1235.4	1236.0	1237.2	1238.4	1239.6	1240.8	1239.6	1238.4	1237.2
175°	1239.6	1239.2	1239.0	1239.7	1241.1	1242.5	1243.9	1245.3	1243.9	1242.5	1241.1
177.5°	1241.1	1240.9	1240.8	1241.5	1242.9	1244.3	1245.7	1247.1	1245.7	1244.3	1242.9
180°	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6

TEST NUMBER: P999436

CATALOG NUMBER: SA2XXRDIP-B1005D925UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2173.3	2174.8	2179.4	2165.7	2144.3	2135.1	2107.6	2103.1	2098.5	2098.5	2103.1
5°	2124.4	2118.3	2119.9	2093.9	2063.4	2045.0	2006.8	2013.0	1993.1	1980.9	1983.9
7.5°	2071.0	2054.2	2052.7	2019.1	1980.9	1947.3	1907.6	1898.4	1880.1	1858.7	1849.5
10°	2003.8	1991.6	1968.7	1930.5	1881.6	1854.1	1800.7	1768.6	1764.0	1731.9	1719.7
12.5°	1935.1	1913.7	1890.8	1837.3	1782.3	1738.0	1698.3	1663.2	1638.8	1611.3	1593.0
15°	1855.6	1829.7	1803.7	1747.2	1683.1	1638.8	1579.2	1527.3	1455.5	1399.0	1366.9
17.5°	1768.6	1739.6	1704.4	1641.8	1579.2	1518.1	1408.2	1347.1	1296.7	1263.1	1243.2
20°	1678.5	1646.4	1611.3	1548.7	1440.2	1333.3	1272.2	1224.9	1194.3	1160.7	1136.3
22.5°	1583.8	1550.2	1512.0	1414.3	1299.7	1224.9	1177.5	1133.2	1089.0	1070.6	1058.4
25°	1495.2	1464.7	1415.8	1282.9	1192.8	1124.1	1070.6	1041.6	1018.7	994.3	971.4
27.5°	1403.6	1347.1	1278.3	1166.8	1110.3	1040.1	1001.9	980.5	940.8	924.0	913.3
30°	1293.6	1231.0	1165.3	1085.9	1020.2	971.4	936.2	901.1	878.2	861.4	843.1
32.5°	1182.1	1122.6	1081.3	998.8	950.0	899.6	866.0	844.6	811.0	800.3	792.7
35°	1085.9	1035.5	998.8	931.6	885.8	840.0	815.6	783.5	762.1	742.3	730.0
37.5°	991.2	963.7	925.5	869.0	820.2	783.5	749.9	739.2	710.2	699.5	687.3
40°	925.5	884.3	852.2	803.4	762.1	722.4	701.0	676.6	656.7	639.9	635.3
42.5°	846.1	815.6	797.2	743.8	701.0	678.1	652.1	624.7	609.4	595.6	578.8
45°	786.6	759.1	733.1	690.3	652.1	623.1	600.2	581.9	555.9	549.8	523.9
47.5°	723.9	696.4	676.6	633.8	598.7	571.2	554.4	530.0	508.6	494.8	482.6
50°	661.3	638.4	620.1	583.4	552.9	523.9	500.9	476.5	467.3	444.4	436.8
52.5°	601.7	586.5	566.6	531.5	500.9	476.5	452.1	432.2	418.5	406.3	397.1
55°	551.3	526.9	517.7	479.6	453.6	427.6	406.3	394.0	377.2	369.6	362.0
57.5°	494.8	481.1	465.8	436.8	407.8	383.3	368.1	349.7	340.6	331.4	325.3
60°	446.0	426.1	413.9	389.5	363.5	340.6	326.8	313.1	300.9	293.2	281.0
62.5°	389.5	374.2	366.5	340.6	319.2	297.8	285.6	271.9	262.7	248.9	233.7
65°	340.6	328.4	319.2	297.8	278.0	258.1	245.9	229.1	216.9	209.2	207.7
67.5°	297.8	288.7	274.9	255.1	235.2	219.9	206.2	192.4	190.9	187.9	187.9
70°	250.5	241.3	233.7	212.3	195.5	178.7	175.6	171.1	166.5	164.9	161.9
72.5°	209.2	201.6	192.4	174.1	157.3	152.7	149.7	146.6	142.0	140.5	139.0
75°	169.5	158.8	152.7	135.9	131.3	128.3	125.2	120.7	117.6	116.1	113.0
77.5°	129.8	119.1	119.1	110.0	106.9	102.3	99.3	96.2	94.7	91.6	91.6
80°	91.6	91.6	88.6	84.0	79.4	77.9	73.3	71.8	70.3	71.8	68.7
82.5°	67.2	61.1	61.1	58.0	55.0	53.5	50.4	50.4	48.9	48.9	48.9
85°	38.2	38.2	36.7	33.6	32.1	32.1	30.5	30.5	29.0	29.0	27.5
87.5°	15.3	13.7	15.3	13.7	13.7	12.2	12.2	12.2	10.7	12.2	10.7
90°	9.7	10.8	11.6	13.2	14.8	16.4	18.0	19.0	20.0	21.0	22.0
92.5°	19.3	18.9	19.2	19.8	20.4	21.0	21.6	22.0	22.4	22.8	23.2
95°	32.1	28.8	29.5	30.9	32.3	33.7	35.1	36.1	37.1	38.1	39.1
97.5°	39.7	31.5	33.1	36.3	39.5	42.7	45.9	46.5	47.1	47.7	48.3
100°	49.7	36.0	37.7	41.1	44.4	47.8	51.2	52.8	54.4	56.0	57.6
102.5°	216.9	216.7	198.5	162.1	125.8	89.4	53.0	55.2	57.4	59.6	61.8
105°	297.3	300.3	273.0	218.5	163.9	109.4	54.8	57.0	59.2	61.4	63.6
107.5°	357.1	359.6	325.9	258.6	191.3	123.9	56.6	58.8	61.0	63.2	65.4
110°	415.1	417.2	388.3	330.6	272.8	215.1	157.3	137.3	117.3	97.4	77.4

TEST NUMBER: P999436

CATALOG NUMBER: SA2XXRDIP-B1005D925UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	470.2	472.0	470.3	466.9	463.6	460.2	456.8	370.7	284.5	198.4	112.3
115°	530.6	532.3	534.8	539.8	544.8	549.8	554.8	462.3	369.8	277.3	184.8
117.5°	586.0	588.0	589.7	593.1	596.5	599.9	603.3	574.7	546.1	517.6	489.0
120°	641.4	642.9	644.7	648.3	651.9	655.5	659.1	661.5	663.9	666.2	668.6
122.5°	692.5	694.1	696.1	700.1	704.1	708.1	712.1	713.3	714.5	715.7	716.9
125°	741.4	742.7	744.6	748.4	752.2	756.0	759.8	761.2	762.6	763.9	765.3
127.5°	788.9	790.3	791.8	794.8	797.8	800.8	803.8	805.8	807.8	809.8	811.8
130°	834.6	836.2	837.3	839.5	841.7	843.9	846.1	848.3	850.5	852.7	854.9
132.5°	877.1	878.4	879.5	881.7	883.9	886.1	888.3	890.1	891.9	893.7	895.5
135°	917.3	918.9	919.8	921.6	923.4	925.2	927.0	929.0	931.0	933.0	935.0
137.5°	953.7	954.9	955.9	957.9	959.9	961.9	963.9	965.9	967.9	969.8	971.8
140°	989.1	989.9	991.0	993.2	995.4	997.6	999.8	1001.6	1003.4	1005.2	1007.0
142.5°	1020.7	1021.4	1022.7	1025.3	1027.9	1030.5	1033.1	1034.7	1036.3	1037.9	1039.5
145°	1048.5	1048.4	1050.1	1053.5	1056.9	1060.3	1063.7	1065.1	1066.5	1067.9	1069.3
147.5°	1076.5	1076.2	1077.9	1081.3	1084.7	1088.1	1091.5	1092.5	1093.5	1094.5	1095.5
150°	1102.1	1101.4	1103.0	1106.2	1109.4	1112.6	1115.8	1117.0	1118.2	1119.4	1120.6
152.5°	1125.6	1124.8	1126.3	1129.3	1132.3	1135.3	1138.3	1139.5	1140.7	1141.9	1143.1
155°	1148.2	1147.3	1148.5	1150.9	1153.3	1155.7	1158.1	1159.3	1160.5	1161.7	1162.9
157.5°	1167.9	1167.1	1168.0	1169.8	1171.5	1173.3	1175.1	1176.5	1177.9	1179.3	1180.7
160°	1185.6	1185.0	1185.6	1186.8	1188.0	1189.2	1190.4	1191.6	1192.8	1194.0	1195.2
162.5°	1200.0	1199.4	1199.9	1200.9	1201.9	1202.9	1203.9	1205.3	1206.7	1208.1	1209.5
165°	1212.6	1212.0	1212.3	1212.9	1213.5	1214.1	1214.7	1216.1	1217.5	1218.9	1220.3
167.5°	1222.5	1221.9	1222.2	1222.8	1223.4	1224.0	1224.6	1226.0	1227.4	1228.8	1230.2
170°	1230.6	1230.0	1230.2	1230.6	1231.0	1231.4	1231.8	1233.2	1234.6	1236.0	1237.4
172.5°	1236.0	1235.4	1235.6	1236.0	1236.4	1236.8	1237.2	1238.6	1240.0	1241.4	1242.8
175°	1239.7	1239.0	1239.2	1239.6	1240.0	1240.4	1240.8	1242.2	1243.6	1245.0	1246.4
177.5°	1241.5	1240.8	1240.9	1241.1	1241.3	1241.5	1241.7	1243.1	1244.5	1245.9	1247.3
180°	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6

TEST NUMBER: P999436

CATALOG NUMBER: SA2XXRDIP-B1005D925UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2103.1	2100.0	2090.8	2093.9	2089.3	2089.3	2086.3	2086.3	2086.3	2093.9	2089.3
5°	1988.5	1977.8	1967.1	1962.6	1958.0	1953.4	1953.4	1951.9	1965.6	1962.6	1974.8
7.5°	1846.5	1843.4	1822.0	1822.0	1814.4	1811.4	1819.0	1820.5	1822.0	1825.1	1832.7
10°	1719.7	1712.1	1681.5	1684.6	1680.0	1673.9	1678.5	1675.4	1686.1	1689.2	1686.1
12.5°	1570.0	1556.3	1522.7	1505.9	1487.6	1473.8	1490.6	1478.4	1521.2	1533.4	1567.0
15°	1371.5	1345.5	1322.6	1322.6	1305.8	1293.6	1301.2	1315.0	1324.2	1337.9	1344.0
17.5°	1238.6	1227.9	1209.6	1198.9	1194.3	1189.8	1189.8	1195.9	1215.7	1214.2	1226.4
20°	1125.6	1119.5	1110.3	1096.6	1092.0	1089.0	1089.0	1089.0	1102.7	1114.9	1122.6
22.5°	1047.7	1043.1	1037.0	1018.7	1009.5	1006.5	1014.1	1018.7	1029.4	1038.6	1046.2
25°	969.8	959.1	948.4	942.3	937.8	937.8	940.8	942.3	946.9	951.5	960.7
27.5°	905.7	898.0	882.8	866.0	866.0	861.4	864.4	867.5	878.2	893.5	901.1
30°	833.9	832.4	826.3	820.2	814.0	811.0	817.1	821.7	823.2	830.8	830.8
32.5°	782.0	771.3	760.6	754.5	751.4	749.9	751.4	757.5	757.5	766.7	777.4
35°	730.0	723.9	713.2	702.5	699.5	691.9	698.0	704.1	714.8	719.3	723.9
37.5°	673.5	665.9	661.3	658.3	652.1	653.7	649.1	658.3	667.4	665.9	668.9
40°	630.8	617.0	603.3	601.7	600.2	598.7	598.7	600.2	606.3	612.4	621.6
42.5°	575.8	571.2	559.0	546.8	543.7	540.7	537.6	543.7	555.9	566.6	571.2
45°	519.3	513.2	510.1	500.9	494.8	493.3	490.3	497.9	508.6	513.2	516.2
47.5°	467.3	465.8	456.7	458.2	453.6	455.1	453.6	458.2	458.2	462.8	465.8
50°	432.2	427.6	423.1	420.0	415.4	415.4	413.9	415.4	421.5	427.6	426.1
52.5°	397.1	389.5	387.9	386.4	383.3	386.4	381.8	383.3	389.5	392.5	391.0
55°	355.9	354.3	351.3	348.2	346.7	345.2	345.2	345.2	351.3	355.9	357.4
57.5°	323.8	316.1	310.0	310.0	303.9	302.4	305.5	307.0	311.6	314.6	317.7
60°	279.5	276.4	267.3	262.7	253.5	252.0	252.0	258.1	265.7	276.4	279.5
62.5°	232.1	227.6	226.0	226.0	226.0	226.0	226.0	226.0	226.0	227.6	227.6
65°	206.2	207.7	206.2	204.7	206.2	206.2	204.7	204.7	204.7	206.2	207.7
67.5°	184.8	183.3	184.8	183.3	181.7	181.7	180.2	181.7	183.3	184.8	184.8
70°	160.4	160.4	158.8	160.4	158.8	157.3	155.8	155.8	158.8	160.4	160.4
72.5°	137.5	137.5	135.9	135.9	132.9	132.9	134.4	132.9	132.9	137.5	137.5
75°	114.5	113.0	111.5	111.5	110.0	110.0	110.0	108.4	111.5	111.5	113.0
77.5°	90.1	90.1	90.1	88.6	88.6	87.1	87.1	88.6	88.6	88.6	90.1
80°	68.7	68.7	68.7	67.2	65.7	65.7	65.7	65.7	65.7	67.2	65.7
82.5°	47.3	47.3	47.3	47.3	47.3	45.8	45.8	45.8	47.3	47.3	45.8
85°	29.0	27.5	29.0	29.0	27.5	29.0	27.5	27.5	26.0	26.0	27.5
87.5°	12.2	10.7	9.2	9.2	10.7	9.2	9.2	9.2	10.7	9.2	9.2
90°	22.5	22.7	23.1	23.5	23.9	24.3	23.9	23.5	23.1	22.7	22.5
92.5°	23.4	23.5	23.7	23.9	24.1	24.3	24.1	23.9	23.7	23.5	23.4
95°	39.6	39.5	39.3	39.1	38.9	38.7	38.9	39.1	39.3	39.5	39.6
97.5°	48.6	48.7	48.9	49.1	49.3	49.5	49.3	49.1	48.9	48.7	48.6
100°	58.4	58.6	59.0	59.4	59.8	60.2	59.8	59.4	59.0	58.6	58.4
102.5°	62.9	63.2	63.8	64.4	65.0	65.6	65.0	64.4	63.8	63.2	62.9
105°	64.7	65.1	65.9	66.7	67.5	68.3	67.5	66.7	65.9	65.1	64.7
107.5°	66.5	66.9	67.7	68.5	69.3	70.1	69.3	68.5	67.7	66.9	66.5
110°	67.4	67.8	68.6	69.4	70.2	71.0	70.2	69.4	68.6	67.8	67.4

TEST NUMBER: P999436

CATALOG NUMBER: SA2XXRDIP-B1005D925UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	69.2	69.5	70.1	70.7	71.3	71.9	71.3	70.7	70.1	69.5	69.2
115°	138.5	131.3	116.9	102.5	88.1	73.7	88.1	102.5	116.9	131.3	138.5
117.5°	474.7	448.5	396.2	343.9	291.5	239.2	291.5	343.9	396.2	448.5	474.7
120°	669.8	656.3	629.4	602.4	575.5	548.5	575.5	602.4	629.4	656.3	669.8
122.5°	717.5	717.6	717.8	718.0	718.2	718.4	718.2	718.0	717.8	717.6	717.5
125°	766.0	766.3	766.9	767.5	768.1	768.7	768.1	767.5	766.9	766.3	766.0
127.5°	812.8	812.9	813.1	813.3	813.5	813.7	813.5	813.3	813.1	812.9	812.8
130°	856.0	855.9	855.7	855.5	855.3	855.1	855.3	855.5	855.7	855.9	856.0
132.5°	896.4	896.3	896.1	895.9	895.7	895.5	895.7	895.9	896.1	896.3	896.4
135°	936.0	935.8	935.4	935.0	934.6	934.2	934.6	935.0	935.4	935.8	936.0
137.5°	972.8	972.5	971.9	971.3	970.7	970.1	970.7	971.3	971.9	972.5	972.8
140°	1007.9	1007.4	1006.4	1005.4	1004.4	1003.4	1004.4	1005.4	1006.4	1007.4	1007.9
142.5°	1040.3	1039.8	1038.8	1037.8	1036.8	1035.8	1036.8	1037.8	1038.8	1039.8	1040.3
145°	1070.0	1069.5	1068.5	1067.5	1066.5	1065.5	1066.5	1067.5	1068.5	1069.5	1070.0
147.5°	1096.0	1095.6	1094.8	1094.0	1093.2	1092.4	1093.2	1094.0	1094.8	1095.6	1096.0
150°	1121.2	1120.7	1119.7	1118.7	1117.7	1116.7	1117.7	1118.7	1119.7	1120.7	1121.2
152.5°	1143.7	1143.0	1141.6	1140.2	1138.8	1137.4	1138.8	1140.2	1141.6	1143.0	1143.7
155°	1163.5	1162.7	1161.1	1159.5	1157.9	1156.3	1157.9	1159.5	1161.1	1162.7	1163.5
157.5°	1181.4	1180.6	1179.0	1177.4	1175.8	1174.2	1175.8	1177.4	1179.0	1180.6	1181.4
160°	1195.8	1195.1	1193.7	1192.3	1190.9	1189.5	1190.9	1192.3	1193.7	1195.1	1195.8
162.5°	1210.2	1209.3	1207.5	1205.7	1203.9	1202.1	1203.9	1205.7	1207.5	1209.3	1210.2
165°	1221.0	1220.3	1218.9	1217.5	1216.1	1214.7	1216.1	1217.5	1218.9	1220.3	1221.0
167.5°	1230.9	1230.0	1228.2	1226.4	1224.6	1222.8	1224.6	1226.4	1228.2	1230.0	1230.9
170°	1238.1	1237.2	1235.4	1233.6	1231.8	1230.0	1231.8	1233.6	1235.4	1237.2	1238.1
172.5°	1243.5	1242.6	1240.8	1239.0	1237.2	1235.4	1237.2	1239.0	1240.8	1242.6	1243.5
175°	1247.1	1246.1	1244.1	1242.1	1240.1	1238.1	1240.1	1242.1	1244.1	1246.1	1247.1
177.5°	1248.0	1247.1	1245.3	1243.5	1241.7	1239.9	1241.7	1243.5	1245.3	1247.1	1248.0
180°	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6

TEST NUMBER: P999436

CATALOG NUMBER: SA2XXRDIP-B1005D925UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8	2197.8
2.5°	2093.9	2101.5	2098.5	2081.7	2098.5	2103.1	2112.2	2121.4	2127.5	2136.7	2144.3
5°	1962.6	1977.8	1987.0	1977.8	2008.4	2013.0	2034.3	2046.6	2064.9	2080.2	2092.4
7.5°	1838.8	1851.1	1869.4	1872.4	1890.8	1912.2	1942.7	1973.2	2002.3	2017.5	2031.3
10°	1706.0	1727.4	1754.8	1748.7	1776.2	1809.8	1841.9	1890.8	1915.2	1942.7	1967.1
12.5°	1573.1	1586.8	1623.5	1635.7	1675.4	1701.4	1745.7	1776.2	1837.3	1869.4	1890.8
15°	1341.0	1397.5	1443.3	1498.3	1550.2	1599.1	1638.8	1693.8	1747.2	1771.6	1806.8
17.5°	1235.6	1261.5	1289.0	1316.5	1383.7	1470.8	1541.0	1600.6	1646.4	1678.5	1719.7
20°	1125.6	1151.6	1182.1	1208.1	1249.3	1311.9	1399.0	1501.3	1556.3	1589.9	1629.6
22.5°	1047.7	1072.2	1092.0	1114.9	1147.0	1192.8	1258.5	1385.2	1458.6	1499.8	1534.9
25°	963.7	994.3	1015.6	1032.4	1058.4	1108.8	1162.3	1234.0	1365.4	1397.5	1446.3
27.5°	905.7	914.8	939.3	965.2	991.2	1018.7	1073.7	1134.8	1223.4	1293.6	1353.2
30°	837.0	859.9	882.8	893.5	916.4	956.1	989.7	1055.4	1124.1	1179.1	1250.8
32.5°	785.0	798.8	814.0	840.0	861.4	888.9	922.5	977.5	1035.5	1070.6	1125.6
35°	727.0	736.1	768.2	778.9	800.3	827.8	861.4	904.2	966.8	994.3	1034.0
37.5°	672.0	693.4	702.5	727.0	746.8	774.3	798.8	847.6	888.9	921.0	957.6
40°	629.2	638.4	655.2	676.6	693.4	714.8	745.3	780.4	824.7	850.7	882.8
42.5°	577.3	584.9	606.3	618.5	646.0	665.9	684.2	727.0	766.7	786.6	818.6
45°	520.8	539.1	552.9	577.3	592.6	617.0	639.9	670.5	707.1	730.0	748.4
47.5°	471.9	490.3	504.0	526.9	551.3	562.0	586.5	618.5	652.1	670.5	696.4
50°	432.2	438.3	464.3	475.0	500.9	522.3	539.1	566.6	603.3	614.0	635.3
52.5°	394.0	398.6	415.4	429.2	452.1	470.4	491.8	517.7	548.3	565.1	581.9
55°	360.4	363.5	371.1	386.4	401.7	424.6	444.4	468.9	494.8	513.2	528.4
57.5°	322.3	328.4	334.5	343.6	358.9	380.3	401.7	424.6	446.0	458.2	478.0
60°	278.0	287.1	297.8	308.5	319.2	334.5	358.9	380.3	400.1	410.8	426.1
62.5°	230.6	248.9	258.1	270.3	279.5	293.2	311.6	336.0	349.7	363.5	375.7
65°	207.7	209.2	210.8	223.0	239.8	253.5	270.3	288.7	310.0	319.2	328.4
67.5°	184.8	186.3	189.4	190.9	197.0	212.3	230.6	250.5	267.3	273.4	282.5
70°	161.9	161.9	168.0	169.5	171.1	172.6	187.9	207.7	223.0	230.6	241.3
72.5°	137.5	139.0	142.0	143.6	146.6	149.7	154.3	164.9	183.3	190.9	203.1
75°	113.0	114.5	116.1	117.6	122.2	123.7	128.3	134.4	142.0	151.2	158.8
77.5°	90.1	90.1	91.6	94.7	97.7	99.3	103.9	106.9	110.0	114.5	120.7
80°	67.2	68.7	68.7	71.8	71.8	73.3	74.8	79.4	82.5	85.5	88.6
82.5°	45.8	48.9	48.9	48.9	50.4	51.9	53.5	53.5	56.5	58.0	62.6
85°	27.5	29.0	29.0	29.0	27.5	30.5	30.5	32.1	32.1	32.1	33.6
87.5°	10.7	9.2	10.7	10.7	10.7	12.2	10.7	10.7	12.2	13.7	13.7
90°	22.0	21.0	20.0	19.0	18.0	16.4	14.8	13.2	11.6	10.8	9.7
92.5°	23.2	22.8	22.4	22.0	21.6	21.0	20.4	19.8	19.2	18.9	19.3
95°	39.1	38.1	37.1	36.1	35.1	33.7	32.3	30.9	29.5	28.8	32.1
97.5°	48.3	47.7	47.1	46.5	45.9	42.7	39.5	36.3	33.1	31.5	39.7
100°	57.6	56.0	54.4	52.8	51.2	47.8	44.4	41.1	37.7	36.0	49.7
102.5°	61.8	59.6	57.4	55.2	53.0	89.4	125.8	162.1	198.5	216.7	216.9
105°	63.6	61.4	59.2	57.0	54.8	109.4	163.9	218.5	273.0	300.3	297.3
107.5°	65.4	63.2	61.0	58.8	56.6	123.9	191.3	258.6	325.9	359.6	357.1
110°	77.4	97.4	117.3	137.3	157.3	215.1	272.8	330.6	388.3	417.2	415.1

TEST NUMBER: P999436

CATALOG NUMBER: SA2XXRDIP-B1005D925UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	112.3	198.4	284.5	370.7	456.8	460.2	463.6	466.9	470.3	472.0	470.2
115°	184.8	277.3	369.8	462.3	554.8	549.8	544.8	539.8	534.8	532.3	530.6
117.5°	489.0	517.6	546.1	574.7	603.3	599.9	596.5	593.1	589.7	588.0	586.0
120°	668.6	666.2	663.9	661.5	659.1	655.5	651.9	648.3	644.7	642.9	641.4
122.5°	716.9	715.7	714.5	713.3	712.1	708.1	704.1	700.1	696.1	694.1	692.5
125°	765.3	763.9	762.6	761.2	759.8	756.0	752.2	748.4	744.6	742.7	741.4
127.5°	811.8	809.8	807.8	805.8	803.8	800.8	797.8	794.8	791.8	790.3	788.9
130°	854.9	852.7	850.5	848.3	846.1	843.9	841.7	839.5	837.3	836.2	834.6
132.5°	895.5	893.7	891.9	890.1	888.3	886.1	883.9	881.7	879.5	878.4	877.1
135°	935.0	933.0	931.0	929.0	927.0	925.2	923.4	921.6	919.8	918.9	917.3
137.5°	971.8	969.8	967.9	965.9	963.9	961.9	959.9	957.9	955.9	954.9	953.7
140°	1007.0	1005.2	1003.4	1001.6	999.8	997.6	995.4	993.2	991.0	989.9	989.1
142.5°	1039.5	1037.9	1036.3	1034.7	1033.1	1030.5	1027.9	1025.3	1022.7	1021.4	1020.7
145°	1069.3	1067.9	1066.5	1065.1	1063.7	1060.3	1056.9	1053.5	1050.1	1048.4	1048.5
147.5°	1095.5	1094.5	1093.5	1092.5	1091.5	1088.1	1084.7	1081.3	1077.9	1076.2	1076.5
150°	1120.6	1119.4	1118.2	1117.0	1115.8	1112.6	1109.4	1106.2	1103.0	1101.4	1102.1
152.5°	1143.1	1141.9	1140.7	1139.5	1138.3	1135.3	1132.3	1129.3	1126.3	1124.8	1125.6
155°	1162.9	1161.7	1160.5	1159.3	1158.1	1155.7	1153.3	1150.9	1148.5	1147.3	1148.2
157.5°	1180.7	1179.3	1177.9	1176.5	1175.1	1173.3	1171.5	1169.8	1168.0	1167.1	1167.9
160°	1195.2	1194.0	1192.8	1191.6	1190.4	1189.2	1188.0	1186.8	1185.6	1185.0	1185.6
162.5°	1209.5	1208.1	1206.7	1205.3	1203.9	1202.9	1201.9	1200.9	1199.9	1199.4	1200.0
165°	1220.3	1218.9	1217.5	1216.1	1214.7	1214.1	1213.5	1212.9	1212.3	1212.0	1212.6
167.5°	1230.2	1228.8	1227.4	1226.0	1224.6	1224.0	1223.4	1222.8	1222.2	1221.9	1222.5
170°	1237.4	1236.0	1234.6	1233.2	1231.8	1231.4	1231.0	1230.6	1230.2	1230.0	1230.6
172.5°	1242.8	1241.4	1240.0	1238.6	1237.2	1236.8	1236.4	1236.0	1235.6	1235.4	1236.0
175°	1246.4	1245.0	1243.6	1242.2	1240.8	1240.4	1240.0	1239.6	1239.2	1239.0	1239.7
177.5°	1247.3	1245.9	1244.5	1243.1	1241.7	1241.5	1241.3	1241.1	1240.9	1240.8	1241.5
180°	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6

TEST NUMBER: P999436

CATALOG NUMBER: SA2XXRDIP-B1005D925UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	2197.8	2197.8	2197.8	2197.8
2.5°	2158.0	2153.5	2181.0	2211.5
5°	2113.8	2121.4	2156.5	2199.3
7.5°	2067.9	2084.7	2126.0	2182.5
10°	2003.8	2034.3	2097.0	2155.0
12.5°	1941.2	1982.4	2042.0	2110.7
15°	1870.9	1916.7	1990.0	2072.5
17.5°	1793.0	1845.0	1930.5	2020.6
20°	1710.6	1779.3	1869.4	1967.1
22.5°	1618.9	1701.4	1794.6	1903.0
25°	1530.3	1620.4	1713.6	1838.8
27.5°	1443.3	1531.9	1635.7	1762.5
30°	1356.2	1437.2	1548.7	1684.6
32.5°	1263.1	1347.1	1464.7	1603.6
35°	1177.5	1261.5	1371.5	1509.0
37.5°	1085.9	1176.0	1281.4	1423.4
40°	979.0	1084.4	1186.7	1322.6
42.5°	890.4	1001.9	1101.2	1229.5
45°	820.2	925.5	1008.0	1133.2
47.5°	754.5	840.0	924.0	1040.1
50°	691.9	757.5	844.6	948.4
52.5°	627.7	684.2	759.1	856.8
55°	569.7	623.1	690.3	765.2
57.5°	516.2	554.4	621.6	688.8
60°	456.7	496.4	548.3	604.8
62.5°	406.3	436.8	485.7	533.0
65°	352.8	381.8	418.5	462.8
67.5°	303.9	329.9	358.9	394.0
70°	259.6	279.5	300.9	331.4
72.5°	212.3	233.7	253.5	278.0
75°	174.1	183.3	200.1	216.9
77.5°	134.4	146.6	155.8	169.5
80°	96.2	106.9	110.0	120.7
82.5°	64.1	70.3	76.4	79.4
85°	36.7	39.7	45.8	47.3
87.5°	13.7	15.3	18.3	21.4
90°	7.5	5.3	3.1	0.9
92.5°	20.1	20.9	21.7	22.5
95°	38.7	45.2	51.8	58.4
97.5°	56.1	72.4	88.8	105.2
100°	77.0	104.4	131.7	159.1
102.5°	217.3	217.7	218.1	218.5
105°	291.3	285.3	279.3	273.3
107.5°	352.1	347.2	342.2	337.2
110°	410.9	406.7	402.5	398.3

TEST NUMBER: P999436

CATALOG NUMBER: SA2XXRDIP-B1005D925UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	466.6	463.1	459.5	455.9
115°	527.2	523.8	520.4	517.0
117.5°	582.0	578.0	574.0	570.0
120°	638.4	635.4	632.4	629.4
122.5°	689.3	686.1	682.9	679.7
125°	738.8	736.2	733.6	731.0
127.5°	786.1	783.3	780.5	777.7
130°	831.4	828.2	825.0	821.8
132.5°	874.5	872.0	869.4	866.8
135°	914.1	910.9	907.7	904.5
137.5°	951.3	948.9	946.5	944.1
140°	987.5	985.9	984.3	982.7
142.5°	1019.3	1017.9	1016.5	1015.1
145°	1048.7	1048.9	1049.1	1049.3
147.5°	1077.1	1077.7	1078.3	1078.9
150°	1103.5	1104.9	1106.3	1107.7
152.5°	1127.2	1128.8	1130.4	1132.0
155°	1150.0	1151.8	1153.6	1155.4
157.5°	1169.5	1171.0	1172.6	1174.2
160°	1186.8	1188.0	1189.2	1190.4
162.5°	1201.2	1202.4	1203.6	1204.8
165°	1213.8	1215.0	1216.2	1217.4
167.5°	1223.7	1224.9	1226.1	1227.3
170°	1231.8	1233.0	1234.2	1235.4
172.5°	1237.2	1238.4	1239.6	1240.8
175°	1241.1	1242.5	1243.9	1245.3
177.5°	1242.9	1244.3	1245.7	1247.1
180°	1242.6	1242.6	1242.6	1242.6

(END OF REPORT)