

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831664

Luminaire Tested: S123DIP-S775D365U950-4F0-1E-UDD-G1

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P831664  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S775D365U950-4F0-1E-UDD-G1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4573.7 lumens  
Efficiency: N/A  
Efficacy: 127.4 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 35.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P831664

CATALOG NUMBER: S123DIP-S775D365U950-4F0-1E-UDD-G1

### Luminous Intensity Polar Plot





TEST NUMBER: P831664

CATALOG NUMBER: S123DIP-S775D365U950-4F0-1E-UDD-G1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78	74				
1	104	100	96	93	99	95	92	89	86	83	81	78	76	74	70	69	68	64				
2	95	88	82	77	90	84	79	74	76	72	69	69	66	63	63	60	58	55				
3	88	78	71	65	83	75	68	63	68	63	59	62	58	55	57	53	51	48				
4	81	70	62	56	77	67	60	55	61	56	51	56	52	48	51	48	45	42				
5	75	63	55	49	71	61	53	48	56	50	45	51	46	42	47	43	40	37				
6	69	57	49	44	66	55	48	42	51	45	40	47	42	38	43	39	35	33				
7	65	52	45	39	61	50	43	38	47	40	36	43	38	34	40	35	32	30				
8	60	48	40	35	57	46	39	34	43	37	33	40	35	31	37	32	29	27				
9	57	44	37	32	54	43	36	31	40	34	30	37	32	28	34	30	27	25				
10	53	41	34	29	51	40	33	29	37	31	27	35	30	26	32	28	25	23				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	22657	22657	22657	22657	22657
5°	28653	27044	22859	18421	16928
10°	28931	29806	22707	14684	12832
15°	21790	27673	22552	12435	10852
20°	15182	22393	22265	10875	9857
25°	11577	17221	21773	10005	9246
30°	10015	13682	20990	9390	8753
35°	9293	11552	20086	8946	8407
40°	8798	10361	18816	8524	8289
45°	8505	9590	17203	8193	8237
50°	8358	8979	15292	7892	8194
55°	8047	8533	13418	7606	8231
60°	7759	8054	11565	7339	8094
65°	7289	7600	9976	7053	7936
70°	6732	7024	8485	6578	7468
75°	6093	6297	7270	6114	6825
80°	5027	5511	5752	5331	5752
85°	3977	4458	4224	4520	4582

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 19642 cd/sqm



TEST NUMBER: P831664

CATALOG NUMBER: S123DIP-S775D365U950-4F0-1E-UDD-G1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	199.0	4.4
10°-20°	495.1	10.8
20°-30°	586.2	12.8
30°-40°	589.4	12.9
40°-50°	540.7	11.8
50°-60°	446.3	9.8
60°-70°	315.7	6.9
70°-80°	168.5	3.7
80°-90°	43.7	1.0
90°-100°	27.6	0.6
100°-110°	83.6	1.8
110°-120°	142.3	3.1
120°-130°	187.3	4.1
130°-140°	210.5	4.6
140°-150°	206.9	4.5
150°-160°	174.2	3.8
160°-170°	116.0	2.5
170°-180°	40.6	0.9
0°-30°	1280.2	28.0
0°-40°	1869.6	40.9
0°-60°	2856.6	62.5
0°-90°	3384.5	74.0
90°-120°	253.6	5.5
90°-150°	858.3	18.8
90°-180°	1189.0	26.0
0°-180°	4573.7	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2105	2105	2105	2105	2105	
5°	2652	2503	2116	1705	1567	253
15°	1955	2483	2024	1116	974	540
25°	975	1450	1833	842	778	460
35°	707	879	1529	681	640	444
45°	559	630	1130	538	541	433
55°	429	455	715	405	439	384
65°	286	298	392	277	312	284
75°	146	151	175	147	164	154
85°	32	36	34	37	37	36
90°	10	8	0	8	10	7
95°	26	25	20	25	26	26
105°	80	80	76	80	80	85
115°	144	144	143	144	144	142
125°	207	210	210	210	207	185
135°	272	274	272	274	272	209
145°	330	332	330	332	330	206
155°	377	378	378	378	377	174
165°	410	411	412	411	410	116
175°	426	427	428	427	426	41
180°	429	429	429	429	429	



TEST NUMBER: P831664

CATALOG NUMBER: S123DIP-S775D365U950-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2104.9	2104.9	2104.9	2104.9	2104.9	2104.9	2104.9	2104.9	2104.9	2104.9	2104.9
2.5°	2372.5	2370.0	2367.6	2355.4	2343.2	2337.3	2331.5	2313.9	2296.3	2276.8	2257.2
5°	2651.8	2658.7	2665.5	2657.7	2649.9	2625.9	2602.0	2570.3	2538.5	2502.9	2467.2
7.5°	2780.8	2784.7	2788.6	2783.7	2778.8	2772.5	2766.1	2737.8	2709.5	2672.8	2636.2
10°	2646.9	2655.7	2664.5	2683.6	2702.6	2724.1	2745.6	2741.7	2737.8	2727.0	2716.3
12.5°	2353.0	2363.7	2374.4	2412.5	2450.6	2499.5	2548.3	2590.3	2632.3	2661.6	2690.9
15°	1955.4	1985.2	2015.0	2049.7	2084.3	2156.1	2227.9	2316.3	2404.7	2483.3	2562.0
17.5°	1610.6	1621.9	1633.1	1670.2	1707.3	1797.7	1888.0	1990.1	2092.2	2222.6	2353.0
20°	1325.4	1335.7	1345.9	1394.8	1443.6	1514.4	1585.2	1700.0	1814.8	1954.9	2095.1
22.5°	1113.5	1129.6	1145.7	1173.1	1200.4	1268.3	1336.2	1438.2	1540.3	1695.1	1849.9
25°	974.8	986.5	998.2	1014.8	1031.4	1085.6	1139.8	1223.8	1307.8	1450.0	1592.1
27.5°	880.0	884.9	889.8	906.4	923.0	958.2	993.3	1065.6	1137.9	1258.5	1379.1
30°	805.8	809.2	812.6	827.3	841.9	865.9	889.8	942.1	994.3	1100.8	1207.2
32.5°	754.0	756.5	758.9	770.2	781.4	798.5	815.6	853.7	891.8	979.7	1067.6
35°	707.2	708.6	710.1	718.4	726.7	739.4	752.1	780.9	809.7	879.1	948.4
37.5°	666.1	668.1	670.0	674.9	679.8	691.0	702.3	725.2	748.2	801.4	854.6
40°	626.1	629.5	632.9	636.3	639.8	649.0	658.3	675.9	693.5	737.4	781.4
42.5°	591.9	595.3	598.7	600.2	601.7	607.0	612.4	628.5	644.6	677.4	710.1
45°	558.7	560.2	561.6	563.1	564.6	568.9	573.3	587.5	601.7	630.0	658.3
47.5°	528.4	528.4	528.4	529.4	530.4	534.3	538.2	548.4	558.7	580.7	602.6
50°	499.1	499.1	499.1	497.6	496.2	498.6	501.1	508.9	516.7	536.2	555.8
52.5°	463.9	463.9	463.9	464.4	464.9	464.9	464.9	471.8	478.6	496.2	513.8
55°	428.8	430.7	432.7	431.2	429.8	430.7	431.7	436.1	440.5	454.7	468.8
57.5°	393.6	394.6	395.6	395.1	394.6	395.1	395.6	399.5	403.4	414.1	424.9
60°	360.4	360.4	360.4	359.4	358.5	359.4	360.4	362.4	364.3	374.1	383.9
62.5°	323.3	323.8	324.3	324.8	325.3	324.3	323.3	325.7	328.2	335.5	342.8
65°	286.2	286.7	287.2	288.6	290.1	289.1	288.1	290.6	293.0	298.4	303.8
67.5°	253.0	252.0	251.0	251.5	252.0	253.5	254.9	255.4	255.9	261.8	267.6
70°	213.9	214.9	215.9	215.4	214.9	215.4	215.9	217.3	218.8	223.2	227.6
72.5°	178.7	179.2	179.7	179.7	179.7	180.7	181.7	183.1	184.6	187.0	189.5
75°	146.5	146.5	146.5	147.5	148.5	149.0	149.4	149.4	149.4	151.4	153.3
77.5°	111.3	113.8	116.2	115.7	115.3	116.2	117.2	118.7	120.1	121.1	122.1
80°	81.1	81.1	81.1	81.6	82.0	83.5	85.0	86.0	86.9	88.9	90.8
82.5°	51.8	52.3	52.7	54.2	55.7	56.7	57.6	59.1	60.6	60.6	60.6
85°	32.2	31.3	30.3	31.3	32.2	33.2	34.2	34.7	35.2	36.1	37.1
87.5°	15.6	15.6	15.6	15.6	15.6	16.1	16.6	16.6	16.6	16.6	16.6
90°	10.1	10.0	9.8	9.7	9.5	9.3	9.0	8.7	8.4	8.1	7.1
92.5°	14.5	14.6	14.8	14.9	15.1	15.1	14.8	14.6	14.4	14.2	13.7
95°	26.3	26.3	26.3	26.3	26.3	26.1	25.8	25.5	25.2	24.9	24.3
97.5°	37.8	37.8	37.9	38.0	38.1	37.9	37.5	37.2	36.8	36.4	36.0
100°	51.2	51.1	50.9	50.8	50.6	50.5	50.2	50.0	49.8	49.6	49.2
102.5°	65.1	65.1	65.2	65.3	65.4	65.3	65.1	64.8	64.6	64.4	63.9
105°	80.2	80.1	79.9	79.8	79.6	79.6	79.6	79.6	79.6	79.6	78.9
107.5°	95.7	95.8	95.9	96.0	96.0	96.0	95.7	95.5	95.3	95.1	94.8
110°	111.6	111.7	111.9	112.0	112.2	112.1	111.8	111.5	111.2	110.9	110.8

TEST NUMBER: P831664

CATALOG NUMBER: S123DIP-S775D365U950-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	128.4	128.4	128.4	128.4	128.4	128.3	127.9	127.5	127.1	126.8	126.8
115°	143.6	143.7	143.8	143.8	143.9	143.9	143.8	143.8	143.7	143.6	143.8
117.5°	159.1	159.4	159.6	159.8	160.0	160.1	160.1	160.1	160.1	160.1	160.3
120°	175.6	175.8	175.9	176.1	176.2	176.4	176.4	176.5	176.6	176.7	177.0
122.5°	191.5	191.7	191.9	192.2	192.4	192.6	192.8	193.1	193.3	193.5	193.7
125°	207.3	207.6	207.9	208.2	208.5	208.8	209.1	209.4	209.7	210.0	210.2
127.5°	223.2	223.5	223.8	224.1	224.4	224.8	225.2	225.7	226.1	226.6	226.7
130°	238.7	239.2	239.7	240.3	240.8	241.2	241.5	241.8	242.1	242.4	242.6
132.5°	254.9	255.2	255.6	256.0	256.4	256.7	257.1	257.5	257.9	258.2	258.4
135°	271.7	271.9	272.0	272.2	272.3	272.6	272.9	273.2	273.5	273.8	273.8
137.5°	286.6	286.8	287.0	287.2	287.5	287.8	288.1	288.5	288.9	289.3	289.0
140°	301.1	301.6	302.1	302.6	303.2	303.5	303.5	303.6	303.7	303.8	303.7
142.5°	315.9	316.3	316.6	317.0	317.4	317.6	317.7	317.8	317.8	317.9	317.8
145°	330.1	330.4	330.7	331.0	331.3	331.4	331.5	331.6	331.7	331.7	331.5
147.5°	342.9	343.3	343.8	344.2	344.7	344.9	344.9	344.9	344.9	344.9	344.7
150°	355.0	355.5	355.9	356.4	356.8	357.0	357.0	357.0	357.0	357.0	356.9
152.5°	366.8	367.2	367.6	367.9	368.3	368.4	368.3	368.1	368.0	367.8	367.7
155°	377.3	377.8	378.3	378.8	379.4	379.5	379.2	378.9	378.6	378.3	378.2
157.5°	387.0	387.5	387.9	388.4	388.8	388.9	388.6	388.3	388.0	387.7	387.6
160°	396.5	396.8	397.1	397.4	397.7	397.6	397.3	396.9	396.5	396.1	396.1
162.5°	403.6	404.1	404.6	405.1	405.6	405.7	405.3	405.0	404.6	404.2	404.2
165°	410.3	410.8	411.3	411.9	412.4	412.4	412.0	411.5	411.1	410.6	410.6
167.5°	416.4	416.8	417.3	417.7	418.2	418.2	417.7	417.3	416.8	416.4	416.3
170°	420.7	421.3	421.8	422.3	422.8	422.8	422.3	421.8	421.3	420.7	420.7
172.5°	424.1	424.6	425.2	425.7	426.2	426.3	425.8	425.4	424.9	424.5	424.5
175°	426.5	427.0	427.5	428.0	428.6	428.6	428.2	427.7	427.3	426.8	426.8
177.5°	427.8	428.3	428.9	429.4	429.9	430.0	429.5	429.1	428.6	428.2	428.2
180°	429.2	429.2	429.2	429.2	429.2	429.2	429.2	429.2	429.2	429.2	429.2



TEST NUMBER: P831664

CATALOG NUMBER: S123DIP-S775D365U950-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2104.9	2104.9	2104.9	2104.9	2104.9	2104.9	2104.9	2104.9	2104.9	2104.9	2104.9
2.5°	2251.4	2245.5	2224.0	2202.5	2178.1	2153.7	2135.6	2117.6	2090.7	2063.8	2041.9
5°	2439.9	2412.5	2367.1	2321.7	2260.2	2198.6	2157.1	2115.6	2059.9	2004.3	1959.8
7.5°	2589.3	2542.4	2478.9	2415.5	2334.9	2254.3	2178.1	2101.9	2017.0	1932.0	1862.6
10°	2684.6	2652.8	2579.6	2506.3	2398.4	2290.4	2184.0	2077.5	1968.1	1858.7	1766.9
12.5°	2693.8	2696.8	2629.4	2562.0	2439.9	2317.8	2188.4	2059.0	1921.2	1783.5	1676.6
15°	2612.3	2662.6	2625.5	2588.3	2465.3	2342.2	2183.0	2023.8	1865.1	1706.4	1582.8
17.5°	2460.9	2568.8	2574.2	2579.6	2456.5	2333.4	2157.1	1980.8	1801.1	1621.4	1491.5
20°	2254.3	2413.5	2468.2	2522.9	2422.8	2322.7	2133.2	1943.7	1742.5	1541.3	1405.0
22.5°	2043.3	2236.7	2336.8	2437.0	2362.7	2288.5	2086.8	1885.1	1672.7	1460.2	1322.0
25°	1803.1	2014.0	2167.9	2321.7	2276.3	2230.9	2032.1	1833.3	1607.2	1381.1	1240.0
27.5°	1593.5	1807.9	1993.5	2179.1	2169.3	2159.6	1962.3	1765.0	1533.5	1302.0	1165.7
30°	1407.0	1606.7	1814.3	2021.8	2045.8	2069.7	1879.2	1688.8	1456.8	1224.8	1093.5
32.5°	1241.9	1416.3	1639.0	1861.7	1908.5	1955.4	1783.5	1611.6	1382.1	1152.5	1026.1
35°	1106.6	1264.9	1487.6	1710.3	1768.9	1827.5	1678.0	1528.6	1304.9	1081.2	960.6
37.5°	987.0	1119.3	1336.7	1554.0	1625.8	1697.6	1563.8	1429.9	1220.4	1010.9	900.1
40°	887.9	994.3	1194.1	1393.8	1476.8	1559.8	1449.5	1339.1	1140.3	941.6	839.5
42.5°	804.8	899.6	1080.8	1261.9	1341.5	1421.1	1327.9	1234.6	1057.8	881.0	787.7
45°	734.0	809.7	974.3	1138.9	1214.6	1290.3	1210.2	1130.1	974.3	818.5	731.6
47.5°	667.6	732.6	873.2	1013.8	1081.2	1148.6	1086.1	1023.6	891.8	759.9	681.3
50°	608.0	660.3	783.3	906.4	965.0	1023.6	968.4	913.2	804.8	696.4	628.0
52.5°	556.2	598.7	701.8	804.8	855.1	905.4	858.1	810.7	724.7	638.8	579.2
55°	505.0	541.1	630.5	719.9	754.0	788.2	751.6	715.0	645.6	576.3	526.0
57.5°	457.1	489.3	562.6	635.9	662.2	688.6	655.4	622.2	569.9	517.7	475.7
60°	410.2	436.6	497.6	558.7	574.8	590.9	564.1	537.2	500.6	463.9	426.3
62.5°	366.8	390.7	436.1	481.5	492.3	503.0	482.5	462.0	434.2	406.3	377.0
65°	321.8	339.9	377.0	414.1	421.0	427.8	409.7	391.7	370.7	349.7	328.2
67.5°	280.3	293.0	323.3	353.6	354.1	354.6	339.9	325.3	313.5	301.8	284.7
70°	239.8	252.0	272.0	292.0	292.5	293.0	281.3	269.6	260.8	252.0	239.3
72.5°	198.3	207.1	222.2	237.3	236.4	235.4	228.1	220.7	213.9	207.1	197.8
75°	160.7	168.0	178.3	188.5	185.6	182.6	178.7	174.8	169.0	163.1	157.3
77.5°	126.5	130.9	136.7	142.6	140.6	138.7	135.3	131.9	127.5	123.1	120.6
80°	92.8	94.7	98.7	102.6	101.6	100.6	96.7	92.8	91.8	90.8	87.4
82.5°	63.0	65.4	66.4	67.4	66.9	66.4	63.5	60.6	59.6	58.6	58.1
85°	37.6	38.1	38.6	39.1	37.6	36.1	35.2	34.2	34.2	34.2	33.7
87.5°	17.1	17.6	17.6	17.6	17.1	16.6	15.6	14.7	15.1	15.6	15.6
90°	6.1	5.2	4.2	3.3	2.6	1.8	1.1	0.3	1.1	1.8	2.6
92.5°	13.3	12.8	12.4	11.9	11.5	11.0	10.6	10.1	10.6	11.0	11.5
95°	23.7	23.1	22.6	22.0	21.5	20.9	20.4	19.9	20.4	20.9	21.5
97.5°	35.5	35.1	34.6	34.2	33.8	33.5	33.1	32.7	33.1	33.5	33.8
100°	48.8	48.4	48.1	47.6	47.2	46.7	46.3	45.9	46.3	46.7	47.2
102.5°	63.3	62.8	62.3	61.9	61.7	61.5	61.2	61.0	61.2	61.5	61.7
105°	78.2	77.5	76.9	76.5	76.3	76.2	76.0	75.9	76.0	76.2	76.3
107.5°	94.5	94.2	93.9	93.7	93.6	93.5	93.5	93.4	93.5	93.5	93.6
110°	110.6	110.5	110.3	110.2	110.0	109.9	109.7	109.6	109.7	109.9	110.0





TEST NUMBER: P831664

CATALOG NUMBER: S123DIP-S775D365U950-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	126.8	126.8	126.8	126.7	126.7	126.6	126.5	126.4	126.5	126.6	126.7
115°	143.9	144.1	144.2	144.2	144.0	143.7	143.5	143.3	143.5	143.7	144.0
117.5°	160.4	160.6	160.7	160.8	160.7	160.6	160.6	160.5	160.6	160.6	160.7
120°	177.4	177.8	178.2	178.1	177.7	177.2	176.8	176.3	176.8	177.2	177.7
122.5°	193.8	194.0	194.1	194.0	193.7	193.4	193.1	192.8	193.1	193.4	193.7
125°	210.3	210.5	210.6	210.6	210.4	210.1	209.9	209.7	209.9	210.1	210.4
127.5°	226.9	227.0	227.2	227.0	226.6	226.1	225.7	225.2	225.7	226.1	226.6
130°	242.8	243.1	243.3	243.1	242.5	241.9	241.3	240.7	241.3	241.9	242.5
132.5°	258.5	258.7	258.8	258.6	258.0	257.4	256.8	256.2	256.8	257.4	258.0
135°	273.9	274.0	274.1	273.9	273.4	273.0	272.5	272.1	272.5	273.0	273.4
137.5°	288.8	288.6	288.4	288.1	287.7	287.3	286.9	286.6	286.9	287.3	287.7
140°	303.6	303.5	303.5	303.2	302.9	302.5	302.1	301.7	302.1	302.5	302.9
142.5°	317.6	317.5	317.3	317.1	316.7	316.3	315.9	315.6	315.9	316.3	316.7
145°	331.3	331.1	330.8	330.7	330.5	330.4	330.2	330.1	330.2	330.4	330.5
147.5°	344.4	344.2	344.0	343.7	343.4	343.1	342.8	342.5	342.8	343.1	343.4
150°	356.7	356.6	356.4	356.3	356.1	356.0	355.8	355.7	355.8	356.0	356.1
152.5°	367.7	367.6	367.5	367.4	367.1	366.9	366.7	366.5	366.7	366.9	367.1
155°	378.1	378.0	378.0	377.9	377.9	377.9	377.9	377.9	377.9	377.9	377.9
157.5°	387.6	387.5	387.4	387.4	387.5	387.6	387.6	387.7	387.6	387.6	387.5
160°	396.1	396.1	396.1	396.2	396.4	396.5	396.7	396.8	396.7	396.5	396.4
162.5°	404.1	404.0	403.9	404.0	404.2	404.4	404.7	404.9	404.7	404.4	404.2
165°	410.6	410.6	410.6	410.7	411.0	411.2	411.4	411.6	411.4	411.2	411.0
167.5°	416.2	416.1	416.1	416.2	416.5	416.8	417.1	417.4	417.1	416.8	416.5
170°	420.7	420.7	420.7	420.9	421.2	421.5	421.8	422.1	421.8	421.5	421.2
172.5°	424.5	424.5	424.5	424.6	424.9	425.2	425.5	425.8	425.5	425.2	424.9
175°	426.8	426.8	426.8	427.0	427.3	427.6	427.9	428.2	427.9	427.6	427.3
177.5°	428.2	428.2	428.2	428.3	428.6	428.9	429.2	429.5	429.2	428.9	428.6
180°	429.2	429.2	429.2	429.2	429.2	429.2	429.2	429.2	429.2	429.2	429.2



TEST NUMBER: P831664

CATALOG NUMBER: S123DIP-S775D365U950-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2104.9	2104.9	2104.9	2104.9	2104.9	2104.9	2104.9	2104.9	2104.9	2104.9	2104.9
2.5°	2019.9	2000.8	1981.8	1967.1	1952.5	1927.6	1902.7	1896.8	1891.0	1882.7	1874.4
5°	1915.4	1868.5	1821.6	1779.6	1737.6	1704.9	1672.2	1650.7	1629.2	1613.6	1597.9
7.5°	1793.3	1723.0	1652.6	1602.8	1553.0	1505.6	1458.3	1443.1	1428.0	1407.5	1387.0
10°	1675.1	1597.4	1519.8	1454.8	1389.9	1343.5	1297.1	1278.5	1260.0	1234.1	1208.2
12.5°	1569.6	1484.6	1399.7	1334.2	1268.8	1223.8	1178.9	1152.1	1125.2	1110.5	1095.9
15°	1459.2	1368.4	1277.6	1217.0	1156.5	1115.9	1075.4	1051.9	1028.5	1014.3	1000.2
17.5°	1361.6	1271.7	1181.8	1123.7	1065.6	1028.5	991.4	970.9	950.4	939.6	928.9
20°	1268.8	1180.9	1093.0	1036.3	979.7	949.4	919.1	905.9	892.7	883.9	875.2
22.5°	1183.8	1097.4	1010.9	962.6	914.2	889.8	865.4	856.1	846.8	839.5	832.2
25°	1098.8	1021.7	944.5	903.5	862.5	842.4	822.4	813.1	803.9	796.5	789.2
27.5°	1029.5	955.7	882.0	846.8	811.7	796.0	780.4	773.1	765.8	758.9	752.1
30°	962.1	896.2	830.2	799.9	769.7	755.5	741.3	734.0	726.7	720.3	714.0
32.5°	899.6	842.9	786.3	758.4	730.6	718.9	707.2	698.4	689.6	684.7	679.8
35°	840.0	789.2	738.4	715.5	692.5	680.8	669.1	661.7	654.4	650.5	646.6
37.5°	789.2	743.8	698.4	676.4	654.4	643.2	631.9	625.6	619.2	617.8	616.3
40°	737.4	698.4	659.3	637.8	616.3	606.6	596.8	592.9	589.0	588.0	587.0
42.5°	694.5	656.4	618.3	598.7	579.2	570.9	562.6	560.6	558.7	560.2	561.6
45°	644.6	612.9	581.2	563.1	545.0	538.2	531.3	529.9	528.4	531.3	534.3
47.5°	602.6	573.3	544.0	526.9	509.9	505.0	500.1	499.6	499.1	503.0	506.9
50°	559.7	531.3	503.0	489.3	475.7	471.3	466.9	468.3	469.8	476.2	482.5
52.5°	519.6	493.3	466.9	454.2	441.5	438.6	435.6	439.0	442.5	449.3	456.1
55°	475.7	451.7	427.8	418.0	408.3	405.3	402.4	409.3	416.1	422.4	428.8
57.5°	433.7	412.7	391.7	382.9	374.1	373.6	373.1	379.5	385.8	392.6	399.5
60°	388.7	371.2	353.6	346.7	339.9	340.9	341.9	349.2	356.5	361.9	367.3
62.5°	347.7	333.1	318.4	312.1	305.7	308.2	310.6	317.9	325.3	331.6	337.9
65°	306.7	294.5	282.3	277.9	273.5	276.9	280.3	286.7	293.0	297.4	301.8
67.5°	267.6	257.4	247.1	243.7	240.3	243.7	247.1	253.5	259.8	264.2	268.6
70°	226.6	218.3	210.0	207.6	205.1	209.0	212.9	218.3	223.7	228.1	232.5
72.5°	188.5	182.2	175.8	175.3	174.8	178.3	181.7	187.0	192.4	195.3	198.3
75°	151.4	148.0	144.6	144.1	143.6	147.0	150.4	153.3	156.3	158.7	161.2
77.5°	118.2	115.3	112.3	112.8	113.3	115.7	118.2	121.1	124.0	125.5	127.0
80°	84.0	83.0	82.0	83.0	84.0	86.0	87.9	89.9	91.8	92.8	93.8
82.5°	57.6	56.7	55.7	57.1	58.6	60.1	61.5	63.0	64.5	65.0	65.4
85°	33.2	34.7	36.1	36.1	36.1	36.6	37.1	37.6	38.1	37.6	37.1
87.5°	15.6	16.1	16.6	16.6	16.6	17.1	17.6	17.6	17.6	17.1	16.6
90°	3.3	4.2	5.2	6.1	7.1	8.1	8.4	8.7	9.0	9.3	9.5
92.5°	11.9	12.4	12.8	13.3	13.7	14.2	14.4	14.6	14.8	15.1	15.1
95°	22.0	22.6	23.1	23.7	24.3	24.9	25.2	25.5	25.8	26.1	26.3
97.5°	34.2	34.6	35.1	35.5	36.0	36.4	36.8	37.2	37.5	37.9	38.1
100°	47.6	48.1	48.4	48.8	49.2	49.6	49.8	50.0	50.2	50.5	50.6
102.5°	61.9	62.3	62.8	63.3	63.9	64.4	64.6	64.8	65.1	65.3	65.4
105°	76.5	76.9	77.5	78.2	78.9	79.6	79.6	79.6	79.6	79.6	79.6
107.5°	93.7	93.9	94.2	94.5	94.8	95.1	95.3	95.5	95.7	96.0	96.0
110°	110.2	110.3	110.5	110.6	110.8	110.9	111.2	111.5	111.8	112.1	112.2



TEST NUMBER: P831664

CATALOG NUMBER: S123DIP-S775D365U950-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	126.7	126.8	126.8	126.8	126.8	126.8	127.1	127.5	127.9	128.3	128.4
115°	144.2	144.2	144.1	143.9	143.8	143.6	143.7	143.8	143.8	143.9	143.9
117.5°	160.8	160.7	160.6	160.4	160.3	160.1	160.1	160.1	160.1	160.1	160.0
120°	178.1	178.2	177.8	177.4	177.0	176.7	176.6	176.5	176.4	176.4	176.2
122.5°	194.0	194.1	194.0	193.8	193.7	193.5	193.3	193.1	192.8	192.6	192.4
125°	210.6	210.6	210.5	210.3	210.2	210.0	209.7	209.4	209.1	208.8	208.5
127.5°	227.0	227.2	227.0	226.9	226.7	226.6	226.1	225.7	225.2	224.8	224.4
130°	243.1	243.3	243.1	242.8	242.6	242.4	242.1	241.8	241.5	241.2	240.8
132.5°	258.6	258.8	258.7	258.5	258.4	258.2	257.9	257.5	257.1	256.7	256.4
135°	273.9	274.1	274.0	273.9	273.8	273.8	273.5	273.2	272.9	272.6	272.3
137.5°	288.1	288.4	288.6	288.8	289.0	289.3	288.9	288.5	288.1	287.8	287.5
140°	303.2	303.5	303.5	303.6	303.7	303.8	303.7	303.6	303.5	303.5	303.2
142.5°	317.1	317.3	317.5	317.6	317.8	317.9	317.8	317.8	317.7	317.6	317.4
145°	330.7	330.8	331.1	331.3	331.5	331.7	331.7	331.6	331.5	331.4	331.3
147.5°	343.7	344.0	344.2	344.4	344.7	344.9	344.9	344.9	344.9	344.9	344.7
150°	356.3	356.4	356.6	356.7	356.9	357.0	357.0	357.0	357.0	357.0	356.8
152.5°	367.4	367.5	367.6	367.7	367.7	367.8	368.0	368.1	368.3	368.4	368.3
155°	377.9	378.0	378.0	378.1	378.2	378.3	378.6	378.9	379.2	379.5	379.4
157.5°	387.4	387.4	387.5	387.6	387.6	387.7	388.0	388.3	388.6	388.9	388.8
160°	396.2	396.1	396.1	396.1	396.1	396.1	396.5	396.9	397.3	397.6	397.7
162.5°	404.0	403.9	404.0	404.1	404.2	404.2	404.6	405.0	405.3	405.7	405.6
165°	410.7	410.6	410.6	410.6	410.6	410.6	411.1	411.5	412.0	412.4	412.4
167.5°	416.2	416.1	416.1	416.2	416.3	416.4	416.8	417.3	417.7	418.2	418.2
170°	420.9	420.7	420.7	420.7	420.7	420.7	421.3	421.8	422.3	422.8	422.8
172.5°	424.6	424.5	424.5	424.5	424.5	424.5	424.9	425.4	425.8	426.3	426.2
175°	427.0	426.8	426.8	426.8	426.8	426.8	427.3	427.7	428.2	428.6	428.6
177.5°	428.3	428.2	428.2	428.2	428.2	428.2	428.6	429.1	429.5	430.0	429.9
180°	429.2	429.2	429.2	429.2	429.2	429.2	429.2	429.2	429.2	429.2	429.2



TEST NUMBER: P831664

CATALOG NUMBER: S123DIP-S775D365U950-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	2104.9	2104.9	2104.9	2104.9
2.5°	1870.9	1867.5	1853.8	1840.2
5°	1586.2	1574.5	1570.6	1566.7
7.5°	1386.0	1385.0	1364.5	1344.0
10°	1209.7	1211.1	1192.6	1174.0
12.5°	1083.7	1071.5	1070.0	1068.5
15°	988.9	977.7	975.8	973.8
17.5°	922.0	915.2	913.2	911.3
20°	871.2	867.3	863.9	860.5
22.5°	827.3	822.4	819.5	816.5
25°	784.8	780.4	779.4	778.5
27.5°	746.7	741.3	741.3	741.3
30°	710.6	707.2	705.7	704.2
32.5°	676.9	673.9	673.9	673.9
35°	645.1	643.7	641.7	639.8
37.5°	616.3	616.3	615.3	614.4
40°	588.5	589.9	589.9	589.9
42.5°	563.1	564.6	564.6	564.6
45°	536.7	539.2	540.1	541.1
47.5°	510.8	514.7	515.7	516.7
50°	485.4	488.4	488.9	489.3
52.5°	459.6	463.0	465.4	467.9
55°	432.2	435.6	437.1	438.6
57.5°	402.9	406.3	406.8	407.3
60°	370.7	374.1	375.1	376.0
62.5°	339.9	341.9	342.8	343.8
65°	304.7	307.7	309.6	311.6
67.5°	271.0	273.5	273.5	273.5
70°	233.4	234.4	235.9	237.3
72.5°	198.8	199.3	199.3	199.3
75°	162.1	163.1	163.6	164.1
77.5°	127.5	128.0	128.0	128.0
80°	93.3	92.8	92.8	92.8
82.5°	64.0	62.5	62.5	62.5
85°	36.6	36.1	36.6	37.1
87.5°	16.6	16.6	16.6	16.6
90°	9.7	9.8	10.0	10.1
92.5°	14.9	14.8	14.6	14.5
95°	26.3	26.3	26.3	26.3
97.5°	38.0	37.9	37.8	37.8
100°	50.8	50.9	51.1	51.2
102.5°	65.3	65.2	65.1	65.1
105°	79.8	79.9	80.1	80.2
107.5°	96.0	95.9	95.8	95.7
110°	112.0	111.9	111.7	111.6



TEST NUMBER: P831664

CATALOG NUMBER: S123DIP-S775D365U950-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	128.4	128.4	128.4	128.4
115°	143.8	143.8	143.7	143.6
117.5°	159.8	159.6	159.4	159.1
120°	176.1	175.9	175.8	175.6
122.5°	192.2	191.9	191.7	191.5
125°	208.2	207.9	207.6	207.3
127.5°	224.1	223.8	223.5	223.2
130°	240.3	239.7	239.2	238.7
132.5°	256.0	255.6	255.2	254.9
135°	272.2	272.0	271.9	271.7
137.5°	287.2	287.0	286.8	286.6
140°	302.6	302.1	301.6	301.1
142.5°	317.0	316.6	316.3	315.9
145°	331.0	330.7	330.4	330.1
147.5°	344.2	343.8	343.3	342.9
150°	356.4	355.9	355.5	355.0
152.5°	367.9	367.6	367.2	366.8
155°	378.8	378.3	377.8	377.3
157.5°	388.4	387.9	387.5	387.0
160°	397.4	397.1	396.8	396.5
162.5°	405.1	404.6	404.1	403.6
165°	411.9	411.3	410.8	410.3
167.5°	417.7	417.3	416.8	416.4
170°	422.3	421.8	421.3	420.7
172.5°	425.7	425.2	424.6	424.1
175°	428.0	427.5	427.0	426.5
177.5°	429.4	428.9	428.3	427.8
180°	429.2	429.2	429.2	429.2



TEST NUMBER: P831664

CATALOG NUMBER: S123DIP-S775D365U950-4F0-1E-UDD-G1

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.41	17.48	17.14	18.22	19.11	18.65	19.72	19.38	20.46	21.34
	3H	18.08	19.03	18.82	19.78	20.70	20.09	21.04	20.83	21.80	22.71
	4H	18.66	19.56	19.42	20.32	21.25	20.55	21.45	21.31	22.21	23.14
	6H	19.04	19.87	19.82	20.64	21.59	20.83	21.66	21.61	22.44	23.38
	8H	19.15	19.93	19.93	20.72	21.67	20.90	21.69	21.69	22.48	23.43
	12H	19.20	19.95	19.98	20.73	21.70	20.93	21.68	21.72	22.46	23.43
4H	2H	17.01	17.91	17.78	18.67	19.60	18.84	19.74	19.60	20.50	21.43
	3H	18.86	19.61	19.63	20.41	21.35	20.47	21.22	21.25	22.02	22.97
	4H	19.56	20.24	20.35	21.04	22.02	21.07	21.74	21.85	22.54	23.52
	6H	20.05	20.64	20.86	21.46	22.44	21.48	22.07	22.29	22.89	23.87
	8H	20.19	20.74	21.00	21.56	22.55	21.60	22.15	22.41	22.96	23.96
	12H	20.27	20.76	21.10	21.60	22.60	21.65	22.14	22.48	22.98	23.98
8H	4H	19.85	20.39	20.66	21.21	22.20	21.19	21.73	22.00	22.55	23.54
	6H	20.44	20.89	21.28	21.76	22.75	21.70	22.15	22.54	23.01	24.00
	8H	20.65	21.05	21.50	21.91	22.92	21.88	22.28	22.73	23.14	24.15
	12H	20.78	21.14	21.64	21.98	23.05	21.99	22.34	22.84	23.19	24.26
12H	4H	19.86	20.35	20.69	21.19	22.19	21.17	21.66	22.00	22.50	23.50
	6H	20.49	20.90	21.34	21.75	22.76	21.71	22.11	22.56	22.97	23.98
	8H	20.74	21.09	21.59	21.94	23.01	21.92	22.27	22.77	23.12	24.19