

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333620-927

Luminaire Tested: **S125RDIP-S1270D590U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333620-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D590U927-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5485.0 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333620-927

CATALOG NUMBER: S125RDIP-S1270D590U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333620-927

CATALOG NUMBER: S125RDIP-S1270D590U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	70
1	103	98	94	91	97	93	90	87	84	81	79	75	73	71	67	65	64	60
2	94	86	80	75	88	82	76	72	74	69	66	66	63	60	59	57	54	51
3	86	76	69	63	81	72	66	60	65	60	56	59	55	51	53	49	47	43
4	79	68	60	53	74	64	57	51	58	52	48	53	48	44	47	43	40	37
5	72	61	52	46	68	58	50	45	52	46	41	47	42	38	43	39	35	33
6	67	55	46	40	63	52	44	39	47	41	36	43	38	34	39	35	31	29
7	62	49	41	36	59	47	40	34	43	37	32	39	34	30	36	31	28	26
8	58	45	37	32	55	43	36	31	39	33	29	36	31	27	33	28	25	23
9	54	41	34	28	51	40	32	28	36	30	26	33	28	24	30	26	23	21
10	50	38	31	26	48	36	30	25	34	28	24	31	26	22	28	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10561	10561	10561
5°	10585	10466	10529
10°	10506	10368	10368
15°	10380	10158	10075
20°	10221	9864	9745
25°	10033	9576	9365
30°	9801	9238	8944
35°	9563	8891	8472
40°	9340	8528	8008
45°	9070	8122	7501
50°	8799	7681	6974
55°	8483	7260	6411
60°	8169	6748	5807
65°	7795	6154	5115
70°	7370	5410	4409
75°	6780	4561	3666
80°	5973	3582	3080
85°	5039	2927	2749



TEST NUMBER: P333620-927

CATALOG NUMBER: S125RDIP-S1270D590U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.8	2.8
10°-20°	429.7	7.8
20°-30°	623.1	11.4
30°-40°	710.2	12.9
40°-50°	692.3	12.6
50°-60°	582.7	10.6
60°-70°	408.5	7.4
70°-80°	210.0	3.8
80°-90°	54.3	1.0
90°-100°	38.9	0.7
100°-110°	114.9	2.1
110°-120°	194.5	3.5
120°-130°	256.0	4.7
130°-140°	286.9	5.2
140°-150°	281.2	5.1
150°-160°	236.2	4.3
160°-170°	157.0	2.9
170°-180°	54.9	1.0
0°-30°	1206.6	22.0
0°-40°	1916.8	34.9
0°-60°	3191.8	58.2
0°-90°	3864.5	70.5
90°-120°	348.3	6.3
90°-150°	1172.4	21.4
90°-180°	1620.0	29.5
0°-180°	5485.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1635	1635	1635	1635	1635	
5°	1633	1627	1614	1626	1624	155
15°	1552	1544	1519	1517	1507	437
25°	1408	1388	1344	1328	1314	648
35°	1213	1182	1128	1093	1074	759
45°	993	955	889	842	821	766
55°	753	712	645	591	569	674
65°	510	467	403	355	335	505
75°	272	234	183	157	147	288
85°	68	47	40	38	37	76
90°	0	4	7	10	11	5
95°	29	30	35	38	39	31
105°	103	105	108	111	112	110
115°	195	197	198	197	197	193
125°	284	287	287	287	286	254
135°	370	372	373	373	371	285
145°	448	450	451	451	450	280
155°	512	512	513	514	512	236
165°	557	556	557	558	556	157
175°	579	578	578	580	577	55
180°	581	581	581	581	581	



TEST NUMBER: P333620-927

CATALOG NUMBER: S125RDIP-S1270D590U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3
2.5°	1638.2	1637.6	1636.9	1636.3	1635.6	1634.2	1632.0	1629.8	1627.6	1625.4	1627.6
5°	1632.8	1631.7	1630.6	1629.5	1628.4	1626.4	1623.3	1620.3	1617.3	1614.3	1617.0
7.5°	1616.8	1615.7	1614.7	1613.6	1612.6	1610.3	1606.6	1603.0	1599.4	1595.8	1597.7
10°	1602.0	1601.1	1600.3	1599.5	1598.6	1596.3	1592.4	1588.6	1584.8	1581.0	1581.8
12.5°	1585.2	1584.1	1583.0	1582.0	1581.0	1577.9	1572.7	1567.6	1562.3	1557.2	1557.8
15°	1552.5	1550.9	1549.3	1547.6	1545.9	1542.2	1536.4	1530.7	1525.0	1519.2	1518.9
17.5°	1515.7	1513.2	1510.7	1508.2	1505.6	1500.7	1493.5	1486.2	1479.0	1471.7	1470.4
20°	1487.1	1484.3	1481.5	1478.8	1476.1	1470.3	1461.6	1452.8	1444.0	1435.2	1433.8
22.5°	1455.5	1452.7	1449.9	1447.2	1444.5	1438.5	1429.3	1420.1	1410.8	1401.6	1398.9
25°	1408.0	1403.9	1399.8	1395.7	1391.5	1384.4	1374.3	1364.1	1353.9	1343.8	1340.2
27.5°	1353.7	1348.7	1343.7	1338.7	1333.7	1325.8	1314.9	1304.0	1293.2	1282.3	1277.3
30°	1314.2	1308.9	1303.7	1298.5	1293.3	1284.9	1273.4	1261.9	1250.3	1238.8	1232.5
32.5°	1275.7	1269.6	1263.5	1257.4	1251.3	1242.3	1230.6	1218.9	1207.0	1195.3	1188.4
35°	1212.9	1206.3	1199.7	1193.1	1186.5	1177.0	1164.7	1152.4	1140.0	1127.7	1119.7
37.5°	1151.4	1143.4	1135.4	1127.4	1119.3	1108.9	1096.2	1083.5	1070.7	1058.0	1048.5
40°	1107.9	1099.6	1091.4	1083.2	1075.0	1064.2	1051.1	1037.9	1024.7	1011.5	1001.2
42.5°	1062.5	1054.0	1045.5	1037.0	1028.6	1017.6	1004.0	990.4	976.8	963.1	953.2
45°	993.0	985.1	977.1	969.2	961.2	949.7	934.5	919.5	904.4	889.3	878.3
47.5°	921.1	912.8	904.4	896.0	887.6	875.8	860.5	845.3	830.1	814.9	803.6
50°	875.7	866.6	857.5	848.5	839.5	827.1	811.4	795.8	780.1	764.5	753.0
52.5°	826.2	817.0	807.7	798.4	789.2	777.1	762.4	747.7	732.8	718.1	705.7
55°	753.4	744.7	735.9	727.1	718.3	706.2	690.9	675.5	660.1	644.8	632.4
57.5°	679.8	670.4	661.0	651.6	642.2	630.2	615.4	600.5	585.7	570.8	558.8
60°	632.4	622.7	613.1	603.6	594.0	581.7	566.9	552.1	537.3	522.4	510.4
62.5°	582.0	572.8	563.6	554.4	545.3	533.2	518.2	503.1	488.1	473.0	461.8
65°	510.1	500.7	491.5	482.1	472.8	460.8	446.3	431.7	417.2	402.7	391.7
67.5°	438.7	429.4	420.0	410.7	401.4	389.8	375.8	361.9	347.9	334.0	323.9
70°	390.3	381.0	371.6	362.3	353.0	341.4	327.7	314.0	300.2	286.5	278.1
72.5°	342.9	333.7	324.6	315.5	306.4	295.4	282.6	269.7	256.9	244.1	236.2
75°	271.7	263.5	255.2	247.0	238.8	228.9	217.4	205.9	194.3	182.8	176.7
77.5°	201.1	194.5	187.9	181.3	174.8	166.8	157.6	148.4	139.2	129.9	125.7
80°	160.6	154.0	147.4	140.8	134.2	127.1	119.4	111.7	104.0	96.3	93.9
82.5°	121.0	115.1	109.2	103.2	97.4	91.7	86.4	81.2	75.9	70.7	69.5
85°	68.0	63.0	58.1	53.1	48.2	45.0	43.6	42.3	40.9	39.5	39.2
87.5°	22.8	21.5	20.0	18.7	17.3	16.6	16.5	16.4	16.3	16.2	16.4
90°	0.5	1.3	2.1	2.9	3.6	4.4	5.1	5.9	6.5	7.2	7.8
92.5°	10.9	11.5	12.0	12.6	13.2	13.9	14.7	15.6	16.5	17.3	18.0
95°	29.4	29.5	29.8	29.9	30.2	30.8	31.8	32.8	33.8	34.8	35.5
97.5°	48.8	48.9	49.0	49.0	49.1	49.8	51.3	52.6	54.0	55.4	56.1
100°	63.3	63.3	63.3	63.3	63.3	63.9	65.2	66.5	67.8	69.2	70.0
102.5°	78.8	79.2	79.6	80.0	80.4	81.0	81.6	82.3	82.9	83.6	84.6
105°	103.1	103.5	104.0	104.6	105.0	105.6	106.2	106.8	107.4	108.0	108.6
107.5°	129.8	130.3	130.8	131.3	131.8	132.3	132.8	133.2	133.6	134.1	134.4
110°	148.2	148.7	149.2	149.7	150.3	150.7	150.9	151.2	151.5	151.9	152.2



TEST NUMBER: P333620-927

CATALOG NUMBER: S125RDIP-S1270D590U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	167.0	167.3	167.5	167.8	168.1	168.4	168.8	169.1	169.5	169.9	170.1
115°	194.8	195.2	195.6	196.0	196.4	196.7	196.9	197.1	197.3	197.5	197.4
117.5°	222.6	222.8	223.0	223.2	223.3	223.6	223.7	223.9	224.0	224.3	224.3
120°	240.0	240.5	241.0	241.5	242.0	242.2	242.4	242.5	242.6	242.6	242.6
122.5°	258.8	259.0	259.1	259.3	259.5	259.7	260.0	260.2	260.5	260.8	260.7
125°	284.2	284.9	285.4	286.1	286.7	287.0	287.1	287.2	287.3	287.4	287.2
127.5°	311.4	311.7	312.0	312.4	312.8	313.0	313.1	313.2	313.3	313.5	313.4
130°	327.6	328.1	328.7	329.2	329.6	330.0	330.2	330.4	330.6	330.8	330.7
132.5°	343.9	344.8	345.5	346.3	347.2	347.6	347.5	347.5	347.5	347.5	347.4
135°	369.6	370.3	370.9	371.5	372.1	372.4	372.6	372.6	372.7	372.8	372.8
137.5°	393.9	394.5	395.1	395.6	396.2	396.6	396.9	397.0	397.3	397.5	397.6
140°	409.4	410.0	410.4	410.9	411.5	411.9	412.2	412.5	412.7	413.0	413.3
142.5°	425.0	425.4	425.8	426.3	426.7	427.1	427.5	427.9	428.3	428.6	428.7
145°	447.8	448.2	448.7	449.1	449.5	449.8	450.1	450.4	450.8	451.0	451.0
147.5°	469.0	469.2	469.4	469.7	469.9	470.1	470.3	470.6	470.9	471.1	471.3
150°	483.1	483.0	482.9	482.8	482.7	482.8	483.2	483.6	484.0	484.4	484.4
152.5°	494.6	494.8	495.0	495.1	495.2	495.4	495.5	495.7	495.8	496.1	496.3
155°	512.5	512.5	512.5	512.5	512.5	512.5	512.6	512.7	512.9	512.9	513.3
157.5°	528.4	528.1	527.9	527.8	527.5	527.4	527.5	527.7	527.8	527.8	528.2
160°	537.8	537.5	537.2	536.9	536.5	536.5	536.5	536.7	536.8	536.9	537.3
162.5°	546.1	545.9	545.7	545.4	545.2	545.1	545.1	545.2	545.2	545.2	545.7
165°	557.2	557.0	556.8	556.6	556.4	556.3	556.4	556.6	556.7	556.7	557.1
167.5°	566.6	566.3	565.8	565.4	565.0	564.8	564.8	564.8	564.8	564.8	565.4
170°	571.6	571.2	570.8	570.5	570.1	569.9	569.9	569.9	569.9	569.9	570.5
172.5°	575.3	574.9	574.5	574.1	573.7	573.5	573.5	573.5	573.5	573.5	574.1
175°	579.3	578.9	578.5	578.1	577.7	577.6	577.6	577.6	577.6	577.6	578.1
177.5°	581.5	581.1	580.8	580.5	580.1	580.0	579.9	579.8	579.7	579.6	580.1
180°	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7



TEST NUMBER: P333620-927

CATALOG NUMBER: S125RDIP-S1270D590U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3
2.5°	1629.8	1632.0	1634.2	1635.1	1635.0	1634.7	1634.5	1634.3
5°	1619.8	1622.5	1625.2	1626.4	1625.8	1625.2	1624.7	1624.1
7.5°	1599.6	1601.6	1603.5	1604.1	1603.5	1602.9	1602.3	1601.7
10°	1582.5	1583.4	1584.2	1584.2	1583.4	1582.5	1581.8	1581.0
12.5°	1558.5	1559.0	1559.6	1559.3	1558.1	1556.8	1555.5	1554.3
15°	1518.6	1518.4	1518.1	1516.7	1514.3	1511.8	1509.3	1506.8
17.5°	1469.0	1467.6	1466.3	1464.6	1462.5	1460.5	1458.5	1456.4
20°	1432.4	1431.1	1429.7	1427.8	1425.3	1422.8	1420.4	1417.9
22.5°	1396.2	1393.5	1390.8	1388.5	1386.5	1384.4	1382.4	1380.4
25°	1336.6	1333.1	1329.5	1326.2	1323.2	1320.2	1317.2	1314.2
27.5°	1272.3	1267.3	1262.3	1258.4	1255.5	1252.5	1249.6	1246.7
30°	1226.2	1219.9	1213.5	1209.2	1206.7	1204.2	1201.7	1199.3
32.5°	1181.4	1174.4	1167.4	1162.4	1159.3	1156.1	1153.0	1149.9
35°	1111.7	1103.7	1095.8	1089.9	1086.1	1082.2	1078.4	1074.5
37.5°	1038.9	1029.4	1019.8	1013.1	1009.4	1005.7	1002.0	998.2
40°	990.7	980.2	969.9	963.0	959.6	956.4	953.1	949.8
42.5°	943.2	933.2	923.2	915.8	910.9	906.1	901.3	896.4
45°	867.3	856.3	845.3	837.8	833.7	829.6	825.5	821.3
47.5°	792.3	781.0	769.7	761.8	757.2	752.7	748.1	743.5
50°	741.5	729.9	718.4	710.6	706.5	702.3	698.2	694.1
52.5°	693.2	680.9	668.4	660.2	656.1	652.0	647.8	643.7
55°	620.0	607.7	595.3	586.9	582.6	578.1	573.8	569.4
57.5°	546.7	534.6	522.5	514.6	510.6	506.8	502.9	499.0
60°	498.3	486.2	474.1	466.0	461.9	457.8	453.7	449.6
62.5°	450.7	439.4	428.3	420.6	416.5	412.3	408.2	404.1
65°	380.7	369.7	358.7	351.2	347.1	342.9	338.8	334.7
67.5°	313.9	303.8	293.8	287.1	283.8	280.5	277.3	273.9
70°	269.5	261.0	252.5	246.6	243.3	240.0	236.7	233.5
72.5°	228.4	220.5	212.6	207.6	205.4	203.3	201.1	198.8
75°	170.7	164.7	158.7	154.6	152.7	150.8	148.9	146.9
77.5°	121.4	117.2	113.0	110.2	108.8	107.3	105.9	104.5
80°	91.4	89.0	86.4	84.9	84.4	83.8	83.3	82.8
82.5°	68.4	67.2	66.1	65.3	65.0	64.6	64.3	64.0
85°	39.0	38.7	38.4	38.2	37.9	37.6	37.3	37.1
87.5°	16.5	16.6	16.6	16.6	16.5	16.3	16.2	16.0
90°	8.2	8.7	9.3	9.7	10.0	10.2	10.5	10.9
92.5°	18.7	19.3	20.0	20.4	20.7	20.9	21.1	21.3
95°	36.2	36.9	37.6	38.0	38.3	38.5	38.7	38.9
97.5°	56.7	57.4	58.1	58.5	58.5	58.7	58.8	58.9
100°	71.0	71.9	72.7	73.3	73.5	73.8	73.9	74.1
102.5°	85.6	86.6	87.5	88.2	88.5	88.7	89.0	89.3
105°	109.2	109.8	110.4	110.9	111.1	111.5	111.8	112.1
107.5°	134.8	135.1	135.3	135.5	135.5	135.5	135.4	135.4
110°	152.4	152.7	153.0	153.1	153.0	153.0	152.8	152.7



TEST NUMBER: P333620-927

CATALOG NUMBER: S125RDIP-S1270D590U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	170.2	170.3	170.5	170.5	170.3	170.1	169.9	169.8
115°	197.3	197.2	197.1	197.0	196.9	196.8	196.7	196.6
117.5°	224.4	224.5	224.6	224.4	224.0	223.6	223.2	222.8
120°	242.6	242.6	242.6	242.5	242.1	241.7	241.3	240.9
122.5°	260.6	260.5	260.5	260.2	259.9	259.6	259.3	259.0
125°	287.0	286.8	286.6	286.5	286.4	286.3	286.1	286.1
127.5°	313.2	313.1	313.1	312.9	312.7	312.5	312.3	312.1
130°	330.6	330.5	330.4	330.3	330.0	329.9	329.6	329.5
132.5°	347.2	347.1	347.1	346.8	346.6	346.3	346.0	345.7
135°	372.8	372.8	372.8	372.6	372.2	371.9	371.5	371.1
137.5°	397.8	397.8	398.0	397.8	397.3	396.8	396.3	395.8
140°	413.4	413.7	413.8	413.7	413.2	412.7	412.2	411.7
142.5°	428.8	429.0	429.0	428.9	428.4	427.9	427.4	426.9
145°	451.0	451.0	451.0	450.8	450.6	450.3	450.0	449.6
147.5°	471.6	471.8	472.1	471.8	471.1	470.5	469.8	469.1
150°	484.4	484.4	484.4	484.3	484.2	483.9	483.8	483.5
152.5°	496.5	496.8	497.0	496.9	496.5	496.2	495.8	495.5
155°	513.7	514.1	514.5	514.5	514.0	513.5	512.9	512.5
157.5°	528.6	529.0	529.4	529.3	528.6	528.0	527.4	526.6
160°	537.7	538.1	538.4	538.4	538.0	537.4	536.9	536.5
162.5°	546.1	546.6	547.2	547.1	546.5	545.9	545.3	544.7
165°	557.5	557.9	558.4	558.3	557.7	557.1	556.4	555.9
167.5°	566.0	566.6	567.2	567.2	566.6	565.9	565.3	564.7
170°	571.1	571.6	572.3	572.2	571.6	570.8	570.1	569.4
172.5°	574.7	575.3	575.9	575.9	575.3	574.6	574.0	573.4
175°	578.8	579.3	580.0	579.9	579.2	578.5	577.8	577.1
177.5°	580.6	581.1	581.5	581.5	581.0	580.4	579.8	579.2
180°	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7

(END OF REPORT)