

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333626-840

Luminaire Tested: **S125RDIP-S1270D810U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333626-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1270D810U840-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7758.6 lumens  
Efficiency: N/A  
Efficacy: 127.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333626-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333626-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69
1	101	97	93	89	95	91	88	85	80	78	75	70	68	67	61	60	58
2	92	85	79	74	86	80	74	70	71	66	63	62	59	56	54	52	50
3	84	75	67	62	79	71	64	59	62	57	53	55	51	48	48	45	43
4	77	66	58	52	72	63	56	50	56	50	46	49	45	41	43	40	37
5	71	59	51	45	67	56	49	43	50	44	40	44	40	36	39	35	32
6	66	53	45	39	61	51	43	38	45	39	35	40	35	32	35	32	29
7	61	48	40	35	57	46	39	33	41	35	31	37	32	28	32	29	25
8	57	44	36	31	53	42	35	30	38	32	27	34	29	25	30	26	23
9	53	40	33	28	50	38	31	27	35	29	25	31	26	23	28	24	21
10	49	37	30	25	46	35	29	24	32	26	22	29	24	21	26	22	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13464	13464	13464
5°	13494	13341	13422
10°	13392	13217	13217
15°	13233	12948	12843
20°	13029	12575	12423
25°	12790	12207	11938
30°	12493	11777	11401
35°	12191	11334	10800
40°	11907	10871	10208
45°	11562	10355	9563
50°	11216	9792	8890
55°	10815	9254	8173
60°	10413	8603	7403
65°	9938	7844	6521
70°	9396	6898	5620
75°	8644	5814	4674
80°	7613	4567	3924
85°	6417	3735	3505



TEST NUMBER: P333626-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	196.0	2.5
10°-20°	547.8	7.1
20°-30°	794.4	10.2
30°-40°	905.3	11.7
40°-50°	882.5	11.4
50°-60°	742.8	9.6
60°-70°	520.7	6.7
70°-80°	267.7	3.4
80°-90°	69.8	0.9
90°-100°	68.0	0.9
100°-110°	200.7	2.6
110°-120°	339.9	4.4
120°-130°	447.4	5.8
130°-140°	501.3	6.5
140°-150°	491.3	6.3
150°-160°	412.7	5.3
160°-170°	274.3	3.5
170°-180°	96.0	1.2
0°-30°	1538.2	19.8
0°-40°	2443.5	31.5
0°-60°	4068.9	52.4
0°-90°	4927.1	63.5
90°-120°	608.6	7.8
90°-150°	2048.6	26.4
90°-180°	2832.0	36.5
0°-180°	7758.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2085	2085	2085	2085	2085	
5°	2082	2075	2058	2073	2070	197
15°	1979	1968	1937	1934	1921	558
25°	1795	1769	1713	1693	1675	826
35°	1546	1507	1438	1393	1370	968
45°	1266	1218	1134	1073	1047	976
55°	960	908	822	754	726	859
65°	650	595	513	452	427	644
75°	346	298	233	200	187	367
85°	87	59	50	49	47	97
90°	1	7	13	17	19	7
95°	51	53	61	66	68	55
105°	180	184	189	193	196	192
115°	340	343	345	344	344	336
125°	497	501	502	501	500	445
135°	646	650	652	651	648	498
145°	782	786	788	788	786	489
155°	895	895	896	899	895	412
165°	974	972	973	976	971	275
175°	1012	1009	1009	1013	1008	96
180°	1015	1015	1015	1015	1015	



TEST NUMBER: P333626-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7
2.5°	2088.4	2087.6	2086.7	2085.9	2085.1	2083.3	2080.4	2077.6	2074.9	2072.0	2074.9
5°	2081.5	2080.1	2078.7	2077.3	2075.9	2073.3	2069.4	2065.6	2061.7	2057.9	2061.3
7.5°	2061.0	2059.7	2058.4	2057.0	2055.7	2052.8	2048.1	2043.5	2038.9	2034.3	2036.7
10°	2042.1	2041.0	2040.0	2039.0	2037.9	2035.0	2030.0	2025.2	2020.2	2015.4	2016.4
12.5°	2020.7	2019.4	2018.0	2016.7	2015.4	2011.4	2004.9	1998.3	1991.7	1985.1	1985.9
15°	1979.1	1977.0	1975.0	1972.9	1970.8	1966.0	1958.6	1951.4	1944.0	1936.6	1936.3
17.5°	1932.2	1929.0	1925.8	1922.6	1919.3	1913.1	1903.9	1894.6	1885.4	1876.1	1874.4
20°	1895.7	1892.2	1888.6	1885.2	1881.7	1874.3	1863.2	1852.0	1840.8	1829.6	1827.9
22.5°	1855.4	1851.9	1848.4	1844.9	1841.4	1833.8	1822.0	1810.3	1798.5	1786.8	1783.3
25°	1794.9	1789.7	1784.4	1779.2	1773.9	1764.8	1751.9	1739.0	1726.0	1713.0	1708.5
27.5°	1725.7	1719.3	1712.9	1706.6	1700.2	1690.1	1676.2	1662.3	1648.5	1634.7	1628.3
30°	1675.3	1668.6	1661.9	1655.4	1648.7	1638.0	1623.3	1608.6	1593.9	1579.2	1571.1
32.5°	1626.2	1618.4	1610.6	1602.9	1595.1	1583.7	1568.7	1553.8	1538.7	1523.8	1514.9
35°	1546.2	1537.7	1529.3	1521.0	1512.6	1500.5	1484.7	1469.1	1453.3	1437.5	1427.3
37.5°	1467.7	1457.5	1447.3	1437.1	1426.8	1413.6	1397.5	1381.2	1364.9	1348.7	1336.6
40°	1412.3	1401.8	1391.3	1380.8	1370.4	1356.7	1339.9	1323.1	1306.3	1289.5	1276.3
42.5°	1354.4	1343.6	1332.8	1322.0	1311.3	1297.2	1279.9	1262.5	1245.2	1227.8	1215.1
45°	1265.9	1255.8	1245.6	1235.5	1225.3	1210.6	1191.3	1172.2	1152.9	1133.7	1119.6
47.5°	1174.3	1163.6	1152.9	1142.2	1131.5	1116.4	1097.0	1077.6	1058.2	1038.8	1024.4
50°	1116.3	1104.8	1093.2	1081.7	1070.2	1054.4	1034.4	1014.5	994.5	974.6	959.9
52.5°	1053.3	1041.5	1029.7	1017.8	1006.0	990.7	971.9	953.1	934.2	915.4	899.6
55°	960.5	949.3	938.1	926.9	915.6	900.3	880.7	861.1	841.5	821.9	806.2
57.5°	866.6	854.6	842.6	830.7	818.7	803.3	784.5	765.5	746.6	727.7	712.4
60°	806.2	793.9	781.6	769.4	757.2	741.5	722.7	703.8	684.9	666.0	650.7
62.5°	741.9	730.2	718.5	706.8	695.2	679.7	660.6	641.4	622.2	603.0	588.8
65°	650.3	638.3	626.5	614.6	602.7	587.4	569.0	550.4	531.8	513.3	499.3
67.5°	559.3	547.3	535.4	523.6	511.7	496.9	479.1	461.3	443.5	425.8	412.9
70°	497.6	485.6	473.7	461.8	450.0	435.3	417.8	400.3	382.7	365.3	354.5
72.5°	437.1	425.5	413.8	402.2	390.6	376.6	360.2	343.9	327.5	311.1	301.1
75°	346.4	335.9	325.4	314.9	304.4	291.9	277.1	262.5	247.7	233.0	225.3
77.5°	256.3	247.9	239.5	231.2	222.8	212.7	200.9	189.1	177.4	165.6	160.3
80°	204.7	196.3	187.9	179.5	171.1	162.0	152.2	142.4	132.6	122.8	119.7
82.5°	154.3	146.7	139.2	131.6	124.1	116.9	110.2	103.5	96.7	90.1	88.6
85°	86.6	80.3	74.0	67.7	61.4	57.4	55.6	53.9	52.1	50.4	50.0
87.5°	29.1	27.5	25.8	24.1	22.4	21.5	21.5	21.5	21.4	21.4	21.6
90°	0.8	2.2	3.6	5.0	6.4	7.7	9.0	10.2	11.4	12.6	13.5
92.5°	19.1	20.1	21.1	22.0	23.0	24.2	25.8	27.3	28.8	30.3	31.5
95°	51.3	51.7	52.0	52.4	52.7	53.8	55.5	57.3	59.1	60.8	62.0
97.5°	85.3	85.4	85.5	85.7	85.8	87.2	89.6	92.0	94.4	96.8	98.0
100°	110.6	110.6	110.6	110.6	110.6	111.7	114.0	116.2	118.6	120.8	122.4
102.5°	137.7	138.5	139.2	139.9	140.6	141.5	142.6	143.8	144.9	146.1	147.8
105°	180.1	181.0	181.8	182.7	183.6	184.5	185.6	186.6	187.6	188.7	189.8
107.5°	226.8	227.6	228.5	229.4	230.4	231.2	232.0	232.8	233.6	234.4	234.9
110°	259.0	259.9	260.7	261.7	262.6	263.3	263.8	264.3	264.8	265.3	265.9



TEST NUMBER: P333626-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	291.9	292.4	292.8	293.3	293.7	294.3	294.9	295.6	296.3	296.9	297.2
115°	340.3	341.0	341.7	342.4	343.2	343.7	344.1	344.4	344.8	345.1	344.9
117.5°	389.0	389.3	389.6	389.9	390.2	390.6	390.9	391.2	391.5	391.8	391.9
120°	419.3	420.2	421.1	421.9	422.8	423.3	423.5	423.7	423.8	424.0	424.0
122.5°	452.1	452.5	452.8	453.1	453.4	453.8	454.2	454.7	455.1	455.7	455.4
125°	496.7	497.8	498.8	499.9	500.9	501.5	501.7	501.9	502.0	502.2	501.9
127.5°	544.1	544.7	545.2	545.8	546.4	546.8	547.0	547.2	547.5	547.8	547.5
130°	572.5	573.4	574.3	575.1	576.0	576.6	576.9	577.3	577.6	578.0	577.8
132.5°	601.0	602.4	603.8	605.2	606.7	607.3	607.3	607.2	607.1	607.1	606.9
135°	645.9	647.0	648.0	649.1	650.2	650.8	651.0	651.2	651.3	651.5	651.5
137.5°	688.3	689.3	690.3	691.4	692.4	693.1	693.5	693.8	694.2	694.6	694.8
140°	715.5	716.3	717.2	718.1	718.9	719.6	720.1	720.7	721.2	721.8	722.2
142.5°	742.7	743.4	744.1	744.8	745.6	746.3	746.9	747.6	748.2	748.9	749.1
145°	782.5	783.3	784.0	784.7	785.4	786.0	786.5	787.0	787.6	788.1	788.1
147.5°	819.5	819.9	820.3	820.7	821.0	821.4	821.9	822.3	822.7	823.1	823.5
150°	844.1	843.9	843.8	843.6	843.4	843.7	844.4	845.2	845.9	846.6	846.6
152.5°	864.3	864.6	864.8	865.2	865.4	865.7	865.9	866.2	866.5	866.8	867.2
155°	895.4	895.4	895.4	895.4	895.4	895.5	895.8	896.0	896.1	896.3	897.0
157.5°	923.3	922.9	922.5	922.1	921.7	921.6	921.8	922.0	922.1	922.3	923.0
160°	939.7	939.2	938.7	938.2	937.6	937.5	937.6	937.8	938.0	938.2	938.9
162.5°	954.2	953.8	953.4	953.1	952.7	952.5	952.5	952.6	952.6	952.7	953.5
165°	973.7	973.3	973.0	972.6	972.3	972.2	972.3	972.5	972.7	972.9	973.6
167.5°	990.1	989.4	988.7	988.0	987.2	986.9	986.9	986.9	986.9	986.9	988.0
170°	999.0	998.3	997.5	996.8	996.1	995.7	995.7	995.7	995.7	995.7	996.8
172.5°	1005.2	1004.5	1003.8	1003.1	1002.4	1002.1	1002.1	1002.1	1002.1	1002.1	1003.1
175°	1012.4	1011.7	1011.0	1010.3	1009.6	1009.2	1009.2	1009.2	1009.2	1009.2	1010.3
177.5°	1016.0	1015.4	1014.9	1014.3	1013.7	1013.4	1013.3	1013.1	1013.0	1012.8	1013.7
180°	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7



TEST NUMBER: P333626-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7
2.5°	2077.6	2080.4	2083.3	2084.5	2084.3	2084.0	2083.7	2083.4
5°	2064.9	2068.4	2071.8	2073.3	2072.5	2071.8	2071.1	2070.4
7.5°	2039.1	2041.6	2044.1	2044.9	2044.1	2043.4	2042.6	2041.8
10°	2017.4	2018.5	2019.5	2019.5	2018.5	2017.4	2016.4	2015.4
12.5°	1986.7	1987.4	1988.2	1987.8	1986.2	1984.6	1983.0	1981.4
15°	1935.9	1935.6	1935.2	1933.5	1930.4	1927.2	1924.0	1920.9
17.5°	1872.7	1870.9	1869.2	1867.0	1864.4	1861.8	1859.3	1856.6
20°	1826.0	1824.3	1822.6	1820.1	1816.9	1813.8	1810.7	1807.6
22.5°	1779.9	1776.5	1773.0	1770.0	1767.5	1764.8	1762.2	1759.7
25°	1703.9	1699.4	1694.9	1690.6	1686.8	1682.9	1679.1	1675.3
27.5°	1621.9	1615.6	1609.2	1604.2	1600.4	1596.7	1593.0	1589.3
30°	1563.2	1555.1	1547.0	1541.5	1538.3	1535.1	1532.0	1528.8
32.5°	1506.0	1497.1	1488.2	1481.8	1477.8	1473.8	1469.9	1465.8
35°	1417.2	1407.0	1396.9	1389.4	1384.5	1379.6	1374.7	1369.8
37.5°	1324.3	1312.2	1300.0	1291.5	1286.8	1282.0	1277.3	1272.5
40°	1262.9	1249.6	1236.4	1227.6	1223.4	1219.2	1215.0	1210.8
42.5°	1202.3	1189.6	1176.9	1167.4	1161.2	1155.1	1148.9	1142.8
45°	1105.6	1091.7	1077.6	1068.0	1062.8	1057.5	1052.3	1047.0
47.5°	1010.1	995.6	981.2	971.1	965.2	959.5	953.6	947.9
50°	945.2	930.5	915.8	905.8	900.6	895.3	890.1	884.8
52.5°	883.7	868.0	852.1	841.6	836.4	831.1	825.9	820.6
55°	790.4	774.7	758.9	748.2	742.7	737.0	731.4	725.9
57.5°	696.9	681.6	666.1	656.0	651.0	646.0	641.1	636.1
60°	635.2	619.9	604.4	594.1	588.9	583.6	578.3	573.1
62.5°	574.5	560.2	545.9	536.1	530.9	525.6	520.4	515.1
65°	485.3	471.3	457.3	447.7	442.4	437.2	431.9	426.7
67.5°	400.1	387.3	374.6	366.0	361.8	357.6	353.5	349.2
70°	343.6	332.8	321.9	314.4	310.1	306.0	301.7	297.6
72.5°	291.1	281.1	271.0	264.7	261.9	259.1	256.3	253.5
75°	217.6	210.0	202.3	197.1	194.7	192.3	189.9	187.3
77.5°	154.8	149.5	144.1	140.5	138.7	136.8	135.0	133.2
80°	116.5	113.4	110.2	108.3	107.6	106.8	106.2	105.5
82.5°	87.2	85.6	84.2	83.2	82.8	82.4	82.0	81.6
85°	49.7	49.4	49.0	48.7	48.3	48.0	47.6	47.3
87.5°	21.8	21.9	22.1	22.1	21.9	21.8	21.6	21.4
90°	14.3	15.2	16.2	16.9	17.4	17.9	18.4	19.0
92.5°	32.6	33.8	34.9	35.7	36.2	36.5	36.9	37.3
95°	63.2	64.5	65.7	66.6	66.9	67.3	67.6	67.9
97.5°	99.2	100.3	101.5	102.1	102.3	102.5	102.8	103.0
100°	124.0	125.5	127.1	128.2	128.5	128.8	129.2	129.5
102.5°	149.6	151.3	153.0	154.1	154.6	155.0	155.5	156.0
105°	190.9	191.9	193.0	193.7	194.3	194.8	195.3	195.8
107.5°	235.4	235.9	236.5	236.7	236.7	236.6	236.6	236.6
110°	266.4	266.9	267.4	267.6	267.4	267.2	267.1	266.9





TEST NUMBER: P333626-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	297.4	297.6	297.9	297.9	297.5	297.2	296.9	296.6
115°	344.8	344.6	344.4	344.2	344.1	343.9	343.7	343.6
117.5°	392.1	392.2	392.4	392.1	391.4	390.7	390.0	389.3
120°	424.0	424.0	424.0	423.7	423.0	422.3	421.6	420.9
122.5°	455.3	455.2	455.0	454.7	454.1	453.6	453.0	452.5
125°	501.5	501.2	500.8	500.6	500.4	500.2	500.1	499.9
127.5°	547.3	547.1	547.0	546.7	546.4	546.0	545.7	545.3
130°	577.6	577.5	577.3	577.0	576.7	576.3	576.0	575.6
132.5°	606.7	606.5	606.4	606.0	605.6	605.1	604.6	604.1
135°	651.5	651.5	651.5	651.2	650.5	649.7	649.0	648.3
137.5°	695.0	695.2	695.4	695.1	694.2	693.4	692.5	691.6
140°	722.5	722.8	723.2	722.9	722.1	721.1	720.2	719.4
142.5°	749.3	749.5	749.7	749.4	748.5	747.7	746.8	745.9
145°	788.1	788.1	788.1	787.8	787.3	786.8	786.3	785.7
147.5°	823.9	824.5	824.9	824.5	823.2	822.0	820.9	819.7
150°	846.6	846.6	846.6	846.4	846.0	845.7	845.3	845.0
152.5°	867.6	868.0	868.4	868.3	867.7	867.1	866.5	865.8
155°	897.7	898.4	899.1	899.0	898.1	897.3	896.4	895.4
157.5°	923.7	924.4	925.1	924.9	923.7	922.6	921.4	920.3
160°	939.6	940.2	940.9	940.9	940.0	939.1	938.2	937.4
162.5°	954.3	955.2	956.0	955.9	954.9	953.9	952.9	951.9
165°	974.3	975.0	975.6	975.5	974.4	973.4	972.3	971.3
167.5°	989.1	990.1	991.2	991.1	990.1	989.0	987.8	986.7
170°	997.8	999.0	1000.0	999.9	998.7	997.4	996.2	995.0
172.5°	1004.2	1005.2	1006.3	1006.3	1005.2	1004.1	1003.0	1001.9
175°	1011.3	1012.4	1013.4	1013.3	1012.1	1010.9	1009.7	1008.5
177.5°	1014.5	1015.3	1016.2	1016.1	1015.1	1014.2	1013.2	1012.2
180°	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7

(END OF REPORT)