

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999556

Luminaire Tested: SA2XXRDIP-B290D530UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999556
REPORT IS A COMBINATION OF REPORTS P988109 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B290D530UB2750-4F0-XX-W2A-F_2700K
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3098.0 lumens
Efficiency: N/A
Efficacy: 109.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999556

CATALOG NUMBER: SA2XXRDIP-B290D530UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P999556

CATALOG NUMBER: SA2XXRDIP-B290D530UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	30	29
3	79	70	63	57	70	63	57	52	51	46	43	39	36	34	28	27	25
4	72	62	54	48	65	56	50	45	45	40	37	35	32	29	26	24	22
5	66	55	47	42	59	50	43	38	40	36	32	31	28	25	23	21	19
6	61	49	42	36	55	45	38	33	36	31	28	28	25	22	21	19	17
7	56	45	37	32	51	41	34	29	33	28	25	26	22	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14
9	49	37	30	25	44	34	27	23	28	23	19	22	18	16	16	14	12
10	45	34	27	22	41	31	25	21	25	21	18	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7666	7666	7666
5°	7679	7293	7239
10°	7603	6918	6689
15°	7498	6473	6062
20°	7360	5968	5406
25°	7218	5451	4805
30°	7029	4945	4151
35°	6843	4437	3587
40°	6653	3938	3008
45°	6432	3421	2502
50°	6206	2924	2037
55°	5969	2427	1617
60°	5693	1942	1223
65°	5375	1481	994
70°	4993	1073	791
75°	4509	820	605
80°	3816	553	406
85°	2656	253	195

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6432 cd/sqm

TEST NUMBER: P999556

CATALOG NUMBER: SA2XXRDIP-B290D530UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.4	1.5
10°-20°	124.6	4.0
20°-30°	174.9	5.6
30°-40°	190.7	6.2
40°-50°	175.3	5.7
50°-60°	137.6	4.4
60°-70°	89.6	2.9
70°-80°	46.1	1.5
80°-90°	13.0	0.4
90°-100°	23.6	0.8
100°-110°	88.1	2.8
110°-120°	233.6	7.5
120°-130°	387.5	12.5
130°-140°	411.6	13.3
140°-150°	382.5	12.3
150°-160°	307.5	9.9
160°-170°	198.2	6.4
170°-180°	68.2	2.2
0°-30°	344.9	11.1
0°-40°	535.6	17.3
0°-60°	848.5	27.4
0°-90°	997.2	32.2
90°-120°	345.3	11.1
90°-150°	1526.9	49.3
90°-180°	2101.0	67.8
0°-180°	3098.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	484	484	484	484	484	
5°	484	482	476	480	479	46
15°	461	456	441	433	428	130
25°	418	404	375	357	351	192
35°	360	338	299	272	262	225
45°	294	265	219	188	178	227
55°	224	190	142	116	108	200
65°	151	116	76	61	60	150
75°	81	50	35	32	32	85
85°	19	10	8	8	8	22
90°	0	6	10	13	14	3
95°	34	17	20	23	22	40
105°	158	173	32	37	39	168
115°	298	307	320	80	42	293
125°	422	428	438	442	443	376
135°	522	530	535	540	539	403
145°	605	605	613	617	614	378
155°	666	662	668	671	667	307
165°	702	699	700	704	700	198
175°	718	714	716	719	714	68
180°	717	717	717	717	717	

TEST NUMBER: P999556

CATALOG NUMBER: SA2XXRDIP-B290D530UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	484.3	484.3	484.3	484.3	484.3
2.5°	486.5	484.3	479.5	483.8	483.0
5°	484.3	482.1	476.4	480.3	479.0
7.5°	480.3	477.7	471.6	473.3	471.1
10°	475.1	472.0	463.3	461.9	459.3
12.5°	468.5	464.6	452.7	450.1	445.3
15°	460.6	455.8	440.9	432.6	428.2
17.5°	451.4	444.4	426.0	416.4	409.3
20°	440.9	432.1	410.2	399.3	389.6
22.5°	429.5	419.4	394.0	379.1	372.5
25°	418.1	404.1	375.2	357.2	350.6
27.5°	404.5	389.6	357.6	337.0	326.9
30°	390.1	373.4	338.3	316.0	304.2
32.5°	376.0	355.9	319.9	293.6	282.7
35°	360.3	337.9	299.3	271.7	262.1
37.5°	344.9	320.8	280.1	249.8	238.9
40°	328.7	302.4	259.9	228.8	217.4
42.5°	312.0	284.0	239.7	207.3	196.3
45°	294.5	265.2	219.1	188.0	177.5
47.5°	277.9	246.7	199.4	168.3	158.7
50°	259.5	228.3	180.1	149.9	140.7
52.5°	241.5	208.6	161.7	132.8	124.5
55°	224.0	189.8	142.4	116.1	107.8
57.5°	206.0	170.9	125.3	100.8	93.8
60°	187.6	152.5	107.4	85.0	78.0
62.5°	169.6	134.5	92.0	71.0	67.5
65°	151.2	115.7	76.3	61.4	60.0
67.5°	133.7	98.2	61.4	53.9	52.6
70°	115.3	81.1	50.8	46.5	44.7
72.5°	97.7	65.3	42.5	39.0	38.1
75°	80.6	50.0	35.1	32.0	31.6
77.5°	63.5	35.5	27.6	25.9	25.0
80°	47.8	25.4	21.0	19.3	19.3
82.5°	33.3	17.1	14.5	13.6	13.6
85°	18.8	9.6	8.3	8.3	8.3
87.5°	7.0	3.5	3.5	3.1	3.1
90°	0.5	6.2	10.4	13.0	14.0
92.5°	13.0	10.9	12.4	13.5	14.0
95°	33.7	16.6	20.2	22.8	22.3
97.5°	60.7	18.1	26.4	28.0	28.5
100°	91.8	20.7	29.6	33.7	34.7
102.5°	126.0	125.0	30.6	36.3	37.9
105°	157.6	173.2	31.6	37.3	39.4
107.5°	194.4	207.4	32.7	38.4	40.4
110°	229.7	240.6	90.7	38.9	41.0

TEST NUMBER: P999556

CATALOG NUMBER: SA2XXRDIP-B290D530UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	262.9	272.2	263.4	39.9	41.5
115°	298.1	307.0	319.9	79.8	42.5
117.5°	328.7	339.1	347.9	273.8	137.9
120°	363.0	370.7	380.1	386.3	316.3
122.5°	392.0	400.3	410.7	413.8	414.3
125°	421.5	428.3	438.1	441.8	443.3
127.5°	448.5	455.8	463.5	468.7	469.2
130°	473.9	482.2	487.9	493.6	493.1
132.5°	499.8	506.6	512.3	516.9	516.4
135°	521.6	529.9	534.6	539.8	538.7
137.5°	544.4	550.7	555.8	561.0	559.5
140°	566.7	570.9	576.6	581.2	578.7
142.5°	585.4	589.0	595.8	599.9	597.3
145°	605.1	604.6	613.4	617.0	614.4
147.5°	622.2	620.6	629.5	632.1	630.0
150°	638.8	635.2	643.5	646.6	644.0
152.5°	652.8	648.6	656.4	659.5	655.9
155°	666.3	661.6	667.8	670.9	666.8
157.5°	677.2	673.0	677.7	681.3	677.2
160°	686.5	683.4	686.5	689.6	686.0
162.5°	694.8	691.7	694.3	697.9	693.2
165°	702.1	698.9	700.5	704.1	700.5
167.5°	707.8	704.6	706.2	709.8	705.2
170°	712.4	709.3	710.4	714.0	709.3
172.5°	715.5	712.4	713.5	717.1	712.4
175°	718.1	714.5	715.5	719.2	714.0
177.5°	719.2	715.5	716.1	719.7	715.0
180°	716.6	716.6	716.6	716.6	716.6

(END OF REPORT)