

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999597

Luminaire Tested: SA2XXRDIP-B290D725UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999597
REPORT IS A COMBINATION OF REPORTS P988150 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B290D725UB2750-4F0-XX-W2A-F_3000K
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3837.0 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999597

CATALOG NUMBER: SA2XXRDIP-B290D725UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P999597

CATALOG NUMBER: SA2XXRDIP-B290D725UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34
1	93	89	85	82	83	79	76	73	62	60	58	46	44	43	31	30	29
2	85	78	72	67	75	70	65	61	54	51	48	40	38	36	27	26	25
3	77	68	62	56	69	61	56	51	48	44	41	36	33	31	24	23	22
4	71	61	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19
5	65	54	46	41	58	49	42	37	38	34	30	29	26	23	20	18	17
6	60	48	41	35	53	44	37	32	34	30	26	26	23	20	18	16	15
7	55	44	36	31	49	39	33	28	31	26	23	24	20	18	17	15	13
8	51	39	32	27	46	36	29	25	28	24	20	22	18	16	15	13	12
9	48	36	29	24	42	33	26	22	26	21	18	20	17	14	14	12	11
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7736	7736	7736
5°	7748	7359	7305
10°	7672	6979	6750
15°	7566	6532	6117
20°	7427	6022	5454
25°	7284	5499	4849
30°	7092	4991	4187
35°	6903	4477	3620
40°	6713	3973	3034
45°	6491	3452	2524
50°	6261	2952	2056
55°	6022	2449	1632
60°	5744	1958	1234
65°	5425	1492	1004
70°	5037	1083	798
75°	4554	827	609
80°	3848	559	410
85°	2684	256	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6491 cd/sqm

TEST NUMBER: P999597

CATALOG NUMBER: SA2XXRDIP-B290D725UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.8	1.2
10°-20°	125.7	3.3
20°-30°	176.5	4.6
30°-40°	192.4	5.0
40°-50°	176.8	4.6
50°-60°	138.9	3.6
60°-70°	90.4	2.4
70°-80°	46.5	1.2
80°-90°	13.6	0.4
90°-100°	31.8	0.8
100°-110°	118.7	3.1
110°-120°	314.7	8.2
120°-130°	522.0	13.6
130°-140°	554.5	14.5
140°-150°	515.4	13.4
150°-160°	414.3	10.8
160°-170°	267.0	7.0
170°-180°	91.9	2.4
0°-30°	348.0	9.1
0°-40°	540.4	14.1
0°-60°	856.2	22.3
0°-90°	1006.7	26.2
90°-120°	465.3	12.1
90°-150°	2057.1	53.6
90°-180°	2830.0	73.8
0°-180°	3837.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	489	489	489	489	489	
5°	489	486	481	485	483	46
15°	465	460	445	436	432	131
25°	422	408	378	360	354	194
35°	364	341	302	274	264	228
45°	297	268	221	190	179	230
55°	226	192	144	117	109	202
65°	153	117	77	62	61	151
75°	81	50	35	32	32	86
85°	19	10	8	8	8	22
90°	1	8	14	18	19	4
95°	45	22	27	31	30	54
105°	212	233	43	50	53	227
115°	402	414	431	108	57	395
125°	568	577	590	595	597	507
135°	703	714	720	727	726	543
145°	815	814	826	831	828	510
155°	898	891	900	904	898	414
165°	946	942	944	949	944	267
175°	968	963	964	969	962	92
180°	965	965	965	965	965	

TEST NUMBER: P999597

CATALOG NUMBER: SA2XXRDIP-B290D725UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	488.7	488.7	488.7	488.7	488.7
2.5°	490.9	488.7	483.8	488.2	487.3
5°	488.7	486.5	480.7	484.7	483.4
7.5°	484.7	482.0	475.8	477.6	475.4
10°	479.4	476.3	467.4	466.1	463.5
12.5°	472.7	468.8	456.8	454.2	449.3
15°	464.8	459.9	444.9	436.5	432.1
17.5°	455.5	448.4	429.8	420.1	413.0
20°	444.9	436.0	413.9	402.9	393.1
22.5°	433.4	423.2	397.6	382.5	375.9
25°	421.9	407.7	378.5	360.4	353.8
27.5°	408.2	393.1	360.9	340.1	329.9
30°	393.6	376.8	341.4	318.8	306.9
32.5°	379.4	359.1	322.8	296.3	285.2
35°	363.5	341.0	302.0	274.2	264.5
37.5°	348.0	323.7	282.6	252.1	241.0
40°	331.7	305.1	262.2	230.8	219.3
42.5°	314.9	286.6	241.9	209.2	198.1
45°	297.2	267.5	221.1	189.7	179.1
47.5°	280.4	249.0	201.2	169.8	160.1
50°	261.8	230.4	181.8	151.2	142.0
52.5°	243.7	210.5	163.2	134.0	125.6
55°	226.0	191.5	143.7	117.2	108.8
57.5°	207.8	172.5	126.5	101.7	94.6
60°	189.3	153.9	108.3	85.8	78.7
62.5°	171.1	135.8	92.9	71.6	68.1
65°	152.6	116.7	76.9	61.9	60.6
67.5°	134.9	99.1	61.9	54.4	53.1
70°	116.3	81.8	51.3	46.9	45.1
72.5°	98.6	65.9	42.9	39.4	38.5
75°	81.4	50.4	35.4	32.3	31.8
77.5°	64.1	35.8	27.9	26.1	25.2
80°	48.2	25.6	21.2	19.5	19.5
82.5°	33.6	17.2	14.6	13.7	13.7
85°	19.0	9.7	8.4	8.4	8.4
87.5°	7.1	3.5	3.5	3.1	3.1
90°	0.7	8.4	14.0	17.5	18.9
92.5°	17.5	14.7	16.8	18.2	18.9
95°	45.4	22.4	27.2	30.7	30.0
97.5°	81.7	24.5	35.6	37.7	38.4
100°	123.6	27.9	39.8	45.4	46.8
102.5°	169.8	168.4	41.2	48.9	51.0
105°	212.4	233.3	42.6	50.3	53.1
107.5°	262.0	279.4	44.0	51.7	54.5
110°	309.5	324.1	122.3	52.4	55.2

TEST NUMBER: P999597

CATALOG NUMBER: SA2XXRDIP-B290D725UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	354.2	366.8	354.9	53.8	55.9
115°	401.7	413.6	431.0	107.6	57.3
117.5°	442.9	456.9	468.7	368.8	185.8
120°	489.0	499.5	512.1	520.4	426.1
122.5°	528.1	539.3	553.3	557.5	558.2
125°	567.9	577.0	590.3	595.2	597.3
127.5°	604.3	614.0	624.5	631.5	632.2
130°	638.5	649.7	657.4	665.0	664.3
132.5°	673.4	682.5	690.2	696.5	695.8
135°	702.8	713.9	720.2	727.2	725.8
137.5°	733.5	741.9	748.9	755.9	753.8
140°	763.5	769.1	776.8	783.1	779.6
142.5°	788.7	793.6	802.7	808.3	804.8
145°	815.2	814.5	826.4	831.3	827.8
147.5°	838.3	836.2	848.1	851.6	848.8
150°	860.6	855.8	866.9	871.1	867.6
152.5°	879.5	873.9	884.4	888.6	883.7
155°	897.7	891.4	899.8	904.0	898.4
157.5°	912.3	906.7	913.0	917.9	912.3
160°	924.9	920.7	924.9	929.1	924.2
162.5°	936.1	931.9	935.4	940.3	934.0
165°	945.9	941.7	943.8	948.7	943.8
167.5°	953.6	949.4	951.5	956.3	950.1
170°	959.8	955.6	957.0	961.9	955.6
172.5°	964.0	959.8	961.2	966.1	959.8
175°	967.5	962.6	964.0	968.9	961.9
177.5°	968.9	964.0	964.7	969.6	963.3
180°	965.4	965.4	965.4	965.4	965.4

(END OF REPORT)