

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999598

Luminaire Tested: SA2XXRDIP-B290D725UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999598
REPORT IS A COMBINATION OF REPORTS P988151 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B290D725UB2750-4F0-XX-W2A-F_3500K
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3853.0 lumens
Efficiency: N/A
Efficacy: 113.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999598

CATALOG NUMBER: SA2XXRDIP-B290D725UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P999598

CATALOG NUMBER: SA2XXRDIP-B290D725UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34
1	93	89	85	82	83	79	76	73	62	60	58	46	44	43	31	30	29
2	85	78	72	67	75	70	65	61	54	51	48	40	38	36	27	26	25
3	77	68	62	56	69	61	56	51	48	44	41	36	33	31	24	23	22
4	71	61	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19
5	65	54	46	41	58	49	42	37	38	34	30	29	26	23	20	18	17
6	60	48	41	35	53	44	37	32	34	30	26	26	23	20	18	16	15
7	55	44	36	31	49	39	33	28	31	26	23	24	20	18	17	15	13
8	51	39	32	27	46	36	29	25	28	24	20	22	18	16	15	13	12
9	48	36	29	24	42	33	26	22	26	21	18	20	17	14	14	12	11
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7766	7766	7766
5°	7778	7388	7334
10°	7702	7007	6776
15°	7596	6558	6141
20°	7457	6047	5476
25°	7313	5522	4868
30°	7121	5011	4204
35°	6932	4494	3634
40°	6740	3989	3046
45°	6517	3467	2534
50°	6284	2963	2063
55°	6046	2459	1638
60°	5765	1967	1239
65°	5446	1500	1007
70°	5058	1088	801
75°	4570	829	612
80°	3864	561	410
85°	2698	256	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6517 cd/sqm

TEST NUMBER: P999598

CATALOG NUMBER: SA2XXRDIP-B290D725UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.0	1.2
10°-20°	126.2	3.3
20°-30°	177.2	4.6
30°-40°	193.2	5.0
40°-50°	177.6	4.6
50°-60°	139.4	3.6
60°-70°	90.8	2.4
70°-80°	46.7	1.2
80°-90°	13.6	0.4
90°-100°	32.0	0.8
100°-110°	119.2	3.1
110°-120°	316.1	8.2
120°-130°	524.2	13.6
130°-140°	556.8	14.5
140°-150°	517.5	13.4
150°-160°	416.1	10.8
160°-170°	268.1	7.0
170°-180°	92.3	2.4
0°-30°	349.4	9.1
0°-40°	542.6	14.1
0°-60°	859.6	22.3
0°-90°	1010.7	26.2
90°-120°	467.2	12.1
90°-150°	2065.8	53.6
90°-180°	2842.0	73.8
0°-180°	3853.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	491	491	491	491	491	
5°	491	488	483	487	485	47
15°	467	462	447	438	434	131
25°	424	409	380	362	355	195
35°	365	342	303	275	266	228
45°	298	269	222	190	180	230
55°	227	192	144	118	109	203
65°	153	117	77	62	61	152
75°	82	51	36	32	32	86
85°	19	10	8	8	8	22
90°	1	8	14	18	19	4
95°	46	22	27	31	30	54
105°	213	234	43	50	53	228
115°	403	415	433	108	58	397
125°	570	580	593	598	600	509
135°	706	717	723	730	729	545
145°	819	818	830	835	831	512
155°	902	895	904	908	902	415
165°	950	946	948	953	948	268
175°	972	967	968	973	966	92
180°	970	970	970	970	970	

TEST NUMBER: P999598

CATALOG NUMBER: SA2XXRDIP-B290D725UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	490.6	490.6	490.6	490.6	490.6
2.5°	492.8	490.6	485.7	490.2	489.3
5°	490.6	488.4	482.6	486.6	485.3
7.5°	486.6	483.9	477.7	479.5	477.3
10°	481.3	478.2	469.3	468.0	465.3
12.5°	474.6	470.6	458.6	456.0	451.1
15°	466.6	461.7	446.7	438.2	433.8
17.5°	457.3	450.2	431.6	421.8	414.7
20°	446.7	437.8	415.6	404.5	394.7
22.5°	435.1	424.9	399.1	384.1	377.4
25°	423.6	409.4	380.1	361.9	355.2
27.5°	409.8	394.7	362.3	341.4	331.2
30°	395.2	378.3	342.8	320.1	308.1
32.5°	380.9	360.5	324.1	297.5	286.4
35°	365.0	342.3	303.2	275.3	265.5
37.5°	349.4	325.0	283.7	253.1	242.0
40°	333.0	306.4	263.3	231.8	220.2
42.5°	316.1	287.7	242.9	210.0	198.9
45°	298.4	268.6	222.0	190.5	179.8
47.5°	281.5	250.0	202.0	170.5	160.7
50°	262.8	231.3	182.5	151.8	142.5
52.5°	244.6	211.3	163.8	134.5	126.1
55°	226.9	192.2	144.3	117.7	109.2
57.5°	208.7	173.2	127.0	102.1	95.0
60°	190.0	154.5	108.8	86.1	79.0
62.5°	171.8	136.3	93.2	71.9	68.4
65°	153.2	117.2	77.3	62.2	60.8
67.5°	135.4	99.5	62.2	54.6	53.3
70°	116.8	82.1	51.5	47.1	45.3
72.5°	99.0	66.2	43.1	39.5	38.6
75°	81.7	50.6	35.5	32.4	32.0
77.5°	64.4	36.0	28.0	26.2	25.3
80°	48.4	25.8	21.3	19.5	19.5
82.5°	33.7	17.3	14.7	13.8	13.8
85°	19.1	9.8	8.4	8.4	8.4
87.5°	7.1	3.6	3.6	3.1	3.1
90°	0.7	8.4	14.0	17.5	18.9
92.5°	17.5	14.7	16.8	18.2	18.9
95°	45.6	22.4	27.4	30.9	30.2
97.5°	82.1	24.6	35.8	37.9	38.6
100°	124.2	28.1	40.0	45.6	47.0
102.5°	170.5	169.1	41.4	49.1	51.2
105°	213.3	234.3	42.8	50.5	53.3
107.5°	263.1	280.6	44.2	51.9	54.7
110°	310.8	325.5	122.8	52.6	55.4

TEST NUMBER: P999598

CATALOG NUMBER: SA2XXRDIP-B290D725UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	355.7	368.3	356.4	54.0	56.1
115°	403.4	415.3	432.8	108.0	57.5
117.5°	444.8	458.8	470.7	370.4	186.6
120°	491.1	501.6	514.2	522.6	427.9
122.5°	530.4	541.6	555.6	559.8	560.5
125°	570.3	579.5	592.8	597.7	599.8
127.5°	606.8	616.6	627.2	634.2	634.9
130°	641.2	652.4	660.1	667.9	667.2
132.5°	676.3	685.4	693.1	699.4	698.7
135°	705.7	717.0	723.3	730.3	728.9
137.5°	736.6	745.0	752.0	759.1	757.0
140°	766.8	772.4	780.1	786.4	782.9
142.5°	792.0	796.9	806.1	811.7	808.2
145°	818.7	818.0	829.9	834.8	831.3
147.5°	841.8	839.7	851.7	855.2	852.4
150°	864.3	859.4	870.6	874.8	871.3
152.5°	883.2	877.6	888.1	892.4	887.4
155°	901.5	895.2	903.6	907.8	902.2
157.5°	916.2	910.6	916.9	921.8	916.2
160°	928.8	924.6	928.8	933.0	928.1
162.5°	940.1	935.8	939.4	944.3	938.0
165°	949.9	945.7	947.8	952.7	947.8
167.5°	957.6	953.4	955.5	960.4	954.1
170°	963.9	959.7	961.1	966.0	959.7
172.5°	968.1	963.9	965.3	970.2	963.9
175°	971.6	966.7	968.1	973.0	966.0
177.5°	973.0	968.1	968.8	973.7	967.4
180°	969.5	969.5	969.5	969.5	969.5

(END OF REPORT)