

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997803

Luminaire Tested: SA2XXDIP-B1005D1080UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P997803
REPORT IS A COMBINATION OF REPORTS P983537 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B1005D1080UB2750-4F0-XX-W2A-F_2700K
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8299.0 lumens
Efficiency: N/A
Efficacy: 86.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997803

CATALOG NUMBER: SA2XXDIP-B1005D1080UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P997803

CATALOG NUMBER: SA2XXDIP-B1005D1080UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49		
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41		
2	89	81	75	70	81	75	70	65	63	60	56	53	50	47	43	41	39	34		
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	35	33	29		
4	74	63	55	49	68	59	52	46	50	44	40	41	38	34	34	31	29	25		
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22		
6	63	51	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22	19		
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17		
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	17	15		
9	50	38	30	25	46	35	29	24	30	25	21	26	22	18	21	18	16	14		
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25067	25067	25067
5°	25108	23894	23724
10°	24904	22805	22353
15°	24540	21709	20909
20°	24047	20514	19542
25°	23556	19269	18178
30°	22937	18098	16746
35°	22355	16861	15339
40°	21634	15642	14009
45°	20918	14433	12705
50°	20138	13201	11353
55°	19313	11886	10071
60°	18389	10461	8739
65°	17377	9013	7339
70°	16089	7428	5926
75°	14310	5728	4576
80°	12159	3892	2945
85°	8814	1811	1253

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20918 cd/sqm

TEST NUMBER: P997803

CATALOG NUMBER: SA2XXDIP-B1005D1080UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.0	1.8
10°-20°	419.4	5.1
20°-30°	616.3	7.4
30°-40°	715.8	8.6
40°-50°	714.9	8.6
50°-60°	623.3	7.5
60°-70°	460.8	5.6
70°-80°	260.7	3.1
80°-90°	71.3	0.9
90°-100°	48.0	0.6
100°-110°	178.9	2.2
110°-120°	474.6	5.7
120°-130°	787.1	9.5
130°-140°	836.1	10.1
140°-150°	777.0	9.4
150°-160°	624.7	7.5
160°-170°	402.5	4.9
170°-180°	138.5	1.7
0°-30°	1184.7	14.3
0°-40°	1900.5	22.9
0°-60°	3238.7	39.0
0°-90°	4031.5	48.6
90°-120°	701.5	8.5
90°-150°	3101.6	37.4
90°-180°	4267.0	51.4
0°-180°	8299.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1584	1584	1584	1584	1584	
5°	1584	1578	1561	1573	1570	150
15°	1508	1498	1479	1485	1477	425
25°	1364	1352	1326	1329	1326	628
35°	1177	1162	1138	1128	1121	735
45°	958	947	924	908	901	739
55°	725	716	697	679	672	648
65°	489	480	464	451	443	483
75°	256	253	245	236	239	273
85°	62	61	59	55	53	70
90°	1	13	21	26	28	8
95°	68	34	41	46	45	81
105°	320	352	64	76	80	342
115°	606	624	650	162	86	596
125°	856	870	890	897	901	764
135°	1060	1076	1086	1096	1094	819
145°	1229	1228	1246	1253	1248	769
155°	1354	1344	1357	1363	1354	624
165°	1426	1420	1423	1430	1423	403
175°	1459	1451	1454	1461	1450	139
180°	1456	1456	1456	1456	1456	

TEST NUMBER: P997803

CATALOG NUMBER: SA2XXDIP-B1005D1080UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1583.6	1583.6	1583.6	1583.6	1583.6
2.5°	1592.8	1585.1	1568.4	1583.6	1580.6
5°	1583.6	1577.5	1560.8	1573.0	1569.9
7.5°	1573.0	1563.8	1547.1	1559.3	1556.2
10°	1556.2	1545.6	1527.3	1539.5	1534.9
12.5°	1533.4	1524.2	1506.0	1513.6	1510.5
15°	1507.5	1498.4	1478.6	1484.7	1477.0
17.5°	1475.5	1466.4	1446.6	1454.2	1446.6
20°	1440.5	1431.4	1410.0	1414.6	1408.5
22.5°	1405.5	1391.8	1372.0	1372.0	1368.9
25°	1364.4	1352.2	1326.3	1329.3	1326.3
27.5°	1318.7	1308.0	1288.2	1283.7	1276.0
30°	1273.0	1260.8	1238.0	1233.4	1227.3
32.5°	1224.3	1215.1	1190.8	1181.6	1175.5
35°	1177.1	1161.8	1137.5	1128.3	1120.7
37.5°	1123.8	1110.1	1085.7	1075.0	1067.4
40°	1068.9	1056.8	1032.4	1018.7	1012.6
42.5°	1015.7	1003.5	979.1	963.9	954.7
45°	957.8	947.1	924.3	907.5	901.4
47.5°	901.4	890.8	866.4	849.7	840.5
50°	842.1	834.4	813.1	791.8	784.2
52.5°	784.2	773.5	753.7	737.0	726.3
55°	724.8	715.7	697.4	679.1	671.5
57.5°	665.4	657.8	638.0	619.7	613.7
60°	606.0	600.0	578.6	561.9	557.3
62.5°	548.2	537.5	522.3	507.1	501.0
65°	488.8	479.7	464.4	450.7	443.1
67.5°	427.9	420.3	406.6	395.9	389.8
70°	371.5	365.5	351.7	341.1	335.0
72.5°	313.7	307.6	300.0	289.3	284.7
75°	255.8	252.8	245.2	236.0	239.1
77.5°	204.0	198.0	194.9	190.3	185.8
80°	152.3	150.7	147.7	143.1	140.1
82.5°	103.5	103.5	102.0	95.9	95.9
85°	62.4	60.9	59.4	54.8	53.3
87.5°	27.4	24.4	21.3	16.7	15.2
90°	1.1	12.6	21.1	26.3	28.4
92.5°	26.3	22.1	25.3	27.4	28.4
95°	68.5	33.7	41.1	46.3	45.3
97.5°	123.2	36.9	53.7	56.9	57.9
100°	186.4	42.1	60.0	68.5	70.6
102.5°	255.9	253.8	62.1	73.7	76.9
105°	320.2	351.8	64.3	75.8	80.0
107.5°	395.0	421.3	66.4	77.9	82.2
110°	466.6	488.7	184.3	79.0	83.2



TEST NUMBER: P997803

CATALOG NUMBER: SA2XXDIP-B1005D1080UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	534.0	553.0	535.1	81.1	84.3
115°	605.6	623.5	649.9	162.2	86.4
117.5°	667.8	688.9	706.8	556.1	280.2
120°	737.3	753.1	772.1	784.7	642.5
122.5°	796.3	813.1	834.2	840.5	841.6
125°	856.3	870.0	890.0	897.4	900.6
127.5°	911.1	925.8	941.6	952.2	953.2
130°	962.7	979.6	991.1	1002.7	1001.7
132.5°	1015.4	1029.1	1040.6	1050.1	1049.1
135°	1059.6	1076.5	1085.9	1096.5	1094.4
137.5°	1106.0	1118.6	1129.1	1139.7	1136.5
140°	1151.2	1159.7	1171.3	1180.7	1175.5
142.5°	1189.2	1196.5	1210.2	1218.7	1213.4
145°	1229.2	1228.1	1246.0	1253.4	1248.1
147.5°	1263.9	1260.8	1278.7	1284.0	1279.7
150°	1297.7	1290.3	1307.1	1313.5	1308.2
152.5°	1326.1	1317.7	1333.5	1339.8	1332.4
155°	1353.5	1344.0	1356.6	1363.0	1354.5
157.5°	1375.6	1367.2	1376.6	1384.0	1375.6
160°	1394.6	1388.2	1394.6	1400.9	1393.5
162.5°	1411.4	1405.1	1410.4	1417.7	1408.2
165°	1426.2	1419.8	1423.0	1430.4	1423.0
167.5°	1437.7	1431.4	1434.6	1442.0	1432.5
170°	1447.2	1440.9	1443.0	1450.4	1440.9
172.5°	1453.5	1447.2	1449.3	1456.7	1447.2
175°	1458.8	1451.4	1453.5	1460.9	1450.4
177.5°	1460.9	1453.5	1454.6	1462.0	1452.5
180°	1455.6	1455.6	1455.6	1455.6	1455.6

TEST NUMBER: P997803

CATALOG NUMBER: SA2XXDIP-B1005D1080UB2750-4F0-XX-W2A-F_2700K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.30	17.14	17.27	18.13	19.42	17.08	17.93	18.05	18.91	20.20
	3H	17.63	18.39	18.61	19.39	20.70	18.70	19.46	19.68	20.46	21.77
	4H	18.04	18.76	19.03	19.75	21.08	19.29	20.01	20.29	21.01	22.33
	6H	18.26	18.92	19.26	19.92	21.25	19.70	20.36	20.70	21.36	22.70
	8H	18.29	18.92	19.30	19.94	21.27	19.81	20.44	20.82	21.45	22.79
	12H	18.28	18.88	19.29	19.89	21.24	19.85	20.45	20.87	21.46	22.82
4H	2H	16.76	17.48	17.76	18.48	19.80	17.41	18.13	18.41	19.12	20.45
	3H	18.28	18.88	19.29	19.91	21.24	19.19	19.79	20.19	20.81	22.15
	4H	18.79	19.34	19.80	20.35	21.71	19.87	20.42	20.88	21.43	22.79
	6H	19.09	19.56	20.11	20.60	21.96	20.36	20.84	21.39	21.88	23.23
	8H	19.14	19.59	20.17	20.62	21.99	20.50	20.95	21.53	21.98	23.35
	12H	19.14	19.54	20.19	20.59	21.97	20.57	20.97	21.61	22.01	23.39
8H	4H	18.96	19.40	19.99	20.44	21.81	19.95	20.39	20.98	21.43	22.80
	6H	19.34	19.71	20.40	20.78	22.15	20.52	20.89	21.57	21.96	23.33
	8H	19.44	19.77	20.51	20.83	22.21	20.71	21.03	21.77	22.09	23.48
	12H	19.48	19.76	20.54	20.81	22.24	20.81	21.09	21.87	22.14	23.57
12H	4H	18.94	19.34	19.99	20.39	21.77	19.91	20.31	20.96	21.36	22.74
	6H	19.36	19.68	20.42	20.74	22.13	20.51	20.83	21.57	21.89	23.28
	8H	19.47	19.76	20.54	20.81	22.24	20.71	20.99	21.77	22.05	23.47