

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999640

Luminaire Tested: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999640
REPORT IS A COMBINATION OF REPORTS P988193 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-F_5000K
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4490.0 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999640

CATALOG NUMBER: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P999640

CATALOG NUMBER: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	89	89	89	89	68	68	68	48	48	48	30	30	30	30	30	22
1	92	88	84	81	81	78	75	72	59	57	56	42	41	40	27	26	26	26	26	19
2	84	77	71	66	74	68	63	59	52	49	46	37	35	34	24	23	22	22	22	16
3	76	67	61	55	67	60	54	50	46	42	39	33	31	29	21	20	19	19	19	14
4	70	60	52	47	62	53	47	42	41	37	33	30	27	25	19	18	16	16	16	12
5	64	53	45	40	56	47	41	36	37	32	29	27	24	21	17	16	14	14	14	11
6	59	48	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	13	13	9
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	14	13	11	11	11	8
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	13	11	10	10	10	8
9	47	35	28	23	41	32	25	21	25	20	17	18	15	13	12	10	9	9	9	7
10	44	32	25	21	39	29	23	19	23	18	15	17	14	12	11	10	8	8	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7435	7435	7435
5°	7447	7073	7021
10°	7374	6709	6488
15°	7272	6278	5879
20°	7138	5789	5243
25°	7001	5287	4661
30°	6816	4798	4025
35°	6636	4303	3479
40°	6452	3820	2916
45°	6238	3318	2427
50°	6017	2836	1975
55°	5788	2354	1569
60°	5520	1882	1187
65°	5212	1436	964
70°	4842	1041	768
75°	4375	794	586
80°	3696	538	393
85°	2585	247	190

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6238 cd/sqm

TEST NUMBER: P999640

CATALOG NUMBER: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.0	1.0
10°-20°	120.8	2.7
20°-30°	169.7	3.8
30°-40°	184.9	4.1
40°-50°	170.0	3.8
50°-60°	133.5	3.0
60°-70°	86.9	1.9
70°-80°	44.7	1.0
80°-90°	13.6	0.3
90°-100°	39.6	0.9
100°-110°	147.7	3.3
110°-120°	391.6	8.7
120°-130°	649.6	14.5
130°-140°	690.0	15.4
140°-150°	641.3	14.3
150°-160°	515.6	11.5
160°-170°	332.2	7.4
170°-180°	114.3	2.5
0°-30°	334.5	7.5
0°-40°	519.5	11.6
0°-60°	823.0	18.3
0°-90°	968.1	21.6
90°-120°	578.9	12.9
90°-150°	2559.8	57.0
90°-180°	3522.0	78.4
0°-180°	4490.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	470	470	470	470	470	
5°	470	468	462	466	465	45
15°	447	442	428	420	415	126
25°	406	392	364	346	340	186
35°	349	328	290	264	254	219
45°	286	257	212	182	172	221
55°	217	184	138	113	105	194
65°	147	112	74	60	58	145
75°	78	48	34	31	31	83
85°	18	9	8	8	8	21
90°	1	10	17	22	24	4
95°	56	28	34	38	37	67
105°	264	290	53	63	66	282
115°	500	515	536	134	71	492
125°	707	718	734	741	743	630
135°	874	888	896	905	903	676
145°	1014	1014	1028	1034	1030	634
155°	1117	1109	1120	1125	1118	515
165°	1177	1172	1174	1180	1174	333
175°	1204	1198	1200	1206	1197	115
180°	1201	1201	1201	1201	1201	

TEST NUMBER: P999640

CATALOG NUMBER: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	469.7	469.7	469.7	469.7	469.7
2.5°	471.8	469.7	465.0	469.3	468.4
5°	469.7	467.6	462.0	465.9	464.6
7.5°	465.9	463.3	457.4	459.1	456.9
10°	460.8	457.8	449.3	448.0	445.5
12.5°	454.4	450.6	439.1	436.5	431.9
15°	446.7	442.1	427.6	419.5	415.3
17.5°	437.8	431.0	413.2	403.8	397.0
20°	427.6	419.1	397.9	387.2	377.9
22.5°	416.6	406.8	382.1	367.7	361.3
25°	405.5	391.9	363.9	346.4	340.1
27.5°	392.3	377.9	346.9	326.9	317.1
30°	378.3	362.2	328.2	306.5	295.0
32.5°	364.7	345.2	310.3	284.8	274.2
35°	349.4	327.7	290.3	263.5	254.2
37.5°	334.5	311.2	271.6	242.3	231.7
40°	318.8	293.3	252.1	221.9	210.8
42.5°	302.6	275.4	232.5	201.1	190.4
45°	285.6	257.2	212.5	182.4	172.2
47.5°	269.5	239.3	193.4	163.2	153.9
50°	251.6	221.5	174.7	145.4	136.4
52.5°	234.2	202.3	156.9	128.8	120.7
55°	217.2	184.1	138.1	112.6	104.6
57.5°	199.8	165.8	121.6	97.8	91.0
60°	181.9	147.9	104.1	82.5	75.7
62.5°	164.5	130.5	89.3	68.9	65.5
65°	146.6	112.2	74.0	59.5	58.2
67.5°	129.6	95.2	59.5	52.3	51.0
70°	111.8	78.6	49.3	45.1	43.4
72.5°	94.8	63.3	41.2	37.8	37.0
75°	78.2	48.5	34.0	31.0	30.6
77.5°	61.6	34.4	26.8	25.1	24.2
80°	46.3	24.7	20.4	18.7	18.7
82.5°	32.3	16.6	14.0	13.2	13.2
85°	18.3	9.4	8.1	8.1	8.1
87.5°	6.8	3.4	3.4	3.0	3.0
90°	0.9	10.4	17.4	21.7	23.5
92.5°	21.7	18.3	20.9	22.6	23.5
95°	56.5	27.8	33.9	38.2	37.4
97.5°	101.7	30.4	44.3	46.9	47.8
100°	153.9	34.8	49.5	56.5	58.2
102.5°	211.2	209.5	51.3	60.8	63.5
105°	264.3	290.3	53.0	62.6	66.1
107.5°	326.0	347.7	54.8	64.3	67.8
110°	385.1	403.3	152.1	65.2	68.7

TEST NUMBER: P999640

CATALOG NUMBER: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	440.7	456.4	441.6	66.9	69.5
115°	499.8	514.6	536.3	133.9	71.3
117.5°	551.1	568.5	583.3	459.0	231.2
120°	608.5	621.5	637.2	647.6	530.3
122.5°	657.2	671.1	688.5	693.7	694.5
125°	706.7	718.0	734.5	740.6	743.2
127.5°	751.9	764.1	777.1	785.8	786.7
130°	794.5	808.4	818.0	827.5	826.7
132.5°	838.0	849.3	858.8	866.7	865.8
135°	874.5	888.4	896.2	904.9	903.2
137.5°	912.7	923.2	931.9	940.6	937.9
140°	950.1	957.1	966.6	974.5	970.1
142.5°	981.4	987.5	998.8	1005.7	1001.4
145°	1014.4	1013.6	1028.3	1034.4	1030.1
147.5°	1043.1	1040.5	1055.3	1059.6	1056.2
150°	1070.9	1064.9	1078.8	1084.0	1079.6
152.5°	1094.4	1087.5	1100.5	1105.7	1099.6
155°	1117.0	1109.2	1119.6	1124.8	1117.9
157.5°	1135.3	1128.3	1136.1	1142.2	1135.3
160°	1150.9	1145.7	1150.9	1156.1	1150.0
162.5°	1164.8	1159.6	1164.0	1170.0	1162.2
165°	1177.0	1171.8	1174.4	1180.5	1174.4
167.5°	1186.6	1181.3	1183.9	1190.0	1182.2
170°	1194.4	1189.2	1190.9	1197.0	1189.2
172.5°	1199.6	1194.4	1196.1	1202.2	1194.4
175°	1203.9	1197.9	1199.6	1205.7	1197.0
177.5°	1205.7	1199.6	1200.5	1206.5	1198.7
180°	1201.3	1201.3	1201.3	1201.3	1201.3

(END OF REPORT)