

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999676

Luminaire Tested: SA2XXRDIP-B485D1080UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999676
REPORT IS A COMBINATION OF REPORTS P988229 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D1080UB2750-4F0-XX-W2A-F_2700K
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5946.0 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999676

CATALOG NUMBER: SA2XXRDIP-B485D1080UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P999676

CATALOG NUMBER: SA2XXRDIP-B485D1080UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	80	77	74	63	61	59	47	46	44	32	32	31
2	85	78	72	67	76	70	65	61	55	52	49	41	39	38	29	28	26
3	78	69	62	56	69	62	56	51	49	45	42	37	34	32	26	24	23
4	71	61	54	48	63	55	49	44	44	39	36	33	30	28	23	21	20
5	65	54	47	41	58	49	42	37	39	34	31	30	26	24	21	19	17
6	60	49	41	35	54	44	37	33	35	30	27	27	24	21	19	17	15
7	56	44	36	31	50	40	33	29	32	27	24	24	21	19	17	15	14
8	51	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	12
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11
10	45	33	26	22	40	30	24	20	24	20	17	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12899	12899	12899
5°	12920	12273	12182
10°	12793	11639	11256
15°	12618	10892	10200
20°	12385	10043	9096
25°	12147	9172	8087
30°	11827	8322	6983
35°	11513	7466	6036
40°	11194	6626	5061
45°	10824	5757	4210
50°	10441	4921	3427
55°	10043	4085	2721
60°	9577	3267	2059
65°	9044	2490	1673
70°	8402	1806	1330
75°	7591	1378	1016
80°	6419	933	681
85°	4478	427	329

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10824 cd/sqm

TEST NUMBER: P999676

CATALOG NUMBER: SA2XXRDIP-B485D1080UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.4	1.3
10°-20°	209.7	3.5
20°-30°	294.4	5.0
30°-40°	320.9	5.4
40°-50°	294.9	5.0
50°-60°	231.6	3.9
60°-70°	150.7	2.5
70°-80°	77.6	1.3
80°-90°	22.4	0.4
90°-100°	48.0	0.8
100°-110°	178.9	3.0
110°-120°	474.6	8.0
120°-130°	787.1	13.2
130°-140°	836.1	14.1
140°-150°	777.0	13.1
150°-160°	624.7	10.5
160°-170°	402.5	6.8
170°-180°	138.5	2.3
0°-30°	580.4	9.8
0°-40°	901.3	15.2
0°-60°	1427.8	24.0
0°-90°	1678.5	28.2
90°-120°	701.5	11.8
90°-150°	3101.6	52.2
90°-180°	4267.0	71.8
0°-180°	5946.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	815	815	815	815	815	
5°	815	811	802	808	806	77
15°	775	767	742	728	720	218
25°	704	680	631	601	590	324
35°	606	569	504	457	441	379
45°	496	446	369	316	299	383
55°	377	319	240	195	181	337
65°	254	195	128	103	101	252
75°	136	84	59	54	53	144
85°	32	16	14	14	14	36
90°	1	13	21	26	28	6
95°	68	34	41	46	45	81
105°	320	352	64	76	80	342
115°	606	624	650	162	86	596
125°	856	870	890	897	901	764
135°	1060	1076	1086	1096	1094	819
145°	1229	1228	1246	1253	1248	769
155°	1354	1344	1357	1363	1354	624
165°	1426	1420	1423	1430	1423	403
175°	1459	1451	1454	1461	1450	139
180°	1456	1456	1456	1456	1456	

TEST NUMBER: P999676

CATALOG NUMBER: SA2XXRDIP-B485D1080UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	814.9	814.9	814.9	814.9	814.9
2.5°	818.6	814.9	806.8	814.2	812.7
5°	814.9	811.2	801.7	808.3	806.1
7.5°	808.3	803.9	793.5	796.5	792.8
10°	799.4	794.3	779.5	777.3	772.9
12.5°	788.4	781.7	761.8	757.4	749.3
15°	775.1	767.0	741.9	727.9	720.5
17.5°	759.6	747.8	716.8	700.6	688.8
20°	741.9	727.2	690.3	671.9	655.6
22.5°	722.7	705.8	663.0	637.9	626.9
25°	703.6	680.0	631.3	601.1	590.0
27.5°	680.7	655.6	601.8	567.1	550.2
30°	656.4	628.3	569.3	531.7	511.8
32.5°	632.8	598.8	538.4	494.1	475.7
35°	606.2	568.6	503.7	457.2	441.0
37.5°	580.4	539.8	471.3	420.4	401.9
40°	553.1	508.9	437.3	385.0	365.8
42.5°	525.1	477.9	403.4	348.8	330.4
45°	495.6	446.2	368.7	316.4	298.7
47.5°	467.6	415.2	335.6	283.2	267.0
50°	436.6	384.2	303.1	252.2	236.7
52.5°	406.4	351.0	272.1	223.5	209.4
55°	376.9	319.3	239.7	195.4	181.4
57.5°	346.6	287.6	210.9	169.6	157.8
60°	315.6	256.6	180.7	143.1	131.3
62.5°	285.4	226.4	154.9	119.5	113.6
65°	254.4	194.7	128.3	103.2	101.0
67.5°	224.9	165.2	103.2	90.7	88.5
70°	194.0	136.4	85.5	78.2	75.2
72.5°	164.5	109.9	71.5	65.6	64.2
75°	135.7	84.1	59.0	53.8	53.1
77.5°	106.9	59.7	46.5	43.5	42.0
80°	80.4	42.8	35.4	32.4	32.4
82.5°	56.0	28.8	24.3	22.9	22.9
85°	31.7	16.2	14.0	14.0	14.0
87.5°	11.8	5.9	5.9	5.2	5.2
90°	1.1	12.6	21.1	26.3	28.4
92.5°	26.3	22.1	25.3	27.4	28.4
95°	68.5	33.7	41.1	46.3	45.3
97.5°	123.2	36.9	53.7	56.9	57.9
100°	186.4	42.1	60.0	68.5	70.6
102.5°	255.9	253.8	62.1	73.7	76.9
105°	320.2	351.8	64.3	75.8	80.0
107.5°	395.0	421.3	66.4	77.9	82.2
110°	466.6	488.7	184.3	79.0	83.2

TEST NUMBER: P999676

CATALOG NUMBER: SA2XXRDIP-B485D1080UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	534.0	553.0	535.1	81.1	84.3
115°	605.6	623.5	649.9	162.2	86.4
117.5°	667.8	688.9	706.8	556.1	280.2
120°	737.3	753.1	772.1	784.7	642.5
122.5°	796.3	813.1	834.2	840.5	841.6
125°	856.3	870.0	890.0	897.4	900.6
127.5°	911.1	925.8	941.6	952.2	953.2
130°	962.7	979.6	991.1	1002.7	1001.7
132.5°	1015.4	1029.1	1040.6	1050.1	1049.1
135°	1059.6	1076.5	1085.9	1096.5	1094.4
137.5°	1106.0	1118.6	1129.1	1139.7	1136.5
140°	1151.2	1159.7	1171.3	1180.7	1175.5
142.5°	1189.2	1196.5	1210.2	1218.7	1213.4
145°	1229.2	1228.1	1246.0	1253.4	1248.1
147.5°	1263.9	1260.8	1278.7	1284.0	1279.7
150°	1297.7	1290.3	1307.1	1313.5	1308.2
152.5°	1326.1	1317.7	1333.5	1339.8	1332.4
155°	1353.5	1344.0	1356.6	1363.0	1354.5
157.5°	1375.6	1367.2	1376.6	1384.0	1375.6
160°	1394.6	1388.2	1394.6	1400.9	1393.5
162.5°	1411.4	1405.1	1410.4	1417.7	1408.2
165°	1426.2	1419.8	1423.0	1430.4	1423.0
167.5°	1437.7	1431.4	1434.6	1442.0	1432.5
170°	1447.2	1440.9	1443.0	1450.4	1440.9
172.5°	1453.5	1447.2	1449.3	1456.7	1447.2
175°	1458.8	1451.4	1453.5	1460.9	1450.4
177.5°	1460.9	1453.5	1454.6	1462.0	1452.5
180°	1455.6	1455.6	1455.6	1455.6	1455.6

(END OF REPORT)