

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999714

Luminaire Tested: SA2XXRDIP-B485D330UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999714
REPORT IS A COMBINATION OF REPORTS P988269 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D330UB2750-4F0-XX-W2A-F_2700K
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2983.0 lumens
Efficiency: N/A
Efficacy: 89.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 33.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999714

CATALOG NUMBER: SA2XXRDIP-B485D330UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P999714

CATALOG NUMBER: SA2XXRDIP-B485D330UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	55	54	53
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	50	48	46
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	30
6	65	53	46	40	61	50	43	38	44	39	34	38	34	31	33	30	27
7	61	49	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12899	12899	12899
5°	12920	12273	12182
10°	12793	11639	11256
15°	12618	10892	10200
20°	12385	10043	9096
25°	12147	9172	8087
30°	11827	8322	6983
35°	11513	7466	6036
40°	11194	6626	5061
45°	10824	5757	4210
50°	10441	4921	3427
55°	10043	4085	2721
60°	9577	3267	2059
65°	9044	2490	1673
70°	8402	1806	1330
75°	7591	1378	1016
80°	6419	933	681
85°	4478	427	329

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10824 cd/sqm

TEST NUMBER: P999714

CATALOG NUMBER: SA2XXRDIP-B485D330UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.4	2.6
10°-20°	209.7	7.0
20°-30°	294.4	9.9
30°-40°	320.9	10.8
40°-50°	294.9	9.9
50°-60°	231.6	7.8
60°-70°	150.7	5.1
70°-80°	77.6	2.6
80°-90°	20.6	0.7
90°-100°	14.7	0.5
100°-110°	54.8	1.8
110°-120°	145.3	4.9
120°-130°	240.9	8.1
130°-140°	255.9	8.6
140°-150°	237.8	8.0
150°-160°	191.2	6.4
160°-170°	123.2	4.1
170°-180°	42.4	1.4
0°-30°	580.4	19.5
0°-40°	901.3	30.2
0°-60°	1427.8	47.9
0°-90°	1676.8	56.2
90°-120°	214.7	7.2
90°-150°	949.4	31.8
90°-180°	1306.0	43.8
0°-180°	2983.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	815	815	815	815	815	
5°	815	811	802	808	806	77
15°	775	767	742	728	720	218
25°	704	680	631	601	590	324
35°	606	569	504	457	441	379
45°	496	446	369	316	299	383
55°	377	319	240	195	181	337
65°	254	195	128	103	101	252
75°	136	84	59	54	53	144
85°	32	16	14	14	14	36
90°	0	4	6	8	9	3
95°	21	10	13	14	14	25
105°	98	108	20	23	24	105
115°	185	191	199	50	26	183
125°	262	266	272	275	276	234
135°	324	330	332	336	335	251
145°	376	376	381	384	382	235
155°	414	411	415	417	415	191
165°	436	435	436	438	436	123
175°	446	444	445	447	444	42
180°	446	446	446	446	446	

TEST NUMBER: P999714

CATALOG NUMBER: SA2XXRDIP-B485D330UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	814.9	814.9	814.9	814.9	814.9
2.5°	818.6	814.9	806.8	814.2	812.7
5°	814.9	811.2	801.7	808.3	806.1
7.5°	808.3	803.9	793.5	796.5	792.8
10°	799.4	794.3	779.5	777.3	772.9
12.5°	788.4	781.7	761.8	757.4	749.3
15°	775.1	767.0	741.9	727.9	720.5
17.5°	759.6	747.8	716.8	700.6	688.8
20°	741.9	727.2	690.3	671.9	655.6
22.5°	722.7	705.8	663.0	637.9	626.9
25°	703.6	680.0	631.3	601.1	590.0
27.5°	680.7	655.6	601.8	567.1	550.2
30°	656.4	628.3	569.3	531.7	511.8
32.5°	632.8	598.8	538.4	494.1	475.7
35°	606.2	568.6	503.7	457.2	441.0
37.5°	580.4	539.8	471.3	420.4	401.9
40°	553.1	508.9	437.3	385.0	365.8
42.5°	525.1	477.9	403.4	348.8	330.4
45°	495.6	446.2	368.7	316.4	298.7
47.5°	467.6	415.2	335.6	283.2	267.0
50°	436.6	384.2	303.1	252.2	236.7
52.5°	406.4	351.0	272.1	223.5	209.4
55°	376.9	319.3	239.7	195.4	181.4
57.5°	346.6	287.6	210.9	169.6	157.8
60°	315.6	256.6	180.7	143.1	131.3
62.5°	285.4	226.4	154.9	119.5	113.6
65°	254.4	194.7	128.3	103.2	101.0
67.5°	224.9	165.2	103.2	90.7	88.5
70°	194.0	136.4	85.5	78.2	75.2
72.5°	164.5	109.9	71.5	65.6	64.2
75°	135.7	84.1	59.0	53.8	53.1
77.5°	106.9	59.7	46.5	43.5	42.0
80°	80.4	42.8	35.4	32.4	32.4
82.5°	56.0	28.8	24.3	22.9	22.9
85°	31.7	16.2	14.0	14.0	14.0
87.5°	11.8	5.9	5.9	5.2	5.2
90°	0.3	3.9	6.4	8.1	8.7
92.5°	8.1	6.8	7.7	8.4	8.7
95°	21.0	10.3	12.6	14.2	13.9
97.5°	37.7	11.3	16.4	17.4	17.7
100°	57.1	12.9	18.4	21.0	21.6
102.5°	78.3	77.7	19.0	22.6	23.5
105°	98.0	107.7	19.7	23.2	24.5
107.5°	120.9	129.0	20.3	23.9	25.1
110°	142.8	149.6	56.4	24.2	25.5

TEST NUMBER: P999714

CATALOG NUMBER: SA2XXRDIP-B485D330UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	163.5	169.3	163.8	24.8	25.8
115°	185.4	190.9	198.9	49.6	26.4
117.5°	204.4	210.8	216.3	170.2	85.8
120°	225.7	230.5	236.3	240.2	196.7
122.5°	243.7	248.9	255.3	257.3	257.6
125°	262.1	266.3	272.4	274.7	275.7
127.5°	278.9	283.4	288.2	291.4	291.8
130°	294.7	299.8	303.4	306.9	306.6
132.5°	310.8	315.0	318.5	321.4	321.1
135°	324.3	329.5	332.4	335.6	335.0
137.5°	338.5	342.4	345.6	348.8	347.9
140°	352.4	355.0	358.5	361.4	359.8
142.5°	364.0	366.2	370.4	373.0	371.4
145°	376.2	375.9	381.4	383.7	382.0
147.5°	386.9	385.9	391.4	393.0	391.7
150°	397.2	394.9	400.1	402.0	400.4
152.5°	405.9	403.3	408.2	410.1	407.8
155°	414.3	411.4	415.3	417.2	414.6
157.5°	421.1	418.5	421.4	423.6	421.1
160°	426.9	424.9	426.9	428.8	426.5
162.5°	432.0	430.1	431.7	434.0	431.0
165°	436.5	434.6	435.6	437.8	435.6
167.5°	440.1	438.1	439.1	441.4	438.5
170°	443.0	441.0	441.7	443.9	441.0
172.5°	444.9	443.0	443.6	445.9	443.0
175°	446.5	444.3	444.9	447.2	443.9
177.5°	447.2	444.9	445.2	447.5	444.6
180°	445.6	445.6	445.6	445.6	445.6

(END OF REPORT)