

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997911

Luminaire Tested: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P997911
REPORT IS A COMBINATION OF REPORTS P983648 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6529.0 lumens
Efficiency: N/A
Efficacy: 85.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997911

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P997911

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	68		
1	102	98	94	91	96	93	90	87	83	80	78	73	72	70	65	64	62	58		
2	94	87	81	75	88	82	77	72	73	69	66	65	62	59	58	56	54	50		
3	86	77	69	64	81	73	66	61	65	60	56	58	54	51	52	49	46	43		
4	79	68	61	55	74	65	58	53	58	53	48	52	48	44	47	43	40	37		
5	73	61	53	47	69	58	51	46	53	47	42	47	43	39	43	39	36	33		
6	67	55	47	42	64	53	46	40	48	42	37	43	38	35	39	35	32	29		
7	63	50	42	37	59	48	41	36	44	38	33	40	35	31	36	32	29	26		
8	58	46	38	33	55	44	37	32	40	34	30	36	31	28	33	29	26	24		
9	55	42	35	30	52	40	34	29	37	31	27	34	29	25	31	27	24	22		
10	51	39	32	27	48	37	31	26	34	29	25	31	26	23	28	24	22	20		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	31633	31633	31633	31633
5°	31709	33727	31831	26833
10°	31340	36820	31537	22123
15°	30581	38835	31006	18635
20°	30103	36464	30103	16197
25°	29144	31327	29277	14485
30°	27566	24625	28092	13119
35°	26167	17029	26605	12005
40°	24560	12857	24839	11114
45°	22576	10566	22945	10154
50°	20865	9273	20900	9296
55°	18908	7902	19033	8363
60°	16826	6600	17060	7298
65°	14963	5368	15236	6232
70°	13105	4212	13438	5028
75°	10998	3057	11429	3646
80°	8583	1938	9197	2163
85°	5636	976	6074	722

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 32700 cd/sqm

TEST NUMBER: P997911

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	190.3	2.9
10°-20°	554.0	8.5
20°-30°	804.0	12.3
30°-40°	847.6	13.0
40°-50°	750.0	11.5
50°-60°	598.9	9.2
60°-70°	406.8	6.2
70°-80°	208.1	3.2
80°-90°	50.5	0.8
90°-100°	23.8	0.4
100°-110°	88.8	1.4
110°-120°	235.6	3.6
120°-130°	390.8	6.0
130°-140°	415.1	6.4
140°-150°	385.8	5.9
150°-160°	310.2	4.8
160°-170°	199.9	3.1
170°-180°	68.8	1.1
0°-30°	1548.4	23.7
0°-40°	2396.0	36.7
0°-60°	3744.9	57.4
0°-90°	4410.3	67.5
90°-120°	348.3	5.3
90°-150°	1539.9	23.6
90°-180°	2119.0	32.5
0°-180°	6529.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1998	1998	1998	1998	1998	
5°	2000	2232	2008	1776	2000	190
15°	1879	2743	1905	1316	1879	531
25°	1688	2286	1696	1057	1688	772
35°	1378	1244	1401	877	1378	862
45°	1034	750	1051	720	1034	802
55°	710	527	714	558	710	633
65°	421	324	429	376	421	418
75°	197	160	204	190	197	211
85°	40	42	43	31	40	47
90°	0	14	0	14	0	4
95°	34	22	34	22	34	40
105°	159	40	159	40	159	170
115°	301	43	301	43	301	296
125°	425	447	425	447	425	379
135°	526	543	526	543	526	406
145°	610	620	610	620	610	382
155°	672	672	672	672	672	310
165°	708	706	708	706	708	200
175°	724	720	724	720	724	69
180°	723	723	723	723	723	

TEST NUMBER: P997911

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4
2.5°	2009.1	2013.7	2021.4	2022.9	2038.3	2050.6	2064.4	2064.4	2069.0	2067.5	2055.2
5°	1999.9	2013.7	2033.7	2050.6	2078.2	2090.5	2109.0	2122.8	2135.1	2144.3	2142.8
7.5°	1984.5	2009.1	2038.3	2070.6	2107.4	2128.9	2155.0	2179.6	2196.5	2211.9	2222.6
10°	1958.4	1999.9	2039.8	2082.8	2130.5	2159.6	2190.4	2222.6	2248.7	2277.9	2305.6
12.5°	1923.1	1983.0	2032.2	2089.0	2147.4	2179.6	2228.8	2253.3	2304.0	2377.8	2397.7
15°	1878.6	1960.0	2006.0	2078.2	2155.0	2181.2	2248.7	2288.7	2393.1	2439.2	2494.5
17.5°	1837.1	1927.7	1989.1	2072.1	2147.4	2198.0	2264.1	2345.5	2433.1	2499.1	2560.5
20°	1803.3	1890.8	1964.6	2056.7	2152.0	2216.5	2285.6	2383.9	2479.1	2546.7	2594.3
22.5°	1726.5	1838.6	1924.6	2027.5	2142.8	2231.8	2297.9	2405.4	2508.3	2549.8	2591.3
25°	1688.1	1784.9	1884.7	2001.4	2136.6	2242.6	2299.4	2419.2	2509.9	2525.2	2534.4
27.5°	1617.4	1726.5	1843.2	1976.9	2135.1	2224.2	2296.4	2405.4	2477.6	2466.9	2439.2
30°	1529.9	1663.5	1792.5	1936.9	2113.6	2210.3	2277.9	2377.8	2414.6	2359.3	2310.2
32.5°	1465.4	1591.3	1734.2	1901.6	2089.0	2181.2	2247.2	2325.5	2333.2	2233.4	2150.4
35°	1377.8	1517.6	1678.9	1855.5	2047.5	2130.5	2191.9	2239.5	2202.7	2062.9	1964.6
37.5°	1299.5	1437.7	1609.8	1789.5	1990.7	2072.1	2121.2	2128.9	2038.3	1915.4	1771.0
40°	1213.5	1356.3	1536.0	1725.0	1927.7	1998.4	2029.1	2006.0	1875.5	1732.6	1565.2
42.5°	1127.4	1268.8	1462.3	1655.8	1847.8	1907.7	1920.0	1857.1	1697.3	1529.9	1336.3
45°	1033.7	1181.2	1374.7	1569.8	1755.7	1789.5	1791.0	1700.4	1511.4	1336.3	1156.6
47.5°	956.9	1093.6	1285.7	1480.7	1637.4	1660.4	1651.2	1546.8	1340.9	1144.3	987.7
50°	872.5	1003.0	1193.5	1385.5	1519.1	1525.3	1502.2	1353.2	1152.0	972.3	847.9
52.5°	781.8	913.9	1089.0	1273.4	1393.2	1384.0	1339.4	1179.7	990.7	841.7	746.5
55°	709.6	826.4	990.7	1170.4	1254.9	1228.8	1179.7	1016.8	867.9	741.9	659.0
57.5°	629.8	732.7	894.0	1050.6	1099.8	1075.2	1026.1	874.0	735.8	640.5	585.2
60°	554.5	648.2	789.5	920.1	958.5	932.4	875.5	738.8	639.0	559.1	517.6
62.5°	485.4	566.8	685.1	804.9	820.2	794.1	745.0	634.4	548.4	485.4	454.7
65°	420.9	497.7	592.9	683.5	697.4	669.7	619.0	539.1	467.0	427.0	397.8
67.5°	357.9	419.3	503.8	569.9	577.5	551.4	510.0	445.4	400.9	357.9	336.4
70°	302.6	348.7	414.7	468.5	471.6	447.0	425.5	367.1	333.3	302.6	285.7
72.5°	248.8	281.1	331.8	371.7	373.3	357.9	337.9	301.1	271.9	250.4	233.5
75°	196.6	224.3	255.0	290.3	288.8	276.5	261.1	238.1	213.5	199.7	192.0
77.5°	150.5	167.4	192.0	215.0	215.0	208.9	199.7	182.8	167.4	153.6	145.9
80°	107.5	118.3	138.2	145.9	149.0	147.5	139.8	127.5	121.3	110.6	107.5
82.5°	69.1	76.8	86.0	93.7	98.3	95.2	93.7	87.6	78.3	75.3	72.2
85°	39.9	43.0	47.6	52.2	53.8	52.2	55.3	50.7	46.1	46.1	44.5
87.5°	16.9	18.4	21.5	21.5	23.0	23.0	21.5	23.0	23.0	21.5	20.0
90°	0.5	1.8	3.1	4.4	5.7	6.3	6.8	7.7	8.6	9.6	10.5
92.5°	13.1	12.6	12.2	11.7	11.2	11.0	11.2	11.5	11.9	12.2	12.6
95°	34.0	30.2	26.3	22.5	18.6	16.7	17.1	17.9	18.8	19.6	20.4
97.5°	61.2	51.7	42.1	32.6	23.1	18.3	19.2	21.1	23.0	24.8	26.7
100°	92.6	76.7	60.7	44.8	28.9	20.9	21.9	23.9	25.8	27.8	29.8
102.5°	127.1	126.9	126.6	126.4	126.1	126.0	115.4	94.3	73.2	52.0	30.9
105°	159.0	162.5	166.0	169.5	173.0	174.7	158.8	127.1	95.4	63.6	31.9
107.5°	196.1	199.0	201.9	204.8	207.7	209.2	189.6	150.4	111.3	72.1	32.9
110°	231.7	234.1	236.5	239.0	241.4	242.6	225.8	192.2	158.7	125.1	91.5

TEST NUMBER: P997911

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	265.1	267.2	269.3	271.4	273.5	274.5	273.5	271.6	269.6	267.7	265.7
115°	300.7	302.7	304.7	306.6	308.6	309.6	311.1	314.0	316.9	319.8	322.7
117.5°	331.5	333.8	336.2	338.5	340.8	342.0	343.0	345.0	346.9	348.9	350.9
120°	366.1	367.8	369.6	371.3	373.0	373.9	374.9	377.0	379.1	381.2	383.3
122.5°	395.3	397.2	399.0	400.9	402.8	403.7	404.9	407.2	409.5	411.9	414.2
125°	425.2	426.7	428.2	429.7	431.2	432.0	433.1	435.3	437.5	439.7	441.9
127.5°	452.3	453.9	455.6	457.2	458.9	459.7	460.6	462.3	464.0	465.8	467.5
130°	478.0	479.8	481.7	483.5	485.4	486.3	486.9	488.2	489.5	490.8	492.1
132.5°	504.1	505.6	507.1	508.6	510.1	510.9	511.5	512.8	514.1	515.4	516.7
135°	526.1	527.9	529.8	531.6	533.5	534.4	534.9	536.0	537.1	538.1	539.2
137.5°	549.1	550.5	551.9	553.3	554.7	555.4	556.0	557.1	558.3	559.4	560.6
140°	571.6	572.5	573.5	574.4	575.3	575.8	576.4	577.7	579.0	580.2	581.5
142.5°	590.4	591.2	592.0	592.9	593.7	594.1	594.9	596.4	597.9	599.4	600.9
145°	610.3	610.2	610.1	610.0	609.9	609.8	610.8	612.7	614.7	616.6	618.6
147.5°	627.5	627.2	626.8	626.5	626.2	626.0	627.0	629.0	630.9	632.9	634.9
150°	644.3	643.5	642.7	641.8	641.0	640.6	641.5	643.4	645.3	647.1	649.0
152.5°	658.4	657.5	656.5	655.6	654.7	654.2	655.1	656.8	658.5	660.3	662.0
155°	672.0	671.0	669.9	668.9	667.8	667.3	668.0	669.4	670.8	672.2	673.6
157.5°	683.0	682.1	681.1	680.2	679.3	678.8	679.3	680.4	681.4	682.5	683.5
160°	692.4	691.7	691.0	690.3	689.6	689.2	689.6	690.3	691.0	691.7	692.4
162.5°	700.7	700.0	699.3	698.6	697.9	697.6	697.9	698.5	699.0	699.6	700.2
165°	708.1	707.4	706.7	706.0	705.3	704.9	705.1	705.4	705.8	706.1	706.5
167.5°	713.8	713.1	712.4	711.7	711.0	710.7	710.9	711.2	711.5	711.9	712.2
170°	718.5	717.8	717.1	716.4	715.7	715.4	715.5	715.7	716.0	716.2	716.4
172.5°	721.7	721.0	720.3	719.6	718.9	718.5	718.6	718.9	719.1	719.4	719.6
175°	724.3	723.5	722.7	721.8	721.0	720.6	720.7	721.0	721.2	721.5	721.7
177.5°	725.3	724.5	723.7	722.9	722.1	721.7	721.8	721.9	722.0	722.1	722.2
180°	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7

TEST NUMBER: P997911

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4
2.5°	2076.7	2078.2	2081.3	2096.7	2104.3	2105.9	2099.7	2113.6	2118.2	2113.6	2110.5
5°	2175.0	2184.2	2202.7	2222.6	2221.1	2222.6	2231.8	2241.1	2244.1	2231.8	2236.4
7.5°	2261.0	2279.5	2299.4	2330.1	2330.1	2345.5	2351.6	2359.3	2377.8	2368.5	2365.5
10°	2359.3	2383.9	2420.8	2469.9	2471.5	2486.8	2502.2	2526.8	2534.4	2528.3	2531.4
12.5°	2482.2	2529.8	2532.9	2586.7	2611.2	2614.3	2638.9	2634.3	2649.6	2649.6	2675.7
15°	2536.0	2609.7	2651.2	2703.4	2718.8	2700.3	2720.3	2741.8	2743.3	2743.3	2741.8
17.5°	2632.7	2661.9	2703.4	2731.0	2737.2	2737.2	2738.7	2747.9	2741.8	2729.5	2738.7
20°	2652.7	2665.0	2680.4	2677.3	2680.4	2665.0	2649.6	2634.3	2635.8	2628.1	2651.2
22.5°	2615.8	2612.8	2577.4	2554.4	2554.4	2523.7	2494.5	2480.7	2466.9	2471.5	2479.1
25°	2523.7	2476.1	2433.1	2399.3	2391.6	2342.4	2302.5	2290.2	2267.2	2285.6	2288.7
27.5°	2376.2	2322.5	2253.3	2224.2	2184.2	2164.3	2136.6	2099.7	2052.1	2079.8	2075.2
30°	2218.0	2138.1	2081.3	2010.7	1947.7	1943.1	1890.8	1829.4	1804.8	1804.8	1818.6
32.5°	2041.4	1935.4	1852.4	1752.6	1691.2	1665.0	1602.1	1540.6	1554.5	1508.4	1525.3
35°	1835.5	1695.8	1591.3	1494.5	1448.5	1417.7	1336.3	1302.5	1265.7	1244.2	1284.1
37.5°	1638.9	1477.7	1344.0	1238.0	1221.1	1165.8	1110.5	1089.0	1067.5	1076.8	1075.2
40°	1399.3	1256.5	1136.7	1053.7	1024.5	998.4	961.5	935.4	921.6	929.3	930.8
42.5°	1182.7	1062.9	973.8	915.5	890.9	872.5	854.0	832.5	827.9	827.9	834.1
45°	1015.3	917.0	857.1	809.5	795.7	781.8	768.0	758.8	755.7	749.6	754.2
47.5°	881.7	803.3	766.5	731.1	715.8	712.7	700.4	695.8	689.7	688.1	689.7
50°	769.5	720.4	686.6	666.6	655.9	651.3	645.1	635.9	632.8	640.5	637.4
52.5°	691.2	645.1	626.7	606.7	600.6	594.4	585.2	586.8	585.2	582.2	582.2
55°	612.9	583.7	565.3	549.9	548.4	542.2	534.5	531.5	529.9	526.9	531.5
57.5°	549.9	526.9	510.0	496.1	490.0	490.0	482.3	476.2	476.2	474.6	476.2
60°	486.9	463.9	453.1	439.3	434.7	433.2	428.6	425.5	420.9	420.9	420.9
62.5°	428.6	410.1	397.8	385.5	387.1	379.4	373.3	370.2	370.2	371.7	371.7
65°	373.3	361.0	345.6	334.9	331.8	330.2	327.2	325.6	321.0	324.1	324.1
67.5°	322.6	305.7	296.5	291.8	287.2	285.7	282.6	279.6	278.0	276.5	279.6
70°	271.9	258.1	250.4	247.3	242.7	241.2	239.6	235.0	236.5	238.1	239.6
72.5°	225.8	213.5	212.0	202.8	202.8	202.8	196.6	199.7	198.1	195.1	198.1
75°	178.2	172.0	169.0	164.4	165.9	164.4	162.8	158.2	158.2	159.7	161.3
77.5°	141.3	135.2	133.6	129.0	126.0	129.0	126.0	124.4	124.4	126.0	126.0
80°	104.4	101.4	96.8	96.8	96.8	95.2	95.2	95.2	93.7	92.2	93.7
82.5°	69.1	69.1	67.6	66.0	67.6	64.5	66.0	66.0	66.0	66.0	66.0
85°	44.5	43.0	43.0	41.5	41.5	41.5	43.0	39.9	39.9	41.5	41.5
87.5°	20.0	20.0	20.0	21.5	20.0	20.0	20.0	21.5	20.0	20.0	20.0
90°	11.1	11.7	12.2	12.8	13.1	13.2	13.4	13.7	13.9	14.1	13.9
92.5°	12.8	13.0	13.3	13.5	13.6	13.7	13.8	13.9	14.0	14.1	14.0
95°	21.0	21.6	22.1	22.7	23.0	22.9	22.8	22.7	22.6	22.5	22.6
97.5°	27.0	27.4	27.7	28.0	28.2	28.3	28.4	28.5	28.7	28.8	28.7
100°	30.7	31.7	32.6	33.5	34.0	34.1	34.3	34.6	34.8	35.0	34.8
102.5°	32.2	33.4	34.7	36.0	36.6	36.8	37.1	37.5	37.8	38.2	37.8
105°	33.2	34.5	35.8	37.1	37.7	37.9	38.4	38.8	39.3	39.7	39.3
107.5°	34.2	35.5	36.8	38.1	38.7	38.9	39.4	39.9	40.3	40.8	40.3
110°	79.9	68.3	56.6	45.0	39.2	39.4	39.9	40.4	40.8	41.3	40.8

TEST NUMBER: P997911

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	215.6	165.5	115.4	65.3	40.3	40.5	40.8	41.1	41.5	41.8	41.5
115°	268.9	215.1	161.2	107.4	80.5	76.3	68.0	59.6	51.3	42.9	51.3
117.5°	334.3	317.7	301.0	284.4	276.1	260.9	230.4	200.0	169.5	139.1	169.5
120°	384.7	386.1	387.5	388.9	389.6	381.8	366.1	350.4	334.7	319.0	334.7
122.5°	414.9	415.6	416.3	417.0	417.3	417.4	417.5	417.6	417.7	417.8	417.7
125°	442.7	443.5	444.3	445.1	445.5	445.7	446.0	446.4	446.7	447.1	446.7
127.5°	468.7	469.8	471.0	472.1	472.7	472.8	472.9	473.0	473.2	473.3	473.2
130°	493.4	494.6	495.9	497.2	497.8	497.7	497.6	497.5	497.4	497.3	497.4
132.5°	517.7	518.8	519.8	520.9	521.4	521.3	521.2	521.1	521.0	520.9	521.0
135°	540.4	541.5	542.7	543.8	544.4	544.3	544.0	543.8	543.5	543.3	543.5
137.5°	561.8	562.9	564.1	565.2	565.8	565.6	565.3	565.0	564.6	564.3	564.6
140°	582.5	583.6	584.6	585.7	586.2	585.9	585.3	584.8	584.2	583.6	584.2
142.5°	601.8	602.7	603.6	604.5	605.0	604.7	604.1	603.6	603.0	602.4	603.0
145°	619.4	620.2	621.1	621.9	622.3	622.0	621.4	620.9	620.3	619.7	620.3
147.5°	635.5	636.1	636.6	637.2	637.5	637.3	636.8	636.3	635.9	635.4	635.9
150°	649.7	650.4	651.1	651.8	652.1	651.8	651.2	650.7	650.1	649.5	650.1
152.5°	662.7	663.4	664.1	664.8	665.2	664.8	664.0	663.1	662.3	661.5	662.3
155°	674.3	675.0	675.7	676.4	676.7	676.2	675.3	674.4	673.4	672.5	673.4
157.5°	684.3	685.1	685.9	686.7	687.1	686.6	685.7	684.8	683.9	683.0	683.9
160°	693.1	693.8	694.5	695.2	695.5	695.1	694.3	693.5	692.7	691.9	692.7
162.5°	701.0	701.8	702.7	703.5	703.9	703.4	702.3	701.3	700.2	699.2	700.2
165°	707.3	708.1	709.0	709.8	710.2	709.8	709.0	708.1	707.3	706.5	707.3
167.5°	713.0	713.8	714.7	715.5	715.9	715.4	714.3	713.3	712.2	711.2	712.2
170°	717.2	718.0	718.9	719.7	720.1	719.6	718.5	717.5	716.4	715.4	716.4
172.5°	720.4	721.2	722.0	722.8	723.2	722.7	721.6	720.6	719.5	718.5	719.5
175°	722.5	723.3	724.1	724.9	725.3	724.7	723.6	722.4	721.3	720.1	721.3
177.5°	723.0	723.8	724.6	725.4	725.8	725.3	724.2	723.2	722.1	721.1	722.1
180°	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7

TEST NUMBER: P997911

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4
2.5°	2118.2	2107.4	2098.2	2099.7	2107.4	2101.3	2085.9	2065.9	2058.3	2049.1	2058.3
5°	2245.7	2236.4	2218.0	2219.6	2214.9	2208.8	2184.2	2153.5	2153.5	2128.9	2125.9
7.5°	2371.6	2357.8	2345.5	2342.4	2325.5	2313.2	2291.7	2248.7	2231.8	2202.7	2185.8
10°	2512.9	2502.2	2488.4	2471.5	2462.2	2440.7	2405.4	2342.4	2311.7	2271.8	2242.6
12.5°	2655.8	2654.2	2623.5	2589.7	2588.2	2554.4	2529.8	2445.3	2403.9	2350.1	2281.0
15°	2746.4	2738.7	2721.8	2704.9	2709.5	2672.7	2617.4	2517.5	2489.9	2425.4	2351.6
17.5°	2744.9	2744.9	2740.3	2737.2	2732.6	2721.8	2691.1	2625.1	2580.5	2499.1	2430.0
20°	2657.3	2677.3	2681.9	2680.4	2695.7	2703.4	2701.9	2660.4	2625.1	2552.9	2482.2
22.5°	2482.2	2528.3	2548.3	2560.5	2592.8	2609.7	2649.6	2634.3	2625.1	2571.3	2511.4
25°	2319.4	2334.8	2394.7	2397.7	2442.3	2483.7	2523.7	2549.8	2583.6	2563.6	2512.9
27.5°	2109.0	2144.3	2187.3	2219.6	2228.8	2313.2	2379.3	2428.5	2505.3	2511.4	2494.5
30°	1870.9	1887.8	1958.4	2001.4	2050.6	2112.0	2207.3	2291.7	2360.9	2423.8	2445.3
32.5°	1580.6	1649.7	1691.2	1743.4	1786.4	1895.5	2012.2	2121.2	2201.1	2307.1	2353.2
35°	1314.8	1368.6	1439.3	1460.8	1539.1	1631.3	1783.3	1923.1	2044.4	2152.0	2245.7
37.5°	1095.2	1138.2	1213.5	1247.2	1293.3	1411.6	1539.1	1712.7	1858.6	1990.7	2107.4
40°	944.7	976.9	1033.7	1044.5	1082.9	1190.4	1293.3	1456.1	1649.7	1827.9	1955.4
42.5°	841.7	857.1	895.5	909.3	933.9	1006.1	1098.3	1251.9	1431.6	1615.9	1795.6
45°	768.0	778.8	801.8	814.1	844.8	877.1	952.3	1075.2	1216.5	1402.4	1595.9
47.5°	702.0	715.8	725.0	732.7	749.6	784.9	834.1	924.7	1059.9	1230.4	1417.7
50°	646.7	651.3	668.2	669.7	680.5	703.5	749.6	804.9	912.4	1050.6	1231.9
52.5°	591.4	596.0	606.7	617.5	622.1	640.5	671.2	717.3	797.2	906.3	1067.5
55°	536.1	542.2	553.0	560.6	565.3	580.6	599.0	643.6	706.6	783.4	915.5
57.5°	480.8	494.6	497.7	502.3	510.0	526.9	543.8	569.9	619.0	689.7	786.4
60°	428.6	433.2	443.9	448.5	456.2	465.4	486.9	506.9	542.2	597.5	685.1
62.5°	374.8	385.5	390.1	394.8	400.9	411.7	425.5	447.0	477.7	522.2	591.4
65°	328.7	330.2	339.5	345.6	351.7	359.4	373.3	393.2	411.7	453.1	503.8
67.5°	284.2	287.2	290.3	296.5	304.1	311.8	324.1	334.9	357.9	385.5	425.5
70°	241.2	241.2	248.8	253.4	251.9	261.1	270.3	282.6	299.5	325.6	357.9
72.5°	202.8	201.2	207.4	208.9	212.0	218.1	224.3	236.5	245.8	265.7	290.3
75°	161.3	164.4	167.4	167.4	172.0	176.6	182.8	188.9	199.7	212.0	230.4
77.5°	127.5	127.5	130.6	132.1	136.7	135.2	141.3	147.5	155.1	165.9	179.7
80°	93.7	96.8	96.8	96.8	98.3	99.8	106.0	110.6	115.2	122.9	129.0
82.5°	66.0	66.0	69.1	69.1	69.1	72.2	72.2	73.7	76.8	81.4	86.0
85°	41.5	41.5	41.5	43.0	41.5	43.0	46.1	44.5	46.1	49.2	49.2
87.5°	20.0	20.0	20.0	20.0	20.0	21.5	20.0	21.5	23.0	23.0	23.0
90°	13.7	13.4	13.2	13.1	12.8	12.2	11.7	11.1	10.5	9.6	8.6
92.5°	13.9	13.8	13.7	13.6	13.5	13.3	13.0	12.8	12.6	12.2	11.9
95°	22.7	22.8	22.9	23.0	22.7	22.1	21.6	21.0	20.4	19.6	18.8
97.5°	28.5	28.4	28.3	28.2	28.0	27.7	27.4	27.0	26.7	24.8	23.0
100°	34.6	34.3	34.1	34.0	33.5	32.6	31.7	30.7	29.8	27.8	25.8
102.5°	37.5	37.1	36.8	36.6	36.0	34.7	33.4	32.2	30.9	52.0	73.2
105°	38.8	38.4	37.9	37.7	37.1	35.8	34.5	33.2	31.9	63.6	95.4
107.5°	39.9	39.4	38.9	38.7	38.1	36.8	35.5	34.2	32.9	72.1	111.3
110°	40.4	39.9	39.4	39.2	45.0	56.6	68.3	79.9	91.5	125.1	158.7

TEST NUMBER: P997911

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	41.1	40.8	40.5	40.3	65.3	115.4	165.5	215.6	265.7	267.7	269.6
115°	59.6	68.0	76.3	80.5	107.4	161.2	215.1	268.9	322.7	319.8	316.9
117.5°	200.0	230.4	260.9	276.1	284.4	301.0	317.7	334.3	350.9	348.9	346.9
120°	350.4	366.1	381.8	389.6	388.9	387.5	386.1	384.7	383.3	381.2	379.1
122.5°	417.6	417.5	417.4	417.3	417.0	416.3	415.6	414.9	414.2	411.9	409.5
125°	446.4	446.0	445.7	445.5	445.1	444.3	443.5	442.7	441.9	439.7	437.5
127.5°	473.0	472.9	472.8	472.7	472.1	471.0	469.8	468.7	467.5	465.8	464.0
130°	497.5	497.6	497.7	497.8	497.2	495.9	494.6	493.4	492.1	490.8	489.5
132.5°	521.1	521.2	521.3	521.4	520.9	519.8	518.8	517.7	516.7	515.4	514.1
135°	543.8	544.0	544.3	544.4	543.8	542.7	541.5	540.4	539.2	538.1	537.1
137.5°	565.0	565.3	565.6	565.8	565.2	564.1	562.9	561.8	560.6	559.4	558.3
140°	584.8	585.3	585.9	586.2	585.7	584.6	583.6	582.5	581.5	580.2	579.0
142.5°	603.6	604.1	604.7	605.0	604.5	603.6	602.7	601.8	600.9	599.4	597.9
145°	620.9	621.4	622.0	622.3	621.9	621.1	620.2	619.4	618.6	616.6	614.7
147.5°	636.3	636.8	637.3	637.5	637.2	636.6	636.1	635.5	634.9	632.9	630.9
150°	650.7	651.2	651.8	652.1	651.8	651.1	650.4	649.7	649.0	647.1	645.3
152.5°	663.1	664.0	664.8	665.2	664.8	664.1	663.4	662.7	662.0	660.3	658.5
155°	674.4	675.3	676.2	676.7	676.4	675.7	675.0	674.3	673.6	672.2	670.8
157.5°	684.8	685.7	686.6	687.1	686.7	685.9	685.1	684.3	683.5	682.5	681.4
160°	693.5	694.3	695.1	695.5	695.2	694.5	693.8	693.1	692.4	691.7	691.0
162.5°	701.3	702.3	703.4	703.9	703.5	702.7	701.8	701.0	700.2	699.6	699.0
165°	708.1	709.0	709.8	710.2	709.8	709.0	708.1	707.3	706.5	706.1	705.8
167.5°	713.3	714.3	715.4	715.9	715.5	714.7	713.8	713.0	712.2	711.9	711.5
170°	717.5	718.5	719.6	720.1	719.7	718.9	718.0	717.2	716.4	716.2	716.0
172.5°	720.6	721.6	722.7	723.2	722.8	722.0	721.2	720.4	719.6	719.4	719.1
175°	722.4	723.6	724.7	725.3	724.9	724.1	723.3	722.5	721.7	721.5	721.2
177.5°	723.2	724.2	725.3	725.8	725.4	724.6	723.8	723.0	722.2	722.1	722.0
180°	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7

TEST NUMBER: P997911

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4
2.5°	2050.6	2042.9	2038.3	2041.4	2032.2	2009.1	2009.1	2016.8	2007.6	1998.4	1984.5
5°	2107.4	2092.1	2082.8	2081.3	2059.8	2022.9	2015.3	2007.6	1987.6	1966.1	1943.1
7.5°	2162.7	2135.1	2119.7	2109.0	2078.2	2030.6	2010.7	1993.8	1961.5	1929.2	1900.1
10°	2208.8	2168.9	2150.4	2133.5	2093.6	2033.7	2001.4	1970.7	1929.2	1887.8	1850.9
12.5°	2245.7	2199.6	2176.5	2152.0	2102.8	2024.5	1984.5	1935.4	1893.9	1838.6	1801.8
15°	2307.1	2211.9	2190.4	2167.3	2116.6	2009.1	1960.0	1904.7	1847.8	1774.1	1734.2
17.5°	2356.3	2228.8	2227.2	2178.1	2112.0	2003.0	1927.7	1855.5	1794.1	1720.3	1657.4
20°	2385.4	2254.9	2230.3	2179.6	2096.7	1961.5	1883.2	1803.3	1737.2	1648.2	1585.2
22.5°	2410.0	2291.7	2227.2	2165.8	2064.4	1947.7	1832.5	1757.2	1666.6	1569.8	1509.9
25°	2419.2	2299.4	2231.8	2161.2	2041.4	1907.7	1777.2	1695.8	1594.4	1506.8	1425.4
27.5°	2420.8	2297.9	2214.9	2141.2	2009.1	1855.5	1721.9	1635.9	1523.7	1422.4	1340.9
30°	2405.4	2281.0	2205.7	2125.9	1978.4	1807.9	1654.3	1559.1	1439.3	1337.9	1253.4
32.5°	2359.3	2247.2	2185.8	2098.2	1938.5	1741.8	1589.8	1483.8	1357.8	1258.0	1176.6
35°	2282.5	2205.7	2138.1	2056.7	1886.2	1680.4	1525.3	1400.9	1273.4	1178.1	1101.3
37.5°	2187.3	2145.8	2082.8	2003.0	1826.3	1625.1	1453.1	1314.8	1187.3	1095.2	1019.9
40°	2058.3	2069.0	2007.6	1935.4	1755.7	1549.8	1359.4	1227.3	1107.5	1021.5	947.7
42.5°	1918.5	1963.0	1927.7	1858.6	1677.3	1466.9	1290.3	1144.3	1027.6	938.5	877.1
45°	1768.0	1844.8	1823.3	1772.6	1595.9	1379.3	1192.0	1050.6	947.7	861.7	807.9
47.5°	1603.6	1712.7	1712.7	1675.8	1505.3	1291.8	1107.5	963.1	861.7	800.3	748.0
50°	1436.2	1559.1	1579.0	1554.5	1403.9	1192.0	1004.6	874.0	786.4	726.5	688.1
52.5°	1261.1	1403.9	1440.8	1428.5	1296.4	1096.7	920.1	792.6	712.7	660.5	626.7
55°	1093.6	1259.5	1299.5	1304.1	1181.2	992.3	826.4	714.3	637.4	602.1	572.9
57.5°	935.4	1095.2	1139.7	1147.4	1064.5	897.0	738.8	640.5	571.4	542.2	519.2
60°	800.3	933.9	992.3	1009.2	937.0	786.4	657.4	562.2	510.0	482.3	460.8
62.5°	689.7	797.2	858.6	863.2	831.0	689.7	572.9	493.1	448.5	423.9	413.2
65°	582.2	678.9	715.8	734.2	708.1	597.5	494.6	428.6	393.2	371.7	361.0
67.5°	496.1	557.6	588.3	612.9	586.8	503.8	420.9	367.1	341.0	319.5	313.3
70°	407.0	457.7	480.8	505.4	482.3	419.3	359.4	310.3	287.2	270.3	262.7
72.5°	325.6	365.6	387.1	402.4	388.6	336.4	287.2	253.4	236.5	224.3	219.7
75°	258.1	285.7	298.0	308.7	302.6	262.7	231.9	204.3	188.9	178.2	175.1
77.5°	196.6	216.6	230.4	233.5	225.8	199.7	173.6	156.7	144.4	138.2	135.2
80°	139.8	152.1	159.7	164.4	156.7	145.9	127.5	115.2	104.4	96.8	95.2
82.5°	93.7	99.8	106.0	104.4	101.4	92.2	81.4	75.3	70.7	64.5	64.5
85°	53.8	55.3	58.4	59.9	58.4	52.2	46.1	43.0	39.9	35.3	35.3
87.5°	23.0	24.6	24.6	26.1	23.0	23.0	20.0	16.9	16.9	15.4	13.8
90°	7.7	6.8	6.3	5.7	4.4	3.1	1.8	0.5	1.8	3.1	4.4
92.5°	11.5	11.2	11.0	11.2	11.7	12.2	12.6	13.1	12.6	12.2	11.7
95°	17.9	17.1	16.7	18.6	22.5	26.3	30.2	34.0	30.2	26.3	22.5
97.5°	21.1	19.2	18.3	23.1	32.6	42.1	51.7	61.2	51.7	42.1	32.6
100°	23.9	21.9	20.9	28.9	44.8	60.7	76.7	92.6	76.7	60.7	44.8
102.5°	94.3	115.4	126.0	126.1	126.4	126.6	126.9	127.1	126.9	126.6	126.4
105°	127.1	158.8	174.7	173.0	169.5	166.0	162.5	159.0	162.5	166.0	169.5
107.5°	150.4	189.6	209.2	207.7	204.8	201.9	199.0	196.1	199.0	201.9	204.8
110°	192.2	225.8	242.6	241.4	239.0	236.5	234.1	231.7	234.1	236.5	239.0

TEST NUMBER: P997911

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	271.6	273.5	274.5	273.5	271.4	269.3	267.2	265.1	267.2	269.3	271.4
115°	314.0	311.1	309.6	308.6	306.6	304.7	302.7	300.7	302.7	304.7	306.6
117.5°	345.0	343.0	342.0	340.8	338.5	336.2	333.8	331.5	333.8	336.2	338.5
120°	377.0	374.9	373.9	373.0	371.3	369.6	367.8	366.1	367.8	369.6	371.3
122.5°	407.2	404.9	403.7	402.8	400.9	399.0	397.2	395.3	397.2	399.0	400.9
125°	435.3	433.1	432.0	431.2	429.7	428.2	426.7	425.2	426.7	428.2	429.7
127.5°	462.3	460.6	459.7	458.9	457.2	455.6	453.9	452.3	453.9	455.6	457.2
130°	488.2	486.9	486.3	485.4	483.5	481.7	479.8	478.0	479.8	481.7	483.5
132.5°	512.8	511.5	510.9	510.1	508.6	507.1	505.6	504.1	505.6	507.1	508.6
135°	536.0	534.9	534.4	533.5	531.6	529.8	527.9	526.1	527.9	529.8	531.6
137.5°	557.1	556.0	555.4	554.7	553.3	551.9	550.5	549.1	550.5	551.9	553.3
140°	577.7	576.4	575.8	575.3	574.4	573.5	572.5	571.6	572.5	573.5	574.4
142.5°	596.4	594.9	594.1	593.7	592.9	592.0	591.2	590.4	591.2	592.0	592.9
145°	612.7	610.8	609.8	609.9	610.0	610.1	610.2	610.3	610.2	610.1	610.0
147.5°	629.0	627.0	626.0	626.2	626.5	626.8	627.2	627.5	627.2	626.8	626.5
150°	643.4	641.5	640.6	641.0	641.8	642.7	643.5	644.3	643.5	642.7	641.8
152.5°	656.8	655.1	654.2	654.7	655.6	656.5	657.5	658.4	657.5	656.5	655.6
155°	669.4	668.0	667.3	667.8	668.9	669.9	671.0	672.0	671.0	669.9	668.9
157.5°	680.4	679.3	678.8	679.3	680.2	681.1	682.1	683.0	682.1	681.1	680.2
160°	690.3	689.6	689.2	689.6	690.3	691.0	691.7	692.4	691.7	691.0	690.3
162.5°	698.5	697.9	697.6	697.9	698.6	699.3	700.0	700.7	700.0	699.3	698.6
165°	705.4	705.1	704.9	705.3	706.0	706.7	707.4	708.1	707.4	706.7	706.0
167.5°	711.2	710.9	710.7	711.0	711.7	712.4	713.1	713.8	713.1	712.4	711.7
170°	715.7	715.5	715.4	715.7	716.4	717.1	717.8	718.5	717.8	717.1	716.4
172.5°	718.9	718.6	718.5	718.9	719.6	720.3	721.0	721.7	721.0	720.3	719.6
175°	721.0	720.7	720.6	721.0	721.8	722.7	723.5	724.3	723.5	722.7	721.8
177.5°	721.9	721.8	721.7	722.1	722.9	723.7	724.5	725.3	724.5	723.7	722.9
180°	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7

TEST NUMBER: P997911

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4
2.5°	1976.9	1984.5	1983.0	1967.6	1950.7	1936.9	1910.8	1913.9	1904.7	1906.2	1915.4
5°	1927.7	1927.7	1921.6	1900.1	1872.4	1857.1	1827.9	1820.2	1801.8	1800.2	1798.7
7.5°	1875.5	1867.8	1860.1	1829.4	1795.6	1771.0	1731.1	1721.9	1703.4	1691.2	1685.0
10°	1814.0	1803.3	1787.9	1752.6	1711.1	1680.4	1638.9	1626.6	1591.3	1576.0	1566.7
12.5°	1746.5	1740.3	1715.7	1686.6	1619.0	1585.2	1525.3	1537.6	1502.2	1471.5	1466.9
15°	1678.9	1655.8	1642.0	1594.4	1513.0	1497.6	1450.0	1425.4	1393.2	1368.6	1368.6
17.5°	1612.8	1577.5	1546.8	1496.1	1436.2	1393.2	1357.8	1345.6	1305.6	1281.0	1276.4
20°	1525.3	1485.3	1477.7	1405.5	1364.0	1316.4	1282.6	1251.9	1222.7	1211.9	1204.2
22.5°	1442.3	1396.2	1384.0	1322.5	1281.0	1233.4	1199.6	1178.1	1156.6	1148.9	1135.1
25°	1353.2	1325.6	1307.2	1241.1	1195.0	1150.5	1127.4	1112.1	1092.1	1090.6	1081.4
27.5°	1267.2	1241.1	1222.7	1159.7	1125.9	1084.4	1066.0	1049.1	1038.4	1033.7	1029.1
30°	1193.5	1164.3	1142.8	1096.7	1055.2	1021.5	1006.1	995.3	989.2	981.5	980.0
32.5°	1112.1	1095.2	1066.0	1030.7	998.4	966.2	956.9	949.3	940.0	937.0	935.4
35°	1043.0	1019.9	1001.5	961.5	947.7	920.1	909.3	903.2	890.9	887.8	884.7
37.5°	975.4	953.9	933.9	909.3	883.2	867.9	861.7	852.5	846.3	847.9	844.8
40°	907.8	890.9	875.5	849.4	834.1	826.4	814.1	804.9	801.8	803.3	801.8
42.5°	841.7	826.4	817.2	797.2	781.8	774.2	766.5	757.3	761.9	761.9	766.5
45°	781.8	768.0	761.9	746.5	737.3	725.0	717.3	715.8	721.9	720.4	720.4
47.5°	720.4	715.8	708.1	694.3	682.0	674.3	672.8	672.8	678.9	682.0	680.5
50°	672.8	663.6	654.3	643.6	634.4	631.3	626.7	629.8	635.9	635.9	639.0
52.5°	612.9	606.7	603.7	594.4	588.3	588.3	588.3	589.8	594.4	599.0	597.5
55°	560.6	556.0	553.0	548.4	540.7	542.2	540.7	543.8	548.4	553.0	556.0
57.5°	505.4	503.8	500.7	493.1	493.1	491.5	496.1	497.7	505.4	508.4	513.0
60°	456.2	451.6	451.6	445.4	445.4	445.4	450.1	454.7	460.8	462.3	465.4
62.5°	404.0	404.0	402.4	397.8	397.8	402.4	404.0	410.1	413.2	413.2	417.8
65°	354.8	353.3	351.7	353.3	354.8	354.8	359.4	362.5	365.6	367.1	368.6
67.5°	305.7	304.1	307.2	305.7	308.7	314.9	313.3	318.0	322.6	322.6	324.1
70°	259.6	262.7	261.1	264.2	262.7	265.7	270.3	271.9	271.9	273.4	278.0
72.5°	216.6	216.6	216.6	215.0	216.6	219.7	222.7	224.3	227.3	228.9	233.5
75°	175.1	175.1	172.0	175.1	175.1	178.2	181.3	181.3	181.3	184.3	188.9
77.5°	132.1	133.6	132.1	135.2	135.2	136.7	139.8	138.2	141.3	142.9	144.4
80°	96.8	95.2	95.2	95.2	96.8	96.8	99.8	101.4	101.4	106.0	102.9
82.5°	61.4	63.0	61.4	63.0	63.0	64.5	63.0	64.5	66.0	69.1	67.6
85°	35.3	33.8	33.8	35.3	33.8	33.8	35.3	33.8	35.3	33.8	35.3
87.5°	13.8	12.3	12.3	12.3	12.3	10.8	10.8	9.2	9.2	9.2	7.7
90°	5.7	6.3	6.8	7.7	8.6	9.6	10.5	11.1	11.7	12.2	12.8
92.5°	11.2	11.0	11.2	11.5	11.9	12.2	12.6	12.8	13.0	13.3	13.5
95°	18.6	16.7	17.1	17.9	18.8	19.6	20.4	21.0	21.6	22.1	22.7
97.5°	23.1	18.3	19.2	21.1	23.0	24.8	26.7	27.0	27.4	27.7	28.0
100°	28.9	20.9	21.9	23.9	25.8	27.8	29.8	30.7	31.7	32.6	33.5
102.5°	126.1	126.0	115.4	94.3	73.2	52.0	30.9	32.2	33.4	34.7	36.0
105°	173.0	174.7	158.8	127.1	95.4	63.6	31.9	33.2	34.5	35.8	37.1
107.5°	207.7	209.2	189.6	150.4	111.3	72.1	32.9	34.2	35.5	36.8	38.1
110°	241.4	242.6	225.8	192.2	158.7	125.1	91.5	79.9	68.3	56.6	45.0

TEST NUMBER: P997911

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	273.5	274.5	273.5	271.6	269.6	267.7	265.7	215.6	165.5	115.4	65.3
115°	308.6	309.6	311.1	314.0	316.9	319.8	322.7	268.9	215.1	161.2	107.4
117.5°	340.8	342.0	343.0	345.0	346.9	348.9	350.9	334.3	317.7	301.0	284.4
120°	373.0	373.9	374.9	377.0	379.1	381.2	383.3	384.7	386.1	387.5	388.9
122.5°	402.8	403.7	404.9	407.2	409.5	411.9	414.2	414.9	415.6	416.3	417.0
125°	431.2	432.0	433.1	435.3	437.5	439.7	441.9	442.7	443.5	444.3	445.1
127.5°	458.9	459.7	460.6	462.3	464.0	465.8	467.5	468.7	469.8	471.0	472.1
130°	485.4	486.3	486.9	488.2	489.5	490.8	492.1	493.4	494.6	495.9	497.2
132.5°	510.1	510.9	511.5	512.8	514.1	515.4	516.7	517.7	518.8	519.8	520.9
135°	533.5	534.4	534.9	536.0	537.1	538.1	539.2	540.4	541.5	542.7	543.8
137.5°	554.7	555.4	556.0	557.1	558.3	559.4	560.6	561.8	562.9	564.1	565.2
140°	575.3	575.8	576.4	577.7	579.0	580.2	581.5	582.5	583.6	584.6	585.7
142.5°	593.7	594.1	594.9	596.4	597.9	599.4	600.9	601.8	602.7	603.6	604.5
145°	609.9	609.8	610.8	612.7	614.7	616.6	618.6	619.4	620.2	621.1	621.9
147.5°	626.2	626.0	627.0	629.0	630.9	632.9	634.9	635.5	636.1	636.6	637.2
150°	641.0	640.6	641.5	643.4	645.3	647.1	649.0	649.7	650.4	651.1	651.8
152.5°	654.7	654.2	655.1	656.8	658.5	660.3	662.0	662.7	663.4	664.1	664.8
155°	667.8	667.3	668.0	669.4	670.8	672.2	673.6	674.3	675.0	675.7	676.4
157.5°	679.3	678.8	679.3	680.4	681.4	682.5	683.5	684.3	685.1	685.9	686.7
160°	689.6	689.2	689.6	690.3	691.0	691.7	692.4	693.1	693.8	694.5	695.2
162.5°	697.9	697.6	697.9	698.5	699.0	699.6	700.2	701.0	701.8	702.7	703.5
165°	705.3	704.9	705.1	705.4	705.8	706.1	706.5	707.3	708.1	709.0	709.8
167.5°	711.0	710.7	710.9	711.2	711.5	711.9	712.2	713.0	713.8	714.7	715.5
170°	715.7	715.4	715.5	715.7	716.0	716.2	716.4	717.2	718.0	718.9	719.7
172.5°	718.9	718.5	718.6	718.9	719.1	719.4	719.6	720.4	721.2	722.0	722.8
175°	721.0	720.6	720.7	721.0	721.2	721.5	721.7	722.5	723.3	724.1	724.9
177.5°	722.1	721.7	721.8	721.9	722.0	722.1	722.2	723.0	723.8	724.6	725.4
180°	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7

TEST NUMBER: P997911

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4
2.5°	1904.7	1909.3	1898.5	1895.5	1898.5	1887.8	1890.8	1893.9	1893.9	1898.5	1901.6
5°	1794.1	1787.9	1777.2	1774.1	1771.0	1775.6	1772.6	1777.2	1778.7	1789.5	1791.0
7.5°	1685.0	1675.8	1666.6	1657.4	1654.3	1646.6	1654.3	1654.3	1665.0	1662.0	1669.7
10°	1556.0	1554.5	1542.2	1537.6	1531.4	1519.1	1536.0	1531.4	1539.1	1552.9	1556.0
12.5°	1460.8	1443.9	1451.5	1430.0	1437.7	1425.4	1427.0	1427.0	1439.3	1440.8	1437.7
15°	1370.1	1356.3	1336.3	1327.1	1322.5	1316.4	1336.3	1337.9	1328.7	1350.2	1342.5
17.5°	1278.0	1278.0	1259.5	1254.9	1242.6	1248.8	1245.7	1247.2	1244.2	1259.5	1267.2
20°	1198.1	1190.4	1184.3	1185.8	1170.4	1167.4	1164.3	1167.4	1178.1	1188.9	1192.0
22.5°	1133.6	1129.0	1113.6	1116.7	1104.4	1109.0	1105.9	1113.6	1115.2	1115.2	1125.9
25°	1072.1	1066.0	1067.5	1061.4	1056.8	1056.8	1052.2	1056.8	1062.9	1066.0	1067.5
27.5°	1026.1	1021.5	1013.8	1009.2	1012.2	1004.6	1010.7	1015.3	1015.3	1012.2	1015.3
30°	970.8	973.8	973.8	958.5	964.6	961.5	966.2	969.2	969.2	970.8	967.7
32.5°	933.9	924.7	923.1	921.6	921.6	915.5	915.5	920.1	921.6	923.1	927.8
35°	884.7	884.7	877.1	881.7	875.5	877.1	875.5	877.1	880.1	875.5	880.1
37.5°	840.2	841.7	838.7	841.7	843.3	840.2	837.1	843.3	840.2	840.2	837.1
40°	801.8	800.3	801.8	801.8	801.8	803.3	800.3	800.3	800.3	797.2	794.1
42.5°	769.5	760.3	763.4	764.9	760.3	760.3	761.9	760.3	764.9	755.7	755.7
45°	723.5	720.4	721.9	721.9	725.0	720.4	723.5	725.0	720.4	718.9	715.8
47.5°	682.0	685.1	682.0	685.1	685.1	688.1	682.0	683.5	685.1	678.9	674.3
50°	640.5	640.5	645.1	643.6	645.1	642.1	642.1	640.5	642.1	639.0	634.4
52.5°	602.1	597.5	605.2	603.7	602.1	600.6	599.0	600.6	597.5	594.4	594.4
55°	554.5	554.5	559.1	560.6	560.6	557.6	554.5	556.0	554.5	553.0	551.4
57.5°	516.1	510.0	513.0	514.6	514.6	510.0	513.0	510.0	510.0	511.5	506.9
60°	467.0	467.0	463.9	468.5	468.5	465.4	465.4	467.0	463.9	462.3	460.8
62.5°	414.7	416.3	420.9	422.4	423.9	420.9	417.8	419.3	419.3	414.7	416.3
65°	370.2	373.3	379.4	377.9	374.8	376.3	373.3	374.8	370.2	371.7	367.1
67.5°	327.2	325.6	327.2	327.2	330.2	328.7	325.6	325.6	324.1	328.7	324.1
70°	281.1	281.1	281.1	281.1	282.6	284.2	281.1	278.0	279.6	276.5	274.9
72.5°	233.5	235.0	233.5	236.5	231.9	235.0	235.0	233.5	231.9	231.9	231.9
75°	188.9	192.0	187.4	188.9	187.4	190.5	188.9	188.9	185.9	184.3	185.9
77.5°	144.4	145.9	142.9	144.4	142.9	144.4	144.4	142.9	142.9	142.9	142.9
80°	102.9	104.4	102.9	101.4	99.8	102.9	99.8	101.4	102.9	101.4	104.4
82.5°	66.0	66.0	64.5	66.0	63.0	63.0	64.5	64.5	63.0	66.0	63.0
85°	32.3	32.3	35.3	32.3	30.7	30.7	30.7	32.3	30.7	33.8	32.3
87.5°	7.7	6.1	7.7	7.7	6.1	6.1	7.7	6.1	7.7	9.2	6.1
90°	13.1	13.2	13.4	13.7	13.9	14.1	13.9	13.7	13.4	13.2	13.1
92.5°	13.6	13.7	13.8	13.9	14.0	14.1	14.0	13.9	13.8	13.7	13.6
95°	23.0	22.9	22.8	22.7	22.6	22.5	22.6	22.7	22.8	22.9	23.0
97.5°	28.2	28.3	28.4	28.5	28.7	28.8	28.7	28.5	28.4	28.3	28.2
100°	34.0	34.1	34.3	34.6	34.8	35.0	34.8	34.6	34.3	34.1	34.0
102.5°	36.6	36.8	37.1	37.5	37.8	38.2	37.8	37.5	37.1	36.8	36.6
105°	37.7	37.9	38.4	38.8	39.3	39.7	39.3	38.8	38.4	37.9	37.7
107.5°	38.7	38.9	39.4	39.9	40.3	40.8	40.3	39.9	39.4	38.9	38.7
110°	39.2	39.4	39.9	40.4	40.8	41.3	40.8	40.4	39.9	39.4	39.2

TEST NUMBER: P997911

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	40.3	40.5	40.8	41.1	41.5	41.8	41.5	41.1	40.8	40.5	40.3
115°	80.5	76.3	68.0	59.6	51.3	42.9	51.3	59.6	68.0	76.3	80.5
117.5°	276.1	260.9	230.4	200.0	169.5	139.1	169.5	200.0	230.4	260.9	276.1
120°	389.6	381.8	366.1	350.4	334.7	319.0	334.7	350.4	366.1	381.8	389.6
122.5°	417.3	417.4	417.5	417.6	417.7	417.8	417.7	417.6	417.5	417.4	417.3
125°	445.5	445.7	446.0	446.4	446.7	447.1	446.7	446.4	446.0	445.7	445.5
127.5°	472.7	472.8	472.9	473.0	473.2	473.3	473.2	473.0	472.9	472.8	472.7
130°	497.8	497.7	497.6	497.5	497.4	497.3	497.4	497.5	497.6	497.7	497.8
132.5°	521.4	521.3	521.2	521.1	521.0	520.9	521.0	521.1	521.2	521.3	521.4
135°	544.4	544.3	544.0	543.8	543.5	543.3	543.5	543.8	544.0	544.3	544.4
137.5°	565.8	565.6	565.3	565.0	564.6	564.3	564.6	565.0	565.3	565.6	565.8
140°	586.2	585.9	585.3	584.8	584.2	583.6	584.2	584.8	585.3	585.9	586.2
142.5°	605.0	604.7	604.1	603.6	603.0	602.4	603.0	603.6	604.1	604.7	605.0
145°	622.3	622.0	621.4	620.9	620.3	619.7	620.3	620.9	621.4	622.0	622.3
147.5°	637.5	637.3	636.8	636.3	635.9	635.4	635.9	636.3	636.8	637.3	637.5
150°	652.1	651.8	651.2	650.7	650.1	649.5	650.1	650.7	651.2	651.8	652.1
152.5°	665.2	664.8	664.0	663.1	662.3	661.5	662.3	663.1	664.0	664.8	665.2
155°	676.7	676.2	675.3	674.4	673.4	672.5	673.4	674.4	675.3	676.2	676.7
157.5°	687.1	686.6	685.7	684.8	683.9	683.0	683.9	684.8	685.7	686.6	687.1
160°	695.5	695.1	694.3	693.5	692.7	691.9	692.7	693.5	694.3	695.1	695.5
162.5°	703.9	703.4	702.3	701.3	700.2	699.2	700.2	701.3	702.3	703.4	703.9
165°	710.2	709.8	709.0	708.1	707.3	706.5	707.3	708.1	709.0	709.8	710.2
167.5°	715.9	715.4	714.3	713.3	712.2	711.2	712.2	713.3	714.3	715.4	715.9
170°	720.1	719.6	718.5	717.5	716.4	715.4	716.4	717.5	718.5	719.6	720.1
172.5°	723.2	722.7	721.6	720.6	719.5	718.5	719.5	720.6	721.6	722.7	723.2
175°	725.3	724.7	723.6	722.4	721.3	720.1	721.3	722.4	723.6	724.7	725.3
177.5°	725.8	725.3	724.2	723.2	722.1	721.1	722.1	723.2	724.2	725.3	725.8
180°	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7

TEST NUMBER: P997911

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4
2.5°	1897.0	1909.3	1904.7	1887.8	1907.7	1907.7	1921.6	1921.6	1938.5	1944.6	1953.8
5°	1789.5	1798.7	1806.4	1798.7	1812.5	1834.0	1846.3	1857.1	1880.1	1889.3	1903.1
7.5°	1674.3	1691.2	1698.8	1698.8	1721.9	1746.5	1771.0	1786.4	1818.6	1830.9	1844.8
10°	1562.1	1582.1	1597.5	1595.9	1634.3	1649.7	1680.4	1715.7	1748.0	1766.4	1786.4
12.5°	1443.9	1454.6	1476.1	1506.8	1516.1	1543.7	1579.0	1623.6	1681.9	1698.8	1728.0
15°	1345.6	1374.7	1391.6	1405.5	1427.0	1453.1	1491.5	1534.5	1592.9	1629.7	1660.4
17.5°	1262.6	1301.0	1311.8	1308.7	1336.3	1376.3	1420.8	1453.1	1505.3	1549.8	1579.0
20°	1195.0	1210.4	1228.8	1236.5	1258.0	1301.0	1344.0	1380.9	1423.9	1459.2	1493.0
22.5°	1127.4	1139.7	1155.1	1168.9	1185.8	1210.4	1251.9	1297.9	1339.4	1373.2	1411.6
25°	1072.1	1079.8	1093.6	1104.4	1122.8	1139.7	1168.9	1219.6	1268.8	1288.7	1322.5
27.5°	1018.4	1024.5	1033.7	1046.0	1055.2	1072.1	1098.3	1139.7	1190.4	1210.4	1256.5
30°	970.8	975.4	984.6	990.7	995.3	1015.3	1035.3	1067.5	1105.9	1133.6	1167.4
32.5°	926.2	930.8	940.0	941.6	947.7	958.5	976.9	1006.1	1039.9	1062.9	1092.1
35°	877.1	880.1	889.4	892.4	897.0	906.3	920.1	941.6	972.3	989.2	1015.3
37.5°	838.7	837.1	843.3	847.9	854.0	858.6	863.2	884.7	907.8	923.1	943.1
40°	797.2	794.1	795.7	801.8	804.9	811.0	811.0	832.5	847.9	860.2	875.5
42.5°	755.7	754.2	751.1	754.2	757.3	758.8	760.3	775.7	791.1	801.8	818.7
45°	714.3	712.7	709.6	711.2	711.2	714.3	718.9	725.0	735.8	745.0	754.2
47.5°	675.8	672.8	668.2	666.6	669.7	669.7	669.7	675.8	686.6	689.7	698.9
50°	635.9	631.3	625.2	622.1	622.1	620.6	623.6	625.2	634.4	637.4	645.1
52.5°	592.9	589.8	583.7	577.5	579.1	576.0	577.5	579.1	582.2	586.8	591.4
55°	549.9	543.8	539.1	537.6	533.0	533.0	528.4	534.5	533.0	534.5	540.7
57.5°	508.4	502.3	494.6	491.5	486.9	485.4	482.3	480.8	482.3	486.9	491.5
60°	459.3	456.2	451.6	447.0	443.9	439.3	436.2	436.2	434.7	434.7	436.2
62.5°	411.7	410.1	404.0	402.4	399.4	396.3	391.7	388.6	388.6	391.7	393.2
65°	365.6	364.0	359.4	357.9	350.2	347.1	345.6	344.1	341.0	341.0	341.0
67.5°	322.6	318.0	318.0	310.3	304.1	301.1	298.0	296.5	296.5	296.5	298.0
70°	274.9	274.9	270.3	265.7	259.6	261.1	256.5	251.9	251.9	248.8	250.4
72.5°	228.9	227.3	222.7	221.2	216.6	212.0	208.9	212.0	207.4	205.8	207.4
75°	184.3	182.8	179.7	176.6	178.2	173.6	169.0	167.4	167.4	164.4	164.4
77.5°	141.3	144.4	138.2	136.7	133.6	130.6	129.0	127.5	127.5	127.5	130.6
80°	98.3	99.8	99.8	96.8	98.3	93.7	93.7	93.7	89.1	90.6	92.2
82.5°	63.0	63.0	61.4	63.0	61.4	61.4	59.9	59.9	58.4	58.4	59.9
85°	35.3	33.8	32.3	35.3	33.8	33.8	32.3	32.3	32.3	32.3	32.3
87.5°	7.7	9.2	9.2	9.2	9.2	10.8	10.8	10.8	12.3	12.3	12.3
90°	12.8	12.2	11.7	11.1	10.5	9.6	8.6	7.7	6.8	6.3	5.7
92.5°	13.5	13.3	13.0	12.8	12.6	12.2	11.9	11.5	11.2	11.0	11.2
95°	22.7	22.1	21.6	21.0	20.4	19.6	18.8	17.9	17.1	16.7	18.6
97.5°	28.0	27.7	27.4	27.0	26.7	24.8	23.0	21.1	19.2	18.3	23.1
100°	33.5	32.6	31.7	30.7	29.8	27.8	25.8	23.9	21.9	20.9	28.9
102.5°	36.0	34.7	33.4	32.2	30.9	52.0	73.2	94.3	115.4	126.0	126.1
105°	37.1	35.8	34.5	33.2	31.9	63.6	95.4	127.1	158.8	174.7	173.0
107.5°	38.1	36.8	35.5	34.2	32.9	72.1	111.3	150.4	189.6	209.2	207.7
110°	45.0	56.6	68.3	79.9	91.5	125.1	158.7	192.2	225.8	242.6	241.4

TEST NUMBER: P997911

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	65.3	115.4	165.5	215.6	265.7	267.7	269.6	271.6	273.5	274.5	273.5
115°	107.4	161.2	215.1	268.9	322.7	319.8	316.9	314.0	311.1	309.6	308.6
117.5°	284.4	301.0	317.7	334.3	350.9	348.9	346.9	345.0	343.0	342.0	340.8
120°	388.9	387.5	386.1	384.7	383.3	381.2	379.1	377.0	374.9	373.9	373.0
122.5°	417.0	416.3	415.6	414.9	414.2	411.9	409.5	407.2	404.9	403.7	402.8
125°	445.1	444.3	443.5	442.7	441.9	439.7	437.5	435.3	433.1	432.0	431.2
127.5°	472.1	471.0	469.8	468.7	467.5	465.8	464.0	462.3	460.6	459.7	458.9
130°	497.2	495.9	494.6	493.4	492.1	490.8	489.5	488.2	486.9	486.3	485.4
132.5°	520.9	519.8	518.8	517.7	516.7	515.4	514.1	512.8	511.5	510.9	510.1
135°	543.8	542.7	541.5	540.4	539.2	538.1	537.1	536.0	534.9	534.4	533.5
137.5°	565.2	564.1	562.9	561.8	560.6	559.4	558.3	557.1	556.0	555.4	554.7
140°	585.7	584.6	583.6	582.5	581.5	580.2	579.0	577.7	576.4	575.8	575.3
142.5°	604.5	603.6	602.7	601.8	600.9	599.4	597.9	596.4	594.9	594.1	593.7
145°	621.9	621.1	620.2	619.4	618.6	616.6	614.7	612.7	610.8	609.8	609.9
147.5°	637.2	636.6	636.1	635.5	634.9	632.9	630.9	629.0	627.0	626.0	626.2
150°	651.8	651.1	650.4	649.7	649.0	647.1	645.3	643.4	641.5	640.6	641.0
152.5°	664.8	664.1	663.4	662.7	662.0	660.3	658.5	656.8	655.1	654.2	654.7
155°	676.4	675.7	675.0	674.3	673.6	672.2	670.8	669.4	668.0	667.3	667.8
157.5°	686.7	685.9	685.1	684.3	683.5	682.5	681.4	680.4	679.3	678.8	679.3
160°	695.2	694.5	693.8	693.1	692.4	691.7	691.0	690.3	689.6	689.2	689.6
162.5°	703.5	702.7	701.8	701.0	700.2	699.6	699.0	698.5	697.9	697.6	697.9
165°	709.8	709.0	708.1	707.3	706.5	706.1	705.8	705.4	705.1	704.9	705.3
167.5°	715.5	714.7	713.8	713.0	712.2	711.9	711.5	711.2	710.9	710.7	711.0
170°	719.7	718.9	718.0	717.2	716.4	716.2	716.0	715.7	715.5	715.4	715.7
172.5°	722.8	722.0	721.2	720.4	719.6	719.4	719.1	718.9	718.6	718.5	718.9
175°	724.9	724.1	723.3	722.5	721.7	721.5	721.2	721.0	720.7	720.6	721.0
177.5°	725.4	724.6	723.8	723.0	722.2	722.1	722.0	721.9	721.8	721.7	722.1
180°	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7	722.7

TEST NUMBER: P997911

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1998.4	1998.4	1998.4	1998.4
2.5°	1961.5	1961.5	1984.5	2009.1
5°	1918.5	1929.2	1966.1	1999.9
7.5°	1877.0	1895.5	1941.5	1984.5
10°	1826.3	1850.9	1907.7	1958.4
12.5°	1777.2	1800.2	1866.3	1923.1
15°	1708.1	1737.2	1807.9	1878.6
17.5°	1638.9	1668.1	1754.1	1837.1
20°	1557.5	1595.9	1692.7	1803.3
22.5°	1482.3	1529.9	1637.4	1726.5
25°	1399.3	1473.0	1572.9	1688.1
27.5°	1325.6	1399.3	1500.7	1617.4
30°	1242.6	1317.9	1422.4	1529.9
32.5°	1162.8	1231.9	1333.3	1465.4
35°	1079.8	1145.9	1244.2	1377.8
37.5°	1004.6	1069.1	1176.6	1299.5
40°	930.8	998.4	1090.6	1213.5
42.5°	861.7	921.6	1004.6	1127.4
45°	798.7	841.7	918.5	1033.7
47.5°	732.7	771.1	841.7	956.9
50°	671.2	703.5	764.9	872.5
52.5°	611.3	639.0	695.8	781.8
55°	557.6	583.7	625.2	709.6
57.5°	502.3	522.2	562.2	629.8
60°	448.5	467.0	499.2	554.5
62.5°	394.8	410.1	440.8	485.4
65°	347.1	359.4	382.5	420.9
67.5°	301.1	308.7	327.2	357.9
70°	256.5	262.7	278.0	302.6
72.5°	208.9	215.0	231.9	248.8
75°	169.0	170.5	182.8	196.6
77.5°	132.1	130.6	139.8	150.5
80°	90.6	95.2	102.9	107.5
82.5°	61.4	63.0	66.0	69.1
85°	33.8	35.3	35.3	39.9
87.5°	13.8	15.4	15.4	16.9
90°	4.4	3.1	1.8	0.5
92.5°	11.7	12.2	12.6	13.1
95°	22.5	26.3	30.2	34.0
97.5°	32.6	42.1	51.7	61.2
100°	44.8	60.7	76.7	92.6
102.5°	126.4	126.6	126.9	127.1
105°	169.5	166.0	162.5	159.0
107.5°	204.8	201.9	199.0	196.1
110°	239.0	236.5	234.1	231.7

TEST NUMBER: P997911

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	271.4	269.3	267.2	265.1
115°	306.6	304.7	302.7	300.7
117.5°	338.5	336.2	333.8	331.5
120°	371.3	369.6	367.8	366.1
122.5°	400.9	399.0	397.2	395.3
125°	429.7	428.2	426.7	425.2
127.5°	457.2	455.6	453.9	452.3
130°	483.5	481.7	479.8	478.0
132.5°	508.6	507.1	505.6	504.1
135°	531.6	529.8	527.9	526.1
137.5°	553.3	551.9	550.5	549.1
140°	574.4	573.5	572.5	571.6
142.5°	592.9	592.0	591.2	590.4
145°	610.0	610.1	610.2	610.3
147.5°	626.5	626.8	627.2	627.5
150°	641.8	642.7	643.5	644.3
152.5°	655.6	656.5	657.5	658.4
155°	668.9	669.9	671.0	672.0
157.5°	680.2	681.1	682.1	683.0
160°	690.3	691.0	691.7	692.4
162.5°	698.6	699.3	700.0	700.7
165°	706.0	706.7	707.4	708.1
167.5°	711.7	712.4	713.1	713.8
170°	716.4	717.1	717.8	718.5
172.5°	719.6	720.3	721.0	721.7
175°	721.8	722.7	723.5	724.3
177.5°	722.9	723.7	724.5	725.3
180°	722.7	722.7	722.7	722.7

TEST NUMBER: P997911

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.35	20.34	20.14	21.16	22.16	16.84	17.83	17.64	18.65	19.65
	3H	20.17	21.06	20.98	21.88	22.91	18.19	19.08	19.01	19.91	20.94
	4H	20.34	21.18	21.17	22.01	23.05	18.66	19.50	19.49	20.33	21.37
	6H	20.40	21.17	21.24	22.01	23.06	18.98	19.75	19.82	20.59	21.64
	8H	20.38	21.11	21.23	21.97	23.02	19.06	19.80	19.91	20.66	21.71
	12H	20.34	21.05	21.20	21.90	22.98	19.11	19.81	19.97	20.66	21.74
4H	2H	19.40	20.24	20.24	21.08	22.12	17.30	18.14	18.13	18.97	20.01
	3H	20.40	21.09	21.24	21.96	23.02	18.77	19.47	19.62	20.34	21.39
	4H	20.68	21.31	21.54	22.18	23.26	19.31	19.95	20.17	20.81	21.89
	6H	20.82	21.36	21.69	22.25	23.34	19.70	20.25	20.57	21.13	22.22
	8H	20.82	21.33	21.69	22.21	23.31	19.81	20.32	20.69	21.21	22.31
	12H	20.79	21.25	21.68	22.15	23.25	19.88	20.33	20.77	21.24	22.34
8H	4H	20.70	21.21	21.57	22.09	23.19	19.47	19.98	20.34	20.86	21.96
	6H	20.88	21.30	21.78	22.23	23.33	19.91	20.33	20.81	21.25	22.35
	8H	20.91	21.28	21.83	22.20	23.32	20.06	20.43	20.97	21.35	22.46
	12H	20.90	21.23	21.82	22.14	23.31	20.16	20.48	21.07	21.39	22.56
12H	4H	20.66	21.12	21.56	22.02	23.13	19.45	19.90	20.34	20.81	21.91
	6H	20.86	21.23	21.77	22.15	23.27	19.91	20.28	20.82	21.20	22.31
	8H	20.90	21.23	21.81	22.14	23.31	20.07	20.40	20.99	21.31	22.48