

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999795

Luminaire Tested: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999795
REPORT IS A COMBINATION OF REPORTS P988350 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-F_3000K
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4522.0 lumens
Efficiency: N/A
Efficacy: 100.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999795

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P999795

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45
1	95	91	88	84	86	83	80	77	67	65	63	53	52	50	40	39	38
2	87	80	74	69	79	73	68	64	59	56	53	47	45	43	36	34	33
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	26	25
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	17	16
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13007	13007	13007
5°	13028	12374	12283
10°	12900	11736	11349
15°	12723	10983	10285
20°	12488	10128	9173
25°	12247	9249	8154
30°	11924	8392	7042
35°	11610	7529	6086
40°	11287	6682	5104
45°	10913	5806	4245
50°	10527	4962	3456
55°	10126	4119	2743
60°	9659	3294	2076
65°	9122	2511	1688
70°	8471	1823	1343
75°	7653	1390	1024
80°	6475	941	687
85°	4520	430	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10913 cd/sqm

TEST NUMBER: P999795

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.0	1.7
10°-20°	211.4	4.7
20°-30°	296.8	6.6
30°-40°	323.6	7.2
40°-50°	297.4	6.6
50°-60°	233.5	5.2
60°-70°	152.0	3.4
70°-80°	78.3	1.7
80°-90°	21.7	0.5
90°-100°	31.8	0.7
100°-110°	118.7	2.6
110°-120°	314.7	7.0
120°-130°	522.0	11.5
130°-140°	554.5	12.3
140°-150°	515.4	11.4
150°-160°	414.3	9.2
160°-170°	267.0	5.9
170°-180°	91.9	2.0
0°-30°	585.3	12.9
0°-40°	908.8	20.1
0°-60°	1439.7	31.8
0°-90°	1691.7	37.4
90°-120°	465.3	10.3
90°-150°	2057.1	45.5
90°-180°	2830.0	62.6
0°-180°	4522.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	822	822	822	822	822	
5°	822	818	808	815	813	78
15°	782	773	748	734	726	220
25°	709	686	637	606	595	326
35°	611	573	508	461	445	383
45°	500	450	372	319	301	386
55°	380	322	242	197	183	340
65°	257	196	129	104	102	254
75°	137	85	60	54	54	145
85°	32	16	14	14	14	37
90°	1	8	14	18	19	4
95°	45	22	27	31	30	54
105°	212	233	43	50	53	227
115°	402	414	431	108	57	395
125°	568	577	590	595	597	507
135°	703	714	720	727	726	543
145°	815	814	826	831	828	510
155°	898	891	900	904	898	414
165°	946	942	944	949	944	267
175°	968	963	964	969	962	92
180°	965	965	965	965	965	

TEST NUMBER: P999795

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	821.7	821.7	821.7	821.7	821.7
2.5°	825.5	821.7	813.6	821.0	819.5
5°	821.7	818.0	808.3	815.0	812.8
7.5°	815.0	810.6	800.2	803.1	799.4
10°	806.1	800.9	786.0	783.8	779.3
12.5°	795.0	788.3	768.2	763.7	755.5
15°	781.6	773.4	748.1	734.0	726.5
17.5°	766.0	754.1	722.8	706.5	694.6
20°	748.1	733.2	696.1	677.5	661.1
22.5°	728.8	711.7	668.5	643.3	632.1
25°	709.4	685.6	636.6	606.1	594.9
27.5°	686.4	661.1	606.8	571.9	554.8
30°	661.8	633.6	574.1	536.2	516.1
32.5°	638.1	603.8	542.9	498.2	479.7
35°	611.3	573.4	507.9	461.1	444.7
37.5°	585.3	544.4	475.2	423.9	405.3
40°	557.7	513.1	441.0	388.2	368.9
42.5°	529.5	481.9	406.8	351.7	333.2
45°	499.7	449.9	371.8	319.0	301.2
47.5°	471.5	418.7	338.4	285.6	269.2
50°	440.2	387.4	305.6	254.3	238.7
52.5°	409.8	354.0	274.4	225.3	211.2
55°	380.0	322.0	241.7	197.1	182.9
57.5°	349.5	290.0	212.7	171.0	159.1
60°	318.3	258.8	182.2	144.3	132.4
62.5°	287.8	228.3	156.2	120.5	114.5
65°	256.6	196.3	129.4	104.1	101.9
67.5°	226.8	166.6	104.1	91.5	89.2
70°	195.6	137.6	86.3	78.8	75.9
72.5°	165.8	110.8	72.1	66.2	64.7
75°	136.8	84.8	59.5	54.3	53.5
77.5°	107.8	60.2	46.8	43.9	42.4
80°	81.1	43.1	35.7	32.7	32.7
82.5°	56.5	29.0	24.5	23.1	23.1
85°	32.0	16.4	14.1	14.1	14.1
87.5°	11.9	5.9	5.9	5.2	5.2
90°	0.7	8.4	14.0	17.5	18.9
92.5°	17.5	14.7	16.8	18.2	18.9
95°	45.4	22.4	27.2	30.7	30.0
97.5°	81.7	24.5	35.6	37.7	38.4
100°	123.6	27.9	39.8	45.4	46.8
102.5°	169.8	168.4	41.2	48.9	51.0
105°	212.4	233.3	42.6	50.3	53.1
107.5°	262.0	279.4	44.0	51.7	54.5
110°	309.5	324.1	122.3	52.4	55.2

TEST NUMBER: P999795

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	354.2	366.8	354.9	53.8	55.9
115°	401.7	413.6	431.0	107.6	57.3
117.5°	442.9	456.9	468.7	368.8	185.8
120°	489.0	499.5	512.1	520.4	426.1
122.5°	528.1	539.3	553.3	557.5	558.2
125°	567.9	577.0	590.3	595.2	597.3
127.5°	604.3	614.0	624.5	631.5	632.2
130°	638.5	649.7	657.4	665.0	664.3
132.5°	673.4	682.5	690.2	696.5	695.8
135°	702.8	713.9	720.2	727.2	725.8
137.5°	733.5	741.9	748.9	755.9	753.8
140°	763.5	769.1	776.8	783.1	779.6
142.5°	788.7	793.6	802.7	808.3	804.8
145°	815.2	814.5	826.4	831.3	827.8
147.5°	838.3	836.2	848.1	851.6	848.8
150°	860.6	855.8	866.9	871.1	867.6
152.5°	879.5	873.9	884.4	888.6	883.7
155°	897.7	891.4	899.8	904.0	898.4
157.5°	912.3	906.7	913.0	917.9	912.3
160°	924.9	920.7	924.9	929.1	924.2
162.5°	936.1	931.9	935.4	940.3	934.0
165°	945.9	941.7	943.8	948.7	943.8
167.5°	953.6	949.4	951.5	956.3	950.1
170°	959.8	955.6	957.0	961.9	955.6
172.5°	964.0	959.8	961.2	966.1	959.8
175°	967.5	962.6	964.0	968.9	961.9
177.5°	968.9	964.0	964.7	969.6	963.3
180°	965.4	965.4	965.4	965.4	965.4

(END OF REPORT)