

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999870

Luminaire Tested: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999870
REPORT IS A COMBINATION OF REPORTS P988425 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3000K
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6859.0 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999870

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P999870

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44
1	95	91	88	85	87	83	80	77	68	66	64	53	52	51	40	39	39
2	87	81	75	70	79	73	69	64	60	57	54	48	45	43	36	35	33
3	80	71	65	59	73	65	59	55	53	49	46	43	40	37	33	31	29
4	74	64	56	51	67	58	52	47	48	43	40	38	35	33	29	27	26
5	68	57	49	44	61	52	46	41	43	38	35	35	31	29	27	25	23
6	63	51	44	38	57	47	40	36	39	34	30	32	28	25	25	22	20
7	58	46	39	34	53	43	36	31	36	31	27	29	25	23	23	20	18
8	54	42	35	30	49	39	32	28	33	28	24	27	23	20	21	19	17
9	50	39	32	27	46	36	29	25	30	25	22	25	21	19	20	17	15
10	47	36	29	24	43	33	27	23	28	23	20	23	19	17	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23375	23375	23375	23375
5°	23431	24829	23511	19835
10°	23172	26244	23337	16379
15°	22670	26252	23054	12305
20°	22065	21700	22544	10152
25°	21332	13559	21793	8636
30°	20395	8682	20950	7435
35°	19256	6672	19880	6363
40°	17986	5609	18756	5566
45°	16631	4774	17326	4672
50°	15240	4056	15950	4041
55°	13699	3525	14437	3478
60°	12332	2688	12984	2655
65°	11052	2022	11710	2294
70°	9644	1615	10398	1870
75°	8151	1238	8900	1414
80°	6475	841	6962	927
85°	4492	435	4930	459

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 21383 cd/sqm

TEST NUMBER: P999870

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.1	2.0
10°-20°	391.0	5.7
20°-30°	503.2	7.3
30°-40°	477.4	7.0
40°-50°	409.1	6.0
50°-60°	311.6	4.5
60°-70°	196.5	2.9
70°-80°	98.0	1.4
80°-90°	27.8	0.4
90°-100°	48.4	0.7
100°-110°	180.5	2.6
110°-120°	478.7	7.0
120°-130°	793.9	11.6
130°-140°	843.3	12.3
140°-150°	783.8	11.4
150°-160°	630.1	9.2
160°-170°	406.0	5.9
170°-180°	139.7	2.0
0°-30°	1034.2	15.1
0°-40°	1511.6	22.0
0°-60°	2232.3	32.5
0°-90°	2554.6	37.2
90°-120°	707.6	10.3
90°-150°	3128.5	45.6
90°-180°	4304.0	62.7
0°-180°	6859.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1477	1477	1477	1477	1477	
5°	1478	1643	1483	1312	1478	140
15°	1393	1854	1416	869	1393	392
25°	1236	989	1262	630	1236	567
35°	1014	488	1047	465	1014	634
45°	762	339	793	332	762	588
55°	514	235	542	232	514	463
65°	311	122	329	138	311	309
75°	146	65	159	74	146	158
85°	32	18	35	20	32	36
90°	1	29	1	29	1	6
95°	69	46	69	46	69	82
105°	323	81	323	81	323	345
115°	611	87	611	87	611	601
125°	864	908	864	908	864	770
135°	1069	1104	1069	1104	1069	826
145°	1240	1259	1240	1259	1240	775
155°	1365	1366	1365	1366	1365	629
165°	1438	1435	1438	1435	1438	406
175°	1471	1463	1471	1463	1471	140
180°	1468	1468	1468	1468	1468	

TEST NUMBER: P999870

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7
2.5°	1486.0	1492.1	1495.2	1499.3	1508.6	1514.7	1524.0	1526.0	1525.0	1529.1	1517.8
5°	1477.8	1491.1	1503.4	1513.7	1530.1	1540.4	1551.7	1565.0	1568.1	1583.5	1574.2
7.5°	1466.5	1486.0	1503.4	1524.0	1548.6	1561.9	1579.4	1599.9	1609.1	1627.6	1632.7
10°	1448.0	1475.7	1505.5	1527.0	1560.9	1584.5	1600.9	1633.8	1655.3	1683.0	1678.9
12.5°	1418.3	1454.2	1494.2	1530.1	1574.2	1589.6	1620.4	1654.3	1682.0	1707.6	1730.2
15°	1392.6	1433.6	1477.8	1521.9	1572.2	1600.9	1631.7	1675.8	1705.6	1750.7	1770.2
17.5°	1357.7	1410.0	1462.4	1511.6	1571.2	1604.0	1642.0	1685.1	1729.2	1772.3	1787.7
20°	1321.8	1378.2	1434.7	1501.4	1569.1	1600.9	1639.9	1693.3	1736.4	1770.2	1770.2
22.5°	1278.7	1347.4	1412.1	1475.7	1549.6	1595.8	1635.8	1698.4	1729.2	1736.4	1708.7
25°	1235.6	1304.3	1375.1	1454.2	1538.3	1579.4	1624.5	1683.0	1693.3	1664.5	1592.7
27.5°	1184.3	1261.2	1341.3	1426.5	1514.7	1566.0	1607.1	1646.1	1626.6	1549.6	1437.7
30°	1131.9	1215.1	1305.4	1386.4	1493.2	1540.4	1575.3	1586.6	1525.0	1399.8	1255.1
32.5°	1077.5	1158.6	1254.1	1351.5	1459.3	1504.5	1527.0	1497.3	1384.4	1226.3	1049.8
35°	1013.9	1105.3	1204.8	1306.4	1413.1	1447.0	1460.3	1387.5	1242.8	1038.5	863.1
37.5°	956.4	1047.8	1154.5	1258.2	1361.8	1380.3	1366.9	1253.0	1069.3	867.2	695.8
40°	888.7	986.2	1090.9	1206.8	1292.0	1297.2	1264.3	1116.5	888.7	698.9	593.2
42.5°	826.1	924.6	1029.3	1147.3	1212.0	1194.5	1150.4	956.4	742.0	602.4	517.2
45°	761.5	854.9	967.7	1072.4	1118.6	1077.5	1010.8	804.6	622.9	518.2	452.6
47.5°	698.9	786.1	898.0	998.5	1006.7	960.6	881.5	674.2	539.8	455.6	402.3
50°	637.3	724.5	829.2	912.3	904.1	840.5	751.2	586.0	469.0	402.3	358.2
52.5°	575.7	654.7	756.3	822.0	787.1	725.5	637.3	496.7	409.5	351.0	317.1
55°	514.1	588.0	675.3	729.6	674.2	603.4	540.8	425.9	355.1	307.9	282.2
57.5°	462.8	521.3	601.4	634.2	567.5	512.1	457.7	366.4	307.9	274.0	244.2
60°	406.4	459.8	525.4	544.9	476.2	431.0	384.8	309.9	263.7	234.0	214.5
62.5°	358.2	402.3	452.6	452.6	392.0	358.2	323.3	259.6	221.7	198.1	188.8
65°	310.9	342.8	378.7	374.6	323.3	293.5	265.8	214.5	185.7	169.3	160.1
67.5°	264.8	289.4	313.0	298.6	261.7	236.0	210.4	173.4	153.9	142.6	130.3
70°	222.7	242.2	254.5	241.2	204.2	182.7	164.2	139.6	124.2	109.8	102.6
72.5°	186.8	195.0	199.1	182.7	151.9	139.6	126.2	108.8	95.4	88.3	86.2
75°	145.7	152.9	149.8	137.5	111.9	102.6	92.4	80.0	77.0	72.9	70.8
77.5°	113.9	113.9	108.8	97.5	80.0	72.9	68.8	62.6	59.5	58.5	56.4
80°	81.1	80.0	77.0	64.7	54.4	50.3	50.3	46.2	45.2	43.1	43.1
82.5°	53.4	53.4	49.3	39.0	35.9	34.9	33.9	31.8	31.8	30.8	30.8
85°	31.8	29.8	24.6	21.6	20.5	20.5	19.5	18.5	19.5	18.5	18.5
87.5°	14.4	11.3	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2
90°	1.1	3.7	6.3	8.8	11.4	12.7	13.6	15.5	17.4	19.3	21.2
92.5°	26.6	25.6	24.7	23.7	22.8	22.3	22.7	23.4	24.1	24.8	25.5
95°	69.1	61.3	53.5	45.7	37.9	34.0	34.8	36.5	38.1	39.8	41.4
97.5°	124.3	104.9	85.6	66.2	46.9	37.2	39.1	42.9	46.6	50.4	54.2
100°	188.0	155.7	123.3	91.0	58.7	42.5	44.5	48.5	52.6	56.6	60.6
102.5°	258.2	257.7	257.2	256.7	256.2	256.0	234.5	191.6	148.6	105.7	62.7
105°	323.0	330.1	337.1	344.2	351.3	354.8	322.6	258.1	193.7	129.2	64.8
107.5°	398.4	404.3	410.2	416.1	422.0	425.0	385.2	305.6	226.1	146.5	66.9
110°	470.6	475.6	480.6	485.5	490.5	493.0	458.9	390.6	322.4	254.1	185.9

TEST NUMBER: P999870

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	538.6	542.9	547.1	551.4	555.7	557.8	555.8	551.8	547.7	543.7	539.7
115°	610.9	614.9	618.9	622.9	626.9	628.9	631.9	637.8	643.7	649.6	655.5
117.5°	673.6	678.3	683.0	687.7	692.4	694.8	696.8	700.8	704.9	708.9	712.9
120°	743.7	747.2	750.8	754.3	757.8	759.6	761.7	766.0	770.3	774.5	778.8
122.5°	803.2	807.0	810.8	814.5	818.3	820.2	822.6	827.3	832.0	836.7	841.4
125°	863.7	866.8	869.9	873.0	876.1	877.6	879.8	884.3	888.8	893.2	897.7
127.5°	919.0	922.3	925.6	928.9	932.2	933.9	935.7	939.2	942.7	946.3	949.8
130°	971.0	974.8	978.6	982.3	986.1	988.0	989.3	991.9	994.5	997.1	999.7
132.5°	1024.2	1027.3	1030.3	1033.4	1036.5	1038.0	1039.3	1041.9	1044.5	1047.1	1049.7
135°	1068.8	1072.6	1076.4	1080.1	1083.9	1085.8	1086.9	1089.0	1091.1	1093.2	1095.3
137.5°	1115.5	1118.3	1121.2	1124.0	1126.9	1128.3	1129.5	1131.8	1134.2	1136.5	1138.9
140°	1161.2	1163.1	1165.0	1166.9	1168.8	1169.7	1171.0	1173.6	1176.2	1178.8	1181.4
142.5°	1199.5	1201.1	1202.8	1204.4	1206.1	1206.9	1208.4	1211.5	1214.6	1217.6	1220.7
145°	1239.8	1239.6	1239.4	1239.1	1238.9	1238.8	1240.8	1244.8	1248.8	1252.8	1256.8
147.5°	1274.9	1274.2	1273.5	1272.8	1272.1	1271.7	1273.7	1277.7	1281.8	1285.8	1289.8
150°	1308.9	1307.3	1305.6	1304.0	1302.3	1301.5	1303.4	1307.2	1310.9	1314.7	1318.5
152.5°	1337.6	1335.7	1333.8	1331.9	1330.0	1329.1	1330.9	1334.4	1337.9	1341.5	1345.0
155°	1365.2	1363.1	1360.9	1358.8	1356.7	1355.6	1357.0	1359.9	1362.7	1365.6	1368.4
157.5°	1387.5	1385.6	1383.7	1381.8	1379.9	1379.0	1380.1	1382.2	1384.3	1386.5	1388.6
160°	1406.6	1405.2	1403.8	1402.4	1401.0	1400.3	1401.0	1402.4	1403.8	1405.2	1406.6
162.5°	1423.6	1422.2	1420.8	1419.4	1418.0	1417.3	1417.9	1419.1	1420.2	1421.4	1422.6
165°	1438.5	1437.1	1435.7	1434.2	1432.8	1432.1	1432.5	1433.2	1433.9	1434.6	1435.3
167.5°	1450.2	1448.8	1447.4	1445.9	1444.5	1443.8	1444.2	1444.9	1445.6	1446.3	1447.0
170°	1459.8	1458.4	1457.0	1455.5	1454.1	1453.4	1453.6	1454.1	1454.6	1455.0	1455.5
172.5°	1466.1	1464.7	1463.3	1461.9	1460.5	1459.8	1460.0	1460.5	1461.0	1461.4	1461.9
175°	1471.4	1469.8	1468.1	1466.5	1464.8	1464.0	1464.2	1464.7	1465.2	1465.6	1466.1
177.5°	1473.6	1471.9	1470.3	1468.6	1466.9	1466.1	1466.2	1466.5	1466.7	1467.0	1467.2
180°	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3

TEST NUMBER: P999870

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7
2.5°	1529.1	1531.1	1534.2	1548.6	1550.6	1554.7	1552.7	1552.7	1553.7	1551.7	1552.7
5°	1594.8	1597.8	1613.2	1630.7	1634.8	1630.7	1635.8	1643.0	1643.0	1643.0	1640.9
7.5°	1656.3	1667.6	1685.1	1710.7	1715.9	1721.0	1730.2	1724.1	1726.1	1735.4	1732.3
10°	1715.9	1732.3	1751.8	1773.3	1784.6	1791.8	1795.9	1805.1	1826.7	1802.1	1811.3
12.5°	1772.3	1795.9	1816.4	1840.0	1848.2	1857.5	1860.6	1868.8	1868.8	1867.7	1874.9
15°	1809.2	1830.8	1849.3	1864.7	1866.7	1864.7	1862.6	1863.6	1866.7	1854.4	1861.6
17.5°	1817.5	1819.5	1825.7	1819.5	1820.5	1799.0	1786.7	1783.6	1754.9	1755.9	1779.5
20°	1777.4	1742.5	1733.3	1699.4	1678.9	1623.5	1621.4	1606.1	1545.5	1564.0	1559.9
22.5°	1667.6	1608.1	1529.1	1490.1	1470.6	1412.1	1366.9	1335.1	1313.6	1292.0	1282.8
25°	1522.9	1426.5	1314.6	1237.6	1226.3	1172.0	1088.8	1049.8	1003.7	989.3	1013.9
27.5°	1336.2	1211.0	1084.7	966.7	945.2	895.9	853.8	826.1	772.8	769.7	771.7
30°	1082.7	956.4	850.7	773.8	720.4	697.8	670.1	649.6	628.1	636.3	638.3
32.5°	889.7	769.7	671.2	630.1	605.5	591.1	567.5	554.2	544.9	541.8	540.8
35°	707.1	627.0	582.9	542.9	528.5	518.2	500.8	494.6	486.4	487.5	487.5
37.5°	605.5	538.8	505.9	485.4	472.1	466.9	455.6	449.5	444.4	442.3	445.4
40°	522.4	476.2	455.6	437.2	425.9	423.8	417.7	410.5	404.3	405.4	408.4
42.5°	461.8	435.1	410.5	396.1	387.9	384.8	379.7	374.6	374.6	371.5	370.5
45°	413.6	392.0	371.5	358.2	353.0	348.9	342.8	341.7	337.6	338.7	339.7
47.5°	370.5	353.0	337.6	324.3	319.2	318.1	312.0	307.9	307.9	306.8	305.8
50°	331.5	314.0	300.7	293.5	286.3	284.3	283.2	282.2	280.2	280.2	281.2
52.5°	299.7	282.2	272.0	265.8	261.7	259.6	259.6	258.6	258.6	258.6	257.6
55°	264.8	250.4	242.2	240.1	238.1	237.1	236.0	234.0	233.0	235.0	233.0
57.5°	231.9	226.8	219.6	217.6	212.4	212.4	209.4	207.3	205.2	207.3	207.3
60°	206.3	199.1	195.0	188.8	184.7	180.6	175.5	174.5	172.4	171.4	170.4
62.5°	179.6	173.4	163.2	153.9	147.8	143.7	141.6	140.6	140.6	139.6	139.6
65°	149.8	135.5	130.3	127.3	126.2	125.2	123.1	122.1	123.1	122.1	123.1
67.5°	117.0	114.9	111.9	109.8	108.8	107.8	107.8	106.7	106.7	106.7	106.7
70°	101.6	96.5	95.4	93.4	93.4	92.4	92.4	92.4	92.4	91.3	93.4
72.5°	84.2	81.1	80.0	79.0	79.0	79.0	78.0	78.0	78.0	77.0	78.0
75°	68.8	67.7	65.7	65.7	64.7	65.7	64.7	64.7	63.6	64.7	64.7
77.5°	55.4	54.4	53.4	53.4	52.3	52.3	52.3	52.3	52.3	52.3	53.4
80°	42.1	41.0	40.0	41.0	40.0	41.0	40.0	40.0	41.0	40.0	40.0
82.5°	30.8	29.8	29.8	28.7	28.7	28.7	28.7	28.7	28.7	28.7	28.7
85°	18.5	17.4	17.4	18.5	17.4	18.5	17.4	17.4	17.4	18.5	18.5
87.5°	8.2	9.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	9.2
90°	22.4	23.6	24.8	26.0	26.6	26.8	27.3	27.8	28.2	28.7	28.2
92.5°	26.0	26.4	26.9	27.4	27.6	27.7	28.0	28.2	28.5	28.7	28.5
95°	42.6	43.8	44.9	46.1	46.7	46.6	46.4	46.1	45.9	45.7	45.9
97.5°	54.9	55.6	56.3	57.0	57.4	57.5	57.7	58.0	58.2	58.4	58.2
100°	62.5	64.4	66.3	68.2	69.1	69.3	69.8	70.3	70.7	71.2	70.7
102.5°	65.3	67.9	70.5	73.1	74.4	74.8	75.5	76.2	76.9	77.6	76.9
105°	67.4	70.0	72.6	75.2	76.5	77.0	77.9	78.8	79.8	80.7	79.8
107.5°	69.5	72.1	74.7	77.3	78.6	79.1	80.0	81.0	81.9	82.9	81.9
110°	162.3	138.7	115.1	91.5	79.7	80.2	81.1	82.0	83.0	83.9	83.0

TEST NUMBER: P999870

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	437.9	336.2	234.4	132.7	81.8	82.2	82.9	83.6	84.3	85.0	84.3
115°	546.2	436.9	327.6	218.3	163.6	155.1	138.1	121.1	104.1	87.1	104.1
117.5°	679.1	645.4	611.6	577.9	561.0	530.1	468.2	406.3	344.5	282.6	344.5
120°	781.6	784.4	787.3	790.1	791.5	775.6	743.7	711.8	680.0	648.1	680.0
122.5°	842.8	844.2	845.7	847.1	847.8	847.9	848.2	848.4	848.7	848.9	848.7
125°	899.4	901.0	902.7	904.4	905.2	905.6	906.3	907.0	907.7	908.4	907.7
127.5°	952.2	954.5	956.9	959.2	960.4	960.5	960.8	961.0	961.3	961.5	961.3
130°	1002.3	1004.9	1007.5	1010.1	1011.4	1011.3	1011.1	1010.8	1010.6	1010.4	1010.6
132.5°	1051.8	1053.9	1056.0	1058.1	1059.2	1059.1	1058.9	1058.6	1058.4	1058.2	1058.4
135°	1097.7	1100.1	1102.4	1104.8	1106.0	1105.8	1105.3	1104.8	1104.3	1103.8	1104.3
137.5°	1141.3	1143.6	1146.0	1148.3	1149.5	1149.1	1148.4	1147.7	1147.0	1146.3	1147.0
140°	1183.5	1185.7	1187.8	1189.9	1191.0	1190.4	1189.2	1188.1	1186.9	1185.7	1186.9
142.5°	1222.6	1224.5	1226.4	1228.3	1229.2	1228.6	1227.4	1226.3	1225.1	1223.9	1225.1
145°	1258.5	1260.1	1261.8	1263.5	1264.3	1263.7	1262.5	1261.4	1260.2	1259.0	1260.2
147.5°	1291.0	1292.2	1293.3	1294.5	1295.1	1294.6	1293.7	1292.7	1291.8	1290.8	1291.8
150°	1319.9	1321.3	1322.7	1324.1	1324.8	1324.2	1323.0	1321.9	1320.7	1319.5	1320.7
152.5°	1346.4	1347.8	1349.3	1350.7	1351.4	1350.6	1348.9	1347.3	1345.6	1344.0	1345.6
155°	1369.8	1371.2	1372.7	1374.1	1374.8	1373.9	1372.0	1370.1	1368.2	1366.3	1368.2
157.5°	1390.2	1391.9	1393.5	1395.2	1396.0	1395.1	1393.2	1391.3	1389.4	1387.5	1389.4
160°	1408.0	1409.4	1410.9	1412.3	1413.0	1412.2	1410.5	1408.9	1407.2	1405.6	1407.2
162.5°	1424.2	1425.9	1427.5	1429.2	1430.0	1428.9	1426.8	1424.7	1422.5	1420.4	1422.5
165°	1437.0	1438.6	1440.3	1442.0	1442.8	1442.0	1440.3	1438.6	1437.0	1435.3	1437.0
167.5°	1448.6	1450.3	1451.9	1453.6	1454.4	1453.3	1451.2	1449.1	1447.0	1444.9	1447.0
170°	1457.1	1458.8	1460.4	1462.1	1462.9	1461.8	1459.7	1457.6	1455.5	1453.4	1455.5
172.5°	1463.5	1465.2	1466.8	1468.5	1469.3	1468.2	1466.1	1464.0	1461.9	1459.8	1461.9
175°	1467.8	1469.4	1471.1	1472.8	1473.6	1472.4	1470.0	1467.7	1465.3	1462.9	1465.3
177.5°	1468.8	1470.5	1472.1	1473.8	1474.6	1473.5	1471.4	1469.3	1467.2	1465.1	1467.2
180°	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3

TEST NUMBER: P999870

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7
2.5°	1556.8	1549.6	1547.6	1549.6	1547.6	1548.6	1541.4	1514.7	1521.9	1510.6	1516.8
5°	1645.0	1638.9	1625.5	1623.5	1621.4	1619.4	1609.1	1585.5	1576.3	1560.9	1559.9
7.5°	1729.2	1729.2	1718.9	1711.8	1702.5	1695.3	1682.0	1647.1	1632.7	1614.3	1604.0
10°	1812.3	1785.6	1796.9	1789.7	1767.2	1763.1	1738.4	1717.9	1690.2	1671.7	1655.3
12.5°	1871.8	1863.6	1853.4	1847.2	1841.1	1827.7	1811.3	1759.0	1744.6	1707.6	1689.2
15°	1869.8	1864.7	1867.7	1867.7	1865.7	1862.6	1849.3	1811.3	1786.7	1750.7	1718.9
17.5°	1769.2	1782.6	1795.9	1805.1	1825.7	1834.9	1847.2	1824.6	1809.2	1778.5	1744.6
20°	1593.7	1626.6	1665.6	1673.8	1692.3	1746.6	1771.3	1790.8	1796.9	1786.7	1759.0
22.5°	1349.5	1377.2	1471.6	1469.6	1496.2	1560.9	1632.7	1691.2	1737.4	1763.1	1752.8
25°	1057.0	1096.0	1146.3	1184.3	1271.5	1368.0	1457.2	1550.6	1630.7	1701.5	1718.9
27.5°	799.4	850.7	890.8	941.1	985.2	1099.1	1214.0	1359.8	1453.1	1587.6	1657.4
30°	646.5	670.1	710.2	733.8	755.3	842.5	972.9	1116.5	1280.7	1435.7	1555.8
32.5°	552.1	568.5	598.3	608.6	631.1	689.6	771.7	903.1	1072.4	1260.2	1418.3
35°	495.7	513.1	519.3	528.5	547.0	583.9	640.4	735.8	888.7	1072.4	1261.2
37.5°	447.4	456.7	474.1	480.3	486.4	514.1	552.1	618.8	720.4	871.3	1080.6
40°	413.6	418.7	427.9	433.1	437.2	456.7	490.5	535.7	610.6	725.5	918.5
42.5°	377.7	383.8	390.0	396.1	401.3	416.6	437.2	480.3	530.6	617.8	757.4
45°	342.8	346.9	354.0	358.2	365.3	377.7	396.1	425.9	471.0	526.5	639.3
47.5°	310.9	316.1	319.2	324.3	329.4	342.8	360.2	379.7	416.6	471.0	553.1
50°	282.2	288.4	292.5	293.5	297.6	309.9	324.3	345.8	369.4	411.5	483.4
52.5°	261.7	262.7	265.8	269.9	268.9	276.1	289.4	305.8	330.4	364.3	416.6
55°	238.1	241.2	243.2	244.2	244.2	250.4	257.6	273.0	292.5	320.2	364.3
57.5°	208.3	211.4	217.6	219.6	222.7	225.8	228.8	239.1	255.5	282.2	318.1
60°	177.5	179.6	185.7	189.9	191.9	200.1	204.2	212.4	221.7	241.2	275.0
62.5°	142.6	144.7	147.8	151.9	156.0	168.3	178.6	186.8	194.0	207.3	235.0
65°	124.2	125.2	127.3	128.3	129.3	134.4	143.7	155.0	168.3	178.6	195.0
67.5°	107.8	108.8	109.8	111.9	112.9	113.9	118.0	121.1	134.4	148.8	161.1
70°	92.4	94.4	95.4	95.4	96.5	98.5	100.6	104.7	108.8	116.0	131.4
72.5°	78.0	79.0	81.1	81.1	81.1	83.1	85.2	87.2	89.3	93.4	99.5
75°	64.7	66.7	66.7	66.7	67.7	67.7	69.8	71.8	73.9	77.0	79.0
77.5°	53.4	53.4	53.4	53.4	54.4	54.4	55.4	57.5	58.5	59.5	61.6
80°	40.0	41.0	41.0	41.0	42.1	42.1	42.1	44.1	45.2	45.2	47.2
82.5°	29.8	29.8	29.8	30.8	29.8	30.8	30.8	31.8	30.8	31.8	32.8
85°	18.5	18.5	18.5	19.5	19.5	19.5	19.5	19.5	19.5	19.5	20.5
87.5°	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	10.3	9.2	9.2
90°	27.8	27.3	26.8	26.6	26.0	24.8	23.6	22.4	21.2	19.3	17.4
92.5°	28.2	28.0	27.7	27.6	27.4	26.9	26.4	26.0	25.5	24.8	24.1
95°	46.1	46.4	46.6	46.7	46.1	44.9	43.8	42.6	41.4	39.8	38.1
97.5°	58.0	57.7	57.5	57.4	57.0	56.3	55.6	54.9	54.2	50.4	46.6
100°	70.3	69.8	69.3	69.1	68.2	66.3	64.4	62.5	60.6	56.6	52.6
102.5°	76.2	75.5	74.8	74.4	73.1	70.5	67.9	65.3	62.7	105.7	148.6
105°	78.8	77.9	77.0	76.5	75.2	72.6	70.0	67.4	64.8	129.2	193.7
107.5°	81.0	80.0	79.1	78.6	77.3	74.7	72.1	69.5	66.9	146.5	226.1
110°	82.0	81.1	80.2	79.7	91.5	115.1	138.7	162.3	185.9	254.1	322.4

TEST NUMBER: P999870

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	83.6	82.9	82.2	81.8	132.7	234.4	336.2	437.9	539.7	543.7	547.7
115°	121.1	138.1	155.1	163.6	218.3	327.6	436.9	546.2	655.5	649.6	643.7
117.5°	406.3	468.2	530.1	561.0	577.9	611.6	645.4	679.1	712.9	708.9	704.9
120°	711.8	743.7	775.6	791.5	790.1	787.3	784.4	781.6	778.8	774.5	770.3
122.5°	848.4	848.2	847.9	847.8	847.1	845.7	844.2	842.8	841.4	836.7	832.0
125°	907.0	906.3	905.6	905.2	904.4	902.7	901.0	899.4	897.7	893.2	888.8
127.5°	961.0	960.8	960.5	960.4	959.2	956.9	954.5	952.2	949.8	946.3	942.7
130°	1010.8	1011.1	1011.3	1011.4	1010.1	1007.5	1004.9	1002.3	999.7	997.1	994.5
132.5°	1058.6	1058.9	1059.1	1059.2	1058.1	1056.0	1053.9	1051.8	1049.7	1047.1	1044.5
135°	1104.8	1105.3	1105.8	1106.0	1104.8	1102.4	1100.1	1097.7	1095.3	1093.2	1091.1
137.5°	1147.7	1148.4	1149.1	1149.5	1148.3	1146.0	1143.6	1141.3	1138.9	1136.5	1134.2
140°	1188.1	1189.2	1190.4	1191.0	1189.9	1187.8	1185.7	1183.5	1181.4	1178.8	1176.2
142.5°	1226.3	1227.4	1228.6	1229.2	1228.3	1226.4	1224.5	1222.6	1220.7	1217.6	1214.6
145°	1261.4	1262.5	1263.7	1264.3	1263.5	1261.8	1260.1	1258.5	1256.8	1252.8	1248.8
147.5°	1292.7	1293.7	1294.6	1295.1	1294.5	1293.3	1292.2	1291.0	1289.8	1285.8	1281.8
150°	1321.9	1323.0	1324.2	1324.8	1324.1	1322.7	1321.3	1319.9	1318.5	1314.7	1310.9
152.5°	1347.3	1348.9	1350.6	1351.4	1350.7	1349.3	1347.8	1346.4	1345.0	1341.5	1337.9
155°	1370.1	1372.0	1373.9	1374.8	1374.1	1372.7	1371.2	1369.8	1368.4	1365.6	1362.7
157.5°	1391.3	1393.2	1395.1	1396.0	1395.2	1393.5	1391.9	1390.2	1388.6	1386.5	1384.3
160°	1408.9	1410.5	1412.2	1413.0	1412.3	1410.9	1409.4	1408.0	1406.6	1405.2	1403.8
162.5°	1424.7	1426.8	1428.9	1430.0	1429.2	1427.5	1425.9	1424.2	1422.6	1421.4	1420.2
165°	1438.6	1440.3	1442.0	1442.8	1442.0	1440.3	1438.6	1437.0	1435.3	1434.6	1433.9
167.5°	1449.1	1451.2	1453.3	1454.4	1453.6	1451.9	1450.3	1448.6	1447.0	1446.3	1445.6
170°	1457.6	1459.7	1461.8	1462.9	1462.1	1460.4	1458.8	1457.1	1455.5	1455.0	1454.6
172.5°	1464.0	1466.1	1468.2	1469.3	1468.5	1466.8	1465.2	1463.5	1461.9	1461.4	1461.0
175°	1467.7	1470.0	1472.4	1473.6	1472.8	1471.1	1469.4	1467.8	1466.1	1465.6	1465.2
177.5°	1469.3	1471.4	1473.5	1474.6	1473.8	1472.1	1470.5	1468.8	1467.2	1467.0	1466.7
180°	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3

TEST NUMBER: P999870

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7
2.5°	1507.5	1502.4	1502.4	1499.3	1499.3	1482.9	1482.9	1488.0	1481.9	1474.7	1464.4
5°	1546.5	1535.2	1532.2	1528.1	1514.7	1494.2	1486.0	1482.9	1470.6	1455.2	1437.7
7.5°	1583.5	1565.0	1555.8	1546.5	1529.1	1500.3	1483.9	1472.6	1454.2	1430.6	1408.0
10°	1619.4	1595.8	1572.2	1560.9	1536.3	1500.3	1476.7	1458.3	1431.6	1399.8	1368.0
12.5°	1652.2	1603.0	1598.9	1576.3	1540.4	1499.3	1463.4	1436.7	1402.9	1365.9	1329.0
15°	1681.0	1630.7	1606.1	1585.5	1538.3	1487.0	1449.0	1416.2	1371.0	1329.0	1283.8
17.5°	1695.3	1640.9	1624.5	1590.7	1542.4	1475.7	1424.4	1384.4	1335.1	1284.8	1233.5
20°	1709.7	1646.1	1619.4	1595.8	1530.1	1454.2	1396.7	1350.5	1296.1	1236.6	1180.2
22.5°	1716.9	1646.1	1614.3	1581.4	1517.8	1430.6	1362.8	1308.4	1244.8	1184.3	1116.5
25°	1704.6	1639.9	1601.9	1568.1	1496.2	1401.8	1323.8	1262.3	1194.5	1125.8	1057.0
27.5°	1673.8	1625.5	1581.4	1546.5	1466.5	1364.9	1282.8	1213.0	1143.2	1066.3	996.5
30°	1616.3	1594.8	1559.9	1520.9	1433.6	1332.0	1234.6	1162.7	1085.8	1008.8	935.9
32.5°	1527.0	1545.5	1522.9	1489.1	1394.6	1286.9	1183.2	1110.4	1026.2	943.1	876.4
35°	1418.3	1483.9	1471.6	1448.0	1353.6	1238.7	1135.0	1046.8	962.6	878.5	811.7
37.5°	1299.2	1398.8	1409.0	1394.6	1306.4	1189.4	1075.5	989.3	903.1	817.9	750.2
40°	1136.0	1288.9	1321.8	1327.9	1257.1	1129.9	1010.8	926.7	841.5	758.4	676.3
42.5°	986.2	1179.1	1220.2	1245.8	1194.5	1071.4	951.3	857.9	773.8	698.9	616.8
45°	845.6	1046.8	1113.5	1146.3	1123.7	1004.7	880.5	793.3	716.3	647.6	568.5
47.5°	700.9	903.1	996.5	1048.8	1048.8	936.9	812.8	726.6	652.7	594.2	524.4
50°	604.4	772.8	869.2	938.0	956.4	868.2	751.2	667.0	597.3	533.6	480.3
52.5°	515.2	666.0	746.1	817.9	871.3	794.3	682.4	606.5	537.7	478.2	436.1
55°	445.4	558.3	631.1	710.2	769.7	719.4	615.7	541.8	482.3	433.1	397.2
57.5°	378.7	477.2	536.7	606.5	670.1	632.2	549.0	485.4	433.1	390.0	358.2
60°	322.2	402.3	448.5	502.9	581.9	555.2	486.4	427.9	385.9	346.9	320.2
62.5°	274.0	337.6	376.6	415.6	487.5	475.1	421.8	376.6	340.7	307.9	285.3
65°	224.7	277.1	307.9	341.7	399.2	404.3	361.2	329.4	296.6	267.8	247.3
67.5°	181.6	222.7	250.4	279.1	325.3	339.7	309.9	283.2	255.5	231.9	213.5
70°	146.8	175.5	196.0	218.6	256.6	274.0	258.6	240.1	217.6	198.1	181.6
72.5°	116.0	134.4	146.8	164.2	195.0	212.4	211.4	195.0	178.6	165.2	151.9
75°	85.2	99.5	109.8	121.1	145.7	162.1	166.2	159.1	142.6	132.4	122.1
77.5°	64.7	72.9	78.0	86.2	103.6	118.0	124.2	122.1	110.8	102.6	95.4
80°	49.3	51.3	53.4	56.4	70.8	84.2	88.3	87.2	81.1	78.0	69.8
82.5°	34.9	35.9	36.9	38.0	43.1	54.4	58.5	60.5	55.4	52.3	45.2
85°	20.5	21.6	21.6	23.6	24.6	27.7	34.9	34.9	33.9	29.8	28.7
87.5°	10.3	10.3	9.2	9.2	10.3	11.3	13.3	15.4	13.3	12.3	11.3
90°	15.5	13.6	12.7	11.4	8.8	6.3	3.7	1.1	3.7	6.3	8.8
92.5°	23.4	22.7	22.3	22.8	23.7	24.7	25.6	26.6	25.6	24.7	23.7
95°	36.5	34.8	34.0	37.9	45.7	53.5	61.3	69.1	61.3	53.5	45.7
97.5°	42.9	39.1	37.2	46.9	66.2	85.6	104.9	124.3	104.9	85.6	66.2
100°	48.5	44.5	42.5	58.7	91.0	123.3	155.7	188.0	155.7	123.3	91.0
102.5°	191.6	234.5	256.0	256.2	256.7	257.2	257.7	258.2	257.7	257.2	256.7
105°	258.1	322.6	354.8	351.3	344.2	337.1	330.1	323.0	330.1	337.1	344.2
107.5°	305.6	385.2	425.0	422.0	416.1	410.2	404.3	398.4	404.3	410.2	416.1
110°	390.6	458.9	493.0	490.5	485.5	480.6	475.6	470.6	475.6	480.6	485.5

TEST NUMBER: P999870

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	551.8	555.8	557.8	555.7	551.4	547.1	542.9	538.6	542.9	547.1	551.4
115°	637.8	631.9	628.9	626.9	622.9	618.9	614.9	610.9	614.9	618.9	622.9
117.5°	700.8	696.8	694.8	692.4	687.7	683.0	678.3	673.6	678.3	683.0	687.7
120°	766.0	761.7	759.6	757.8	754.3	750.8	747.2	743.7	747.2	750.8	754.3
122.5°	827.3	822.6	820.2	818.3	814.5	810.8	807.0	803.2	807.0	810.8	814.5
125°	884.3	879.8	877.6	876.1	873.0	869.9	866.8	863.7	866.8	869.9	873.0
127.5°	939.2	935.7	933.9	932.2	928.9	925.6	922.3	919.0	922.3	925.6	928.9
130°	991.9	989.3	988.0	986.1	982.3	978.6	974.8	971.0	974.8	978.6	982.3
132.5°	1041.9	1039.3	1038.0	1036.5	1033.4	1030.3	1027.3	1024.2	1027.3	1030.3	1033.4
135°	1089.0	1086.9	1085.8	1083.9	1080.1	1076.4	1072.6	1068.8	1072.6	1076.4	1080.1
137.5°	1131.8	1129.5	1128.3	1126.9	1124.0	1121.2	1118.3	1115.5	1118.3	1121.2	1124.0
140°	1173.6	1171.0	1169.7	1168.8	1166.9	1165.0	1163.1	1161.2	1163.1	1165.0	1166.9
142.5°	1211.5	1208.4	1206.9	1206.1	1204.4	1202.8	1201.1	1199.5	1201.1	1202.8	1204.4
145°	1244.8	1240.8	1238.8	1238.9	1239.1	1239.4	1239.6	1239.8	1239.6	1239.4	1239.1
147.5°	1277.7	1273.7	1271.7	1272.1	1272.8	1273.5	1274.2	1274.9	1274.2	1273.5	1272.8
150°	1307.2	1303.4	1301.5	1302.3	1304.0	1305.6	1307.3	1308.9	1307.3	1305.6	1304.0
152.5°	1334.4	1330.9	1329.1	1330.0	1331.9	1333.8	1335.7	1337.6	1335.7	1333.8	1331.9
155°	1359.9	1357.0	1355.6	1356.7	1358.8	1360.9	1363.1	1365.2	1363.1	1360.9	1358.8
157.5°	1382.2	1380.1	1379.0	1379.9	1381.8	1383.7	1385.6	1387.5	1385.6	1383.7	1381.8
160°	1402.4	1401.0	1400.3	1401.0	1402.4	1403.8	1405.2	1406.6	1405.2	1403.8	1402.4
162.5°	1419.1	1417.9	1417.3	1418.0	1419.4	1420.8	1422.2	1423.6	1422.2	1420.8	1419.4
165°	1433.2	1432.5	1432.1	1432.8	1434.2	1435.7	1437.1	1438.5	1437.1	1435.7	1434.2
167.5°	1444.9	1444.2	1443.8	1444.5	1445.9	1447.4	1448.8	1450.2	1448.8	1447.4	1445.9
170°	1454.1	1453.6	1453.4	1454.1	1455.5	1457.0	1458.4	1459.8	1458.4	1457.0	1455.5
172.5°	1460.5	1460.0	1459.8	1460.5	1461.9	1463.3	1464.7	1466.1	1464.7	1463.3	1461.9
175°	1464.7	1464.2	1464.0	1464.8	1466.5	1468.1	1469.8	1471.4	1469.8	1468.1	1466.5
177.5°	1466.5	1466.2	1466.1	1466.9	1468.6	1470.3	1471.9	1473.6	1471.9	1470.3	1468.6
180°	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3

TEST NUMBER: P999870

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7
2.5°	1460.3	1461.4	1464.4	1455.2	1440.8	1434.7	1416.2	1413.1	1410.0	1410.0	1413.1
5°	1427.5	1423.4	1424.4	1407.0	1386.4	1374.1	1348.5	1352.6	1339.2	1331.0	1333.1
7.5°	1391.6	1380.3	1379.3	1356.7	1331.0	1308.4	1281.8	1275.6	1263.3	1248.9	1242.8
10°	1346.4	1338.2	1322.8	1297.2	1264.3	1245.8	1209.9	1188.4	1185.3	1163.7	1155.5
12.5°	1300.2	1285.9	1270.5	1234.6	1197.6	1167.9	1141.2	1117.6	1101.1	1082.7	1070.4
15°	1246.9	1229.4	1212.0	1174.0	1130.9	1101.1	1061.1	1026.2	978.0	940.0	918.5
17.5°	1188.4	1168.9	1145.3	1103.2	1061.1	1020.1	946.2	905.1	871.3	848.7	835.4
20°	1127.8	1106.3	1082.7	1040.6	967.7	895.9	854.9	823.0	802.5	779.9	763.5
22.5°	1064.2	1041.6	1016.0	950.3	873.3	823.0	791.2	761.5	731.7	719.4	711.2
25°	1004.7	984.2	951.3	862.0	801.5	755.3	719.4	699.9	684.5	668.1	652.7
27.5°	943.1	905.1	859.0	784.0	746.1	698.9	673.2	658.8	632.2	620.9	613.7
30°	869.2	827.1	783.0	729.6	685.5	652.7	629.1	605.5	590.1	578.8	566.5
32.5°	794.3	754.3	726.6	671.2	638.3	604.4	581.9	567.5	544.9	537.7	532.6
35°	729.6	695.8	671.2	626.0	595.2	564.4	548.0	526.5	512.1	498.7	490.5
37.5°	666.0	647.6	621.9	583.9	551.1	526.5	503.9	496.7	477.2	470.0	461.8
40°	621.9	594.2	572.6	539.8	512.1	485.4	471.0	454.6	441.3	430.0	426.9
42.5°	568.5	548.0	535.7	499.8	471.0	455.6	438.2	419.7	409.5	400.2	388.9
45°	528.5	510.0	492.6	463.9	438.2	418.7	403.3	391.0	373.5	369.4	352.0
47.5°	486.4	468.0	454.6	425.9	402.3	383.8	372.5	356.1	341.7	332.5	324.3
50°	444.4	429.0	416.6	392.0	371.5	352.0	336.6	320.2	314.0	298.6	293.5
52.5°	404.3	394.1	380.7	357.1	336.6	320.2	303.8	290.4	281.2	273.0	266.8
55°	370.5	354.0	347.9	322.2	304.8	287.3	273.0	264.8	253.5	248.3	243.2
57.5°	332.5	323.3	313.0	293.5	274.0	257.6	247.3	235.0	228.8	222.7	218.6
60°	299.7	286.3	278.1	261.7	244.2	228.8	219.6	210.4	202.2	197.0	188.8
62.5°	261.7	251.4	246.3	228.8	214.5	200.1	191.9	182.7	176.5	167.3	157.0
65°	228.8	220.6	214.5	200.1	186.8	173.4	165.2	153.9	145.7	140.6	139.6
67.5°	200.1	194.0	184.7	171.4	158.0	147.8	138.5	129.3	128.3	126.2	126.2
70°	168.3	162.1	157.0	142.6	131.4	120.1	118.0	114.9	111.9	110.8	108.8
72.5°	140.6	135.5	129.3	117.0	105.7	102.6	100.6	98.5	95.4	94.4	93.4
75°	113.9	106.7	102.6	91.3	88.3	86.2	84.2	81.1	79.0	78.0	75.9
77.5°	87.2	80.0	80.0	73.9	71.8	68.8	66.7	64.7	63.6	61.6	61.6
80°	61.6	61.6	59.5	56.4	53.4	52.3	49.3	48.2	47.2	48.2	46.2
82.5°	45.2	41.0	41.0	39.0	36.9	35.9	33.9	33.9	32.8	32.8	32.8
85°	25.7	25.7	24.6	22.6	21.6	21.6	20.5	20.5	19.5	19.5	18.5
87.5°	10.3	9.2	10.3	9.2	9.2	8.2	8.2	8.2	7.2	8.2	7.2
90°	11.4	12.7	13.6	15.5	17.4	19.3	21.2	22.4	23.6	24.8	26.0
92.5°	22.8	22.3	22.7	23.4	24.1	24.8	25.5	26.0	26.4	26.9	27.4
95°	37.9	34.0	34.8	36.5	38.1	39.8	41.4	42.6	43.8	44.9	46.1
97.5°	46.9	37.2	39.1	42.9	46.6	50.4	54.2	54.9	55.6	56.3	57.0
100°	58.7	42.5	44.5	48.5	52.6	56.6	60.6	62.5	64.4	66.3	68.2
102.5°	256.2	256.0	234.5	191.6	148.6	105.7	62.7	65.3	67.9	70.5	73.1
105°	351.3	354.8	322.6	258.1	193.7	129.2	64.8	67.4	70.0	72.6	75.2
107.5°	422.0	425.0	385.2	305.6	226.1	146.5	66.9	69.5	72.1	74.7	77.3
110°	490.5	493.0	458.9	390.6	322.4	254.1	185.9	162.3	138.7	115.1	91.5

TEST NUMBER: P999870

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	555.7	557.8	555.8	551.8	547.7	543.7	539.7	437.9	336.2	234.4	132.7
115°	626.9	628.9	631.9	637.8	643.7	649.6	655.5	546.2	436.9	327.6	218.3
117.5°	692.4	694.8	696.8	700.8	704.9	708.9	712.9	679.1	645.4	611.6	577.9
120°	757.8	759.6	761.7	766.0	770.3	774.5	778.8	781.6	784.4	787.3	790.1
122.5°	818.3	820.2	822.6	827.3	832.0	836.7	841.4	842.8	844.2	845.7	847.1
125°	876.1	877.6	879.8	884.3	888.8	893.2	897.7	899.4	901.0	902.7	904.4
127.5°	932.2	933.9	935.7	939.2	942.7	946.3	949.8	952.2	954.5	956.9	959.2
130°	986.1	988.0	989.3	991.9	994.5	997.1	999.7	1002.3	1004.9	1007.5	1010.1
132.5°	1036.5	1038.0	1039.3	1041.9	1044.5	1047.1	1049.7	1051.8	1053.9	1056.0	1058.1
135°	1083.9	1085.8	1086.9	1089.0	1091.1	1093.2	1095.3	1097.7	1100.1	1102.4	1104.8
137.5°	1126.9	1128.3	1129.5	1131.8	1134.2	1136.5	1138.9	1141.3	1143.6	1146.0	1148.3
140°	1168.8	1169.7	1171.0	1173.6	1176.2	1178.8	1181.4	1183.5	1185.7	1187.8	1189.9
142.5°	1206.1	1206.9	1208.4	1211.5	1214.6	1217.6	1220.7	1222.6	1224.5	1226.4	1228.3
145°	1238.9	1238.8	1240.8	1244.8	1248.8	1252.8	1256.8	1258.5	1260.1	1261.8	1263.5
147.5°	1272.1	1271.7	1273.7	1277.7	1281.8	1285.8	1289.8	1291.0	1292.2	1293.3	1294.5
150°	1302.3	1301.5	1303.4	1307.2	1310.9	1314.7	1318.5	1319.9	1321.3	1322.7	1324.1
152.5°	1330.0	1329.1	1330.9	1334.4	1337.9	1341.5	1345.0	1346.4	1347.8	1349.3	1350.7
155°	1356.7	1355.6	1357.0	1359.9	1362.7	1365.6	1368.4	1369.8	1371.2	1372.7	1374.1
157.5°	1379.9	1379.0	1380.1	1382.2	1384.3	1386.5	1388.6	1390.2	1391.9	1393.5	1395.2
160°	1401.0	1400.3	1401.0	1402.4	1403.8	1405.2	1406.6	1408.0	1409.4	1410.9	1412.3
162.5°	1418.0	1417.3	1417.9	1419.1	1420.2	1421.4	1422.6	1424.2	1425.9	1427.5	1429.2
165°	1432.8	1432.1	1432.5	1433.2	1433.9	1434.6	1435.3	1437.0	1438.6	1440.3	1442.0
167.5°	1444.5	1443.8	1444.2	1444.9	1445.6	1446.3	1447.0	1448.6	1450.3	1451.9	1453.6
170°	1454.1	1453.4	1453.6	1454.1	1454.6	1455.0	1455.5	1457.1	1458.8	1460.4	1462.1
172.5°	1460.5	1459.8	1460.0	1460.5	1461.0	1461.4	1461.9	1463.5	1465.2	1466.8	1468.5
175°	1464.8	1464.0	1464.2	1464.7	1465.2	1465.6	1466.1	1467.8	1469.4	1471.1	1472.8
177.5°	1466.9	1466.1	1466.2	1466.5	1466.7	1467.0	1467.2	1468.8	1470.5	1472.1	1473.8
180°	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3

TEST NUMBER: P999870

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7
2.5°	1413.1	1411.1	1404.9	1407.0	1403.9	1403.9	1401.8	1401.8	1401.8	1407.0	1403.9
5°	1336.2	1329.0	1321.8	1318.7	1315.6	1312.5	1312.5	1311.5	1320.8	1318.7	1326.9
7.5°	1240.7	1238.7	1224.3	1224.3	1219.2	1217.1	1222.2	1223.3	1224.3	1226.3	1231.5
10°	1155.5	1150.4	1129.9	1131.9	1128.9	1124.7	1127.8	1125.8	1133.0	1135.0	1133.0
12.5°	1055.0	1045.7	1023.2	1011.9	999.5	990.3	1001.6	993.4	1022.1	1030.3	1052.9
15°	921.6	904.1	888.7	888.7	877.4	869.2	874.3	883.6	889.7	899.0	903.1
17.5°	832.3	825.1	812.8	805.6	802.5	799.4	799.4	803.5	816.9	815.9	824.1
20°	756.3	752.2	746.1	736.8	733.8	731.7	731.7	731.7	740.9	749.1	754.3
22.5°	704.0	700.9	696.8	684.5	678.3	676.3	681.4	684.5	691.7	697.8	703.0
25°	651.7	644.5	637.3	633.2	630.1	630.1	632.2	633.2	636.3	639.3	645.5
27.5°	608.6	603.4	593.2	581.9	581.9	578.8	580.8	582.9	590.1	600.3	605.5
30°	560.3	559.3	555.2	551.1	547.0	544.9	549.0	552.1	553.1	558.3	558.3
32.5°	525.4	518.2	511.1	507.0	504.9	503.9	504.9	509.0	509.0	515.2	522.4
35°	490.5	486.4	479.2	472.1	470.0	464.9	469.0	473.1	480.3	483.4	486.4
37.5°	452.6	447.4	444.4	442.3	438.2	439.2	436.1	442.3	448.5	447.4	449.5
40°	423.8	414.6	405.4	404.3	403.3	402.3	402.3	403.3	407.4	411.5	417.7
42.5°	386.9	383.8	375.6	367.4	365.3	363.3	361.2	365.3	373.5	380.7	383.8
45°	348.9	344.8	342.8	336.6	332.5	331.5	329.4	334.6	341.7	344.8	346.9
47.5°	314.0	313.0	306.8	307.9	304.8	305.8	304.8	307.9	307.9	310.9	313.0
50°	290.4	287.3	284.3	282.2	279.1	279.1	278.1	279.1	283.2	287.3	286.3
52.5°	266.8	261.7	260.7	259.6	257.6	259.6	256.6	257.6	261.7	263.7	262.7
55°	239.1	238.1	236.0	234.0	233.0	231.9	231.9	231.9	236.0	239.1	240.1
57.5°	217.6	212.4	208.3	208.3	204.2	203.2	205.2	206.3	209.4	211.4	213.5
60°	187.8	185.7	179.6	176.5	170.4	169.3	169.3	173.4	178.6	185.7	187.8
62.5°	156.0	152.9	151.9	151.9	151.9	151.9	151.9	151.9	151.9	152.9	152.9
65°	138.5	139.6	138.5	137.5	138.5	138.5	137.5	137.5	137.5	138.5	139.6
67.5°	124.2	123.1	124.2	123.1	122.1	122.1	121.1	122.1	123.1	124.2	124.2
70°	107.8	107.8	106.7	107.8	106.7	105.7	104.7	104.7	106.7	107.8	107.8
72.5°	92.4	92.4	91.3	91.3	89.3	89.3	90.3	89.3	89.3	92.4	92.4
75°	77.0	75.9	74.9	74.9	73.9	73.9	73.9	72.9	74.9	74.9	75.9
77.5°	60.5	60.5	60.5	59.5	59.5	58.5	58.5	59.5	59.5	59.5	60.5
80°	46.2	46.2	46.2	45.2	44.1	44.1	44.1	44.1	44.1	45.2	44.1
82.5°	31.8	31.8	31.8	31.8	31.8	30.8	30.8	30.8	31.8	31.8	30.8
85°	19.5	18.5	19.5	19.5	18.5	19.5	18.5	18.5	17.4	17.4	18.5
87.5°	8.2	7.2	6.2	6.2	7.2	6.2	6.2	6.2	7.2	6.2	6.2
90°	26.6	26.8	27.3	27.8	28.2	28.7	28.2	27.8	27.3	26.8	26.6
92.5°	27.6	27.7	28.0	28.2	28.5	28.7	28.5	28.2	28.0	27.7	27.6
95°	46.7	46.6	46.4	46.1	45.9	45.7	45.9	46.1	46.4	46.6	46.7
97.5°	57.4	57.5	57.7	58.0	58.2	58.4	58.2	58.0	57.7	57.5	57.4
100°	69.1	69.3	69.8	70.3	70.7	71.2	70.7	70.3	69.8	69.3	69.1
102.5°	74.4	74.8	75.5	76.2	76.9	77.6	76.9	76.2	75.5	74.8	74.4
105°	76.5	77.0	77.9	78.8	79.8	80.7	79.8	78.8	77.9	77.0	76.5
107.5°	78.6	79.1	80.0	81.0	81.9	82.9	81.9	81.0	80.0	79.1	78.6
110°	79.7	80.2	81.1	82.0	83.0	83.9	83.0	82.0	81.1	80.2	79.7

TEST NUMBER: P999870

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	81.8	82.2	82.9	83.6	84.3	85.0	84.3	83.6	82.9	82.2	81.8
115°	163.6	155.1	138.1	121.1	104.1	87.1	104.1	121.1	138.1	155.1	163.6
117.5°	561.0	530.1	468.2	406.3	344.5	282.6	344.5	406.3	468.2	530.1	561.0
120°	791.5	775.6	743.7	711.8	680.0	648.1	680.0	711.8	743.7	775.6	791.5
122.5°	847.8	847.9	848.2	848.4	848.7	848.9	848.7	848.4	848.2	847.9	847.8
125°	905.2	905.6	906.3	907.0	907.7	908.4	907.7	907.0	906.3	905.6	905.2
127.5°	960.4	960.5	960.8	961.0	961.3	961.5	961.3	961.0	960.8	960.5	960.4
130°	1011.4	1011.3	1011.1	1010.8	1010.6	1010.4	1010.6	1010.8	1011.1	1011.3	1011.4
132.5°	1059.2	1059.1	1058.9	1058.6	1058.4	1058.2	1058.4	1058.6	1058.9	1059.1	1059.2
135°	1106.0	1105.8	1105.3	1104.8	1104.3	1103.8	1104.3	1104.8	1105.3	1105.8	1106.0
137.5°	1149.5	1149.1	1148.4	1147.7	1147.0	1146.3	1147.0	1147.7	1148.4	1149.1	1149.5
140°	1191.0	1190.4	1189.2	1188.1	1186.9	1185.7	1186.9	1188.1	1189.2	1190.4	1191.0
142.5°	1229.2	1228.6	1227.4	1226.3	1225.1	1223.9	1225.1	1226.3	1227.4	1228.6	1229.2
145°	1264.3	1263.7	1262.5	1261.4	1260.2	1259.0	1260.2	1261.4	1262.5	1263.7	1264.3
147.5°	1295.1	1294.6	1293.7	1292.7	1291.8	1290.8	1291.8	1292.7	1293.7	1294.6	1295.1
150°	1324.8	1324.2	1323.0	1321.9	1320.7	1319.5	1320.7	1321.9	1323.0	1324.2	1324.8
152.5°	1351.4	1350.6	1348.9	1347.3	1345.6	1344.0	1345.6	1347.3	1348.9	1350.6	1351.4
155°	1374.8	1373.9	1372.0	1370.1	1368.2	1366.3	1368.2	1370.1	1372.0	1373.9	1374.8
157.5°	1396.0	1395.1	1393.2	1391.3	1389.4	1387.5	1389.4	1391.3	1393.2	1395.1	1396.0
160°	1413.0	1412.2	1410.5	1408.9	1407.2	1405.6	1407.2	1408.9	1410.5	1412.2	1413.0
162.5°	1430.0	1428.9	1426.8	1424.7	1422.5	1420.4	1422.5	1424.7	1426.8	1428.9	1430.0
165°	1442.8	1442.0	1440.3	1438.6	1437.0	1435.3	1437.0	1438.6	1440.3	1442.0	1442.8
167.5°	1454.4	1453.3	1451.2	1449.1	1447.0	1444.9	1447.0	1449.1	1451.2	1453.3	1454.4
170°	1462.9	1461.8	1459.7	1457.6	1455.5	1453.4	1455.5	1457.6	1459.7	1461.8	1462.9
172.5°	1469.3	1468.2	1466.1	1464.0	1461.9	1459.8	1461.9	1464.0	1466.1	1468.2	1469.3
175°	1473.6	1472.4	1470.0	1467.7	1465.3	1462.9	1465.3	1467.7	1470.0	1472.4	1473.6
177.5°	1474.6	1473.5	1471.4	1469.3	1467.2	1465.1	1467.2	1469.3	1471.4	1473.5	1474.6
180°	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3

TEST NUMBER: P999870

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7
2.5°	1407.0	1412.1	1410.0	1398.8	1410.0	1413.1	1419.3	1425.4	1429.5	1435.7	1440.8
5°	1318.7	1329.0	1335.1	1329.0	1349.5	1352.6	1366.9	1375.1	1387.5	1397.7	1405.9
7.5°	1235.6	1243.8	1256.1	1258.2	1270.5	1284.8	1305.4	1325.9	1345.4	1355.7	1364.9
10°	1146.3	1160.7	1179.1	1175.0	1193.5	1216.1	1237.6	1270.5	1286.9	1305.4	1321.8
12.5°	1057.0	1066.3	1090.9	1099.1	1125.8	1143.2	1173.0	1193.5	1234.6	1256.1	1270.5
15°	901.0	939.0	969.8	1006.7	1041.6	1074.5	1101.1	1138.1	1174.0	1190.4	1214.0
17.5°	830.2	847.7	866.1	884.6	929.8	988.3	1035.5	1075.5	1106.3	1127.8	1155.5
20°	756.3	773.8	794.3	811.7	839.5	881.5	940.0	1008.8	1045.7	1068.3	1095.0
22.5°	704.0	720.4	733.8	749.1	770.7	801.5	845.6	930.8	980.1	1007.8	1031.4
25°	647.6	668.1	682.4	693.7	711.2	745.0	781.0	829.2	917.5	939.0	971.8
27.5°	608.6	614.7	631.1	648.6	666.0	684.5	721.4	762.5	822.0	869.2	909.2
30°	562.4	577.8	593.2	600.3	615.7	642.4	665.0	709.1	755.3	792.3	840.5
32.5°	527.5	536.7	547.0	564.4	578.8	597.3	619.8	656.8	695.8	719.4	756.3
35°	488.5	494.6	516.2	523.4	537.7	556.2	578.8	607.5	649.6	668.1	694.8
37.5°	451.5	465.9	472.1	488.5	501.8	520.3	536.7	569.6	597.3	618.8	643.4
40°	422.8	429.0	440.3	454.6	465.9	480.3	500.8	524.4	554.2	571.6	593.2
42.5°	387.9	393.0	407.4	415.6	434.1	447.4	459.8	488.5	515.2	528.5	550.1
45°	349.9	362.3	371.5	387.9	398.2	414.6	430.0	450.5	475.1	490.5	502.9
47.5°	317.1	329.4	338.7	354.0	370.5	377.7	394.1	415.6	438.2	450.5	468.0
50°	290.4	294.5	312.0	319.2	336.6	351.0	362.3	380.7	405.4	412.5	426.9
52.5°	264.8	267.8	279.1	288.4	303.8	316.1	330.4	347.9	368.4	379.7	391.0
55°	242.2	244.2	249.4	259.6	269.9	285.3	298.6	315.1	332.5	344.8	355.1
57.5°	216.5	220.6	224.7	230.9	241.2	255.5	269.9	285.3	299.7	307.9	321.2
60°	186.8	192.9	200.1	207.3	214.5	224.7	241.2	255.5	268.9	276.1	286.3
62.5°	155.0	167.3	173.4	181.6	187.8	197.0	209.4	225.8	235.0	244.2	252.5
65°	139.6	140.6	141.6	149.8	161.1	170.4	181.6	194.0	208.3	214.5	220.6
67.5°	124.2	125.2	127.3	128.3	132.4	142.6	155.0	168.3	179.6	183.7	189.9
70°	108.8	108.8	112.9	113.9	114.9	116.0	126.2	139.6	149.8	155.0	162.1
72.5°	92.4	93.4	95.4	96.5	98.5	100.6	103.6	110.8	123.1	128.3	136.5
75°	75.9	77.0	78.0	79.0	82.1	83.1	86.2	90.3	95.4	101.6	106.7
77.5°	60.5	60.5	61.6	63.6	65.7	66.7	69.8	71.8	73.9	77.0	81.1
80°	45.2	46.2	46.2	48.2	48.2	49.3	50.3	53.4	55.4	57.5	59.5
82.5°	30.8	32.8	32.8	32.8	33.9	34.9	35.9	35.9	38.0	39.0	42.1
85°	18.5	19.5	19.5	19.5	18.5	20.5	20.5	21.6	21.6	21.6	22.6
87.5°	7.2	6.2	7.2	7.2	7.2	8.2	7.2	7.2	8.2	9.2	9.2
90°	26.0	24.8	23.6	22.4	21.2	19.3	17.4	15.5	13.6	12.7	11.4
92.5°	27.4	26.9	26.4	26.0	25.5	24.8	24.1	23.4	22.7	22.3	22.8
95°	46.1	44.9	43.8	42.6	41.4	39.8	38.1	36.5	34.8	34.0	37.9
97.5°	57.0	56.3	55.6	54.9	54.2	50.4	46.6	42.9	39.1	37.2	46.9
100°	68.2	66.3	64.4	62.5	60.6	56.6	52.6	48.5	44.5	42.5	58.7
102.5°	73.1	70.5	67.9	65.3	62.7	105.7	148.6	191.6	234.5	256.0	256.2
105°	75.2	72.6	70.0	67.4	64.8	129.2	193.7	258.1	322.6	354.8	351.3
107.5°	77.3	74.7	72.1	69.5	66.9	146.5	226.1	305.6	385.2	425.0	422.0
110°	91.5	115.1	138.7	162.3	185.9	254.1	322.4	390.6	458.9	493.0	490.5

TEST NUMBER: P999870

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	132.7	234.4	336.2	437.9	539.7	543.7	547.7	551.8	555.8	557.8	555.7
115°	218.3	327.6	436.9	546.2	655.5	649.6	643.7	637.8	631.9	628.9	626.9
117.5°	577.9	611.6	645.4	679.1	712.9	708.9	704.9	700.8	696.8	694.8	692.4
120°	790.1	787.3	784.4	781.6	778.8	774.5	770.3	766.0	761.7	759.6	757.8
122.5°	847.1	845.7	844.2	842.8	841.4	836.7	832.0	827.3	822.6	820.2	818.3
125°	904.4	902.7	901.0	899.4	897.7	893.2	888.8	884.3	879.8	877.6	876.1
127.5°	959.2	956.9	954.5	952.2	949.8	946.3	942.7	939.2	935.7	933.9	932.2
130°	1010.1	1007.5	1004.9	1002.3	999.7	997.1	994.5	991.9	989.3	988.0	986.1
132.5°	1058.1	1056.0	1053.9	1051.8	1049.7	1047.1	1044.5	1041.9	1039.3	1038.0	1036.5
135°	1104.8	1102.4	1100.1	1097.7	1095.3	1093.2	1091.1	1089.0	1086.9	1085.8	1083.9
137.5°	1148.3	1146.0	1143.6	1141.3	1138.9	1136.5	1134.2	1131.8	1129.5	1128.3	1126.9
140°	1189.9	1187.8	1185.7	1183.5	1181.4	1178.8	1176.2	1173.6	1171.0	1169.7	1168.8
142.5°	1228.3	1226.4	1224.5	1222.6	1220.7	1217.6	1214.6	1211.5	1208.4	1206.9	1206.1
145°	1263.5	1261.8	1260.1	1258.5	1256.8	1252.8	1248.8	1244.8	1240.8	1238.8	1238.9
147.5°	1294.5	1293.3	1292.2	1291.0	1289.8	1285.8	1281.8	1277.7	1273.7	1271.7	1272.1
150°	1324.1	1322.7	1321.3	1319.9	1318.5	1314.7	1310.9	1307.2	1303.4	1301.5	1302.3
152.5°	1350.7	1349.3	1347.8	1346.4	1345.0	1341.5	1337.9	1334.4	1330.9	1329.1	1330.0
155°	1374.1	1372.7	1371.2	1369.8	1368.4	1365.6	1362.7	1359.9	1357.0	1355.6	1356.7
157.5°	1395.2	1393.5	1391.9	1390.2	1388.6	1386.5	1384.3	1382.2	1380.1	1379.0	1379.9
160°	1412.3	1410.9	1409.4	1408.0	1406.6	1405.2	1403.8	1402.4	1401.0	1400.3	1401.0
162.5°	1429.2	1427.5	1425.9	1424.2	1422.6	1421.4	1420.2	1419.1	1417.9	1417.3	1418.0
165°	1442.0	1440.3	1438.6	1437.0	1435.3	1434.6	1433.9	1433.2	1432.5	1432.1	1432.8
167.5°	1453.6	1451.9	1450.3	1448.6	1447.0	1446.3	1445.6	1444.9	1444.2	1443.8	1444.5
170°	1462.1	1460.4	1458.8	1457.1	1455.5	1455.0	1454.6	1454.1	1453.6	1453.4	1454.1
172.5°	1468.5	1466.8	1465.2	1463.5	1461.9	1461.4	1461.0	1460.5	1460.0	1459.8	1460.5
175°	1472.8	1471.1	1469.4	1467.8	1466.1	1465.6	1465.2	1464.7	1464.2	1464.0	1464.8
177.5°	1473.8	1472.1	1470.5	1468.8	1467.2	1467.0	1466.7	1466.5	1466.2	1466.1	1466.9
180°	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3	1468.3

TEST NUMBER: P999870

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1476.7	1476.7	1476.7	1476.7
2.5°	1450.1	1447.0	1465.5	1486.0
5°	1420.3	1425.4	1449.0	1477.8
7.5°	1389.5	1400.8	1428.5	1466.5
10°	1346.4	1366.9	1409.0	1448.0
12.5°	1304.3	1332.0	1372.1	1418.3
15°	1257.1	1287.9	1337.2	1392.6
17.5°	1204.8	1239.7	1297.2	1357.7
20°	1149.4	1195.6	1256.1	1321.8
22.5°	1087.8	1143.2	1205.8	1278.7
25°	1028.3	1088.8	1151.4	1235.6
27.5°	969.8	1029.3	1099.1	1184.3
30°	911.3	965.7	1040.6	1131.9
32.5°	848.7	905.1	984.2	1077.5
35°	791.2	847.7	921.6	1013.9
37.5°	729.6	790.2	861.0	956.4
40°	657.8	728.6	797.4	888.7
42.5°	598.3	673.2	739.9	826.1
45°	551.1	621.9	677.3	761.5
47.5°	507.0	564.4	620.9	698.9
50°	464.9	509.0	567.5	637.3
52.5°	421.8	459.8	510.0	575.7
55°	382.8	418.7	463.9	514.1
57.5°	346.9	372.5	417.7	462.8
60°	306.8	333.5	368.4	406.4
62.5°	273.0	293.5	326.3	358.2
65°	237.1	256.6	281.2	310.9
67.5°	204.2	221.7	241.2	264.8
70°	174.5	187.8	202.2	222.7
72.5°	142.6	157.0	170.4	186.8
75°	117.0	123.1	134.4	145.7
77.5°	90.3	98.5	104.7	113.9
80°	64.7	71.8	73.9	81.1
82.5°	43.1	47.2	51.3	53.4
85°	24.6	26.7	30.8	31.8
87.5°	9.2	10.3	12.3	14.4
90°	8.8	6.3	3.7	1.1
92.5°	23.7	24.7	25.6	26.6
95°	45.7	53.5	61.3	69.1
97.5°	66.2	85.6	104.9	124.3
100°	91.0	123.3	155.7	188.0
102.5°	256.7	257.2	257.7	258.2
105°	344.2	337.1	330.1	323.0
107.5°	416.1	410.2	404.3	398.4
110°	485.5	480.6	475.6	470.6

TEST NUMBER: P999870

CATALOG NUMBER: SA2XXRDIP-B675D1080UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	551.4	547.1	542.9	538.6
115°	622.9	618.9	614.9	610.9
117.5°	687.7	683.0	678.3	673.6
120°	754.3	750.8	747.2	743.7
122.5°	814.5	810.8	807.0	803.2
125°	873.0	869.9	866.8	863.7
127.5°	928.9	925.6	922.3	919.0
130°	982.3	978.6	974.8	971.0
132.5°	1033.4	1030.3	1027.3	1024.2
135°	1080.1	1076.4	1072.6	1068.8
137.5°	1124.0	1121.2	1118.3	1115.5
140°	1166.9	1165.0	1163.1	1161.2
142.5°	1204.4	1202.8	1201.1	1199.5
145°	1239.1	1239.4	1239.6	1239.8
147.5°	1272.8	1273.5	1274.2	1274.9
150°	1304.0	1305.6	1307.3	1308.9
152.5°	1331.9	1333.8	1335.7	1337.6
155°	1358.8	1360.9	1363.1	1365.2
157.5°	1381.8	1383.7	1385.6	1387.5
160°	1402.4	1403.8	1405.2	1406.6
162.5°	1419.4	1420.8	1422.2	1423.6
165°	1434.2	1435.7	1437.1	1438.5
167.5°	1445.9	1447.4	1448.8	1450.2
170°	1455.5	1457.0	1458.4	1459.8
172.5°	1461.9	1463.3	1464.7	1466.1
175°	1466.5	1468.1	1469.8	1471.4
177.5°	1468.6	1470.3	1471.9	1473.6
180°	1468.3	1468.3	1468.3	1468.3

(END OF REPORT)