

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999954

Luminaire Tested: SA2XXRDIP-B675D530UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999954
REPORT IS A COMBINATION OF REPORTS P988511 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D530UB2750-4F0-XX-W2A-F_3500K
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4471.0 lumens
Efficiency: N/A
Efficacy: 87.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999954

CATALOG NUMBER: SA2XXRDIP-B675D530UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P999954

CATALOG NUMBER: SA2XXRDIP-B675D530UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	99	95	91	88	91	88	85	82	75	73	71	63	62	60	52	51	50
2	90	83	77	72	83	77	72	68	66	63	59	56	53	51	47	45	43
3	83	74	67	61	76	69	62	57	59	54	50	50	47	44	42	39	37
4	76	66	58	52	70	61	54	49	53	48	43	45	41	38	38	35	33
5	70	59	51	45	65	55	48	43	47	42	38	41	36	33	34	31	29
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	31	28	26
7	60	48	40	35	55	45	38	33	39	34	30	34	29	26	29	25	23
8	56	44	36	31	52	41	34	29	36	30	26	31	27	24	26	23	21
9	52	40	33	28	48	38	31	26	33	28	24	29	24	21	25	21	19
10	49	37	30	25	45	35	28	24	30	25	22	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18026	18026	18026
5°	18056	17149	17022
10°	17877	16265	15728
15°	17631	15221	14253
20°	17306	14034	12712
25°	16973	12817	11299
30°	16526	11630	9758
35°	16088	10434	8435
40°	15643	9259	7072
45°	15124	8046	5883
50°	14590	6877	4789
55°	14032	5708	3802
60°	13385	4565	2876
65°	12638	3480	2339
70°	11736	2524	1859
75°	10606	1925	1420
80°	8966	1304	952
85°	6258	598	461

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15124 cd/sqm

TEST NUMBER: P999954

CATALOG NUMBER: SA2XXRDIP-B675D530UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.7	2.4
10°-20°	293.0	6.6
20°-30°	411.3	9.2
30°-40°	448.4	10.0
40°-50°	412.1	9.2
50°-60°	323.6	7.2
60°-70°	210.7	4.7
70°-80°	108.4	2.4
80°-90°	29.0	0.6
90°-100°	23.9	0.5
100°-110°	89.2	2.0
110°-120°	236.6	5.3
120°-130°	392.4	8.8
130°-140°	416.9	9.3
140°-150°	387.4	8.7
150°-160°	311.5	7.0
160°-170°	200.7	4.5
170°-180°	69.1	1.5
0°-30°	811.1	18.1
0°-40°	1259.4	28.2
0°-60°	1995.2	44.6
0°-90°	2343.3	52.4
90°-120°	349.8	7.8
90°-150°	1546.5	34.6
90°-180°	2128.0	47.6
0°-180°	4471.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1139	1139	1139	1139	1139	
5°	1139	1134	1120	1130	1126	108
15°	1083	1072	1037	1017	1007	305
25°	983	950	882	840	824	452
35°	847	795	704	639	616	530
45°	692	624	515	442	417	535
55°	527	446	335	273	254	471
65°	356	272	179	144	141	352
75°	190	118	82	75	74	201
85°	44	23	20	20	20	51
90°	0	6	10	13	14	4
95°	34	17	20	23	23	40
105°	160	175	32	38	40	171
115°	302	311	324	81	43	297
125°	427	434	444	447	449	381
135°	528	537	541	547	546	408
145°	613	612	621	625	622	383
155°	675	670	676	680	675	311
165°	711	708	710	713	710	201
175°	727	724	725	728	723	69
180°	726	726	726	726	726	

TEST NUMBER: P999954

CATALOG NUMBER: SA2XXRDIP-B675D530UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1138.8	1138.8	1138.8	1138.8	1138.8
2.5°	1143.9	1138.8	1127.4	1137.7	1135.7
5°	1138.8	1133.6	1120.2	1129.5	1126.4
7.5°	1129.5	1123.3	1108.9	1113.0	1107.8
10°	1117.1	1109.9	1089.3	1086.2	1080.0
12.5°	1101.7	1092.4	1064.6	1058.4	1047.0
15°	1083.1	1071.8	1036.7	1017.2	1006.8
17.5°	1061.5	1045.0	1001.7	979.0	962.5
20°	1036.7	1016.1	964.6	938.8	916.2
22.5°	1009.9	986.2	926.5	891.4	876.0
25°	983.1	950.2	882.2	839.9	824.4
27.5°	951.2	916.2	840.9	792.5	768.8
30°	917.2	878.0	795.6	743.0	715.2
32.5°	884.2	836.8	752.3	690.5	664.7
35°	847.1	794.6	703.9	638.9	616.3
37.5°	811.0	754.4	658.5	587.4	561.6
40°	772.9	711.1	611.1	537.9	511.2
42.5°	733.8	667.8	563.7	487.4	461.7
45°	692.5	623.5	515.3	442.1	417.4
47.5°	653.4	580.2	468.9	395.7	373.1
50°	610.1	536.9	423.6	352.4	330.8
52.5°	567.8	490.5	380.3	312.3	292.7
55°	526.6	446.2	334.9	273.1	253.5
57.5°	484.4	401.9	294.7	237.0	220.5
60°	441.1	358.6	252.5	199.9	183.4
62.5°	398.8	316.4	216.4	166.9	158.7
65°	355.5	272.1	179.3	144.3	141.2
67.5°	314.3	230.8	144.3	126.8	123.7
70°	271.0	190.7	119.5	109.2	105.1
72.5°	229.8	153.6	100.0	91.7	89.7
75°	189.6	117.5	82.4	75.2	74.2
77.5°	149.4	83.5	64.9	60.8	58.7
80°	112.3	59.8	49.5	45.3	45.3
82.5°	78.3	40.2	34.0	31.9	31.9
85°	44.3	22.7	19.6	19.6	19.6
87.5°	16.5	8.2	8.2	7.2	7.2
90°	0.5	6.3	10.5	13.1	14.2
92.5°	13.1	11.0	12.6	13.7	14.2
95°	34.1	16.8	20.5	23.1	22.6
97.5°	61.4	18.4	26.8	28.4	28.9
100°	93.0	21.0	29.9	34.1	35.2
102.5°	127.6	126.6	31.0	36.8	38.3
105°	159.6	175.4	32.0	37.8	39.9
107.5°	196.9	210.1	33.1	38.9	41.0
110°	232.6	243.7	91.9	39.4	41.5

TEST NUMBER: P999954

CATALOG NUMBER: SA2XXRDIP-B675D530UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	266.3	275.7	266.8	40.4	42.0
115°	302.0	310.9	324.0	80.9	43.1
117.5°	333.0	343.5	352.4	277.3	139.7
120°	367.6	375.5	384.9	391.2	320.4
122.5°	397.0	405.4	415.9	419.1	419.6
125°	427.0	433.8	443.8	447.4	449.0
127.5°	454.3	461.6	469.5	474.7	475.3
130°	480.0	488.4	494.2	500.0	499.4
132.5°	506.3	513.1	518.9	523.6	523.1
135°	528.3	536.7	541.4	546.7	545.6
137.5°	551.4	557.7	563.0	568.2	566.7
140°	574.0	578.2	584.0	588.7	586.1
142.5°	592.9	596.6	603.4	607.6	605.0
145°	612.9	612.3	621.3	624.9	622.3
147.5°	630.2	628.6	637.5	640.2	638.1
150°	647.0	643.3	651.7	654.9	652.3
152.5°	661.2	657.0	664.9	668.0	664.3
155°	674.8	670.1	676.4	679.6	675.4
157.5°	685.9	681.7	686.4	690.1	685.9
160°	695.3	692.2	695.3	698.5	694.8
162.5°	703.7	700.6	703.2	706.9	702.1
165°	711.1	707.9	709.5	713.2	709.5
167.5°	716.8	713.7	715.3	718.9	714.2
170°	721.6	718.4	719.5	723.2	718.4
172.5°	724.7	721.6	722.6	726.3	721.6
175°	727.4	723.7	724.7	728.4	723.2
177.5°	728.4	724.7	725.3	728.9	724.2
180°	725.8	725.8	725.8	725.8	725.8

(END OF REPORT)