

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000033

Luminaire Tested: SA2XXRDIP-B675D925UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000033
REPORT IS A COMBINATION OF REPORTS P988590 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B675D925UB2750-4F0-XX-W2A-F_3000K
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5997.0 lumens
Efficiency: N/A
Efficacy: 93.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000033

CATALOG NUMBER: SA2XXRDIP-B675D925UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1000033

CATALOG NUMBER: SA2XXRDIP-B675D925UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46
1	96	92	88	85	87	83	80	77	68	66	64	54	53	51	41	40	39
2	87	80	75	70	79	73	68	64	60	57	54	48	46	43	37	35	34
3	80	71	64	58	72	65	59	54	53	49	45	43	40	37	33	31	29
4	73	63	55	50	66	58	51	46	48	43	39	38	35	32	30	27	25
5	67	56	48	43	61	52	45	40	43	38	34	34	31	28	27	24	22
6	62	51	43	37	56	46	40	35	39	33	30	31	28	25	24	22	20
7	57	46	38	33	52	42	35	30	35	30	26	29	25	22	22	20	18
8	53	41	34	29	48	38	32	27	32	27	23	26	22	20	21	18	16
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17949	17949	17949
5°	17978	17076	16950
10°	17800	16195	15661
15°	17557	15156	14192
20°	17232	13974	12656
25°	16900	12761	11251
30°	16456	11581	9716
35°	16019	10390	8398
40°	15576	9219	7042
45°	15061	8012	5858
50°	14527	6847	4769
55°	13973	5684	3785
60°	13327	4545	2865
65°	12584	3464	2329
70°	11689	2513	1852
75°	10562	1918	1414
80°	8934	1299	950
85°	6229	595	459

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15061 cd/sqm

TEST NUMBER: P1000033

CATALOG NUMBER: SA2XXRDIP-B675D925UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.3	1.8
10°-20°	291.7	4.9
20°-30°	409.6	6.8
30°-40°	446.5	7.4
40°-50°	410.3	6.8
50°-60°	322.3	5.4
60°-70°	209.8	3.5
70°-80°	108.0	1.8
80°-90°	29.8	0.5
90°-100°	41.2	0.7
100°-110°	153.6	2.6
110°-120°	407.3	6.8
120°-130°	675.6	11.3
130°-140°	717.6	12.0
140°-150°	666.9	11.1
150°-160°	536.2	8.9
160°-170°	345.5	5.8
170°-180°	118.9	2.0
0°-30°	807.6	13.5
0°-40°	1254.0	20.9
0°-60°	1986.6	33.1
0°-90°	2334.2	38.9
90°-120°	602.1	10.0
90°-150°	2662.2	44.4
90°-180°	3663.0	61.1
0°-180°	5997.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1134	1134	1134	1134	1134	
5°	1134	1129	1115	1125	1122	108
15°	1078	1067	1032	1013	1002	304
25°	979	946	878	836	821	450
35°	844	791	701	636	614	528
45°	690	621	513	440	416	533
55°	524	444	334	272	252	469
65°	354	271	178	144	141	351
75°	189	117	82	75	74	200
85°	44	23	20	20	20	51
90°	1	11	18	23	24	6
95°	59	29	35	40	39	70
105°	275	302	55	65	69	294
115°	520	535	558	139	74	512
125°	735	747	764	770	773	656
135°	910	924	932	941	939	703
145°	1055	1054	1070	1076	1071	660
155°	1162	1154	1164	1170	1163	535
165°	1224	1219	1221	1228	1221	346
175°	1252	1246	1248	1254	1245	119
180°	1249	1249	1249	1249	1249	

TEST NUMBER: P1000033

CATALOG NUMBER: SA2XXRDIP-B675D925UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1133.9	1133.9	1133.9	1133.9	1133.9
2.5°	1139.0	1133.9	1122.6	1132.9	1130.8
5°	1133.9	1128.8	1115.4	1124.7	1121.6
7.5°	1124.7	1118.5	1104.1	1108.2	1103.1
10°	1112.3	1105.2	1084.6	1081.6	1075.4
12.5°	1097.0	1087.7	1060.0	1053.9	1042.6
15°	1078.5	1067.2	1032.3	1012.8	1002.5
17.5°	1056.9	1040.5	997.4	974.8	958.4
20°	1032.3	1011.8	960.5	934.8	912.2
22.5°	1005.6	982.0	922.5	887.6	872.2
25°	978.9	946.1	878.4	836.3	820.9
27.5°	947.1	912.2	837.3	789.1	765.5
30°	913.3	874.3	792.2	739.9	712.1
32.5°	880.4	833.2	749.1	687.5	661.9
35°	843.5	791.2	700.9	636.2	613.6
37.5°	807.6	751.1	655.7	584.9	559.3
40°	769.6	708.0	608.5	535.6	509.0
42.5°	730.6	664.9	561.3	485.4	459.7
45°	689.6	620.8	513.1	440.2	415.6
47.5°	650.6	577.7	466.9	394.0	371.5
50°	607.5	534.6	421.7	350.9	329.4
52.5°	565.4	488.4	378.6	310.9	291.4
55°	524.4	444.3	333.5	271.9	252.4
57.5°	482.3	400.2	293.5	236.0	219.6
60°	439.2	357.1	251.4	199.1	182.7
62.5°	397.1	315.0	215.5	166.2	158.0
65°	354.0	270.9	178.5	143.7	140.6
67.5°	313.0	229.9	143.7	126.2	123.1
70°	269.9	189.8	119.0	108.8	104.7
72.5°	228.8	152.9	99.5	91.3	89.3
75°	188.8	117.0	82.1	74.9	73.9
77.5°	148.8	83.1	64.6	60.5	58.5
80°	111.9	59.5	49.3	45.2	45.2
82.5°	78.0	40.0	33.9	31.8	31.8
85°	44.1	22.6	19.5	19.5	19.5
87.5°	16.4	8.2	8.2	7.2	7.2
90°	0.9	10.8	18.1	22.6	24.4
92.5°	22.6	19.0	21.7	23.5	24.4
95°	58.8	28.9	35.3	39.8	38.9
97.5°	105.8	31.6	46.1	48.8	49.7
100°	160.0	36.2	51.5	58.8	60.6
102.5°	219.7	217.9	53.3	63.3	66.0
105°	274.8	302.0	55.1	65.1	68.7
107.5°	339.0	361.6	57.0	66.9	70.5
110°	400.5	419.5	158.2	67.8	71.4

TEST NUMBER: P1000033

CATALOG NUMBER: SA2XXRDIP-B675D925UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	458.4	474.6	459.3	69.6	72.3
115°	519.8	535.2	557.8	139.2	74.1
117.5°	573.2	591.2	606.6	477.3	240.5
120°	632.8	646.4	662.7	673.5	551.5
122.5°	683.5	697.9	716.0	721.4	722.3
125°	735.0	746.7	763.9	770.3	773.0
127.5°	782.0	794.7	808.2	817.3	818.2
130°	826.3	840.8	850.7	860.7	859.8
132.5°	871.5	883.3	893.2	901.3	900.4
135°	909.5	923.9	932.1	941.1	939.3
137.5°	949.3	960.1	969.1	978.2	975.5
140°	988.1	995.4	1005.3	1013.4	1008.9
142.5°	1020.7	1027.0	1038.8	1046.0	1041.5
145°	1055.0	1054.1	1069.5	1075.8	1071.3
147.5°	1084.9	1082.2	1097.5	1102.0	1098.4
150°	1113.8	1107.5	1121.9	1127.4	1122.8
152.5°	1138.2	1131.0	1144.5	1150.0	1143.6
155°	1161.7	1153.6	1164.4	1169.8	1162.6
157.5°	1180.7	1173.5	1181.6	1187.9	1180.7
160°	1197.0	1191.5	1197.0	1202.4	1196.1
162.5°	1211.4	1206.0	1210.5	1216.9	1208.7
165°	1224.1	1218.7	1221.4	1227.7	1221.4
167.5°	1234.0	1228.6	1231.3	1237.6	1229.5
170°	1242.2	1236.7	1238.6	1244.9	1236.7
172.5°	1247.6	1242.2	1244.0	1250.3	1242.2
175°	1252.1	1245.8	1247.6	1253.9	1244.9
177.5°	1253.9	1247.6	1248.5	1254.8	1246.7
180°	1249.4	1249.4	1249.4	1249.4	1249.4

(END OF REPORT)