

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000072

Luminaire Tested: SA2XXRDIP-B865D1080UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000072
REPORT IS A COMBINATION OF REPORTS P988629 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D1080UB2750-4F0-XX-W2A-F_2700K
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7242.0 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000072

CATALOG NUMBER: SA2XXRDIP-B865D1080UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1000072

CATALOG NUMBER: SA2XXRDIP-B865D1080UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41
2	88	81	75	70	80	74	69	65	61	58	54	49	47	45	38	37	35
3	80	71	64	59	73	65	59	55	54	50	46	44	41	38	34	32	31
4	74	63	56	50	67	58	52	47	48	44	40	39	36	33	31	29	27
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21
7	58	46	38	33	53	42	36	31	36	30	27	29	26	23	23	21	19
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22875	22875	22875
5°	22912	21762	21601
10°	22686	20640	19959
15°	22375	19315	18088
20°	21962	17809	16131
25°	21539	16263	14339
30°	20971	14759	12384
35°	20416	13240	10703
40°	19851	11750	8975
45°	19193	10211	7465
50°	18514	8727	6077
55°	17808	7243	4825
60°	16984	5793	3651
65°	16040	4417	2968
70°	14893	3204	2360
75°	13459	2443	1803
80°	11377	1655	1209
85°	7939	756	583

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19193 cd/sqm

TEST NUMBER: P1000072

CATALOG NUMBER: SA2XXRDIP-B865D1080UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.4	1.9
10°-20°	371.8	5.1
20°-30°	522.0	7.2
30°-40°	569.0	7.9
40°-50°	523.0	7.2
50°-60°	410.7	5.7
60°-70°	267.3	3.7
70°-80°	137.6	1.9
80°-90°	37.7	0.5
90°-100°	48.0	0.7
100°-110°	178.9	2.5
110°-120°	474.6	6.6
120°-130°	787.1	10.9
130°-140°	836.1	11.5
140°-150°	777.0	10.7
150°-160°	624.7	8.6
160°-170°	402.5	5.6
170°-180°	138.5	1.9
0°-30°	1029.2	14.2
0°-40°	1598.2	22.1
0°-60°	2531.9	35.0
0°-90°	2974.6	41.1
90°-120°	701.5	9.7
90°-150°	3101.6	42.8
90°-180°	4267.0	58.9
0°-180°	7242.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1445	1445	1445	1445	1445	
5°	1445	1438	1422	1433	1429	137
15°	1374	1360	1316	1291	1278	387
25°	1248	1206	1119	1066	1046	574
35°	1075	1008	893	811	782	673
45°	879	791	654	561	530	679
55°	668	566	425	347	322	597
65°	451	345	228	183	179	447
75°	241	149	105	96	94	254
85°	56	29	25	25	25	65
90°	1	13	21	26	28	7
95°	68	34	41	46	45	81
105°	320	352	64	76	80	342
115°	606	624	650	162	86	596
125°	856	870	890	897	901	764
135°	1060	1076	1086	1096	1094	819
145°	1229	1228	1246	1253	1248	769
155°	1354	1344	1357	1363	1354	624
165°	1426	1420	1423	1430	1423	403
175°	1459	1451	1454	1461	1450	139
180°	1456	1456	1456	1456	1456	

TEST NUMBER: P1000072

CATALOG NUMBER: SA2XXRDIP-B865D1080UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1445.1	1445.1	1445.1	1445.1	1445.1
2.5°	1451.6	1445.1	1430.7	1443.8	1441.2
5°	1445.1	1438.5	1421.5	1433.3	1429.4
7.5°	1433.3	1425.5	1407.2	1412.4	1405.9
10°	1417.6	1408.5	1382.3	1378.4	1370.5
12.5°	1398.0	1386.2	1350.9	1343.1	1328.7
15°	1374.5	1360.1	1315.6	1290.8	1277.7
17.5°	1347.0	1326.1	1271.2	1242.4	1221.5
20°	1315.6	1289.5	1224.1	1191.4	1162.6
22.5°	1281.6	1251.5	1175.7	1131.2	1111.6
25°	1247.6	1205.8	1119.4	1065.8	1046.2
27.5°	1207.1	1162.6	1067.1	1005.7	975.6
30°	1163.9	1114.2	1009.6	942.9	907.6
32.5°	1122.1	1061.9	954.7	876.2	843.5
35°	1075.0	1008.3	893.2	810.8	782.0
37.5°	1029.2	957.3	835.7	745.4	712.7
40°	980.8	902.4	775.5	682.7	648.7
42.5°	931.1	847.4	715.3	618.6	585.9
45°	878.8	791.2	653.9	561.0	529.6
47.5°	829.1	736.3	595.0	502.2	473.4
50°	774.2	681.3	537.5	447.3	419.8
52.5°	720.6	622.5	482.6	396.3	371.4
55°	668.3	566.3	425.0	346.6	321.7
57.5°	614.7	510.0	374.0	300.8	279.9
60°	559.7	455.1	320.4	253.7	232.8
62.5°	506.1	401.5	274.6	211.9	201.4
65°	451.2	345.3	227.6	183.1	179.2
67.5°	398.9	292.9	183.1	160.9	156.9
70°	343.9	241.9	151.7	138.6	133.4
72.5°	291.6	194.9	126.9	116.4	113.8
75°	240.6	149.1	104.6	95.5	94.2
77.5°	189.6	105.9	82.4	77.2	74.5
80°	142.5	75.9	62.8	57.5	57.5
82.5°	99.4	51.0	43.2	40.5	40.5
85°	56.2	28.8	24.8	24.8	24.8
87.5°	20.9	10.5	10.5	9.2	9.2
90°	1.1	12.6	21.1	26.3	28.4
92.5°	26.3	22.1	25.3	27.4	28.4
95°	68.5	33.7	41.1	46.3	45.3
97.5°	123.2	36.9	53.7	56.9	57.9
100°	186.4	42.1	60.0	68.5	70.6
102.5°	255.9	253.8	62.1	73.7	76.9
105°	320.2	351.8	64.3	75.8	80.0
107.5°	395.0	421.3	66.4	77.9	82.2
110°	466.6	488.7	184.3	79.0	83.2

TEST NUMBER: P1000072

CATALOG NUMBER: SA2XXRDIP-B865D1080UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	534.0	553.0	535.1	81.1	84.3
115°	605.6	623.5	649.9	162.2	86.4
117.5°	667.8	688.9	706.8	556.1	280.2
120°	737.3	753.1	772.1	784.7	642.5
122.5°	796.3	813.1	834.2	840.5	841.6
125°	856.3	870.0	890.0	897.4	900.6
127.5°	911.1	925.8	941.6	952.2	953.2
130°	962.7	979.6	991.1	1002.7	1001.7
132.5°	1015.4	1029.1	1040.6	1050.1	1049.1
135°	1059.6	1076.5	1085.9	1096.5	1094.4
137.5°	1106.0	1118.6	1129.1	1139.7	1136.5
140°	1151.2	1159.7	1171.3	1180.7	1175.5
142.5°	1189.2	1196.5	1210.2	1218.7	1213.4
145°	1229.2	1228.1	1246.0	1253.4	1248.1
147.5°	1263.9	1260.8	1278.7	1284.0	1279.7
150°	1297.7	1290.3	1307.1	1313.5	1308.2
152.5°	1326.1	1317.7	1333.5	1339.8	1332.4
155°	1353.5	1344.0	1356.6	1363.0	1354.5
157.5°	1375.6	1367.2	1376.6	1384.0	1375.6
160°	1394.6	1388.2	1394.6	1400.9	1393.5
162.5°	1411.4	1405.1	1410.4	1417.7	1408.2
165°	1426.2	1419.8	1423.0	1430.4	1423.0
167.5°	1437.7	1431.4	1434.6	1442.0	1432.5
170°	1447.2	1440.9	1443.0	1450.4	1440.9
172.5°	1453.5	1447.2	1449.3	1456.7	1447.2
175°	1458.8	1451.4	1453.5	1460.9	1450.4
177.5°	1460.9	1453.5	1454.6	1462.0	1452.5
180°	1455.6	1455.6	1455.6	1455.6	1455.6

(END OF REPORT)