

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998092

Luminaire Tested: SA2XXDIP-B290D1080UB2750-4F0-XX-W2A-A_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998092
REPORT IS A COMBINATION OF REPORTS P983829 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B290D1080UB2750-4F0-XX-W2A-A_3500K
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5600.0 lumens
Efficiency: N/A
Efficacy: 116.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998092

CATALOG NUMBER: SA2XXDIP-B290D1080UB2750-4F0-XX-W2A-A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P998092

CATALOG NUMBER: SA2XXDIP-B290D1080UB2750-4F0-XX-W2A-A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	31	31	23
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	27	27	27	20
2	84	77	71	66	74	68	64	60	53	50	47	38	36	34	25	24	23	23	23	17
3	77	68	61	55	68	60	55	50	47	43	40	34	31	29	22	21	20	20	20	14
4	70	60	53	47	62	54	47	42	41	37	34	30	28	25	20	18	17	17	17	13
5	64	53	46	40	57	48	41	36	37	33	29	27	24	22	18	16	15	15	15	11
6	59	48	40	35	52	43	36	31	33	29	25	25	22	19	16	15	13	13	13	10
7	55	43	35	30	48	39	32	28	30	26	22	22	19	17	15	13	12	12	12	9
8	51	39	32	27	45	35	29	24	27	23	20	20	17	15	14	12	11	11	11	8
9	47	35	28	24	42	32	26	22	25	21	17	19	16	14	13	11	10	10	10	7
10	44	32	26	21	39	29	23	19	23	19	16	17	14	12	12	10	9	9	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9148	9148	9148	9148
5°	9169	9753	9205	7760
10°	9062	10647	9120	6398
15°	8843	11230	8966	5389
20°	8706	10545	8706	4684
25°	8428	9060	8466	4189
30°	7971	7121	8124	3794
35°	7566	4924	7693	3471
40°	7102	3717	7183	3214
45°	6528	3056	6635	2936
50°	6033	2681	6043	2688
55°	5468	2286	5502	2418
60°	4867	1908	4934	2111
65°	4326	1552	4405	1802
70°	3789	1217	3885	1454
75°	3183	884	3306	1055
80°	2483	561	2659	626
85°	1624	282	1752	209

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 9457 cd/sqm

TEST NUMBER: P998092

CATALOG NUMBER: SA2XXDIP-B290D1080UB2750-4F0-XX-W2A-A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.0	1.0
10°-20°	160.2	2.9
20°-30°	232.5	4.2
30°-40°	245.1	4.4
40°-50°	216.9	3.9
50°-60°	173.2	3.1
60°-70°	117.6	2.1
70°-80°	60.2	1.1
80°-90°	16.8	0.3
90°-100°	48.6	0.9
100°-110°	181.2	3.2
110°-120°	480.7	8.6
120°-130°	797.2	14.2
130°-140°	846.8	15.1
140°-150°	787.0	14.1
150°-160°	632.7	11.3
160°-170°	407.7	7.3
170°-180°	140.3	2.5
0°-30°	447.8	8.0
0°-40°	692.9	12.4
0°-60°	1083.0	19.3
0°-90°	1277.6	22.8
90°-120°	710.5	12.7
90°-150°	3141.6	56.1
90°-180°	4322.0	77.2
0°-180°	5600.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	578	578	578	578	578	
5°	578	645	581	514	578	55
15°	543	793	551	381	543	153
25°	488	661	490	306	488	223
35°	398	360	405	254	398	249
45°	299	217	304	208	299	232
55°	205	152	206	161	205	183
65°	122	94	124	109	122	121
75°	57	46	59	55	57	61
85°	12	12	12	9	12	13
90°	1	29	1	29	1	5
95°	69	46	69	46	69	82
105°	324	81	324	81	324	347
115°	613	88	613	88	613	604
125°	867	912	867	912	867	774
135°	1073	1108	1073	1108	1073	829
145°	1245	1264	1245	1264	1245	779
155°	1371	1372	1371	1372	1371	632
165°	1444	1441	1444	1441	1444	408
175°	1478	1469	1478	1469	1478	141
180°	1474	1474	1474	1474	1474	

TEST NUMBER: P998092

CATALOG NUMBER: SA2XXDIP-B290D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	581.0	582.3	584.6	585.0	589.4	593.0	597.0	597.0	598.3	597.9	594.3
5°	578.3	582.3	588.1	593.0	601.0	604.5	609.9	613.9	617.4	620.1	619.6
7.5°	573.9	581.0	589.4	598.8	609.4	615.6	623.2	630.3	635.2	639.6	642.7
10°	566.3	578.3	589.9	602.3	616.1	624.5	633.4	642.7	650.3	658.7	666.7
12.5°	556.1	573.4	587.7	604.1	621.0	630.3	644.5	651.6	666.3	687.6	693.4
15°	543.2	566.8	580.1	601.0	623.2	630.7	650.3	661.8	692.0	705.4	721.4
17.5°	531.2	557.5	575.2	599.2	621.0	635.6	654.7	678.3	703.6	722.7	740.5
20°	521.5	546.8	568.1	594.8	622.3	641.0	661.0	689.4	716.9	736.5	750.2
22.5°	499.3	531.7	556.6	586.3	619.6	645.4	664.5	695.6	725.4	737.4	749.3
25°	488.2	516.1	545.0	578.8	617.9	648.5	665.0	699.6	725.8	730.2	732.9
27.5°	467.7	499.3	533.0	571.7	617.4	643.2	664.1	695.6	716.5	713.4	705.4
30°	442.4	481.1	518.4	560.1	611.2	639.2	658.7	687.6	698.3	682.3	668.1
32.5°	423.8	460.2	501.5	549.9	604.1	630.7	649.8	672.5	674.7	645.9	621.9
35°	398.4	438.9	485.5	536.6	592.1	616.1	633.9	647.6	637.0	596.5	568.1
37.5°	375.8	415.8	465.5	517.5	575.7	599.2	613.4	615.6	589.4	553.9	512.1
40°	350.9	392.2	444.2	498.8	557.5	577.9	586.8	580.1	542.4	501.0	452.6
42.5°	326.0	366.9	422.9	478.8	534.4	551.7	555.2	537.0	490.8	442.4	386.4
45°	298.9	341.6	397.5	454.0	507.7	517.5	517.9	491.7	437.1	386.4	334.5
47.5°	276.7	316.3	371.8	428.2	473.5	480.2	477.5	447.3	387.8	330.9	285.6
50°	252.3	290.1	345.1	400.7	439.3	441.1	434.4	391.3	333.1	281.2	245.2
52.5°	226.1	264.3	314.9	368.2	402.9	400.2	387.3	341.1	286.5	243.4	215.9
55°	205.2	239.0	286.5	338.5	362.9	355.4	341.1	294.1	251.0	214.5	190.6
57.5°	182.1	211.9	258.5	303.8	318.0	310.9	296.7	252.7	212.8	185.2	169.2
60°	160.4	187.4	228.3	266.1	277.2	269.6	253.2	213.7	184.8	161.7	149.7
62.5°	140.4	163.9	198.1	232.8	237.2	229.6	215.4	183.4	158.6	140.4	131.5
65°	121.7	143.9	171.5	197.7	201.7	193.7	179.0	155.9	135.0	123.5	115.0
67.5°	103.5	121.3	145.7	164.8	167.0	159.5	147.5	128.8	115.9	103.5	97.3
70°	87.5	100.8	119.9	135.5	136.4	129.3	123.0	106.2	96.4	87.5	82.6
72.5°	72.0	81.3	95.9	107.5	107.9	103.5	97.7	87.1	78.6	72.4	67.5
75°	56.9	64.9	73.7	84.0	83.5	80.0	75.5	68.8	61.7	57.7	55.5
77.5°	43.5	48.4	55.5	62.2	62.2	60.4	57.7	52.9	48.4	44.4	42.2
80°	31.1	34.2	40.0	42.2	43.1	42.6	40.4	36.9	35.1	32.0	31.1
82.5°	20.0	22.2	24.9	27.1	28.4	27.5	27.1	25.3	22.7	21.8	20.9
85°	11.5	12.4	13.8	15.1	15.5	15.1	16.0	14.7	13.3	13.3	12.9
87.5°	4.9	5.3	6.2	6.2	6.7	6.7	6.2	6.7	6.7	6.2	5.8
90°	1.1	3.7	6.3	8.9	11.5	12.8	13.7	15.6	17.5	19.4	21.3
92.5°	26.7	25.7	24.8	23.8	22.9	22.4	22.8	23.5	24.2	24.9	25.6
95°	69.3	61.5	53.7	45.8	38.0	34.1	34.9	36.6	38.3	39.9	41.6
97.5°	124.8	105.4	85.9	66.5	47.0	37.3	39.2	43.0	46.8	50.6	54.4
100°	188.8	156.3	123.9	91.4	58.9	42.7	44.7	48.7	52.8	56.8	60.8
102.5°	259.2	258.7	258.3	257.8	257.3	257.1	235.5	192.4	149.2	106.1	62.9
105°	324.3	331.4	338.5	345.6	352.7	356.3	323.9	259.2	194.5	129.8	65.1
107.5°	400.1	406.0	411.9	417.8	423.7	426.7	386.8	306.9	227.0	147.1	67.2
110°	472.6	477.6	482.6	487.5	492.5	495.0	460.7	392.2	323.7	255.2	186.7

TEST NUMBER: P998092

CATALOG NUMBER: SA2XXDIP-B290D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	540.9	545.2	549.4	553.7	558.0	560.1	558.1	554.1	550.0	546.0	542.0
115°	613.4	617.4	621.5	625.5	629.6	631.6	634.6	640.5	646.4	652.3	658.2
117.5°	676.4	681.1	685.9	690.6	695.3	697.7	699.7	703.8	707.8	711.9	715.9
120°	746.8	750.4	753.9	757.5	761.0	762.8	764.9	769.2	773.5	777.7	782.0
122.5°	806.5	810.3	814.1	817.9	821.7	823.6	826.0	830.7	835.4	840.2	844.9
125°	867.4	870.5	873.5	876.6	879.7	881.2	883.5	888.0	892.5	897.0	901.5
127.5°	922.8	926.1	929.5	932.8	936.1	937.8	939.6	943.1	946.7	950.2	953.8
130°	975.1	978.9	982.7	986.5	990.3	992.2	993.5	996.1	998.7	1001.3	1003.9
132.5°	1028.4	1031.5	1034.6	1037.7	1040.8	1042.3	1043.6	1046.2	1048.9	1051.5	1054.1
135°	1073.3	1077.1	1080.9	1084.6	1088.4	1090.3	1091.4	1093.5	1095.6	1097.8	1099.9
137.5°	1120.2	1123.0	1125.9	1128.7	1131.6	1133.0	1134.2	1136.6	1138.9	1141.3	1143.7
140°	1166.1	1168.0	1169.9	1171.8	1173.7	1174.6	1175.9	1178.5	1181.1	1183.7	1186.3
142.5°	1204.5	1206.1	1207.8	1209.4	1211.1	1211.9	1213.4	1216.5	1219.6	1222.7	1225.8
145°	1245.0	1244.8	1244.6	1244.3	1244.1	1244.0	1246.0	1250.0	1254.1	1258.1	1262.1
147.5°	1280.2	1279.5	1278.8	1278.1	1277.4	1277.0	1279.0	1283.1	1287.1	1291.2	1295.2
150°	1314.4	1312.7	1311.1	1309.4	1307.7	1306.9	1308.8	1312.6	1316.4	1320.2	1324.0
152.5°	1343.2	1341.3	1339.4	1337.5	1335.6	1334.6	1336.4	1339.9	1343.5	1347.0	1350.6
155°	1370.9	1368.8	1366.6	1364.5	1362.4	1361.3	1362.7	1365.6	1368.4	1371.3	1374.1
157.5°	1393.3	1391.4	1389.5	1387.6	1385.7	1384.8	1385.9	1388.0	1390.1	1392.3	1394.4
160°	1412.5	1411.1	1409.7	1408.2	1406.8	1406.1	1406.8	1408.2	1409.7	1411.1	1412.5
162.5°	1429.6	1428.2	1426.8	1425.3	1423.9	1423.2	1423.8	1425.0	1426.1	1427.3	1428.5
165°	1444.5	1443.1	1441.7	1440.2	1438.8	1438.1	1438.5	1439.2	1439.9	1440.6	1441.3
167.5°	1456.3	1454.9	1453.5	1452.0	1450.6	1449.9	1450.3	1451.0	1451.7	1452.4	1453.1
170°	1465.9	1464.5	1463.1	1461.6	1460.2	1459.5	1459.7	1460.2	1460.7	1461.1	1461.6
172.5°	1472.3	1470.9	1469.5	1468.0	1466.6	1465.9	1466.1	1466.6	1467.1	1467.5	1468.0
175°	1477.6	1475.9	1474.3	1472.6	1470.9	1470.1	1470.3	1470.8	1471.3	1471.8	1472.3
177.5°	1479.7	1478.1	1476.4	1474.8	1473.1	1472.3	1472.4	1472.6	1472.9	1473.1	1473.3
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P998092

CATALOG NUMBER: SA2XXDIP-B290D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	600.5	601.0	601.9	606.3	608.5	609.0	607.2	611.2	612.5	611.2	610.3
5°	629.0	631.6	637.0	642.7	642.3	642.7	645.4	648.1	649.0	645.4	646.7
7.5°	653.8	659.2	665.0	673.8	673.8	678.3	680.1	682.3	687.6	684.9	684.1
10°	682.3	689.4	700.0	714.3	714.7	719.1	723.6	730.7	732.9	731.1	732.0
12.5°	717.8	731.6	732.5	748.0	755.1	756.0	763.1	761.8	766.2	766.2	773.8
15°	733.4	754.7	766.7	781.8	786.2	780.9	786.7	792.9	793.3	793.3	792.9
17.5°	761.3	769.8	781.8	789.8	791.5	791.5	792.0	794.7	792.9	789.3	792.0
20°	767.1	770.7	775.1	774.2	775.1	770.7	766.2	761.8	762.2	760.0	766.7
22.5°	756.5	755.6	745.3	738.7	738.7	729.8	721.4	717.4	713.4	714.7	716.9
25°	729.8	716.0	703.6	693.8	691.6	677.4	665.8	662.3	655.6	661.0	661.8
27.5°	687.2	671.6	651.6	643.2	631.6	625.9	617.9	607.2	593.4	601.4	600.1
30°	641.4	618.3	601.9	581.4	563.2	561.9	546.8	529.0	521.9	521.9	525.9
32.5°	590.3	559.7	535.7	506.8	489.1	481.5	463.3	445.5	449.5	436.2	441.1
35°	530.8	490.4	460.2	432.2	418.9	410.0	386.4	376.7	366.0	359.8	371.3
37.5°	473.9	427.3	388.7	358.0	353.1	337.1	321.1	314.9	308.7	311.4	310.9
40°	404.7	363.3	328.7	304.7	296.3	288.7	278.1	270.5	266.5	268.7	269.2
42.5°	342.0	307.4	281.6	264.7	257.6	252.3	247.0	240.8	239.4	239.4	241.2
45°	293.6	265.2	247.9	234.1	230.1	226.1	222.1	219.4	218.5	216.8	218.1
47.5°	255.0	232.3	221.7	211.4	207.0	206.1	202.6	201.2	199.4	199.0	199.4
50°	222.5	208.3	198.6	192.8	189.7	188.3	186.6	183.9	183.0	185.2	184.3
52.5°	199.9	186.6	181.2	175.5	173.7	171.9	169.2	169.7	169.2	168.3	168.3
55°	177.2	168.8	163.5	159.0	158.6	156.8	154.6	153.7	153.2	152.4	153.7
57.5°	159.0	152.4	147.5	143.5	141.7	141.7	139.5	137.7	137.7	137.3	137.7
60°	140.8	134.1	131.0	127.0	125.7	125.3	123.9	123.0	121.7	121.7	121.7
62.5°	123.9	118.6	115.0	111.5	111.9	109.7	107.9	107.0	107.0	107.5	107.5
65°	107.9	104.4	99.9	96.8	95.9	95.5	94.6	94.2	92.8	93.7	93.7
67.5°	93.3	88.4	85.7	84.4	83.1	82.6	81.7	80.8	80.4	80.0	80.8
70°	78.6	74.6	72.4	71.5	70.2	69.7	69.3	68.0	68.4	68.8	69.3
72.5°	65.3	61.7	61.3	58.6	58.6	58.6	56.9	57.7	57.3	56.4	57.3
75°	51.5	49.7	48.9	47.5	48.0	47.5	47.1	45.8	45.8	46.2	46.6
77.5°	40.9	39.1	38.6	37.3	36.4	37.3	36.4	36.0	36.0	36.4	36.4
80°	30.2	29.3	28.0	28.0	28.0	27.5	27.5	27.5	27.1	26.7	27.1
82.5°	20.0	20.0	19.5	19.1	19.5	18.7	19.1	19.1	19.1	19.1	19.1
85°	12.9	12.4	12.4	12.0	12.0	12.0	12.4	11.5	11.5	12.0	12.0
87.5°	5.8	5.8	5.8	6.2	5.8	5.8	5.8	6.2	5.8	5.8	5.8
90°	22.5	23.7	24.9	26.1	26.7	26.9	27.4	27.9	28.3	28.8	28.3
92.5°	26.1	26.5	27.0	27.5	27.7	27.8	28.1	28.3	28.6	28.8	28.6
95°	42.8	44.0	45.1	46.3	46.9	46.8	46.6	46.3	46.1	45.9	46.1
97.5°	55.1	55.8	56.5	57.2	57.6	57.7	58.0	58.2	58.5	58.7	58.5
100°	62.7	64.6	66.5	68.4	69.3	69.5	70.0	70.5	71.0	71.5	71.0
102.5°	65.5	68.1	70.8	73.4	74.7	75.1	75.8	76.5	77.2	77.9	77.2
105°	67.7	70.3	72.9	75.5	76.8	77.3	78.2	79.2	80.1	81.1	80.1
107.5°	69.8	72.4	75.0	77.6	78.9	79.4	80.3	81.3	82.2	83.2	82.2
110°	163.0	139.3	115.6	91.9	80.0	80.5	81.4	82.4	83.3	84.3	83.3

TEST NUMBER: P998092

CATALOG NUMBER: SA2XXDIP-B290D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	439.8	337.6	235.4	133.2	82.1	82.5	83.2	83.9	84.6	85.3	84.6
115°	548.4	438.7	328.9	219.2	164.3	155.8	138.7	121.6	104.6	87.5	104.6
117.5°	682.0	648.1	614.2	580.3	563.3	532.2	470.1	408.0	345.9	283.8	345.9
120°	784.8	787.7	790.5	793.4	794.8	778.8	746.8	714.8	682.8	650.8	682.8
122.5°	846.3	847.8	849.2	850.7	851.4	851.5	851.7	852.0	852.2	852.4	852.2
125°	903.2	904.8	906.5	908.2	909.0	909.4	910.1	910.8	911.5	912.2	911.5
127.5°	956.2	958.5	960.9	963.2	964.4	964.5	964.8	965.0	965.3	965.5	965.3
130°	1006.5	1009.1	1011.7	1014.3	1015.6	1015.5	1015.3	1015.0	1014.8	1014.6	1014.8
132.5°	1056.2	1058.4	1060.5	1062.6	1063.7	1063.6	1063.3	1063.1	1062.8	1062.6	1062.8
135°	1102.3	1104.7	1107.0	1109.4	1110.6	1110.4	1109.9	1109.4	1109.0	1108.5	1109.0
137.5°	1146.1	1148.4	1150.8	1153.1	1154.3	1153.9	1153.2	1152.5	1151.8	1151.1	1151.8
140°	1188.4	1190.6	1192.7	1194.8	1195.9	1195.3	1194.1	1193.0	1191.8	1190.6	1191.8
142.5°	1227.7	1229.6	1231.5	1233.4	1234.4	1233.8	1232.6	1231.4	1230.2	1229.0	1230.2
145°	1263.8	1265.4	1267.1	1268.8	1269.6	1269.0	1267.8	1266.6	1265.4	1264.2	1265.4
147.5°	1296.4	1297.6	1298.7	1299.9	1300.5	1300.0	1299.1	1298.1	1297.2	1296.2	1297.2
150°	1325.4	1326.8	1328.3	1329.7	1330.4	1329.8	1328.6	1327.4	1326.2	1325.0	1326.2
152.5°	1352.0	1353.4	1354.9	1356.3	1357.0	1356.2	1354.5	1352.9	1351.2	1349.6	1351.2
155°	1375.5	1376.9	1378.4	1379.8	1380.5	1379.6	1377.7	1375.8	1373.9	1372.0	1373.9
157.5°	1396.0	1397.7	1399.3	1401.0	1401.8	1400.9	1399.0	1397.1	1395.2	1393.3	1395.2
160°	1413.9	1415.3	1416.8	1418.2	1418.9	1418.1	1416.4	1414.7	1413.1	1411.4	1413.1
162.5°	1430.2	1431.8	1433.5	1435.2	1436.0	1434.9	1432.8	1430.7	1428.5	1426.4	1428.5
165°	1443.0	1444.6	1446.3	1448.0	1448.8	1448.0	1446.3	1444.6	1443.0	1441.3	1443.0
167.5°	1454.7	1456.4	1458.0	1459.7	1460.5	1459.4	1457.3	1455.2	1453.0	1450.9	1453.0
170°	1463.3	1464.9	1466.6	1468.3	1469.1	1468.0	1465.9	1463.8	1461.6	1459.5	1461.6
172.5°	1469.7	1471.3	1473.0	1474.7	1475.5	1474.4	1472.3	1470.2	1468.0	1465.9	1468.0
175°	1473.9	1475.6	1477.2	1478.9	1479.7	1478.5	1476.2	1473.8	1471.5	1469.1	1471.5
177.5°	1475.0	1476.6	1478.3	1480.0	1480.8	1479.7	1477.6	1475.5	1473.3	1471.2	1473.3
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P998092

CATALOG NUMBER: SA2XXDIP-B290D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	612.5	609.4	606.8	607.2	609.4	607.7	603.2	597.4	595.2	592.5	595.2
5°	649.4	646.7	641.4	641.9	640.5	638.7	631.6	622.8	622.8	615.6	614.8
7.5°	685.8	681.8	678.3	677.4	672.5	668.9	662.7	650.3	645.4	637.0	632.1
10°	726.7	723.6	719.6	714.7	712.0	705.8	695.6	677.4	668.5	657.0	648.5
12.5°	768.0	767.6	758.7	748.9	748.5	738.7	731.6	707.1	695.2	679.6	659.6
15°	794.2	792.0	787.1	782.2	783.5	772.9	756.9	728.0	720.0	701.4	680.1
17.5°	793.8	793.8	792.4	791.5	790.2	787.1	778.2	759.1	746.2	722.7	702.7
20°	768.4	774.2	775.6	775.1	779.6	781.8	781.3	769.3	759.1	738.2	717.8
22.5°	717.8	731.1	736.9	740.5	749.8	754.7	766.2	761.8	759.1	743.6	726.2
25°	670.7	675.2	692.5	693.4	706.3	718.3	729.8	737.4	747.1	741.4	726.7
27.5°	609.9	620.1	632.5	641.9	644.5	668.9	688.0	702.3	724.5	726.2	721.4
30°	541.0	545.9	566.3	578.8	593.0	610.8	638.3	662.7	682.7	700.9	707.1
32.5°	457.1	477.1	489.1	504.2	516.6	548.1	581.9	613.4	636.5	667.2	680.5
35°	380.2	395.8	416.2	422.4	445.1	471.7	515.7	556.1	591.2	622.3	649.4
37.5°	316.7	329.1	350.9	360.7	374.0	408.2	445.1	495.3	537.5	575.7	609.4
40°	273.2	282.5	298.9	302.0	313.2	344.2	374.0	421.1	477.1	528.6	565.5
42.5°	243.4	247.9	259.0	263.0	270.1	290.9	317.6	362.0	414.0	467.3	519.3
45°	222.1	225.2	231.9	235.4	244.3	253.6	275.4	310.9	351.8	405.5	461.5
47.5°	203.0	207.0	209.7	211.9	216.8	227.0	241.2	267.4	306.5	355.8	410.0
50°	187.0	188.3	193.2	193.7	196.8	203.4	216.8	232.8	263.8	303.8	356.2
52.5°	171.0	172.3	175.5	178.6	179.9	185.2	194.1	207.4	230.5	262.1	308.7
55°	155.0	156.8	159.9	162.1	163.5	167.9	173.2	186.1	204.3	226.5	264.7
57.5°	139.0	143.0	143.9	145.2	147.5	152.4	157.2	164.8	179.0	199.4	227.4
60°	123.9	125.3	128.4	129.7	131.9	134.6	140.8	146.6	156.8	172.8	198.1
62.5°	108.4	111.5	112.8	114.2	115.9	119.0	123.0	129.3	138.1	151.0	171.0
65°	95.1	95.5	98.2	99.9	101.7	103.9	107.9	113.7	119.0	131.0	145.7
67.5°	82.2	83.1	84.0	85.7	87.9	90.2	93.7	96.8	103.5	111.5	123.0
70°	69.7	69.7	72.0	73.3	72.8	75.5	78.2	81.7	86.6	94.2	103.5
72.5°	58.6	58.2	60.0	60.4	61.3	63.1	64.9	68.4	71.1	76.8	84.0
75°	46.6	47.5	48.4	48.4	49.7	51.1	52.9	54.6	57.7	61.3	66.6
77.5°	36.9	36.9	37.8	38.2	39.5	39.1	40.9	42.6	44.9	48.0	52.0
80°	27.1	28.0	28.0	28.0	28.4	28.9	30.6	32.0	33.3	35.5	37.3
82.5°	19.1	19.1	20.0	20.0	20.0	20.9	20.9	21.3	22.2	23.5	24.9
85°	12.0	12.0	12.0	12.4	12.0	12.4	13.3	12.9	13.3	14.2	14.2
87.5°	5.8	5.8	5.8	5.8	5.8	6.2	5.8	6.2	6.7	6.7	6.7
90°	27.9	27.4	26.9	26.7	26.1	24.9	23.7	22.5	21.3	19.4	17.5
92.5°	28.3	28.1	27.8	27.7	27.5	27.0	26.5	26.1	25.6	24.9	24.2
95°	46.3	46.6	46.8	46.9	46.3	45.1	44.0	42.8	41.6	39.9	38.3
97.5°	58.2	58.0	57.7	57.6	57.2	56.5	55.8	55.1	54.4	50.6	46.8
100°	70.5	70.0	69.5	69.3	68.4	66.5	64.6	62.7	60.8	56.8	52.8
102.5°	76.5	75.8	75.1	74.7	73.4	70.8	68.1	65.5	62.9	106.1	149.2
105°	79.2	78.2	77.3	76.8	75.5	72.9	70.3	67.7	65.1	129.8	194.5
107.5°	81.3	80.3	79.4	78.9	77.6	75.0	72.4	69.8	67.2	147.1	227.0
110°	82.4	81.4	80.5	80.0	91.9	115.6	139.3	163.0	186.7	255.2	323.7

TEST NUMBER: P998092

CATALOG NUMBER: SA2XXDIP-B290D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	83.9	83.2	82.5	82.1	133.2	235.4	337.6	439.8	542.0	546.0	550.0
115°	121.6	138.7	155.8	164.3	219.2	328.9	438.7	548.4	658.2	652.3	646.4
117.5°	408.0	470.1	532.2	563.3	580.3	614.2	648.1	682.0	715.9	711.9	707.8
120°	714.8	746.8	778.8	794.8	793.4	790.5	787.7	784.8	782.0	777.7	773.5
122.5°	852.0	851.7	851.5	851.4	850.7	849.2	847.8	846.3	844.9	840.2	835.4
125°	910.8	910.1	909.4	909.0	908.2	906.5	904.8	903.2	901.5	897.0	892.5
127.5°	965.0	964.8	964.5	964.4	963.2	960.9	958.5	956.2	953.8	950.2	946.7
130°	1015.0	1015.3	1015.5	1015.6	1014.3	1011.7	1009.1	1006.5	1003.9	1001.3	998.7
132.5°	1063.1	1063.3	1063.6	1063.7	1062.6	1060.5	1058.4	1056.2	1054.1	1051.5	1048.9
135°	1109.4	1109.9	1110.4	1110.6	1109.4	1107.0	1104.7	1102.3	1099.9	1097.8	1095.6
137.5°	1152.5	1153.2	1153.9	1154.3	1153.1	1150.8	1148.4	1146.1	1143.7	1141.3	1138.9
140°	1193.0	1194.1	1195.3	1195.9	1194.8	1192.7	1190.6	1188.4	1186.3	1183.7	1181.1
142.5°	1231.4	1232.6	1233.8	1234.4	1233.4	1231.5	1229.6	1227.7	1225.8	1222.7	1219.6
145°	1266.6	1267.8	1269.0	1269.6	1268.8	1267.1	1265.4	1263.8	1262.1	1258.1	1254.1
147.5°	1298.1	1299.1	1300.0	1300.5	1299.9	1298.7	1297.6	1296.4	1295.2	1291.2	1287.1
150°	1327.4	1328.6	1329.8	1330.4	1329.7	1328.3	1326.8	1325.4	1324.0	1320.2	1316.4
152.5°	1352.9	1354.5	1356.2	1357.0	1356.3	1354.9	1353.4	1352.0	1350.6	1347.0	1343.5
155°	1375.8	1377.7	1379.6	1380.5	1379.8	1378.4	1376.9	1375.5	1374.1	1371.3	1368.4
157.5°	1397.1	1399.0	1400.9	1401.8	1401.0	1399.3	1397.7	1396.0	1394.4	1392.3	1390.1
160°	1414.7	1416.4	1418.1	1418.9	1418.2	1416.8	1415.3	1413.9	1412.5	1411.1	1409.7
162.5°	1430.7	1432.8	1434.9	1436.0	1435.2	1433.5	1431.8	1430.2	1428.5	1427.3	1426.1
165°	1444.6	1446.3	1448.0	1448.8	1448.0	1446.3	1444.6	1443.0	1441.3	1440.6	1439.9
167.5°	1455.2	1457.3	1459.4	1460.5	1459.7	1458.0	1456.4	1454.7	1453.1	1452.4	1451.7
170°	1463.8	1465.9	1468.0	1469.1	1468.3	1466.6	1464.9	1463.3	1461.6	1461.1	1460.7
172.5°	1470.2	1472.3	1474.4	1475.5	1474.7	1473.0	1471.3	1469.7	1468.0	1467.5	1467.1
175°	1473.8	1476.2	1478.5	1479.7	1478.9	1477.2	1475.6	1473.9	1472.3	1471.8	1471.3
177.5°	1475.5	1477.6	1479.7	1480.8	1480.0	1478.3	1476.6	1475.0	1473.3	1473.1	1472.9
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P998092

CATALOG NUMBER: SA2XXDIP-B290D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	593.0	590.8	589.4	590.3	587.7	581.0	581.0	583.2	580.6	577.9	573.9
5°	609.4	605.0	602.3	601.9	595.7	585.0	582.8	580.6	574.8	568.6	561.9
7.5°	625.4	617.4	613.0	609.9	601.0	587.2	581.4	576.6	567.2	557.9	549.5
10°	638.7	627.2	621.9	617.0	605.4	588.1	578.8	569.9	557.9	545.9	535.2
12.5°	649.4	636.1	629.4	622.3	608.1	585.4	573.9	559.7	547.7	531.7	521.0
15°	667.2	639.6	633.4	626.8	612.1	581.0	566.8	550.8	534.4	513.0	501.5
17.5°	681.4	644.5	644.1	629.9	610.8	579.2	557.5	536.6	518.8	497.5	479.3
20°	689.8	652.1	645.0	630.3	606.3	567.2	544.6	521.5	502.4	476.6	458.4
22.5°	696.9	662.7	644.1	626.3	597.0	563.2	529.9	508.2	481.9	454.0	436.6
25°	699.6	665.0	645.4	625.0	590.3	551.7	513.9	490.4	461.1	435.7	412.2
27.5°	700.0	664.5	640.5	619.2	581.0	536.6	497.9	473.1	440.6	411.3	387.8
30°	695.6	659.6	637.9	614.8	572.1	522.8	478.4	450.9	416.2	386.9	362.5
32.5°	682.3	649.8	632.1	606.8	560.6	503.7	459.7	429.1	392.7	363.8	340.2
35°	660.1	637.9	618.3	594.8	545.5	485.9	441.1	405.1	368.2	340.7	318.5
37.5°	632.5	620.5	602.3	579.2	528.1	470.0	420.2	380.2	343.4	316.7	294.9
40°	595.2	598.3	580.6	559.7	507.7	448.2	393.1	354.9	320.3	295.4	274.1
42.5°	554.8	567.7	557.5	537.5	485.1	424.2	373.1	330.9	297.2	271.4	253.6
45°	511.3	533.5	527.3	512.6	461.5	398.9	344.7	303.8	274.1	249.2	233.6
47.5°	463.7	495.3	495.3	484.6	435.3	373.6	320.3	278.5	249.2	231.4	216.3
50°	415.3	450.9	456.6	449.5	406.0	344.7	290.5	252.7	227.4	210.1	199.0
52.5°	364.7	406.0	416.6	413.1	374.9	317.2	266.1	229.2	206.1	191.0	181.2
55°	316.3	364.2	375.8	377.1	341.6	286.9	239.0	206.5	184.3	174.1	165.7
57.5°	270.5	316.7	329.6	331.8	307.8	259.4	213.7	185.2	165.2	156.8	150.1
60°	231.4	270.1	286.9	291.8	271.0	227.4	190.1	162.6	147.5	139.5	133.3
62.5°	199.4	230.5	248.3	249.6	240.3	199.4	165.7	142.6	129.7	122.6	119.5
65°	168.3	196.3	207.0	212.3	204.8	172.8	143.0	123.9	113.7	107.5	104.4
67.5°	143.5	161.2	170.1	177.2	169.7	145.7	121.7	106.2	98.6	92.4	90.6
70°	117.7	132.4	139.0	146.1	139.5	121.3	103.9	89.7	83.1	78.2	76.0
72.5°	94.2	105.7	111.9	116.4	112.4	97.3	83.1	73.3	68.4	64.9	63.5
75°	74.6	82.6	86.2	89.3	87.5	76.0	67.1	59.1	54.6	51.5	50.6
77.5°	56.9	62.6	66.6	67.5	65.3	57.7	50.2	45.3	41.8	40.0	39.1
80°	40.4	44.0	46.2	47.5	45.3	42.2	36.9	33.3	30.2	28.0	27.5
82.5°	27.1	28.9	30.6	30.2	29.3	26.7	23.5	21.8	20.4	18.7	18.7
85°	15.5	16.0	16.9	17.3	16.9	15.1	13.3	12.4	11.5	10.2	10.2
87.5°	6.7	7.1	7.1	7.6	6.7	6.7	5.8	4.9	4.9	4.4	4.0
90°	15.6	13.7	12.8	11.5	8.9	6.3	3.7	1.1	3.7	6.3	8.9
92.5°	23.5	22.8	22.4	22.9	23.8	24.8	25.7	26.7	25.7	24.8	23.8
95°	36.6	34.9	34.1	38.0	45.8	53.7	61.5	69.3	61.5	53.7	45.8
97.5°	43.0	39.2	37.3	47.0	66.5	85.9	105.4	124.8	105.4	85.9	66.5
100°	48.7	44.7	42.7	58.9	91.4	123.9	156.3	188.8	156.3	123.9	91.4
102.5°	192.4	235.5	257.1	257.3	257.8	258.3	258.7	259.2	258.7	258.3	257.8
105°	259.2	323.9	356.3	352.7	345.6	338.5	331.4	324.3	331.4	338.5	345.6
107.5°	306.9	386.8	426.7	423.7	417.8	411.9	406.0	400.1	406.0	411.9	417.8
110°	392.2	460.7	495.0	492.5	487.5	482.6	477.6	472.6	477.6	482.6	487.5

TEST NUMBER: P998092

CATALOG NUMBER: SA2XXDIP-B290D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	554.1	558.1	560.1	558.0	553.7	549.4	545.2	540.9	545.2	549.4	553.7
115°	640.5	634.6	631.6	629.6	625.5	621.5	617.4	613.4	617.4	621.5	625.5
117.5°	703.8	699.7	697.7	695.3	690.6	685.9	681.1	676.4	681.1	685.9	690.6
120°	769.2	764.9	762.8	761.0	757.5	753.9	750.4	746.8	750.4	753.9	757.5
122.5°	830.7	826.0	823.6	821.7	817.9	814.1	810.3	806.5	810.3	814.1	817.9
125°	888.0	883.5	881.2	879.7	876.6	873.5	870.5	867.4	870.5	873.5	876.6
127.5°	943.1	939.6	937.8	936.1	932.8	929.5	926.1	922.8	926.1	929.5	932.8
130°	996.1	993.5	992.2	990.3	986.5	982.7	978.9	975.1	978.9	982.7	986.5
132.5°	1046.2	1043.6	1042.3	1040.8	1037.7	1034.6	1031.5	1028.4	1031.5	1034.6	1037.7
135°	1093.5	1091.4	1090.3	1088.4	1084.6	1080.9	1077.1	1073.3	1077.1	1080.9	1084.6
137.5°	1136.6	1134.2	1133.0	1131.6	1128.7	1125.9	1123.0	1120.2	1123.0	1125.9	1128.7
140°	1178.5	1175.9	1174.6	1173.7	1171.8	1169.9	1168.0	1166.1	1168.0	1169.9	1171.8
142.5°	1216.5	1213.4	1211.9	1211.1	1209.4	1207.8	1206.1	1204.5	1206.1	1207.8	1209.4
145°	1250.0	1246.0	1244.0	1244.1	1244.3	1244.6	1244.8	1245.0	1244.8	1244.6	1244.3
147.5°	1283.1	1279.0	1277.0	1277.4	1278.1	1278.8	1279.5	1280.2	1279.5	1278.8	1278.1
150°	1312.6	1308.8	1306.9	1307.7	1309.4	1311.1	1312.7	1314.4	1312.7	1311.1	1309.4
152.5°	1339.9	1336.4	1334.6	1335.6	1337.5	1339.4	1341.3	1343.2	1341.3	1339.4	1337.5
155°	1365.6	1362.7	1361.3	1362.4	1364.5	1366.6	1368.8	1370.9	1368.8	1366.6	1364.5
157.5°	1388.0	1385.9	1384.8	1385.7	1387.6	1389.5	1391.4	1393.3	1391.4	1389.5	1387.6
160°	1408.2	1406.8	1406.1	1406.8	1408.2	1409.7	1411.1	1412.5	1411.1	1409.7	1408.2
162.5°	1425.0	1423.8	1423.2	1423.9	1425.3	1426.8	1428.2	1429.6	1428.2	1426.8	1425.3
165°	1439.2	1438.5	1438.1	1438.8	1440.2	1441.7	1443.1	1444.5	1443.1	1441.7	1440.2
167.5°	1451.0	1450.3	1449.9	1450.6	1452.0	1453.5	1454.9	1456.3	1454.9	1453.5	1452.0
170°	1460.2	1459.7	1459.5	1460.2	1461.6	1463.1	1464.5	1465.9	1464.5	1463.1	1461.6
172.5°	1466.6	1466.1	1465.9	1466.6	1468.0	1469.5	1470.9	1472.3	1470.9	1469.5	1468.0
175°	1470.8	1470.3	1470.1	1470.9	1472.6	1474.3	1475.9	1477.6	1475.9	1474.3	1472.6
177.5°	1472.6	1472.4	1472.3	1473.1	1474.8	1476.4	1478.1	1479.7	1478.1	1476.4	1474.8
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P998092

CATALOG NUMBER: SA2XXDIP-B290D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	571.7	573.9	573.4	569.0	564.1	560.1	552.6	553.5	550.8	551.2	553.9
5°	557.5	557.5	555.7	549.5	541.5	537.0	528.6	526.4	521.0	520.6	520.1
7.5°	542.4	540.1	537.9	529.0	519.3	512.1	500.6	497.9	492.6	489.1	487.3
10°	524.6	521.5	517.0	506.8	494.8	485.9	473.9	470.4	460.2	455.7	453.1
12.5°	505.0	503.3	496.2	487.7	468.2	458.4	441.1	444.6	434.4	425.5	424.2
15°	485.5	478.8	474.8	461.1	437.5	433.1	419.3	412.2	402.9	395.8	395.8
17.5°	466.4	456.2	447.3	432.6	415.3	402.9	392.7	389.1	377.6	370.5	369.1
20°	441.1	429.5	427.3	406.4	394.4	380.7	370.9	362.0	353.6	350.5	348.2
22.5°	417.1	403.8	400.2	382.4	370.5	356.7	346.9	340.7	334.5	332.3	328.3
25°	391.3	383.3	378.0	358.9	345.6	332.7	326.0	321.6	315.8	315.4	312.7
27.5°	366.5	358.9	353.6	335.4	325.6	313.6	308.3	303.4	300.3	298.9	297.6
30°	345.1	336.7	330.5	317.2	305.2	295.4	290.9	287.8	286.1	283.8	283.4
32.5°	321.6	316.7	308.3	298.1	288.7	279.4	276.7	274.5	271.8	271.0	270.5
35°	301.6	294.9	289.6	278.1	274.1	266.1	263.0	261.2	257.6	256.7	255.9
37.5°	282.1	275.8	270.1	263.0	255.4	251.0	249.2	246.5	244.7	245.2	244.3
40°	262.5	257.6	253.2	245.6	241.2	239.0	235.4	232.8	231.9	232.3	231.9
42.5°	243.4	239.0	236.3	230.5	226.1	223.9	221.7	219.0	220.3	220.3	221.7
45°	226.1	222.1	220.3	215.9	213.2	209.7	207.4	207.0	208.8	208.3	208.3
47.5°	208.3	207.0	204.8	200.8	197.2	195.0	194.6	194.6	196.3	197.2	196.8
50°	194.6	191.9	189.2	186.1	183.4	182.6	181.2	182.1	183.9	183.9	184.8
52.5°	177.2	175.5	174.6	171.9	170.1	170.1	170.1	170.6	171.9	173.2	172.8
55°	162.1	160.8	159.9	158.6	156.4	156.8	156.4	157.2	158.6	159.9	160.8
57.5°	146.1	145.7	144.8	142.6	142.6	142.1	143.5	143.9	146.1	147.0	148.4
60°	131.9	130.6	130.6	128.8	128.8	128.8	130.1	131.5	133.3	133.7	134.6
62.5°	116.8	116.8	116.4	115.0	115.0	116.4	116.8	118.6	119.5	119.5	120.8
65°	102.6	102.2	101.7	102.2	102.6	102.6	103.9	104.8	105.7	106.2	106.6
67.5°	88.4	87.9	88.8	88.4	89.3	91.1	90.6	91.9	93.3	93.3	93.7
70°	75.1	76.0	75.5	76.4	76.0	76.8	78.2	78.6	78.6	79.1	80.4
72.5°	62.6	62.6	62.6	62.2	62.6	63.5	64.4	64.9	65.7	66.2	67.5
75°	50.6	50.6	49.7	50.6	50.6	51.5	52.4	52.4	52.4	53.3	54.6
77.5°	38.2	38.6	38.2	39.1	39.1	39.5	40.4	40.0	40.9	41.3	41.8
80°	28.0	27.5	27.5	27.5	28.0	28.0	28.9	29.3	29.3	30.6	29.8
82.5°	17.8	18.2	17.8	18.2	18.2	18.7	18.2	18.7	19.1	20.0	19.5
85°	10.2	9.8	9.8	10.2	9.8	9.8	10.2	9.8	10.2	9.8	10.2
87.5°	4.0	3.6	3.6	3.6	3.6	3.1	3.1	2.7	2.7	2.7	2.2
90°	11.5	12.8	13.7	15.6	17.5	19.4	21.3	22.5	23.7	24.9	26.1
92.5°	22.9	22.4	22.8	23.5	24.2	24.9	25.6	26.1	26.5	27.0	27.5
95°	38.0	34.1	34.9	36.6	38.3	39.9	41.6	42.8	44.0	45.1	46.3
97.5°	47.0	37.3	39.2	43.0	46.8	50.6	54.4	55.1	55.8	56.5	57.2
100°	58.9	42.7	44.7	48.7	52.8	56.8	60.8	62.7	64.6	66.5	68.4
102.5°	257.3	257.1	235.5	192.4	149.2	106.1	62.9	65.5	68.1	70.8	73.4
105°	352.7	356.3	323.9	259.2	194.5	129.8	65.1	67.7	70.3	72.9	75.5
107.5°	423.7	426.7	386.8	306.9	227.0	147.1	67.2	69.8	72.4	75.0	77.6
110°	492.5	495.0	460.7	392.2	323.7	255.2	186.7	163.0	139.3	115.6	91.9

TEST NUMBER: P998092

CATALOG NUMBER: SA2XXDIP-B290D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	558.0	560.1	558.1	554.1	550.0	546.0	542.0	439.8	337.6	235.4	133.2
115°	629.6	631.6	634.6	640.5	646.4	652.3	658.2	548.4	438.7	328.9	219.2
117.5°	695.3	697.7	699.7	703.8	707.8	711.9	715.9	682.0	648.1	614.2	580.3
120°	761.0	762.8	764.9	769.2	773.5	777.7	782.0	784.8	787.7	790.5	793.4
122.5°	821.7	823.6	826.0	830.7	835.4	840.2	844.9	846.3	847.8	849.2	850.7
125°	879.7	881.2	883.5	888.0	892.5	897.0	901.5	903.2	904.8	906.5	908.2
127.5°	936.1	937.8	939.6	943.1	946.7	950.2	953.8	956.2	958.5	960.9	963.2
130°	990.3	992.2	993.5	996.1	998.7	1001.3	1003.9	1006.5	1009.1	1011.7	1014.3
132.5°	1040.8	1042.3	1043.6	1046.2	1048.9	1051.5	1054.1	1056.2	1058.4	1060.5	1062.6
135°	1088.4	1090.3	1091.4	1093.5	1095.6	1097.8	1099.9	1102.3	1104.7	1107.0	1109.4
137.5°	1131.6	1133.0	1134.2	1136.6	1138.9	1141.3	1143.7	1146.1	1148.4	1150.8	1153.1
140°	1173.7	1174.6	1175.9	1178.5	1181.1	1183.7	1186.3	1188.4	1190.6	1192.7	1194.8
142.5°	1211.1	1211.9	1213.4	1216.5	1219.6	1222.7	1225.8	1227.7	1229.6	1231.5	1233.4
145°	1244.1	1244.0	1246.0	1250.0	1254.1	1258.1	1262.1	1263.8	1265.4	1267.1	1268.8
147.5°	1277.4	1277.0	1279.0	1283.1	1287.1	1291.2	1295.2	1296.4	1297.6	1298.7	1299.9
150°	1307.7	1306.9	1308.8	1312.6	1316.4	1320.2	1324.0	1325.4	1326.8	1328.3	1329.7
152.5°	1335.6	1334.6	1336.4	1339.9	1343.5	1347.0	1350.6	1352.0	1353.4	1354.9	1356.3
155°	1362.4	1361.3	1362.7	1365.6	1368.4	1371.3	1374.1	1375.5	1376.9	1378.4	1379.8
157.5°	1385.7	1384.8	1385.9	1388.0	1390.1	1392.3	1394.4	1396.0	1397.7	1399.3	1401.0
160°	1406.8	1406.1	1406.8	1408.2	1409.7	1411.1	1412.5	1413.9	1415.3	1416.8	1418.2
162.5°	1423.9	1423.2	1423.8	1425.0	1426.1	1427.3	1428.5	1430.2	1431.8	1433.5	1435.2
165°	1438.8	1438.1	1438.5	1439.2	1439.9	1440.6	1441.3	1443.0	1444.6	1446.3	1448.0
167.5°	1450.6	1449.9	1450.3	1451.0	1451.7	1452.4	1453.1	1454.7	1456.4	1458.0	1459.7
170°	1460.2	1459.5	1459.7	1460.2	1460.7	1461.1	1461.6	1463.3	1464.9	1466.6	1468.3
172.5°	1466.6	1465.9	1466.1	1466.6	1467.1	1467.5	1468.0	1469.7	1471.3	1473.0	1474.7
175°	1470.9	1470.1	1470.3	1470.8	1471.3	1471.8	1472.3	1473.9	1475.6	1477.2	1478.9
177.5°	1473.1	1472.3	1472.4	1472.6	1472.9	1473.1	1473.3	1475.0	1476.6	1478.3	1480.0
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P998092

CATALOG NUMBER: SA2XXDIP-B290D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	550.8	552.1	549.0	548.1	549.0	545.9	546.8	547.7	547.7	549.0	549.9
5°	518.8	517.0	513.9	513.0	512.1	513.5	512.6	513.9	514.4	517.5	517.9
7.5°	487.3	484.6	481.9	479.3	478.4	476.2	478.4	478.4	481.5	480.6	482.8
10°	450.0	449.5	446.0	444.6	442.9	439.3	444.2	442.9	445.1	449.1	450.0
12.5°	422.4	417.5	419.8	413.5	415.8	412.2	412.7	412.7	416.2	416.6	415.8
15°	396.2	392.2	386.4	383.8	382.4	380.7	386.4	386.9	384.2	390.4	388.2
17.5°	369.6	369.6	364.2	362.9	359.3	361.1	360.2	360.7	359.8	364.2	366.5
20°	346.5	344.2	342.5	342.9	338.5	337.6	336.7	337.6	340.7	343.8	344.7
22.5°	327.8	326.5	322.0	322.9	319.4	320.7	319.8	322.0	322.5	322.5	325.6
25°	310.0	308.3	308.7	306.9	305.6	305.6	304.3	305.6	307.4	308.3	308.7
27.5°	296.7	295.4	293.2	291.8	292.7	290.5	292.3	293.6	293.6	292.7	293.6
30°	280.7	281.6	281.6	277.2	279.0	278.1	279.4	280.3	280.3	280.7	279.8
32.5°	270.1	267.4	267.0	266.5	266.5	264.7	264.7	266.1	266.5	267.0	268.3
35°	255.9	255.9	253.6	255.0	253.2	253.6	253.2	253.6	254.5	253.2	254.5
37.5°	243.0	243.4	242.5	243.4	243.9	243.0	242.1	243.9	243.0	243.0	242.1
40°	231.9	231.4	231.9	231.9	231.9	232.3	231.4	231.4	231.4	230.5	229.6
42.5°	222.5	219.9	220.8	221.2	219.9	219.9	220.3	219.9	221.2	218.5	218.5
45°	209.2	208.3	208.8	208.8	209.7	208.3	209.2	209.7	208.3	207.9	207.0
47.5°	197.2	198.1	197.2	198.1	198.1	199.0	197.2	197.7	198.1	196.3	195.0
50°	185.2	185.2	186.6	186.1	186.6	185.7	185.7	185.2	185.7	184.8	183.4
52.5°	174.1	172.8	175.0	174.6	174.1	173.7	173.2	173.7	172.8	171.9	171.9
55°	160.4	160.4	161.7	162.1	162.1	161.2	160.4	160.8	160.4	159.9	159.5
57.5°	149.2	147.5	148.4	148.8	148.8	147.5	148.4	147.5	147.5	147.9	146.6
60°	135.0	135.0	134.1	135.5	135.5	134.6	134.6	135.0	134.1	133.7	133.3
62.5°	119.9	120.4	121.7	122.2	122.6	121.7	120.8	121.3	121.3	119.9	120.4
65°	107.0	107.9	109.7	109.3	108.4	108.8	107.9	108.4	107.0	107.5	106.2
67.5°	94.6	94.2	94.6	94.6	95.5	95.1	94.2	94.2	93.7	95.1	93.7
70°	81.3	81.3	81.3	81.3	81.7	82.2	81.3	80.4	80.8	80.0	79.5
72.5°	67.5	68.0	67.5	68.4	67.1	68.0	68.0	67.5	67.1	67.1	67.1
75°	54.6	55.5	54.2	54.6	54.2	55.1	54.6	54.6	53.7	53.3	53.7
77.5°	41.8	42.2	41.3	41.8	41.3	41.8	41.8	41.3	41.3	41.3	41.3
80°	29.8	30.2	29.8	29.3	28.9	29.8	28.9	29.3	29.8	29.3	30.2
82.5°	19.1	19.1	18.7	19.1	18.2	18.2	18.7	18.7	18.2	19.1	18.2
85°	9.3	9.3	10.2	9.3	8.9	8.9	8.9	9.3	8.9	9.8	9.3
87.5°	2.2	1.8	2.2	2.2	1.8	1.8	2.2	1.8	2.2	2.7	1.8
90°	26.7	26.9	27.4	27.9	28.3	28.8	28.3	27.9	27.4	26.9	26.7
92.5°	27.7	27.8	28.1	28.3	28.6	28.8	28.6	28.3	28.1	27.8	27.7
95°	46.9	46.8	46.6	46.3	46.1	45.9	46.1	46.3	46.6	46.8	46.9
97.5°	57.6	57.7	58.0	58.2	58.5	58.7	58.5	58.2	58.0	57.7	57.6
100°	69.3	69.5	70.0	70.5	71.0	71.5	71.0	70.5	70.0	69.5	69.3
102.5°	74.7	75.1	75.8	76.5	77.2	77.9	77.2	76.5	75.8	75.1	74.7
105°	76.8	77.3	78.2	79.2	80.1	81.1	80.1	79.2	78.2	77.3	76.8
107.5°	78.9	79.4	80.3	81.3	82.2	83.2	82.2	81.3	80.3	79.4	78.9
110°	80.0	80.5	81.4	82.4	83.3	84.3	83.3	82.4	81.4	80.5	80.0

TEST NUMBER: P998092

CATALOG NUMBER: SA2XXDIP-B290D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	82.1	82.5	83.2	83.9	84.6	85.3	84.6	83.9	83.2	82.5	82.1
115°	164.3	155.8	138.7	121.6	104.6	87.5	104.6	121.6	138.7	155.8	164.3
117.5°	563.3	532.2	470.1	408.0	345.9	283.8	345.9	408.0	470.1	532.2	563.3
120°	794.8	778.8	746.8	714.8	682.8	650.8	682.8	714.8	746.8	778.8	794.8
122.5°	851.4	851.5	851.7	852.0	852.2	852.4	852.2	852.0	851.7	851.5	851.4
125°	909.0	909.4	910.1	910.8	911.5	912.2	911.5	910.8	910.1	909.4	909.0
127.5°	964.4	964.5	964.8	965.0	965.3	965.5	965.3	965.0	964.8	964.5	964.4
130°	1015.6	1015.5	1015.3	1015.0	1014.8	1014.6	1014.8	1015.0	1015.3	1015.5	1015.6
132.5°	1063.7	1063.6	1063.3	1063.1	1062.8	1062.6	1062.8	1063.1	1063.3	1063.6	1063.7
135°	1110.6	1110.4	1109.9	1109.4	1109.0	1108.5	1109.0	1109.4	1109.9	1110.4	1110.6
137.5°	1154.3	1153.9	1153.2	1152.5	1151.8	1151.1	1151.8	1152.5	1153.2	1153.9	1154.3
140°	1195.9	1195.3	1194.1	1193.0	1191.8	1190.6	1191.8	1193.0	1194.1	1195.3	1195.9
142.5°	1234.4	1233.8	1232.6	1231.4	1230.2	1229.0	1230.2	1231.4	1232.6	1233.8	1234.4
145°	1269.6	1269.0	1267.8	1266.6	1265.4	1264.2	1265.4	1266.6	1267.8	1269.0	1269.6
147.5°	1300.5	1300.0	1299.1	1298.1	1297.2	1296.2	1297.2	1298.1	1299.1	1300.0	1300.5
150°	1330.4	1329.8	1328.6	1327.4	1326.2	1325.0	1326.2	1327.4	1328.6	1329.8	1330.4
152.5°	1357.0	1356.2	1354.5	1352.9	1351.2	1349.6	1351.2	1352.9	1354.5	1356.2	1357.0
155°	1380.5	1379.6	1377.7	1375.8	1373.9	1372.0	1373.9	1375.8	1377.7	1379.6	1380.5
157.5°	1401.8	1400.9	1399.0	1397.1	1395.2	1393.3	1395.2	1397.1	1399.0	1400.9	1401.8
160°	1418.9	1418.1	1416.4	1414.7	1413.1	1411.4	1413.1	1414.7	1416.4	1418.1	1418.9
162.5°	1436.0	1434.9	1432.8	1430.7	1428.5	1426.4	1428.5	1430.7	1432.8	1434.9	1436.0
165°	1448.8	1448.0	1446.3	1444.6	1443.0	1441.3	1443.0	1444.6	1446.3	1448.0	1448.8
167.5°	1460.5	1459.4	1457.3	1455.2	1453.0	1450.9	1453.0	1455.2	1457.3	1459.4	1460.5
170°	1469.1	1468.0	1465.9	1463.8	1461.6	1459.5	1461.6	1463.8	1465.9	1468.0	1469.1
172.5°	1475.5	1474.4	1472.3	1470.2	1468.0	1465.9	1468.0	1470.2	1472.3	1474.4	1475.5
175°	1479.7	1478.5	1476.2	1473.8	1471.5	1469.1	1471.5	1473.8	1476.2	1478.5	1479.7
177.5°	1480.8	1479.7	1477.6	1475.5	1473.3	1471.2	1473.3	1475.5	1477.6	1479.7	1480.8
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P998092

CATALOG NUMBER: SA2XXDIP-B290D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	548.6	552.1	550.8	545.9	551.7	551.7	555.7	555.7	560.6	562.3	565.0
5°	517.5	520.1	522.4	520.1	524.1	530.4	533.9	537.0	543.7	546.4	550.3
7.5°	484.2	489.1	491.3	491.3	497.9	505.0	512.1	516.6	525.9	529.5	533.5
10°	451.7	457.5	462.0	461.5	472.6	477.1	485.9	496.2	505.5	510.8	516.6
12.5°	417.5	420.6	426.9	435.7	438.4	446.4	456.6	469.5	486.4	491.3	499.7
15°	389.1	397.5	402.4	406.4	412.7	420.2	431.3	443.7	460.6	471.3	480.2
17.5°	365.1	376.2	379.3	378.4	386.4	398.0	410.9	420.2	435.3	448.2	456.6
20°	345.6	350.0	355.4	357.6	363.8	376.2	388.7	399.3	411.8	422.0	431.8
22.5°	326.0	329.6	334.0	338.0	342.9	350.0	362.0	375.3	387.3	397.1	408.2
25°	310.0	312.3	316.3	319.4	324.7	329.6	338.0	352.7	366.9	372.7	382.4
27.5°	294.5	296.3	298.9	302.5	305.2	310.0	317.6	329.6	344.2	350.0	363.3
30°	280.7	282.1	284.7	286.5	287.8	293.6	299.4	308.7	319.8	327.8	337.6
32.5°	267.8	269.2	271.8	272.3	274.1	277.2	282.5	290.9	300.7	307.4	315.8
35°	253.6	254.5	257.2	258.1	259.4	262.1	266.1	272.3	281.2	286.1	293.6
37.5°	242.5	242.1	243.9	245.2	247.0	248.3	249.6	255.9	262.5	267.0	272.7
40°	230.5	229.6	230.1	231.9	232.8	234.5	234.5	240.8	245.2	248.7	253.2
42.5°	218.5	218.1	217.2	218.1	219.0	219.4	219.9	224.3	228.8	231.9	236.8
45°	206.5	206.1	205.2	205.7	205.7	206.5	207.9	209.7	212.8	215.4	218.1
47.5°	195.4	194.6	193.2	192.8	193.7	193.7	193.7	195.4	198.6	199.4	202.1
50°	183.9	182.6	180.8	179.9	179.9	179.5	180.3	180.8	183.4	184.3	186.6
52.5°	171.5	170.6	168.8	167.0	167.5	166.6	167.0	167.5	168.3	169.7	171.0
55°	159.0	157.2	155.9	155.5	154.1	154.1	152.8	154.6	154.1	154.6	156.4
57.5°	147.0	145.2	143.0	142.1	140.8	140.4	139.5	139.0	139.5	140.8	142.1
60°	132.8	131.9	130.6	129.3	128.4	127.0	126.1	126.1	125.7	125.7	126.1
62.5°	119.0	118.6	116.8	116.4	115.5	114.6	113.3	112.4	112.4	113.3	113.7
65°	105.7	105.3	103.9	103.5	101.3	100.4	99.9	99.5	98.6	98.6	98.6
67.5°	93.3	91.9	91.9	89.7	87.9	87.1	86.2	85.7	85.7	85.7	86.2
70°	79.5	79.5	78.2	76.8	75.1	75.5	74.2	72.8	72.8	72.0	72.4
72.5°	66.2	65.7	64.4	64.0	62.6	61.3	60.4	61.3	60.0	59.5	60.0
75°	53.3	52.9	52.0	51.1	51.5	50.2	48.9	48.4	48.4	47.5	47.5
77.5°	40.9	41.8	40.0	39.5	38.6	37.8	37.3	36.9	36.9	36.9	37.8
80°	28.4	28.9	28.9	28.0	28.4	27.1	27.1	27.1	25.8	26.2	26.7
82.5°	18.2	18.2	17.8	18.2	17.8	17.8	17.3	17.3	16.9	16.9	17.3
85°	10.2	9.8	9.3	10.2	9.8	9.8	9.3	9.3	9.3	9.3	9.3
87.5°	2.2	2.7	2.7	2.7	2.7	3.1	3.1	3.1	3.6	3.6	3.6
90°	26.1	24.9	23.7	22.5	21.3	19.4	17.5	15.6	13.7	12.8	11.5
92.5°	27.5	27.0	26.5	26.1	25.6	24.9	24.2	23.5	22.8	22.4	22.9
95°	46.3	45.1	44.0	42.8	41.6	39.9	38.3	36.6	34.9	34.1	38.0
97.5°	57.2	56.5	55.8	55.1	54.4	50.6	46.8	43.0	39.2	37.3	47.0
100°	68.4	66.5	64.6	62.7	60.8	56.8	52.8	48.7	44.7	42.7	58.9
102.5°	73.4	70.8	68.1	65.5	62.9	106.1	149.2	192.4	235.5	257.1	257.3
105°	75.5	72.9	70.3	67.7	65.1	129.8	194.5	259.2	323.9	356.3	352.7
107.5°	77.6	75.0	72.4	69.8	67.2	147.1	227.0	306.9	386.8	426.7	423.7
110°	91.9	115.6	139.3	163.0	186.7	255.2	323.7	392.2	460.7	495.0	492.5

TEST NUMBER: P998092

CATALOG NUMBER: SA2XXDIP-B290D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	133.2	235.4	337.6	439.8	542.0	546.0	550.0	554.1	558.1	560.1	558.0
115°	219.2	328.9	438.7	548.4	658.2	652.3	646.4	640.5	634.6	631.6	629.6
117.5°	580.3	614.2	648.1	682.0	715.9	711.9	707.8	703.8	699.7	697.7	695.3
120°	793.4	790.5	787.7	784.8	782.0	777.7	773.5	769.2	764.9	762.8	761.0
122.5°	850.7	849.2	847.8	846.3	844.9	840.2	835.4	830.7	826.0	823.6	821.7
125°	908.2	906.5	904.8	903.2	901.5	897.0	892.5	888.0	883.5	881.2	879.7
127.5°	963.2	960.9	958.5	956.2	953.8	950.2	946.7	943.1	939.6	937.8	936.1
130°	1014.3	1011.7	1009.1	1006.5	1003.9	1001.3	998.7	996.1	993.5	992.2	990.3
132.5°	1062.6	1060.5	1058.4	1056.2	1054.1	1051.5	1048.9	1046.2	1043.6	1042.3	1040.8
135°	1109.4	1107.0	1104.7	1102.3	1099.9	1097.8	1095.6	1093.5	1091.4	1090.3	1088.4
137.5°	1153.1	1150.8	1148.4	1146.1	1143.7	1141.3	1138.9	1136.6	1134.2	1133.0	1131.6
140°	1194.8	1192.7	1190.6	1188.4	1186.3	1183.7	1181.1	1178.5	1175.9	1174.6	1173.7
142.5°	1233.4	1231.5	1229.6	1227.7	1225.8	1222.7	1219.6	1216.5	1213.4	1211.9	1211.1
145°	1268.8	1267.1	1265.4	1263.8	1262.1	1258.1	1254.1	1250.0	1246.0	1244.0	1244.1
147.5°	1299.9	1298.7	1297.6	1296.4	1295.2	1291.2	1287.1	1283.1	1279.0	1277.0	1277.4
150°	1329.7	1328.3	1326.8	1325.4	1324.0	1320.2	1316.4	1312.6	1308.8	1306.9	1307.7
152.5°	1356.3	1354.9	1353.4	1352.0	1350.6	1347.0	1343.5	1339.9	1336.4	1334.6	1335.6
155°	1379.8	1378.4	1376.9	1375.5	1374.1	1371.3	1368.4	1365.6	1362.7	1361.3	1362.4
157.5°	1401.0	1399.3	1397.7	1396.0	1394.4	1392.3	1390.1	1388.0	1385.9	1384.8	1385.7
160°	1418.2	1416.8	1415.3	1413.9	1412.5	1411.1	1409.7	1408.2	1406.8	1406.1	1406.8
162.5°	1435.2	1433.5	1431.8	1430.2	1428.5	1427.3	1426.1	1425.0	1423.8	1423.2	1423.9
165°	1448.0	1446.3	1444.6	1443.0	1441.3	1440.6	1439.9	1439.2	1438.5	1438.1	1438.8
167.5°	1459.7	1458.0	1456.4	1454.7	1453.1	1452.4	1451.7	1451.0	1450.3	1449.9	1450.6
170°	1468.3	1466.6	1464.9	1463.3	1461.6	1461.1	1460.7	1460.2	1459.7	1459.5	1460.2
172.5°	1474.7	1473.0	1471.3	1469.7	1468.0	1467.5	1467.1	1466.6	1466.1	1465.9	1466.6
175°	1478.9	1477.2	1475.6	1473.9	1472.3	1471.8	1471.3	1470.8	1470.3	1470.1	1470.9
177.5°	1480.0	1478.3	1476.6	1475.0	1473.3	1473.1	1472.9	1472.6	1472.4	1472.3	1473.1
180°	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P998092

CATALOG NUMBER: SA2XXDIP-B290D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	577.9	577.9	577.9	577.9
2.5°	567.2	567.2	573.9	581.0
5°	554.8	557.9	568.6	578.3
7.5°	542.8	548.1	561.5	573.9
10°	528.1	535.2	551.7	566.3
12.5°	513.9	520.6	539.7	556.1
15°	493.9	502.4	522.8	543.2
17.5°	473.9	482.4	507.3	531.2
20°	450.4	461.5	489.5	521.5
22.5°	428.6	442.4	473.5	499.3
25°	404.7	426.0	454.8	488.2
27.5°	383.3	404.7	434.0	467.7
30°	359.3	381.1	411.3	442.4
32.5°	336.3	356.2	385.6	423.8
35°	312.3	331.4	359.8	398.4
37.5°	290.5	309.2	340.2	375.8
40°	269.2	288.7	315.4	350.9
42.5°	249.2	266.5	290.5	326.0
45°	231.0	243.4	265.6	298.9
47.5°	211.9	223.0	243.4	276.7
50°	194.1	203.4	221.2	252.3
52.5°	176.8	184.8	201.2	226.1
55°	161.2	168.8	180.8	205.2
57.5°	145.2	151.0	162.6	182.1
60°	129.7	135.0	144.4	160.4
62.5°	114.2	118.6	127.5	140.4
65°	100.4	103.9	110.6	121.7
67.5°	87.1	89.3	94.6	103.5
70°	74.2	76.0	80.4	87.5
72.5°	60.4	62.2	67.1	72.0
75°	48.9	49.3	52.9	56.9
77.5°	38.2	37.8	40.4	43.5
80°	26.2	27.5	29.8	31.1
82.5°	17.8	18.2	19.1	20.0
85°	9.8	10.2	10.2	11.5
87.5°	4.0	4.4	4.4	4.9
90°	8.9	6.3	3.7	1.1
92.5°	23.8	24.8	25.7	26.7
95°	45.8	53.7	61.5	69.3
97.5°	66.5	85.9	105.4	124.8
100°	91.4	123.9	156.3	188.8
102.5°	257.8	258.3	258.7	259.2
105°	345.6	338.5	331.4	324.3
107.5°	417.8	411.9	406.0	400.1
110°	487.5	482.6	477.6	472.6

TEST NUMBER: P998092

CATALOG NUMBER: SA2XXDIP-B290D1080UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	553.7	549.4	545.2	540.9
115°	625.5	621.5	617.4	613.4
117.5°	690.6	685.9	681.1	676.4
120°	757.5	753.9	750.4	746.8
122.5°	817.9	814.1	810.3	806.5
125°	876.6	873.5	870.5	867.4
127.5°	932.8	929.5	926.1	922.8
130°	986.5	982.7	978.9	975.1
132.5°	1037.7	1034.6	1031.5	1028.4
135°	1084.6	1080.9	1077.1	1073.3
137.5°	1128.7	1125.9	1123.0	1120.2
140°	1171.8	1169.9	1168.0	1166.1
142.5°	1209.4	1207.8	1206.1	1204.5
145°	1244.3	1244.6	1244.8	1245.0
147.5°	1278.1	1278.8	1279.5	1280.2
150°	1309.4	1311.1	1312.7	1314.4
152.5°	1337.5	1339.4	1341.3	1343.2
155°	1364.5	1366.6	1368.8	1370.9
157.5°	1387.6	1389.5	1391.4	1393.3
160°	1408.2	1409.7	1411.1	1412.5
162.5°	1425.3	1426.8	1428.2	1429.6
165°	1440.2	1441.7	1443.1	1444.5
167.5°	1452.0	1453.5	1454.9	1456.3
170°	1461.6	1463.1	1464.5	1465.9
172.5°	1468.0	1469.5	1470.9	1472.3
175°	1472.6	1474.3	1475.9	1477.6
177.5°	1474.8	1476.4	1478.1	1479.7
180°	1474.4	1474.4	1474.4	1474.4

TEST NUMBER: P998092

CATALOG NUMBER: SA2XXDIP-B290D1080UB2750-4F0-XX-W2A-A_3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.20	10.84	11.36	11.99	13.61	7.69	8.34	8.86	9.49	11.10
	3H	10.99	11.57	12.16	12.73	14.36	9.02	9.60	10.19	10.75	12.38
	4H	11.15	11.70	12.33	12.86	14.49	9.47	10.02	10.65	11.18	12.81
	6H	11.19	11.69	12.37	12.85	14.49	9.77	10.27	10.96	11.43	13.08
	8H	11.16	11.64	12.35	12.81	14.45	9.85	10.33	11.03	11.50	13.13
	12H	11.11	11.57	12.31	12.74	14.39	9.88	10.34	11.07	11.50	13.16
4H	2H	10.21	10.76	11.40	11.92	13.55	8.11	8.66	9.30	9.82	11.45
	3H	11.17	11.63	12.37	12.81	14.46	9.55	10.01	10.74	11.19	12.84
	4H	11.44	11.87	12.64	13.03	14.70	10.08	10.50	11.27	11.67	13.33
	6H	11.56	11.92	12.76	13.11	14.77	10.45	10.81	11.64	12.00	13.65
	8H	11.56	11.89	12.75	13.07	14.74	10.55	10.89	11.75	12.07	13.74
	12H	11.51	11.82	12.72	13.01	14.68	10.60	10.90	11.81	12.10	13.77
8H	4H	11.44	11.77	12.63	12.95	14.62	10.20	10.54	11.40	11.72	13.39
	6H	11.61	11.88	12.82	13.11	14.77	10.63	10.91	11.85	12.13	13.80
	8H	11.64	11.88	12.85	13.08	14.76	10.78	11.02	12.00	12.22	13.91
	12H	11.61	11.82	12.83	13.02	14.74	10.86	11.07	12.09	12.27	13.99
12H	4H	11.38	11.69	12.59	12.88	14.55	10.17	10.47	11.38	11.67	13.34
	6H	11.58	11.83	12.80	13.03	14.71	10.63	10.87	11.85	12.07	13.76
	8H	11.61	11.82	12.83	13.02	14.74	10.78	10.99	12.00	12.19	13.91