

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000074

Luminaire Tested: SA2XXRDIP-B865D1080UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000074
REPORT IS A COMBINATION OF REPORTS P988631 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D1080UB2750-4F0-XX-W2A-F_3500K
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7335.0 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000074

CATALOG NUMBER: SA2XXRDIP-B865D1080UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1000074

CATALOG NUMBER: SA2XXRDIP-B865D1080UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41		
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	35		
2	88	81	75	70	80	74	69	65	61	58	54	49	47	45	38	37	35	30		
3	80	71	64	59	73	65	59	55	54	50	46	44	41	38	34	32	31	26		
4	74	63	56	50	67	58	52	47	48	44	40	39	36	33	31	29	27	23		
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23	20		
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18		
7	58	46	38	33	53	42	36	31	36	30	27	29	26	23	23	21	19	16		
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	14		
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13		
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23168	23168	23168
5°	23205	22040	21878
10°	22975	20905	20215
15°	22660	19562	18318
20°	22242	18036	16337
25°	21815	16472	14523
30°	21240	14947	12542
35°	20676	13409	10840
40°	20106	11900	9088
45°	19440	10340	7560
50°	18751	8839	6156
55°	18034	7337	4886
60°	17202	5867	3698
65°	16243	4474	3006
70°	15084	3244	2390
75°	13633	2476	1826
80°	11529	1676	1226
85°	8052	768	593

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19440 cd/sqm

TEST NUMBER: P1000074

CATALOG NUMBER: SA2XXRDIP-B865D1080UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.2	1.9
10°-20°	376.6	5.1
20°-30°	528.7	7.2
30°-40°	576.3	7.9
40°-50°	529.7	7.2
50°-60°	416.0	5.7
60°-70°	270.7	3.7
70°-80°	139.4	1.9
80°-90°	38.2	0.5
90°-100°	48.6	0.7
100°-110°	181.2	2.5
110°-120°	480.7	6.6
120°-130°	797.2	10.9
130°-140°	846.8	11.5
140°-150°	787.0	10.7
150°-160°	632.7	8.6
160°-170°	407.7	5.6
170°-180°	140.3	1.9
0°-30°	1042.4	14.2
0°-40°	1618.7	22.1
0°-60°	2564.3	35.0
0°-90°	3012.6	41.1
90°-120°	710.5	9.7
90°-150°	3141.6	42.8
90°-180°	4322.0	58.9
0°-180°	7335.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1464	1464	1464	1464	1464	
5°	1464	1457	1440	1452	1448	139
15°	1392	1378	1332	1307	1294	392
25°	1264	1221	1134	1080	1060	581
35°	1089	1021	905	821	792	681
45°	890	801	662	568	536	687
55°	677	574	430	351	326	605
65°	457	350	230	185	182	453
75°	244	151	106	97	95	258
85°	57	29	25	25	25	65
90°	1	13	21	27	29	7
95°	69	34	42	47	46	82
105°	324	356	65	77	81	347
115°	613	632	658	164	88	604
125°	867	881	902	909	912	774
135°	1073	1090	1100	1111	1108	829
145°	1245	1244	1262	1270	1264	779
155°	1371	1361	1374	1380	1372	632
165°	1444	1438	1441	1449	1441	408
175°	1478	1470	1472	1480	1469	141
180°	1474	1474	1474	1474	1474	

TEST NUMBER: P1000074

CATALOG NUMBER: SA2XXRDIP-B865D1080UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1463.6	1463.6	1463.6	1463.6	1463.6
2.5°	1470.2	1463.6	1449.0	1462.2	1459.6
5°	1463.6	1456.9	1439.7	1451.6	1447.7
7.5°	1451.6	1443.7	1425.2	1430.4	1423.8
10°	1435.7	1426.5	1400.0	1396.0	1388.1
12.5°	1415.9	1404.0	1368.2	1360.3	1345.7
15°	1392.0	1377.5	1332.4	1307.3	1294.0
17.5°	1364.2	1343.0	1287.4	1258.3	1237.1
20°	1332.4	1305.9	1239.7	1206.6	1177.5
22.5°	1298.0	1267.5	1190.7	1145.7	1125.8
25°	1263.6	1221.2	1133.8	1079.5	1059.6
27.5°	1222.5	1177.5	1080.8	1018.5	988.1
30°	1178.8	1128.5	1022.5	955.0	919.2
32.5°	1136.4	1075.5	966.9	887.4	854.3
35°	1088.7	1021.2	904.6	821.2	792.0
37.5°	1042.4	969.5	846.3	755.0	721.8
40°	993.4	913.9	785.4	691.4	656.9
42.5°	943.0	858.3	724.5	626.5	593.4
45°	890.1	801.3	662.2	568.2	536.4
47.5°	839.7	745.7	602.6	508.6	479.5
50°	784.1	690.1	544.4	453.0	425.2
52.5°	729.8	630.5	488.7	401.3	376.2
55°	676.8	573.5	430.5	351.0	325.8
57.5°	622.5	516.6	378.8	304.6	283.4
60°	566.9	460.9	324.5	257.0	235.8
62.5°	512.6	406.6	278.1	214.6	204.0
65°	456.9	349.7	230.5	185.4	181.5
67.5°	404.0	296.7	185.4	162.9	158.9
70°	348.3	245.0	153.6	140.4	135.1
72.5°	295.4	197.3	128.5	117.9	115.2
75°	243.7	151.0	106.0	96.7	95.4
77.5°	192.1	107.3	83.4	78.1	75.5
80°	144.4	76.8	63.6	58.3	58.3
82.5°	100.7	51.7	43.7	41.1	41.1
85°	57.0	29.1	25.2	25.2	25.2
87.5°	21.2	10.6	10.6	9.3	9.3
90°	1.1	12.8	21.3	26.7	28.8
92.5°	26.7	22.4	25.6	27.7	28.8
95°	69.3	34.1	41.6	46.9	45.9
97.5°	124.8	37.3	54.4	57.6	58.7
100°	188.8	42.7	60.8	69.3	71.5
102.5°	259.2	257.1	62.9	74.7	77.9
105°	324.3	356.3	65.1	76.8	81.1
107.5°	400.1	426.7	67.2	78.9	83.2
110°	472.6	495.0	186.7	80.0	84.3

TEST NUMBER: P1000074

CATALOG NUMBER: SA2XXRDIP-B865D1080UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	540.9	560.1	542.0	82.1	85.3
115°	613.4	631.6	658.2	164.3	87.5
117.5°	676.4	697.7	715.9	563.3	283.8
120°	746.8	762.8	782.0	794.8	650.8
122.5°	806.5	823.6	844.9	851.4	852.4
125°	867.4	881.2	901.5	909.0	912.2
127.5°	922.8	937.8	953.8	964.4	965.5
130°	975.1	992.2	1003.9	1015.6	1014.6
132.5°	1028.4	1042.3	1054.1	1063.7	1062.6
135°	1073.3	1090.3	1099.9	1110.6	1108.5
137.5°	1120.2	1133.0	1143.7	1154.3	1151.1
140°	1166.1	1174.6	1186.3	1195.9	1190.6
142.5°	1204.5	1211.9	1225.8	1234.4	1229.0
145°	1245.0	1244.0	1262.1	1269.6	1264.2
147.5°	1280.2	1277.0	1295.2	1300.5	1296.2
150°	1314.4	1306.9	1324.0	1330.4	1325.0
152.5°	1343.2	1334.6	1350.6	1357.0	1349.6
155°	1370.9	1361.3	1374.1	1380.5	1372.0
157.5°	1393.3	1384.8	1394.4	1401.8	1393.3
160°	1412.5	1406.1	1412.5	1418.9	1411.4
162.5°	1429.6	1423.2	1428.5	1436.0	1426.4
165°	1444.5	1438.1	1441.3	1448.8	1441.3
167.5°	1456.3	1449.9	1453.1	1460.5	1450.9
170°	1465.9	1459.5	1461.6	1469.1	1459.5
172.5°	1472.3	1465.9	1468.0	1475.5	1465.9
175°	1477.6	1470.1	1472.3	1479.7	1469.1
177.5°	1479.7	1472.3	1473.3	1480.8	1471.2
180°	1474.4	1474.4	1474.4	1474.4	1474.4

(END OF REPORT)