

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000114

Luminaire Tested: SA2XXRDIP-B865D330UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000114
REPORT IS A COMBINATION OF REPORTS P988674 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D330UB2750-4F0-XX-W2A-F_5000K
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4150.0 lumens
Efficiency: N/A
Efficacy: 74.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000114

CATALOG NUMBER: SA2XXRDIP-B865D330UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1000114

CATALOG NUMBER: SA2XXRDIP-B865D330UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	69		
1	103	99	95	91	97	93	90	87	84	81	79	75	73	71	66	65	64	60		
2	94	87	81	76	89	82	77	73	74	70	66	66	63	60	59	57	55	51		
3	86	77	70	64	81	73	67	62	66	61	57	59	55	52	53	50	47	44		
4	79	69	61	55	75	65	58	53	59	54	49	53	49	45	48	44	41	39		
5	73	62	54	48	69	59	52	46	53	47	43	48	43	40	44	40	37	34		
6	68	56	48	42	64	53	46	41	48	42	38	44	39	35	40	36	33	30		
7	63	51	43	37	60	48	41	36	44	38	34	40	35	31	37	32	29	27		
8	59	46	39	33	55	44	37	32	41	35	30	37	32	28	34	30	26	24		
9	55	43	35	30	52	41	34	29	37	32	27	34	29	26	31	27	24	22		
10	51	39	32	27	49	38	31	26	35	29	25	32	27	23	29	25	22	20		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22182	22182	22182
5°	22218	21103	20947
10°	21999	20016	19354
15°	21696	18731	17540
20°	21297	17270	15642
25°	20886	15770	13905
30°	20337	14311	12008
35°	19797	12840	10380
40°	19249	11394	8702
45°	18612	9901	7239
50°	17954	8462	5894
55°	17267	7025	4679
60°	16471	5617	3539
65°	15553	4283	2877
70°	14443	3107	2289
75°	13051	2371	1748
80°	11034	1605	1173
85°	7698	735	567

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18612 cd/sqm

TEST NUMBER: P1000114

CATALOG NUMBER: SA2XXRDIP-B865D330UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.3	3.2
10°-20°	360.5	8.7
20°-30°	506.2	12.2
30°-40°	551.8	13.3
40°-50°	507.1	12.2
50°-60°	398.3	9.6
60°-70°	259.2	6.2
70°-80°	133.5	3.2
80°-90°	34.8	0.8
90°-100°	14.3	0.3
100°-110°	53.1	1.3
110°-120°	140.9	3.4
120°-130°	233.7	5.6
130°-140°	248.3	6.0
140°-150°	230.7	5.6
150°-160°	185.5	4.5
160°-170°	119.5	2.9
170°-180°	41.1	1.0
0°-30°	998.1	24.0
0°-40°	1549.8	37.3
0°-60°	2455.2	59.2
0°-90°	2882.8	69.5
90°-120°	208.3	5.0
90°-150°	921.1	22.2
90°-180°	1267.0	30.5
0°-180°	4150.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1401	1401	1401	1401	1401	
5°	1401	1395	1378	1390	1386	133
15°	1333	1319	1276	1252	1239	376
25°	1210	1169	1086	1034	1014	556
35°	1042	978	866	786	758	652
45°	852	767	634	544	514	658
55°	648	549	412	336	312	579
65°	438	335	221	178	174	434
75°	233	145	102	93	91	247
85°	54	28	24	24	24	63
90°	0	4	6	8	8	4
95°	20	10	12	14	13	24
105°	95	104	19	22	24	102
115°	180	185	193	48	26	177
125°	254	258	264	266	267	227
135°	315	320	322	326	325	243
145°	365	365	370	372	371	228
155°	402	399	403	405	402	185
165°	424	422	423	425	423	120
175°	433	431	432	434	431	41
180°	432	432	432	432	432	

TEST NUMBER: P1000114

CATALOG NUMBER: SA2XXRDIP-B865D330UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1401.3	1401.3	1401.3	1401.3	1401.3
2.5°	1407.7	1401.3	1387.4	1400.1	1397.5
5°	1401.3	1395.0	1378.5	1389.9	1386.1
7.5°	1389.9	1382.3	1364.5	1369.6	1363.3
10°	1374.7	1365.8	1340.5	1336.6	1329.0
12.5°	1355.7	1344.3	1310.0	1302.4	1288.5
15°	1332.8	1318.9	1275.8	1251.7	1239.0
17.5°	1306.2	1285.9	1232.7	1204.8	1184.5
20°	1275.8	1250.4	1187.0	1155.3	1127.4
22.5°	1242.8	1213.6	1140.1	1097.0	1077.9
25°	1209.8	1169.2	1085.5	1033.6	1014.5
27.5°	1170.5	1127.4	1034.8	975.2	946.1
30°	1128.7	1080.5	979.0	914.3	880.1
32.5°	1088.1	1029.8	925.8	849.7	818.0
35°	1042.4	977.8	866.2	786.3	758.4
37.5°	998.0	928.3	810.4	722.9	691.2
40°	951.1	875.0	752.0	662.0	629.0
42.5°	902.9	821.8	693.7	599.8	568.1
45°	852.2	767.2	634.1	544.0	513.6
47.5°	804.0	714.0	577.0	487.0	459.1
50°	750.8	660.7	521.2	433.7	407.1
52.5°	698.8	603.6	468.0	384.3	360.2
55°	648.0	549.1	412.2	336.1	312.0
57.5°	596.0	494.6	362.7	291.7	271.4
60°	542.8	441.3	310.7	246.0	225.7
62.5°	490.8	389.3	266.3	205.4	195.3
65°	437.5	334.8	220.7	177.5	173.7
67.5°	386.8	284.1	177.5	156.0	152.2
70°	333.5	234.6	147.1	134.4	129.4
72.5°	282.8	189.0	123.0	112.9	110.3
75°	233.3	144.6	101.5	92.6	91.3
77.5°	183.9	102.7	79.9	74.8	72.3
80°	138.2	73.6	60.9	55.8	55.8
82.5°	96.4	49.5	41.8	39.3	39.3
85°	54.5	27.9	24.1	24.1	24.1
87.5°	20.3	10.1	10.1	8.9	8.9
90°	0.3	3.8	6.3	7.8	8.4
92.5°	7.8	6.6	7.5	8.1	8.4
95°	20.3	10.0	12.2	13.8	13.4
97.5°	36.6	10.9	16.0	16.9	17.2
100°	55.4	12.5	17.8	20.3	21.0
102.5°	76.0	75.4	18.5	21.9	22.8
105°	95.1	104.5	19.1	22.5	23.8
107.5°	117.3	125.1	19.7	23.1	24.4
110°	138.6	145.1	54.7	23.5	24.7

TEST NUMBER: P1000114

CATALOG NUMBER: SA2XXRDIP-B865D330UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	158.6	164.2	158.9	24.1	25.0
115°	179.8	185.2	193.0	48.2	25.6
117.5°	198.3	204.6	209.9	165.1	83.2
120°	218.9	223.6	229.3	233.0	190.8
122.5°	236.5	241.5	247.7	249.6	249.9
125°	254.3	258.4	264.3	266.5	267.4
127.5°	270.6	274.9	279.6	282.8	283.1
130°	285.9	290.9	294.3	297.8	297.5
132.5°	301.5	305.6	309.0	311.8	311.5
135°	314.7	319.7	322.5	325.6	325.0
137.5°	328.4	332.2	335.3	338.4	337.5
140°	341.9	344.4	347.8	350.6	349.1
142.5°	353.1	355.3	359.4	361.9	360.3
145°	365.0	364.7	370.0	372.2	370.6
147.5°	375.3	374.4	379.7	381.3	380.0
150°	385.3	383.2	388.2	390.0	388.5
152.5°	393.8	391.3	396.0	397.9	395.7
155°	401.9	399.1	402.9	404.7	402.2
157.5°	408.5	406.0	408.8	411.0	408.5
160°	414.1	412.2	414.1	416.0	413.8
162.5°	419.1	417.2	418.8	421.0	418.2
165°	423.5	421.6	422.6	424.8	422.6
167.5°	426.9	425.1	426.0	428.2	425.4
170°	429.8	427.9	428.5	430.7	427.9
172.5°	431.6	429.8	430.4	432.6	429.8
175°	433.2	431.0	431.6	433.8	430.7
177.5°	433.8	431.6	431.9	434.1	431.3
180°	432.3	432.3	432.3	432.3	432.3

(END OF REPORT)