

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998216

Luminaire Tested: SA2XXDIP-B290D530UB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998216
REPORT IS A COMBINATION OF REPORTS P983956 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B290D530UB2750-4F0-XX-W2A-D_5000K
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3157.1 lumens
Efficiency: N/A
Efficacy: 111.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998216

CATALOG NUMBER: SA2XXDIP-B290D530UB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P998216

CATALOG NUMBER: SA2XXDIP-B290D530UB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39
1	93	88	84	80	83	79	76	73	63	60	58	47	46	44	33	32	31
2	84	76	70	65	75	69	63	59	54	50	47	41	38	36	29	27	25
3	76	67	59	53	68	60	54	49	47	43	39	36	33	30	25	23	21
4	70	59	51	45	62	53	46	41	42	37	33	32	28	25	22	20	18
5	64	52	44	38	57	47	40	35	37	32	28	28	25	22	20	17	16
6	59	46	38	33	52	42	35	30	33	28	24	25	22	19	18	15	14
7	54	42	34	28	48	38	31	26	30	25	21	23	19	17	16	14	12
8	50	38	30	25	45	34	27	23	27	22	19	21	17	15	15	12	11
9	46	34	27	22	42	31	25	20	25	20	17	19	16	13	14	11	9
10	43	31	24	19	39	28	22	18	23	18	15	18	14	12	13	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4643	4643	4643
5°	4663	4444	4419
10°	4631	4290	4228
15°	4566	4131	4032
20°	4484	3963	3845
25°	4402	3803	3676
30°	4288	3641	3508
35°	4172	3483	3386
40°	4052	3348	3264
45°	3936	3226	3157
50°	3812	3112	3052
55°	3680	2991	2946
60°	3520	2866	2832
65°	3356	2723	2703
70°	3166	2568	2563
75°	2926	2413	2433
80°	2547	2250	2296
85°	2161	2101	2180

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3936 cd/sqm

TEST NUMBER: P998216

CATALOG NUMBER: SA2XXDIP-B290D530UB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.8	0.9
10°-20°	79.7	2.5
20°-30°	120.8	3.8
30°-40°	147.1	4.7
40°-50°	158.3	5.0
50°-60°	153.7	4.9
60°-70°	134.3	4.3
70°-80°	103.3	3.3
80°-90°	70.4	2.2
90°-100°	70.7	2.2
100°-110°	120.3	3.8
110°-120°	249.5	7.9
120°-130°	388.5	12.3
130°-140°	404.4	12.8
140°-150°	371.8	11.8
150°-160°	298.2	9.4
160°-170°	192.1	6.1
170°-180°	66.1	2.1
0°-30°	228.3	7.2
0°-40°	375.5	11.9
0°-60°	687.5	21.8
0°-90°	995.5	31.5
90°-120°	440.5	14.0
90°-150°	1605.2	50.8
90°-180°	2162.0	68.5
0°-180°	3157.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	293	293	293	293	293	
5°	294	293	290	293	292	28
15°	280	281	281	285	285	79
25°	255	258	262	267	268	117
35°	220	227	235	244	247	137
45°	180	192	207	220	224	139
55°	138	153	176	191	196	124
65°	94	115	140	158	163	94
75°	52	76	103	122	127	55
85°	15	42	69	87	93	16
90°	5	35	66	86	92	5
95°	36	40	68	87	92	41
105°	155	182	67	88	94	166
115°	291	304	336	116	84	286
125°	410	416	439	454	460	365
135°	506	514	523	537	539	391
145°	587	586	595	601	600	367
155°	646	642	648	650	646	298
165°	681	678	679	683	679	192
175°	696	693	694	697	692	66
180°	695	695	695	695	695	

TEST NUMBER: P998216

CATALOG NUMBER: SA2XXDIP-B290D530UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	293.3	293.3	293.3	293.3	293.3
2.5°	295.4	294.1	291.1	293.3	292.4
5°	294.1	292.8	290.3	292.8	292.4
7.5°	292.0	291.1	289.0	292.0	291.6
10°	289.4	288.6	287.3	290.7	290.3
12.5°	285.2	285.6	284.8	288.2	287.7
15°	280.5	281.4	281.4	285.2	284.8
17.5°	274.6	276.3	277.5	281.4	281.4
20°	268.6	270.7	272.4	277.1	277.1
22.5°	262.2	264.8	267.3	272.0	272.9
25°	255.0	258.0	261.8	266.9	268.2
27.5°	246.5	251.2	255.4	261.8	262.7
30°	238.0	243.5	249.1	255.9	257.1
32.5°	228.7	235.0	241.8	249.9	252.5
35°	219.7	227.0	235.0	244.4	247.4
37.5°	210.0	218.0	228.2	238.4	241.4
40°	200.2	209.5	221.0	232.1	235.9
42.5°	190.8	200.2	213.8	226.1	229.9
45°	180.2	191.7	206.6	219.7	224.0
47.5°	170.0	182.3	199.3	212.9	217.6
50°	159.4	172.6	191.7	206.1	210.8
52.5°	149.2	163.2	183.6	198.5	203.6
55°	138.1	153.4	175.5	190.8	196.4
57.5°	127.5	144.5	166.6	183.2	188.7
60°	116.0	134.3	158.5	174.7	180.6
62.5°	105.8	125.0	149.2	166.6	172.1
65°	94.4	115.2	140.3	157.7	163.2
67.5°	84.2	105.8	131.3	148.8	154.7
70°	73.1	95.2	121.6	139.8	144.9
72.5°	62.9	85.9	112.6	130.5	136.9
75°	52.3	76.1	103.3	121.6	127.1
77.5°	42.1	66.7	94.4	112.6	118.6
80°	31.9	57.8	85.4	103.3	109.2
82.5°	23.4	48.9	76.9	94.8	100.3
85°	15.3	41.7	68.9	86.7	92.7
87.5°	9.4	34.9	62.1	79.5	85.0
90°	4.8	34.9	66.2	85.7	91.8
92.5°	16.4	37.0	64.4	82.0	87.6
95°	36.1	39.5	68.5	87.1	91.7
97.5°	61.8	38.9	71.5	88.7	94.3
100°	92.0	38.8	71.2	90.9	96.6
102.5°	124.8	137.8	69.2	90.0	96.2
105°	154.9	182.4	67.3	87.6	94.3
107.5°	190.6	213.4	65.3	85.2	91.9
110°	224.4	243.5	119.0	82.3	89.0

TEST NUMBER: P998216

CATALOG NUMBER: SA2XXDIP-B290D530UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	256.6	272.4	283.5	80.4	86.5
115°	290.8	304.0	335.7	115.7	84.1
117.5°	320.0	333.5	359.8	300.7	173.2
120°	353.2	362.4	388.5	406.4	343.3
122.5°	381.4	389.8	415.6	430.1	434.4
125°	409.6	416.1	439.3	454.2	459.6
127.5°	435.8	442.3	461.3	477.0	481.4
130°	460.4	467.9	482.5	498.2	501.1
132.5°	485.5	491.6	503.5	517.8	520.7
135°	506.1	514.2	523.0	536.9	539.3
137.5°	528.3	534.3	541.5	554.5	556.0
140°	549.9	553.5	559.9	571.2	571.2
142.5°	568.0	571.1	577.6	586.7	586.3
145°	586.7	586.2	594.7	600.8	600.4
147.5°	603.3	601.8	610.3	613.2	612.5
150°	619.3	615.8	623.9	626.9	624.4
152.5°	632.9	628.9	636.4	639.5	635.9
155°	646.0	641.5	647.5	650.5	646.5
157.5°	656.5	652.5	657.1	660.6	656.5
160°	665.6	662.6	665.6	668.6	665.1
162.5°	673.6	670.6	673.1	676.7	672.1
165°	680.7	677.7	679.2	682.7	679.2
167.5°	686.2	683.2	684.7	688.2	683.7
170°	690.7	687.7	688.7	692.2	687.7
172.5°	693.7	690.7	691.7	695.3	690.7
175°	696.3	692.7	693.7	697.3	692.2
177.5°	697.3	693.7	694.3	697.8	693.2
180°	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P998216

CATALOG NUMBER: SA2XXDIP-B290D530UB2750-4F0-XX-W2A-D_5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.56	9.30	9.65	10.40	11.91	11.64	12.38	12.73	13.48	14.99
	3H	10.01	10.69	11.11	11.79	13.32	14.22	14.89	15.32	15.99	17.52
	4H	10.48	11.12	11.60	12.23	13.76	15.47	16.11	16.58	17.21	18.74
	6H	10.76	11.35	11.88	12.46	14.01	16.76	17.35	17.88	18.46	20.00
	8H	10.82	11.38	11.94	12.51	14.04	17.41	17.98	18.54	19.10	20.64
	12H	10.83	11.37	11.96	12.49	14.05	18.13	18.67	19.26	19.79	21.35
4H	2H	9.60	10.24	10.72	11.34	12.88	11.95	12.59	13.07	13.70	15.23
	3H	11.30	11.84	12.42	12.97	14.51	14.74	15.28	15.86	16.41	17.95
	4H	11.92	12.41	13.04	13.54	15.10	16.15	16.65	17.28	17.77	19.33
	6H	12.33	12.76	13.46	13.90	15.45	17.61	18.04	18.74	19.18	20.74
	8H	12.43	12.83	13.56	13.97	15.54	18.36	18.77	19.50	19.90	21.48
	12H	12.47	12.84	13.62	13.98	15.56	19.19	19.55	20.34	20.70	22.28
8H	4H	12.70	13.10	13.83	14.24	15.81	16.28	16.69	17.42	17.82	19.39
	6H	13.32	13.66	14.48	14.84	16.41	17.91	18.24	19.06	19.42	20.99
	8H	13.55	13.84	14.71	15.00	16.59	18.80	19.09	19.96	20.25	21.84
	12H	13.67	13.94	14.84	15.09	16.71	19.79	20.05	20.95	21.20	22.82
12H	4H	12.89	13.26	14.04	14.40	15.98	16.25	16.62	17.40	17.77	19.34
	6H	13.66	13.95	14.82	15.11	16.70	17.93	18.23	19.09	19.38	20.97
	8H	13.96	14.22	15.12	15.37	16.99	18.85	19.12	20.02	20.27	21.89