

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000152

Luminaire Tested: SA2XXRDIP-B865D530UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000152
REPORT IS A COMBINATION OF REPORTS P988712 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D530UB2750-4F0-XX-W2A-F_3500K
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5139.0 lumens
Efficiency: N/A
Efficacy: 82.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000152

CATALOG NUMBER: SA2XXRDIP-B865D530UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1000152

CATALOG NUMBER: SA2XXRDIP-B865D530UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	96	92	89	93	90	87	84	78	76	74	67	66	64	57	56	55
2	92	85	79	74	85	79	74	70	69	65	62	60	57	54	51	49	47
3	84	75	68	62	78	70	64	59	62	57	53	53	50	47	46	43	41
4	77	67	59	53	72	63	56	50	55	50	45	48	44	41	41	38	36
5	71	60	52	46	66	56	49	44	50	44	40	43	39	36	38	34	32
6	66	54	46	40	61	51	44	38	45	39	35	39	35	31	34	31	28
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	25	23
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	27	23	21
10	50	38	30	26	46	36	29	25	32	27	23	28	24	21	25	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23168	23168	23168
5°	23205	22040	21878
10°	22975	20905	20215
15°	22660	19562	18318
20°	22242	18036	16337
25°	21815	16472	14523
30°	21240	14947	12542
35°	20676	13409	10840
40°	20106	11900	9088
45°	19440	10340	7560
50°	18751	8839	6156
55°	18034	7337	4886
60°	17202	5867	3698
65°	16243	4474	3006
70°	15084	3244	2390
75°	13633	2476	1826
80°	11529	1676	1226
85°	8052	768	593

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19440 cd/sqm

TEST NUMBER: P1000152

CATALOG NUMBER: SA2XXRDIP-B865D530UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.2	2.7
10°-20°	376.6	7.3
20°-30°	528.7	10.3
30°-40°	576.3	11.2
40°-50°	529.7	10.3
50°-60°	416.0	8.1
60°-70°	270.7	5.3
70°-80°	139.4	2.7
80°-90°	36.9	0.7
90°-100°	23.9	0.5
100°-110°	89.2	1.7
110°-120°	236.6	4.6
120°-130°	392.4	7.6
130°-140°	416.9	8.1
140°-150°	387.4	7.5
150°-160°	311.5	6.1
160°-170°	200.7	3.9
170°-180°	69.1	1.3
0°-30°	1042.4	20.3
0°-40°	1618.7	31.5
0°-60°	2564.3	49.9
0°-90°	3011.3	58.6
90°-120°	349.8	6.8
90°-150°	1546.5	30.1
90°-180°	2128.0	41.4
0°-180°	5139.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1464	1464	1464	1464	1464	
5°	1464	1457	1440	1452	1448	139
15°	1392	1378	1332	1307	1294	392
25°	1264	1221	1134	1080	1060	581
35°	1089	1021	905	821	792	681
45°	890	801	662	568	536	687
55°	677	574	430	351	326	605
65°	457	350	230	185	182	453
75°	244	151	106	97	95	258
85°	57	29	25	25	25	65
90°	0	6	10	13	14	5
95°	34	17	20	23	23	40
105°	160	175	32	38	40	171
115°	302	311	324	81	43	297
125°	427	434	444	447	449	381
135°	528	537	541	547	546	408
145°	613	612	621	625	622	383
155°	675	670	676	680	675	311
165°	711	708	710	713	710	201
175°	727	724	725	728	723	69
180°	726	726	726	726	726	

TEST NUMBER: P1000152

CATALOG NUMBER: SA2XXRDIP-B865D530UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1463.6	1463.6	1463.6	1463.6	1463.6
2.5°	1470.2	1463.6	1449.0	1462.2	1459.6
5°	1463.6	1456.9	1439.7	1451.6	1447.7
7.5°	1451.6	1443.7	1425.2	1430.4	1423.8
10°	1435.7	1426.5	1400.0	1396.0	1388.1
12.5°	1415.9	1404.0	1368.2	1360.3	1345.7
15°	1392.0	1377.5	1332.4	1307.3	1294.0
17.5°	1364.2	1343.0	1287.4	1258.3	1237.1
20°	1332.4	1305.9	1239.7	1206.6	1177.5
22.5°	1298.0	1267.5	1190.7	1145.7	1125.8
25°	1263.6	1221.2	1133.8	1079.5	1059.6
27.5°	1222.5	1177.5	1080.8	1018.5	988.1
30°	1178.8	1128.5	1022.5	955.0	919.2
32.5°	1136.4	1075.5	966.9	887.4	854.3
35°	1088.7	1021.2	904.6	821.2	792.0
37.5°	1042.4	969.5	846.3	755.0	721.8
40°	993.4	913.9	785.4	691.4	656.9
42.5°	943.0	858.3	724.5	626.5	593.4
45°	890.1	801.3	662.2	568.2	536.4
47.5°	839.7	745.7	602.6	508.6	479.5
50°	784.1	690.1	544.4	453.0	425.2
52.5°	729.8	630.5	488.7	401.3	376.2
55°	676.8	573.5	430.5	351.0	325.8
57.5°	622.5	516.6	378.8	304.6	283.4
60°	566.9	460.9	324.5	257.0	235.8
62.5°	512.6	406.6	278.1	214.6	204.0
65°	456.9	349.7	230.5	185.4	181.5
67.5°	404.0	296.7	185.4	162.9	158.9
70°	348.3	245.0	153.6	140.4	135.1
72.5°	295.4	197.3	128.5	117.9	115.2
75°	243.7	151.0	106.0	96.7	95.4
77.5°	192.1	107.3	83.4	78.1	75.5
80°	144.4	76.8	63.6	58.3	58.3
82.5°	100.7	51.7	43.7	41.1	41.1
85°	57.0	29.1	25.2	25.2	25.2
87.5°	21.2	10.6	10.6	9.3	9.3
90°	0.5	6.3	10.5	13.1	14.2
92.5°	13.1	11.0	12.6	13.7	14.2
95°	34.1	16.8	20.5	23.1	22.6
97.5°	61.4	18.4	26.8	28.4	28.9
100°	93.0	21.0	29.9	34.1	35.2
102.5°	127.6	126.6	31.0	36.8	38.3
105°	159.6	175.4	32.0	37.8	39.9
107.5°	196.9	210.1	33.1	38.9	41.0
110°	232.6	243.7	91.9	39.4	41.5

TEST NUMBER: P1000152

CATALOG NUMBER: SA2XXRDIP-B865D530UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	266.3	275.7	266.8	40.4	42.0
115°	302.0	310.9	324.0	80.9	43.1
117.5°	333.0	343.5	352.4	277.3	139.7
120°	367.6	375.5	384.9	391.2	320.4
122.5°	397.0	405.4	415.9	419.1	419.6
125°	427.0	433.8	443.8	447.4	449.0
127.5°	454.3	461.6	469.5	474.7	475.3
130°	480.0	488.4	494.2	500.0	499.4
132.5°	506.3	513.1	518.9	523.6	523.1
135°	528.3	536.7	541.4	546.7	545.6
137.5°	551.4	557.7	563.0	568.2	566.7
140°	574.0	578.2	584.0	588.7	586.1
142.5°	592.9	596.6	603.4	607.6	605.0
145°	612.9	612.3	621.3	624.9	622.3
147.5°	630.2	628.6	637.5	640.2	638.1
150°	647.0	643.3	651.7	654.9	652.3
152.5°	661.2	657.0	664.9	668.0	664.3
155°	674.8	670.1	676.4	679.6	675.4
157.5°	685.9	681.7	686.4	690.1	685.9
160°	695.3	692.2	695.3	698.5	694.8
162.5°	703.7	700.6	703.2	706.9	702.1
165°	711.1	707.9	709.5	713.2	709.5
167.5°	716.8	713.7	715.3	718.9	714.2
170°	721.6	718.4	719.5	723.2	718.4
172.5°	724.7	721.6	722.6	726.3	721.6
175°	727.4	723.7	724.7	728.4	723.2
177.5°	728.4	724.7	725.3	728.9	724.2
180°	725.8	725.8	725.8	725.8	725.8

(END OF REPORT)