

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000154

Luminaire Tested: SA2XXRDIP-B865D530UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000154
REPORT IS A COMBINATION OF REPORTS P988714 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D530UB2750-4F0-XX-W2A-F_5000K
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4920.0 lumens
Efficiency: N/A
Efficacy: 79.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000154

CATALOG NUMBER: SA2XXRDIP-B865D530UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1000154

CATALOG NUMBER: SA2XXRDIP-B865D530UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	96	92	89	93	90	87	84	78	76	74	67	66	64	57	56	55
2	92	85	79	74	85	79	74	70	69	65	62	60	57	54	51	49	47
3	84	75	68	62	78	70	64	59	62	57	53	53	50	47	46	43	41
4	77	67	59	53	72	63	56	50	55	50	45	48	44	41	41	38	36
5	71	60	52	46	66	56	49	44	50	44	40	43	39	36	38	34	32
6	66	54	46	40	61	51	44	38	45	39	35	39	35	31	34	31	28
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	25	23
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	27	23	21
10	50	38	30	26	46	36	29	25	32	27	23	28	24	21	25	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22182	22182	22182
5°	22218	21103	20947
10°	21999	20016	19354
15°	21696	18731	17540
20°	21297	17270	15642
25°	20886	15770	13905
30°	20337	14311	12008
35°	19797	12840	10380
40°	19249	11394	8702
45°	18612	9901	7239
50°	17954	8462	5894
55°	17267	7025	4679
60°	16471	5617	3539
65°	15553	4283	2877
70°	14443	3107	2289
75°	13051	2371	1748
80°	11034	1605	1173
85°	7698	735	567

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18612 cd/sqm

TEST NUMBER: P1000154

CATALOG NUMBER: SA2XXRDIP-B865D530UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.3	2.7
10°-20°	360.5	7.3
20°-30°	506.2	10.3
30°-40°	551.8	11.2
40°-50°	507.1	10.3
50°-60°	398.3	8.1
60°-70°	259.2	5.3
70°-80°	133.5	2.7
80°-90°	35.3	0.7
90°-100°	22.9	0.5
100°-110°	85.4	1.7
110°-120°	226.5	4.6
120°-130°	375.7	7.6
130°-140°	399.0	8.1
140°-150°	370.9	7.5
150°-160°	298.2	6.1
160°-170°	192.1	3.9
170°-180°	66.1	1.3
0°-30°	998.1	20.3
0°-40°	1549.8	31.5
0°-60°	2455.2	49.9
0°-90°	2883.2	58.6
90°-120°	334.8	6.8
90°-150°	1480.4	30.1
90°-180°	2037.0	41.4
0°-180°	4920.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1401	1401	1401	1401	1401	
5°	1401	1395	1378	1390	1386	133
15°	1333	1319	1276	1252	1239	376
25°	1210	1169	1086	1034	1014	556
35°	1042	978	866	786	758	652
45°	852	767	634	544	514	658
55°	648	549	412	336	312	579
65°	438	335	221	178	174	434
75°	233	145	102	93	91	247
85°	54	28	24	24	24	63
90°	0	6	10	13	14	5
95°	33	16	20	22	22	39
105°	153	168	31	36	38	163
115°	289	298	310	77	41	285
125°	409	415	425	428	430	365
135°	506	514	518	523	522	391
145°	587	586	595	598	596	367
155°	646	642	648	650	646	298
165°	681	678	679	683	679	192
175°	696	693	694	697	692	66
180°	695	695	695	695	695	

TEST NUMBER: P1000154

CATALOG NUMBER: SA2XXRDIP-B865D530UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1401.3	1401.3	1401.3	1401.3	1401.3
2.5°	1407.7	1401.3	1387.4	1400.1	1397.5
5°	1401.3	1395.0	1378.5	1389.9	1386.1
7.5°	1389.9	1382.3	1364.5	1369.6	1363.3
10°	1374.7	1365.8	1340.5	1336.6	1329.0
12.5°	1355.7	1344.3	1310.0	1302.4	1288.5
15°	1332.8	1318.9	1275.8	1251.7	1239.0
17.5°	1306.2	1285.9	1232.7	1204.8	1184.5
20°	1275.8	1250.4	1187.0	1155.3	1127.4
22.5°	1242.8	1213.6	1140.1	1097.0	1077.9
25°	1209.8	1169.2	1085.5	1033.6	1014.5
27.5°	1170.5	1127.4	1034.8	975.2	946.1
30°	1128.7	1080.5	979.0	914.3	880.1
32.5°	1088.1	1029.8	925.8	849.7	818.0
35°	1042.4	977.8	866.2	786.3	758.4
37.5°	998.0	928.3	810.4	722.9	691.2
40°	951.1	875.0	752.0	662.0	629.0
42.5°	902.9	821.8	693.7	599.8	568.1
45°	852.2	767.2	634.1	544.0	513.6
47.5°	804.0	714.0	577.0	487.0	459.1
50°	750.8	660.7	521.2	433.7	407.1
52.5°	698.8	603.6	468.0	384.3	360.2
55°	648.0	549.1	412.2	336.1	312.0
57.5°	596.0	494.6	362.7	291.7	271.4
60°	542.8	441.3	310.7	246.0	225.7
62.5°	490.8	389.3	266.3	205.4	195.3
65°	437.5	334.8	220.7	177.5	173.7
67.5°	386.8	284.1	177.5	156.0	152.2
70°	333.5	234.6	147.1	134.4	129.4
72.5°	282.8	189.0	123.0	112.9	110.3
75°	233.3	144.6	101.5	92.6	91.3
77.5°	183.9	102.7	79.9	74.8	72.3
80°	138.2	73.6	60.9	55.8	55.8
82.5°	96.4	49.5	41.8	39.3	39.3
85°	54.5	27.9	24.1	24.1	24.1
87.5°	20.3	10.1	10.1	8.9	8.9
90°	0.5	6.0	10.1	12.6	13.6
92.5°	12.6	10.6	12.1	13.1	13.6
95°	32.7	16.1	19.6	22.1	21.6
97.5°	58.8	17.6	25.6	27.1	27.6
100°	89.0	20.1	28.7	32.7	33.7
102.5°	122.2	121.2	29.7	35.2	36.7
105°	152.8	167.9	30.7	36.2	38.2
107.5°	188.5	201.1	31.7	37.2	39.2
110°	222.7	233.3	88.0	37.7	39.7

TEST NUMBER: P1000154

CATALOG NUMBER: SA2XXRDIP-B865D530UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	254.9	263.9	255.4	38.7	40.2
115°	289.1	297.6	310.2	77.4	41.2
117.5°	318.7	328.8	337.3	265.4	133.7
120°	351.9	359.4	368.5	374.5	306.7
122.5°	380.1	388.1	398.2	401.2	401.7
125°	408.7	415.2	424.8	428.3	429.8
127.5°	434.9	441.9	449.4	454.5	455.0
130°	459.5	467.5	473.1	478.6	478.1
132.5°	484.6	491.2	496.7	501.2	500.7
135°	505.7	513.8	518.3	523.3	522.3
137.5°	527.9	533.9	538.9	543.9	542.4
140°	549.5	553.5	559.0	563.5	561.0
142.5°	567.6	571.1	577.6	581.6	579.1
145°	586.7	586.2	594.7	598.2	595.7
147.5°	603.3	601.8	610.3	612.8	610.8
150°	619.3	615.8	623.9	626.9	624.4
152.5°	632.9	628.9	636.4	639.5	635.9
155°	646.0	641.5	647.5	650.5	646.5
157.5°	656.5	652.5	657.1	660.6	656.5
160°	665.6	662.6	665.6	668.6	665.1
162.5°	673.6	670.6	673.1	676.7	672.1
165°	680.7	677.7	679.2	682.7	679.2
167.5°	686.2	683.2	684.7	688.2	683.7
170°	690.7	687.7	688.7	692.2	687.7
172.5°	693.7	690.7	691.7	695.3	690.7
175°	696.3	692.7	693.7	697.3	692.2
177.5°	697.3	693.7	694.3	697.8	693.2
180°	694.8	694.8	694.8	694.8	694.8

(END OF REPORT)