

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000230

Luminaire Tested: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000230
REPORT IS A COMBINATION OF REPORTS P988790 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-F_2700K
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6606.0 lumens
Efficiency: N/A
Efficacy: 87.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000230

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1000230

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52			45
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44			39
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38			33
3	81	72	65	60	74	67	60	56	56	51	48	46	43	40	37	35	33			29
4	75	64	57	51	68	59	53	47	50	45	41	41	38	35	33	31	29			25
5	69	57	49	44	63	53	46	41	45	40	36	37	33	30	30	27	25			22
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	22			20
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20			17
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18			16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	16			14
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15			13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22875	22875	22875
5°	22912	21762	21601
10°	22686	20640	19959
15°	22375	19315	18088
20°	21962	17809	16131
25°	21539	16263	14339
30°	20971	14759	12384
35°	20416	13240	10703
40°	19851	11750	8975
45°	19193	10211	7465
50°	18514	8727	6077
55°	17808	7243	4825
60°	16984	5793	3651
65°	16040	4417	2968
70°	14893	3204	2360
75°	13459	2443	1803
80°	11377	1655	1209
85°	7939	756	583

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19193 cd/sqm

TEST NUMBER: P1000230

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.4	2.1
10°-20°	371.8	5.6
20°-30°	522.0	7.9
30°-40°	569.0	8.6
40°-50°	523.0	7.9
50°-60°	410.7	6.2
60°-70°	267.3	4.0
70°-80°	137.6	2.1
80°-90°	37.3	0.6
90°-100°	40.9	0.6
100°-110°	152.3	2.3
110°-120°	403.9	6.1
120°-130°	669.8	10.1
130°-140°	711.5	10.8
140°-150°	661.3	10.0
150°-160°	531.6	8.0
160°-170°	342.6	5.2
170°-180°	117.9	1.8
0°-30°	1029.2	15.6
0°-40°	1598.2	24.2
0°-60°	2531.9	38.3
0°-90°	2974.2	45.0
90°-120°	597.0	9.0
90°-150°	2639.6	40.0
90°-180°	3632.0	55.0
0°-180°	6606.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1445	1445	1445	1445	1445	
5°	1445	1438	1422	1433	1429	137
15°	1374	1360	1316	1291	1278	387
25°	1248	1206	1119	1066	1046	574
35°	1075	1008	893	811	782	673
45°	879	791	654	561	530	679
55°	668	566	425	347	322	597
65°	451	345	228	183	179	447
75°	241	149	105	96	94	254
85°	56	29	25	25	25	65
90°	1	11	18	22	24	6
95°	58	29	35	39	38	69
105°	272	299	55	64	68	291
115°	515	531	553	138	74	507
125°	729	740	758	764	766	650
135°	902	916	924	933	931	697
145°	1046	1045	1060	1067	1062	654
155°	1152	1144	1155	1160	1153	531
165°	1214	1208	1211	1217	1211	343
175°	1242	1235	1237	1243	1234	118
180°	1239	1239	1239	1239	1239	

TEST NUMBER: P1000230

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1445.1	1445.1	1445.1	1445.1	1445.1
2.5°	1451.6	1445.1	1430.7	1443.8	1441.2
5°	1445.1	1438.5	1421.5	1433.3	1429.4
7.5°	1433.3	1425.5	1407.2	1412.4	1405.9
10°	1417.6	1408.5	1382.3	1378.4	1370.5
12.5°	1398.0	1386.2	1350.9	1343.1	1328.7
15°	1374.5	1360.1	1315.6	1290.8	1277.7
17.5°	1347.0	1326.1	1271.2	1242.4	1221.5
20°	1315.6	1289.5	1224.1	1191.4	1162.6
22.5°	1281.6	1251.5	1175.7	1131.2	1111.6
25°	1247.6	1205.8	1119.4	1065.8	1046.2
27.5°	1207.1	1162.6	1067.1	1005.7	975.6
30°	1163.9	1114.2	1009.6	942.9	907.6
32.5°	1122.1	1061.9	954.7	876.2	843.5
35°	1075.0	1008.3	893.2	810.8	782.0
37.5°	1029.2	957.3	835.7	745.4	712.7
40°	980.8	902.4	775.5	682.7	648.7
42.5°	931.1	847.4	715.3	618.6	585.9
45°	878.8	791.2	653.9	561.0	529.6
47.5°	829.1	736.3	595.0	502.2	473.4
50°	774.2	681.3	537.5	447.3	419.8
52.5°	720.6	622.5	482.6	396.3	371.4
55°	668.3	566.3	425.0	346.6	321.7
57.5°	614.7	510.0	374.0	300.8	279.9
60°	559.7	455.1	320.4	253.7	232.8
62.5°	506.1	401.5	274.6	211.9	201.4
65°	451.2	345.3	227.6	183.1	179.2
67.5°	398.9	292.9	183.1	160.9	156.9
70°	343.9	241.9	151.7	138.6	133.4
72.5°	291.6	194.9	126.9	116.4	113.8
75°	240.6	149.1	104.6	95.5	94.2
77.5°	189.6	105.9	82.4	77.2	74.5
80°	142.5	75.9	62.8	57.5	57.5
82.5°	99.4	51.0	43.2	40.5	40.5
85°	56.2	28.8	24.8	24.8	24.8
87.5°	20.9	10.5	10.5	9.2	9.2
90°	0.9	10.8	17.9	22.4	24.2
92.5°	22.4	18.8	21.5	23.3	24.2
95°	58.3	28.7	35.0	39.4	38.5
97.5°	104.9	31.4	45.7	48.4	49.3
100°	158.7	35.9	51.1	58.3	60.1
102.5°	217.8	216.0	52.9	62.7	65.4
105°	272.5	299.4	54.7	64.5	68.1
107.5°	336.2	358.6	56.5	66.3	69.9
110°	397.1	415.9	156.9	67.2	70.8

TEST NUMBER: P1000230

CATALOG NUMBER: SA2XXRDIP-B865D925UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	454.5	470.6	455.4	69.0	71.7
115°	515.4	530.7	553.1	138.0	73.5
117.5°	568.3	586.2	601.5	473.3	238.4
120°	627.5	640.9	657.1	667.8	546.8
122.5°	677.7	692.0	710.0	715.3	716.2
125°	728.8	740.4	757.5	763.7	766.4
127.5°	775.4	787.9	801.4	810.4	811.2
130°	819.3	833.7	843.5	853.4	852.5
132.5°	864.1	875.8	885.6	893.7	892.8
135°	901.8	916.1	924.2	933.2	931.4
137.5°	941.2	952.0	960.9	969.9	967.2
140°	979.8	986.9	996.8	1004.9	1000.4
142.5°	1012.0	1018.3	1030.0	1037.1	1032.7
145°	1046.1	1045.2	1060.4	1066.7	1062.2
147.5°	1075.7	1073.0	1088.2	1092.7	1089.1
150°	1104.4	1098.1	1112.4	1117.8	1113.3
152.5°	1128.6	1121.4	1134.8	1140.2	1134.0
155°	1151.9	1143.8	1154.6	1159.9	1152.8
157.5°	1170.7	1163.5	1171.6	1177.9	1170.7
160°	1186.8	1181.5	1186.8	1192.2	1185.9
162.5°	1201.2	1195.8	1200.3	1206.6	1198.5
165°	1213.7	1208.4	1211.0	1217.3	1211.0
167.5°	1223.6	1218.2	1220.9	1227.2	1219.1
170°	1231.7	1226.3	1228.1	1234.3	1226.3
172.5°	1237.0	1231.7	1233.5	1239.7	1231.7
175°	1241.5	1235.2	1237.0	1243.3	1234.3
177.5°	1243.3	1237.0	1237.9	1244.2	1236.1
180°	1238.8	1238.8	1238.8	1238.8	1238.8

(END OF REPORT)