

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997791

Luminaire Tested: SA2XXDIP-B1005D1080UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P997791
REPORT IS A COMBINATION OF REPORTS P983525 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B1005D1080UB27-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7846.0 lumens
Efficiency: N/A
Efficacy: 81.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997791

CATALOG NUMBER: SA2XXDIP-B1005D1080UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P997791

CATALOG NUMBER: SA2XXDIP-B1005D1080UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	98	94	90	86	91	87	83	80	74	71	69	62	60	58	51	50	48
2	89	82	76	71	82	76	71	66	65	61	57	54	51	49	45	43	41
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	40	37	35
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	26	23	20
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	22	19	17
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25067	25067	25067
5°	25108	23894	23724
10°	24904	22805	22353
15°	24540	21709	20909
20°	24047	20514	19542
25°	23556	19269	18178
30°	22937	18098	16746
35°	22355	16861	15339
40°	21634	15642	14009
45°	20918	14433	12705
50°	20138	13201	11353
55°	19313	11886	10071
60°	18389	10461	8739
65°	17377	9013	7339
70°	16089	7428	5926
75°	14310	5728	4576
80°	12159	3892	2945
85°	8814	1811	1253

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20918 cd/sqm

TEST NUMBER: P997791

CATALOG NUMBER: SA2XXDIP-B1005D1080UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.0	1.9
10°-20°	419.4	5.3
20°-30°	616.3	7.9
30°-40°	715.8	9.1
40°-50°	714.9	9.1
50°-60°	623.3	7.9
60°-70°	460.8	5.9
70°-80°	260.7	3.3
80°-90°	72.7	0.9
90°-100°	84.4	1.1
100°-110°	268.2	3.4
110°-120°	458.9	5.8
120°-130°	603.6	7.7
130°-140°	677.5	8.6
140°-150°	664.4	8.5
150°-160°	557.3	7.1
160°-170°	369.6	4.7
170°-180°	129.2	1.6
0°-30°	1184.7	15.1
0°-40°	1900.5	24.2
0°-60°	3238.7	41.3
0°-90°	4032.9	51.4
90°-120°	811.5	10.3
90°-150°	2757.0	35.1
90°-180°	3813.0	48.6
0°-180°	7846.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1584	1584	1584	1584	1584	
5°	1584	1578	1561	1573	1570	150
15°	1508	1498	1479	1485	1477	425
25°	1364	1352	1326	1329	1326	628
35°	1177	1162	1138	1128	1121	735
45°	958	947	924	908	901	739
55°	725	716	697	679	672	648
65°	489	480	464	451	443	483
75°	256	253	245	236	239	273
85°	62	61	59	55	53	70
90°	1	15	40	38	39	8
95°	60	71	74	74	71	67
105°	248	251	253	256	256	261
115°	460	467	465	464	460	455
125°	670	680	677	673	672	599
135°	867	879	882	880	877	670
145°	1052	1060	1067	1068	1064	657
155°	1203	1206	1210	1215	1212	554
165°	1309	1308	1308	1316	1310	369
175°	1362	1358	1356	1364	1357	129
180°	1364	1364	1364	1364	1364	

TEST NUMBER: P997791

CATALOG NUMBER: SA2XXDIP-B1005D1080UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1583.6	1583.6	1583.6	1583.6	1583.6
2.5°	1592.8	1585.1	1568.4	1583.6	1580.6
5°	1583.6	1577.5	1560.8	1573.0	1569.9
7.5°	1573.0	1563.8	1547.1	1559.3	1556.2
10°	1556.2	1545.6	1527.3	1539.5	1534.9
12.5°	1533.4	1524.2	1506.0	1513.6	1510.5
15°	1507.5	1498.4	1478.6	1484.7	1477.0
17.5°	1475.5	1466.4	1446.6	1454.2	1446.6
20°	1440.5	1431.4	1410.0	1414.6	1408.5
22.5°	1405.5	1391.8	1372.0	1372.0	1368.9
25°	1364.4	1352.2	1326.3	1329.3	1326.3
27.5°	1318.7	1308.0	1288.2	1283.7	1276.0
30°	1273.0	1260.8	1238.0	1233.4	1227.3
32.5°	1224.3	1215.1	1190.8	1181.6	1175.5
35°	1177.1	1161.8	1137.5	1128.3	1120.7
37.5°	1123.8	1110.1	1085.7	1075.0	1067.4
40°	1068.9	1056.8	1032.4	1018.7	1012.6
42.5°	1015.7	1003.5	979.1	963.9	954.7
45°	957.8	947.1	924.3	907.5	901.4
47.5°	901.4	890.8	866.4	849.7	840.5
50°	842.1	834.4	813.1	791.8	784.2
52.5°	784.2	773.5	753.7	737.0	726.3
55°	724.8	715.7	697.4	679.1	671.5
57.5°	665.4	657.8	638.0	619.7	613.7
60°	606.0	600.0	578.6	561.9	557.3
62.5°	548.2	537.5	522.3	507.1	501.0
65°	488.8	479.7	464.4	450.7	443.1
67.5°	427.9	420.3	406.6	395.9	389.8
70°	371.5	365.5	351.7	341.1	335.0
72.5°	313.7	307.6	300.0	289.3	284.7
75°	255.8	252.8	245.2	236.0	239.1
77.5°	204.0	198.0	194.9	190.3	185.8
80°	152.3	150.7	147.7	143.1	140.1
82.5°	103.5	103.5	102.0	95.9	95.9
85°	62.4	60.9	59.4	54.8	53.3
87.5°	27.4	24.4	21.3	16.7	15.2
90°	1.2	15.0	40.3	38.0	39.1
92.5°	25.3	34.5	35.7	36.8	36.8
95°	59.8	71.4	73.7	73.7	71.4
97.5°	100.1	110.5	115.1	115.1	115.1
100°	146.2	155.4	158.8	158.8	157.7
102.5°	194.5	201.4	206.0	207.2	206.0
105°	247.5	250.9	253.2	255.5	255.5
107.5°	300.4	305.0	305.0	306.2	300.4
110°	351.0	357.9	357.9	357.9	354.5

TEST NUMBER: P997791

CATALOG NUMBER: SA2XXDIP-B1005D1080UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	406.3	413.2	412.0	408.6	406.3
115°	460.4	467.3	465.0	463.8	460.4
117.5°	514.5	523.7	517.9	514.5	511.0
120°	568.6	577.8	568.6	568.6	565.1
122.5°	618.1	629.6	623.8	620.4	618.1
125°	669.8	680.2	676.8	673.3	672.2
127.5°	720.5	733.2	728.5	723.9	720.5
130°	767.7	782.6	780.3	778.0	773.4
132.5°	820.6	832.1	833.3	827.5	824.1
135°	866.7	879.3	881.6	880.5	877.0
137.5°	917.3	927.7	930.0	928.8	924.2
140°	962.2	972.5	978.3	978.3	973.7
142.5°	1008.2	1018.6	1022.0	1023.2	1018.6
145°	1052.0	1060.0	1066.9	1068.1	1063.5
147.5°	1091.1	1101.5	1106.1	1108.4	1103.8
150°	1131.4	1138.3	1142.9	1146.3	1142.9
152.5°	1167.1	1174.0	1179.7	1184.3	1179.7
155°	1202.7	1206.2	1209.6	1215.4	1211.9
157.5°	1233.8	1236.1	1238.4	1246.5	1240.7
160°	1261.4	1263.7	1264.9	1271.8	1267.2
162.5°	1286.8	1286.8	1287.9	1296.0	1290.2
165°	1308.6	1307.5	1307.5	1315.5	1309.8
167.5°	1328.2	1324.7	1324.7	1332.8	1327.0
170°	1343.2	1339.7	1338.5	1346.6	1339.7
172.5°	1353.5	1350.1	1348.9	1357.0	1350.1
175°	1361.6	1358.1	1355.8	1363.9	1357.0
177.5°	1366.2	1362.7	1360.4	1367.3	1360.4
180°	1363.9	1363.9	1363.9	1363.9	1363.9

TEST NUMBER: P997791

CATALOG NUMBER: SA2XXDIP-B1005D1080UB27-4F0-XX-W2A-F1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.56	17.43	17.50	18.39	19.64	17.34	18.21	18.28	19.17	20.42
	3H	17.89	18.68	18.85	19.65	20.92	18.97	19.75	19.92	20.72	21.99
	4H	18.30	19.04	19.27	20.02	21.30	19.56	20.30	20.53	21.27	22.56
	6H	18.52	19.20	19.50	20.18	21.48	19.96	20.65	20.94	21.63	22.92
	8H	18.55	19.20	19.54	20.20	21.49	20.07	20.72	21.06	21.72	23.01
	12H	18.54	19.16	19.54	20.15	21.47	20.12	20.74	21.11	21.73	23.04
4H	2H	17.03	17.77	18.00	18.74	20.03	17.67	18.41	18.65	19.39	20.67
	3H	18.55	19.16	19.53	20.17	21.47	19.45	20.07	20.44	21.07	22.37
	4H	19.05	19.62	20.05	20.62	21.94	20.13	20.70	21.13	21.70	23.02
	6H	19.36	19.84	20.36	20.86	22.18	20.63	21.12	21.64	22.14	23.46
	8H	19.41	19.87	20.42	20.88	22.22	20.77	21.23	21.78	22.24	23.58
	12H	19.41	19.83	20.44	20.85	22.19	20.84	21.25	21.86	22.28	23.62
8H	4H	19.23	19.68	20.24	20.70	22.03	20.22	20.68	21.23	21.69	23.02
	6H	19.61	19.99	20.64	21.05	22.38	20.79	21.17	21.82	22.22	23.55
	8H	19.72	20.05	20.76	21.09	22.44	20.98	21.31	22.02	22.35	23.70
	12H	19.75	20.04	20.79	21.08	22.47	21.08	21.37	22.12	22.41	23.80
12H	4H	19.21	19.62	20.24	20.65	21.99	20.18	20.60	21.21	21.63	22.96
	6H	19.63	19.96	20.67	21.00	22.35	20.78	21.11	21.82	22.16	23.51
	8H	19.74	20.04	20.79	21.07	22.47	20.98	21.27	22.02	22.31	23.70