

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997833

Luminaire Tested: SA2XXDIP-B1005D1080UB50-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P997833
REPORT IS A COMBINATION OF REPORTS P983570 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B1005D1080UB50-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7941.0 lumens
Efficiency: N/A
Efficacy: 82.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997833

CATALOG NUMBER: SA2XXDIP-B1005D1080UB50-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P997833

CATALOG NUMBER: SA2XXDIP-B1005D1080UB50-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51
2	91	83	78	73	84	78	73	68	67	63	60	57	54	52	47	46	44
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	42	40	38
4	76	66	58	52	70	61	55	49	53	48	44	45	42	38	38	35	33
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	29	26
7	60	48	40	35	56	45	38	33	39	34	30	34	30	27	29	26	23
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	24	21
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	22	19
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30413	30413	30413	30413
5°	30486	32427	30603	25799
10°	30132	35400	30321	21271
15°	29401	37339	29809	17916
20°	28943	35058	28943	15573
25°	28020	30119	28148	13925
30°	26503	23676	27007	12614
35°	25158	16372	25578	11542
40°	23613	12361	23882	10686
45°	21707	10158	22061	9762
50°	20059	8915	20095	8937
55°	18181	7596	18298	8040
60°	16177	6345	16401	7017
65°	14383	5161	14646	5992
70°	12598	4049	12919	4833
75°	10573	2940	10987	3505
80°	8255	1863	8846	2079
85°	5424	938	5848	694

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 31439 cd/sqm

TEST NUMBER: P997833

CATALOG NUMBER: SA2XXDIP-B1005D1080UB50-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.0	2.3
10°-20°	532.6	6.7
20°-30°	773.0	9.7
30°-40°	814.9	10.3
40°-50°	721.1	9.1
50°-60°	575.8	7.3
60°-70°	391.1	4.9
70°-80°	200.1	2.5
80°-90°	51.1	0.6
90°-100°	81.8	1.0
100°-110°	260.1	3.3
110°-120°	445.1	5.6
120°-130°	585.4	7.4
130°-140°	657.1	8.3
140°-150°	644.4	8.1
150°-160°	540.5	6.8
160°-170°	358.5	4.5
170°-180°	125.3	1.6
0°-30°	1488.7	18.7
0°-40°	2303.6	29.0
0°-60°	3600.5	45.3
0°-90°	4242.8	53.4
90°-120°	787.1	9.9
90°-150°	2673.9	33.7
90°-180°	3698.0	46.6
0°-180°	7941.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1921	1921	1921	1921	1921	
5°	1923	2146	1930	1707	1923	182
15°	1806	2638	1831	1266	1806	510
25°	1623	2198	1630	1016	1623	742
35°	1325	1196	1347	843	1325	829
45°	994	721	1010	693	994	771
55°	682	506	687	536	682	609
65°	405	312	412	362	405	402
75°	189	154	196	183	189	203
85°	38	40	41	30	38	45
90°	1	38	1	38	1	6
95°	58	69	58	69	58	65
105°	240	248	240	248	240	253
115°	446	446	446	446	446	442
125°	650	652	650	652	650	581
135°	840	851	840	851	840	650
145°	1020	1031	1020	1031	1020	637
155°	1166	1175	1166	1175	1166	537
165°	1269	1270	1269	1270	1269	358
175°	1320	1316	1320	1316	1320	125
180°	1323	1323	1323	1323	1323	

TEST NUMBER: P997833

CATALOG NUMBER: SA2XXDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1931.6	1936.1	1943.5	1944.9	1959.7	1971.5	1984.8	1984.8	1989.2	1987.8	1976.0
5°	1922.8	1936.1	1955.3	1971.5	1998.1	2009.9	2027.6	2040.9	2052.7	2061.6	2060.1
7.5°	1908.0	1931.6	1959.7	1990.7	2026.2	2046.8	2071.9	2095.6	2111.8	2126.6	2136.9
10°	1882.9	1922.8	1961.2	2002.5	2048.3	2076.4	2105.9	2136.9	2162.0	2190.1	2216.7
12.5°	1848.9	1906.5	1953.8	2008.4	2064.6	2095.6	2142.8	2166.5	2215.2	2286.1	2305.3
15°	1806.1	1884.4	1928.7	1998.1	2071.9	2097.1	2162.0	2200.4	2300.8	2345.2	2398.3
17.5°	1766.2	1853.4	1912.5	1992.2	2064.6	2113.3	2176.8	2255.1	2339.2	2402.7	2461.8
20°	1733.8	1817.9	1888.8	1977.4	2069.0	2131.0	2197.5	2292.0	2383.5	2448.5	2494.3
22.5°	1659.9	1767.7	1850.4	1949.4	2060.1	2145.8	2209.3	2312.7	2411.6	2451.5	2491.4
25°	1623.0	1716.0	1812.0	1924.3	2054.2	2156.1	2210.8	2326.0	2413.1	2427.9	2436.7
27.5°	1555.1	1659.9	1772.2	1900.6	2052.7	2138.4	2207.8	2312.7	2382.1	2371.7	2345.2
30°	1470.9	1599.4	1723.4	1862.2	2032.1	2125.1	2190.1	2286.1	2321.5	2268.4	2221.1
32.5°	1408.9	1530.0	1667.3	1828.3	2008.4	2097.1	2160.6	2235.9	2243.3	2147.3	2067.5
35°	1324.7	1459.1	1614.1	1784.0	1968.6	2048.3	2107.4	2153.2	2117.7	1983.3	1888.8
37.5°	1249.4	1382.3	1547.7	1720.5	1913.9	1992.2	2039.5	2046.8	1959.7	1841.6	1702.7
40°	1166.7	1304.0	1476.8	1658.4	1853.4	1921.3	1950.8	1928.7	1803.2	1665.8	1504.9
42.5°	1084.0	1219.8	1405.9	1592.0	1776.6	1834.2	1846.0	1785.4	1631.9	1470.9	1284.8
45°	993.9	1135.7	1321.7	1509.3	1688.0	1720.5	1721.9	1634.8	1453.2	1284.8	1112.0
47.5°	920.0	1051.5	1236.1	1423.6	1574.3	1596.4	1587.6	1487.1	1289.2	1100.2	949.6
50°	838.8	964.3	1147.5	1332.1	1460.6	1466.5	1444.3	1301.1	1107.6	934.8	815.2
52.5°	751.7	878.7	1047.0	1224.3	1339.5	1330.6	1287.8	1134.2	952.5	809.3	717.7
55°	682.3	794.5	952.5	1125.3	1206.5	1181.4	1134.2	977.6	834.4	713.3	633.5
57.5°	605.5	704.4	859.5	1010.1	1057.4	1033.8	986.5	840.3	707.4	615.8	562.7
60°	533.1	623.2	759.1	884.6	921.5	896.4	841.8	710.3	614.3	537.6	497.7
62.5°	466.7	544.9	658.7	773.8	788.6	763.5	716.2	609.9	527.2	466.7	437.1
65°	404.6	478.5	570.0	657.2	670.5	643.9	595.1	518.4	448.9	410.5	382.5
67.5°	344.1	403.2	484.4	547.9	555.3	530.2	490.3	428.3	385.4	344.1	323.4
70°	290.9	335.2	398.7	450.4	453.4	429.7	409.1	353.0	320.5	290.9	274.7
72.5°	239.2	270.3	319.0	357.4	358.9	344.1	324.9	289.5	261.4	240.7	224.5
75°	189.0	215.6	245.1	279.1	277.6	265.8	251.1	228.9	205.3	192.0	184.6
77.5°	144.7	161.0	184.6	206.8	206.8	200.8	192.0	175.7	161.0	147.7	140.3
80°	103.4	113.7	132.9	140.3	143.2	141.8	134.4	122.6	116.7	106.3	103.4
82.5°	66.5	73.8	82.7	90.1	94.5	91.6	90.1	84.2	75.3	72.4	69.4
85°	38.4	41.4	45.8	50.2	51.7	50.2	53.2	48.7	44.3	44.3	42.8
87.5°	16.2	17.7	20.7	20.7	22.2	22.2	20.7	22.2	22.2	20.7	19.2
90°	1.1	4.1	7.1	10.0	13.0	14.5	17.2	22.7	28.2	33.6	39.1
92.5°	24.6	26.6	28.6	30.5	32.5	33.5	33.6	33.9	34.1	34.4	34.6
95°	58.0	60.5	63.0	65.5	68.0	69.2	69.4	69.9	70.4	70.9	71.4
97.5°	97.1	99.3	101.6	103.8	106.1	107.2	107.7	108.7	109.6	110.6	111.6
100°	141.8	143.8	145.8	147.7	149.7	150.7	151.1	151.8	152.5	153.3	154.0
102.5°	188.6	190.1	191.6	193.1	194.6	195.3	195.8	196.8	197.8	198.8	199.8
105°	240.0	240.7	241.5	242.2	242.9	243.3	243.6	244.1	244.6	245.1	245.6
107.5°	291.3	292.3	293.3	294.3	295.3	295.8	295.8	295.8	295.8	295.8	295.8
110°	340.5	342.0	343.5	345.0	346.5	347.2	347.2	347.2	347.2	347.2	347.2

TEST NUMBER: P997833

CATALOG NUMBER: SA2XXDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	394.0	395.5	397.0	398.5	400.0	400.7	400.6	400.3	400.1	399.8	399.6
115°	446.5	448.0	449.5	451.0	452.5	453.2	453.0	452.5	452.0	451.5	451.0
117.5°	499.0	501.0	503.0	504.9	506.9	507.9	507.3	506.0	504.8	503.5	502.3
120°	551.4	553.4	555.4	557.4	559.4	560.4	559.4	557.4	555.4	553.4	551.4
122.5°	599.4	601.9	604.4	606.9	609.4	610.6	610.0	608.7	607.5	606.2	605.0
125°	649.7	651.9	654.1	656.4	658.6	659.7	659.3	658.6	657.9	657.1	656.4
127.5°	698.8	701.5	704.3	707.0	709.7	711.1	710.6	709.6	708.6	707.6	706.6
130°	744.6	747.8	751.0	754.3	757.5	759.1	758.8	758.3	757.8	757.3	756.8
132.5°	795.9	798.4	800.9	803.4	805.9	807.1	807.2	807.5	807.7	808.0	808.2
135°	840.5	843.2	846.0	848.7	851.4	852.8	853.1	853.6	854.1	854.6	855.1
137.5°	889.7	891.9	894.1	896.4	898.6	899.7	899.9	900.4	900.9	901.4	901.9
140°	933.2	935.4	937.6	939.9	942.1	943.2	943.8	945.1	946.3	947.6	948.8
142.5°	977.9	980.1	982.3	984.6	986.8	987.9	988.3	989.0	989.7	990.5	991.2
145°	1020.3	1022.0	1023.8	1025.5	1027.2	1028.1	1028.8	1030.3	1031.8	1033.3	1034.8
147.5°	1058.2	1060.4	1062.7	1064.9	1067.2	1068.3	1068.8	1069.8	1070.7	1071.7	1072.7
150°	1097.3	1098.8	1100.3	1101.8	1103.3	1104.0	1104.5	1105.5	1106.5	1107.5	1108.5
152.5°	1131.9	1133.4	1134.9	1136.4	1137.9	1138.6	1139.2	1140.5	1141.7	1143.0	1144.2
155°	1166.5	1167.2	1168.0	1168.7	1169.4	1169.8	1170.2	1170.9	1171.7	1172.4	1173.2
157.5°	1196.6	1197.1	1197.6	1198.1	1198.6	1198.9	1199.1	1199.6	1200.1	1200.6	1201.1
160°	1223.4	1223.9	1224.4	1224.9	1225.4	1225.7	1225.8	1226.1	1226.3	1226.6	1226.8
162.5°	1248.0	1248.0	1248.0	1248.0	1248.0	1248.0	1248.1	1248.4	1248.6	1248.9	1249.1
165°	1269.2	1269.0	1268.7	1268.5	1268.2	1268.1	1268.1	1268.1	1268.1	1268.1	1268.1
167.5°	1288.2	1287.4	1286.7	1285.9	1285.2	1284.8	1284.8	1284.8	1284.8	1284.8	1284.8
170°	1302.7	1301.9	1301.2	1300.4	1299.7	1299.3	1299.2	1298.9	1298.7	1298.4	1298.2
172.5°	1312.7	1312.0	1311.2	1310.5	1309.8	1309.4	1309.3	1309.0	1308.8	1308.5	1308.3
175°	1320.5	1319.8	1319.0	1318.3	1317.6	1317.2	1317.0	1316.5	1316.0	1315.5	1315.0
177.5°	1325.0	1324.3	1323.5	1322.8	1322.1	1321.7	1321.4	1320.9	1320.4	1319.9	1319.4
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P997833

CATALOG NUMBER: SA2XXDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1996.6	1998.1	2001.1	2015.8	2023.2	2024.7	2018.8	2032.1	2036.5	2032.1	2029.1
5°	2091.1	2100.0	2117.7	2136.9	2135.4	2136.9	2145.8	2154.6	2157.6	2145.8	2150.2
7.5°	2173.8	2191.6	2210.8	2240.3	2240.3	2255.1	2261.0	2268.4	2286.1	2277.2	2274.3
10°	2268.4	2292.0	2327.4	2374.7	2376.2	2390.9	2405.7	2429.3	2436.7	2430.8	2433.8
12.5°	2386.5	2432.3	2435.2	2486.9	2510.6	2513.5	2537.1	2532.7	2547.5	2547.5	2572.6
15°	2438.2	2509.1	2549.0	2599.2	2613.9	2596.2	2615.4	2636.1	2637.6	2637.6	2636.1
17.5°	2531.2	2559.3	2599.2	2625.7	2631.7	2631.7	2633.1	2642.0	2636.1	2624.3	2633.1
20°	2550.4	2562.2	2577.0	2574.1	2577.0	2562.2	2547.5	2532.7	2534.2	2526.8	2549.0
22.5°	2515.0	2512.0	2478.1	2455.9	2455.9	2426.4	2398.3	2385.0	2371.7	2376.2	2383.5
25°	2426.4	2380.6	2339.2	2306.8	2299.4	2252.1	2213.7	2201.9	2179.8	2197.5	2200.4
27.5°	2284.6	2232.9	2166.5	2138.4	2100.0	2080.8	2054.2	2018.8	1973.0	1999.6	1995.2
30°	2132.5	2055.7	2001.1	1933.1	1872.6	1868.1	1817.9	1758.9	1735.2	1735.2	1748.5
32.5°	1962.7	1860.8	1781.0	1685.0	1626.0	1600.8	1540.3	1481.2	1494.5	1450.2	1466.5
35°	1764.8	1630.4	1530.0	1436.9	1392.6	1363.1	1284.8	1252.3	1216.9	1196.2	1234.6
37.5°	1575.7	1420.7	1292.2	1190.3	1174.1	1120.9	1067.7	1047.0	1026.4	1035.2	1033.8
40°	1345.4	1208.0	1092.8	1013.1	985.0	959.9	924.5	899.4	886.1	893.5	894.9
42.5°	1137.1	1021.9	936.3	880.2	856.5	838.8	821.1	800.4	796.0	796.0	801.9
45°	976.2	881.6	824.1	778.3	765.0	751.7	738.4	729.5	726.6	720.7	725.1
47.5°	847.7	772.4	736.9	703.0	688.2	685.2	673.4	669.0	663.1	661.6	663.1
50°	739.9	692.6	660.1	640.9	630.6	626.2	620.3	611.4	608.4	615.8	612.9
52.5°	664.6	620.3	602.5	583.3	577.4	571.5	562.7	564.1	562.7	559.7	559.7
55°	589.2	561.2	543.5	528.7	527.2	521.3	513.9	511.0	509.5	506.5	511.0
57.5°	528.7	506.5	490.3	477.0	471.1	471.1	463.7	457.8	457.8	456.3	457.8
60°	468.1	446.0	435.7	422.4	417.9	416.5	412.0	409.1	404.6	404.6	404.6
62.5°	412.0	394.3	382.5	370.7	372.2	364.8	358.9	355.9	355.9	357.4	357.4
65°	358.9	347.0	332.3	321.9	319.0	317.5	314.6	313.1	308.7	311.6	311.6
67.5°	310.1	293.9	285.0	280.6	276.2	274.7	271.7	268.8	267.3	265.8	268.8
70°	261.4	248.1	240.7	237.8	233.3	231.9	230.4	225.9	227.4	228.9	230.4
72.5°	217.1	205.3	203.8	194.9	194.9	194.9	189.0	192.0	190.5	187.6	190.5
75°	171.3	165.4	162.4	158.0	159.5	158.0	156.5	152.1	152.1	153.6	155.1
77.5°	135.9	130.0	128.5	124.1	121.1	124.1	121.1	119.6	119.6	121.1	121.1
80°	100.4	97.5	93.0	93.0	93.0	91.6	91.6	91.6	90.1	88.6	90.1
82.5°	66.5	66.5	65.0	63.5	65.0	62.0	63.5	63.5	63.5	63.5	63.5
85°	42.8	41.4	41.4	39.9	39.9	39.9	41.4	38.4	38.4	39.9	39.9
87.5°	19.2	19.2	19.2	20.7	19.2	19.2	19.2	20.7	19.2	19.2	19.2
90°	38.6	38.1	37.6	37.1	36.8	36.9	37.2	37.5	37.7	38.0	37.7
92.5°	34.8	35.1	35.3	35.6	35.7	35.7	35.7	35.7	35.7	35.7	35.7
95°	71.4	71.4	71.4	71.4	71.4	71.2	70.7	70.2	69.7	69.2	69.7
97.5°	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6
100°	154.0	154.0	154.0	154.0	154.0	153.9	153.6	153.4	153.1	152.9	153.1
102.5°	200.0	200.3	200.5	200.8	200.9	200.8	200.5	200.3	200.0	199.8	200.0
105°	246.1	246.6	247.1	247.6	247.8	247.8	247.8	247.8	247.8	247.8	247.8
107.5°	296.0	296.3	296.5	296.8	296.9	296.3	295.0	293.8	292.5	291.3	292.5
110°	347.2	347.2	347.2	347.2	347.2	346.8	346.1	345.3	344.6	343.8	344.6

TEST NUMBER: P997833

CATALOG NUMBER: SA2XXDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	398.9	398.1	397.4	396.7	396.3	396.0	395.5	395.0	394.5	394.0	394.5
115°	450.8	450.5	450.3	450.0	449.9	449.5	448.8	448.0	447.3	446.5	447.3
117.5°	501.6	500.8	500.1	499.4	499.0	498.6	497.9	497.1	496.4	495.6	496.4
120°	551.4	551.4	551.4	551.4	551.4	551.0	550.3	549.6	548.8	548.1	548.8
122.5°	604.3	603.5	602.8	602.1	601.7	601.4	600.9	600.4	599.9	599.4	599.9
125°	655.6	654.9	654.1	653.4	653.0	652.9	652.6	652.4	652.1	651.9	652.1
127.5°	705.6	704.6	703.6	702.6	702.1	701.7	701.0	700.3	699.5	698.8	699.5
130°	756.3	755.8	755.3	754.8	754.6	754.1	753.1	752.1	751.1	750.1	751.1
132.5°	807.0	805.7	804.5	803.2	802.6	802.2	801.5	800.7	800.0	799.2	800.0
135°	854.8	854.6	854.3	854.0	853.9	853.5	852.8	852.1	851.3	850.6	851.3
137.5°	901.7	901.4	901.2	900.9	900.8	900.3	899.3	898.4	897.4	896.4	897.4
140°	948.8	948.8	948.8	948.8	948.8	948.3	947.3	946.4	945.4	944.4	945.4
142.5°	991.5	991.7	992.0	992.3	992.4	991.9	990.9	989.9	988.9	987.9	988.9
145°	1035.0	1035.3	1035.5	1035.8	1035.9	1035.4	1034.4	1033.4	1032.4	1031.4	1032.4
147.5°	1073.2	1073.7	1074.2	1074.7	1075.0	1074.5	1073.5	1072.5	1071.5	1070.5	1071.5
150°	1109.2	1110.0	1110.7	1111.4	1111.8	1111.4	1110.7	1110.0	1109.2	1108.5	1109.2
152.5°	1145.2	1146.2	1147.1	1148.1	1148.6	1148.1	1147.1	1146.2	1145.2	1144.2	1145.2
155°	1174.4	1175.7	1176.9	1178.2	1178.8	1178.4	1177.7	1176.9	1176.2	1175.4	1176.2
157.5°	1202.8	1204.6	1206.3	1208.0	1208.9	1208.3	1207.0	1205.8	1204.5	1203.3	1204.5
160°	1228.3	1229.8	1231.3	1232.8	1233.5	1233.0	1232.0	1231.0	1230.0	1229.0	1230.0
162.5°	1250.8	1252.6	1254.3	1256.0	1256.9	1256.3	1255.0	1253.8	1252.5	1251.3	1252.5
165°	1269.8	1271.6	1273.3	1275.0	1275.9	1275.3	1274.0	1272.8	1271.5	1270.3	1271.5
167.5°	1286.5	1288.3	1290.0	1291.7	1292.6	1292.0	1290.8	1289.5	1288.3	1287.1	1288.3
170°	1299.9	1301.7	1303.4	1305.1	1306.0	1305.3	1303.8	1302.3	1300.8	1299.3	1300.8
172.5°	1310.0	1311.8	1313.5	1315.2	1316.1	1315.4	1313.9	1312.4	1310.9	1309.4	1310.9
175°	1316.7	1318.5	1320.2	1321.9	1322.8	1322.1	1320.6	1319.1	1317.6	1316.1	1317.6
177.5°	1320.9	1322.4	1323.9	1325.4	1326.1	1325.4	1323.9	1322.4	1320.9	1319.4	1320.9
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P997833

CATALOG NUMBER: SA2XXDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	2036.5	2026.2	2017.3	2018.8	2026.2	2020.3	2005.5	1986.3	1978.9	1970.0	1978.9
5°	2159.1	2150.2	2132.5	2134.0	2129.5	2123.6	2100.0	2070.5	2070.5	2046.8	2043.9
7.5°	2280.2	2266.9	2255.1	2252.1	2235.9	2224.1	2203.4	2162.0	2145.8	2117.7	2101.5
10°	2416.0	2405.7	2392.4	2376.2	2367.3	2346.6	2312.7	2252.1	2222.6	2184.2	2156.1
12.5°	2553.4	2551.9	2522.4	2489.9	2488.4	2455.9	2432.3	2351.1	2311.2	2259.5	2193.0
15°	2640.5	2633.1	2616.9	2600.6	2605.1	2569.6	2516.5	2420.5	2393.9	2331.9	2261.0
17.5°	2639.0	2639.0	2634.6	2631.7	2627.2	2616.9	2587.3	2523.8	2481.0	2402.7	2336.3
20°	2554.9	2574.1	2578.5	2577.0	2591.8	2599.2	2597.7	2557.8	2523.8	2454.4	2386.5
22.5°	2386.5	2430.8	2450.0	2461.8	2492.8	2509.1	2547.5	2532.7	2523.8	2472.2	2414.6
25°	2230.0	2244.7	2302.3	2305.3	2348.1	2388.0	2426.4	2451.5	2484.0	2464.8	2416.0
27.5°	2027.6	2061.6	2103.0	2134.0	2142.8	2224.1	2287.6	2334.8	2408.7	2414.6	2398.3
30°	1798.7	1815.0	1882.9	1924.3	1971.5	2030.6	2122.2	2203.4	2269.8	2330.4	2351.1
32.5°	1519.6	1586.1	1626.0	1676.2	1717.5	1822.4	1934.6	2039.5	2116.2	2218.1	2262.5
35°	1264.1	1315.8	1383.8	1404.4	1479.8	1568.4	1714.6	1848.9	1965.6	2069.0	2159.1
37.5°	1053.0	1094.3	1166.7	1199.2	1243.5	1357.2	1479.8	1646.6	1786.9	1913.9	2026.2
40°	908.2	939.2	993.9	1004.2	1041.1	1144.5	1243.5	1400.0	1586.1	1757.4	1880.0
42.5°	809.3	824.1	861.0	874.3	897.9	967.3	1055.9	1203.6	1376.4	1553.6	1726.4
45°	738.4	748.7	770.9	782.7	812.2	843.3	915.6	1033.8	1169.6	1348.3	1534.4
47.5°	674.9	688.2	697.0	704.4	720.7	754.6	801.9	889.0	1019.0	1182.9	1363.1
50°	621.7	626.2	642.4	643.9	654.2	676.4	720.7	773.8	877.2	1010.1	1184.4
52.5°	568.6	573.0	583.3	593.7	598.1	615.8	645.4	689.7	766.5	871.3	1026.4
55°	515.4	521.3	531.6	539.0	543.5	558.2	576.0	618.8	679.3	753.2	880.2
57.5°	462.2	475.5	478.5	482.9	490.3	506.5	522.8	547.9	595.1	663.1	756.1
60°	412.0	416.5	426.8	431.2	438.6	447.5	468.1	487.3	521.3	574.5	658.7
62.5°	360.3	370.7	375.1	379.5	385.4	395.8	409.1	429.7	459.3	502.1	568.6
65°	316.0	317.5	326.4	332.3	338.2	345.6	358.9	378.1	395.8	435.7	484.4
67.5°	273.2	276.2	279.1	285.0	292.4	299.8	311.6	321.9	344.1	370.7	409.1
70°	231.9	231.9	239.2	243.7	242.2	251.1	259.9	271.7	288.0	313.1	344.1
72.5°	194.9	193.5	199.4	200.8	203.8	209.7	215.6	227.4	236.3	255.5	279.1
75°	155.1	158.0	161.0	161.0	165.4	169.8	175.7	181.6	192.0	203.8	221.5
77.5°	122.6	122.6	125.5	127.0	131.4	130.0	135.9	141.8	149.2	159.5	172.8
80°	90.1	93.0	93.0	93.0	94.5	96.0	101.9	106.3	110.8	118.1	124.1
82.5°	63.5	63.5	66.5	66.5	66.5	69.4	69.4	70.9	73.8	78.3	82.7
85°	39.9	39.9	39.9	41.4	39.9	41.4	44.3	42.8	44.3	47.3	47.3
87.5°	19.2	19.2	19.2	19.2	19.2	20.7	19.2	20.7	22.2	22.2	22.2
90°	37.5	37.2	36.9	36.8	37.1	37.6	38.1	38.6	39.1	33.6	28.2
92.5°	35.7	35.7	35.7	35.7	35.6	35.3	35.1	34.8	34.6	34.4	34.1
95°	70.2	70.7	71.2	71.4	71.4	71.4	71.4	71.4	71.4	70.9	70.4
97.5°	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	110.6	109.6
100°	153.4	153.6	153.9	154.0	154.0	154.0	154.0	154.0	154.0	153.3	152.5
102.5°	200.3	200.5	200.8	200.9	200.8	200.5	200.3	200.0	199.8	198.8	197.8
105°	247.8	247.8	247.8	247.8	247.6	247.1	246.6	246.1	245.6	245.1	244.6
107.5°	293.8	295.0	296.3	296.9	296.8	296.5	296.3	296.0	295.8	295.8	295.8
110°	345.3	346.1	346.8	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2

TEST NUMBER: P997833

CATALOG NUMBER: SA2XXDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	395.0	395.5	396.0	396.3	396.7	397.4	398.1	398.9	399.6	399.8	400.1
115°	448.0	448.8	449.5	449.9	450.0	450.3	450.5	450.8	451.0	451.5	452.0
117.5°	497.1	497.9	498.6	499.0	499.4	500.1	500.8	501.6	502.3	503.5	504.8
120°	549.6	550.3	551.0	551.4	551.4	551.4	551.4	551.4	551.4	553.4	555.4
122.5°	600.4	600.9	601.4	601.7	602.1	602.8	603.5	604.3	605.0	606.2	607.5
125°	652.4	652.6	652.9	653.0	653.4	654.1	654.9	655.6	656.4	657.1	657.9
127.5°	700.3	701.0	701.7	702.1	702.6	703.6	704.6	705.6	706.6	707.6	708.6
130°	752.1	753.1	754.1	754.6	754.8	755.3	755.8	756.3	756.8	757.3	757.8
132.5°	800.7	801.5	802.2	802.6	803.2	804.5	805.7	807.0	808.2	808.0	807.7
135°	852.1	852.8	853.5	853.9	854.0	854.3	854.6	854.8	855.1	854.6	854.1
137.5°	898.4	899.3	900.3	900.8	900.9	901.2	901.4	901.7	901.9	901.4	900.9
140°	946.4	947.3	948.3	948.8	948.8	948.8	948.8	948.8	948.8	947.6	946.3
142.5°	989.9	990.9	991.9	992.4	992.3	992.0	991.7	991.5	991.2	990.5	989.7
145°	1033.4	1034.4	1035.4	1035.9	1035.8	1035.5	1035.3	1035.0	1034.8	1033.3	1031.8
147.5°	1072.5	1073.5	1074.5	1075.0	1074.7	1074.2	1073.7	1073.2	1072.7	1071.7	1070.7
150°	1110.0	1110.7	1111.4	1111.8	1111.4	1110.7	1110.0	1109.2	1108.5	1107.5	1106.5
152.5°	1146.2	1147.1	1148.1	1148.6	1148.1	1147.1	1146.2	1145.2	1144.2	1143.0	1141.7
155°	1176.9	1177.7	1178.4	1178.8	1178.2	1176.9	1175.7	1174.4	1173.2	1172.4	1171.7
157.5°	1205.8	1207.0	1208.3	1208.9	1208.0	1206.3	1204.6	1202.8	1201.1	1200.6	1200.1
160°	1231.0	1232.0	1233.0	1233.5	1232.8	1231.3	1229.8	1228.3	1226.8	1226.6	1226.3
162.5°	1253.8	1255.0	1256.3	1256.9	1256.0	1254.3	1252.6	1250.8	1249.1	1248.9	1248.6
165°	1272.8	1274.0	1275.3	1275.9	1275.0	1273.3	1271.6	1269.8	1268.1	1268.1	1268.1
167.5°	1289.5	1290.8	1292.0	1292.6	1291.7	1290.0	1288.3	1286.5	1284.8	1284.8	1284.8
170°	1302.3	1303.8	1305.3	1306.0	1305.1	1303.4	1301.7	1299.9	1298.2	1298.4	1298.7
172.5°	1312.4	1313.9	1315.4	1316.1	1315.2	1313.5	1311.8	1310.0	1308.3	1308.5	1308.8
175°	1319.1	1320.6	1322.1	1322.8	1321.9	1320.2	1318.5	1316.7	1315.0	1315.5	1316.0
177.5°	1322.4	1323.9	1325.4	1326.1	1325.4	1323.9	1322.4	1320.9	1319.4	1319.9	1320.4
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P997833

CATALOG NUMBER: SA2XXDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1971.5	1964.1	1959.7	1962.7	1953.8	1931.6	1931.6	1939.0	1930.2	1921.3	1908.0
5°	2026.2	2011.4	2002.5	2001.1	1980.4	1944.9	1937.6	1930.2	1911.0	1890.3	1868.1
7.5°	2079.3	2052.7	2038.0	2027.6	1998.1	1952.3	1933.1	1916.9	1885.9	1854.9	1826.8
10°	2123.6	2085.2	2067.5	2051.3	2012.9	1955.3	1924.3	1894.7	1854.9	1815.0	1779.5
12.5°	2159.1	2114.8	2092.6	2069.0	2021.7	1946.4	1908.0	1860.8	1820.9	1767.7	1732.3
15°	2218.1	2126.6	2105.9	2083.8	2035.0	1931.6	1884.4	1831.2	1776.6	1705.7	1667.3
17.5°	2265.4	2142.8	2141.4	2094.1	2030.6	1925.7	1853.4	1784.0	1724.9	1654.0	1593.5
20°	2293.5	2167.9	2144.3	2095.6	2015.8	1885.9	1810.6	1733.8	1670.3	1584.6	1524.1
22.5°	2317.1	2203.4	2141.4	2082.3	1984.8	1872.6	1761.8	1689.5	1602.3	1509.3	1451.7
25°	2326.0	2210.8	2145.8	2077.9	1962.7	1834.2	1708.7	1630.4	1532.9	1448.7	1370.5
27.5°	2327.4	2209.3	2129.5	2058.7	1931.6	1784.0	1655.5	1572.8	1465.0	1367.5	1289.2
30°	2312.7	2193.0	2120.7	2043.9	1902.1	1738.2	1590.5	1498.9	1383.8	1286.3	1205.1
32.5°	2268.4	2160.6	2101.5	2017.3	1863.7	1674.7	1528.5	1426.6	1305.5	1209.5	1131.2
35°	2194.5	2120.7	2055.7	1977.4	1813.5	1615.6	1466.5	1346.8	1224.3	1132.7	1058.9
37.5°	2103.0	2063.1	2002.5	1925.7	1755.9	1562.5	1397.0	1264.1	1141.6	1053.0	980.6
40°	1978.9	1989.2	1930.2	1860.8	1688.0	1490.1	1307.0	1180.0	1064.8	982.1	911.2
42.5°	1844.5	1887.3	1853.4	1786.9	1612.7	1410.3	1240.5	1100.2	988.0	902.3	843.3
45°	1699.8	1773.6	1753.0	1704.2	1534.4	1326.2	1146.0	1010.1	911.2	828.5	776.8
47.5°	1541.8	1646.6	1646.6	1611.2	1447.3	1242.0	1064.8	926.0	828.5	769.4	719.2
50°	1380.8	1498.9	1518.1	1494.5	1349.8	1146.0	965.8	840.3	756.1	698.5	661.6
52.5°	1212.4	1349.8	1385.2	1373.4	1246.4	1054.4	884.6	762.0	685.2	635.0	602.5
55°	1051.5	1211.0	1249.4	1253.8	1135.7	954.0	794.5	686.7	612.9	578.9	550.8
57.5°	899.4	1053.0	1095.8	1103.2	1023.4	862.4	710.3	615.8	549.4	521.3	499.2
60°	769.4	897.9	954.0	970.3	900.8	756.1	632.1	540.5	490.3	463.7	443.0
62.5°	663.1	766.5	825.5	830.0	798.9	663.1	550.8	474.1	431.2	407.6	397.3
65°	559.7	652.7	688.2	705.9	680.8	574.5	475.5	412.0	378.1	357.4	347.0
67.5°	477.0	536.1	565.6	589.2	564.1	484.4	404.6	353.0	327.8	307.2	301.3
70°	391.4	440.1	462.2	485.9	463.7	403.2	345.6	298.3	276.2	259.9	252.5
72.5°	313.1	351.5	372.2	386.9	373.6	323.4	276.2	243.7	227.4	215.6	211.2
75°	248.1	274.7	286.5	296.8	290.9	252.5	223.0	196.4	181.6	171.3	168.4
77.5°	189.0	208.2	221.5	224.5	217.1	192.0	166.9	150.6	138.8	132.9	130.0
80°	134.4	146.2	153.6	158.0	150.6	140.3	122.6	110.8	100.4	93.0	91.6
82.5°	90.1	96.0	101.9	100.4	97.5	88.6	78.3	72.4	67.9	62.0	62.0
85°	51.7	53.2	56.1	57.6	56.1	50.2	44.3	41.4	38.4	34.0	34.0
87.5°	22.2	23.6	23.6	25.1	22.2	22.2	19.2	16.2	16.2	14.8	13.3
90°	22.7	17.2	14.5	13.0	10.0	7.1	4.1	1.1	4.1	7.1	10.0
92.5°	33.9	33.6	33.5	32.5	30.5	28.6	26.6	24.6	26.6	28.6	30.5
95°	69.9	69.4	69.2	68.0	65.5	63.0	60.5	58.0	60.5	63.0	65.5
97.5°	108.7	107.7	107.2	106.1	103.8	101.6	99.3	97.1	99.3	101.6	103.8
100°	151.8	151.1	150.7	149.7	147.7	145.8	143.8	141.8	143.8	145.8	147.7
102.5°	196.8	195.8	195.3	194.6	193.1	191.6	190.1	188.6	190.1	191.6	193.1
105°	244.1	243.6	243.3	242.9	242.2	241.5	240.7	240.0	240.7	241.5	242.2
107.5°	295.8	295.8	295.8	295.3	294.3	293.3	292.3	291.3	292.3	293.3	294.3
110°	347.2	347.2	347.2	346.5	345.0	343.5	342.0	340.5	342.0	343.5	345.0

TEST NUMBER: P997833

CATALOG NUMBER: SA2XXDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	400.3	400.6	400.7	400.0	398.5	397.0	395.5	394.0	395.5	397.0	398.5
115°	452.5	453.0	453.2	452.5	451.0	449.5	448.0	446.5	448.0	449.5	451.0
117.5°	506.0	507.3	507.9	506.9	504.9	503.0	501.0	499.0	501.0	503.0	504.9
120°	557.4	559.4	560.4	559.4	557.4	555.4	553.4	551.4	553.4	555.4	557.4
122.5°	608.7	610.0	610.6	609.4	606.9	604.4	601.9	599.4	601.9	604.4	606.9
125°	658.6	659.3	659.7	658.6	656.4	654.1	651.9	649.7	651.9	654.1	656.4
127.5°	709.6	710.6	711.1	709.7	707.0	704.3	701.5	698.8	701.5	704.3	707.0
130°	758.3	758.8	759.1	757.5	754.3	751.0	747.8	744.6	747.8	751.0	754.3
132.5°	807.5	807.2	807.1	805.9	803.4	800.9	798.4	795.9	798.4	800.9	803.4
135°	853.6	853.1	852.8	851.4	848.7	846.0	843.2	840.5	843.2	846.0	848.7
137.5°	900.4	899.9	899.7	898.6	896.4	894.1	891.9	889.7	891.9	894.1	896.4
140°	945.1	943.8	943.2	942.1	939.9	937.6	935.4	933.2	935.4	937.6	939.9
142.5°	989.0	988.3	987.9	986.8	984.6	982.3	980.1	977.9	980.1	982.3	984.6
145°	1030.3	1028.8	1028.1	1027.2	1025.5	1023.8	1022.0	1020.3	1022.0	1023.8	1025.5
147.5°	1069.8	1068.8	1068.3	1067.2	1064.9	1062.7	1060.4	1058.2	1060.4	1062.7	1064.9
150°	1105.5	1104.5	1104.0	1103.3	1101.8	1100.3	1098.8	1097.3	1098.8	1100.3	1101.8
152.5°	1140.5	1139.2	1138.6	1137.9	1136.4	1134.9	1133.4	1131.9	1133.4	1134.9	1136.4
155°	1170.9	1170.2	1169.8	1169.4	1168.7	1168.0	1167.2	1166.5	1167.2	1168.0	1168.7
157.5°	1199.6	1199.1	1198.9	1198.6	1198.1	1197.6	1197.1	1196.6	1197.1	1197.6	1198.1
160°	1226.1	1225.8	1225.7	1225.4	1224.9	1224.4	1223.9	1223.4	1223.9	1224.4	1224.9
162.5°	1248.4	1248.1	1248.0	1248.0	1248.0	1248.0	1248.0	1248.0	1248.0	1248.0	1248.0
165°	1268.1	1268.1	1268.1	1268.2	1268.5	1268.7	1269.0	1269.2	1269.0	1268.7	1268.5
167.5°	1284.8	1284.8	1284.8	1285.2	1285.9	1286.7	1287.4	1288.2	1287.4	1286.7	1285.9
170°	1298.9	1299.2	1299.3	1299.7	1300.4	1301.2	1301.9	1302.7	1301.9	1301.2	1300.4
172.5°	1309.0	1309.3	1309.4	1309.8	1310.5	1311.2	1312.0	1312.7	1312.0	1311.2	1310.5
175°	1316.5	1317.0	1317.2	1317.6	1318.3	1319.0	1319.8	1320.5	1319.8	1319.0	1318.3
177.5°	1320.9	1321.4	1321.7	1322.1	1322.8	1323.5	1324.3	1325.0	1324.3	1323.5	1322.8
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P997833

CATALOG NUMBER: SA2XXDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1900.6	1908.0	1906.5	1891.8	1875.5	1862.2	1837.1	1840.1	1831.2	1832.7	1841.6
5°	1853.4	1853.4	1847.5	1826.8	1800.2	1785.4	1757.4	1750.0	1732.3	1730.8	1729.3
7.5°	1803.2	1795.8	1788.4	1758.9	1726.4	1702.7	1664.3	1655.5	1637.8	1626.0	1620.0
10°	1744.1	1733.8	1719.0	1685.0	1645.2	1615.6	1575.7	1563.9	1530.0	1515.2	1506.3
12.5°	1679.1	1673.2	1649.6	1621.5	1556.5	1524.1	1466.5	1478.3	1444.3	1414.8	1410.3
15°	1614.1	1592.0	1578.7	1532.9	1454.6	1439.9	1394.1	1370.5	1339.5	1315.8	1315.8
17.5°	1550.6	1516.7	1487.1	1438.4	1380.8	1339.5	1305.5	1293.7	1255.3	1231.6	1227.2
20°	1466.5	1428.1	1420.7	1351.3	1311.4	1265.6	1233.1	1203.6	1175.5	1165.2	1157.8
22.5°	1386.7	1342.4	1330.6	1271.5	1231.6	1185.9	1153.4	1132.7	1112.0	1104.6	1091.4
25°	1301.1	1274.5	1256.8	1193.3	1148.9	1106.1	1084.0	1069.2	1050.0	1048.5	1039.7
27.5°	1218.4	1193.3	1175.5	1115.0	1082.5	1042.6	1024.9	1008.7	998.3	993.9	989.5
30°	1147.5	1119.4	1098.7	1054.4	1014.6	982.1	967.3	957.0	951.1	943.7	942.2
32.5°	1069.2	1053.0	1024.9	990.9	959.9	928.9	920.0	912.7	903.8	900.8	899.4
35°	1002.7	980.6	962.9	924.5	911.2	884.6	874.3	868.4	856.5	853.6	850.6
37.5°	937.8	917.1	897.9	874.3	849.2	834.4	828.5	819.6	813.7	815.2	812.2
40°	872.8	856.5	841.8	816.7	801.9	794.5	782.7	773.8	770.9	772.4	770.9
42.5°	809.3	794.5	785.7	766.5	751.7	744.3	736.9	728.1	732.5	732.5	736.9
45°	751.7	738.4	732.5	717.7	708.9	697.0	689.7	688.2	694.1	692.6	692.6
47.5°	692.6	688.2	680.8	667.5	655.7	648.3	646.8	646.8	652.7	655.7	654.2
50°	646.8	638.0	629.1	618.8	609.9	607.0	602.5	605.5	611.4	611.4	614.3
52.5°	589.2	583.3	580.4	571.5	565.6	565.6	565.6	567.1	571.5	576.0	574.5
55°	539.0	534.6	531.6	527.2	519.8	521.3	519.8	522.8	527.2	531.6	534.6
57.5°	485.9	484.4	481.4	474.1	474.1	472.6	477.0	478.5	485.9	488.8	493.3
60°	438.6	434.2	434.2	428.3	428.3	428.3	432.7	437.1	443.0	444.5	447.5
62.5°	388.4	388.4	386.9	382.5	382.5	386.9	388.4	394.3	397.3	397.3	401.7
65°	341.1	339.7	338.2	339.7	341.1	341.1	345.6	348.5	351.5	353.0	354.4
67.5°	293.9	292.4	295.4	293.9	296.8	302.7	301.3	305.7	310.1	310.1	311.6
70°	249.6	252.5	251.1	254.0	252.5	255.5	259.9	261.4	261.4	262.9	267.3
72.5°	208.2	208.2	208.2	206.8	208.2	211.2	214.1	215.6	218.6	220.0	224.5
75°	168.4	168.4	165.4	168.4	168.4	171.3	174.3	174.3	174.3	177.2	181.6
77.5°	127.0	128.5	127.0	130.0	130.0	131.4	134.4	132.9	135.9	137.3	138.8
80°	93.0	91.6	91.6	91.6	93.0	93.0	96.0	97.5	97.5	101.9	98.9
82.5°	59.1	60.5	59.1	60.5	60.5	62.0	60.5	62.0	63.5	66.5	65.0
85°	34.0	32.5	32.5	34.0	32.5	32.5	34.0	32.5	34.0	32.5	34.0
87.5°	13.3	11.8	11.8	11.8	11.8	10.3	10.3	8.9	8.9	8.9	7.4
90°	13.0	14.5	17.2	22.7	28.2	33.6	39.1	38.6	38.1	37.6	37.1
92.5°	32.5	33.5	33.6	33.9	34.1	34.4	34.6	34.8	35.1	35.3	35.6
95°	68.0	69.2	69.4	69.9	70.4	70.9	71.4	71.4	71.4	71.4	71.4
97.5°	106.1	107.2	107.7	108.7	109.6	110.6	111.6	111.6	111.6	111.6	111.6
100°	149.7	150.7	151.1	151.8	152.5	153.3	154.0	154.0	154.0	154.0	154.0
102.5°	194.6	195.3	195.8	196.8	197.8	198.8	199.8	200.0	200.3	200.5	200.8
105°	242.9	243.3	243.6	244.1	244.6	245.1	245.6	246.1	246.6	247.1	247.6
107.5°	295.3	295.8	295.8	295.8	295.8	295.8	295.8	296.0	296.3	296.5	296.8
110°	346.5	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2

TEST NUMBER: P997833

CATALOG NUMBER: SA2XXDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	400.0	400.7	400.6	400.3	400.1	399.8	399.6	398.9	398.1	397.4	396.7
115°	452.5	453.2	453.0	452.5	452.0	451.5	451.0	450.8	450.5	450.3	450.0
117.5°	506.9	507.9	507.3	506.0	504.8	503.5	502.3	501.6	500.8	500.1	499.4
120°	559.4	560.4	559.4	557.4	555.4	553.4	551.4	551.4	551.4	551.4	551.4
122.5°	609.4	610.6	610.0	608.7	607.5	606.2	605.0	604.3	603.5	602.8	602.1
125°	658.6	659.7	659.3	658.6	657.9	657.1	656.4	655.6	654.9	654.1	653.4
127.5°	709.7	711.1	710.6	709.6	708.6	707.6	706.6	705.6	704.6	703.6	702.6
130°	757.5	759.1	758.8	758.3	757.8	757.3	756.8	756.3	755.8	755.3	754.8
132.5°	805.9	807.1	807.2	807.5	807.7	808.0	808.2	807.0	805.7	804.5	803.2
135°	851.4	852.8	853.1	853.6	854.1	854.6	855.1	854.8	854.6	854.3	854.0
137.5°	898.6	899.7	899.9	900.4	900.9	901.4	901.9	901.7	901.4	901.2	900.9
140°	942.1	943.2	943.8	945.1	946.3	947.6	948.8	948.8	948.8	948.8	948.8
142.5°	986.8	987.9	988.3	989.0	989.7	990.5	991.2	991.5	991.7	992.0	992.3
145°	1027.2	1028.1	1028.8	1030.3	1031.8	1033.3	1034.8	1035.0	1035.3	1035.5	1035.8
147.5°	1067.2	1068.3	1068.8	1069.8	1070.7	1071.7	1072.7	1073.2	1073.7	1074.2	1074.7
150°	1103.3	1104.0	1104.5	1105.5	1106.5	1107.5	1108.5	1109.2	1110.0	1110.7	1111.4
152.5°	1137.9	1138.6	1139.2	1140.5	1141.7	1143.0	1144.2	1145.2	1146.2	1147.1	1148.1
155°	1169.4	1169.8	1170.2	1170.9	1171.7	1172.4	1173.2	1174.4	1175.7	1176.9	1178.2
157.5°	1198.6	1198.9	1199.1	1199.6	1200.1	1200.6	1201.1	1202.8	1204.6	1206.3	1208.0
160°	1225.4	1225.7	1225.8	1226.1	1226.3	1226.6	1226.8	1228.3	1229.8	1231.3	1232.8
162.5°	1248.0	1248.0	1248.1	1248.4	1248.6	1248.9	1249.1	1250.8	1252.6	1254.3	1256.0
165°	1268.2	1268.1	1268.1	1268.1	1268.1	1268.1	1268.1	1269.8	1271.6	1273.3	1275.0
167.5°	1285.2	1284.8	1284.8	1284.8	1284.8	1284.8	1284.8	1286.5	1288.3	1290.0	1291.7
170°	1299.7	1299.3	1299.2	1298.9	1298.7	1298.4	1298.2	1299.9	1301.7	1303.4	1305.1
172.5°	1309.8	1309.4	1309.3	1309.0	1308.8	1308.5	1308.3	1310.0	1311.8	1313.5	1315.2
175°	1317.6	1317.2	1317.0	1316.5	1316.0	1315.5	1315.0	1316.7	1318.5	1320.2	1321.9
177.5°	1322.1	1321.7	1321.4	1320.9	1320.4	1319.9	1319.4	1320.9	1322.4	1323.9	1325.4
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P997833

CATALOG NUMBER: SA2XXDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1831.2	1835.7	1825.3	1822.4	1825.3	1815.0	1817.9	1820.9	1820.9	1825.3	1828.3
5°	1724.9	1719.0	1708.7	1705.7	1702.7	1707.2	1704.2	1708.7	1710.1	1720.5	1721.9
7.5°	1620.0	1611.2	1602.3	1593.5	1590.5	1583.1	1590.5	1590.5	1600.8	1597.9	1605.3
10°	1496.0	1494.5	1482.7	1478.3	1472.4	1460.6	1476.8	1472.4	1479.8	1493.0	1496.0
12.5°	1404.4	1388.2	1395.6	1374.9	1382.3	1370.5	1371.9	1371.9	1383.8	1385.2	1382.3
15°	1317.3	1304.0	1284.8	1276.0	1271.5	1265.6	1284.8	1286.3	1277.4	1298.1	1290.7
17.5°	1228.7	1228.7	1211.0	1206.5	1194.7	1200.6	1197.7	1199.2	1196.2	1211.0	1218.4
20°	1151.9	1144.5	1138.6	1140.1	1125.3	1122.4	1119.4	1122.4	1132.7	1143.0	1146.0
22.5°	1089.9	1085.4	1070.7	1073.6	1061.8	1066.2	1063.3	1070.7	1072.2	1072.2	1082.5
25°	1030.8	1024.9	1026.4	1020.5	1016.0	1016.0	1011.6	1016.0	1021.9	1024.9	1026.4
27.5°	986.5	982.1	974.7	970.3	973.2	965.8	971.7	976.2	976.2	973.2	976.2
30°	933.3	936.3	936.3	921.5	927.4	924.5	928.9	931.9	931.9	933.3	930.4
32.5°	897.9	889.0	887.6	886.1	886.1	880.2	880.2	884.6	886.1	887.6	892.0
35°	850.6	850.6	843.3	847.7	841.8	843.3	841.8	843.3	846.2	841.8	846.2
37.5°	807.8	809.3	806.3	809.3	810.8	807.8	804.9	810.8	807.8	807.8	804.9
40°	770.9	769.4	770.9	770.9	770.9	772.4	769.4	769.4	769.4	766.5	763.5
42.5°	739.9	731.0	734.0	735.4	731.0	731.0	732.5	731.0	735.4	726.6	726.6
45°	695.6	692.6	694.1	694.1	697.0	692.6	695.6	697.0	692.6	691.1	688.2
47.5°	655.7	658.7	655.7	658.7	658.7	661.6	655.7	657.2	658.7	652.7	648.3
50°	615.8	615.8	620.3	618.8	620.3	617.3	617.3	615.8	617.3	614.3	609.9
52.5°	578.9	574.5	581.9	580.4	578.9	577.4	576.0	577.4	574.5	571.5	571.5
55°	533.1	533.1	537.6	539.0	539.0	536.1	533.1	534.6	533.1	531.6	530.2
57.5°	496.2	490.3	493.3	494.7	494.7	490.3	493.3	490.3	490.3	491.8	487.3
60°	448.9	448.9	446.0	450.4	450.4	447.5	447.5	448.9	446.0	444.5	443.0
62.5°	398.7	400.2	404.6	406.1	407.6	404.6	401.7	403.2	403.2	398.7	400.2
65°	355.9	358.9	364.8	363.3	360.3	361.8	358.9	360.3	355.9	357.4	353.0
67.5°	314.6	313.1	314.6	314.6	317.5	316.0	313.1	313.1	311.6	316.0	311.6
70°	270.3	270.3	270.3	270.3	271.7	273.2	270.3	267.3	268.8	265.8	264.3
72.5°	224.5	225.9	224.5	227.4	223.0	225.9	225.9	224.5	223.0	223.0	223.0
75°	181.6	184.6	180.2	181.6	180.2	183.1	181.6	181.6	178.7	177.2	178.7
77.5°	138.8	140.3	137.3	138.8	137.3	138.8	138.8	137.3	137.3	137.3	137.3
80°	98.9	100.4	98.9	97.5	96.0	98.9	96.0	97.5	98.9	97.5	100.4
82.5°	63.5	63.5	62.0	63.5	60.5	60.5	62.0	62.0	60.5	63.5	60.5
85°	31.0	31.0	34.0	31.0	29.5	29.5	29.5	31.0	29.5	32.5	31.0
87.5°	7.4	5.9	7.4	7.4	5.9	5.9	7.4	5.9	7.4	8.9	5.9
90°	36.8	36.9	37.2	37.5	37.7	38.0	37.7	37.5	37.2	36.9	36.8
92.5°	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7
95°	71.4	71.2	70.7	70.2	69.7	69.2	69.7	70.2	70.7	71.2	71.4
97.5°	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6
100°	154.0	153.9	153.6	153.4	153.1	152.9	153.1	153.4	153.6	153.9	154.0
102.5°	200.9	200.8	200.5	200.3	200.0	199.8	200.0	200.3	200.5	200.8	200.9
105°	247.8	247.8	247.8	247.8	247.8	247.8	247.8	247.8	247.8	247.8	247.8
107.5°	296.9	296.3	295.0	293.8	292.5	291.3	292.5	293.8	295.0	296.3	296.9
110°	347.2	346.8	346.1	345.3	344.6	343.8	344.6	345.3	346.1	346.8	347.2

TEST NUMBER: P997833

CATALOG NUMBER: SA2XXDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	396.3	396.0	395.5	395.0	394.5	394.0	394.5	395.0	395.5	396.0	396.3
115°	449.9	449.5	448.8	448.0	447.3	446.5	447.3	448.0	448.8	449.5	449.9
117.5°	499.0	498.6	497.9	497.1	496.4	495.6	496.4	497.1	497.9	498.6	499.0
120°	551.4	551.0	550.3	549.6	548.8	548.1	548.8	549.6	550.3	551.0	551.4
122.5°	601.7	601.4	600.9	600.4	599.9	599.4	599.9	600.4	600.9	601.4	601.7
125°	653.0	652.9	652.6	652.4	652.1	651.9	652.1	652.4	652.6	652.9	653.0
127.5°	702.1	701.7	701.0	700.3	699.5	698.8	699.5	700.3	701.0	701.7	702.1
130°	754.6	754.1	753.1	752.1	751.1	750.1	751.1	752.1	753.1	754.1	754.6
132.5°	802.6	802.2	801.5	800.7	800.0	799.2	800.0	800.7	801.5	802.2	802.6
135°	853.9	853.5	852.8	852.1	851.3	850.6	851.3	852.1	852.8	853.5	853.9
137.5°	900.8	900.3	899.3	898.4	897.4	896.4	897.4	898.4	899.3	900.3	900.8
140°	948.8	948.3	947.3	946.4	945.4	944.4	945.4	946.4	947.3	948.3	948.8
142.5°	992.4	991.9	990.9	989.9	988.9	987.9	988.9	989.9	990.9	991.9	992.4
145°	1035.9	1035.4	1034.4	1033.4	1032.4	1031.4	1032.4	1033.4	1034.4	1035.4	1035.9
147.5°	1075.0	1074.5	1073.5	1072.5	1071.5	1070.5	1071.5	1072.5	1073.5	1074.5	1075.0
150°	1111.8	1111.4	1110.7	1110.0	1109.2	1108.5	1109.2	1110.0	1110.7	1111.4	1111.8
152.5°	1148.6	1148.1	1147.1	1146.2	1145.2	1144.2	1145.2	1146.2	1147.1	1148.1	1148.6
155°	1178.8	1178.4	1177.7	1176.9	1176.2	1175.4	1176.2	1176.9	1177.7	1178.4	1178.8
157.5°	1208.9	1208.3	1207.0	1205.8	1204.5	1203.3	1204.5	1205.8	1207.0	1208.3	1208.9
160°	1233.5	1233.0	1232.0	1231.0	1230.0	1229.0	1230.0	1231.0	1232.0	1233.0	1233.5
162.5°	1256.9	1256.3	1255.0	1253.8	1252.5	1251.3	1252.5	1253.8	1255.0	1256.3	1256.9
165°	1275.9	1275.3	1274.0	1272.8	1271.5	1270.3	1271.5	1272.8	1274.0	1275.3	1275.9
167.5°	1292.6	1292.0	1290.8	1289.5	1288.3	1287.1	1288.3	1289.5	1290.8	1292.0	1292.6
170°	1306.0	1305.3	1303.8	1302.3	1300.8	1299.3	1300.8	1302.3	1303.8	1305.3	1306.0
172.5°	1316.1	1315.4	1313.9	1312.4	1310.9	1309.4	1310.9	1312.4	1313.9	1315.4	1316.1
175°	1322.8	1322.1	1320.6	1319.1	1317.6	1316.1	1317.6	1319.1	1320.6	1322.1	1322.8
177.5°	1326.1	1325.4	1323.9	1322.4	1320.9	1319.4	1320.9	1322.4	1323.9	1325.4	1326.1
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P997833

CATALOG NUMBER: SA2XXDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1823.8	1835.7	1831.2	1815.0	1834.2	1834.2	1847.5	1847.5	1863.7	1869.6	1878.5
5°	1720.5	1729.3	1736.7	1729.3	1742.6	1763.3	1775.1	1785.4	1807.6	1816.5	1829.8
7.5°	1609.7	1626.0	1633.3	1633.3	1655.5	1679.1	1702.7	1717.5	1748.5	1760.3	1773.6
10°	1501.9	1521.1	1535.9	1534.4	1571.3	1586.1	1615.6	1649.6	1680.6	1698.3	1717.5
12.5°	1388.2	1398.5	1419.2	1448.7	1457.6	1484.2	1518.1	1561.0	1617.1	1633.3	1661.4
15°	1293.7	1321.7	1338.0	1351.3	1371.9	1397.0	1434.0	1475.3	1531.4	1566.9	1596.4
17.5°	1213.9	1250.8	1261.2	1258.2	1284.8	1323.2	1366.0	1397.0	1447.3	1490.1	1518.1
20°	1148.9	1163.7	1181.4	1188.8	1209.5	1250.8	1292.2	1327.6	1369.0	1403.0	1435.4
22.5°	1084.0	1095.8	1110.6	1123.8	1140.1	1163.7	1203.6	1247.9	1287.8	1320.3	1357.2
25°	1030.8	1038.2	1051.5	1061.8	1079.5	1095.8	1123.8	1172.6	1219.8	1239.0	1271.5
27.5°	979.1	985.0	993.9	1005.7	1014.6	1030.8	1055.9	1095.8	1144.5	1163.7	1208.0
30°	933.3	937.8	946.6	952.5	957.0	976.2	995.4	1026.4	1063.3	1089.9	1122.4
32.5°	890.5	894.9	903.8	905.3	911.2	921.5	939.2	967.3	999.8	1021.9	1050.0
35°	843.3	846.2	855.1	858.0	862.4	871.3	884.6	905.3	934.8	951.1	976.2
37.5°	806.3	804.9	810.8	815.2	821.1	825.5	830.0	850.6	872.8	887.6	906.8
40°	766.5	763.5	765.0	770.9	773.8	779.7	779.7	800.4	815.2	827.0	841.8
42.5°	726.6	725.1	722.2	725.1	728.1	729.5	731.0	745.8	760.6	770.9	787.1
45°	686.7	685.2	682.3	683.8	683.8	686.7	691.1	697.0	707.4	716.2	725.1
47.5°	649.8	646.8	642.4	640.9	643.9	643.9	643.9	649.8	660.1	663.1	671.9
50°	611.4	607.0	601.1	598.1	598.1	596.6	599.6	601.1	609.9	612.9	620.3
52.5°	570.0	567.1	561.2	555.3	556.8	553.8	555.3	556.8	559.7	564.1	568.6
55°	528.7	522.8	518.4	516.9	512.4	512.4	508.0	513.9	512.4	513.9	519.8
57.5°	488.8	482.9	475.5	472.6	468.1	466.7	463.7	462.2	463.7	468.1	472.6
60°	441.6	438.6	434.2	429.7	426.8	422.4	419.4	419.4	417.9	417.9	419.4
62.5°	395.8	394.3	388.4	386.9	384.0	381.0	376.6	373.6	373.6	376.6	378.1
65°	351.5	350.0	345.6	344.1	336.7	333.8	332.3	330.8	327.8	327.8	327.8
67.5°	310.1	305.7	305.7	298.3	292.4	289.5	286.5	285.0	285.0	285.0	286.5
70°	264.3	264.3	259.9	255.5	249.6	251.1	246.6	242.2	242.2	239.2	240.7
72.5°	220.0	218.6	214.1	212.7	208.2	203.8	200.8	203.8	199.4	197.9	199.4
75°	177.2	175.7	172.8	169.8	171.3	166.9	162.4	161.0	161.0	158.0	158.0
77.5°	135.9	138.8	132.9	131.4	128.5	125.5	124.1	122.6	122.6	122.6	125.5
80°	94.5	96.0	96.0	93.0	94.5	90.1	90.1	90.1	85.7	87.1	88.6
82.5°	60.5	60.5	59.1	60.5	59.1	59.1	57.6	57.6	56.1	56.1	57.6
85°	34.0	32.5	31.0	34.0	32.5	32.5	31.0	31.0	31.0	31.0	31.0
87.5°	7.4	8.9	8.9	8.9	8.9	10.3	10.3	10.3	11.8	11.8	11.8
90°	37.1	37.6	38.1	38.6	39.1	33.6	28.2	22.7	17.2	14.5	13.0
92.5°	35.6	35.3	35.1	34.8	34.6	34.4	34.1	33.9	33.6	33.5	32.5
95°	71.4	71.4	71.4	71.4	71.4	70.9	70.4	69.9	69.4	69.2	68.0
97.5°	111.6	111.6	111.6	111.6	111.6	110.6	109.6	108.7	107.7	107.2	106.1
100°	154.0	154.0	154.0	154.0	154.0	153.3	152.5	151.8	151.1	150.7	149.7
102.5°	200.8	200.5	200.3	200.0	199.8	198.8	197.8	196.8	195.8	195.3	194.6
105°	247.6	247.1	246.6	246.1	245.6	245.1	244.6	244.1	243.6	243.3	242.9
107.5°	296.8	296.5	296.3	296.0	295.8	295.8	295.8	295.8	295.8	295.8	295.3
110°	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2	346.5

TEST NUMBER: P997833

CATALOG NUMBER: SA2XXDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	396.7	397.4	398.1	398.9	399.6	399.8	400.1	400.3	400.6	400.7	400.0
115°	450.0	450.3	450.5	450.8	451.0	451.5	452.0	452.5	453.0	453.2	452.5
117.5°	499.4	500.1	500.8	501.6	502.3	503.5	504.8	506.0	507.3	507.9	506.9
120°	551.4	551.4	551.4	551.4	551.4	553.4	555.4	557.4	559.4	560.4	559.4
122.5°	602.1	602.8	603.5	604.3	605.0	606.2	607.5	608.7	610.0	610.6	609.4
125°	653.4	654.1	654.9	655.6	656.4	657.1	657.9	658.6	659.3	659.7	658.6
127.5°	702.6	703.6	704.6	705.6	706.6	707.6	708.6	709.6	710.6	711.1	709.7
130°	754.8	755.3	755.8	756.3	756.8	757.3	757.8	758.3	758.8	759.1	757.5
132.5°	803.2	804.5	805.7	807.0	808.2	808.0	807.7	807.5	807.2	807.1	805.9
135°	854.0	854.3	854.6	854.8	855.1	854.6	854.1	853.6	853.1	852.8	851.4
137.5°	900.9	901.2	901.4	901.7	901.9	901.4	900.9	900.4	899.9	899.7	898.6
140°	948.8	948.8	948.8	948.8	948.8	947.6	946.3	945.1	943.8	943.2	942.1
142.5°	992.3	992.0	991.7	991.5	991.2	990.5	989.7	989.0	988.3	987.9	986.8
145°	1035.8	1035.5	1035.3	1035.0	1034.8	1033.3	1031.8	1030.3	1028.8	1028.1	1027.2
147.5°	1074.7	1074.2	1073.7	1073.2	1072.7	1071.7	1070.7	1069.8	1068.8	1068.3	1067.2
150°	1111.4	1110.7	1110.0	1109.2	1108.5	1107.5	1106.5	1105.5	1104.5	1104.0	1103.3
152.5°	1148.1	1147.1	1146.2	1145.2	1144.2	1143.0	1141.7	1140.5	1139.2	1138.6	1137.9
155°	1178.2	1176.9	1175.7	1174.4	1173.2	1172.4	1171.7	1170.9	1170.2	1169.8	1169.4
157.5°	1208.0	1206.3	1204.6	1202.8	1201.1	1200.6	1200.1	1199.6	1199.1	1198.9	1198.6
160°	1232.8	1231.3	1229.8	1228.3	1226.8	1226.6	1226.3	1226.1	1225.8	1225.7	1225.4
162.5°	1256.0	1254.3	1252.6	1250.8	1249.1	1248.9	1248.6	1248.4	1248.1	1248.0	1248.0
165°	1275.0	1273.3	1271.6	1269.8	1268.1	1268.1	1268.1	1268.1	1268.1	1268.1	1268.2
167.5°	1291.7	1290.0	1288.3	1286.5	1284.8	1284.8	1284.8	1284.8	1284.8	1284.8	1285.2
170°	1305.1	1303.4	1301.7	1299.9	1298.2	1298.4	1298.7	1298.9	1299.2	1299.3	1299.7
172.5°	1315.2	1313.5	1311.8	1310.0	1308.3	1308.5	1308.8	1309.0	1309.3	1309.4	1309.8
175°	1321.9	1320.2	1318.5	1316.7	1315.0	1315.5	1316.0	1316.5	1317.0	1317.2	1317.6
177.5°	1325.4	1323.9	1322.4	1320.9	1319.4	1319.9	1320.4	1320.9	1321.4	1321.7	1322.1
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P997833

CATALOG NUMBER: SA2XXDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1921.3	1921.3	1921.3	1921.3
2.5°	1885.9	1885.9	1908.0	1931.6
5°	1844.5	1854.9	1890.3	1922.8
7.5°	1804.6	1822.4	1866.7	1908.0
10°	1755.9	1779.5	1834.2	1882.9
12.5°	1708.7	1730.8	1794.3	1848.9
15°	1642.2	1670.3	1738.2	1806.1
17.5°	1575.7	1603.8	1686.5	1766.2
20°	1497.5	1534.4	1627.4	1733.8
22.5°	1425.1	1470.9	1574.3	1659.9
25°	1345.4	1416.2	1512.2	1623.0
27.5°	1274.5	1345.4	1442.8	1555.1
30°	1194.7	1267.1	1367.5	1470.9
32.5°	1117.9	1184.4	1281.9	1408.9
35°	1038.2	1101.7	1196.2	1324.7
37.5°	965.8	1027.9	1131.2	1249.4
40°	894.9	959.9	1048.5	1166.7
42.5°	828.5	886.1	965.8	1084.0
45°	767.9	809.3	883.1	993.9
47.5°	704.4	741.4	809.3	920.0
50°	645.4	676.4	735.4	838.8
52.5°	587.8	614.3	669.0	751.7
55°	536.1	561.2	601.1	682.3
57.5°	482.9	502.1	540.5	605.5
60°	431.2	448.9	480.0	533.1
62.5°	379.5	394.3	423.8	466.7
65°	333.8	345.6	367.7	404.6
67.5°	289.5	296.8	314.6	344.1
70°	246.6	252.5	267.3	290.9
72.5°	200.8	206.8	223.0	239.2
75°	162.4	163.9	175.7	189.0
77.5°	127.0	125.5	134.4	144.7
80°	87.1	91.6	98.9	103.4
82.5°	59.1	60.5	63.5	66.5
85°	32.5	34.0	34.0	38.4
87.5°	13.3	14.8	14.8	16.2
90°	10.0	7.1	4.1	1.1
92.5°	30.5	28.6	26.6	24.6
95°	65.5	63.0	60.5	58.0
97.5°	103.8	101.6	99.3	97.1
100°	147.7	145.8	143.8	141.8
102.5°	193.1	191.6	190.1	188.6
105°	242.2	241.5	240.7	240.0
107.5°	294.3	293.3	292.3	291.3
110°	345.0	343.5	342.0	340.5



TEST NUMBER: P997833

CATALOG NUMBER: SA2XXDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	398.5	397.0	395.5	394.0
115°	451.0	449.5	448.0	446.5
117.5°	504.9	503.0	501.0	499.0
120°	557.4	555.4	553.4	551.4
122.5°	606.9	604.4	601.9	599.4
125°	656.4	654.1	651.9	649.7
127.5°	707.0	704.3	701.5	698.8
130°	754.3	751.0	747.8	744.6
132.5°	803.4	800.9	798.4	795.9
135°	848.7	846.0	843.2	840.5
137.5°	896.4	894.1	891.9	889.7
140°	939.9	937.6	935.4	933.2
142.5°	984.6	982.3	980.1	977.9
145°	1025.5	1023.8	1022.0	1020.3
147.5°	1064.9	1062.7	1060.4	1058.2
150°	1101.8	1100.3	1098.8	1097.3
152.5°	1136.4	1134.9	1133.4	1131.9
155°	1168.7	1168.0	1167.2	1166.5
157.5°	1198.1	1197.6	1197.1	1196.6
160°	1224.9	1224.4	1223.9	1223.4
162.5°	1248.0	1248.0	1248.0	1248.0
165°	1268.5	1268.7	1269.0	1269.2
167.5°	1285.9	1286.7	1287.4	1288.2
170°	1300.4	1301.2	1301.9	1302.7
172.5°	1310.5	1311.2	1312.0	1312.7
175°	1318.3	1319.0	1319.8	1320.5
177.5°	1322.8	1323.5	1324.3	1325.0
180°	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P997833

CATALOG NUMBER: SA2XXDIP-B1005D1080UB50-4F0-XX-W2A-A1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.02	18.88	18.96	19.83	21.05	15.51	16.37	16.45	17.32	18.54
	3H	18.83	19.60	19.78	20.56	21.80	16.86	17.63	17.81	18.58	19.83
	4H	19.00	19.73	19.96	20.69	21.94	17.32	18.05	18.28	19.01	20.26
	6H	19.05	19.71	20.02	20.68	21.95	17.63	18.30	18.60	19.26	20.53
	8H	19.03	19.66	20.00	20.64	21.91	17.71	18.35	18.69	19.33	20.60
	12H	18.99	19.59	19.97	20.57	21.86	17.75	18.36	18.74	19.33	20.63
4H	2H	18.06	18.79	19.03	19.75	21.00	15.96	16.69	16.93	17.65	18.90
	3H	19.04	19.65	20.02	20.64	21.91	17.42	18.02	18.40	19.01	20.28
	4H	19.32	19.87	20.30	20.85	22.15	17.96	18.51	18.94	19.49	20.78
	6H	19.45	19.92	20.45	20.93	22.22	18.34	18.81	19.33	19.81	21.11
	8H	19.45	19.89	20.45	20.89	22.20	18.45	18.89	19.44	19.89	21.19
	12H	19.41	19.81	20.43	20.83	22.14	18.50	18.90	19.52	19.92	21.23
8H	4H	19.33	19.77	20.33	20.77	22.08	18.10	18.54	19.10	19.54	20.85
	6H	19.51	19.87	20.53	20.91	22.22	18.53	18.90	19.55	19.94	21.24
	8H	19.54	19.86	20.57	20.89	22.21	18.68	19.00	19.71	20.03	21.36
	12H	19.52	19.80	20.56	20.83	22.20	18.78	19.06	19.81	20.08	21.45
12H	4H	19.29	19.68	20.30	20.70	22.01	18.07	18.47	19.09	19.49	20.80
	6H	19.49	19.81	20.52	20.84	22.16	18.53	18.85	19.56	19.88	21.21
	8H	19.52	19.80	20.55	20.82	22.19	18.69	18.97	19.72	19.99	21.36