

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998391

Luminaire Tested: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998391
REPORT IS A COMBINATION OF REPORTS P984131 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_5000K
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6194.0 lumens
Efficiency: N/A
Efficacy: 105.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998391

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P998391

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	94	90	87	83	85	82	78	76	65	63	61	50	49	48	36	36	35
2	86	79	73	68	77	72	67	63	57	54	51	44	42	40	32	31	30
3	79	70	63	57	71	63	57	53	51	47	43	40	37	34	29	27	26
4	72	62	54	49	65	56	50	45	45	41	37	35	32	30	26	24	22
5	66	55	47	42	60	50	44	39	41	36	32	32	29	26	24	22	20
6	61	50	42	36	55	45	38	34	37	32	28	29	25	23	22	19	18
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	17	16
8	52	41	33	28	47	37	31	26	30	25	22	24	21	18	18	16	14
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13
10	45	34	27	22	41	31	25	21	26	21	18	20	17	15	16	13	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14729	14729	14729	14729
5°	14764	15704	14821	12495
10°	14593	17145	14684	10302
15°	14239	18083	14438	8678
20°	14017	16980	14017	7542
25°	13570	14587	13632	6745
30°	12836	11467	13081	6109
35°	12185	7929	12388	5590
40°	11435	5986	11567	5176
45°	10514	4919	10684	4727
50°	9716	4319	9733	4329
55°	8804	3679	8863	3893
60°	7835	3074	7944	3398
65°	6968	2499	7092	2902
70°	6102	1962	6258	2340
75°	5119	1424	5320	1698
80°	4000	902	4279	1007
85°	2627	454	2825	336

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15226 cd/sqm

TEST NUMBER: P998391

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.6	1.4
10°-20°	258.0	4.2
20°-30°	374.4	6.0
30°-40°	394.7	6.4
40°-50°	349.2	5.6
50°-60°	278.9	4.5
60°-70°	189.4	3.1
70°-80°	96.9	1.6
80°-90°	25.4	0.4
90°-100°	46.6	0.8
100°-110°	173.5	2.8
110°-120°	460.2	7.4
120°-130°	763.3	12.3
130°-140°	810.8	13.1
140°-150°	753.6	12.2
150°-160°	605.8	9.8
160°-170°	390.4	6.3
170°-180°	134.4	2.2
0°-30°	721.0	11.6
0°-40°	1115.7	18.0
0°-60°	1743.8	28.2
0°-90°	2055.5	33.2
90°-120°	680.3	11.0
90°-150°	3007.9	48.6
90°-180°	4139.0	66.8
0°-180°	6194.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	930	930	930	930	930	
5°	931	1039	935	827	931	88
15°	875	1277	887	613	875	247
25°	786	1064	790	492	786	359
35°	642	579	652	408	642	401
45°	481	349	489	335	481	373
55°	330	245	333	260	330	295
65°	196	151	200	175	196	195
75°	92	74	95	89	92	98
85°	19	19	20	14	19	22
90°	1	28	1	28	1	5
95°	66	44	66	44	66	79
105°	310	78	310	78	310	332
115°	587	84	587	84	587	578
125°	830	873	830	873	830	741
135°	1028	1061	1028	1061	1028	794
145°	1192	1210	1192	1210	1192	746
155°	1313	1314	1313	1314	1313	605
165°	1383	1380	1383	1380	1383	391
175°	1415	1407	1415	1407	1415	135
180°	1412	1412	1412	1412	1412	

TEST NUMBER: P998391

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	935.5	937.7	941.2	942.0	949.1	954.8	961.3	961.3	963.4	962.7	957.0
5°	931.2	937.7	947.0	954.8	967.7	973.4	982.0	988.4	994.2	998.5	997.7
7.5°	924.1	935.5	949.1	964.1	981.3	991.3	1003.5	1014.9	1022.8	1029.9	1034.9
10°	911.9	931.2	949.8	969.9	992.0	1005.6	1019.9	1034.9	1047.1	1060.7	1073.6
12.5°	895.5	923.4	946.3	972.7	999.9	1014.9	1037.8	1049.2	1072.8	1107.2	1116.5
15°	874.7	912.6	934.1	967.7	1003.5	1015.6	1047.1	1065.7	1114.3	1135.8	1161.5
17.5°	855.4	897.6	926.2	964.8	999.9	1023.5	1054.3	1092.2	1132.9	1163.7	1192.3
20°	839.7	880.4	914.8	957.7	1002.0	1032.1	1064.3	1110.0	1154.4	1185.9	1208.0
22.5°	803.9	856.1	896.2	944.1	997.7	1039.2	1070.0	1120.1	1168.0	1187.3	1206.6
25°	786.0	831.1	877.6	931.9	994.9	1044.2	1070.7	1126.5	1168.7	1175.8	1180.1
27.5°	753.1	803.9	858.3	920.5	994.2	1035.7	1069.3	1120.1	1153.7	1148.7	1135.8
30°	712.4	774.6	834.7	901.9	984.2	1029.2	1060.7	1107.2	1124.3	1098.6	1075.7
32.5°	682.3	741.0	807.5	885.5	972.7	1015.6	1046.4	1082.9	1086.4	1039.9	1001.3
35°	641.6	706.6	781.7	864.0	953.4	992.0	1020.6	1042.8	1025.6	960.6	914.8
37.5°	605.1	669.5	749.6	833.2	926.9	964.8	987.7	991.3	949.1	891.9	824.7
40°	565.0	631.5	715.2	803.2	897.6	930.5	944.8	934.1	873.3	806.8	728.8
42.5°	525.0	590.8	680.9	771.0	860.4	888.3	894.0	864.7	790.3	712.4	622.3
45°	481.4	550.0	640.1	731.0	817.5	833.2	834.0	791.8	703.8	622.3	538.6
47.5°	445.6	509.2	598.6	689.5	762.4	773.2	768.9	720.2	624.4	532.8	459.9
50°	406.3	467.0	555.7	645.1	707.4	710.2	699.5	630.1	536.4	452.7	394.8
52.5°	364.1	425.6	507.1	592.9	648.7	644.4	623.7	549.3	461.3	391.9	347.6
55°	330.4	384.8	461.3	545.0	584.3	572.2	549.3	473.5	404.1	345.5	306.8
57.5°	293.2	341.2	416.3	489.2	512.1	500.7	477.8	407.0	342.6	298.3	272.5
60°	258.2	301.8	367.6	428.4	446.3	434.1	407.7	344.0	297.5	260.3	241.0
62.5°	226.0	263.9	319.0	374.8	381.9	369.8	346.9	295.4	255.3	226.0	211.7
65°	196.0	231.7	276.1	318.3	324.7	311.8	288.2	251.0	217.4	198.8	185.2
67.5°	166.6	195.3	234.6	265.4	268.9	256.8	237.5	207.4	186.7	166.6	156.6
70°	140.9	162.4	193.1	218.1	219.6	208.1	198.1	170.9	155.2	140.9	133.0
72.5°	115.9	130.9	154.5	173.1	173.8	166.6	157.4	140.2	126.6	116.6	108.7
75°	91.5	104.4	118.7	135.2	134.5	128.7	121.6	110.9	99.4	93.0	89.4
77.5°	70.1	78.0	89.4	100.1	100.1	97.3	93.0	85.1	78.0	71.5	67.9
80°	50.1	55.1	64.4	67.9	69.4	68.7	65.1	59.4	56.5	51.5	50.1
82.5°	32.2	35.8	40.1	43.6	45.8	44.3	43.6	40.8	36.5	35.0	33.6
85°	18.6	20.0	22.2	24.3	25.0	24.3	25.7	23.6	21.5	21.5	20.7
87.5°	7.9	8.6	10.0	10.0	10.7	10.7	10.0	10.7	10.7	10.0	9.3
90°	1.0	3.5	6.0	8.5	11.0	12.3	13.2	15.0	16.8	18.6	20.4
92.5°	25.5	24.6	23.7	22.8	21.9	21.5	21.8	22.5	23.2	23.8	24.5
95°	66.4	58.9	51.4	43.9	36.4	32.7	33.5	35.1	36.6	38.2	39.8
97.5°	119.5	100.9	82.3	63.7	45.1	35.8	37.6	41.2	44.9	48.5	52.1
100°	180.8	149.7	118.6	87.5	56.4	40.9	42.8	46.7	50.5	54.4	58.2
102.5°	248.2	247.8	247.3	246.9	246.4	246.2	225.5	184.2	142.9	101.6	60.3
105°	310.5	317.3	324.1	331.0	337.8	341.2	310.2	248.2	186.3	124.3	62.3
107.5°	383.1	388.8	394.4	400.1	405.8	408.6	370.4	293.9	217.4	140.9	64.4
110°	452.5	457.3	462.1	466.8	471.6	474.0	441.2	375.6	310.0	244.4	178.8

TEST NUMBER: P998391

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	517.9	522.0	526.1	530.2	534.3	536.3	534.4	530.5	526.6	522.8	518.9
115°	587.3	591.2	595.0	598.9	602.8	604.7	607.5	613.2	618.9	624.5	630.2
117.5°	647.6	652.1	656.7	661.2	665.7	668.0	669.9	673.8	677.7	681.5	685.4
120°	715.0	718.4	721.8	725.2	728.6	730.3	732.3	736.4	740.5	744.6	748.7
122.5°	772.2	775.8	779.5	783.1	786.8	788.6	790.9	795.4	799.9	804.5	809.0
125°	830.5	833.4	836.4	839.3	842.2	843.7	845.9	850.2	854.5	858.8	863.1
127.5°	883.6	886.8	890.0	893.1	896.3	897.9	899.6	903.0	906.4	909.8	913.2
130°	933.6	937.2	940.9	944.5	948.2	950.0	951.2	953.7	956.2	958.7	961.2
132.5°	984.7	987.7	990.6	993.6	996.5	998.0	999.2	1001.7	1004.2	1006.7	1009.2
135°	1027.6	1031.2	1034.8	1038.5	1042.1	1043.9	1044.9	1047.0	1049.0	1051.1	1053.1
137.5°	1072.5	1075.2	1078.0	1080.7	1083.4	1084.8	1085.9	1088.2	1090.5	1092.7	1095.0
140°	1116.5	1118.3	1120.1	1121.9	1123.7	1124.6	1125.9	1128.4	1130.9	1133.4	1135.9
142.5°	1153.2	1154.8	1156.4	1158.0	1159.6	1160.4	1161.9	1164.8	1167.8	1170.7	1173.7
145°	1192.1	1191.9	1191.6	1191.4	1191.1	1191.0	1192.9	1196.8	1200.7	1204.5	1208.4
147.5°	1225.8	1225.1	1224.4	1223.7	1223.0	1222.7	1224.6	1228.5	1232.4	1236.2	1240.1
150°	1258.4	1256.8	1255.2	1253.7	1252.1	1251.3	1253.1	1256.7	1260.4	1264.0	1267.6
152.5°	1286.0	1284.2	1282.4	1280.6	1278.8	1277.9	1279.6	1283.0	1286.4	1289.8	1293.2
155°	1312.6	1310.6	1308.5	1306.5	1304.4	1303.4	1304.8	1307.5	1310.2	1313.0	1315.7
157.5°	1334.0	1332.2	1330.4	1328.6	1326.8	1325.9	1326.9	1329.0	1331.0	1333.1	1335.1
160°	1352.4	1351.0	1349.7	1348.3	1347.0	1346.3	1347.0	1348.3	1349.7	1351.0	1352.4
162.5°	1368.8	1367.4	1366.0	1364.7	1363.3	1362.6	1363.2	1364.3	1365.4	1366.6	1367.7
165°	1383.1	1381.7	1380.3	1379.0	1377.6	1376.9	1377.2	1377.9	1378.6	1379.3	1380.0
167.5°	1394.3	1392.9	1391.6	1390.2	1388.9	1388.2	1388.5	1389.2	1389.9	1390.5	1391.2
170°	1403.5	1402.1	1400.8	1399.4	1398.1	1397.4	1397.6	1398.1	1398.5	1399.0	1399.4
172.5°	1409.6	1408.2	1406.9	1405.5	1404.2	1403.5	1403.7	1404.2	1404.6	1405.1	1405.5
175°	1414.7	1413.1	1411.5	1410.0	1408.4	1407.6	1407.8	1408.3	1408.7	1409.2	1409.6
177.5°	1416.8	1415.2	1413.6	1412.0	1410.4	1409.6	1409.7	1409.9	1410.2	1410.4	1410.6
180°	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7

TEST NUMBER: P998391

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	967.0	967.7	969.1	976.3	979.9	980.6	977.7	984.2	986.3	984.2	982.7
5°	1012.8	1017.1	1025.6	1034.9	1034.2	1034.9	1039.2	1043.5	1045.0	1039.2	1041.4
7.5°	1052.8	1061.4	1070.7	1085.0	1085.0	1092.2	1095.0	1098.6	1107.2	1102.9	1101.5
10°	1098.6	1110.0	1127.2	1150.1	1150.8	1158.0	1165.1	1176.6	1180.1	1177.3	1178.7
12.5°	1155.8	1178.0	1179.4	1204.4	1215.9	1217.3	1228.8	1226.6	1233.8	1233.8	1245.9
15°	1180.8	1215.2	1234.5	1258.8	1266.0	1257.4	1266.7	1276.7	1277.4	1277.4	1276.7
17.5°	1225.9	1239.5	1258.8	1271.7	1274.5	1274.5	1275.3	1279.5	1276.7	1271.0	1275.3
20°	1235.2	1240.9	1248.1	1246.6	1248.1	1240.9	1233.8	1226.6	1227.3	1223.8	1234.5
22.5°	1218.0	1216.6	1200.2	1189.4	1189.4	1175.1	1161.5	1155.1	1148.7	1150.8	1154.4
25°	1175.1	1153.0	1132.9	1117.2	1113.6	1090.7	1072.1	1066.4	1055.7	1064.3	1065.7
27.5°	1106.5	1081.4	1049.2	1035.7	1017.1	1007.8	994.9	977.7	955.5	968.4	966.3
30°	1032.8	995.6	969.1	936.2	906.9	904.8	880.4	851.8	840.4	840.4	846.8
32.5°	950.5	901.2	862.6	816.1	787.5	775.3	746.0	717.4	723.8	702.4	710.2
35°	854.7	789.6	741.0	695.9	674.5	660.2	622.3	606.5	589.4	579.3	597.9
37.5°	763.2	688.1	625.8	576.5	568.6	542.9	517.1	507.1	497.1	501.4	500.7
40°	651.6	585.1	529.3	490.6	477.1	464.9	447.7	435.6	429.1	432.7	433.4
42.5°	550.7	494.9	453.5	426.3	414.8	406.3	397.7	387.7	385.5	385.5	388.4
45°	472.8	427.0	399.1	376.9	370.5	364.1	357.6	353.3	351.9	349.0	351.2
47.5°	410.5	374.1	356.9	340.4	333.3	331.9	326.1	324.0	321.1	320.4	321.1
50°	358.3	335.4	319.7	310.4	305.4	303.3	300.4	296.1	294.7	298.3	296.8
52.5°	321.9	300.4	291.8	282.5	279.7	276.8	272.5	273.2	272.5	271.1	271.1
55°	285.4	271.8	263.2	256.1	255.3	252.5	248.9	247.5	246.8	245.3	247.5
57.5°	256.1	245.3	237.5	231.0	228.2	228.2	224.6	221.7	221.7	221.0	221.7
60°	226.7	216.0	211.0	204.6	202.4	201.7	199.5	198.1	196.0	196.0	196.0
62.5°	199.5	191.0	185.2	179.5	180.2	176.7	173.8	172.4	172.4	173.1	173.1
65°	173.8	168.1	160.9	155.9	154.5	153.8	152.3	151.6	149.5	150.9	150.9
67.5°	150.2	142.3	138.0	135.9	133.7	133.0	131.6	130.2	129.5	128.7	130.2
70°	126.6	120.2	116.6	115.2	113.0	112.3	111.6	109.4	110.1	110.9	111.6
72.5°	105.1	99.4	98.7	94.4	94.4	94.4	91.5	93.0	92.3	90.8	92.3
75°	83.0	80.1	78.7	76.5	77.2	76.5	75.8	73.7	73.7	74.4	75.1
77.5°	65.8	62.9	62.2	60.1	58.6	60.1	58.6	57.9	57.9	58.6	58.6
80°	48.6	47.2	45.1	45.1	45.1	44.3	44.3	44.3	43.6	42.9	43.6
82.5°	32.2	32.2	31.5	30.8	31.5	30.0	30.8	30.8	30.8	30.8	30.8
85°	20.7	20.0	20.0	19.3	19.3	19.3	20.0	18.6	18.6	19.3	19.3
87.5°	9.3	9.3	9.3	10.0	9.3	9.3	9.3	10.0	9.3	9.3	9.3
90°	21.5	22.7	23.8	24.9	25.5	25.7	26.2	26.7	27.1	27.6	27.1
92.5°	25.0	25.4	25.9	26.4	26.6	26.7	26.9	27.2	27.4	27.6	27.4
95°	40.9	42.1	43.2	44.3	44.9	44.8	44.6	44.3	44.1	43.9	44.1
97.5°	52.8	53.5	54.2	54.9	55.2	55.3	55.5	55.8	56.0	56.2	56.0
100°	60.0	61.8	63.7	65.5	66.4	66.6	67.1	67.5	68.0	68.4	68.0
102.5°	62.8	65.3	67.8	70.3	71.5	71.8	72.5	73.2	73.9	74.6	73.9
105°	64.8	67.3	69.8	72.3	73.5	74.0	74.9	75.8	76.7	77.6	76.7
107.5°	66.9	69.4	71.9	74.4	75.6	76.1	77.0	77.9	78.8	79.7	78.8
110°	156.1	133.4	110.7	88.0	76.6	77.1	78.0	78.9	79.8	80.7	79.8

TEST NUMBER: P998391

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	421.1	323.3	225.4	127.6	78.7	79.0	79.7	80.4	81.0	81.7	81.0
115°	525.1	420.0	314.9	209.8	157.3	149.1	132.8	116.5	100.1	83.8	100.1
117.5°	652.9	620.5	588.0	555.5	539.3	509.6	450.1	390.6	331.2	271.7	331.2
120°	751.4	754.2	756.9	759.6	761.0	745.7	715.0	684.4	653.7	623.1	653.7
122.5°	810.4	811.7	813.1	814.4	815.1	815.2	815.5	815.7	816.0	816.2	816.0
125°	864.7	866.3	867.9	869.5	870.3	870.6	871.3	872.0	872.7	873.4	872.7
127.5°	915.5	917.7	920.0	922.3	923.4	923.5	923.7	924.0	924.2	924.4	924.2
130°	963.7	966.2	968.7	971.2	972.4	972.3	972.1	971.8	971.6	971.4	971.6
132.5°	1011.2	1013.3	1015.3	1017.4	1018.4	1018.3	1018.1	1017.8	1017.6	1017.4	1017.6
135°	1055.4	1057.6	1059.9	1062.2	1063.3	1063.1	1062.6	1062.2	1061.7	1061.3	1061.7
137.5°	1097.3	1099.5	1101.8	1104.1	1105.2	1104.9	1104.2	1103.5	1102.9	1102.2	1102.9
140°	1137.9	1140.0	1142.0	1144.1	1145.1	1144.5	1143.4	1142.3	1141.1	1140.0	1141.1
142.5°	1175.5	1177.3	1179.1	1180.9	1181.8	1181.2	1180.1	1179.0	1177.8	1176.7	1177.8
145°	1210.0	1211.6	1213.1	1214.7	1215.5	1214.9	1213.8	1212.7	1211.5	1210.4	1211.5
147.5°	1241.2	1242.4	1243.5	1244.6	1245.2	1244.7	1243.8	1242.9	1242.0	1241.1	1242.0
150°	1269.0	1270.4	1271.7	1273.1	1273.8	1273.2	1272.1	1271.0	1269.8	1268.7	1269.8
152.5°	1294.6	1295.9	1297.3	1298.6	1299.3	1298.5	1296.9	1295.4	1293.8	1292.2	1293.8
155°	1317.1	1318.4	1319.8	1321.1	1321.8	1320.9	1319.1	1317.2	1315.4	1313.6	1315.4
157.5°	1336.7	1338.3	1339.8	1341.4	1342.2	1341.3	1339.5	1337.6	1335.8	1334.0	1335.8
160°	1353.8	1355.2	1356.5	1357.9	1358.6	1357.8	1356.2	1354.6	1353.0	1351.4	1353.0
162.5°	1369.3	1370.9	1372.5	1374.1	1374.9	1373.9	1371.8	1369.8	1367.7	1365.7	1367.7
165°	1381.6	1383.2	1384.8	1386.4	1387.2	1386.4	1384.8	1383.2	1381.6	1380.0	1381.6
167.5°	1392.8	1394.4	1396.0	1397.6	1398.4	1397.4	1395.3	1393.3	1391.2	1389.2	1391.2
170°	1401.0	1402.6	1404.2	1405.8	1406.6	1405.6	1403.5	1401.5	1399.4	1397.4	1399.4
172.5°	1407.1	1408.7	1410.3	1411.9	1412.7	1411.7	1409.6	1407.6	1405.5	1403.5	1405.5
175°	1411.2	1412.8	1414.4	1416.0	1416.8	1415.7	1413.4	1411.1	1408.9	1406.6	1408.9
177.5°	1412.2	1413.8	1415.4	1417.0	1417.8	1416.8	1414.7	1412.7	1410.6	1408.6	1410.6
180°	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7

TEST NUMBER: P998391

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	986.3	981.3	977.0	977.7	981.3	978.4	971.3	962.0	958.4	954.1	958.4
5°	1045.7	1041.4	1032.8	1033.5	1031.4	1028.5	1017.1	1002.8	1002.8	991.3	989.9
7.5°	1104.3	1097.9	1092.2	1090.7	1082.9	1077.1	1067.1	1047.1	1039.2	1025.6	1017.8
10°	1170.1	1165.1	1158.7	1150.8	1146.5	1136.5	1120.1	1090.7	1076.4	1057.8	1044.2
12.5°	1236.6	1235.9	1221.6	1205.9	1205.2	1189.4	1178.0	1138.6	1119.3	1094.3	1062.1
15°	1278.8	1275.3	1267.4	1259.5	1261.7	1244.5	1218.8	1172.3	1159.4	1129.3	1095.0
17.5°	1278.1	1278.1	1276.0	1274.5	1272.4	1267.4	1253.1	1222.3	1201.6	1163.7	1131.5
20°	1237.3	1246.6	1248.8	1248.1	1255.2	1258.8	1258.1	1238.8	1222.3	1188.7	1155.8
22.5°	1155.8	1177.3	1186.6	1192.3	1207.3	1215.2	1233.8	1226.6	1222.3	1197.3	1169.4
25°	1080.0	1087.2	1115.0	1116.5	1137.2	1156.5	1175.1	1187.3	1203.0	1193.7	1170.1
27.5°	982.0	998.5	1018.5	1033.5	1037.8	1077.1	1107.9	1130.8	1166.5	1169.4	1161.5
30°	871.2	879.0	911.9	931.9	954.8	983.4	1027.8	1067.1	1099.3	1128.6	1138.6
32.5°	736.0	768.2	787.5	811.8	831.8	882.6	937.0	987.7	1024.9	1074.3	1095.7
35°	612.2	637.3	670.2	680.2	716.7	759.6	830.4	895.5	952.0	1002.0	1045.7
37.5°	510.0	530.0	565.0	580.8	602.2	657.3	716.7	797.5	865.4	926.9	981.3
40°	439.9	454.9	481.4	486.4	504.2	554.3	602.2	678.0	768.2	851.1	910.5
42.5°	391.9	399.1	417.0	423.4	434.9	468.5	511.4	582.9	666.6	752.4	836.1
45°	357.6	362.6	373.4	379.1	393.4	408.4	443.4	500.7	566.5	653.0	743.1
47.5°	326.9	333.3	337.6	341.2	349.0	365.5	388.4	430.6	493.5	572.9	660.2
50°	301.1	303.3	311.1	311.8	316.8	327.6	349.0	374.8	424.8	489.2	573.6
52.5°	275.4	277.5	282.5	287.5	289.7	298.3	312.6	334.0	371.2	422.0	497.1
55°	249.6	252.5	257.5	261.1	263.2	270.4	278.9	299.7	329.0	364.8	426.3
57.5°	223.9	230.3	231.7	233.9	237.5	245.3	253.2	265.4	288.2	321.1	366.2
60°	199.5	201.7	206.7	208.8	212.4	216.7	226.7	236.0	252.5	278.2	319.0
62.5°	174.5	179.5	181.7	183.8	186.7	191.7	198.1	208.1	222.4	243.2	275.4
65°	153.1	153.8	158.1	160.9	163.8	167.4	173.8	183.1	191.7	211.0	234.6
67.5°	132.3	133.7	135.2	138.0	141.6	145.2	150.9	155.9	166.6	179.5	198.1
70°	112.3	112.3	115.9	118.0	117.3	121.6	125.9	131.6	139.5	151.6	166.6
72.5°	94.4	93.7	96.6	97.3	98.7	101.6	104.4	110.1	114.4	123.7	135.2
75°	75.1	76.5	78.0	78.0	80.1	82.3	85.1	88.0	93.0	98.7	107.3
77.5°	59.4	59.4	60.8	61.5	63.7	62.9	65.8	68.7	72.2	77.2	83.7
80°	43.6	45.1	45.1	45.1	45.8	46.5	49.4	51.5	53.6	57.2	60.1
82.5°	30.8	30.8	32.2	32.2	32.2	33.6	33.6	34.3	35.8	37.9	40.1
85°	19.3	19.3	19.3	20.0	19.3	20.0	21.5	20.7	21.5	22.9	22.9
87.5°	9.3	9.3	9.3	9.3	9.3	10.0	9.3	10.0	10.7	10.7	10.7
90°	26.7	26.2	25.7	25.5	24.9	23.8	22.7	21.5	20.4	18.6	16.8
92.5°	27.2	26.9	26.7	26.6	26.4	25.9	25.4	25.0	24.5	23.8	23.2
95°	44.3	44.6	44.8	44.9	44.3	43.2	42.1	40.9	39.8	38.2	36.6
97.5°	55.8	55.5	55.3	55.2	54.9	54.2	53.5	52.8	52.1	48.5	44.9
100°	67.5	67.1	66.6	66.4	65.5	63.7	61.8	60.0	58.2	54.4	50.5
102.5°	73.2	72.5	71.8	71.5	70.3	67.8	65.3	62.8	60.3	101.6	142.9
105°	75.8	74.9	74.0	73.5	72.3	69.8	67.3	64.8	62.3	124.3	186.3
107.5°	77.9	77.0	76.1	75.6	74.4	71.9	69.4	66.9	64.4	140.9	217.4
110°	78.9	78.0	77.1	76.6	88.0	110.7	133.4	156.1	178.8	244.4	310.0

TEST NUMBER: P998391

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	80.4	79.7	79.0	78.7	127.6	225.4	323.3	421.1	518.9	522.8	526.6
115°	116.5	132.8	149.1	157.3	209.8	314.9	420.0	525.1	630.2	624.5	618.9
117.5°	390.6	450.1	509.6	539.3	555.5	588.0	620.5	652.9	685.4	681.5	677.7
120°	684.4	715.0	745.7	761.0	759.6	756.9	754.2	751.4	748.7	744.6	740.5
122.5°	815.7	815.5	815.2	815.1	814.4	813.1	811.7	810.4	809.0	804.5	799.9
125°	872.0	871.3	870.6	870.3	869.5	867.9	866.3	864.7	863.1	858.8	854.5
127.5°	924.0	923.7	923.5	923.4	922.3	920.0	917.7	915.5	913.2	909.8	906.4
130°	971.8	972.1	972.3	972.4	971.2	968.7	966.2	963.7	961.2	958.7	956.2
132.5°	1017.8	1018.1	1018.3	1018.4	1017.4	1015.3	1013.3	1011.2	1009.2	1006.7	1004.2
135°	1062.2	1062.6	1063.1	1063.3	1062.2	1059.9	1057.6	1055.4	1053.1	1051.1	1049.0
137.5°	1103.5	1104.2	1104.9	1105.2	1104.1	1101.8	1099.5	1097.3	1095.0	1092.7	1090.5
140°	1142.3	1143.4	1144.5	1145.1	1144.1	1142.0	1140.0	1137.9	1135.9	1133.4	1130.9
142.5°	1179.0	1180.1	1181.2	1181.8	1180.9	1179.1	1177.3	1175.5	1173.7	1170.7	1167.8
145°	1212.7	1213.8	1214.9	1215.5	1214.7	1213.1	1211.6	1210.0	1208.4	1204.5	1200.7
147.5°	1242.9	1243.8	1244.7	1245.2	1244.6	1243.5	1242.4	1241.2	1240.1	1236.2	1232.4
150°	1271.0	1272.1	1273.2	1273.8	1273.1	1271.7	1270.4	1269.0	1267.6	1264.0	1260.4
152.5°	1295.4	1296.9	1298.5	1299.3	1298.6	1297.3	1295.9	1294.6	1293.2	1289.8	1286.4
155°	1317.2	1319.1	1320.9	1321.8	1321.1	1319.8	1318.4	1317.1	1315.7	1313.0	1310.2
157.5°	1337.6	1339.5	1341.3	1342.2	1341.4	1339.8	1338.3	1336.7	1335.1	1333.1	1331.0
160°	1354.6	1356.2	1357.8	1358.6	1357.9	1356.5	1355.2	1353.8	1352.4	1351.0	1349.7
162.5°	1369.8	1371.8	1373.9	1374.9	1374.1	1372.5	1370.9	1369.3	1367.7	1366.6	1365.4
165°	1383.2	1384.8	1386.4	1387.2	1386.4	1384.8	1383.2	1381.6	1380.0	1379.3	1378.6
167.5°	1393.3	1395.3	1397.4	1398.4	1397.6	1396.0	1394.4	1392.8	1391.2	1390.5	1389.9
170°	1401.5	1403.5	1405.6	1406.6	1405.8	1404.2	1402.6	1401.0	1399.4	1399.0	1398.5
172.5°	1407.6	1409.6	1411.7	1412.7	1411.9	1410.3	1408.7	1407.1	1405.5	1405.1	1404.6
175°	1411.1	1413.4	1415.7	1416.8	1416.0	1414.4	1412.8	1411.2	1409.6	1409.2	1408.7
177.5°	1412.7	1414.7	1416.8	1417.8	1417.0	1415.4	1413.8	1412.2	1410.6	1410.4	1410.2
180°	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7

TEST NUMBER: P998391

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	954.8	951.3	949.1	950.5	946.3	935.5	935.5	939.1	934.8	930.5	924.1
5°	981.3	974.1	969.9	969.1	959.1	942.0	938.4	934.8	925.5	915.5	904.8
7.5°	1007.0	994.2	987.0	982.0	967.7	945.5	936.2	928.4	913.3	898.3	884.7
10°	1028.5	1009.9	1001.3	993.5	974.9	947.0	931.9	917.6	898.3	879.0	861.9
12.5°	1045.7	1024.2	1013.5	1002.0	979.2	942.7	924.1	901.2	881.9	856.1	839.0
15°	1074.3	1029.9	1019.9	1009.2	985.6	935.5	912.6	886.9	860.4	826.1	807.5
17.5°	1097.2	1037.8	1037.1	1014.2	983.4	932.7	897.6	864.0	835.4	801.1	771.7
20°	1110.8	1050.0	1038.5	1014.9	976.3	913.3	876.9	839.7	808.9	767.4	738.1
22.5°	1122.2	1067.1	1037.1	1008.5	961.3	906.9	853.3	818.2	776.0	731.0	703.1
25°	1126.5	1070.7	1039.2	1006.3	950.5	888.3	827.5	789.6	742.4	701.6	663.7
27.5°	1127.2	1070.0	1031.4	997.0	935.5	864.0	801.8	761.7	709.5	662.3	624.4
30°	1120.1	1062.1	1027.1	989.9	921.2	841.8	770.3	726.0	670.2	623.0	583.6
32.5°	1098.6	1046.4	1017.8	977.0	902.6	811.1	740.3	690.9	632.3	585.8	547.9
35°	1062.8	1027.1	995.6	957.7	878.3	782.5	710.2	652.3	592.9	548.6	512.8
37.5°	1018.5	999.2	969.9	932.7	850.4	756.7	676.6	612.2	552.9	510.0	474.9
40°	958.4	963.4	934.8	901.2	817.5	721.7	633.0	571.5	515.7	475.6	441.3
42.5°	893.3	914.1	897.6	865.4	781.0	683.0	600.8	532.8	478.5	437.0	408.4
45°	823.2	859.0	849.0	825.4	743.1	642.3	555.0	489.2	441.3	401.2	376.2
47.5°	746.7	797.5	797.5	780.3	700.9	601.5	515.7	448.4	401.2	372.6	348.3
50°	668.7	726.0	735.3	723.8	653.7	555.0	467.8	407.0	366.2	338.3	320.4
52.5°	587.2	653.7	670.9	665.2	603.7	510.7	428.4	369.1	331.9	307.5	291.8
55°	509.2	586.5	605.1	607.2	550.0	462.0	384.8	332.6	296.8	280.4	266.8
57.5°	435.6	510.0	530.7	534.3	495.7	417.7	344.0	298.3	266.1	252.5	241.7
60°	372.6	434.9	462.0	469.9	436.3	366.2	306.1	261.8	237.5	224.6	214.6
62.5°	321.1	371.2	399.8	402.0	386.9	321.1	266.8	229.6	208.8	197.4	192.4
65°	271.1	316.1	333.3	341.9	329.7	278.2	230.3	199.5	183.1	173.1	168.1
67.5°	231.0	259.6	273.9	285.4	273.2	234.6	196.0	170.9	158.8	148.8	145.9
70°	189.5	213.1	223.9	235.3	224.6	195.3	167.4	144.5	133.7	125.9	122.3
72.5°	151.6	170.2	180.2	187.4	181.0	156.6	133.7	118.0	110.1	104.4	102.3
75°	120.2	133.0	138.8	143.8	140.9	122.3	108.0	95.1	88.0	83.0	81.5
77.5°	91.5	100.8	107.3	108.7	105.1	93.0	80.8	73.0	67.2	64.4	62.9
80°	65.1	70.8	74.4	76.5	73.0	67.9	59.4	53.6	48.6	45.1	44.3
82.5°	43.6	46.5	49.4	48.6	47.2	42.9	37.9	35.0	32.9	30.0	30.0
85°	25.0	25.7	27.2	27.9	27.2	24.3	21.5	20.0	18.6	16.5	16.5
87.5°	10.7	11.4	11.4	12.2	10.7	10.7	9.3	7.9	7.9	7.2	6.4
90°	15.0	13.2	12.3	11.0	8.5	6.0	3.5	1.0	3.5	6.0	8.5
92.5°	22.5	21.8	21.5	21.9	22.8	23.7	24.6	25.5	24.6	23.7	22.8
95°	35.1	33.5	32.7	36.4	43.9	51.4	58.9	66.4	58.9	51.4	43.9
97.5°	41.2	37.6	35.8	45.1	63.7	82.3	100.9	119.5	100.9	82.3	63.7
100°	46.7	42.8	40.9	56.4	87.5	118.6	149.7	180.8	149.7	118.6	87.5
102.5°	184.2	225.5	246.2	246.4	246.9	247.3	247.8	248.2	247.8	247.3	246.9
105°	248.2	310.2	341.2	337.8	331.0	324.1	317.3	310.5	317.3	324.1	331.0
107.5°	293.9	370.4	408.6	405.8	400.1	394.4	388.8	383.1	388.8	394.4	400.1
110°	375.6	441.2	474.0	471.6	466.8	462.1	457.3	452.5	457.3	462.1	466.8

TEST NUMBER: P998391

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	530.5	534.4	536.3	534.3	530.2	526.1	522.0	517.9	522.0	526.1	530.2
115°	613.2	607.5	604.7	602.8	598.9	595.0	591.2	587.3	591.2	595.0	598.9
117.5°	673.8	669.9	668.0	665.7	661.2	656.7	652.1	647.6	652.1	656.7	661.2
120°	736.4	732.3	730.3	728.6	725.2	721.8	718.4	715.0	718.4	721.8	725.2
122.5°	795.4	790.9	788.6	786.8	783.1	779.5	775.8	772.2	775.8	779.5	783.1
125°	850.2	845.9	843.7	842.2	839.3	836.4	833.4	830.5	833.4	836.4	839.3
127.5°	903.0	899.6	897.9	896.3	893.1	890.0	886.8	883.6	886.8	890.0	893.1
130°	953.7	951.2	950.0	948.2	944.5	940.9	937.2	933.6	937.2	940.9	944.5
132.5°	1001.7	999.2	998.0	996.5	993.6	990.6	987.7	984.7	987.7	990.6	993.6
135°	1047.0	1044.9	1043.9	1042.1	1038.5	1034.8	1031.2	1027.6	1031.2	1034.8	1038.5
137.5°	1088.2	1085.9	1084.8	1083.4	1080.7	1078.0	1075.2	1072.5	1075.2	1078.0	1080.7
140°	1128.4	1125.9	1124.6	1123.7	1121.9	1120.1	1118.3	1116.5	1118.3	1120.1	1121.9
142.5°	1164.8	1161.9	1160.4	1159.6	1158.0	1156.4	1154.8	1153.2	1154.8	1156.4	1158.0
145°	1196.8	1192.9	1191.0	1191.1	1191.4	1191.6	1191.9	1192.1	1191.9	1191.6	1191.4
147.5°	1228.5	1224.6	1222.7	1223.0	1223.7	1224.4	1225.1	1225.8	1225.1	1224.4	1223.7
150°	1256.7	1253.1	1251.3	1252.1	1253.7	1255.2	1256.8	1258.4	1256.8	1255.2	1253.7
152.5°	1283.0	1279.6	1277.9	1278.8	1280.6	1282.4	1284.2	1286.0	1284.2	1282.4	1280.6
155°	1307.5	1304.8	1303.4	1304.4	1306.5	1308.5	1310.6	1312.6	1310.6	1308.5	1306.5
157.5°	1329.0	1326.9	1325.9	1326.8	1328.6	1330.4	1332.2	1334.0	1332.2	1330.4	1328.6
160°	1348.3	1347.0	1346.3	1347.0	1348.3	1349.7	1351.0	1352.4	1351.0	1349.7	1348.3
162.5°	1364.3	1363.2	1362.6	1363.3	1364.7	1366.0	1367.4	1368.8	1367.4	1366.0	1364.7
165°	1377.9	1377.2	1376.9	1377.6	1379.0	1380.3	1381.7	1383.1	1381.7	1380.3	1379.0
167.5°	1389.2	1388.5	1388.2	1388.9	1390.2	1391.6	1392.9	1394.3	1392.9	1391.6	1390.2
170°	1398.1	1397.6	1397.4	1398.1	1399.4	1400.8	1402.1	1403.5	1402.1	1400.8	1399.4
172.5°	1404.2	1403.7	1403.5	1404.2	1405.5	1406.9	1408.2	1409.6	1408.2	1406.9	1405.5
175°	1408.3	1407.8	1407.6	1408.4	1410.0	1411.5	1413.1	1414.7	1413.1	1411.5	1410.0
177.5°	1409.9	1409.7	1409.6	1410.4	1412.0	1413.6	1415.2	1416.8	1415.2	1413.6	1412.0
180°	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7

TEST NUMBER: P998391

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	920.5	924.1	923.4	916.2	908.3	901.9	889.7	891.2	886.9	887.6	891.9
5°	897.6	897.6	894.8	884.7	871.9	864.7	851.1	847.5	839.0	838.3	837.5
7.5°	873.3	869.7	866.1	851.8	836.1	824.7	806.1	801.8	793.2	787.5	784.6
10°	844.7	839.7	832.5	816.1	796.8	782.5	763.2	757.4	741.0	733.8	729.5
12.5°	813.2	810.4	798.9	785.3	753.9	738.1	710.2	715.9	699.5	685.2	683.0
15°	781.7	771.0	764.6	742.4	704.5	697.3	675.2	663.7	648.7	637.3	637.3
17.5°	751.0	734.5	720.2	696.6	668.7	648.7	632.3	626.5	607.9	596.5	594.4
20°	710.2	691.6	688.1	654.4	635.1	613.0	597.2	582.9	569.3	564.3	560.7
22.5°	671.6	650.1	644.4	615.8	596.5	574.3	558.6	548.6	538.6	535.0	528.6
25°	630.1	617.2	608.7	577.9	556.4	535.7	525.0	517.8	508.5	507.8	503.5
27.5°	590.1	577.9	569.3	540.0	524.3	505.0	496.4	488.5	483.5	481.4	479.2
30°	555.7	542.1	532.1	510.7	491.4	475.6	468.5	463.5	460.6	457.0	456.3
32.5°	517.8	510.0	496.4	479.9	464.9	449.9	445.6	442.0	437.7	436.3	435.6
35°	485.6	474.9	466.3	447.7	441.3	428.4	423.4	420.6	414.8	413.4	412.0
37.5°	454.2	444.2	434.9	423.4	411.3	404.1	401.2	397.0	394.1	394.8	393.4
40°	422.7	414.8	407.7	395.5	388.4	384.8	379.1	374.8	373.4	374.1	373.4
42.5°	391.9	384.8	380.5	371.2	364.1	360.5	356.9	352.6	354.8	354.8	356.9
45°	364.1	357.6	354.8	347.6	343.3	337.6	334.0	333.3	336.2	335.4	335.4
47.5°	335.4	333.3	329.7	323.3	317.6	314.0	313.3	313.3	316.1	317.6	316.8
50°	313.3	309.0	304.7	299.7	295.4	294.0	291.8	293.2	296.1	296.1	297.5
52.5°	285.4	282.5	281.1	276.8	273.9	273.9	273.9	274.6	276.8	278.9	278.2
55°	261.1	258.9	257.5	255.3	251.8	252.5	251.8	253.2	255.3	257.5	258.9
57.5°	235.3	234.6	233.2	229.6	229.6	228.9	231.0	231.7	235.3	236.7	238.9
60°	212.4	210.3	210.3	207.4	207.4	207.4	209.6	211.7	214.6	215.3	216.7
62.5°	188.1	188.1	187.4	185.2	185.2	187.4	188.1	191.0	192.4	192.4	194.5
65°	165.2	164.5	163.8	164.5	165.2	165.2	167.4	168.8	170.2	170.9	171.7
67.5°	142.3	141.6	143.0	142.3	143.8	146.6	145.9	148.1	150.2	150.2	150.9
70°	120.9	122.3	121.6	123.0	122.3	123.7	125.9	126.6	126.6	127.3	129.5
72.5°	100.8	100.8	100.8	100.1	100.8	102.3	103.7	104.4	105.9	106.6	108.7
75°	81.5	81.5	80.1	81.5	81.5	83.0	84.4	84.4	84.4	85.8	88.0
77.5°	61.5	62.2	61.5	62.9	62.9	63.7	65.1	64.4	65.8	66.5	67.2
80°	45.1	44.3	44.3	44.3	45.1	45.1	46.5	47.2	47.2	49.4	47.9
82.5°	28.6	29.3	28.6	29.3	29.3	30.0	29.3	30.0	30.8	32.2	31.5
85°	16.5	15.7	15.7	16.5	15.7	15.7	16.5	15.7	16.5	15.7	16.5
87.5°	6.4	5.7	5.7	5.7	5.7	5.0	5.0	4.3	4.3	4.3	3.6
90°	11.0	12.3	13.2	15.0	16.8	18.6	20.4	21.5	22.7	23.8	24.9
92.5°	21.9	21.5	21.8	22.5	23.2	23.8	24.5	25.0	25.4	25.9	26.4
95°	36.4	32.7	33.5	35.1	36.6	38.2	39.8	40.9	42.1	43.2	44.3
97.5°	45.1	35.8	37.6	41.2	44.9	48.5	52.1	52.8	53.5	54.2	54.9
100°	56.4	40.9	42.8	46.7	50.5	54.4	58.2	60.0	61.8	63.7	65.5
102.5°	246.4	246.2	225.5	184.2	142.9	101.6	60.3	62.8	65.3	67.8	70.3
105°	337.8	341.2	310.2	248.2	186.3	124.3	62.3	64.8	67.3	69.8	72.3
107.5°	405.8	408.6	370.4	293.9	217.4	140.9	64.4	66.9	69.4	71.9	74.4
110°	471.6	474.0	441.2	375.6	310.0	244.4	178.8	156.1	133.4	110.7	88.0

TEST NUMBER: P998391

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	534.3	536.3	534.4	530.5	526.6	522.8	518.9	421.1	323.3	225.4	127.6
115°	602.8	604.7	607.5	613.2	618.9	624.5	630.2	525.1	420.0	314.9	209.8
117.5°	665.7	668.0	669.9	673.8	677.7	681.5	685.4	652.9	620.5	588.0	555.5
120°	728.6	730.3	732.3	736.4	740.5	744.6	748.7	751.4	754.2	756.9	759.6
122.5°	786.8	788.6	790.9	795.4	799.9	804.5	809.0	810.4	811.7	813.1	814.4
125°	842.2	843.7	845.9	850.2	854.5	858.8	863.1	864.7	866.3	867.9	869.5
127.5°	896.3	897.9	899.6	903.0	906.4	909.8	913.2	915.5	917.7	920.0	922.3
130°	948.2	950.0	951.2	953.7	956.2	958.7	961.2	963.7	966.2	968.7	971.2
132.5°	996.5	998.0	999.2	1001.7	1004.2	1006.7	1009.2	1011.2	1013.3	1015.3	1017.4
135°	1042.1	1043.9	1044.9	1047.0	1049.0	1051.1	1053.1	1055.4	1057.6	1059.9	1062.2
137.5°	1083.4	1084.8	1085.9	1088.2	1090.5	1092.7	1095.0	1097.3	1099.5	1101.8	1104.1
140°	1123.7	1124.6	1125.9	1128.4	1130.9	1133.4	1135.9	1137.9	1140.0	1142.0	1144.1
142.5°	1159.6	1160.4	1161.9	1164.8	1167.8	1170.7	1173.7	1175.5	1177.3	1179.1	1180.9
145°	1191.1	1191.0	1192.9	1196.8	1200.7	1204.5	1208.4	1210.0	1211.6	1213.1	1214.7
147.5°	1223.0	1222.7	1224.6	1228.5	1232.4	1236.2	1240.1	1241.2	1242.4	1243.5	1244.6
150°	1252.1	1251.3	1253.1	1256.7	1260.4	1264.0	1267.6	1269.0	1270.4	1271.7	1273.1
152.5°	1278.8	1277.9	1279.6	1283.0	1286.4	1289.8	1293.2	1294.6	1295.9	1297.3	1298.6
155°	1304.4	1303.4	1304.8	1307.5	1310.2	1313.0	1315.7	1317.1	1318.4	1319.8	1321.1
157.5°	1326.8	1325.9	1326.9	1329.0	1331.0	1333.1	1335.1	1336.7	1338.3	1339.8	1341.4
160°	1347.0	1346.3	1347.0	1348.3	1349.7	1351.0	1352.4	1353.8	1355.2	1356.5	1357.9
162.5°	1363.3	1362.6	1363.2	1364.3	1365.4	1366.6	1367.7	1369.3	1370.9	1372.5	1374.1
165°	1377.6	1376.9	1377.2	1377.9	1378.6	1379.3	1380.0	1381.6	1383.2	1384.8	1386.4
167.5°	1388.9	1388.2	1388.5	1389.2	1389.9	1390.5	1391.2	1392.8	1394.4	1396.0	1397.6
170°	1398.1	1397.4	1397.6	1398.1	1398.5	1399.0	1399.4	1401.0	1402.6	1404.2	1405.8
172.5°	1404.2	1403.5	1403.7	1404.2	1404.6	1405.1	1405.5	1407.1	1408.7	1410.3	1411.9
175°	1408.4	1407.6	1407.8	1408.3	1408.7	1409.2	1409.6	1411.2	1412.8	1414.4	1416.0
177.5°	1410.4	1409.6	1409.7	1409.9	1410.2	1410.4	1410.6	1412.2	1413.8	1415.4	1417.0
180°	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7

TEST NUMBER: P998391

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	886.9	889.0	884.0	882.6	884.0	879.0	880.4	881.9	881.9	884.0	885.5
5°	835.4	832.5	827.5	826.1	824.7	826.8	825.4	827.5	828.2	833.2	834.0
7.5°	784.6	780.3	776.0	771.7	770.3	766.7	770.3	770.3	775.3	773.9	777.5
10°	724.5	723.8	718.1	715.9	713.1	707.4	715.2	713.1	716.7	723.1	724.5
12.5°	680.2	672.3	675.9	665.9	669.5	663.7	664.4	664.4	670.2	670.9	669.5
15°	638.0	631.5	622.3	618.0	615.8	613.0	622.3	623.0	618.7	628.7	625.1
17.5°	595.1	595.1	586.5	584.3	578.6	581.5	580.1	580.8	579.3	586.5	590.1
20°	557.9	554.3	551.4	552.2	545.0	543.6	542.1	543.6	548.6	553.6	555.0
22.5°	527.8	525.7	518.5	520.0	514.3	516.4	515.0	518.5	519.3	519.3	524.3
25°	499.2	496.4	497.1	494.2	492.1	492.1	489.9	492.1	494.9	496.4	497.1
27.5°	477.8	475.6	472.1	469.9	471.3	467.8	470.6	472.8	472.8	471.3	472.8
30°	452.0	453.5	453.5	446.3	449.2	447.7	449.9	451.3	451.3	452.0	450.6
32.5°	434.9	430.6	429.9	429.1	429.1	426.3	426.3	428.4	429.1	429.9	432.0
35°	412.0	412.0	408.4	410.5	407.7	408.4	407.7	408.4	409.8	407.7	409.8
37.5°	391.2	391.9	390.5	391.9	392.7	391.2	389.8	392.7	391.2	391.2	389.8
40°	373.4	372.6	373.4	373.4	373.4	374.1	372.6	372.6	372.6	371.2	369.8
42.5°	358.3	354.0	355.5	356.2	354.0	354.0	354.8	354.0	356.2	351.9	351.9
45°	336.9	335.4	336.2	336.2	337.6	335.4	336.9	337.6	335.4	334.7	333.3
47.5°	317.6	319.0	317.6	319.0	319.0	320.4	317.6	318.3	319.0	316.1	314.0
50°	298.3	298.3	300.4	299.7	300.4	299.0	299.0	298.3	299.0	297.5	295.4
52.5°	280.4	278.2	281.8	281.1	280.4	279.7	278.9	279.7	278.2	276.8	276.8
55°	258.2	258.2	260.3	261.1	261.1	259.6	258.2	258.9	258.2	257.5	256.8
57.5°	240.3	237.5	238.9	239.6	239.6	237.5	238.9	237.5	237.5	238.2	236.0
60°	217.4	217.4	216.0	218.1	218.1	216.7	216.7	217.4	216.0	215.3	214.6
62.5°	193.1	193.8	196.0	196.7	197.4	196.0	194.5	195.3	195.3	193.1	193.8
65°	172.4	173.8	176.7	175.9	174.5	175.2	173.8	174.5	172.4	173.1	170.9
67.5°	152.3	151.6	152.3	152.3	153.8	153.1	151.6	151.6	150.9	153.1	150.9
70°	130.9	130.9	130.9	130.9	131.6	132.3	130.9	129.5	130.2	128.7	128.0
72.5°	108.7	109.4	108.7	110.1	108.0	109.4	109.4	108.7	108.0	108.0	108.0
75°	88.0	89.4	87.3	88.0	87.3	88.7	88.0	88.0	86.5	85.8	86.5
77.5°	67.2	67.9	66.5	67.2	66.5	67.2	67.2	66.5	66.5	66.5	66.5
80°	47.9	48.6	47.9	47.2	46.5	47.9	46.5	47.2	47.9	47.2	48.6
82.5°	30.8	30.8	30.0	30.8	29.3	29.3	30.0	30.0	29.3	30.8	29.3
85°	15.0	15.0	16.5	15.0	14.3	14.3	14.3	15.0	14.3	15.7	15.0
87.5°	3.6	2.9	3.6	3.6	2.9	2.9	3.6	2.9	3.6	4.3	2.9
90°	25.5	25.7	26.2	26.7	27.1	27.6	27.1	26.7	26.2	25.7	25.5
92.5°	26.6	26.7	26.9	27.2	27.4	27.6	27.4	27.2	26.9	26.7	26.6
95°	44.9	44.8	44.6	44.3	44.1	43.9	44.1	44.3	44.6	44.8	44.9
97.5°	55.2	55.3	55.5	55.8	56.0	56.2	56.0	55.8	55.5	55.3	55.2
100°	66.4	66.6	67.1	67.5	68.0	68.4	68.0	67.5	67.1	66.6	66.4
102.5°	71.5	71.8	72.5	73.2	73.9	74.6	73.9	73.2	72.5	71.8	71.5
105°	73.5	74.0	74.9	75.8	76.7	77.6	76.7	75.8	74.9	74.0	73.5
107.5°	75.6	76.1	77.0	77.9	78.8	79.7	78.8	77.9	77.0	76.1	75.6
110°	76.6	77.1	78.0	78.9	79.8	80.7	79.8	78.9	78.0	77.1	76.6

TEST NUMBER: P998391

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	78.7	79.0	79.7	80.4	81.0	81.7	81.0	80.4	79.7	79.0	78.7
115°	157.3	149.1	132.8	116.5	100.1	83.8	100.1	116.5	132.8	149.1	157.3
117.5°	539.3	509.6	450.1	390.6	331.2	271.7	331.2	390.6	450.1	509.6	539.3
120°	761.0	745.7	715.0	684.4	653.7	623.1	653.7	684.4	715.0	745.7	761.0
122.5°	815.1	815.2	815.5	815.7	816.0	816.2	816.0	815.7	815.5	815.2	815.1
125°	870.3	870.6	871.3	872.0	872.7	873.4	872.7	872.0	871.3	870.6	870.3
127.5°	923.4	923.5	923.7	924.0	924.2	924.4	924.2	924.0	923.7	923.5	923.4
130°	972.4	972.3	972.1	971.8	971.6	971.4	971.6	971.8	972.1	972.3	972.4
132.5°	1018.4	1018.3	1018.1	1017.8	1017.6	1017.4	1017.6	1017.8	1018.1	1018.3	1018.4
135°	1063.3	1063.1	1062.6	1062.2	1061.7	1061.3	1061.7	1062.2	1062.6	1063.1	1063.3
137.5°	1105.2	1104.9	1104.2	1103.5	1102.9	1102.2	1102.9	1103.5	1104.2	1104.9	1105.2
140°	1145.1	1144.5	1143.4	1142.3	1141.1	1140.0	1141.1	1142.3	1143.4	1144.5	1145.1
142.5°	1181.8	1181.2	1180.1	1179.0	1177.8	1176.7	1177.8	1179.0	1180.1	1181.2	1181.8
145°	1215.5	1214.9	1213.8	1212.7	1211.5	1210.4	1211.5	1212.7	1213.8	1214.9	1215.5
147.5°	1245.2	1244.7	1243.8	1242.9	1242.0	1241.1	1242.0	1242.9	1243.8	1244.7	1245.2
150°	1273.8	1273.2	1272.1	1271.0	1269.8	1268.7	1269.8	1271.0	1272.1	1273.2	1273.8
152.5°	1299.3	1298.5	1296.9	1295.4	1293.8	1292.2	1293.8	1295.4	1296.9	1298.5	1299.3
155°	1321.8	1320.9	1319.1	1317.2	1315.4	1313.6	1315.4	1317.2	1319.1	1320.9	1321.8
157.5°	1342.2	1341.3	1339.5	1337.6	1335.8	1334.0	1335.8	1337.6	1339.5	1341.3	1342.2
160°	1358.6	1357.8	1356.2	1354.6	1353.0	1351.4	1353.0	1354.6	1356.2	1357.8	1358.6
162.5°	1374.9	1373.9	1371.8	1369.8	1367.7	1365.7	1367.7	1369.8	1371.8	1373.9	1374.9
165°	1387.2	1386.4	1384.8	1383.2	1381.6	1380.0	1381.6	1383.2	1384.8	1386.4	1387.2
167.5°	1398.4	1397.4	1395.3	1393.3	1391.2	1389.2	1391.2	1393.3	1395.3	1397.4	1398.4
170°	1406.6	1405.6	1403.5	1401.5	1399.4	1397.4	1399.4	1401.5	1403.5	1405.6	1406.6
172.5°	1412.7	1411.7	1409.6	1407.6	1405.5	1403.5	1405.5	1407.6	1409.6	1411.7	1412.7
175°	1416.8	1415.7	1413.4	1411.1	1408.9	1406.6	1408.9	1411.1	1413.4	1415.7	1416.8
177.5°	1417.8	1416.8	1414.7	1412.7	1410.6	1408.6	1410.6	1412.7	1414.7	1416.8	1417.8
180°	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7

TEST NUMBER: P998391

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5	930.5
2.5°	883.3	889.0	886.9	879.0	888.3	888.3	894.8	894.8	902.6	905.5	909.8
5°	833.2	837.5	841.1	837.5	844.0	854.0	859.7	864.7	875.4	879.7	886.2
7.5°	779.6	787.5	791.0	791.0	801.8	813.2	824.7	831.8	846.8	852.6	859.0
10°	727.4	736.7	743.8	743.1	761.0	768.2	782.5	798.9	813.9	822.5	831.8
12.5°	672.3	677.3	687.3	701.6	705.9	718.8	735.3	756.0	783.2	791.0	804.6
15°	626.5	640.1	648.0	654.4	664.4	676.6	694.5	714.5	741.7	758.9	773.2
17.5°	587.9	605.8	610.8	609.4	622.3	640.8	661.6	676.6	700.9	721.7	735.3
20°	556.4	563.6	572.2	575.8	585.8	605.8	625.8	643.0	663.0	679.5	695.2
22.5°	525.0	530.7	537.9	544.3	552.2	563.6	582.9	604.4	623.7	639.4	657.3
25°	499.2	502.8	509.2	514.3	522.8	530.7	544.3	567.9	590.8	600.1	615.8
27.5°	474.2	477.1	481.4	487.1	491.4	499.2	511.4	530.7	554.3	563.6	585.1
30°	452.0	454.2	458.5	461.3	463.5	472.8	482.1	497.1	515.0	527.8	543.6
32.5°	431.3	433.4	437.7	438.4	441.3	446.3	454.9	468.5	484.2	494.9	508.5
35°	408.4	409.8	414.1	415.5	417.7	422.0	428.4	438.4	452.7	460.6	472.8
37.5°	390.5	389.8	392.7	394.8	397.7	399.8	402.0	412.0	422.7	429.9	439.2
40°	371.2	369.8	370.5	373.4	374.8	377.6	377.6	387.7	394.8	400.5	407.7
42.5°	351.9	351.2	349.7	351.2	352.6	353.3	354.0	361.2	368.3	373.4	381.2
45°	332.6	331.9	330.4	331.2	331.2	332.6	334.7	337.6	342.6	346.9	351.2
47.5°	314.7	313.3	311.1	310.4	311.8	311.8	311.8	314.7	319.7	321.1	325.4
50°	296.1	294.0	291.1	289.7	289.7	289.0	290.4	291.1	295.4	296.8	300.4
52.5°	276.1	274.6	271.8	268.9	269.6	268.2	268.9	269.6	271.1	273.2	275.4
55°	256.1	253.2	251.0	250.3	248.2	248.2	246.0	248.9	248.2	248.9	251.8
57.5°	236.7	233.9	230.3	228.9	226.7	226.0	224.6	223.9	224.6	226.7	228.9
60°	213.9	212.4	210.3	208.1	206.7	204.6	203.1	203.1	202.4	202.4	203.1
62.5°	191.7	191.0	188.1	187.4	186.0	184.5	182.4	181.0	181.0	182.4	183.1
65°	170.2	169.5	167.4	166.6	163.1	161.6	160.9	160.2	158.8	158.8	158.8
67.5°	150.2	148.1	148.1	144.5	141.6	140.2	138.8	138.0	138.0	138.0	138.8
70°	128.0	128.0	125.9	123.7	120.9	121.6	119.4	117.3	117.3	115.9	116.6
72.5°	106.6	105.9	103.7	103.0	100.8	98.7	97.3	98.7	96.6	95.8	96.6
75°	85.8	85.1	83.7	82.3	83.0	80.8	78.7	78.0	78.0	76.5	76.5
77.5°	65.8	67.2	64.4	63.7	62.2	60.8	60.1	59.4	59.4	59.4	60.8
80°	45.8	46.5	46.5	45.1	45.8	43.6	43.6	43.6	41.5	42.2	42.9
82.5°	29.3	29.3	28.6	29.3	28.6	28.6	27.9	27.9	27.2	27.2	27.9
85°	16.5	15.7	15.0	16.5	15.7	15.7	15.0	15.0	15.0	15.0	15.0
87.5°	3.6	4.3	4.3	4.3	4.3	5.0	5.0	5.0	5.7	5.7	5.7
90°	24.9	23.8	22.7	21.5	20.4	18.6	16.8	15.0	13.2	12.3	11.0
92.5°	26.4	25.9	25.4	25.0	24.5	23.8	23.2	22.5	21.8	21.5	21.9
95°	44.3	43.2	42.1	40.9	39.8	38.2	36.6	35.1	33.5	32.7	36.4
97.5°	54.9	54.2	53.5	52.8	52.1	48.5	44.9	41.2	37.6	35.8	45.1
100°	65.5	63.7	61.8	60.0	58.2	54.4	50.5	46.7	42.8	40.9	56.4
102.5°	70.3	67.8	65.3	62.8	60.3	101.6	142.9	184.2	225.5	246.2	246.4
105°	72.3	69.8	67.3	64.8	62.3	124.3	186.3	248.2	310.2	341.2	337.8
107.5°	74.4	71.9	69.4	66.9	64.4	140.9	217.4	293.9	370.4	408.6	405.8
110°	88.0	110.7	133.4	156.1	178.8	244.4	310.0	375.6	441.2	474.0	471.6

TEST NUMBER: P998391

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	127.6	225.4	323.3	421.1	518.9	522.8	526.6	530.5	534.4	536.3	534.3
115°	209.8	314.9	420.0	525.1	630.2	624.5	618.9	613.2	607.5	604.7	602.8
117.5°	555.5	588.0	620.5	652.9	685.4	681.5	677.7	673.8	669.9	668.0	665.7
120°	759.6	756.9	754.2	751.4	748.7	744.6	740.5	736.4	732.3	730.3	728.6
122.5°	814.4	813.1	811.7	810.4	809.0	804.5	799.9	795.4	790.9	788.6	786.8
125°	869.5	867.9	866.3	864.7	863.1	858.8	854.5	850.2	845.9	843.7	842.2
127.5°	922.3	920.0	917.7	915.5	913.2	909.8	906.4	903.0	899.6	897.9	896.3
130°	971.2	968.7	966.2	963.7	961.2	958.7	956.2	953.7	951.2	950.0	948.2
132.5°	1017.4	1015.3	1013.3	1011.2	1009.2	1006.7	1004.2	1001.7	999.2	998.0	996.5
135°	1062.2	1059.9	1057.6	1055.4	1053.1	1051.1	1049.0	1047.0	1044.9	1043.9	1042.1
137.5°	1104.1	1101.8	1099.5	1097.3	1095.0	1092.7	1090.5	1088.2	1085.9	1084.8	1083.4
140°	1144.1	1142.0	1140.0	1137.9	1135.9	1133.4	1130.9	1128.4	1125.9	1124.6	1123.7
142.5°	1180.9	1179.1	1177.3	1175.5	1173.7	1170.7	1167.8	1164.8	1161.9	1160.4	1159.6
145°	1214.7	1213.1	1211.6	1210.0	1208.4	1204.5	1200.7	1196.8	1192.9	1191.0	1191.1
147.5°	1244.6	1243.5	1242.4	1241.2	1240.1	1236.2	1232.4	1228.5	1224.6	1222.7	1223.0
150°	1273.1	1271.7	1270.4	1269.0	1267.6	1264.0	1260.4	1256.7	1253.1	1251.3	1252.1
152.5°	1298.6	1297.3	1295.9	1294.6	1293.2	1289.8	1286.4	1283.0	1279.6	1277.9	1278.8
155°	1321.1	1319.8	1318.4	1317.1	1315.7	1313.0	1310.2	1307.5	1304.8	1303.4	1304.4
157.5°	1341.4	1339.8	1338.3	1336.7	1335.1	1333.1	1331.0	1329.0	1326.9	1325.9	1326.8
160°	1357.9	1356.5	1355.2	1353.8	1352.4	1351.0	1349.7	1348.3	1347.0	1346.3	1347.0
162.5°	1374.1	1372.5	1370.9	1369.3	1367.7	1366.6	1365.4	1364.3	1363.2	1362.6	1363.3
165°	1386.4	1384.8	1383.2	1381.6	1380.0	1379.3	1378.6	1377.9	1377.2	1376.9	1377.6
167.5°	1397.6	1396.0	1394.4	1392.8	1391.2	1390.5	1389.9	1389.2	1388.5	1388.2	1388.9
170°	1405.8	1404.2	1402.6	1401.0	1399.4	1399.0	1398.5	1398.1	1397.6	1397.4	1398.1
172.5°	1411.9	1410.3	1408.7	1407.1	1405.5	1405.1	1404.6	1404.2	1403.7	1403.5	1404.2
175°	1416.0	1414.4	1412.8	1411.2	1409.6	1409.2	1408.7	1408.3	1407.8	1407.6	1408.4
177.5°	1417.0	1415.4	1413.8	1412.2	1410.6	1410.4	1410.2	1409.9	1409.7	1409.6	1410.4
180°	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7	1411.7

TEST NUMBER: P998391

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	930.5	930.5	930.5	930.5
2.5°	913.3	913.3	924.1	935.5
5°	893.3	898.3	915.5	931.2
7.5°	874.0	882.6	904.1	924.1
10°	850.4	861.9	888.3	911.9
12.5°	827.5	838.3	869.0	895.5
15°	795.3	808.9	841.8	874.7
17.5°	763.2	776.7	816.8	855.4
20°	725.2	743.1	788.2	839.7
22.5°	690.2	712.4	762.4	803.9
25°	651.6	685.9	732.4	786.0
27.5°	617.2	651.6	698.8	753.1
30°	578.6	613.7	662.3	712.4
32.5°	541.4	573.6	620.8	682.3
35°	502.8	533.6	579.3	641.6
37.5°	467.8	497.8	547.9	605.1
40°	433.4	464.9	507.8	565.0
42.5°	401.2	429.1	467.8	525.0
45°	371.9	391.9	427.7	481.4
47.5°	341.2	359.0	391.9	445.6
50°	312.6	327.6	356.2	406.3
52.5°	284.7	297.5	324.0	364.1
55°	259.6	271.8	291.1	330.4
57.5°	233.9	243.2	261.8	293.2
60°	208.8	217.4	232.4	258.2
62.5°	183.8	191.0	205.3	226.0
65°	161.6	167.4	178.1	196.0
67.5°	140.2	143.8	152.3	166.6
70°	119.4	122.3	129.5	140.9
72.5°	97.3	100.1	108.0	115.9
75°	78.7	79.4	85.1	91.5
77.5°	61.5	60.8	65.1	70.1
80°	42.2	44.3	47.9	50.1
82.5°	28.6	29.3	30.8	32.2
85°	15.7	16.5	16.5	18.6
87.5°	6.4	7.2	7.2	7.9
90°	8.5	6.0	3.5	1.0
92.5°	22.8	23.7	24.6	25.5
95°	43.9	51.4	58.9	66.4
97.5°	63.7	82.3	100.9	119.5
100°	87.5	118.6	149.7	180.8
102.5°	246.9	247.3	247.8	248.2
105°	331.0	324.1	317.3	310.5
107.5°	400.1	394.4	388.8	383.1
110°	466.8	462.1	457.3	452.5

TEST NUMBER: P998391

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	530.2	526.1	522.0	517.9
115°	598.9	595.0	591.2	587.3
117.5°	661.2	656.7	652.1	647.6
120°	725.2	721.8	718.4	715.0
122.5°	783.1	779.5	775.8	772.2
125°	839.3	836.4	833.4	830.5
127.5°	893.1	890.0	886.8	883.6
130°	944.5	940.9	937.2	933.6
132.5°	993.6	990.6	987.7	984.7
135°	1038.5	1034.8	1031.2	1027.6
137.5°	1080.7	1078.0	1075.2	1072.5
140°	1121.9	1120.1	1118.3	1116.5
142.5°	1158.0	1156.4	1154.8	1153.2
145°	1191.4	1191.6	1191.9	1192.1
147.5°	1223.7	1224.4	1225.1	1225.8
150°	1253.7	1255.2	1256.8	1258.4
152.5°	1280.6	1282.4	1284.2	1286.0
155°	1306.5	1308.5	1310.6	1312.6
157.5°	1328.6	1330.4	1332.2	1334.0
160°	1348.3	1349.7	1351.0	1352.4
162.5°	1364.7	1366.0	1367.4	1368.8
165°	1379.0	1380.3	1381.7	1383.1
167.5°	1390.2	1391.6	1392.9	1394.3
170°	1399.4	1400.8	1402.1	1403.5
172.5°	1405.5	1406.9	1408.2	1409.6
175°	1410.0	1411.5	1413.1	1414.7
177.5°	1412.0	1413.6	1415.2	1416.8
180°	1411.7	1411.7	1411.7	1411.7

TEST NUMBER: P998391

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.38	14.08	14.47	15.17	16.67	10.87	11.58	11.96	12.67	14.16
	3H	14.18	14.81	15.28	15.91	17.42	12.20	12.84	13.31	13.93	15.45
	4H	14.34	14.94	15.45	16.04	17.56	12.66	13.26	13.77	14.36	15.88
	6H	14.38	14.93	15.50	16.03	17.56	12.96	13.51	14.08	14.61	16.14
	8H	14.35	14.88	15.48	15.99	17.52	13.04	13.56	14.16	14.68	16.20
	12H	14.31	14.81	15.44	15.92	17.46	13.07	13.57	14.20	14.68	16.23
4H	2H	13.40	14.00	14.52	15.10	16.62	11.30	11.90	12.42	13.00	14.51
	3H	14.37	14.87	15.49	15.99	17.52	12.74	13.24	13.87	14.37	15.90
	4H	14.64	15.10	15.77	16.21	17.76	13.27	13.73	14.40	14.85	16.40
	6H	14.76	15.15	15.90	16.29	17.83	13.64	14.04	14.78	15.17	16.72
	8H	14.75	15.12	15.89	16.25	17.81	13.75	14.12	14.89	15.25	16.81
	12H	14.71	15.04	15.86	16.18	17.75	13.80	14.13	14.95	15.27	16.84
8H	4H	14.63	15.00	15.77	16.13	17.69	13.40	13.77	14.54	14.90	16.46
	6H	14.81	15.11	15.96	16.28	17.84	13.83	14.13	14.99	15.31	16.86
	8H	14.84	15.10	16.00	16.25	17.83	13.98	14.25	15.15	15.40	16.97
	12H	14.82	15.05	15.98	16.19	17.80	14.07	14.30	15.23	15.45	17.06
12H	4H	14.58	14.92	15.74	16.06	17.62	13.37	13.70	14.52	14.84	16.41
	6H	14.79	15.05	15.95	16.20	17.78	13.83	14.10	14.99	15.25	16.82
	8H	14.81	15.04	15.98	16.19	17.80	13.98	14.21	15.15	15.36	16.97