

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997875

Luminaire Tested: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P997875
REPORT IS A COMBINATION OF REPORTS P983612 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-A1
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5612.0 lumens
Efficiency: N/A
Efficacy: 79.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997875

CATALOG NUMBER: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P997875

CATALOG NUMBER: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	114	114	114	114	109	109	109	109	99	99	99	91	91	91	83	83	83	79		
1	105	101	97	94	100	97	93	90	88	86	83	81	79	77	74	73	71	68		
2	96	89	83	78	92	85	80	75	78	74	70	72	69	66	66	64	61	58		
3	88	79	72	66	84	76	69	64	70	65	60	65	60	57	60	56	53	50		
4	81	71	63	57	78	68	61	55	63	57	52	58	53	49	54	50	46	44		
5	75	63	55	49	72	61	54	48	57	50	46	53	47	43	49	45	41	39		
6	70	57	49	43	66	55	48	42	52	45	40	48	43	38	45	40	37	34		
7	65	52	44	39	62	51	43	38	47	41	36	44	39	34	41	36	33	31		
8	60	48	40	35	58	46	39	34	43	37	32	41	35	31	38	33	30	28		
9	56	44	36	31	54	43	36	31	40	34	29	37	32	28	35	30	27	25		
10	53	41	33	28	51	39	33	28	37	31	27	35	30	26	33	28	25	23		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	31769	31769	31769	31769
5°	31845	33874	31967	26949
10°	31476	36978	31673	22219
15°	30711	39004	31139	18715
20°	30233	36622	30233	16267
25°	29270	31461	29403	14546
30°	27685	24732	28213	13176
35°	26279	17101	26719	12055
40°	24665	12912	24947	11162
45°	22674	10611	23046	10198
50°	20953	9313	20991	9335
55°	18991	7935	19113	8399
60°	16899	6629	17133	7330
65°	15027	5391	15300	6259
70°	13161	4230	13494	5049
75°	11048	3070	11479	3662
80°	8622	1947	9237	2174
85°	5664	981	6102	727

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 32840 cd/sqm

TEST NUMBER: P997875

CATALOG NUMBER: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.2	3.4
10°-20°	556.4	9.9
20°-30°	807.5	14.4
30°-40°	851.2	15.2
40°-50°	753.3	13.4
50°-60°	601.5	10.7
60°-70°	408.5	7.3
70°-80°	209.0	3.7
80°-90°	50.6	0.9
90°-100°	26.2	0.5
100°-110°	83.2	1.5
110°-120°	142.4	2.5
120°-130°	187.2	3.3
130°-140°	210.2	3.7
140°-150°	206.1	3.7
150°-160°	172.9	3.1
160°-170°	114.7	2.0
170°-180°	40.1	0.7
0°-30°	1555.0	27.7
0°-40°	2406.3	42.9
0°-60°	3761.0	67.0
0°-90°	4429.2	78.9
90°-120°	251.7	4.5
90°-150°	855.2	15.2
90°-180°	1183.0	21.1
0°-180°	5612.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2007	2007	2007	2007	2007	
5°	2008	2242	2016	1783	2008	190
15°	1887	2755	1913	1322	1887	533
25°	1695	2295	1703	1061	1695	775
35°	1384	1250	1407	881	1384	866
45°	1038	753	1055	724	1038	805
55°	713	529	717	560	713	636
65°	423	326	430	378	423	420
75°	198	160	205	191	198	212
85°	40	42	43	31	40	47
90°	0	12	0	12	0	4
95°	19	22	19	22	19	21
105°	77	79	77	79	77	81
115°	143	143	143	143	143	141
125°	208	208	208	208	208	186
135°	269	272	269	272	269	208
145°	326	330	326	330	326	204
155°	373	376	373	376	373	172
165°	406	406	406	406	406	115
175°	422	421	422	421	422	40
180°	423	423	423	423	423	

TEST NUMBER: P997875

CATALOG NUMBER: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	2017.8	2022.4	2030.1	2031.7	2047.1	2059.4	2073.3	2073.3	2077.9	2076.4	2064.1
5°	2008.5	2022.4	2042.5	2059.4	2087.2	2099.5	2118.0	2131.9	2144.3	2153.5	2152.0
7.5°	1993.1	2017.8	2047.1	2079.5	2116.5	2138.1	2164.3	2189.0	2206.0	2221.4	2232.2
10°	1966.9	2008.5	2048.6	2091.8	2139.6	2169.0	2199.8	2232.2	2258.4	2287.7	2315.5
12.5°	1931.4	1991.5	2040.9	2098.0	2156.6	2189.0	2238.4	2263.1	2314.0	2388.0	2408.1
15°	1886.6	1968.4	2014.7	2087.2	2164.3	2190.6	2258.4	2298.5	2403.4	2449.7	2505.2
17.5°	1845.0	1936.0	1997.7	2081.0	2156.6	2207.5	2273.9	2355.6	2443.5	2509.9	2571.6
20°	1811.1	1899.0	1973.0	2065.6	2161.2	2226.0	2295.4	2394.2	2489.8	2557.7	2605.5
22.5°	1733.9	1846.5	1932.9	2036.3	2152.0	2241.5	2307.8	2415.8	2519.1	2560.8	2602.4
25°	1695.4	1792.5	1892.8	2010.1	2145.8	2252.3	2309.3	2429.7	2520.7	2536.1	2545.4
27.5°	1624.4	1733.9	1851.2	1985.4	2144.3	2233.7	2306.2	2415.8	2488.3	2477.5	2449.7
30°	1536.5	1670.7	1800.3	1945.3	2122.7	2219.9	2287.7	2388.0	2425.0	2369.5	2320.1
32.5°	1471.7	1598.2	1741.6	1909.8	2098.0	2190.6	2256.9	2335.6	2343.3	2243.0	2159.7
35°	1383.7	1524.1	1686.1	1863.5	2056.3	2139.6	2201.3	2249.2	2212.1	2071.8	1973.0
37.5°	1305.1	1443.9	1616.7	1797.2	1999.3	2081.0	2130.4	2138.1	2047.1	1923.7	1778.7
40°	1218.7	1362.2	1542.6	1732.4	1936.0	2007.0	2037.8	2014.7	1883.6	1740.1	1572.0
42.5°	1132.3	1274.2	1468.6	1663.0	1855.8	1916.0	1928.3	1865.1	1704.6	1536.5	1342.1
45°	1038.2	1186.3	1380.7	1576.6	1763.2	1797.2	1798.7	1707.7	1518.0	1342.1	1161.6
47.5°	961.1	1098.4	1291.2	1487.1	1644.5	1667.6	1658.3	1553.4	1346.7	1149.3	991.9
50°	876.2	1007.3	1198.6	1391.5	1525.7	1531.8	1508.7	1359.1	1157.0	976.5	851.5
52.5°	785.2	917.9	1093.7	1278.8	1399.2	1389.9	1345.2	1184.7	995.0	845.4	749.7
55°	712.7	829.9	995.0	1175.5	1260.3	1234.1	1184.7	1021.2	871.6	745.1	661.8
57.5°	632.5	735.8	897.8	1055.2	1104.5	1079.8	1030.5	877.8	738.9	643.3	587.7
60°	556.9	651.0	792.9	924.0	962.6	936.4	879.3	742.0	641.7	561.5	519.9
62.5°	487.5	569.2	688.0	808.3	823.8	797.5	748.2	637.1	550.7	487.5	456.6
65°	422.7	499.8	595.5	686.5	700.4	672.6	621.7	541.5	469.0	428.9	399.5
67.5°	359.4	421.1	506.0	572.3	580.0	553.8	512.2	447.4	402.6	359.4	337.8
70°	303.9	350.2	416.5	470.5	473.6	448.9	427.3	368.7	334.8	303.9	286.9
72.5°	249.9	282.3	333.2	373.3	374.9	359.4	339.4	302.4	273.0	251.5	234.5
75°	197.5	225.2	256.1	291.6	290.0	277.7	262.2	239.1	214.4	200.5	192.8
77.5°	151.2	168.1	192.8	216.0	216.0	209.8	200.5	183.6	168.1	154.3	146.6
80°	108.0	118.8	138.8	146.6	149.6	148.1	140.4	128.0	121.9	111.1	108.0
82.5°	69.4	77.1	86.4	94.1	98.7	95.6	94.1	87.9	78.7	75.6	72.5
85°	40.1	43.2	47.8	52.4	54.0	52.4	55.5	50.9	46.3	46.3	44.7
87.5°	17.0	18.5	21.6	21.6	23.1	23.1	21.6	23.1	23.1	21.6	20.1
90°	0.4	1.3	2.3	3.2	4.1	4.6	5.5	7.2	9.0	10.7	12.5
92.5°	7.9	8.5	9.1	9.8	10.4	10.7	10.7	10.8	10.9	11.0	11.1
95°	18.6	19.4	20.2	20.9	21.7	22.1	22.2	22.3	22.5	22.6	22.8
97.5°	31.1	31.8	32.5	33.2	33.9	34.3	34.5	34.8	35.1	35.4	35.7
100°	45.3	45.9	46.6	47.2	47.9	48.2	48.3	48.6	48.8	49.1	49.3
102.5°	60.3	60.8	61.3	61.8	62.3	62.5	62.7	63.0	63.3	63.6	63.9
105°	76.8	77.0	77.2	77.5	77.7	77.8	77.9	78.0	78.2	78.3	78.5
107.5°	93.2	93.5	93.8	94.1	94.4	94.6	94.6	94.6	94.6	94.6	94.6
110°	108.9	109.4	109.8	110.3	110.8	111.0	111.0	111.0	111.0	111.0	111.0

TEST NUMBER: P997875

CATALOG NUMBER: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	126.0	126.5	127.0	127.5	128.0	128.2	128.2	128.1	128.0	127.9	127.8
115°	142.8	143.3	143.7	144.2	144.7	144.9	144.8	144.7	144.5	144.4	144.2
117.5°	159.6	160.2	160.8	161.5	162.1	162.4	162.2	161.8	161.5	161.1	160.7
120°	176.4	177.0	177.6	178.3	178.9	179.2	178.9	178.3	177.6	177.0	176.4
122.5°	191.7	192.5	193.3	194.1	194.9	195.3	195.1	194.7	194.3	193.9	193.5
125°	207.8	208.5	209.2	209.9	210.6	211.0	210.9	210.6	210.4	210.1	209.9
127.5°	223.5	224.4	225.2	226.1	227.0	227.4	227.2	226.9	226.6	226.3	226.0
130°	238.1	239.1	240.2	241.2	242.3	242.8	242.7	242.6	242.4	242.3	242.1
132.5°	254.6	255.4	256.2	256.9	257.7	258.1	258.1	258.2	258.3	258.4	258.5
135°	268.8	269.7	270.6	271.5	272.4	272.8	272.9	273.0	273.2	273.3	273.5
137.5°	284.5	285.2	286.0	286.7	287.4	287.8	287.9	288.0	288.2	288.3	288.5
140°	298.5	299.2	299.9	300.6	301.3	301.7	301.9	302.3	302.7	303.1	303.5
142.5°	312.7	313.4	314.2	314.9	315.6	316.0	316.1	316.3	316.6	316.8	317.0
145°	326.3	326.9	327.4	328.0	328.5	328.8	329.0	329.5	330.0	330.5	331.0
147.5°	338.4	339.1	339.9	340.6	341.3	341.7	341.9	342.2	342.5	342.8	343.1
150°	350.9	351.4	351.9	352.4	352.9	353.1	353.3	353.6	353.9	354.2	354.5
152.5°	362.0	362.5	363.0	363.5	364.0	364.2	364.4	364.8	365.1	365.5	365.9
155°	373.1	373.3	373.5	373.8	374.0	374.1	374.2	374.5	374.7	375.0	375.2
157.5°	382.7	382.9	383.0	383.2	383.3	383.4	383.5	383.6	383.8	383.9	384.1
160°	391.3	391.5	391.6	391.8	391.9	392.0	392.0	392.1	392.2	392.3	392.4
162.5°	399.1	399.1	399.1	399.1	399.1	399.1	399.1	399.2	399.3	399.4	399.5
165°	405.9	405.8	405.8	405.7	405.6	405.6	405.6	405.6	405.6	405.6	405.6
167.5°	412.0	411.8	411.5	411.3	411.0	410.9	410.9	410.9	410.9	410.9	410.9
170°	416.6	416.4	416.2	415.9	415.7	415.6	415.6	415.5	415.4	415.3	415.2
172.5°	419.8	419.6	419.4	419.1	418.9	418.8	418.8	418.7	418.6	418.5	418.4
175°	422.3	422.1	421.9	421.6	421.4	421.3	421.2	421.1	420.9	420.8	420.6
177.5°	423.8	423.6	423.3	423.1	422.8	422.7	422.6	422.5	422.3	422.2	422.0
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1

TEST NUMBER: P997875

CATALOG NUMBER: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	2085.7	2087.2	2090.3	2105.7	2113.4	2115.0	2108.8	2122.7	2127.3	2122.7	2119.6
5°	2184.4	2193.6	2212.1	2232.2	2230.7	2232.2	2241.5	2250.7	2253.8	2241.5	2246.1
7.5°	2270.8	2289.3	2309.3	2340.2	2340.2	2355.6	2361.8	2369.5	2388.0	2378.8	2375.7
10°	2369.5	2394.2	2431.2	2480.6	2482.1	2497.5	2513.0	2537.6	2545.4	2539.2	2542.3
12.5°	2492.9	2540.7	2543.8	2597.8	2622.5	2625.6	2650.3	2645.6	2661.1	2661.1	2687.3
15°	2546.9	2620.9	2662.6	2715.0	2730.5	2712.0	2732.0	2753.6	2755.2	2755.2	2753.6
17.5°	2644.1	2673.4	2715.0	2742.8	2749.0	2749.0	2750.5	2759.8	2753.6	2741.3	2750.5
20°	2664.1	2676.5	2691.9	2688.8	2691.9	2676.5	2661.1	2645.6	2647.2	2639.5	2662.6
22.5°	2627.1	2624.0	2588.6	2565.4	2565.4	2534.6	2505.2	2491.4	2477.5	2482.1	2489.8
25°	2534.6	2486.7	2443.5	2409.6	2401.9	2352.5	2312.4	2300.1	2276.9	2295.4	2298.5
27.5°	2386.5	2332.5	2263.1	2233.7	2193.6	2173.6	2145.8	2108.8	2061.0	2088.7	2084.1
30°	2227.6	2147.4	2090.3	2019.3	1956.1	1951.4	1899.0	1837.3	1812.6	1812.6	1826.5
32.5°	2050.2	1943.7	1860.4	1760.2	1698.4	1672.2	1609.0	1547.3	1561.2	1514.9	1531.8
35°	1843.5	1703.1	1598.2	1501.0	1454.7	1423.9	1342.1	1308.2	1271.1	1249.5	1289.6
37.5°	1646.0	1484.0	1349.8	1243.4	1226.4	1170.9	1115.3	1093.7	1072.1	1081.4	1079.8
40°	1405.3	1261.9	1141.6	1058.3	1028.9	1002.7	965.7	939.5	925.6	933.3	934.8
42.5°	1187.8	1067.5	978.0	919.4	894.7	876.2	857.7	836.1	831.5	831.5	837.7
45°	1019.7	921.0	860.8	813.0	799.1	785.2	771.3	762.1	759.0	752.8	757.4
47.5°	885.5	806.8	769.8	734.3	718.9	715.8	703.4	698.8	692.6	691.1	692.6
50°	772.9	723.5	689.6	669.5	658.7	654.1	647.9	638.7	635.6	643.3	640.2
52.5°	694.2	647.9	629.4	609.3	603.2	597.0	587.7	589.3	587.7	584.7	584.7
55°	615.5	586.2	567.7	552.3	550.7	544.6	536.8	533.8	532.2	529.1	533.8
57.5°	552.3	529.1	512.2	498.3	492.1	492.1	484.4	478.2	478.2	476.7	478.2
60°	489.0	465.9	455.1	441.2	436.6	435.0	430.4	427.3	422.7	422.7	422.7
62.5°	430.4	411.9	399.5	387.2	388.7	381.0	374.9	371.8	371.8	373.3	373.3
65°	374.9	362.5	347.1	336.3	333.2	331.7	328.6	327.0	322.4	325.5	325.5
67.5°	324.0	307.0	297.7	293.1	288.5	286.9	283.8	280.8	279.2	277.7	280.8
70°	273.0	259.2	251.5	248.4	243.7	242.2	240.7	236.0	237.6	239.1	240.7
72.5°	226.8	214.4	212.9	203.6	203.6	203.6	197.5	200.5	199.0	195.9	199.0
75°	178.9	172.8	169.7	165.1	166.6	165.1	163.5	158.9	158.9	160.4	162.0
77.5°	141.9	135.8	134.2	129.6	126.5	129.6	126.5	125.0	125.0	126.5	126.5
80°	104.9	101.8	97.2	97.2	97.2	95.6	95.6	95.6	94.1	92.6	94.1
82.5°	69.4	69.4	67.9	66.3	67.9	64.8	66.3	66.3	66.3	66.3	66.3
85°	44.7	43.2	43.2	41.7	41.7	41.7	43.2	40.1	40.1	41.7	41.7
87.5°	20.1	20.1	20.1	21.6	20.1	20.1	20.1	21.6	20.1	20.1	20.1
90°	12.3	12.2	12.0	11.9	11.8	11.8	11.9	12.0	12.0	12.1	12.0
92.5°	11.2	11.2	11.3	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4
95°	22.8	22.8	22.8	22.8	22.8	22.7	22.6	22.4	22.3	22.1	22.3
97.5°	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7
100°	49.3	49.3	49.3	49.3	49.3	49.3	49.2	49.1	49.0	48.9	49.0
102.5°	64.0	64.1	64.2	64.3	64.3	64.3	64.2	64.1	64.0	63.9	64.0
105°	78.7	78.9	79.0	79.2	79.3	79.3	79.3	79.3	79.3	79.3	79.3
107.5°	94.7	94.8	94.9	95.0	95.0	94.8	94.4	94.0	93.6	93.2	93.6
110°	111.0	111.0	111.0	111.0	111.0	110.9	110.7	110.4	110.2	110.0	110.2

TEST NUMBER: P997875

CATALOG NUMBER: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	127.6	127.3	127.1	126.8	126.7	126.6	126.5	126.3	126.2	126.0	126.2
115°	144.1	144.1	144.0	143.9	143.9	143.8	143.5	143.3	143.0	142.8	143.0
117.5°	160.5	160.2	160.0	159.7	159.6	159.5	159.2	159.0	158.7	158.5	158.7
120°	176.4	176.4	176.4	176.4	176.4	176.3	176.0	175.8	175.5	175.3	175.5
122.5°	193.3	193.0	192.8	192.5	192.4	192.3	192.2	192.0	191.9	191.7	191.9
125°	209.7	209.5	209.2	209.0	208.9	208.9	208.8	208.7	208.6	208.5	208.6
127.5°	225.7	225.4	225.1	224.8	224.6	224.5	224.2	224.0	223.7	223.5	223.7
130°	241.9	241.7	241.6	241.4	241.3	241.1	240.8	240.5	240.2	239.9	240.2
132.5°	258.1	257.7	257.3	256.9	256.7	256.6	256.3	256.1	255.8	255.6	255.8
135°	273.4	273.3	273.2	273.1	273.1	273.0	272.7	272.5	272.2	272.0	272.2
137.5°	288.4	288.3	288.2	288.1	288.1	287.9	287.6	287.3	287.0	286.7	287.0
140°	303.5	303.5	303.5	303.5	303.5	303.3	303.0	302.7	302.3	302.0	302.3
142.5°	317.1	317.2	317.3	317.4	317.4	317.2	316.9	316.6	316.3	316.0	316.3
145°	331.1	331.1	331.2	331.3	331.3	331.1	330.8	330.5	330.2	329.9	330.2
147.5°	343.3	343.4	343.6	343.7	343.8	343.6	343.3	343.0	342.7	342.4	342.7
150°	354.7	355.0	355.2	355.5	355.6	355.5	355.2	355.0	354.7	354.5	354.7
152.5°	366.2	366.6	366.9	367.2	367.4	367.2	366.9	366.6	366.2	365.9	366.2
155°	375.6	376.0	376.4	376.8	377.0	376.9	376.6	376.4	376.1	375.9	376.1
157.5°	384.7	385.2	385.8	386.3	386.6	386.4	386.0	385.7	385.3	384.9	385.3
160°	392.9	393.3	393.8	394.3	394.5	394.3	394.0	393.7	393.4	393.1	393.4
162.5°	400.1	400.6	401.2	401.7	402.0	401.8	401.4	401.0	400.6	400.2	400.6
165°	406.2	406.7	407.3	407.8	408.1	407.9	407.5	407.1	406.7	406.3	406.7
167.5°	411.5	412.0	412.6	413.1	413.4	413.2	412.8	412.4	412.0	411.6	412.0
170°	415.8	416.3	416.9	417.4	417.7	417.5	417.0	416.5	416.1	415.6	416.1
172.5°	419.0	419.5	420.1	420.6	420.9	420.7	420.2	419.7	419.3	418.8	419.3
175°	421.2	421.7	422.3	422.8	423.1	422.9	422.4	421.9	421.4	420.9	421.4
177.5°	422.5	422.9	423.4	423.9	424.1	423.9	423.4	422.9	422.5	422.0	422.5
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1

TEST NUMBER: P997875

CATALOG NUMBER: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	2127.3	2116.5	2107.2	2108.8	2116.5	2110.3	2094.9	2074.9	2067.1	2057.9	2067.1
5°	2255.3	2246.1	2227.6	2229.1	2224.5	2218.3	2193.6	2162.8	2162.8	2138.1	2135.0
7.5°	2381.8	2368.0	2355.6	2352.5	2335.6	2323.2	2301.6	2258.4	2241.5	2212.1	2195.2
10°	2523.8	2513.0	2499.1	2482.1	2472.9	2451.3	2415.8	2352.5	2321.7	2281.6	2252.3
12.5°	2667.2	2665.7	2634.8	2600.9	2599.3	2565.4	2540.7	2455.9	2414.2	2360.2	2290.8
15°	2758.2	2750.5	2733.6	2716.6	2721.2	2684.2	2628.7	2528.4	2500.6	2435.8	2361.8
17.5°	2756.7	2756.7	2752.1	2749.0	2744.4	2733.6	2702.7	2636.4	2591.6	2509.9	2440.5
20°	2668.8	2688.8	2693.5	2691.9	2707.3	2715.0	2713.5	2671.9	2636.4	2563.9	2492.9
22.5°	2492.9	2539.2	2559.2	2571.6	2604.0	2620.9	2661.1	2645.6	2636.4	2582.4	2522.2
25°	2329.4	2344.8	2405.0	2408.1	2452.8	2494.5	2534.6	2560.8	2594.7	2574.7	2523.8
27.5°	2118.0	2153.5	2196.7	2229.1	2238.4	2323.2	2389.6	2438.9	2516.0	2522.2	2505.2
30°	1878.9	1895.9	1966.9	2010.1	2059.4	2121.1	2216.8	2301.6	2371.0	2434.3	2455.9
32.5°	1587.4	1656.8	1698.4	1750.9	1794.1	1903.6	2020.9	2130.4	2210.6	2317.0	2363.3
35°	1320.5	1374.5	1445.5	1467.1	1545.7	1638.3	1791.0	1931.4	2053.3	2161.2	2255.3
37.5°	1099.9	1143.1	1218.7	1252.6	1298.9	1417.7	1545.7	1720.0	1866.6	1999.3	2116.5
40°	948.7	981.1	1038.2	1049.0	1087.6	1195.5	1298.9	1462.4	1656.8	1835.7	1963.8
42.5°	845.4	860.8	899.4	913.2	937.9	1010.4	1103.0	1257.3	1437.7	1622.9	1803.3
45°	771.3	782.1	805.3	817.6	848.5	880.8	956.4	1079.8	1221.8	1408.4	1602.8
47.5°	705.0	718.9	728.1	735.8	752.8	788.3	837.7	928.7	1064.4	1235.7	1423.9
50°	649.5	654.1	671.0	672.6	683.4	706.5	752.8	808.3	916.3	1055.2	1237.2
52.5°	593.9	598.5	609.3	620.1	624.8	643.3	674.1	720.4	800.6	910.2	1072.1
55°	538.4	544.6	555.4	563.1	567.7	583.1	601.6	646.4	709.6	786.7	919.4
57.5°	482.8	496.7	499.8	504.4	512.2	529.1	546.1	572.3	621.7	692.6	789.8
60°	430.4	435.0	445.8	450.5	458.2	467.4	489.0	509.1	544.6	600.1	688.0
62.5°	376.4	387.2	391.8	396.5	402.6	413.4	427.3	448.9	479.8	524.5	593.9
65°	330.1	331.7	340.9	347.1	353.3	361.0	374.9	394.9	413.4	455.1	506.0
67.5°	285.4	288.5	291.6	297.7	305.4	313.2	325.5	336.3	359.4	387.2	427.3
70°	242.2	242.2	249.9	254.5	253.0	262.2	271.5	283.8	300.8	327.0	359.4
72.5°	203.6	202.1	208.3	209.8	212.9	219.1	225.2	237.6	246.8	266.9	291.6
75°	162.0	165.1	168.1	168.1	172.8	177.4	183.6	189.7	200.5	212.9	231.4
77.5°	128.0	128.0	131.1	132.7	137.3	135.8	141.9	148.1	155.8	166.6	180.5
80°	94.1	97.2	97.2	97.2	98.7	100.3	106.4	111.1	115.7	123.4	129.6
82.5°	66.3	66.3	69.4	69.4	69.4	72.5	72.5	74.0	77.1	81.8	86.4
85°	41.7	41.7	41.7	43.2	41.7	43.2	46.3	44.7	46.3	49.4	49.4
87.5°	20.1	20.1	20.1	20.1	20.1	21.6	20.1	21.6	23.1	23.1	23.1
90°	12.0	11.9	11.8	11.8	11.9	12.0	12.2	12.3	12.5	10.7	9.0
92.5°	11.4	11.4	11.4	11.4	11.4	11.3	11.2	11.2	11.1	11.0	10.9
95°	22.4	22.6	22.7	22.8	22.8	22.8	22.8	22.8	22.8	22.6	22.5
97.5°	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.4	35.1
100°	49.1	49.2	49.3	49.3	49.3	49.3	49.3	49.3	49.3	49.1	48.8
102.5°	64.1	64.2	64.3	64.3	64.3	64.2	64.1	64.0	63.9	63.6	63.3
105°	79.3	79.3	79.3	79.3	79.2	79.0	78.9	78.7	78.5	78.3	78.2
107.5°	94.0	94.4	94.8	95.0	95.0	94.9	94.8	94.7	94.6	94.6	94.6
110°	110.4	110.7	110.9	111.0	111.0	111.0	111.0	111.0	111.0	111.0	111.0

TEST NUMBER: P997875

CATALOG NUMBER: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	126.3	126.5	126.6	126.7	126.8	127.1	127.3	127.6	127.8	127.9	128.0
115°	143.3	143.5	143.8	143.9	143.9	144.0	144.1	144.1	144.2	144.4	144.5
117.5°	159.0	159.2	159.5	159.6	159.7	160.0	160.2	160.5	160.7	161.1	161.5
120°	175.8	176.0	176.3	176.4	176.4	176.4	176.4	176.4	176.4	177.0	177.6
122.5°	192.0	192.2	192.3	192.4	192.5	192.8	193.0	193.3	193.5	193.9	194.3
125°	208.7	208.8	208.9	208.9	209.0	209.2	209.5	209.7	209.9	210.1	210.4
127.5°	224.0	224.2	224.5	224.6	224.8	225.1	225.4	225.7	226.0	226.3	226.6
130°	240.5	240.8	241.1	241.3	241.4	241.6	241.7	241.9	242.1	242.3	242.4
132.5°	256.1	256.3	256.6	256.7	256.9	257.3	257.7	258.1	258.5	258.4	258.3
135°	272.5	272.7	273.0	273.1	273.1	273.2	273.3	273.4	273.5	273.3	273.2
137.5°	287.3	287.6	287.9	288.1	288.1	288.2	288.3	288.4	288.5	288.3	288.2
140°	302.7	303.0	303.3	303.5	303.5	303.5	303.5	303.5	303.5	303.1	302.7
142.5°	316.6	316.9	317.2	317.4	317.4	317.3	317.2	317.1	317.0	316.8	316.6
145°	330.5	330.8	331.1	331.3	331.3	331.2	331.1	331.1	331.0	330.5	330.0
147.5°	343.0	343.3	343.6	343.8	343.7	343.6	343.4	343.3	343.1	342.8	342.5
150°	355.0	355.2	355.5	355.6	355.5	355.2	355.0	354.7	354.5	354.2	353.9
152.5°	366.6	366.9	367.2	367.4	367.2	366.9	366.6	366.2	365.9	365.5	365.1
155°	376.4	376.6	376.9	377.0	376.8	376.4	376.0	375.6	375.2	375.0	374.7
157.5°	385.7	386.0	386.4	386.6	386.3	385.8	385.2	384.7	384.1	383.9	383.8
160°	393.7	394.0	394.3	394.5	394.3	393.8	393.3	392.9	392.4	392.3	392.2
162.5°	401.0	401.4	401.8	402.0	401.7	401.2	400.6	400.1	399.5	399.4	399.3
165°	407.1	407.5	407.9	408.1	407.8	407.3	406.7	406.2	405.6	405.6	405.6
167.5°	412.4	412.8	413.2	413.4	413.1	412.6	412.0	411.5	410.9	410.9	410.9
170°	416.5	417.0	417.5	417.7	417.4	416.9	416.3	415.8	415.2	415.3	415.4
172.5°	419.7	420.2	420.7	420.9	420.6	420.1	419.5	419.0	418.4	418.5	418.6
175°	421.9	422.4	422.9	423.1	422.8	422.3	421.7	421.2	420.6	420.8	420.9
177.5°	422.9	423.4	423.9	424.1	423.9	423.4	422.9	422.5	422.0	422.2	422.3
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1

TEST NUMBER: P997875

CATALOG NUMBER: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	2059.4	2051.7	2047.1	2050.2	2040.9	2017.8	2017.8	2025.5	2016.2	2007.0	1993.1
5°	2116.5	2101.1	2091.8	2090.3	2068.7	2031.7	2023.9	2016.2	1996.2	1974.6	1951.4
7.5°	2172.0	2144.3	2128.8	2118.0	2087.2	2039.4	2019.3	2002.3	1970.0	1937.6	1908.2
10°	2218.3	2178.2	2159.7	2142.7	2102.6	2042.5	2010.1	1979.2	1937.6	1895.9	1858.9
12.5°	2255.3	2209.1	2185.9	2161.2	2111.9	2033.2	1993.1	1943.7	1902.1	1846.5	1809.5
15°	2317.0	2221.4	2199.8	2176.7	2125.8	2017.8	1968.4	1912.9	1855.8	1781.8	1741.6
17.5°	2366.4	2238.4	2236.8	2187.5	2121.1	2011.6	1936.0	1863.5	1801.8	1727.8	1664.5
20°	2395.7	2264.6	2239.9	2189.0	2105.7	1970.0	1891.3	1811.1	1744.7	1655.3	1592.0
22.5°	2420.4	2301.6	2236.8	2175.1	2073.3	1956.1	1840.4	1764.8	1673.8	1576.6	1516.4
25°	2429.7	2309.3	2241.5	2170.5	2050.2	1916.0	1784.8	1703.1	1601.3	1513.3	1431.6
27.5°	2431.2	2307.8	2224.5	2150.4	2017.8	1863.5	1729.3	1642.9	1530.3	1428.5	1346.7
30°	2415.8	2290.8	2215.2	2135.0	1986.9	1815.7	1661.4	1565.8	1445.5	1343.6	1258.8
32.5°	2369.5	2256.9	2195.2	2107.2	1946.8	1749.4	1596.6	1490.2	1363.7	1263.4	1181.7
35°	2292.4	2215.2	2147.4	2065.6	1894.4	1687.6	1531.8	1406.9	1278.8	1183.2	1106.1
37.5°	2196.7	2155.1	2091.8	2011.6	1834.2	1632.1	1459.3	1320.5	1192.5	1099.9	1024.3
40°	2067.1	2077.9	2016.2	1943.7	1763.2	1556.5	1365.2	1232.6	1112.2	1025.9	951.8
42.5°	1926.8	1971.5	1936.0	1866.6	1684.6	1473.2	1295.8	1149.3	1032.0	942.6	880.8
45°	1775.6	1852.7	1831.1	1780.2	1602.8	1385.3	1197.1	1055.2	951.8	865.4	811.4
47.5°	1610.5	1720.0	1720.0	1683.0	1511.8	1297.4	1112.2	967.2	865.4	803.7	751.3
50°	1442.4	1565.8	1585.8	1561.2	1410.0	1197.1	1008.9	877.8	789.8	729.7	691.1
52.5°	1266.5	1410.0	1447.0	1434.7	1302.0	1101.4	924.0	796.0	715.8	663.3	629.4
55°	1098.4	1265.0	1305.1	1309.7	1186.3	996.5	829.9	717.3	640.2	604.7	575.4
57.5°	939.5	1099.9	1144.6	1152.4	1069.1	900.9	742.0	643.3	573.9	544.6	521.4
60°	803.7	937.9	996.5	1013.5	941.0	789.8	660.3	564.6	512.2	484.4	462.8
62.5°	692.6	800.6	862.3	867.0	834.6	692.6	575.4	495.2	450.5	425.8	415.0
65°	584.7	681.8	718.9	737.4	711.2	600.1	496.7	430.4	394.9	373.3	362.5
67.5°	498.3	560.0	590.8	615.5	589.3	506.0	422.7	368.7	342.5	320.9	314.7
70°	408.8	459.7	482.8	507.5	484.4	421.1	361.0	311.6	288.5	271.5	263.8
72.5°	327.0	367.1	388.7	404.2	390.3	337.8	288.5	254.5	237.6	225.2	220.6
75°	259.2	286.9	299.3	310.1	303.9	263.8	232.9	205.2	189.7	178.9	175.9
77.5°	197.5	217.5	231.4	234.5	226.8	200.5	174.3	157.3	145.0	138.8	135.8
80°	140.4	152.7	160.4	165.1	157.3	146.6	128.0	115.7	104.9	97.2	95.6
82.5°	94.1	100.3	106.4	104.9	101.8	92.6	81.8	75.6	71.0	64.8	64.8
85°	54.0	55.5	58.6	60.2	58.6	52.4	46.3	43.2	40.1	35.5	35.5
87.5°	23.1	24.7	24.7	26.2	23.1	23.1	20.1	17.0	17.0	15.4	13.9
90°	7.2	5.5	4.6	4.1	3.2	2.3	1.3	0.4	1.3	2.3	3.2
92.5°	10.8	10.7	10.7	10.4	9.8	9.1	8.5	7.9	8.5	9.1	9.8
95°	22.3	22.2	22.1	21.7	20.9	20.2	19.4	18.6	19.4	20.2	20.9
97.5°	34.8	34.5	34.3	33.9	33.2	32.5	31.8	31.1	31.8	32.5	33.2
100°	48.6	48.3	48.2	47.9	47.2	46.6	45.9	45.3	45.9	46.6	47.2
102.5°	63.0	62.7	62.5	62.3	61.8	61.3	60.8	60.3	60.8	61.3	61.8
105°	78.0	77.9	77.8	77.7	77.5	77.2	77.0	76.8	77.0	77.2	77.5
107.5°	94.6	94.6	94.6	94.4	94.1	93.8	93.5	93.2	93.5	93.8	94.1
110°	111.0	111.0	111.0	110.8	110.3	109.8	109.4	108.9	109.4	109.8	110.3

TEST NUMBER: P997875

CATALOG NUMBER: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	128.1	128.2	128.2	128.0	127.5	127.0	126.5	126.0	126.5	127.0	127.5
115°	144.7	144.8	144.9	144.7	144.2	143.7	143.3	142.8	143.3	143.7	144.2
117.5°	161.8	162.2	162.4	162.1	161.5	160.8	160.2	159.6	160.2	160.8	161.5
120°	178.3	178.9	179.2	178.9	178.3	177.6	177.0	176.4	177.0	177.6	178.3
122.5°	194.7	195.1	195.3	194.9	194.1	193.3	192.5	191.7	192.5	193.3	194.1
125°	210.6	210.9	211.0	210.6	209.9	209.2	208.5	207.8	208.5	209.2	209.9
127.5°	226.9	227.2	227.4	227.0	226.1	225.2	224.4	223.5	224.4	225.2	226.1
130°	242.6	242.7	242.8	242.3	241.2	240.2	239.1	238.1	239.1	240.2	241.2
132.5°	258.2	258.1	258.1	257.7	256.9	256.2	255.4	254.6	255.4	256.2	256.9
135°	273.0	272.9	272.8	272.4	271.5	270.6	269.7	268.8	269.7	270.6	271.5
137.5°	288.0	287.9	287.8	287.4	286.7	286.0	285.2	284.5	285.2	286.0	286.7
140°	302.3	301.9	301.7	301.3	300.6	299.9	299.2	298.5	299.2	299.9	300.6
142.5°	316.3	316.1	316.0	315.6	314.9	314.2	313.4	312.7	313.4	314.2	314.9
145°	329.5	329.0	328.8	328.5	328.0	327.4	326.9	326.3	326.9	327.4	328.0
147.5°	342.2	341.9	341.7	341.3	340.6	339.9	339.1	338.4	339.1	339.9	340.6
150°	353.6	353.3	353.1	352.9	352.4	351.9	351.4	350.9	351.4	351.9	352.4
152.5°	364.8	364.4	364.2	364.0	363.5	363.0	362.5	362.0	362.5	363.0	363.5
155°	374.5	374.2	374.1	374.0	373.8	373.5	373.3	373.1	373.3	373.5	373.8
157.5°	383.6	383.5	383.4	383.3	383.2	383.0	382.9	382.7	382.9	383.0	383.2
160°	392.1	392.0	392.0	391.9	391.8	391.6	391.5	391.3	391.5	391.6	391.8
162.5°	399.2	399.1	399.1	399.1	399.1	399.1	399.1	399.1	399.1	399.1	399.1
165°	405.6	405.6	405.6	405.6	405.7	405.8	405.8	405.9	405.8	405.8	405.7
167.5°	410.9	410.9	410.9	411.0	411.3	411.5	411.8	412.0	411.8	411.5	411.3
170°	415.5	415.6	415.6	415.7	415.9	416.2	416.4	416.6	416.4	416.2	415.9
172.5°	418.7	418.8	418.8	418.9	419.1	419.4	419.6	419.8	419.6	419.4	419.1
175°	421.1	421.2	421.3	421.4	421.6	421.9	422.1	422.3	422.1	421.9	421.6
177.5°	422.5	422.6	422.7	422.8	423.1	423.3	423.6	423.8	423.6	423.3	423.1
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1

TEST NUMBER: P997875

CATALOG NUMBER: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	1985.4	1993.1	1991.5	1976.1	1959.2	1945.3	1919.0	1922.1	1912.9	1914.4	1923.7
5°	1936.0	1936.0	1929.8	1908.2	1880.5	1865.1	1835.7	1828.0	1809.5	1808.0	1806.4
7.5°	1883.6	1875.9	1868.1	1837.3	1803.3	1778.7	1738.6	1729.3	1710.8	1698.4	1692.3
10°	1821.9	1811.1	1795.6	1760.2	1718.5	1687.6	1646.0	1633.7	1598.2	1582.7	1573.5
12.5°	1754.0	1747.8	1723.1	1693.8	1625.9	1592.0	1531.8	1544.2	1508.7	1477.9	1473.2
15°	1686.1	1663.0	1649.1	1601.3	1519.5	1504.1	1456.3	1431.6	1399.2	1374.5	1374.5
17.5°	1619.8	1584.3	1553.4	1502.5	1442.4	1399.2	1363.7	1351.4	1311.2	1286.6	1281.9
20°	1531.8	1491.7	1484.0	1411.5	1369.9	1322.0	1288.1	1257.3	1227.9	1217.1	1209.4
22.5°	1448.5	1402.3	1389.9	1328.2	1286.6	1238.7	1204.8	1183.2	1161.6	1153.9	1140.0
25°	1359.1	1331.3	1312.8	1246.5	1200.2	1155.4	1132.3	1116.9	1096.8	1095.3	1086.0
27.5°	1272.7	1246.5	1227.9	1164.7	1130.8	1089.1	1070.6	1053.6	1042.8	1038.2	1033.6
30°	1198.6	1169.3	1147.7	1101.4	1059.8	1025.9	1010.4	999.6	993.5	985.7	984.2
32.5°	1116.9	1099.9	1070.6	1035.1	1002.7	970.3	961.1	953.4	944.1	941.0	939.5
35°	1047.5	1024.3	1005.8	965.7	951.8	924.0	913.2	907.1	894.7	891.6	888.6
37.5°	979.6	958.0	937.9	913.2	887.0	871.6	865.4	856.2	850.0	851.5	848.5
40°	911.7	894.7	879.3	853.1	837.7	829.9	817.6	808.3	805.3	806.8	805.3
42.5°	845.4	829.9	820.7	800.6	785.2	777.5	769.8	760.5	765.1	765.1	769.8
45°	785.2	771.3	765.1	749.7	740.5	728.1	720.4	718.9	725.0	723.5	723.5
47.5°	723.5	718.9	711.2	697.3	684.9	677.2	675.7	675.7	681.8	684.9	683.4
50°	675.7	666.4	657.2	646.4	637.1	634.0	629.4	632.5	638.7	638.7	641.7
52.5°	615.5	609.3	606.3	597.0	590.8	590.8	590.8	592.4	597.0	601.6	600.1
55°	563.1	558.4	555.4	550.7	543.0	544.6	543.0	546.1	550.7	555.4	558.4
57.5°	507.5	506.0	502.9	495.2	495.2	493.6	498.3	499.8	507.5	510.6	515.2
60°	458.2	453.5	453.5	447.4	447.4	447.4	452.0	456.6	462.8	464.3	467.4
62.5°	405.7	405.7	404.2	399.5	399.5	404.2	405.7	411.9	415.0	415.0	419.6
65°	356.4	354.8	353.3	354.8	356.4	356.4	361.0	364.1	367.1	368.7	370.2
67.5°	307.0	305.4	308.5	307.0	310.1	316.2	314.7	319.3	324.0	324.0	325.5
70°	260.7	263.8	262.2	265.3	263.8	266.9	271.5	273.0	273.0	274.6	279.2
72.5°	217.5	217.5	217.5	216.0	217.5	220.6	223.7	225.2	228.3	229.9	234.5
75°	175.9	175.9	172.8	175.9	175.9	178.9	182.0	182.0	182.0	185.1	189.7
77.5°	132.7	134.2	132.7	135.8	135.8	137.3	140.4	138.8	141.9	143.5	145.0
80°	97.2	95.6	95.6	95.6	97.2	97.2	100.3	101.8	101.8	106.4	103.4
82.5°	61.7	63.2	61.7	63.2	63.2	64.8	63.2	64.8	66.3	69.4	67.9
85°	35.5	33.9	33.9	35.5	33.9	33.9	35.5	33.9	35.5	33.9	35.5
87.5°	13.9	12.3	12.3	12.3	12.3	10.8	10.8	9.3	9.3	9.3	7.7
90°	4.1	4.6	5.5	7.2	9.0	10.7	12.5	12.3	12.2	12.0	11.9
92.5°	10.4	10.7	10.7	10.8	10.9	11.0	11.1	11.2	11.2	11.3	11.4
95°	21.7	22.1	22.2	22.3	22.5	22.6	22.8	22.8	22.8	22.8	22.8
97.5°	33.9	34.3	34.5	34.8	35.1	35.4	35.7	35.7	35.7	35.7	35.7
100°	47.9	48.2	48.3	48.6	48.8	49.1	49.3	49.3	49.3	49.3	49.3
102.5°	62.3	62.5	62.7	63.0	63.3	63.6	63.9	64.0	64.1	64.2	64.3
105°	77.7	77.8	77.9	78.0	78.2	78.3	78.5	78.7	78.9	79.0	79.2
107.5°	94.4	94.6	94.6	94.6	94.6	94.6	94.6	94.7	94.8	94.9	95.0
110°	110.8	111.0	111.0	111.0	111.0	111.0	111.0	111.0	111.0	111.0	111.0

TEST NUMBER: P997875

CATALOG NUMBER: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	128.0	128.2	128.2	128.1	128.0	127.9	127.8	127.6	127.3	127.1	126.8
115°	144.7	144.9	144.8	144.7	144.5	144.4	144.2	144.1	144.1	144.0	143.9
117.5°	162.1	162.4	162.2	161.8	161.5	161.1	160.7	160.5	160.2	160.0	159.7
120°	178.9	179.2	178.9	178.3	177.6	177.0	176.4	176.4	176.4	176.4	176.4
122.5°	194.9	195.3	195.1	194.7	194.3	193.9	193.5	193.3	193.0	192.8	192.5
125°	210.6	211.0	210.9	210.6	210.4	210.1	209.9	209.7	209.5	209.2	209.0
127.5°	227.0	227.4	227.2	226.9	226.6	226.3	226.0	225.7	225.4	225.1	224.8
130°	242.3	242.8	242.7	242.6	242.4	242.3	242.1	241.9	241.7	241.6	241.4
132.5°	257.7	258.1	258.1	258.2	258.3	258.4	258.5	258.1	257.7	257.3	256.9
135°	272.4	272.8	272.9	273.0	273.2	273.3	273.5	273.4	273.3	273.2	273.1
137.5°	287.4	287.8	287.9	288.0	288.2	288.3	288.5	288.4	288.3	288.2	288.1
140°	301.3	301.7	301.9	302.3	302.7	303.1	303.5	303.5	303.5	303.5	303.5
142.5°	315.6	316.0	316.1	316.3	316.6	316.8	317.0	317.1	317.2	317.3	317.4
145°	328.5	328.8	329.0	329.5	330.0	330.5	331.0	331.1	331.1	331.2	331.3
147.5°	341.3	341.7	341.9	342.2	342.5	342.8	343.1	343.3	343.4	343.6	343.7
150°	352.9	353.1	353.3	353.6	353.9	354.2	354.5	354.7	355.0	355.2	355.5
152.5°	364.0	364.2	364.4	364.8	365.1	365.5	365.9	366.2	366.6	366.9	367.2
155°	374.0	374.1	374.2	374.5	374.7	375.0	375.2	375.6	376.0	376.4	376.8
157.5°	383.3	383.4	383.5	383.6	383.8	383.9	384.1	384.7	385.2	385.8	386.3
160°	391.9	392.0	392.0	392.1	392.2	392.3	392.4	392.9	393.3	393.8	394.3
162.5°	399.1	399.1	399.1	399.2	399.3	399.4	399.5	400.1	400.6	401.2	401.7
165°	405.6	405.6	405.6	405.6	405.6	405.6	405.6	406.2	406.7	407.3	407.8
167.5°	411.0	410.9	410.9	410.9	410.9	410.9	410.9	411.5	412.0	412.6	413.1
170°	415.7	415.6	415.6	415.5	415.4	415.3	415.2	415.8	416.3	416.9	417.4
172.5°	418.9	418.8	418.8	418.7	418.6	418.5	418.4	419.0	419.5	420.1	420.6
175°	421.4	421.3	421.2	421.1	420.9	420.8	420.6	421.2	421.7	422.3	422.8
177.5°	422.8	422.7	422.6	422.5	422.3	422.2	422.0	422.5	422.9	423.4	423.9
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1

TEST NUMBER: P997875

CATALOG NUMBER: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	1912.9	1917.5	1906.7	1903.6	1906.7	1895.9	1899.0	1902.1	1902.1	1906.7	1909.8
5°	1801.8	1795.6	1784.8	1781.8	1778.7	1783.3	1780.2	1784.8	1786.4	1797.2	1798.7
7.5°	1692.3	1683.0	1673.8	1664.5	1661.4	1653.7	1661.4	1661.4	1672.2	1669.1	1676.9
10°	1562.7	1561.2	1548.8	1544.2	1538.0	1525.7	1542.6	1538.0	1545.7	1559.6	1562.7
12.5°	1467.1	1450.1	1457.8	1436.2	1443.9	1431.6	1433.1	1433.1	1445.5	1447.0	1443.9
15°	1376.0	1362.2	1342.1	1332.8	1328.2	1322.0	1342.1	1343.6	1334.4	1356.0	1348.3
17.5°	1283.5	1283.5	1265.0	1260.3	1248.0	1254.2	1251.1	1252.6	1249.5	1265.0	1272.7
20°	1203.3	1195.5	1189.4	1190.9	1175.5	1172.4	1169.3	1172.4	1183.2	1194.0	1197.1
22.5°	1138.5	1133.8	1118.4	1121.5	1109.2	1113.8	1110.7	1118.4	1120.0	1120.0	1130.8
25°	1076.8	1070.6	1072.1	1066.0	1061.3	1061.3	1056.7	1061.3	1067.5	1070.6	1072.1
27.5°	1030.5	1025.9	1018.1	1013.5	1016.6	1008.9	1015.1	1019.7	1019.7	1016.6	1019.7
30°	974.9	978.0	978.0	962.6	968.8	965.7	970.3	973.4	973.4	974.9	971.9
32.5°	937.9	928.7	927.1	925.6	925.6	919.4	919.4	924.0	925.6	927.1	931.8
35°	888.6	888.6	880.8	885.5	879.3	880.8	879.3	880.8	883.9	879.3	883.9
37.5°	843.8	845.4	842.3	845.4	846.9	843.8	840.7	846.9	843.8	843.8	840.7
40°	805.3	803.7	805.3	805.3	805.3	806.8	803.7	803.7	803.7	800.6	797.5
42.5°	772.9	763.6	766.7	768.2	763.6	763.6	765.1	763.6	768.2	759.0	759.0
45°	726.6	723.5	725.0	725.0	728.1	723.5	726.6	728.1	723.5	722.0	718.9
47.5°	684.9	688.0	684.9	688.0	688.0	691.1	684.9	686.5	688.0	681.8	677.2
50°	643.3	643.3	647.9	646.4	647.9	644.8	644.8	643.3	644.8	641.7	637.1
52.5°	604.7	600.1	607.8	606.3	604.7	603.2	601.6	603.2	600.1	597.0	597.0
55°	556.9	556.9	561.5	563.1	563.1	560.0	556.9	558.4	556.9	555.4	553.8
57.5°	518.3	512.2	515.2	516.8	516.8	512.2	515.2	512.2	512.2	513.7	509.1
60°	469.0	469.0	465.9	470.5	470.5	467.4	467.4	469.0	465.9	464.3	462.8
62.5°	416.5	418.1	422.7	424.2	425.8	422.7	419.6	421.1	421.1	416.5	418.1
65°	371.8	374.9	381.0	379.5	376.4	377.9	374.9	376.4	371.8	373.3	368.7
67.5°	328.6	327.0	328.6	328.6	331.7	330.1	327.0	327.0	325.5	330.1	325.5
70°	282.3	282.3	282.3	282.3	283.8	285.4	282.3	279.2	280.8	277.7	276.1
72.5°	234.5	236.0	234.5	237.6	232.9	236.0	236.0	234.5	232.9	232.9	232.9
75°	189.7	192.8	188.2	189.7	188.2	191.3	189.7	189.7	186.7	185.1	186.7
77.5°	145.0	146.6	143.5	145.0	143.5	145.0	145.0	143.5	143.5	143.5	143.5
80°	103.4	104.9	103.4	101.8	100.3	103.4	100.3	101.8	103.4	101.8	104.9
82.5°	66.3	66.3	64.8	66.3	63.2	63.2	64.8	64.8	63.2	66.3	63.2
85°	32.4	32.4	35.5	32.4	30.9	30.9	30.9	32.4	30.9	33.9	32.4
87.5°	7.7	6.2	7.7	7.7	6.2	6.2	7.7	6.2	7.7	9.3	6.2
90°	11.8	11.8	11.9	12.0	12.0	12.1	12.0	12.0	11.9	11.8	11.8
92.5°	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4
95°	22.8	22.7	22.6	22.4	22.3	22.1	22.3	22.4	22.6	22.7	22.8
97.5°	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7
100°	49.3	49.3	49.2	49.1	49.0	48.9	49.0	49.1	49.2	49.3	49.3
102.5°	64.3	64.3	64.2	64.1	64.0	63.9	64.0	64.1	64.2	64.3	64.3
105°	79.3	79.3	79.3	79.3	79.3	79.3	79.3	79.3	79.3	79.3	79.3
107.5°	95.0	94.8	94.4	94.0	93.6	93.2	93.6	94.0	94.4	94.8	95.0
110°	111.0	110.9	110.7	110.4	110.2	110.0	110.2	110.4	110.7	110.9	111.0

TEST NUMBER: P997875

CATALOG NUMBER: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	126.7	126.6	126.5	126.3	126.2	126.0	126.2	126.3	126.5	126.6	126.7
115°	143.9	143.8	143.5	143.3	143.0	142.8	143.0	143.3	143.5	143.8	143.9
117.5°	159.6	159.5	159.2	159.0	158.7	158.5	158.7	159.0	159.2	159.5	159.6
120°	176.4	176.3	176.0	175.8	175.5	175.3	175.5	175.8	176.0	176.3	176.4
122.5°	192.4	192.3	192.2	192.0	191.9	191.7	191.9	192.0	192.2	192.3	192.4
125°	208.9	208.9	208.8	208.7	208.6	208.5	208.6	208.7	208.8	208.9	208.9
127.5°	224.6	224.5	224.2	224.0	223.7	223.5	223.7	224.0	224.2	224.5	224.6
130°	241.3	241.1	240.8	240.5	240.2	239.9	240.2	240.5	240.8	241.1	241.3
132.5°	256.7	256.6	256.3	256.1	255.8	255.6	255.8	256.1	256.3	256.6	256.7
135°	273.1	273.0	272.7	272.5	272.2	272.0	272.2	272.5	272.7	273.0	273.1
137.5°	288.1	287.9	287.6	287.3	287.0	286.7	287.0	287.3	287.6	287.9	288.1
140°	303.5	303.3	303.0	302.7	302.3	302.0	302.3	302.7	303.0	303.3	303.5
142.5°	317.4	317.2	316.9	316.6	316.3	316.0	316.3	316.6	316.9	317.2	317.4
145°	331.3	331.1	330.8	330.5	330.2	329.9	330.2	330.5	330.8	331.1	331.3
147.5°	343.8	343.6	343.3	343.0	342.7	342.4	342.7	343.0	343.3	343.6	343.8
150°	355.6	355.5	355.2	355.0	354.7	354.5	354.7	355.0	355.2	355.5	355.6
152.5°	367.4	367.2	366.9	366.6	366.2	365.9	366.2	366.6	366.9	367.2	367.4
155°	377.0	376.9	376.6	376.4	376.1	375.9	376.1	376.4	376.6	376.9	377.0
157.5°	386.6	386.4	386.0	385.7	385.3	384.9	385.3	385.7	386.0	386.4	386.6
160°	394.5	394.3	394.0	393.7	393.4	393.1	393.4	393.7	394.0	394.3	394.5
162.5°	402.0	401.8	401.4	401.0	400.6	400.2	400.6	401.0	401.4	401.8	402.0
165°	408.1	407.9	407.5	407.1	406.7	406.3	406.7	407.1	407.5	407.9	408.1
167.5°	413.4	413.2	412.8	412.4	412.0	411.6	412.0	412.4	412.8	413.2	413.4
170°	417.7	417.5	417.0	416.5	416.1	415.6	416.1	416.5	417.0	417.5	417.7
172.5°	420.9	420.7	420.2	419.7	419.3	418.8	419.3	419.7	420.2	420.7	420.9
175°	423.1	422.9	422.4	421.9	421.4	420.9	421.4	421.9	422.4	422.9	423.1
177.5°	424.1	423.9	423.4	422.9	422.5	422.0	422.5	422.9	423.4	423.9	424.1
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1

TEST NUMBER: P997875

CATALOG NUMBER: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	1905.2	1917.5	1912.9	1895.9	1916.0	1916.0	1929.8	1929.8	1946.8	1953.0	1962.2
5°	1797.2	1806.4	1814.1	1806.4	1820.3	1841.9	1854.3	1865.1	1888.2	1897.4	1911.3
7.5°	1681.5	1698.4	1706.2	1706.2	1729.3	1754.0	1778.7	1794.1	1826.5	1838.8	1852.7
10°	1568.9	1588.9	1604.3	1602.8	1641.4	1656.8	1687.6	1723.1	1755.5	1774.0	1794.1
12.5°	1450.1	1460.9	1482.5	1513.3	1522.6	1550.4	1585.8	1630.6	1689.2	1706.2	1735.5
15°	1351.4	1380.7	1397.6	1411.5	1433.1	1459.3	1497.9	1541.1	1599.7	1636.7	1667.6
17.5°	1268.1	1306.6	1317.4	1314.3	1342.1	1382.2	1426.9	1459.3	1511.8	1556.5	1585.8
20°	1200.2	1215.6	1234.1	1241.8	1263.4	1306.6	1349.8	1386.8	1430.0	1465.5	1499.4
22.5°	1132.3	1144.6	1160.1	1173.9	1190.9	1215.6	1257.3	1303.5	1345.2	1379.1	1417.7
25°	1076.8	1084.5	1098.4	1109.2	1127.7	1144.6	1173.9	1224.9	1274.2	1294.3	1328.2
27.5°	1022.8	1028.9	1038.2	1050.5	1059.8	1076.8	1103.0	1144.6	1195.5	1215.6	1261.9
30°	974.9	979.6	988.8	995.0	999.6	1019.7	1039.7	1072.1	1110.7	1138.5	1172.4
32.5°	930.2	934.8	944.1	945.6	951.8	962.6	981.1	1010.4	1044.4	1067.5	1096.8
35°	880.8	883.9	893.2	896.3	900.9	910.2	924.0	945.6	976.5	993.5	1019.7
37.5°	842.3	840.7	846.9	851.5	857.7	862.3	867.0	888.6	911.7	927.1	947.2
40°	800.6	797.5	799.1	805.3	808.3	814.5	814.5	836.1	851.5	863.9	879.3
42.5°	759.0	757.4	754.4	757.4	760.5	762.1	763.6	779.0	794.5	805.3	822.2
45°	717.3	715.8	712.7	714.2	714.2	717.3	722.0	728.1	738.9	748.2	757.4
47.5°	678.8	675.7	671.0	669.5	672.6	672.6	672.6	678.8	689.6	692.6	701.9
50°	638.7	634.0	627.9	624.8	624.8	623.2	626.3	627.9	637.1	640.2	647.9
52.5°	595.5	592.4	586.2	580.0	581.6	578.5	580.0	581.6	584.7	589.3	593.9
55°	552.3	546.1	541.5	539.9	535.3	535.3	530.7	536.8	535.3	536.8	543.0
57.5°	510.6	504.4	496.7	493.6	489.0	487.5	484.4	482.8	484.4	489.0	493.6
60°	461.2	458.2	453.5	448.9	445.8	441.2	438.1	438.1	436.6	436.6	438.1
62.5°	413.4	411.9	405.7	404.2	401.1	398.0	393.4	390.3	390.3	393.4	394.9
65°	367.1	365.6	361.0	359.4	351.7	348.6	347.1	345.6	342.5	342.5	342.5
67.5°	324.0	319.3	319.3	311.6	305.4	302.4	299.3	297.7	297.7	297.7	299.3
70°	276.1	276.1	271.5	266.9	260.7	262.2	257.6	253.0	253.0	249.9	251.5
72.5°	229.9	228.3	223.7	222.1	217.5	212.9	209.8	212.9	208.3	206.7	208.3
75°	185.1	183.6	180.5	177.4	178.9	174.3	169.7	168.1	168.1	165.1	165.1
77.5°	141.9	145.0	138.8	137.3	134.2	131.1	129.6	128.0	128.0	128.0	131.1
80°	98.7	100.3	100.3	97.2	98.7	94.1	94.1	94.1	89.5	91.0	92.6
82.5°	63.2	63.2	61.7	63.2	61.7	61.7	60.2	60.2	58.6	58.6	60.2
85°	35.5	33.9	32.4	35.5	33.9	33.9	32.4	32.4	32.4	32.4	32.4
87.5°	7.7	9.3	9.3	9.3	9.3	10.8	10.8	10.8	12.3	12.3	12.3
90°	11.9	12.0	12.2	12.3	12.5	10.7	9.0	7.2	5.5	4.6	4.1
92.5°	11.4	11.3	11.2	11.2	11.1	11.0	10.9	10.8	10.7	10.7	10.4
95°	22.8	22.8	22.8	22.8	22.8	22.6	22.5	22.3	22.2	22.1	21.7
97.5°	35.7	35.7	35.7	35.7	35.7	35.4	35.1	34.8	34.5	34.3	33.9
100°	49.3	49.3	49.3	49.3	49.3	49.1	48.8	48.6	48.3	48.2	47.9
102.5°	64.3	64.2	64.1	64.0	63.9	63.6	63.3	63.0	62.7	62.5	62.3
105°	79.2	79.0	78.9	78.7	78.5	78.3	78.2	78.0	77.9	77.8	77.7
107.5°	95.0	94.9	94.8	94.7	94.6	94.6	94.6	94.6	94.6	94.6	94.4
110°	111.0	111.0	111.0	111.0	111.0	111.0	111.0	111.0	111.0	111.0	110.8

TEST NUMBER: P997875

CATALOG NUMBER: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	126.8	127.1	127.3	127.6	127.8	127.9	128.0	128.1	128.2	128.2	128.0
115°	143.9	144.0	144.1	144.1	144.2	144.4	144.5	144.7	144.8	144.9	144.7
117.5°	159.7	160.0	160.2	160.5	160.7	161.1	161.5	161.8	162.2	162.4	162.1
120°	176.4	176.4	176.4	176.4	176.4	177.0	177.6	178.3	178.9	179.2	178.9
122.5°	192.5	192.8	193.0	193.3	193.5	193.9	194.3	194.7	195.1	195.3	194.9
125°	209.0	209.2	209.5	209.7	209.9	210.1	210.4	210.6	210.9	211.0	210.6
127.5°	224.8	225.1	225.4	225.7	226.0	226.3	226.6	226.9	227.2	227.4	227.0
130°	241.4	241.6	241.7	241.9	242.1	242.3	242.4	242.6	242.7	242.8	242.3
132.5°	256.9	257.3	257.7	258.1	258.5	258.4	258.3	258.2	258.1	258.1	257.7
135°	273.1	273.2	273.3	273.4	273.5	273.3	273.2	273.0	272.9	272.8	272.4
137.5°	288.1	288.2	288.3	288.4	288.5	288.3	288.2	288.0	287.9	287.8	287.4
140°	303.5	303.5	303.5	303.5	303.5	303.1	302.7	302.3	301.9	301.7	301.3
142.5°	317.4	317.3	317.2	317.1	317.0	316.8	316.6	316.3	316.1	316.0	315.6
145°	331.3	331.2	331.1	331.1	331.0	330.5	330.0	329.5	329.0	328.8	328.5
147.5°	343.7	343.6	343.4	343.3	343.1	342.8	342.5	342.2	341.9	341.7	341.3
150°	355.5	355.2	355.0	354.7	354.5	354.2	353.9	353.6	353.3	353.1	352.9
152.5°	367.2	366.9	366.6	366.2	365.9	365.5	365.1	364.8	364.4	364.2	364.0
155°	376.8	376.4	376.0	375.6	375.2	375.0	374.7	374.5	374.2	374.1	374.0
157.5°	386.3	385.8	385.2	384.7	384.1	383.9	383.8	383.6	383.5	383.4	383.3
160°	394.3	393.8	393.3	392.9	392.4	392.3	392.2	392.1	392.0	392.0	391.9
162.5°	401.7	401.2	400.6	400.1	399.5	399.4	399.3	399.2	399.1	399.1	399.1
165°	407.8	407.3	406.7	406.2	405.6	405.6	405.6	405.6	405.6	405.6	405.6
167.5°	413.1	412.6	412.0	411.5	410.9	410.9	410.9	410.9	410.9	410.9	411.0
170°	417.4	416.9	416.3	415.8	415.2	415.3	415.4	415.5	415.6	415.6	415.7
172.5°	420.6	420.1	419.5	419.0	418.4	418.5	418.6	418.7	418.8	418.8	418.9
175°	422.8	422.3	421.7	421.2	420.6	420.8	420.9	421.1	421.2	421.3	421.4
177.5°	423.9	423.4	422.9	422.5	422.0	422.2	422.3	422.5	422.6	422.7	422.8
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1

TEST NUMBER: P997875

CATALOG NUMBER: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	2007.0	2007.0	2007.0	2007.0
2.5°	1970.0	1970.0	1993.1	2017.8
5°	1926.8	1937.6	1974.6	2008.5
7.5°	1885.1	1903.6	1949.9	1993.1
10°	1834.2	1858.9	1916.0	1966.9
12.5°	1784.8	1808.0	1874.3	1931.4
15°	1715.4	1744.7	1815.7	1886.6
17.5°	1646.0	1675.3	1761.7	1845.0
20°	1564.2	1602.8	1700.0	1811.1
22.5°	1488.6	1536.5	1644.5	1733.9
25°	1405.3	1479.4	1579.7	1695.4
27.5°	1331.3	1405.3	1507.2	1624.4
30°	1248.0	1323.6	1428.5	1536.5
32.5°	1167.8	1237.2	1339.0	1471.7
35°	1084.5	1150.8	1249.5	1383.7
37.5°	1008.9	1073.7	1181.7	1305.1
40°	934.8	1002.7	1095.3	1218.7
42.5°	865.4	925.6	1008.9	1132.3
45°	802.2	845.4	922.5	1038.2
47.5°	735.8	774.4	845.4	961.1
50°	674.1	706.5	768.2	876.2
52.5°	614.0	641.7	698.8	785.2
55°	560.0	586.2	627.9	712.7
57.5°	504.4	524.5	564.6	632.5
60°	450.5	469.0	501.4	556.9
62.5°	396.5	411.9	442.7	487.5
65°	348.6	361.0	384.1	422.7
67.5°	302.4	310.1	328.6	359.4
70°	257.6	263.8	279.2	303.9
72.5°	209.8	216.0	232.9	249.9
75°	169.7	171.2	183.6	197.5
77.5°	132.7	131.1	140.4	151.2
80°	91.0	95.6	103.4	108.0
82.5°	61.7	63.2	66.3	69.4
85°	33.9	35.5	35.5	40.1
87.5°	13.9	15.4	15.4	17.0
90°	3.2	2.3	1.3	0.4
92.5°	9.8	9.1	8.5	7.9
95°	20.9	20.2	19.4	18.6
97.5°	33.2	32.5	31.8	31.1
100°	47.2	46.6	45.9	45.3
102.5°	61.8	61.3	60.8	60.3
105°	77.5	77.2	77.0	76.8
107.5°	94.1	93.8	93.5	93.2
110°	110.3	109.8	109.4	108.9



TEST NUMBER: P997875

CATALOG NUMBER: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	127.5	127.0	126.5	126.0
115°	144.2	143.7	143.3	142.8
117.5°	161.5	160.8	160.2	159.6
120°	178.3	177.6	177.0	176.4
122.5°	194.1	193.3	192.5	191.7
125°	209.9	209.2	208.5	207.8
127.5°	226.1	225.2	224.4	223.5
130°	241.2	240.2	239.1	238.1
132.5°	256.9	256.2	255.4	254.6
135°	271.5	270.6	269.7	268.8
137.5°	286.7	286.0	285.2	284.5
140°	300.6	299.9	299.2	298.5
142.5°	314.9	314.2	313.4	312.7
145°	328.0	327.4	326.9	326.3
147.5°	340.6	339.9	339.1	338.4
150°	352.4	351.9	351.4	350.9
152.5°	363.5	363.0	362.5	362.0
155°	373.8	373.5	373.3	373.1
157.5°	383.2	383.0	382.9	382.7
160°	391.8	391.6	391.5	391.3
162.5°	399.1	399.1	399.1	399.1
165°	405.7	405.8	405.8	405.9
167.5°	411.3	411.5	411.8	412.0
170°	415.9	416.2	416.4	416.6
172.5°	419.1	419.4	419.6	419.8
175°	421.6	421.9	422.1	422.3
177.5°	423.1	423.3	423.6	423.8
180°	423.1	423.1	423.1	423.1

TEST NUMBER: P997875

CATALOG NUMBER: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-A1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.23	21.37	20.90	22.05	22.84	17.73	18.86	18.39	19.54	20.33
	3H	21.06	22.08	21.75	22.77	23.60	19.09	20.11	19.77	20.80	21.62
	4H	21.25	22.20	21.95	22.90	23.74	19.57	20.52	20.27	21.22	22.06
	6H	21.30	22.19	22.02	22.90	23.75	19.89	20.77	20.60	21.48	22.33
	8H	21.29	22.13	22.02	22.86	23.72	19.98	20.82	20.70	21.55	22.40
	12H	21.26	22.06	21.99	22.79	23.67	20.03	20.83	20.76	21.55	22.43
4H	2H	20.31	21.26	21.01	21.96	22.80	18.20	19.16	18.91	19.86	20.70
	3H	21.31	22.11	22.03	22.85	23.70	19.69	20.48	20.41	21.22	22.08
	4H	21.60	22.32	22.33	23.06	23.95	20.23	20.95	20.97	21.70	22.58
	6H	21.74	22.37	22.50	23.13	24.03	20.63	21.25	21.38	22.02	22.91
	8H	21.75	22.33	22.50	23.09	24.00	20.74	21.33	21.50	22.09	22.99
	12H	21.72	22.24	22.50	23.03	23.94	20.81	21.33	21.59	22.12	23.03
8H	4H	21.63	22.21	22.38	22.97	23.88	20.40	20.98	21.15	21.74	22.65
	6H	21.82	22.30	22.60	23.10	24.01	20.84	21.32	21.63	22.13	23.03
	8H	21.85	22.27	22.65	23.08	24.00	20.99	21.42	21.79	22.23	23.15
	12H	21.84	22.22	22.64	23.01	24.00	21.10	21.47	21.90	22.27	23.25
12H	4H	21.60	22.12	22.37	22.90	23.82	20.38	20.90	21.16	21.69	22.60
	6H	21.80	22.22	22.59	23.03	23.95	20.84	21.27	21.64	22.08	23.00
	8H	21.84	22.22	22.64	23.01	24.00	21.01	21.39	21.81	22.18	23.17