

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997879

Luminaire Tested: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-D4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P997879
REPORT IS A COMBINATION OF REPORTS P983616 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-D4
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5356.5 lumens
Efficiency: N/A
Efficacy: 75.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997879

CATALOG NUMBER: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P997879

CATALOG NUMBER: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72
1	100	94	90	85	94	89	85	81	79	75	72	69	67	64	61	59	57
2	90	81	74	68	84	77	70	65	68	63	58	60	56	52	52	49	46
3	82	71	62	56	76	67	59	53	59	53	48	52	47	43	46	42	39
4	74	62	53	47	70	59	51	45	52	46	41	46	41	37	40	36	33
5	68	55	46	40	64	52	44	38	47	40	35	41	36	31	36	32	28
6	63	50	41	34	59	47	39	33	42	35	30	37	32	27	33	28	25
7	58	45	36	30	54	42	34	29	38	31	26	34	28	24	30	25	22
8	54	41	32	27	50	38	31	25	35	28	23	31	25	21	27	23	19
9	50	37	29	24	47	35	28	23	32	25	21	28	23	19	25	21	17
10	47	34	26	21	44	32	25	20	29	23	19	26	21	17	23	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16847	16847	16847
5°	16924	16128	16037
10°	16809	15569	15342
15°	16572	14992	14631
20°	16273	14385	13954
25°	15978	13805	13340
30°	15564	13214	12733
35°	15146	12644	12286
40°	14704	12153	11844
45°	14283	11705	11458
50°	13832	11295	11076
55°	13358	10856	10688
60°	12778	10401	10279
65°	12172	9879	9810
70°	11489	9316	9305
75°	10612	8755	8828
80°	9237	8169	8334
85°	7840	7620	7908

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14283 cd/sqm

TEST NUMBER: P997879

CATALOG NUMBER: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.9	1.9
10°-20°	289.4	5.4
20°-30°	438.5	8.2
30°-40°	533.9	10.0
40°-50°	574.5	10.7
50°-60°	557.9	10.4
60°-70°	487.2	9.1
70°-80°	375.0	7.0
80°-90°	252.3	4.7
90°-100°	248.5	4.6
100°-110°	380.9	7.1
110°-120°	351.0	6.6
120°-130°	266.5	5.0
130°-140°	196.3	3.7
140°-150°	136.8	2.6
150°-160°	93.9	1.8
160°-170°	55.3	1.0
170°-180°	18.0	0.3
0°-30°	828.7	15.5
0°-40°	1362.6	25.4
0°-60°	2495.0	46.6
0°-90°	3609.5	67.4
90°-120°	980.4	18.3
90°-150°	1579.9	29.5
90°-180°	1747.0	32.6
0°-180°	5356.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1064	1064	1064	1064	1064	
5°	1067	1063	1054	1063	1061	101
15°	1018	1021	1021	1035	1034	287
25°	926	936	950	969	973	426
35°	798	824	853	887	898	498
45°	654	696	750	798	813	505
55°	501	557	637	693	713	448
65°	342	418	509	572	592	340
75°	190	276	375	441	461	201
85°	56	151	250	315	336	59
90°	16	110	216	277	296	12
95°	25	116	317	289	295	23
105°	51	118	397	659	606	55
115°	83	120	314	596	685	82
125°	110	130	265	464	538	99
135°	127	151	227	360	418	99
145°	144	165	209	269	301	90
155°	163	176	203	230	239	75
165°	178	183	195	206	210	50
175°	185	185	187	189	189	18
180°	186	186	186	186	186	

TEST NUMBER: P997879

CATALOG NUMBER: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1064.3	1064.3	1064.3	1064.3	1064.3
2.5°	1072.0	1067.4	1056.6	1064.3	1061.2
5°	1067.4	1062.8	1053.5	1062.8	1061.2
7.5°	1059.7	1056.6	1048.9	1059.7	1058.1
10°	1050.4	1047.3	1042.7	1055.0	1053.5
12.5°	1035.0	1036.5	1033.5	1045.8	1044.2
15°	1018.0	1021.1	1021.1	1035.0	1033.5
17.5°	996.4	1002.6	1007.2	1021.1	1021.1
20°	974.8	982.6	988.7	1005.7	1005.7
22.5°	951.7	961.0	970.2	987.2	990.3
25°	925.5	936.3	950.2	968.7	973.3
27.5°	894.6	911.6	927.0	950.2	953.2
30°	863.8	883.8	903.9	928.6	933.2
32.5°	829.8	853.0	877.7	907.0	916.2
35°	797.5	823.7	853.0	886.9	897.7
37.5°	762.0	791.3	828.3	865.3	876.1
40°	726.5	760.4	802.1	842.2	856.1
42.5°	692.6	726.5	775.9	820.6	834.5
45°	654.0	695.7	749.6	797.5	812.9
47.5°	617.0	661.7	723.4	772.8	789.7
50°	578.4	626.2	695.7	748.1	765.1
52.5°	541.4	592.3	666.3	720.3	738.8
55°	501.3	556.8	637.0	692.6	712.6
57.5°	462.7	524.4	604.6	664.8	684.9
60°	421.1	487.4	575.3	634.0	655.5
62.5°	384.1	453.5	541.4	604.6	624.7
65°	342.4	418.0	509.0	572.3	592.3
67.5°	305.4	384.1	476.6	539.9	561.5
70°	265.3	345.5	441.1	507.5	526.0
72.5°	228.3	311.6	408.8	473.5	496.7
75°	189.7	276.1	374.8	441.1	461.2
77.5°	152.7	242.2	342.4	408.8	430.3
80°	115.7	209.8	310.0	374.8	396.4
82.5°	84.8	177.4	279.2	344.0	364.0
85°	55.5	151.2	249.9	314.7	336.3
87.5°	33.9	126.5	225.2	288.4	308.5
90°	15.8	109.8	215.7	276.9	295.6
92.5°	19.3	112.6	244.7	275.2	290.2
95°	24.8	115.5	317.3	288.8	295.2
97.5°	29.4	117.6	394.7	329.7	310.4
100°	38.3	117.5	436.2	422.5	356.1
102.5°	45.0	118.0	427.2	556.0	465.1
105°	51.3	118.1	397.2	659.4	605.9
107.5°	59.8	118.2	368.6	689.1	696.8
110°	66.9	118.6	347.1	670.0	726.5



TEST NUMBER: P997879

CATALOG NUMBER: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	74.7	120.0	328.5	636.2	715.0
115°	83.0	120.0	313.8	595.6	685.2
117.5°	89.9	121.6	300.3	557.8	646.4
120°	97.8	122.9	288.5	521.4	610.4
122.5°	105.3	126.0	277.8	491.9	570.0
125°	110.2	129.8	265.2	464.1	537.5
127.5°	115.6	134.8	254.9	437.4	504.7
130°	120.2	140.7	244.9	412.0	475.6
132.5°	124.5	146.4	235.3	386.0	447.4
135°	127.2	151.4	227.3	360.3	417.6
137.5°	131.1	155.8	219.6	334.6	387.1
140°	135.7	158.2	213.0	310.6	355.8
142.5°	140.4	161.4	209.9	288.6	326.1
145°	143.5	165.0	209.2	269.0	301.2
147.5°	148.5	167.8	208.1	252.1	276.5
150°	153.5	170.6	207.1	242.8	258.1
152.5°	158.5	173.5	205.3	236.2	247.8
155°	163.1	176.2	203.1	229.8	238.8
157.5°	167.1	178.3	201.0	223.7	231.0
160°	171.0	180.4	198.8	217.6	223.5
162.5°	174.9	182.0	197.1	211.9	216.3
165°	177.8	183.1	194.6	206.4	209.6
167.5°	180.3	184.2	192.4	201.4	203.1
170°	182.8	184.8	190.6	196.8	197.4
172.5°	184.2	185.2	188.5	192.6	192.8
175°	185.3	185.4	187.1	189.4	188.9
177.5°	186.0	185.6	185.6	187.1	186.0
180°	185.6	185.6	185.6	185.6	185.6

TEST NUMBER: P997879

CATALOG NUMBER: SA2XXDIP-B1005D330UB35-4F0-XX-W2A-D4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.46	17.57	17.24	18.39	19.38	19.53	20.65	20.31	21.46	22.46
	3H	17.93	18.95	18.72	19.77	20.79	22.14	23.15	22.93	23.97	25.00
	4H	18.42	19.38	19.23	20.21	21.24	23.40	24.36	24.21	25.19	26.23
	6H	18.71	19.61	19.54	20.45	21.49	24.71	25.60	25.53	26.44	27.49
	8H	18.78	19.64	19.61	20.49	21.54	25.37	26.23	26.20	27.09	28.14
	12H	18.80	19.62	19.64	20.47	21.55	26.11	26.93	26.95	27.78	28.85
4H	2H	17.53	18.50	18.34	19.33	20.36	19.89	20.85	20.70	21.68	22.71
	3H	19.26	20.08	20.08	20.94	21.99	22.70	23.52	23.52	24.38	25.43
	4H	19.89	20.65	20.73	21.50	22.58	24.12	24.88	24.96	25.74	26.81
	6H	20.32	20.98	21.17	21.87	22.94	25.60	26.27	26.46	27.15	28.23
	8H	20.43	21.06	21.29	21.94	23.03	26.37	26.99	27.22	27.87	28.96
	12H	20.49	21.06	21.37	21.96	23.06	27.21	27.78	28.09	28.68	29.77
8H	4H	20.70	21.32	21.56	22.20	23.30	24.29	24.91	25.14	25.79	26.88
	6H	21.34	21.87	22.23	22.79	23.88	25.93	26.45	26.81	27.37	28.46
	8H	21.57	22.04	22.46	22.95	24.06	26.82	27.29	27.71	28.20	29.31
	12H	21.72	22.14	22.61	23.04	24.20	27.83	28.25	28.72	29.15	30.31
12H	4H	20.91	21.48	21.79	22.38	23.48	24.27	24.84	25.15	25.74	26.84
	6H	21.68	22.15	22.57	23.07	24.17	25.95	26.43	26.85	27.34	28.45
	8H	22.00	22.42	22.90	23.32	24.48	26.90	27.32	27.79	28.22	29.38