

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997897

Luminaire Tested: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-D4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P997897
REPORT IS A COMBINATION OF REPORTS P983634 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-D4
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5128.4 lumens
Efficiency: N/A
Efficacy: 72.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997897

CATALOG NUMBER: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-D4

Luminous Intensity Polar Plot



TEST NUMBER: P997897

CATALOG NUMBER: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72
1	100	94	90	85	94	89	85	81	79	75	72	69	67	64	61	59	57
2	90	81	74	68	84	77	70	65	68	63	58	60	56	52	52	49	46
3	82	71	62	56	76	67	59	53	59	53	48	52	47	43	46	42	39
4	74	62	53	47	70	59	51	45	52	46	41	46	41	37	40	36	33
5	68	55	46	40	64	52	44	38	47	40	35	41	36	31	36	32	28
6	63	50	41	34	59	47	39	33	42	35	30	37	32	27	33	28	25
7	58	45	36	30	54	42	34	29	38	31	26	34	28	24	30	25	22
8	54	41	32	27	50	38	31	25	35	28	23	31	25	21	27	23	19
9	50	37	29	24	47	35	28	23	32	25	21	28	23	19	25	21	17
10	47	34	26	21	44	32	25	20	29	23	19	26	21	17	23	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16130	16130	16130
5°	16202	15441	15354
10°	16094	14906	14688
15°	15867	14353	14006
20°	15580	13772	13358
25°	15298	13216	12771
30°	14901	12651	12190
35°	14500	12105	11764
40°	14078	11634	11339
45°	13674	11207	10970
50°	13243	10813	10604
55°	12787	10395	10233
60°	12235	9958	9842
65°	11653	9457	9392
70°	11000	8921	8909
75°	10159	8383	8452
80°	8846	7821	7978
85°	7515	7294	7570

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13674 cd/sqm

TEST NUMBER: P997897

CATALOG NUMBER: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.6	1.9
10°-20°	277.0	5.4
20°-30°	419.8	8.2
30°-40°	511.2	10.0
40°-50°	550.0	10.7
50°-60°	534.1	10.4
60°-70°	466.4	9.1
70°-80°	359.0	7.0
80°-90°	241.6	4.7
90°-100°	237.9	4.6
100°-110°	364.7	7.1
110°-120°	336.0	6.6
120°-130°	255.1	5.0
130°-140°	187.9	3.7
140°-150°	131.0	2.6
150°-160°	89.9	1.8
160°-170°	52.9	1.0
170°-180°	17.2	0.3
0°-30°	793.4	15.5
0°-40°	1304.6	25.4
0°-60°	2388.7	46.6
0°-90°	3455.7	67.4
90°-120°	938.7	18.3
90°-150°	1512.7	29.5
90°-180°	1673.0	32.6
0°-180°	5128.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1019	1019	1019	1019	1019	
5°	1022	1018	1009	1018	1016	97
15°	975	978	978	991	989	275
25°	886	896	910	927	932	407
35°	764	789	817	849	860	477
45°	626	666	718	764	778	483
55°	480	533	610	663	682	429
65°	328	400	487	548	567	326
75°	182	264	359	422	442	192
85°	53	145	239	301	322	56
90°	15	105	206	265	283	11
95°	24	111	304	276	283	22
105°	49	113	380	631	580	53
115°	79	115	300	570	656	78
125°	106	124	254	444	515	94
135°	122	145	218	345	400	95
145°	137	158	200	258	288	87
155°	156	169	194	220	229	72
165°	170	175	186	198	201	48
175°	177	178	179	181	181	17
180°	178	178	178	178	178	

TEST NUMBER: P997897

CATALOG NUMBER: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1019.0	1019.0	1019.0	1019.0	1019.0
2.5°	1026.3	1021.9	1011.6	1019.0	1016.0
5°	1021.9	1017.5	1008.6	1017.5	1016.0
7.5°	1014.5	1011.6	1004.2	1014.5	1013.1
10°	1005.7	1002.7	998.3	1010.1	1008.6
12.5°	990.9	992.4	989.4	1001.2	999.8
15°	974.7	977.6	977.6	990.9	989.4
17.5°	954.0	959.9	964.3	977.6	977.6
20°	933.3	940.7	946.6	962.8	962.8
22.5°	911.2	920.0	928.9	945.1	948.1
25°	886.1	896.4	909.7	927.4	931.8
27.5°	856.5	872.8	887.5	909.7	912.6
30°	827.0	846.2	865.4	889.0	893.4
32.5°	794.5	816.6	840.3	868.3	877.2
35°	763.5	788.6	816.6	849.1	859.5
37.5°	729.5	757.6	793.0	828.5	838.8
40°	695.6	728.0	767.9	806.3	819.6
42.5°	663.1	695.6	742.8	785.6	798.9
45°	626.1	666.0	717.7	763.5	778.3
47.5°	590.7	633.5	692.6	739.9	756.1
50°	553.8	599.6	666.0	716.2	732.5
52.5°	518.3	567.1	638.0	689.6	707.4
55°	479.9	533.1	609.9	663.1	682.3
57.5°	443.0	502.1	578.9	636.5	655.7
60°	403.2	466.7	550.8	606.9	627.6
62.5°	367.7	434.2	518.3	578.9	598.1
65°	327.8	400.2	487.3	547.9	567.1
67.5°	292.4	367.7	456.3	516.9	537.5
70°	254.0	330.8	422.4	485.9	503.6
72.5°	218.6	298.3	391.3	453.4	475.5
75°	181.6	264.3	358.9	422.4	441.6
77.5°	146.2	231.9	327.8	391.3	412.0
80°	110.8	200.8	296.8	358.9	379.5
82.5°	81.2	169.8	267.3	329.3	348.5
85°	53.2	144.7	239.2	301.3	321.9
87.5°	32.5	121.1	215.6	276.2	295.4
90°	15.1	105.0	206.5	265.1	283.0
92.5°	18.4	107.8	234.2	263.4	277.9
95°	23.8	110.6	303.8	276.5	282.7
97.5°	28.1	112.6	377.9	315.6	297.2
100°	36.6	112.5	417.7	404.5	341.0
102.5°	43.1	113.0	409.1	532.3	445.3
105°	49.1	113.1	380.3	631.4	580.1
107.5°	57.3	113.2	352.9	659.8	667.1
110°	64.0	113.6	332.4	641.5	695.7



TEST NUMBER: P997897

CATALOG NUMBER: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-D4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	71.5	115.0	314.6	609.1	684.7
115°	79.4	115.0	300.5	570.3	656.1
117.5°	86.1	116.4	287.5	534.2	618.9
120°	93.6	117.6	276.2	499.2	584.4
122.5°	100.8	120.6	265.9	470.9	545.8
125°	105.5	124.4	253.9	444.4	514.6
127.5°	110.7	129.2	244.0	418.8	483.3
130°	115.1	134.8	234.5	394.4	455.4
132.5°	119.2	140.3	225.3	369.5	428.3
135°	121.8	145.1	217.5	345.0	399.9
137.5°	125.6	149.1	210.2	320.2	370.7
140°	130.0	151.4	204.0	297.3	340.7
142.5°	134.5	154.5	201.0	276.3	312.2
145°	137.4	158.0	200.3	257.5	288.3
147.5°	142.2	160.6	199.3	241.4	264.7
150°	147.0	163.4	198.3	232.4	247.1
152.5°	151.8	166.2	196.6	226.2	237.2
155°	156.2	168.7	194.5	220.0	228.7
157.5°	160.0	170.8	192.4	214.2	221.2
160°	163.7	172.8	190.4	208.3	214.0
162.5°	167.5	174.4	188.7	202.8	207.1
165°	170.2	175.4	186.3	197.6	200.7
167.5°	172.6	176.4	184.2	192.8	194.5
170°	175.0	176.9	182.5	188.4	189.0
172.5°	176.4	177.4	180.5	184.4	184.6
175°	177.4	177.6	179.1	181.4	180.8
177.5°	178.1	177.8	177.8	179.1	178.1
180°	177.8	177.8	177.8	177.8	177.8

TEST NUMBER: P997897

CATALOG NUMBER: SA2XXDIP-B1005D330UB50-4F0-XX-W2A-D4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.31	17.42	17.09	18.23	19.23	19.38	20.50	20.16	21.31	22.30
	3H	17.78	18.80	18.57	19.62	20.64	21.98	23.00	22.78	23.82	24.84
	4H	18.27	19.23	19.07	20.06	21.09	23.25	24.21	24.06	25.04	26.07
	6H	18.56	19.46	19.38	20.30	21.34	24.56	25.45	25.38	26.29	27.34
	8H	18.63	19.49	19.46	20.34	21.39	25.22	26.08	26.05	26.94	27.98
	12H	18.65	19.47	19.49	20.32	21.40	25.96	26.78	26.79	27.63	28.70
4H	2H	17.38	18.35	18.19	19.17	20.21	19.74	20.70	20.55	21.53	22.56
	3H	19.11	19.93	19.93	20.79	21.84	22.55	23.37	23.37	24.23	25.28
	4H	19.74	20.49	20.58	21.35	22.43	23.97	24.73	24.81	25.59	26.66
	6H	20.17	20.83	21.02	21.71	22.79	25.45	26.12	26.30	27.00	28.08
	8H	20.28	20.91	21.14	21.78	22.88	26.22	26.84	27.07	27.72	28.81
	12H	20.34	20.91	21.22	21.80	22.90	27.06	27.63	27.94	28.52	29.62
8H	4H	20.55	21.17	21.40	22.05	23.14	24.14	24.76	24.99	25.64	26.73
	6H	21.19	21.72	22.08	22.64	23.73	25.77	26.30	26.66	27.22	28.31
	8H	21.42	21.89	22.31	22.80	23.91	26.67	27.14	27.56	28.05	29.16
	12H	21.56	21.98	22.46	22.89	24.05	27.68	28.10	28.57	29.00	30.16
12H	4H	20.76	21.33	21.64	22.23	23.32	24.12	24.69	25.00	25.59	26.69
	6H	21.53	22.00	22.42	22.91	24.02	25.80	26.28	26.70	27.19	28.30
	8H	21.85	22.27	22.74	23.17	24.33	26.75	27.17	27.64	28.07	29.23