

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997908

Luminaire Tested: SA2XXDIP-B1005D530UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P997908
REPORT IS A COMBINATION OF REPORTS P983645 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B1005D530UB27-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5908.0 lumens
Efficiency: N/A
Efficacy: 77.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997908

CATALOG NUMBER: SA2XXDIP-B1005D530UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P997908

CATALOG NUMBER: SA2XXDIP-B1005D530UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93	83	83	83	73	73	73	63	63	63
1	102	97	93	90	96	92	89	85	82	79	77	73	71	69	64	63	62	57	57	57
2	93	85	79	73	87	81	75	70	72	68	64	64	61	58	57	54	52	48	48	48
3	85	75	67	61	80	71	64	59	64	58	54	57	52	49	50	47	44	41	41	41
4	78	66	58	52	73	63	56	50	57	51	46	51	46	42	45	41	38	35	35	35
5	71	59	51	45	67	56	49	43	51	44	40	45	40	36	41	37	33	30	30	30
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	33	29	27	27	27
7	61	48	40	34	57	46	38	33	42	35	31	37	32	28	34	29	26	24	24	24
8	57	44	36	30	53	42	35	29	38	32	27	34	29	25	31	27	23	21	21	21
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	24	21	19	19	19
10	49	37	30	25	47	35	28	24	32	26	22	29	24	21	27	22	19	17	17	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25067	25067	25067
5°	25108	23894	23724
10°	24904	22805	22353
15°	24540	21709	20909
20°	24047	20514	19542
25°	23556	19269	18178
30°	22937	18098	16746
35°	22355	16861	15339
40°	21634	15642	14009
45°	20918	14433	12705
50°	20138	13201	11353
55°	19313	11886	10071
60°	18389	10461	8739
65°	17377	9013	7339
70°	16089	7428	5926
75°	14310	5728	4576
80°	12159	3892	2945
85°	8814	1811	1253

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20918 cd/sqm

TEST NUMBER: P997908

CATALOG NUMBER: SA2XXDIP-B1005D530UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.0	2.5
10°-20°	419.4	7.1
20°-30°	616.3	10.4
30°-40°	715.8	12.1
40°-50°	714.9	12.1
50°-60°	623.3	10.6
60°-70°	460.8	7.8
70°-80°	260.7	4.4
80°-90°	70.7	1.2
90°-100°	41.5	0.7
100°-110°	132.0	2.2
110°-120°	225.9	3.8
120°-130°	297.1	5.0
130°-140°	333.5	5.6
140°-150°	327.1	5.5
150°-160°	274.3	4.6
160°-170°	182.0	3.1
170°-180°	63.6	1.1
0°-30°	1184.7	20.1
0°-40°	1900.5	32.2
0°-60°	3238.7	54.8
0°-90°	4030.9	68.2
90°-120°	399.5	6.8
90°-150°	1357.2	23.0
90°-180°	1877.0	31.8
0°-180°	5908.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1584	1584	1584	1584	1584	
5°	1584	1578	1561	1573	1570	150
15°	1508	1498	1479	1485	1477	425
25°	1364	1352	1326	1329	1326	628
35°	1177	1162	1138	1128	1121	735
45°	958	947	924	908	901	739
55°	725	716	697	679	672	648
65°	489	480	464	451	443	483
75°	256	253	245	236	239	273
85°	62	61	59	55	53	70
90°	1	7	20	19	19	6
95°	30	35	36	36	35	33
105°	122	124	125	126	126	129
115°	227	230	229	228	227	224
125°	330	335	333	331	331	295
135°	427	433	434	433	432	330
145°	518	522	525	526	524	324
155°	592	594	596	598	597	273
165°	644	644	644	648	645	182
175°	670	669	667	671	668	64
180°	671	671	671	671	671	

TEST NUMBER: P997908

CATALOG NUMBER: SA2XXDIP-B1005D530UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1583.6	1583.6	1583.6	1583.6	1583.6
2.5°	1592.8	1585.1	1568.4	1583.6	1580.6
5°	1583.6	1577.5	1560.8	1573.0	1569.9
7.5°	1573.0	1563.8	1547.1	1559.3	1556.2
10°	1556.2	1545.6	1527.3	1539.5	1534.9
12.5°	1533.4	1524.2	1506.0	1513.6	1510.5
15°	1507.5	1498.4	1478.6	1484.7	1477.0
17.5°	1475.5	1466.4	1446.6	1454.2	1446.6
20°	1440.5	1431.4	1410.0	1414.6	1408.5
22.5°	1405.5	1391.8	1372.0	1372.0	1368.9
25°	1364.4	1352.2	1326.3	1329.3	1326.3
27.5°	1318.7	1308.0	1288.2	1283.7	1276.0
30°	1273.0	1260.8	1238.0	1233.4	1227.3
32.5°	1224.3	1215.1	1190.8	1181.6	1175.5
35°	1177.1	1161.8	1137.5	1128.3	1120.7
37.5°	1123.8	1110.1	1085.7	1075.0	1067.4
40°	1068.9	1056.8	1032.4	1018.7	1012.6
42.5°	1015.7	1003.5	979.1	963.9	954.7
45°	957.8	947.1	924.3	907.5	901.4
47.5°	901.4	890.8	866.4	849.7	840.5
50°	842.1	834.4	813.1	791.8	784.2
52.5°	784.2	773.5	753.7	737.0	726.3
55°	724.8	715.7	697.4	679.1	671.5
57.5°	665.4	657.8	638.0	619.7	613.7
60°	606.0	600.0	578.6	561.9	557.3
62.5°	548.2	537.5	522.3	507.1	501.0
65°	488.8	479.7	464.4	450.7	443.1
67.5°	427.9	420.3	406.6	395.9	389.8
70°	371.5	365.5	351.7	341.1	335.0
72.5°	313.7	307.6	300.0	289.3	284.7
75°	255.8	252.8	245.2	236.0	239.1
77.5°	204.0	198.0	194.9	190.3	185.8
80°	152.3	150.7	147.7	143.1	140.1
82.5°	103.5	103.5	102.0	95.9	95.9
85°	62.4	60.9	59.4	54.8	53.3
87.5°	27.4	24.4	21.3	16.7	15.2
90°	0.6	7.4	19.8	18.7	19.3
92.5°	12.5	17.0	17.6	18.1	18.1
95°	29.5	35.1	36.3	36.3	35.1
97.5°	49.3	54.4	56.7	56.7	56.7
100°	72.0	76.5	78.2	78.2	77.6
102.5°	95.8	99.2	101.4	102.0	101.4
105°	121.8	123.5	124.6	125.8	125.8
107.5°	147.9	150.1	150.1	150.7	147.9
110°	172.8	176.2	176.2	176.2	174.5

TEST NUMBER: P997908

CATALOG NUMBER: SA2XXDIP-B1005D530UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	200.0	203.4	202.8	201.1	200.0
115°	226.6	230.0	228.9	228.3	226.6
117.5°	253.3	257.8	255.0	253.3	251.6
120°	279.9	284.4	279.9	279.9	278.2
122.5°	304.3	309.9	307.1	305.4	304.3
125°	329.7	334.8	333.1	331.4	330.9
127.5°	354.7	360.9	358.6	356.4	354.7
130°	377.9	385.3	384.1	383.0	380.7
132.5°	404.0	409.6	410.2	407.4	405.7
135°	426.6	432.9	434.0	433.4	431.7
137.5°	451.6	456.7	457.8	457.2	455.0
140°	473.7	478.8	481.6	481.6	479.3
142.5°	496.3	501.4	503.1	503.7	501.4
145°	517.9	521.8	525.2	525.8	523.5
147.5°	537.1	542.2	544.5	545.6	543.3
150°	556.9	560.3	562.6	564.3	562.6
152.5°	574.5	577.9	580.7	583.0	580.7
155°	592.1	593.8	595.5	598.3	596.6
157.5°	607.4	608.5	609.6	613.6	610.8
160°	621.0	622.1	622.7	626.1	623.8
162.5°	633.4	633.4	634.0	638.0	635.1
165°	644.2	643.6	643.6	647.6	644.8
167.5°	653.8	652.1	652.1	656.1	653.3
170°	661.2	659.5	658.9	662.9	659.5
172.5°	666.3	664.6	664.0	668.0	664.6
175°	670.3	668.6	667.4	671.4	668.0
177.5°	672.5	670.8	669.7	673.1	669.7
180°	671.4	671.4	671.4	671.4	671.4

TEST NUMBER: P997908

CATALOG NUMBER: SA2XXDIP-B1005D530UB27-4F0-XX-W2A-F1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.96	19.01	18.74	19.82	20.80	18.74	19.80	19.53	20.60	21.59
	3H	19.31	20.26	20.11	21.07	22.09	20.38	21.33	21.18	22.14	23.16
	4H	19.73	20.62	20.54	21.44	22.47	20.98	21.88	21.80	22.70	23.73
	6H	19.96	20.78	20.78	21.61	22.65	21.40	22.22	22.22	23.05	24.09
	8H	19.99	20.78	20.83	21.63	22.67	21.51	22.30	22.35	23.15	24.19
	12H	19.99	20.74	20.83	21.58	22.65	21.56	22.31	22.40	23.15	24.22
4H	2H	18.45	19.35	19.27	20.17	21.19	19.10	19.99	19.91	20.81	21.84
	3H	19.99	20.73	20.82	21.59	22.63	20.89	21.64	21.72	22.50	23.54
	4H	20.50	21.18	21.34	22.04	23.10	21.58	22.26	22.43	23.12	24.19
	6H	20.81	21.40	21.67	22.28	23.35	22.09	22.68	22.95	23.56	24.63
	8H	20.88	21.43	21.74	22.30	23.39	22.24	22.79	23.10	23.66	24.75
	12H	20.89	21.38	21.77	22.27	23.37	22.31	22.80	23.19	23.70	24.79
8H	4H	20.69	21.24	21.55	22.12	23.20	21.68	22.23	22.55	23.11	24.19
	6H	21.08	21.54	21.97	22.45	23.54	22.26	22.72	23.15	23.63	24.72
	8H	21.19	21.59	22.09	22.50	23.60	22.45	22.85	23.35	23.76	24.87
	12H	21.23	21.58	22.13	22.49	23.64	22.56	22.91	23.46	23.82	24.97
12H	4H	20.68	21.18	21.57	22.07	23.16	21.66	22.15	22.54	23.05	24.14
	6H	21.10	21.51	22.00	22.42	23.52	22.25	22.66	23.15	23.57	24.67
	8H	21.22	21.58	22.13	22.48	23.64	22.46	22.81	23.36	23.72	24.87