

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998566

Luminaire Tested: SA2XXDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998566
REPORT IS A COMBINATION OF REPORTS P984309 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D725UB2750-4F0-XX-W2A-A_3500K
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4988.0 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998566

CATALOG NUMBER: SA2XXDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P998566

CATALOG NUMBER: SA2XXDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	97	93	89	85	88	85	82	79	70	68	66	57	55	54	45	44	43
2	88	81	75	70	81	75	70	65	62	58	55	50	48	46	40	38	37
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	33	32
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	26	24
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	27	24	22
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19
8	54	42	35	29	49	39	32	28	33	28	24	28	24	21	22	20	17
9	50	39	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15383	15383	15383	15383
5°	15419	16401	15478	13049
10°	15240	17905	15336	10758
15°	14871	18885	15077	9062
20°	14638	17732	14638	7877
25°	14172	15233	14236	7044
30°	13404	11974	13659	6380
35°	12724	8280	12937	5837
40°	11943	6252	12079	5404
45°	10979	5138	11158	4937
50°	10147	4510	10163	4520
55°	9196	3842	9254	4066
60°	8181	3210	8296	3549
65°	7277	2610	7408	3031
70°	6370	2049	6535	2445
75°	5348	1487	5555	1772
80°	4176	942	4471	1051
85°	2740	475	2952	350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15901 cd/sqm

TEST NUMBER: P998566

CATALOG NUMBER: SA2XXDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.6	1.9
10°-20°	269.4	5.4
20°-30°	391.0	7.8
30°-40°	412.2	8.3
40°-50°	364.7	7.3
50°-60°	291.2	5.8
60°-70°	197.8	4.0
70°-80°	101.2	2.0
80°-90°	25.6	0.5
90°-100°	32.0	0.6
100°-110°	119.2	2.4
110°-120°	316.1	6.3
120°-130°	524.2	10.5
130°-140°	556.8	11.2
140°-150°	517.5	10.4
150°-160°	416.1	8.3
160°-170°	268.1	5.4
170°-180°	92.3	1.9
0°-30°	752.9	15.1
0°-40°	1165.1	23.4
0°-60°	1821.1	36.5
0°-90°	2145.7	43.0
90°-120°	467.2	9.4
90°-150°	2065.8	41.4
90°-180°	2842.0	57.0
0°-180°	4988.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	972	972	972	972	972	
5°	972	1085	976	864	972	92
15°	914	1334	926	640	914	258
25°	821	1111	825	514	821	375
35°	670	605	681	426	670	419
45°	503	364	511	350	503	390
55°	345	256	347	271	345	308
65°	205	158	208	183	205	203
75°	96	78	99	93	96	103
85°	19	20	21	15	19	23
90°	1	19	1	19	1	4
95°	46	30	46	30	46	54
105°	213	53	213	53	213	228
115°	403	58	403	58	403	397
125°	570	600	570	600	570	509
135°	706	729	706	729	706	545
145°	819	831	819	831	819	512
155°	902	902	902	902	902	415
165°	950	948	950	948	950	268
175°	972	966	972	966	972	92
180°	970	970	970	970	970	

TEST NUMBER: P998566

CATALOG NUMBER: SA2XXDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	977.0	979.2	983.0	983.7	991.2	997.2	1003.9	1003.9	1006.1	1005.4	999.4
5°	972.5	979.2	988.9	997.2	1010.6	1016.6	1025.5	1032.3	1038.2	1042.7	1042.0
7.5°	965.0	977.0	991.2	1006.9	1024.8	1035.3	1047.9	1059.9	1068.1	1075.6	1080.8
10°	952.3	972.5	991.9	1012.8	1036.0	1050.2	1065.1	1080.8	1093.5	1107.7	1121.1
12.5°	935.2	964.3	988.2	1015.8	1044.2	1059.9	1083.8	1095.8	1120.4	1156.3	1166.0
15°	913.5	953.1	975.5	1010.6	1047.9	1060.6	1093.5	1112.9	1163.7	1186.1	1213.0
17.5°	893.3	937.4	967.3	1007.6	1044.2	1068.9	1101.0	1140.6	1183.1	1215.3	1245.1
20°	876.9	919.5	955.3	1000.1	1046.5	1077.8	1111.4	1159.2	1205.6	1238.4	1261.6
22.5°	839.6	894.1	935.9	986.0	1042.0	1085.3	1117.4	1169.7	1219.7	1239.9	1260.1
25°	820.9	867.9	916.5	973.3	1039.0	1090.5	1118.2	1176.4	1220.5	1228.0	1232.4
27.5°	786.5	839.6	896.3	961.3	1038.2	1081.6	1116.7	1169.7	1204.8	1199.6	1186.1
30°	743.9	808.9	871.7	941.9	1027.8	1074.8	1107.7	1156.3	1174.2	1147.3	1123.4
32.5°	712.6	773.8	843.3	924.7	1015.8	1060.6	1092.8	1130.9	1134.6	1086.0	1045.7
35°	670.0	738.0	816.4	902.3	995.7	1036.0	1065.9	1089.0	1071.1	1003.1	955.3
37.5°	631.9	699.1	782.8	870.2	968.0	1007.6	1031.5	1035.3	991.2	931.4	861.2
40°	590.1	659.5	746.9	838.8	937.4	971.8	986.7	975.5	912.0	842.5	761.1
42.5°	548.2	617.0	711.1	805.2	898.6	927.7	933.7	903.0	825.4	743.9	649.8
45°	502.7	574.4	668.5	763.4	853.7	870.2	870.9	826.9	735.0	649.8	562.4
47.5°	465.3	531.8	625.2	720.0	796.2	807.4	803.0	752.2	652.1	556.5	480.3
50°	424.3	487.7	580.4	673.7	738.7	741.7	730.5	658.0	560.2	472.8	412.3
52.5°	380.2	444.4	529.6	619.2	677.5	673.0	651.3	573.6	481.8	409.3	363.0
55°	345.1	401.9	481.8	569.2	610.2	597.5	573.6	494.5	422.0	360.8	320.4
57.5°	306.2	356.3	434.7	510.9	534.8	522.9	499.0	425.0	357.8	311.5	284.6
60°	269.6	315.2	383.9	447.4	466.1	453.4	425.8	359.3	310.7	271.9	251.7
62.5°	236.0	275.6	333.1	391.4	398.9	386.2	362.3	308.5	266.7	236.0	221.1
65°	204.7	242.0	288.3	332.4	339.1	325.7	301.0	262.2	227.1	207.6	193.5
67.5°	174.0	203.9	245.0	277.1	280.8	268.1	248.0	216.6	194.9	174.0	163.6
70°	147.1	169.6	201.7	227.8	229.3	217.4	206.9	178.5	162.1	147.1	138.9
72.5°	121.0	136.7	161.3	180.8	181.5	174.0	164.3	146.4	132.2	121.8	113.5
75°	95.6	109.1	124.0	141.2	140.4	134.4	127.0	115.8	103.8	97.1	93.4
77.5°	73.2	81.4	93.4	104.6	104.6	101.6	97.1	88.9	81.4	74.7	71.0
80°	52.3	57.5	67.2	71.0	72.5	71.7	68.0	62.0	59.0	53.8	52.3
82.5°	33.6	37.3	41.8	45.6	47.8	46.3	45.6	42.6	38.1	36.6	35.1
85°	19.4	20.9	23.2	25.4	26.1	25.4	26.9	24.6	22.4	22.4	21.7
87.5°	8.2	9.0	10.5	10.5	11.2	11.2	10.5	11.2	11.2	10.5	9.7
90°	0.7	2.4	4.1	5.8	7.5	8.4	9.0	10.3	11.5	12.8	14.0
92.5°	17.5	16.9	16.3	15.6	15.0	14.7	14.9	15.4	15.9	16.3	16.8
95°	45.6	40.4	35.3	30.1	25.0	22.4	23.0	24.1	25.2	26.3	27.4
97.5°	82.1	69.3	56.5	43.8	31.0	24.6	25.8	28.3	30.8	33.3	35.8
100°	124.2	102.8	81.5	60.1	38.8	28.1	29.4	32.1	34.7	37.4	40.0
102.5°	170.5	170.2	169.9	169.6	169.3	169.1	154.9	126.5	98.2	69.8	41.4
105°	213.3	218.0	222.6	227.3	232.0	234.3	213.0	170.5	127.9	85.4	42.8
107.5°	263.1	267.0	270.9	274.8	278.7	280.6	254.3	201.8	149.3	96.7	44.2
110°	310.8	314.1	317.3	320.6	323.9	325.5	303.0	257.9	212.9	167.8	122.8

TEST NUMBER: P998566

CATALOG NUMBER: SA2XXDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	355.7	358.5	361.3	364.1	366.9	368.3	367.0	364.3	361.7	359.0	356.4
115°	403.4	406.0	408.7	411.3	414.0	415.3	417.2	421.1	425.0	428.9	432.8
117.5°	444.8	447.9	451.0	454.1	457.2	458.8	460.1	462.8	465.4	468.1	470.7
120°	491.1	493.4	495.8	498.1	500.4	501.6	503.0	505.8	508.6	511.4	514.2
122.5°	530.4	532.9	535.4	537.9	540.4	541.6	543.2	546.3	549.4	552.5	555.6
125°	570.3	572.3	574.4	576.4	578.5	579.5	581.0	583.9	586.9	589.8	592.8
127.5°	606.8	609.0	611.2	613.3	615.5	616.6	617.8	620.1	622.5	624.8	627.2
130°	641.2	643.7	646.2	648.7	651.2	652.4	653.3	655.0	656.7	658.4	660.1
132.5°	676.3	678.3	680.3	682.4	684.4	685.4	686.3	688.0	689.7	691.4	693.1
135°	705.7	708.2	710.7	713.2	715.7	717.0	717.7	719.1	720.5	721.9	723.3
137.5°	736.6	738.5	740.3	742.2	744.1	745.0	745.8	747.3	748.9	750.4	752.0
140°	766.8	768.0	769.3	770.5	771.8	772.4	773.3	775.0	776.7	778.4	780.1
142.5°	792.0	793.1	794.2	795.3	796.4	796.9	797.9	800.0	802.0	804.1	806.1
145°	818.7	818.5	818.4	818.2	818.1	818.0	819.3	822.0	824.6	827.3	829.9
147.5°	841.8	841.3	840.9	840.4	839.9	839.7	841.0	843.7	846.4	849.0	851.7
150°	864.3	863.2	862.1	861.0	859.9	859.4	860.6	863.1	865.6	868.1	870.6
152.5°	883.2	882.0	880.7	879.5	878.2	877.6	878.8	881.1	883.4	885.8	888.1
155°	901.5	900.1	898.7	897.3	895.9	895.2	896.1	898.0	899.9	901.7	903.6
157.5°	916.2	915.0	913.7	912.5	911.2	910.6	911.3	912.7	914.1	915.5	916.9
160°	928.8	927.9	926.9	926.0	925.1	924.6	925.1	926.0	926.9	927.9	928.8
162.5°	940.1	939.1	938.2	937.2	936.3	935.8	936.2	937.0	937.8	938.6	939.4
165°	949.9	949.0	948.0	947.1	946.2	945.7	945.9	946.4	946.9	947.3	947.8
167.5°	957.6	956.7	955.7	954.8	953.9	953.4	953.6	954.1	954.6	955.0	955.5
170°	963.9	963.0	962.0	961.1	960.2	959.7	959.9	960.2	960.5	960.8	961.1
172.5°	968.1	967.2	966.2	965.3	964.4	963.9	964.1	964.4	964.7	965.0	965.3
175°	971.6	970.5	969.4	968.3	967.2	966.7	966.9	967.2	967.5	967.8	968.1
177.5°	973.0	971.9	970.8	969.7	968.6	968.1	968.2	968.3	968.5	968.6	968.8
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P998566

CATALOG NUMBER: SA2XXDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	1009.9	1010.6	1012.1	1019.6	1023.3	1024.0	1021.1	1027.8	1030.0	1027.8	1026.3
5°	1057.7	1062.1	1071.1	1080.8	1080.1	1080.8	1085.3	1089.8	1091.3	1085.3	1087.5
7.5°	1099.5	1108.4	1118.2	1133.1	1133.1	1140.6	1143.6	1147.3	1156.3	1151.8	1150.3
10°	1147.3	1159.2	1177.2	1201.1	1201.8	1209.3	1216.8	1228.7	1232.4	1229.5	1230.9
12.5°	1207.0	1230.2	1231.7	1257.8	1269.8	1271.3	1283.2	1281.0	1288.5	1288.5	1301.2
15°	1233.2	1269.0	1289.2	1314.6	1322.1	1313.1	1322.8	1333.3	1334.0	1334.0	1333.3
17.5°	1280.2	1294.4	1314.6	1328.0	1331.0	1331.0	1331.8	1336.3	1333.3	1327.3	1331.8
20°	1290.0	1295.9	1303.4	1301.9	1303.4	1295.9	1288.5	1281.0	1281.7	1278.0	1289.2
22.5°	1272.0	1270.5	1253.4	1242.2	1242.2	1227.2	1213.0	1206.3	1199.6	1201.8	1205.6
25°	1227.2	1204.1	1183.1	1166.7	1163.0	1139.1	1119.7	1113.7	1102.5	1111.4	1112.9
27.5°	1155.5	1129.4	1095.8	1081.6	1062.1	1052.4	1039.0	1021.1	997.9	1011.3	1009.1
30°	1078.6	1039.7	1012.1	977.7	947.1	944.9	919.5	889.6	877.6	877.6	884.4
32.5°	992.7	941.1	900.8	852.3	822.4	809.7	779.1	749.2	755.9	733.5	741.7
35°	892.6	824.6	773.8	726.8	704.4	689.4	649.8	633.4	615.5	605.0	624.4
37.5°	797.0	718.6	653.6	602.0	593.8	566.9	540.0	529.6	519.1	523.6	522.9
40°	680.5	611.0	552.7	512.4	498.2	485.5	467.6	454.9	448.2	451.9	452.6
42.5°	575.1	516.9	473.6	445.2	433.2	424.3	415.3	404.8	402.6	402.6	405.6
45°	493.7	445.9	416.8	393.6	386.9	380.2	373.5	369.0	367.5	364.5	366.7
47.5°	428.7	390.6	372.7	355.5	348.1	346.6	340.6	338.4	335.4	334.6	335.4
50°	374.2	350.3	333.9	324.2	318.9	316.7	313.7	309.2	307.7	311.5	310.0
52.5°	336.1	313.7	304.7	295.0	292.1	289.1	284.6	285.3	284.6	283.1	283.1
55°	298.0	283.8	274.9	267.4	266.7	263.7	259.9	258.4	257.7	256.2	258.4
57.5°	267.4	256.2	248.0	241.3	238.3	238.3	234.5	231.5	231.5	230.8	231.5
60°	236.8	225.6	220.3	213.6	211.4	210.6	208.4	206.9	204.7	204.7	204.7
62.5°	208.4	199.4	193.5	187.5	188.2	184.5	181.5	180.0	180.0	180.8	180.8
65°	181.5	175.5	168.1	162.8	161.3	160.6	159.1	158.3	156.1	157.6	157.6
67.5°	156.9	148.6	144.2	141.9	139.7	138.9	137.4	135.9	135.2	134.4	135.9
70°	132.2	125.5	121.8	120.3	118.0	117.3	116.5	114.3	115.0	115.8	116.5
72.5°	109.8	103.8	103.1	98.6	98.6	98.6	95.6	97.1	96.4	94.9	96.4
75°	86.6	83.7	82.2	79.9	80.7	79.9	79.2	76.9	76.9	77.7	78.4
77.5°	68.7	65.7	65.0	62.7	61.2	62.7	61.2	60.5	60.5	61.2	61.2
80°	50.8	49.3	47.1	47.1	47.1	46.3	46.3	46.3	45.6	44.8	45.6
82.5°	33.6	33.6	32.9	32.1	32.9	31.4	32.1	32.1	32.1	32.1	32.1
85°	21.7	20.9	20.9	20.2	20.2	20.2	20.9	19.4	19.4	20.2	20.2
87.5°	9.7	9.7	9.7	10.5	9.7	9.7	9.7	10.5	9.7	9.7	9.7
90°	14.8	15.6	16.3	17.1	17.5	17.7	18.0	18.3	18.6	18.9	18.6
92.5°	17.1	17.4	17.7	18.0	18.2	18.3	18.4	18.6	18.7	18.9	18.7
95°	28.2	29.0	29.7	30.5	30.9	30.8	30.7	30.5	30.4	30.2	30.4
97.5°	36.3	36.7	37.2	37.7	37.9	38.0	38.1	38.3	38.4	38.6	38.4
100°	41.2	42.5	43.7	45.0	45.6	45.8	46.1	46.4	46.7	47.0	46.7
102.5°	43.1	44.8	46.5	48.2	49.1	49.3	49.8	50.3	50.7	51.2	50.7
105°	44.5	46.2	47.9	49.6	50.5	50.8	51.4	52.1	52.7	53.3	52.7
107.5°	45.9	47.6	49.3	51.0	51.9	52.2	52.8	53.5	54.1	54.7	54.1
110°	107.2	91.6	76.0	60.4	52.6	52.9	53.5	54.2	54.8	55.4	54.8

TEST NUMBER: P998566

CATALOG NUMBER: SA2XXDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	289.2	222.0	154.8	87.6	54.0	54.2	54.7	55.2	55.6	56.1	55.6
115°	360.6	288.4	216.3	144.1	108.0	102.4	91.2	79.9	68.7	57.5	68.7
117.5°	448.4	426.1	403.8	381.5	370.4	350.0	309.1	268.3	227.4	186.6	227.4
120°	516.1	517.9	519.8	521.7	522.6	512.1	491.0	470.0	448.9	427.9	448.9
122.5°	556.5	557.5	558.4	559.3	559.8	559.9	560.0	560.2	560.3	560.5	560.3
125°	593.9	595.0	596.1	597.2	597.7	597.9	598.4	598.9	599.3	599.8	599.3
127.5°	628.8	630.3	631.9	633.4	634.2	634.3	634.4	634.6	634.7	634.9	634.7
130°	661.8	663.6	665.3	667.0	667.9	667.8	667.7	667.5	667.4	667.2	667.4
132.5°	694.5	695.9	697.3	698.7	699.4	699.3	699.2	699.0	698.9	698.7	698.9
135°	724.9	726.4	728.0	729.5	730.3	730.1	729.8	729.5	729.2	728.9	729.2
137.5°	753.6	755.2	756.7	758.3	759.1	758.9	758.4	757.9	757.5	757.0	757.5
140°	781.5	782.9	784.3	785.7	786.4	786.0	785.2	784.5	783.7	782.9	783.7
142.5°	807.3	808.6	809.8	811.1	811.7	811.3	810.5	809.8	809.0	808.2	809.0
145°	831.0	832.1	833.2	834.3	834.8	834.4	833.6	832.9	832.1	831.3	832.1
147.5°	852.5	853.3	854.0	854.8	855.2	854.9	854.3	853.6	853.0	852.4	853.0
150°	871.5	872.5	873.4	874.3	874.8	874.4	873.6	872.9	872.1	871.3	872.1
152.5°	889.1	890.0	891.0	891.9	892.4	891.8	890.7	889.6	888.5	887.4	888.5
155°	904.5	905.5	906.4	907.3	907.8	907.2	905.9	904.7	903.4	902.2	903.4
157.5°	918.0	919.1	920.2	921.3	921.8	921.2	919.9	918.7	917.4	916.2	917.4
160°	929.7	930.7	931.6	932.5	933.0	932.5	931.4	930.3	929.2	928.1	929.2
162.5°	940.5	941.6	942.7	943.8	944.3	943.6	942.2	940.8	939.4	938.0	939.4
165°	948.9	950.0	951.1	952.2	952.7	952.2	951.1	950.0	948.9	947.8	948.9
167.5°	956.6	957.7	958.8	959.9	960.4	959.7	958.3	956.9	955.5	954.1	955.5
170°	962.2	963.3	964.4	965.5	966.0	965.3	963.9	962.5	961.1	959.7	961.1
172.5°	966.4	967.5	968.6	969.7	970.2	969.5	968.1	966.7	965.3	963.9	965.3
175°	969.2	970.3	971.4	972.5	973.0	972.2	970.7	969.1	967.6	966.0	967.6
177.5°	969.9	971.0	972.1	973.2	973.7	973.0	971.6	970.2	968.8	967.4	968.8
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P998566

CATALOG NUMBER: SA2XXDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	1030.0	1024.8	1020.3	1021.1	1024.8	1021.8	1014.3	1004.6	1000.9	996.4	1000.9
5°	1092.0	1087.5	1078.6	1079.3	1077.1	1074.1	1062.1	1047.2	1047.2	1035.3	1033.8
7.5°	1153.3	1146.5	1140.6	1139.1	1130.9	1124.9	1114.4	1093.5	1085.3	1071.1	1062.9
10°	1222.0	1216.8	1210.0	1201.8	1197.3	1186.9	1169.7	1139.1	1124.1	1104.7	1090.5
12.5°	1291.4	1290.7	1275.8	1259.3	1258.6	1242.2	1230.2	1189.1	1169.0	1142.8	1109.2
15°	1335.5	1331.8	1323.6	1315.4	1317.6	1299.7	1272.8	1224.2	1210.8	1179.4	1143.6
17.5°	1334.8	1334.8	1332.5	1331.0	1328.8	1323.6	1308.6	1276.5	1254.8	1215.3	1181.6
20°	1292.2	1301.9	1304.1	1303.4	1310.9	1314.6	1313.9	1293.7	1276.5	1241.4	1207.0
22.5°	1207.0	1229.5	1239.2	1245.1	1260.8	1269.0	1288.5	1281.0	1276.5	1250.4	1221.2
25°	1127.9	1135.3	1164.5	1166.0	1187.6	1207.8	1227.2	1239.9	1256.3	1246.6	1222.0
27.5°	1025.5	1042.7	1063.6	1079.3	1083.8	1124.9	1157.0	1180.9	1218.2	1221.2	1213.0
30°	909.8	918.0	952.3	973.3	997.2	1027.0	1073.3	1114.4	1148.0	1178.7	1189.1
32.5°	768.6	802.2	822.4	847.8	868.7	921.7	978.5	1031.5	1070.4	1121.9	1144.3
35°	639.4	665.5	699.9	710.3	748.4	793.2	867.2	935.2	994.2	1046.5	1092.0
37.5°	532.6	553.5	590.1	606.5	628.9	686.4	748.4	832.8	903.8	968.0	1024.8
40°	459.4	475.0	502.7	507.9	526.6	578.9	628.9	708.1	802.2	888.9	950.8
42.5°	409.3	416.8	435.5	442.2	454.1	489.2	534.1	608.8	696.1	785.8	873.2
45°	373.5	378.7	389.9	395.9	410.8	426.5	463.1	522.9	591.6	682.0	776.1
47.5°	341.3	348.1	352.6	356.3	364.5	381.7	405.6	449.7	515.4	598.3	689.4
50°	314.5	316.7	324.9	325.7	330.9	342.1	364.5	391.4	443.7	510.9	599.0
52.5°	287.6	289.8	295.0	300.3	302.5	311.5	326.4	348.8	387.7	440.7	519.1
55°	260.7	263.7	268.9	272.6	274.9	282.3	291.3	313.0	343.6	380.9	445.2
57.5°	233.8	240.5	242.0	244.2	248.0	256.2	264.4	277.1	301.0	335.4	382.4
60°	208.4	210.6	215.9	218.1	221.8	226.3	236.8	246.5	263.7	290.6	333.1
62.5°	182.3	187.5	189.7	192.0	194.9	200.2	206.9	217.4	232.3	254.0	287.6
65°	159.8	160.6	165.1	168.1	171.0	174.8	181.5	191.2	200.2	220.3	245.0
67.5°	138.2	139.7	141.2	144.2	147.9	151.6	157.6	162.8	174.0	187.5	206.9
70°	117.3	117.3	121.0	123.2	122.5	127.0	131.5	137.4	145.7	158.3	174.0
72.5°	98.6	97.8	100.8	101.6	103.1	106.1	109.1	115.0	119.5	129.2	141.2
75°	78.4	79.9	81.4	81.4	83.7	85.9	88.9	91.9	97.1	103.1	112.0
77.5°	62.0	62.0	63.5	64.2	66.5	65.7	68.7	71.7	75.4	80.7	87.4
80°	45.6	47.1	47.1	47.1	47.8	48.6	51.5	53.8	56.0	59.8	62.7
82.5°	32.1	32.1	33.6	33.6	33.6	35.1	35.1	35.9	37.3	39.6	41.8
85°	20.2	20.2	20.2	20.9	20.2	20.9	22.4	21.7	22.4	23.9	23.9
87.5°	9.7	9.7	9.7	9.7	9.7	10.5	9.7	10.5	11.2	11.2	11.2
90°	18.3	18.0	17.7	17.5	17.1	16.3	15.6	14.8	14.0	12.8	11.5
92.5°	18.6	18.4	18.3	18.2	18.0	17.7	17.4	17.1	16.8	16.3	15.9
95°	30.5	30.7	30.8	30.9	30.5	29.7	29.0	28.2	27.4	26.3	25.2
97.5°	38.3	38.1	38.0	37.9	37.7	37.2	36.7	36.3	35.8	33.3	30.8
100°	46.4	46.1	45.8	45.6	45.0	43.7	42.5	41.2	40.0	37.4	34.7
102.5°	50.3	49.8	49.3	49.1	48.2	46.5	44.8	43.1	41.4	39.8	38.2
105°	52.1	51.4	50.8	50.5	49.6	47.9	46.2	44.5	42.8	41.4	40.0
107.5°	53.5	52.8	52.2	51.9	51.0	49.3	47.6	45.9	44.2	42.8	41.4
110°	54.2	53.5	52.9	52.6	60.4	76.0	91.6	107.2	122.8	167.8	212.9

TEST NUMBER: P998566

CATALOG NUMBER: SA2XXDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	55.2	54.7	54.2	54.0	87.6	154.8	222.0	289.2	356.4	359.0	361.7
115°	79.9	91.2	102.4	108.0	144.1	216.3	288.4	360.6	432.8	428.9	425.0
117.5°	268.3	309.1	350.0	370.4	381.5	403.8	426.1	448.4	470.7	468.1	465.4
120°	470.0	491.0	512.1	522.6	521.7	519.8	517.9	516.1	514.2	511.4	508.6
122.5°	560.2	560.0	559.9	559.8	559.3	558.4	557.5	556.5	555.6	552.5	549.4
125°	598.9	598.4	597.9	597.7	597.2	596.1	595.0	593.9	592.8	589.8	586.9
127.5°	634.6	634.4	634.3	634.2	633.4	631.9	630.3	628.8	627.2	624.8	622.5
130°	667.5	667.7	667.8	667.9	667.0	665.3	663.6	661.8	660.1	658.4	656.7
132.5°	699.0	699.2	699.3	699.4	698.7	697.3	695.9	694.5	693.1	691.4	689.7
135°	729.5	729.8	730.1	730.3	729.5	728.0	726.4	724.9	723.3	721.9	720.5
137.5°	757.9	758.4	758.9	759.1	758.3	756.7	755.2	753.6	752.0	750.4	748.9
140°	784.5	785.2	786.0	786.4	785.7	784.3	782.9	781.5	780.1	778.4	776.7
142.5°	809.8	810.5	811.3	811.7	811.1	809.8	808.6	807.3	806.1	804.1	802.0
145°	832.9	833.6	834.4	834.8	834.3	833.2	832.1	831.0	829.9	827.3	824.6
147.5°	853.6	854.3	854.9	855.2	854.8	854.0	853.3	852.5	851.7	849.0	846.4
150°	872.9	873.6	874.4	874.8	874.3	873.4	872.5	871.5	870.6	868.1	865.6
152.5°	889.6	890.7	891.8	892.4	891.9	891.0	890.0	889.1	888.1	885.8	883.4
155°	904.7	905.9	907.2	907.8	907.3	906.4	905.5	904.5	903.6	901.7	899.9
157.5°	918.7	919.9	921.2	921.8	921.3	920.2	919.1	918.0	916.9	915.5	914.1
160°	930.3	931.4	932.5	933.0	932.5	931.6	930.7	929.7	928.8	927.9	926.9
162.5°	940.8	942.2	943.6	944.3	943.8	942.7	941.6	940.5	939.4	938.6	937.8
165°	950.0	951.1	952.2	952.7	952.2	951.1	950.0	948.9	947.8	947.3	946.9
167.5°	956.9	958.3	959.7	960.4	959.9	958.8	957.7	956.6	955.5	955.0	954.6
170°	962.5	963.9	965.3	966.0	965.5	964.4	963.3	962.2	961.1	960.8	960.5
172.5°	966.7	968.1	969.5	970.2	969.7	968.6	967.5	966.4	965.3	965.0	964.7
175°	969.1	970.7	972.2	973.0	972.5	971.4	970.3	969.2	968.1	967.8	967.5
177.5°	970.2	971.6	973.0	973.7	973.2	972.1	971.0	969.9	968.8	968.6	968.5
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P998566

CATALOG NUMBER: SA2XXDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	997.2	993.4	991.2	992.7	988.2	977.0	977.0	980.7	976.2	971.8	965.0
5°	1024.8	1017.3	1012.8	1012.1	1001.6	983.7	980.0	976.2	966.5	956.1	944.9
7.5°	1051.7	1038.2	1030.8	1025.5	1010.6	987.4	977.7	969.5	953.8	938.1	924.0
10°	1074.1	1054.7	1045.7	1037.5	1018.1	988.9	973.3	958.3	938.1	918.0	900.1
12.5°	1092.0	1069.6	1058.4	1046.5	1022.6	984.5	965.0	941.1	921.0	894.1	876.2
15°	1121.9	1075.6	1065.1	1053.9	1029.3	977.0	953.1	926.2	898.6	862.7	843.3
17.5°	1145.8	1083.8	1083.1	1059.2	1027.0	974.0	937.4	902.3	872.4	836.6	805.9
20°	1160.0	1096.5	1084.5	1059.9	1019.6	953.8	915.7	876.9	844.8	801.5	770.8
22.5°	1171.9	1114.4	1083.1	1053.2	1003.9	947.1	891.1	854.5	810.4	763.4	734.2
25°	1176.4	1118.2	1085.3	1050.9	992.7	927.7	864.2	824.6	775.3	732.7	693.2
27.5°	1177.2	1117.4	1077.1	1041.2	977.0	902.3	837.3	795.5	741.0	691.7	652.1
30°	1169.7	1109.2	1072.6	1033.8	962.1	879.1	804.4	758.1	699.9	650.6	609.5
32.5°	1147.3	1092.8	1062.9	1020.3	942.6	847.0	773.1	721.5	660.3	611.7	572.2
35°	1109.9	1072.6	1039.7	1000.1	917.2	817.1	741.7	681.2	619.2	572.9	535.6
37.5°	1063.6	1043.5	1012.8	974.0	888.1	790.3	706.6	639.4	577.4	532.6	496.0
40°	1000.9	1006.1	976.2	941.1	853.7	753.7	661.0	596.8	538.5	496.7	460.9
42.5°	932.9	954.6	937.4	903.8	815.7	713.3	627.4	556.5	499.7	456.4	426.5
45°	859.7	897.1	886.6	862.0	776.1	670.7	579.6	510.9	460.9	419.0	392.9
47.5°	779.8	832.8	832.8	814.9	732.0	628.2	538.5	468.3	419.0	389.2	363.8
50°	698.4	758.1	767.8	755.9	682.7	579.6	488.5	425.0	382.4	353.3	334.6
52.5°	613.2	682.7	700.6	694.6	630.4	533.3	447.4	385.4	346.6	321.2	304.7
55°	531.8	612.5	631.9	634.1	574.4	482.5	401.9	347.3	310.0	292.8	278.6
57.5°	454.9	532.6	554.2	558.0	517.6	436.2	359.3	311.5	277.9	263.7	252.5
60°	389.2	454.1	482.5	490.7	455.6	382.4	319.7	273.4	248.0	234.5	224.1
62.5°	335.4	387.7	417.5	419.8	404.1	335.4	278.6	239.8	218.1	206.2	200.9
65°	283.1	330.1	348.1	357.0	344.3	290.6	240.5	208.4	191.2	180.8	175.5
67.5°	241.3	271.1	286.1	298.0	285.3	245.0	204.7	178.5	165.8	155.4	152.4
70°	197.9	222.6	233.8	245.7	234.5	203.9	174.8	150.9	139.7	131.5	127.7
72.5°	158.3	177.8	188.2	195.7	189.0	163.6	139.7	123.2	115.0	109.1	106.8
75°	125.5	138.9	144.9	150.1	147.1	127.7	112.8	99.3	91.9	86.6	85.2
77.5°	95.6	105.3	112.0	113.5	109.8	97.1	84.4	76.2	70.2	67.2	65.7
80°	68.0	73.9	77.7	79.9	76.2	71.0	62.0	56.0	50.8	47.1	46.3
82.5°	45.6	48.6	51.5	50.8	49.3	44.8	39.6	36.6	34.4	31.4	31.4
85°	26.1	26.9	28.4	29.1	28.4	25.4	22.4	20.9	19.4	17.2	17.2
87.5°	11.2	12.0	12.0	12.7	11.2	11.2	9.7	8.2	8.2	7.5	6.7
90°	10.3	9.0	8.4	7.5	5.8	4.1	2.4	0.7	2.4	4.1	5.8
92.5°	15.4	14.9	14.7	15.0	15.6	16.3	16.9	17.5	16.9	16.3	15.6
95°	24.1	23.0	22.4	25.0	30.1	35.3	40.4	45.6	40.4	35.3	30.1
97.5°	28.3	25.8	24.6	31.0	43.8	56.5	69.3	82.1	69.3	56.5	43.8
100°	32.1	29.4	28.1	38.8	60.1	81.5	102.8	124.2	102.8	81.5	60.1
102.5°	126.5	154.9	169.1	169.3	169.6	169.9	170.2	170.5	170.2	169.9	169.6
105°	170.5	213.0	234.3	232.0	227.3	222.6	218.0	213.3	218.0	222.6	227.3
107.5°	201.8	254.3	280.6	278.7	274.8	270.9	267.0	263.1	267.0	270.9	274.8
110°	257.9	303.0	325.5	323.9	320.6	317.3	314.1	310.8	314.1	317.3	320.6

TEST NUMBER: P998566

CATALOG NUMBER: SA2XXDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	364.3	367.0	368.3	366.9	364.1	361.3	358.5	355.7	358.5	361.3	364.1
115°	421.1	417.2	415.3	414.0	411.3	408.7	406.0	403.4	406.0	408.7	411.3
117.5°	462.8	460.1	458.8	457.2	454.1	451.0	447.9	444.8	447.9	451.0	454.1
120°	505.8	503.0	501.6	500.4	498.1	495.8	493.4	491.1	493.4	495.8	498.1
122.5°	546.3	543.2	541.6	540.4	537.9	535.4	532.9	530.4	532.9	535.4	537.9
125°	583.9	581.0	579.5	578.5	576.4	574.4	572.3	570.3	572.3	574.4	576.4
127.5°	620.1	617.8	616.6	615.5	613.3	611.2	609.0	606.8	609.0	611.2	613.3
130°	655.0	653.3	652.4	651.2	648.7	646.2	643.7	641.2	643.7	646.2	648.7
132.5°	688.0	686.3	685.4	684.4	682.4	680.3	678.3	676.3	678.3	680.3	682.4
135°	719.1	717.7	717.0	715.7	713.2	710.7	708.2	705.7	708.2	710.7	713.2
137.5°	747.3	745.8	745.0	744.1	742.2	740.3	738.5	736.6	738.5	740.3	742.2
140°	775.0	773.3	772.4	771.8	770.5	769.3	768.0	766.8	768.0	769.3	770.5
142.5°	800.0	797.9	796.9	796.4	795.3	794.2	793.1	792.0	793.1	794.2	795.3
145°	822.0	819.3	818.0	818.1	818.2	818.4	818.5	818.7	818.5	818.4	818.2
147.5°	843.7	841.0	839.7	839.9	840.4	840.9	841.3	841.8	841.3	840.9	840.4
150°	863.1	860.6	859.4	859.9	861.0	862.1	863.2	864.3	863.2	862.1	861.0
152.5°	881.1	878.8	877.6	878.2	879.5	880.7	882.0	883.2	882.0	880.7	879.5
155°	898.0	896.1	895.2	895.9	897.3	898.7	900.1	901.5	900.1	898.7	897.3
157.5°	912.7	911.3	910.6	911.2	912.5	913.7	915.0	916.2	915.0	913.7	912.5
160°	926.0	925.1	924.6	925.1	926.0	926.9	927.9	928.8	927.9	926.9	926.0
162.5°	937.0	936.2	935.8	936.3	937.2	938.2	939.1	940.1	939.1	938.2	937.2
165°	946.4	945.9	945.7	946.2	947.1	948.0	949.0	949.9	949.0	948.0	947.1
167.5°	954.1	953.6	953.4	953.9	954.8	955.7	956.7	957.6	956.7	955.7	954.8
170°	960.2	959.9	959.7	960.2	961.1	962.0	963.0	963.9	963.0	962.0	961.1
172.5°	964.4	964.1	963.9	964.4	965.3	966.2	967.2	968.1	967.2	966.2	965.3
175°	967.2	966.9	966.7	967.2	968.3	969.4	970.5	971.6	970.5	969.4	968.3
177.5°	968.3	968.2	968.1	968.6	969.7	970.8	971.9	973.0	971.9	970.8	969.7
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P998566

CATALOG NUMBER: SA2XXDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	961.3	965.0	964.3	956.8	948.6	941.9	929.2	930.7	926.2	926.9	931.4
5°	937.4	937.4	934.4	924.0	910.5	903.0	888.9	885.1	876.2	875.4	874.7
7.5°	912.0	908.3	904.5	889.6	873.2	861.2	841.8	837.3	828.3	822.4	819.4
10°	882.1	876.9	869.4	852.3	832.1	817.1	797.0	791.0	773.8	766.4	761.9
12.5°	849.3	846.3	834.3	820.1	787.3	770.8	741.7	747.7	730.5	715.6	713.3
15°	816.4	805.2	798.5	775.3	735.7	728.3	705.1	693.2	677.5	665.5	665.5
17.5°	784.3	767.1	752.2	727.5	698.4	677.5	660.3	654.3	634.9	622.9	620.7
20°	741.7	722.3	718.6	683.4	663.3	640.1	623.7	608.8	594.6	589.3	585.6
22.5°	701.4	679.0	673.0	643.1	622.9	599.8	583.4	572.9	562.4	558.7	552.0
25°	658.0	644.6	635.6	603.5	581.1	559.5	548.2	540.8	531.1	530.3	525.8
27.5°	616.2	603.5	594.6	563.9	547.5	527.3	518.4	510.2	504.9	502.7	500.4
30°	580.4	566.2	555.7	533.3	513.1	496.7	489.2	484.0	481.0	477.3	476.5
32.5°	540.8	532.6	518.4	501.2	485.5	469.8	465.3	461.6	457.1	455.6	454.9
35°	507.2	496.0	487.0	467.6	460.9	447.4	442.2	439.2	433.2	431.7	430.2
37.5°	474.3	463.8	454.1	442.2	429.5	422.0	419.0	414.5	411.6	412.3	410.8
40°	441.4	433.2	425.8	413.1	405.6	401.9	395.9	391.4	389.9	390.6	389.9
42.5°	409.3	401.9	397.4	387.7	380.2	376.5	372.7	368.2	370.5	370.5	372.7
45°	380.2	373.5	370.5	363.0	358.5	352.6	348.8	348.1	351.1	350.3	350.3
47.5°	350.3	348.1	344.3	337.6	331.6	327.9	327.2	327.2	330.1	331.6	330.9
50°	327.2	322.7	318.2	313.0	308.5	307.0	304.7	306.2	309.2	309.2	310.7
52.5°	298.0	295.0	293.5	289.1	286.1	286.1	286.1	286.8	289.1	291.3	290.6
55°	272.6	270.4	268.9	266.7	262.9	263.7	262.9	264.4	266.7	268.9	270.4
57.5°	245.7	245.0	243.5	239.8	239.8	239.0	241.3	242.0	245.7	247.2	249.5
60°	221.8	219.6	219.6	216.6	216.6	216.6	218.9	221.1	224.1	224.8	226.3
62.5°	196.4	196.4	195.7	193.5	193.5	195.7	196.4	199.4	200.9	200.9	203.2
65°	172.5	171.8	171.0	171.8	172.5	172.5	174.8	176.3	177.8	178.5	179.3
67.5°	148.6	147.9	149.4	148.6	150.1	153.1	152.4	154.6	156.9	156.9	157.6
70°	126.2	127.7	127.0	128.5	127.7	129.2	131.5	132.2	132.2	133.0	135.2
72.5°	105.3	105.3	105.3	104.6	105.3	106.8	108.3	109.1	110.5	111.3	113.5
75°	85.2	85.2	83.7	85.2	85.2	86.6	88.1	88.1	88.1	89.6	91.9
77.5°	64.2	65.0	64.2	65.7	65.7	66.5	68.0	67.2	68.7	69.5	70.2
80°	47.1	46.3	46.3	46.3	47.1	47.1	48.6	49.3	49.3	51.5	50.0
82.5°	29.9	30.6	29.9	30.6	30.6	31.4	30.6	31.4	32.1	33.6	32.9
85°	17.2	16.4	16.4	17.2	16.4	16.4	17.2	16.4	17.2	16.4	17.2
87.5°	6.7	6.0	6.0	6.0	6.0	5.2	5.2	4.5	4.5	4.5	3.7
90°	7.5	8.4	9.0	10.3	11.5	12.8	14.0	14.8	15.6	16.3	17.1
92.5°	15.0	14.7	14.9	15.4	15.9	16.3	16.8	17.1	17.4	17.7	18.0
95°	25.0	22.4	23.0	24.1	25.2	26.3	27.4	28.2	29.0	29.7	30.5
97.5°	31.0	24.6	25.8	28.3	30.8	33.3	35.8	36.3	36.7	37.2	37.7
100°	38.8	28.1	29.4	32.1	34.7	37.4	40.0	41.2	42.5	43.7	45.0
102.5°	169.3	169.1	154.9	126.5	98.2	69.8	41.4	43.1	44.8	46.5	48.2
105°	232.0	234.3	213.0	170.5	127.9	85.4	42.8	44.5	46.2	47.9	49.6
107.5°	278.7	280.6	254.3	201.8	149.3	96.7	44.2	45.9	47.6	49.3	51.0
110°	323.9	325.5	303.0	257.9	212.9	167.8	122.8	107.2	91.6	76.0	60.4

TEST NUMBER: P998566

CATALOG NUMBER: SA2XXDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	366.9	368.3	367.0	364.3	361.7	359.0	356.4	289.2	222.0	154.8	87.6
115°	414.0	415.3	417.2	421.1	425.0	428.9	432.8	360.6	288.4	216.3	144.1
117.5°	457.2	458.8	460.1	462.8	465.4	468.1	470.7	448.4	426.1	403.8	381.5
120°	500.4	501.6	503.0	505.8	508.6	511.4	514.2	516.1	517.9	519.8	521.7
122.5°	540.4	541.6	543.2	546.3	549.4	552.5	555.6	556.5	557.5	558.4	559.3
125°	578.5	579.5	581.0	583.9	586.9	589.8	592.8	593.9	595.0	596.1	597.2
127.5°	615.5	616.6	617.8	620.1	622.5	624.8	627.2	628.8	630.3	631.9	633.4
130°	651.2	652.4	653.3	655.0	656.7	658.4	660.1	661.8	663.6	665.3	667.0
132.5°	684.4	685.4	686.3	688.0	689.7	691.4	693.1	694.5	695.9	697.3	698.7
135°	715.7	717.0	717.7	719.1	720.5	721.9	723.3	724.9	726.4	728.0	729.5
137.5°	744.1	745.0	745.8	747.3	748.9	750.4	752.0	753.6	755.2	756.7	758.3
140°	771.8	772.4	773.3	775.0	776.7	778.4	780.1	781.5	782.9	784.3	785.7
142.5°	796.4	796.9	797.9	800.0	802.0	804.1	806.1	807.3	808.6	809.8	811.1
145°	818.1	818.0	819.3	822.0	824.6	827.3	829.9	831.0	832.1	833.2	834.3
147.5°	839.9	839.7	841.0	843.7	846.4	849.0	851.7	852.5	853.3	854.0	854.8
150°	859.9	859.4	860.6	863.1	865.6	868.1	870.6	871.5	872.5	873.4	874.3
152.5°	878.2	877.6	878.8	881.1	883.4	885.8	888.1	889.1	890.0	891.0	891.9
155°	895.9	895.2	896.1	898.0	899.9	901.7	903.6	904.5	905.5	906.4	907.3
157.5°	911.2	910.6	911.3	912.7	914.1	915.5	916.9	918.0	919.1	920.2	921.3
160°	925.1	924.6	925.1	926.0	926.9	927.9	928.8	929.7	930.7	931.6	932.5
162.5°	936.3	935.8	936.2	937.0	937.8	938.6	939.4	940.5	941.6	942.7	943.8
165°	946.2	945.7	945.9	946.4	946.9	947.3	947.8	948.9	950.0	951.1	952.2
167.5°	953.9	953.4	953.6	954.1	954.6	955.0	955.5	956.6	957.7	958.8	959.9
170°	960.2	959.7	959.9	960.2	960.5	960.8	961.1	962.2	963.3	964.4	965.5
172.5°	964.4	963.9	964.1	964.4	964.7	965.0	965.3	966.4	967.5	968.6	969.7
175°	967.2	966.7	966.9	967.2	967.5	967.8	968.1	969.2	970.3	971.4	972.5
177.5°	968.6	968.1	968.2	968.3	968.5	968.6	968.8	969.9	971.0	972.1	973.2
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P998566

CATALOG NUMBER: SA2XXDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	926.2	928.4	923.2	921.7	923.2	918.0	919.5	921.0	921.0	923.2	924.7
5°	872.4	869.4	864.2	862.7	861.2	863.5	862.0	864.2	864.9	870.2	870.9
7.5°	819.4	814.9	810.4	805.9	804.4	800.7	804.4	804.4	809.7	808.2	811.9
10°	756.6	755.9	749.9	747.7	744.7	738.7	746.9	744.7	748.4	755.1	756.6
12.5°	710.3	702.1	705.9	695.4	699.1	693.2	693.9	693.9	699.9	700.6	699.1
15°	666.3	659.5	649.8	645.4	643.1	640.1	649.8	650.6	646.1	656.6	652.8
17.5°	621.4	621.4	612.5	610.2	604.3	607.3	605.8	606.5	605.0	612.5	616.2
20°	582.6	578.9	575.9	576.6	569.2	567.7	566.2	567.7	572.9	578.1	579.6
22.5°	551.2	549.0	541.5	543.0	537.0	539.3	537.8	541.5	542.3	542.3	547.5
25°	521.4	518.4	519.1	516.1	513.9	513.9	511.6	513.9	516.9	518.4	519.1
27.5°	499.0	496.7	493.0	490.7	492.2	488.5	491.5	493.7	493.7	492.2	493.7
30°	472.1	473.6	473.6	466.1	469.1	467.6	469.8	471.3	471.3	472.1	470.6
32.5°	454.1	449.7	448.9	448.2	448.2	445.2	445.2	447.4	448.2	448.9	451.1
35°	430.2	430.2	426.5	428.7	425.8	426.5	425.8	426.5	428.0	425.8	428.0
37.5°	408.6	409.3	407.8	409.3	410.1	408.6	407.1	410.1	408.6	408.6	407.1
40°	389.9	389.2	389.9	389.9	389.9	390.6	389.2	389.2	389.2	387.7	386.2
42.5°	374.2	369.7	371.2	372.0	369.7	369.7	370.5	369.7	372.0	367.5	367.5
45°	351.8	350.3	351.1	351.1	352.6	350.3	351.8	352.6	350.3	349.6	348.1
47.5°	331.6	333.1	331.6	333.1	333.1	334.6	331.6	332.4	333.1	330.1	327.9
50°	311.5	311.5	313.7	313.0	313.7	312.2	312.2	311.5	312.2	310.7	308.5
52.5°	292.8	290.6	294.3	293.5	292.8	292.1	291.3	292.1	290.6	289.1	289.1
55°	269.6	269.6	271.9	272.6	272.6	271.1	269.6	270.4	269.6	268.9	268.1
57.5°	251.0	248.0	249.5	250.2	250.2	248.0	249.5	248.0	248.0	248.7	246.5
60°	227.1	227.1	225.6	227.8	227.8	226.3	226.3	227.1	225.6	224.8	224.1
62.5°	201.7	202.4	204.7	205.4	206.2	204.7	203.2	203.9	203.9	201.7	202.4
65°	180.0	181.5	184.5	183.7	182.3	183.0	181.5	182.3	180.0	180.8	178.5
67.5°	159.1	158.3	159.1	159.1	160.6	159.8	158.3	158.3	157.6	159.8	157.6
70°	136.7	136.7	136.7	136.7	137.4	138.2	136.7	135.2	135.9	134.4	133.7
72.5°	113.5	114.3	113.5	115.0	112.8	114.3	114.3	113.5	112.8	112.8	112.8
75°	91.9	93.4	91.1	91.9	91.1	92.6	91.9	91.9	90.4	89.6	90.4
77.5°	70.2	71.0	69.5	70.2	69.5	70.2	70.2	69.5	69.5	69.5	69.5
80°	50.0	50.8	50.0	49.3	48.6	50.0	48.6	49.3	50.0	49.3	50.8
82.5°	32.1	32.1	31.4	32.1	30.6	30.6	31.4	31.4	30.6	32.1	30.6
85°	15.7	15.7	17.2	15.7	14.9	14.9	14.9	15.7	14.9	16.4	15.7
87.5°	3.7	3.0	3.7	3.7	3.0	3.0	3.7	3.0	3.7	4.5	3.0
90°	17.5	17.7	18.0	18.3	18.6	18.9	18.6	18.3	18.0	17.7	17.5
92.5°	18.2	18.3	18.4	18.6	18.7	18.9	18.7	18.6	18.4	18.3	18.2
95°	30.9	30.8	30.7	30.5	30.4	30.2	30.4	30.5	30.7	30.8	30.9
97.5°	37.9	38.0	38.1	38.3	38.4	38.6	38.4	38.3	38.1	38.0	37.9
100°	45.6	45.8	46.1	46.4	46.7	47.0	46.7	46.4	46.1	45.8	45.6
102.5°	49.1	49.3	49.8	50.3	50.7	51.2	50.7	50.3	49.8	49.3	49.1
105°	50.5	50.8	51.4	52.1	52.7	53.3	52.7	52.1	51.4	50.8	50.5
107.5°	51.9	52.2	52.8	53.5	54.1	54.7	54.1	53.5	52.8	52.2	51.9
110°	52.6	52.9	53.5	54.2	54.8	55.4	54.8	54.2	53.5	52.9	52.6

TEST NUMBER: P998566

CATALOG NUMBER: SA2XXDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	54.0	54.2	54.7	55.2	55.6	56.1	55.6	55.2	54.7	54.2	54.0
115°	108.0	102.4	91.2	79.9	68.7	57.5	68.7	79.9	91.2	102.4	108.0
117.5°	370.4	350.0	309.1	268.3	227.4	186.6	227.4	268.3	309.1	350.0	370.4
120°	522.6	512.1	491.0	470.0	448.9	427.9	448.9	470.0	491.0	512.1	522.6
122.5°	559.8	559.9	560.0	560.2	560.3	560.5	560.3	560.2	560.0	559.9	559.8
125°	597.7	597.9	598.4	598.9	599.3	599.8	599.3	598.9	598.4	597.9	597.7
127.5°	634.2	634.3	634.4	634.6	634.7	634.9	634.7	634.6	634.4	634.3	634.2
130°	667.9	667.8	667.7	667.5	667.4	667.2	667.4	667.5	667.7	667.8	667.9
132.5°	699.4	699.3	699.2	699.0	698.9	698.7	698.9	699.0	699.2	699.3	699.4
135°	730.3	730.1	729.8	729.5	729.2	728.9	729.2	729.5	729.8	730.1	730.3
137.5°	759.1	758.9	758.4	757.9	757.5	757.0	757.5	757.9	758.4	758.9	759.1
140°	786.4	786.0	785.2	784.5	783.7	782.9	783.7	784.5	785.2	786.0	786.4
142.5°	811.7	811.3	810.5	809.8	809.0	808.2	809.0	809.8	810.5	811.3	811.7
145°	834.8	834.4	833.6	832.9	832.1	831.3	832.1	832.9	833.6	834.4	834.8
147.5°	855.2	854.9	854.3	853.6	853.0	852.4	853.0	853.6	854.3	854.9	855.2
150°	874.8	874.4	873.6	872.9	872.1	871.3	872.1	872.9	873.6	874.4	874.8
152.5°	892.4	891.8	890.7	889.6	888.5	887.4	888.5	889.6	890.7	891.8	892.4
155°	907.8	907.2	905.9	904.7	903.4	902.2	903.4	904.7	905.9	907.2	907.8
157.5°	921.8	921.2	919.9	918.7	917.4	916.2	917.4	918.7	919.9	921.2	921.8
160°	933.0	932.5	931.4	930.3	929.2	928.1	929.2	930.3	931.4	932.5	933.0
162.5°	944.3	943.6	942.2	940.8	939.4	938.0	939.4	940.8	942.2	943.6	944.3
165°	952.7	952.2	951.1	950.0	948.9	947.8	948.9	950.0	951.1	952.2	952.7
167.5°	960.4	959.7	958.3	956.9	955.5	954.1	955.5	956.9	958.3	959.7	960.4
170°	966.0	965.3	963.9	962.5	961.1	959.7	961.1	962.5	963.9	965.3	966.0
172.5°	970.2	969.5	968.1	966.7	965.3	963.9	965.3	966.7	968.1	969.5	970.2
175°	973.0	972.2	970.7	969.1	967.6	966.0	967.6	969.1	970.7	972.2	973.0
177.5°	973.7	973.0	971.6	970.2	968.8	967.4	968.8	970.2	971.6	973.0	973.7
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P998566

CATALOG NUMBER: SA2XXDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	922.5	928.4	926.2	918.0	927.7	927.7	934.4	934.4	942.6	945.6	950.1
5°	870.2	874.7	878.4	874.7	881.4	891.8	897.8	903.0	914.2	918.7	925.5
7.5°	814.2	822.4	826.1	826.1	837.3	849.3	861.2	868.7	884.4	890.3	897.1
10°	759.6	769.3	776.8	776.1	794.7	802.2	817.1	834.3	850.0	859.0	868.7
12.5°	702.1	707.3	717.8	732.7	737.2	750.7	767.8	789.5	817.9	826.1	840.3
15°	654.3	668.5	676.7	683.4	693.9	706.6	725.3	746.2	774.6	792.5	807.4
17.5°	614.0	632.7	637.9	636.4	649.8	669.3	690.9	706.6	732.0	753.7	767.8
20°	581.1	588.6	597.5	601.3	611.7	632.7	653.6	671.5	692.4	709.6	726.0
22.5°	548.2	554.2	561.7	568.4	576.6	588.6	608.8	631.2	651.3	667.8	686.4
25°	521.4	525.1	531.8	537.0	546.0	554.2	568.4	593.1	617.0	626.7	643.1
27.5°	495.2	498.2	502.7	508.7	513.1	521.4	534.1	554.2	578.9	588.6	611.0
30°	472.1	474.3	478.8	481.8	484.0	493.7	503.4	519.1	537.8	551.2	567.7
32.5°	450.4	452.6	457.1	457.9	460.9	466.1	475.0	489.2	505.7	516.9	531.1
35°	426.5	428.0	432.5	434.0	436.2	440.7	447.4	457.9	472.8	481.0	493.7
37.5°	407.8	407.1	410.1	412.3	415.3	417.5	419.8	430.2	441.4	448.9	458.6
40°	387.7	386.2	386.9	389.9	391.4	394.4	394.4	404.8	412.3	418.3	425.8
42.5°	367.5	366.7	365.3	366.7	368.2	369.0	369.7	377.2	384.7	389.9	398.1
45°	347.3	346.6	345.1	345.8	345.8	347.3	349.6	352.6	357.8	362.3	366.7
47.5°	328.7	327.2	324.9	324.2	325.7	325.7	325.7	328.7	333.9	335.4	339.9
50°	309.2	307.0	304.0	302.5	302.5	301.8	303.3	304.0	308.5	310.0	313.7
52.5°	288.3	286.8	283.8	280.8	281.6	280.1	280.8	281.6	283.1	285.3	287.6
55°	267.4	264.4	262.2	261.4	259.2	259.2	256.9	259.9	259.2	259.9	262.9
57.5°	247.2	244.2	240.5	239.0	236.8	236.0	234.5	233.8	234.5	236.8	239.0
60°	223.3	221.8	219.6	217.4	215.9	213.6	212.1	212.1	211.4	211.4	212.1
62.5°	200.2	199.4	196.4	195.7	194.2	192.7	190.5	189.0	189.0	190.5	191.2
65°	177.8	177.0	174.8	174.0	170.3	168.8	168.1	167.3	165.8	165.8	165.8
67.5°	156.9	154.6	154.6	150.9	147.9	146.4	144.9	144.2	144.2	144.2	144.9
70°	133.7	133.7	131.5	129.2	126.2	127.0	124.7	122.5	122.5	121.0	121.8
72.5°	111.3	110.5	108.3	107.6	105.3	103.1	101.6	103.1	100.8	100.1	100.8
75°	89.6	88.9	87.4	85.9	86.6	84.4	82.2	81.4	81.4	79.9	79.9
77.5°	68.7	70.2	67.2	66.5	65.0	63.5	62.7	62.0	62.0	62.0	63.5
80°	47.8	48.6	48.6	47.1	47.8	45.6	45.6	45.6	43.3	44.1	44.8
82.5°	30.6	30.6	29.9	30.6	29.9	29.9	29.1	29.1	28.4	28.4	29.1
85°	17.2	16.4	15.7	17.2	16.4	16.4	15.7	15.7	15.7	15.7	15.7
87.5°	3.7	4.5	4.5	4.5	4.5	5.2	5.2	5.2	6.0	6.0	6.0
90°	17.1	16.3	15.6	14.8	14.0	12.8	11.5	10.3	9.0	8.4	7.5
92.5°	18.0	17.7	17.4	17.1	16.8	16.3	15.9	15.4	14.9	14.7	15.0
95°	30.5	29.7	29.0	28.2	27.4	26.3	25.2	24.1	23.0	22.4	25.0
97.5°	37.7	37.2	36.7	36.3	35.8	33.3	30.8	28.3	25.8	24.6	31.0
100°	45.0	43.7	42.5	41.2	40.0	37.4	34.7	32.1	29.4	28.1	38.8
102.5°	48.2	46.5	44.8	43.1	41.4	69.8	98.2	126.5	154.9	169.1	169.3
105°	49.6	47.9	46.2	44.5	42.8	85.4	127.9	170.5	213.0	234.3	232.0
107.5°	51.0	49.3	47.6	45.9	44.2	96.7	149.3	201.8	254.3	280.6	278.7
110°	60.4	76.0	91.6	107.2	122.8	167.8	212.9	257.9	303.0	325.5	323.9

TEST NUMBER: P998566

CATALOG NUMBER: SA2XXDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	87.6	154.8	222.0	289.2	356.4	359.0	361.7	364.3	367.0	368.3	366.9
115°	144.1	216.3	288.4	360.6	432.8	428.9	425.0	421.1	417.2	415.3	414.0
117.5°	381.5	403.8	426.1	448.4	470.7	468.1	465.4	462.8	460.1	458.8	457.2
120°	521.7	519.8	517.9	516.1	514.2	511.4	508.6	505.8	503.0	501.6	500.4
122.5°	559.3	558.4	557.5	556.5	555.6	552.5	549.4	546.3	543.2	541.6	540.4
125°	597.2	596.1	595.0	593.9	592.8	589.8	586.9	583.9	581.0	579.5	578.5
127.5°	633.4	631.9	630.3	628.8	627.2	624.8	622.5	620.1	617.8	616.6	615.5
130°	667.0	665.3	663.6	661.8	660.1	658.4	656.7	655.0	653.3	652.4	651.2
132.5°	698.7	697.3	695.9	694.5	693.1	691.4	689.7	688.0	686.3	685.4	684.4
135°	729.5	728.0	726.4	724.9	723.3	721.9	720.5	719.1	717.7	717.0	715.7
137.5°	758.3	756.7	755.2	753.6	752.0	750.4	748.9	747.3	745.8	745.0	744.1
140°	785.7	784.3	782.9	781.5	780.1	778.4	776.7	775.0	773.3	772.4	771.8
142.5°	811.1	809.8	808.6	807.3	806.1	804.1	802.0	800.0	797.9	796.9	796.4
145°	834.3	833.2	832.1	831.0	829.9	827.3	824.6	822.0	819.3	818.0	818.1
147.5°	854.8	854.0	853.3	852.5	851.7	849.0	846.4	843.7	841.0	839.7	839.9
150°	874.3	873.4	872.5	871.5	870.6	868.1	865.6	863.1	860.6	859.4	859.9
152.5°	891.9	891.0	890.0	889.1	888.1	885.8	883.4	881.1	878.8	877.6	878.2
155°	907.3	906.4	905.5	904.5	903.6	901.7	899.9	898.0	896.1	895.2	895.9
157.5°	921.3	920.2	919.1	918.0	916.9	915.5	914.1	912.7	911.3	910.6	911.2
160°	932.5	931.6	930.7	929.7	928.8	927.9	926.9	926.0	925.1	924.6	925.1
162.5°	943.8	942.7	941.6	940.5	939.4	938.6	937.8	937.0	936.2	935.8	936.3
165°	952.2	951.1	950.0	948.9	947.8	947.3	946.9	946.4	945.9	945.7	946.2
167.5°	959.9	958.8	957.7	956.6	955.5	955.0	954.6	954.1	953.6	953.4	953.9
170°	965.5	964.4	963.3	962.2	961.1	960.8	960.5	960.2	959.9	959.7	960.2
172.5°	969.7	968.6	967.5	966.4	965.3	965.0	964.7	964.4	964.1	963.9	964.4
175°	972.5	971.4	970.3	969.2	968.1	967.8	967.5	967.2	966.9	966.7	967.2
177.5°	973.2	972.1	971.0	969.9	968.8	968.6	968.5	968.3	968.2	968.1	968.6
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P998566

CATALOG NUMBER: SA2XXDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	971.8	971.8	971.8	971.8
2.5°	953.8	953.8	965.0	977.0
5°	932.9	938.1	956.1	972.5
7.5°	912.8	921.7	944.1	965.0
10°	888.1	900.1	927.7	952.3
12.5°	864.2	875.4	907.5	935.2
15°	830.6	844.8	879.1	913.5
17.5°	797.0	811.2	853.0	893.3
20°	757.4	776.1	823.1	876.9
22.5°	720.8	743.9	796.2	839.6
25°	680.5	716.3	764.9	820.9
27.5°	644.6	680.5	729.8	786.5
30°	604.3	640.9	691.7	743.9
32.5°	565.4	599.0	648.3	712.6
35°	525.1	557.2	605.0	670.0
37.5°	488.5	519.9	572.2	631.9
40°	452.6	485.5	530.3	590.1
42.5°	419.0	448.2	488.5	548.2
45°	388.4	409.3	446.7	502.7
47.5°	356.3	375.0	409.3	465.3
50°	326.4	342.1	372.0	424.3
52.5°	297.3	310.7	338.4	380.2
55°	271.1	283.8	304.0	345.1
57.5°	244.2	254.0	273.4	306.2
60°	218.1	227.1	242.8	269.6
62.5°	192.0	199.4	214.4	236.0
65°	168.8	174.8	186.0	204.7
67.5°	146.4	150.1	159.1	174.0
70°	124.7	127.7	135.2	147.1
72.5°	101.6	104.6	112.8	121.0
75°	82.2	82.9	88.9	95.6
77.5°	64.2	63.5	68.0	73.2
80°	44.1	46.3	50.0	52.3
82.5°	29.9	30.6	32.1	33.6
85°	16.4	17.2	17.2	19.4
87.5°	6.7	7.5	7.5	8.2
90°	5.8	4.1	2.4	0.7
92.5°	15.6	16.3	16.9	17.5
95°	30.1	35.3	40.4	45.6
97.5°	43.8	56.5	69.3	82.1
100°	60.1	81.5	102.8	124.2
102.5°	169.6	169.9	170.2	170.5
105°	227.3	222.6	218.0	213.3
107.5°	274.8	270.9	267.0	263.1
110°	320.6	317.3	314.1	310.8



TEST NUMBER: P998566

CATALOG NUMBER: SA2XXDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	364.1	361.3	358.5	355.7
115°	411.3	408.7	406.0	403.4
117.5°	454.1	451.0	447.9	444.8
120°	498.1	495.8	493.4	491.1
122.5°	537.9	535.4	532.9	530.4
125°	576.4	574.4	572.3	570.3
127.5°	613.3	611.2	609.0	606.8
130°	648.7	646.2	643.7	641.2
132.5°	682.4	680.3	678.3	676.3
135°	713.2	710.7	708.2	705.7
137.5°	742.2	740.3	738.5	736.6
140°	770.5	769.3	768.0	766.8
142.5°	795.3	794.2	793.1	792.0
145°	818.2	818.4	818.5	818.7
147.5°	840.4	840.9	841.3	841.8
150°	861.0	862.1	863.2	864.3
152.5°	879.5	880.7	882.0	883.2
155°	897.3	898.7	900.1	901.5
157.5°	912.5	913.7	915.0	916.2
160°	926.0	926.9	927.9	928.8
162.5°	937.2	938.2	939.1	940.1
165°	947.1	948.0	949.0	949.9
167.5°	954.8	955.7	956.7	957.6
170°	961.1	962.0	963.0	963.9
172.5°	965.3	966.2	967.2	968.1
175°	968.3	969.4	970.5	971.6
177.5°	969.7	970.8	971.9	973.0
180°	969.5	969.5	969.5	969.5

TEST NUMBER: P998566

CATALOG NUMBER: SA2XXDIP-B485D725UB2750-4F0-XX-W2A-A_3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.65	15.43	15.67	16.45	17.82	12.14	12.92	13.17	13.94	15.31
	3H	15.46	16.15	16.49	17.18	18.57	13.48	14.18	14.51	15.21	16.60
	4H	15.62	16.28	16.66	17.31	18.71	13.94	14.60	14.98	15.63	17.03
	6H	15.66	16.27	16.72	17.31	18.72	14.24	14.85	15.30	15.89	17.30
	8H	15.64	16.21	16.70	17.27	18.67	14.32	14.90	15.38	15.96	17.36
	12H	15.60	16.14	16.66	17.19	18.62	14.36	14.91	15.43	15.96	17.39
4H	2H	14.68	15.34	15.73	16.37	17.77	12.58	13.24	13.63	14.27	15.67
	3H	15.65	16.20	16.71	17.27	18.68	14.03	14.58	15.09	15.64	17.05
	4H	15.93	16.43	16.99	17.48	18.92	14.56	15.06	15.63	16.12	17.55
	6H	16.05	16.48	17.13	17.56	18.99	14.94	15.37	16.01	16.45	17.87
	8H	16.05	16.45	17.12	17.52	18.96	15.05	15.45	16.12	16.52	17.96
	12H	16.01	16.37	17.10	17.46	18.90	15.10	15.46	16.19	16.55	17.99
8H	4H	15.93	16.33	17.00	17.40	18.84	14.70	15.10	15.77	16.17	17.61
	6H	16.11	16.44	17.20	17.55	18.99	15.13	15.46	16.23	16.58	18.01
	8H	16.14	16.43	17.24	17.52	18.98	15.28	15.57	16.38	16.67	18.13
	12H	16.12	16.37	17.22	17.46	18.96	15.37	15.62	16.48	16.72	18.22
12H	4H	15.88	16.25	16.97	17.33	18.78	14.67	15.03	15.76	16.12	17.56
	6H	16.08	16.37	17.19	17.47	18.93	15.13	15.42	16.23	16.52	17.98
	8H	16.11	16.37	17.22	17.46	18.96	15.28	15.54	16.39	16.63	18.13