

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997952

Luminaire Tested: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P997952
REPORT IS A COMBINATION OF REPORTS P983689 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6277.0 lumens
Efficiency: N/A
Efficacy: 81.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997952

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P997952

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	68		
1	102	98	94	91	96	93	90	87	83	80	78	73	72	70	65	64	62	58		
2	94	87	81	75	88	82	77	72	73	69	66	65	62	59	58	56	54	50		
3	86	77	69	64	81	73	66	61	65	60	56	58	54	51	52	49	46	43		
4	79	68	61	55	74	65	58	53	58	53	48	52	48	44	47	43	40	37		
5	73	61	53	47	69	58	51	46	53	47	42	47	43	39	43	39	36	33		
6	67	55	47	42	64	53	46	40	48	42	37	43	38	35	39	35	32	29		
7	63	50	42	37	59	48	41	36	44	38	33	40	35	31	36	32	29	26		
8	58	46	38	33	55	44	37	32	40	34	30	36	31	28	33	29	26	24		
9	55	42	35	30	52	40	34	29	37	31	27	34	29	25	31	27	24	22		
10	51	39	32	27	48	37	31	26	34	29	25	31	26	23	28	24	22	20		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30413	30413	30413	30413
5°	30486	32427	30603	25799
10°	30132	35400	30321	21271
15°	29401	37339	29809	17916
20°	28943	35058	28943	15573
25°	28020	30119	28148	13925
30°	26503	23676	27007	12614
35°	25158	16372	25578	11542
40°	23613	12361	23882	10686
45°	21707	10158	22061	9762
50°	20059	8915	20095	8937
55°	18181	7596	18298	8040
60°	16177	6345	16401	7017
65°	14383	5161	14646	5992
70°	12598	4049	12919	4833
75°	10573	2940	10987	3505
80°	8255	1863	8846	2079
85°	5424	938	5848	694

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 31439 cd/sqm

TEST NUMBER: P997952

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.0	2.9
10°-20°	532.6	8.5
20°-30°	773.0	12.3
30°-40°	814.9	13.0
40°-50°	721.1	11.5
50°-60°	575.8	9.2
60°-70°	391.1	6.2
70°-80°	200.1	3.2
80°-90°	48.5	0.8
90°-100°	22.9	0.4
100°-110°	85.4	1.4
110°-120°	226.5	3.6
120°-130°	375.7	6.0
130°-140°	399.0	6.4
140°-150°	370.9	5.9
150°-160°	298.2	4.7
160°-170°	192.1	3.1
170°-180°	66.1	1.1
0°-30°	1488.7	23.7
0°-40°	2303.6	36.7
0°-60°	3600.5	57.4
0°-90°	4240.2	67.6
90°-120°	334.8	5.3
90°-150°	1480.4	23.6
90°-180°	2037.0	32.5
0°-180°	6277.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1921	1921	1921	1921	1921	
5°	1923	2146	1930	1707	1923	182
15°	1806	2638	1831	1266	1806	510
25°	1623	2198	1630	1016	1623	742
35°	1325	1196	1347	843	1325	829
45°	994	721	1010	693	994	771
55°	682	506	687	536	682	609
65°	405	312	412	362	405	402
75°	189	154	196	183	189	203
85°	38	40	41	30	38	45
90°	0	14	0	14	0	4
95°	33	22	33	22	33	39
105°	153	38	153	38	153	163
115°	289	41	289	41	289	285
125°	409	430	409	430	409	365
135°	506	522	506	522	506	391
145°	587	596	587	596	587	367
155°	646	646	646	646	646	298
165°	681	679	681	679	681	192
175°	696	692	696	692	696	66
180°	695	695	695	695	695	

TEST NUMBER: P997952

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1931.6	1936.1	1943.5	1944.9	1959.7	1971.5	1984.8	1984.8	1989.2	1987.8	1976.0
5°	1922.8	1936.1	1955.3	1971.5	1998.1	2009.9	2027.6	2040.9	2052.7	2061.6	2060.1
7.5°	1908.0	1931.6	1959.7	1990.7	2026.2	2046.8	2071.9	2095.6	2111.8	2126.6	2136.9
10°	1882.9	1922.8	1961.2	2002.5	2048.3	2076.4	2105.9	2136.9	2162.0	2190.1	2216.7
12.5°	1848.9	1906.5	1953.8	2008.4	2064.6	2095.6	2142.8	2166.5	2215.2	2286.1	2305.3
15°	1806.1	1884.4	1928.7	1998.1	2071.9	2097.1	2162.0	2200.4	2300.8	2345.2	2398.3
17.5°	1766.2	1853.4	1912.5	1992.2	2064.6	2113.3	2176.8	2255.1	2339.2	2402.7	2461.8
20°	1733.8	1817.9	1888.8	1977.4	2069.0	2131.0	2197.5	2292.0	2383.5	2448.5	2494.3
22.5°	1659.9	1767.7	1850.4	1949.4	2060.1	2145.8	2209.3	2312.7	2411.6	2451.5	2491.4
25°	1623.0	1716.0	1812.0	1924.3	2054.2	2156.1	2210.8	2326.0	2413.1	2427.9	2436.7
27.5°	1555.1	1659.9	1772.2	1900.6	2052.7	2138.4	2207.8	2312.7	2382.1	2371.7	2345.2
30°	1470.9	1599.4	1723.4	1862.2	2032.1	2125.1	2190.1	2286.1	2321.5	2268.4	2221.1
32.5°	1408.9	1530.0	1667.3	1828.3	2008.4	2097.1	2160.6	2235.9	2243.3	2147.3	2067.5
35°	1324.7	1459.1	1614.1	1784.0	1968.6	2048.3	2107.4	2153.2	2117.7	1983.3	1888.8
37.5°	1249.4	1382.3	1547.7	1720.5	1913.9	1992.2	2039.5	2046.8	1959.7	1841.6	1702.7
40°	1166.7	1304.0	1476.8	1658.4	1853.4	1921.3	1950.8	1928.7	1803.2	1665.8	1504.9
42.5°	1084.0	1219.8	1405.9	1592.0	1776.6	1834.2	1846.0	1785.4	1631.9	1470.9	1284.8
45°	993.9	1135.7	1321.7	1509.3	1688.0	1720.5	1721.9	1634.8	1453.2	1284.8	1112.0
47.5°	920.0	1051.5	1236.1	1423.6	1574.3	1596.4	1587.6	1487.1	1289.2	1100.2	949.6
50°	838.8	964.3	1147.5	1332.1	1460.6	1466.5	1444.3	1301.1	1107.6	934.8	815.2
52.5°	751.7	878.7	1047.0	1224.3	1339.5	1330.6	1287.8	1134.2	952.5	809.3	717.7
55°	682.3	794.5	952.5	1125.3	1206.5	1181.4	1134.2	977.6	834.4	713.3	633.5
57.5°	605.5	704.4	859.5	1010.1	1057.4	1033.8	986.5	840.3	707.4	615.8	562.7
60°	533.1	623.2	759.1	884.6	921.5	896.4	841.8	710.3	614.3	537.6	497.7
62.5°	466.7	544.9	658.7	773.8	788.6	763.5	716.2	609.9	527.2	466.7	437.1
65°	404.6	478.5	570.0	657.2	670.5	643.9	595.1	518.4	448.9	410.5	382.5
67.5°	344.1	403.2	484.4	547.9	555.3	530.2	490.3	428.3	385.4	344.1	323.4
70°	290.9	335.2	398.7	450.4	453.4	429.7	409.1	353.0	320.5	290.9	274.7
72.5°	239.2	270.3	319.0	357.4	358.9	344.1	324.9	289.5	261.4	240.7	224.5
75°	189.0	215.6	245.1	279.1	277.6	265.8	251.1	228.9	205.3	192.0	184.6
77.5°	144.7	161.0	184.6	206.8	206.8	200.8	192.0	175.7	161.0	147.7	140.3
80°	103.4	113.7	132.9	140.3	143.2	141.8	134.4	122.6	116.7	106.3	103.4
82.5°	66.5	73.8	82.7	90.1	94.5	91.6	90.1	84.2	75.3	72.4	69.4
85°	38.4	41.4	45.8	50.2	51.7	50.2	53.2	48.7	44.3	44.3	42.8
87.5°	16.2	17.7	20.7	20.7	22.2	22.2	20.7	22.2	22.2	20.7	19.2
90°	0.5	1.7	2.9	4.2	5.4	6.0	6.5	7.4	8.3	9.2	10.1
92.5°	12.6	12.2	11.7	11.3	10.8	10.6	10.8	11.1	11.4	11.8	12.1
95°	32.7	29.0	25.3	21.6	17.9	16.1	16.5	17.3	18.0	18.8	19.6
97.5°	58.8	49.6	40.5	31.3	22.2	17.6	18.5	20.3	22.0	23.8	25.6
100°	89.0	73.7	58.4	43.1	27.8	20.1	21.1	23.0	24.9	26.8	28.7
102.5°	122.2	122.0	121.8	121.5	121.3	121.2	111.0	90.7	70.4	50.0	29.7
105°	152.8	156.2	159.5	162.9	166.2	167.9	152.7	122.2	91.7	61.2	30.7
107.5°	188.5	191.3	194.1	196.9	199.7	201.1	182.3	144.6	107.0	69.3	31.7
110°	222.7	225.1	227.4	229.8	232.1	233.3	217.2	184.9	152.6	120.3	88.0

TEST NUMBER: P997952

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	254.9	256.9	258.9	260.9	262.9	263.9	263.0	261.1	259.2	257.3	255.4
115°	289.1	291.0	292.9	294.8	296.7	297.6	299.0	301.8	304.6	307.4	310.2
117.5°	318.7	320.9	323.2	325.4	327.7	328.8	329.7	331.6	333.5	335.4	337.3
120°	351.9	353.6	355.2	356.9	358.6	359.4	360.4	362.4	364.5	366.5	368.5
122.5°	380.1	381.9	383.7	385.4	387.2	388.1	389.2	391.5	393.7	396.0	398.2
125°	408.7	410.1	411.6	413.0	414.5	415.2	416.3	418.4	420.5	422.7	424.8
127.5°	434.9	436.5	438.0	439.6	441.1	441.9	442.7	444.4	446.1	447.7	449.4
130°	459.5	461.3	463.1	464.8	466.6	467.5	468.1	469.4	470.6	471.9	473.1
132.5°	484.6	486.1	487.5	489.0	490.5	491.2	491.8	493.0	494.3	495.5	496.7
135°	505.7	507.5	509.3	511.1	512.9	513.8	514.3	515.3	516.3	517.3	518.3
137.5°	527.9	529.2	530.6	531.9	533.2	533.9	534.5	535.6	536.7	537.8	538.9
140°	549.5	550.4	551.3	552.2	553.1	553.5	554.1	555.3	556.6	557.8	559.0
142.5°	567.6	568.4	569.2	569.9	570.7	571.1	571.8	573.3	574.7	576.2	577.6
145°	586.7	586.6	586.5	586.4	586.3	586.2	587.1	589.0	590.9	592.8	594.7
147.5°	603.3	603.0	602.6	602.3	602.0	601.8	602.7	604.6	606.5	608.4	610.3
150°	619.3	618.5	617.7	617.0	616.2	615.8	616.7	618.5	620.3	622.1	623.9
152.5°	632.9	632.0	631.1	630.2	629.3	628.9	629.7	631.4	633.1	634.7	636.4
155°	646.0	645.0	644.0	643.0	642.0	641.5	642.2	643.5	644.8	646.2	647.5
157.5°	656.5	655.6	654.7	653.8	652.9	652.5	653.0	654.0	655.1	656.1	657.1
160°	665.6	664.9	664.3	663.6	662.9	662.6	662.9	663.6	664.3	664.9	665.6
162.5°	673.6	672.9	672.3	671.6	670.9	670.6	670.9	671.4	672.0	672.5	673.1
165°	680.7	680.0	679.4	678.7	678.0	677.7	677.9	678.2	678.5	678.9	679.2
167.5°	686.2	685.5	684.9	684.2	683.5	683.2	683.4	683.7	684.0	684.4	684.7
170°	690.7	690.0	689.4	688.7	688.0	687.7	687.8	688.0	688.3	688.5	688.7
172.5°	693.7	693.0	692.4	691.7	691.0	690.7	690.8	691.0	691.3	691.5	691.7
175°	696.3	695.5	694.7	693.9	693.1	692.7	692.8	693.0	693.3	693.5	693.7
177.5°	697.3	696.5	695.7	694.9	694.1	693.7	693.8	693.9	694.0	694.2	694.3
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P997952

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1996.6	1998.1	2001.1	2015.8	2023.2	2024.7	2018.8	2032.1	2036.5	2032.1	2029.1
5°	2091.1	2100.0	2117.7	2136.9	2135.4	2136.9	2145.8	2154.6	2157.6	2145.8	2150.2
7.5°	2173.8	2191.6	2210.8	2240.3	2240.3	2255.1	2261.0	2268.4	2286.1	2277.2	2274.3
10°	2268.4	2292.0	2327.4	2374.7	2376.2	2390.9	2405.7	2429.3	2436.7	2430.8	2433.8
12.5°	2386.5	2432.3	2435.2	2486.9	2510.6	2513.5	2537.1	2532.7	2547.5	2547.5	2572.6
15°	2438.2	2509.1	2549.0	2599.2	2613.9	2596.2	2615.4	2636.1	2637.6	2637.6	2636.1
17.5°	2531.2	2559.3	2599.2	2625.7	2631.7	2631.7	2633.1	2642.0	2636.1	2624.3	2633.1
20°	2550.4	2562.2	2577.0	2574.1	2577.0	2562.2	2547.5	2532.7	2534.2	2526.8	2549.0
22.5°	2515.0	2512.0	2478.1	2455.9	2455.9	2426.4	2398.3	2385.0	2371.7	2376.2	2383.5
25°	2426.4	2380.6	2339.2	2306.8	2299.4	2252.1	2213.7	2201.9	2179.8	2197.5	2200.4
27.5°	2284.6	2232.9	2166.5	2138.4	2100.0	2080.8	2054.2	2018.8	1973.0	1999.6	1995.2
30°	2132.5	2055.7	2001.1	1933.1	1872.6	1868.1	1817.9	1758.9	1735.2	1735.2	1748.5
32.5°	1962.7	1860.8	1781.0	1685.0	1626.0	1600.8	1540.3	1481.2	1494.5	1450.2	1466.5
35°	1764.8	1630.4	1530.0	1436.9	1392.6	1363.1	1284.8	1252.3	1216.9	1196.2	1234.6
37.5°	1575.7	1420.7	1292.2	1190.3	1174.1	1120.9	1067.7	1047.0	1026.4	1035.2	1033.8
40°	1345.4	1208.0	1092.8	1013.1	985.0	959.9	924.5	899.4	886.1	893.5	894.9
42.5°	1137.1	1021.9	936.3	880.2	856.5	838.8	821.1	800.4	796.0	796.0	801.9
45°	976.2	881.6	824.1	778.3	765.0	751.7	738.4	729.5	726.6	720.7	725.1
47.5°	847.7	772.4	736.9	703.0	688.2	685.2	673.4	669.0	663.1	661.6	663.1
50°	739.9	692.6	660.1	640.9	630.6	626.2	620.3	611.4	608.4	615.8	612.9
52.5°	664.6	620.3	602.5	583.3	577.4	571.5	562.7	564.1	562.7	559.7	559.7
55°	589.2	561.2	543.5	528.7	527.2	521.3	513.9	511.0	509.5	506.5	511.0
57.5°	528.7	506.5	490.3	477.0	471.1	471.1	463.7	457.8	457.8	456.3	457.8
60°	468.1	446.0	435.7	422.4	417.9	416.5	412.0	409.1	404.6	404.6	404.6
62.5°	412.0	394.3	382.5	370.7	372.2	364.8	358.9	355.9	355.9	357.4	357.4
65°	358.9	347.0	332.3	321.9	319.0	317.5	314.6	313.1	308.7	311.6	311.6
67.5°	310.1	293.9	285.0	280.6	276.2	274.7	271.7	268.8	267.3	265.8	268.8
70°	261.4	248.1	240.7	237.8	233.3	231.9	230.4	225.9	227.4	228.9	230.4
72.5°	217.1	205.3	203.8	194.9	194.9	194.9	189.0	192.0	190.5	187.6	190.5
75°	171.3	165.4	162.4	158.0	159.5	158.0	156.5	152.1	152.1	153.6	155.1
77.5°	135.9	130.0	128.5	124.1	121.1	124.1	121.1	119.6	119.6	121.1	121.1
80°	100.4	97.5	93.0	93.0	93.0	91.6	91.6	91.6	90.1	88.6	90.1
82.5°	66.5	66.5	65.0	63.5	65.0	62.0	63.5	63.5	63.5	63.5	63.5
85°	42.8	41.4	41.4	39.9	39.9	39.9	41.4	38.4	38.4	39.9	39.9
87.5°	19.2	19.2	19.2	20.7	19.2	19.2	19.2	20.7	19.2	19.2	19.2
90°	10.7	11.2	11.8	12.3	12.6	12.7	12.9	13.2	13.4	13.6	13.4
92.5°	12.3	12.5	12.8	13.0	13.1	13.2	13.3	13.4	13.5	13.6	13.5
95°	20.2	20.7	21.3	21.8	22.1	22.0	21.9	21.8	21.7	21.6	21.7
97.5°	25.9	26.3	26.6	26.9	27.1	27.2	27.3	27.4	27.5	27.6	27.5
100°	29.6	30.5	31.4	32.3	32.7	32.8	33.0	33.3	33.5	33.7	33.5
102.5°	30.9	32.1	33.4	34.6	35.2	35.4	35.7	36.0	36.4	36.7	36.4
105°	31.9	33.1	34.4	35.6	36.2	36.4	36.9	37.3	37.8	38.2	37.8
107.5°	32.9	34.1	35.4	36.6	37.2	37.4	37.9	38.3	38.8	39.2	38.8
110°	76.8	65.6	54.5	43.3	37.7	37.9	38.4	38.8	39.3	39.7	39.3

TEST NUMBER: P997952

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	207.2	159.1	110.9	62.8	38.7	38.9	39.2	39.5	39.9	40.2	39.9
115°	258.5	206.7	155.0	103.3	77.4	73.4	65.3	57.3	49.2	41.2	49.2
117.5°	321.3	305.3	289.4	273.4	265.4	250.8	221.5	192.2	163.0	133.7	163.0
120°	369.8	371.2	372.5	373.8	374.5	367.0	351.9	336.8	321.8	306.7	321.8
122.5°	398.9	399.5	400.2	400.9	401.2	401.3	401.4	401.5	401.6	401.7	401.6
125°	425.6	426.4	427.1	427.9	428.3	428.5	428.8	429.1	429.5	429.8	429.5
127.5°	450.5	451.7	452.8	453.9	454.5	454.6	454.7	454.8	454.9	455.0	454.9
130°	474.3	475.5	476.8	478.0	478.6	478.5	478.4	478.3	478.2	478.1	478.2
132.5°	497.7	498.7	499.7	500.7	501.2	501.1	501.0	500.9	500.8	500.7	500.8
135°	519.4	520.5	521.6	522.7	523.3	523.2	523.0	522.7	522.5	522.3	522.5
137.5°	540.0	541.1	542.2	543.3	543.9	543.7	543.4	543.1	542.7	542.4	542.7
140°	560.0	561.0	562.0	563.0	563.5	563.2	562.7	562.1	561.6	561.0	561.6
142.5°	578.5	579.4	580.3	581.2	581.6	581.3	580.8	580.2	579.7	579.1	579.7
145°	595.5	596.3	597.0	597.8	598.2	597.9	597.4	596.8	596.3	595.7	596.3
147.5°	610.9	611.4	612.0	612.5	612.8	612.6	612.1	611.7	611.2	610.8	611.2
150°	624.6	625.2	625.9	626.6	626.9	626.6	626.1	625.5	625.0	624.4	625.0
152.5°	637.1	637.8	638.5	639.2	639.5	639.1	638.3	637.5	636.7	635.9	636.7
155°	648.2	648.8	649.5	650.2	650.5	650.1	649.2	648.3	647.4	646.5	647.4
157.5°	657.9	658.7	659.4	660.2	660.6	660.1	659.2	658.3	657.4	656.5	657.4
160°	666.3	666.9	667.6	668.3	668.6	668.2	667.4	666.7	665.9	665.1	665.9
162.5°	673.9	674.7	675.5	676.3	676.7	676.2	675.2	674.1	673.1	672.1	673.1
165°	680.0	680.8	681.5	682.3	682.7	682.3	681.5	680.8	680.0	679.2	680.0
167.5°	685.5	686.3	687.0	687.8	688.2	687.7	686.7	685.7	684.7	683.7	684.7
170°	689.5	690.3	691.0	691.8	692.2	691.7	690.7	689.7	688.7	687.7	688.7
172.5°	692.5	693.3	694.1	694.9	695.3	694.8	693.8	692.7	691.7	690.7	691.7
175°	694.5	695.3	696.1	696.9	697.3	696.7	695.6	694.5	693.3	692.2	693.3
177.5°	695.1	695.9	696.6	697.4	697.8	697.3	696.3	695.2	694.2	693.2	694.2
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P997952

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	2036.5	2026.2	2017.3	2018.8	2026.2	2020.3	2005.5	1986.3	1978.9	1970.0	1978.9
5°	2159.1	2150.2	2132.5	2134.0	2129.5	2123.6	2100.0	2070.5	2070.5	2046.8	2043.9
7.5°	2280.2	2266.9	2255.1	2252.1	2235.9	2224.1	2203.4	2162.0	2145.8	2117.7	2101.5
10°	2416.0	2405.7	2392.4	2376.2	2367.3	2346.6	2312.7	2252.1	2222.6	2184.2	2156.1
12.5°	2553.4	2551.9	2522.4	2489.9	2488.4	2455.9	2432.3	2351.1	2311.2	2259.5	2193.0
15°	2640.5	2633.1	2616.9	2600.6	2605.1	2569.6	2516.5	2420.5	2393.9	2331.9	2261.0
17.5°	2639.0	2639.0	2634.6	2631.7	2627.2	2616.9	2587.3	2523.8	2481.0	2402.7	2336.3
20°	2554.9	2574.1	2578.5	2577.0	2591.8	2599.2	2597.7	2557.8	2523.8	2454.4	2386.5
22.5°	2386.5	2430.8	2450.0	2461.8	2492.8	2509.1	2547.5	2532.7	2523.8	2472.2	2414.6
25°	2230.0	2244.7	2302.3	2305.3	2348.1	2388.0	2426.4	2451.5	2484.0	2464.8	2416.0
27.5°	2027.6	2061.6	2103.0	2134.0	2142.8	2224.1	2287.6	2334.8	2408.7	2414.6	2398.3
30°	1798.7	1815.0	1882.9	1924.3	1971.5	2030.6	2122.2	2203.4	2269.8	2330.4	2351.1
32.5°	1519.6	1586.1	1626.0	1676.2	1717.5	1822.4	1934.6	2039.5	2116.2	2218.1	2262.5
35°	1264.1	1315.8	1383.8	1404.4	1479.8	1568.4	1714.6	1848.9	1965.6	2069.0	2159.1
37.5°	1053.0	1094.3	1166.7	1199.2	1243.5	1357.2	1479.8	1646.6	1786.9	1913.9	2026.2
40°	908.2	939.2	993.9	1004.2	1041.1	1144.5	1243.5	1400.0	1586.1	1757.4	1880.0
42.5°	809.3	824.1	861.0	874.3	897.9	967.3	1055.9	1203.6	1376.4	1553.6	1726.4
45°	738.4	748.7	770.9	782.7	812.2	843.3	915.6	1033.8	1169.6	1348.3	1534.4
47.5°	674.9	688.2	697.0	704.4	720.7	754.6	801.9	889.0	1019.0	1182.9	1363.1
50°	621.7	626.2	642.4	643.9	654.2	676.4	720.7	773.8	877.2	1010.1	1184.4
52.5°	568.6	573.0	583.3	593.7	598.1	615.8	645.4	689.7	766.5	871.3	1026.4
55°	515.4	521.3	531.6	539.0	543.5	558.2	576.0	618.8	679.3	753.2	880.2
57.5°	462.2	475.5	478.5	482.9	490.3	506.5	522.8	547.9	595.1	663.1	756.1
60°	412.0	416.5	426.8	431.2	438.6	447.5	468.1	487.3	521.3	574.5	658.7
62.5°	360.3	370.7	375.1	379.5	385.4	395.8	409.1	429.7	459.3	502.1	568.6
65°	316.0	317.5	326.4	332.3	338.2	345.6	358.9	378.1	395.8	435.7	484.4
67.5°	273.2	276.2	279.1	285.0	292.4	299.8	311.6	321.9	344.1	370.7	409.1
70°	231.9	231.9	239.2	243.7	242.2	251.1	259.9	271.7	288.0	313.1	344.1
72.5°	194.9	193.5	199.4	200.8	203.8	209.7	215.6	227.4	236.3	255.5	279.1
75°	155.1	158.0	161.0	161.0	165.4	169.8	175.7	181.6	192.0	203.8	221.5
77.5°	122.6	122.6	125.5	127.0	131.4	130.0	135.9	141.8	149.2	159.5	172.8
80°	90.1	93.0	93.0	93.0	94.5	96.0	101.9	106.3	110.8	118.1	124.1
82.5°	63.5	63.5	66.5	66.5	66.5	69.4	69.4	70.9	73.8	78.3	82.7
85°	39.9	39.9	39.9	41.4	39.9	41.4	44.3	42.8	44.3	47.3	47.3
87.5°	19.2	19.2	19.2	19.2	19.2	20.7	19.2	20.7	22.2	22.2	22.2
90°	13.2	12.9	12.7	12.6	12.3	11.8	11.2	10.7	10.1	9.2	8.3
92.5°	13.4	13.3	13.2	13.1	13.0	12.8	12.5	12.3	12.1	11.8	11.4
95°	21.8	21.9	22.0	22.1	21.8	21.3	20.7	20.2	19.6	18.8	18.0
97.5°	27.4	27.3	27.2	27.1	26.9	26.6	26.3	25.9	25.6	23.8	22.0
100°	33.3	33.0	32.8	32.7	32.3	31.4	30.5	29.6	28.7	26.8	24.9
102.5°	36.0	35.7	35.4	35.2	34.6	33.4	32.1	30.9	29.7	50.0	70.4
105°	37.3	36.9	36.4	36.2	35.6	34.4	33.1	31.9	30.7	61.2	91.7
107.5°	38.3	37.9	37.4	37.2	36.6	35.4	34.1	32.9	31.7	69.3	107.0
110°	38.8	38.4	37.9	37.7	43.3	54.5	65.6	76.8	88.0	120.3	152.6

TEST NUMBER: P997952

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	39.5	39.2	38.9	38.7	62.8	110.9	159.1	207.2	255.4	257.3	259.2
115°	57.3	65.3	73.4	77.4	103.3	155.0	206.7	258.5	310.2	307.4	304.6
117.5°	192.2	221.5	250.8	265.4	273.4	289.4	305.3	321.3	337.3	335.4	333.5
120°	336.8	351.9	367.0	374.5	373.8	372.5	371.2	369.8	368.5	366.5	364.5
122.5°	401.5	401.4	401.3	401.2	400.9	400.2	399.5	398.9	398.2	396.0	393.7
125°	429.1	428.8	428.5	428.3	427.9	427.1	426.4	425.6	424.8	422.7	420.5
127.5°	454.8	454.7	454.6	454.5	453.9	452.8	451.7	450.5	449.4	447.7	446.1
130°	478.3	478.4	478.5	478.6	478.0	476.8	475.5	474.3	473.1	471.9	470.6
132.5°	500.9	501.0	501.1	501.2	500.7	499.7	498.7	497.7	496.7	495.5	494.3
135°	522.7	523.0	523.2	523.3	522.7	521.6	520.5	519.4	518.3	517.3	516.3
137.5°	543.1	543.4	543.7	543.9	543.3	542.2	541.1	540.0	538.9	537.8	536.7
140°	562.1	562.7	563.2	563.5	563.0	562.0	561.0	560.0	559.0	557.8	556.6
142.5°	580.2	580.8	581.3	581.6	581.2	580.3	579.4	578.5	577.6	576.2	574.7
145°	596.8	597.4	597.9	598.2	597.8	597.0	596.3	595.5	594.7	592.8	590.9
147.5°	611.7	612.1	612.6	612.8	612.5	612.0	611.4	610.9	610.3	608.4	606.5
150°	625.5	626.1	626.6	626.9	626.6	625.9	625.2	624.6	623.9	622.1	620.3
152.5°	637.5	638.3	639.1	639.5	639.2	638.5	637.8	637.1	636.4	634.7	633.1
155°	648.3	649.2	650.1	650.5	650.2	649.5	648.8	648.2	647.5	646.2	644.8
157.5°	658.3	659.2	660.1	660.6	660.2	659.4	658.7	657.9	657.1	656.1	655.1
160°	666.7	667.4	668.2	668.6	668.3	667.6	666.9	666.3	665.6	664.9	664.3
162.5°	674.1	675.2	676.2	676.7	676.3	675.5	674.7	673.9	673.1	672.5	672.0
165°	680.8	681.5	682.3	682.7	682.3	681.5	680.8	680.0	679.2	678.9	678.5
167.5°	685.7	686.7	687.7	688.2	687.8	687.0	686.3	685.5	684.7	684.4	684.0
170°	689.7	690.7	691.7	692.2	691.8	691.0	690.3	689.5	688.7	688.5	688.3
172.5°	692.7	693.8	694.8	695.3	694.9	694.1	693.3	692.5	691.7	691.5	691.3
175°	694.5	695.6	696.7	697.3	696.9	696.1	695.3	694.5	693.7	693.5	693.3
177.5°	695.2	696.3	697.3	697.8	697.4	696.6	695.9	695.1	694.3	694.2	694.0
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P997952

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1971.5	1964.1	1959.7	1962.7	1953.8	1931.6	1931.6	1939.0	1930.2	1921.3	1908.0
5°	2026.2	2011.4	2002.5	2001.1	1980.4	1944.9	1937.6	1930.2	1911.0	1890.3	1868.1
7.5°	2079.3	2052.7	2038.0	2027.6	1998.1	1952.3	1933.1	1916.9	1885.9	1854.9	1826.8
10°	2123.6	2085.2	2067.5	2051.3	2012.9	1955.3	1924.3	1894.7	1854.9	1815.0	1779.5
12.5°	2159.1	2114.8	2092.6	2069.0	2021.7	1946.4	1908.0	1860.8	1820.9	1767.7	1732.3
15°	2218.1	2126.6	2105.9	2083.8	2035.0	1931.6	1884.4	1831.2	1776.6	1705.7	1667.3
17.5°	2265.4	2142.8	2141.4	2094.1	2030.6	1925.7	1853.4	1784.0	1724.9	1654.0	1593.5
20°	2293.5	2167.9	2144.3	2095.6	2015.8	1885.9	1810.6	1733.8	1670.3	1584.6	1524.1
22.5°	2317.1	2203.4	2141.4	2082.3	1984.8	1872.6	1761.8	1689.5	1602.3	1509.3	1451.7
25°	2326.0	2210.8	2145.8	2077.9	1962.7	1834.2	1708.7	1630.4	1532.9	1448.7	1370.5
27.5°	2327.4	2209.3	2129.5	2058.7	1931.6	1784.0	1655.5	1572.8	1465.0	1367.5	1289.2
30°	2312.7	2193.0	2120.7	2043.9	1902.1	1738.2	1590.5	1498.9	1383.8	1286.3	1205.1
32.5°	2268.4	2160.6	2101.5	2017.3	1863.7	1674.7	1528.5	1426.6	1305.5	1209.5	1131.2
35°	2194.5	2120.7	2055.7	1977.4	1813.5	1615.6	1466.5	1346.8	1224.3	1132.7	1058.9
37.5°	2103.0	2063.1	2002.5	1925.7	1755.9	1562.5	1397.0	1264.1	1141.6	1053.0	980.6
40°	1978.9	1989.2	1930.2	1860.8	1688.0	1490.1	1307.0	1180.0	1064.8	982.1	911.2
42.5°	1844.5	1887.3	1853.4	1786.9	1612.7	1410.3	1240.5	1100.2	988.0	902.3	843.3
45°	1699.8	1773.6	1753.0	1704.2	1534.4	1326.2	1146.0	1010.1	911.2	828.5	776.8
47.5°	1541.8	1646.6	1646.6	1611.2	1447.3	1242.0	1064.8	926.0	828.5	769.4	719.2
50°	1380.8	1498.9	1518.1	1494.5	1349.8	1146.0	965.8	840.3	756.1	698.5	661.6
52.5°	1212.4	1349.8	1385.2	1373.4	1246.4	1054.4	884.6	762.0	685.2	635.0	602.5
55°	1051.5	1211.0	1249.4	1253.8	1135.7	954.0	794.5	686.7	612.9	578.9	550.8
57.5°	899.4	1053.0	1095.8	1103.2	1023.4	862.4	710.3	615.8	549.4	521.3	499.2
60°	769.4	897.9	954.0	970.3	900.8	756.1	632.1	540.5	490.3	463.7	443.0
62.5°	663.1	766.5	825.5	830.0	798.9	663.1	550.8	474.1	431.2	407.6	397.3
65°	559.7	652.7	688.2	705.9	680.8	574.5	475.5	412.0	378.1	357.4	347.0
67.5°	477.0	536.1	565.6	589.2	564.1	484.4	404.6	353.0	327.8	307.2	301.3
70°	391.4	440.1	462.2	485.9	463.7	403.2	345.6	298.3	276.2	259.9	252.5
72.5°	313.1	351.5	372.2	386.9	373.6	323.4	276.2	243.7	227.4	215.6	211.2
75°	248.1	274.7	286.5	296.8	290.9	252.5	223.0	196.4	181.6	171.3	168.4
77.5°	189.0	208.2	221.5	224.5	217.1	192.0	166.9	150.6	138.8	132.9	130.0
80°	134.4	146.2	153.6	158.0	150.6	140.3	122.6	110.8	100.4	93.0	91.6
82.5°	90.1	96.0	101.9	100.4	97.5	88.6	78.3	72.4	67.9	62.0	62.0
85°	51.7	53.2	56.1	57.6	56.1	50.2	44.3	41.4	38.4	34.0	34.0
87.5°	22.2	23.6	23.6	25.1	22.2	22.2	19.2	16.2	16.2	14.8	13.3
90°	7.4	6.5	6.0	5.4	4.2	2.9	1.7	0.5	1.7	2.9	4.2
92.5°	11.1	10.8	10.6	10.8	11.3	11.7	12.2	12.6	12.2	11.7	11.3
95°	17.3	16.5	16.1	17.9	21.6	25.3	29.0	32.7	29.0	25.3	21.6
97.5°	20.3	18.5	17.6	22.2	31.3	40.5	49.6	58.8	49.6	40.5	31.3
100°	23.0	21.1	20.1	27.8	43.1	58.4	73.7	89.0	73.7	58.4	43.1
102.5°	90.7	111.0	121.2	121.3	121.5	121.8	122.0	122.2	122.0	121.8	121.5
105°	122.2	152.7	167.9	166.2	162.9	159.5	156.2	152.8	156.2	159.5	162.9
107.5°	144.6	182.3	201.1	199.7	196.9	194.1	191.3	188.5	191.3	194.1	196.9
110°	184.9	217.2	233.3	232.1	229.8	227.4	225.1	222.7	225.1	227.4	229.8

TEST NUMBER: P997952

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	261.1	263.0	263.9	262.9	260.9	258.9	256.9	254.9	256.9	258.9	260.9
115°	301.8	299.0	297.6	296.7	294.8	292.9	291.0	289.1	291.0	292.9	294.8
117.5°	331.6	329.7	328.8	327.7	325.4	323.2	320.9	318.7	320.9	323.2	325.4
120°	362.4	360.4	359.4	358.6	356.9	355.2	353.6	351.9	353.6	355.2	356.9
122.5°	391.5	389.2	388.1	387.2	385.4	383.7	381.9	380.1	381.9	383.7	385.4
125°	418.4	416.3	415.2	414.5	413.0	411.6	410.1	408.7	410.1	411.6	413.0
127.5°	444.4	442.7	441.9	441.1	439.6	438.0	436.5	434.9	436.5	438.0	439.6
130°	469.4	468.1	467.5	466.6	464.8	463.1	461.3	459.5	461.3	463.1	464.8
132.5°	493.0	491.8	491.2	490.5	489.0	487.5	486.1	484.6	486.1	487.5	489.0
135°	515.3	514.3	513.8	512.9	511.1	509.3	507.5	505.7	507.5	509.3	511.1
137.5°	535.6	534.5	533.9	533.2	531.9	530.6	529.2	527.9	529.2	530.6	531.9
140°	555.3	554.1	553.5	553.1	552.2	551.3	550.4	549.5	550.4	551.3	552.2
142.5°	573.3	571.8	571.1	570.7	569.9	569.2	568.4	567.6	568.4	569.2	569.9
145°	589.0	587.1	586.2	586.3	586.4	586.5	586.6	586.7	586.6	586.5	586.4
147.5°	604.6	602.7	601.8	602.0	602.3	602.6	603.0	603.3	603.0	602.6	602.3
150°	618.5	616.7	615.8	616.2	617.0	617.7	618.5	619.3	618.5	617.7	617.0
152.5°	631.4	629.7	628.9	629.3	630.2	631.1	632.0	632.9	632.0	631.1	630.2
155°	643.5	642.2	641.5	642.0	643.0	644.0	645.0	646.0	645.0	644.0	643.0
157.5°	654.0	653.0	652.5	652.9	653.8	654.7	655.6	656.5	655.6	654.7	653.8
160°	663.6	662.9	662.6	662.9	663.6	664.3	664.9	665.6	664.9	664.3	663.6
162.5°	671.4	670.9	670.6	670.9	671.6	672.3	672.9	673.6	672.9	672.3	671.6
165°	678.2	677.9	677.7	678.0	678.7	679.4	680.0	680.7	680.0	679.4	678.7
167.5°	683.7	683.4	683.2	683.5	684.2	684.9	685.5	686.2	685.5	684.9	684.2
170°	688.0	687.8	687.7	688.0	688.7	689.4	690.0	690.7	690.0	689.4	688.7
172.5°	691.0	690.8	690.7	691.0	691.7	692.4	693.0	693.7	693.0	692.4	691.7
175°	693.0	692.8	692.7	693.1	693.9	694.7	695.5	696.3	695.5	694.7	693.9
177.5°	693.9	693.8	693.7	694.1	694.9	695.7	696.5	697.3	696.5	695.7	694.9
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P997952

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1900.6	1908.0	1906.5	1891.8	1875.5	1862.2	1837.1	1840.1	1831.2	1832.7	1841.6
5°	1853.4	1853.4	1847.5	1826.8	1800.2	1785.4	1757.4	1750.0	1732.3	1730.8	1729.3
7.5°	1803.2	1795.8	1788.4	1758.9	1726.4	1702.7	1664.3	1655.5	1637.8	1626.0	1620.0
10°	1744.1	1733.8	1719.0	1685.0	1645.2	1615.6	1575.7	1563.9	1530.0	1515.2	1506.3
12.5°	1679.1	1673.2	1649.6	1621.5	1556.5	1524.1	1466.5	1478.3	1444.3	1414.8	1410.3
15°	1614.1	1592.0	1578.7	1532.9	1454.6	1439.9	1394.1	1370.5	1339.5	1315.8	1315.8
17.5°	1550.6	1516.7	1487.1	1438.4	1380.8	1339.5	1305.5	1293.7	1255.3	1231.6	1227.2
20°	1466.5	1428.1	1420.7	1351.3	1311.4	1265.6	1233.1	1203.6	1175.5	1165.2	1157.8
22.5°	1386.7	1342.4	1330.6	1271.5	1231.6	1185.9	1153.4	1132.7	1112.0	1104.6	1091.4
25°	1301.1	1274.5	1256.8	1193.3	1148.9	1106.1	1084.0	1069.2	1050.0	1048.5	1039.7
27.5°	1218.4	1193.3	1175.5	1115.0	1082.5	1042.6	1024.9	1008.7	998.3	993.9	989.5
30°	1147.5	1119.4	1098.7	1054.4	1014.6	982.1	967.3	957.0	951.1	943.7	942.2
32.5°	1069.2	1053.0	1024.9	990.9	959.9	928.9	920.0	912.7	903.8	900.8	899.4
35°	1002.7	980.6	962.9	924.5	911.2	884.6	874.3	868.4	856.5	853.6	850.6
37.5°	937.8	917.1	897.9	874.3	849.2	834.4	828.5	819.6	813.7	815.2	812.2
40°	872.8	856.5	841.8	816.7	801.9	794.5	782.7	773.8	770.9	772.4	770.9
42.5°	809.3	794.5	785.7	766.5	751.7	744.3	736.9	728.1	732.5	732.5	736.9
45°	751.7	738.4	732.5	717.7	708.9	697.0	689.7	688.2	694.1	692.6	692.6
47.5°	692.6	688.2	680.8	667.5	655.7	648.3	646.8	646.8	652.7	655.7	654.2
50°	646.8	638.0	629.1	618.8	609.9	607.0	602.5	605.5	611.4	611.4	614.3
52.5°	589.2	583.3	580.4	571.5	565.6	565.6	565.6	567.1	571.5	576.0	574.5
55°	539.0	534.6	531.6	527.2	519.8	521.3	519.8	522.8	527.2	531.6	534.6
57.5°	485.9	484.4	481.4	474.1	474.1	472.6	477.0	478.5	485.9	488.8	493.3
60°	438.6	434.2	434.2	428.3	428.3	428.3	432.7	437.1	443.0	444.5	447.5
62.5°	388.4	388.4	386.9	382.5	382.5	386.9	388.4	394.3	397.3	397.3	401.7
65°	341.1	339.7	338.2	339.7	341.1	341.1	345.6	348.5	351.5	353.0	354.4
67.5°	293.9	292.4	295.4	293.9	296.8	302.7	301.3	305.7	310.1	310.1	311.6
70°	249.6	252.5	251.1	254.0	252.5	255.5	259.9	261.4	261.4	262.9	267.3
72.5°	208.2	208.2	208.2	206.8	208.2	211.2	214.1	215.6	218.6	220.0	224.5
75°	168.4	168.4	165.4	168.4	168.4	171.3	174.3	174.3	174.3	177.2	181.6
77.5°	127.0	128.5	127.0	130.0	130.0	131.4	134.4	132.9	135.9	137.3	138.8
80°	93.0	91.6	91.6	91.6	93.0	93.0	96.0	97.5	97.5	101.9	98.9
82.5°	59.1	60.5	59.1	60.5	60.5	62.0	60.5	62.0	63.5	66.5	65.0
85°	34.0	32.5	32.5	34.0	32.5	32.5	34.0	32.5	34.0	32.5	34.0
87.5°	13.3	11.8	11.8	11.8	11.8	10.3	10.3	8.9	8.9	8.9	7.4
90°	5.4	6.0	6.5	7.4	8.3	9.2	10.1	10.7	11.2	11.8	12.3
92.5°	10.8	10.6	10.8	11.1	11.4	11.8	12.1	12.3	12.5	12.8	13.0
95°	17.9	16.1	16.5	17.3	18.0	18.8	19.6	20.2	20.7	21.3	21.8
97.5°	22.2	17.6	18.5	20.3	22.0	23.8	25.6	25.9	26.3	26.6	26.9
100°	27.8	20.1	21.1	23.0	24.9	26.8	28.7	29.6	30.5	31.4	32.3
102.5°	121.3	121.2	111.0	90.7	70.4	50.0	29.7	30.9	32.1	33.4	34.6
105°	166.2	167.9	152.7	122.2	91.7	61.2	30.7	31.9	33.1	34.4	35.6
107.5°	199.7	201.1	182.3	144.6	107.0	69.3	31.7	32.9	34.1	35.4	36.6
110°	232.1	233.3	217.2	184.9	152.6	120.3	88.0	76.8	65.6	54.5	43.3

TEST NUMBER: P997952

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	262.9	263.9	263.0	261.1	259.2	257.3	255.4	207.2	159.1	110.9	62.8
115°	296.7	297.6	299.0	301.8	304.6	307.4	310.2	258.5	206.7	155.0	103.3
117.5°	327.7	328.8	329.7	331.6	333.5	335.4	337.3	321.3	305.3	289.4	273.4
120°	358.6	359.4	360.4	362.4	364.5	366.5	368.5	369.8	371.2	372.5	373.8
122.5°	387.2	388.1	389.2	391.5	393.7	396.0	398.2	398.9	399.5	400.2	400.9
125°	414.5	415.2	416.3	418.4	420.5	422.7	424.8	425.6	426.4	427.1	427.9
127.5°	441.1	441.9	442.7	444.4	446.1	447.7	449.4	450.5	451.7	452.8	453.9
130°	466.6	467.5	468.1	469.4	470.6	471.9	473.1	474.3	475.5	476.8	478.0
132.5°	490.5	491.2	491.8	493.0	494.3	495.5	496.7	497.7	498.7	499.7	500.7
135°	512.9	513.8	514.3	515.3	516.3	517.3	518.3	519.4	520.5	521.6	522.7
137.5°	533.2	533.9	534.5	535.6	536.7	537.8	538.9	540.0	541.1	542.2	543.3
140°	553.1	553.5	554.1	555.3	556.6	557.8	559.0	560.0	561.0	562.0	563.0
142.5°	570.7	571.1	571.8	573.3	574.7	576.2	577.6	578.5	579.4	580.3	581.2
145°	586.3	586.2	587.1	589.0	590.9	592.8	594.7	595.5	596.3	597.0	597.8
147.5°	602.0	601.8	602.7	604.6	606.5	608.4	610.3	610.9	611.4	612.0	612.5
150°	616.2	615.8	616.7	618.5	620.3	622.1	623.9	624.6	625.2	625.9	626.6
152.5°	629.3	628.9	629.7	631.4	633.1	634.7	636.4	637.1	637.8	638.5	639.2
155°	642.0	641.5	642.2	643.5	644.8	646.2	647.5	648.2	648.8	649.5	650.2
157.5°	652.9	652.5	653.0	654.0	655.1	656.1	657.1	657.9	658.7	659.4	660.2
160°	662.9	662.6	662.9	663.6	664.3	664.9	665.6	666.3	666.9	667.6	668.3
162.5°	670.9	670.6	670.9	671.4	672.0	672.5	673.1	673.9	674.7	675.5	676.3
165°	678.0	677.7	677.9	678.2	678.5	678.9	679.2	680.0	680.8	681.5	682.3
167.5°	683.5	683.2	683.4	683.7	684.0	684.4	684.7	685.5	686.3	687.0	687.8
170°	688.0	687.7	687.8	688.0	688.3	688.5	688.7	689.5	690.3	691.0	691.8
172.5°	691.0	690.7	690.8	691.0	691.3	691.5	691.7	692.5	693.3	694.1	694.9
175°	693.1	692.7	692.8	693.0	693.3	693.5	693.7	694.5	695.3	696.1	696.9
177.5°	694.1	693.7	693.8	693.9	694.0	694.2	694.3	695.1	695.9	696.6	697.4
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P997952

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1831.2	1835.7	1825.3	1822.4	1825.3	1815.0	1817.9	1820.9	1820.9	1825.3	1828.3
5°	1724.9	1719.0	1708.7	1705.7	1702.7	1707.2	1704.2	1708.7	1710.1	1720.5	1721.9
7.5°	1620.0	1611.2	1602.3	1593.5	1590.5	1583.1	1590.5	1590.5	1600.8	1597.9	1605.3
10°	1496.0	1494.5	1482.7	1478.3	1472.4	1460.6	1476.8	1472.4	1479.8	1493.0	1496.0
12.5°	1404.4	1388.2	1395.6	1374.9	1382.3	1370.5	1371.9	1371.9	1383.8	1385.2	1382.3
15°	1317.3	1304.0	1284.8	1276.0	1271.5	1265.6	1284.8	1286.3	1277.4	1298.1	1290.7
17.5°	1228.7	1228.7	1211.0	1206.5	1194.7	1200.6	1197.7	1199.2	1196.2	1211.0	1218.4
20°	1151.9	1144.5	1138.6	1140.1	1125.3	1122.4	1119.4	1122.4	1132.7	1143.0	1146.0
22.5°	1089.9	1085.4	1070.7	1073.6	1061.8	1066.2	1063.3	1070.7	1072.2	1072.2	1082.5
25°	1030.8	1024.9	1026.4	1020.5	1016.0	1016.0	1011.6	1016.0	1021.9	1024.9	1026.4
27.5°	986.5	982.1	974.7	970.3	973.2	965.8	971.7	976.2	976.2	973.2	976.2
30°	933.3	936.3	936.3	921.5	927.4	924.5	928.9	931.9	931.9	933.3	930.4
32.5°	897.9	889.0	887.6	886.1	886.1	880.2	880.2	884.6	886.1	887.6	892.0
35°	850.6	850.6	843.3	847.7	841.8	843.3	841.8	843.3	846.2	841.8	846.2
37.5°	807.8	809.3	806.3	809.3	810.8	807.8	804.9	810.8	807.8	807.8	804.9
40°	770.9	769.4	770.9	770.9	770.9	772.4	769.4	769.4	769.4	766.5	763.5
42.5°	739.9	731.0	734.0	735.4	731.0	731.0	732.5	731.0	735.4	726.6	726.6
45°	695.6	692.6	694.1	694.1	697.0	692.6	695.6	697.0	692.6	691.1	688.2
47.5°	655.7	658.7	655.7	658.7	658.7	661.6	655.7	657.2	658.7	652.7	648.3
50°	615.8	615.8	620.3	618.8	620.3	617.3	617.3	615.8	617.3	614.3	609.9
52.5°	578.9	574.5	581.9	580.4	578.9	577.4	576.0	577.4	574.5	571.5	571.5
55°	533.1	533.1	537.6	539.0	539.0	536.1	533.1	534.6	533.1	531.6	530.2
57.5°	496.2	490.3	493.3	494.7	494.7	490.3	493.3	490.3	490.3	491.8	487.3
60°	448.9	448.9	446.0	450.4	450.4	447.5	447.5	448.9	446.0	444.5	443.0
62.5°	398.7	400.2	404.6	406.1	407.6	404.6	401.7	403.2	403.2	398.7	400.2
65°	355.9	358.9	364.8	363.3	360.3	361.8	358.9	360.3	355.9	357.4	353.0
67.5°	314.6	313.1	314.6	314.6	317.5	316.0	313.1	313.1	311.6	316.0	311.6
70°	270.3	270.3	270.3	270.3	271.7	273.2	270.3	267.3	268.8	265.8	264.3
72.5°	224.5	225.9	224.5	227.4	223.0	225.9	225.9	224.5	223.0	223.0	223.0
75°	181.6	184.6	180.2	181.6	180.2	183.1	181.6	181.6	178.7	177.2	178.7
77.5°	138.8	140.3	137.3	138.8	137.3	138.8	138.8	137.3	137.3	137.3	137.3
80°	98.9	100.4	98.9	97.5	96.0	98.9	96.0	97.5	98.9	97.5	100.4
82.5°	63.5	63.5	62.0	63.5	60.5	60.5	62.0	62.0	60.5	63.5	60.5
85°	31.0	31.0	34.0	31.0	29.5	29.5	29.5	31.0	29.5	32.5	31.0
87.5°	7.4	5.9	7.4	7.4	5.9	5.9	7.4	5.9	7.4	8.9	5.9
90°	12.6	12.7	12.9	13.2	13.4	13.6	13.4	13.2	12.9	12.7	12.6
92.5°	13.1	13.2	13.3	13.4	13.5	13.6	13.5	13.4	13.3	13.2	13.1
95°	22.1	22.0	21.9	21.8	21.7	21.6	21.7	21.8	21.9	22.0	22.1
97.5°	27.1	27.2	27.3	27.4	27.5	27.6	27.5	27.4	27.3	27.2	27.1
100°	32.7	32.8	33.0	33.3	33.5	33.7	33.5	33.3	33.0	32.8	32.7
102.5°	35.2	35.4	35.7	36.0	36.4	36.7	36.4	36.0	35.7	35.4	35.2
105°	36.2	36.4	36.9	37.3	37.8	38.2	37.8	37.3	36.9	36.4	36.2
107.5°	37.2	37.4	37.9	38.3	38.8	39.2	38.8	38.3	37.9	37.4	37.2
110°	37.7	37.9	38.4	38.8	39.3	39.7	39.3	38.8	38.4	37.9	37.7

TEST NUMBER: P997952

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	38.7	38.9	39.2	39.5	39.9	40.2	39.9	39.5	39.2	38.9	38.7
115°	77.4	73.4	65.3	57.3	49.2	41.2	49.2	57.3	65.3	73.4	77.4
117.5°	265.4	250.8	221.5	192.2	163.0	133.7	163.0	192.2	221.5	250.8	265.4
120°	374.5	367.0	351.9	336.8	321.8	306.7	321.8	336.8	351.9	367.0	374.5
122.5°	401.2	401.3	401.4	401.5	401.6	401.7	401.6	401.5	401.4	401.3	401.2
125°	428.3	428.5	428.8	429.1	429.5	429.8	429.5	429.1	428.8	428.5	428.3
127.5°	454.5	454.6	454.7	454.8	454.9	455.0	454.9	454.8	454.7	454.6	454.5
130°	478.6	478.5	478.4	478.3	478.2	478.1	478.2	478.3	478.4	478.5	478.6
132.5°	501.2	501.1	501.0	500.9	500.8	500.7	500.8	500.9	501.0	501.1	501.2
135°	523.3	523.2	523.0	522.7	522.5	522.3	522.5	522.7	523.0	523.2	523.3
137.5°	543.9	543.7	543.4	543.1	542.7	542.4	542.7	543.1	543.4	543.7	543.9
140°	563.5	563.2	562.7	562.1	561.6	561.0	561.6	562.1	562.7	563.2	563.5
142.5°	581.6	581.3	580.8	580.2	579.7	579.1	579.7	580.2	580.8	581.3	581.6
145°	598.2	597.9	597.4	596.8	596.3	595.7	596.3	596.8	597.4	597.9	598.2
147.5°	612.8	612.6	612.1	611.7	611.2	610.8	611.2	611.7	612.1	612.6	612.8
150°	626.9	626.6	626.1	625.5	625.0	624.4	625.0	625.5	626.1	626.6	626.9
152.5°	639.5	639.1	638.3	637.5	636.7	635.9	636.7	637.5	638.3	639.1	639.5
155°	650.5	650.1	649.2	648.3	647.4	646.5	647.4	648.3	649.2	650.1	650.5
157.5°	660.6	660.1	659.2	658.3	657.4	656.5	657.4	658.3	659.2	660.1	660.6
160°	668.6	668.2	667.4	666.7	665.9	665.1	665.9	666.7	667.4	668.2	668.6
162.5°	676.7	676.2	675.2	674.1	673.1	672.1	673.1	674.1	675.2	676.2	676.7
165°	682.7	682.3	681.5	680.8	680.0	679.2	680.0	680.8	681.5	682.3	682.7
167.5°	688.2	687.7	686.7	685.7	684.7	683.7	684.7	685.7	686.7	687.7	688.2
170°	692.2	691.7	690.7	689.7	688.7	687.7	688.7	689.7	690.7	691.7	692.2
172.5°	695.3	694.8	693.8	692.7	691.7	690.7	691.7	692.7	693.8	694.8	695.3
175°	697.3	696.7	695.6	694.5	693.3	692.2	693.3	694.5	695.6	696.7	697.3
177.5°	697.8	697.3	696.3	695.2	694.2	693.2	694.2	695.2	696.3	697.3	697.8
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P997952

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1823.8	1835.7	1831.2	1815.0	1834.2	1834.2	1847.5	1847.5	1863.7	1869.6	1878.5
5°	1720.5	1729.3	1736.7	1729.3	1742.6	1763.3	1775.1	1785.4	1807.6	1816.5	1829.8
7.5°	1609.7	1626.0	1633.3	1633.3	1655.5	1679.1	1702.7	1717.5	1748.5	1760.3	1773.6
10°	1501.9	1521.1	1535.9	1534.4	1571.3	1586.1	1615.6	1649.6	1680.6	1698.3	1717.5
12.5°	1388.2	1398.5	1419.2	1448.7	1457.6	1484.2	1518.1	1561.0	1617.1	1633.3	1661.4
15°	1293.7	1321.7	1338.0	1351.3	1371.9	1397.0	1434.0	1475.3	1531.4	1566.9	1596.4
17.5°	1213.9	1250.8	1261.2	1258.2	1284.8	1323.2	1366.0	1397.0	1447.3	1490.1	1518.1
20°	1148.9	1163.7	1181.4	1188.8	1209.5	1250.8	1292.2	1327.6	1369.0	1403.0	1435.4
22.5°	1084.0	1095.8	1110.6	1123.8	1140.1	1163.7	1203.6	1247.9	1287.8	1320.3	1357.2
25°	1030.8	1038.2	1051.5	1061.8	1079.5	1095.8	1123.8	1172.6	1219.8	1239.0	1271.5
27.5°	979.1	985.0	993.9	1005.7	1014.6	1030.8	1055.9	1095.8	1144.5	1163.7	1208.0
30°	933.3	937.8	946.6	952.5	957.0	976.2	995.4	1026.4	1063.3	1089.9	1122.4
32.5°	890.5	894.9	903.8	905.3	911.2	921.5	939.2	967.3	999.8	1021.9	1050.0
35°	843.3	846.2	855.1	858.0	862.4	871.3	884.6	905.3	934.8	951.1	976.2
37.5°	806.3	804.9	810.8	815.2	821.1	825.5	830.0	850.6	872.8	887.6	906.8
40°	766.5	763.5	765.0	770.9	773.8	779.7	779.7	800.4	815.2	827.0	841.8
42.5°	726.6	725.1	722.2	725.1	728.1	729.5	731.0	745.8	760.6	770.9	787.1
45°	686.7	685.2	682.3	683.8	683.8	686.7	691.1	697.0	707.4	716.2	725.1
47.5°	649.8	646.8	642.4	640.9	643.9	643.9	643.9	649.8	660.1	663.1	671.9
50°	611.4	607.0	601.1	598.1	598.1	596.6	599.6	601.1	609.9	612.9	620.3
52.5°	570.0	567.1	561.2	555.3	556.8	553.8	555.3	556.8	559.7	564.1	568.6
55°	528.7	522.8	518.4	516.9	512.4	512.4	508.0	513.9	512.4	513.9	519.8
57.5°	488.8	482.9	475.5	472.6	468.1	466.7	463.7	462.2	463.7	468.1	472.6
60°	441.6	438.6	434.2	429.7	426.8	422.4	419.4	419.4	417.9	417.9	419.4
62.5°	395.8	394.3	388.4	386.9	384.0	381.0	376.6	373.6	373.6	376.6	378.1
65°	351.5	350.0	345.6	344.1	336.7	333.8	332.3	330.8	327.8	327.8	327.8
67.5°	310.1	305.7	305.7	298.3	292.4	289.5	286.5	285.0	285.0	285.0	286.5
70°	264.3	264.3	259.9	255.5	249.6	251.1	246.6	242.2	242.2	239.2	240.7
72.5°	220.0	218.6	214.1	212.7	208.2	203.8	200.8	203.8	199.4	197.9	199.4
75°	177.2	175.7	172.8	169.8	171.3	166.9	162.4	161.0	161.0	158.0	158.0
77.5°	135.9	138.8	132.9	131.4	128.5	125.5	124.1	122.6	122.6	122.6	125.5
80°	94.5	96.0	96.0	93.0	94.5	90.1	90.1	90.1	85.7	87.1	88.6
82.5°	60.5	60.5	59.1	60.5	59.1	59.1	57.6	57.6	56.1	56.1	57.6
85°	34.0	32.5	31.0	34.0	32.5	32.5	31.0	31.0	31.0	31.0	31.0
87.5°	7.4	8.9	8.9	8.9	8.9	10.3	10.3	10.3	11.8	11.8	11.8
90°	12.3	11.8	11.2	10.7	10.1	9.2	8.3	7.4	6.5	6.0	5.4
92.5°	13.0	12.8	12.5	12.3	12.1	11.8	11.4	11.1	10.8	10.6	10.8
95°	21.8	21.3	20.7	20.2	19.6	18.8	18.0	17.3	16.5	16.1	17.9
97.5°	26.9	26.6	26.3	25.9	25.6	23.8	22.0	20.3	18.5	17.6	22.2
100°	32.3	31.4	30.5	29.6	28.7	26.8	24.9	23.0	21.1	20.1	27.8
102.5°	34.6	33.4	32.1	30.9	29.7	50.0	70.4	90.7	111.0	121.2	121.3
105°	35.6	34.4	33.1	31.9	30.7	61.2	91.7	122.2	152.7	167.9	166.2
107.5°	36.6	35.4	34.1	32.9	31.7	69.3	107.0	144.6	182.3	201.1	199.7
110°	43.3	54.5	65.6	76.8	88.0	120.3	152.6	184.9	217.2	233.3	232.1

TEST NUMBER: P997952

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	62.8	110.9	159.1	207.2	255.4	257.3	259.2	261.1	263.0	263.9	262.9
115°	103.3	155.0	206.7	258.5	310.2	307.4	304.6	301.8	299.0	297.6	296.7
117.5°	273.4	289.4	305.3	321.3	337.3	335.4	333.5	331.6	329.7	328.8	327.7
120°	373.8	372.5	371.2	369.8	368.5	366.5	364.5	362.4	360.4	359.4	358.6
122.5°	400.9	400.2	399.5	398.9	398.2	396.0	393.7	391.5	389.2	388.1	387.2
125°	427.9	427.1	426.4	425.6	424.8	422.7	420.5	418.4	416.3	415.2	414.5
127.5°	453.9	452.8	451.7	450.5	449.4	447.7	446.1	444.4	442.7	441.9	441.1
130°	478.0	476.8	475.5	474.3	473.1	471.9	470.6	469.4	468.1	467.5	466.6
132.5°	500.7	499.7	498.7	497.7	496.7	495.5	494.3	493.0	491.8	491.2	490.5
135°	522.7	521.6	520.5	519.4	518.3	517.3	516.3	515.3	514.3	513.8	512.9
137.5°	543.3	542.2	541.1	540.0	538.9	537.8	536.7	535.6	534.5	533.9	533.2
140°	563.0	562.0	561.0	560.0	559.0	557.8	556.6	555.3	554.1	553.5	553.1
142.5°	581.2	580.3	579.4	578.5	577.6	576.2	574.7	573.3	571.8	571.1	570.7
145°	597.8	597.0	596.3	595.5	594.7	592.8	590.9	589.0	587.1	586.2	586.3
147.5°	612.5	612.0	611.4	610.9	610.3	608.4	606.5	604.6	602.7	601.8	602.0
150°	626.6	625.9	625.2	624.6	623.9	622.1	620.3	618.5	616.7	615.8	616.2
152.5°	639.2	638.5	637.8	637.1	636.4	634.7	633.1	631.4	629.7	628.9	629.3
155°	650.2	649.5	648.8	648.2	647.5	646.2	644.8	643.5	642.2	641.5	642.0
157.5°	660.2	659.4	658.7	657.9	657.1	656.1	655.1	654.0	653.0	652.5	652.9
160°	668.3	667.6	666.9	666.3	665.6	664.9	664.3	663.6	662.9	662.6	662.9
162.5°	676.3	675.5	674.7	673.9	673.1	672.5	672.0	671.4	670.9	670.6	670.9
165°	682.3	681.5	680.8	680.0	679.2	678.9	678.5	678.2	677.9	677.7	678.0
167.5°	687.8	687.0	686.3	685.5	684.7	684.4	684.0	683.7	683.4	683.2	683.5
170°	691.8	691.0	690.3	689.5	688.7	688.5	688.3	688.0	687.8	687.7	688.0
172.5°	694.9	694.1	693.3	692.5	691.7	691.5	691.3	691.0	690.8	690.7	691.0
175°	696.9	696.1	695.3	694.5	693.7	693.5	693.3	693.0	692.8	692.7	693.1
177.5°	697.4	696.6	695.9	695.1	694.3	694.2	694.0	693.9	693.8	693.7	694.1
180°	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8	694.8

TEST NUMBER: P997952

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1921.3	1921.3	1921.3	1921.3
2.5°	1885.9	1885.9	1908.0	1931.6
5°	1844.5	1854.9	1890.3	1922.8
7.5°	1804.6	1822.4	1866.7	1908.0
10°	1755.9	1779.5	1834.2	1882.9
12.5°	1708.7	1730.8	1794.3	1848.9
15°	1642.2	1670.3	1738.2	1806.1
17.5°	1575.7	1603.8	1686.5	1766.2
20°	1497.5	1534.4	1627.4	1733.8
22.5°	1425.1	1470.9	1574.3	1659.9
25°	1345.4	1416.2	1512.2	1623.0
27.5°	1274.5	1345.4	1442.8	1555.1
30°	1194.7	1267.1	1367.5	1470.9
32.5°	1117.9	1184.4	1281.9	1408.9
35°	1038.2	1101.7	1196.2	1324.7
37.5°	965.8	1027.9	1131.2	1249.4
40°	894.9	959.9	1048.5	1166.7
42.5°	828.5	886.1	965.8	1084.0
45°	767.9	809.3	883.1	993.9
47.5°	704.4	741.4	809.3	920.0
50°	645.4	676.4	735.4	838.8
52.5°	587.8	614.3	669.0	751.7
55°	536.1	561.2	601.1	682.3
57.5°	482.9	502.1	540.5	605.5
60°	431.2	448.9	480.0	533.1
62.5°	379.5	394.3	423.8	466.7
65°	333.8	345.6	367.7	404.6
67.5°	289.5	296.8	314.6	344.1
70°	246.6	252.5	267.3	290.9
72.5°	200.8	206.8	223.0	239.2
75°	162.4	163.9	175.7	189.0
77.5°	127.0	125.5	134.4	144.7
80°	87.1	91.6	98.9	103.4
82.5°	59.1	60.5	63.5	66.5
85°	32.5	34.0	34.0	38.4
87.5°	13.3	14.8	14.8	16.2
90°	4.2	2.9	1.7	0.5
92.5°	11.3	11.7	12.2	12.6
95°	21.6	25.3	29.0	32.7
97.5°	31.3	40.5	49.6	58.8
100°	43.1	58.4	73.7	89.0
102.5°	121.5	121.8	122.0	122.2
105°	162.9	159.5	156.2	152.8
107.5°	196.9	194.1	191.3	188.5
110°	229.8	227.4	225.1	222.7

TEST NUMBER: P997952

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	260.9	258.9	256.9	254.9
115°	294.8	292.9	291.0	289.1
117.5°	325.4	323.2	320.9	318.7
120°	356.9	355.2	353.6	351.9
122.5°	385.4	383.7	381.9	380.1
125°	413.0	411.6	410.1	408.7
127.5°	439.6	438.0	436.5	434.9
130°	464.8	463.1	461.3	459.5
132.5°	489.0	487.5	486.1	484.6
135°	511.1	509.3	507.5	505.7
137.5°	531.9	530.6	529.2	527.9
140°	552.2	551.3	550.4	549.5
142.5°	569.9	569.2	568.4	567.6
145°	586.4	586.5	586.6	586.7
147.5°	602.3	602.6	603.0	603.3
150°	617.0	617.7	618.5	619.3
152.5°	630.2	631.1	632.0	632.9
155°	643.0	644.0	645.0	646.0
157.5°	653.8	654.7	655.6	656.5
160°	663.6	664.3	664.9	665.6
162.5°	671.6	672.3	672.9	673.6
165°	678.7	679.4	680.0	680.7
167.5°	684.2	684.9	685.5	686.2
170°	688.7	689.4	690.0	690.7
172.5°	691.7	692.4	693.0	693.7
175°	693.9	694.7	695.5	696.3
177.5°	694.9	695.7	696.5	697.3
180°	694.8	694.8	694.8	694.8

TEST NUMBER: P997952

CATALOG NUMBER: SA2XXDIP-B1005D530UB50-4F0-XX-W2A-A

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.21	20.20	20.01	21.02	22.02	16.70	17.70	17.50	18.51	19.51
	3H	20.03	20.92	20.84	21.75	22.78	18.06	18.95	18.87	19.77	20.80
	4H	20.21	21.05	21.04	21.88	22.92	18.53	19.37	19.36	20.20	21.24
	6H	20.26	21.03	21.10	21.87	22.92	18.84	19.61	19.68	20.45	21.51
	8H	20.24	20.98	21.09	21.84	22.89	18.93	19.66	19.78	20.52	21.57
	12H	20.21	20.91	21.06	21.76	22.84	18.97	19.67	19.83	20.53	21.61
4H	2H	19.27	20.11	20.10	20.94	21.98	17.17	18.00	18.00	18.84	19.88
	3H	20.26	20.96	21.10	21.82	22.88	18.64	19.34	19.48	20.20	21.26
	4H	20.54	21.18	21.40	22.04	23.12	19.18	19.81	20.03	20.68	21.76
	6H	20.68	21.23	21.55	22.11	23.20	19.56	20.11	20.44	21.00	22.09
	8H	20.68	21.19	21.56	22.07	23.17	19.68	20.19	20.55	21.07	22.17
	12H	20.65	21.11	21.55	22.01	23.12	19.74	20.20	20.64	21.10	22.21
8H	4H	20.56	21.07	21.44	21.95	23.05	19.33	19.84	20.21	20.72	21.82
	6H	20.74	21.17	21.65	22.09	23.19	19.77	20.19	20.67	21.12	22.21
	8H	20.78	21.15	21.69	22.07	23.18	19.92	20.29	20.83	21.21	22.33
	12H	20.77	21.09	21.68	22.00	23.17	20.02	20.35	20.93	21.26	22.43
12H	4H	20.52	20.98	21.42	21.88	22.99	19.31	19.77	20.21	20.67	21.78
	6H	20.72	21.10	21.64	22.02	23.13	19.77	20.14	20.68	21.06	22.18
	8H	20.76	21.09	21.68	22.00	23.17	19.93	20.26	20.85	21.17	22.34