

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997987

Luminaire Tested: SA2XXDIP-B1005D725UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P997987
REPORT IS A COMBINATION OF REPORTS P983724 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B1005D725UB30-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7176.0 lumens
Efficiency: N/A
Efficacy: 87.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997987

CATALOG NUMBER: SA2XXDIP-B1005D725UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P997987

CATALOG NUMBER: SA2XXDIP-B1005D725UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	61		
1	101	97	93	90	94	91	88	85	80	77	75	69	68	66	60	59	57	53		
2	92	85	79	74	86	80	75	70	70	67	63	62	59	56	53	51	49	45		
3	85	75	68	63	79	71	65	60	63	58	54	55	51	48	48	45	43	39		
4	78	67	59	54	73	63	56	51	56	51	46	49	45	42	43	40	37	34		
5	72	60	52	46	67	57	50	44	51	45	40	45	40	37	39	36	33	30		
6	66	54	46	41	62	51	44	39	46	40	36	41	36	32	36	32	29	27		
7	62	49	42	36	58	47	40	35	42	36	32	37	33	29	33	29	26	24		
8	57	45	37	32	54	43	36	31	38	33	28	34	30	26	30	27	24	22		
9	53	41	34	29	50	39	32	28	35	30	26	32	27	24	28	24	22	20		
10	50	38	31	26	47	36	30	25	33	27	23	29	25	22	26	22	20	18		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	31633	31633	31633	31633
5°	31709	33727	31831	26833
10°	31340	36820	31537	22123
15°	30581	38835	31006	18635
20°	30103	36464	30103	16197
25°	29144	31327	29277	14485
30°	27566	24625	28092	13119
35°	26167	17029	26605	12005
40°	24560	12857	24839	11114
45°	22576	10566	22945	10154
50°	20865	9273	20900	9296
55°	18908	7902	19033	8363
60°	16826	6600	17060	7298
65°	14963	5368	15236	6232
70°	13105	4212	13438	5028
75°	10998	3057	11429	3646
80°	8583	1938	9197	2163
85°	5636	976	6074	722

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 32700 cd/sqm

TEST NUMBER: P997987

CATALOG NUMBER: SA2XXDIP-B1005D725UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	190.3	2.7
10°-20°	554.0	7.7
20°-30°	804.0	11.2
30°-40°	847.6	11.8
40°-50°	750.0	10.5
50°-60°	598.9	8.3
60°-70°	406.8	5.7
70°-80°	208.1	2.9
80°-90°	51.7	0.7
90°-100°	154.7	2.2
100°-110°	545.0	7.6
110°-120°	572.3	8.0
120°-130°	470.9	6.6
130°-140°	378.3	5.3
140°-150°	285.7	4.0
150°-160°	200.9	2.8
160°-170°	118.2	1.6
170°-180°	38.5	0.5
0°-30°	1548.4	21.6
0°-40°	2396.0	33.4
0°-60°	3744.9	52.2
0°-90°	4411.6	61.5
90°-120°	1272.1	17.7
90°-150°	2406.9	33.5
90°-180°	2764.0	38.5
0°-180°	7176.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1998	1998	1998	1998	1998	
5°	2000	2232	2008	1776	2000	190
15°	1879	2743	1905	1316	1879	531
25°	1688	2286	1696	1057	1688	772
35°	1378	1244	1401	877	1378	862
45°	1034	750	1051	720	1034	802
55°	710	527	714	558	710	633
65°	421	324	429	376	421	418
75°	197	160	204	190	197	211
85°	40	42	43	31	40	47
90°	1	25	1	25	1	4
95°	27	87	27	87	27	28
105°	93	860	93	860	93	99
115°	164	1132	164	1132	164	163
125°	229	918	229	918	229	204
135°	269	761	269	761	269	208
145°	307	608	307	608	307	193
155°	349	511	349	511	349	161
165°	380	448	380	448	380	107
175°	396	404	396	404	396	38
180°	397	397	397	397	397	

TEST NUMBER: P997987

CATALOG NUMBER: SA2XXDIP-B1005D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4
2.5°	2009.1	2013.7	2021.4	2022.9	2038.3	2050.6	2064.4	2064.4	2069.0	2067.5	2055.2
5°	1999.9	2013.7	2033.7	2050.6	2078.2	2090.5	2109.0	2122.8	2135.1	2144.3	2142.8
7.5°	1984.5	2009.1	2038.3	2070.6	2107.4	2128.9	2155.0	2179.6	2196.5	2211.9	2222.6
10°	1958.4	1999.9	2039.8	2082.8	2130.5	2159.6	2190.4	2222.6	2248.7	2277.9	2305.6
12.5°	1923.1	1983.0	2032.2	2089.0	2147.4	2179.6	2228.8	2253.3	2304.0	2377.8	2397.7
15°	1878.6	1960.0	2006.0	2078.2	2155.0	2181.2	2248.7	2288.7	2393.1	2439.2	2494.5
17.5°	1837.1	1927.7	1989.1	2072.1	2147.4	2198.0	2264.1	2345.5	2433.1	2499.1	2560.5
20°	1803.3	1890.8	1964.6	2056.7	2152.0	2216.5	2285.6	2383.9	2479.1	2546.7	2594.3
22.5°	1726.5	1838.6	1924.6	2027.5	2142.8	2231.8	2297.9	2405.4	2508.3	2549.8	2591.3
25°	1688.1	1784.9	1884.7	2001.4	2136.6	2242.6	2299.4	2419.2	2509.9	2525.2	2534.4
27.5°	1617.4	1726.5	1843.2	1976.9	2135.1	2224.2	2296.4	2405.4	2477.6	2466.9	2439.2
30°	1529.9	1663.5	1792.5	1936.9	2113.6	2210.3	2277.9	2377.8	2414.6	2359.3	2310.2
32.5°	1465.4	1591.3	1734.2	1901.6	2089.0	2181.2	2247.2	2325.5	2333.2	2233.4	2150.4
35°	1377.8	1517.6	1678.9	1855.5	2047.5	2130.5	2191.9	2239.5	2202.7	2062.9	1964.6
37.5°	1299.5	1437.7	1609.8	1789.5	1990.7	2072.1	2121.2	2128.9	2038.3	1915.4	1771.0
40°	1213.5	1356.3	1536.0	1725.0	1927.7	1998.4	2029.1	2006.0	1875.5	1732.6	1565.2
42.5°	1127.4	1268.8	1462.3	1655.8	1847.8	1907.7	1920.0	1857.1	1697.3	1529.9	1336.3
45°	1033.7	1181.2	1374.7	1569.8	1755.7	1789.5	1791.0	1700.4	1511.4	1336.3	1156.6
47.5°	956.9	1093.6	1285.7	1480.7	1637.4	1660.4	1651.2	1546.8	1340.9	1144.3	987.7
50°	872.5	1003.0	1193.5	1385.5	1519.1	1525.3	1502.2	1353.2	1152.0	972.3	847.9
52.5°	781.8	913.9	1089.0	1273.4	1393.2	1384.0	1339.4	1179.7	990.7	841.7	746.5
55°	709.6	826.4	990.7	1170.4	1254.9	1228.8	1179.7	1016.8	867.9	741.9	659.0
57.5°	629.8	732.7	894.0	1050.6	1099.8	1075.2	1026.1	874.0	735.8	640.5	585.2
60°	554.5	648.2	789.5	920.1	958.5	932.4	875.5	738.8	639.0	559.1	517.6
62.5°	485.4	566.8	685.1	804.9	820.2	794.1	745.0	634.4	548.4	485.4	454.7
65°	420.9	497.7	592.9	683.5	697.4	669.7	619.0	539.1	467.0	427.0	397.8
67.5°	357.9	419.3	503.8	569.9	577.5	551.4	510.0	445.4	400.9	357.9	336.4
70°	302.6	348.7	414.7	468.5	471.6	447.0	425.5	367.1	333.3	302.6	285.7
72.5°	248.8	281.1	331.8	371.7	373.3	357.9	337.9	301.1	271.9	250.4	233.5
75°	196.6	224.3	255.0	290.3	288.8	276.5	261.1	238.1	213.5	199.7	192.0
77.5°	150.5	167.4	192.0	215.0	215.0	208.9	199.7	182.8	167.4	153.6	145.9
80°	107.5	118.3	138.2	145.9	149.0	147.5	139.8	127.5	121.3	110.6	107.5
82.5°	69.1	76.8	86.0	93.7	98.3	95.2	93.7	87.6	78.3	75.3	72.2
85°	39.9	43.0	47.6	52.2	53.8	52.2	55.3	50.7	46.1	46.1	44.5
87.5°	16.9	18.4	21.5	21.5	23.0	23.0	21.5	23.0	23.0	21.5	20.0
90°	0.8	3.1	6.1	7.6	9.2	10.4	11.5	15.3	20.6	25.2	26.0
92.5°	11.5	16.0	22.1	26.0	32.1	36.3	40.5	61.1	90.1	116.0	117.6
95°	26.7	29.8	37.4	44.3	56.5	65.6	74.8	109.9	176.3	264.9	299.2
97.5°	39.7	44.3	52.7	62.6	76.3	86.6	97.0	142.0	234.4	377.1	487.8
100°	58.8	61.1	67.9	80.2	95.4	106.1	116.8	157.3	250.4	415.3	603.1
102.5°	76.3	77.9	84.7	97.0	113.0	123.7	134.4	171.0	251.2	400.8	606.9
105°	93.1	96.2	101.5	113.0	129.8	140.5	151.2	187.0	255.0	380.9	565.7
107.5°	111.5	113.7	119.1	129.8	146.6	157.2	167.9	203.1	263.4	370.2	527.5
110°	129.8	132.8	137.4	147.3	163.4	174.4	185.5	219.1	274.1	367.2	501.5

TEST NUMBER: P997987

CATALOG NUMBER: SA2XXDIP-B1005D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	146.6	149.6	155.0	164.1	179.4	190.9	202.3	234.4	285.5	368.0	484.8
115°	164.1	167.9	172.5	181.7	197.0	207.3	217.6	250.4	297.0	371.0	473.3
117.5°	182.4	185.5	190.1	198.5	213.0	223.7	234.4	264.9	309.2	375.6	467.2
120°	199.2	202.3	206.9	213.7	229.0	239.7	250.4	280.2	321.4	380.2	461.8
122.5°	215.3	217.6	222.1	229.8	245.0	256.1	267.2	294.7	332.1	385.5	458.8
125°	229.0	231.3	235.9	245.0	260.3	271.0	281.7	309.2	343.5	390.9	455.0
127.5°	240.5	243.5	249.6	259.6	274.1	285.2	296.2	322.9	354.2	396.2	452.7
130°	250.4	253.4	261.1	271.8	287.0	297.7	308.4	335.1	364.1	402.3	451.2
132.5°	259.6	263.4	271.8	283.2	299.2	309.9	320.6	345.8	374.1	408.4	450.4
135°	268.7	271.8	280.9	292.4	309.9	320.6	331.3	355.7	382.5	413.0	449.6
137.5°	277.1	280.9	290.1	302.3	319.9	329.8	339.7	364.1	389.3	417.6	449.6
140°	287.0	290.1	299.2	311.5	328.3	338.2	348.1	371.0	394.7	420.6	448.9
142.5°	297.0	299.2	307.6	319.9	335.9	345.0	354.2	376.3	399.3	422.9	448.9
145°	306.9	309.9	317.6	329.0	344.3	352.7	361.1	381.7	403.1	424.4	447.3
147.5°	317.6	319.9	327.5	338.2	351.2	358.8	366.4	386.3	405.4	425.2	445.1
150°	328.3	330.5	336.7	346.6	358.0	364.9	371.8	389.3	406.9	424.4	442.8
152.5°	338.9	339.7	345.8	354.2	364.9	371.0	377.1	392.4	407.6	422.9	438.9
155°	348.9	349.6	354.2	362.6	371.0	376.8	382.5	395.4	408.4	421.4	434.4
157.5°	357.3	358.0	361.8	369.5	376.3	381.3	386.3	397.7	408.4	418.3	429.8
160°	365.7	366.4	369.5	375.6	381.7	385.9	390.1	399.3	408.4	416.0	425.2
162.5°	374.1	373.3	376.3	380.9	386.3	389.4	392.4	400.0	407.6	413.8	421.4
165°	380.2	379.4	380.9	385.5	389.3	391.6	393.9	400.8	406.1	410.7	416.0
167.5°	385.5	384.7	386.3	389.3	392.4	393.9	395.4	400.8	405.4	407.6	411.5
170°	390.9	389.3	390.1	392.4	393.9	395.0	396.2	400.0	403.8	405.4	407.6
172.5°	393.9	393.1	392.4	394.7	395.4	396.2	397.0	399.3	401.5	402.3	403.1
175°	396.2	395.4	394.7	396.2	396.2	396.6	397.0	398.5	400.0	399.3	400.0
177.5°	397.7	396.2	395.4	397.0	397.0	397.0	397.0	397.7	399.3	397.7	397.0
180°	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0

TEST NUMBER: P997987

CATALOG NUMBER: SA2XXDIP-B1005D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4
2.5°	2076.7	2078.2	2081.3	2096.7	2104.3	2105.9	2099.7	2113.6	2118.2	2113.6	2110.5
5°	2175.0	2184.2	2202.7	2222.6	2221.1	2222.6	2231.8	2241.1	2244.1	2231.8	2236.4
7.5°	2261.0	2279.5	2299.4	2330.1	2330.1	2345.5	2351.6	2359.3	2377.8	2368.5	2365.5
10°	2359.3	2383.9	2420.8	2469.9	2471.5	2486.8	2502.2	2526.8	2534.4	2528.3	2531.4
12.5°	2482.2	2529.8	2532.9	2586.7	2611.2	2614.3	2638.9	2634.3	2649.6	2649.6	2675.7
15°	2536.0	2609.7	2651.2	2703.4	2718.8	2700.3	2720.3	2741.8	2743.3	2743.3	2741.8
17.5°	2632.7	2661.9	2703.4	2731.0	2737.2	2737.2	2738.7	2747.9	2741.8	2729.5	2738.7
20°	2652.7	2665.0	2680.4	2677.3	2680.4	2665.0	2649.6	2634.3	2635.8	2628.1	2651.2
22.5°	2615.8	2612.8	2577.4	2554.4	2554.4	2523.7	2494.5	2480.7	2466.9	2471.5	2479.1
25°	2523.7	2476.1	2433.1	2399.3	2391.6	2342.4	2302.5	2290.2	2267.2	2285.6	2288.7
27.5°	2376.2	2322.5	2253.3	2224.2	2184.2	2164.3	2136.6	2099.7	2052.1	2079.8	2075.2
30°	2218.0	2138.1	2081.3	2010.7	1947.7	1943.1	1890.8	1829.4	1804.8	1804.8	1818.6
32.5°	2041.4	1935.4	1852.4	1752.6	1691.2	1665.0	1602.1	1540.6	1554.5	1508.4	1525.3
35°	1835.5	1695.8	1591.3	1494.5	1448.5	1417.7	1336.3	1302.5	1265.7	1244.2	1284.1
37.5°	1638.9	1477.7	1344.0	1238.0	1221.1	1165.8	1110.5	1089.0	1067.5	1076.8	1075.2
40°	1399.3	1256.5	1136.7	1053.7	1024.5	998.4	961.5	935.4	921.6	929.3	930.8
42.5°	1182.7	1062.9	973.8	915.5	890.9	872.5	854.0	832.5	827.9	827.9	834.1
45°	1015.3	917.0	857.1	809.5	795.7	781.8	768.0	758.8	755.7	749.6	754.2
47.5°	881.7	803.3	766.5	731.1	715.8	712.7	700.4	695.8	689.7	688.1	689.7
50°	769.5	720.4	686.6	666.6	655.9	651.3	645.1	635.9	632.8	640.5	637.4
52.5°	691.2	645.1	626.7	606.7	600.6	594.4	585.2	586.8	585.2	582.2	582.2
55°	612.9	583.7	565.3	549.9	548.4	542.2	534.5	531.5	529.9	526.9	531.5
57.5°	549.9	526.9	510.0	496.1	490.0	490.0	482.3	476.2	476.2	474.6	476.2
60°	486.9	463.9	453.1	439.3	434.7	433.2	428.6	425.5	420.9	420.9	420.9
62.5°	428.6	410.1	397.8	385.5	387.1	379.4	373.3	370.2	370.2	371.7	371.7
65°	373.3	361.0	345.6	334.9	331.8	330.2	327.2	325.6	321.0	324.1	324.1
67.5°	322.6	305.7	296.5	291.8	287.2	285.7	282.6	279.6	278.0	276.5	279.6
70°	271.9	258.1	250.4	247.3	242.7	241.2	239.6	235.0	236.5	238.1	239.6
72.5°	225.8	213.5	212.0	202.8	202.8	202.8	196.6	199.7	198.1	195.1	198.1
75°	178.2	172.0	169.0	164.4	165.9	164.4	162.8	158.2	158.2	159.7	161.3
77.5°	141.3	135.2	133.6	129.0	126.0	129.0	126.0	124.4	124.4	126.0	126.0
80°	104.4	101.4	96.8	96.8	96.8	95.2	95.2	95.2	93.7	92.2	93.7
82.5°	69.1	69.1	67.6	66.0	67.6	64.5	66.0	66.0	66.0	66.0	66.0
85°	44.5	43.0	43.0	41.5	41.5	41.5	43.0	39.9	39.9	41.5	41.5
87.5°	20.0	20.0	20.0	21.5	20.0	20.0	20.0	21.5	20.0	20.0	20.0
90°	25.2	24.4	22.9	24.4	24.8	25.2	25.2	25.2	25.2	25.2	25.2
92.5°	98.5	77.1	65.7	57.3	54.2	51.1	50.4	47.3	48.1	46.6	48.1
95°	261.8	200.0	153.4	121.4	113.0	104.6	94.7	88.6	86.3	87.0	86.3
97.5°	491.6	409.2	326.7	249.6	226.7	203.8	174.1	158.8	150.4	145.8	150.4
100°	713.0	697.0	602.3	497.7	451.6	405.4	342.0	309.2	287.0	273.3	287.0
102.5°	795.4	885.5	882.5	813.0	763.4	713.8	643.5	581.7	552.7	532.8	552.7
105°	768.7	927.5	1013.8	1023.7	1011.1	998.5	951.2	903.9	871.0	860.3	871.0
107.5°	712.2	882.5	1010.7	1085.5	1100.8	1116.1	1115.3	1108.4	1098.5	1081.0	1098.5
110°	659.6	820.6	957.3	1055.0	1086.3	1117.6	1150.4	1164.9	1171.8	1171.0	1171.8

TEST NUMBER: P997987

CATALOG NUMBER: SA2XXDIP-B1005D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	622.9	764.2	893.9	1000.0	1037.0	1074.1	1122.9	1149.7	1164.2	1169.5	1164.2
115°	593.9	719.9	837.4	937.4	976.8	1016.1	1070.3	1105.4	1125.2	1132.1	1125.2
117.5°	574.1	683.2	788.6	881.7	919.1	956.5	1012.3	1049.7	1070.3	1075.6	1070.3
120°	558.8	657.3	751.9	832.9	867.6	902.3	955.8	991.6	1013.8	1021.4	1013.8
122.5°	545.8	636.7	721.4	797.0	827.5	858.0	904.6	939.7	958.8	964.9	958.8
125°	533.6	616.8	695.4	762.6	791.2	819.9	864.2	893.2	912.2	918.4	912.2
127.5°	522.2	597.0	669.5	733.6	760.4	787.1	826.0	853.5	870.3	874.8	870.3
130°	510.7	577.9	643.5	703.8	729.0	754.2	791.6	817.6	832.9	839.0	832.9
132.5°	501.5	559.6	619.1	673.3	696.6	719.9	756.5	782.5	796.2	801.6	796.2
135°	493.1	542.8	593.2	643.5	664.9	686.3	719.1	744.3	758.0	761.1	758.0
137.5°	487.0	529.0	572.5	613.8	632.8	651.9	683.2	705.4	717.6	722.2	717.6
140°	481.7	516.0	552.7	587.8	604.6	621.4	645.8	665.7	677.1	681.7	677.1
142.5°	476.4	505.4	535.1	564.1	577.5	590.9	613.8	631.3	641.2	641.2	641.2
145°	471.8	495.4	520.6	544.3	555.3	566.4	584.8	597.7	605.4	607.7	605.4
147.5°	467.2	487.8	508.4	527.5	535.9	544.3	560.3	571.0	576.4	577.9	576.4
150°	461.1	479.4	496.2	512.2	519.1	526.0	537.4	546.6	551.2	551.9	551.2
152.5°	455.7	471.0	486.3	499.3	505.0	510.7	519.1	526.7	529.8	529.8	529.8
155°	448.9	463.4	475.6	487.0	491.2	495.4	503.8	509.2	512.2	510.7	512.2
157.5°	442.8	454.2	464.9	474.8	478.2	481.7	487.8	492.4	493.9	493.9	493.9
160°	435.9	445.8	454.2	462.6	465.3	468.0	473.3	477.1	477.9	477.9	477.9
162.5°	429.8	437.4	444.3	451.2	453.1	455.0	460.3	462.6	463.4	462.6	463.4
165°	422.9	429.0	434.4	439.7	441.2	442.8	445.8	448.9	448.9	448.1	448.9
167.5°	416.0	420.6	425.2	429.0	430.6	432.1	433.6	435.1	435.1	434.4	435.1
170°	410.7	414.5	416.8	419.9	420.6	421.4	422.2	424.4	423.7	422.2	423.7
172.5°	405.4	407.6	409.2	411.5	411.8	412.2	413.0	413.8	413.0	412.2	413.0
175°	400.8	403.1	403.8	404.6	405.0	405.4	405.4	406.1	405.4	403.8	405.4
177.5°	397.7	399.3	399.3	400.0	400.0	400.0	400.0	400.0	399.3	397.7	399.3
180°	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0

TEST NUMBER: P997987

CATALOG NUMBER: SA2XXDIP-B1005D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4
2.5°	2118.2	2107.4	2098.2	2099.7	2107.4	2101.3	2085.9	2065.9	2058.3	2049.1	2058.3
5°	2245.7	2236.4	2218.0	2219.6	2214.9	2208.8	2184.2	2153.5	2153.5	2128.9	2125.9
7.5°	2371.6	2357.8	2345.5	2342.4	2325.5	2313.2	2291.7	2248.7	2231.8	2202.7	2185.8
10°	2512.9	2502.2	2488.4	2471.5	2462.2	2440.7	2405.4	2342.4	2311.7	2271.8	2242.6
12.5°	2655.8	2654.2	2623.5	2589.7	2588.2	2554.4	2529.8	2445.3	2403.9	2350.1	2281.0
15°	2746.4	2738.7	2721.8	2704.9	2709.5	2672.7	2617.4	2517.5	2489.9	2425.4	2351.6
17.5°	2744.9	2744.9	2740.3	2737.2	2732.6	2721.8	2691.1	2625.1	2580.5	2499.1	2430.0
20°	2657.3	2677.3	2681.9	2680.4	2695.7	2703.4	2701.9	2660.4	2625.1	2552.9	2482.2
22.5°	2482.2	2528.3	2548.3	2560.5	2592.8	2609.7	2649.6	2634.3	2625.1	2571.3	2511.4
25°	2319.4	2334.8	2394.7	2397.7	2442.3	2483.7	2523.7	2549.8	2583.6	2563.6	2512.9
27.5°	2109.0	2144.3	2187.3	2219.6	2228.8	2313.2	2379.3	2428.5	2505.3	2511.4	2494.5
30°	1870.9	1887.8	1958.4	2001.4	2050.6	2112.0	2207.3	2291.7	2360.9	2423.8	2445.3
32.5°	1580.6	1649.7	1691.2	1743.4	1786.4	1895.5	2012.2	2121.2	2201.1	2307.1	2353.2
35°	1314.8	1368.6	1439.3	1460.8	1539.1	1631.3	1783.3	1923.1	2044.4	2152.0	2245.7
37.5°	1095.2	1138.2	1213.5	1247.2	1293.3	1411.6	1539.1	1712.7	1858.6	1990.7	2107.4
40°	944.7	976.9	1033.7	1044.5	1082.9	1190.4	1293.3	1456.1	1649.7	1827.9	1955.4
42.5°	841.7	857.1	895.5	909.3	933.9	1006.1	1098.3	1251.9	1431.6	1615.9	1795.6
45°	768.0	778.8	801.8	814.1	844.8	877.1	952.3	1075.2	1216.5	1402.4	1595.9
47.5°	702.0	715.8	725.0	732.7	749.6	784.9	834.1	924.7	1059.9	1230.4	1417.7
50°	646.7	651.3	668.2	669.7	680.5	703.5	749.6	804.9	912.4	1050.6	1231.9
52.5°	591.4	596.0	606.7	617.5	622.1	640.5	671.2	717.3	797.2	906.3	1067.5
55°	536.1	542.2	553.0	560.6	565.3	580.6	599.0	643.6	706.6	783.4	915.5
57.5°	480.8	494.6	497.7	502.3	510.0	526.9	543.8	569.9	619.0	689.7	786.4
60°	428.6	433.2	443.9	448.5	456.2	465.4	486.9	506.9	542.2	597.5	685.1
62.5°	374.8	385.5	390.1	394.8	400.9	411.7	425.5	447.0	477.7	522.2	591.4
65°	328.7	330.2	339.5	345.6	351.7	359.4	373.3	393.2	411.7	453.1	503.8
67.5°	284.2	287.2	290.3	296.5	304.1	311.8	324.1	334.9	357.9	385.5	425.5
70°	241.2	241.2	248.8	253.4	251.9	261.1	270.3	282.6	299.5	325.6	357.9
72.5°	202.8	201.2	207.4	208.9	212.0	218.1	224.3	236.5	245.8	265.7	290.3
75°	161.3	164.4	167.4	167.4	172.0	176.6	182.8	188.9	199.7	212.0	230.4
77.5°	127.5	127.5	130.6	132.1	136.7	135.2	141.3	147.5	155.1	165.9	179.7
80°	93.7	96.8	96.8	96.8	98.3	99.8	106.0	110.6	115.2	122.9	129.0
82.5°	66.0	66.0	69.1	69.1	69.1	72.2	72.2	73.7	76.8	81.4	86.0
85°	41.5	41.5	41.5	43.0	41.5	43.0	46.1	44.5	46.1	49.2	49.2
87.5°	20.0	20.0	20.0	20.0	20.0	21.5	20.0	21.5	23.0	23.0	23.0
90°	25.2	25.2	25.2	24.8	24.4	22.9	24.4	25.2	26.0	25.2	20.6
92.5°	47.3	50.4	51.1	54.2	57.3	65.7	77.1	98.5	117.6	116.0	90.1
95°	88.6	94.7	104.6	113.0	121.4	153.4	200.0	261.8	299.2	264.9	176.3
97.5°	158.8	174.1	203.8	226.7	249.6	326.7	409.2	491.6	487.8	377.1	234.4
100°	309.2	342.0	405.4	451.6	497.7	602.3	697.0	713.0	603.1	415.3	250.4
102.5°	581.7	643.5	713.8	763.4	813.0	882.5	885.5	795.4	606.9	400.8	251.2
105°	903.9	951.2	998.5	1011.1	1023.7	1013.8	927.5	768.7	565.7	380.9	255.0
107.5°	1108.4	1115.3	1116.1	1100.8	1085.5	1010.7	882.5	712.2	527.5	370.2	263.4
110°	1164.9	1150.4	1117.6	1086.3	1055.0	957.3	820.6	659.6	501.5	367.2	274.1

TEST NUMBER: P997987

CATALOG NUMBER: SA2XXDIP-B1005D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1149.7	1122.9	1074.1	1037.0	1000.0	893.9	764.2	622.9	484.8	368.0	285.5
115°	1105.4	1070.3	1016.1	976.8	937.4	837.4	719.9	593.9	473.3	371.0	297.0
117.5°	1049.7	1012.3	956.5	919.1	881.7	788.6	683.2	574.1	467.2	375.6	309.2
120°	991.6	955.8	902.3	867.6	832.9	751.9	657.3	558.8	461.8	380.2	321.4
122.5°	939.7	904.6	858.0	827.5	797.0	721.4	636.7	545.8	458.8	385.5	332.1
125°	893.2	864.2	819.9	791.2	762.6	695.4	616.8	533.6	455.0	390.9	343.5
127.5°	853.5	826.0	787.1	760.4	733.6	669.5	597.0	522.2	452.7	396.2	354.2
130°	817.6	791.6	754.2	729.0	703.8	643.5	577.9	510.7	451.2	402.3	364.1
132.5°	782.5	756.5	719.9	696.6	673.3	619.1	559.6	501.5	450.4	408.4	374.1
135°	744.3	719.1	686.3	664.9	643.5	593.2	542.8	493.1	449.6	413.0	382.5
137.5°	705.4	683.2	651.9	632.8	613.8	572.5	529.0	487.0	449.6	417.6	389.3
140°	665.7	645.8	621.4	604.6	587.8	552.7	516.0	481.7	448.9	420.6	394.7
142.5°	631.3	613.8	590.9	577.5	564.1	535.1	505.4	476.4	448.9	422.9	399.3
145°	597.7	584.8	566.4	555.3	544.3	520.6	495.4	471.8	447.3	424.4	403.1
147.5°	571.0	560.3	544.3	535.9	527.5	508.4	487.8	467.2	445.1	425.2	405.4
150°	546.6	537.4	526.0	519.1	512.2	496.2	479.4	461.1	442.8	424.4	406.9
152.5°	526.7	519.1	510.7	505.0	499.3	486.3	471.0	455.7	438.9	422.9	407.6
155°	509.2	503.8	495.4	491.2	487.0	475.6	463.4	448.9	434.4	421.4	408.4
157.5°	492.4	487.8	481.7	478.2	474.8	464.9	454.2	442.8	429.8	418.3	408.4
160°	477.1	473.3	468.0	465.3	462.6	454.2	445.8	435.9	425.2	416.0	408.4
162.5°	462.6	460.3	455.0	453.1	451.2	444.3	437.4	429.8	421.4	413.8	407.6
165°	448.9	445.8	442.8	441.2	439.7	434.4	429.0	422.9	416.0	410.7	406.1
167.5°	435.1	433.6	432.1	430.6	429.0	425.2	420.6	416.0	411.5	407.6	405.4
170°	424.4	422.2	421.4	420.6	419.9	416.8	414.5	410.7	407.6	405.4	403.8
172.5°	413.8	413.0	412.2	411.8	411.5	409.2	407.6	405.4	403.1	402.3	401.5
175°	406.1	405.4	405.4	405.0	404.6	403.8	403.1	400.8	400.0	399.3	400.0
177.5°	400.0	400.0	400.0	400.0	400.0	399.3	399.3	397.7	397.0	397.7	399.3
180°	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0

TEST NUMBER: P997987

CATALOG NUMBER: SA2XXDIP-B1005D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4
2.5°	2050.6	2042.9	2038.3	2041.4	2032.2	2009.1	2009.1	2016.8	2007.6	1998.4	1984.5
5°	2107.4	2092.1	2082.8	2081.3	2059.8	2022.9	2015.3	2007.6	1987.6	1966.1	1943.1
7.5°	2162.7	2135.1	2119.7	2109.0	2078.2	2030.6	2010.7	1993.8	1961.5	1929.2	1900.1
10°	2208.8	2168.9	2150.4	2133.5	2093.6	2033.7	2001.4	1970.7	1929.2	1887.8	1850.9
12.5°	2245.7	2199.6	2176.5	2152.0	2102.8	2024.5	1984.5	1935.4	1893.9	1838.6	1801.8
15°	2307.1	2211.9	2190.4	2167.3	2116.6	2009.1	1960.0	1904.7	1847.8	1774.1	1734.2
17.5°	2356.3	2228.8	2227.2	2178.1	2112.0	2003.0	1927.7	1855.5	1794.1	1720.3	1657.4
20°	2385.4	2254.9	2230.3	2179.6	2096.7	1961.5	1883.2	1803.3	1737.2	1648.2	1585.2
22.5°	2410.0	2291.7	2227.2	2165.8	2064.4	1947.7	1832.5	1757.2	1666.6	1569.8	1509.9
25°	2419.2	2299.4	2231.8	2161.2	2041.4	1907.7	1777.2	1695.8	1594.4	1506.8	1425.4
27.5°	2420.8	2297.9	2214.9	2141.2	2009.1	1855.5	1721.9	1635.9	1523.7	1422.4	1340.9
30°	2405.4	2281.0	2205.7	2125.9	1978.4	1807.9	1654.3	1559.1	1439.3	1337.9	1253.4
32.5°	2359.3	2247.2	2185.8	2098.2	1938.5	1741.8	1589.8	1483.8	1357.8	1258.0	1176.6
35°	2282.5	2205.7	2138.1	2056.7	1886.2	1680.4	1525.3	1400.9	1273.4	1178.1	1101.3
37.5°	2187.3	2145.8	2082.8	2003.0	1826.3	1625.1	1453.1	1314.8	1187.3	1095.2	1019.9
40°	2058.3	2069.0	2007.6	1935.4	1755.7	1549.8	1359.4	1227.3	1107.5	1021.5	947.7
42.5°	1918.5	1963.0	1927.7	1858.6	1677.3	1466.9	1290.3	1144.3	1027.6	938.5	877.1
45°	1768.0	1844.8	1823.3	1772.6	1595.9	1379.3	1192.0	1050.6	947.7	861.7	807.9
47.5°	1603.6	1712.7	1712.7	1675.8	1505.3	1291.8	1107.5	963.1	861.7	800.3	748.0
50°	1436.2	1559.1	1579.0	1554.5	1403.9	1192.0	1004.6	874.0	786.4	726.5	688.1
52.5°	1261.1	1403.9	1440.8	1428.5	1296.4	1096.7	920.1	792.6	712.7	660.5	626.7
55°	1093.6	1259.5	1299.5	1304.1	1181.2	992.3	826.4	714.3	637.4	602.1	572.9
57.5°	935.4	1095.2	1139.7	1147.4	1064.5	897.0	738.8	640.5	571.4	542.2	519.2
60°	800.3	933.9	992.3	1009.2	937.0	786.4	657.4	562.2	510.0	482.3	460.8
62.5°	689.7	797.2	858.6	863.2	831.0	689.7	572.9	493.1	448.5	423.9	413.2
65°	582.2	678.9	715.8	734.2	708.1	597.5	494.6	428.6	393.2	371.7	361.0
67.5°	496.1	557.6	588.3	612.9	586.8	503.8	420.9	367.1	341.0	319.5	313.3
70°	407.0	457.7	480.8	505.4	482.3	419.3	359.4	310.3	287.2	270.3	262.7
72.5°	325.6	365.6	387.1	402.4	388.6	336.4	287.2	253.4	236.5	224.3	219.7
75°	258.1	285.7	298.0	308.7	302.6	262.7	231.9	204.3	188.9	178.2	175.1
77.5°	196.6	216.6	230.4	233.5	225.8	199.7	173.6	156.7	144.4	138.2	135.2
80°	139.8	152.1	159.7	164.4	156.7	145.9	127.5	115.2	104.4	96.8	95.2
82.5°	93.7	99.8	106.0	104.4	101.4	92.2	81.4	75.3	70.7	64.5	64.5
85°	53.8	55.3	58.4	59.9	58.4	52.2	46.1	43.0	39.9	35.3	35.3
87.5°	23.0	24.6	24.6	26.1	23.0	23.0	20.0	16.9	16.9	15.4	13.8
90°	15.3	11.5	10.4	9.2	7.6	6.1	3.1	0.8	3.1	6.1	7.6
92.5°	61.1	40.5	36.3	32.1	26.0	22.1	16.0	11.5	16.0	22.1	26.0
95°	109.9	74.8	65.6	56.5	44.3	37.4	29.8	26.7	29.8	37.4	44.3
97.5°	142.0	97.0	86.6	76.3	62.6	52.7	44.3	39.7	44.3	52.7	62.6
100°	157.3	116.8	106.1	95.4	80.2	67.9	61.1	58.8	61.1	67.9	80.2
102.5°	171.0	134.4	123.7	113.0	97.0	84.7	77.9	76.3	77.9	84.7	97.0
105°	187.0	151.2	140.5	129.8	113.0	101.5	96.2	93.1	96.2	101.5	113.0
107.5°	203.1	167.9	157.2	146.6	129.8	119.1	113.7	111.5	113.7	119.1	129.8
110°	219.1	185.5	174.4	163.4	147.3	137.4	132.8	129.8	132.8	137.4	147.3

TEST NUMBER: P997987

CATALOG NUMBER: SA2XXDIP-B1005D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	234.4	202.3	190.9	179.4	164.1	155.0	149.6	146.6	149.6	155.0	164.1
115°	250.4	217.6	207.3	197.0	181.7	172.5	167.9	164.1	167.9	172.5	181.7
117.5°	264.9	234.4	223.7	213.0	198.5	190.1	185.5	182.4	185.5	190.1	198.5
120°	280.2	250.4	239.7	229.0	213.7	206.9	202.3	199.2	202.3	206.9	213.7
122.5°	294.7	267.2	256.1	245.0	229.8	222.1	217.6	215.3	217.6	222.1	229.8
125°	309.2	281.7	271.0	260.3	245.0	235.9	231.3	229.0	231.3	235.9	245.0
127.5°	322.9	296.2	285.2	274.1	259.6	249.6	243.5	240.5	243.5	249.6	259.6
130°	335.1	308.4	297.7	287.0	271.8	261.1	253.4	250.4	253.4	261.1	271.8
132.5°	345.8	320.6	309.9	299.2	283.2	271.8	263.4	259.6	263.4	271.8	283.2
135°	355.7	331.3	320.6	309.9	292.4	280.9	271.8	268.7	271.8	280.9	292.4
137.5°	364.1	339.7	329.8	319.9	302.3	290.1	280.9	277.1	280.9	290.1	302.3
140°	371.0	348.1	338.2	328.3	311.5	299.2	290.1	287.0	290.1	299.2	311.5
142.5°	376.3	354.2	345.0	335.9	319.9	307.6	299.2	297.0	299.2	307.6	319.9
145°	381.7	361.1	352.7	344.3	329.0	317.6	309.9	306.9	309.9	317.6	329.0
147.5°	386.3	366.4	358.8	351.2	338.2	327.5	319.9	317.6	319.9	327.5	338.2
150°	389.3	371.8	364.9	358.0	346.6	336.7	330.5	328.3	330.5	336.7	346.6
152.5°	392.4	377.1	371.0	364.9	354.2	345.8	339.7	338.9	339.7	345.8	354.2
155°	395.4	382.5	376.8	371.0	362.6	354.2	349.6	348.9	349.6	354.2	362.6
157.5°	397.7	386.3	381.3	376.3	369.5	361.8	358.0	357.3	358.0	361.8	369.5
160°	399.3	390.1	385.9	381.7	375.6	369.5	366.4	365.7	366.4	369.5	375.6
162.5°	400.0	392.4	389.4	386.3	380.9	376.3	373.3	374.1	373.3	376.3	380.9
165°	400.8	393.9	391.6	389.3	385.5	380.9	379.4	380.2	379.4	380.9	385.5
167.5°	400.8	395.4	393.9	392.4	389.3	386.3	384.7	385.5	384.7	386.3	389.3
170°	400.0	396.2	395.0	393.9	392.4	390.1	389.3	390.9	389.3	390.1	392.4
172.5°	399.3	397.0	396.2	395.4	394.7	392.4	393.1	393.9	393.1	392.4	394.7
175°	398.5	397.0	396.6	396.2	396.2	394.7	395.4	396.2	395.4	394.7	396.2
177.5°	397.7	397.0	397.0	397.0	397.0	395.4	396.2	397.7	396.2	395.4	397.0
180°	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0

TEST NUMBER: P997987

CATALOG NUMBER: SA2XXDIP-B1005D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4
2.5°	1976.9	1984.5	1983.0	1967.6	1950.7	1936.9	1910.8	1913.9	1904.7	1906.2	1915.4
5°	1927.7	1927.7	1921.6	1900.1	1872.4	1857.1	1827.9	1820.2	1801.8	1800.2	1798.7
7.5°	1875.5	1867.8	1860.1	1829.4	1795.6	1771.0	1731.1	1721.9	1703.4	1691.2	1685.0
10°	1814.0	1803.3	1787.9	1752.6	1711.1	1680.4	1638.9	1626.6	1591.3	1576.0	1566.7
12.5°	1746.5	1740.3	1715.7	1686.6	1619.0	1585.2	1525.3	1537.6	1502.2	1471.5	1466.9
15°	1678.9	1655.8	1642.0	1594.4	1513.0	1497.6	1450.0	1425.4	1393.2	1368.6	1368.6
17.5°	1612.8	1577.5	1546.8	1496.1	1436.2	1393.2	1357.8	1345.6	1305.6	1281.0	1276.4
20°	1525.3	1485.3	1477.7	1405.5	1364.0	1316.4	1282.6	1251.9	1222.7	1211.9	1204.2
22.5°	1442.3	1396.2	1384.0	1322.5	1281.0	1233.4	1199.6	1178.1	1156.6	1148.9	1135.1
25°	1353.2	1325.6	1307.2	1241.1	1195.0	1150.5	1127.4	1112.1	1092.1	1090.6	1081.4
27.5°	1267.2	1241.1	1222.7	1159.7	1125.9	1084.4	1066.0	1049.1	1038.4	1033.7	1029.1
30°	1193.5	1164.3	1142.8	1096.7	1055.2	1021.5	1006.1	995.3	989.2	981.5	980.0
32.5°	1112.1	1095.2	1066.0	1030.7	998.4	966.2	956.9	949.3	940.0	937.0	935.4
35°	1043.0	1019.9	1001.5	961.5	947.7	920.1	909.3	903.2	890.9	887.8	884.7
37.5°	975.4	953.9	933.9	909.3	883.2	867.9	861.7	852.5	846.3	847.9	844.8
40°	907.8	890.9	875.5	849.4	834.1	826.4	814.1	804.9	801.8	803.3	801.8
42.5°	841.7	826.4	817.2	797.2	781.8	774.2	766.5	757.3	761.9	761.9	766.5
45°	781.8	768.0	761.9	746.5	737.3	725.0	717.3	715.8	721.9	720.4	720.4
47.5°	720.4	715.8	708.1	694.3	682.0	674.3	672.8	672.8	678.9	682.0	680.5
50°	672.8	663.6	654.3	643.6	634.4	631.3	626.7	629.8	635.9	635.9	639.0
52.5°	612.9	606.7	603.7	594.4	588.3	588.3	588.3	589.8	594.4	599.0	597.5
55°	560.6	556.0	553.0	548.4	540.7	542.2	540.7	543.8	548.4	553.0	556.0
57.5°	505.4	503.8	500.7	493.1	493.1	491.5	496.1	497.7	505.4	508.4	513.0
60°	456.2	451.6	451.6	445.4	445.4	445.4	450.1	454.7	460.8	462.3	465.4
62.5°	404.0	404.0	402.4	397.8	397.8	402.4	404.0	410.1	413.2	413.2	417.8
65°	354.8	353.3	351.7	353.3	354.8	354.8	359.4	362.5	365.6	367.1	368.6
67.5°	305.7	304.1	307.2	305.7	308.7	314.9	313.3	318.0	322.6	322.6	324.1
70°	259.6	262.7	261.1	264.2	262.7	265.7	270.3	271.9	271.9	273.4	278.0
72.5°	216.6	216.6	216.6	215.0	216.6	219.7	222.7	224.3	227.3	228.9	233.5
75°	175.1	175.1	172.0	175.1	175.1	178.2	181.3	181.3	181.3	184.3	188.9
77.5°	132.1	133.6	132.1	135.2	135.2	136.7	139.8	138.2	141.3	142.9	144.4
80°	96.8	95.2	95.2	95.2	96.8	96.8	99.8	101.4	101.4	106.0	102.9
82.5°	61.4	63.0	61.4	63.0	63.0	64.5	63.0	64.5	66.0	69.1	67.6
85°	35.3	33.8	33.8	35.3	33.8	33.8	35.3	33.8	35.3	33.8	35.3
87.5°	13.8	12.3	12.3	12.3	12.3	10.8	10.8	9.2	9.2	9.2	7.7
90°	9.2	10.4	11.5	15.3	20.6	25.2	26.0	25.2	24.4	22.9	24.4
92.5°	32.1	36.3	40.5	61.1	90.1	116.0	117.6	98.5	77.1	65.7	57.3
95°	56.5	65.6	74.8	109.9	176.3	264.9	299.2	261.8	200.0	153.4	121.4
97.5°	76.3	86.6	97.0	142.0	234.4	377.1	487.8	491.6	409.2	326.7	249.6
100°	95.4	106.1	116.8	157.3	250.4	415.3	603.1	713.0	697.0	602.3	497.7
102.5°	113.0	123.7	134.4	171.0	251.2	400.8	606.9	795.4	885.5	882.5	813.0
105°	129.8	140.5	151.2	187.0	255.0	380.9	565.7	768.7	927.5	1013.8	1023.7
107.5°	146.6	157.2	167.9	203.1	263.4	370.2	527.5	712.2	882.5	1010.7	1085.5
110°	163.4	174.4	185.5	219.1	274.1	367.2	501.5	659.6	820.6	957.3	1055.0

TEST NUMBER: P997987

CATALOG NUMBER: SA2XXDIP-B1005D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	179.4	190.9	202.3	234.4	285.5	368.0	484.8	622.9	764.2	893.9	1000.0
115°	197.0	207.3	217.6	250.4	297.0	371.0	473.3	593.9	719.9	837.4	937.4
117.5°	213.0	223.7	234.4	264.9	309.2	375.6	467.2	574.1	683.2	788.6	881.7
120°	229.0	239.7	250.4	280.2	321.4	380.2	461.8	558.8	657.3	751.9	832.9
122.5°	245.0	256.1	267.2	294.7	332.1	385.5	458.8	545.8	636.7	721.4	797.0
125°	260.3	271.0	281.7	309.2	343.5	390.9	455.0	533.6	616.8	695.4	762.6
127.5°	274.1	285.2	296.2	322.9	354.2	396.2	452.7	522.2	597.0	669.5	733.6
130°	287.0	297.7	308.4	335.1	364.1	402.3	451.2	510.7	577.9	643.5	703.8
132.5°	299.2	309.9	320.6	345.8	374.1	408.4	450.4	501.5	559.6	619.1	673.3
135°	309.9	320.6	331.3	355.7	382.5	413.0	449.6	493.1	542.8	593.2	643.5
137.5°	319.9	329.8	339.7	364.1	389.3	417.6	449.6	487.0	529.0	572.5	613.8
140°	328.3	338.2	348.1	371.0	394.7	420.6	448.9	481.7	516.0	552.7	587.8
142.5°	335.9	345.0	354.2	376.3	399.3	422.9	448.9	476.4	505.4	535.1	564.1
145°	344.3	352.7	361.1	381.7	403.1	424.4	447.3	471.8	495.4	520.6	544.3
147.5°	351.2	358.8	366.4	386.3	405.4	425.2	445.1	467.2	487.8	508.4	527.5
150°	358.0	364.9	371.8	389.3	406.9	424.4	442.8	461.1	479.4	496.2	512.2
152.5°	364.9	371.0	377.1	392.4	407.6	422.9	438.9	455.7	471.0	486.3	499.3
155°	371.0	376.8	382.5	395.4	408.4	421.4	434.4	448.9	463.4	475.6	487.0
157.5°	376.3	381.3	386.3	397.7	408.4	418.3	429.8	442.8	454.2	464.9	474.8
160°	381.7	385.9	390.1	399.3	408.4	416.0	425.2	435.9	445.8	454.2	462.6
162.5°	386.3	389.4	392.4	400.0	407.6	413.8	421.4	429.8	437.4	444.3	451.2
165°	389.3	391.6	393.9	400.8	406.1	410.7	416.0	422.9	429.0	434.4	439.7
167.5°	392.4	393.9	395.4	400.8	405.4	407.6	411.5	416.0	420.6	425.2	429.0
170°	393.9	395.0	396.2	400.0	403.8	405.4	407.6	410.7	414.5	416.8	419.9
172.5°	395.4	396.2	397.0	399.3	401.5	402.3	403.1	405.4	407.6	409.2	411.5
175°	396.2	396.6	397.0	398.5	400.0	399.3	400.0	400.8	403.1	403.8	404.6
177.5°	397.0	397.0	397.0	397.7	399.3	397.7	397.0	397.7	399.3	399.3	400.0
180°	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0

TEST NUMBER: P997987

CATALOG NUMBER: SA2XXDIP-B1005D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4
2.5°	1904.7	1909.3	1898.5	1895.5	1898.5	1887.8	1890.8	1893.9	1893.9	1898.5	1901.6
5°	1794.1	1787.9	1777.2	1774.1	1771.0	1775.6	1772.6	1777.2	1778.7	1789.5	1791.0
7.5°	1685.0	1675.8	1666.6	1657.4	1654.3	1646.6	1654.3	1654.3	1665.0	1662.0	1669.7
10°	1556.0	1554.5	1542.2	1537.6	1531.4	1519.1	1536.0	1531.4	1539.1	1552.9	1556.0
12.5°	1460.8	1443.9	1451.5	1430.0	1437.7	1425.4	1427.0	1427.0	1439.3	1440.8	1437.7
15°	1370.1	1356.3	1336.3	1327.1	1322.5	1316.4	1336.3	1337.9	1328.7	1350.2	1342.5
17.5°	1278.0	1278.0	1259.5	1254.9	1242.6	1248.8	1245.7	1247.2	1244.2	1259.5	1267.2
20°	1198.1	1190.4	1184.3	1185.8	1170.4	1167.4	1164.3	1167.4	1178.1	1188.9	1192.0
22.5°	1133.6	1129.0	1113.6	1116.7	1104.4	1109.0	1105.9	1113.6	1115.2	1115.2	1125.9
25°	1072.1	1066.0	1067.5	1061.4	1056.8	1056.8	1052.2	1056.8	1062.9	1066.0	1067.5
27.5°	1026.1	1021.5	1013.8	1009.2	1012.2	1004.6	1010.7	1015.3	1015.3	1012.2	1015.3
30°	970.8	973.8	973.8	958.5	964.6	961.5	966.2	969.2	969.2	970.8	967.7
32.5°	933.9	924.7	923.1	921.6	921.6	915.5	915.5	920.1	921.6	923.1	927.8
35°	884.7	884.7	877.1	881.7	875.5	877.1	875.5	877.1	880.1	875.5	880.1
37.5°	840.2	841.7	838.7	841.7	843.3	840.2	837.1	843.3	840.2	840.2	837.1
40°	801.8	800.3	801.8	801.8	801.8	803.3	800.3	800.3	800.3	797.2	794.1
42.5°	769.5	760.3	763.4	764.9	760.3	760.3	761.9	760.3	764.9	755.7	755.7
45°	723.5	720.4	721.9	721.9	725.0	720.4	723.5	725.0	720.4	718.9	715.8
47.5°	682.0	685.1	682.0	685.1	685.1	688.1	682.0	683.5	685.1	678.9	674.3
50°	640.5	640.5	645.1	643.6	645.1	642.1	642.1	640.5	642.1	639.0	634.4
52.5°	602.1	597.5	605.2	603.7	602.1	600.6	599.0	600.6	597.5	594.4	594.4
55°	554.5	554.5	559.1	560.6	560.6	557.6	554.5	556.0	554.5	553.0	551.4
57.5°	516.1	510.0	513.0	514.6	514.6	510.0	513.0	510.0	510.0	511.5	506.9
60°	467.0	467.0	463.9	468.5	468.5	465.4	465.4	467.0	463.9	462.3	460.8
62.5°	414.7	416.3	420.9	422.4	423.9	420.9	417.8	419.3	419.3	414.7	416.3
65°	370.2	373.3	379.4	377.9	374.8	376.3	373.3	374.8	370.2	371.7	367.1
67.5°	327.2	325.6	327.2	327.2	330.2	328.7	325.6	325.6	324.1	328.7	324.1
70°	281.1	281.1	281.1	281.1	282.6	284.2	281.1	278.0	279.6	276.5	274.9
72.5°	233.5	235.0	233.5	236.5	231.9	235.0	235.0	233.5	231.9	231.9	231.9
75°	188.9	192.0	187.4	188.9	187.4	190.5	188.9	188.9	185.9	184.3	185.9
77.5°	144.4	145.9	142.9	144.4	142.9	144.4	144.4	142.9	142.9	142.9	142.9
80°	102.9	104.4	102.9	101.4	99.8	102.9	99.8	101.4	102.9	101.4	104.4
82.5°	66.0	66.0	64.5	66.0	63.0	63.0	64.5	64.5	63.0	66.0	63.0
85°	32.3	32.3	35.3	32.3	30.7	30.7	30.7	32.3	30.7	33.8	32.3
87.5°	7.7	6.1	7.7	7.7	6.1	6.1	7.7	6.1	7.7	9.2	6.1
90°	24.8	25.2	25.2	25.2	25.2	25.2	25.2	25.2	25.2	25.2	24.8
92.5°	54.2	51.1	50.4	47.3	48.1	46.6	48.1	47.3	50.4	51.1	54.2
95°	113.0	104.6	94.7	88.6	86.3	87.0	86.3	88.6	94.7	104.6	113.0
97.5°	226.7	203.8	174.1	158.8	150.4	145.8	150.4	158.8	174.1	203.8	226.7
100°	451.6	405.4	342.0	309.2	287.0	273.3	287.0	309.2	342.0	405.4	451.6
102.5°	763.4	713.8	643.5	581.7	552.7	532.8	552.7	581.7	643.5	713.8	763.4
105°	1011.1	998.5	951.2	903.9	871.0	860.3	871.0	903.9	951.2	998.5	1011.1
107.5°	1100.8	1116.1	1115.3	1108.4	1098.5	1081.0	1098.5	1108.4	1115.3	1116.1	1100.8
110°	1086.3	1117.6	1150.4	1164.9	1171.8	1171.0	1171.8	1164.9	1150.4	1117.6	1086.3

TEST NUMBER: P997987

CATALOG NUMBER: SA2XXDIP-B1005D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1037.0	1074.1	1122.9	1149.7	1164.2	1169.5	1164.2	1149.7	1122.9	1074.1	1037.0
115°	976.8	1016.1	1070.3	1105.4	1125.2	1132.1	1125.2	1105.4	1070.3	1016.1	976.8
117.5°	919.1	956.5	1012.3	1049.7	1070.3	1075.6	1070.3	1049.7	1012.3	956.5	919.1
120°	867.6	902.3	955.8	991.6	1013.8	1021.4	1013.8	991.6	955.8	902.3	867.6
122.5°	827.5	858.0	904.6	939.7	958.8	964.9	958.8	939.7	904.6	858.0	827.5
125°	791.2	819.9	864.2	893.2	912.2	918.4	912.2	893.2	864.2	819.9	791.2
127.5°	760.4	787.1	826.0	853.5	870.3	874.8	870.3	853.5	826.0	787.1	760.4
130°	729.0	754.2	791.6	817.6	832.9	839.0	832.9	817.6	791.6	754.2	729.0
132.5°	696.6	719.9	756.5	782.5	796.2	801.6	796.2	782.5	756.5	719.9	696.6
135°	664.9	686.3	719.1	744.3	758.0	761.1	758.0	744.3	719.1	686.3	664.9
137.5°	632.8	651.9	683.2	705.4	717.6	722.2	717.6	705.4	683.2	651.9	632.8
140°	604.6	621.4	645.8	665.7	677.1	681.7	677.1	665.7	645.8	621.4	604.6
142.5°	577.5	590.9	613.8	631.3	641.2	641.2	641.2	631.3	613.8	590.9	577.5
145°	555.3	566.4	584.8	597.7	605.4	607.7	605.4	597.7	584.8	566.4	555.3
147.5°	535.9	544.3	560.3	571.0	576.4	577.9	576.4	571.0	560.3	544.3	535.9
150°	519.1	526.0	537.4	546.6	551.2	551.9	551.2	546.6	537.4	526.0	519.1
152.5°	505.0	510.7	519.1	526.7	529.8	529.8	529.8	526.7	519.1	510.7	505.0
155°	491.2	495.4	503.8	509.2	512.2	510.7	512.2	509.2	503.8	495.4	491.2
157.5°	478.2	481.7	487.8	492.4	493.9	493.9	493.9	492.4	487.8	481.7	478.2
160°	465.3	468.0	473.3	477.1	477.9	477.9	477.9	477.1	473.3	468.0	465.3
162.5°	453.1	455.0	460.3	462.6	463.4	462.6	463.4	462.6	460.3	455.0	453.1
165°	441.2	442.8	445.8	448.9	448.9	448.1	448.9	448.9	445.8	442.8	441.2
167.5°	430.6	432.1	433.6	435.1	435.1	434.4	435.1	435.1	433.6	432.1	430.6
170°	420.6	421.4	422.2	424.4	423.7	422.2	423.7	424.4	422.2	421.4	420.6
172.5°	411.8	412.2	413.0	413.8	413.0	412.2	413.0	413.8	413.0	412.2	411.8
175°	405.0	405.4	405.4	406.1	405.4	403.8	405.4	406.1	405.4	405.4	405.0
177.5°	400.0	400.0	400.0	400.0	399.3	397.7	399.3	400.0	400.0	400.0	400.0
180°	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0

TEST NUMBER: P997987

CATALOG NUMBER: SA2XXDIP-B1005D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4	1998.4
2.5°	1897.0	1909.3	1904.7	1887.8	1907.7	1907.7	1921.6	1921.6	1938.5	1944.6	1953.8
5°	1789.5	1798.7	1806.4	1798.7	1812.5	1834.0	1846.3	1857.1	1880.1	1889.3	1903.1
7.5°	1674.3	1691.2	1698.8	1698.8	1721.9	1746.5	1771.0	1786.4	1818.6	1830.9	1844.8
10°	1562.1	1582.1	1597.5	1595.9	1634.3	1649.7	1680.4	1715.7	1748.0	1766.4	1786.4
12.5°	1443.9	1454.6	1476.1	1506.8	1516.1	1543.7	1579.0	1623.6	1681.9	1698.8	1728.0
15°	1345.6	1374.7	1391.6	1405.5	1427.0	1453.1	1491.5	1534.5	1592.9	1629.7	1660.4
17.5°	1262.6	1301.0	1311.8	1308.7	1336.3	1376.3	1420.8	1453.1	1505.3	1549.8	1579.0
20°	1195.0	1210.4	1228.8	1236.5	1258.0	1301.0	1344.0	1380.9	1423.9	1459.2	1493.0
22.5°	1127.4	1139.7	1155.1	1168.9	1185.8	1210.4	1251.9	1297.9	1339.4	1373.2	1411.6
25°	1072.1	1079.8	1093.6	1104.4	1122.8	1139.7	1168.9	1219.6	1268.8	1288.7	1322.5
27.5°	1018.4	1024.5	1033.7	1046.0	1055.2	1072.1	1098.3	1139.7	1190.4	1210.4	1256.5
30°	970.8	975.4	984.6	990.7	995.3	1015.3	1035.3	1067.5	1105.9	1133.6	1167.4
32.5°	926.2	930.8	940.0	941.6	947.7	958.5	976.9	1006.1	1039.9	1062.9	1092.1
35°	877.1	880.1	889.4	892.4	897.0	906.3	920.1	941.6	972.3	989.2	1015.3
37.5°	838.7	837.1	843.3	847.9	854.0	858.6	863.2	884.7	907.8	923.1	943.1
40°	797.2	794.1	795.7	801.8	804.9	811.0	811.0	832.5	847.9	860.2	875.5
42.5°	755.7	754.2	751.1	754.2	757.3	758.8	760.3	775.7	791.1	801.8	818.7
45°	714.3	712.7	709.6	711.2	711.2	714.3	718.9	725.0	735.8	745.0	754.2
47.5°	675.8	672.8	668.2	666.6	669.7	669.7	669.7	675.8	686.6	689.7	698.9
50°	635.9	631.3	625.2	622.1	622.1	620.6	623.6	625.2	634.4	637.4	645.1
52.5°	592.9	589.8	583.7	577.5	579.1	576.0	577.5	579.1	582.2	586.8	591.4
55°	549.9	543.8	539.1	537.6	533.0	533.0	528.4	534.5	533.0	534.5	540.7
57.5°	508.4	502.3	494.6	491.5	486.9	485.4	482.3	480.8	482.3	486.9	491.5
60°	459.3	456.2	451.6	447.0	443.9	439.3	436.2	436.2	434.7	434.7	436.2
62.5°	411.7	410.1	404.0	402.4	399.4	396.3	391.7	388.6	388.6	391.7	393.2
65°	365.6	364.0	359.4	357.9	350.2	347.1	345.6	344.1	341.0	341.0	341.0
67.5°	322.6	318.0	318.0	310.3	304.1	301.1	298.0	296.5	296.5	296.5	298.0
70°	274.9	274.9	270.3	265.7	259.6	261.1	256.5	251.9	251.9	248.8	250.4
72.5°	228.9	227.3	222.7	221.2	216.6	212.0	208.9	212.0	207.4	205.8	207.4
75°	184.3	182.8	179.7	176.6	178.2	173.6	169.0	167.4	167.4	164.4	164.4
77.5°	141.3	144.4	138.2	136.7	133.6	130.6	129.0	127.5	127.5	127.5	130.6
80°	98.3	99.8	99.8	96.8	98.3	93.7	93.7	93.7	89.1	90.6	92.2
82.5°	63.0	63.0	61.4	63.0	61.4	61.4	59.9	59.9	58.4	58.4	59.9
85°	35.3	33.8	32.3	35.3	33.8	33.8	32.3	32.3	32.3	32.3	32.3
87.5°	7.7	9.2	9.2	9.2	9.2	10.8	10.8	10.8	12.3	12.3	12.3
90°	24.4	22.9	24.4	25.2	26.0	25.2	20.6	15.3	11.5	10.4	9.2
92.5°	57.3	65.7	77.1	98.5	117.6	116.0	90.1	61.1	40.5	36.3	32.1
95°	121.4	153.4	200.0	261.8	299.2	264.9	176.3	109.9	74.8	65.6	56.5
97.5°	249.6	326.7	409.2	491.6	487.8	377.1	234.4	142.0	97.0	86.6	76.3
100°	497.7	602.3	697.0	713.0	603.1	415.3	250.4	157.3	116.8	106.1	95.4
102.5°	813.0	882.5	885.5	795.4	606.9	400.8	251.2	171.0	134.4	123.7	113.0
105°	1023.7	1013.8	927.5	768.7	565.7	380.9	255.0	187.0	151.2	140.5	129.8
107.5°	1085.5	1010.7	882.5	712.2	527.5	370.2	263.4	203.1	167.9	157.2	146.6
110°	1055.0	957.3	820.6	659.6	501.5	367.2	274.1	219.1	185.5	174.4	163.4

TEST NUMBER: P997987

CATALOG NUMBER: SA2XXDIP-B1005D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1000.0	893.9	764.2	622.9	484.8	368.0	285.5	234.4	202.3	190.9	179.4
115°	937.4	837.4	719.9	593.9	473.3	371.0	297.0	250.4	217.6	207.3	197.0
117.5°	881.7	788.6	683.2	574.1	467.2	375.6	309.2	264.9	234.4	223.7	213.0
120°	832.9	751.9	657.3	558.8	461.8	380.2	321.4	280.2	250.4	239.7	229.0
122.5°	797.0	721.4	636.7	545.8	458.8	385.5	332.1	294.7	267.2	256.1	245.0
125°	762.6	695.4	616.8	533.6	455.0	390.9	343.5	309.2	281.7	271.0	260.3
127.5°	733.6	669.5	597.0	522.2	452.7	396.2	354.2	322.9	296.2	285.2	274.1
130°	703.8	643.5	577.9	510.7	451.2	402.3	364.1	335.1	308.4	297.7	287.0
132.5°	673.3	619.1	559.6	501.5	450.4	408.4	374.1	345.8	320.6	309.9	299.2
135°	643.5	593.2	542.8	493.1	449.6	413.0	382.5	355.7	331.3	320.6	309.9
137.5°	613.8	572.5	529.0	487.0	449.6	417.6	389.3	364.1	339.7	329.8	319.9
140°	587.8	552.7	516.0	481.7	448.9	420.6	394.7	371.0	348.1	338.2	328.3
142.5°	564.1	535.1	505.4	476.4	448.9	422.9	399.3	376.3	354.2	345.0	335.9
145°	544.3	520.6	495.4	471.8	447.3	424.4	403.1	381.7	361.1	352.7	344.3
147.5°	527.5	508.4	487.8	467.2	445.1	425.2	405.4	386.3	366.4	358.8	351.2
150°	512.2	496.2	479.4	461.1	442.8	424.4	406.9	389.3	371.8	364.9	358.0
152.5°	499.3	486.3	471.0	455.7	438.9	422.9	407.6	392.4	377.1	371.0	364.9
155°	487.0	475.6	463.4	448.9	434.4	421.4	408.4	395.4	382.5	376.8	371.0
157.5°	474.8	464.9	454.2	442.8	429.8	418.3	408.4	397.7	386.3	381.3	376.3
160°	462.6	454.2	445.8	435.9	425.2	416.0	408.4	399.3	390.1	385.9	381.7
162.5°	451.2	444.3	437.4	429.8	421.4	413.8	407.6	400.0	392.4	389.4	386.3
165°	439.7	434.4	429.0	422.9	416.0	410.7	406.1	400.8	393.9	391.6	389.3
167.5°	429.0	425.2	420.6	416.0	411.5	407.6	405.4	400.8	395.4	393.9	392.4
170°	419.9	416.8	414.5	410.7	407.6	405.4	403.8	400.0	396.2	395.0	393.9
172.5°	411.5	409.2	407.6	405.4	403.1	402.3	401.5	399.3	397.0	396.2	395.4
175°	404.6	403.8	403.1	400.8	400.0	399.3	400.0	398.5	397.0	396.6	396.2
177.5°	400.0	399.3	399.3	397.7	397.0	397.7	399.3	397.7	397.0	397.0	397.0
180°	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0	397.0

TEST NUMBER: P997987

CATALOG NUMBER: SA2XXDIP-B1005D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1998.4	1998.4	1998.4	1998.4
2.5°	1961.5	1961.5	1984.5	2009.1
5°	1918.5	1929.2	1966.1	1999.9
7.5°	1877.0	1895.5	1941.5	1984.5
10°	1826.3	1850.9	1907.7	1958.4
12.5°	1777.2	1800.2	1866.3	1923.1
15°	1708.1	1737.2	1807.9	1878.6
17.5°	1638.9	1668.1	1754.1	1837.1
20°	1557.5	1595.9	1692.7	1803.3
22.5°	1482.3	1529.9	1637.4	1726.5
25°	1399.3	1473.0	1572.9	1688.1
27.5°	1325.6	1399.3	1500.7	1617.4
30°	1242.6	1317.9	1422.4	1529.9
32.5°	1162.8	1231.9	1333.3	1465.4
35°	1079.8	1145.9	1244.2	1377.8
37.5°	1004.6	1069.1	1176.6	1299.5
40°	930.8	998.4	1090.6	1213.5
42.5°	861.7	921.6	1004.6	1127.4
45°	798.7	841.7	918.5	1033.7
47.5°	732.7	771.1	841.7	956.9
50°	671.2	703.5	764.9	872.5
52.5°	611.3	639.0	695.8	781.8
55°	557.6	583.7	625.2	709.6
57.5°	502.3	522.2	562.2	629.8
60°	448.5	467.0	499.2	554.5
62.5°	394.8	410.1	440.8	485.4
65°	347.1	359.4	382.5	420.9
67.5°	301.1	308.7	327.2	357.9
70°	256.5	262.7	278.0	302.6
72.5°	208.9	215.0	231.9	248.8
75°	169.0	170.5	182.8	196.6
77.5°	132.1	130.6	139.8	150.5
80°	90.6	95.2	102.9	107.5
82.5°	61.4	63.0	66.0	69.1
85°	33.8	35.3	35.3	39.9
87.5°	13.8	15.4	15.4	16.9
90°	7.6	6.1	3.1	0.8
92.5°	26.0	22.1	16.0	11.5
95°	44.3	37.4	29.8	26.7
97.5°	62.6	52.7	44.3	39.7
100°	80.2	67.9	61.1	58.8
102.5°	97.0	84.7	77.9	76.3
105°	113.0	101.5	96.2	93.1
107.5°	129.8	119.1	113.7	111.5
110°	147.3	137.4	132.8	129.8



TEST NUMBER: P997987

CATALOG NUMBER: SA2XXDIP-B1005D725UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	164.1	155.0	149.6	146.6
115°	181.7	172.5	167.9	164.1
117.5°	198.5	190.1	185.5	182.4
120°	213.7	206.9	202.3	199.2
122.5°	229.8	222.1	217.6	215.3
125°	245.0	235.9	231.3	229.0
127.5°	259.6	249.6	243.5	240.5
130°	271.8	261.1	253.4	250.4
132.5°	283.2	271.8	263.4	259.6
135°	292.4	280.9	271.8	268.7
137.5°	302.3	290.1	280.9	277.1
140°	311.5	299.2	290.1	287.0
142.5°	319.9	307.6	299.2	297.0
145°	329.0	317.6	309.9	306.9
147.5°	338.2	327.5	319.9	317.6
150°	346.6	336.7	330.5	328.3
152.5°	354.2	345.8	339.7	338.9
155°	362.6	354.2	349.6	348.9
157.5°	369.5	361.8	358.0	357.3
160°	375.6	369.5	366.4	365.7
162.5°	380.9	376.3	373.3	374.1
165°	385.5	380.9	379.4	380.2
167.5°	389.3	386.3	384.7	385.5
170°	392.4	390.1	389.3	390.9
172.5°	394.7	392.4	393.1	393.9
175°	396.2	394.7	395.4	396.2
177.5°	397.0	395.4	396.2	397.7
180°	397.0	397.0	397.0	397.0

TEST NUMBER: P997987

CATALOG NUMBER: SA2XXDIP-B1005D725UB30-4F0-XX-W2A-A4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.85	19.78	19.71	20.66	21.76	16.35	17.28	17.21	18.15	19.25
	3H	19.67	20.50	20.54	21.39	22.52	17.70	18.53	18.57	19.42	20.54
	4H	19.84	20.63	20.73	21.52	22.66	18.16	18.95	19.05	19.84	20.98
	6H	19.89	20.62	20.79	21.51	22.66	18.47	19.20	19.37	20.10	21.25
	8H	19.87	20.56	20.78	21.48	22.63	18.56	19.25	19.47	20.16	21.31
	12H	19.84	20.49	20.75	21.40	22.58	18.60	19.26	19.52	20.17	21.34
4H	2H	18.90	19.69	19.80	20.58	21.72	16.80	17.59	17.69	18.48	19.62
	3H	19.89	20.54	20.79	21.47	22.62	18.27	18.92	19.17	19.85	21.00
	4H	20.17	20.77	21.08	21.68	22.86	18.81	19.40	19.72	20.32	21.50
	6H	20.30	20.82	21.23	21.76	22.94	19.19	19.70	20.12	20.64	21.82
	8H	20.30	20.78	21.23	21.72	22.91	19.30	19.78	20.23	20.72	21.91
	12H	20.27	20.70	21.22	21.66	22.85	19.36	19.79	20.31	20.75	21.94
8H	4H	20.18	20.66	21.12	21.60	22.79	18.95	19.43	19.88	20.37	21.56
	6H	20.37	20.76	21.32	21.74	22.93	19.39	19.79	20.35	20.76	21.96
	8H	20.40	20.74	21.36	21.71	22.92	19.54	19.89	20.51	20.86	22.07
	12H	20.38	20.69	21.35	21.65	22.91	19.64	19.94	20.61	20.91	22.16
12H	4H	20.14	20.57	21.09	21.53	22.73	18.93	19.36	19.88	20.32	21.51
	6H	20.34	20.69	21.31	21.66	22.87	19.39	19.74	20.36	20.71	21.92
	8H	20.38	20.69	21.35	21.65	22.91	19.55	19.86	20.52	20.82	22.08