

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997996

Luminaire Tested: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P997996
REPORT IS A COMBINATION OF REPORTS P983733 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7207.0 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997996

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P997996

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	101	97	93	90	94	91	88	85	80	77	75	69	68	66	60	59	57
2	92	85	79	74	86	80	75	70	70	67	63	62	59	56	53	51	49
3	85	75	68	63	79	71	65	60	63	58	54	55	51	48	48	45	43
4	78	67	59	54	73	63	56	51	56	51	46	49	45	42	43	40	37
5	72	60	52	46	67	57	50	44	51	45	40	45	40	37	39	36	33
6	66	54	46	41	62	51	44	39	46	40	36	41	36	32	36	32	29
7	62	49	42	36	58	47	40	35	42	36	32	37	33	29	33	29	26
8	57	45	37	32	54	43	36	31	38	33	28	34	30	26	30	27	24
9	53	41	34	29	50	39	32	28	35	30	26	32	27	24	28	24	22
10	50	38	31	26	47	36	30	25	33	27	23	29	25	22	26	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	31769	31769	31769	31769
5°	31845	33874	31967	26949
10°	31476	36978	31673	22219
15°	30711	39004	31139	18715
20°	30233	36622	30233	16267
25°	29270	31461	29403	14546
30°	27685	24732	28213	13176
35°	26279	17101	26719	12055
40°	24665	12912	24947	11162
45°	22674	10611	23046	10198
50°	20953	9313	20991	9335
55°	18991	7935	19113	8399
60°	16899	6629	17133	7330
65°	15027	5391	15300	6259
70°	13161	4230	13494	5049
75°	11048	3070	11479	3662
80°	8622	1947	9237	2174
85°	5664	981	6102	727

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 32840 cd/sqm

TEST NUMBER: P997996

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.2	2.7
10°-20°	556.4	7.7
20°-30°	807.5	11.2
30°-40°	851.2	11.8
40°-50°	753.3	10.5
50°-60°	601.5	8.3
60°-70°	408.5	5.7
70°-80°	209.0	2.9
80°-90°	52.0	0.7
90°-100°	155.4	2.2
100°-110°	547.3	7.6
110°-120°	574.8	8.0
120°-130°	472.9	6.6
130°-140°	379.9	5.3
140°-150°	287.0	4.0
150°-160°	201.7	2.8
160°-170°	118.8	1.6
170°-180°	38.6	0.5
0°-30°	1555.0	21.6
0°-40°	2406.3	33.4
0°-60°	3761.0	52.2
0°-90°	4430.6	61.5
90°-120°	1277.5	17.7
90°-150°	2417.3	33.5
90°-180°	2776.0	38.5
0°-180°	7207.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2007	2007	2007	2007	2007	
5°	2008	2242	2016	1783	2008	190
15°	1887	2755	1913	1322	1887	533
25°	1695	2295	1703	1061	1695	775
35°	1384	1250	1407	881	1384	866
45°	1038	753	1055	724	1038	805
55°	713	529	717	560	713	636
65°	423	326	430	378	423	420
75°	198	160	205	191	198	212
85°	40	42	43	31	40	47
90°	1	25	1	25	1	4
95°	27	87	27	87	27	28
105°	94	864	94	864	94	99
115°	165	1137	165	1137	165	163
125°	230	922	230	922	230	204
135°	270	764	270	764	270	208
145°	308	610	308	610	308	193
155°	350	513	350	513	350	161
165°	382	450	382	450	382	108
175°	398	406	398	406	398	38
180°	399	399	399	399	399	

TEST NUMBER: P997996

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	2017.8	2022.4	2030.1	2031.7	2047.1	2059.4	2073.3	2073.3	2077.9	2076.4	2064.1
5°	2008.5	2022.4	2042.5	2059.4	2087.2	2099.5	2118.0	2131.9	2144.3	2153.5	2152.0
7.5°	1993.1	2017.8	2047.1	2079.5	2116.5	2138.1	2164.3	2189.0	2206.0	2221.4	2232.2
10°	1966.9	2008.5	2048.6	2091.8	2139.6	2169.0	2199.8	2232.2	2258.4	2287.7	2315.5
12.5°	1931.4	1991.5	2040.9	2098.0	2156.6	2189.0	2238.4	2263.1	2314.0	2388.0	2408.1
15°	1886.6	1968.4	2014.7	2087.2	2164.3	2190.6	2258.4	2298.5	2403.4	2449.7	2505.2
17.5°	1845.0	1936.0	1997.7	2081.0	2156.6	2207.5	2273.9	2355.6	2443.5	2509.9	2571.6
20°	1811.1	1899.0	1973.0	2065.6	2161.2	2226.0	2295.4	2394.2	2489.8	2557.7	2605.5
22.5°	1733.9	1846.5	1932.9	2036.3	2152.0	2241.5	2307.8	2415.8	2519.1	2560.8	2602.4
25°	1695.4	1792.5	1892.8	2010.1	2145.8	2252.3	2309.3	2429.7	2520.7	2536.1	2545.4
27.5°	1624.4	1733.9	1851.2	1985.4	2144.3	2233.7	2306.2	2415.8	2488.3	2477.5	2449.7
30°	1536.5	1670.7	1800.3	1945.3	2122.7	2219.9	2287.7	2388.0	2425.0	2369.5	2320.1
32.5°	1471.7	1598.2	1741.6	1909.8	2098.0	2190.6	2256.9	2335.6	2343.3	2243.0	2159.7
35°	1383.7	1524.1	1686.1	1863.5	2056.3	2139.6	2201.3	2249.2	2212.1	2071.8	1973.0
37.5°	1305.1	1443.9	1616.7	1797.2	1999.3	2081.0	2130.4	2138.1	2047.1	1923.7	1778.7
40°	1218.7	1362.2	1542.6	1732.4	1936.0	2007.0	2037.8	2014.7	1883.6	1740.1	1572.0
42.5°	1132.3	1274.2	1468.6	1663.0	1855.8	1916.0	1928.3	1865.1	1704.6	1536.5	1342.1
45°	1038.2	1186.3	1380.7	1576.6	1763.2	1797.2	1798.7	1707.7	1518.0	1342.1	1161.6
47.5°	961.1	1098.4	1291.2	1487.1	1644.5	1667.6	1658.3	1553.4	1346.7	1149.3	991.9
50°	876.2	1007.3	1198.6	1391.5	1525.7	1531.8	1508.7	1359.1	1157.0	976.5	851.5
52.5°	785.2	917.9	1093.7	1278.8	1399.2	1389.9	1345.2	1184.7	995.0	845.4	749.7
55°	712.7	829.9	995.0	1175.5	1260.3	1234.1	1184.7	1021.2	871.6	745.1	661.8
57.5°	632.5	735.8	897.8	1055.2	1104.5	1079.8	1030.5	877.8	738.9	643.3	587.7
60°	556.9	651.0	792.9	924.0	962.6	936.4	879.3	742.0	641.7	561.5	519.9
62.5°	487.5	569.2	688.0	808.3	823.8	797.5	748.2	637.1	550.7	487.5	456.6
65°	422.7	499.8	595.5	686.5	700.4	672.6	621.7	541.5	469.0	428.9	399.5
67.5°	359.4	421.1	506.0	572.3	580.0	553.8	512.2	447.4	402.6	359.4	337.8
70°	303.9	350.2	416.5	470.5	473.6	448.9	427.3	368.7	334.8	303.9	286.9
72.5°	249.9	282.3	333.2	373.3	374.9	359.4	339.4	302.4	273.0	251.5	234.5
75°	197.5	225.2	256.1	291.6	290.0	277.7	262.2	239.1	214.4	200.5	192.8
77.5°	151.2	168.1	192.8	216.0	216.0	209.8	200.5	183.6	168.1	154.3	146.6
80°	108.0	118.8	138.8	146.6	149.6	148.1	140.4	128.0	121.9	111.1	108.0
82.5°	69.4	77.1	86.4	94.1	98.7	95.6	94.1	87.9	78.7	75.6	72.5
85°	40.1	43.2	47.8	52.4	54.0	52.4	55.5	50.9	46.3	46.3	44.7
87.5°	17.0	18.5	21.6	21.6	23.1	23.1	21.6	23.1	23.1	21.6	20.1
90°	0.8	3.1	6.1	7.7	9.2	10.4	11.5	15.3	20.7	25.3	26.1
92.5°	11.5	16.1	22.2	26.1	32.2	36.4	40.6	61.3	90.5	116.5	118.1
95°	26.8	29.9	37.6	44.5	56.7	65.9	75.1	110.4	177.1	266.0	300.5
97.5°	39.9	44.5	52.9	62.9	76.7	87.1	97.4	142.6	235.4	378.7	489.9
100°	59.0	61.3	68.2	80.5	95.8	106.6	117.3	157.9	251.5	417.1	605.7
102.5°	76.7	78.2	85.1	97.4	113.5	124.2	134.9	171.7	252.2	402.5	609.5
105°	93.5	96.6	102.0	113.5	130.3	141.0	151.8	187.8	256.1	382.6	568.1
107.5°	111.9	114.2	119.6	130.3	147.2	158.0	168.7	203.9	264.5	371.8	529.8
110°	130.3	133.4	138.0	148.0	164.1	175.2	186.3	220.0	275.2	368.8	503.7

TEST NUMBER: P997996

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	147.2	150.3	155.6	164.8	180.2	191.7	203.2	235.4	286.7	369.5	486.9
115°	164.8	168.7	173.3	182.5	197.8	208.2	218.5	251.5	298.2	372.6	475.4
117.5°	183.2	186.3	190.9	199.3	213.9	224.6	235.4	266.0	310.5	377.2	469.2
120°	200.1	203.2	207.8	214.7	230.0	240.8	251.5	281.4	322.8	381.8	463.9
122.5°	216.2	218.5	223.1	230.8	246.1	257.2	268.3	295.9	333.5	387.2	460.8
125°	230.0	232.3	236.9	246.1	261.4	272.2	282.9	310.5	345.0	392.5	457.0
127.5°	241.5	244.6	250.7	260.7	275.2	286.4	297.5	324.3	355.7	397.9	454.7
130°	251.5	254.5	262.2	272.9	288.3	299.0	309.7	336.6	365.7	404.0	453.1
132.5°	260.7	264.5	272.9	284.4	300.5	311.2	322.0	347.3	375.7	410.2	452.4
135°	269.9	272.9	282.1	293.6	311.3	322.0	332.7	357.3	384.1	414.8	451.6
137.5°	278.3	282.1	291.3	303.6	321.2	331.2	341.2	365.7	391.0	419.4	451.6
140°	288.3	291.3	300.5	312.8	329.7	339.6	349.6	372.6	396.4	422.5	450.8
142.5°	298.2	300.5	309.0	321.2	337.3	346.5	355.7	378.0	401.0	424.8	450.8
145°	308.2	311.3	318.9	330.4	345.8	354.2	362.6	383.3	404.8	426.3	449.3
147.5°	318.9	321.2	328.9	339.6	352.7	360.4	368.0	387.9	407.1	427.1	447.0
150°	329.7	332.0	338.1	348.1	359.6	366.5	373.4	391.0	408.6	426.3	444.7
152.5°	340.4	341.2	347.3	355.7	366.5	372.6	378.7	394.1	409.4	424.8	440.9
155°	350.4	351.1	355.7	364.2	372.6	378.4	384.1	397.1	410.2	423.2	436.3
157.5°	358.8	359.6	363.4	371.1	378.0	383.0	387.9	399.4	410.2	420.2	431.7
160°	367.2	368.0	371.1	377.2	383.3	387.6	391.8	401.0	410.2	417.9	427.1
162.5°	375.7	374.9	378.0	382.6	387.9	391.0	394.1	401.7	409.4	415.6	423.2
165°	381.8	381.0	382.6	387.2	391.0	393.3	395.6	402.5	407.9	412.5	417.9
167.5°	387.2	386.4	387.9	391.0	394.1	395.6	397.1	402.5	407.1	409.4	413.3
170°	392.5	391.0	391.8	394.1	395.6	396.8	397.9	401.7	405.6	407.1	409.4
172.5°	395.6	394.8	394.1	396.4	397.1	397.9	398.7	401.0	403.3	404.0	404.8
175°	397.9	397.1	396.4	397.9	397.9	398.3	398.7	400.2	401.7	401.0	401.7
177.5°	399.4	397.9	397.1	398.7	398.7	398.7	398.7	399.4	401.0	399.4	398.7
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P997996

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	2085.7	2087.2	2090.3	2105.7	2113.4	2115.0	2108.8	2122.7	2127.3	2122.7	2119.6
5°	2184.4	2193.6	2212.1	2232.2	2230.7	2232.2	2241.5	2250.7	2253.8	2241.5	2246.1
7.5°	2270.8	2289.3	2309.3	2340.2	2340.2	2355.6	2361.8	2369.5	2388.0	2378.8	2375.7
10°	2369.5	2394.2	2431.2	2480.6	2482.1	2497.5	2513.0	2537.6	2545.4	2539.2	2542.3
12.5°	2492.9	2540.7	2543.8	2597.8	2622.5	2625.6	2650.3	2645.6	2661.1	2661.1	2687.3
15°	2546.9	2620.9	2662.6	2715.0	2730.5	2712.0	2732.0	2753.6	2755.2	2755.2	2753.6
17.5°	2644.1	2673.4	2715.0	2742.8	2749.0	2749.0	2750.5	2759.8	2753.6	2741.3	2750.5
20°	2664.1	2676.5	2691.9	2688.8	2691.9	2676.5	2661.1	2645.6	2647.2	2639.5	2662.6
22.5°	2627.1	2624.0	2588.6	2565.4	2565.4	2534.6	2505.2	2491.4	2477.5	2482.1	2489.8
25°	2534.6	2486.7	2443.5	2409.6	2401.9	2352.5	2312.4	2300.1	2276.9	2295.4	2298.5
27.5°	2386.5	2332.5	2263.1	2233.7	2193.6	2173.6	2145.8	2108.8	2061.0	2088.7	2084.1
30°	2227.6	2147.4	2090.3	2019.3	1956.1	1951.4	1899.0	1837.3	1812.6	1812.6	1826.5
32.5°	2050.2	1943.7	1860.4	1760.2	1698.4	1672.2	1609.0	1547.3	1561.2	1514.9	1531.8
35°	1843.5	1703.1	1598.2	1501.0	1454.7	1423.9	1342.1	1308.2	1271.1	1249.5	1289.6
37.5°	1646.0	1484.0	1349.8	1243.4	1226.4	1170.9	1115.3	1093.7	1072.1	1081.4	1079.8
40°	1405.3	1261.9	1141.6	1058.3	1028.9	1002.7	965.7	939.5	925.6	933.3	934.8
42.5°	1187.8	1067.5	978.0	919.4	894.7	876.2	857.7	836.1	831.5	831.5	837.7
45°	1019.7	921.0	860.8	813.0	799.1	785.2	771.3	762.1	759.0	752.8	757.4
47.5°	885.5	806.8	769.8	734.3	718.9	715.8	703.4	698.8	692.6	691.1	692.6
50°	772.9	723.5	689.6	669.5	658.7	654.1	647.9	638.7	635.6	643.3	640.2
52.5°	694.2	647.9	629.4	609.3	603.2	597.0	587.7	589.3	587.7	584.7	584.7
55°	615.5	586.2	567.7	552.3	550.7	544.6	536.8	533.8	532.2	529.1	533.8
57.5°	552.3	529.1	512.2	498.3	492.1	492.1	484.4	478.2	478.2	476.7	478.2
60°	489.0	465.9	455.1	441.2	436.6	435.0	430.4	427.3	422.7	422.7	422.7
62.5°	430.4	411.9	399.5	387.2	388.7	381.0	374.9	371.8	371.8	373.3	373.3
65°	374.9	362.5	347.1	336.3	333.2	331.7	328.6	327.0	322.4	325.5	325.5
67.5°	324.0	307.0	297.7	293.1	288.5	286.9	283.8	280.8	279.2	277.7	280.8
70°	273.0	259.2	251.5	248.4	243.7	242.2	240.7	236.0	237.6	239.1	240.7
72.5°	226.8	214.4	212.9	203.6	203.6	203.6	197.5	200.5	199.0	195.9	199.0
75°	178.9	172.8	169.7	165.1	166.6	165.1	163.5	158.9	158.9	160.4	162.0
77.5°	141.9	135.8	134.2	129.6	126.5	129.6	126.5	125.0	125.0	126.5	126.5
80°	104.9	101.8	97.2	97.2	97.2	95.6	95.6	95.6	94.1	92.6	94.1
82.5°	69.4	69.4	67.9	66.3	67.9	64.8	66.3	66.3	66.3	66.3	66.3
85°	44.7	43.2	43.2	41.7	41.7	41.7	43.2	40.1	40.1	41.7	41.7
87.5°	20.1	20.1	20.1	21.6	20.1	20.1	20.1	21.6	20.1	20.1	20.1
90°	25.3	24.5	23.0	24.5	24.9	25.3	25.3	25.3	25.3	25.3	25.3
92.5°	98.9	77.4	65.9	57.5	54.4	51.4	50.6	47.5	48.3	46.8	48.3
95°	263.0	200.9	154.1	121.9	113.4	105.0	95.1	88.9	86.6	87.4	86.6
97.5°	493.8	410.9	328.1	250.7	227.7	204.7	174.8	159.5	151.0	146.4	151.0
100°	716.1	700.0	604.9	499.9	453.5	407.1	343.5	310.5	288.3	274.5	288.3
102.5°	798.9	889.4	886.3	816.5	766.7	716.9	646.3	584.2	555.1	535.2	555.1
105°	772.1	931.5	1018.2	1028.1	1015.4	1002.8	955.3	907.8	874.8	864.1	874.8
107.5°	715.3	886.3	1015.1	1090.2	1105.6	1120.9	1120.1	1113.2	1103.3	1085.6	1103.3
110°	662.4	824.2	961.4	1059.6	1091.0	1122.4	1155.4	1170.0	1176.9	1176.1	1176.9

TEST NUMBER: P997996

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	625.6	767.5	897.8	1004.4	1041.6	1078.7	1127.8	1154.6	1169.2	1174.6	1169.2
115°	596.5	723.0	841.1	941.5	981.0	1020.5	1074.9	1110.2	1130.1	1137.0	1130.1
117.5°	576.6	686.2	792.0	885.5	923.1	960.7	1016.6	1054.2	1074.9	1080.3	1074.9
120°	561.2	660.1	755.2	836.5	871.4	906.2	959.9	995.9	1018.2	1025.8	1018.2
122.5°	548.2	639.4	724.5	800.4	831.1	861.8	908.5	943.8	963.0	969.1	963.0
125°	535.9	619.5	698.5	765.9	794.6	823.4	867.9	897.0	916.2	922.3	916.2
127.5°	524.4	599.6	672.4	736.8	763.6	790.5	829.6	857.2	874.0	878.6	874.0
130°	512.9	580.4	646.3	706.9	732.2	757.5	795.1	821.1	836.5	842.6	836.5
132.5°	503.7	562.0	621.8	676.2	699.6	723.0	759.8	785.9	799.7	805.0	799.7
135°	495.3	545.1	595.7	646.3	667.8	689.3	722.2	747.5	761.3	764.4	761.3
137.5°	489.2	531.3	575.0	616.4	635.6	654.8	686.2	708.4	720.7	725.3	720.7
140°	483.8	518.3	555.1	590.4	607.2	624.1	648.6	668.6	680.1	684.7	680.1
142.5°	478.4	507.6	537.5	566.6	580.0	593.4	616.4	634.1	644.0	644.0	644.0
145°	473.8	497.6	522.9	546.7	557.8	568.9	587.3	600.3	608.0	610.3	608.0
147.5°	469.2	489.9	510.6	529.8	538.2	546.7	562.8	573.5	578.9	580.4	578.9
150°	463.1	481.5	498.4	514.5	521.4	528.3	539.8	549.0	553.6	554.3	553.6
152.5°	457.7	473.1	488.4	501.4	507.2	512.9	521.4	529.0	532.1	532.1	532.1
155°	450.8	465.4	477.7	489.2	493.4	497.6	506.0	511.4	514.5	512.9	514.5
157.5°	444.7	456.2	466.9	476.9	480.4	483.8	489.9	494.5	496.1	496.1	496.1
160°	437.8	447.8	456.2	464.6	467.3	470.0	475.4	479.2	480.0	480.0	480.0
162.5°	431.7	439.3	446.2	453.1	455.0	457.0	462.3	464.6	465.4	464.6	465.4
165°	424.8	430.9	436.3	441.6	443.2	444.7	447.8	450.8	450.8	450.1	450.8
167.5°	417.9	422.5	427.1	430.9	432.4	434.0	435.5	437.0	437.0	436.3	437.0
170°	412.5	416.3	418.6	421.7	422.4	423.2	424.0	426.3	425.5	424.0	425.5
172.5°	407.1	409.4	410.9	413.3	413.6	414.0	414.8	415.6	414.8	414.0	414.8
175°	402.5	404.8	405.6	406.3	406.7	407.1	407.1	407.9	407.1	405.6	407.1
177.5°	399.4	401.0	401.0	401.7	401.7	401.7	401.7	401.7	401.0	399.4	401.0
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P997996

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	2127.3	2116.5	2107.2	2108.8	2116.5	2110.3	2094.9	2074.9	2067.1	2057.9	2067.1
5°	2255.3	2246.1	2227.6	2229.1	2224.5	2218.3	2193.6	2162.8	2162.8	2138.1	2135.0
7.5°	2381.8	2368.0	2355.6	2352.5	2335.6	2323.2	2301.6	2258.4	2241.5	2212.1	2195.2
10°	2523.8	2513.0	2499.1	2482.1	2472.9	2451.3	2415.8	2352.5	2321.7	2281.6	2252.3
12.5°	2667.2	2665.7	2634.8	2600.9	2599.3	2565.4	2540.7	2455.9	2414.2	2360.2	2290.8
15°	2758.2	2750.5	2733.6	2716.6	2721.2	2684.2	2628.7	2528.4	2500.6	2435.8	2361.8
17.5°	2756.7	2756.7	2752.1	2749.0	2744.4	2733.6	2702.7	2636.4	2591.6	2509.9	2440.5
20°	2668.8	2688.8	2693.5	2691.9	2707.3	2715.0	2713.5	2671.9	2636.4	2563.9	2492.9
22.5°	2492.9	2539.2	2559.2	2571.6	2604.0	2620.9	2661.1	2645.6	2636.4	2582.4	2522.2
25°	2329.4	2344.8	2405.0	2408.1	2452.8	2494.5	2534.6	2560.8	2594.7	2574.7	2523.8
27.5°	2118.0	2153.5	2196.7	2229.1	2238.4	2323.2	2389.6	2438.9	2516.0	2522.2	2505.2
30°	1878.9	1895.9	1966.9	2010.1	2059.4	2121.1	2216.8	2301.6	2371.0	2434.3	2455.9
32.5°	1587.4	1656.8	1698.4	1750.9	1794.1	1903.6	2020.9	2130.4	2210.6	2317.0	2363.3
35°	1320.5	1374.5	1445.5	1467.1	1545.7	1638.3	1791.0	1931.4	2053.3	2161.2	2255.3
37.5°	1099.9	1143.1	1218.7	1252.6	1298.9	1417.7	1545.7	1720.0	1866.6	1999.3	2116.5
40°	948.7	981.1	1038.2	1049.0	1087.6	1195.5	1298.9	1462.4	1656.8	1835.7	1963.8
42.5°	845.4	860.8	899.4	913.2	937.9	1010.4	1103.0	1257.3	1437.7	1622.9	1803.3
45°	771.3	782.1	805.3	817.6	848.5	880.8	956.4	1079.8	1221.8	1408.4	1602.8
47.5°	705.0	718.9	728.1	735.8	752.8	788.3	837.7	928.7	1064.4	1235.7	1423.9
50°	649.5	654.1	671.0	672.6	683.4	706.5	752.8	808.3	916.3	1055.2	1237.2
52.5°	593.9	598.5	609.3	620.1	624.8	643.3	674.1	720.4	800.6	910.2	1072.1
55°	538.4	544.6	555.4	563.1	567.7	583.1	601.6	646.4	709.6	786.7	919.4
57.5°	482.8	496.7	499.8	504.4	512.2	529.1	546.1	572.3	621.7	692.6	789.8
60°	430.4	435.0	445.8	450.5	458.2	467.4	489.0	509.1	544.6	600.1	688.0
62.5°	376.4	387.2	391.8	396.5	402.6	413.4	427.3	448.9	479.8	524.5	593.9
65°	330.1	331.7	340.9	347.1	353.3	361.0	374.9	394.9	413.4	455.1	506.0
67.5°	285.4	288.5	291.6	297.7	305.4	313.2	325.5	336.3	359.4	387.2	427.3
70°	242.2	242.2	249.9	254.5	253.0	262.2	271.5	283.8	300.8	327.0	359.4
72.5°	203.6	202.1	208.3	209.8	212.9	219.1	225.2	237.6	246.8	266.9	291.6
75°	162.0	165.1	168.1	168.1	172.8	177.4	183.6	189.7	200.5	212.9	231.4
77.5°	128.0	128.0	131.1	132.7	137.3	135.8	141.9	148.1	155.8	166.6	180.5
80°	94.1	97.2	97.2	97.2	98.7	100.3	106.4	111.1	115.7	123.4	129.6
82.5°	66.3	66.3	69.4	69.4	69.4	72.5	72.5	74.0	77.1	81.8	86.4
85°	41.7	41.7	41.7	43.2	41.7	43.2	46.3	44.7	46.3	49.4	49.4
87.5°	20.1	20.1	20.1	20.1	20.1	21.6	20.1	21.6	23.1	23.1	23.1
90°	25.3	25.3	25.3	24.9	24.5	23.0	24.5	25.3	26.1	25.3	20.7
92.5°	47.5	50.6	51.4	54.4	57.5	65.9	77.4	98.9	118.1	116.5	90.5
95°	88.9	95.1	105.0	113.4	121.9	154.1	200.9	263.0	300.5	266.0	177.1
97.5°	159.5	174.8	204.7	227.7	250.7	328.1	410.9	493.8	489.9	378.7	235.4
100°	310.5	343.5	407.1	453.5	499.9	604.9	700.0	716.1	605.7	417.1	251.5
102.5°	584.2	646.3	716.9	766.7	816.5	886.3	889.4	798.9	609.5	402.5	252.2
105°	907.8	955.3	1002.8	1015.4	1028.1	1018.2	931.5	772.1	568.1	382.6	256.1
107.5°	1113.2	1120.1	1120.9	1105.6	1090.2	1015.1	886.3	715.3	529.8	371.8	264.5
110°	1170.0	1155.4	1122.4	1091.0	1059.6	961.4	824.2	662.4	503.7	368.8	275.2

TEST NUMBER: P997996

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1154.6	1127.8	1078.7	1041.6	1004.4	897.8	767.5	625.6	486.9	369.5	286.7
115°	1110.2	1074.9	1020.5	981.0	941.5	841.1	723.0	596.5	475.4	372.6	298.2
117.5°	1054.2	1016.6	960.7	923.1	885.5	792.0	686.2	576.6	469.2	377.2	310.5
120°	995.9	959.9	906.2	871.4	836.5	755.2	660.1	561.2	463.9	381.8	322.8
122.5°	943.8	908.5	861.8	831.1	800.4	724.5	639.4	548.2	460.8	387.2	333.5
125°	897.0	867.9	823.4	794.6	765.9	698.5	619.5	535.9	457.0	392.5	345.0
127.5°	857.2	829.6	790.5	763.6	736.8	672.4	599.6	524.4	454.7	397.9	355.7
130°	821.1	795.1	757.5	732.2	706.9	646.3	580.4	512.9	453.1	404.0	365.7
132.5°	785.9	759.8	723.0	699.6	676.2	621.8	562.0	503.7	452.4	410.2	375.7
135°	747.5	722.2	689.3	667.8	646.3	595.7	545.1	495.3	451.6	414.8	384.1
137.5°	708.4	686.2	654.8	635.6	616.4	575.0	531.3	489.2	451.6	419.4	391.0
140°	668.6	648.6	624.1	607.2	590.4	555.1	518.3	483.8	450.8	422.5	396.4
142.5°	634.1	616.4	593.4	580.0	566.6	537.5	507.6	478.4	450.8	424.8	401.0
145°	600.3	587.3	568.9	557.8	546.7	522.9	497.6	473.8	449.3	426.3	404.8
147.5°	573.5	562.8	546.7	538.2	529.8	510.6	489.9	469.2	447.0	427.1	407.1
150°	549.0	539.8	528.3	521.4	514.5	498.4	481.5	463.1	444.7	426.3	408.6
152.5°	529.0	521.4	512.9	507.2	501.4	488.4	473.1	457.7	440.9	424.8	409.4
155°	511.4	506.0	497.6	493.4	489.2	477.7	465.4	450.8	436.3	423.2	410.2
157.5°	494.5	489.9	483.8	480.4	476.9	466.9	456.2	444.7	431.7	420.2	410.2
160°	479.2	475.4	470.0	467.3	464.6	456.2	447.8	437.8	427.1	417.9	410.2
162.5°	464.6	462.3	457.0	455.0	453.1	446.2	439.3	431.7	423.2	415.6	409.4
165°	450.8	447.8	444.7	443.2	441.6	436.3	430.9	424.8	417.9	412.5	407.9
167.5°	437.0	435.5	434.0	432.4	430.9	427.1	422.5	417.9	413.3	409.4	407.1
170°	426.3	424.0	423.2	422.4	421.7	418.6	416.3	412.5	409.4	407.1	405.6
172.5°	415.6	414.8	414.0	413.6	413.3	410.9	409.4	407.1	404.8	404.0	403.3
175°	407.9	407.1	407.1	406.7	406.3	405.6	404.8	402.5	401.7	401.0	401.7
177.5°	401.7	401.7	401.7	401.7	401.7	401.0	401.0	399.4	398.7	399.4	401.0
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P997996

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	2059.4	2051.7	2047.1	2050.2	2040.9	2017.8	2017.8	2025.5	2016.2	2007.0	1993.1
5°	2116.5	2101.1	2091.8	2090.3	2068.7	2031.7	2023.9	2016.2	1996.2	1974.6	1951.4
7.5°	2172.0	2144.3	2128.8	2118.0	2087.2	2039.4	2019.3	2002.3	1970.0	1937.6	1908.2
10°	2218.3	2178.2	2159.7	2142.7	2102.6	2042.5	2010.1	1979.2	1937.6	1895.9	1858.9
12.5°	2255.3	2209.1	2185.9	2161.2	2111.9	2033.2	1993.1	1943.7	1902.1	1846.5	1809.5
15°	2317.0	2221.4	2199.8	2176.7	2125.8	2017.8	1968.4	1912.9	1855.8	1781.8	1741.6
17.5°	2366.4	2238.4	2236.8	2187.5	2121.1	2011.6	1936.0	1863.5	1801.8	1727.8	1664.5
20°	2395.7	2264.6	2239.9	2189.0	2105.7	1970.0	1891.3	1811.1	1744.7	1655.3	1592.0
22.5°	2420.4	2301.6	2236.8	2175.1	2073.3	1956.1	1840.4	1764.8	1673.8	1576.6	1516.4
25°	2429.7	2309.3	2241.5	2170.5	2050.2	1916.0	1784.8	1703.1	1601.3	1513.3	1431.6
27.5°	2431.2	2307.8	2224.5	2150.4	2017.8	1863.5	1729.3	1642.9	1530.3	1428.5	1346.7
30°	2415.8	2290.8	2215.2	2135.0	1986.9	1815.7	1661.4	1565.8	1445.5	1343.6	1258.8
32.5°	2369.5	2256.9	2195.2	2107.2	1946.8	1749.4	1596.6	1490.2	1363.7	1263.4	1181.7
35°	2292.4	2215.2	2147.4	2065.6	1894.4	1687.6	1531.8	1406.9	1278.8	1183.2	1106.1
37.5°	2196.7	2155.1	2091.8	2011.6	1834.2	1632.1	1459.3	1320.5	1192.5	1099.9	1024.3
40°	2067.1	2077.9	2016.2	1943.7	1763.2	1556.5	1365.2	1232.6	1112.2	1025.9	951.8
42.5°	1926.8	1971.5	1936.0	1866.6	1684.6	1473.2	1295.8	1149.3	1032.0	942.6	880.8
45°	1775.6	1852.7	1831.1	1780.2	1602.8	1385.3	1197.1	1055.2	951.8	865.4	811.4
47.5°	1610.5	1720.0	1720.0	1683.0	1511.8	1297.4	1112.2	967.2	865.4	803.7	751.3
50°	1442.4	1565.8	1585.8	1561.2	1410.0	1197.1	1008.9	877.8	789.8	729.7	691.1
52.5°	1266.5	1410.0	1447.0	1434.7	1302.0	1101.4	924.0	796.0	715.8	663.3	629.4
55°	1098.4	1265.0	1305.1	1309.7	1186.3	996.5	829.9	717.3	640.2	604.7	575.4
57.5°	939.5	1099.9	1144.6	1152.4	1069.1	900.9	742.0	643.3	573.9	544.6	521.4
60°	803.7	937.9	996.5	1013.5	941.0	789.8	660.3	564.6	512.2	484.4	462.8
62.5°	692.6	800.6	862.3	867.0	834.6	692.6	575.4	495.2	450.5	425.8	415.0
65°	584.7	681.8	718.9	737.4	711.2	600.1	496.7	430.4	394.9	373.3	362.5
67.5°	498.3	560.0	590.8	615.5	589.3	506.0	422.7	368.7	342.5	320.9	314.7
70°	408.8	459.7	482.8	507.5	484.4	421.1	361.0	311.6	288.5	271.5	263.8
72.5°	327.0	367.1	388.7	404.2	390.3	337.8	288.5	254.5	237.6	225.2	220.6
75°	259.2	286.9	299.3	310.1	303.9	263.8	232.9	205.2	189.7	178.9	175.9
77.5°	197.5	217.5	231.4	234.5	226.8	200.5	174.3	157.3	145.0	138.8	135.8
80°	140.4	152.7	160.4	165.1	157.3	146.6	128.0	115.7	104.9	97.2	95.6
82.5°	94.1	100.3	106.4	104.9	101.8	92.6	81.8	75.6	71.0	64.8	64.8
85°	54.0	55.5	58.6	60.2	58.6	52.4	46.3	43.2	40.1	35.5	35.5
87.5°	23.1	24.7	24.7	26.2	23.1	23.1	20.1	17.0	17.0	15.4	13.9
90°	15.3	11.5	10.4	9.2	7.7	6.1	3.1	0.8	3.1	6.1	7.7
92.5°	61.3	40.6	36.4	32.2	26.1	22.2	16.1	11.5	16.1	22.2	26.1
95°	110.4	75.1	65.9	56.7	44.5	37.6	29.9	26.8	29.9	37.6	44.5
97.5°	142.6	97.4	87.1	76.7	62.9	52.9	44.5	39.9	44.5	52.9	62.9
100°	157.9	117.3	106.6	95.8	80.5	68.2	61.3	59.0	61.3	68.2	80.5
102.5°	171.7	134.9	124.2	113.5	97.4	85.1	78.2	76.7	78.2	85.1	97.4
105°	187.8	151.8	141.0	130.3	113.5	102.0	96.6	93.5	96.6	102.0	113.5
107.5°	203.9	168.7	158.0	147.2	130.3	119.6	114.2	111.9	114.2	119.6	130.3
110°	220.0	186.3	175.2	164.1	148.0	138.0	133.4	130.3	133.4	138.0	148.0

TEST NUMBER: P997996

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	235.4	203.2	191.7	180.2	164.8	155.6	150.3	147.2	150.3	155.6	164.8
115°	251.5	218.5	208.2	197.8	182.5	173.3	168.7	164.8	168.7	173.3	182.5
117.5°	266.0	235.4	224.6	213.9	199.3	190.9	186.3	183.2	186.3	190.9	199.3
120°	281.4	251.5	240.8	230.0	214.7	207.8	203.2	200.1	203.2	207.8	214.7
122.5°	295.9	268.3	257.2	246.1	230.8	223.1	218.5	216.2	218.5	223.1	230.8
125°	310.5	282.9	272.2	261.4	246.1	236.9	232.3	230.0	232.3	236.9	246.1
127.5°	324.3	297.5	286.4	275.2	260.7	250.7	244.6	241.5	244.6	250.7	260.7
130°	336.6	309.7	299.0	288.3	272.9	262.2	254.5	251.5	254.5	262.2	272.9
132.5°	347.3	322.0	311.2	300.5	284.4	272.9	264.5	260.7	264.5	272.9	284.4
135°	357.3	332.7	322.0	311.3	293.6	282.1	272.9	269.9	272.9	282.1	293.6
137.5°	365.7	341.2	331.2	321.2	303.6	291.3	282.1	278.3	282.1	291.3	303.6
140°	372.6	349.6	339.6	329.7	312.8	300.5	291.3	288.3	291.3	300.5	312.8
142.5°	378.0	355.7	346.5	337.3	321.2	309.0	300.5	298.2	300.5	309.0	321.2
145°	383.3	362.6	354.2	345.8	330.4	318.9	311.3	308.2	311.3	318.9	330.4
147.5°	387.9	368.0	360.4	352.7	339.6	328.9	321.2	318.9	321.2	328.9	339.6
150°	391.0	373.4	366.5	359.6	348.1	338.1	332.0	329.7	332.0	338.1	348.1
152.5°	394.1	378.7	372.6	366.5	355.7	347.3	341.2	340.4	341.2	347.3	355.7
155°	397.1	384.1	378.4	372.6	364.2	355.7	351.1	350.4	351.1	355.7	364.2
157.5°	399.4	387.9	383.0	378.0	371.1	363.4	359.6	358.8	359.6	363.4	371.1
160°	401.0	391.8	387.6	383.3	377.2	371.1	368.0	367.2	368.0	371.1	377.2
162.5°	401.7	394.1	391.0	387.9	382.6	378.0	374.9	375.7	374.9	378.0	382.6
165°	402.5	395.6	393.3	391.0	387.2	382.6	381.0	381.8	381.0	382.6	387.2
167.5°	402.5	397.1	395.6	394.1	391.0	387.9	386.4	387.2	386.4	387.9	391.0
170°	401.7	397.9	396.8	395.6	394.1	391.8	391.0	392.5	391.0	391.8	394.1
172.5°	401.0	398.7	397.9	397.1	396.4	394.1	394.8	395.6	394.8	394.1	396.4
175°	400.2	398.7	398.3	397.9	397.9	396.4	397.1	397.9	397.1	396.4	397.9
177.5°	399.4	398.7	398.7	398.7	398.7	397.1	397.9	399.4	397.9	397.1	398.7
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P997996

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	1985.4	1993.1	1991.5	1976.1	1959.2	1945.3	1919.0	1922.1	1912.9	1914.4	1923.7
5°	1936.0	1936.0	1929.8	1908.2	1880.5	1865.1	1835.7	1828.0	1809.5	1808.0	1806.4
7.5°	1883.6	1875.9	1868.1	1837.3	1803.3	1778.7	1738.6	1729.3	1710.8	1698.4	1692.3
10°	1821.9	1811.1	1795.6	1760.2	1718.5	1687.6	1646.0	1633.7	1598.2	1582.7	1573.5
12.5°	1754.0	1747.8	1723.1	1693.8	1625.9	1592.0	1531.8	1544.2	1508.7	1477.9	1473.2
15°	1686.1	1663.0	1649.1	1601.3	1519.5	1504.1	1456.3	1431.6	1399.2	1374.5	1374.5
17.5°	1619.8	1584.3	1553.4	1502.5	1442.4	1399.2	1363.7	1351.4	1311.2	1286.6	1281.9
20°	1531.8	1491.7	1484.0	1411.5	1369.9	1322.0	1288.1	1257.3	1227.9	1217.1	1209.4
22.5°	1448.5	1402.3	1389.9	1328.2	1286.6	1238.7	1204.8	1183.2	1161.6	1153.9	1140.0
25°	1359.1	1331.3	1312.8	1246.5	1200.2	1155.4	1132.3	1116.9	1096.8	1095.3	1086.0
27.5°	1272.7	1246.5	1227.9	1164.7	1130.8	1089.1	1070.6	1053.6	1042.8	1038.2	1033.6
30°	1198.6	1169.3	1147.7	1101.4	1059.8	1025.9	1010.4	999.6	993.5	985.7	984.2
32.5°	1116.9	1099.9	1070.6	1035.1	1002.7	970.3	961.1	953.4	944.1	941.0	939.5
35°	1047.5	1024.3	1005.8	965.7	951.8	924.0	913.2	907.1	894.7	891.6	888.6
37.5°	979.6	958.0	937.9	913.2	887.0	871.6	865.4	856.2	850.0	851.5	848.5
40°	911.7	894.7	879.3	853.1	837.7	829.9	817.6	808.3	805.3	806.8	805.3
42.5°	845.4	829.9	820.7	800.6	785.2	777.5	769.8	760.5	765.1	765.1	769.8
45°	785.2	771.3	765.1	749.7	740.5	728.1	720.4	718.9	725.0	723.5	723.5
47.5°	723.5	718.9	711.2	697.3	684.9	677.2	675.7	675.7	681.8	684.9	683.4
50°	675.7	666.4	657.2	646.4	637.1	634.0	629.4	632.5	638.7	638.7	641.7
52.5°	615.5	609.3	606.3	597.0	590.8	590.8	590.8	592.4	597.0	601.6	600.1
55°	563.1	558.4	555.4	550.7	543.0	544.6	543.0	546.1	550.7	555.4	558.4
57.5°	507.5	506.0	502.9	495.2	495.2	493.6	498.3	499.8	507.5	510.6	515.2
60°	458.2	453.5	453.5	447.4	447.4	447.4	452.0	456.6	462.8	464.3	467.4
62.5°	405.7	405.7	404.2	399.5	399.5	404.2	405.7	411.9	415.0	415.0	419.6
65°	356.4	354.8	353.3	354.8	356.4	356.4	361.0	364.1	367.1	368.7	370.2
67.5°	307.0	305.4	308.5	307.0	310.1	316.2	314.7	319.3	324.0	324.0	325.5
70°	260.7	263.8	262.2	265.3	263.8	266.9	271.5	273.0	273.0	274.6	279.2
72.5°	217.5	217.5	217.5	216.0	217.5	220.6	223.7	225.2	228.3	229.9	234.5
75°	175.9	175.9	172.8	175.9	175.9	178.9	182.0	182.0	182.0	185.1	189.7
77.5°	132.7	134.2	132.7	135.8	135.8	137.3	140.4	138.8	141.9	143.5	145.0
80°	97.2	95.6	95.6	95.6	97.2	97.2	100.3	101.8	101.8	106.4	103.4
82.5°	61.7	63.2	61.7	63.2	63.2	64.8	63.2	64.8	66.3	69.4	67.9
85°	35.5	33.9	33.9	35.5	33.9	33.9	35.5	33.9	35.5	33.9	35.5
87.5°	13.9	12.3	12.3	12.3	12.3	10.8	10.8	9.3	9.3	9.3	7.7
90°	9.2	10.4	11.5	15.3	20.7	25.3	26.1	25.3	24.5	23.0	24.5
92.5°	32.2	36.4	40.6	61.3	90.5	116.5	118.1	98.9	77.4	65.9	57.5
95°	56.7	65.9	75.1	110.4	177.1	266.0	300.5	263.0	200.9	154.1	121.9
97.5°	76.7	87.1	97.4	142.6	235.4	378.7	489.9	493.8	410.9	328.1	250.7
100°	95.8	106.6	117.3	157.9	251.5	417.1	605.7	716.1	700.0	604.9	499.9
102.5°	113.5	124.2	134.9	171.7	252.2	402.5	609.5	798.9	889.4	886.3	816.5
105°	130.3	141.0	151.8	187.8	256.1	382.6	568.1	772.1	931.5	1018.2	1028.1
107.5°	147.2	158.0	168.7	203.9	264.5	371.8	529.8	715.3	886.3	1015.1	1090.2
110°	164.1	175.2	186.3	220.0	275.2	368.8	503.7	662.4	824.2	961.4	1059.6

TEST NUMBER: P997996

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	180.2	191.7	203.2	235.4	286.7	369.5	486.9	625.6	767.5	897.8	1004.4
115°	197.8	208.2	218.5	251.5	298.2	372.6	475.4	596.5	723.0	841.1	941.5
117.5°	213.9	224.6	235.4	266.0	310.5	377.2	469.2	576.6	686.2	792.0	885.5
120°	230.0	240.8	251.5	281.4	322.8	381.8	463.9	561.2	660.1	755.2	836.5
122.5°	246.1	257.2	268.3	295.9	333.5	387.2	460.8	548.2	639.4	724.5	800.4
125°	261.4	272.2	282.9	310.5	345.0	392.5	457.0	535.9	619.5	698.5	765.9
127.5°	275.2	286.4	297.5	324.3	355.7	397.9	454.7	524.4	599.6	672.4	736.8
130°	288.3	299.0	309.7	336.6	365.7	404.0	453.1	512.9	580.4	646.3	706.9
132.5°	300.5	311.2	322.0	347.3	375.7	410.2	452.4	503.7	562.0	621.8	676.2
135°	311.3	322.0	332.7	357.3	384.1	414.8	451.6	495.3	545.1	595.7	646.3
137.5°	321.2	331.2	341.2	365.7	391.0	419.4	451.6	489.2	531.3	575.0	616.4
140°	329.7	339.6	349.6	372.6	396.4	422.5	450.8	483.8	518.3	555.1	590.4
142.5°	337.3	346.5	355.7	378.0	401.0	424.8	450.8	478.4	507.6	537.5	566.6
145°	345.8	354.2	362.6	383.3	404.8	426.3	449.3	473.8	497.6	522.9	546.7
147.5°	352.7	360.4	368.0	387.9	407.1	427.1	447.0	469.2	489.9	510.6	529.8
150°	359.6	366.5	373.4	391.0	408.6	426.3	444.7	463.1	481.5	498.4	514.5
152.5°	366.5	372.6	378.7	394.1	409.4	424.8	440.9	457.7	473.1	488.4	501.4
155°	372.6	378.4	384.1	397.1	410.2	423.2	436.3	450.8	465.4	477.7	489.2
157.5°	378.0	383.0	387.9	399.4	410.2	420.2	431.7	444.7	456.2	466.9	476.9
160°	383.3	387.6	391.8	401.0	410.2	417.9	427.1	437.8	447.8	456.2	464.6
162.5°	387.9	391.0	394.1	401.7	409.4	415.6	423.2	431.7	439.3	446.2	453.1
165°	391.0	393.3	395.6	402.5	407.9	412.5	417.9	424.8	430.9	436.3	441.6
167.5°	394.1	395.6	397.1	402.5	407.1	409.4	413.3	417.9	422.5	427.1	430.9
170°	395.6	396.8	397.9	401.7	405.6	407.1	409.4	412.5	416.3	418.6	421.7
172.5°	397.1	397.9	398.7	401.0	403.3	404.0	404.8	407.1	409.4	410.9	413.3
175°	397.9	398.3	398.7	400.2	401.7	401.0	401.7	402.5	404.8	405.6	406.3
177.5°	398.7	398.7	398.7	399.4	401.0	399.4	398.7	399.4	401.0	401.0	401.7
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P997996

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	1912.9	1917.5	1906.7	1903.6	1906.7	1895.9	1899.0	1902.1	1902.1	1906.7	1909.8
5°	1801.8	1795.6	1784.8	1781.8	1778.7	1783.3	1780.2	1784.8	1786.4	1797.2	1798.7
7.5°	1692.3	1683.0	1673.8	1664.5	1661.4	1653.7	1661.4	1661.4	1672.2	1669.1	1676.9
10°	1562.7	1561.2	1548.8	1544.2	1538.0	1525.7	1542.6	1538.0	1545.7	1559.6	1562.7
12.5°	1467.1	1450.1	1457.8	1436.2	1443.9	1431.6	1433.1	1433.1	1445.5	1447.0	1443.9
15°	1376.0	1362.2	1342.1	1332.8	1328.2	1322.0	1342.1	1343.6	1334.4	1356.0	1348.3
17.5°	1283.5	1283.5	1265.0	1260.3	1248.0	1254.2	1251.1	1252.6	1249.5	1265.0	1272.7
20°	1203.3	1195.5	1189.4	1190.9	1175.5	1172.4	1169.3	1172.4	1183.2	1194.0	1197.1
22.5°	1138.5	1133.8	1118.4	1121.5	1109.2	1113.8	1110.7	1118.4	1120.0	1120.0	1130.8
25°	1076.8	1070.6	1072.1	1066.0	1061.3	1061.3	1056.7	1061.3	1067.5	1070.6	1072.1
27.5°	1030.5	1025.9	1018.1	1013.5	1016.6	1008.9	1015.1	1019.7	1019.7	1016.6	1019.7
30°	974.9	978.0	978.0	962.6	968.8	965.7	970.3	973.4	973.4	974.9	971.9
32.5°	937.9	928.7	927.1	925.6	925.6	919.4	919.4	924.0	925.6	927.1	931.8
35°	888.6	888.6	880.8	885.5	879.3	880.8	879.3	880.8	883.9	879.3	883.9
37.5°	843.8	845.4	842.3	845.4	846.9	843.8	840.7	846.9	843.8	843.8	840.7
40°	805.3	803.7	805.3	805.3	805.3	806.8	803.7	803.7	803.7	800.6	797.5
42.5°	772.9	763.6	766.7	768.2	763.6	763.6	765.1	763.6	768.2	759.0	759.0
45°	726.6	723.5	725.0	725.0	728.1	723.5	726.6	728.1	723.5	722.0	718.9
47.5°	684.9	688.0	684.9	688.0	688.0	691.1	684.9	686.5	688.0	681.8	677.2
50°	643.3	643.3	647.9	646.4	647.9	644.8	644.8	643.3	644.8	641.7	637.1
52.5°	604.7	600.1	607.8	606.3	604.7	603.2	601.6	603.2	600.1	597.0	597.0
55°	556.9	556.9	561.5	563.1	563.1	560.0	556.9	558.4	556.9	555.4	553.8
57.5°	518.3	512.2	515.2	516.8	516.8	512.2	515.2	512.2	512.2	513.7	509.1
60°	469.0	469.0	465.9	470.5	470.5	467.4	467.4	469.0	465.9	464.3	462.8
62.5°	416.5	418.1	422.7	424.2	425.8	422.7	419.6	421.1	421.1	416.5	418.1
65°	371.8	374.9	381.0	379.5	376.4	377.9	374.9	376.4	371.8	373.3	368.7
67.5°	328.6	327.0	328.6	328.6	331.7	330.1	327.0	327.0	325.5	330.1	325.5
70°	282.3	282.3	282.3	282.3	283.8	285.4	282.3	279.2	280.8	277.7	276.1
72.5°	234.5	236.0	234.5	237.6	232.9	236.0	236.0	234.5	232.9	232.9	232.9
75°	189.7	192.8	188.2	189.7	188.2	191.3	189.7	189.7	186.7	185.1	186.7
77.5°	145.0	146.6	143.5	145.0	143.5	145.0	145.0	143.5	143.5	143.5	143.5
80°	103.4	104.9	103.4	101.8	100.3	103.4	100.3	101.8	103.4	101.8	104.9
82.5°	66.3	66.3	64.8	66.3	63.2	63.2	64.8	64.8	63.2	66.3	63.2
85°	32.4	32.4	35.5	32.4	30.9	30.9	30.9	32.4	30.9	33.9	32.4
87.5°	7.7	6.2	7.7	7.7	6.2	6.2	7.7	6.2	7.7	9.3	6.2
90°	24.9	25.3	25.3	25.3	25.3	25.3	25.3	25.3	25.3	25.3	24.9
92.5°	54.4	51.4	50.6	47.5	48.3	46.8	48.3	47.5	50.6	51.4	54.4
95°	113.4	105.0	95.1	88.9	86.6	87.4	86.6	88.9	95.1	105.0	113.4
97.5°	227.7	204.7	174.8	159.5	151.0	146.4	151.0	159.5	174.8	204.7	227.7
100°	453.5	407.1	343.5	310.5	288.3	274.5	288.3	310.5	343.5	407.1	453.5
102.5°	766.7	716.9	646.3	584.2	555.1	535.2	555.1	584.2	646.3	716.9	766.7
105°	1015.4	1002.8	955.3	907.8	874.8	864.1	874.8	907.8	955.3	1002.8	1015.4
107.5°	1105.6	1120.9	1120.1	1113.2	1103.3	1085.6	1103.3	1113.2	1120.1	1120.9	1105.6
110°	1091.0	1122.4	1155.4	1170.0	1176.9	1176.1	1176.9	1170.0	1155.4	1122.4	1091.0

TEST NUMBER: P997996

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1041.6	1078.7	1127.8	1154.6	1169.2	1174.6	1169.2	1154.6	1127.8	1078.7	1041.6
115°	981.0	1020.5	1074.9	1110.2	1130.1	1137.0	1130.1	1110.2	1074.9	1020.5	981.0
117.5°	923.1	960.7	1016.6	1054.2	1074.9	1080.3	1074.9	1054.2	1016.6	960.7	923.1
120°	871.4	906.2	959.9	995.9	1018.2	1025.8	1018.2	995.9	959.9	906.2	871.4
122.5°	831.1	861.8	908.5	943.8	963.0	969.1	963.0	943.8	908.5	861.8	831.1
125°	794.6	823.4	867.9	897.0	916.2	922.3	916.2	897.0	867.9	823.4	794.6
127.5°	763.6	790.5	829.6	857.2	874.0	878.6	874.0	857.2	829.6	790.5	763.6
130°	732.2	757.5	795.1	821.1	836.5	842.6	836.5	821.1	795.1	757.5	732.2
132.5°	699.6	723.0	759.8	785.9	799.7	805.0	799.7	785.9	759.8	723.0	699.6
135°	667.8	689.3	722.2	747.5	761.3	764.4	761.3	747.5	722.2	689.3	667.8
137.5°	635.6	654.8	686.2	708.4	720.7	725.3	720.7	708.4	686.2	654.8	635.6
140°	607.2	624.1	648.6	668.6	680.1	684.7	680.1	668.6	648.6	624.1	607.2
142.5°	580.0	593.4	616.4	634.1	644.0	644.0	644.0	634.1	616.4	593.4	580.0
145°	557.8	568.9	587.3	600.3	608.0	610.3	608.0	600.3	587.3	568.9	557.8
147.5°	538.2	546.7	562.8	573.5	578.9	580.4	578.9	573.5	562.8	546.7	538.2
150°	521.4	528.3	539.8	549.0	553.6	554.3	553.6	549.0	539.8	528.3	521.4
152.5°	507.2	512.9	521.4	529.0	532.1	532.1	532.1	529.0	521.4	512.9	507.2
155°	493.4	497.6	506.0	511.4	514.5	512.9	514.5	511.4	506.0	497.6	493.4
157.5°	480.4	483.8	489.9	494.5	496.1	496.1	496.1	494.5	489.9	483.8	480.4
160°	467.3	470.0	475.4	479.2	480.0	480.0	480.0	479.2	475.4	470.0	467.3
162.5°	455.0	457.0	462.3	464.6	465.4	464.6	465.4	464.6	462.3	457.0	455.0
165°	443.2	444.7	447.8	450.8	450.8	450.1	450.8	450.8	447.8	444.7	443.2
167.5°	432.4	434.0	435.5	437.0	437.0	436.3	437.0	437.0	435.5	434.0	432.4
170°	422.4	423.2	424.0	426.3	425.5	424.0	425.5	426.3	424.0	423.2	422.4
172.5°	413.6	414.0	414.8	415.6	414.8	414.0	414.8	415.6	414.8	414.0	413.6
175°	406.7	407.1	407.1	407.9	407.1	405.6	407.1	407.9	407.1	407.1	406.7
177.5°	401.7	401.7	401.7	401.7	401.0	399.4	401.0	401.7	401.7	401.7	401.7
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P997996

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	1905.2	1917.5	1912.9	1895.9	1916.0	1916.0	1929.8	1929.8	1946.8	1953.0	1962.2
5°	1797.2	1806.4	1814.1	1806.4	1820.3	1841.9	1854.3	1865.1	1888.2	1897.4	1911.3
7.5°	1681.5	1698.4	1706.2	1706.2	1729.3	1754.0	1778.7	1794.1	1826.5	1838.8	1852.7
10°	1568.9	1588.9	1604.3	1602.8	1641.4	1656.8	1687.6	1723.1	1755.5	1774.0	1794.1
12.5°	1450.1	1460.9	1482.5	1513.3	1522.6	1550.4	1585.8	1630.6	1689.2	1706.2	1735.5
15°	1351.4	1380.7	1397.6	1411.5	1433.1	1459.3	1497.9	1541.1	1599.7	1636.7	1667.6
17.5°	1268.1	1306.6	1317.4	1314.3	1342.1	1382.2	1426.9	1459.3	1511.8	1556.5	1585.8
20°	1200.2	1215.6	1234.1	1241.8	1263.4	1306.6	1349.8	1386.8	1430.0	1465.5	1499.4
22.5°	1132.3	1144.6	1160.1	1173.9	1190.9	1215.6	1257.3	1303.5	1345.2	1379.1	1417.7
25°	1076.8	1084.5	1098.4	1109.2	1127.7	1144.6	1173.9	1224.9	1274.2	1294.3	1328.2
27.5°	1022.8	1028.9	1038.2	1050.5	1059.8	1076.8	1103.0	1144.6	1195.5	1215.6	1261.9
30°	974.9	979.6	988.8	995.0	999.6	1019.7	1039.7	1072.1	1110.7	1138.5	1172.4
32.5°	930.2	934.8	944.1	945.6	951.8	962.6	981.1	1010.4	1044.4	1067.5	1096.8
35°	880.8	883.9	893.2	896.3	900.9	910.2	924.0	945.6	976.5	993.5	1019.7
37.5°	842.3	840.7	846.9	851.5	857.7	862.3	867.0	888.6	911.7	927.1	947.2
40°	800.6	797.5	799.1	805.3	808.3	814.5	814.5	836.1	851.5	863.9	879.3
42.5°	759.0	757.4	754.4	757.4	760.5	762.1	763.6	779.0	794.5	805.3	822.2
45°	717.3	715.8	712.7	714.2	714.2	717.3	722.0	728.1	738.9	748.2	757.4
47.5°	678.8	675.7	671.0	669.5	672.6	672.6	672.6	678.8	689.6	692.6	701.9
50°	638.7	634.0	627.9	624.8	624.8	623.2	626.3	627.9	637.1	640.2	647.9
52.5°	595.5	592.4	586.2	580.0	581.6	578.5	580.0	581.6	584.7	589.3	593.9
55°	552.3	546.1	541.5	539.9	535.3	535.3	530.7	536.8	535.3	536.8	543.0
57.5°	510.6	504.4	496.7	493.6	489.0	487.5	484.4	482.8	484.4	489.0	493.6
60°	461.2	458.2	453.5	448.9	445.8	441.2	438.1	438.1	436.6	436.6	438.1
62.5°	413.4	411.9	405.7	404.2	401.1	398.0	393.4	390.3	390.3	393.4	394.9
65°	367.1	365.6	361.0	359.4	351.7	348.6	347.1	345.6	342.5	342.5	342.5
67.5°	324.0	319.3	319.3	311.6	305.4	302.4	299.3	297.7	297.7	297.7	299.3
70°	276.1	276.1	271.5	266.9	260.7	262.2	257.6	253.0	253.0	249.9	251.5
72.5°	229.9	228.3	223.7	222.1	217.5	212.9	209.8	212.9	208.3	206.7	208.3
75°	185.1	183.6	180.5	177.4	178.9	174.3	169.7	168.1	168.1	165.1	165.1
77.5°	141.9	145.0	138.8	137.3	134.2	131.1	129.6	128.0	128.0	128.0	131.1
80°	98.7	100.3	100.3	97.2	98.7	94.1	94.1	94.1	89.5	91.0	92.6
82.5°	63.2	63.2	61.7	63.2	61.7	61.7	60.2	60.2	58.6	58.6	60.2
85°	35.5	33.9	32.4	35.5	33.9	33.9	32.4	32.4	32.4	32.4	32.4
87.5°	7.7	9.3	9.3	9.3	9.3	10.8	10.8	10.8	12.3	12.3	12.3
90°	24.5	23.0	24.5	25.3	26.1	25.3	20.7	15.3	11.5	10.4	9.2
92.5°	57.5	65.9	77.4	98.9	118.1	116.5	90.5	61.3	40.6	36.4	32.2
95°	121.9	154.1	200.9	263.0	300.5	266.0	177.1	110.4	75.1	65.9	56.7
97.5°	250.7	328.1	410.9	493.8	489.9	378.7	235.4	142.6	97.4	87.1	76.7
100°	499.9	604.9	700.0	716.1	605.7	417.1	251.5	157.9	117.3	106.6	95.8
102.5°	816.5	886.3	889.4	798.9	609.5	402.5	252.2	171.7	134.9	124.2	113.5
105°	1028.1	1018.2	931.5	772.1	568.1	382.6	256.1	187.8	151.8	141.0	130.3
107.5°	1090.2	1015.1	886.3	715.3	529.8	371.8	264.5	203.9	168.7	158.0	147.2
110°	1059.6	961.4	824.2	662.4	503.7	368.8	275.2	220.0	186.3	175.2	164.1

TEST NUMBER: P997996

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1004.4	897.8	767.5	625.6	486.9	369.5	286.7	235.4	203.2	191.7	180.2
115°	941.5	841.1	723.0	596.5	475.4	372.6	298.2	251.5	218.5	208.2	197.8
117.5°	885.5	792.0	686.2	576.6	469.2	377.2	310.5	266.0	235.4	224.6	213.9
120°	836.5	755.2	660.1	561.2	463.9	381.8	322.8	281.4	251.5	240.8	230.0
122.5°	800.4	724.5	639.4	548.2	460.8	387.2	333.5	295.9	268.3	257.2	246.1
125°	765.9	698.5	619.5	535.9	457.0	392.5	345.0	310.5	282.9	272.2	261.4
127.5°	736.8	672.4	599.6	524.4	454.7	397.9	355.7	324.3	297.5	286.4	275.2
130°	706.9	646.3	580.4	512.9	453.1	404.0	365.7	336.6	309.7	299.0	288.3
132.5°	676.2	621.8	562.0	503.7	452.4	410.2	375.7	347.3	322.0	311.2	300.5
135°	646.3	595.7	545.1	495.3	451.6	414.8	384.1	357.3	332.7	322.0	311.3
137.5°	616.4	575.0	531.3	489.2	451.6	419.4	391.0	365.7	341.2	331.2	321.2
140°	590.4	555.1	518.3	483.8	450.8	422.5	396.4	372.6	349.6	339.6	329.7
142.5°	566.6	537.5	507.6	478.4	450.8	424.8	401.0	378.0	355.7	346.5	337.3
145°	546.7	522.9	497.6	473.8	449.3	426.3	404.8	383.3	362.6	354.2	345.8
147.5°	529.8	510.6	489.9	469.2	447.0	427.1	407.1	387.9	368.0	360.4	352.7
150°	514.5	498.4	481.5	463.1	444.7	426.3	408.6	391.0	373.4	366.5	359.6
152.5°	501.4	488.4	473.1	457.7	440.9	424.8	409.4	394.1	378.7	372.6	366.5
155°	489.2	477.7	465.4	450.8	436.3	423.2	410.2	397.1	384.1	378.4	372.6
157.5°	476.9	466.9	456.2	444.7	431.7	420.2	410.2	399.4	387.9	383.0	378.0
160°	464.6	456.2	447.8	437.8	427.1	417.9	410.2	401.0	391.8	387.6	383.3
162.5°	453.1	446.2	439.3	431.7	423.2	415.6	409.4	401.7	394.1	391.0	387.9
165°	441.6	436.3	430.9	424.8	417.9	412.5	407.9	402.5	395.6	393.3	391.0
167.5°	430.9	427.1	422.5	417.9	413.3	409.4	407.1	402.5	397.1	395.6	394.1
170°	421.7	418.6	416.3	412.5	409.4	407.1	405.6	401.7	397.9	396.8	395.6
172.5°	413.3	410.9	409.4	407.1	404.8	404.0	403.3	401.0	398.7	397.9	397.1
175°	406.3	405.6	404.8	402.5	401.7	401.0	401.7	400.2	398.7	398.3	397.9
177.5°	401.7	401.0	401.0	399.4	398.7	399.4	401.0	399.4	398.7	398.7	398.7
180°	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7	398.7

TEST NUMBER: P997996

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	2007.0	2007.0	2007.0	2007.0
2.5°	1970.0	1970.0	1993.1	2017.8
5°	1926.8	1937.6	1974.6	2008.5
7.5°	1885.1	1903.6	1949.9	1993.1
10°	1834.2	1858.9	1916.0	1966.9
12.5°	1784.8	1808.0	1874.3	1931.4
15°	1715.4	1744.7	1815.7	1886.6
17.5°	1646.0	1675.3	1761.7	1845.0
20°	1564.2	1602.8	1700.0	1811.1
22.5°	1488.6	1536.5	1644.5	1733.9
25°	1405.3	1479.4	1579.7	1695.4
27.5°	1331.3	1405.3	1507.2	1624.4
30°	1248.0	1323.6	1428.5	1536.5
32.5°	1167.8	1237.2	1339.0	1471.7
35°	1084.5	1150.8	1249.5	1383.7
37.5°	1008.9	1073.7	1181.7	1305.1
40°	934.8	1002.7	1095.3	1218.7
42.5°	865.4	925.6	1008.9	1132.3
45°	802.2	845.4	922.5	1038.2
47.5°	735.8	774.4	845.4	961.1
50°	674.1	706.5	768.2	876.2
52.5°	614.0	641.7	698.8	785.2
55°	560.0	586.2	627.9	712.7
57.5°	504.4	524.5	564.6	632.5
60°	450.5	469.0	501.4	556.9
62.5°	396.5	411.9	442.7	487.5
65°	348.6	361.0	384.1	422.7
67.5°	302.4	310.1	328.6	359.4
70°	257.6	263.8	279.2	303.9
72.5°	209.8	216.0	232.9	249.9
75°	169.7	171.2	183.6	197.5
77.5°	132.7	131.1	140.4	151.2
80°	91.0	95.6	103.4	108.0
82.5°	61.7	63.2	66.3	69.4
85°	33.9	35.5	35.5	40.1
87.5°	13.9	15.4	15.4	17.0
90°	7.7	6.1	3.1	0.8
92.5°	26.1	22.2	16.1	11.5
95°	44.5	37.6	29.9	26.8
97.5°	62.9	52.9	44.5	39.9
100°	80.5	68.2	61.3	59.0
102.5°	97.4	85.1	78.2	76.7
105°	113.5	102.0	96.6	93.5
107.5°	130.3	119.6	114.2	111.9
110°	148.0	138.0	133.4	130.3



TEST NUMBER: P997996

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	164.8	155.6	150.3	147.2
115°	182.5	173.3	168.7	164.8
117.5°	199.3	190.9	186.3	183.2
120°	214.7	207.8	203.2	200.1
122.5°	230.8	223.1	218.5	216.2
125°	246.1	236.9	232.3	230.0
127.5°	260.7	250.7	244.6	241.5
130°	272.9	262.2	254.5	251.5
132.5°	284.4	272.9	264.5	260.7
135°	293.6	282.1	272.9	269.9
137.5°	303.6	291.3	282.1	278.3
140°	312.8	300.5	291.3	288.3
142.5°	321.2	309.0	300.5	298.2
145°	330.4	318.9	311.3	308.2
147.5°	339.6	328.9	321.2	318.9
150°	348.1	338.1	332.0	329.7
152.5°	355.7	347.3	341.2	340.4
155°	364.2	355.7	351.1	350.4
157.5°	371.1	363.4	359.6	358.8
160°	377.2	371.1	368.0	367.2
162.5°	382.6	378.0	374.9	375.7
165°	387.2	382.6	381.0	381.8
167.5°	391.0	387.9	386.4	387.2
170°	394.1	391.8	391.0	392.5
172.5°	396.4	394.1	394.8	395.6
175°	397.9	396.4	397.1	397.9
177.5°	398.7	397.1	397.9	399.4
180°	398.7	398.7	398.7	398.7

TEST NUMBER: P997996

CATALOG NUMBER: SA2XXDIP-B1005D725UB35-4F0-XX-W2A-A4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.87	19.80	19.73	20.68	21.78	16.36	17.29	17.22	18.17	19.27
	3H	19.69	20.52	20.56	21.40	22.53	17.71	18.55	18.58	19.43	20.56
	4H	19.86	20.64	20.75	21.54	22.67	18.18	18.96	19.07	19.86	20.99
	6H	19.91	20.63	20.81	21.53	22.68	18.49	19.21	19.39	20.11	21.26
	8H	19.89	20.58	20.80	21.49	22.64	18.57	19.26	19.48	20.18	21.33
	12H	19.85	20.51	20.77	21.42	22.59	18.62	19.27	19.53	20.18	21.36
4H	2H	18.92	19.70	19.81	20.60	21.73	16.82	17.60	17.71	18.49	19.63
	3H	19.91	20.56	20.81	21.48	22.63	18.28	18.94	19.19	19.86	21.01
	4H	20.19	20.78	21.10	21.70	22.88	18.82	19.42	19.74	20.33	21.51
	6H	20.32	20.83	21.25	21.77	22.95	19.20	19.72	20.13	20.66	21.84
	8H	20.32	20.80	21.25	21.73	22.93	19.32	19.79	20.25	20.73	21.92
	12H	20.29	20.72	21.24	21.67	22.87	19.38	19.81	20.33	20.76	21.96
8H	4H	20.20	20.68	21.13	21.61	22.81	18.97	19.45	19.90	20.38	21.58
	6H	20.38	20.78	21.34	21.75	22.95	19.41	19.80	20.36	20.78	21.97
	8H	20.41	20.76	21.38	21.73	22.94	19.56	19.90	20.52	20.87	22.08
	12H	20.40	20.71	21.37	21.67	22.93	19.65	19.96	20.62	20.92	22.18
12H	4H	20.16	20.59	21.11	21.54	22.74	18.95	19.38	19.90	20.33	21.53
	6H	20.36	20.71	21.33	21.68	22.89	19.41	19.75	20.37	20.72	21.93
	8H	20.40	20.70	21.36	21.66	22.92	19.57	19.87	20.54	20.83	22.09