

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998745

Luminaire Tested: SA2XXDIP-B675D330UB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998745
REPORT IS A COMBINATION OF REPORTS P984491 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B675D330UB2750-4F0-XX-W2A-A_5000K
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4100.0 lumens
Efficiency: N/A
Efficacy: 90.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998745

CATALOG NUMBER: SA2XXDIP-B675D330UB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P998745

CATALOG NUMBER: SA2XXDIP-B675D330UB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	74	74	74	69		
1	103	99	95	91	97	93	90	87	83	81	79	74	73	71	66	65	64	60		
2	94	87	81	76	89	82	77	73	74	70	66	66	63	60	59	57	55	51		
3	86	77	70	64	81	73	67	62	66	61	57	59	55	52	53	50	47	44		
4	79	69	61	55	75	65	58	53	59	53	49	53	49	45	48	44	41	38		
5	73	62	54	48	69	59	51	46	53	47	43	48	43	40	43	40	36	34		
6	68	56	48	42	64	53	46	40	48	42	38	44	39	35	40	36	32	30		
7	63	51	43	37	59	48	41	36	44	38	34	40	35	31	36	32	29	27		
8	59	46	39	33	55	44	37	32	41	35	30	37	32	28	34	29	26	24		
9	55	43	35	30	52	41	34	29	37	31	27	34	29	26	31	27	24	22		
10	51	39	32	27	49	38	31	26	35	29	25	32	27	23	29	25	22	20		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	20318	20318	20318	20318
5°	20367	21665	20445	17235
10°	20130	23650	20257	14211
15°	19642	24945	19915	11969
20°	19336	23422	19336	10403
25°	18720	20122	18804	9304
30°	17706	15818	18043	8427
35°	16808	10938	17089	7711
40°	15774	8258	15954	7139
45°	14502	6787	14738	6522
50°	13401	5956	13425	5970
55°	12145	5075	12225	5371
60°	10809	4239	10957	4687
65°	9609	3448	9787	4003
70°	8419	2705	8631	3229
75°	7065	1964	7339	2341
80°	5517	1245	5908	1390
85°	3630	626	3899	463

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 21003 cd/sqm

TEST NUMBER: P998745

CATALOG NUMBER: SA2XXDIP-B675D330UB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.3	3.0
10°-20°	355.8	8.7
20°-30°	516.4	12.6
30°-40°	544.4	13.3
40°-50°	481.8	11.8
50°-60°	384.7	9.4
60°-70°	261.3	6.4
70°-80°	133.7	3.3
80°-90°	32.3	0.8
90°-100°	14.3	0.3
100°-110°	53.1	1.3
110°-120°	140.9	3.4
120°-130°	233.7	5.7
130°-140°	248.3	6.1
140°-150°	230.7	5.6
150°-160°	185.5	4.5
160°-170°	119.5	2.9
170°-180°	41.1	1.0
0°-30°	994.6	24.3
0°-40°	1539.0	37.5
0°-60°	2405.4	58.7
0°-90°	2832.8	69.1
90°-120°	208.3	5.1
90°-150°	921.1	22.5
90°-180°	1267.0	30.9
0°-180°	4100.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1284	1284	1284	1284	1284	
5°	1285	1434	1290	1140	1285	122
15°	1207	1762	1223	846	1207	341
25°	1084	1468	1089	679	1084	496
35°	885	799	900	563	885	554
45°	664	482	675	463	664	515
55°	456	338	459	358	456	407
65°	270	208	275	242	270	269
75°	126	103	131	122	126	136
85°	26	27	28	20	26	30
90°	0	8	0	8	0	3
95°	20	13	20	13	20	24
105°	95	24	95	24	95	102
115°	180	26	180	26	180	177
125°	254	267	254	267	254	227
135°	315	325	315	325	315	243
145°	365	371	365	371	365	228
155°	402	402	402	402	402	185
165°	424	423	424	423	424	120
175°	433	431	433	431	433	41
180°	432	432	432	432	432	

TEST NUMBER: P998745

CATALOG NUMBER: SA2XXDIP-B675D330UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1290.5	1293.5	1298.4	1299.4	1309.2	1317.1	1326.0	1326.0	1329.0	1328.0	1320.1
5°	1284.6	1293.5	1306.3	1317.1	1334.9	1342.8	1354.6	1363.5	1371.4	1377.3	1376.3
7.5°	1274.7	1290.5	1309.2	1330.0	1353.6	1367.5	1384.2	1400.0	1410.9	1420.7	1427.6
10°	1257.9	1284.6	1310.2	1337.9	1368.4	1387.2	1406.9	1427.6	1444.4	1463.2	1480.9
12.5°	1235.2	1273.7	1305.3	1341.8	1379.3	1400.0	1431.6	1447.4	1479.9	1527.3	1540.1
15°	1206.6	1258.9	1288.5	1334.9	1384.2	1401.0	1444.4	1470.1	1537.2	1566.8	1602.3
17.5°	1180.0	1238.2	1277.7	1331.0	1379.3	1411.9	1454.3	1506.6	1562.8	1605.2	1644.7
20°	1158.3	1214.5	1261.9	1321.1	1382.3	1423.7	1468.1	1531.2	1592.4	1635.8	1666.4
22.5°	1109.0	1181.0	1236.2	1302.3	1376.3	1433.6	1476.0	1545.0	1611.2	1637.8	1664.4
25°	1084.3	1146.5	1210.6	1285.6	1372.4	1440.5	1477.0	1553.9	1612.1	1622.0	1627.9
27.5°	1038.9	1109.0	1183.9	1269.8	1371.4	1428.6	1475.0	1545.0	1591.4	1584.5	1566.8
30°	982.7	1068.5	1151.4	1244.1	1357.6	1419.7	1463.2	1527.3	1551.0	1515.5	1483.9
32.5°	941.2	1022.1	1113.9	1221.4	1341.8	1401.0	1443.4	1493.7	1498.7	1434.5	1381.3
35°	885.0	974.8	1078.4	1191.8	1315.2	1368.4	1407.9	1438.5	1414.8	1325.0	1261.9
37.5°	834.7	923.5	1034.0	1149.4	1278.7	1331.0	1362.5	1367.5	1309.2	1230.3	1137.6
40°	779.4	871.2	986.6	1108.0	1238.2	1283.6	1303.3	1288.5	1204.7	1112.9	1005.4
42.5°	724.2	814.9	939.3	1063.6	1186.9	1225.4	1233.3	1192.8	1090.2	982.7	858.4
45°	664.0	758.7	883.0	1008.3	1127.7	1149.4	1150.4	1092.2	970.8	858.4	742.9
47.5°	614.7	702.5	825.8	951.1	1051.7	1066.5	1060.6	993.5	861.3	735.0	634.4
50°	560.4	644.3	766.6	889.9	975.8	979.7	964.9	869.2	740.0	624.5	544.6
52.5°	502.2	587.0	699.5	817.9	894.9	888.9	860.3	757.7	636.4	540.7	479.5
55°	455.8	530.8	636.4	751.8	806.1	789.3	757.7	653.1	557.4	476.5	423.3
57.5°	404.5	470.6	574.2	674.8	706.4	690.6	659.1	561.4	472.6	411.4	375.9
60°	356.2	416.4	507.1	591.0	615.7	598.9	562.4	474.6	410.4	359.1	332.5
62.5°	311.8	364.1	440.0	517.0	526.9	510.1	478.5	407.5	352.2	311.8	292.0
65°	270.3	319.7	380.8	439.0	447.9	430.2	397.6	346.3	299.9	274.3	255.5
67.5°	229.9	269.3	323.6	366.0	371.0	354.2	327.6	286.1	257.5	229.9	216.1
70°	194.4	224.0	266.4	300.9	302.9	287.1	273.3	235.8	214.1	194.4	183.5
72.5°	159.8	180.6	213.1	238.8	239.7	229.9	217.1	193.4	174.6	160.8	150.0
75°	126.3	144.0	163.8	186.5	185.5	177.6	167.7	152.9	137.1	128.3	123.3
77.5°	96.7	107.5	123.3	138.1	138.1	134.2	128.3	117.4	107.5	98.7	93.7
80°	69.1	76.0	88.8	93.7	95.7	94.7	89.8	81.9	77.9	71.0	69.1
82.5°	44.4	49.3	55.3	60.2	63.1	61.2	60.2	56.2	50.3	48.3	46.4
85°	25.7	27.6	30.6	33.5	34.5	33.5	35.5	32.6	29.6	29.6	28.6
87.5°	10.9	11.8	13.8	13.8	14.8	14.8	13.8	14.8	14.8	13.8	12.8
90°	0.3	1.1	1.9	2.6	3.4	3.8	4.1	4.6	5.2	5.7	6.3
92.5°	7.8	7.5	7.3	7.0	6.7	6.6	6.7	6.9	7.1	7.3	7.5
95°	20.3	18.0	15.7	13.4	11.1	10.0	10.2	10.7	11.2	11.7	12.2
97.5°	36.6	30.9	25.2	19.5	13.8	10.9	11.5	12.6	13.7	14.9	16.0
100°	55.4	45.9	36.3	26.8	17.3	12.5	13.1	14.3	15.4	16.6	17.8
102.5°	76.0	75.9	75.7	75.6	75.5	75.4	69.1	56.4	43.8	31.1	18.5
105°	95.1	97.2	99.3	101.4	103.5	104.5	95.0	76.0	57.1	38.1	19.1
107.5°	117.3	119.0	120.8	122.5	124.2	125.1	113.4	90.0	66.5	43.1	19.7
110°	138.6	140.0	141.5	142.9	144.4	145.1	135.1	115.0	94.9	74.8	54.7

TEST NUMBER: P998745

CATALOG NUMBER: SA2XXDIP-B675D330UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	158.6	159.8	161.1	162.3	163.6	164.2	163.6	162.4	161.3	160.1	158.9
115°	179.8	181.0	182.2	183.4	184.6	185.2	186.1	187.8	189.5	191.3	193.0
117.5°	198.3	199.7	201.1	202.5	203.9	204.6	205.2	206.4	207.5	208.7	209.9
120°	218.9	219.9	221.0	222.0	223.1	223.6	224.2	225.5	226.8	228.0	229.3
122.5°	236.5	237.6	238.7	239.8	240.9	241.5	242.2	243.6	244.9	246.3	247.7
125°	254.3	255.2	256.1	257.0	257.9	258.4	259.1	260.4	261.7	263.0	264.3
127.5°	270.6	271.6	272.5	273.5	274.4	274.9	275.4	276.5	277.5	278.6	279.6
130°	285.9	287.0	288.1	289.2	290.3	290.9	291.3	292.0	292.8	293.5	294.3
132.5°	301.5	302.4	303.3	304.2	305.1	305.6	306.0	306.7	307.5	308.2	309.0
135°	314.7	315.8	316.9	318.0	319.1	319.7	320.0	320.6	321.3	321.9	322.5
137.5°	328.4	329.2	330.1	330.9	331.8	332.2	332.5	333.2	333.9	334.6	335.3
140°	341.9	342.5	343.0	343.6	344.1	344.4	344.8	345.5	346.3	347.0	347.8
142.5°	353.1	353.6	354.1	354.6	355.1	355.3	355.8	356.7	357.6	358.5	359.4
145°	365.0	364.9	364.9	364.8	364.7	364.7	365.3	366.5	367.6	368.8	370.0
147.5°	375.3	375.1	374.9	374.7	374.5	374.4	375.0	376.2	377.3	378.5	379.7
150°	385.3	384.8	384.4	383.9	383.4	383.2	383.8	384.9	386.0	387.1	388.2
152.5°	393.8	393.2	392.7	392.1	391.6	391.3	391.8	392.9	393.9	395.0	396.0
155°	401.9	401.3	400.7	400.0	399.4	399.1	399.5	400.4	401.2	402.1	402.9
157.5°	408.5	407.9	407.4	406.8	406.3	406.0	406.3	406.9	407.6	408.2	408.8
160°	414.1	413.7	413.3	412.8	412.4	412.2	412.4	412.8	413.3	413.7	414.1
162.5°	419.1	418.7	418.3	417.8	417.4	417.2	417.4	417.7	418.1	418.4	418.8
165°	423.5	423.1	422.7	422.2	421.8	421.6	421.7	421.9	422.2	422.4	422.6
167.5°	426.9	426.5	426.1	425.7	425.3	425.1	425.2	425.4	425.6	425.8	426.0
170°	429.8	429.4	429.0	428.5	428.1	427.9	428.0	428.1	428.2	428.4	428.5
172.5°	431.6	431.2	430.8	430.4	430.0	429.8	429.9	430.0	430.1	430.3	430.4
175°	433.2	432.7	432.2	431.7	431.2	431.0	431.1	431.2	431.3	431.5	431.6
177.5°	433.8	433.3	432.8	432.3	431.8	431.6	431.6	431.7	431.8	431.8	431.9
180°	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3

TEST NUMBER: P998745

CATALOG NUMBER: SA2XXDIP-B675D330UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1333.9	1334.9	1336.9	1346.7	1351.7	1352.7	1348.7	1357.6	1360.6	1357.6	1355.6
5°	1397.1	1403.0	1414.8	1427.6	1426.7	1427.6	1433.6	1439.5	1441.5	1433.6	1436.5
7.5°	1452.3	1464.1	1477.0	1496.7	1496.7	1506.6	1510.5	1515.5	1527.3	1521.4	1519.4
10°	1515.5	1531.2	1554.9	1586.5	1587.5	1597.3	1607.2	1623.0	1627.9	1624.0	1626.0
12.5°	1594.4	1625.0	1626.9	1661.5	1677.3	1679.2	1695.0	1692.1	1701.9	1701.9	1718.7
15°	1628.9	1676.3	1702.9	1736.5	1746.3	1734.5	1747.3	1761.1	1762.1	1762.1	1761.1
17.5°	1691.1	1709.8	1736.5	1754.2	1758.2	1758.2	1759.1	1765.1	1761.1	1753.2	1759.1
20°	1703.9	1711.8	1721.7	1719.7	1721.7	1711.8	1701.9	1692.1	1693.0	1688.1	1702.9
22.5°	1680.2	1678.2	1655.6	1640.8	1640.8	1621.0	1602.3	1593.4	1584.5	1587.5	1592.4
25°	1621.0	1590.4	1562.8	1541.1	1536.2	1504.6	1478.9	1471.1	1456.3	1468.1	1470.1
27.5°	1526.3	1491.8	1447.4	1428.6	1403.0	1390.1	1372.4	1348.7	1318.1	1335.9	1332.9
30°	1424.7	1373.4	1336.9	1291.5	1251.0	1248.1	1214.5	1175.1	1159.3	1159.3	1168.2
32.5°	1311.2	1243.1	1189.9	1125.7	1086.3	1069.5	1029.0	989.6	998.5	968.9	979.7
35°	1179.0	1089.2	1022.1	960.0	930.4	910.7	858.4	836.7	813.0	799.2	824.8
37.5°	1052.7	949.1	863.3	795.2	784.4	748.8	713.3	699.5	685.7	691.6	690.6
40°	898.8	807.1	730.1	676.8	658.1	641.3	617.6	600.9	592.0	596.9	597.9
42.5°	759.7	682.7	625.5	588.0	572.2	560.4	548.6	534.7	531.8	531.8	535.7
45°	652.2	589.0	550.5	519.9	511.1	502.2	493.3	487.4	485.4	481.5	484.4
47.5°	566.3	516.0	492.3	469.6	459.8	457.8	449.9	446.9	443.0	442.0	443.0
50°	494.3	462.7	441.0	428.2	421.3	418.3	414.4	408.5	406.5	411.4	409.4
52.5°	444.0	414.4	402.5	389.7	385.8	381.8	375.9	376.9	375.9	373.9	373.9
55°	393.7	374.9	363.1	353.2	352.2	348.3	343.3	341.4	340.4	338.4	341.4
57.5°	353.2	338.4	327.6	318.7	314.7	314.7	309.8	305.9	305.9	304.9	305.9
60°	312.8	298.0	291.1	282.2	279.2	278.2	275.3	273.3	270.3	270.3	270.3
62.5°	275.3	263.4	255.5	247.6	248.6	243.7	239.7	237.8	237.8	238.8	238.8
65°	239.7	231.9	222.0	215.1	213.1	212.1	210.2	209.2	206.2	208.2	208.2
67.5°	207.2	196.3	190.4	187.5	184.5	183.5	181.5	179.6	178.6	177.6	179.6
70°	174.6	165.8	160.8	158.8	155.9	154.9	153.9	151.0	151.9	152.9	153.9
72.5°	145.0	137.1	136.2	130.2	130.2	130.2	126.3	128.3	127.3	125.3	127.3
75°	114.4	110.5	108.5	105.6	106.6	105.6	104.6	101.6	101.6	102.6	103.6
77.5°	90.8	86.8	85.8	82.9	80.9	82.9	80.9	79.9	79.9	80.9	80.9
80°	67.1	65.1	62.2	62.2	62.2	61.2	61.2	61.2	60.2	59.2	60.2
82.5°	44.4	44.4	43.4	42.4	43.4	41.4	42.4	42.4	42.4	42.4	42.4
85°	28.6	27.6	27.6	26.6	26.6	26.6	27.6	25.7	25.7	26.6	26.6
87.5°	12.8	12.8	12.8	13.8	12.8	12.8	12.8	13.8	12.8	12.8	12.8
90°	6.6	7.0	7.3	7.6	7.8	7.9	8.0	8.1	8.3	8.4	8.3
92.5°	7.6	7.8	7.9	8.0	8.1	8.1	8.2	8.3	8.3	8.4	8.3
95°	12.6	12.9	13.3	13.6	13.8	13.8	13.7	13.6	13.5	13.4	13.5
97.5°	16.2	16.4	16.6	16.8	16.9	16.9	17.0	17.1	17.1	17.2	17.1
100°	18.4	18.9	19.5	20.0	20.3	20.4	20.5	20.7	20.8	21.0	20.8
102.5°	19.3	20.0	20.8	21.5	21.9	22.0	22.2	22.4	22.6	22.8	22.6
105°	19.9	20.6	21.4	22.1	22.5	22.6	22.9	23.2	23.5	23.8	23.5
107.5°	20.5	21.2	22.0	22.7	23.1	23.2	23.5	23.8	24.1	24.4	24.1
110°	47.8	40.8	33.9	27.0	23.5	23.6	23.9	24.2	24.4	24.7	24.4

TEST NUMBER: P998745

CATALOG NUMBER: SA2XXDIP-B675D330UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	128.9	99.0	69.0	39.1	24.1	24.2	24.4	24.6	24.8	25.0	24.8
115°	160.8	128.6	96.5	64.3	48.2	45.7	40.7	35.6	30.6	25.6	30.6
117.5°	199.9	190.0	180.0	170.1	165.1	156.0	137.8	119.6	101.4	83.2	101.4
120°	230.1	230.9	231.8	232.6	233.0	228.3	218.9	209.6	200.2	190.8	200.2
122.5°	248.1	248.5	249.0	249.4	249.6	249.6	249.7	249.8	249.8	249.9	249.8
125°	264.8	265.3	265.8	266.3	266.5	266.6	266.8	267.0	267.2	267.4	267.2
127.5°	280.3	281.0	281.7	282.4	282.8	282.8	282.9	283.0	283.0	283.1	283.0
130°	295.1	295.9	296.6	297.4	297.8	297.8	297.7	297.6	297.6	297.5	297.6
132.5°	309.6	310.2	310.9	311.5	311.8	311.8	311.7	311.6	311.6	311.5	311.6
135°	323.2	323.9	324.6	325.3	325.6	325.5	325.4	325.3	325.1	325.0	325.1
137.5°	336.0	336.7	337.4	338.1	338.4	338.3	338.1	337.9	337.7	337.5	337.7
140°	348.4	349.0	349.7	350.3	350.6	350.4	350.1	349.8	349.4	349.1	349.4
142.5°	360.0	360.5	361.1	361.6	361.9	361.7	361.4	361.0	360.7	360.3	360.7
145°	370.5	371.0	371.5	372.0	372.2	372.0	371.7	371.3	371.0	370.6	371.0
147.5°	380.1	380.4	380.8	381.1	381.3	381.2	380.9	380.6	380.3	380.0	380.3
150°	388.6	389.0	389.4	389.8	390.0	389.8	389.5	389.2	388.8	388.5	388.8
152.5°	396.4	396.8	397.3	397.7	397.9	397.7	397.2	396.7	396.2	395.7	396.2
155°	403.3	403.7	404.1	404.5	404.7	404.4	403.9	403.3	402.8	402.2	402.8
157.5°	409.3	409.8	410.3	410.8	411.0	410.7	410.2	409.6	409.1	408.5	409.1
160°	414.5	414.9	415.4	415.8	416.0	415.8	415.3	414.8	414.3	413.8	414.3
162.5°	419.3	419.8	420.3	420.8	421.0	420.7	420.1	419.4	418.8	418.2	418.8
165°	423.1	423.6	424.1	424.6	424.8	424.6	424.1	423.6	423.1	422.6	423.1
167.5°	426.5	427.0	427.5	428.0	428.2	427.9	427.3	426.6	426.0	425.4	426.0
170°	429.0	429.5	430.0	430.5	430.7	430.4	429.8	429.1	428.5	427.9	428.5
172.5°	430.9	431.4	431.9	432.4	432.6	432.3	431.7	431.0	430.4	429.8	430.4
175°	432.1	432.6	433.1	433.6	433.8	433.5	432.8	432.1	431.4	430.7	431.4
177.5°	432.4	432.9	433.4	433.9	434.1	433.8	433.2	432.5	431.9	431.3	431.9
180°	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3

TEST NUMBER: P998745

CATALOG NUMBER: SA2XXDIP-B675D330UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1360.6	1353.6	1347.7	1348.7	1353.6	1349.7	1339.8	1327.0	1322.1	1316.2	1322.1
5°	1442.4	1436.5	1424.7	1425.7	1422.7	1418.8	1403.0	1383.2	1383.2	1367.5	1365.5
7.5°	1523.3	1514.5	1506.6	1504.6	1493.7	1485.9	1472.0	1444.4	1433.6	1414.8	1404.0
10°	1614.1	1607.2	1598.3	1587.5	1581.6	1567.7	1545.0	1504.6	1484.9	1459.2	1440.5
12.5°	1705.9	1704.9	1685.1	1663.4	1662.5	1640.8	1625.0	1570.7	1544.1	1509.5	1465.1
15°	1764.1	1759.1	1748.3	1737.4	1740.4	1716.7	1681.2	1617.1	1599.3	1557.9	1510.5
17.5°	1763.1	1763.1	1760.1	1758.2	1755.2	1748.3	1728.6	1686.1	1657.5	1605.2	1560.8
20°	1706.9	1719.7	1722.6	1721.7	1731.5	1736.5	1735.5	1708.8	1686.1	1639.8	1594.4
22.5°	1594.4	1624.0	1636.8	1644.7	1665.4	1676.3	1701.9	1692.1	1686.1	1651.6	1613.1
25°	1489.8	1499.7	1538.1	1540.1	1568.7	1595.4	1621.0	1637.8	1659.5	1646.7	1614.1
27.5°	1354.6	1377.3	1404.9	1425.7	1431.6	1485.9	1528.3	1559.8	1609.2	1613.1	1602.3
30°	1201.7	1212.6	1257.9	1285.6	1317.1	1356.6	1417.8	1472.0	1516.4	1556.9	1570.7
32.5°	1015.2	1059.6	1086.3	1119.8	1147.4	1217.5	1292.5	1362.5	1413.8	1481.9	1511.5
35°	844.5	879.1	924.5	938.3	988.6	1047.8	1145.5	1235.2	1313.2	1382.3	1442.4
37.5°	703.5	731.1	779.4	801.1	830.7	906.7	988.6	1100.1	1193.8	1278.7	1353.6
40°	606.8	627.5	664.0	670.9	695.6	764.6	830.7	935.3	1059.6	1174.1	1256.0
42.5°	540.7	550.5	575.2	584.1	599.9	646.2	705.4	804.1	919.5	1037.9	1153.4
45°	493.3	500.2	515.0	522.9	542.6	563.4	611.7	690.6	781.4	900.8	1025.1
47.5°	450.9	459.8	465.7	470.6	481.5	504.2	535.7	593.9	680.8	790.3	910.7
50°	415.4	418.3	429.2	430.2	437.1	451.9	481.5	517.0	586.1	674.8	791.3
52.5°	379.8	382.8	389.7	396.6	399.6	411.4	431.2	460.8	512.1	582.1	685.7
55°	344.3	348.3	355.2	360.1	363.1	372.9	384.8	413.4	453.8	503.2	588.0
57.5°	308.8	317.7	319.7	322.6	327.6	338.4	349.3	366.0	397.6	443.0	505.2
60°	275.3	278.2	285.1	288.1	293.0	298.9	312.8	325.6	348.3	383.8	440.0
62.5°	240.7	247.6	250.6	253.6	257.5	264.4	273.3	287.1	306.8	335.5	379.8
65°	211.1	212.1	218.0	222.0	225.9	230.9	239.7	252.6	264.4	291.1	323.6
67.5°	182.5	184.5	186.5	190.4	195.4	200.3	208.2	215.1	229.9	247.6	273.3
70°	154.9	154.9	159.8	162.8	161.8	167.7	173.6	181.5	192.4	209.2	229.9
72.5°	130.2	129.2	133.2	134.2	136.2	140.1	144.0	151.9	157.9	170.7	186.5
75°	103.6	105.6	107.5	107.5	110.5	113.5	117.4	121.4	128.3	136.2	148.0
77.5°	81.9	81.9	83.9	84.8	87.8	86.8	90.8	94.7	99.6	106.6	115.4
80°	60.2	62.2	62.2	62.2	63.1	64.1	68.1	71.0	74.0	78.9	82.9
82.5°	42.4	42.4	44.4	44.4	44.4	46.4	46.4	47.4	49.3	52.3	55.3
85°	26.6	26.6	26.6	27.6	26.6	27.6	29.6	28.6	29.6	31.6	31.6
87.5°	12.8	12.8	12.8	12.8	12.8	13.8	12.8	13.8	14.8	14.8	14.8
90°	8.1	8.0	7.9	7.8	7.6	7.3	7.0	6.6	6.3	5.7	5.2
92.5°	8.3	8.2	8.1	8.1	8.0	7.9	7.8	7.6	7.5	7.3	7.1
95°	13.6	13.7	13.8	13.8	13.6	13.3	12.9	12.6	12.2	11.7	11.2
97.5°	17.1	17.0	16.9	16.9	16.8	16.6	16.4	16.2	16.0	14.9	13.7
100°	20.7	20.5	20.4	20.3	20.0	19.5	18.9	18.4	17.8	16.6	15.4
102.5°	22.4	22.2	22.0	21.9	21.5	20.8	20.0	19.3	18.5	31.1	43.8
105°	23.2	22.9	22.6	22.5	22.1	21.4	20.6	19.9	19.1	38.1	57.1
107.5°	23.8	23.5	23.2	23.1	22.7	22.0	21.2	20.5	19.7	43.1	66.5
110°	24.2	23.9	23.6	23.5	27.0	33.9	40.8	47.8	54.7	74.8	94.9

TEST NUMBER: P998745

CATALOG NUMBER: SA2XXDIP-B675D330UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	24.6	24.4	24.2	24.1	39.1	69.0	99.0	128.9	158.9	160.1	161.3
115°	35.6	40.7	45.7	48.2	64.3	96.5	128.6	160.8	193.0	191.3	189.5
117.5°	119.6	137.8	156.0	165.1	170.1	180.0	190.0	199.9	209.9	208.7	207.5
120°	209.6	218.9	228.3	233.0	232.6	231.8	230.9	230.1	229.3	228.0	226.8
122.5°	249.8	249.7	249.6	249.6	249.4	249.0	248.5	248.1	247.7	246.3	244.9
125°	267.0	266.8	266.6	266.5	266.3	265.8	265.3	264.8	264.3	263.0	261.7
127.5°	283.0	282.9	282.8	282.8	282.4	281.7	281.0	280.3	279.6	278.6	277.5
130°	297.6	297.7	297.8	297.8	297.4	296.6	295.9	295.1	294.3	293.5	292.8
132.5°	311.6	311.7	311.8	311.8	311.5	310.9	310.2	309.6	309.0	308.2	307.5
135°	325.3	325.4	325.5	325.6	325.3	324.6	323.9	323.2	322.5	321.9	321.3
137.5°	337.9	338.1	338.3	338.4	338.1	337.4	336.7	336.0	335.3	334.6	333.9
140°	349.8	350.1	350.4	350.6	350.3	349.7	349.0	348.4	347.8	347.0	346.3
142.5°	361.0	361.4	361.7	361.9	361.6	361.1	360.5	360.0	359.4	358.5	357.6
145°	371.3	371.7	372.0	372.2	372.0	371.5	371.0	370.5	370.0	368.8	367.6
147.5°	380.6	380.9	381.2	381.3	381.1	380.8	380.4	380.1	379.7	378.5	377.3
150°	389.2	389.5	389.8	390.0	389.8	389.4	389.0	388.6	388.2	387.1	386.0
152.5°	396.7	397.2	397.7	397.9	397.7	397.3	396.8	396.4	396.0	395.0	393.9
155°	403.3	403.9	404.4	404.7	404.5	404.1	403.7	403.3	402.9	402.1	401.2
157.5°	409.6	410.2	410.7	411.0	410.8	410.3	409.8	409.3	408.8	408.2	407.6
160°	414.8	415.3	415.8	416.0	415.8	415.4	414.9	414.5	414.1	413.7	413.3
162.5°	419.4	420.1	420.7	421.0	420.8	420.3	419.8	419.3	418.8	418.4	418.1
165°	423.6	424.1	424.6	424.8	424.6	424.1	423.6	423.1	422.6	422.4	422.2
167.5°	426.6	427.3	427.9	428.2	428.0	427.5	427.0	426.5	426.0	425.8	425.6
170°	429.1	429.8	430.4	430.7	430.5	430.0	429.5	429.0	428.5	428.4	428.2
172.5°	431.0	431.7	432.3	432.6	432.4	431.9	431.4	430.9	430.4	430.3	430.1
175°	432.1	432.8	433.5	433.8	433.6	433.1	432.6	432.1	431.6	431.5	431.3
177.5°	432.5	433.2	433.8	434.1	433.9	433.4	432.9	432.4	431.9	431.8	431.8
180°	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3

TEST NUMBER: P998745

CATALOG NUMBER: SA2XXDIP-B675D330UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1317.1	1312.2	1309.2	1311.2	1305.3	1290.5	1290.5	1295.4	1289.5	1283.6	1274.7
5°	1353.6	1343.8	1337.9	1336.9	1323.1	1299.4	1294.4	1289.5	1276.7	1262.9	1248.1
7.5°	1389.2	1371.4	1361.5	1354.6	1334.9	1304.3	1291.5	1280.6	1259.9	1239.2	1220.5
10°	1418.8	1393.1	1381.3	1370.4	1344.8	1306.3	1285.6	1265.8	1239.2	1212.6	1188.9
12.5°	1442.4	1412.8	1398.0	1382.3	1350.7	1300.4	1274.7	1243.1	1216.5	1181.0	1157.3
15°	1481.9	1420.7	1406.9	1392.1	1359.6	1290.5	1258.9	1223.4	1186.9	1139.5	1113.9
17.5°	1513.5	1431.6	1430.6	1399.0	1356.6	1286.6	1238.2	1191.8	1152.4	1105.0	1064.6
20°	1532.2	1448.4	1432.6	1400.0	1346.7	1259.9	1209.6	1158.3	1115.9	1058.6	1018.2
22.5°	1548.0	1472.0	1430.6	1391.1	1326.0	1251.0	1177.0	1128.7	1070.5	1008.3	969.8
25°	1553.9	1477.0	1433.6	1388.2	1311.2	1225.4	1141.5	1089.2	1024.1	967.9	915.6
27.5°	1554.9	1476.0	1422.7	1375.4	1290.5	1191.8	1106.0	1050.8	978.7	913.6	861.3
30°	1545.0	1465.1	1416.8	1365.5	1270.8	1161.3	1062.6	1001.4	924.5	859.3	805.1
32.5°	1515.5	1443.4	1404.0	1347.7	1245.1	1118.8	1021.2	953.1	872.2	808.0	755.8
35°	1466.1	1416.8	1373.4	1321.1	1211.6	1079.4	979.7	899.8	817.9	756.7	707.4
37.5°	1404.9	1378.3	1337.9	1286.6	1173.1	1043.8	933.3	844.5	762.7	703.5	655.1
40°	1322.1	1329.0	1289.5	1243.1	1127.7	995.5	873.2	788.3	711.4	656.1	608.7
42.5°	1232.3	1260.9	1238.2	1193.8	1077.4	942.2	828.8	735.0	660.0	602.8	563.4
45°	1135.6	1184.9	1171.1	1138.6	1025.1	886.0	765.6	674.8	608.7	553.5	519.0
47.5°	1030.0	1100.1	1100.1	1076.4	966.9	829.7	711.4	618.6	553.5	514.0	480.5
50°	922.5	1001.4	1014.2	998.5	901.8	765.6	645.3	561.4	505.2	466.7	442.0
52.5°	810.0	901.8	925.5	917.6	832.7	704.4	591.0	509.1	457.8	424.2	402.5
55°	702.5	809.0	834.7	837.6	758.7	637.4	530.8	458.8	409.4	386.8	368.0
57.5°	600.9	703.5	732.1	737.0	683.7	576.2	474.6	411.4	367.0	348.3	333.5
60°	514.0	599.9	637.4	648.2	601.8	505.2	422.3	361.1	327.6	309.8	296.0
62.5°	443.0	512.1	551.5	554.5	533.8	443.0	368.0	316.7	288.1	272.3	265.4
65°	373.9	436.1	459.8	471.6	454.8	383.8	317.7	275.3	252.6	238.8	231.9
67.5°	318.7	358.1	377.9	393.7	376.9	323.6	270.3	235.8	219.0	205.2	201.3
70°	261.5	294.0	308.8	324.6	309.8	269.3	230.9	199.3	184.5	173.6	168.7
72.5°	209.2	234.8	248.6	258.5	249.6	216.1	184.5	162.8	151.9	144.0	141.1
75°	165.8	183.5	191.4	198.3	194.4	168.7	149.0	131.2	121.4	114.4	112.5
77.5°	126.3	139.1	148.0	150.0	145.0	128.3	111.5	100.6	92.7	88.8	86.8
80°	89.8	97.7	102.6	105.6	100.6	93.7	81.9	74.0	67.1	62.2	61.2
82.5°	60.2	64.1	68.1	67.1	65.1	59.2	52.3	48.3	45.4	41.4	41.4
85°	34.5	35.5	37.5	38.5	37.5	33.5	29.6	27.6	25.7	22.7	22.7
87.5°	14.8	15.8	15.8	16.8	14.8	14.8	12.8	10.9	10.9	9.9	8.9
90°	4.6	4.1	3.8	3.4	2.6	1.9	1.1	0.3	1.1	1.9	2.6
92.5°	6.9	6.7	6.6	6.7	7.0	7.3	7.5	7.8	7.5	7.3	7.0
95°	10.7	10.2	10.0	11.1	13.4	15.7	18.0	20.3	18.0	15.7	13.4
97.5°	12.6	11.5	10.9	13.8	19.5	25.2	30.9	36.6	30.9	25.2	19.5
100°	14.3	13.1	12.5	17.3	26.8	36.3	45.9	55.4	45.9	36.3	26.8
102.5°	56.4	69.1	75.4	75.5	75.6	75.7	75.9	76.0	75.9	75.7	75.6
105°	76.0	95.0	104.5	103.5	101.4	99.3	97.2	95.1	97.2	99.3	101.4
107.5°	90.0	113.4	125.1	124.2	122.5	120.8	119.0	117.3	119.0	120.8	122.5
110°	115.0	135.1	145.1	144.4	142.9	141.5	140.0	138.6	140.0	141.5	142.9

TEST NUMBER: P998745

CATALOG NUMBER: SA2XXDIP-B675D330UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	162.4	163.6	164.2	163.6	162.3	161.1	159.8	158.6	159.8	161.1	162.3
115°	187.8	186.1	185.2	184.6	183.4	182.2	181.0	179.8	181.0	182.2	183.4
117.5°	206.4	205.2	204.6	203.9	202.5	201.1	199.7	198.3	199.7	201.1	202.5
120°	225.5	224.2	223.6	223.1	222.0	221.0	219.9	218.9	219.9	221.0	222.0
122.5°	243.6	242.2	241.5	240.9	239.8	238.7	237.6	236.5	237.6	238.7	239.8
125°	260.4	259.1	258.4	257.9	257.0	256.1	255.2	254.3	255.2	256.1	257.0
127.5°	276.5	275.4	274.9	274.4	273.5	272.5	271.6	270.6	271.6	272.5	273.5
130°	292.0	291.3	290.9	290.3	289.2	288.1	287.0	285.9	287.0	288.1	289.2
132.5°	306.7	306.0	305.6	305.1	304.2	303.3	302.4	301.5	302.4	303.3	304.2
135°	320.6	320.0	319.7	319.1	318.0	316.9	315.8	314.7	315.8	316.9	318.0
137.5°	333.2	332.5	332.2	331.8	330.9	330.1	329.2	328.4	329.2	330.1	330.9
140°	345.5	344.8	344.4	344.1	343.6	343.0	342.5	341.9	342.5	343.0	343.6
142.5°	356.7	355.8	355.3	355.1	354.6	354.1	353.6	353.1	353.6	354.1	354.6
145°	366.5	365.3	364.7	364.7	364.8	364.9	364.9	365.0	364.9	364.9	364.8
147.5°	376.2	375.0	374.4	374.5	374.7	374.9	375.1	375.3	375.1	374.9	374.7
150°	384.9	383.8	383.2	383.4	383.9	384.4	384.8	385.3	384.8	384.4	383.9
152.5°	392.9	391.8	391.3	391.6	392.1	392.7	393.2	393.8	393.2	392.7	392.1
155°	400.4	399.5	399.1	399.4	400.0	400.7	401.3	401.9	401.3	400.7	400.0
157.5°	406.9	406.3	406.0	406.3	406.8	407.4	407.9	408.5	407.9	407.4	406.8
160°	412.8	412.4	412.2	412.4	412.8	413.3	413.7	414.1	413.7	413.3	412.8
162.5°	417.7	417.4	417.2	417.4	417.8	418.3	418.7	419.1	418.7	418.3	417.8
165°	421.9	421.7	421.6	421.8	422.2	422.7	423.1	423.5	423.1	422.7	422.2
167.5°	425.4	425.2	425.1	425.3	425.7	426.1	426.5	426.9	426.5	426.1	425.7
170°	428.1	428.0	427.9	428.1	428.5	429.0	429.4	429.8	429.4	429.0	428.5
172.5°	430.0	429.9	429.8	430.0	430.4	430.8	431.2	431.6	431.2	430.8	430.4
175°	431.2	431.1	431.0	431.2	431.7	432.2	432.7	433.2	432.7	432.2	431.7
177.5°	431.7	431.6	431.6	431.8	432.3	432.8	433.3	433.8	433.3	432.8	432.3
180°	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3

TEST NUMBER: P998745

CATALOG NUMBER: SA2XXDIP-B675D330UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1269.8	1274.7	1273.7	1263.9	1253.0	1244.1	1227.4	1229.3	1223.4	1224.4	1230.3
5°	1238.2	1238.2	1234.3	1220.5	1202.7	1192.8	1174.1	1169.1	1157.3	1156.3	1155.3
7.5°	1204.7	1199.7	1194.8	1175.1	1153.4	1137.6	1111.9	1106.0	1094.2	1086.3	1082.3
10°	1165.2	1158.3	1148.4	1125.7	1099.1	1079.4	1052.7	1044.8	1022.1	1012.3	1006.4
12.5°	1121.8	1117.8	1102.1	1083.3	1039.9	1018.2	979.7	987.6	964.9	945.2	942.2
15°	1078.4	1063.6	1054.7	1024.1	971.8	962.0	931.4	915.6	894.9	879.1	879.1
17.5°	1036.0	1013.3	993.5	961.0	922.5	894.9	872.2	864.3	838.6	822.8	819.9
20°	979.7	954.1	949.1	902.8	876.1	845.5	823.8	804.1	785.4	778.4	773.5
22.5°	926.4	896.8	888.9	849.5	822.8	792.3	770.6	756.7	742.9	738.0	729.1
25°	869.2	851.5	839.6	797.2	767.6	739.0	724.2	714.3	701.5	700.5	694.6
27.5°	814.0	797.2	785.4	744.9	723.2	696.6	684.7	673.9	667.0	664.0	661.0
30°	766.6	747.9	734.0	704.4	677.8	656.1	646.2	639.3	635.4	630.5	629.5
32.5°	714.3	703.5	684.7	662.0	641.3	620.6	614.7	609.7	603.8	601.8	600.9
35°	669.9	655.1	643.3	617.6	608.7	591.0	584.1	580.1	572.2	570.3	568.3
37.5°	626.5	612.7	599.9	584.1	567.3	557.4	553.5	547.6	543.6	544.6	542.6
40°	583.1	572.2	562.4	545.6	535.7	530.8	522.9	517.0	515.0	516.0	515.0
42.5°	540.7	530.8	524.9	512.1	502.2	497.3	492.3	486.4	489.4	489.4	492.3
45°	502.2	493.3	489.4	479.5	473.6	465.7	460.8	459.8	463.7	462.7	462.7
47.5°	462.7	459.8	454.8	446.0	438.1	433.1	432.1	432.1	436.1	438.1	437.1
50°	432.1	426.2	420.3	413.4	407.5	405.5	402.5	404.5	408.5	408.5	410.4
52.5°	393.7	389.7	387.7	381.8	377.9	377.9	377.9	378.9	381.8	384.8	383.8
55°	360.1	357.2	355.2	352.2	347.3	348.3	347.3	349.3	352.2	355.2	357.2
57.5°	324.6	323.6	321.6	316.7	316.7	315.7	318.7	319.7	324.6	326.6	329.5
60°	293.0	290.1	290.1	286.1	286.1	286.1	289.1	292.0	296.0	297.0	298.9
62.5°	259.5	259.5	258.5	255.5	255.5	258.5	259.5	263.4	265.4	265.4	268.4
65°	227.9	226.9	225.9	226.9	227.9	227.9	230.9	232.8	234.8	235.8	236.8
67.5°	196.3	195.4	197.3	196.3	198.3	202.3	201.3	204.2	207.2	207.2	208.2
70°	166.7	168.7	167.7	169.7	168.7	170.7	173.6	174.6	174.6	175.6	178.6
72.5°	139.1	139.1	139.1	138.1	139.1	141.1	143.1	144.0	146.0	147.0	150.0
75°	112.5	112.5	110.5	112.5	112.5	114.4	116.4	116.4	116.4	118.4	121.4
77.5°	84.8	85.8	84.8	86.8	86.8	87.8	89.8	88.8	90.8	91.8	92.7
80°	62.2	61.2	61.2	61.2	62.2	62.2	64.1	65.1	65.1	68.1	66.1
82.5°	39.5	40.5	39.5	40.5	40.5	41.4	40.5	41.4	42.4	44.4	43.4
85°	22.7	21.7	21.7	22.7	21.7	21.7	22.7	21.7	22.7	21.7	22.7
87.5°	8.9	7.9	7.9	7.9	7.9	6.9	6.9	5.9	5.9	5.9	4.9
90°	3.4	3.8	4.1	4.6	5.2	5.7	6.3	6.6	7.0	7.3	7.6
92.5°	6.7	6.6	6.7	6.9	7.1	7.3	7.5	7.6	7.8	7.9	8.0
95°	11.1	10.0	10.2	10.7	11.2	11.7	12.2	12.6	12.9	13.3	13.6
97.5°	13.8	10.9	11.5	12.6	13.7	14.9	16.0	16.2	16.4	16.6	16.8
100°	17.3	12.5	13.1	14.3	15.4	16.6	17.8	18.4	18.9	19.5	20.0
102.5°	75.5	75.4	69.1	56.4	43.8	31.1	18.5	19.3	20.0	20.8	21.5
105°	103.5	104.5	95.0	76.0	57.1	38.1	19.1	19.9	20.6	21.4	22.1
107.5°	124.2	125.1	113.4	90.0	66.5	43.1	19.7	20.5	21.2	22.0	22.7
110°	144.4	145.1	135.1	115.0	94.9	74.8	54.7	47.8	40.8	33.9	27.0

TEST NUMBER: P998745

CATALOG NUMBER: SA2XXDIP-B675D330UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	163.6	164.2	163.6	162.4	161.3	160.1	158.9	128.9	99.0	69.0	39.1
115°	184.6	185.2	186.1	187.8	189.5	191.3	193.0	160.8	128.6	96.5	64.3
117.5°	203.9	204.6	205.2	206.4	207.5	208.7	209.9	199.9	190.0	180.0	170.1
120°	223.1	223.6	224.2	225.5	226.8	228.0	229.3	230.1	230.9	231.8	232.6
122.5°	240.9	241.5	242.2	243.6	244.9	246.3	247.7	248.1	248.5	249.0	249.4
125°	257.9	258.4	259.1	260.4	261.7	263.0	264.3	264.8	265.3	265.8	266.3
127.5°	274.4	274.9	275.4	276.5	277.5	278.6	279.6	280.3	281.0	281.7	282.4
130°	290.3	290.9	291.3	292.0	292.8	293.5	294.3	295.1	295.9	296.6	297.4
132.5°	305.1	305.6	306.0	306.7	307.5	308.2	309.0	309.6	310.2	310.9	311.5
135°	319.1	319.7	320.0	320.6	321.3	321.9	322.5	323.2	323.9	324.6	325.3
137.5°	331.8	332.2	332.5	333.2	333.9	334.6	335.3	336.0	336.7	337.4	338.1
140°	344.1	344.4	344.8	345.5	346.3	347.0	347.8	348.4	349.0	349.7	350.3
142.5°	355.1	355.3	355.8	356.7	357.6	358.5	359.4	360.0	360.5	361.1	361.6
145°	364.7	364.7	365.3	366.5	367.6	368.8	370.0	370.5	371.0	371.5	372.0
147.5°	374.5	374.4	375.0	376.2	377.3	378.5	379.7	380.1	380.4	380.8	381.1
150°	383.4	383.2	383.8	384.9	386.0	387.1	388.2	388.6	389.0	389.4	389.8
152.5°	391.6	391.3	391.8	392.9	393.9	395.0	396.0	396.4	396.8	397.3	397.7
155°	399.4	399.1	399.5	400.4	401.2	402.1	402.9	403.3	403.7	404.1	404.5
157.5°	406.3	406.0	406.3	406.9	407.6	408.2	408.8	409.3	409.8	410.3	410.8
160°	412.4	412.2	412.4	412.8	413.3	413.7	414.1	414.5	414.9	415.4	415.8
162.5°	417.4	417.2	417.4	417.7	418.1	418.4	418.8	419.3	419.8	420.3	420.8
165°	421.8	421.6	421.7	421.9	422.2	422.4	422.6	423.1	423.6	424.1	424.6
167.5°	425.3	425.1	425.2	425.4	425.6	425.8	426.0	426.5	427.0	427.5	428.0
170°	428.1	427.9	428.0	428.1	428.2	428.4	428.5	429.0	429.5	430.0	430.5
172.5°	430.0	429.8	429.9	430.0	430.1	430.3	430.4	430.9	431.4	431.9	432.4
175°	431.2	431.0	431.1	431.2	431.3	431.5	431.6	432.1	432.6	433.1	433.6
177.5°	431.8	431.6	431.6	431.7	431.8	431.8	431.9	432.4	432.9	433.4	433.9
180°	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3

TEST NUMBER: P998745

CATALOG NUMBER: SA2XXDIP-B675D330UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1223.4	1226.4	1219.5	1217.5	1219.5	1212.6	1214.5	1216.5	1216.5	1219.5	1221.4
5°	1152.4	1148.4	1141.5	1139.5	1137.6	1140.5	1138.6	1141.5	1142.5	1149.4	1150.4
7.5°	1082.3	1076.4	1070.5	1064.6	1062.6	1057.7	1062.6	1062.6	1069.5	1067.5	1072.5
10°	999.4	998.5	990.6	987.6	983.7	975.8	986.6	983.7	988.6	997.5	999.4
12.5°	938.3	927.4	932.4	918.5	923.5	915.6	916.6	916.6	924.5	925.5	923.5
15°	880.1	871.2	858.4	852.4	849.5	845.5	858.4	859.3	853.4	867.2	862.3
17.5°	820.9	820.9	809.0	806.1	798.2	802.1	800.1	801.1	799.2	809.0	814.0
20°	769.6	764.6	760.7	761.7	751.8	749.8	747.9	749.8	756.7	763.6	765.6
22.5°	728.1	725.2	715.3	717.3	709.4	712.3	710.4	715.3	716.3	716.3	723.2
25°	688.7	684.7	685.7	681.8	678.8	678.8	675.8	678.8	682.7	684.7	685.7
27.5°	659.1	656.1	651.2	648.2	650.2	645.3	649.2	652.2	652.2	650.2	652.2
30°	623.5	625.5	625.5	615.7	619.6	617.6	620.6	622.6	622.6	623.5	621.6
32.5°	599.9	593.9	593.0	592.0	592.0	588.0	588.0	591.0	592.0	593.0	595.9
35°	568.3	568.3	563.4	566.3	562.4	563.4	562.4	563.4	565.3	562.4	565.3
37.5°	539.7	540.7	538.7	540.7	541.7	539.7	537.7	541.7	539.7	539.7	537.7
40°	515.0	514.0	515.0	515.0	515.0	516.0	514.0	514.0	514.0	512.1	510.1
42.5°	494.3	488.4	490.4	491.3	488.4	488.4	489.4	488.4	491.3	485.4	485.4
45°	464.7	462.7	463.7	463.7	465.7	462.7	464.7	465.7	462.7	461.7	459.8
47.5°	438.1	440.0	438.1	440.0	440.0	442.0	438.1	439.0	440.0	436.1	433.1
50°	411.4	411.4	414.4	413.4	414.4	412.4	412.4	411.4	412.4	410.4	407.5
52.5°	386.8	383.8	388.7	387.7	386.8	385.8	384.8	385.8	383.8	381.8	381.8
55°	356.2	356.2	359.1	360.1	360.1	358.1	356.2	357.2	356.2	355.2	354.2
57.5°	331.5	327.6	329.5	330.5	330.5	327.6	329.5	327.6	327.6	328.5	325.6
60°	299.9	299.9	298.0	300.9	300.9	298.9	298.9	299.9	298.0	297.0	296.0
62.5°	266.4	267.4	270.3	271.3	272.3	270.3	268.4	269.3	269.3	266.4	267.4
65°	237.8	239.7	243.7	242.7	240.7	241.7	239.7	240.7	237.8	238.8	235.8
67.5°	210.2	209.2	210.2	210.2	212.1	211.1	209.2	209.2	208.2	211.1	208.2
70°	180.6	180.6	180.6	180.6	181.5	182.5	180.6	178.6	179.6	177.6	176.6
72.5°	150.0	151.0	150.0	151.9	149.0	151.0	151.0	150.0	149.0	149.0	149.0
75°	121.4	123.3	120.4	121.4	120.4	122.3	121.4	121.4	119.4	118.4	119.4
77.5°	92.7	93.7	91.8	92.7	91.8	92.7	92.7	91.8	91.8	91.8	91.8
80°	66.1	67.1	66.1	65.1	64.1	66.1	64.1	65.1	66.1	65.1	67.1
82.5°	42.4	42.4	41.4	42.4	40.5	40.5	41.4	41.4	40.5	42.4	40.5
85°	20.7	20.7	22.7	20.7	19.7	19.7	19.7	20.7	19.7	21.7	20.7
87.5°	4.9	3.9	4.9	4.9	3.9	3.9	4.9	3.9	4.9	5.9	3.9
90°	7.8	7.9	8.0	8.1	8.3	8.4	8.3	8.1	8.0	7.9	7.8
92.5°	8.1	8.1	8.2	8.3	8.3	8.4	8.3	8.3	8.2	8.1	8.1
95°	13.8	13.8	13.7	13.6	13.5	13.4	13.5	13.6	13.7	13.8	13.8
97.5°	16.9	16.9	17.0	17.1	17.1	17.2	17.1	17.1	17.0	16.9	16.9
100°	20.3	20.4	20.5	20.7	20.8	21.0	20.8	20.7	20.5	20.4	20.3
102.5°	21.9	22.0	22.2	22.4	22.6	22.8	22.6	22.4	22.2	22.0	21.9
105°	22.5	22.6	22.9	23.2	23.5	23.8	23.5	23.2	22.9	22.6	22.5
107.5°	23.1	23.2	23.5	23.8	24.1	24.4	24.1	23.8	23.5	23.2	23.1
110°	23.5	23.6	23.9	24.2	24.4	24.7	24.4	24.2	23.9	23.6	23.5

TEST NUMBER: P998745

CATALOG NUMBER: SA2XXDIP-B675D330UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	24.1	24.2	24.4	24.6	24.8	25.0	24.8	24.6	24.4	24.2	24.1
115°	48.2	45.7	40.7	35.6	30.6	25.6	30.6	35.6	40.7	45.7	48.2
117.5°	165.1	156.0	137.8	119.6	101.4	83.2	101.4	119.6	137.8	156.0	165.1
120°	233.0	228.3	218.9	209.6	200.2	190.8	200.2	209.6	218.9	228.3	233.0
122.5°	249.6	249.6	249.7	249.8	249.8	249.9	249.8	249.8	249.7	249.6	249.6
125°	266.5	266.6	266.8	267.0	267.2	267.4	267.2	267.0	266.8	266.6	266.5
127.5°	282.8	282.8	282.9	283.0	283.0	283.1	283.0	283.0	282.9	282.8	282.8
130°	297.8	297.8	297.7	297.6	297.6	297.5	297.6	297.6	297.7	297.8	297.8
132.5°	311.8	311.8	311.7	311.6	311.6	311.5	311.6	311.6	311.7	311.8	311.8
135°	325.6	325.5	325.4	325.3	325.1	325.0	325.1	325.3	325.4	325.5	325.6
137.5°	338.4	338.3	338.1	337.9	337.7	337.5	337.7	337.9	338.1	338.3	338.4
140°	350.6	350.4	350.1	349.8	349.4	349.1	349.4	349.8	350.1	350.4	350.6
142.5°	361.9	361.7	361.4	361.0	360.7	360.3	360.7	361.0	361.4	361.7	361.9
145°	372.2	372.0	371.7	371.3	371.0	370.6	371.0	371.3	371.7	372.0	372.2
147.5°	381.3	381.2	380.9	380.6	380.3	380.0	380.3	380.6	380.9	381.2	381.3
150°	390.0	389.8	389.5	389.2	388.8	388.5	388.8	389.2	389.5	389.8	390.0
152.5°	397.9	397.7	397.2	396.7	396.2	395.7	396.2	396.7	397.2	397.7	397.9
155°	404.7	404.4	403.9	403.3	402.8	402.2	402.8	403.3	403.9	404.4	404.7
157.5°	411.0	410.7	410.2	409.6	409.1	408.5	409.1	409.6	410.2	410.7	411.0
160°	416.0	415.8	415.3	414.8	414.3	413.8	414.3	414.8	415.3	415.8	416.0
162.5°	421.0	420.7	420.1	419.4	418.8	418.2	418.8	419.4	420.1	420.7	421.0
165°	424.8	424.6	424.1	423.6	423.1	422.6	423.1	423.6	424.1	424.6	424.8
167.5°	428.2	427.9	427.3	426.6	426.0	425.4	426.0	426.6	427.3	427.9	428.2
170°	430.7	430.4	429.8	429.1	428.5	427.9	428.5	429.1	429.8	430.4	430.7
172.5°	432.6	432.3	431.7	431.0	430.4	429.8	430.4	431.0	431.7	432.3	432.6
175°	433.8	433.5	432.8	432.1	431.4	430.7	431.4	432.1	432.8	433.5	433.8
177.5°	434.1	433.8	433.2	432.5	431.9	431.3	431.9	432.5	433.2	433.8	434.1
180°	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3

TEST NUMBER: P998745

CATALOG NUMBER: SA2XXDIP-B675D330UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1218.5	1226.4	1223.4	1212.6	1225.4	1225.4	1234.3	1234.3	1245.1	1249.1	1255.0
5°	1149.4	1155.3	1160.3	1155.3	1164.2	1178.0	1185.9	1192.8	1207.6	1213.5	1222.4
7.5°	1075.4	1086.3	1091.2	1091.2	1106.0	1121.8	1137.6	1147.4	1168.2	1176.1	1184.9
10°	1003.4	1016.2	1026.1	1025.1	1049.8	1059.6	1079.4	1102.1	1122.8	1134.6	1147.4
12.5°	927.4	934.3	948.1	967.9	973.8	991.6	1014.2	1042.9	1080.4	1091.2	1109.9
15°	864.3	883.0	893.9	902.8	916.6	933.3	958.0	985.6	1023.1	1046.8	1066.5
17.5°	811.0	835.7	842.6	840.6	858.4	884.0	912.6	933.3	966.9	995.5	1014.2
20°	767.6	777.5	789.3	794.2	808.0	835.7	863.3	887.0	914.6	937.3	959.0
22.5°	724.2	732.1	741.9	750.8	761.7	777.5	804.1	833.7	860.3	882.0	906.7
25°	688.7	693.6	702.5	709.4	721.2	732.1	750.8	783.4	814.9	827.8	849.5
27.5°	654.1	658.1	664.0	671.9	677.8	688.7	705.4	732.1	764.6	777.5	807.1
30°	623.5	626.5	632.4	636.4	639.3	652.2	665.0	685.7	710.4	728.1	749.8
32.5°	594.9	597.9	603.8	604.8	608.7	615.7	627.5	646.2	667.9	682.7	701.5
35°	563.4	565.3	571.3	573.2	576.2	582.1	591.0	604.8	624.5	635.4	652.2
37.5°	538.7	537.7	541.7	544.6	548.6	551.5	554.5	568.3	583.1	593.0	605.8
40°	512.1	510.1	511.1	515.0	517.0	520.9	520.9	534.7	544.6	552.5	562.4
42.5°	485.4	484.4	482.5	484.4	486.4	487.4	488.4	498.2	508.1	515.0	525.9
45°	458.8	457.8	455.8	456.8	456.8	458.8	461.7	465.7	472.6	478.5	484.4
47.5°	434.1	432.1	429.2	428.2	430.2	430.2	430.2	434.1	441.0	443.0	448.9
50°	408.5	405.5	401.6	399.6	399.6	398.6	400.6	401.6	407.5	409.4	414.4
52.5°	380.8	378.9	374.9	371.0	372.0	370.0	371.0	372.0	373.9	376.9	379.8
55°	353.2	349.3	346.3	345.3	342.4	342.4	339.4	343.3	342.4	343.3	347.3
57.5°	326.6	322.6	317.7	315.7	312.8	311.8	309.8	308.8	309.8	312.8	315.7
60°	295.0	293.0	290.1	287.1	285.1	282.2	280.2	280.2	279.2	279.2	280.2
62.5°	264.4	263.4	259.5	258.5	256.5	254.5	251.6	249.6	249.6	251.6	252.6
65°	234.8	233.8	230.9	229.9	224.9	223.0	222.0	221.0	219.0	219.0	219.0
67.5°	207.2	204.2	204.2	199.3	195.4	193.4	191.4	190.4	190.4	190.4	191.4
70°	176.6	176.6	173.6	170.7	166.7	167.7	164.8	161.8	161.8	159.8	160.8
72.5°	147.0	146.0	143.1	142.1	139.1	136.2	134.2	136.2	133.2	132.2	133.2
75°	118.4	117.4	115.4	113.5	114.4	111.5	108.5	107.5	107.5	105.6	105.6
77.5°	90.8	92.7	88.8	87.8	85.8	83.9	82.9	81.9	81.9	81.9	83.9
80°	63.1	64.1	64.1	62.2	63.1	60.2	60.2	60.2	57.2	58.2	59.2
82.5°	40.5	40.5	39.5	40.5	39.5	39.5	38.5	38.5	37.5	37.5	38.5
85°	22.7	21.7	20.7	22.7	21.7	21.7	20.7	20.7	20.7	20.7	20.7
87.5°	4.9	5.9	5.9	5.9	5.9	6.9	6.9	6.9	7.9	7.9	7.9
90°	7.6	7.3	7.0	6.6	6.3	5.7	5.2	4.6	4.1	3.8	3.4
92.5°	8.0	7.9	7.8	7.6	7.5	7.3	7.1	6.9	6.7	6.6	6.7
95°	13.6	13.3	12.9	12.6	12.2	11.7	11.2	10.7	10.2	10.0	11.1
97.5°	16.8	16.6	16.4	16.2	16.0	14.9	13.7	12.6	11.5	10.9	13.8
100°	20.0	19.5	18.9	18.4	17.8	16.6	15.4	14.3	13.1	12.5	17.3
102.5°	21.5	20.8	20.0	19.3	18.5	31.1	43.8	56.4	69.1	75.4	75.5
105°	22.1	21.4	20.6	19.9	19.1	38.1	57.1	76.0	95.0	104.5	103.5
107.5°	22.7	22.0	21.2	20.5	19.7	43.1	66.5	90.0	113.4	125.1	124.2
110°	27.0	33.9	40.8	47.8	54.7	74.8	94.9	115.0	135.1	145.1	144.4

TEST NUMBER: P998745

CATALOG NUMBER: SA2XXDIP-B675D330UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	39.1	69.0	99.0	128.9	158.9	160.1	161.3	162.4	163.6	164.2	163.6
115°	64.3	96.5	128.6	160.8	193.0	191.3	189.5	187.8	186.1	185.2	184.6
117.5°	170.1	180.0	190.0	199.9	209.9	208.7	207.5	206.4	205.2	204.6	203.9
120°	232.6	231.8	230.9	230.1	229.3	228.0	226.8	225.5	224.2	223.6	223.1
122.5°	249.4	249.0	248.5	248.1	247.7	246.3	244.9	243.6	242.2	241.5	240.9
125°	266.3	265.8	265.3	264.8	264.3	263.0	261.7	260.4	259.1	258.4	257.9
127.5°	282.4	281.7	281.0	280.3	279.6	278.6	277.5	276.5	275.4	274.9	274.4
130°	297.4	296.6	295.9	295.1	294.3	293.5	292.8	292.0	291.3	290.9	290.3
132.5°	311.5	310.9	310.2	309.6	309.0	308.2	307.5	306.7	306.0	305.6	305.1
135°	325.3	324.6	323.9	323.2	322.5	321.9	321.3	320.6	320.0	319.7	319.1
137.5°	338.1	337.4	336.7	336.0	335.3	334.6	333.9	333.2	332.5	332.2	331.8
140°	350.3	349.7	349.0	348.4	347.8	347.0	346.3	345.5	344.8	344.4	344.1
142.5°	361.6	361.1	360.5	360.0	359.4	358.5	357.6	356.7	355.8	355.3	355.1
145°	372.0	371.5	371.0	370.5	370.0	368.8	367.6	366.5	365.3	364.7	364.7
147.5°	381.1	380.8	380.4	380.1	379.7	378.5	377.3	376.2	375.0	374.4	374.5
150°	389.8	389.4	389.0	388.6	388.2	387.1	386.0	384.9	383.8	383.2	383.4
152.5°	397.7	397.3	396.8	396.4	396.0	395.0	393.9	392.9	391.8	391.3	391.6
155°	404.5	404.1	403.7	403.3	402.9	402.1	401.2	400.4	399.5	399.1	399.4
157.5°	410.8	410.3	409.8	409.3	408.8	408.2	407.6	406.9	406.3	406.0	406.3
160°	415.8	415.4	414.9	414.5	414.1	413.7	413.3	412.8	412.4	412.2	412.4
162.5°	420.8	420.3	419.8	419.3	418.8	418.4	418.1	417.7	417.4	417.2	417.4
165°	424.6	424.1	423.6	423.1	422.6	422.4	422.2	421.9	421.7	421.6	421.8
167.5°	428.0	427.5	427.0	426.5	426.0	425.8	425.6	425.4	425.2	425.1	425.3
170°	430.5	430.0	429.5	429.0	428.5	428.4	428.2	428.1	428.0	427.9	428.1
172.5°	432.4	431.9	431.4	430.9	430.4	430.3	430.1	430.0	429.9	429.8	430.0
175°	433.6	433.1	432.6	432.1	431.6	431.5	431.3	431.2	431.1	431.0	431.2
177.5°	433.9	433.4	432.9	432.4	431.9	431.8	431.8	431.7	431.6	431.6	431.8
180°	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3	432.3

TEST NUMBER: P998745

CATALOG NUMBER: SA2XXDIP-B675D330UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1283.6	1283.6	1283.6	1283.6
2.5°	1259.9	1259.9	1274.7	1290.5
5°	1232.3	1239.2	1262.9	1284.6
7.5°	1205.7	1217.5	1247.1	1274.7
10°	1173.1	1188.9	1225.4	1257.9
12.5°	1141.5	1156.3	1198.7	1235.2
15°	1097.1	1115.9	1161.3	1206.6
17.5°	1052.7	1071.5	1126.7	1180.0
20°	1000.4	1025.1	1087.3	1158.3
22.5°	952.1	982.7	1051.7	1109.0
25°	898.8	946.2	1010.3	1084.3
27.5°	851.5	898.8	963.9	1038.9
30°	798.2	846.5	913.6	982.7
32.5°	746.9	791.3	856.4	941.2
35°	693.6	736.0	799.2	885.0
37.5°	645.3	686.7	755.8	834.7
40°	597.9	641.3	700.5	779.4
42.5°	553.5	592.0	645.3	724.2
45°	513.0	540.7	590.0	664.0
47.5°	470.6	495.3	540.7	614.7
50°	431.2	451.9	491.3	560.4
52.5°	392.7	410.4	446.9	502.2
55°	358.1	374.9	401.6	455.8
57.5°	322.6	335.5	361.1	404.5
60°	288.1	299.9	320.7	356.2
62.5°	253.6	263.4	283.2	311.8
65°	223.0	230.9	245.7	270.3
67.5°	193.4	198.3	210.2	229.9
70°	164.8	168.7	178.6	194.4
72.5°	134.2	138.1	149.0	159.8
75°	108.5	109.5	117.4	126.3
77.5°	84.8	83.9	89.8	96.7
80°	58.2	61.2	66.1	69.1
82.5°	39.5	40.5	42.4	44.4
85°	21.7	22.7	22.7	25.7
87.5°	8.9	9.9	9.9	10.9
90°	2.6	1.9	1.1	0.3
92.5°	7.0	7.3	7.5	7.8
95°	13.4	15.7	18.0	20.3
97.5°	19.5	25.2	30.9	36.6
100°	26.8	36.3	45.9	55.4
102.5°	75.6	75.7	75.9	76.0
105°	101.4	99.3	97.2	95.1
107.5°	122.5	120.8	119.0	117.3
110°	142.9	141.5	140.0	138.6

TEST NUMBER: P998745

CATALOG NUMBER: SA2XXDIP-B675D330UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	162.3	161.1	159.8	158.6
115°	183.4	182.2	181.0	179.8
117.5°	202.5	201.1	199.7	198.3
120°	222.0	221.0	219.9	218.9
122.5°	239.8	238.7	237.6	236.5
125°	257.0	256.1	255.2	254.3
127.5°	273.5	272.5	271.6	270.6
130°	289.2	288.1	287.0	285.9
132.5°	304.2	303.3	302.4	301.5
135°	318.0	316.9	315.8	314.7
137.5°	330.9	330.1	329.2	328.4
140°	343.6	343.0	342.5	341.9
142.5°	354.6	354.1	353.6	353.1
145°	364.8	364.9	364.9	365.0
147.5°	374.7	374.9	375.1	375.3
150°	383.9	384.4	384.8	385.3
152.5°	392.1	392.7	393.2	393.8
155°	400.0	400.7	401.3	401.9
157.5°	406.8	407.4	407.9	408.5
160°	412.8	413.3	413.7	414.1
162.5°	417.8	418.3	418.7	419.1
165°	422.2	422.7	423.1	423.5
167.5°	425.7	426.1	426.5	426.9
170°	428.5	429.0	429.4	429.8
172.5°	430.4	430.8	431.2	431.6
175°	431.7	432.2	432.7	433.2
177.5°	432.3	432.8	433.3	433.8
180°	432.3	432.3	432.3	432.3

TEST NUMBER: P998745

CATALOG NUMBER: SA2XXDIP-B675D330UB2750-4F0-XX-W2A-A_5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.93	18.94	18.71	19.74	20.71	15.42	16.43	16.20	17.23	18.21
	3H	18.75	19.66	19.55	20.47	21.47	16.78	17.69	17.57	18.49	19.50
	4H	18.93	19.78	19.74	20.60	21.61	17.25	18.10	18.06	18.92	19.93
	6H	18.98	19.77	19.81	20.59	21.62	17.56	18.35	18.39	19.17	20.20
	8H	18.96	19.71	19.80	20.56	21.58	17.65	18.40	18.49	19.24	20.27
	12H	18.93	19.64	19.77	20.48	21.53	17.70	18.41	18.54	19.25	20.30
4H	2H	17.99	18.84	18.81	19.66	20.67	15.89	16.74	16.70	17.56	18.57
	3H	18.98	19.69	19.81	20.54	21.57	17.36	18.07	18.19	18.92	19.95
	4H	19.27	19.91	20.11	20.76	21.82	17.90	18.55	18.74	19.39	20.45
	6H	19.40	19.96	20.26	20.83	21.90	18.29	18.85	19.15	19.72	20.78
	8H	19.41	19.92	20.27	20.79	21.87	18.40	18.92	19.26	19.79	20.86
	12H	19.38	19.84	20.26	20.73	21.81	18.47	18.93	19.35	19.82	20.90
8H	4H	19.29	19.80	20.15	20.67	21.75	18.06	18.57	18.92	19.44	20.52
	6H	19.47	19.90	20.36	20.81	21.88	18.50	18.92	19.38	19.83	20.91
	8H	19.50	19.88	20.40	20.78	21.88	18.65	19.03	19.55	19.93	21.02
	12H	19.49	19.83	20.39	20.72	21.87	18.75	19.08	19.65	19.97	21.12
12H	4H	19.25	19.72	20.13	20.60	21.68	18.04	18.50	18.92	19.39	20.47
	6H	19.45	19.83	20.35	20.73	21.83	18.50	18.88	19.40	19.78	20.87
	8H	19.49	19.82	20.39	20.72	21.86	18.66	18.99	19.56	19.89	21.04