

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998864

Luminaire Tested: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998864
REPORT IS A COMBINATION OF REPORTS P984610 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_4000K
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5745.0 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998864

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P998864

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49
2	90	83	77	72	83	77	72	68	66	62	59	55	53	50	46	44	42
3	83	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32
5	70	58	51	45	64	54	47	42	47	42	37	40	36	33	33	30	28
6	64	53	45	39	59	49	42	37	43	37	33	36	32	29	31	27	25
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	23	20
9	52	40	32	27	48	37	31	26	33	27	24	28	24	21	24	21	18
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21015	21015	21015	21015
5°	21065	22407	21146	17826
10°	20820	24460	20951	14697
15°	20316	25800	20597	12380
20°	19999	24224	19999	10760
25°	19360	20811	19448	9622
30°	18312	16359	18661	8716
35°	17383	11312	17674	7975
40°	16315	8542	16501	7384
45°	14998	7019	15244	6746
50°	13860	6160	13884	6174
55°	12561	5249	12644	5555
60°	11179	4385	11334	4849
65°	9940	3566	10121	4141
70°	8705	2799	8926	3340
75°	7306	2031	7591	2421
80°	5700	1287	6108	1438
85°	3743	649	4040	480

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 21722 cd/sqm

TEST NUMBER: P998864

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.4	2.2
10°-20°	368.0	6.4
20°-30°	534.1	9.3
30°-40°	563.1	9.8
40°-50°	498.3	8.7
50°-60°	397.9	6.9
60°-70°	270.2	4.7
70°-80°	138.3	2.4
80°-90°	34.4	0.6
90°-100°	31.7	0.6
100°-110°	118.0	2.1
110°-120°	313.0	5.4
120°-130°	519.1	9.0
130°-140°	551.4	9.6
140°-150°	512.4	8.9
150°-160°	412.0	7.2
160°-170°	265.5	4.6
170°-180°	91.4	1.6
0°-30°	1028.6	17.9
0°-40°	1591.7	27.7
0°-60°	2487.8	43.3
0°-90°	2930.7	51.0
90°-120°	462.7	8.1
90°-150°	2045.5	35.6
90°-180°	2814.0	49.0
0°-180°	5745.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1328	1328	1328	1328	1328	
5°	1329	1483	1334	1180	1329	126
15°	1248	1822	1265	874	1248	352
25°	1121	1518	1126	702	1121	513
35°	915	826	931	583	915	573
45°	687	498	698	479	687	533
55°	471	350	474	370	471	421
65°	280	215	285	250	280	278
75°	131	106	136	126	131	140
85°	26	28	29	20	26	31
90°	1	19	1	19	1	4
95°	45	30	45	30	45	53
105°	211	53	211	53	211	226
115°	399	57	399	57	399	393
125°	565	594	565	594	565	504
135°	699	722	699	722	699	540
145°	811	823	811	823	811	507
155°	893	893	893	893	893	411
165°	940	938	940	938	940	266
175°	962	956	962	956	962	92
180°	960	960	960	960	960	

TEST NUMBER: P998864

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1334.7	1337.8	1342.9	1343.9	1354.1	1362.3	1371.4	1371.4	1374.5	1373.5	1365.3
5°	1328.6	1337.8	1351.0	1362.3	1380.6	1388.8	1401.0	1410.2	1418.4	1424.5	1423.5
7.5°	1318.4	1334.7	1354.1	1375.5	1400.0	1414.3	1431.6	1448.0	1459.2	1469.4	1476.5
10°	1301.0	1328.6	1355.1	1383.7	1415.3	1434.7	1455.1	1476.5	1493.9	1513.3	1531.6
12.5°	1277.6	1317.4	1350.0	1387.8	1426.5	1448.0	1480.6	1496.9	1530.6	1579.6	1592.9
15°	1248.0	1302.0	1332.7	1380.6	1431.6	1449.0	1493.9	1520.4	1589.8	1620.4	1657.2
17.5°	1220.4	1280.6	1321.4	1376.5	1426.5	1460.2	1504.1	1558.2	1616.3	1660.2	1701.0
20°	1198.0	1256.1	1305.1	1366.3	1429.6	1472.5	1518.4	1583.7	1646.9	1691.8	1723.5
22.5°	1146.9	1221.4	1278.6	1346.9	1423.5	1482.7	1526.5	1598.0	1666.3	1693.9	1721.4
25°	1121.4	1185.7	1252.0	1329.6	1419.4	1489.8	1527.6	1607.2	1667.4	1677.6	1683.7
27.5°	1074.5	1146.9	1224.5	1313.3	1418.4	1477.6	1525.5	1598.0	1645.9	1638.8	1620.4
30°	1016.3	1105.1	1190.8	1286.7	1404.1	1468.4	1513.3	1579.6	1604.1	1567.4	1534.7
32.5°	973.5	1057.1	1152.0	1263.3	1387.8	1449.0	1492.9	1544.9	1550.0	1483.7	1428.6
35°	915.3	1008.2	1115.3	1232.7	1360.2	1415.3	1456.1	1487.8	1463.3	1370.4	1305.1
37.5°	863.3	955.1	1069.4	1188.8	1322.5	1376.5	1409.2	1414.3	1354.1	1272.5	1176.5
40°	806.1	901.0	1020.4	1145.9	1280.6	1327.6	1348.0	1332.7	1245.9	1151.0	1039.8
42.5°	749.0	842.9	971.4	1100.0	1227.6	1267.4	1275.5	1233.7	1127.6	1016.3	887.8
45°	686.7	784.7	913.3	1042.9	1166.3	1188.8	1189.8	1129.6	1004.1	887.8	768.4
47.5°	635.7	726.5	854.1	983.7	1087.8	1103.1	1096.9	1027.6	890.8	760.2	656.1
50°	579.6	666.3	792.9	920.4	1009.2	1013.3	998.0	899.0	765.3	645.9	563.3
52.5°	519.4	607.1	723.5	845.9	925.5	919.4	889.8	783.7	658.2	559.2	495.9
55°	471.4	549.0	658.2	777.6	833.7	816.3	783.7	675.5	576.5	492.9	437.8
57.5°	418.4	486.7	593.9	698.0	730.6	714.3	681.6	580.6	488.8	425.5	388.8
60°	368.4	430.6	524.5	611.2	636.7	619.4	581.6	490.8	424.5	371.4	343.9
62.5°	322.5	376.5	455.1	534.7	544.9	527.6	494.9	421.4	364.3	322.5	302.0
65°	279.6	330.6	393.9	454.1	463.3	444.9	411.2	358.2	310.2	283.7	264.3
67.5°	237.8	278.6	334.7	378.6	383.7	366.3	338.8	295.9	266.3	237.8	223.5
70°	201.0	231.6	275.5	311.2	313.3	296.9	282.7	243.9	221.4	201.0	189.8
72.5°	165.3	186.7	220.4	246.9	248.0	237.8	224.5	200.0	180.6	166.3	155.1
75°	130.6	149.0	169.4	192.9	191.8	183.7	173.5	158.2	141.8	132.7	127.6
77.5°	100.0	111.2	127.6	142.9	142.9	138.8	132.7	121.4	111.2	102.0	96.9
80°	71.4	78.6	91.8	96.9	99.0	98.0	92.9	84.7	80.6	73.5	71.4
82.5°	45.9	51.0	57.1	62.2	65.3	63.3	62.2	58.2	52.0	50.0	48.0
85°	26.5	28.6	31.6	34.7	35.7	34.7	36.7	33.7	30.6	30.6	29.6
87.5°	11.2	12.2	14.3	14.3	15.3	15.3	14.3	15.3	15.3	14.3	13.3
90°	0.7	2.4	4.1	5.8	7.5	8.3	8.9	10.2	11.4	12.7	13.9
92.5°	17.4	16.8	16.2	15.5	14.9	14.6	14.8	15.3	15.8	16.2	16.7
95°	45.2	40.1	35.0	29.9	24.8	22.2	22.7	23.8	24.9	26.0	27.1
97.5°	81.3	68.6	56.0	43.3	30.6	24.3	25.5	28.0	30.5	32.9	35.4
100°	122.9	101.8	80.6	59.5	38.4	27.8	29.1	31.7	34.4	37.0	39.6
102.5°	168.8	168.5	168.2	167.9	167.6	167.4	153.4	125.3	97.2	69.1	41.0
105°	211.2	215.8	220.4	225.1	229.7	232.0	210.9	168.8	126.7	84.5	42.4
107.5°	260.5	264.4	268.2	272.1	276.0	277.9	251.9	199.9	147.8	95.8	43.8
110°	307.7	310.9	314.2	317.4	320.7	322.3	300.0	255.4	210.8	166.2	121.6

TEST NUMBER: P998864

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	352.2	355.0	357.8	360.5	363.3	364.7	363.4	360.8	358.1	355.5	352.9
115°	399.4	402.0	404.6	407.3	409.9	411.2	413.1	417.0	420.9	424.7	428.6
117.5°	440.4	443.5	446.6	449.7	452.8	454.3	455.6	458.2	460.9	463.5	466.1
120°	486.2	488.5	490.9	493.2	495.5	496.7	498.1	500.9	503.6	506.4	509.2
122.5°	525.1	527.6	530.1	532.6	535.1	536.3	537.8	540.9	544.0	547.0	550.1
125°	564.7	566.7	568.7	570.8	572.8	573.8	575.3	578.2	581.1	584.1	587.0
127.5°	600.9	603.1	605.2	607.4	609.5	610.6	611.8	614.1	616.4	618.7	621.0
130°	634.9	637.4	639.8	642.3	644.8	646.0	646.8	648.5	650.2	651.9	653.6
132.5°	669.6	671.6	673.6	675.7	677.7	678.7	679.5	681.2	682.9	684.6	686.3
135°	698.8	701.3	703.7	706.2	708.7	709.9	710.6	712.0	713.4	714.8	716.2
137.5°	729.4	731.2	733.1	734.9	736.8	737.7	738.5	740.0	741.5	743.1	744.6
140°	759.2	760.4	761.7	762.9	764.2	764.8	765.6	767.3	769.0	770.7	772.4
142.5°	784.2	785.3	786.4	787.5	788.6	789.1	790.1	792.1	794.1	796.1	798.1
145°	810.6	810.4	810.3	810.1	810.0	809.9	811.2	813.8	816.5	819.1	821.7
147.5°	833.6	833.1	832.7	832.2	831.7	831.5	832.8	835.4	838.1	840.7	843.3
150°	855.8	854.7	853.6	852.5	851.4	850.9	852.1	854.6	857.1	859.5	862.0
152.5°	874.5	873.3	872.1	870.8	869.6	869.0	870.2	872.5	874.8	877.1	879.4
155°	892.6	891.2	889.8	888.4	887.0	886.3	887.2	889.1	891.0	892.8	894.7
157.5°	907.2	906.0	904.7	903.5	902.2	901.6	902.3	903.7	905.1	906.5	907.9
160°	919.7	918.8	917.8	916.9	916.0	915.5	916.0	916.9	917.8	918.8	919.7
162.5°	930.8	929.9	928.9	928.0	927.1	926.6	927.0	927.8	928.5	929.3	930.1
165°	940.5	939.6	938.7	937.8	936.9	936.4	936.6	937.1	937.5	938.0	938.4
167.5°	948.2	947.3	946.3	945.4	944.5	944.0	944.2	944.7	945.2	945.6	946.1
170°	954.4	953.5	952.6	951.7	950.8	950.3	950.4	950.7	951.0	951.3	951.6
172.5°	958.6	957.7	956.7	955.8	954.9	954.4	954.6	954.9	955.2	955.5	955.8
175°	962.1	961.0	959.9	958.8	957.7	957.2	957.4	957.7	958.0	958.3	958.6
177.5°	963.4	962.3	961.3	960.2	959.1	958.6	958.7	958.8	959.0	959.1	959.3
180°	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0

TEST NUMBER: P998864

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1379.6	1380.6	1382.7	1392.9	1398.0	1399.0	1394.9	1404.1	1407.2	1404.1	1402.0
5°	1444.9	1451.0	1463.3	1476.5	1475.5	1476.5	1482.7	1488.8	1490.8	1482.7	1485.7
7.5°	1502.1	1514.3	1527.6	1548.0	1548.0	1558.2	1562.3	1567.4	1579.6	1573.5	1571.4
10°	1567.4	1583.7	1608.2	1640.8	1641.8	1652.1	1662.3	1678.6	1683.7	1679.6	1681.6
12.5°	1649.0	1680.6	1682.7	1718.4	1734.7	1736.7	1753.1	1750.0	1760.2	1760.2	1777.6
15°	1684.7	1733.7	1761.2	1795.9	1806.1	1793.9	1807.2	1821.4	1822.5	1822.5	1821.4
17.5°	1749.0	1768.4	1795.9	1814.3	1818.4	1818.4	1819.4	1825.5	1821.4	1813.3	1819.4
20°	1762.3	1770.4	1780.6	1778.6	1780.6	1770.4	1760.2	1750.0	1751.0	1745.9	1761.2
22.5°	1737.8	1735.7	1712.3	1696.9	1696.9	1676.5	1657.2	1648.0	1638.8	1641.8	1646.9
25°	1676.5	1644.9	1616.3	1593.9	1588.8	1556.1	1529.6	1521.4	1506.1	1518.4	1520.4
27.5°	1578.6	1542.9	1496.9	1477.6	1451.0	1437.8	1419.4	1394.9	1363.3	1381.6	1378.6
30°	1473.5	1420.4	1382.7	1335.7	1293.9	1290.8	1256.1	1215.3	1199.0	1199.0	1208.2
32.5°	1356.1	1285.7	1230.6	1164.3	1123.5	1106.1	1064.3	1023.5	1032.7	1002.0	1013.3
35°	1219.4	1126.5	1057.1	992.9	962.3	941.8	887.8	865.3	840.8	826.5	853.1
37.5°	1088.8	981.6	892.9	822.5	811.2	774.5	737.8	723.5	709.2	715.3	714.3
40°	929.6	834.7	755.1	700.0	680.6	663.3	638.8	621.4	612.2	617.4	618.4
42.5°	785.7	706.1	646.9	608.2	591.8	579.6	567.4	553.1	550.0	550.0	554.1
45°	674.5	609.2	569.4	537.8	528.6	519.4	510.2	504.1	502.0	498.0	501.0
47.5°	585.7	533.7	509.2	485.7	475.5	473.5	465.3	462.2	458.2	457.1	458.2
50°	511.2	478.6	456.1	442.9	435.7	432.7	428.6	422.5	420.4	425.5	423.5
52.5°	459.2	428.6	416.3	403.1	399.0	394.9	388.8	389.8	388.8	386.7	386.7
55°	407.1	387.8	375.5	365.3	364.3	360.2	355.1	353.1	352.0	350.0	353.1
57.5°	365.3	350.0	338.8	329.6	325.5	325.5	320.4	316.3	316.3	315.3	316.3
60°	323.5	308.2	301.0	291.8	288.8	287.8	284.7	282.7	279.6	279.6	279.6
62.5°	284.7	272.5	264.3	256.1	257.1	252.0	248.0	245.9	245.9	246.9	246.9
65°	248.0	239.8	229.6	222.5	220.4	219.4	217.3	216.3	213.3	215.3	215.3
67.5°	214.3	203.1	196.9	193.9	190.8	189.8	187.8	185.7	184.7	183.7	185.7
70°	180.6	171.4	166.3	164.3	161.2	160.2	159.2	156.1	157.1	158.2	159.2
72.5°	150.0	141.8	140.8	134.7	134.7	134.7	130.6	132.7	131.6	129.6	131.6
75°	118.4	114.3	112.2	109.2	110.2	109.2	108.2	105.1	105.1	106.1	107.1
77.5°	93.9	89.8	88.8	85.7	83.7	85.7	83.7	82.7	82.7	83.7	83.7
80°	69.4	67.3	64.3	64.3	64.3	63.3	63.3	63.3	62.2	61.2	62.2
82.5°	45.9	45.9	44.9	43.9	44.9	42.9	43.9	43.9	43.9	43.9	43.9
85°	29.6	28.6	28.6	27.6	27.6	27.6	28.6	26.5	26.5	27.6	27.6
87.5°	13.3	13.3	13.3	14.3	13.3	13.3	13.3	14.3	13.3	13.3	13.3
90°	14.7	15.5	16.2	17.0	17.4	17.6	17.9	18.2	18.5	18.8	18.5
92.5°	17.0	17.3	17.6	17.9	18.1	18.2	18.3	18.5	18.6	18.8	18.6
95°	27.9	28.7	29.4	30.2	30.6	30.5	30.4	30.2	30.1	29.9	30.1
97.5°	35.9	36.3	36.8	37.3	37.5	37.6	37.7	37.9	38.0	38.2	38.0
100°	40.8	42.1	43.3	44.6	45.2	45.3	45.6	45.9	46.2	46.5	46.2
102.5°	42.7	44.4	46.1	47.8	48.6	48.8	49.3	49.8	50.2	50.7	50.2
105°	44.1	45.8	47.5	49.2	50.0	50.3	50.9	51.6	52.2	52.8	52.2
107.5°	45.5	47.2	48.9	50.6	51.4	51.7	52.3	53.0	53.6	54.2	53.6
110°	106.2	90.7	75.3	59.8	52.1	52.4	53.0	53.7	54.3	54.9	54.3

TEST NUMBER: P998864

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	286.4	219.8	153.3	86.8	53.5	53.7	54.2	54.7	55.1	55.6	55.1
115°	357.1	285.7	214.2	142.7	107.0	101.4	90.3	79.2	68.1	57.0	68.1
117.5°	444.0	422.0	399.9	377.8	366.8	346.6	306.1	265.7	225.2	184.8	225.2
120°	511.0	512.9	514.7	516.6	517.5	507.1	486.2	465.4	444.5	423.7	444.5
122.5°	551.0	552.0	552.9	553.8	554.3	554.4	554.5	554.7	554.8	555.0	554.8
125°	588.1	589.1	590.2	591.3	591.8	592.0	592.5	593.0	593.4	593.9	593.4
127.5°	622.5	624.1	625.6	627.1	627.9	628.0	628.1	628.3	628.4	628.6	628.4
130°	655.3	657.0	658.7	660.4	661.3	661.2	661.1	660.9	660.8	660.6	660.8
132.5°	687.7	689.1	690.4	691.8	692.5	692.4	692.3	692.1	692.0	691.8	692.0
135°	717.7	719.3	720.8	722.3	723.1	722.9	722.6	722.3	722.0	721.7	722.0
137.5°	746.2	747.7	749.3	750.8	751.6	751.4	750.9	750.4	750.0	749.5	750.0
140°	773.8	775.2	776.6	778.0	778.7	778.3	777.5	776.8	776.0	775.2	776.0
142.5°	799.3	800.6	801.8	803.1	803.7	803.3	802.5	801.8	801.0	800.2	801.0
145°	822.8	823.9	825.0	826.1	826.6	826.2	825.4	824.7	823.9	823.1	823.9
147.5°	844.1	844.9	845.6	846.4	846.8	846.5	845.9	845.2	844.6	844.0	844.6
150°	862.9	863.9	864.8	865.7	866.2	865.8	865.0	864.3	863.5	862.7	863.5
152.5°	880.3	881.3	882.2	883.1	883.6	883.1	882.0	880.9	879.8	878.7	879.8
155°	895.6	896.5	897.4	898.3	898.8	898.2	897.0	895.7	894.5	893.3	894.5
157.5°	909.0	910.0	911.1	912.2	912.7	912.1	910.9	909.6	908.4	907.2	908.4
160°	920.6	921.6	922.5	923.4	923.9	923.4	922.3	921.2	920.1	919.0	920.1
162.5°	931.2	932.3	933.4	934.5	935.0	934.3	932.9	931.5	930.1	928.7	930.1
165°	939.5	940.6	941.7	942.8	943.3	942.8	941.7	940.6	939.5	938.4	939.5
167.5°	947.2	948.2	949.3	950.4	950.9	950.2	948.8	947.5	946.1	944.7	946.1
170°	952.7	953.8	954.9	956.0	956.5	955.8	954.4	953.1	951.7	950.3	951.7
172.5°	956.9	958.0	959.1	960.2	960.7	960.0	958.6	957.2	955.8	954.4	955.8
175°	959.7	960.7	961.8	962.9	963.4	962.6	961.1	959.6	958.0	956.5	958.0
177.5°	960.4	961.4	962.5	963.6	964.1	963.4	962.0	960.7	959.3	957.9	959.3
180°	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0

TEST NUMBER: P998864

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1407.2	1400.0	1393.9	1394.9	1400.0	1395.9	1385.7	1372.5	1367.4	1361.2	1367.4
5°	1491.8	1485.7	1473.5	1474.5	1471.4	1467.4	1451.0	1430.6	1430.6	1414.3	1412.3
7.5°	1575.5	1566.3	1558.2	1556.1	1544.9	1536.7	1522.5	1493.9	1482.7	1463.3	1452.0
10°	1669.4	1662.3	1653.1	1641.8	1635.7	1621.4	1598.0	1556.1	1535.7	1509.2	1489.8
12.5°	1764.3	1763.3	1742.9	1720.4	1719.4	1696.9	1680.6	1624.5	1596.9	1561.2	1515.3
15°	1824.5	1819.4	1808.2	1796.9	1800.0	1775.5	1738.8	1672.5	1654.1	1611.2	1562.3
17.5°	1823.5	1823.5	1820.4	1818.4	1815.3	1808.2	1787.8	1743.9	1714.3	1660.2	1614.3
20°	1765.3	1778.6	1781.6	1780.6	1790.8	1795.9	1794.9	1767.4	1743.9	1695.9	1649.0
22.5°	1649.0	1679.6	1692.9	1701.0	1722.5	1733.7	1760.2	1750.0	1743.9	1708.2	1668.4
25°	1540.8	1551.0	1590.8	1592.9	1622.5	1650.0	1676.5	1693.9	1716.3	1703.1	1669.4
27.5°	1401.0	1424.5	1453.1	1474.5	1480.6	1536.7	1580.6	1613.3	1664.3	1668.4	1657.2
30°	1242.9	1254.1	1301.0	1329.6	1362.3	1403.1	1466.3	1522.5	1568.4	1610.2	1624.5
32.5°	1050.0	1095.9	1123.5	1158.2	1186.7	1259.2	1336.7	1409.2	1462.3	1532.7	1563.3
35°	873.5	909.2	956.1	970.4	1022.5	1083.7	1184.7	1277.6	1358.2	1429.6	1491.8
37.5°	727.6	756.1	806.1	828.6	859.2	937.8	1022.5	1137.8	1234.7	1322.5	1400.0
40°	627.6	649.0	686.7	693.9	719.4	790.8	859.2	967.4	1095.9	1214.3	1299.0
42.5°	559.2	569.4	594.9	604.1	620.4	668.4	729.6	831.6	951.0	1073.5	1192.9
45°	510.2	517.4	532.7	540.8	561.2	582.7	632.7	714.3	808.2	931.6	1060.2
47.5°	466.3	475.5	481.6	486.7	498.0	521.4	554.1	614.3	704.1	817.4	941.8
50°	429.6	432.7	443.9	444.9	452.0	467.3	498.0	534.7	606.1	698.0	818.4
52.5°	392.9	395.9	403.1	410.2	413.3	425.5	445.9	476.5	529.6	602.0	709.2
55°	356.1	360.2	367.3	372.5	375.5	385.7	398.0	427.6	469.4	520.4	608.2
57.5°	319.4	328.6	330.6	333.7	338.8	350.0	361.2	378.6	411.2	458.2	522.5
60°	284.7	287.8	294.9	298.0	303.1	309.2	323.5	336.7	360.2	396.9	455.1
62.5°	249.0	256.1	259.2	262.2	266.3	273.5	282.7	296.9	317.3	346.9	392.9
65°	218.4	219.4	225.5	229.6	233.7	238.8	248.0	261.2	273.5	301.0	334.7
67.5°	188.8	190.8	192.9	196.9	202.0	207.1	215.3	222.5	237.8	256.1	282.7
70°	160.2	160.2	165.3	168.4	167.3	173.5	179.6	187.8	199.0	216.3	237.8
72.5°	134.7	133.7	137.8	138.8	140.8	144.9	149.0	157.1	163.3	176.5	192.9
75°	107.1	109.2	111.2	111.2	114.3	117.3	121.4	125.5	132.7	140.8	153.1
77.5°	84.7	84.7	86.7	87.8	90.8	89.8	93.9	98.0	103.1	110.2	119.4
80°	62.2	64.3	64.3	64.3	65.3	66.3	70.4	73.5	76.5	81.6	85.7
82.5°	43.9	43.9	45.9	45.9	45.9	48.0	48.0	49.0	51.0	54.1	57.1
85°	27.6	27.6	27.6	28.6	27.6	28.6	30.6	29.6	30.6	32.7	32.7
87.5°	13.3	13.3	13.3	13.3	13.3	14.3	13.3	14.3	15.3	15.3	15.3
90°	18.2	17.9	17.6	17.4	17.0	16.2	15.5	14.7	13.9	12.7	11.4
92.5°	18.5	18.3	18.2	18.1	17.9	17.6	17.3	17.0	16.7	16.2	15.8
95°	30.2	30.4	30.5	30.6	30.2	29.4	28.7	27.9	27.1	26.0	24.9
97.5°	37.9	37.7	37.6	37.5	37.3	36.8	36.3	35.9	35.4	32.9	30.5
100°	45.9	45.6	45.3	45.2	44.6	43.3	42.1	40.8	39.6	37.0	34.4
102.5°	49.8	49.3	48.8	48.6	47.8	46.1	44.4	42.7	41.0	69.1	97.2
105°	51.6	50.9	50.3	50.0	49.2	47.5	45.8	44.1	42.4	84.5	126.7
107.5°	53.0	52.3	51.7	51.4	50.6	48.9	47.2	45.5	43.8	95.8	147.8
110°	53.7	53.0	52.4	52.1	59.8	75.3	90.7	106.2	121.6	166.2	210.8

TEST NUMBER: P998864

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	54.7	54.2	53.7	53.5	86.8	153.3	219.8	286.4	352.9	355.5	358.1
115°	79.2	90.3	101.4	107.0	142.7	214.2	285.7	357.1	428.6	424.7	420.9
117.5°	265.7	306.1	346.6	366.8	377.8	399.9	422.0	444.0	466.1	463.5	460.9
120°	465.4	486.2	507.1	517.5	516.6	514.7	512.9	511.0	509.2	506.4	503.6
122.5°	554.7	554.5	554.4	554.3	553.8	552.9	552.0	551.0	550.1	547.0	544.0
125°	593.0	592.5	592.0	591.8	591.3	590.2	589.1	588.1	587.0	584.1	581.1
127.5°	628.3	628.1	628.0	627.9	627.1	625.6	624.1	622.5	621.0	618.7	616.4
130°	660.9	661.1	661.2	661.3	660.4	658.7	657.0	655.3	653.6	651.9	650.2
132.5°	692.1	692.3	692.4	692.5	691.8	690.4	689.1	687.7	686.3	684.6	682.9
135°	722.3	722.6	722.9	723.1	722.3	720.8	719.3	717.7	716.2	714.8	713.4
137.5°	750.4	750.9	751.4	751.6	750.8	749.3	747.7	746.2	744.6	743.1	741.5
140°	776.8	777.5	778.3	778.7	778.0	776.6	775.2	773.8	772.4	770.7	769.0
142.5°	801.8	802.5	803.3	803.7	803.1	801.8	800.6	799.3	798.1	796.1	794.1
145°	824.7	825.4	826.2	826.6	826.1	825.0	823.9	822.8	821.7	819.1	816.5
147.5°	845.2	845.9	846.5	846.8	846.4	845.6	844.9	844.1	843.3	840.7	838.1
150°	864.3	865.0	865.8	866.2	865.7	864.8	863.9	862.9	862.0	859.5	857.1
152.5°	880.9	882.0	883.1	883.6	883.1	882.2	881.3	880.3	879.4	877.1	874.8
155°	895.7	897.0	898.2	898.8	898.3	897.4	896.5	895.6	894.7	892.8	891.0
157.5°	909.6	910.9	912.1	912.7	912.2	911.1	910.0	909.0	907.9	906.5	905.1
160°	921.2	922.3	923.4	923.9	923.4	922.5	921.6	920.6	919.7	918.8	917.8
162.5°	931.5	932.9	934.3	935.0	934.5	933.4	932.3	931.2	930.1	929.3	928.5
165°	940.6	941.7	942.8	943.3	942.8	941.7	940.6	939.5	938.4	938.0	937.5
167.5°	947.5	948.8	950.2	950.9	950.4	949.3	948.2	947.2	946.1	945.6	945.2
170°	953.1	954.4	955.8	956.5	956.0	954.9	953.8	952.7	951.6	951.3	951.0
172.5°	957.2	958.6	960.0	960.7	960.2	959.1	958.0	956.9	955.8	955.5	955.2
175°	959.6	961.1	962.6	963.4	962.9	961.8	960.7	959.7	958.6	958.3	958.0
177.5°	960.7	962.0	963.4	964.1	963.6	962.5	961.4	960.4	959.3	959.1	959.0
180°	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0

TEST NUMBER: P998864

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1362.3	1357.2	1354.1	1356.1	1350.0	1334.7	1334.7	1339.8	1333.7	1327.6	1318.4
5°	1400.0	1389.8	1383.7	1382.7	1368.4	1343.9	1338.8	1333.7	1320.4	1306.1	1290.8
7.5°	1436.7	1418.4	1408.2	1401.0	1380.6	1349.0	1335.7	1324.5	1303.1	1281.6	1262.3
10°	1467.4	1440.8	1428.6	1417.4	1390.8	1351.0	1329.6	1309.2	1281.6	1254.1	1229.6
12.5°	1491.8	1461.2	1445.9	1429.6	1396.9	1344.9	1318.4	1285.7	1258.2	1221.4	1196.9
15°	1532.7	1469.4	1455.1	1439.8	1406.1	1334.7	1302.0	1265.3	1227.6	1178.6	1152.0
17.5°	1565.3	1480.6	1479.6	1446.9	1403.1	1330.6	1280.6	1232.7	1191.8	1142.9	1101.0
20°	1584.7	1498.0	1481.6	1448.0	1392.9	1303.1	1251.0	1198.0	1154.1	1094.9	1053.1
22.5°	1601.0	1522.5	1479.6	1438.8	1371.4	1293.9	1217.4	1167.4	1107.1	1042.9	1003.1
25°	1607.2	1527.6	1482.7	1435.7	1356.1	1267.4	1180.6	1126.5	1059.2	1001.0	946.9
27.5°	1608.2	1526.5	1471.4	1422.5	1334.7	1232.7	1143.9	1086.7	1012.3	944.9	890.8
30°	1598.0	1515.3	1465.3	1412.3	1314.3	1201.0	1099.0	1035.7	956.1	888.8	832.7
32.5°	1567.4	1492.9	1452.0	1393.9	1287.8	1157.2	1056.1	985.7	902.0	835.7	781.6
35°	1516.3	1465.3	1420.4	1366.3	1253.1	1116.3	1013.3	930.6	845.9	782.7	731.6
37.5°	1453.1	1425.5	1383.7	1330.6	1213.3	1079.6	965.3	873.5	788.8	727.6	677.6
40°	1367.4	1374.5	1333.7	1285.7	1166.3	1029.6	903.1	815.3	735.7	678.6	629.6
42.5°	1274.5	1304.1	1280.6	1234.7	1114.3	974.5	857.1	760.2	682.7	623.5	582.7
45°	1174.5	1225.5	1211.2	1177.6	1060.2	916.3	791.8	698.0	629.6	572.5	536.7
47.5°	1065.3	1137.8	1137.8	1113.3	1000.0	858.2	735.7	639.8	572.5	531.6	496.9
50°	954.1	1035.7	1049.0	1032.7	932.7	791.8	667.4	580.6	522.5	482.7	457.1
52.5°	837.8	932.7	957.1	949.0	861.2	728.6	611.2	526.5	473.5	438.8	416.3
55°	726.5	836.7	863.3	866.3	784.7	659.2	549.0	474.5	423.5	400.0	380.6
57.5°	621.4	727.6	757.1	762.2	707.1	595.9	490.8	425.5	379.6	360.2	344.9
60°	531.6	620.4	659.2	670.4	622.5	522.5	436.7	373.5	338.8	320.4	306.1
62.5°	458.2	529.6	570.4	573.5	552.0	458.2	380.6	327.6	298.0	281.6	274.5
65°	386.7	451.0	475.5	487.8	470.4	396.9	328.6	284.7	261.2	246.9	239.8
67.5°	329.6	370.4	390.8	407.1	389.8	334.7	279.6	243.9	226.5	212.2	208.2
70°	270.4	304.1	319.4	335.7	320.4	278.6	238.8	206.1	190.8	179.6	174.5
72.5°	216.3	242.9	257.1	267.3	258.2	223.5	190.8	168.4	157.1	149.0	145.9
75°	171.4	189.8	198.0	205.1	201.0	174.5	154.1	135.7	125.5	118.4	116.3
77.5°	130.6	143.9	153.1	155.1	150.0	132.7	115.3	104.1	95.9	91.8	89.8
80°	92.9	101.0	106.1	109.2	104.1	96.9	84.7	76.5	69.4	64.3	63.3
82.5°	62.2	66.3	70.4	69.4	67.3	61.2	54.1	50.0	46.9	42.9	42.9
85°	35.7	36.7	38.8	39.8	38.8	34.7	30.6	28.6	26.5	23.5	23.5
87.5°	15.3	16.3	16.3	17.3	15.3	15.3	13.3	11.2	11.2	10.2	9.2
90°	10.2	8.9	8.3	7.5	5.8	4.1	2.4	0.7	2.4	4.1	5.8
92.5°	15.3	14.8	14.6	14.9	15.5	16.2	16.8	17.4	16.8	16.2	15.5
95°	23.8	22.7	22.2	24.8	29.9	35.0	40.1	45.2	40.1	35.0	29.9
97.5°	28.0	25.5	24.3	30.6	43.3	56.0	68.6	81.3	68.6	56.0	43.3
100°	31.7	29.1	27.8	38.4	59.5	80.6	101.8	122.9	101.8	80.6	59.5
102.5°	125.3	153.4	167.4	167.6	167.9	168.2	168.5	168.8	168.5	168.2	167.9
105°	168.8	210.9	232.0	229.7	225.1	220.4	215.8	211.2	215.8	220.4	225.1
107.5°	199.9	251.9	277.9	276.0	272.1	268.2	264.4	260.5	264.4	268.2	272.1
110°	255.4	300.0	322.3	320.7	317.4	314.2	310.9	307.7	310.9	314.2	317.4

TEST NUMBER: P998864

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	360.8	363.4	364.7	363.3	360.5	357.8	355.0	352.2	355.0	357.8	360.5
115°	417.0	413.1	411.2	409.9	407.3	404.6	402.0	399.4	402.0	404.6	407.3
117.5°	458.2	455.6	454.3	452.8	449.7	446.6	443.5	440.4	443.5	446.6	449.7
120°	500.9	498.1	496.7	495.5	493.2	490.9	488.5	486.2	488.5	490.9	493.2
122.5°	540.9	537.8	536.3	535.1	532.6	530.1	527.6	525.1	527.6	530.1	532.6
125°	578.2	575.3	573.8	572.8	570.8	568.7	566.7	564.7	566.7	568.7	570.8
127.5°	614.1	611.8	610.6	609.5	607.4	605.2	603.1	600.9	603.1	605.2	607.4
130°	648.5	646.8	646.0	644.8	642.3	639.8	637.4	634.9	637.4	639.8	642.3
132.5°	681.2	679.5	678.7	677.7	675.7	673.6	671.6	669.6	671.6	673.6	675.7
135°	712.0	710.6	709.9	708.7	706.2	703.7	701.3	698.8	701.3	703.7	706.2
137.5°	740.0	738.5	737.7	736.8	734.9	733.1	731.2	729.4	731.2	733.1	734.9
140°	767.3	765.6	764.8	764.2	762.9	761.7	760.4	759.2	760.4	761.7	762.9
142.5°	792.1	790.1	789.1	788.6	787.5	786.4	785.3	784.2	785.3	786.4	787.5
145°	813.8	811.2	809.9	810.0	810.1	810.3	810.4	810.6	810.4	810.3	810.1
147.5°	835.4	832.8	831.5	831.7	832.2	832.7	833.1	833.6	833.1	832.7	832.2
150°	854.6	852.1	850.9	851.4	852.5	853.6	854.7	855.8	854.7	853.6	852.5
152.5°	872.5	870.2	869.0	869.6	870.8	872.1	873.3	874.5	873.3	872.1	870.8
155°	889.1	887.2	886.3	887.0	888.4	889.8	891.2	892.6	891.2	889.8	888.4
157.5°	903.7	902.3	901.6	902.2	903.5	904.7	906.0	907.2	906.0	904.7	903.5
160°	916.9	916.0	915.5	916.0	916.9	917.8	918.8	919.7	918.8	917.8	916.9
162.5°	927.8	927.0	926.6	927.1	928.0	928.9	929.9	930.8	929.9	928.9	928.0
165°	937.1	936.6	936.4	936.9	937.8	938.7	939.6	940.5	939.6	938.7	937.8
167.5°	944.7	944.2	944.0	944.5	945.4	946.3	947.3	948.2	947.3	946.3	945.4
170°	950.7	950.4	950.3	950.8	951.7	952.6	953.5	954.4	953.5	952.6	951.7
172.5°	954.9	954.6	954.4	954.9	955.8	956.7	957.7	958.6	957.7	956.7	955.8
175°	957.7	957.4	957.2	957.7	958.8	959.9	961.0	962.1	961.0	959.9	958.8
177.5°	958.8	958.7	958.6	959.1	960.2	961.3	962.3	963.4	962.3	961.3	960.2
180°	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0

TEST NUMBER: P998864

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1313.3	1318.4	1317.4	1307.2	1295.9	1286.7	1269.4	1271.4	1265.3	1266.3	1272.5
5°	1280.6	1280.6	1276.5	1262.3	1243.9	1233.7	1214.3	1209.2	1196.9	1195.9	1194.9
7.5°	1245.9	1240.8	1235.7	1215.3	1192.9	1176.5	1150.0	1143.9	1131.6	1123.5	1119.4
10°	1205.1	1198.0	1187.8	1164.3	1136.7	1116.3	1088.8	1080.6	1057.1	1046.9	1040.8
12.5°	1160.2	1156.1	1139.8	1120.4	1075.5	1053.1	1013.3	1021.4	998.0	977.6	974.5
15°	1115.3	1100.0	1090.8	1059.2	1005.1	994.9	963.3	946.9	925.5	909.2	909.2
17.5°	1071.4	1048.0	1027.6	993.9	954.1	925.5	902.0	893.9	867.4	851.0	848.0
20°	1013.3	986.7	981.6	933.7	906.1	874.5	852.0	831.6	812.2	805.1	800.0
22.5°	958.2	927.6	919.4	878.6	851.0	819.4	796.9	782.7	768.4	763.3	754.1
25°	899.0	880.6	868.4	824.5	793.9	764.3	749.0	738.8	725.5	724.5	718.4
27.5°	841.8	824.5	812.2	770.4	748.0	720.4	708.2	696.9	689.8	686.7	683.7
30°	792.9	773.5	759.2	728.6	701.0	678.6	668.4	661.2	657.1	652.0	651.0
32.5°	738.8	727.6	708.2	684.7	663.3	641.8	635.7	630.6	624.5	622.5	621.4
35°	692.9	677.6	665.3	638.8	629.6	611.2	604.1	600.0	591.8	589.8	587.8
37.5°	648.0	633.7	620.4	604.1	586.7	576.5	572.5	566.3	562.2	563.3	561.2
40°	603.1	591.8	581.6	564.3	554.1	549.0	540.8	534.7	532.7	533.7	532.7
42.5°	559.2	549.0	542.9	529.6	519.4	514.3	509.2	503.1	506.1	506.1	509.2
45°	519.4	510.2	506.1	495.9	489.8	481.6	476.5	475.5	479.6	478.6	478.6
47.5°	478.6	475.5	470.4	461.2	453.1	448.0	446.9	446.9	451.0	453.1	452.0
50°	446.9	440.8	434.7	427.6	421.4	419.4	416.3	418.4	422.5	422.5	424.5
52.5°	407.1	403.1	401.0	394.9	390.8	390.8	390.8	391.8	394.9	398.0	396.9
55°	372.5	369.4	367.3	364.3	359.2	360.2	359.2	361.2	364.3	367.3	369.4
57.5°	335.7	334.7	332.7	327.6	327.6	326.5	329.6	330.6	335.7	337.8	340.8
60°	303.1	300.0	300.0	295.9	295.9	295.9	299.0	302.0	306.1	307.1	309.2
62.5°	268.4	268.4	267.3	264.3	264.3	267.3	268.4	272.5	274.5	274.5	277.6
65°	235.7	234.7	233.7	234.7	235.7	235.7	238.8	240.8	242.9	243.9	244.9
67.5°	203.1	202.0	204.1	203.1	205.1	209.2	208.2	211.2	214.3	214.3	215.3
70°	172.5	174.5	173.5	175.5	174.5	176.5	179.6	180.6	180.6	181.6	184.7
72.5°	143.9	143.9	143.9	142.9	143.9	145.9	148.0	149.0	151.0	152.0	155.1
75°	116.3	116.3	114.3	116.3	116.3	118.4	120.4	120.4	120.4	122.4	125.5
77.5°	87.8	88.8	87.8	89.8	89.8	90.8	92.9	91.8	93.9	94.9	95.9
80°	64.3	63.3	63.3	63.3	64.3	64.3	66.3	67.3	67.3	70.4	68.4
82.5°	40.8	41.8	40.8	41.8	41.8	42.9	41.8	42.9	43.9	45.9	44.9
85°	23.5	22.4	22.4	23.5	22.4	22.4	23.5	22.4	23.5	22.4	23.5
87.5°	9.2	8.2	8.2	8.2	8.2	7.1	7.1	6.1	6.1	6.1	5.1
90°	7.5	8.3	8.9	10.2	11.4	12.7	13.9	14.7	15.5	16.2	17.0
92.5°	14.9	14.6	14.8	15.3	15.8	16.2	16.7	17.0	17.3	17.6	17.9
95°	24.8	22.2	22.7	23.8	24.9	26.0	27.1	27.9	28.7	29.4	30.2
97.5°	30.6	24.3	25.5	28.0	30.5	32.9	35.4	35.9	36.3	36.8	37.3
100°	38.4	27.8	29.1	31.7	34.4	37.0	39.6	40.8	42.1	43.3	44.6
102.5°	167.6	167.4	153.4	125.3	97.2	69.1	41.0	42.7	44.4	46.1	47.8
105°	229.7	232.0	210.9	168.8	126.7	84.5	42.4	44.1	45.8	47.5	49.2
107.5°	276.0	277.9	251.9	199.9	147.8	95.8	43.8	45.5	47.2	48.9	50.6
110°	320.7	322.3	300.0	255.4	210.8	166.2	121.6	106.2	90.7	75.3	59.8

TEST NUMBER: P998864

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	363.3	364.7	363.4	360.8	358.1	355.5	352.9	286.4	219.8	153.3	86.8
115°	409.9	411.2	413.1	417.0	420.9	424.7	428.6	357.1	285.7	214.2	142.7
117.5°	452.8	454.3	455.6	458.2	460.9	463.5	466.1	444.0	422.0	399.9	377.8
120°	495.5	496.7	498.1	500.9	503.6	506.4	509.2	511.0	512.9	514.7	516.6
122.5°	535.1	536.3	537.8	540.9	544.0	547.0	550.1	551.0	552.0	552.9	553.8
125°	572.8	573.8	575.3	578.2	581.1	584.1	587.0	588.1	589.1	590.2	591.3
127.5°	609.5	610.6	611.8	614.1	616.4	618.7	621.0	622.5	624.1	625.6	627.1
130°	644.8	646.0	646.8	648.5	650.2	651.9	653.6	655.3	657.0	658.7	660.4
132.5°	677.7	678.7	679.5	681.2	682.9	684.6	686.3	687.7	689.1	690.4	691.8
135°	708.7	709.9	710.6	712.0	713.4	714.8	716.2	717.7	719.3	720.8	722.3
137.5°	736.8	737.7	738.5	740.0	741.5	743.1	744.6	746.2	747.7	749.3	750.8
140°	764.2	764.8	765.6	767.3	769.0	770.7	772.4	773.8	775.2	776.6	778.0
142.5°	788.6	789.1	790.1	792.1	794.1	796.1	798.1	799.3	800.6	801.8	803.1
145°	810.0	809.9	811.2	813.8	816.5	819.1	821.7	822.8	823.9	825.0	826.1
147.5°	831.7	831.5	832.8	835.4	838.1	840.7	843.3	844.1	844.9	845.6	846.4
150°	851.4	850.9	852.1	854.6	857.1	859.5	862.0	862.9	863.9	864.8	865.7
152.5°	869.6	869.0	870.2	872.5	874.8	877.1	879.4	880.3	881.3	882.2	883.1
155°	887.0	886.3	887.2	889.1	891.0	892.8	894.7	895.6	896.5	897.4	898.3
157.5°	902.2	901.6	902.3	903.7	905.1	906.5	907.9	909.0	910.0	911.1	912.2
160°	916.0	915.5	916.0	916.9	917.8	918.8	919.7	920.6	921.6	922.5	923.4
162.5°	927.1	926.6	927.0	927.8	928.5	929.3	930.1	931.2	932.3	933.4	934.5
165°	936.9	936.4	936.6	937.1	937.5	938.0	938.4	939.5	940.6	941.7	942.8
167.5°	944.5	944.0	944.2	944.7	945.2	945.6	946.1	947.2	948.2	949.3	950.4
170°	950.8	950.3	950.4	950.7	951.0	951.3	951.6	952.7	953.8	954.9	956.0
172.5°	954.9	954.4	954.6	954.9	955.2	955.5	955.8	956.9	958.0	959.1	960.2
175°	957.7	957.2	957.4	957.7	958.0	958.3	958.6	959.7	960.7	961.8	962.9
177.5°	959.1	958.6	958.7	958.8	959.0	959.1	959.3	960.4	961.4	962.5	963.6
180°	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0

TEST NUMBER: P998864

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1265.3	1268.4	1261.2	1259.2	1261.2	1254.1	1256.1	1258.2	1258.2	1261.2	1263.3
5°	1191.8	1187.8	1180.6	1178.6	1176.5	1179.6	1177.6	1180.6	1181.6	1188.8	1189.8
7.5°	1119.4	1113.3	1107.1	1101.0	1099.0	1093.9	1099.0	1099.0	1106.1	1104.1	1109.2
10°	1033.7	1032.7	1024.5	1021.4	1017.4	1009.2	1020.4	1017.4	1022.5	1031.6	1033.7
12.5°	970.4	959.2	964.3	950.0	955.1	946.9	948.0	948.0	956.1	957.1	955.1
15°	910.2	901.0	887.8	881.6	878.6	874.5	887.8	888.8	882.7	896.9	891.8
17.5°	849.0	849.0	836.7	833.7	825.5	829.6	827.6	828.6	826.5	836.7	841.8
20°	795.9	790.8	786.7	787.8	777.6	775.5	773.5	775.5	782.7	789.8	791.8
22.5°	753.1	750.0	739.8	741.8	733.7	736.7	734.7	739.8	740.8	740.8	748.0
25°	712.2	708.2	709.2	705.1	702.0	702.0	699.0	702.0	706.1	708.2	709.2
27.5°	681.6	678.6	673.5	670.4	672.5	667.4	671.4	674.5	674.5	672.5	674.5
30°	644.9	646.9	646.9	636.7	640.8	638.8	641.8	643.9	643.9	644.9	642.9
32.5°	620.4	614.3	613.3	612.2	612.2	608.2	608.2	611.2	612.2	613.3	616.3
35°	587.8	587.8	582.7	585.7	581.6	582.7	581.6	582.7	584.7	581.6	584.7
37.5°	558.2	559.2	557.1	559.2	560.2	558.2	556.1	560.2	558.2	558.2	556.1
40°	532.7	531.6	532.7	532.7	532.7	533.7	531.6	531.6	531.6	529.6	527.6
42.5°	511.2	505.1	507.1	508.2	505.1	505.1	506.1	505.1	508.2	502.0	502.0
45°	480.6	478.6	479.6	479.6	481.6	478.6	480.6	481.6	478.6	477.6	475.5
47.5°	453.1	455.1	453.1	455.1	455.1	457.1	453.1	454.1	455.1	451.0	448.0
50°	425.5	425.5	428.6	427.6	428.6	426.5	426.5	425.5	426.5	424.5	421.4
52.5°	400.0	396.9	402.0	401.0	400.0	399.0	398.0	399.0	396.9	394.9	394.9
55°	368.4	368.4	371.4	372.5	372.5	370.4	368.4	369.4	368.4	367.3	366.3
57.5°	342.9	338.8	340.8	341.8	341.8	338.8	340.8	338.8	338.8	339.8	336.7
60°	310.2	310.2	308.2	311.2	311.2	309.2	309.2	310.2	308.2	307.1	306.1
62.5°	275.5	276.5	279.6	280.6	281.6	279.6	277.6	278.6	278.6	275.5	276.5
65°	245.9	248.0	252.0	251.0	249.0	250.0	248.0	249.0	245.9	246.9	243.9
67.5°	217.3	216.3	217.3	217.3	219.4	218.4	216.3	216.3	215.3	218.4	215.3
70°	186.7	186.7	186.7	186.7	187.8	188.8	186.7	184.7	185.7	183.7	182.7
72.5°	155.1	156.1	155.1	157.1	154.1	156.1	156.1	155.1	154.1	154.1	154.1
75°	125.5	127.6	124.5	125.5	124.5	126.5	125.5	125.5	123.5	122.4	123.5
77.5°	95.9	96.9	94.9	95.9	94.9	95.9	95.9	94.9	94.9	94.9	94.9
80°	68.4	69.4	68.4	67.3	66.3	68.4	66.3	67.3	68.4	67.3	69.4
82.5°	43.9	43.9	42.9	43.9	41.8	41.8	42.9	42.9	41.8	43.9	41.8
85°	21.4	21.4	23.5	21.4	20.4	20.4	20.4	21.4	20.4	22.4	21.4
87.5°	5.1	4.1	5.1	5.1	4.1	4.1	5.1	4.1	5.1	6.1	4.1
90°	17.4	17.6	17.9	18.2	18.5	18.8	18.5	18.2	17.9	17.6	17.4
92.5°	18.1	18.2	18.3	18.5	18.6	18.8	18.6	18.5	18.3	18.2	18.1
95°	30.6	30.5	30.4	30.2	30.1	29.9	30.1	30.2	30.4	30.5	30.6
97.5°	37.5	37.6	37.7	37.9	38.0	38.2	38.0	37.9	37.7	37.6	37.5
100°	45.2	45.3	45.6	45.9	46.2	46.5	46.2	45.9	45.6	45.3	45.2
102.5°	48.6	48.8	49.3	49.8	50.2	50.7	50.2	49.8	49.3	48.8	48.6
105°	50.0	50.3	50.9	51.6	52.2	52.8	52.2	51.6	50.9	50.3	50.0
107.5°	51.4	51.7	52.3	53.0	53.6	54.2	53.6	53.0	52.3	51.7	51.4
110°	52.1	52.4	53.0	53.7	54.3	54.9	54.3	53.7	53.0	52.4	52.1

TEST NUMBER: P998864

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	53.5	53.7	54.2	54.7	55.1	55.6	55.1	54.7	54.2	53.7	53.5
115°	107.0	101.4	90.3	79.2	68.1	57.0	68.1	79.2	90.3	101.4	107.0
117.5°	366.8	346.6	306.1	265.7	225.2	184.8	225.2	265.7	306.1	346.6	366.8
120°	517.5	507.1	486.2	465.4	444.5	423.7	444.5	465.4	486.2	507.1	517.5
122.5°	554.3	554.4	554.5	554.7	554.8	555.0	554.8	554.7	554.5	554.4	554.3
125°	591.8	592.0	592.5	593.0	593.4	593.9	593.4	593.0	592.5	592.0	591.8
127.5°	627.9	628.0	628.1	628.3	628.4	628.6	628.4	628.3	628.1	628.0	627.9
130°	661.3	661.2	661.1	660.9	660.8	660.6	660.8	660.9	661.1	661.2	661.3
132.5°	692.5	692.4	692.3	692.1	692.0	691.8	692.0	692.1	692.3	692.4	692.5
135°	723.1	722.9	722.6	722.3	722.0	721.7	722.0	722.3	722.6	722.9	723.1
137.5°	751.6	751.4	750.9	750.4	750.0	749.5	750.0	750.4	750.9	751.4	751.6
140°	778.7	778.3	777.5	776.8	776.0	775.2	776.0	776.8	777.5	778.3	778.7
142.5°	803.7	803.3	802.5	801.8	801.0	800.2	801.0	801.8	802.5	803.3	803.7
145°	826.6	826.2	825.4	824.7	823.9	823.1	823.9	824.7	825.4	826.2	826.6
147.5°	846.8	846.5	845.9	845.2	844.6	844.0	844.6	845.2	845.9	846.5	846.8
150°	866.2	865.8	865.0	864.3	863.5	862.7	863.5	864.3	865.0	865.8	866.2
152.5°	883.6	883.1	882.0	880.9	879.8	878.7	879.8	880.9	882.0	883.1	883.6
155°	898.8	898.2	897.0	895.7	894.5	893.3	894.5	895.7	897.0	898.2	898.8
157.5°	912.7	912.1	910.9	909.6	908.4	907.2	908.4	909.6	910.9	912.1	912.7
160°	923.9	923.4	922.3	921.2	920.1	919.0	920.1	921.2	922.3	923.4	923.9
162.5°	935.0	934.3	932.9	931.5	930.1	928.7	930.1	931.5	932.9	934.3	935.0
165°	943.3	942.8	941.7	940.6	939.5	938.4	939.5	940.6	941.7	942.8	943.3
167.5°	950.9	950.2	948.8	947.5	946.1	944.7	946.1	947.5	948.8	950.2	950.9
170°	956.5	955.8	954.4	953.1	951.7	950.3	951.7	953.1	954.4	955.8	956.5
172.5°	960.7	960.0	958.6	957.2	955.8	954.4	955.8	957.2	958.6	960.0	960.7
175°	963.4	962.6	961.1	959.6	958.0	956.5	958.0	959.6	961.1	962.6	963.4
177.5°	964.1	963.4	962.0	960.7	959.3	957.9	959.3	960.7	962.0	963.4	964.1
180°	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0

TEST NUMBER: P998864

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1260.2	1268.4	1265.3	1254.1	1267.4	1267.4	1276.5	1276.5	1287.8	1291.8	1298.0
5°	1188.8	1194.9	1200.0	1194.9	1204.1	1218.4	1226.5	1233.7	1249.0	1255.1	1264.3
7.5°	1112.3	1123.5	1128.6	1128.6	1143.9	1160.2	1176.5	1186.7	1208.2	1216.3	1225.5
10°	1037.8	1051.0	1061.2	1060.2	1085.7	1095.9	1116.3	1139.8	1161.2	1173.5	1186.7
12.5°	959.2	966.3	980.6	1001.0	1007.1	1025.5	1049.0	1078.6	1117.4	1128.6	1148.0
15°	893.9	913.3	924.5	933.7	948.0	965.3	990.8	1019.4	1058.2	1082.7	1103.1
17.5°	838.8	864.3	871.4	869.4	887.8	914.3	943.9	965.3	1000.0	1029.6	1049.0
20°	793.9	804.1	816.3	821.4	835.7	864.3	892.9	917.4	945.9	969.4	991.8
22.5°	749.0	757.1	767.4	776.5	787.8	804.1	831.6	862.3	889.8	912.3	937.8
25°	712.2	717.4	726.5	733.7	745.9	757.1	776.5	810.2	842.9	856.1	878.6
27.5°	676.5	680.6	686.7	694.9	701.0	712.2	729.6	757.1	790.8	804.1	834.7
30°	644.9	648.0	654.1	658.2	661.2	674.5	687.8	709.2	734.7	753.1	775.5
32.5°	615.3	618.4	624.5	625.5	629.6	636.7	649.0	668.4	690.8	706.1	725.5
35°	582.7	584.7	590.8	592.9	595.9	602.0	611.2	625.5	645.9	657.1	674.5
37.5°	557.1	556.1	560.2	563.3	567.4	570.4	573.5	587.8	603.1	613.3	626.5
40°	529.6	527.6	528.6	532.7	534.7	538.8	538.8	553.1	563.3	571.4	581.6
42.5°	502.0	501.0	499.0	501.0	503.1	504.1	505.1	515.3	525.5	532.7	543.9
45°	474.5	473.5	471.4	472.5	472.5	474.5	477.6	481.6	488.8	494.9	501.0
47.5°	449.0	446.9	443.9	442.9	444.9	444.9	444.9	449.0	456.1	458.2	464.3
50°	422.5	419.4	415.3	413.3	413.3	412.2	414.3	415.3	421.4	423.5	428.6
52.5°	393.9	391.8	387.8	383.7	384.7	382.7	383.7	384.7	386.7	389.8	392.9
55°	365.3	361.2	358.2	357.1	354.1	354.1	351.0	355.1	354.1	355.1	359.2
57.5°	337.8	333.7	328.6	326.5	323.5	322.5	320.4	319.4	320.4	323.5	326.5
60°	305.1	303.1	300.0	296.9	294.9	291.8	289.8	289.8	288.8	288.8	289.8
62.5°	273.5	272.5	268.4	267.3	265.3	263.3	260.2	258.2	258.2	260.2	261.2
65°	242.9	241.8	238.8	237.8	232.7	230.6	229.6	228.6	226.5	226.5	226.5
67.5°	214.3	211.2	211.2	206.1	202.0	200.0	198.0	196.9	196.9	196.9	198.0
70°	182.7	182.7	179.6	176.5	172.5	173.5	170.4	167.3	167.3	165.3	166.3
72.5°	152.0	151.0	148.0	146.9	143.9	140.8	138.8	140.8	137.8	136.7	137.8
75°	122.4	121.4	119.4	117.3	118.4	115.3	112.2	111.2	111.2	109.2	109.2
77.5°	93.9	95.9	91.8	90.8	88.8	86.7	85.7	84.7	84.7	84.7	86.7
80°	65.3	66.3	66.3	64.3	65.3	62.2	62.2	62.2	59.2	60.2	61.2
82.5°	41.8	41.8	40.8	41.8	40.8	40.8	39.8	39.8	38.8	38.8	39.8
85°	23.5	22.4	21.4	23.5	22.4	22.4	21.4	21.4	21.4	21.4	21.4
87.5°	5.1	6.1	6.1	6.1	6.1	7.1	7.1	7.1	8.2	8.2	8.2
90°	17.0	16.2	15.5	14.7	13.9	12.7	11.4	10.2	8.9	8.3	7.5
92.5°	17.9	17.6	17.3	17.0	16.7	16.2	15.8	15.3	14.8	14.6	14.9
95°	30.2	29.4	28.7	27.9	27.1	26.0	24.9	23.8	22.7	22.2	24.8
97.5°	37.3	36.8	36.3	35.9	35.4	32.9	30.5	28.0	25.5	24.3	30.6
100°	44.6	43.3	42.1	40.8	39.6	37.0	34.4	31.7	29.1	27.8	38.4
102.5°	47.8	46.1	44.4	42.7	41.0	69.1	97.2	125.3	153.4	167.4	167.6
105°	49.2	47.5	45.8	44.1	42.4	84.5	126.7	168.8	210.9	232.0	229.7
107.5°	50.6	48.9	47.2	45.5	43.8	95.8	147.8	199.9	251.9	277.9	276.0
110°	59.8	75.3	90.7	106.2	121.6	166.2	210.8	255.4	300.0	322.3	320.7

TEST NUMBER: P998864

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	86.8	153.3	219.8	286.4	352.9	355.5	358.1	360.8	363.4	364.7	363.3
115°	142.7	214.2	285.7	357.1	428.6	424.7	420.9	417.0	413.1	411.2	409.9
117.5°	377.8	399.9	422.0	444.0	466.1	463.5	460.9	458.2	455.6	454.3	452.8
120°	516.6	514.7	512.9	511.0	509.2	506.4	503.6	500.9	498.1	496.7	495.5
122.5°	553.8	552.9	552.0	551.0	550.1	547.0	544.0	540.9	537.8	536.3	535.1
125°	591.3	590.2	589.1	588.1	587.0	584.1	581.1	578.2	575.3	573.8	572.8
127.5°	627.1	625.6	624.1	622.5	621.0	618.7	616.4	614.1	611.8	610.6	609.5
130°	660.4	658.7	657.0	655.3	653.6	651.9	650.2	648.5	646.8	646.0	644.8
132.5°	691.8	690.4	689.1	687.7	686.3	684.6	682.9	681.2	679.5	678.7	677.7
135°	722.3	720.8	719.3	717.7	716.2	714.8	713.4	712.0	710.6	709.9	708.7
137.5°	750.8	749.3	747.7	746.2	744.6	743.1	741.5	740.0	738.5	737.7	736.8
140°	778.0	776.6	775.2	773.8	772.4	770.7	769.0	767.3	765.6	764.8	764.2
142.5°	803.1	801.8	800.6	799.3	798.1	796.1	794.1	792.1	790.1	789.1	788.6
145°	826.1	825.0	823.9	822.8	821.7	819.1	816.5	813.8	811.2	809.9	810.0
147.5°	846.4	845.6	844.9	844.1	843.3	840.7	838.1	835.4	832.8	831.5	831.7
150°	865.7	864.8	863.9	862.9	862.0	859.5	857.1	854.6	852.1	850.9	851.4
152.5°	883.1	882.2	881.3	880.3	879.4	877.1	874.8	872.5	870.2	869.0	869.6
155°	898.3	897.4	896.5	895.6	894.7	892.8	891.0	889.1	887.2	886.3	887.0
157.5°	912.2	911.1	910.0	909.0	907.9	906.5	905.1	903.7	902.3	901.6	902.2
160°	923.4	922.5	921.6	920.6	919.7	918.8	917.8	916.9	916.0	915.5	916.0
162.5°	934.5	933.4	932.3	931.2	930.1	929.3	928.5	927.8	927.0	926.6	927.1
165°	942.8	941.7	940.6	939.5	938.4	938.0	937.5	937.1	936.6	936.4	936.9
167.5°	950.4	949.3	948.2	947.2	946.1	945.6	945.2	944.7	944.2	944.0	944.5
170°	956.0	954.9	953.8	952.7	951.6	951.3	951.0	950.7	950.4	950.3	950.8
172.5°	960.2	959.1	958.0	956.9	955.8	955.5	955.2	954.9	954.6	954.4	954.9
175°	962.9	961.8	960.7	959.7	958.6	958.3	958.0	957.7	957.4	957.2	957.7
177.5°	963.6	962.5	961.4	960.4	959.3	959.1	959.0	958.8	958.7	958.6	959.1
180°	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0

TEST NUMBER: P998864

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1327.6	1327.6	1327.6	1327.6
2.5°	1303.1	1303.1	1318.4	1334.7
5°	1274.5	1281.6	1306.1	1328.6
7.5°	1246.9	1259.2	1289.8	1318.4
10°	1213.3	1229.6	1267.4	1301.0
12.5°	1180.6	1195.9	1239.8	1277.6
15°	1134.7	1154.1	1201.0	1248.0
17.5°	1088.8	1108.2	1165.3	1220.4
20°	1034.7	1060.2	1124.5	1198.0
22.5°	984.7	1016.3	1087.8	1146.9
25°	929.6	978.6	1044.9	1121.4
27.5°	880.6	929.6	996.9	1074.5
30°	825.5	875.5	944.9	1016.3
32.5°	772.5	818.4	885.7	973.5
35°	717.4	761.2	826.5	915.3
37.5°	667.4	710.2	781.6	863.3
40°	618.4	663.3	724.5	806.1
42.5°	572.5	612.2	667.4	749.0
45°	530.6	559.2	610.2	686.7
47.5°	486.7	512.2	559.2	635.7
50°	445.9	467.3	508.2	579.6
52.5°	406.1	424.5	462.2	519.4
55°	370.4	387.8	415.3	471.4
57.5°	333.7	346.9	373.5	418.4
60°	298.0	310.2	331.6	368.4
62.5°	262.2	272.5	292.9	322.5
65°	230.6	238.8	254.1	279.6
67.5°	200.0	205.1	217.3	237.8
70°	170.4	174.5	184.7	201.0
72.5°	138.8	142.9	154.1	165.3
75°	112.2	113.3	121.4	130.6
77.5°	87.8	86.7	92.9	100.0
80°	60.2	63.3	68.4	71.4
82.5°	40.8	41.8	43.9	45.9
85°	22.4	23.5	23.5	26.5
87.5°	9.2	10.2	10.2	11.2
90°	5.8	4.1	2.4	0.7
92.5°	15.5	16.2	16.8	17.4
95°	29.9	35.0	40.1	45.2
97.5°	43.3	56.0	68.6	81.3
100°	59.5	80.6	101.8	122.9
102.5°	167.9	168.2	168.5	168.8
105°	225.1	220.4	215.8	211.2
107.5°	272.1	268.2	264.4	260.5
110°	317.4	314.2	310.9	307.7



TEST NUMBER: P998864

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	360.5	357.8	355.0	352.2
115°	407.3	404.6	402.0	399.4
117.5°	449.7	446.6	443.5	440.4
120°	493.2	490.9	488.5	486.2
122.5°	532.6	530.1	527.6	525.1
125°	570.8	568.7	566.7	564.7
127.5°	607.4	605.2	603.1	600.9
130°	642.3	639.8	637.4	634.9
132.5°	675.7	673.6	671.6	669.6
135°	706.2	703.7	701.3	698.8
137.5°	734.9	733.1	731.2	729.4
140°	762.9	761.7	760.4	759.2
142.5°	787.5	786.4	785.3	784.2
145°	810.1	810.3	810.4	810.6
147.5°	832.2	832.7	833.1	833.6
150°	852.5	853.6	854.7	855.8
152.5°	870.8	872.1	873.3	874.5
155°	888.4	889.8	891.2	892.6
157.5°	903.5	904.7	906.0	907.2
160°	916.9	917.8	918.8	919.7
162.5°	928.0	928.9	929.9	930.8
165°	937.8	938.7	939.6	940.5
167.5°	945.4	946.3	947.3	948.2
170°	951.7	952.6	953.5	954.4
172.5°	955.8	956.7	957.7	958.6
175°	958.8	959.9	961.0	962.1
177.5°	960.2	961.3	962.3	963.4
180°	960.0	960.0	960.0	960.0

TEST NUMBER: P998864

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.52	17.35	17.47	18.32	19.58	14.01	14.85	14.97	15.81	17.07
	3H	17.33	18.08	18.30	19.05	20.33	15.35	16.10	16.32	17.08	18.36
	4H	17.50	18.20	18.48	19.18	20.47	15.82	16.52	16.80	17.50	18.79
	6H	17.54	18.19	18.53	19.18	20.48	16.12	16.77	17.11	17.76	19.06
	8H	17.52	18.14	18.52	19.14	20.44	16.20	16.82	17.20	17.82	19.13
	12H	17.48	18.07	18.48	19.06	20.39	16.25	16.84	17.25	17.83	19.15
4H	2H	16.56	17.26	17.54	18.24	19.53	14.45	15.16	15.44	16.14	17.43
	3H	17.54	18.12	18.53	19.13	20.44	15.91	16.50	16.91	17.51	18.81
	4H	17.81	18.35	18.82	19.35	20.68	16.45	16.98	17.45	17.99	19.31
	6H	17.94	18.40	18.96	19.43	20.75	16.83	17.29	17.84	18.31	19.64
	8H	17.94	18.37	18.95	19.39	20.73	16.94	17.37	17.95	18.38	19.72
	12H	17.90	18.29	18.94	19.32	20.67	16.99	17.38	18.03	18.41	19.76
8H	4H	17.82	18.25	18.83	19.27	20.61	16.59	17.02	17.60	18.04	19.38
	6H	18.00	18.35	19.04	19.41	20.75	17.02	17.38	18.06	18.44	19.77
	8H	18.03	18.34	19.07	19.39	20.74	17.17	17.48	18.22	18.53	19.89
	12H	18.01	18.29	19.06	19.33	20.73	17.26	17.54	18.31	18.58	19.98
12H	4H	17.77	18.16	18.81	19.20	20.54	16.56	16.95	17.59	17.98	19.33
	6H	17.98	18.29	19.02	19.33	20.69	17.02	17.33	18.07	18.38	19.74
	8H	18.01	18.28	19.06	19.32	20.72	17.18	17.45	18.23	18.49	19.89