

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998171

Luminaire Tested: SA2XXDIP-B290D330UB35-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998171
REPORT IS A COMBINATION OF REPORTS P983911 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B290D330UB35-4F0-XX-W2A-A
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2599.0 lumens
Efficiency: N/A
Efficacy: 116.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998171

CATALOG NUMBER: SA2XXDIP-B290D330UB35-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P998171

CATALOG NUMBER: SA2XXDIP-B290D330UB35-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	54	48	51	46	42	43	40	37	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	30	27
6	64	52	44	39	59	49	42	37	42	36	32	36	31	28	30	27	24
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9148	9148	9148	9148
5°	9169	9753	9205	7760
10°	9062	10647	9120	6398
15°	8843	11230	8966	5389
20°	8706	10545	8706	4684
25°	8428	9060	8466	4189
30°	7971	7121	8124	3794
35°	7566	4924	7693	3471
40°	7102	3717	7183	3214
45°	6528	3056	6635	2936
50°	6033	2681	6043	2688
55°	5468	2286	5502	2418
60°	4867	1908	4934	2111
65°	4326	1552	4405	1802
70°	3789	1217	3885	1454
75°	3183	884	3306	1055
80°	2483	561	2659	626
85°	1624	282	1752	209

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 9457 cd/sqm

TEST NUMBER: P998171

CATALOG NUMBER: SA2XXDIP-B290D330UB35-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.0	2.1
10°-20°	160.2	6.2
20°-30°	232.5	8.9
30°-40°	245.1	9.4
40°-50°	216.9	8.3
50°-60°	173.2	6.7
60°-70°	117.6	4.5
70°-80°	60.2	2.3
80°-90°	15.0	0.6
90°-100°	14.9	0.6
100°-110°	55.5	2.1
110°-120°	147.1	5.7
120°-130°	244.0	9.4
130°-140°	259.2	10.0
140°-150°	240.9	9.3
150°-160°	193.7	7.5
160°-170°	124.8	4.8
170°-180°	43.0	1.7
0°-30°	447.8	17.2
0°-40°	692.9	26.7
0°-60°	1083.0	41.7
0°-90°	1275.8	49.1
90°-120°	217.5	8.4
90°-150°	961.7	37.0
90°-180°	1323.0	50.9
0°-180°	2599.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	578	578	578	578	578	
5°	578	645	581	514	578	55
15°	543	793	551	381	543	153
25°	488	661	490	306	488	223
35°	398	360	405	254	398	249
45°	299	217	304	208	299	232
55°	205	152	206	161	205	183
65°	122	94	124	109	122	121
75°	57	46	59	55	57	61
85°	12	12	12	9	12	13
90°	0	9	0	9	0	2
95°	21	14	21	14	21	25
105°	99	25	99	25	99	106
115°	188	27	188	27	188	185
125°	266	279	266	279	266	237
135°	329	339	329	339	329	254
145°	381	387	381	387	381	238
155°	420	420	420	420	420	193
165°	442	441	442	441	442	125
175°	452	450	452	450	452	43
180°	451	451	451	451	451	

TEST NUMBER: P998171

CATALOG NUMBER: SA2XXDIP-B290D330UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	581.0	582.3	584.6	585.0	589.4	593.0	597.0	597.0	598.3	597.9	594.3
5°	578.3	582.3	588.1	593.0	601.0	604.5	609.9	613.9	617.4	620.1	619.6
7.5°	573.9	581.0	589.4	598.8	609.4	615.6	623.2	630.3	635.2	639.6	642.7
10°	566.3	578.3	589.9	602.3	616.1	624.5	633.4	642.7	650.3	658.7	666.7
12.5°	556.1	573.4	587.7	604.1	621.0	630.3	644.5	651.6	666.3	687.6	693.4
15°	543.2	566.8	580.1	601.0	623.2	630.7	650.3	661.8	692.0	705.4	721.4
17.5°	531.2	557.5	575.2	599.2	621.0	635.6	654.7	678.3	703.6	722.7	740.5
20°	521.5	546.8	568.1	594.8	622.3	641.0	661.0	689.4	716.9	736.5	750.2
22.5°	499.3	531.7	556.6	586.3	619.6	645.4	664.5	695.6	725.4	737.4	749.3
25°	488.2	516.1	545.0	578.8	617.9	648.5	665.0	699.6	725.8	730.2	732.9
27.5°	467.7	499.3	533.0	571.7	617.4	643.2	664.1	695.6	716.5	713.4	705.4
30°	442.4	481.1	518.4	560.1	611.2	639.2	658.7	687.6	698.3	682.3	668.1
32.5°	423.8	460.2	501.5	549.9	604.1	630.7	649.8	672.5	674.7	645.9	621.9
35°	398.4	438.9	485.5	536.6	592.1	616.1	633.9	647.6	637.0	596.5	568.1
37.5°	375.8	415.8	465.5	517.5	575.7	599.2	613.4	615.6	589.4	553.9	512.1
40°	350.9	392.2	444.2	498.8	557.5	577.9	586.8	580.1	542.4	501.0	452.6
42.5°	326.0	366.9	422.9	478.8	534.4	551.7	555.2	537.0	490.8	442.4	386.4
45°	298.9	341.6	397.5	454.0	507.7	517.5	517.9	491.7	437.1	386.4	334.5
47.5°	276.7	316.3	371.8	428.2	473.5	480.2	477.5	447.3	387.8	330.9	285.6
50°	252.3	290.1	345.1	400.7	439.3	441.1	434.4	391.3	333.1	281.2	245.2
52.5°	226.1	264.3	314.9	368.2	402.9	400.2	387.3	341.1	286.5	243.4	215.9
55°	205.2	239.0	286.5	338.5	362.9	355.4	341.1	294.1	251.0	214.5	190.6
57.5°	182.1	211.9	258.5	303.8	318.0	310.9	296.7	252.7	212.8	185.2	169.2
60°	160.4	187.4	228.3	266.1	277.2	269.6	253.2	213.7	184.8	161.7	149.7
62.5°	140.4	163.9	198.1	232.8	237.2	229.6	215.4	183.4	158.6	140.4	131.5
65°	121.7	143.9	171.5	197.7	201.7	193.7	179.0	155.9	135.0	123.5	115.0
67.5°	103.5	121.3	145.7	164.8	167.0	159.5	147.5	128.8	115.9	103.5	97.3
70°	87.5	100.8	119.9	135.5	136.4	129.3	123.0	106.2	96.4	87.5	82.6
72.5°	72.0	81.3	95.9	107.5	107.9	103.5	97.7	87.1	78.6	72.4	67.5
75°	56.9	64.9	73.7	84.0	83.5	80.0	75.5	68.8	61.7	57.7	55.5
77.5°	43.5	48.4	55.5	62.2	62.2	60.4	57.7	52.9	48.4	44.4	42.2
80°	31.1	34.2	40.0	42.2	43.1	42.6	40.4	36.9	35.1	32.0	31.1
82.5°	20.0	22.2	24.9	27.1	28.4	27.5	27.1	25.3	22.7	21.8	20.9
85°	11.5	12.4	13.8	15.1	15.5	15.1	16.0	14.7	13.3	13.3	12.9
87.5°	4.9	5.3	6.2	6.2	6.7	6.7	6.2	6.7	6.7	6.2	5.8
90°	0.3	1.1	1.9	2.7	3.5	3.9	4.2	4.8	5.3	5.9	6.5
92.5°	8.2	7.9	7.6	7.3	7.0	6.9	7.0	7.2	7.4	7.6	7.8
95°	21.2	18.8	16.4	14.1	11.7	10.5	10.7	11.2	11.7	12.2	12.7
97.5°	38.2	32.2	26.3	20.3	14.4	11.4	12.0	13.2	14.3	15.5	16.7
100°	57.8	47.9	37.9	28.0	18.1	13.1	13.7	14.9	16.2	17.4	18.6
102.5°	79.4	79.2	79.1	78.9	78.8	78.7	72.1	58.9	45.7	32.5	19.3
105°	99.3	101.5	103.7	105.8	108.0	109.1	99.2	79.4	59.5	39.7	19.9
107.5°	122.5	124.3	126.1	127.9	129.7	130.6	118.4	93.9	69.5	45.0	20.6
110°	144.7	146.2	147.7	149.2	150.7	151.5	141.0	120.1	99.1	78.2	57.2

TEST NUMBER: P998171

CATALOG NUMBER: SA2XXDIP-B290D330UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	165.6	166.9	168.2	169.5	170.8	171.5	170.9	169.6	168.4	167.1	165.9
115°	187.8	189.0	190.2	191.5	192.7	193.3	194.2	196.0	197.9	199.7	201.5
117.5°	207.1	208.5	210.0	211.4	212.9	213.6	214.2	215.4	216.7	217.9	219.1
120°	228.6	229.7	230.8	231.9	233.0	233.5	234.2	235.5	236.8	238.1	239.4
122.5°	246.9	248.1	249.2	250.4	251.5	252.1	252.8	254.3	255.8	257.2	258.7
125°	265.5	266.5	267.4	268.4	269.3	269.8	270.5	271.9	273.2	274.6	276.0
127.5°	282.5	283.5	284.5	285.6	286.6	287.1	287.6	288.7	289.8	290.9	292.0
130°	298.5	299.7	300.8	302.0	303.1	303.7	304.1	304.9	305.7	306.5	307.3
132.5°	314.8	315.8	316.7	317.7	318.6	319.1	319.5	320.3	321.1	321.9	322.7
135°	328.6	329.8	330.9	332.1	333.2	333.8	334.1	334.8	335.4	336.1	336.7
137.5°	342.9	343.8	344.6	345.5	346.4	346.8	347.2	347.9	348.6	349.4	350.1
140°	357.0	357.6	358.2	358.7	359.3	359.6	360.0	360.8	361.6	362.4	363.2
142.5°	368.7	369.2	369.7	370.2	370.7	371.0	371.5	372.4	373.4	374.3	375.3
145°	381.1	381.0	381.0	380.9	380.8	380.8	381.4	382.7	383.9	385.2	386.4
147.5°	391.9	391.7	391.5	391.2	391.0	390.9	391.5	392.8	394.0	395.3	396.5
150°	402.4	401.9	401.4	400.9	400.4	400.1	400.7	401.8	403.0	404.1	405.3
152.5°	411.2	410.6	410.0	409.5	408.9	408.6	409.1	410.2	411.3	412.4	413.5
155°	419.7	419.0	418.4	417.7	417.0	416.7	417.1	418.0	418.9	419.8	420.7
157.5°	426.5	425.9	425.3	424.8	424.2	423.9	424.2	424.9	425.6	426.2	426.9
160°	432.4	432.0	431.6	431.1	430.7	430.5	430.7	431.1	431.6	432.0	432.4
162.5°	437.6	437.2	436.8	436.3	435.9	435.7	435.9	436.2	436.6	436.9	437.3
165°	442.2	441.8	441.3	440.9	440.4	440.2	440.3	440.5	440.8	441.0	441.2
167.5°	445.8	445.4	444.9	444.5	444.0	443.8	443.9	444.1	444.4	444.6	444.8
170°	448.7	448.3	447.9	447.4	447.0	446.8	446.9	447.0	447.1	447.3	447.4
172.5°	450.7	450.3	449.8	449.4	448.9	448.7	448.8	448.9	449.1	449.2	449.4
175°	452.3	451.8	451.3	450.8	450.3	450.0	450.1	450.2	450.4	450.5	450.7
177.5°	453.0	452.5	452.0	451.5	451.0	450.7	450.7	450.8	450.9	450.9	451.0
180°	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4

TEST NUMBER: P998171

CATALOG NUMBER: SA2XXDIP-B290D330UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	600.5	601.0	601.9	606.3	608.5	609.0	607.2	611.2	612.5	611.2	610.3
5°	629.0	631.6	637.0	642.7	642.3	642.7	645.4	648.1	649.0	645.4	646.7
7.5°	653.8	659.2	665.0	673.8	673.8	678.3	680.1	682.3	687.6	684.9	684.1
10°	682.3	689.4	700.0	714.3	714.7	719.1	723.6	730.7	732.9	731.1	732.0
12.5°	717.8	731.6	732.5	748.0	755.1	756.0	763.1	761.8	766.2	766.2	773.8
15°	733.4	754.7	766.7	781.8	786.2	780.9	786.7	792.9	793.3	793.3	792.9
17.5°	761.3	769.8	781.8	789.8	791.5	791.5	792.0	794.7	792.9	789.3	792.0
20°	767.1	770.7	775.1	774.2	775.1	770.7	766.2	761.8	762.2	760.0	766.7
22.5°	756.5	755.6	745.3	738.7	738.7	729.8	721.4	717.4	713.4	714.7	716.9
25°	729.8	716.0	703.6	693.8	691.6	677.4	665.8	662.3	655.6	661.0	661.8
27.5°	687.2	671.6	651.6	643.2	631.6	625.9	617.9	607.2	593.4	601.4	600.1
30°	641.4	618.3	601.9	581.4	563.2	561.9	546.8	529.0	521.9	521.9	525.9
32.5°	590.3	559.7	535.7	506.8	489.1	481.5	463.3	445.5	449.5	436.2	441.1
35°	530.8	490.4	460.2	432.2	418.9	410.0	386.4	376.7	366.0	359.8	371.3
37.5°	473.9	427.3	388.7	358.0	353.1	337.1	321.1	314.9	308.7	311.4	310.9
40°	404.7	363.3	328.7	304.7	296.3	288.7	278.1	270.5	266.5	268.7	269.2
42.5°	342.0	307.4	281.6	264.7	257.6	252.3	247.0	240.8	239.4	239.4	241.2
45°	293.6	265.2	247.9	234.1	230.1	226.1	222.1	219.4	218.5	216.8	218.1
47.5°	255.0	232.3	221.7	211.4	207.0	206.1	202.6	201.2	199.4	199.0	199.4
50°	222.5	208.3	198.6	192.8	189.7	188.3	186.6	183.9	183.0	185.2	184.3
52.5°	199.9	186.6	181.2	175.5	173.7	171.9	169.2	169.7	169.2	168.3	168.3
55°	177.2	168.8	163.5	159.0	158.6	156.8	154.6	153.7	153.2	152.4	153.7
57.5°	159.0	152.4	147.5	143.5	141.7	141.7	139.5	137.7	137.7	137.3	137.7
60°	140.8	134.1	131.0	127.0	125.7	125.3	123.9	123.0	121.7	121.7	121.7
62.5°	123.9	118.6	115.0	111.5	111.9	109.7	107.9	107.0	107.0	107.5	107.5
65°	107.9	104.4	99.9	96.8	95.9	95.5	94.6	94.2	92.8	93.7	93.7
67.5°	93.3	88.4	85.7	84.4	83.1	82.6	81.7	80.8	80.4	80.0	80.8
70°	78.6	74.6	72.4	71.5	70.2	69.7	69.3	68.0	68.4	68.8	69.3
72.5°	65.3	61.7	61.3	58.6	58.6	58.6	56.9	57.7	57.3	56.4	57.3
75°	51.5	49.7	48.9	47.5	48.0	47.5	47.1	45.8	45.8	46.2	46.6
77.5°	40.9	39.1	38.6	37.3	36.4	37.3	36.4	36.0	36.0	36.4	36.4
80°	30.2	29.3	28.0	28.0	28.0	27.5	27.5	27.5	27.1	26.7	27.1
82.5°	20.0	20.0	19.5	19.1	19.5	18.7	19.1	19.1	19.1	19.1	19.1
85°	12.9	12.4	12.4	12.0	12.0	12.0	12.4	11.5	11.5	12.0	12.0
87.5°	5.8	5.8	5.8	6.2	5.8	5.8	5.8	6.2	5.8	5.8	5.8
90°	6.9	7.3	7.6	8.0	8.2	8.3	8.4	8.5	8.7	8.8	8.7
92.5°	8.0	8.1	8.3	8.4	8.5	8.5	8.6	8.7	8.7	8.8	8.7
95°	13.1	13.5	13.8	14.2	14.4	14.4	14.3	14.2	14.1	14.0	14.1
97.5°	16.9	17.1	17.3	17.5	17.6	17.6	17.7	17.8	17.9	18.0	17.9
100°	19.2	19.8	20.3	20.9	21.2	21.3	21.4	21.6	21.7	21.9	21.7
102.5°	20.1	20.9	21.7	22.5	22.9	23.0	23.2	23.4	23.6	23.8	23.6
105°	20.7	21.5	22.3	23.1	23.5	23.6	23.9	24.2	24.5	24.8	24.5
107.5°	21.4	22.2	23.0	23.8	24.2	24.3	24.6	24.9	25.2	25.5	25.2
110°	49.9	42.7	35.4	28.1	24.5	24.6	24.9	25.2	25.5	25.8	25.5

TEST NUMBER: P998171

CATALOG NUMBER: SA2XXDIP-B290D330UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	134.6	103.3	72.0	40.7	25.1	25.2	25.4	25.7	25.9	26.1	25.9
115°	167.9	134.3	100.7	67.1	50.3	47.7	42.5	37.2	32.0	26.8	32.0
117.5°	208.7	198.3	188.0	177.6	172.4	162.9	143.9	124.9	105.9	86.9	105.9
120°	240.3	241.1	242.0	242.9	243.3	238.4	228.6	218.8	209.0	199.2	209.0
122.5°	259.1	259.5	260.0	260.4	260.6	260.6	260.7	260.8	260.8	260.9	260.8
125°	276.5	277.0	277.5	278.0	278.3	278.4	278.6	278.8	279.0	279.2	279.0
127.5°	292.7	293.4	294.1	294.8	295.2	295.2	295.3	295.4	295.5	295.6	295.5
130°	308.1	308.9	309.7	310.5	310.9	310.9	310.8	310.7	310.7	310.6	310.7
132.5°	323.3	324.0	324.6	325.3	325.6	325.6	325.5	325.4	325.4	325.3	325.4
135°	337.4	338.2	338.9	339.6	340.0	339.9	339.8	339.6	339.5	339.3	339.5
137.5°	350.8	351.6	352.3	353.0	353.4	353.3	353.1	352.8	352.6	352.4	352.6
140°	363.8	364.5	365.1	365.8	366.1	365.9	365.6	365.2	364.9	364.5	364.9
142.5°	375.9	376.5	377.0	377.6	377.9	377.7	377.3	377.0	376.6	376.2	376.6
145°	386.9	387.4	387.9	388.4	388.6	388.4	388.1	387.7	387.4	387.0	387.4
147.5°	396.9	397.2	397.6	397.9	398.1	398.0	397.7	397.4	397.1	396.8	397.1
150°	405.7	406.2	406.6	407.1	407.3	407.1	406.7	406.4	406.0	405.6	406.0
152.5°	413.9	414.3	414.8	415.2	415.4	415.1	414.6	414.1	413.6	413.1	413.6
155°	421.1	421.5	422.0	422.4	422.6	422.3	421.7	421.2	420.6	420.0	420.6
157.5°	427.4	427.9	428.4	428.9	429.1	428.8	428.2	427.7	427.1	426.5	427.1
160°	432.8	433.3	433.7	434.2	434.4	434.1	433.6	433.1	432.6	432.1	432.6
162.5°	437.8	438.3	438.8	439.3	439.6	439.3	438.6	438.0	437.3	436.7	437.3
165°	441.7	442.2	442.7	443.2	443.5	443.2	442.7	442.2	441.7	441.2	441.7
167.5°	445.3	445.8	446.3	446.8	447.1	446.8	446.1	445.5	444.8	444.2	444.8
170°	447.9	448.4	448.9	449.4	449.7	449.4	448.7	448.1	447.4	446.8	447.4
172.5°	449.9	450.4	450.9	451.4	451.7	451.4	450.7	450.0	449.4	448.7	449.4
175°	451.2	451.7	452.2	452.7	453.0	452.6	451.9	451.2	450.4	449.7	450.4
177.5°	451.5	452.0	452.5	453.0	453.3	453.0	452.3	451.7	451.0	450.4	451.0
180°	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4

TEST NUMBER: P998171

CATALOG NUMBER: SA2XXDIP-B290D330UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	612.5	609.4	606.8	607.2	609.4	607.7	603.2	597.4	595.2	592.5	595.2
5°	649.4	646.7	641.4	641.9	640.5	638.7	631.6	622.8	622.8	615.6	614.8
7.5°	685.8	681.8	678.3	677.4	672.5	668.9	662.7	650.3	645.4	637.0	632.1
10°	726.7	723.6	719.6	714.7	712.0	705.8	695.6	677.4	668.5	657.0	648.5
12.5°	768.0	767.6	758.7	748.9	748.5	738.7	731.6	707.1	695.2	679.6	659.6
15°	794.2	792.0	787.1	782.2	783.5	772.9	756.9	728.0	720.0	701.4	680.1
17.5°	793.8	793.8	792.4	791.5	790.2	787.1	778.2	759.1	746.2	722.7	702.7
20°	768.4	774.2	775.6	775.1	779.6	781.8	781.3	769.3	759.1	738.2	717.8
22.5°	717.8	731.1	736.9	740.5	749.8	754.7	766.2	761.8	759.1	743.6	726.2
25°	670.7	675.2	692.5	693.4	706.3	718.3	729.8	737.4	747.1	741.4	726.7
27.5°	609.9	620.1	632.5	641.9	644.5	668.9	688.0	702.3	724.5	726.2	721.4
30°	541.0	545.9	566.3	578.8	593.0	610.8	638.3	662.7	682.7	700.9	707.1
32.5°	457.1	477.1	489.1	504.2	516.6	548.1	581.9	613.4	636.5	667.2	680.5
35°	380.2	395.8	416.2	422.4	445.1	471.7	515.7	556.1	591.2	622.3	649.4
37.5°	316.7	329.1	350.9	360.7	374.0	408.2	445.1	495.3	537.5	575.7	609.4
40°	273.2	282.5	298.9	302.0	313.2	344.2	374.0	421.1	477.1	528.6	565.5
42.5°	243.4	247.9	259.0	263.0	270.1	290.9	317.6	362.0	414.0	467.3	519.3
45°	222.1	225.2	231.9	235.4	244.3	253.6	275.4	310.9	351.8	405.5	461.5
47.5°	203.0	207.0	209.7	211.9	216.8	227.0	241.2	267.4	306.5	355.8	410.0
50°	187.0	188.3	193.2	193.7	196.8	203.4	216.8	232.8	263.8	303.8	356.2
52.5°	171.0	172.3	175.5	178.6	179.9	185.2	194.1	207.4	230.5	262.1	308.7
55°	155.0	156.8	159.9	162.1	163.5	167.9	173.2	186.1	204.3	226.5	264.7
57.5°	139.0	143.0	143.9	145.2	147.5	152.4	157.2	164.8	179.0	199.4	227.4
60°	123.9	125.3	128.4	129.7	131.9	134.6	140.8	146.6	156.8	172.8	198.1
62.5°	108.4	111.5	112.8	114.2	115.9	119.0	123.0	129.3	138.1	151.0	171.0
65°	95.1	95.5	98.2	99.9	101.7	103.9	107.9	113.7	119.0	131.0	145.7
67.5°	82.2	83.1	84.0	85.7	87.9	90.2	93.7	96.8	103.5	111.5	123.0
70°	69.7	69.7	72.0	73.3	72.8	75.5	78.2	81.7	86.6	94.2	103.5
72.5°	58.6	58.2	60.0	60.4	61.3	63.1	64.9	68.4	71.1	76.8	84.0
75°	46.6	47.5	48.4	48.4	49.7	51.1	52.9	54.6	57.7	61.3	66.6
77.5°	36.9	36.9	37.8	38.2	39.5	39.1	40.9	42.6	44.9	48.0	52.0
80°	27.1	28.0	28.0	28.0	28.4	28.9	30.6	32.0	33.3	35.5	37.3
82.5°	19.1	19.1	20.0	20.0	20.0	20.9	20.9	21.3	22.2	23.5	24.9
85°	12.0	12.0	12.0	12.4	12.0	12.4	13.3	12.9	13.3	14.2	14.2
87.5°	5.8	5.8	5.8	5.8	5.8	6.2	5.8	6.2	6.7	6.7	6.7
90°	8.5	8.4	8.3	8.2	8.0	7.6	7.3	6.9	6.5	5.9	5.3
92.5°	8.7	8.6	8.5	8.5	8.4	8.3	8.1	8.0	7.8	7.6	7.4
95°	14.2	14.3	14.4	14.4	14.2	13.8	13.5	13.1	12.7	12.2	11.7
97.5°	17.8	17.7	17.6	17.6	17.5	17.3	17.1	16.9	16.7	15.5	14.3
100°	21.6	21.4	21.3	21.2	20.9	20.3	19.8	19.2	18.6	17.4	16.2
102.5°	23.4	23.2	23.0	22.9	22.5	21.7	20.9	20.1	19.3	32.5	45.7
105°	24.2	23.9	23.6	23.5	23.1	22.3	21.5	20.7	19.9	39.7	59.5
107.5°	24.9	24.6	24.3	24.2	23.8	23.0	22.2	21.4	20.6	45.0	69.5
110°	25.2	24.9	24.6	24.5	28.1	35.4	42.7	49.9	57.2	78.2	99.1

TEST NUMBER: P998171

CATALOG NUMBER: SA2XXDIP-B290D330UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	25.7	25.4	25.2	25.1	40.7	72.0	103.3	134.6	165.9	167.1	168.4
115°	37.2	42.5	47.7	50.3	67.1	100.7	134.3	167.9	201.5	199.7	197.9
117.5°	124.9	143.9	162.9	172.4	177.6	188.0	198.3	208.7	219.1	217.9	216.7
120°	218.8	228.6	238.4	243.3	242.9	242.0	241.1	240.3	239.4	238.1	236.8
122.5°	260.8	260.7	260.6	260.6	260.4	260.0	259.5	259.1	258.7	257.2	255.8
125°	278.8	278.6	278.4	278.3	278.0	277.5	277.0	276.5	276.0	274.6	273.2
127.5°	295.4	295.3	295.2	295.2	294.8	294.1	293.4	292.7	292.0	290.9	289.8
130°	310.7	310.8	310.9	310.9	310.5	309.7	308.9	308.1	307.3	306.5	305.7
132.5°	325.4	325.5	325.6	325.6	325.3	324.6	324.0	323.3	322.7	321.9	321.1
135°	339.6	339.8	339.9	340.0	339.6	338.9	338.2	337.4	336.7	336.1	335.4
137.5°	352.8	353.1	353.3	353.4	353.0	352.3	351.6	350.8	350.1	349.4	348.6
140°	365.2	365.6	365.9	366.1	365.8	365.1	364.5	363.8	363.2	362.4	361.6
142.5°	377.0	377.3	377.7	377.9	377.6	377.0	376.5	375.9	375.3	374.3	373.4
145°	387.7	388.1	388.4	388.6	388.4	387.9	387.4	386.9	386.4	385.2	383.9
147.5°	397.4	397.7	398.0	398.1	397.9	397.6	397.2	396.9	396.5	395.3	394.0
150°	406.4	406.7	407.1	407.3	407.1	406.6	406.2	405.7	405.3	404.1	403.0
152.5°	414.1	414.6	415.1	415.4	415.2	414.8	414.3	413.9	413.5	412.4	411.3
155°	421.2	421.7	422.3	422.6	422.4	422.0	421.5	421.1	420.7	419.8	418.9
157.5°	427.7	428.2	428.8	429.1	428.9	428.4	427.9	427.4	426.9	426.2	425.6
160°	433.1	433.6	434.1	434.4	434.2	433.7	433.3	432.8	432.4	432.0	431.6
162.5°	438.0	438.6	439.3	439.6	439.3	438.8	438.3	437.8	437.3	436.9	436.6
165°	442.2	442.7	443.2	443.5	443.2	442.7	442.2	441.7	441.2	441.0	440.8
167.5°	445.5	446.1	446.8	447.1	446.8	446.3	445.8	445.3	444.8	444.6	444.4
170°	448.1	448.7	449.4	449.7	449.4	448.9	448.4	447.9	447.4	447.3	447.1
172.5°	450.0	450.7	451.4	451.7	451.4	450.9	450.4	449.9	449.4	449.2	449.1
175°	451.2	451.9	452.6	453.0	452.7	452.2	451.7	451.2	450.7	450.5	450.4
177.5°	451.7	452.3	453.0	453.3	453.0	452.5	452.0	451.5	451.0	450.9	450.9
180°	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4

TEST NUMBER: P998171

CATALOG NUMBER: SA2XXDIP-B290D330UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	593.0	590.8	589.4	590.3	587.7	581.0	581.0	583.2	580.6	577.9	573.9
5°	609.4	605.0	602.3	601.9	595.7	585.0	582.8	580.6	574.8	568.6	561.9
7.5°	625.4	617.4	613.0	609.9	601.0	587.2	581.4	576.6	567.2	557.9	549.5
10°	638.7	627.2	621.9	617.0	605.4	588.1	578.8	569.9	557.9	545.9	535.2
12.5°	649.4	636.1	629.4	622.3	608.1	585.4	573.9	559.7	547.7	531.7	521.0
15°	667.2	639.6	633.4	626.8	612.1	581.0	566.8	550.8	534.4	513.0	501.5
17.5°	681.4	644.5	644.1	629.9	610.8	579.2	557.5	536.6	518.8	497.5	479.3
20°	689.8	652.1	645.0	630.3	606.3	567.2	544.6	521.5	502.4	476.6	458.4
22.5°	696.9	662.7	644.1	626.3	597.0	563.2	529.9	508.2	481.9	454.0	436.6
25°	699.6	665.0	645.4	625.0	590.3	551.7	513.9	490.4	461.1	435.7	412.2
27.5°	700.0	664.5	640.5	619.2	581.0	536.6	497.9	473.1	440.6	411.3	387.8
30°	695.6	659.6	637.9	614.8	572.1	522.8	478.4	450.9	416.2	386.9	362.5
32.5°	682.3	649.8	632.1	606.8	560.6	503.7	459.7	429.1	392.7	363.8	340.2
35°	660.1	637.9	618.3	594.8	545.5	485.9	441.1	405.1	368.2	340.7	318.5
37.5°	632.5	620.5	602.3	579.2	528.1	470.0	420.2	380.2	343.4	316.7	294.9
40°	595.2	598.3	580.6	559.7	507.7	448.2	393.1	354.9	320.3	295.4	274.1
42.5°	554.8	567.7	557.5	537.5	485.1	424.2	373.1	330.9	297.2	271.4	253.6
45°	511.3	533.5	527.3	512.6	461.5	398.9	344.7	303.8	274.1	249.2	233.6
47.5°	463.7	495.3	495.3	484.6	435.3	373.6	320.3	278.5	249.2	231.4	216.3
50°	415.3	450.9	456.6	449.5	406.0	344.7	290.5	252.7	227.4	210.1	199.0
52.5°	364.7	406.0	416.6	413.1	374.9	317.2	266.1	229.2	206.1	191.0	181.2
55°	316.3	364.2	375.8	377.1	341.6	286.9	239.0	206.5	184.3	174.1	165.7
57.5°	270.5	316.7	329.6	331.8	307.8	259.4	213.7	185.2	165.2	156.8	150.1
60°	231.4	270.1	286.9	291.8	271.0	227.4	190.1	162.6	147.5	139.5	133.3
62.5°	199.4	230.5	248.3	249.6	240.3	199.4	165.7	142.6	129.7	122.6	119.5
65°	168.3	196.3	207.0	212.3	204.8	172.8	143.0	123.9	113.7	107.5	104.4
67.5°	143.5	161.2	170.1	177.2	169.7	145.7	121.7	106.2	98.6	92.4	90.6
70°	117.7	132.4	139.0	146.1	139.5	121.3	103.9	89.7	83.1	78.2	76.0
72.5°	94.2	105.7	111.9	116.4	112.4	97.3	83.1	73.3	68.4	64.9	63.5
75°	74.6	82.6	86.2	89.3	87.5	76.0	67.1	59.1	54.6	51.5	50.6
77.5°	56.9	62.6	66.6	67.5	65.3	57.7	50.2	45.3	41.8	40.0	39.1
80°	40.4	44.0	46.2	47.5	45.3	42.2	36.9	33.3	30.2	28.0	27.5
82.5°	27.1	28.9	30.6	30.2	29.3	26.7	23.5	21.8	20.4	18.7	18.7
85°	15.5	16.0	16.9	17.3	16.9	15.1	13.3	12.4	11.5	10.2	10.2
87.5°	6.7	7.1	7.1	7.6	6.7	6.7	5.8	4.9	4.9	4.4	4.0
90°	4.8	4.2	3.9	3.5	2.7	1.9	1.1	0.3	1.1	1.9	2.7
92.5°	7.2	7.0	6.9	7.0	7.3	7.6	7.9	8.2	7.9	7.6	7.3
95°	11.2	10.7	10.5	11.7	14.1	16.4	18.8	21.2	18.8	16.4	14.1
97.5°	13.2	12.0	11.4	14.4	20.3	26.3	32.2	38.2	32.2	26.3	20.3
100°	14.9	13.7	13.1	18.1	28.0	37.9	47.9	57.8	47.9	37.9	28.0
102.5°	58.9	72.1	78.7	78.8	78.9	79.1	79.2	79.4	79.2	79.1	78.9
105°	79.4	99.2	109.1	108.0	105.8	103.7	101.5	99.3	101.5	103.7	105.8
107.5°	93.9	118.4	130.6	129.7	127.9	126.1	124.3	122.5	124.3	126.1	127.9
110°	120.1	141.0	151.5	150.7	149.2	147.7	146.2	144.7	146.2	147.7	149.2

TEST NUMBER: P998171

CATALOG NUMBER: SA2XXDIP-B290D330UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	169.6	170.9	171.5	170.8	169.5	168.2	166.9	165.6	166.9	168.2	169.5
115°	196.0	194.2	193.3	192.7	191.5	190.2	189.0	187.8	189.0	190.2	191.5
117.5°	215.4	214.2	213.6	212.9	211.4	210.0	208.5	207.1	208.5	210.0	211.4
120°	235.5	234.2	233.5	233.0	231.9	230.8	229.7	228.6	229.7	230.8	231.9
122.5°	254.3	252.8	252.1	251.5	250.4	249.2	248.1	246.9	248.1	249.2	250.4
125°	271.9	270.5	269.8	269.3	268.4	267.4	266.5	265.5	266.5	267.4	268.4
127.5°	288.7	287.6	287.1	286.6	285.6	284.5	283.5	282.5	283.5	284.5	285.6
130°	304.9	304.1	303.7	303.1	302.0	300.8	299.7	298.5	299.7	300.8	302.0
132.5°	320.3	319.5	319.1	318.6	317.7	316.7	315.8	314.8	315.8	316.7	317.7
135°	334.8	334.1	333.8	333.2	332.1	330.9	329.8	328.6	329.8	330.9	332.1
137.5°	347.9	347.2	346.8	346.4	345.5	344.6	343.8	342.9	343.8	344.6	345.5
140°	360.8	360.0	359.6	359.3	358.7	358.2	357.6	357.0	357.6	358.2	358.7
142.5°	372.4	371.5	371.0	370.7	370.2	369.7	369.2	368.7	369.2	369.7	370.2
145°	382.7	381.4	380.8	380.8	380.9	381.0	381.0	381.1	381.0	381.0	380.9
147.5°	392.8	391.5	390.9	391.0	391.2	391.5	391.7	391.9	391.7	391.5	391.2
150°	401.8	400.7	400.1	400.4	400.9	401.4	401.9	402.4	401.9	401.4	400.9
152.5°	410.2	409.1	408.6	408.9	409.5	410.0	410.6	411.2	410.6	410.0	409.5
155°	418.0	417.1	416.7	417.0	417.7	418.4	419.0	419.7	419.0	418.4	417.7
157.5°	424.9	424.2	423.9	424.2	424.8	425.3	425.9	426.5	425.9	425.3	424.8
160°	431.1	430.7	430.5	430.7	431.1	431.6	432.0	432.4	432.0	431.6	431.1
162.5°	436.2	435.9	435.7	435.9	436.3	436.8	437.2	437.6	437.2	436.8	436.3
165°	440.5	440.3	440.2	440.4	440.9	441.3	441.8	442.2	441.8	441.3	440.9
167.5°	444.1	443.9	443.8	444.0	444.5	444.9	445.4	445.8	445.4	444.9	444.5
170°	447.0	446.9	446.8	447.0	447.4	447.9	448.3	448.7	448.3	447.9	447.4
172.5°	448.9	448.8	448.7	448.9	449.4	449.8	450.3	450.7	450.3	449.8	449.4
175°	450.2	450.1	450.0	450.3	450.8	451.3	451.8	452.3	451.8	451.3	450.8
177.5°	450.8	450.7	450.7	451.0	451.5	452.0	452.5	453.0	452.5	452.0	451.5
180°	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4

TEST NUMBER: P998171

CATALOG NUMBER: SA2XXDIP-B290D330UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	571.7	573.9	573.4	569.0	564.1	560.1	552.6	553.5	550.8	551.2	553.9
5°	557.5	557.5	555.7	549.5	541.5	537.0	528.6	526.4	521.0	520.6	520.1
7.5°	542.4	540.1	537.9	529.0	519.3	512.1	500.6	497.9	492.6	489.1	487.3
10°	524.6	521.5	517.0	506.8	494.8	485.9	473.9	470.4	460.2	455.7	453.1
12.5°	505.0	503.3	496.2	487.7	468.2	458.4	441.1	444.6	434.4	425.5	424.2
15°	485.5	478.8	474.8	461.1	437.5	433.1	419.3	412.2	402.9	395.8	395.8
17.5°	466.4	456.2	447.3	432.6	415.3	402.9	392.7	389.1	377.6	370.5	369.1
20°	441.1	429.5	427.3	406.4	394.4	380.7	370.9	362.0	353.6	350.5	348.2
22.5°	417.1	403.8	400.2	382.4	370.5	356.7	346.9	340.7	334.5	332.3	328.3
25°	391.3	383.3	378.0	358.9	345.6	332.7	326.0	321.6	315.8	315.4	312.7
27.5°	366.5	358.9	353.6	335.4	325.6	313.6	308.3	303.4	300.3	298.9	297.6
30°	345.1	336.7	330.5	317.2	305.2	295.4	290.9	287.8	286.1	283.8	283.4
32.5°	321.6	316.7	308.3	298.1	288.7	279.4	276.7	274.5	271.8	271.0	270.5
35°	301.6	294.9	289.6	278.1	274.1	266.1	263.0	261.2	257.6	256.7	255.9
37.5°	282.1	275.8	270.1	263.0	255.4	251.0	249.2	246.5	244.7	245.2	244.3
40°	262.5	257.6	253.2	245.6	241.2	239.0	235.4	232.8	231.9	232.3	231.9
42.5°	243.4	239.0	236.3	230.5	226.1	223.9	221.7	219.0	220.3	220.3	221.7
45°	226.1	222.1	220.3	215.9	213.2	209.7	207.4	207.0	208.8	208.3	208.3
47.5°	208.3	207.0	204.8	200.8	197.2	195.0	194.6	194.6	196.3	197.2	196.8
50°	194.6	191.9	189.2	186.1	183.4	182.6	181.2	182.1	183.9	183.9	184.8
52.5°	177.2	175.5	174.6	171.9	170.1	170.1	170.1	170.6	171.9	173.2	172.8
55°	162.1	160.8	159.9	158.6	156.4	156.8	156.4	157.2	158.6	159.9	160.8
57.5°	146.1	145.7	144.8	142.6	142.6	142.1	143.5	143.9	146.1	147.0	148.4
60°	131.9	130.6	130.6	128.8	128.8	128.8	130.1	131.5	133.3	133.7	134.6
62.5°	116.8	116.8	116.4	115.0	115.0	116.4	116.8	118.6	119.5	119.5	120.8
65°	102.6	102.2	101.7	102.2	102.6	102.6	103.9	104.8	105.7	106.2	106.6
67.5°	88.4	87.9	88.8	88.4	89.3	91.1	90.6	91.9	93.3	93.3	93.7
70°	75.1	76.0	75.5	76.4	76.0	76.8	78.2	78.6	78.6	79.1	80.4
72.5°	62.6	62.6	62.6	62.2	62.6	63.5	64.4	64.9	65.7	66.2	67.5
75°	50.6	50.6	49.7	50.6	50.6	51.5	52.4	52.4	52.4	53.3	54.6
77.5°	38.2	38.6	38.2	39.1	39.1	39.5	40.4	40.0	40.9	41.3	41.8
80°	28.0	27.5	27.5	27.5	28.0	28.0	28.9	29.3	29.3	30.6	29.8
82.5°	17.8	18.2	17.8	18.2	18.2	18.7	18.2	18.7	19.1	20.0	19.5
85°	10.2	9.8	9.8	10.2	9.8	9.8	10.2	9.8	10.2	9.8	10.2
87.5°	4.0	3.6	3.6	3.6	3.6	3.1	3.1	2.7	2.7	2.7	2.2
90°	3.5	3.9	4.2	4.8	5.3	5.9	6.5	6.9	7.3	7.6	8.0
92.5°	7.0	6.9	7.0	7.2	7.4	7.6	7.8	8.0	8.1	8.3	8.4
95°	11.7	10.5	10.7	11.2	11.7	12.2	12.7	13.1	13.5	13.8	14.2
97.5°	14.4	11.4	12.0	13.2	14.3	15.5	16.7	16.9	17.1	17.3	17.5
100°	18.1	13.1	13.7	14.9	16.2	17.4	18.6	19.2	19.8	20.3	20.9
102.5°	78.8	78.7	72.1	58.9	45.7	32.5	19.3	20.1	20.9	21.7	22.5
105°	108.0	109.1	99.2	79.4	59.5	39.7	19.9	20.7	21.5	22.3	23.1
107.5°	129.7	130.6	118.4	93.9	69.5	45.0	20.6	21.4	22.2	23.0	23.8
110°	150.7	151.5	141.0	120.1	99.1	78.2	57.2	49.9	42.7	35.4	28.1

TEST NUMBER: P998171

CATALOG NUMBER: SA2XXDIP-B290D330UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	170.8	171.5	170.9	169.6	168.4	167.1	165.9	134.6	103.3	72.0	40.7
115°	192.7	193.3	194.2	196.0	197.9	199.7	201.5	167.9	134.3	100.7	67.1
117.5°	212.9	213.6	214.2	215.4	216.7	217.9	219.1	208.7	198.3	188.0	177.6
120°	233.0	233.5	234.2	235.5	236.8	238.1	239.4	240.3	241.1	242.0	242.9
122.5°	251.5	252.1	252.8	254.3	255.8	257.2	258.7	259.1	259.5	260.0	260.4
125°	269.3	269.8	270.5	271.9	273.2	274.6	276.0	276.5	277.0	277.5	278.0
127.5°	286.6	287.1	287.6	288.7	289.8	290.9	292.0	292.7	293.4	294.1	294.8
130°	303.1	303.7	304.1	304.9	305.7	306.5	307.3	308.1	308.9	309.7	310.5
132.5°	318.6	319.1	319.5	320.3	321.1	321.9	322.7	323.3	324.0	324.6	325.3
135°	333.2	333.8	334.1	334.8	335.4	336.1	336.7	337.4	338.2	338.9	339.6
137.5°	346.4	346.8	347.2	347.9	348.6	349.4	350.1	350.8	351.6	352.3	353.0
140°	359.3	359.6	360.0	360.8	361.6	362.4	363.2	363.8	364.5	365.1	365.8
142.5°	370.7	371.0	371.5	372.4	373.4	374.3	375.3	375.9	376.5	377.0	377.6
145°	380.8	380.8	381.4	382.7	383.9	385.2	386.4	386.9	387.4	387.9	388.4
147.5°	391.0	390.9	391.5	392.8	394.0	395.3	396.5	396.9	397.2	397.6	397.9
150°	400.4	400.1	400.7	401.8	403.0	404.1	405.3	405.7	406.2	406.6	407.1
152.5°	408.9	408.6	409.1	410.2	411.3	412.4	413.5	413.9	414.3	414.8	415.2
155°	417.0	416.7	417.1	418.0	418.9	419.8	420.7	421.1	421.5	422.0	422.4
157.5°	424.2	423.9	424.2	424.9	425.6	426.2	426.9	427.4	427.9	428.4	428.9
160°	430.7	430.5	430.7	431.1	431.6	432.0	432.4	432.8	433.3	433.7	434.2
162.5°	435.9	435.7	435.9	436.2	436.6	436.9	437.3	437.8	438.3	438.8	439.3
165°	440.4	440.2	440.3	440.5	440.8	441.0	441.2	441.7	442.2	442.7	443.2
167.5°	444.0	443.8	443.9	444.1	444.4	444.6	444.8	445.3	445.8	446.3	446.8
170°	447.0	446.8	446.9	447.0	447.1	447.3	447.4	447.9	448.4	448.9	449.4
172.5°	448.9	448.7	448.8	448.9	449.1	449.2	449.4	449.9	450.4	450.9	451.4
175°	450.3	450.0	450.1	450.2	450.4	450.5	450.7	451.2	451.7	452.2	452.7
177.5°	451.0	450.7	450.7	450.8	450.9	450.9	451.0	451.5	452.0	452.5	453.0
180°	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4

TEST NUMBER: P998171

CATALOG NUMBER: SA2XXDIP-B290D330UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	550.8	552.1	549.0	548.1	549.0	545.9	546.8	547.7	547.7	549.0	549.9
5°	518.8	517.0	513.9	513.0	512.1	513.5	512.6	513.9	514.4	517.5	517.9
7.5°	487.3	484.6	481.9	479.3	478.4	476.2	478.4	478.4	481.5	480.6	482.8
10°	450.0	449.5	446.0	444.6	442.9	439.3	444.2	442.9	445.1	449.1	450.0
12.5°	422.4	417.5	419.8	413.5	415.8	412.2	412.7	412.7	416.2	416.6	415.8
15°	396.2	392.2	386.4	383.8	382.4	380.7	386.4	386.9	384.2	390.4	388.2
17.5°	369.6	369.6	364.2	362.9	359.3	361.1	360.2	360.7	359.8	364.2	366.5
20°	346.5	344.2	342.5	342.9	338.5	337.6	336.7	337.6	340.7	343.8	344.7
22.5°	327.8	326.5	322.0	322.9	319.4	320.7	319.8	322.0	322.5	322.5	325.6
25°	310.0	308.3	308.7	306.9	305.6	305.6	304.3	305.6	307.4	308.3	308.7
27.5°	296.7	295.4	293.2	291.8	292.7	290.5	292.3	293.6	293.6	292.7	293.6
30°	280.7	281.6	281.6	277.2	279.0	278.1	279.4	280.3	280.3	280.7	279.8
32.5°	270.1	267.4	267.0	266.5	266.5	264.7	264.7	266.1	266.5	267.0	268.3
35°	255.9	255.9	253.6	255.0	253.2	253.6	253.2	253.6	254.5	253.2	254.5
37.5°	243.0	243.4	242.5	243.4	243.9	243.0	242.1	243.9	243.0	243.0	242.1
40°	231.9	231.4	231.9	231.9	231.9	232.3	231.4	231.4	231.4	230.5	229.6
42.5°	222.5	219.9	220.8	221.2	219.9	219.9	220.3	219.9	221.2	218.5	218.5
45°	209.2	208.3	208.8	208.8	209.7	208.3	209.2	209.7	208.3	207.9	207.0
47.5°	197.2	198.1	197.2	198.1	198.1	199.0	197.2	197.7	198.1	196.3	195.0
50°	185.2	185.2	186.6	186.1	186.6	185.7	185.7	185.2	185.7	184.8	183.4
52.5°	174.1	172.8	175.0	174.6	174.1	173.7	173.2	173.7	172.8	171.9	171.9
55°	160.4	160.4	161.7	162.1	162.1	161.2	160.4	160.8	160.4	159.9	159.5
57.5°	149.2	147.5	148.4	148.8	148.8	147.5	148.4	147.5	147.5	147.9	146.6
60°	135.0	135.0	134.1	135.5	135.5	134.6	134.6	135.0	134.1	133.7	133.3
62.5°	119.9	120.4	121.7	122.2	122.6	121.7	120.8	121.3	121.3	119.9	120.4
65°	107.0	107.9	109.7	109.3	108.4	108.8	107.9	108.4	107.0	107.5	106.2
67.5°	94.6	94.2	94.6	94.6	95.5	95.1	94.2	94.2	93.7	95.1	93.7
70°	81.3	81.3	81.3	81.3	81.7	82.2	81.3	80.4	80.8	80.0	79.5
72.5°	67.5	68.0	67.5	68.4	67.1	68.0	68.0	67.5	67.1	67.1	67.1
75°	54.6	55.5	54.2	54.6	54.2	55.1	54.6	54.6	53.7	53.3	53.7
77.5°	41.8	42.2	41.3	41.8	41.3	41.8	41.8	41.3	41.3	41.3	41.3
80°	29.8	30.2	29.8	29.3	28.9	29.8	28.9	29.3	29.8	29.3	30.2
82.5°	19.1	19.1	18.7	19.1	18.2	18.2	18.7	18.7	18.2	19.1	18.2
85°	9.3	9.3	10.2	9.3	8.9	8.9	8.9	9.3	8.9	9.8	9.3
87.5°	2.2	1.8	2.2	2.2	1.8	1.8	2.2	1.8	2.2	2.7	1.8
90°	8.2	8.3	8.4	8.5	8.7	8.8	8.7	8.5	8.4	8.3	8.2
92.5°	8.5	8.5	8.6	8.7	8.7	8.8	8.7	8.7	8.6	8.5	8.5
95°	14.4	14.4	14.3	14.2	14.1	14.0	14.1	14.2	14.3	14.4	14.4
97.5°	17.6	17.6	17.7	17.8	17.9	18.0	17.9	17.8	17.7	17.6	17.6
100°	21.2	21.3	21.4	21.6	21.7	21.9	21.7	21.6	21.4	21.3	21.2
102.5°	22.9	23.0	23.2	23.4	23.6	23.8	23.6	23.4	23.2	23.0	22.9
105°	23.5	23.6	23.9	24.2	24.5	24.8	24.5	24.2	23.9	23.6	23.5
107.5°	24.2	24.3	24.6	24.9	25.2	25.5	25.2	24.9	24.6	24.3	24.2
110°	24.5	24.6	24.9	25.2	25.5	25.8	25.5	25.2	24.9	24.6	24.5

TEST NUMBER: P998171

CATALOG NUMBER: SA2XXDIP-B290D330UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	25.1	25.2	25.4	25.7	25.9	26.1	25.9	25.7	25.4	25.2	25.1
115°	50.3	47.7	42.5	37.2	32.0	26.8	32.0	37.2	42.5	47.7	50.3
117.5°	172.4	162.9	143.9	124.9	105.9	86.9	105.9	124.9	143.9	162.9	172.4
120°	243.3	238.4	228.6	218.8	209.0	199.2	209.0	218.8	228.6	238.4	243.3
122.5°	260.6	260.6	260.7	260.8	260.8	260.9	260.8	260.8	260.7	260.6	260.6
125°	278.3	278.4	278.6	278.8	279.0	279.2	279.0	278.8	278.6	278.4	278.3
127.5°	295.2	295.2	295.3	295.4	295.5	295.6	295.5	295.4	295.3	295.2	295.2
130°	310.9	310.9	310.8	310.7	310.7	310.6	310.7	310.7	310.8	310.9	310.9
132.5°	325.6	325.6	325.5	325.4	325.4	325.3	325.4	325.4	325.5	325.6	325.6
135°	340.0	339.9	339.8	339.6	339.5	339.3	339.5	339.6	339.8	339.9	340.0
137.5°	353.4	353.3	353.1	352.8	352.6	352.4	352.6	352.8	353.1	353.3	353.4
140°	366.1	365.9	365.6	365.2	364.9	364.5	364.9	365.2	365.6	365.9	366.1
142.5°	377.9	377.7	377.3	377.0	376.6	376.2	376.6	377.0	377.3	377.7	377.9
145°	388.6	388.4	388.1	387.7	387.4	387.0	387.4	387.7	388.1	388.4	388.6
147.5°	398.1	398.0	397.7	397.4	397.1	396.8	397.1	397.4	397.7	398.0	398.1
150°	407.3	407.1	406.7	406.4	406.0	405.6	406.0	406.4	406.7	407.1	407.3
152.5°	415.4	415.1	414.6	414.1	413.6	413.1	413.6	414.1	414.6	415.1	415.4
155°	422.6	422.3	421.7	421.2	420.6	420.0	420.6	421.2	421.7	422.3	422.6
157.5°	429.1	428.8	428.2	427.7	427.1	426.5	427.1	427.7	428.2	428.8	429.1
160°	434.4	434.1	433.6	433.1	432.6	432.1	432.6	433.1	433.6	434.1	434.4
162.5°	439.6	439.3	438.6	438.0	437.3	436.7	437.3	438.0	438.6	439.3	439.6
165°	443.5	443.2	442.7	442.2	441.7	441.2	441.7	442.2	442.7	443.2	443.5
167.5°	447.1	446.8	446.1	445.5	444.8	444.2	444.8	445.5	446.1	446.8	447.1
170°	449.7	449.4	448.7	448.1	447.4	446.8	447.4	448.1	448.7	449.4	449.7
172.5°	451.7	451.4	450.7	450.0	449.4	448.7	449.4	450.0	450.7	451.4	451.7
175°	453.0	452.6	451.9	451.2	450.4	449.7	450.4	451.2	451.9	452.6	453.0
177.5°	453.3	453.0	452.3	451.7	451.0	450.4	451.0	451.7	452.3	453.0	453.3
180°	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4

TEST NUMBER: P998171

CATALOG NUMBER: SA2XXDIP-B290D330UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
2.5°	548.6	552.1	550.8	545.9	551.7	551.7	555.7	555.7	560.6	562.3	565.0
5°	517.5	520.1	522.4	520.1	524.1	530.4	533.9	537.0	543.7	546.4	550.3
7.5°	484.2	489.1	491.3	491.3	497.9	505.0	512.1	516.6	525.9	529.5	533.5
10°	451.7	457.5	462.0	461.5	472.6	477.1	485.9	496.2	505.5	510.8	516.6
12.5°	417.5	420.6	426.9	435.7	438.4	446.4	456.6	469.5	486.4	491.3	499.7
15°	389.1	397.5	402.4	406.4	412.7	420.2	431.3	443.7	460.6	471.3	480.2
17.5°	365.1	376.2	379.3	378.4	386.4	398.0	410.9	420.2	435.3	448.2	456.6
20°	345.6	350.0	355.4	357.6	363.8	376.2	388.7	399.3	411.8	422.0	431.8
22.5°	326.0	329.6	334.0	338.0	342.9	350.0	362.0	375.3	387.3	397.1	408.2
25°	310.0	312.3	316.3	319.4	324.7	329.6	338.0	352.7	366.9	372.7	382.4
27.5°	294.5	296.3	298.9	302.5	305.2	310.0	317.6	329.6	344.2	350.0	363.3
30°	280.7	282.1	284.7	286.5	287.8	293.6	299.4	308.7	319.8	327.8	337.6
32.5°	267.8	269.2	271.8	272.3	274.1	277.2	282.5	290.9	300.7	307.4	315.8
35°	253.6	254.5	257.2	258.1	259.4	262.1	266.1	272.3	281.2	286.1	293.6
37.5°	242.5	242.1	243.9	245.2	247.0	248.3	249.6	255.9	262.5	267.0	272.7
40°	230.5	229.6	230.1	231.9	232.8	234.5	234.5	240.8	245.2	248.7	253.2
42.5°	218.5	218.1	217.2	218.1	219.0	219.4	219.9	224.3	228.8	231.9	236.8
45°	206.5	206.1	205.2	205.7	205.7	206.5	207.9	209.7	212.8	215.4	218.1
47.5°	195.4	194.6	193.2	192.8	193.7	193.7	193.7	195.4	198.6	199.4	202.1
50°	183.9	182.6	180.8	179.9	179.9	179.5	180.3	180.8	183.4	184.3	186.6
52.5°	171.5	170.6	168.8	167.0	167.5	166.6	167.0	167.5	168.3	169.7	171.0
55°	159.0	157.2	155.9	155.5	154.1	154.1	152.8	154.6	154.1	154.6	156.4
57.5°	147.0	145.2	143.0	142.1	140.8	140.4	139.5	139.0	139.5	140.8	142.1
60°	132.8	131.9	130.6	129.3	128.4	127.0	126.1	126.1	125.7	125.7	126.1
62.5°	119.0	118.6	116.8	116.4	115.5	114.6	113.3	112.4	112.4	113.3	113.7
65°	105.7	105.3	103.9	103.5	101.3	100.4	99.9	99.5	98.6	98.6	98.6
67.5°	93.3	91.9	91.9	89.7	87.9	87.1	86.2	85.7	85.7	85.7	86.2
70°	79.5	79.5	78.2	76.8	75.1	75.5	74.2	72.8	72.8	72.0	72.4
72.5°	66.2	65.7	64.4	64.0	62.6	61.3	60.4	61.3	60.0	59.5	60.0
75°	53.3	52.9	52.0	51.1	51.5	50.2	48.9	48.4	48.4	47.5	47.5
77.5°	40.9	41.8	40.0	39.5	38.6	37.8	37.3	36.9	36.9	36.9	37.8
80°	28.4	28.9	28.9	28.0	28.4	27.1	27.1	27.1	25.8	26.2	26.7
82.5°	18.2	18.2	17.8	18.2	17.8	17.8	17.3	17.3	16.9	16.9	17.3
85°	10.2	9.8	9.3	10.2	9.8	9.8	9.3	9.3	9.3	9.3	9.3
87.5°	2.2	2.7	2.7	2.7	2.7	3.1	3.1	3.1	3.6	3.6	3.6
90°	8.0	7.6	7.3	6.9	6.5	5.9	5.3	4.8	4.2	3.9	3.5
92.5°	8.4	8.3	8.1	8.0	7.8	7.6	7.4	7.2	7.0	6.9	7.0
95°	14.2	13.8	13.5	13.1	12.7	12.2	11.7	11.2	10.7	10.5	11.7
97.5°	17.5	17.3	17.1	16.9	16.7	15.5	14.3	13.2	12.0	11.4	14.4
100°	20.9	20.3	19.8	19.2	18.6	17.4	16.2	14.9	13.7	13.1	18.1
102.5°	22.5	21.7	20.9	20.1	19.3	32.5	45.7	58.9	72.1	78.7	78.8
105°	23.1	22.3	21.5	20.7	19.9	39.7	59.5	79.4	99.2	109.1	108.0
107.5°	23.8	23.0	22.2	21.4	20.6	45.0	69.5	93.9	118.4	130.6	129.7
110°	28.1	35.4	42.7	49.9	57.2	78.2	99.1	120.1	141.0	151.5	150.7

TEST NUMBER: P998171

CATALOG NUMBER: SA2XXDIP-B290D330UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	40.7	72.0	103.3	134.6	165.9	167.1	168.4	169.6	170.9	171.5	170.8
115°	67.1	100.7	134.3	167.9	201.5	199.7	197.9	196.0	194.2	193.3	192.7
117.5°	177.6	188.0	198.3	208.7	219.1	217.9	216.7	215.4	214.2	213.6	212.9
120°	242.9	242.0	241.1	240.3	239.4	238.1	236.8	235.5	234.2	233.5	233.0
122.5°	260.4	260.0	259.5	259.1	258.7	257.2	255.8	254.3	252.8	252.1	251.5
125°	278.0	277.5	277.0	276.5	276.0	274.6	273.2	271.9	270.5	269.8	269.3
127.5°	294.8	294.1	293.4	292.7	292.0	290.9	289.8	288.7	287.6	287.1	286.6
130°	310.5	309.7	308.9	308.1	307.3	306.5	305.7	304.9	304.1	303.7	303.1
132.5°	325.3	324.6	324.0	323.3	322.7	321.9	321.1	320.3	319.5	319.1	318.6
135°	339.6	338.9	338.2	337.4	336.7	336.1	335.4	334.8	334.1	333.8	333.2
137.5°	353.0	352.3	351.6	350.8	350.1	349.4	348.6	347.9	347.2	346.8	346.4
140°	365.8	365.1	364.5	363.8	363.2	362.4	361.6	360.8	360.0	359.6	359.3
142.5°	377.6	377.0	376.5	375.9	375.3	374.3	373.4	372.4	371.5	371.0	370.7
145°	388.4	387.9	387.4	386.9	386.4	385.2	383.9	382.7	381.4	380.8	380.8
147.5°	397.9	397.6	397.2	396.9	396.5	395.3	394.0	392.8	391.5	390.9	391.0
150°	407.1	406.6	406.2	405.7	405.3	404.1	403.0	401.8	400.7	400.1	400.4
152.5°	415.2	414.8	414.3	413.9	413.5	412.4	411.3	410.2	409.1	408.6	408.9
155°	422.4	422.0	421.5	421.1	420.7	419.8	418.9	418.0	417.1	416.7	417.0
157.5°	428.9	428.4	427.9	427.4	426.9	426.2	425.6	424.9	424.2	423.9	424.2
160°	434.2	433.7	433.3	432.8	432.4	432.0	431.6	431.1	430.7	430.5	430.7
162.5°	439.3	438.8	438.3	437.8	437.3	436.9	436.6	436.2	435.9	435.7	435.9
165°	443.2	442.7	442.2	441.7	441.2	441.0	440.8	440.5	440.3	440.2	440.4
167.5°	446.8	446.3	445.8	445.3	444.8	444.6	444.4	444.1	443.9	443.8	444.0
170°	449.4	448.9	448.4	447.9	447.4	447.3	447.1	447.0	446.9	446.8	447.0
172.5°	451.4	450.9	450.4	449.9	449.4	449.2	449.1	448.9	448.8	448.7	448.9
175°	452.7	452.2	451.7	451.2	450.7	450.5	450.4	450.2	450.1	450.0	450.3
177.5°	453.0	452.5	452.0	451.5	451.0	450.9	450.9	450.8	450.7	450.7	451.0
180°	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4	451.4

TEST NUMBER: P998171

CATALOG NUMBER: SA2XXDIP-B290D330UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	577.9	577.9	577.9	577.9
2.5°	567.2	567.2	573.9	581.0
5°	554.8	557.9	568.6	578.3
7.5°	542.8	548.1	561.5	573.9
10°	528.1	535.2	551.7	566.3
12.5°	513.9	520.6	539.7	556.1
15°	493.9	502.4	522.8	543.2
17.5°	473.9	482.4	507.3	531.2
20°	450.4	461.5	489.5	521.5
22.5°	428.6	442.4	473.5	499.3
25°	404.7	426.0	454.8	488.2
27.5°	383.3	404.7	434.0	467.7
30°	359.3	381.1	411.3	442.4
32.5°	336.3	356.2	385.6	423.8
35°	312.3	331.4	359.8	398.4
37.5°	290.5	309.2	340.2	375.8
40°	269.2	288.7	315.4	350.9
42.5°	249.2	266.5	290.5	326.0
45°	231.0	243.4	265.6	298.9
47.5°	211.9	223.0	243.4	276.7
50°	194.1	203.4	221.2	252.3
52.5°	176.8	184.8	201.2	226.1
55°	161.2	168.8	180.8	205.2
57.5°	145.2	151.0	162.6	182.1
60°	129.7	135.0	144.4	160.4
62.5°	114.2	118.6	127.5	140.4
65°	100.4	103.9	110.6	121.7
67.5°	87.1	89.3	94.6	103.5
70°	74.2	76.0	80.4	87.5
72.5°	60.4	62.2	67.1	72.0
75°	48.9	49.3	52.9	56.9
77.5°	38.2	37.8	40.4	43.5
80°	26.2	27.5	29.8	31.1
82.5°	17.8	18.2	19.1	20.0
85°	9.8	10.2	10.2	11.5
87.5°	4.0	4.4	4.4	4.9
90°	2.7	1.9	1.1	0.3
92.5°	7.3	7.6	7.9	8.2
95°	14.1	16.4	18.8	21.2
97.5°	20.3	26.3	32.2	38.2
100°	28.0	37.9	47.9	57.8
102.5°	78.9	79.1	79.2	79.4
105°	105.8	103.7	101.5	99.3
107.5°	127.9	126.1	124.3	122.5
110°	149.2	147.7	146.2	144.7



TEST NUMBER: P998171

CATALOG NUMBER: SA2XXDIP-B290D330UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	169.5	168.2	166.9	165.6
115°	191.5	190.2	189.0	187.8
117.5°	211.4	210.0	208.5	207.1
120°	231.9	230.8	229.7	228.6
122.5°	250.4	249.2	248.1	246.9
125°	268.4	267.4	266.5	265.5
127.5°	285.6	284.5	283.5	282.5
130°	302.0	300.8	299.7	298.5
132.5°	317.7	316.7	315.8	314.8
135°	332.1	330.9	329.8	328.6
137.5°	345.5	344.6	343.8	342.9
140°	358.7	358.2	357.6	357.0
142.5°	370.2	369.7	369.2	368.7
145°	380.9	381.0	381.0	381.1
147.5°	391.2	391.5	391.7	391.9
150°	400.9	401.4	401.9	402.4
152.5°	409.5	410.0	410.6	411.2
155°	417.7	418.4	419.0	419.7
157.5°	424.8	425.3	425.9	426.5
160°	431.1	431.6	432.0	432.4
162.5°	436.3	436.8	437.2	437.6
165°	440.9	441.3	441.8	442.2
167.5°	444.5	444.9	445.4	445.8
170°	447.4	447.9	448.3	448.7
172.5°	449.4	449.8	450.3	450.7
175°	450.8	451.3	451.8	452.3
177.5°	451.5	452.0	452.5	453.0
180°	451.4	451.4	451.4	451.4

TEST NUMBER: P998171

CATALOG NUMBER: SA2XXDIP-B290D330UB35-4F0-XX-W2A-A

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.45	14.27	14.42	15.25	16.54	10.94	11.76	11.91	12.74	14.03
	3H	14.26	14.99	15.24	15.98	17.29	12.28	13.02	13.27	14.01	15.32
	4H	14.42	15.12	15.42	16.11	17.43	12.74	13.44	13.74	14.43	15.75
	6H	14.47	15.11	15.47	16.10	17.43	13.05	13.69	14.06	14.69	16.02
	8H	14.44	15.05	15.46	16.07	17.39	13.13	13.74	14.14	14.75	16.08
	12H	14.41	14.98	15.42	15.99	17.34	13.17	13.75	14.19	14.76	16.11
4H	2H	13.48	14.18	14.49	15.17	16.49	11.38	12.08	12.38	13.07	14.39
	3H	14.46	15.04	15.47	16.06	17.39	12.84	13.42	13.85	14.44	15.77
	4H	14.74	15.26	15.76	16.28	17.63	13.37	13.90	14.39	14.92	16.27
	6H	14.87	15.32	15.89	16.36	17.71	13.75	14.20	14.78	15.24	16.59
	8H	14.86	15.29	15.89	16.32	17.68	13.86	14.28	14.89	15.31	16.68
	12H	14.82	15.21	15.87	16.25	17.62	13.91	14.30	14.96	15.34	16.71
8H	4H	14.74	15.17	15.77	16.20	17.56	13.51	13.93	14.54	14.97	16.33
	6H	14.92	15.27	15.97	16.34	17.71	13.95	14.29	15.00	15.37	16.73
	8H	14.95	15.26	16.01	16.32	17.70	14.10	14.40	15.16	15.46	16.84
	12H	14.93	15.20	16.00	16.26	17.68	14.19	14.46	15.25	15.51	16.93
12H	4H	14.70	15.08	15.75	16.13	17.50	13.48	13.87	14.53	14.91	16.28
	6H	14.90	15.21	15.96	16.26	17.65	13.95	14.25	15.01	15.31	16.69
	8H	14.93	15.20	15.99	16.25	17.68	14.10	14.37	15.17	15.42	16.85