

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998984

Luminaire Tested: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-A_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998984
REPORT IS A COMBINATION OF REPORTS P984730 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-A_4000K
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8047.0 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998984

CATALOG NUMBER: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P998984

CATALOG NUMBER: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53
1	98	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39
3	82	73	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30
5	69	58	50	44	63	53	47	41	45	40	36	38	34	31	31	28	26
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	28	26	23
7	59	47	39	34	54	44	37	32	37	32	28	32	28	24	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	27013	27013	27013	27013
5°	27077	28801	27180	22914
10°	26763	31441	26931	18891
15°	26114	33163	26477	15913
20°	25706	31139	25706	13832
25°	24887	26752	25001	12368
30°	23539	21029	23987	11203
35°	22345	14541	22718	10251
40°	20972	10979	21211	9491
45°	19278	9022	19595	8671
50°	17816	7919	17847	7938
55°	16148	6748	16251	7141
60°	14368	5636	14568	6232
65°	12776	4584	13011	5323
70°	11191	3597	11476	4294
75°	9392	2611	9762	3112
80°	7329	1655	7856	1848
85°	4817	832	5184	616

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 27922 cd/sqm

TEST NUMBER: P998984

CATALOG NUMBER: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	2.0
10°-20°	473.1	5.9
20°-30°	686.6	8.5
30°-40°	723.8	9.0
40°-50°	640.5	8.0
50°-60°	511.4	6.4
60°-70°	347.4	4.3
70°-80°	177.7	2.2
80°-90°	44.6	0.6
90°-100°	48.2	0.6
100°-110°	179.4	2.2
110°-120°	475.9	5.9
120°-130°	789.3	9.8
130°-140°	838.4	10.4
140°-150°	779.2	9.7
150°-160°	626.5	7.8
160°-170°	403.7	5.0
170°-180°	138.9	1.7
0°-30°	1322.2	16.4
0°-40°	2046.0	25.4
0°-60°	3197.9	39.7
0°-90°	3767.6	46.8
90°-120°	703.5	8.7
90°-150°	3110.4	38.7
90°-180°	4279.0	53.2
0°-180°	8047.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1706	1706	1706	1706	1706	
5°	1708	1906	1714	1516	1708	162
15°	1604	2343	1626	1124	1604	453
25°	1442	1952	1448	902	1442	659
35°	1177	1062	1196	749	1177	736
45°	883	640	897	615	883	685
55°	606	450	610	476	606	541
65°	359	277	366	321	359	357
75°	168	136	174	163	168	180
85°	34	35	37	26	34	40
90°	1	28	1	28	1	6
95°	69	45	69	45	69	81
105°	321	80	321	80	321	343
115°	607	87	607	87	607	598
125°	859	903	859	903	859	766
135°	1063	1097	1063	1097	1063	821
145°	1233	1252	1233	1252	1233	771
155°	1357	1358	1357	1358	1357	625
165°	1430	1427	1430	1427	1430	404
175°	1463	1454	1463	1454	1463	139
180°	1460	1460	1460	1460	1460	

TEST NUMBER: P998984

CATALOG NUMBER: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1715.7	1719.6	1726.1	1727.5	1740.6	1751.1	1762.9	1762.9	1766.8	1765.5	1755.0
5°	1707.8	1719.6	1736.6	1751.1	1774.7	1785.2	1800.9	1812.7	1823.2	1831.1	1829.8
7.5°	1694.7	1715.7	1740.6	1768.1	1799.6	1818.0	1840.3	1861.2	1875.7	1888.8	1898.0
10°	1672.4	1707.8	1741.9	1778.6	1819.3	1844.2	1870.4	1898.0	1920.3	1945.2	1968.8
12.5°	1642.2	1693.4	1735.3	1783.9	1833.7	1861.2	1903.2	1924.2	1967.5	2030.5	2047.5
15°	1604.2	1673.7	1713.0	1774.7	1840.3	1862.6	1920.3	1954.4	2043.6	2082.9	2130.1
17.5°	1568.7	1646.1	1698.6	1769.4	1833.7	1877.0	1933.4	2002.9	2077.7	2134.1	2186.5
20°	1539.9	1614.7	1677.6	1756.3	1837.6	1892.7	1951.8	2035.7	2117.0	2174.7	2215.4
22.5°	1474.3	1570.1	1643.5	1731.4	1829.8	1905.8	1962.2	2054.1	2141.9	2177.4	2212.8
25°	1441.5	1524.2	1609.4	1709.1	1824.5	1915.0	1963.6	2065.9	2143.3	2156.4	2164.2
27.5°	1381.2	1474.3	1574.0	1688.1	1823.2	1899.3	1960.9	2054.1	2115.7	2106.5	2082.9
30°	1306.4	1420.5	1530.7	1654.0	1804.8	1887.5	1945.2	2030.5	2061.9	2014.7	1972.7
32.5°	1251.3	1358.9	1480.9	1623.8	1783.9	1862.6	1919.0	1985.9	1992.4	1907.2	1836.3
35°	1176.6	1295.9	1433.6	1584.5	1748.4	1819.3	1871.7	1912.4	1880.9	1761.6	1677.6
37.5°	1109.7	1227.7	1374.6	1528.1	1699.9	1769.4	1811.4	1818.0	1740.6	1635.6	1512.3
40°	1036.2	1158.2	1311.7	1473.0	1646.1	1706.5	1732.7	1713.0	1601.5	1479.6	1336.6
42.5°	962.8	1083.4	1248.7	1414.0	1577.9	1629.1	1639.6	1585.8	1449.4	1306.4	1141.1
45°	882.7	1008.7	1173.9	1340.5	1499.2	1528.1	1529.4	1452.0	1290.7	1141.1	987.7
47.5°	817.2	933.9	1097.9	1264.4	1398.2	1417.9	1410.0	1320.8	1145.1	977.2	843.4
50°	745.0	856.5	1019.2	1183.1	1297.2	1302.5	1282.8	1155.6	983.7	830.3	724.0
52.5°	667.6	780.4	930.0	1087.4	1189.7	1181.8	1143.8	1007.4	846.0	718.8	637.5
55°	606.0	705.7	846.0	999.5	1071.6	1049.3	1007.4	868.3	741.1	633.5	562.7
57.5°	537.8	625.7	763.4	897.2	939.2	918.2	876.2	746.3	628.3	547.0	499.7
60°	473.5	553.5	674.2	785.7	818.5	796.2	747.6	630.9	545.7	477.4	442.0
62.5°	414.5	484.0	585.0	687.3	700.4	678.1	636.2	541.7	468.3	414.5	388.3
65°	359.4	425.0	506.3	583.7	595.5	571.9	528.6	460.4	398.7	364.6	339.7
67.5°	305.6	358.1	430.2	486.6	493.2	470.9	435.5	380.4	342.3	305.6	287.3
70°	258.4	297.7	354.1	400.1	402.7	381.7	363.3	313.5	284.6	258.4	244.0
72.5°	212.5	240.0	283.3	317.4	318.7	305.6	288.6	257.1	232.2	213.8	199.4
75°	167.9	191.5	217.7	247.9	246.6	236.1	223.0	203.3	182.3	170.5	164.0
77.5°	128.5	143.0	164.0	183.6	183.6	178.4	170.5	156.1	143.0	131.2	124.6
80°	91.8	101.0	118.0	124.6	127.2	125.9	119.4	108.9	103.6	94.4	91.8
82.5°	59.0	65.6	73.5	80.0	83.9	81.3	80.0	74.8	66.9	64.3	61.6
85°	34.1	36.7	40.7	44.6	45.9	44.6	47.2	43.3	39.3	39.3	38.0
87.5°	14.4	15.7	18.4	18.4	19.7	19.7	18.4	19.7	19.7	18.4	17.1
90°	1.1	3.7	6.3	8.8	11.4	12.7	13.6	15.5	17.4	19.2	21.1
92.5°	26.4	25.5	24.5	23.6	22.7	22.2	22.5	23.2	23.9	24.6	25.3
95°	68.7	60.9	53.2	45.4	37.7	33.8	34.6	36.3	37.9	39.6	41.2
97.5°	123.6	104.4	85.1	65.9	46.6	37.0	38.9	42.6	46.4	50.1	53.9
100°	187.0	154.8	122.6	90.5	58.3	42.2	44.2	48.2	52.2	56.2	60.2
102.5°	256.7	256.2	255.8	255.3	254.8	254.6	233.2	190.5	147.8	105.0	62.3
105°	321.1	328.1	335.2	342.2	349.3	352.8	320.8	256.7	192.6	128.5	64.4
107.5°	396.1	402.0	407.8	413.7	419.6	422.5	382.9	303.8	224.7	145.6	66.5
110°	467.9	472.8	477.8	482.7	487.6	490.1	456.2	388.3	320.5	252.6	184.8

TEST NUMBER: P998984

CATALOG NUMBER: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	535.5	539.7	543.9	548.2	552.4	554.5	552.5	548.5	544.6	540.6	536.6
115°	607.3	611.3	615.3	619.3	623.3	625.3	628.2	634.1	640.0	645.8	651.7
117.5°	669.7	674.4	679.1	683.8	688.5	690.8	692.8	696.8	700.7	704.7	708.7
120°	739.4	742.9	746.4	749.9	753.4	755.2	757.3	761.5	765.8	770.0	774.2
122.5°	798.5	802.3	806.0	809.8	813.5	815.4	817.7	822.4	827.1	831.8	836.5
125°	858.7	861.8	864.8	867.9	871.0	872.5	874.7	879.2	883.6	888.1	892.5
127.5°	913.7	917.0	920.2	923.5	926.8	928.4	930.2	933.7	937.2	940.8	944.3
130°	965.4	969.2	972.9	976.7	980.4	982.3	983.6	986.2	988.7	991.3	993.9
132.5°	1018.2	1021.3	1024.3	1027.4	1030.5	1032.0	1033.3	1035.9	1038.4	1041.0	1043.6
135°	1062.6	1066.4	1070.1	1073.9	1077.6	1079.5	1080.6	1082.7	1084.8	1086.9	1089.0
137.5°	1109.1	1111.9	1114.7	1117.5	1120.3	1121.7	1122.9	1125.2	1127.6	1129.9	1132.3
140°	1154.5	1156.4	1158.2	1160.1	1162.0	1162.9	1164.2	1166.8	1169.3	1171.9	1174.5
142.5°	1192.5	1194.1	1195.8	1197.4	1199.1	1199.9	1201.4	1204.5	1207.5	1210.6	1213.6
145°	1232.6	1232.4	1232.2	1231.9	1231.7	1231.6	1233.6	1237.6	1241.5	1245.5	1249.5
147.5°	1267.5	1266.8	1266.1	1265.4	1264.7	1264.3	1266.3	1270.3	1274.3	1278.3	1282.3
150°	1301.3	1299.7	1298.0	1296.4	1294.7	1293.9	1295.8	1299.5	1303.3	1307.0	1310.8
152.5°	1329.8	1327.9	1326.1	1324.2	1322.3	1321.4	1323.2	1326.7	1330.2	1333.7	1337.2
155°	1357.3	1355.2	1353.1	1351.0	1348.9	1347.8	1349.2	1352.0	1354.8	1357.6	1360.4
157.5°	1379.5	1377.6	1375.7	1373.8	1371.9	1371.0	1372.1	1374.2	1376.3	1378.4	1380.5
160°	1398.5	1397.1	1395.7	1394.2	1392.8	1392.1	1392.8	1394.2	1395.7	1397.1	1398.5
162.5°	1415.4	1414.0	1412.6	1411.1	1409.7	1409.0	1409.6	1410.8	1411.9	1413.1	1414.3
165°	1430.2	1428.8	1427.4	1425.9	1424.5	1423.8	1424.2	1424.9	1425.6	1426.3	1427.0
167.5°	1441.8	1440.4	1439.0	1437.5	1436.1	1435.4	1435.8	1436.5	1437.2	1437.9	1438.6
170°	1451.3	1449.9	1448.5	1447.0	1445.6	1444.9	1445.1	1445.6	1446.1	1446.6	1447.1
172.5°	1457.6	1456.2	1454.8	1453.4	1452.0	1451.3	1451.5	1452.0	1452.5	1452.9	1453.4
175°	1462.9	1461.3	1459.6	1458.0	1456.3	1455.5	1455.7	1456.2	1456.7	1457.1	1457.6
177.5°	1465.0	1463.4	1461.7	1460.1	1458.4	1457.6	1457.7	1458.0	1458.2	1458.5	1458.7
180°	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7

TEST NUMBER: P998984

CATALOG NUMBER: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1773.4	1774.7	1777.3	1790.4	1797.0	1798.3	1793.0	1804.8	1808.8	1804.8	1802.2
5°	1857.3	1865.2	1880.9	1898.0	1896.7	1898.0	1905.8	1913.7	1916.3	1905.8	1909.8
7.5°	1930.8	1946.5	1963.6	1989.8	1989.8	2002.9	2008.2	2014.7	2030.5	2022.6	2020.0
10°	2014.7	2035.7	2067.2	2109.2	2110.5	2123.6	2136.7	2157.7	2164.2	2159.0	2161.6
12.5°	2119.6	2160.3	2162.9	2208.8	2229.8	2232.5	2253.4	2249.5	2262.6	2262.6	2284.9
15°	2165.6	2228.5	2263.9	2308.5	2321.6	2305.9	2323.0	2341.3	2342.6	2342.6	2341.3
17.5°	2248.2	2273.1	2308.5	2332.1	2337.4	2337.4	2338.7	2346.6	2341.3	2330.8	2338.7
20°	2265.2	2275.7	2288.9	2286.2	2288.9	2275.7	2262.6	2249.5	2250.8	2244.3	2263.9
22.5°	2233.8	2231.1	2201.0	2181.3	2181.3	2155.1	2130.1	2118.3	2106.5	2110.5	2117.0
25°	2155.1	2114.4	2077.7	2048.8	2042.3	2000.3	1966.2	1955.7	1936.0	1951.8	1954.4
27.5°	2029.1	1983.2	1924.2	1899.3	1865.2	1848.1	1824.5	1793.0	1752.4	1776.0	1772.1
30°	1894.0	1825.8	1777.3	1717.0	1663.2	1659.3	1614.7	1562.2	1541.2	1541.2	1553.0
32.5°	1743.2	1652.7	1581.9	1496.6	1444.1	1421.8	1368.1	1315.6	1327.4	1288.1	1302.5
35°	1567.4	1448.1	1358.9	1276.2	1236.9	1210.7	1141.1	1112.3	1080.8	1062.4	1096.6
37.5°	1399.5	1261.8	1147.7	1057.2	1042.8	995.6	948.3	930.0	911.6	919.5	918.2
40°	1194.9	1072.9	970.6	899.8	874.9	852.6	821.1	798.8	787.0	793.6	794.9
42.5°	1010.0	907.7	831.6	781.8	760.8	745.0	729.3	710.9	707.0	707.0	712.2
45°	867.0	783.1	731.9	691.2	679.4	667.6	655.8	648.0	645.3	640.1	644.0
47.5°	752.9	686.0	654.5	624.4	611.2	608.6	598.1	594.2	588.9	587.6	588.9
50°	657.1	615.2	586.3	569.3	560.1	556.1	550.9	543.0	540.4	547.0	544.3
52.5°	590.2	550.9	535.2	518.1	512.9	507.6	499.7	501.1	499.7	497.1	497.1
55°	523.4	498.4	482.7	469.6	468.3	463.0	456.5	453.8	452.5	449.9	453.8
57.5°	469.6	449.9	435.5	423.7	418.4	418.4	411.9	406.6	406.6	405.3	406.6
60°	415.8	396.1	386.9	375.1	371.2	369.9	366.0	363.3	359.4	359.4	359.4
62.5°	366.0	350.2	339.7	329.2	330.5	324.0	318.7	316.1	316.1	317.4	317.4
65°	318.7	308.2	295.1	285.9	283.3	282.0	279.4	278.1	274.1	276.8	276.8
67.5°	275.4	261.0	253.2	249.2	245.3	244.0	241.3	238.7	237.4	236.1	238.7
70°	232.2	220.4	213.8	211.2	207.2	205.9	204.6	200.7	202.0	203.3	204.6
72.5°	192.8	182.3	181.0	173.1	173.1	173.1	167.9	170.5	169.2	166.6	169.2
75°	152.2	146.9	144.3	140.3	141.7	140.3	139.0	135.1	135.1	136.4	137.7
77.5°	120.7	115.4	114.1	110.2	107.6	110.2	107.6	106.2	106.2	107.6	107.6
80°	89.2	86.6	82.6	82.6	82.6	81.3	81.3	81.3	80.0	78.7	80.0
82.5°	59.0	59.0	57.7	56.4	57.7	55.1	56.4	56.4	56.4	56.4	56.4
85°	38.0	36.7	36.7	35.4	35.4	35.4	36.7	34.1	34.1	35.4	35.4
87.5°	17.1	17.1	17.1	18.4	17.1	17.1	17.1	18.4	17.1	17.1	17.1
90°	22.3	23.5	24.6	25.8	26.4	26.6	27.1	27.6	28.0	28.5	28.0
92.5°	25.8	26.3	26.8	27.3	27.5	27.6	27.8	28.1	28.3	28.5	28.3
95°	42.4	43.6	44.7	45.9	46.5	46.4	46.1	45.9	45.6	45.4	45.6
97.5°	54.6	55.3	56.0	56.7	57.0	57.1	57.4	57.6	57.9	58.1	57.9
100°	62.1	64.0	65.9	67.8	68.7	68.9	69.4	69.9	70.3	70.8	70.3
102.5°	64.9	67.5	70.0	72.6	73.9	74.3	75.0	75.7	76.4	77.1	76.4
105°	67.0	69.6	72.1	74.7	76.0	76.5	77.4	78.4	79.3	80.3	79.3
107.5°	69.1	71.7	74.3	76.9	78.2	78.7	79.6	80.5	81.5	82.4	81.5
110°	161.3	137.9	114.4	90.9	79.2	79.7	80.6	81.5	82.5	83.4	82.5

TEST NUMBER: P998984

CATALOG NUMBER: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	435.4	334.2	233.1	131.9	81.3	81.7	82.4	83.1	83.8	84.5	83.8
115°	543.0	434.4	325.7	217.0	162.7	154.2	137.3	120.4	103.5	86.6	103.5
117.5°	675.1	641.6	608.0	574.5	557.7	527.0	465.5	404.0	342.5	281.0	342.5
120°	777.0	779.8	782.7	785.5	786.9	771.1	739.4	707.7	676.0	644.3	676.0
122.5°	837.9	839.3	840.8	842.2	842.9	843.0	843.2	843.5	843.7	843.9	843.7
125°	894.1	895.8	897.4	899.1	899.9	900.3	901.0	901.7	902.4	903.1	902.4
127.5°	946.6	949.0	951.3	953.6	954.8	954.9	955.2	955.4	955.7	955.9	955.7
130°	996.5	999.1	1001.6	1004.2	1005.5	1005.4	1005.2	1004.9	1004.7	1004.5	1004.7
132.5°	1045.7	1047.8	1049.9	1052.0	1053.1	1053.0	1052.7	1052.5	1052.2	1052.0	1052.2
135°	1091.4	1093.7	1096.1	1098.4	1099.6	1099.4	1098.9	1098.4	1097.9	1097.4	1097.9
137.5°	1134.7	1137.0	1139.4	1141.7	1142.9	1142.5	1141.8	1141.1	1140.4	1139.7	1140.4
140°	1176.6	1178.8	1180.9	1183.0	1184.1	1183.5	1182.3	1181.2	1180.0	1178.8	1180.0
142.5°	1215.5	1217.4	1219.3	1221.2	1222.1	1221.5	1220.3	1219.2	1218.0	1216.8	1218.0
145°	1251.1	1252.8	1254.4	1256.1	1256.9	1256.3	1255.2	1254.0	1252.9	1251.7	1252.9
147.5°	1283.5	1284.7	1285.8	1287.0	1287.6	1287.1	1286.2	1285.2	1284.3	1283.3	1284.3
150°	1312.2	1313.6	1315.0	1316.4	1317.1	1316.5	1315.4	1314.2	1313.1	1311.9	1313.1
152.5°	1338.6	1340.0	1341.4	1342.8	1343.5	1342.7	1341.1	1339.4	1337.8	1336.2	1337.8
155°	1361.8	1363.2	1364.7	1366.1	1366.8	1365.9	1364.0	1362.1	1360.2	1358.3	1360.2
157.5°	1382.1	1383.8	1385.4	1387.1	1387.9	1387.0	1385.1	1383.2	1381.4	1379.5	1381.4
160°	1399.9	1401.3	1402.7	1404.1	1404.8	1404.0	1402.3	1400.7	1399.0	1397.4	1399.0
162.5°	1415.9	1417.6	1419.2	1420.9	1421.7	1420.6	1418.5	1416.4	1414.3	1412.2	1414.3
165°	1428.6	1430.3	1431.9	1433.6	1434.4	1433.6	1431.9	1430.3	1428.6	1427.0	1428.6
167.5°	1440.2	1441.9	1443.5	1445.2	1446.0	1444.9	1442.8	1440.7	1438.6	1436.5	1438.6
170°	1448.7	1450.4	1452.0	1453.7	1454.5	1453.4	1451.3	1449.2	1447.0	1444.9	1447.0
172.5°	1455.0	1456.7	1458.3	1460.0	1460.8	1459.7	1457.6	1455.5	1453.4	1451.3	1453.4
175°	1459.2	1460.9	1462.5	1464.2	1465.0	1463.8	1461.5	1459.2	1456.8	1454.5	1456.8
177.5°	1460.3	1462.0	1463.6	1465.3	1466.1	1465.0	1462.9	1460.8	1458.7	1456.6	1458.7
180°	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7

TEST NUMBER: P998984

CATALOG NUMBER: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1808.8	1799.6	1791.7	1793.0	1799.6	1794.4	1781.2	1764.2	1757.6	1749.8	1757.6
5°	1917.7	1909.8	1894.0	1895.4	1891.4	1886.2	1865.2	1839.0	1839.0	1818.0	1815.3
7.5°	2025.2	2013.4	2002.9	2000.3	1985.9	1975.4	1957.0	1920.3	1905.8	1880.9	1866.5
10°	2145.9	2136.7	2124.9	2110.5	2102.6	2084.2	2054.1	2000.3	1974.1	1939.9	1915.0
12.5°	2267.9	2266.6	2240.3	2211.5	2210.2	2181.3	2160.3	2088.2	2052.8	2006.8	1947.8
15°	2345.3	2338.7	2324.3	2309.8	2313.8	2282.3	2235.1	2149.8	2126.2	2071.1	2008.2
17.5°	2343.9	2343.9	2340.0	2337.4	2333.4	2324.3	2298.0	2241.6	2203.6	2134.1	2075.1
20°	2269.2	2286.2	2290.2	2288.9	2302.0	2308.5	2307.2	2271.8	2241.6	2180.0	2119.6
22.5°	2119.6	2159.0	2176.0	2186.5	2214.1	2228.5	2262.6	2249.5	2241.6	2195.7	2144.6
25°	1980.6	1993.7	2044.9	2047.5	2085.5	2121.0	2155.1	2177.4	2206.2	2189.2	2145.9
27.5°	1800.9	1831.1	1867.8	1895.4	1903.2	1975.4	2031.8	2073.7	2139.3	2144.6	2130.1
30°	1597.6	1612.0	1672.4	1709.1	1751.1	1803.5	1884.9	1957.0	2016.0	2069.8	2088.2
32.5°	1349.7	1408.7	1444.1	1488.7	1525.5	1618.6	1718.3	1811.4	1879.6	1970.1	2009.5
35°	1122.8	1168.7	1229.0	1247.4	1314.3	1393.0	1522.8	1642.2	1745.8	1837.6	1917.7
37.5°	935.2	971.9	1036.2	1065.1	1104.4	1205.4	1314.3	1462.5	1587.1	1699.9	1799.6
40°	806.7	834.2	882.7	891.9	924.7	1016.5	1104.4	1243.5	1408.7	1560.9	1669.7
42.5°	718.8	731.9	764.7	776.5	797.5	859.1	937.8	1069.0	1222.5	1379.9	1533.3
45°	655.8	665.0	684.7	695.2	721.4	749.0	813.2	918.2	1038.8	1197.5	1362.8
47.5°	599.4	611.2	619.1	625.7	640.1	670.3	712.2	789.6	905.0	1050.6	1210.7
50°	552.2	556.1	570.6	571.9	581.1	600.7	640.1	687.3	779.1	897.2	1052.0
52.5°	505.0	508.9	518.1	527.3	531.2	547.0	573.2	612.5	680.8	773.9	911.6
55°	457.8	463.0	472.2	478.8	482.7	495.8	511.5	549.6	603.4	668.9	781.8
57.5°	410.6	422.4	425.0	428.9	435.5	449.9	464.3	486.6	528.6	588.9	671.6
60°	366.0	369.9	379.1	383.0	389.6	397.4	415.8	432.8	463.0	510.2	585.0
62.5°	320.0	329.2	333.2	337.1	342.3	351.5	363.3	381.7	407.9	446.0	505.0
65°	280.7	282.0	289.9	295.1	300.4	306.9	318.7	335.8	351.5	386.9	430.2
67.5°	242.7	245.3	247.9	253.2	259.7	266.3	276.8	285.9	305.6	329.2	363.3
70°	205.9	205.9	212.5	216.4	215.1	223.0	230.9	241.3	255.8	278.1	305.6
72.5°	173.1	171.8	177.1	178.4	181.0	186.3	191.5	202.0	209.9	226.9	247.9
75°	137.7	140.3	143.0	143.0	146.9	150.8	156.1	161.3	170.5	181.0	196.7
77.5°	108.9	108.9	111.5	112.8	116.7	115.4	120.7	125.9	132.5	141.7	153.5
80°	80.0	82.6	82.6	82.6	83.9	85.3	90.5	94.4	98.4	104.9	110.2
82.5°	56.4	56.4	59.0	59.0	59.0	61.6	61.6	63.0	65.6	69.5	73.5
85°	35.4	35.4	35.4	36.7	35.4	36.7	39.3	38.0	39.3	42.0	42.0
87.5°	17.1	17.1	17.1	17.1	17.1	18.4	17.1	18.4	19.7	19.7	19.7
90°	27.6	27.1	26.6	26.4	25.8	24.6	23.5	22.3	21.1	19.2	17.4
92.5°	28.1	27.8	27.6	27.5	27.3	26.8	26.3	25.8	25.3	24.6	23.9
95°	45.9	46.1	46.4	46.5	45.9	44.7	43.6	42.4	41.2	39.6	37.9
97.5°	57.6	57.4	57.1	57.0	56.7	56.0	55.3	54.6	53.9	50.1	46.4
100°	69.9	69.4	68.9	68.7	67.8	65.9	64.0	62.1	60.2	56.2	52.2
102.5°	75.7	75.0	74.3	73.9	72.6	70.0	67.5	64.9	62.3	105.0	147.8
105°	78.4	77.4	76.5	76.0	74.7	72.1	69.6	67.0	64.4	128.5	192.6
107.5°	80.5	79.6	78.7	78.2	76.9	74.3	71.7	69.1	66.5	145.6	224.7
110°	81.5	80.6	79.7	79.2	90.9	114.4	137.9	161.3	184.8	252.6	320.5

TEST NUMBER: P998984

CATALOG NUMBER: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	83.1	82.4	81.7	81.3	131.9	233.1	334.2	435.4	536.6	540.6	544.6
115°	120.4	137.3	154.2	162.7	217.0	325.7	434.4	543.0	651.7	645.8	640.0
117.5°	404.0	465.5	527.0	557.7	574.5	608.0	641.6	675.1	708.7	704.7	700.7
120°	707.7	739.4	771.1	786.9	785.5	782.7	779.8	777.0	774.2	770.0	765.8
122.5°	843.5	843.2	843.0	842.9	842.2	840.8	839.3	837.9	836.5	831.8	827.1
125°	901.7	901.0	900.3	899.9	899.1	897.4	895.8	894.1	892.5	888.1	883.6
127.5°	955.4	955.2	954.9	954.8	953.6	951.3	949.0	946.6	944.3	940.8	937.2
130°	1004.9	1005.2	1005.4	1005.5	1004.2	1001.6	999.1	996.5	993.9	991.3	988.7
132.5°	1052.5	1052.7	1053.0	1053.1	1052.0	1049.9	1047.8	1045.7	1043.6	1041.0	1038.4
135°	1098.4	1098.9	1099.4	1099.6	1098.4	1096.1	1093.7	1091.4	1089.0	1086.9	1084.8
137.5°	1141.1	1141.8	1142.5	1142.9	1141.7	1139.4	1137.0	1134.7	1132.3	1129.9	1127.6
140°	1181.2	1182.3	1183.5	1184.1	1183.0	1180.9	1178.8	1176.6	1174.5	1171.9	1169.3
142.5°	1219.2	1220.3	1221.5	1222.1	1221.2	1219.3	1217.4	1215.5	1213.6	1210.6	1207.5
145°	1254.0	1255.2	1256.3	1256.9	1256.1	1254.4	1252.8	1251.1	1249.5	1245.5	1241.5
147.5°	1285.2	1286.2	1287.1	1287.6	1287.0	1285.8	1284.7	1283.5	1282.3	1278.3	1274.3
150°	1314.2	1315.4	1316.5	1317.1	1316.4	1315.0	1313.6	1312.2	1310.8	1307.0	1303.3
152.5°	1339.4	1341.1	1342.7	1343.5	1342.8	1341.4	1340.0	1338.6	1337.2	1333.7	1330.2
155°	1362.1	1364.0	1365.9	1366.8	1366.1	1364.7	1363.2	1361.8	1360.4	1357.6	1354.8
157.5°	1383.2	1385.1	1387.0	1387.9	1387.1	1385.4	1383.8	1382.1	1380.5	1378.4	1376.3
160°	1400.7	1402.3	1404.0	1404.8	1404.1	1402.7	1401.3	1399.9	1398.5	1397.1	1395.7
162.5°	1416.4	1418.5	1420.6	1421.7	1420.9	1419.2	1417.6	1415.9	1414.3	1413.1	1411.9
165°	1430.3	1431.9	1433.6	1434.4	1433.6	1431.9	1430.3	1428.6	1427.0	1426.3	1425.6
167.5°	1440.7	1442.8	1444.9	1446.0	1445.2	1443.5	1441.9	1440.2	1438.6	1437.9	1437.2
170°	1449.2	1451.3	1453.4	1454.5	1453.7	1452.0	1450.4	1448.7	1447.1	1446.6	1446.1
172.5°	1455.5	1457.6	1459.7	1460.8	1460.0	1458.3	1456.7	1455.0	1453.4	1452.9	1452.5
175°	1459.2	1461.5	1463.8	1465.0	1464.2	1462.5	1460.9	1459.2	1457.6	1457.1	1456.7
177.5°	1460.8	1462.9	1465.0	1466.1	1465.3	1463.6	1462.0	1460.3	1458.7	1458.5	1458.2
180°	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7

TEST NUMBER: P998984

CATALOG NUMBER: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1751.1	1744.5	1740.6	1743.2	1735.3	1715.7	1715.7	1722.2	1714.3	1706.5	1694.7
5°	1799.6	1786.5	1778.6	1777.3	1758.9	1727.5	1720.9	1714.3	1697.3	1678.9	1659.3
7.5°	1846.8	1823.2	1810.1	1800.9	1774.7	1734.0	1717.0	1702.5	1675.0	1647.4	1622.5
10°	1886.2	1852.1	1836.3	1821.9	1787.8	1736.6	1709.1	1682.9	1647.4	1612.0	1580.6
12.5°	1917.7	1878.3	1858.6	1837.6	1795.7	1728.8	1694.7	1652.7	1617.3	1570.1	1538.6
15°	1970.1	1888.8	1870.4	1850.8	1807.5	1715.7	1673.7	1626.5	1577.9	1515.0	1480.9
17.5°	2012.1	1903.2	1901.9	1859.9	1803.5	1710.4	1646.1	1584.5	1532.0	1469.1	1415.3
20°	2037.0	1925.5	1904.5	1861.2	1790.4	1675.0	1608.1	1539.9	1483.5	1407.4	1353.6
22.5°	2058.0	1957.0	1901.9	1849.4	1762.9	1663.2	1564.8	1500.5	1423.2	1340.5	1289.4
25°	2065.9	1963.6	1905.8	1845.5	1743.2	1629.1	1517.6	1448.1	1361.5	1286.7	1217.2
27.5°	2067.2	1962.2	1891.4	1828.5	1715.7	1584.5	1470.4	1396.9	1301.2	1214.6	1145.1
30°	2054.1	1947.8	1883.5	1815.3	1689.4	1543.8	1412.7	1331.3	1229.0	1142.5	1070.3
32.5°	2014.7	1919.0	1866.5	1791.7	1655.3	1487.4	1357.6	1267.1	1159.5	1074.3	1004.7
35°	1949.1	1883.5	1825.8	1756.3	1610.7	1435.0	1302.5	1196.2	1087.4	1006.0	940.5
37.5°	1867.8	1832.4	1778.6	1710.4	1559.6	1387.7	1240.8	1122.8	1013.9	935.2	870.9
40°	1757.6	1766.8	1714.3	1652.7	1499.2	1323.5	1160.8	1048.0	945.7	872.3	809.3
42.5°	1638.3	1676.3	1646.1	1587.1	1432.3	1252.6	1101.8	977.2	877.5	801.4	749.0
45°	1509.7	1575.3	1556.9	1513.7	1362.8	1177.9	1017.9	897.2	809.3	735.8	689.9
47.5°	1369.4	1462.5	1462.5	1431.0	1285.4	1103.1	945.7	822.4	735.8	683.4	638.8
50°	1226.4	1331.3	1348.4	1327.4	1198.9	1017.9	857.8	746.3	671.6	620.4	587.6
52.5°	1076.9	1198.9	1230.3	1219.8	1107.0	936.5	785.7	676.8	608.6	564.0	535.2
55°	933.9	1075.6	1109.7	1113.6	1008.7	847.3	705.7	609.9	544.3	514.2	489.3
57.5°	798.8	935.2	973.3	979.8	909.0	766.0	630.9	547.0	487.9	463.0	443.3
60°	683.4	797.5	847.3	861.8	800.1	671.6	561.4	480.1	435.5	411.9	393.5
62.5°	588.9	680.8	733.2	737.2	709.6	588.9	489.3	421.0	383.0	362.0	352.8
65°	497.1	579.8	611.2	627.0	604.7	510.2	422.4	366.0	335.8	317.4	308.2
67.5°	423.7	476.1	502.4	523.4	501.1	430.2	359.4	313.5	291.2	272.8	267.6
70°	347.6	390.9	410.6	431.5	411.9	358.1	306.9	265.0	245.3	230.9	224.3
72.5°	278.1	312.2	330.5	343.7	331.9	287.3	245.3	216.4	202.0	191.5	187.6
75°	220.4	244.0	254.5	263.6	258.4	224.3	198.1	174.5	161.3	152.2	149.5
77.5°	167.9	184.9	196.7	199.4	192.8	170.5	148.2	133.8	123.3	118.0	115.4
80°	119.4	129.9	136.4	140.3	133.8	124.6	108.9	98.4	89.2	82.6	81.3
82.5°	80.0	85.3	90.5	89.2	86.6	78.7	69.5	64.3	60.3	55.1	55.1
85°	45.9	47.2	49.8	51.2	49.8	44.6	39.3	36.7	34.1	30.2	30.2
87.5°	19.7	21.0	21.0	22.3	19.7	19.7	17.1	14.4	14.4	13.1	11.8
90°	15.5	13.6	12.7	11.4	8.8	6.3	3.7	1.1	3.7	6.3	8.8
92.5°	23.2	22.5	22.2	22.7	23.6	24.5	25.5	26.4	25.5	24.5	23.6
95°	36.3	34.6	33.8	37.7	45.4	53.2	60.9	68.7	60.9	53.2	45.4
97.5°	42.6	38.9	37.0	46.6	65.9	85.1	104.4	123.6	104.4	85.1	65.9
100°	48.2	44.2	42.2	58.3	90.5	122.6	154.8	187.0	154.8	122.6	90.5
102.5°	190.5	233.2	254.6	254.8	255.3	255.8	256.2	256.7	256.2	255.8	255.3
105°	256.7	320.8	352.8	349.3	342.2	335.2	328.1	321.1	328.1	335.2	342.2
107.5°	303.8	382.9	422.5	419.6	413.7	407.8	402.0	396.1	402.0	407.8	413.7
110°	388.3	456.2	490.1	487.6	482.7	477.8	472.8	467.9	472.8	477.8	482.7

TEST NUMBER: P998984

CATALOG NUMBER: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	548.5	552.5	554.5	552.4	548.2	543.9	539.7	535.5	539.7	543.9	548.2
115°	634.1	628.2	625.3	623.3	619.3	615.3	611.3	607.3	611.3	615.3	619.3
117.5°	696.8	692.8	690.8	688.5	683.8	679.1	674.4	669.7	674.4	679.1	683.8
120°	761.5	757.3	755.2	753.4	749.9	746.4	742.9	739.4	742.9	746.4	749.9
122.5°	822.4	817.7	815.4	813.5	809.8	806.0	802.3	798.5	802.3	806.0	809.8
125°	879.2	874.7	872.5	871.0	867.9	864.8	861.8	858.7	861.8	864.8	867.9
127.5°	933.7	930.2	928.4	926.8	923.5	920.2	917.0	913.7	917.0	920.2	923.5
130°	986.2	983.6	982.3	980.4	976.7	972.9	969.2	965.4	969.2	972.9	976.7
132.5°	1035.9	1033.3	1032.0	1030.5	1027.4	1024.3	1021.3	1018.2	1021.3	1024.3	1027.4
135°	1082.7	1080.6	1079.5	1077.6	1073.9	1070.1	1066.4	1062.6	1066.4	1070.1	1073.9
137.5°	1125.2	1122.9	1121.7	1120.3	1117.5	1114.7	1111.9	1109.1	1111.9	1114.7	1117.5
140°	1166.8	1164.2	1162.9	1162.0	1160.1	1158.2	1156.4	1154.5	1156.4	1158.2	1160.1
142.5°	1204.5	1201.4	1199.9	1199.1	1197.4	1195.8	1194.1	1192.5	1194.1	1195.8	1197.4
145°	1237.6	1233.6	1231.6	1231.7	1231.9	1232.2	1232.4	1232.6	1232.4	1232.2	1231.9
147.5°	1270.3	1266.3	1264.3	1264.7	1265.4	1266.1	1266.8	1267.5	1266.8	1266.1	1265.4
150°	1299.5	1295.8	1293.9	1294.7	1296.4	1298.0	1299.7	1301.3	1299.7	1298.0	1296.4
152.5°	1326.7	1323.2	1321.4	1322.3	1324.2	1326.1	1327.9	1329.8	1327.9	1326.1	1324.2
155°	1352.0	1349.2	1347.8	1348.9	1351.0	1353.1	1355.2	1357.3	1355.2	1353.1	1351.0
157.5°	1374.2	1372.1	1371.0	1371.9	1373.8	1375.7	1377.6	1379.5	1377.6	1375.7	1373.8
160°	1394.2	1392.8	1392.1	1392.8	1394.2	1395.7	1397.1	1398.5	1397.1	1395.7	1394.2
162.5°	1410.8	1409.6	1409.0	1409.7	1411.1	1412.6	1414.0	1415.4	1414.0	1412.6	1411.1
165°	1424.9	1424.2	1423.8	1424.5	1425.9	1427.4	1428.8	1430.2	1428.8	1427.4	1425.9
167.5°	1436.5	1435.8	1435.4	1436.1	1437.5	1439.0	1440.4	1441.8	1440.4	1439.0	1437.5
170°	1445.6	1445.1	1444.9	1445.6	1447.0	1448.5	1449.9	1451.3	1449.9	1448.5	1447.0
172.5°	1452.0	1451.5	1451.3	1452.0	1453.4	1454.8	1456.2	1457.6	1456.2	1454.8	1453.4
175°	1456.2	1455.7	1455.5	1456.3	1458.0	1459.6	1461.3	1462.9	1461.3	1459.6	1458.0
177.5°	1458.0	1457.7	1457.6	1458.4	1460.1	1461.7	1463.4	1465.0	1463.4	1461.7	1460.1
180°	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7

TEST NUMBER: P998984

CATALOG NUMBER: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1688.1	1694.7	1693.4	1680.2	1665.8	1654.0	1631.7	1634.3	1626.5	1627.8	1635.6
5°	1646.1	1646.1	1640.9	1622.5	1598.9	1585.8	1560.9	1554.3	1538.6	1537.3	1536.0
7.5°	1601.5	1595.0	1588.4	1562.2	1533.3	1512.3	1478.2	1470.4	1454.6	1444.1	1438.9
10°	1549.1	1539.9	1526.8	1496.6	1461.2	1435.0	1399.5	1389.1	1358.9	1345.8	1337.9
12.5°	1491.4	1486.1	1465.1	1440.2	1382.5	1353.6	1302.5	1313.0	1282.8	1256.6	1252.6
15°	1433.6	1414.0	1402.2	1361.5	1292.0	1278.9	1238.2	1217.2	1189.7	1168.7	1168.7
17.5°	1377.2	1347.1	1320.8	1277.6	1226.4	1189.7	1159.5	1149.0	1114.9	1093.9	1090.0
20°	1302.5	1268.4	1261.8	1200.2	1164.8	1124.1	1095.2	1069.0	1044.1	1034.9	1028.3
22.5°	1231.7	1192.3	1181.8	1129.3	1093.9	1053.3	1024.4	1006.0	987.7	981.1	969.3
25°	1155.6	1132.0	1116.2	1059.8	1020.5	982.4	962.8	949.6	932.6	931.3	923.4
27.5°	1082.1	1059.8	1044.1	990.3	961.4	926.0	910.3	895.9	886.7	882.7	878.8
30°	1019.2	994.2	975.9	936.5	901.1	872.3	859.1	850.0	844.7	838.2	836.8
32.5°	949.6	935.2	910.3	880.1	852.6	825.0	817.2	810.6	802.7	800.1	798.8
35°	890.6	870.9	855.2	821.1	809.3	785.7	776.5	771.3	760.8	758.1	755.5
37.5°	832.9	814.5	797.5	776.5	754.2	741.1	735.8	728.0	722.7	724.0	721.4
40°	775.2	760.8	747.6	725.3	712.2	705.7	695.2	687.3	684.7	686.0	684.7
42.5°	718.8	705.7	697.8	680.8	667.6	661.1	654.5	646.6	650.6	650.6	654.5
45°	667.6	655.8	650.6	637.5	629.6	619.1	612.5	611.2	616.5	615.2	615.2
47.5°	615.2	611.2	604.7	592.9	582.4	575.8	574.5	574.5	579.8	582.4	581.1
50°	574.5	566.6	558.8	549.6	541.7	539.1	535.2	537.8	543.0	543.0	545.7
52.5°	523.4	518.1	515.5	507.6	502.4	502.4	502.4	503.7	507.6	511.5	510.2
55°	478.8	474.8	472.2	468.3	461.7	463.0	461.7	464.3	468.3	472.2	474.8
57.5°	431.5	430.2	427.6	421.0	421.0	419.7	423.7	425.0	431.5	434.2	438.1
60°	389.6	385.6	385.6	380.4	380.4	380.4	384.3	388.3	393.5	394.8	397.4
62.5°	345.0	345.0	343.7	339.7	339.7	343.7	345.0	350.2	352.8	352.8	356.8
65°	303.0	301.7	300.4	301.7	303.0	303.0	306.9	309.6	312.2	313.5	314.8
67.5°	261.0	259.7	262.3	261.0	263.6	268.9	267.6	271.5	275.4	275.4	276.8
70°	221.7	224.3	223.0	225.6	224.3	226.9	230.9	232.2	232.2	233.5	237.4
72.5°	184.9	184.9	184.9	183.6	184.9	187.6	190.2	191.5	194.1	195.4	199.4
75°	149.5	149.5	146.9	149.5	149.5	152.2	154.8	154.8	154.8	157.4	161.3
77.5°	112.8	114.1	112.8	115.4	115.4	116.7	119.4	118.0	120.7	122.0	123.3
80°	82.6	81.3	81.3	81.3	82.6	82.6	85.3	86.6	86.6	90.5	87.9
82.5°	52.5	53.8	52.5	53.8	53.8	55.1	53.8	55.1	56.4	59.0	57.7
85°	30.2	28.9	28.9	30.2	28.9	28.9	30.2	28.9	30.2	28.9	30.2
87.5°	11.8	10.5	10.5	10.5	10.5	9.2	9.2	7.9	7.9	7.9	6.6
90°	11.4	12.7	13.6	15.5	17.4	19.2	21.1	22.3	23.5	24.6	25.8
92.5°	22.7	22.2	22.5	23.2	23.9	24.6	25.3	25.8	26.3	26.8	27.3
95°	37.7	33.8	34.6	36.3	37.9	39.6	41.2	42.4	43.6	44.7	45.9
97.5°	46.6	37.0	38.9	42.6	46.4	50.1	53.9	54.6	55.3	56.0	56.7
100°	58.3	42.2	44.2	48.2	52.2	56.2	60.2	62.1	64.0	65.9	67.8
102.5°	254.8	254.6	233.2	190.5	147.8	105.0	62.3	64.9	67.5	70.0	72.6
105°	349.3	352.8	320.8	256.7	192.6	128.5	64.4	67.0	69.6	72.1	74.7
107.5°	419.6	422.5	382.9	303.8	224.7	145.6	66.5	69.1	71.7	74.3	76.9
110°	487.6	490.1	456.2	388.3	320.5	252.6	184.8	161.3	137.9	114.4	90.9

TEST NUMBER: P998984

CATALOG NUMBER: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	552.4	554.5	552.5	548.5	544.6	540.6	536.6	435.4	334.2	233.1	131.9
115°	623.3	625.3	628.2	634.1	640.0	645.8	651.7	543.0	434.4	325.7	217.0
117.5°	688.5	690.8	692.8	696.8	700.7	704.7	708.7	675.1	641.6	608.0	574.5
120°	753.4	755.2	757.3	761.5	765.8	770.0	774.2	777.0	779.8	782.7	785.5
122.5°	813.5	815.4	817.7	822.4	827.1	831.8	836.5	837.9	839.3	840.8	842.2
125°	871.0	872.5	874.7	879.2	883.6	888.1	892.5	894.1	895.8	897.4	899.1
127.5°	926.8	928.4	930.2	933.7	937.2	940.8	944.3	946.6	949.0	951.3	953.6
130°	980.4	982.3	983.6	986.2	988.7	991.3	993.9	996.5	999.1	1001.6	1004.2
132.5°	1030.5	1032.0	1033.3	1035.9	1038.4	1041.0	1043.6	1045.7	1047.8	1049.9	1052.0
135°	1077.6	1079.5	1080.6	1082.7	1084.8	1086.9	1089.0	1091.4	1093.7	1096.1	1098.4
137.5°	1120.3	1121.7	1122.9	1125.2	1127.6	1129.9	1132.3	1134.7	1137.0	1139.4	1141.7
140°	1162.0	1162.9	1164.2	1166.8	1169.3	1171.9	1174.5	1176.6	1178.8	1180.9	1183.0
142.5°	1199.1	1199.9	1201.4	1204.5	1207.5	1210.6	1213.6	1215.5	1217.4	1219.3	1221.2
145°	1231.7	1231.6	1233.6	1237.6	1241.5	1245.5	1249.5	1251.1	1252.8	1254.4	1256.1
147.5°	1264.7	1264.3	1266.3	1270.3	1274.3	1278.3	1282.3	1283.5	1284.7	1285.8	1287.0
150°	1294.7	1293.9	1295.8	1299.5	1303.3	1307.0	1310.8	1312.2	1313.6	1315.0	1316.4
152.5°	1322.3	1321.4	1323.2	1326.7	1330.2	1333.7	1337.2	1338.6	1340.0	1341.4	1342.8
155°	1348.9	1347.8	1349.2	1352.0	1354.8	1357.6	1360.4	1361.8	1363.2	1364.7	1366.1
157.5°	1371.9	1371.0	1372.1	1374.2	1376.3	1378.4	1380.5	1382.1	1383.8	1385.4	1387.1
160°	1392.8	1392.1	1392.8	1394.2	1395.7	1397.1	1398.5	1399.9	1401.3	1402.7	1404.1
162.5°	1409.7	1409.0	1409.6	1410.8	1411.9	1413.1	1414.3	1415.9	1417.6	1419.2	1420.9
165°	1424.5	1423.8	1424.2	1424.9	1425.6	1426.3	1427.0	1428.6	1430.3	1431.9	1433.6
167.5°	1436.1	1435.4	1435.8	1436.5	1437.2	1437.9	1438.6	1440.2	1441.9	1443.5	1445.2
170°	1445.6	1444.9	1445.1	1445.6	1446.1	1446.6	1447.1	1448.7	1450.4	1452.0	1453.7
172.5°	1452.0	1451.3	1451.5	1452.0	1452.5	1452.9	1453.4	1455.0	1456.7	1458.3	1460.0
175°	1456.3	1455.5	1455.7	1456.2	1456.7	1457.1	1457.6	1459.2	1460.9	1462.5	1464.2
177.5°	1458.4	1457.6	1457.7	1458.0	1458.2	1458.5	1458.7	1460.3	1462.0	1463.6	1465.3
180°	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7

TEST NUMBER: P998984

CATALOG NUMBER: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1626.5	1630.4	1621.2	1618.6	1621.2	1612.0	1614.7	1617.3	1617.3	1621.2	1623.8
5°	1532.0	1526.8	1517.6	1515.0	1512.3	1516.3	1513.7	1517.6	1518.9	1528.1	1529.4
7.5°	1438.9	1431.0	1423.2	1415.3	1412.7	1406.1	1412.7	1412.7	1421.8	1419.2	1425.8
10°	1328.7	1327.4	1316.9	1313.0	1307.7	1297.2	1311.7	1307.7	1314.3	1326.1	1328.7
12.5°	1247.4	1233.0	1239.5	1221.2	1227.7	1217.2	1218.5	1218.5	1229.0	1230.3	1227.7
15°	1170.0	1158.2	1141.1	1133.3	1129.3	1124.1	1141.1	1142.5	1134.6	1153.0	1146.4
17.5°	1091.3	1091.3	1075.6	1071.6	1061.1	1066.4	1063.8	1065.1	1062.4	1075.6	1082.1
20°	1023.1	1016.5	1011.3	1012.6	999.5	996.9	994.2	996.9	1006.0	1015.2	1017.9
22.5°	968.0	964.1	951.0	953.6	943.1	947.0	944.4	951.0	952.3	952.3	961.4
25°	915.5	910.3	911.6	906.4	902.4	902.4	898.5	902.4	907.7	910.3	911.6
27.5°	876.2	872.3	865.7	861.8	864.4	857.8	863.1	867.0	867.0	864.4	867.0
30°	829.0	831.6	831.6	818.5	823.7	821.1	825.0	827.7	827.7	829.0	826.3
32.5°	797.5	789.6	788.3	787.0	787.0	781.8	781.8	785.7	787.0	788.3	792.2
35°	755.5	755.5	749.0	752.9	747.6	749.0	747.6	749.0	751.6	747.6	751.6
37.5°	717.5	718.8	716.2	718.8	720.1	717.5	714.9	720.1	717.5	717.5	714.9
40°	684.7	683.4	684.7	684.7	684.7	686.0	683.4	683.4	683.4	680.8	678.1
42.5°	657.1	649.3	651.9	653.2	649.3	649.3	650.6	649.3	653.2	645.3	645.3
45°	617.8	615.2	616.5	616.5	619.1	615.2	617.8	619.1	615.2	613.9	611.2
47.5°	582.4	585.0	582.4	585.0	585.0	587.6	582.4	583.7	585.0	579.8	575.8
50°	547.0	547.0	550.9	549.6	550.9	548.3	548.3	547.0	548.3	545.7	541.7
52.5°	514.2	510.2	516.8	515.5	514.2	512.9	511.5	512.9	510.2	507.6	507.6
55°	473.5	473.5	477.4	478.8	478.8	476.1	473.5	474.8	473.5	472.2	470.9
57.5°	440.7	435.5	438.1	439.4	439.4	435.5	438.1	435.5	435.5	436.8	432.8
60°	398.7	398.7	396.1	400.1	400.1	397.4	397.4	398.7	396.1	394.8	393.5
62.5°	354.1	355.5	359.4	360.7	362.0	359.4	356.8	358.1	358.1	354.1	355.5
65°	316.1	318.7	324.0	322.7	320.0	321.4	318.7	320.0	316.1	317.4	313.5
67.5°	279.4	278.1	279.4	279.4	282.0	280.7	278.1	278.1	276.8	280.7	276.8
70°	240.0	240.0	240.0	240.0	241.3	242.7	240.0	237.4	238.7	236.1	234.8
72.5°	199.4	200.7	199.4	202.0	198.1	200.7	200.7	199.4	198.1	198.1	198.1
75°	161.3	164.0	160.0	161.3	160.0	162.6	161.3	161.3	158.7	157.4	158.7
77.5°	123.3	124.6	122.0	123.3	122.0	123.3	123.3	122.0	122.0	122.0	122.0
80°	87.9	89.2	87.9	86.6	85.3	87.9	85.3	86.6	87.9	86.6	89.2
82.5°	56.4	56.4	55.1	56.4	53.8	53.8	55.1	55.1	53.8	56.4	53.8
85°	27.5	27.5	30.2	27.5	26.2	26.2	26.2	27.5	26.2	28.9	27.5
87.5°	6.6	5.2	6.6	6.6	5.2	5.2	6.6	5.2	6.6	7.9	5.2
90°	26.4	26.6	27.1	27.6	28.0	28.5	28.0	27.6	27.1	26.6	26.4
92.5°	27.5	27.6	27.8	28.1	28.3	28.5	28.3	28.1	27.8	27.6	27.5
95°	46.5	46.4	46.1	45.9	45.6	45.4	45.6	45.9	46.1	46.4	46.5
97.5°	57.0	57.1	57.4	57.6	57.9	58.1	57.9	57.6	57.4	57.1	57.0
100°	68.7	68.9	69.4	69.9	70.3	70.8	70.3	69.9	69.4	68.9	68.7
102.5°	73.9	74.3	75.0	75.7	76.4	77.1	76.4	75.7	75.0	74.3	73.9
105°	76.0	76.5	77.4	78.4	79.3	80.3	79.3	78.4	77.4	76.5	76.0
107.5°	78.2	78.7	79.6	80.5	81.5	82.4	81.5	80.5	79.6	78.7	78.2
110°	79.2	79.7	80.6	81.5	82.5	83.4	82.5	81.5	80.6	79.7	79.2

TEST NUMBER: P998984

CATALOG NUMBER: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	81.3	81.7	82.4	83.1	83.8	84.5	83.8	83.1	82.4	81.7	81.3
115°	162.7	154.2	137.3	120.4	103.5	86.6	103.5	120.4	137.3	154.2	162.7
117.5°	557.7	527.0	465.5	404.0	342.5	281.0	342.5	404.0	465.5	527.0	557.7
120°	786.9	771.1	739.4	707.7	676.0	644.3	676.0	707.7	739.4	771.1	786.9
122.5°	842.9	843.0	843.2	843.5	843.7	843.9	843.7	843.5	843.2	843.0	842.9
125°	899.9	900.3	901.0	901.7	902.4	903.1	902.4	901.7	901.0	900.3	899.9
127.5°	954.8	954.9	955.2	955.4	955.7	955.9	955.7	955.4	955.2	954.9	954.8
130°	1005.5	1005.4	1005.2	1004.9	1004.7	1004.5	1004.7	1004.9	1005.2	1005.4	1005.5
132.5°	1053.1	1053.0	1052.7	1052.5	1052.2	1052.0	1052.2	1052.5	1052.7	1053.0	1053.1
135°	1099.6	1099.4	1098.9	1098.4	1097.9	1097.4	1097.9	1098.4	1098.9	1099.4	1099.6
137.5°	1142.9	1142.5	1141.8	1141.1	1140.4	1139.7	1140.4	1141.1	1141.8	1142.5	1142.9
140°	1184.1	1183.5	1182.3	1181.2	1180.0	1178.8	1180.0	1181.2	1182.3	1183.5	1184.1
142.5°	1222.1	1221.5	1220.3	1219.2	1218.0	1216.8	1218.0	1219.2	1220.3	1221.5	1222.1
145°	1256.9	1256.3	1255.2	1254.0	1252.9	1251.7	1252.9	1254.0	1255.2	1256.3	1256.9
147.5°	1287.6	1287.1	1286.2	1285.2	1284.3	1283.3	1284.3	1285.2	1286.2	1287.1	1287.6
150°	1317.1	1316.5	1315.4	1314.2	1313.1	1311.9	1313.1	1314.2	1315.4	1316.5	1317.1
152.5°	1343.5	1342.7	1341.1	1339.4	1337.8	1336.2	1337.8	1339.4	1341.1	1342.7	1343.5
155°	1366.8	1365.9	1364.0	1362.1	1360.2	1358.3	1360.2	1362.1	1364.0	1365.9	1366.8
157.5°	1387.9	1387.0	1385.1	1383.2	1381.4	1379.5	1381.4	1383.2	1385.1	1387.0	1387.9
160°	1404.8	1404.0	1402.3	1400.7	1399.0	1397.4	1399.0	1400.7	1402.3	1404.0	1404.8
162.5°	1421.7	1420.6	1418.5	1416.4	1414.3	1412.2	1414.3	1416.4	1418.5	1420.6	1421.7
165°	1434.4	1433.6	1431.9	1430.3	1428.6	1427.0	1428.6	1430.3	1431.9	1433.6	1434.4
167.5°	1446.0	1444.9	1442.8	1440.7	1438.6	1436.5	1438.6	1440.7	1442.8	1444.9	1446.0
170°	1454.5	1453.4	1451.3	1449.2	1447.0	1444.9	1447.0	1449.2	1451.3	1453.4	1454.5
172.5°	1460.8	1459.7	1457.6	1455.5	1453.4	1451.3	1453.4	1455.5	1457.6	1459.7	1460.8
175°	1465.0	1463.8	1461.5	1459.2	1456.8	1454.5	1456.8	1459.2	1461.5	1463.8	1465.0
177.5°	1466.1	1465.0	1462.9	1460.8	1458.7	1456.6	1458.7	1460.8	1462.9	1465.0	1466.1
180°	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7

TEST NUMBER: P998984

CATALOG NUMBER: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1619.9	1630.4	1626.5	1612.0	1629.1	1629.1	1640.9	1640.9	1655.3	1660.6	1668.4
5°	1528.1	1536.0	1542.5	1536.0	1547.8	1566.1	1576.6	1585.8	1605.5	1613.3	1625.2
7.5°	1429.7	1444.1	1450.7	1450.7	1470.4	1491.4	1512.3	1525.5	1553.0	1563.5	1575.3
10°	1334.0	1351.0	1364.1	1362.8	1395.6	1408.7	1435.0	1465.1	1492.7	1508.4	1525.5
12.5°	1233.0	1242.1	1260.5	1286.7	1294.6	1318.2	1348.4	1386.4	1436.3	1450.7	1475.6
15°	1149.0	1173.9	1188.4	1200.2	1218.5	1240.8	1273.6	1310.4	1360.2	1391.7	1417.9
17.5°	1078.2	1111.0	1120.2	1117.5	1141.1	1175.2	1213.3	1240.8	1285.4	1323.5	1348.4
20°	1020.5	1033.6	1049.3	1055.9	1074.3	1111.0	1147.7	1179.2	1215.9	1246.1	1274.9
22.5°	962.8	973.3	986.4	998.2	1012.6	1033.6	1069.0	1108.4	1143.8	1172.6	1205.4
25°	915.5	922.1	933.9	943.1	958.8	973.3	998.2	1041.5	1083.4	1100.5	1129.3
27.5°	869.6	874.9	882.7	893.2	901.1	915.5	937.8	973.3	1016.5	1033.6	1072.9
30°	829.0	832.9	840.8	846.0	850.0	867.0	884.1	911.6	944.4	968.0	996.9
32.5°	790.9	794.9	802.7	804.0	809.3	818.5	834.2	859.1	888.0	907.7	932.6
35°	749.0	751.6	759.5	762.1	766.0	773.9	785.7	804.0	830.3	844.7	867.0
37.5°	716.2	714.9	720.1	724.0	729.3	733.2	737.2	755.5	775.2	788.3	805.4
40°	680.8	678.1	679.4	684.7	687.3	692.6	692.6	710.9	724.0	734.5	747.6
42.5°	645.3	644.0	641.4	644.0	646.6	648.0	649.3	662.4	675.5	684.7	699.1
45°	609.9	608.6	606.0	607.3	607.3	609.9	613.9	619.1	628.3	636.2	644.0
47.5°	577.1	574.5	570.6	569.3	571.9	571.9	571.9	577.1	586.3	588.9	596.8
50°	543.0	539.1	533.8	531.2	531.2	529.9	532.5	533.8	541.7	544.3	550.9
52.5°	506.3	503.7	498.4	493.2	494.5	491.9	493.2	494.5	497.1	501.1	505.0
55°	469.6	464.3	460.4	459.1	455.1	455.1	451.2	456.5	455.1	456.5	461.7
57.5°	434.2	428.9	422.4	419.7	415.8	414.5	411.9	410.6	411.9	415.8	419.7
60°	392.2	389.6	385.6	381.7	379.1	375.1	372.5	372.5	371.2	371.2	372.5
62.5°	351.5	350.2	345.0	343.7	341.0	338.4	334.5	331.9	331.9	334.5	335.8
65°	312.2	310.9	306.9	305.6	299.1	296.4	295.1	293.8	291.2	291.2	291.2
67.5°	275.4	271.5	271.5	265.0	259.7	257.1	254.5	253.2	253.2	253.2	254.5
70°	234.8	234.8	230.9	226.9	221.7	223.0	219.0	215.1	215.1	212.5	213.8
72.5°	195.4	194.1	190.2	188.9	184.9	181.0	178.4	181.0	177.1	175.8	177.1
75°	157.4	156.1	153.5	150.8	152.2	148.2	144.3	143.0	143.0	140.3	140.3
77.5°	120.7	123.3	118.0	116.7	114.1	111.5	110.2	108.9	108.9	108.9	111.5
80°	83.9	85.3	85.3	82.6	83.9	80.0	80.0	80.0	76.1	77.4	78.7
82.5°	53.8	53.8	52.5	53.8	52.5	52.5	51.2	51.2	49.8	49.8	51.2
85°	30.2	28.9	27.5	30.2	28.9	28.9	27.5	27.5	27.5	27.5	27.5
87.5°	6.6	7.9	7.9	7.9	7.9	9.2	9.2	9.2	10.5	10.5	10.5
90°	25.8	24.6	23.5	22.3	21.1	19.2	17.4	15.5	13.6	12.7	11.4
92.5°	27.3	26.8	26.3	25.8	25.3	24.6	23.9	23.2	22.5	22.2	22.7
95°	45.9	44.7	43.6	42.4	41.2	39.6	37.9	36.3	34.6	33.8	37.7
97.5°	56.7	56.0	55.3	54.6	53.9	50.1	46.4	42.6	38.9	37.0	46.6
100°	67.8	65.9	64.0	62.1	60.2	56.2	52.2	48.2	44.2	42.2	58.3
102.5°	72.6	70.0	67.5	64.9	62.3	105.0	147.8	190.5	233.2	254.6	254.8
105°	74.7	72.1	69.6	67.0	64.4	128.5	192.6	256.7	320.8	352.8	349.3
107.5°	76.9	74.3	71.7	69.1	66.5	145.6	224.7	303.8	382.9	422.5	419.6
110°	90.9	114.4	137.9	161.3	184.8	252.6	320.5	388.3	456.2	490.1	487.6

TEST NUMBER: P998984

CATALOG NUMBER: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	131.9	233.1	334.2	435.4	536.6	540.6	544.6	548.5	552.5	554.5	552.4
115°	217.0	325.7	434.4	543.0	651.7	645.8	640.0	634.1	628.2	625.3	623.3
117.5°	574.5	608.0	641.6	675.1	708.7	704.7	700.7	696.8	692.8	690.8	688.5
120°	785.5	782.7	779.8	777.0	774.2	770.0	765.8	761.5	757.3	755.2	753.4
122.5°	842.2	840.8	839.3	837.9	836.5	831.8	827.1	822.4	817.7	815.4	813.5
125°	899.1	897.4	895.8	894.1	892.5	888.1	883.6	879.2	874.7	872.5	871.0
127.5°	953.6	951.3	949.0	946.6	944.3	940.8	937.2	933.7	930.2	928.4	926.8
130°	1004.2	1001.6	999.1	996.5	993.9	991.3	988.7	986.2	983.6	982.3	980.4
132.5°	1052.0	1049.9	1047.8	1045.7	1043.6	1041.0	1038.4	1035.9	1033.3	1032.0	1030.5
135°	1098.4	1096.1	1093.7	1091.4	1089.0	1086.9	1084.8	1082.7	1080.6	1079.5	1077.6
137.5°	1141.7	1139.4	1137.0	1134.7	1132.3	1129.9	1127.6	1125.2	1122.9	1121.7	1120.3
140°	1183.0	1180.9	1178.8	1176.6	1174.5	1171.9	1169.3	1166.8	1164.2	1162.9	1162.0
142.5°	1221.2	1219.3	1217.4	1215.5	1213.6	1210.6	1207.5	1204.5	1201.4	1199.9	1199.1
145°	1256.1	1254.4	1252.8	1251.1	1249.5	1245.5	1241.5	1237.6	1233.6	1231.6	1231.7
147.5°	1287.0	1285.8	1284.7	1283.5	1282.3	1278.3	1274.3	1270.3	1266.3	1264.3	1264.7
150°	1316.4	1315.0	1313.6	1312.2	1310.8	1307.0	1303.3	1299.5	1295.8	1293.9	1294.7
152.5°	1342.8	1341.4	1340.0	1338.6	1337.2	1333.7	1330.2	1326.7	1323.2	1321.4	1322.3
155°	1366.1	1364.7	1363.2	1361.8	1360.4	1357.6	1354.8	1352.0	1349.2	1347.8	1348.9
157.5°	1387.1	1385.4	1383.8	1382.1	1380.5	1378.4	1376.3	1374.2	1372.1	1371.0	1371.9
160°	1404.1	1402.7	1401.3	1399.9	1398.5	1397.1	1395.7	1394.2	1392.8	1392.1	1392.8
162.5°	1420.9	1419.2	1417.6	1415.9	1414.3	1413.1	1411.9	1410.8	1409.6	1409.0	1409.7
165°	1433.6	1431.9	1430.3	1428.6	1427.0	1426.3	1425.6	1424.9	1424.2	1423.8	1424.5
167.5°	1445.2	1443.5	1441.9	1440.2	1438.6	1437.9	1437.2	1436.5	1435.8	1435.4	1436.1
170°	1453.7	1452.0	1450.4	1448.7	1447.1	1446.6	1446.1	1445.6	1445.1	1444.9	1445.6
172.5°	1460.0	1458.3	1456.7	1455.0	1453.4	1452.9	1452.5	1452.0	1451.5	1451.3	1452.0
175°	1464.2	1462.5	1460.9	1459.2	1457.6	1457.1	1456.7	1456.2	1455.7	1455.5	1456.3
177.5°	1465.3	1463.6	1462.0	1460.3	1458.7	1458.5	1458.2	1458.0	1457.7	1457.6	1458.4
180°	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7	1459.7

TEST NUMBER: P998984

CATALOG NUMBER: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1706.5	1706.5	1706.5	1706.5
2.5°	1675.0	1675.0	1694.7	1715.7
5°	1638.3	1647.4	1678.9	1707.8
7.5°	1602.9	1618.6	1657.9	1694.7
10°	1559.6	1580.6	1629.1	1672.4
12.5°	1517.6	1537.3	1593.7	1642.2
15°	1458.6	1483.5	1543.8	1604.2
17.5°	1399.5	1424.5	1497.9	1568.7
20°	1330.0	1362.8	1445.5	1539.9
22.5°	1265.8	1306.4	1398.2	1474.3
25°	1194.9	1257.9	1343.1	1441.5
27.5°	1132.0	1194.9	1281.5	1381.2
30°	1061.1	1125.4	1214.6	1306.4
32.5°	992.9	1052.0	1138.5	1251.3
35°	922.1	978.5	1062.4	1176.6
37.5°	857.8	912.9	1004.7	1109.7
40°	794.9	852.6	931.3	1036.2
42.5°	735.8	787.0	857.8	962.8
45°	682.1	718.8	784.4	882.7
47.5°	625.7	658.5	718.8	817.2
50°	573.2	600.7	653.2	745.0
52.5°	522.0	545.7	594.2	667.6
55°	476.1	498.4	533.8	606.0
57.5°	428.9	446.0	480.1	537.8
60°	383.0	398.7	426.3	473.5
62.5°	337.1	350.2	376.4	414.5
65°	296.4	306.9	326.6	359.4
67.5°	257.1	263.6	279.4	305.6
70°	219.0	224.3	237.4	258.4
72.5°	178.4	183.6	198.1	212.5
75°	144.3	145.6	156.1	167.9
77.5°	112.8	111.5	119.4	128.5
80°	77.4	81.3	87.9	91.8
82.5°	52.5	53.8	56.4	59.0
85°	28.9	30.2	30.2	34.1
87.5°	11.8	13.1	13.1	14.4
90°	8.8	6.3	3.7	1.1
92.5°	23.6	24.5	25.5	26.4
95°	45.4	53.2	60.9	68.7
97.5°	65.9	85.1	104.4	123.6
100°	90.5	122.6	154.8	187.0
102.5°	255.3	255.8	256.2	256.7
105°	342.2	335.2	328.1	321.1
107.5°	413.7	407.8	402.0	396.1
110°	482.7	477.8	472.8	467.9



TEST NUMBER: P998984

CATALOG NUMBER: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	548.2	543.9	539.7	535.5
115°	619.3	615.3	611.3	607.3
117.5°	683.8	679.1	674.4	669.7
120°	749.9	746.4	742.9	739.4
122.5°	809.8	806.0	802.3	798.5
125°	867.9	864.8	861.8	858.7
127.5°	923.5	920.2	917.0	913.7
130°	976.7	972.9	969.2	965.4
132.5°	1027.4	1024.3	1021.3	1018.2
135°	1073.9	1070.1	1066.4	1062.6
137.5°	1117.5	1114.7	1111.9	1109.1
140°	1160.1	1158.2	1156.4	1154.5
142.5°	1197.4	1195.8	1194.1	1192.5
145°	1231.9	1232.2	1232.4	1232.6
147.5°	1265.4	1266.1	1266.8	1267.5
150°	1296.4	1298.0	1299.7	1301.3
152.5°	1324.2	1326.1	1327.9	1329.8
155°	1351.0	1353.1	1355.2	1357.3
157.5°	1373.8	1375.7	1377.6	1379.5
160°	1394.2	1395.7	1397.1	1398.5
162.5°	1411.1	1412.6	1414.0	1415.4
165°	1425.9	1427.4	1428.8	1430.2
167.5°	1437.5	1439.0	1440.4	1441.8
170°	1447.0	1448.5	1449.9	1451.3
172.5°	1453.4	1454.8	1456.2	1457.6
175°	1458.0	1459.6	1461.3	1462.9
177.5°	1460.1	1461.7	1463.4	1465.0
180°	1459.7	1459.7	1459.7	1459.7

TEST NUMBER: P998984

CATALOG NUMBER: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-A_4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.99	17.79	17.98	18.79	20.11	14.48	15.29	15.48	16.29	17.60
	3H	17.80	18.52	18.80	19.52	20.86	15.83	16.54	16.83	17.55	18.89
	4H	17.96	18.64	18.98	19.65	21.00	16.28	16.96	17.30	17.97	19.32
	6H	18.01	18.63	19.03	19.65	21.01	16.59	17.21	17.61	18.23	19.59
	8H	17.98	18.58	19.02	19.61	20.97	16.67	17.27	17.70	18.30	19.65
	12H	17.95	18.51	18.98	19.54	20.92	16.71	17.28	17.75	18.30	19.68
4H	2H	17.03	17.71	18.05	18.72	20.06	14.92	15.60	15.94	16.61	17.96
	3H	18.00	18.57	19.03	19.61	20.97	16.38	16.94	17.41	17.98	19.34
	4H	18.28	18.79	19.31	19.82	21.21	16.91	17.43	17.95	18.46	19.84
	6H	18.40	18.85	19.45	19.90	21.28	17.29	17.73	18.33	18.79	20.17
	8H	18.40	18.81	19.45	19.86	21.26	17.40	17.81	18.44	18.86	20.25
	12H	18.36	18.74	19.43	19.80	21.20	17.45	17.82	18.52	18.89	20.29
8H	4H	18.28	18.69	19.33	19.74	21.14	17.05	17.46	18.10	18.51	19.91
	6H	18.46	18.80	19.53	19.89	21.28	17.48	17.82	18.55	18.91	20.30
	8H	18.49	18.79	19.56	19.86	21.27	17.63	17.93	18.71	19.01	20.42
	12H	18.47	18.73	19.55	19.80	21.25	17.72	17.99	18.80	19.05	20.51
12H	4H	18.24	18.61	19.30	19.67	21.07	17.02	17.39	18.09	18.46	19.86
	6H	18.44	18.74	19.51	19.81	21.22	17.48	17.78	18.56	18.86	20.27
	8H	18.47	18.73	19.55	19.80	21.25	17.64	17.90	18.72	18.97	20.42