

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998191

Luminaire Tested: SA2XXDIP-B290D330UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998191
REPORT IS A COMBINATION OF REPORTS P983931 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B290D330UB50-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2460.0 lumens
Efficiency: N/A
Efficacy: 110.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998191

CATALOG NUMBER: SA2XXDIP-B290D330UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P998191

CATALOG NUMBER: SA2XXDIP-B290D330UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48
2	90	83	77	72	83	77	71	67	65	61	58	54	52	49	45	43	41
3	82	73	66	60	76	68	62	57	58	53	49	49	45	42	40	38	36
4	75	65	57	52	69	60	54	48	52	47	43	44	40	37	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27
6	64	52	44	39	59	49	42	37	42	37	33	36	32	28	30	27	24
7	59	47	40	34	55	44	37	32	38	33	29	33	28	25	27	24	22
8	55	43	36	30	51	40	34	29	35	30	26	30	26	23	25	22	20
9	51	40	32	27	48	37	30	26	32	27	23	28	24	21	23	20	18
10	48	36	29	25	45	34	28	23	30	25	21	26	22	19	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8760	8760	8760	8760
5°	8781	9341	8815	7431
10°	8680	10197	8734	6127
15°	8468	10755	8587	5160
20°	8337	10098	8337	4486
25°	8071	8676	8107	4012
30°	7634	6819	7780	3633
35°	7247	4716	7367	3324
40°	6800	3561	6879	3078
45°	6253	2926	6355	2812
50°	5778	2568	5787	2574
55°	5236	2188	5271	2316
60°	4661	1828	4725	2021
65°	4145	1487	4220	1726
70°	3629	1166	3720	1392
75°	3043	846	3166	1009
80°	2379	536	2547	599
85°	1568	270	1681	200

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 9055 cd/sqm

TEST NUMBER: P998191

CATALOG NUMBER: SA2XXDIP-B290D330UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.7	2.1
10°-20°	153.4	6.2
20°-30°	222.7	9.1
30°-40°	234.7	9.5
40°-50°	207.7	8.4
50°-60°	165.9	6.7
60°-70°	112.7	4.6
70°-80°	57.6	2.3
80°-90°	14.8	0.6
90°-100°	69.3	2.8
100°-110°	244.0	9.9
110°-120°	256.3	10.4
120°-130°	210.8	8.6
130°-140°	169.4	6.9
140°-150°	127.9	5.2
150°-160°	89.9	3.7
160°-170°	52.9	2.2
170°-180°	17.2	0.7
0°-30°	428.8	17.4
0°-40°	663.5	27.0
0°-60°	1037.1	42.2
0°-90°	1222.1	49.7
90°-120°	569.6	23.2
90°-150°	1077.7	43.8
90°-180°	1238.0	50.3
0°-180°	2460.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	553	553	553	553	553	
5°	554	618	556	492	554	53
15°	520	760	528	364	520	147
25°	468	633	470	293	468	214
35°	382	345	388	243	382	239
45°	286	208	291	200	286	222
55°	196	146	198	154	196	175
65°	117	90	119	104	117	116
75°	54	44	57	53	54	58
85°	11	12	12	8	11	13
90°	0	11	0	11	0	1
95°	12	39	12	39	12	12
105°	42	385	42	385	42	44
115°	74	507	74	507	74	73
125°	102	411	102	411	102	91
135°	120	341	120	341	120	93
145°	137	272	137	272	137	86
155°	156	229	156	229	156	72
165°	170	201	170	201	170	48
175°	177	181	177	181	177	17
180°	178	178	178	178	178	

TEST NUMBER: P998191

CATALOG NUMBER: SA2XXDIP-B290D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	556.4	557.7	559.8	560.2	564.5	567.9	571.7	571.7	573.0	572.6	569.2
5°	553.8	557.7	563.2	567.9	575.5	578.9	584.0	587.9	591.3	593.8	593.4
7.5°	549.6	556.4	564.5	573.4	583.6	589.6	596.8	603.6	608.3	612.5	615.5
10°	542.4	553.8	564.9	576.8	590.0	598.1	606.6	615.5	622.8	630.8	638.5
12.5°	532.6	549.2	562.8	578.5	594.7	603.6	617.2	624.0	638.1	658.5	664.0
15°	520.2	542.8	555.5	575.5	596.8	604.0	622.8	633.8	662.7	675.5	690.8
17.5°	508.7	533.8	550.9	573.8	594.7	608.7	627.0	649.5	673.8	692.1	709.1
20°	499.4	523.6	544.1	569.6	596.0	613.8	633.0	660.2	686.6	705.3	718.5
22.5°	478.1	509.2	533.0	561.5	593.4	618.1	636.4	666.1	694.6	706.1	717.6
25°	467.5	494.3	521.9	554.3	591.7	621.0	636.8	670.0	695.1	699.3	701.9
27.5°	447.9	478.1	510.5	547.5	591.3	615.9	635.9	666.1	686.1	683.2	675.5
30°	423.7	460.7	496.4	536.4	585.3	612.1	630.8	658.5	668.7	653.4	639.8
32.5°	405.8	440.7	480.2	526.6	578.5	604.0	622.3	644.0	646.1	618.5	595.5
35°	381.6	420.3	464.9	513.9	567.0	590.0	607.0	620.2	610.0	571.3	544.1
37.5°	359.9	398.2	445.8	495.6	551.3	573.8	587.4	589.6	564.5	530.4	490.5
40°	336.0	375.6	425.4	477.7	533.8	553.4	561.9	555.5	519.4	479.8	433.5
42.5°	312.2	351.4	405.0	458.6	511.7	528.3	531.7	514.3	470.0	423.7	370.1
45°	286.3	327.1	380.7	434.7	486.2	495.6	496.0	470.9	418.6	370.1	320.3
47.5°	265.0	302.9	356.0	410.1	453.5	459.8	457.3	428.4	371.4	316.9	273.5
50°	241.6	277.8	330.5	383.7	420.7	422.4	416.0	374.8	319.0	269.3	234.8
52.5°	216.5	253.1	301.6	352.6	385.8	383.3	370.9	326.7	274.4	233.1	206.7
55°	196.5	228.9	274.4	324.1	347.5	340.3	326.7	281.6	240.3	205.5	182.5
57.5°	174.4	202.9	247.6	291.0	304.6	297.8	284.2	242.0	203.8	177.4	162.1
60°	153.6	179.5	218.6	254.8	265.4	258.2	242.5	204.6	177.0	154.8	143.4
62.5°	134.4	157.0	189.7	222.9	227.2	219.9	206.3	175.7	151.9	134.4	125.9
65°	116.6	137.8	164.2	189.3	193.1	185.5	171.4	149.3	129.3	118.3	110.2
67.5°	99.1	116.1	139.5	157.8	159.9	152.7	141.2	123.4	111.0	99.1	93.2
70°	83.8	96.6	114.9	129.7	130.6	123.8	117.8	101.7	92.3	83.8	79.1
72.5°	68.9	77.8	91.9	102.9	103.4	99.1	93.6	83.4	75.3	69.3	64.7
75°	54.4	62.1	70.6	80.4	80.0	76.6	72.3	65.9	59.1	55.3	53.2
77.5°	41.7	46.4	53.2	59.6	59.6	57.9	55.3	50.6	46.4	42.5	40.4
80°	29.8	32.8	38.3	40.4	41.3	40.8	38.7	35.3	33.6	30.6	29.8
82.5°	19.1	21.3	23.8	25.9	27.2	26.4	25.9	24.2	21.7	20.8	20.0
85°	11.1	11.9	13.2	14.5	14.9	14.5	15.3	14.0	12.8	12.8	12.3
87.5°	4.7	5.1	6.0	6.0	6.4	6.4	6.0	6.4	6.4	6.0	5.5
90°	0.3	1.4	2.7	3.4	4.1	4.6	5.1	6.8	9.2	11.3	11.6
92.5°	5.1	7.2	9.9	11.6	14.4	16.2	18.1	27.3	40.3	52.0	52.6
95°	12.0	13.3	16.7	19.8	25.3	29.4	33.5	49.2	79.0	118.6	134.0
97.5°	17.8	19.8	23.6	28.0	34.2	38.8	43.4	63.6	104.9	168.9	218.4
100°	26.3	27.3	30.4	35.9	42.7	47.5	52.3	70.4	112.1	186.0	270.0
102.5°	34.2	34.9	37.9	43.4	50.6	55.4	60.2	76.6	112.5	179.5	271.8
105°	41.7	43.1	45.5	50.6	58.1	62.9	67.7	83.7	114.2	170.6	253.3
107.5°	49.9	50.9	53.3	58.1	65.6	70.4	75.2	90.9	117.9	165.8	236.2
110°	58.1	59.5	61.5	66.0	73.2	78.2	83.1	98.1	122.7	164.4	224.6



TEST NUMBER: P998191

CATALOG NUMBER: SA2XXDIP-B290D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	65.6	67.0	69.4	73.5	80.3	85.4	90.6	104.9	127.8	164.8	217.1
115°	73.5	75.2	77.3	81.4	88.2	92.8	97.4	112.1	133.0	166.1	211.9
117.5°	81.7	83.1	85.1	88.9	95.4	100.2	104.9	118.6	138.4	168.2	209.2
120°	89.2	90.6	92.6	95.7	102.5	107.3	112.1	125.5	143.9	170.2	206.8
122.5°	96.4	97.4	99.5	102.9	109.7	114.6	119.6	131.9	148.7	172.6	205.4
125°	102.5	103.6	105.6	109.7	116.6	121.4	126.1	138.4	153.8	175.0	203.7
127.5°	107.7	109.0	111.8	116.2	122.7	127.6	132.6	144.6	158.6	177.4	202.7
130°	112.1	113.5	116.9	121.7	128.5	133.3	138.1	150.1	163.1	180.1	202.0
132.5°	116.2	117.9	121.7	126.8	134.0	138.8	143.6	154.8	167.5	182.9	201.7
135°	120.3	121.7	125.8	130.9	138.8	143.6	148.4	159.3	171.3	184.9	201.3
137.5°	124.1	125.8	129.9	135.4	143.2	147.6	152.1	163.1	174.3	187.0	201.3
140°	128.5	129.9	134.0	139.5	147.0	151.4	155.9	166.1	176.7	188.3	201.0
142.5°	133.0	134.0	137.8	143.2	150.4	154.5	158.6	168.5	178.8	189.4	201.0
145°	137.4	138.8	142.2	147.3	154.2	158.0	161.7	170.9	180.5	190.1	200.3
147.5°	142.2	143.2	146.6	151.4	157.2	160.6	164.1	173.0	181.5	190.4	199.3
150°	147.0	148.0	150.7	155.2	160.3	163.4	166.5	174.3	182.2	190.1	198.3
152.5°	151.8	152.1	154.8	158.6	163.4	166.2	168.9	175.7	182.5	189.4	196.6
155°	156.2	156.6	158.6	162.4	166.1	168.7	171.3	177.1	182.9	188.7	194.5
157.5°	160.0	160.3	162.0	165.4	168.5	170.8	173.0	178.1	182.9	187.3	192.4
160°	163.7	164.1	165.4	168.2	170.9	172.8	174.7	178.8	182.9	186.3	190.4
162.5°	167.5	167.2	168.5	170.6	173.0	174.4	175.7	179.1	182.5	185.3	188.7
165°	170.2	169.9	170.6	172.6	174.3	175.4	176.4	179.5	181.9	183.9	186.3
167.5°	172.6	172.3	173.0	174.3	175.7	176.4	177.1	179.5	181.5	182.5	184.2
170°	175.0	174.3	174.7	175.7	176.4	176.9	177.4	179.1	180.8	181.5	182.5
172.5°	176.4	176.0	175.7	176.7	177.1	177.4	177.8	178.8	179.8	180.1	180.5
175°	177.4	177.1	176.7	177.4	177.4	177.6	177.8	178.4	179.1	178.8	179.1
177.5°	178.1	177.4	177.1	177.8	177.8	177.8	177.8	178.1	178.8	178.1	177.8
180°	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8

TEST NUMBER: P998191

CATALOG NUMBER: SA2XXDIP-B290D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	575.1	575.5	576.4	580.6	582.8	583.2	581.5	585.3	586.6	585.3	584.5
5°	602.3	604.9	610.0	615.5	615.1	615.5	618.1	620.6	621.5	618.1	619.3
7.5°	626.2	631.3	636.8	645.3	645.3	649.5	651.3	653.4	658.5	655.9	655.1
10°	653.4	660.2	670.4	684.0	684.4	688.7	692.9	699.7	701.9	700.2	701.0
12.5°	687.4	700.6	701.4	716.3	723.1	724.0	730.8	729.5	733.8	733.8	741.0
15°	702.3	722.7	734.2	748.7	752.9	747.8	753.3	759.3	759.7	759.7	759.3
17.5°	729.1	737.2	748.7	756.3	758.0	758.0	758.4	761.0	759.3	755.9	758.4
20°	734.6	738.0	742.3	741.4	742.3	738.0	733.8	729.5	729.9	727.8	734.2
22.5°	724.4	723.6	713.8	707.4	707.4	698.9	690.8	687.0	683.2	684.4	686.6
25°	698.9	685.7	673.8	664.4	662.3	648.7	637.6	634.2	627.9	633.0	633.8
27.5°	658.1	643.2	624.0	615.9	604.9	599.4	591.7	581.5	568.3	576.0	574.7
30°	614.2	592.1	576.4	556.8	539.4	538.1	523.6	506.6	499.8	499.8	503.6
32.5°	565.3	536.0	513.0	485.4	468.3	461.1	443.7	426.7	430.5	417.7	422.4
35°	508.3	469.6	440.7	413.9	401.1	392.6	370.1	360.7	350.5	344.6	355.6
37.5°	453.9	409.2	372.2	342.9	338.2	322.9	307.5	301.6	295.6	298.2	297.8
40°	387.5	348.0	314.8	291.8	283.7	276.5	266.3	259.1	255.2	257.4	257.8
42.5°	327.5	294.4	269.7	253.5	246.7	241.6	236.5	230.6	229.3	229.3	231.0
45°	281.2	253.9	237.4	224.2	220.3	216.5	212.7	210.1	209.3	207.6	208.9
47.5°	244.2	222.5	212.3	202.5	198.2	197.4	194.0	192.7	191.0	190.6	191.0
50°	213.1	199.5	190.1	184.6	181.6	180.4	178.7	176.1	175.3	177.4	176.5
52.5°	191.4	178.7	173.6	168.0	166.3	164.6	162.1	162.5	162.1	161.2	161.2
55°	169.7	161.6	156.5	152.3	151.9	150.2	148.0	147.2	146.8	145.9	147.2
57.5°	152.3	145.9	141.2	137.4	135.7	135.7	133.6	131.9	131.9	131.4	131.9
60°	134.8	128.5	125.5	121.7	120.4	120.0	118.7	117.8	116.6	116.6	116.6
62.5°	118.7	113.6	110.2	106.8	107.2	105.1	103.4	102.5	102.5	102.9	102.9
65°	103.4	100.0	95.7	92.7	91.9	91.5	90.6	90.2	88.9	89.8	89.8
67.5°	89.3	84.6	82.1	80.8	79.5	79.1	78.3	77.4	77.0	76.6	77.4
70°	75.3	71.5	69.3	68.5	67.2	66.8	66.4	65.1	65.5	65.9	66.4
72.5°	62.5	59.1	58.7	56.1	56.1	56.1	54.4	55.3	54.9	54.0	54.9
75°	49.3	47.6	46.8	45.5	45.9	45.5	45.1	43.8	43.8	44.2	44.7
77.5°	39.1	37.4	37.0	35.7	34.9	35.7	34.9	34.5	34.5	34.9	34.9
80°	28.9	28.1	26.8	26.8	26.8	26.4	26.4	26.4	25.9	25.5	25.9
82.5°	19.1	19.1	18.7	18.3	18.7	17.9	18.3	18.3	18.3	18.3	18.3
85°	12.3	11.9	11.9	11.5	11.5	11.5	11.9	11.1	11.1	11.5	11.5
87.5°	5.5	5.5	5.5	6.0	5.5	5.5	5.5	6.0	5.5	5.5	5.5
90°	11.3	10.9	10.3	10.9	11.1	11.3	11.3	11.3	11.3	11.3	11.3
92.5°	44.1	34.5	29.4	25.6	24.2	22.9	22.6	21.2	21.5	20.9	21.5
95°	117.2	89.6	68.7	54.4	50.6	46.8	42.4	39.7	38.6	39.0	38.6
97.5°	220.1	183.2	146.3	111.8	101.6	91.3	77.9	71.1	67.3	65.3	67.3
100°	319.3	312.1	269.7	222.9	202.2	181.5	153.1	138.4	128.5	122.4	128.5
102.5°	356.2	396.5	395.2	364.0	341.8	319.6	288.2	260.5	247.5	238.6	247.5
105°	344.2	415.3	453.9	458.4	452.8	447.1	425.9	404.7	390.0	385.2	390.0
107.5°	318.9	395.2	452.6	486.1	493.0	499.8	499.4	496.3	491.9	484.0	491.9
110°	295.3	367.5	428.7	472.4	486.4	500.4	515.1	521.6	524.7	524.4	524.7

TEST NUMBER: P998191

CATALOG NUMBER: SA2XXDIP-B290D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	278.9	342.2	400.3	447.8	464.4	481.0	502.8	514.8	521.3	523.7	521.3
115°	265.9	322.3	375.0	419.8	437.4	455.0	479.2	495.0	503.9	506.9	503.9
117.5°	257.1	305.9	353.1	394.8	411.6	428.3	453.3	470.0	479.2	481.6	479.2
120°	250.2	294.3	336.7	372.9	388.4	404.0	428.0	444.0	453.9	457.4	453.9
122.5°	244.4	285.1	323.0	356.9	370.5	384.2	405.1	420.8	429.3	432.1	429.3
125°	238.9	276.2	311.4	341.5	354.3	367.1	386.9	399.9	408.5	411.2	408.5
127.5°	233.8	267.3	299.8	328.5	340.4	352.4	369.9	382.2	389.7	391.7	389.7
130°	228.7	258.8	288.2	315.2	326.4	337.7	354.5	366.1	372.9	375.7	372.9
132.5°	224.6	250.6	277.2	301.5	311.9	322.3	338.8	350.4	356.5	358.9	356.5
135°	220.8	243.0	265.6	288.2	297.8	307.3	322.0	333.3	339.4	340.8	339.4
137.5°	218.1	236.9	256.4	274.8	283.4	291.9	305.9	315.8	321.3	323.4	321.3
140°	215.7	231.1	247.5	263.2	270.7	278.2	289.2	298.1	303.2	305.3	303.2
142.5°	213.3	226.3	239.6	252.6	258.6	264.6	274.8	282.7	287.1	287.1	287.1
145°	211.2	221.8	233.1	243.7	248.6	253.6	261.8	267.7	271.1	272.1	271.1
147.5°	209.2	218.4	227.7	236.2	240.0	243.7	250.9	255.7	258.1	258.8	258.1
150°	206.5	214.7	222.2	229.4	232.4	235.5	240.6	244.7	246.8	247.1	246.8
152.5°	204.1	210.9	217.7	223.6	226.2	228.7	232.4	235.9	237.2	237.2	237.2
155°	201.0	207.5	213.0	218.1	220.0	221.8	225.6	228.0	229.4	228.7	229.4
157.5°	198.3	203.4	208.2	212.6	214.2	215.7	218.4	220.5	221.2	221.2	221.2
160°	195.2	199.6	203.4	207.1	208.3	209.5	211.9	213.6	214.0	214.0	214.0
162.5°	192.4	195.9	198.9	202.0	202.8	203.7	206.1	207.1	207.5	207.1	207.5
165°	189.4	192.1	194.5	196.9	197.6	198.3	199.6	201.0	201.0	200.7	201.0
167.5°	186.3	188.3	190.4	192.1	192.8	193.5	194.2	194.8	194.8	194.5	194.8
170°	183.9	185.6	186.6	188.0	188.4	188.7	189.0	190.1	189.7	189.0	189.7
172.5°	181.5	182.5	183.2	184.2	184.4	184.6	184.9	185.3	184.9	184.6	184.9
175°	179.5	180.5	180.8	181.2	181.4	181.5	181.5	181.9	181.5	180.8	181.5
177.5°	178.1	178.8	178.8	179.1	179.1	179.1	179.1	179.1	178.8	178.1	178.8
180°	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8

TEST NUMBER: P998191

CATALOG NUMBER: SA2XXDIP-B290D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	586.6	583.6	581.1	581.5	583.6	581.9	577.7	572.1	570.0	567.5	570.0
5°	621.9	619.3	614.2	614.7	613.4	611.7	604.9	596.4	596.4	589.6	588.7
7.5°	656.8	653.0	649.5	648.7	644.0	640.6	634.7	622.8	618.1	610.0	605.3
10°	695.9	692.9	689.1	684.4	681.9	675.9	666.1	648.7	640.2	629.1	621.0
12.5°	735.5	735.0	726.5	717.2	716.8	707.4	700.6	677.2	665.7	650.8	631.7
15°	760.6	758.4	753.8	749.1	750.4	740.2	724.8	697.2	689.5	671.7	651.3
17.5°	760.1	760.1	758.9	758.0	756.7	753.8	745.3	727.0	714.6	692.1	672.9
20°	735.9	741.4	742.7	742.3	746.5	748.7	748.2	736.8	727.0	707.0	687.4
22.5°	687.4	700.2	705.7	709.1	718.0	722.7	733.8	729.5	727.0	712.1	695.5
25°	642.3	646.6	663.2	664.0	676.3	687.8	698.9	706.1	715.5	710.0	695.9
27.5°	584.0	593.8	605.7	614.7	617.2	640.6	658.9	672.5	693.8	695.5	690.8
30°	518.1	522.8	542.4	554.3	567.9	584.9	611.3	634.7	653.8	671.2	677.2
32.5°	437.7	456.9	468.3	482.8	494.7	524.9	557.2	587.4	609.6	638.9	651.7
35°	364.1	379.0	398.6	404.5	426.2	451.7	493.9	532.6	566.2	596.0	621.9
37.5°	303.3	315.2	336.0	345.4	358.2	390.9	426.2	474.3	514.7	551.3	583.6
40°	261.6	270.5	286.3	289.3	299.9	329.7	358.2	403.3	456.9	506.2	541.5
42.5°	233.1	237.4	248.0	251.8	258.6	278.6	304.1	346.7	396.5	447.5	497.3
45°	212.7	215.7	222.0	225.4	234.0	242.9	263.7	297.8	336.9	388.4	442.0
47.5°	194.4	198.2	200.8	202.9	207.6	217.4	231.0	256.1	293.5	340.7	392.6
50°	179.1	180.4	185.0	185.5	188.4	194.8	207.6	222.9	252.7	291.0	341.2
52.5°	163.8	165.0	168.0	171.0	172.3	177.4	185.9	198.7	220.8	251.0	295.6
55°	148.5	150.2	153.1	155.3	156.5	160.8	165.9	178.2	195.7	216.9	253.5
57.5°	133.1	137.0	137.8	139.1	141.2	145.9	150.6	157.8	171.4	191.0	217.8
60°	118.7	120.0	122.9	124.2	126.3	128.9	134.8	140.4	150.2	165.5	189.7
62.5°	103.8	106.8	108.0	109.3	111.0	114.0	117.8	123.8	132.3	144.6	163.8
65°	91.0	91.5	94.0	95.7	97.4	99.5	103.4	108.9	114.0	125.5	139.5
67.5°	78.7	79.5	80.4	82.1	84.2	86.4	89.8	92.7	99.1	106.8	117.8
70°	66.8	66.8	68.9	70.2	69.8	72.3	74.9	78.3	82.9	90.2	99.1
72.5°	56.1	55.7	57.4	57.9	58.7	60.4	62.1	65.5	68.1	73.6	80.4
75°	44.7	45.5	46.4	46.4	47.6	48.9	50.6	52.3	55.3	58.7	63.8
77.5°	35.3	35.3	36.2	36.6	37.9	37.4	39.1	40.8	43.0	45.9	49.8
80°	25.9	26.8	26.8	26.8	27.2	27.6	29.4	30.6	31.9	34.0	35.7
82.5°	18.3	18.3	19.1	19.1	19.1	20.0	20.0	20.4	21.3	22.5	23.8
85°	11.5	11.5	11.5	11.9	11.5	11.9	12.8	12.3	12.8	13.6	13.6
87.5°	5.5	5.5	5.5	5.5	5.5	6.0	5.5	6.0	6.4	6.4	6.4
90°	11.3	11.3	11.3	11.1	10.9	10.3	10.9	11.3	11.6	11.3	9.2
92.5°	21.2	22.6	22.9	24.2	25.6	29.4	34.5	44.1	52.6	52.0	40.3
95°	39.7	42.4	46.8	50.6	54.4	68.7	89.6	117.2	134.0	118.6	79.0
97.5°	71.1	77.9	91.3	101.6	111.8	146.3	183.2	220.1	218.4	168.9	104.9
100°	138.4	153.1	181.5	202.2	222.9	269.7	312.1	319.3	270.0	186.0	112.1
102.5°	260.5	288.2	319.6	341.8	364.0	395.2	396.5	356.2	271.8	179.5	112.5
105°	404.7	425.9	447.1	452.8	458.4	453.9	415.3	344.2	253.3	170.6	114.2
107.5°	496.3	499.4	499.8	493.0	486.1	452.6	395.2	318.9	236.2	165.8	117.9
110°	521.6	515.1	500.4	486.4	472.4	428.7	367.5	295.3	224.6	164.4	122.7

TEST NUMBER: P998191

CATALOG NUMBER: SA2XXDIP-B290D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	514.8	502.8	481.0	464.4	447.8	400.3	342.2	278.9	217.1	164.8	127.8
115°	495.0	479.2	455.0	437.4	419.8	375.0	322.3	265.9	211.9	166.1	133.0
117.5°	470.0	453.3	428.3	411.6	394.8	353.1	305.9	257.1	209.2	168.2	138.4
120°	444.0	428.0	404.0	388.4	372.9	336.7	294.3	250.2	206.8	170.2	143.9
122.5°	420.8	405.1	384.2	370.5	356.9	323.0	285.1	244.4	205.4	172.6	148.7
125°	399.9	386.9	367.1	354.3	341.5	311.4	276.2	238.9	203.7	175.0	153.8
127.5°	382.2	369.9	352.4	340.4	328.5	299.8	267.3	233.8	202.7	177.4	158.6
130°	366.1	354.5	337.7	326.4	315.2	288.2	258.8	228.7	202.0	180.1	163.1
132.5°	350.4	338.8	322.3	311.9	301.5	277.2	250.6	224.6	201.7	182.9	167.5
135°	333.3	322.0	307.3	297.8	288.2	265.6	243.0	220.8	201.3	184.9	171.3
137.5°	315.8	305.9	291.9	283.4	274.8	256.4	236.9	218.1	201.3	187.0	174.3
140°	298.1	289.2	278.2	270.7	263.2	247.5	231.1	215.7	201.0	188.3	176.7
142.5°	282.7	274.8	264.6	258.6	252.6	239.6	226.3	213.3	201.0	189.4	178.8
145°	267.7	261.8	253.6	248.6	243.7	233.1	221.8	211.2	200.3	190.1	180.5
147.5°	255.7	250.9	243.7	240.0	236.2	227.7	218.4	209.2	199.3	190.4	181.5
150°	244.7	240.6	235.5	232.4	229.4	222.2	214.7	206.5	198.3	190.1	182.2
152.5°	235.9	232.4	228.7	226.2	223.6	217.7	210.9	204.1	196.6	189.4	182.5
155°	228.0	225.6	221.8	220.0	218.1	213.0	207.5	201.0	194.5	188.7	182.9
157.5°	220.5	218.4	215.7	214.2	212.6	208.2	203.4	198.3	192.4	187.3	182.9
160°	213.6	211.9	209.5	208.3	207.1	203.4	199.6	195.2	190.4	186.3	182.9
162.5°	207.1	206.1	203.7	202.8	202.0	198.9	195.9	192.4	188.7	185.3	182.5
165°	201.0	199.6	198.3	197.6	196.9	194.5	192.1	189.4	186.3	183.9	181.9
167.5°	194.8	194.2	193.5	192.8	192.1	190.4	188.3	186.3	184.2	182.5	181.5
170°	190.1	189.0	188.7	188.4	188.0	186.6	185.6	183.9	182.5	181.5	180.8
172.5°	185.3	184.9	184.6	184.4	184.2	183.2	182.5	181.5	180.5	180.1	179.8
175°	181.9	181.5	181.5	181.4	181.2	180.8	180.5	179.5	179.1	178.8	179.1
177.5°	179.1	179.1	179.1	179.1	179.1	178.8	178.8	178.1	177.8	178.1	178.8
180°	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8

TEST NUMBER: P998191

CATALOG NUMBER: SA2XXDIP-B290D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	567.9	565.7	564.5	565.3	562.8	556.4	556.4	558.5	556.0	553.4	549.6
5°	583.6	579.4	576.8	576.4	570.4	560.2	558.1	556.0	550.4	544.5	538.1
7.5°	598.9	591.3	587.0	584.0	575.5	562.3	556.8	552.1	543.2	534.3	526.2
10°	611.7	600.6	595.5	590.8	579.8	563.2	554.3	545.8	534.3	522.8	512.6
12.5°	621.9	609.1	602.8	596.0	582.3	560.6	549.6	536.0	524.5	509.2	499.0
15°	638.9	612.5	606.6	600.2	586.2	556.4	542.8	527.5	511.7	491.3	480.2
17.5°	652.5	617.2	616.8	603.2	584.9	554.7	533.8	513.9	496.8	476.4	459.0
20°	660.6	624.5	617.6	603.6	580.6	543.2	521.5	499.4	481.1	456.4	439.0
22.5°	667.4	634.7	616.8	599.8	571.7	539.4	507.5	486.6	461.5	434.7	418.1
25°	670.0	636.8	618.1	598.5	565.3	528.3	492.2	469.6	441.5	417.3	394.7
27.5°	670.4	636.4	613.4	593.0	556.4	513.9	476.8	453.0	422.0	393.9	371.4
30°	666.1	631.7	610.8	588.7	547.9	500.7	458.1	431.8	398.6	370.5	347.1
32.5°	653.4	622.3	605.3	581.1	536.8	482.4	440.3	410.9	376.0	348.4	325.8
35°	632.1	610.8	592.1	569.6	522.4	465.4	422.4	387.9	352.6	326.3	305.0
37.5°	605.7	594.3	576.8	554.7	505.8	450.0	402.4	364.1	328.8	303.3	282.4
40°	570.0	573.0	556.0	536.0	486.2	429.2	376.5	339.9	306.7	282.9	262.5
42.5°	531.3	543.6	533.8	514.7	464.5	406.2	357.3	316.9	284.6	259.9	242.9
45°	489.6	510.9	504.9	490.9	442.0	382.0	330.1	291.0	262.5	238.6	223.7
47.5°	444.1	474.3	474.3	464.1	416.9	357.7	306.7	266.7	238.6	221.6	207.2
50°	397.7	431.8	437.3	430.5	388.8	330.1	278.2	242.0	217.8	201.2	190.6
52.5°	349.2	388.8	399.0	395.6	359.0	303.7	254.8	219.5	197.4	182.9	173.6
55°	302.9	348.8	359.9	361.1	327.1	274.8	228.9	197.8	176.5	166.7	158.7
57.5°	259.1	303.3	315.6	317.8	294.8	248.4	204.6	177.4	158.2	150.2	143.8
60°	221.6	258.6	274.8	279.5	259.5	217.8	182.1	155.7	141.2	133.6	127.6
62.5°	191.0	220.8	237.8	239.1	230.1	191.0	158.7	136.5	124.2	117.4	114.4
65°	161.2	188.0	198.2	203.3	196.1	165.5	137.0	118.7	108.9	102.9	100.0
67.5°	137.4	154.4	162.9	169.7	162.5	139.5	116.6	101.7	94.4	88.5	86.8
70°	112.7	126.8	133.1	139.9	133.6	116.1	99.5	85.9	79.5	74.9	72.7
72.5°	90.2	101.2	107.2	111.4	107.6	93.2	79.5	70.2	65.5	62.1	60.8
75°	71.5	79.1	82.5	85.5	83.8	72.7	64.2	56.6	52.3	49.3	48.5
77.5°	54.4	60.0	63.8	64.7	62.5	55.3	48.1	43.4	40.0	38.3	37.4
80°	38.7	42.1	44.2	45.5	43.4	40.4	35.3	31.9	28.9	26.8	26.4
82.5°	25.9	27.6	29.4	28.9	28.1	25.5	22.5	20.8	19.6	17.9	17.9
85°	14.9	15.3	16.2	16.6	16.2	14.5	12.8	11.9	11.1	9.8	9.8
87.5°	6.4	6.8	6.8	7.2	6.4	6.4	5.5	4.7	4.7	4.3	3.8
90°	6.8	5.1	4.6	4.1	3.4	2.7	1.4	0.3	1.4	2.7	3.4
92.5°	27.3	18.1	16.2	14.4	11.6	9.9	7.2	5.1	7.2	9.9	11.6
95°	49.2	33.5	29.4	25.3	19.8	16.7	13.3	12.0	13.3	16.7	19.8
97.5°	63.6	43.4	38.8	34.2	28.0	23.6	19.8	17.8	19.8	23.6	28.0
100°	70.4	52.3	47.5	42.7	35.9	30.4	27.3	26.3	27.3	30.4	35.9
102.5°	76.6	60.2	55.4	50.6	43.4	37.9	34.9	34.2	34.9	37.9	43.4
105°	83.7	67.7	62.9	58.1	50.6	45.5	43.1	41.7	43.1	45.5	50.6
107.5°	90.9	75.2	70.4	65.6	58.1	53.3	50.9	49.9	50.9	53.3	58.1
110°	98.1	83.1	78.2	73.2	66.0	61.5	59.5	58.1	59.5	61.5	66.0

TEST NUMBER: P998191

CATALOG NUMBER: SA2XXDIP-B290D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	104.9	90.6	85.4	80.3	73.5	69.4	67.0	65.6	67.0	69.4	73.5
115°	112.1	97.4	92.8	88.2	81.4	77.3	75.2	73.5	75.2	77.3	81.4
117.5°	118.6	104.9	100.2	95.4	88.9	85.1	83.1	81.7	83.1	85.1	88.9
120°	125.5	112.1	107.3	102.5	95.7	92.6	90.6	89.2	90.6	92.6	95.7
122.5°	131.9	119.6	114.6	109.7	102.9	99.5	97.4	96.4	97.4	99.5	102.9
125°	138.4	126.1	121.4	116.6	109.7	105.6	103.6	102.5	103.6	105.6	109.7
127.5°	144.6	132.6	127.6	122.7	116.2	111.8	109.0	107.7	109.0	111.8	116.2
130°	150.1	138.1	133.3	128.5	121.7	116.9	113.5	112.1	113.5	116.9	121.7
132.5°	154.8	143.6	138.8	134.0	126.8	121.7	117.9	116.2	117.9	121.7	126.8
135°	159.3	148.4	143.6	138.8	130.9	125.8	121.7	120.3	121.7	125.8	130.9
137.5°	163.1	152.1	147.6	143.2	135.4	129.9	125.8	124.1	125.8	129.9	135.4
140°	166.1	155.9	151.4	147.0	139.5	134.0	129.9	128.5	129.9	134.0	139.5
142.5°	168.5	158.6	154.5	150.4	143.2	137.8	134.0	133.0	134.0	137.8	143.2
145°	170.9	161.7	158.0	154.2	147.3	142.2	138.8	137.4	138.8	142.2	147.3
147.5°	173.0	164.1	160.6	157.2	151.4	146.6	143.2	142.2	143.2	146.6	151.4
150°	174.3	166.5	163.4	160.3	155.2	150.7	148.0	147.0	148.0	150.7	155.2
152.5°	175.7	168.9	166.2	163.4	158.6	154.8	152.1	151.8	152.1	154.8	158.6
155°	177.1	171.3	168.7	166.1	162.4	158.6	156.6	156.2	156.6	158.6	162.4
157.5°	178.1	173.0	170.8	168.5	165.4	162.0	160.3	160.0	160.3	162.0	165.4
160°	178.8	174.7	172.8	170.9	168.2	165.4	164.1	163.7	164.1	165.4	168.2
162.5°	179.1	175.7	174.4	173.0	170.6	168.5	167.2	167.5	167.2	168.5	170.6
165°	179.5	176.4	175.4	174.3	172.6	170.6	169.9	170.2	169.9	170.6	172.6
167.5°	179.5	177.1	176.4	175.7	174.3	173.0	172.3	172.6	172.3	173.0	174.3
170°	179.1	177.4	176.9	176.4	175.7	174.7	174.3	175.0	174.3	174.7	175.7
172.5°	178.8	177.8	177.4	177.1	176.7	175.7	176.0	176.4	176.0	175.7	176.7
175°	178.4	177.8	177.6	177.4	177.4	176.7	177.1	177.4	177.1	176.7	177.4
177.5°	178.1	177.8	177.8	177.8	177.8	177.1	177.4	178.1	177.4	177.1	177.8
180°	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8

TEST NUMBER: P998191

CATALOG NUMBER: SA2XXDIP-B290D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	547.5	549.6	549.2	544.9	540.2	536.4	529.2	530.0	527.5	527.9	530.4
5°	533.8	533.8	532.1	526.2	518.5	514.3	506.2	504.1	499.0	498.5	498.1
7.5°	519.4	517.3	515.1	506.6	497.3	490.5	479.4	476.8	471.7	468.3	466.6
10°	502.4	499.4	495.1	485.4	473.9	465.4	453.9	450.5	440.7	436.4	433.9
12.5°	483.7	482.0	475.1	467.1	448.3	439.0	422.4	425.8	416.0	407.5	406.2
15°	464.9	458.6	454.7	441.5	419.0	414.7	401.6	394.7	385.8	379.0	379.0
17.5°	446.6	436.9	428.4	414.3	397.7	385.8	376.0	372.6	361.6	354.8	353.5
20°	422.4	411.3	409.2	389.2	377.7	364.5	355.2	346.7	338.6	335.6	333.5
22.5°	399.4	386.7	383.3	366.2	354.8	341.6	332.2	326.3	320.3	318.2	314.4
25°	374.8	367.1	362.0	343.7	330.9	318.6	312.2	308.0	302.4	302.0	299.5
27.5°	350.9	343.7	338.6	321.2	311.8	300.3	295.2	290.5	287.6	286.3	285.0
30°	330.5	322.4	316.5	303.7	292.2	282.9	278.6	275.6	273.9	271.8	271.4
32.5°	308.0	303.3	295.2	285.4	276.5	267.6	265.0	262.9	260.3	259.5	259.1
35°	288.8	282.4	277.3	266.3	262.5	254.8	251.8	250.1	246.7	245.9	245.0
37.5°	270.1	264.2	258.6	251.8	244.6	240.3	238.6	236.1	234.4	234.8	234.0
40°	251.4	246.7	242.5	235.2	231.0	228.9	225.4	222.9	222.0	222.5	222.0
42.5°	233.1	228.9	226.3	220.8	216.5	214.4	212.3	209.7	211.0	211.0	212.3
45°	216.5	212.7	211.0	206.7	204.2	200.8	198.7	198.2	199.9	199.5	199.5
47.5°	199.5	198.2	196.1	192.3	188.9	186.7	186.3	186.3	188.0	188.9	188.4
50°	186.3	183.8	181.2	178.2	175.7	174.8	173.6	174.4	176.1	176.1	177.0
52.5°	169.7	168.0	167.2	164.6	162.9	162.9	162.9	163.3	164.6	165.9	165.5
55°	155.3	154.0	153.1	151.9	149.7	150.2	149.7	150.6	151.9	153.1	154.0
57.5°	139.9	139.5	138.7	136.5	136.5	136.1	137.4	137.8	139.9	140.8	142.1
60°	126.3	125.1	125.1	123.4	123.4	123.4	124.6	125.9	127.6	128.0	128.9
62.5°	111.9	111.9	111.4	110.2	110.2	111.4	111.9	113.6	114.4	114.4	115.7
65°	98.3	97.8	97.4	97.8	98.3	98.3	99.5	100.4	101.2	101.7	102.1
67.5°	84.6	84.2	85.1	84.6	85.5	87.2	86.8	88.1	89.3	89.3	89.8
70°	71.9	72.7	72.3	73.2	72.7	73.6	74.9	75.3	75.3	75.7	77.0
72.5°	60.0	60.0	60.0	59.6	60.0	60.8	61.7	62.1	63.0	63.4	64.7
75°	48.5	48.5	47.6	48.5	48.5	49.3	50.2	50.2	50.2	51.0	52.3
77.5°	36.6	37.0	36.6	37.4	37.4	37.9	38.7	38.3	39.1	39.6	40.0
80°	26.8	26.4	26.4	26.4	26.8	26.8	27.6	28.1	28.1	29.4	28.5
82.5°	17.0	17.4	17.0	17.4	17.4	17.9	17.4	17.9	18.3	19.1	18.7
85°	9.8	9.4	9.4	9.8	9.4	9.4	9.8	9.4	9.8	9.4	9.8
87.5°	3.8	3.4	3.4	3.4	3.4	3.0	3.0	2.6	2.6	2.6	2.1
90°	4.1	4.6	5.1	6.8	9.2	11.3	11.6	11.3	10.9	10.3	10.9
92.5°	14.4	16.2	18.1	27.3	40.3	52.0	52.6	44.1	34.5	29.4	25.6
95°	25.3	29.4	33.5	49.2	79.0	118.6	134.0	117.2	89.6	68.7	54.4
97.5°	34.2	38.8	43.4	63.6	104.9	168.9	218.4	220.1	183.2	146.3	111.8
100°	42.7	47.5	52.3	70.4	112.1	186.0	270.0	319.3	312.1	269.7	222.9
102.5°	50.6	55.4	60.2	76.6	112.5	179.5	271.8	356.2	396.5	395.2	364.0
105°	58.1	62.9	67.7	83.7	114.2	170.6	253.3	344.2	415.3	453.9	458.4
107.5°	65.6	70.4	75.2	90.9	117.9	165.8	236.2	318.9	395.2	452.6	486.1
110°	73.2	78.2	83.1	98.1	122.7	164.4	224.6	295.3	367.5	428.7	472.4

TEST NUMBER: P998191

CATALOG NUMBER: SA2XXDIP-B290D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	80.3	85.4	90.6	104.9	127.8	164.8	217.1	278.9	342.2	400.3	447.8
115°	88.2	92.8	97.4	112.1	133.0	166.1	211.9	265.9	322.3	375.0	419.8
117.5°	95.4	100.2	104.9	118.6	138.4	168.2	209.2	257.1	305.9	353.1	394.8
120°	102.5	107.3	112.1	125.5	143.9	170.2	206.8	250.2	294.3	336.7	372.9
122.5°	109.7	114.6	119.6	131.9	148.7	172.6	205.4	244.4	285.1	323.0	356.9
125°	116.6	121.4	126.1	138.4	153.8	175.0	203.7	238.9	276.2	311.4	341.5
127.5°	122.7	127.6	132.6	144.6	158.6	177.4	202.7	233.8	267.3	299.8	328.5
130°	128.5	133.3	138.1	150.1	163.1	180.1	202.0	228.7	258.8	288.2	315.2
132.5°	134.0	138.8	143.6	154.8	167.5	182.9	201.7	224.6	250.6	277.2	301.5
135°	138.8	143.6	148.4	159.3	171.3	184.9	201.3	220.8	243.0	265.6	288.2
137.5°	143.2	147.6	152.1	163.1	174.3	187.0	201.3	218.1	236.9	256.4	274.8
140°	147.0	151.4	155.9	166.1	176.7	188.3	201.0	215.7	231.1	247.5	263.2
142.5°	150.4	154.5	158.6	168.5	178.8	189.4	201.0	213.3	226.3	239.6	252.6
145°	154.2	158.0	161.7	170.9	180.5	190.1	200.3	211.2	221.8	233.1	243.7
147.5°	157.2	160.6	164.1	173.0	181.5	190.4	199.3	209.2	218.4	227.7	236.2
150°	160.3	163.4	166.5	174.3	182.2	190.1	198.3	206.5	214.7	222.2	229.4
152.5°	163.4	166.2	168.9	175.7	182.5	189.4	196.6	204.1	210.9	217.7	223.6
155°	166.1	168.7	171.3	177.1	182.9	188.7	194.5	201.0	207.5	213.0	218.1
157.5°	168.5	170.8	173.0	178.1	182.9	187.3	192.4	198.3	203.4	208.2	212.6
160°	170.9	172.8	174.7	178.8	182.9	186.3	190.4	195.2	199.6	203.4	207.1
162.5°	173.0	174.4	175.7	179.1	182.5	185.3	188.7	192.4	195.9	198.9	202.0
165°	174.3	175.4	176.4	179.5	181.9	183.9	186.3	189.4	192.1	194.5	196.9
167.5°	175.7	176.4	177.1	179.5	181.5	182.5	184.2	186.3	188.3	190.4	192.1
170°	176.4	176.9	177.4	179.1	180.8	181.5	182.5	183.9	185.6	186.6	188.0
172.5°	177.1	177.4	177.8	178.8	179.8	180.1	180.5	181.5	182.5	183.2	184.2
175°	177.4	177.6	177.8	178.4	179.1	178.8	179.1	179.5	180.5	180.8	181.2
177.5°	177.8	177.8	177.8	178.1	178.8	178.1	177.8	178.1	178.8	178.8	179.1
180°	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8

TEST NUMBER: P998191

CATALOG NUMBER: SA2XXDIP-B290D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	527.5	528.7	525.8	524.9	525.8	522.8	523.6	524.5	524.5	525.8	526.6
5°	496.8	495.1	492.2	491.3	490.5	491.7	490.9	492.2	492.6	495.6	496.0
7.5°	466.6	464.1	461.5	459.0	458.1	456.0	458.1	458.1	461.1	460.3	462.4
10°	430.9	430.5	427.1	425.8	424.1	420.7	425.4	424.1	426.2	430.1	430.9
12.5°	404.5	399.9	402.0	396.0	398.2	394.7	395.2	395.2	398.6	399.0	398.2
15°	379.4	375.6	370.1	367.5	366.2	364.5	370.1	370.5	368.0	373.9	371.8
17.5°	353.9	353.9	348.8	347.5	344.1	345.8	345.0	345.4	344.6	348.8	350.9
20°	331.8	329.7	328.0	328.4	324.1	323.3	322.4	323.3	326.3	329.2	330.1
22.5°	313.9	312.7	308.4	309.2	305.8	307.1	306.3	308.4	308.8	308.8	311.8
25°	296.9	295.2	295.6	293.9	292.7	292.7	291.4	292.7	294.4	295.2	295.6
27.5°	284.2	282.9	280.7	279.5	280.3	278.2	279.9	281.2	281.2	280.3	281.2
30°	268.8	269.7	269.7	265.4	267.1	266.3	267.6	268.4	268.4	268.8	268.0
32.5°	258.6	256.1	255.7	255.2	255.2	253.5	253.5	254.8	255.2	255.7	256.9
35°	245.0	245.0	242.9	244.2	242.5	242.9	242.5	242.9	243.7	242.5	243.7
37.5°	232.7	233.1	232.3	233.1	233.5	232.7	231.8	233.5	232.7	232.7	231.8
40°	222.0	221.6	222.0	222.0	222.0	222.5	221.6	221.6	221.6	220.8	219.9
42.5°	213.1	210.6	211.4	211.8	210.6	210.6	211.0	210.6	211.8	209.3	209.3
45°	200.4	199.5	199.9	199.9	200.8	199.5	200.4	200.8	199.5	199.1	198.2
47.5°	188.9	189.7	188.9	189.7	189.7	190.6	188.9	189.3	189.7	188.0	186.7
50°	177.4	177.4	178.7	178.2	178.7	177.8	177.8	177.4	177.8	177.0	175.7
52.5°	166.7	165.5	167.6	167.2	166.7	166.3	165.9	166.3	165.5	164.6	164.6
55°	153.6	153.6	154.8	155.3	155.3	154.4	153.6	154.0	153.6	153.1	152.7
57.5°	142.9	141.2	142.1	142.5	142.5	141.2	142.1	141.2	141.2	141.7	140.4
60°	129.3	129.3	128.5	129.7	129.7	128.9	128.9	129.3	128.5	128.0	127.6
62.5°	114.9	115.3	116.6	117.0	117.4	116.6	115.7	116.1	116.1	114.9	115.3
65°	102.5	103.4	105.1	104.6	103.8	104.2	103.4	103.8	102.5	102.9	101.7
67.5°	90.6	90.2	90.6	90.6	91.5	91.0	90.2	90.2	89.8	91.0	89.8
70°	77.8	77.8	77.8	77.8	78.3	78.7	77.8	77.0	77.4	76.6	76.1
72.5°	64.7	65.1	64.7	65.5	64.2	65.1	65.1	64.7	64.2	64.2	64.2
75°	52.3	53.2	51.9	52.3	51.9	52.7	52.3	52.3	51.5	51.0	51.5
77.5°	40.0	40.4	39.6	40.0	39.6	40.0	40.0	39.6	39.6	39.6	39.6
80°	28.5	28.9	28.5	28.1	27.6	28.5	27.6	28.1	28.5	28.1	28.9
82.5°	18.3	18.3	17.9	18.3	17.4	17.4	17.9	17.9	17.4	18.3	17.4
85°	8.9	8.9	9.8	8.9	8.5	8.5	8.5	8.9	8.5	9.4	8.9
87.5°	2.1	1.7	2.1	2.1	1.7	1.7	2.1	1.7	2.1	2.6	1.7
90°	11.1	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.1
92.5°	24.2	22.9	22.6	21.2	21.5	20.9	21.5	21.2	22.6	22.9	24.2
95°	50.6	46.8	42.4	39.7	38.6	39.0	38.6	39.7	42.4	46.8	50.6
97.5°	101.6	91.3	77.9	71.1	67.3	65.3	67.3	71.1	77.9	91.3	101.6
100°	202.2	181.5	153.1	138.4	128.5	122.4	128.5	138.4	153.1	181.5	202.2
102.5°	341.8	319.6	288.2	260.5	247.5	238.6	247.5	260.5	288.2	319.6	341.8
105°	452.8	447.1	425.9	404.7	390.0	385.2	390.0	404.7	425.9	447.1	452.8
107.5°	493.0	499.8	499.4	496.3	491.9	484.0	491.9	496.3	499.4	499.8	493.0
110°	486.4	500.4	515.1	521.6	524.7	524.4	524.7	521.6	515.1	500.4	486.4

TEST NUMBER: P998191

CATALOG NUMBER: SA2XXDIP-B290D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	464.4	481.0	502.8	514.8	521.3	523.7	521.3	514.8	502.8	481.0	464.4
115°	437.4	455.0	479.2	495.0	503.9	506.9	503.9	495.0	479.2	455.0	437.4
117.5°	411.6	428.3	453.3	470.0	479.2	481.6	479.2	470.0	453.3	428.3	411.6
120°	388.4	404.0	428.0	444.0	453.9	457.4	453.9	444.0	428.0	404.0	388.4
122.5°	370.5	384.2	405.1	420.8	429.3	432.1	429.3	420.8	405.1	384.2	370.5
125°	354.3	367.1	386.9	399.9	408.5	411.2	408.5	399.9	386.9	367.1	354.3
127.5°	340.4	352.4	369.9	382.2	389.7	391.7	389.7	382.2	369.9	352.4	340.4
130°	326.4	337.7	354.5	366.1	372.9	375.7	372.9	366.1	354.5	337.7	326.4
132.5°	311.9	322.3	338.8	350.4	356.5	358.9	356.5	350.4	338.8	322.3	311.9
135°	297.8	307.3	322.0	333.3	339.4	340.8	339.4	333.3	322.0	307.3	297.8
137.5°	283.4	291.9	305.9	315.8	321.3	323.4	321.3	315.8	305.9	291.9	283.4
140°	270.7	278.2	289.2	298.1	303.2	305.3	303.2	298.1	289.2	278.2	270.7
142.5°	258.6	264.6	274.8	282.7	287.1	287.1	287.1	282.7	274.8	264.6	258.6
145°	248.6	253.6	261.8	267.7	271.1	272.1	271.1	267.7	261.8	253.6	248.6
147.5°	240.0	243.7	250.9	255.7	258.1	258.8	258.1	255.7	250.9	243.7	240.0
150°	232.4	235.5	240.6	244.7	246.8	247.1	246.8	244.7	240.6	235.5	232.4
152.5°	226.2	228.7	232.4	235.9	237.2	237.2	237.2	235.9	232.4	228.7	226.2
155°	220.0	221.8	225.6	228.0	229.4	228.7	229.4	228.0	225.6	221.8	220.0
157.5°	214.2	215.7	218.4	220.5	221.2	221.2	221.2	220.5	218.4	215.7	214.2
160°	208.3	209.5	211.9	213.6	214.0	214.0	214.0	213.6	211.9	209.5	208.3
162.5°	202.8	203.7	206.1	207.1	207.5	207.1	207.5	207.1	206.1	203.7	202.8
165°	197.6	198.3	199.6	201.0	201.0	200.7	201.0	201.0	199.6	198.3	197.6
167.5°	192.8	193.5	194.2	194.8	194.8	194.5	194.8	194.8	194.2	193.5	192.8
170°	188.4	188.7	189.0	190.1	189.7	189.0	189.7	190.1	189.0	188.7	188.4
172.5°	184.4	184.6	184.9	185.3	184.9	184.6	184.9	185.3	184.9	184.6	184.4
175°	181.4	181.5	181.5	181.9	181.5	180.8	181.5	181.9	181.5	181.5	181.4
177.5°	179.1	179.1	179.1	179.1	178.8	178.1	178.8	179.1	179.1	179.1	179.1
180°	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8

TEST NUMBER: P998191

CATALOG NUMBER: SA2XXDIP-B290D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4	553.4
2.5°	525.3	528.7	527.5	522.8	528.3	528.3	532.1	532.1	536.8	538.5	541.1
5°	495.6	498.1	500.2	498.1	501.9	507.9	511.3	514.3	520.7	523.2	527.0
7.5°	463.7	468.3	470.5	470.5	476.8	483.7	490.5	494.7	503.6	507.0	510.9
10°	432.6	438.1	442.4	442.0	452.6	456.9	465.4	475.1	484.1	489.2	494.7
12.5°	399.9	402.8	408.8	417.3	419.8	427.5	437.3	449.6	465.8	470.5	478.5
15°	372.6	380.7	385.4	389.2	395.2	402.4	413.0	425.0	441.1	451.3	459.8
17.5°	349.7	360.3	363.3	362.4	370.1	381.1	393.5	402.4	416.9	429.2	437.3
20°	330.9	335.2	340.3	342.4	348.4	360.3	372.2	382.4	394.3	404.1	413.5
22.5°	312.2	315.6	319.9	323.7	328.4	335.2	346.7	359.4	370.9	380.3	390.9
25°	296.9	299.0	302.9	305.8	310.9	315.6	323.7	337.7	351.4	356.9	366.2
27.5°	282.0	283.7	286.3	289.7	292.2	296.9	304.1	315.6	329.7	335.2	348.0
30°	268.8	270.1	272.7	274.4	275.6	281.2	286.7	295.6	306.3	313.9	323.3
32.5°	256.5	257.8	260.3	260.8	262.5	265.4	270.5	278.6	288.0	294.4	302.4
35°	242.9	243.7	246.3	247.1	248.4	251.0	254.8	260.8	269.3	273.9	281.2
37.5°	232.3	231.8	233.5	234.8	236.5	237.8	239.1	245.0	251.4	255.7	261.2
40°	220.8	219.9	220.3	222.0	222.9	224.6	224.6	230.6	234.8	238.2	242.5
42.5°	209.3	208.9	208.0	208.9	209.7	210.1	210.6	214.8	219.1	222.0	226.7
45°	197.8	197.4	196.5	196.9	196.9	197.8	199.1	200.8	203.8	206.3	208.9
47.5°	187.2	186.3	185.0	184.6	185.5	185.5	185.5	187.2	190.1	191.0	193.5
50°	176.1	174.8	173.1	172.3	172.3	171.9	172.7	173.1	175.7	176.5	178.7
52.5°	164.2	163.3	161.6	159.9	160.4	159.5	159.9	160.4	161.2	162.5	163.8
55°	152.3	150.6	149.3	148.9	147.6	147.6	146.3	148.0	147.6	148.0	149.7
57.5°	140.8	139.1	137.0	136.1	134.8	134.4	133.6	133.1	133.6	134.8	136.1
60°	127.2	126.3	125.1	123.8	122.9	121.7	120.8	120.8	120.4	120.4	120.8
62.5°	114.0	113.6	111.9	111.4	110.6	109.7	108.5	107.6	107.6	108.5	108.9
65°	101.2	100.8	99.5	99.1	97.0	96.1	95.7	95.3	94.4	94.4	94.4
67.5°	89.3	88.1	88.1	85.9	84.2	83.4	82.5	82.1	82.1	82.1	82.5
70°	76.1	76.1	74.9	73.6	71.9	72.3	71.0	69.8	69.8	68.9	69.3
72.5°	63.4	63.0	61.7	61.3	60.0	58.7	57.9	58.7	57.4	57.0	57.4
75°	51.0	50.6	49.8	48.9	49.3	48.1	46.8	46.4	46.4	45.5	45.5
77.5°	39.1	40.0	38.3	37.9	37.0	36.2	35.7	35.3	35.3	35.3	36.2
80°	27.2	27.6	27.6	26.8	27.2	25.9	25.9	25.9	24.7	25.1	25.5
82.5°	17.4	17.4	17.0	17.4	17.0	17.0	16.6	16.6	16.2	16.2	16.6
85°	9.8	9.4	8.9	9.8	9.4	9.4	8.9	8.9	8.9	8.9	8.9
87.5°	2.1	2.6	2.6	2.6	2.6	3.0	3.0	3.0	3.4	3.4	3.4
90°	10.9	10.3	10.9	11.3	11.6	11.3	9.2	6.8	5.1	4.6	4.1
92.5°	25.6	29.4	34.5	44.1	52.6	52.0	40.3	27.3	18.1	16.2	14.4
95°	54.4	68.7	89.6	117.2	134.0	118.6	79.0	49.2	33.5	29.4	25.3
97.5°	111.8	146.3	183.2	220.1	218.4	168.9	104.9	63.6	43.4	38.8	34.2
100°	222.9	269.7	312.1	319.3	270.0	186.0	112.1	70.4	52.3	47.5	42.7
102.5°	364.0	395.2	396.5	356.2	271.8	179.5	112.5	76.6	60.2	55.4	50.6
105°	458.4	453.9	415.3	344.2	253.3	170.6	114.2	83.7	67.7	62.9	58.1
107.5°	486.1	452.6	395.2	318.9	236.2	165.8	117.9	90.9	75.2	70.4	65.6
110°	472.4	428.7	367.5	295.3	224.6	164.4	122.7	98.1	83.1	78.2	73.2

TEST NUMBER: P998191

CATALOG NUMBER: SA2XXDIP-B290D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	447.8	400.3	342.2	278.9	217.1	164.8	127.8	104.9	90.6	85.4	80.3
115°	419.8	375.0	322.3	265.9	211.9	166.1	133.0	112.1	97.4	92.8	88.2
117.5°	394.8	353.1	305.9	257.1	209.2	168.2	138.4	118.6	104.9	100.2	95.4
120°	372.9	336.7	294.3	250.2	206.8	170.2	143.9	125.5	112.1	107.3	102.5
122.5°	356.9	323.0	285.1	244.4	205.4	172.6	148.7	131.9	119.6	114.6	109.7
125°	341.5	311.4	276.2	238.9	203.7	175.0	153.8	138.4	126.1	121.4	116.6
127.5°	328.5	299.8	267.3	233.8	202.7	177.4	158.6	144.6	132.6	127.6	122.7
130°	315.2	288.2	258.8	228.7	202.0	180.1	163.1	150.1	138.1	133.3	128.5
132.5°	301.5	277.2	250.6	224.6	201.7	182.9	167.5	154.8	143.6	138.8	134.0
135°	288.2	265.6	243.0	220.8	201.3	184.9	171.3	159.3	148.4	143.6	138.8
137.5°	274.8	256.4	236.9	218.1	201.3	187.0	174.3	163.1	152.1	147.6	143.2
140°	263.2	247.5	231.1	215.7	201.0	188.3	176.7	166.1	155.9	151.4	147.0
142.5°	252.6	239.6	226.3	213.3	201.0	189.4	178.8	168.5	158.6	154.5	150.4
145°	243.7	233.1	221.8	211.2	200.3	190.1	180.5	170.9	161.7	158.0	154.2
147.5°	236.2	227.7	218.4	209.2	199.3	190.4	181.5	173.0	164.1	160.6	157.2
150°	229.4	222.2	214.7	206.5	198.3	190.1	182.2	174.3	166.5	163.4	160.3
152.5°	223.6	217.7	210.9	204.1	196.6	189.4	182.5	175.7	168.9	166.2	163.4
155°	218.1	213.0	207.5	201.0	194.5	188.7	182.9	177.1	171.3	168.7	166.1
157.5°	212.6	208.2	203.4	198.3	192.4	187.3	182.9	178.1	173.0	170.8	168.5
160°	207.1	203.4	199.6	195.2	190.4	186.3	182.9	178.8	174.7	172.8	170.9
162.5°	202.0	198.9	195.9	192.4	188.7	185.3	182.5	179.1	175.7	174.4	173.0
165°	196.9	194.5	192.1	189.4	186.3	183.9	181.9	179.5	176.4	175.4	174.3
167.5°	192.1	190.4	188.3	186.3	184.2	182.5	181.5	179.5	177.1	176.4	175.7
170°	188.0	186.6	185.6	183.9	182.5	181.5	180.8	179.1	177.4	176.9	176.4
172.5°	184.2	183.2	182.5	181.5	180.5	180.1	179.8	178.8	177.8	177.4	177.1
175°	181.2	180.8	180.5	179.5	179.1	178.8	179.1	178.4	177.8	177.6	177.4
177.5°	179.1	178.8	178.8	178.1	177.8	178.1	178.8	178.1	177.8	177.8	177.8
180°	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8

TEST NUMBER: P998191

CATALOG NUMBER: SA2XXDIP-B290D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	553.4	553.4	553.4	553.4
2.5°	543.2	543.2	549.6	556.4
5°	531.3	534.3	544.5	553.8
7.5°	519.8	524.9	537.7	549.6
10°	505.8	512.6	528.3	542.4
12.5°	492.2	498.5	516.8	532.6
15°	473.0	481.1	500.7	520.2
17.5°	453.9	462.0	485.8	508.7
20°	431.3	442.0	468.8	499.4
22.5°	410.5	423.7	453.5	478.1
25°	387.5	407.9	435.6	467.5
27.5°	367.1	387.5	415.6	447.9
30°	344.1	365.0	393.9	423.7
32.5°	322.0	341.2	369.2	405.8
35°	299.0	317.3	344.6	381.6
37.5°	278.2	296.1	325.8	359.9
40°	257.8	276.5	302.0	336.0
42.5°	238.6	255.2	278.2	312.2
45°	221.2	233.1	254.4	286.3
47.5°	202.9	213.5	233.1	265.0
50°	185.9	194.8	211.8	241.6
52.5°	169.3	177.0	192.7	216.5
55°	154.4	161.6	173.1	196.5
57.5°	139.1	144.6	155.7	174.4
60°	124.2	129.3	138.2	153.6
62.5°	109.3	113.6	122.1	134.4
65°	96.1	99.5	105.9	116.6
67.5°	83.4	85.5	90.6	99.1
70°	71.0	72.7	77.0	83.8
72.5°	57.9	59.6	64.2	68.9
75°	46.8	47.2	50.6	54.4
77.5°	36.6	36.2	38.7	41.7
80°	25.1	26.4	28.5	29.8
82.5°	17.0	17.4	18.3	19.1
85°	9.4	9.8	9.8	11.1
87.5°	3.8	4.3	4.3	4.7
90°	3.4	2.7	1.4	0.3
92.5°	11.6	9.9	7.2	5.1
95°	19.8	16.7	13.3	12.0
97.5°	28.0	23.6	19.8	17.8
100°	35.9	30.4	27.3	26.3
102.5°	43.4	37.9	34.9	34.2
105°	50.6	45.5	43.1	41.7
107.5°	58.1	53.3	50.9	49.9
110°	66.0	61.5	59.5	58.1



TEST NUMBER: P998191

CATALOG NUMBER: SA2XXDIP-B290D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	73.5	69.4	67.0	65.6
115°	81.4	77.3	75.2	73.5
117.5°	88.9	85.1	83.1	81.7
120°	95.7	92.6	90.6	89.2
122.5°	102.9	99.5	97.4	96.4
125°	109.7	105.6	103.6	102.5
127.5°	116.2	111.8	109.0	107.7
130°	121.7	116.9	113.5	112.1
132.5°	126.8	121.7	117.9	116.2
135°	130.9	125.8	121.7	120.3
137.5°	135.4	129.9	125.8	124.1
140°	139.5	134.0	129.9	128.5
142.5°	143.2	137.8	134.0	133.0
145°	147.3	142.2	138.8	137.4
147.5°	151.4	146.6	143.2	142.2
150°	155.2	150.7	148.0	147.0
152.5°	158.6	154.8	152.1	151.8
155°	162.4	158.6	156.6	156.2
157.5°	165.4	162.0	160.3	160.0
160°	168.2	165.4	164.1	163.7
162.5°	170.6	168.5	167.2	167.5
165°	172.6	170.6	169.9	170.2
167.5°	174.3	173.0	172.3	172.6
170°	175.7	174.7	174.3	175.0
172.5°	176.7	175.7	176.0	176.4
175°	177.4	176.7	177.1	177.4
177.5°	177.8	177.1	177.4	178.1
180°	177.8	177.8	177.8	177.8

TEST NUMBER: P998191

CATALOG NUMBER: SA2XXDIP-B290D330UB50-4F0-XX-W2A-A4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.35	14.18	14.32	15.16	16.43	10.85	11.67	11.81	12.65	13.93
	3H	14.16	14.90	15.14	15.89	17.19	12.19	12.93	13.17	13.91	15.21
	4H	14.33	15.03	15.32	16.02	17.33	12.65	13.35	13.64	14.34	15.65
	6H	14.37	15.02	15.37	16.01	17.33	12.95	13.60	13.96	14.59	15.91
	8H	14.35	14.96	15.36	15.97	17.29	13.04	13.65	14.05	14.66	15.98
	12H	14.31	14.89	15.33	15.90	17.24	13.08	13.66	14.09	14.66	16.01
4H	2H	13.39	14.09	14.39	15.08	16.39	11.29	11.99	12.29	12.98	14.29
	3H	14.37	14.95	15.37	15.97	17.29	12.75	13.33	13.75	14.35	15.67
	4H	14.64	15.17	15.66	16.19	17.53	13.28	13.81	14.29	14.82	16.17
	6H	14.77	15.23	15.80	16.26	17.61	13.66	14.11	14.68	15.15	16.49
	8H	14.77	15.19	15.80	16.22	17.58	13.77	14.19	14.79	15.22	16.58
	12H	14.73	15.12	15.78	16.16	17.52	13.82	14.21	14.87	15.25	16.61
8H	4H	14.65	15.08	15.68	16.10	17.46	13.42	13.84	14.44	14.87	16.23
	6H	14.83	15.18	15.88	16.25	17.60	13.85	14.20	14.90	15.27	16.63
	8H	14.86	15.17	15.91	16.22	17.59	14.00	14.31	15.06	15.37	16.74
	12H	14.84	15.11	15.90	16.16	17.58	14.09	14.36	15.15	15.41	16.83
12H	4H	14.61	14.99	15.65	16.03	17.39	13.39	13.77	14.43	14.82	16.18
	6H	14.81	15.11	15.86	16.17	17.54	13.85	14.16	14.91	15.22	16.59
	8H	14.84	15.11	15.90	16.16	17.57	14.01	14.28	15.07	15.33	16.75