

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998995

Luminaire Tested: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998995
REPORT IS A COMBINATION OF REPORTS P984741 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-F_5000K
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7497.0 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998995

CATALOG NUMBER: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P998995

CATALOG NUMBER: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43
2	88	81	75	69	80	74	69	64	62	58	55	50	48	45	40	38	37
3	80	71	64	58	73	65	59	54	54	50	46	45	41	38	35	33	31
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	28	26	23
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16
9	49	37	30	25	45	35	28	23	29	24	21	25	21	18	20	17	15
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20880	20880	20880
5°	20914	19903	19762
10°	20745	18996	18619
15°	20441	18082	17417
20°	20030	17088	16278
25°	19621	16049	15141
30°	19106	15074	13949
35°	18619	14045	12776
40°	18021	13030	11670
45°	17424	12022	10584
50°	16773	10997	9456
55°	16086	9900	8388
60°	15318	8714	7279
65°	14472	7509	6113
70°	13404	6188	4936
75°	11921	4770	3811
80°	10123	3241	2453
85°	7345	1509	1044

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17424 cd/sqm

TEST NUMBER: P998995

CATALOG NUMBER: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.1	1.7
10°-20°	349.3	4.7
20°-30°	513.3	6.8
30°-40°	596.2	8.0
40°-50°	595.5	7.9
50°-60°	519.2	6.9
60°-70°	383.8	5.1
70°-80°	217.2	2.9
80°-90°	59.8	0.8
90°-100°	46.6	0.6
100°-110°	173.5	2.3
110°-120°	460.2	6.1
120°-130°	763.3	10.2
130°-140°	810.8	10.8
140°-150°	753.6	10.1
150°-160°	605.8	8.1
160°-170°	390.4	5.2
170°-180°	134.4	1.8
0°-30°	986.8	13.2
0°-40°	1583.0	21.1
0°-60°	2697.7	36.0
0°-90°	3358.5	44.8
90°-120°	680.3	9.1
90°-150°	3007.9	40.1
90°-180°	4139.0	55.2
0°-180°	7497.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1319	1319	1319	1319	1319	
5°	1319	1314	1300	1310	1308	125
15°	1256	1248	1232	1237	1230	354
25°	1136	1126	1105	1107	1105	523
35°	980	968	948	940	934	612
45°	798	789	770	756	751	616
55°	604	596	581	566	559	540
65°	407	400	387	375	369	403
75°	213	210	204	197	199	227
85°	52	51	50	46	44	58
90°	1	12	20	26	28	7
95°	66	33	40	45	44	79
105°	310	341	62	74	78	332
115°	587	605	630	157	84	578
125°	830	844	863	870	873	741
135°	1028	1044	1053	1063	1061	794
145°	1192	1191	1208	1216	1210	746
155°	1313	1303	1316	1322	1314	605
165°	1383	1377	1380	1387	1380	391
175°	1415	1408	1410	1417	1407	135
180°	1412	1412	1412	1412	1412	

TEST NUMBER: P998995

CATALOG NUMBER: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1319.1	1319.1	1319.1	1319.1	1319.1
2.5°	1326.7	1320.4	1306.4	1319.1	1316.6
5°	1319.1	1314.0	1300.1	1310.2	1307.7
7.5°	1310.2	1302.6	1288.7	1298.8	1296.3
10°	1296.3	1287.4	1272.2	1282.3	1278.5
12.5°	1277.2	1269.6	1254.4	1260.8	1258.2
15°	1255.7	1248.1	1231.6	1236.7	1230.3
17.5°	1229.0	1221.4	1204.9	1211.3	1204.9
20°	1199.9	1192.3	1174.5	1178.3	1173.2
22.5°	1170.7	1159.3	1142.8	1142.8	1140.3
25°	1136.5	1126.3	1104.7	1107.3	1104.7
27.5°	1098.4	1089.5	1073.0	1069.2	1062.9
30°	1060.4	1050.2	1031.2	1027.4	1022.3
32.5°	1019.8	1012.2	991.9	984.3	979.2
35°	980.4	967.8	947.5	939.9	933.5
37.5°	936.1	924.6	904.3	895.5	889.1
40°	890.4	880.2	860.0	848.5	843.5
42.5°	846.0	835.9	815.6	802.9	795.3
45°	797.8	788.9	769.9	755.9	750.9
47.5°	750.9	742.0	721.7	707.7	700.1
50°	701.4	695.1	677.3	659.5	653.2
52.5°	653.2	644.3	627.8	613.9	605.0
55°	603.7	596.1	580.9	565.7	559.3
57.5°	554.3	547.9	531.4	516.2	511.2
60°	504.8	499.7	482.0	468.0	464.2
62.5°	456.6	447.7	435.0	422.4	417.3
65°	407.1	399.5	386.9	375.4	369.1
67.5°	356.4	350.1	338.7	329.8	324.7
70°	309.5	304.4	293.0	284.1	279.0
72.5°	261.3	256.2	249.9	241.0	237.2
75°	213.1	210.5	204.2	196.6	199.1
77.5°	170.0	164.9	162.4	158.5	154.7
80°	126.8	125.6	123.0	119.2	116.7
82.5°	86.2	86.2	85.0	79.9	79.9
85°	52.0	50.7	49.5	45.7	44.4
87.5°	22.8	20.3	17.8	14.0	12.7
90°	1.0	12.3	20.4	25.5	27.6
92.5°	25.5	21.5	24.5	26.6	27.6
95°	66.4	32.7	39.8	44.9	43.9
97.5°	119.5	35.8	52.1	55.2	56.2
100°	180.8	40.9	58.2	66.4	68.4
102.5°	248.2	246.2	60.3	71.5	74.6
105°	310.5	341.2	62.3	73.5	77.6
107.5°	383.1	408.6	64.4	75.6	79.7
110°	452.5	474.0	178.8	76.6	80.7

TEST NUMBER: P998995

CATALOG NUMBER: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	517.9	536.3	518.9	78.7	81.7
115°	587.3	604.7	630.2	157.3	83.8
117.5°	647.6	668.0	685.4	539.3	271.7
120°	715.0	730.3	748.7	761.0	623.1
122.5°	772.2	788.6	809.0	815.1	816.2
125°	830.5	843.7	863.1	870.3	873.4
127.5°	883.6	897.9	913.2	923.4	924.4
130°	933.6	950.0	961.2	972.4	971.4
132.5°	984.7	998.0	1009.2	1018.4	1017.4
135°	1027.6	1043.9	1053.1	1063.3	1061.3
137.5°	1072.5	1084.8	1095.0	1105.2	1102.2
140°	1116.5	1124.6	1135.9	1145.1	1140.0
142.5°	1153.2	1160.4	1173.7	1181.8	1176.7
145°	1192.1	1191.0	1208.4	1215.5	1210.4
147.5°	1225.8	1222.7	1240.1	1245.2	1241.1
150°	1258.4	1251.3	1267.6	1273.8	1268.7
152.5°	1286.0	1277.9	1293.2	1299.3	1292.2
155°	1312.6	1303.4	1315.7	1321.8	1313.6
157.5°	1334.0	1325.9	1335.1	1342.2	1334.0
160°	1352.4	1346.3	1352.4	1358.6	1351.4
162.5°	1368.8	1362.6	1367.7	1374.9	1365.7
165°	1383.1	1376.9	1380.0	1387.2	1380.0
167.5°	1394.3	1388.2	1391.2	1398.4	1389.2
170°	1403.5	1397.4	1399.4	1406.6	1397.4
172.5°	1409.6	1403.5	1405.5	1412.7	1403.5
175°	1414.7	1407.6	1409.6	1416.8	1406.6
177.5°	1416.8	1409.6	1410.6	1417.8	1408.6
180°	1411.7	1411.7	1411.7	1411.7	1411.7

TEST NUMBER: P998995

CATALOG NUMBER: SA2XXDIP-B865D1080UB2750-4F0-XX-W2A-F_5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.29	16.11	16.29	17.12	18.46	16.07	16.89	17.08	17.90	19.25
	3H	16.63	17.36	17.64	18.38	19.74	17.70	18.43	18.71	19.45	20.81
	4H	17.03	17.72	18.05	18.75	20.12	18.29	18.98	19.31	20.00	21.38
	6H	17.25	17.89	18.28	18.91	20.30	18.69	19.33	19.72	20.35	21.74
	8H	17.28	17.88	18.32	18.93	20.31	18.80	19.40	19.83	20.45	21.83
	12H	17.27	17.84	18.31	18.88	20.29	18.84	19.42	19.88	20.46	21.86
4H	2H	15.76	16.45	16.79	17.47	18.85	16.40	17.09	17.43	18.12	19.49
	3H	17.27	17.85	18.31	18.90	20.29	18.18	18.75	19.21	19.81	21.19
	4H	17.77	18.30	18.82	19.35	20.75	18.86	19.39	19.90	20.43	21.84
	6H	18.07	18.53	19.13	19.60	21.00	19.35	19.80	20.40	20.87	22.27
	8H	18.13	18.56	19.19	19.61	21.03	19.49	19.92	20.55	20.98	22.39
	12H	18.13	18.51	19.20	19.59	21.01	19.55	19.94	20.62	21.01	22.43
8H	4H	17.95	18.37	19.00	19.43	20.85	18.94	19.36	19.99	20.42	21.84
	6H	18.33	18.68	19.41	19.78	21.20	19.50	19.86	20.58	20.96	22.37
	8H	18.43	18.74	19.52	19.82	21.26	19.69	20.00	20.78	21.09	22.52
	12H	18.46	18.73	19.55	19.81	21.29	19.79	20.06	20.88	21.14	22.62
12H	4H	17.93	18.31	19.00	19.38	20.81	18.90	19.28	19.97	20.36	21.78
	6H	18.34	18.65	19.43	19.74	21.17	19.50	19.81	20.58	20.89	22.32
	8H	18.46	18.73	19.55	19.81	21.28	19.69	19.96	20.78	21.04	22.52