

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998240

Luminaire Tested: SA2XXDIP-B290D530UB40-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998240
REPORT IS A COMBINATION OF REPORTS P983980 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B290D530UB40-4F0-XX-W2A-A
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3370.0 lumens
Efficiency: N/A
Efficacy: 118.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998240

CATALOG NUMBER: SA2XXDIP-B290D530UB40-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P998240

CATALOG NUMBER: SA2XXDIP-B290D530UB40-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45
1	95	91	88	84	86	83	80	77	67	65	63	53	52	50	40	39	38
2	87	80	74	69	79	73	68	64	59	56	53	47	45	43	36	34	33
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	21	19
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9054	9054	9054	9054
5°	9075	9654	9110	7680
10°	8971	10539	9027	6332
15°	8753	11116	8875	5334
20°	8617	10438	8617	4636
25°	8342	8967	8380	4146
30°	7890	7049	8041	3755
35°	7490	4874	7616	3435
40°	7029	3680	7110	3181
45°	6462	3025	6567	2906
50°	5971	2654	5983	2661
55°	5412	2262	5446	2394
60°	4816	1890	4882	2089
65°	4284	1537	4362	1784
70°	3750	1205	3846	1438
75°	3149	875	3273	1043
80°	2459	555	2635	620
85°	1610	280	1737	207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 9360 cd/sqm

TEST NUMBER: P998240

CATALOG NUMBER: SA2XXDIP-B290D530UB40-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.5	1.6
10°-20°	158.6	4.7
20°-30°	230.1	6.8
30°-40°	242.6	7.2
40°-50°	214.7	6.4
50°-60°	171.4	5.1
60°-70°	116.4	3.5
70°-80°	59.6	1.8
80°-90°	15.3	0.5
90°-100°	23.7	0.7
100°-110°	88.3	2.6
110°-120°	234.3	7.0
120°-130°	388.6	11.5
130°-140°	412.7	12.2
140°-150°	383.6	11.4
150°-160°	308.4	9.2
160°-170°	198.7	5.9
170°-180°	68.4	2.0
0°-30°	443.2	13.2
0°-40°	685.8	20.4
0°-60°	1071.9	31.8
0°-90°	1263.3	37.5
90°-120°	346.3	10.3
90°-150°	1531.2	45.4
90°-180°	2107.0	62.5
0°-180°	3370.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	572	572	572	572	572	
5°	572	639	575	508	572	54
15°	538	785	545	377	538	152
25°	483	654	485	302	483	221
35°	394	356	401	251	394	247
45°	296	215	301	206	296	230
55°	203	151	204	160	203	181
65°	120	93	123	108	120	120
75°	56	46	58	54	56	60
85°	11	12	12	9	11	13
90°	0	14	0	14	0	3
95°	34	22	34	22	34	40
105°	158	40	158	40	158	169
115°	299	43	299	43	299	294
125°	423	445	423	445	423	377
135°	523	540	523	540	523	404
145°	607	616	607	616	607	380
155°	668	669	668	669	668	308
165°	704	702	704	702	704	199
175°	720	716	720	716	720	69
180°	719	719	719	719	719	

TEST NUMBER: P998240

CATALOG NUMBER: SA2XXDIP-B290D530UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	575.1	576.4	578.6	579.0	583.4	586.9	590.9	590.9	592.2	591.8	588.3
5°	572.4	576.4	582.1	586.9	594.9	598.4	603.7	607.6	611.1	613.8	613.3
7.5°	568.0	575.1	583.4	592.7	603.2	609.4	616.8	623.9	628.7	633.1	636.2
10°	560.6	572.4	583.9	596.2	609.8	618.2	627.0	636.2	643.7	652.0	659.9
12.5°	550.5	567.6	581.7	597.9	614.6	623.9	637.9	645.0	659.5	680.6	686.3
15°	537.7	561.0	574.2	594.9	616.8	624.3	643.7	655.1	685.0	698.2	714.0
17.5°	525.8	551.8	569.4	593.1	614.6	629.2	648.1	671.4	696.4	715.3	732.9
20°	516.2	541.2	562.3	588.7	616.0	634.4	654.2	682.4	709.6	729.0	742.6
22.5°	494.2	526.3	550.9	580.4	613.3	638.8	657.7	688.5	718.0	729.8	741.7
25°	483.2	510.9	539.5	572.9	611.6	641.9	658.2	692.5	718.4	722.8	725.4
27.5°	463.0	494.2	527.6	565.8	611.1	636.6	657.3	688.5	709.2	706.1	698.2
30°	437.9	476.2	513.1	554.4	605.0	632.7	652.0	680.6	691.1	675.3	661.2
32.5°	419.4	455.5	496.4	544.3	597.9	624.3	643.2	665.6	667.8	639.3	615.5
35°	394.4	434.4	480.5	531.1	586.1	609.8	627.4	641.0	630.5	590.5	562.3
37.5°	372.0	411.5	460.8	512.2	569.8	593.1	607.2	609.4	583.4	548.3	506.9
40°	347.3	388.2	439.7	493.7	551.8	572.0	580.8	574.2	536.8	495.9	448.0
42.5°	322.7	363.2	418.6	474.0	528.9	546.1	549.6	531.5	485.8	437.9	382.5
45°	295.9	338.1	393.5	449.3	502.5	512.2	512.6	486.7	432.6	382.5	331.1
47.5°	273.9	313.0	368.0	423.8	468.7	475.3	472.6	442.7	383.8	327.5	282.7
50°	249.7	287.1	341.6	396.6	434.8	436.6	430.0	387.3	329.7	278.3	242.7
52.5°	223.8	261.6	311.7	364.5	398.8	396.1	383.4	337.7	283.6	240.9	213.7
55°	203.1	236.5	283.6	335.0	359.2	351.7	337.7	291.1	248.4	212.4	188.6
57.5°	180.3	209.7	255.9	300.7	314.8	307.8	293.7	250.2	210.6	183.3	167.5
60°	158.7	185.5	226.0	263.4	274.3	266.9	250.6	211.5	182.9	160.0	148.2
62.5°	138.9	162.2	196.1	230.4	234.8	227.3	213.2	181.6	157.0	138.9	130.1
65°	120.5	142.4	169.7	195.6	199.6	191.7	177.2	154.3	133.7	122.2	113.9
67.5°	102.4	120.0	144.2	163.1	165.3	157.8	146.0	127.5	114.8	102.4	96.3
70°	86.6	99.8	118.7	134.1	135.0	127.9	121.8	105.1	95.4	86.6	81.8
72.5°	71.2	80.5	95.0	106.4	106.8	102.4	96.7	86.2	77.8	71.7	66.8
75°	56.3	64.2	73.0	83.1	82.7	79.1	74.7	68.1	61.1	57.2	55.0
77.5°	43.1	47.9	55.0	61.6	61.6	59.8	57.2	52.3	47.9	44.0	41.8
80°	30.8	33.9	39.6	41.8	42.6	42.2	40.0	36.5	34.7	31.7	30.8
82.5°	19.8	22.0	24.6	26.8	28.1	27.3	26.8	25.1	22.4	21.5	20.7
85°	11.4	12.3	13.6	14.9	15.4	14.9	15.8	14.5	13.2	13.2	12.8
87.5°	4.8	5.3	6.2	6.2	6.6	6.6	6.2	6.6	6.6	6.2	5.7
90°	0.5	1.8	3.0	4.3	5.6	6.2	6.7	7.6	8.5	9.5	10.4
92.5°	13.0	12.5	12.1	11.6	11.1	10.9	11.1	11.4	11.8	12.1	12.5
95°	33.8	30.0	26.2	22.3	18.5	16.6	17.0	17.8	18.7	19.5	20.3
97.5°	60.8	51.3	41.9	32.4	22.9	18.2	19.1	21.0	22.8	24.7	26.5
100°	92.0	76.2	60.4	44.5	28.7	20.8	21.8	23.7	25.7	27.6	29.6
102.5°	126.4	126.2	125.9	125.7	125.4	125.3	114.8	93.8	72.7	51.7	30.7
105°	158.1	161.6	165.0	168.5	172.0	173.7	157.9	126.4	94.8	63.3	31.7
107.5°	195.0	197.9	200.8	203.7	206.6	208.0	188.5	149.6	110.7	71.7	32.8
110°	230.4	232.8	235.2	237.7	240.1	241.3	224.6	191.2	157.8	124.4	91.0

TEST NUMBER: P998240

CATALOG NUMBER: SA2XXDIP-B290D530UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	263.6	265.7	267.8	269.9	272.0	273.0	272.0	270.1	268.1	266.2	264.2
115°	299.0	301.0	302.9	304.9	306.8	307.8	309.2	312.1	315.0	317.9	320.8
117.5°	329.7	332.0	334.3	336.6	338.9	340.1	341.1	343.0	345.0	346.9	348.9
120°	364.0	365.7	367.5	369.2	370.9	371.8	372.8	374.9	377.0	379.0	381.1
122.5°	393.1	394.9	396.8	398.6	400.5	401.4	402.6	404.9	407.2	409.5	411.8
125°	422.7	424.2	425.7	427.2	428.7	429.5	430.6	432.8	435.0	437.2	439.4
127.5°	449.8	451.4	453.0	454.7	456.3	457.1	458.0	459.7	461.4	463.2	464.9
130°	475.3	477.1	479.0	480.8	482.7	483.6	484.2	485.5	486.8	488.0	489.3
132.5°	501.3	502.8	504.3	505.8	507.3	508.0	508.6	509.9	511.2	512.4	513.7
135°	523.1	524.9	526.8	528.6	530.5	531.4	531.9	533.0	534.0	535.1	536.1
137.5°	546.0	547.4	548.8	550.1	551.5	552.2	552.8	553.9	555.1	556.2	557.4
140°	568.3	569.2	570.2	571.1	572.0	572.5	573.1	574.4	575.7	576.9	578.2
142.5°	587.1	587.9	588.7	589.5	590.3	590.7	591.5	593.0	594.5	596.0	597.5
145°	606.8	606.7	606.6	606.5	606.4	606.3	607.3	609.2	611.2	613.1	615.1
147.5°	624.0	623.6	623.3	622.9	622.6	622.4	623.4	625.4	627.3	629.3	631.3
150°	640.6	639.8	639.0	638.2	637.4	637.0	637.9	639.8	641.6	643.5	645.3
152.5°	654.7	653.8	652.8	651.9	651.0	650.5	651.4	653.1	654.8	656.6	658.3
155°	668.2	667.2	666.1	665.1	664.0	663.5	664.2	665.6	666.9	668.3	669.7
157.5°	679.1	678.2	677.2	676.3	675.4	674.9	675.4	676.5	677.5	678.6	679.6
160°	688.5	687.8	687.1	686.4	685.7	685.3	685.7	686.4	687.1	687.8	688.5
162.5°	696.8	696.1	695.4	694.7	694.0	693.7	694.0	694.6	695.1	695.7	696.3
165°	704.1	703.4	702.7	702.0	701.3	700.9	701.1	701.4	701.8	702.1	702.5
167.5°	709.8	709.1	708.4	707.7	707.0	706.7	706.9	707.2	707.5	707.9	708.2
170°	714.5	713.8	713.1	712.4	711.7	711.3	711.4	711.7	711.9	712.2	712.4
172.5°	717.6	716.9	716.2	715.5	714.8	714.5	714.6	714.8	715.1	715.3	715.5
175°	720.2	719.4	718.6	717.7	716.9	716.5	716.6	716.9	717.1	717.4	717.6
177.5°	721.2	720.4	719.6	718.8	718.0	717.6	717.7	717.8	717.9	718.0	718.1
180°	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6

TEST NUMBER: P998240

CATALOG NUMBER: SA2XXDIP-B290D530UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	594.4	594.9	595.7	600.1	602.3	602.8	601.0	605.0	606.3	605.0	604.1
5°	622.6	625.2	630.5	636.2	635.7	636.2	638.8	641.5	642.3	638.8	640.1
7.5°	647.2	652.5	658.2	667.0	667.0	671.4	673.1	675.3	680.6	678.0	677.1
10°	675.3	682.4	692.9	707.0	707.4	711.8	716.2	723.2	725.4	723.7	724.6
12.5°	710.5	724.1	725.0	740.4	747.4	748.3	755.3	754.0	758.4	758.4	765.9
15°	725.9	747.0	758.9	773.8	778.2	772.9	778.6	784.8	785.2	785.2	784.8
17.5°	753.6	761.9	773.8	781.7	783.5	783.5	783.9	786.6	784.8	781.3	783.9
20°	759.3	762.8	767.2	766.3	767.2	762.8	758.4	754.0	754.5	752.3	758.9
22.5°	748.7	747.9	737.7	731.2	731.2	722.4	714.0	710.1	706.1	707.4	709.6
25°	722.4	708.7	696.4	686.7	684.6	670.5	659.0	655.5	648.9	654.2	655.1
27.5°	680.2	664.8	645.0	636.6	625.2	619.5	611.6	601.0	587.4	595.3	594.0
30°	634.9	612.0	595.7	575.5	557.5	556.2	541.2	523.6	516.6	516.6	520.6
32.5°	584.3	554.0	530.2	501.7	484.1	476.6	458.6	441.0	444.9	431.7	436.6
35°	525.4	485.4	455.5	427.8	414.6	405.8	382.5	372.8	362.3	356.1	367.6
37.5°	469.1	423.0	384.7	354.4	349.5	333.7	317.9	311.7	305.6	308.2	307.8
40°	400.5	359.6	325.3	301.6	293.3	285.8	275.2	267.8	263.8	266.0	266.4
42.5°	338.5	304.2	278.7	262.0	255.0	249.7	244.5	238.3	237.0	237.0	238.7
45°	290.6	262.5	245.3	231.7	227.7	223.8	219.8	217.2	216.3	214.6	215.9
47.5°	252.4	229.9	219.4	209.3	204.9	204.0	200.5	199.2	197.4	197.0	197.4
50°	220.3	206.2	196.5	190.8	187.7	186.4	184.7	182.0	181.1	183.3	182.5
52.5°	197.8	184.7	179.4	173.7	171.9	170.1	167.5	167.9	167.5	166.6	166.6
55°	175.4	167.1	161.8	157.4	157.0	155.2	153.0	152.1	151.7	150.8	152.1
57.5°	157.4	150.8	146.0	142.0	140.3	140.3	138.1	136.3	136.3	135.9	136.3
60°	139.4	132.8	129.7	125.7	124.4	124.0	122.7	121.8	120.5	120.5	120.5
62.5°	122.7	117.4	113.9	110.4	110.8	108.6	106.8	106.0	106.0	106.4	106.4
65°	106.8	103.3	98.9	95.8	95.0	94.5	93.6	93.2	91.9	92.8	92.8
67.5°	92.3	87.5	84.9	83.5	82.2	81.8	80.9	80.0	79.6	79.1	80.0
70°	77.8	73.9	71.7	70.8	69.5	69.0	68.6	67.3	67.7	68.1	68.6
72.5°	64.6	61.1	60.7	58.0	58.0	58.0	56.3	57.2	56.7	55.8	56.7
75°	51.0	49.2	48.4	47.0	47.5	47.0	46.6	45.3	45.3	45.7	46.2
77.5°	40.4	38.7	38.3	36.9	36.1	36.9	36.1	35.6	35.6	36.1	36.1
80°	29.9	29.0	27.7	27.7	27.7	27.3	27.3	27.3	26.8	26.4	26.8
82.5°	19.8	19.8	19.3	18.9	19.3	18.5	18.9	18.9	18.9	18.9	18.9
85°	12.8	12.3	12.3	11.9	11.9	11.9	12.3	11.4	11.4	11.9	11.9
87.5°	5.7	5.7	5.7	6.2	5.7	5.7	5.7	6.2	5.7	5.7	5.7
90°	11.0	11.6	12.1	12.7	13.0	13.1	13.3	13.6	13.8	14.0	13.8
92.5°	12.7	12.9	13.2	13.4	13.5	13.6	13.7	13.8	13.9	14.0	13.9
95°	20.9	21.5	22.0	22.6	22.9	22.8	22.7	22.6	22.5	22.4	22.5
97.5°	26.9	27.2	27.6	27.9	28.1	28.2	28.3	28.4	28.5	28.6	28.5
100°	30.5	31.5	32.4	33.3	33.8	33.9	34.1	34.4	34.6	34.8	34.6
102.5°	32.0	33.2	34.5	35.8	36.4	36.6	36.9	37.3	37.6	38.0	37.6
105°	33.0	34.2	35.5	36.8	37.4	37.6	38.1	38.6	39.0	39.5	39.0
107.5°	34.1	35.3	36.6	37.9	38.5	38.7	39.2	39.7	40.1	40.6	40.1
110°	79.4	67.9	56.3	44.8	39.0	39.2	39.7	40.2	40.6	41.1	40.6

TEST NUMBER: P998240

CATALOG NUMBER: SA2XXDIP-B290D530UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	214.4	164.6	114.7	64.9	40.0	40.2	40.5	40.9	41.2	41.6	41.2
115°	267.3	213.8	160.3	106.8	80.1	75.9	67.6	59.3	50.9	42.6	50.9
117.5°	332.4	315.9	299.4	282.9	274.6	259.5	229.2	198.9	168.6	138.3	168.6
120°	382.5	383.9	385.3	386.7	387.4	379.6	364.0	348.4	332.8	317.2	332.8
122.5°	412.5	413.2	413.9	414.6	414.9	415.0	415.1	415.2	415.4	415.5	415.4
125°	440.2	441.0	441.8	442.6	443.0	443.2	443.5	443.9	444.2	444.6	444.2
127.5°	466.1	467.2	468.4	469.5	470.1	470.2	470.3	470.4	470.5	470.6	470.5
130°	490.6	491.8	493.1	494.4	495.0	494.9	494.8	494.7	494.6	494.5	494.6
132.5°	514.7	515.8	516.8	517.9	518.4	518.3	518.2	518.1	518.0	517.9	518.0
135°	537.3	538.4	539.6	540.7	541.3	541.2	541.0	540.7	540.5	540.3	540.5
137.5°	558.6	559.7	560.9	562.0	562.6	562.4	562.1	561.8	561.4	561.1	561.4
140°	579.2	580.3	581.3	582.4	582.9	582.6	582.0	581.5	580.9	580.3	580.9
142.5°	598.4	599.3	600.2	601.1	601.6	601.3	600.7	600.2	599.6	599.0	599.6
145°	615.9	616.7	617.6	618.4	618.8	618.5	617.9	617.4	616.8	616.2	616.8
147.5°	631.9	632.5	633.0	633.6	633.9	633.7	633.2	632.7	632.3	631.8	632.3
150°	646.0	646.7	647.4	648.1	648.4	648.1	647.5	647.0	646.4	645.8	646.4
152.5°	659.0	659.7	660.4	661.1	661.4	661.0	660.2	659.4	658.6	657.8	658.6
155°	670.4	671.1	671.8	672.5	672.9	672.4	671.5	670.6	669.6	668.7	669.6
157.5°	680.4	681.2	682.1	682.9	683.3	682.8	681.9	681.0	680.0	679.1	680.0
160°	689.2	689.9	690.6	691.3	691.6	691.2	690.4	689.5	688.7	687.9	688.7
162.5°	697.1	697.9	698.7	699.5	699.9	699.4	698.3	697.3	696.2	695.2	696.2
165°	703.3	704.1	704.9	705.7	706.1	705.7	704.9	704.1	703.3	702.5	703.3
167.5°	709.0	709.8	710.7	711.5	711.9	711.4	710.3	709.3	708.2	707.2	708.2
170°	713.2	714.0	714.8	715.6	716.0	715.5	714.4	713.4	712.3	711.3	712.3
172.5°	716.3	717.1	717.9	718.7	719.1	718.6	717.6	716.5	715.5	714.5	715.5
175°	718.4	719.2	720.0	720.8	721.2	720.6	719.5	718.3	717.2	716.0	717.2
177.5°	718.9	719.7	720.5	721.3	721.7	721.2	720.2	719.1	718.1	717.1	718.1
180°	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6

TEST NUMBER: P998240

CATALOG NUMBER: SA2XXDIP-B290D530UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	606.3	603.2	600.6	601.0	603.2	601.5	597.1	591.3	589.1	586.5	589.1
5°	642.8	640.1	634.9	635.3	634.0	632.2	625.2	616.4	616.4	609.4	608.5
7.5°	678.8	674.9	671.4	670.5	665.6	662.1	656.0	643.7	638.8	630.5	625.6
10°	719.3	716.2	712.2	707.4	704.8	698.6	688.5	670.5	661.7	650.3	641.9
12.5°	760.2	759.7	750.9	741.3	740.8	731.2	724.1	699.9	688.1	672.7	652.9
15°	786.1	783.9	779.1	774.2	775.6	765.0	749.2	720.6	712.7	694.2	673.1
17.5°	785.7	785.7	784.4	783.5	782.2	779.1	770.3	751.4	738.6	715.3	695.5
20°	760.6	766.3	767.6	767.2	771.6	773.8	773.4	761.5	751.4	730.7	710.5
22.5°	710.5	723.7	729.4	732.9	742.1	747.0	758.4	754.0	751.4	736.0	718.8
25°	663.9	668.3	685.4	686.3	699.1	710.9	722.4	729.8	739.5	733.8	719.3
27.5°	603.7	613.8	626.1	635.3	637.9	662.1	681.0	695.1	717.1	718.8	714.0
30°	535.5	540.3	560.6	572.9	586.9	604.5	631.8	656.0	675.8	693.8	699.9
32.5°	452.4	472.2	484.1	499.0	511.3	542.5	576.0	607.2	630.0	660.4	673.6
35°	376.3	391.7	412.0	418.1	440.5	466.9	510.4	550.5	585.2	616.0	642.8
37.5°	313.5	325.8	347.3	357.0	370.2	404.0	440.5	490.2	532.0	569.8	603.2
40°	270.4	279.6	295.9	299.0	310.0	340.7	370.2	416.8	472.2	523.2	559.7
42.5°	240.9	245.3	256.3	260.3	267.3	288.0	314.4	358.3	409.8	462.5	514.0
45°	219.8	222.9	229.5	233.0	241.8	251.0	272.6	307.8	348.2	401.4	456.8
47.5°	200.9	204.9	207.5	209.7	214.6	224.7	238.7	264.7	303.4	352.2	405.8
50°	185.1	186.4	191.3	191.7	194.8	201.4	214.6	230.4	261.2	300.7	352.6
52.5°	169.3	170.6	173.7	176.7	178.1	183.3	192.1	205.3	228.2	259.4	305.6
55°	153.4	155.2	158.3	160.5	161.8	166.2	171.5	184.2	202.2	224.2	262.0
57.5°	137.6	141.6	142.4	143.8	146.0	150.8	155.6	163.1	177.2	197.4	225.1
60°	122.7	124.0	127.1	128.4	130.6	133.2	139.4	145.1	155.2	171.0	196.1
62.5°	107.3	110.4	111.7	113.0	114.8	117.8	121.8	127.9	136.7	149.5	169.3
65°	94.1	94.5	97.2	98.9	100.7	102.9	106.8	112.6	117.8	129.7	144.2
67.5°	81.3	82.2	83.1	84.9	87.1	89.3	92.8	95.8	102.4	110.4	121.8
70°	69.0	69.0	71.2	72.5	72.1	74.7	77.4	80.9	85.7	93.2	102.4
72.5°	58.0	57.6	59.4	59.8	60.7	62.4	64.2	67.7	70.3	76.1	83.1
75°	46.2	47.0	47.9	47.9	49.2	50.6	52.3	54.1	57.2	60.7	65.9
77.5°	36.5	36.5	37.4	37.8	39.1	38.7	40.4	42.2	44.4	47.5	51.4
80°	26.8	27.7	27.7	27.7	28.1	28.6	30.3	31.7	33.0	35.2	36.9
82.5°	18.9	18.9	19.8	19.8	19.8	20.7	20.7	21.1	22.0	23.3	24.6
85°	11.9	11.9	11.9	12.3	11.9	12.3	13.2	12.8	13.2	14.1	14.1
87.5°	5.7	5.7	5.7	5.7	5.7	6.2	5.7	6.2	6.6	6.6	6.6
90°	13.6	13.3	13.1	13.0	12.7	12.1	11.6	11.0	10.4	9.5	8.5
92.5°	13.8	13.7	13.6	13.5	13.4	13.2	12.9	12.7	12.5	12.1	11.8
95°	22.6	22.7	22.8	22.9	22.6	22.0	21.5	20.9	20.3	19.5	18.7
97.5°	28.4	28.3	28.2	28.1	27.9	27.6	27.2	26.9	26.5	24.7	22.8
100°	34.4	34.1	33.9	33.8	33.3	32.4	31.5	30.5	29.6	27.6	25.7
102.5°	37.3	36.9	36.6	36.4	35.8	34.5	33.2	32.0	30.7	51.7	72.7
105°	38.6	38.1	37.6	37.4	36.8	35.5	34.2	33.0	31.7	63.3	94.8
107.5°	39.7	39.2	38.7	38.5	37.9	36.6	35.3	34.1	32.8	71.7	110.7
110°	40.2	39.7	39.2	39.0	44.8	56.3	67.9	79.4	91.0	124.4	157.8

TEST NUMBER: P998240

CATALOG NUMBER: SA2XXDIP-B290D530UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	40.9	40.5	40.2	40.0	64.9	114.7	164.6	214.4	264.2	266.2	268.1
115°	59.3	67.6	75.9	80.1	106.8	160.3	213.8	267.3	320.8	317.9	315.0
117.5°	198.9	229.2	259.5	274.6	282.9	299.4	315.9	332.4	348.9	346.9	345.0
120°	348.4	364.0	379.6	387.4	386.7	385.3	383.9	382.5	381.1	379.0	377.0
122.5°	415.2	415.1	415.0	414.9	414.6	413.9	413.2	412.5	411.8	409.5	407.2
125°	443.9	443.5	443.2	443.0	442.6	441.8	441.0	440.2	439.4	437.2	435.0
127.5°	470.4	470.3	470.2	470.1	469.5	468.4	467.2	466.1	464.9	463.2	461.4
130°	494.7	494.8	494.9	495.0	494.4	493.1	491.8	490.6	489.3	488.0	486.8
132.5°	518.1	518.2	518.3	518.4	517.9	516.8	515.8	514.7	513.7	512.4	511.2
135°	540.7	541.0	541.2	541.3	540.7	539.6	538.4	537.3	536.1	535.1	534.0
137.5°	561.8	562.1	562.4	562.6	562.0	560.9	559.7	558.6	557.4	556.2	555.1
140°	581.5	582.0	582.6	582.9	582.4	581.3	580.3	579.2	578.2	576.9	575.7
142.5°	600.2	600.7	601.3	601.6	601.1	600.2	599.3	598.4	597.5	596.0	594.5
145°	617.4	617.9	618.5	618.8	618.4	617.6	616.7	615.9	615.1	613.1	611.2
147.5°	632.7	633.2	633.7	633.9	633.6	633.0	632.5	631.9	631.3	629.3	627.3
150°	647.0	647.5	648.1	648.4	648.1	647.4	646.7	646.0	645.3	643.5	641.6
152.5°	659.4	660.2	661.0	661.4	661.1	660.4	659.7	659.0	658.3	656.6	654.8
155°	670.6	671.5	672.4	672.9	672.5	671.8	671.1	670.4	669.7	668.3	666.9
157.5°	681.0	681.9	682.8	683.3	682.9	682.1	681.2	680.4	679.6	678.6	677.5
160°	689.5	690.4	691.2	691.6	691.3	690.6	689.9	689.2	688.5	687.8	687.1
162.5°	697.3	698.3	699.4	699.9	699.5	698.7	697.9	697.1	696.3	695.7	695.1
165°	704.1	704.9	705.7	706.1	705.7	704.9	704.1	703.3	702.5	702.1	701.8
167.5°	709.3	710.3	711.4	711.9	711.5	710.7	709.8	709.0	708.2	707.9	707.5
170°	713.4	714.4	715.5	716.0	715.6	714.8	714.0	713.2	712.4	712.2	711.9
172.5°	716.5	717.6	718.6	719.1	718.7	717.9	717.1	716.3	715.5	715.3	715.1
175°	718.3	719.5	720.6	721.2	720.8	720.0	719.2	718.4	717.6	717.4	717.1
177.5°	719.1	720.2	721.2	721.7	721.3	720.5	719.7	718.9	718.1	718.0	717.9
180°	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6

TEST NUMBER: P998240

CATALOG NUMBER: SA2XXDIP-B290D530UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	586.9	584.7	583.4	584.3	581.7	575.1	575.1	577.3	574.6	572.0	568.0
5°	603.2	598.8	596.2	595.7	589.6	579.0	576.8	574.6	568.9	562.8	556.2
7.5°	619.0	611.1	606.7	603.7	594.9	581.2	575.5	570.7	561.4	552.2	543.9
10°	632.2	620.8	615.5	610.7	599.3	582.1	572.9	564.1	552.2	540.3	529.8
12.5°	642.8	629.6	623.0	616.0	601.9	579.5	568.0	554.0	542.1	526.3	515.7
15°	660.4	633.1	627.0	620.4	605.9	575.1	561.0	545.2	528.9	507.8	496.4
17.5°	674.4	637.9	637.5	623.4	604.5	573.3	551.8	531.1	513.5	492.4	474.4
20°	682.8	645.4	638.4	623.9	600.1	561.4	539.0	516.2	497.3	471.8	453.7
22.5°	689.8	656.0	637.5	619.9	590.9	557.5	524.5	503.0	477.0	449.3	432.2
25°	692.5	658.2	638.8	618.6	584.3	546.1	508.7	485.4	456.4	431.3	408.0
27.5°	692.9	657.7	634.0	612.9	575.1	531.1	492.9	468.2	436.1	407.1	383.8
30°	688.5	652.9	631.4	608.5	566.3	517.5	473.5	446.3	412.0	382.9	358.8
32.5°	675.3	643.2	625.6	600.6	554.9	498.6	455.0	424.7	388.7	360.1	336.8
35°	653.3	631.4	612.0	588.7	539.9	481.0	436.6	401.0	364.5	337.2	315.2
37.5°	626.1	614.2	596.2	573.3	522.8	465.2	415.9	376.3	339.9	313.5	291.9
40°	589.1	592.2	574.6	554.0	502.5	443.6	389.1	351.3	317.0	292.4	271.3
42.5°	549.1	561.9	551.8	532.0	480.1	419.9	369.3	327.5	294.1	268.6	251.0
45°	506.0	528.0	521.9	507.4	456.8	394.8	341.2	300.7	271.3	246.6	231.3
47.5°	459.0	490.2	490.2	479.7	430.9	369.8	317.0	275.7	246.6	229.1	214.1
50°	411.1	446.3	452.0	444.9	401.8	341.2	287.5	250.2	225.1	208.0	197.0
52.5°	361.0	401.8	412.4	408.9	371.1	313.9	263.4	226.9	204.0	189.1	179.4
55°	313.0	360.5	372.0	373.3	338.1	284.0	236.5	204.4	182.5	172.3	164.0
57.5°	267.8	313.5	326.2	328.4	304.7	256.8	211.5	183.3	163.6	155.2	148.6
60°	229.1	267.3	284.0	288.9	268.2	225.1	188.2	160.9	146.0	138.1	131.9
62.5°	197.4	228.2	245.8	247.1	237.9	197.4	164.0	141.1	128.4	121.3	118.3
65°	166.6	194.3	204.9	210.2	202.7	171.0	141.6	122.7	112.6	106.4	103.3
67.5°	142.0	159.6	168.4	175.4	167.9	144.2	120.5	105.1	97.6	91.4	89.7
70°	116.5	131.0	137.6	144.6	138.1	120.0	102.9	88.8	82.2	77.4	75.2
72.5°	93.2	104.6	110.8	115.2	111.2	96.3	82.2	72.5	67.7	64.2	62.9
75°	73.9	81.8	85.3	88.4	86.6	75.2	66.4	58.5	54.1	51.0	50.1
77.5°	56.3	62.0	65.9	66.8	64.6	57.2	49.7	44.8	41.3	39.6	38.7
80°	40.0	43.5	45.7	47.0	44.8	41.8	36.5	33.0	29.9	27.7	27.3
82.5°	26.8	28.6	30.3	29.9	29.0	26.4	23.3	21.5	20.2	18.5	18.5
85°	15.4	15.8	16.7	17.1	16.7	14.9	13.2	12.3	11.4	10.1	10.1
87.5°	6.6	7.0	7.0	7.5	6.6	6.6	5.7	4.8	4.8	4.4	4.0
90°	7.6	6.7	6.2	5.6	4.3	3.0	1.8	0.5	1.8	3.0	4.3
92.5°	11.4	11.1	10.9	11.1	11.6	12.1	12.5	13.0	12.5	12.1	11.6
95°	17.8	17.0	16.6	18.5	22.3	26.2	30.0	33.8	30.0	26.2	22.3
97.5°	21.0	19.1	18.2	22.9	32.4	41.9	51.3	60.8	51.3	41.9	32.4
100°	23.7	21.8	20.8	28.7	44.5	60.4	76.2	92.0	76.2	60.4	44.5
102.5°	93.8	114.8	125.3	125.4	125.7	125.9	126.2	126.4	126.2	125.9	125.7
105°	126.4	157.9	173.7	172.0	168.5	165.0	161.6	158.1	161.6	165.0	168.5
107.5°	149.6	188.5	208.0	206.6	203.7	200.8	197.9	195.0	197.9	200.8	203.7
110°	191.2	224.6	241.3	240.1	237.7	235.2	232.8	230.4	232.8	235.2	237.7

TEST NUMBER: P998240

CATALOG NUMBER: SA2XXDIP-B290D530UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	270.1	272.0	273.0	272.0	269.9	267.8	265.7	263.6	265.7	267.8	269.9
115°	312.1	309.2	307.8	306.8	304.9	302.9	301.0	299.0	301.0	302.9	304.9
117.5°	343.0	341.1	340.1	338.9	336.6	334.3	332.0	329.7	332.0	334.3	336.6
120°	374.9	372.8	371.8	370.9	369.2	367.5	365.7	364.0	365.7	367.5	369.2
122.5°	404.9	402.6	401.4	400.5	398.6	396.8	394.9	393.1	394.9	396.8	398.6
125°	432.8	430.6	429.5	428.7	427.2	425.7	424.2	422.7	424.2	425.7	427.2
127.5°	459.7	458.0	457.1	456.3	454.7	453.0	451.4	449.8	451.4	453.0	454.7
130°	485.5	484.2	483.6	482.7	480.8	479.0	477.1	475.3	477.1	479.0	480.8
132.5°	509.9	508.6	508.0	507.3	505.8	504.3	502.8	501.3	502.8	504.3	505.8
135°	533.0	531.9	531.4	530.5	528.6	526.8	524.9	523.1	524.9	526.8	528.6
137.5°	553.9	552.8	552.2	551.5	550.1	548.8	547.4	546.0	547.4	548.8	550.1
140°	574.4	573.1	572.5	572.0	571.1	570.2	569.2	568.3	569.2	570.2	571.1
142.5°	593.0	591.5	590.7	590.3	589.5	588.7	587.9	587.1	587.9	588.7	589.5
145°	609.2	607.3	606.3	606.4	606.5	606.6	606.7	606.8	606.7	606.6	606.5
147.5°	625.4	623.4	622.4	622.6	622.9	623.3	623.6	624.0	623.6	623.3	622.9
150°	639.8	637.9	637.0	637.4	638.2	639.0	639.8	640.6	639.8	639.0	638.2
152.5°	653.1	651.4	650.5	651.0	651.9	652.8	653.8	654.7	653.8	652.8	651.9
155°	665.6	664.2	663.5	664.0	665.1	666.1	667.2	668.2	667.2	666.1	665.1
157.5°	676.5	675.4	674.9	675.4	676.3	677.2	678.2	679.1	678.2	677.2	676.3
160°	686.4	685.7	685.3	685.7	686.4	687.1	687.8	688.5	687.8	687.1	686.4
162.5°	694.6	694.0	693.7	694.0	694.7	695.4	696.1	696.8	696.1	695.4	694.7
165°	701.4	701.1	700.9	701.3	702.0	702.7	703.4	704.1	703.4	702.7	702.0
167.5°	707.2	706.9	706.7	707.0	707.7	708.4	709.1	709.8	709.1	708.4	707.7
170°	711.7	711.4	711.3	711.7	712.4	713.1	713.8	714.5	713.8	713.1	712.4
172.5°	714.8	714.6	714.5	714.8	715.5	716.2	716.9	717.6	716.9	716.2	715.5
175°	716.9	716.6	716.5	716.9	717.7	718.6	719.4	720.2	719.4	718.6	717.7
177.5°	717.8	717.7	717.6	718.0	718.8	719.6	720.4	721.2	720.4	719.6	718.8
180°	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6

TEST NUMBER: P998240

CATALOG NUMBER: SA2XXDIP-B290D530UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	565.8	568.0	567.6	563.2	558.4	554.4	546.9	547.8	545.2	545.6	548.3
5°	551.8	551.8	550.0	543.9	535.9	531.5	523.2	521.0	515.7	515.3	514.8
7.5°	536.8	534.6	532.4	523.6	514.0	506.9	495.5	492.9	487.6	484.1	482.3
10°	519.2	516.2	511.8	501.7	489.8	481.0	469.1	465.6	455.5	451.1	448.5
12.5°	499.9	498.1	491.1	482.7	463.4	453.7	436.6	440.1	430.0	421.2	419.9
15°	480.5	474.0	470.0	456.4	433.1	428.7	415.0	408.0	398.8	391.7	391.7
17.5°	461.6	451.5	442.7	428.2	411.1	398.8	388.7	385.1	373.7	366.7	365.4
20°	436.6	425.2	423.0	402.3	390.4	376.8	367.1	358.3	350.0	346.9	344.7
22.5°	412.8	399.7	396.1	378.5	366.7	353.0	343.4	337.2	331.1	328.9	324.9
25°	387.3	379.4	374.2	355.2	342.1	329.3	322.7	318.3	312.6	312.2	309.5
27.5°	362.7	355.2	350.0	331.9	322.3	310.4	305.1	300.3	297.2	295.9	294.6
30°	341.6	333.3	327.1	313.9	302.0	292.4	288.0	284.9	283.1	280.9	280.5
32.5°	318.3	313.5	305.1	295.0	285.8	276.5	273.9	271.7	269.1	268.2	267.8
35°	298.5	291.9	286.7	275.2	271.3	263.4	260.3	258.5	255.0	254.1	253.2
37.5°	279.2	273.0	267.3	260.3	252.8	248.4	246.6	244.0	242.3	242.7	241.8
40°	259.8	255.0	250.6	243.1	238.7	236.5	233.0	230.4	229.5	229.9	229.5
42.5°	240.9	236.5	233.9	228.2	223.8	221.6	219.4	216.8	218.1	218.1	219.4
45°	223.8	219.8	218.1	213.7	211.0	207.5	205.3	204.9	206.6	206.2	206.2
47.5°	206.2	204.9	202.7	198.7	195.2	193.0	192.6	192.6	194.3	195.2	194.8
50°	192.6	189.9	187.3	184.2	181.6	180.7	179.4	180.3	182.0	182.0	182.9
52.5°	175.4	173.7	172.8	170.1	168.4	168.4	168.4	168.8	170.1	171.5	171.0
55°	160.5	159.2	158.3	157.0	154.8	155.2	154.8	155.6	157.0	158.3	159.2
57.5°	144.6	144.2	143.3	141.1	141.1	140.7	142.0	142.4	144.6	145.5	146.8
60°	130.6	129.3	129.3	127.5	127.5	127.5	128.8	130.1	131.9	132.3	133.2
62.5°	115.6	115.6	115.2	113.9	113.9	115.2	115.6	117.4	118.3	118.3	119.6
65°	101.6	101.1	100.7	101.1	101.6	101.6	102.9	103.8	104.6	105.1	105.5
67.5°	87.5	87.1	87.9	87.5	88.4	90.1	89.7	91.0	92.3	92.3	92.8
70°	74.3	75.2	74.7	75.6	75.2	76.1	77.4	77.8	77.8	78.3	79.6
72.5°	62.0	62.0	62.0	61.6	62.0	62.9	63.8	64.2	65.1	65.5	66.8
75°	50.1	50.1	49.2	50.1	50.1	51.0	51.9	51.9	51.9	52.8	54.1
77.5°	37.8	38.3	37.8	38.7	38.7	39.1	40.0	39.6	40.4	40.9	41.3
80°	27.7	27.3	27.3	27.3	27.7	27.7	28.6	29.0	29.0	30.3	29.5
82.5°	17.6	18.0	17.6	18.0	18.0	18.5	18.0	18.5	18.9	19.8	19.3
85°	10.1	9.7	9.7	10.1	9.7	9.7	10.1	9.7	10.1	9.7	10.1
87.5°	4.0	3.5	3.5	3.5	3.5	3.1	3.1	2.6	2.6	2.6	2.2
90°	5.6	6.2	6.7	7.6	8.5	9.5	10.4	11.0	11.6	12.1	12.7
92.5°	11.1	10.9	11.1	11.4	11.8	12.1	12.5	12.7	12.9	13.2	13.4
95°	18.5	16.6	17.0	17.8	18.7	19.5	20.3	20.9	21.5	22.0	22.6
97.5°	22.9	18.2	19.1	21.0	22.8	24.7	26.5	26.9	27.2	27.6	27.9
100°	28.7	20.8	21.8	23.7	25.7	27.6	29.6	30.5	31.5	32.4	33.3
102.5°	125.4	125.3	114.8	93.8	72.7	51.7	30.7	32.0	33.2	34.5	35.8
105°	172.0	173.7	157.9	126.4	94.8	63.3	31.7	33.0	34.2	35.5	36.8
107.5°	206.6	208.0	188.5	149.6	110.7	71.7	32.8	34.1	35.3	36.6	37.9
110°	240.1	241.3	224.6	191.2	157.8	124.4	91.0	79.4	67.9	56.3	44.8

TEST NUMBER: P998240

CATALOG NUMBER: SA2XXDIP-B290D530UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	272.0	273.0	272.0	270.1	268.1	266.2	264.2	214.4	164.6	114.7	64.9
115°	306.8	307.8	309.2	312.1	315.0	317.9	320.8	267.3	213.8	160.3	106.8
117.5°	338.9	340.1	341.1	343.0	345.0	346.9	348.9	332.4	315.9	299.4	282.9
120°	370.9	371.8	372.8	374.9	377.0	379.0	381.1	382.5	383.9	385.3	386.7
122.5°	400.5	401.4	402.6	404.9	407.2	409.5	411.8	412.5	413.2	413.9	414.6
125°	428.7	429.5	430.6	432.8	435.0	437.2	439.4	440.2	441.0	441.8	442.6
127.5°	456.3	457.1	458.0	459.7	461.4	463.2	464.9	466.1	467.2	468.4	469.5
130°	482.7	483.6	484.2	485.5	486.8	488.0	489.3	490.6	491.8	493.1	494.4
132.5°	507.3	508.0	508.6	509.9	511.2	512.4	513.7	514.7	515.8	516.8	517.9
135°	530.5	531.4	531.9	533.0	534.0	535.1	536.1	537.3	538.4	539.6	540.7
137.5°	551.5	552.2	552.8	553.9	555.1	556.2	557.4	558.6	559.7	560.9	562.0
140°	572.0	572.5	573.1	574.4	575.7	576.9	578.2	579.2	580.3	581.3	582.4
142.5°	590.3	590.7	591.5	593.0	594.5	596.0	597.5	598.4	599.3	600.2	601.1
145°	606.4	606.3	607.3	609.2	611.2	613.1	615.1	615.9	616.7	617.6	618.4
147.5°	622.6	622.4	623.4	625.4	627.3	629.3	631.3	631.9	632.5	633.0	633.6
150°	637.4	637.0	637.9	639.8	641.6	643.5	645.3	646.0	646.7	647.4	648.1
152.5°	651.0	650.5	651.4	653.1	654.8	656.6	658.3	659.0	659.7	660.4	661.1
155°	664.0	663.5	664.2	665.6	666.9	668.3	669.7	670.4	671.1	671.8	672.5
157.5°	675.4	674.9	675.4	676.5	677.5	678.6	679.6	680.4	681.2	682.1	682.9
160°	685.7	685.3	685.7	686.4	687.1	687.8	688.5	689.2	689.9	690.6	691.3
162.5°	694.0	693.7	694.0	694.6	695.1	695.7	696.3	697.1	697.9	698.7	699.5
165°	701.3	700.9	701.1	701.4	701.8	702.1	702.5	703.3	704.1	704.9	705.7
167.5°	707.0	706.7	706.9	707.2	707.5	707.9	708.2	709.0	709.8	710.7	711.5
170°	711.7	711.3	711.4	711.7	711.9	712.2	712.4	713.2	714.0	714.8	715.6
172.5°	714.8	714.5	714.6	714.8	715.1	715.3	715.5	716.3	717.1	717.9	718.7
175°	716.9	716.5	716.6	716.9	717.1	717.4	717.6	718.4	719.2	720.0	720.8
177.5°	718.0	717.6	717.7	717.8	717.9	718.0	718.1	718.9	719.7	720.5	721.3
180°	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6

TEST NUMBER: P998240

CATALOG NUMBER: SA2XXDIP-B290D530UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	545.2	546.5	543.4	542.5	543.4	540.3	541.2	542.1	542.1	543.4	544.3
5°	513.5	511.8	508.7	507.8	506.9	508.2	507.4	508.7	509.1	512.2	512.6
7.5°	482.3	479.7	477.0	474.4	473.5	471.3	473.5	473.5	476.6	475.7	477.9
10°	445.4	444.9	441.4	440.1	438.3	434.8	439.7	438.3	440.5	444.5	445.4
12.5°	418.1	413.3	415.5	409.3	411.5	408.0	408.4	408.4	412.0	412.4	411.5
15°	392.2	388.2	382.5	379.9	378.5	376.8	382.5	382.9	380.3	386.5	384.3
17.5°	365.8	365.8	360.5	359.2	355.7	357.4	356.6	357.0	356.1	360.5	362.7
20°	342.9	340.7	339.0	339.4	335.0	334.1	333.3	334.1	337.2	340.3	341.2
22.5°	324.5	323.1	318.8	319.6	316.1	317.4	316.6	318.8	319.2	319.2	322.3
25°	306.9	305.1	305.6	303.8	302.5	302.5	301.2	302.5	304.2	305.1	305.6
27.5°	293.7	292.4	290.2	288.9	289.7	287.5	289.3	290.6	290.6	289.7	290.6
30°	277.9	278.7	278.7	274.3	276.1	275.2	276.5	277.4	277.4	277.9	277.0
32.5°	267.3	264.7	264.2	263.8	263.8	262.0	262.0	263.4	263.8	264.2	265.6
35°	253.2	253.2	251.0	252.4	250.6	251.0	250.6	251.0	251.9	250.6	251.9
37.5°	240.5	240.9	240.1	240.9	241.4	240.5	239.6	241.4	240.5	240.5	239.6
40°	229.5	229.1	229.5	229.5	229.5	229.9	229.1	229.1	229.1	228.2	227.3
42.5°	220.3	217.6	218.5	219.0	217.6	217.6	218.1	217.6	219.0	216.3	216.3
45°	207.1	206.2	206.6	206.6	207.5	206.2	207.1	207.5	206.2	205.8	204.9
47.5°	195.2	196.1	195.2	196.1	196.1	197.0	195.2	195.6	196.1	194.3	193.0
50°	183.3	183.3	184.7	184.2	184.7	183.8	183.8	183.3	183.8	182.9	181.6
52.5°	172.3	171.0	173.2	172.8	172.3	171.9	171.5	171.9	171.0	170.1	170.1
55°	158.7	158.7	160.0	160.5	160.5	159.6	158.7	159.2	158.7	158.3	157.8
57.5°	147.7	146.0	146.8	147.3	147.3	146.0	146.8	146.0	146.0	146.4	145.1
60°	133.7	133.7	132.8	134.1	134.1	133.2	133.2	133.7	132.8	132.3	131.9
62.5°	118.7	119.1	120.5	120.9	121.3	120.5	119.6	120.0	120.0	118.7	119.1
65°	106.0	106.8	108.6	108.2	107.3	107.7	106.8	107.3	106.0	106.4	105.1
67.5°	93.6	93.2	93.6	93.6	94.5	94.1	93.2	93.2	92.8	94.1	92.8
70°	80.5	80.5	80.5	80.5	80.9	81.3	80.5	79.6	80.0	79.1	78.7
72.5°	66.8	67.3	66.8	67.7	66.4	67.3	67.3	66.8	66.4	66.4	66.4
75°	54.1	55.0	53.6	54.1	53.6	54.5	54.1	54.1	53.2	52.8	53.2
77.5°	41.3	41.8	40.9	41.3	40.9	41.3	41.3	40.9	40.9	40.9	40.9
80°	29.5	29.9	29.5	29.0	28.6	29.5	28.6	29.0	29.5	29.0	29.9
82.5°	18.9	18.9	18.5	18.9	18.0	18.0	18.5	18.5	18.0	18.9	18.0
85°	9.2	9.2	10.1	9.2	8.8	8.8	8.8	9.2	8.8	9.7	9.2
87.5°	2.2	1.8	2.2	2.2	1.8	1.8	2.2	1.8	2.2	2.6	1.8
90°	13.0	13.1	13.3	13.6	13.8	14.0	13.8	13.6	13.3	13.1	13.0
92.5°	13.5	13.6	13.7	13.8	13.9	14.0	13.9	13.8	13.7	13.6	13.5
95°	22.9	22.8	22.7	22.6	22.5	22.4	22.5	22.6	22.7	22.8	22.9
97.5°	28.1	28.2	28.3	28.4	28.5	28.6	28.5	28.4	28.3	28.2	28.1
100°	33.8	33.9	34.1	34.4	34.6	34.8	34.6	34.4	34.1	33.9	33.8
102.5°	36.4	36.6	36.9	37.3	37.6	38.0	37.6	37.3	36.9	36.6	36.4
105°	37.4	37.6	38.1	38.6	39.0	39.5	39.0	38.6	38.1	37.6	37.4
107.5°	38.5	38.7	39.2	39.7	40.1	40.6	40.1	39.7	39.2	38.7	38.5
110°	39.0	39.2	39.7	40.2	40.6	41.1	40.6	40.2	39.7	39.2	39.0

TEST NUMBER: P998240

CATALOG NUMBER: SA2XXDIP-B290D530UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	40.0	40.2	40.5	40.9	41.2	41.6	41.2	40.9	40.5	40.2	40.0
115°	80.1	75.9	67.6	59.3	50.9	42.6	50.9	59.3	67.6	75.9	80.1
117.5°	274.6	259.5	229.2	198.9	168.6	138.3	168.6	198.9	229.2	259.5	274.6
120°	387.4	379.6	364.0	348.4	332.8	317.2	332.8	348.4	364.0	379.6	387.4
122.5°	414.9	415.0	415.1	415.2	415.4	415.5	415.4	415.2	415.1	415.0	414.9
125°	443.0	443.2	443.5	443.9	444.2	444.6	444.2	443.9	443.5	443.2	443.0
127.5°	470.1	470.2	470.3	470.4	470.5	470.6	470.5	470.4	470.3	470.2	470.1
130°	495.0	494.9	494.8	494.7	494.6	494.5	494.6	494.7	494.8	494.9	495.0
132.5°	518.4	518.3	518.2	518.1	518.0	517.9	518.0	518.1	518.2	518.3	518.4
135°	541.3	541.2	541.0	540.7	540.5	540.3	540.5	540.7	541.0	541.2	541.3
137.5°	562.6	562.4	562.1	561.8	561.4	561.1	561.4	561.8	562.1	562.4	562.6
140°	582.9	582.6	582.0	581.5	580.9	580.3	580.9	581.5	582.0	582.6	582.9
142.5°	601.6	601.3	600.7	600.2	599.6	599.0	599.6	600.2	600.7	601.3	601.6
145°	618.8	618.5	617.9	617.4	616.8	616.2	616.8	617.4	617.9	618.5	618.8
147.5°	633.9	633.7	633.2	632.7	632.3	631.8	632.3	632.7	633.2	633.7	633.9
150°	648.4	648.1	647.5	647.0	646.4	645.8	646.4	647.0	647.5	648.1	648.4
152.5°	661.4	661.0	660.2	659.4	658.6	657.8	658.6	659.4	660.2	661.0	661.4
155°	672.9	672.4	671.5	670.6	669.6	668.7	669.6	670.6	671.5	672.4	672.9
157.5°	683.3	682.8	681.9	681.0	680.0	679.1	680.0	681.0	681.9	682.8	683.3
160°	691.6	691.2	690.4	689.5	688.7	687.9	688.7	689.5	690.4	691.2	691.6
162.5°	699.9	699.4	698.3	697.3	696.2	695.2	696.2	697.3	698.3	699.4	699.9
165°	706.1	705.7	704.9	704.1	703.3	702.5	703.3	704.1	704.9	705.7	706.1
167.5°	711.9	711.4	710.3	709.3	708.2	707.2	708.2	709.3	710.3	711.4	711.9
170°	716.0	715.5	714.4	713.4	712.3	711.3	712.3	713.4	714.4	715.5	716.0
172.5°	719.1	718.6	717.6	716.5	715.5	714.5	715.5	716.5	717.6	718.6	719.1
175°	721.2	720.6	719.5	718.3	717.2	716.0	717.2	718.3	719.5	720.6	721.2
177.5°	721.7	721.2	720.2	719.1	718.1	717.1	718.1	719.1	720.2	721.2	721.7
180°	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6

TEST NUMBER: P998240

CATALOG NUMBER: SA2XXDIP-B290D530UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	543.0	546.5	545.2	540.3	546.1	546.1	550.0	550.0	554.9	556.6	559.2
5°	512.2	514.8	517.0	514.8	518.8	525.0	528.5	531.5	538.1	540.8	544.7
7.5°	479.2	484.1	486.3	486.3	492.9	499.9	506.9	511.3	520.6	524.1	528.0
10°	447.1	452.8	457.2	456.8	467.8	472.2	481.0	491.1	500.3	505.6	511.3
12.5°	413.3	416.4	422.5	431.3	433.9	441.9	452.0	464.7	481.4	486.3	494.6
15°	385.1	393.5	398.3	402.3	408.4	415.9	426.9	439.2	455.9	466.5	475.3
17.5°	361.4	372.4	375.5	374.6	382.5	393.9	406.7	415.9	430.9	443.6	452.0
20°	342.1	346.5	351.7	353.9	360.1	372.4	384.7	395.3	407.6	417.7	427.3
22.5°	322.7	326.2	330.6	334.6	339.4	346.5	358.3	371.5	383.4	393.1	404.0
25°	306.9	309.1	313.0	316.1	321.4	326.2	334.6	349.1	363.2	368.9	378.5
27.5°	291.5	293.3	295.9	299.4	302.0	306.9	314.4	326.2	340.7	346.5	359.6
30°	277.9	279.2	281.8	283.6	284.9	290.6	296.3	305.6	316.6	324.5	334.1
32.5°	265.1	266.4	269.1	269.5	271.3	274.3	279.6	288.0	297.6	304.2	312.6
35°	251.0	251.9	254.6	255.4	256.8	259.4	263.4	269.5	278.3	283.1	290.6
37.5°	240.1	239.6	241.4	242.7	244.5	245.8	247.1	253.2	259.8	264.2	270.0
40°	228.2	227.3	227.7	229.5	230.4	232.1	232.1	238.3	242.7	246.2	250.6
42.5°	216.3	215.9	215.0	215.9	216.8	217.2	217.6	222.0	226.4	229.5	234.3
45°	204.4	204.0	203.1	203.6	203.6	204.4	205.8	207.5	210.6	213.2	215.9
47.5°	193.5	192.6	191.3	190.8	191.7	191.7	191.7	193.5	196.5	197.4	200.0
50°	182.0	180.7	178.9	178.1	178.1	177.6	178.5	178.9	181.6	182.5	184.7
52.5°	169.7	168.8	167.1	165.3	165.8	164.9	165.3	165.8	166.6	167.9	169.3
55°	157.4	155.6	154.3	153.9	152.6	152.6	151.2	153.0	152.6	153.0	154.8
57.5°	145.5	143.8	141.6	140.7	139.4	138.9	138.1	137.6	138.1	139.4	140.7
60°	131.5	130.6	129.3	127.9	127.1	125.7	124.9	124.9	124.4	124.4	124.9
62.5°	117.8	117.4	115.6	115.2	114.3	113.4	112.1	111.2	111.2	112.1	112.6
65°	104.6	104.2	102.9	102.4	100.2	99.4	98.9	98.5	97.6	97.6	97.6
67.5°	92.3	91.0	91.0	88.8	87.1	86.2	85.3	84.9	84.9	84.9	85.3
70°	78.7	78.7	77.4	76.1	74.3	74.7	73.4	72.1	72.1	71.2	71.7
72.5°	65.5	65.1	63.8	63.3	62.0	60.7	59.8	60.7	59.4	58.9	59.4
75°	52.8	52.3	51.4	50.6	51.0	49.7	48.4	47.9	47.9	47.0	47.0
77.5°	40.4	41.3	39.6	39.1	38.3	37.4	36.9	36.5	36.5	36.5	37.4
80°	28.1	28.6	28.6	27.7	28.1	26.8	26.8	26.8	25.5	25.9	26.4
82.5°	18.0	18.0	17.6	18.0	17.6	17.6	17.1	17.1	16.7	16.7	17.1
85°	10.1	9.7	9.2	10.1	9.7	9.7	9.2	9.2	9.2	9.2	9.2
87.5°	2.2	2.6	2.6	2.6	2.6	3.1	3.1	3.1	3.5	3.5	3.5
90°	12.7	12.1	11.6	11.0	10.4	9.5	8.5	7.6	6.7	6.2	5.6
92.5°	13.4	13.2	12.9	12.7	12.5	12.1	11.8	11.4	11.1	10.9	11.1
95°	22.6	22.0	21.5	20.9	20.3	19.5	18.7	17.8	17.0	16.6	18.5
97.5°	27.9	27.6	27.2	26.9	26.5	24.7	22.8	21.0	19.1	18.2	22.9
100°	33.3	32.4	31.5	30.5	29.6	27.6	25.7	23.7	21.8	20.8	28.7
102.5°	35.8	34.5	33.2	32.0	30.7	51.7	72.7	93.8	114.8	125.3	125.4
105°	36.8	35.5	34.2	33.0	31.7	63.3	94.8	126.4	157.9	173.7	172.0
107.5°	37.9	36.6	35.3	34.1	32.8	71.7	110.7	149.6	188.5	208.0	206.6
110°	44.8	56.3	67.9	79.4	91.0	124.4	157.8	191.2	224.6	241.3	240.1

TEST NUMBER: P998240

CATALOG NUMBER: SA2XXDIP-B290D530UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	64.9	114.7	164.6	214.4	264.2	266.2	268.1	270.1	272.0	273.0	272.0
115°	106.8	160.3	213.8	267.3	320.8	317.9	315.0	312.1	309.2	307.8	306.8
117.5°	282.9	299.4	315.9	332.4	348.9	346.9	345.0	343.0	341.1	340.1	338.9
120°	386.7	385.3	383.9	382.5	381.1	379.0	377.0	374.9	372.8	371.8	370.9
122.5°	414.6	413.9	413.2	412.5	411.8	409.5	407.2	404.9	402.6	401.4	400.5
125°	442.6	441.8	441.0	440.2	439.4	437.2	435.0	432.8	430.6	429.5	428.7
127.5°	469.5	468.4	467.2	466.1	464.9	463.2	461.4	459.7	458.0	457.1	456.3
130°	494.4	493.1	491.8	490.6	489.3	488.0	486.8	485.5	484.2	483.6	482.7
132.5°	517.9	516.8	515.8	514.7	513.7	512.4	511.2	509.9	508.6	508.0	507.3
135°	540.7	539.6	538.4	537.3	536.1	535.1	534.0	533.0	531.9	531.4	530.5
137.5°	562.0	560.9	559.7	558.6	557.4	556.2	555.1	553.9	552.8	552.2	551.5
140°	582.4	581.3	580.3	579.2	578.2	576.9	575.7	574.4	573.1	572.5	572.0
142.5°	601.1	600.2	599.3	598.4	597.5	596.0	594.5	593.0	591.5	590.7	590.3
145°	618.4	617.6	616.7	615.9	615.1	613.1	611.2	609.2	607.3	606.3	606.4
147.5°	633.6	633.0	632.5	631.9	631.3	629.3	627.3	625.4	623.4	622.4	622.6
150°	648.1	647.4	646.7	646.0	645.3	643.5	641.6	639.8	637.9	637.0	637.4
152.5°	661.1	660.4	659.7	659.0	658.3	656.6	654.8	653.1	651.4	650.5	651.0
155°	672.5	671.8	671.1	670.4	669.7	668.3	666.9	665.6	664.2	663.5	664.0
157.5°	682.9	682.1	681.2	680.4	679.6	678.6	677.5	676.5	675.4	674.9	675.4
160°	691.3	690.6	689.9	689.2	688.5	687.8	687.1	686.4	685.7	685.3	685.7
162.5°	699.5	698.7	697.9	697.1	696.3	695.7	695.1	694.6	694.0	693.7	694.0
165°	705.7	704.9	704.1	703.3	702.5	702.1	701.8	701.4	701.1	700.9	701.3
167.5°	711.5	710.7	709.8	709.0	708.2	707.9	707.5	707.2	706.9	706.7	707.0
170°	715.6	714.8	714.0	713.2	712.4	712.2	711.9	711.7	711.4	711.3	711.7
172.5°	718.7	717.9	717.1	716.3	715.5	715.3	715.1	714.8	714.6	714.5	714.8
175°	720.8	720.0	719.2	718.4	717.6	717.4	717.1	716.9	716.6	716.5	716.9
177.5°	721.3	720.5	719.7	718.9	718.1	718.0	717.9	717.8	717.7	717.6	718.0
180°	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6

TEST NUMBER: P998240

CATALOG NUMBER: SA2XXDIP-B290D530UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	572.0	572.0	572.0	572.0
2.5°	561.4	561.4	568.0	575.1
5°	549.1	552.2	562.8	572.4
7.5°	537.3	542.5	555.7	568.0
10°	522.8	529.8	546.1	560.6
12.5°	508.7	515.3	534.2	550.5
15°	488.9	497.3	517.5	537.7
17.5°	469.1	477.5	502.1	525.8
20°	445.8	456.8	484.5	516.2
22.5°	424.3	437.9	468.7	494.2
25°	400.5	421.6	450.2	483.2
27.5°	379.4	400.5	429.5	463.0
30°	355.7	377.2	407.1	437.9
32.5°	332.8	352.6	381.6	419.4
35°	309.1	328.0	356.1	394.4
37.5°	287.5	306.0	336.8	372.0
40°	266.4	285.8	312.2	347.3
42.5°	246.6	263.8	287.5	322.7
45°	228.6	240.9	262.9	295.9
47.5°	209.7	220.7	240.9	273.9
50°	192.1	201.4	219.0	249.7
52.5°	175.0	182.9	199.2	223.8
55°	159.6	167.1	178.9	203.1
57.5°	143.8	149.5	160.9	180.3
60°	128.4	133.7	142.9	158.7
62.5°	113.0	117.4	126.2	138.9
65°	99.4	102.9	109.5	120.5
67.5°	86.2	88.4	93.6	102.4
70°	73.4	75.2	79.6	86.6
72.5°	59.8	61.6	66.4	71.2
75°	48.4	48.8	52.3	56.3
77.5°	37.8	37.4	40.0	43.1
80°	25.9	27.3	29.5	30.8
82.5°	17.6	18.0	18.9	19.8
85°	9.7	10.1	10.1	11.4
87.5°	4.0	4.4	4.4	4.8
90°	4.3	3.0	1.8	0.5
92.5°	11.6	12.1	12.5	13.0
95°	22.3	26.2	30.0	33.8
97.5°	32.4	41.9	51.3	60.8
100°	44.5	60.4	76.2	92.0
102.5°	125.7	125.9	126.2	126.4
105°	168.5	165.0	161.6	158.1
107.5°	203.7	200.8	197.9	195.0
110°	237.7	235.2	232.8	230.4



TEST NUMBER: P998240

CATALOG NUMBER: SA2XXDIP-B290D530UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	269.9	267.8	265.7	263.6
115°	304.9	302.9	301.0	299.0
117.5°	336.6	334.3	332.0	329.7
120°	369.2	367.5	365.7	364.0
122.5°	398.6	396.8	394.9	393.1
125°	427.2	425.7	424.2	422.7
127.5°	454.7	453.0	451.4	449.8
130°	480.8	479.0	477.1	475.3
132.5°	505.8	504.3	502.8	501.3
135°	528.6	526.8	524.9	523.1
137.5°	550.1	548.8	547.4	546.0
140°	571.1	570.2	569.2	568.3
142.5°	589.5	588.7	587.9	587.1
145°	606.5	606.6	606.7	606.8
147.5°	622.9	623.3	623.6	624.0
150°	638.2	639.0	639.8	640.6
152.5°	651.9	652.8	653.8	654.7
155°	665.1	666.1	667.2	668.2
157.5°	676.3	677.2	678.2	679.1
160°	686.4	687.1	687.8	688.5
162.5°	694.7	695.4	696.1	696.8
165°	702.0	702.7	703.4	704.1
167.5°	707.7	708.4	709.1	709.8
170°	712.4	713.1	713.8	714.5
172.5°	715.5	716.2	716.9	717.6
175°	717.7	718.6	719.4	720.2
177.5°	718.8	719.6	720.4	721.2
180°	718.6	718.6	718.6	718.6

TEST NUMBER: P998240

CATALOG NUMBER: SA2XXDIP-B290D530UB40-4F0-XX-W2A-A

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.20	12.94	13.27	14.00	15.44	9.70	10.43	10.76	11.50	12.94
	3H	13.01	13.67	14.08	14.74	16.20	11.03	11.69	12.11	12.76	14.22
	4H	13.17	13.79	14.25	14.87	16.33	11.49	12.11	12.57	13.19	14.65
	6H	13.21	13.78	14.30	14.86	16.34	11.79	12.36	12.88	13.44	14.92
	8H	13.18	13.73	14.28	14.82	16.29	11.87	12.42	12.97	13.51	14.98
	12H	13.14	13.66	14.24	14.75	16.24	11.91	12.43	13.01	13.51	15.01
4H	2H	12.23	12.85	13.32	13.93	15.39	10.13	10.75	11.22	11.83	13.29
	3H	13.20	13.72	14.30	14.82	16.30	11.58	12.10	12.68	13.20	14.68
	4H	13.47	13.95	14.57	15.04	16.54	12.11	12.58	13.21	13.67	15.17
	6H	13.60	14.00	14.71	15.12	16.61	12.48	12.89	13.59	14.00	15.50
	8H	13.59	13.97	14.70	15.08	16.59	12.59	12.97	13.70	14.07	15.58
	12H	13.55	13.89	14.68	15.01	16.53	12.64	12.98	13.77	14.10	15.62
8H	4H	13.47	13.85	14.58	14.96	16.47	12.24	12.62	13.35	13.73	15.24
	6H	13.65	13.96	14.78	15.11	16.61	12.67	12.99	13.80	14.13	15.64
	8H	13.68	13.95	14.81	15.08	16.60	12.82	13.10	13.96	14.22	15.75
	12H	13.66	13.90	14.80	15.02	16.58	12.91	13.15	14.05	14.27	15.84
12H	4H	13.42	13.77	14.55	14.89	16.40	12.21	12.55	13.34	13.67	15.19
	6H	13.62	13.90	14.76	15.03	16.55	12.67	12.95	13.81	14.07	15.60
	8H	13.65	13.89	14.79	15.02	16.58	12.82	13.06	13.96	14.19	15.75